

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331732-935

Luminaire Tested: **SA2XXRDIP-C865D1080U935-4F0-1E-UDD-F**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331732-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXRDIP-C865D1080U935-4F0-1E-UDD-F  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1080 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6306.6 lumens  
Efficiency: N/A  
Efficacy: 96.4 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 65.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331732-935  
CATALOG NUMBER: SA2XXRDIP-C865D1080U935-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P331732-935

CATALOG NUMBER: SA2XXRDIP-C865D1080U935-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	105	105	105	105	96	96	96	96	78	78	78	63	63	63	48	48	48	41				
1	96	92	88	85	88	84	81	78	69	67	65	56	54	53	43	42	41	35				
2	88	81	75	70	80	74	69	65	61	58	55	49	47	45	38	37	35	30				
3	80	71	64	59	73	65	59	55	54	50	46	44	41	38	34	32	31	26				
4	74	63	56	50	67	58	52	47	48	44	40	39	36	33	31	29	27	23				
5	68	57	49	43	62	52	45	40	44	38	34	36	32	29	28	26	23	20				
6	63	51	43	37	57	47	40	35	39	34	30	32	28	25	26	23	21	18				
7	58	46	38	33	53	42	36	31	36	31	27	29	26	23	23	21	19	16				
8	54	42	34	29	49	39	32	27	33	27	24	27	23	20	22	19	17	14				
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	20	17	15	13				
10	47	35	28	23	43	32	26	22	28	23	19	23	19	17	19	16	14	12				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	20384	20384	20384
5°	20462	20128	20238
10°	20305	19799	19630
15°	20072	19211	18658
20°	19747	18374	17452
25°	19417	17423	16283
30°	18957	16444	14783
35°	18510	15380	13466
40°	18061	14280	11944
45°	17532	13045	10565
50°	16990	11796	9211
55°	16434	10452	7910
60°	15791	9038	6568
65°	15060	7595	5979
70°	14186	6255	5500
75°	13119	5702	5128
80°	11576	5095	4677
85°	9114	4020	4020



TEST NUMBER: P331732-935

CATALOG NUMBER: SA2XXRDIP-C865D1080U935-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	118.2	1.9
10°-20°	324.5	5.1
20°-30°	455.6	7.2
30°-40°	496.8	7.9
40°-50°	456.8	7.2
50°-60°	358.8	5.7
60°-70°	233.9	3.7
70°-80°	120.6	1.9
80°-90°	34.4	0.5
90°-100°	42.2	0.7
100°-110°	154.7	2.5
110°-120°	413.6	6.6
120°-130°	682.8	10.8
130°-140°	726.1	11.5
140°-150°	674.9	10.7
150°-160°	542.6	8.6
160°-170°	349.7	5.5
170°-180°	120.4	1.9
0°-30°	898.3	14.2
0°-40°	1395.1	22.1
0°-60°	2210.7	35.1
0°-90°	2599.7	41.2
90°-120°	610.5	9.7
90°-150°	2694.3	42.7
90°-180°	3707.0	58.8
0°-180°	6306.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1262	1262	1262	1262	1262	
5°	1262	1256	1242	1251	1249	120
15°	1201	1187	1149	1128	1116	338
25°	1090	1051	978	933	914	501
35°	939	878	780	711	683	587
45°	768	689	571	493	463	593
55°	584	493	371	305	281	521
65°	394	301	199	162	156	391
75°	210	133	91	84	82	223
85°	49	26	22	22	22	58
90°	1	11	18	23	25	5
95°	60	31	36	40	39	73
105°	278	290	56	66	70	297
115°	526	542	565	161	75	518
125°	744	756	773	780	783	663
135°	921	935	944	952	951	711
145°	1068	1068	1083	1089	1085	668
155°	1176	1169	1179	1184	1177	542
165°	1239	1234	1237	1242	1237	350
175°	1268	1262	1263	1269	1260	121
180°	1265	1265	1265	1265	1265	



TEST NUMBER: P331732-935

CATALOG NUMBER: SA2XXRDIP-C865D1080U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1262.5	1262.5	1262.5	1262.5	1262.5	1262.5	1262.5	1262.5	1262.5	1262.5	1262.5
2.5°	1267.0	1266.0	1265.0	1263.9	1263.0	1261.4	1259.1	1256.9	1254.6	1252.4	1254.5
5°	1262.5	1261.2	1259.9	1258.6	1257.4	1255.1	1251.8	1248.5	1245.2	1241.9	1244.1
7.5°	1249.4	1247.8	1246.3	1244.7	1243.1	1240.4	1236.6	1232.7	1228.8	1224.9	1225.6
10°	1238.5	1236.7	1234.9	1233.1	1231.3	1228.0	1222.9	1217.8	1212.7	1207.6	1206.9
12.5°	1224.8	1222.5	1220.4	1218.2	1216.0	1211.7	1205.1	1198.7	1192.1	1185.7	1184.3
15°	1200.8	1198.0	1195.2	1192.4	1189.6	1183.9	1175.3	1166.7	1158.0	1149.3	1144.5
17.5°	1171.3	1167.0	1162.8	1158.5	1154.3	1146.6	1135.5	1124.4	1113.4	1102.3	1096.6
20°	1149.3	1144.3	1139.2	1134.1	1129.0	1120.2	1107.4	1094.8	1082.1	1069.4	1063.0
22.5°	1125.6	1119.9	1114.2	1108.5	1102.9	1092.9	1078.5	1064.2	1049.9	1035.5	1027.3
25°	1089.9	1081.8	1073.7	1065.6	1057.5	1045.0	1028.2	1011.5	994.7	978.0	967.6
27.5°	1047.0	1038.1	1029.3	1020.5	1011.7	997.8	978.9	960.0	941.1	922.2	910.1
30°	1016.8	1007.2	997.6	987.9	978.3	963.3	943.0	922.6	902.3	882.0	869.1
32.5°	987.6	976.3	965.0	953.7	942.5	926.5	905.8	885.0	864.4	843.6	828.9
35°	939.1	926.2	913.3	900.3	887.3	869.7	847.3	825.0	802.7	780.3	764.3
37.5°	890.7	876.5	862.3	848.0	833.8	814.8	791.0	767.2	743.4	719.5	701.9
40°	856.9	841.6	826.4	811.1	795.9	776.0	751.4	726.8	702.1	677.5	659.4
42.5°	822.2	806.1	790.1	774.0	757.9	737.2	711.8	686.3	660.9	635.4	616.8
45°	767.8	750.7	733.7	716.7	699.7	677.9	651.3	624.6	597.9	571.3	553.2
47.5°	714.7	696.7	678.7	660.6	642.7	619.8	592.4	564.8	537.3	509.8	491.9
50°	676.4	658.3	640.3	622.2	604.2	581.3	553.4	525.4	497.5	469.6	452.0
52.5°	638.9	620.0	601.2	582.4	563.5	540.4	513.2	485.8	458.5	431.2	414.2
55°	583.8	564.0	544.2	524.4	504.6	481.0	453.6	426.1	398.7	371.3	356.1
57.5°	527.4	507.0	486.7	466.4	446.2	422.8	396.4	370.1	343.7	317.4	303.4
60°	489.0	468.6	448.4	428.1	407.8	384.5	358.3	332.2	306.1	279.9	267.0
62.5°	451.5	431.2	410.9	390.5	370.2	347.7	322.7	297.8	272.9	247.9	235.6
65°	394.2	373.6	353.0	332.4	311.9	290.2	267.3	244.5	221.6	198.8	190.2
67.5°	338.9	318.5	298.1	277.6	257.2	236.7	216.2	195.6	175.0	154.5	150.5
70°	300.5	280.7	260.9	241.1	221.3	202.6	185.1	167.6	150.1	132.5	130.0
72.5°	263.9	245.0	225.9	207.0	188.0	171.4	157.4	143.3	129.2	115.2	113.0
75°	210.3	192.4	174.7	156.9	139.1	126.0	117.3	108.7	100.0	91.4	89.6
77.5°	157.5	141.8	126.2	110.6	95.1	85.2	81.0	76.9	72.8	68.5	67.5
80°	124.5	111.6	98.7	85.7	72.8	65.0	62.4	59.9	57.3	54.8	53.8
82.5°	94.4	84.3	74.1	64.1	54.0	48.0	46.3	44.6	42.9	41.2	40.6
85°	49.2	43.8	38.5	33.1	27.8	24.8	24.0	23.2	22.5	21.7	21.7
87.5°	14.8	13.6	12.5	11.3	10.1	9.6	10.0	10.3	10.7	10.9	10.9
90°	0.9	3.2	5.4	7.7	9.9	11.8	13.4	15.1	16.7	18.3	19.3
92.5°	18.5	18.3	18.1	17.9	17.7	18.0	18.8	19.6	20.4	21.3	21.8
95°	59.5	52.8	46.1	39.3	32.6	30.0	31.4	32.9	34.3	35.7	36.7
97.5°	118.0	99.2	80.2	61.3	42.4	34.6	37.9	41.2	44.5	47.8	48.6
100°	162.0	134.1	106.2	78.4	50.5	38.3	41.8	45.3	48.7	52.2	53.8
102.5°	210.3	204.4	198.5	192.6	186.8	169.4	140.4	111.5	82.6	53.6	55.8
105°	278.3	284.4	290.4	296.5	302.6	277.9	222.4	166.9	111.3	55.8	58.0
107.5°	355.7	360.6	365.5	370.4	375.4	344.6	277.9	211.4	144.7	78.2	75.9
110°	405.4	409.7	414.1	418.3	422.6	395.3	336.5	277.8	219.0	160.1	139.8



TEST NUMBER: P331732-935

CATALOG NUMBER: SA2XXRDIP-C865D1080U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	452.4	456.2	459.9	463.6	467.4	462.1	447.5	433.1	418.5	404.0	329.8
115°	526.3	529.8	533.2	536.7	540.1	544.4	549.5	554.6	559.6	564.7	470.5
117.5°	592.4	596.2	600.1	604.0	607.9	611.5	615.0	618.5	622.0	625.5	602.7
120°	640.7	643.8	646.8	649.9	652.9	656.3	660.0	663.6	667.3	670.9	673.3
122.5°	681.7	684.9	688.1	691.4	694.6	698.2	702.1	706.1	710.2	714.1	715.6
125°	744.2	746.7	749.4	752.1	754.7	757.9	761.8	765.7	769.6	773.4	774.8
127.5°	800.7	803.7	806.6	809.5	812.4	815.3	818.2	821.0	824.0	826.9	829.0
130°	836.5	839.8	843.1	846.4	849.5	852.3	854.5	856.8	859.0	861.3	863.5
132.5°	873.1	876.0	878.7	881.5	884.2	886.7	889.0	891.2	893.5	895.7	897.6
135°	920.8	924.0	927.3	930.6	933.8	936.3	938.1	940.0	941.8	943.7	945.7
137.5°	968.9	971.2	973.4	975.8	978.0	980.2	982.3	984.4	986.4	988.5	990.5
140°	1000.4	1002.0	1003.7	1005.3	1006.9	1008.8	1011.1	1013.3	1015.5	1017.8	1019.6
142.5°	1026.7	1028.2	1029.7	1031.1	1032.6	1034.7	1037.2	1039.7	1042.3	1044.9	1046.5
145°	1068.2	1067.9	1067.7	1067.6	1067.3	1068.9	1072.4	1075.8	1079.3	1082.8	1084.2
147.5°	1104.2	1103.5	1102.7	1101.9	1101.1	1102.4	1105.9	1109.2	1112.7	1116.1	1117.1
150°	1127.7	1126.2	1124.8	1123.3	1122.0	1122.8	1126.1	1129.4	1132.6	1135.8	1137.1
152.5°	1147.4	1145.8	1144.2	1142.6	1141.1	1141.8	1144.9	1148.0	1151.1	1154.2	1155.4
155°	1176.1	1174.3	1172.5	1170.6	1168.8	1169.2	1171.6	1174.0	1176.5	1178.9	1180.1
157.5°	1198.7	1197.1	1195.6	1194.0	1192.5	1192.6	1194.3	1195.9	1197.7	1199.4	1200.8
160°	1211.9	1210.7	1209.4	1208.2	1206.9	1206.9	1208.2	1209.4	1210.7	1211.9	1213.1
162.5°	1223.6	1222.4	1221.1	1219.9	1218.7	1218.6	1219.6	1220.7	1221.8	1222.8	1224.2
165°	1239.3	1238.0	1236.8	1235.6	1234.4	1234.1	1234.7	1235.4	1236.0	1236.6	1237.9
167.5°	1251.0	1249.8	1248.5	1247.3	1246.1	1245.8	1246.4	1246.9	1247.5	1248.1	1249.5
170°	1257.6	1256.4	1255.2	1254.0	1252.8	1252.3	1252.8	1253.1	1253.5	1254.0	1255.3
172.5°	1262.0	1260.8	1259.6	1258.4	1257.1	1256.7	1257.1	1257.5	1257.9	1258.4	1259.7
175°	1267.7	1266.3	1264.8	1263.4	1262.0	1261.5	1261.9	1262.3	1262.7	1263.1	1264.6
177.5°	1268.6	1267.5	1266.3	1265.2	1264.0	1263.5	1263.7	1263.9	1264.0	1264.2	1265.3
180°	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9



TEST NUMBER: P331732-935

CATALOG NUMBER: SA2XXRDIP-C865D1080U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1262.5	1262.5	1262.5	1262.5	1262.5	1262.5	1262.5	1262.5
2.5°	1256.5	1258.5	1260.5	1261.4	1260.9	1260.5	1260.2	1259.7
5°	1246.5	1248.7	1251.0	1251.8	1251.0	1250.3	1249.5	1248.7
7.5°	1226.3	1226.9	1227.6	1227.3	1226.0	1224.7	1223.3	1222.0
10°	1206.1	1205.3	1204.5	1203.4	1201.9	1200.4	1198.9	1197.3
12.5°	1182.9	1181.6	1180.2	1178.3	1175.7	1173.2	1170.6	1168.1
15°	1139.7	1134.9	1130.1	1126.4	1123.9	1121.3	1118.8	1116.2
17.5°	1090.8	1085.0	1079.3	1074.3	1069.9	1065.6	1061.2	1056.8
20°	1056.7	1050.3	1044.0	1038.0	1032.4	1026.8	1021.2	1015.7
22.5°	1019.3	1011.1	1002.9	996.7	992.6	988.3	984.2	980.1
25°	957.2	946.8	936.3	929.2	925.4	921.6	917.8	914.0
27.5°	897.9	885.8	873.7	864.6	858.6	852.5	846.4	840.4
30°	856.1	843.2	830.2	820.3	813.5	806.6	799.8	792.9
32.5°	814.1	799.3	784.5	773.9	767.5	761.0	754.6	748.1
35°	748.3	732.4	716.4	705.6	700.0	694.4	688.8	683.2
37.5°	684.3	666.7	649.1	637.1	630.7	624.2	617.9	611.5
40°	641.4	623.5	605.4	593.1	586.5	579.9	573.3	566.7
42.5°	598.2	579.5	560.9	548.4	542.0	535.6	529.2	522.8
45°	535.2	517.2	499.1	487.1	481.0	474.9	468.8	462.7
47.5°	473.9	456.0	438.1	426.4	420.9	415.3	409.7	404.2
50°	434.5	417.0	399.5	388.1	382.7	377.4	372.0	366.7
52.5°	397.4	380.5	363.5	352.7	347.7	342.8	337.9	332.9
55°	340.9	325.6	310.4	300.3	295.5	290.7	285.9	281.0
57.5°	289.5	275.5	261.6	252.5	248.5	244.4	240.3	236.3
60°	254.0	241.1	228.1	219.6	215.5	211.5	207.4	203.4
62.5°	223.3	210.9	198.5	191.1	188.7	186.3	183.8	181.4
65°	181.5	172.9	164.3	159.5	158.8	158.1	157.3	156.5
67.5°	146.5	142.6	138.6	136.2	135.4	134.6	133.8	133.0
70°	127.4	124.9	122.3	120.6	119.6	118.6	117.5	116.5
72.5°	110.9	108.7	106.6	105.3	104.6	104.0	103.4	102.8
75°	87.8	86.1	84.3	83.3	83.0	82.7	82.5	82.2
77.5°	66.6	65.5	64.5	63.8	63.4	62.9	62.6	62.2
80°	52.8	51.8	50.8	50.3	50.3	50.3	50.3	50.3
82.5°	40.0	39.3	38.7	38.4	38.4	38.4	38.4	38.4
85°	21.7	21.7	21.7	21.7	21.7	21.7	21.7	21.7
87.5°	10.9	10.9	10.9	11.0	11.1	11.2	11.3	11.4
90°	20.3	21.4	22.4	23.1	23.5	23.9	24.3	24.7
92.5°	22.3	22.8	23.3	23.8	24.0	24.2	24.5	24.7
95°	37.7	38.7	39.8	40.2	40.0	39.8	39.5	39.3
97.5°	49.4	50.2	51.1	51.6	51.8	52.1	52.3	52.5
100°	55.4	57.1	58.7	59.7	60.1	60.5	61.0	61.3
102.5°	57.9	60.0	62.1	63.5	64.0	64.6	65.2	65.7
105°	60.3	62.5	64.7	66.3	67.2	67.9	68.7	69.6
107.5°	73.6	71.3	69.1	68.4	69.1	69.9	70.8	71.5
110°	119.5	99.2	78.8	69.1	69.8	70.7	71.5	72.3





TEST NUMBER: P331732-935

CATALOG NUMBER: SA2XXRDIP-C865D1080U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	255.6	181.4	107.2	70.4	71.1	71.7	72.4	73.0
115°	376.3	282.2	188.0	133.6	119.0	104.4	89.7	75.1
117.5°	580.0	557.2	534.4	498.9	450.8	402.7	354.6	306.4
120°	675.8	678.2	680.7	668.1	640.7	613.2	585.7	558.4
122.5°	717.0	718.5	720.0	718.0	712.7	707.4	702.1	696.7
125°	776.3	777.7	779.1	780.2	780.8	781.4	782.0	782.6
127.5°	831.0	833.1	835.2	836.3	836.4	836.5	836.6	836.7
130°	865.7	868.0	870.2	871.2	871.1	870.8	870.6	870.5
132.5°	899.5	901.5	903.4	904.2	904.0	903.8	903.6	903.4
135°	947.7	949.8	951.7	952.6	952.2	951.7	951.4	951.0
137.5°	992.5	994.5	996.4	997.1	996.4	995.7	995.1	994.4
140°	1021.5	1023.3	1025.1	1025.5	1024.5	1023.5	1022.4	1021.5
142.5°	1048.2	1049.9	1051.5	1051.9	1050.9	1049.8	1048.9	1047.8
145°	1085.6	1087.0	1088.5	1088.6	1087.7	1086.7	1085.6	1084.6
147.5°	1118.2	1119.3	1120.3	1120.4	1119.6	1118.7	1117.8	1117.0
150°	1138.3	1139.5	1140.7	1140.8	1139.8	1138.8	1137.8	1136.8
152.5°	1156.6	1157.9	1159.1	1159.0	1157.6	1156.3	1154.9	1153.7
155°	1181.3	1182.6	1183.8	1183.5	1181.9	1180.3	1178.7	1177.1
157.5°	1202.1	1203.5	1204.9	1204.8	1203.2	1201.6	1200.1	1198.4
160°	1214.3	1215.5	1216.7	1216.6	1215.2	1213.8	1212.4	1210.9
162.5°	1225.5	1226.9	1228.4	1228.1	1226.4	1224.7	1222.9	1221.2
165°	1239.4	1240.8	1242.3	1242.3	1240.8	1239.4	1237.9	1236.6
167.5°	1250.9	1252.3	1253.8	1253.5	1251.7	1249.9	1248.1	1246.2
170°	1256.8	1258.2	1259.6	1259.4	1257.6	1255.8	1254.0	1252.1
172.5°	1261.2	1262.6	1264.0	1263.9	1262.0	1260.2	1258.4	1256.5
175°	1265.9	1267.4	1268.8	1268.5	1266.4	1264.4	1262.4	1260.3
177.5°	1266.4	1267.6	1268.8	1268.6	1267.1	1265.7	1264.2	1262.7
180°	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9

(END OF REPORT)