

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331392-930

Luminaire Tested: **SA2XXDIP-C865D530U930-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331392-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C865D530U930-4F0-1E-UDD-F4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 530 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4547.1 lumens
Efficiency: N/A
Efficacy: 93.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 48.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331392-930
CATALOG NUMBER: SA2XXDIP-C865D530U930-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331392-930

CATALOG NUMBER: SA2XXDIP-C865D530U930-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	91	91	91	79	79	79	68	68	68	63
1	101	96	92	89	94	90	87	84	79	77	74	69	68	66	60	59	57	53
2	92	84	78	73	86	79	74	69	70	65	62	61	58	55	53	51	48	44
3	84	74	66	60	78	70	63	58	61	56	52	54	50	46	47	44	41	38
4	77	66	57	51	72	62	55	49	55	49	44	48	44	40	42	38	36	32
5	70	58	50	44	66	55	48	42	49	43	38	43	38	35	38	34	31	28
6	65	53	44	38	61	50	42	37	44	38	34	39	34	30	34	30	27	25
7	60	48	39	34	56	45	38	32	40	34	30	36	31	27	31	27	24	22
8	56	43	35	30	52	41	34	29	37	31	26	33	28	24	29	25	22	20
9	52	40	32	27	49	38	31	26	34	28	24	30	25	22	27	23	20	18
10	49	36	29	24	46	35	28	23	31	25	21	28	23	20	25	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18166	18166	18166
5°	18235	17973	18078
10°	18126	17790	17879
15°	17904	17560	17541
20°	17584	17213	17194
25°	17268	16787	16787
30°	16861	16397	16257
35°	16484	15928	15693
40°	16008	15460	15163
45°	15536	14995	14625
50°	15028	14511	13996
55°	14494	13948	13430
60°	13905	13275	12788
65°	13268	12607	12027
70°	12463	11797	11235
75°	11335	10861	10593
80°	10060	9754	9252
85°	8225	7818	7003



TEST NUMBER: P331392-930

CATALOG NUMBER: SA2XXDIP-C865D530U930-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	105.8	2.3
10°-20°	297.7	6.5
20°-30°	437.6	9.6
30°-40°	508.3	11.2
40°-50°	507.7	11.2
50°-60°	442.8	9.7
60°-70°	327.4	7.2
70°-80°	185.4	4.1
80°-90°	52.0	1.1
90°-100°	96.7	2.1
100°-110°	328.1	7.2
110°-120°	348.5	7.7
120°-130°	286.9	6.3
130°-140°	230.4	5.1
140°-150°	174.1	3.8
150°-160°	122.4	2.7
160°-170°	72.0	1.6
170°-180°	23.4	0.5
0°-30°	841.1	18.5
0°-40°	1349.3	29.7
0°-60°	2299.8	50.6
0°-90°	2864.7	63.0
90°-120°	773.2	17.0
90°-150°	1464.6	32.2
90°-180°	1682.0	37.0
0°-180°	4547.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1125	1125	1125	1125	1125	
5°	1125	1120	1109	1117	1115	107
15°	1071	1064	1050	1054	1049	301
25°	969	960	942	944	942	446
35°	836	825	808	802	796	522
45°	680	672	657	645	640	525
55°	515	508	496	483	477	460
65°	347	341	330	320	315	343
75°	182	179	174	168	170	194
85°	44	43	42	39	38	51
90°	0	6	16	15	15	3
95°	16	40	182	69	53	17
105°	57	86	344	616	524	60
115°	100	126	288	595	690	99
125°	140	165	277	482	559	124
135°	164	195	274	405	464	126
145°	187	215	272	338	370	117
155°	212	229	265	299	311	98
165°	232	238	253	269	273	65
175°	241	242	244	247	246	23
180°	242	242	242	242	242	



TEST NUMBER: P331392-930

CATALOG NUMBER: SA2XXDIP-C865D530U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1
2.5°	1130.3	1129.4	1128.4	1127.5	1126.5	1124.9	1122.8	1120.7	1118.6	1116.5	1118.4
5°	1125.1	1124.1	1123.2	1122.3	1121.3	1119.5	1116.9	1114.2	1111.6	1108.9	1110.8
7.5°	1115.2	1113.7	1112.2	1110.7	1109.2	1107.1	1104.4	1101.7	1099.0	1096.3	1098.3
10°	1105.6	1104.0	1102.3	1100.6	1098.9	1096.7	1093.7	1090.9	1088.0	1085.1	1087.0
12.5°	1092.7	1091.2	1089.7	1088.2	1086.7	1084.5	1081.7	1078.7	1075.9	1073.0	1074.3
15°	1071.1	1069.6	1068.1	1066.7	1065.3	1063.0	1059.9	1056.7	1053.6	1050.5	1051.4
17.5°	1043.3	1041.9	1040.5	1039.0	1037.5	1035.3	1032.1	1028.9	1025.7	1022.5	1023.7
20°	1023.4	1022.0	1020.6	1019.1	1017.7	1015.3	1011.9	1008.5	1005.2	1001.8	1002.5
22.5°	1003.6	1001.5	999.5	997.4	995.5	992.9	989.7	986.5	983.3	980.2	980.3
25°	969.3	967.4	965.5	963.6	961.6	958.6	954.6	950.5	946.4	942.3	942.8
27.5°	930.4	928.7	926.9	925.2	923.5	921.0	917.8	914.5	911.3	908.1	907.4
30°	904.4	902.5	900.6	898.7	896.7	894.0	890.4	886.8	883.1	879.5	878.8
32.5°	876.8	875.2	873.7	872.1	870.6	867.9	864.1	860.3	856.6	852.7	851.4
35°	836.3	833.9	831.4	829.1	826.6	823.5	819.7	815.9	812.0	808.1	806.7
37.5°	790.6	788.5	786.4	784.2	782.2	779.2	775.3	771.5	767.6	763.8	762.0
40°	759.5	757.6	755.6	753.7	751.8	748.9	745.0	741.2	737.4	733.5	731.3
42.5°	729.2	727.2	725.3	723.4	721.5	718.6	714.8	710.9	707.0	703.2	700.8
45°	680.4	678.8	677.1	675.5	673.8	671.1	667.5	663.9	660.3	656.7	654.0
47.5°	632.0	630.5	628.8	627.3	625.7	623.0	619.2	615.5	611.7	608.0	605.2
50°	598.3	597.0	595.9	594.7	593.5	591.2	587.8	584.4	581.1	577.7	574.4
52.5°	565.4	563.8	562.2	560.6	559.1	556.7	553.5	550.3	547.1	544.0	541.2
55°	514.9	513.6	512.1	510.6	509.2	507.0	504.2	501.2	498.4	495.5	492.6
57.5°	464.3	463.2	462.0	460.9	459.7	457.5	454.4	451.2	448.0	444.8	442.1
60°	430.6	429.6	428.7	427.7	426.7	424.6	421.2	417.8	414.5	411.1	408.5
62.5°	397.7	396.2	394.6	393.1	391.5	389.5	386.9	384.3	381.6	379.1	376.7
65°	347.3	345.8	344.4	342.9	341.5	339.6	337.2	334.8	332.4	330.0	327.8
67.5°	296.0	294.8	293.7	292.5	291.4	289.8	287.6	285.4	283.2	281.0	279.4
70°	264.0	263.0	262.0	261.1	260.2	258.5	256.4	254.2	252.1	249.9	248.3
72.5°	231.1	230.2	229.2	228.2	227.2	226.1	224.7	223.3	221.8	220.5	218.8
75°	181.7	181.2	180.8	180.3	179.9	179.0	177.8	176.6	175.4	174.1	172.8
77.5°	137.6	136.8	136.0	135.2	134.4	133.7	133.2	132.7	132.2	131.8	131.0
80°	108.2	107.9	107.7	107.5	107.2	106.9	106.4	105.9	105.4	104.9	104.2
82.5°	80.5	80.5	80.4	80.3	80.3	80.1	79.8	79.6	79.2	79.0	78.0
85°	44.4	44.1	43.9	43.6	43.4	43.1	42.9	42.6	42.4	42.2	41.5
87.5°	15.7	15.6	15.6	15.3	15.2	15.1	15.2	15.4	15.6	15.2	14.6
90°	0.5	1.9	3.8	4.6	5.5	7.0	9.3	12.6	15.3	15.8	15.3
92.5°	5.7	8.2	11.5	13.6	16.7	21.1	31.6	46.4	59.6	60.4	51.0
95°	16.3	18.1	22.7	27.0	34.4	45.6	66.9	107.4	161.3	182.3	159.5
97.5°	26.5	29.0	33.9	40.3	48.8	61.5	88.4	144.7	234.3	311.1	326.4
100°	35.8	37.2	41.4	48.8	58.1	71.2	95.8	152.5	252.9	367.3	434.2
102.5°	44.4	45.4	49.6	57.0	66.7	79.7	102.5	152.9	245.9	369.2	474.4
105°	56.7	58.6	61.8	68.8	79.0	92.0	113.9	155.3	232.0	344.5	468.2
107.5°	70.1	71.6	74.8	81.2	91.3	104.4	125.6	161.7	225.1	318.1	427.4
110°	79.0	80.9	83.7	89.8	99.5	113.0	133.5	166.9	223.6	305.5	401.7



TEST NUMBER: P331392-930

CATALOG NUMBER: SA2XXDIP-C865D530U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	87.2	89.1	92.2	97.9	107.3	121.2	140.9	172.5	224.0	297.3	383.8
115°	100.0	102.3	105.1	110.6	119.9	132.5	152.5	180.8	226.0	288.3	361.7
117.5°	113.2	115.0	117.8	122.8	131.7	144.7	163.2	189.8	229.3	283.9	347.8
120°	121.3	123.2	126.0	130.2	139.5	152.5	170.6	195.8	231.5	281.3	340.4
122.5°	129.1	130.7	133.5	138.0	147.3	160.7	177.7	201.0	234.2	279.8	334.0
125°	139.5	140.9	143.7	149.3	158.6	171.5	188.3	209.2	238.1	277.1	325.0
127.5°	147.7	149.5	153.4	159.6	168.5	181.9	198.2	217.0	242.1	275.6	316.7
130°	152.5	154.3	159.0	165.5	174.8	187.8	204.2	221.8	245.0	274.8	311.0
132.5°	156.9	159.2	164.2	171.1	180.8	193.8	209.3	226.7	248.0	274.4	306.6
135°	163.6	165.5	171.1	178.1	188.7	201.8	216.7	232.9	251.5	273.9	300.4
137.5°	170.0	172.2	177.8	185.2	195.8	207.9	222.7	237.7	254.7	273.8	296.0
140°	174.8	176.7	182.3	189.7	199.9	212.1	226.0	240.4	256.2	273.4	293.4
142.5°	179.7	181.2	186.4	193.8	203.7	215.0	228.6	242.6	257.3	273.4	290.8
145°	186.9	188.7	193.4	200.4	209.7	219.9	232.4	245.5	258.5	272.5	287.3
147.5°	194.7	196.1	200.6	207.0	214.7	223.8	235.6	247.1	258.9	270.8	283.8
150°	199.9	201.3	205.0	211.1	218.1	226.4	237.1	247.9	258.5	269.7	280.9
152.5°	205.1	205.8	209.5	214.8	221.4	229.0	238.6	248.2	257.8	267.8	278.3
155°	212.5	213.0	215.7	220.9	226.0	232.9	240.8	248.7	256.7	264.6	273.4
157.5°	218.6	219.1	221.4	225.8	229.9	235.7	242.4	248.7	254.5	261.2	268.8
160°	222.7	223.1	225.0	228.8	232.4	237.6	243.2	248.7	253.4	259.0	265.5
162.5°	226.8	226.5	228.4	231.4	234.7	238.7	243.5	248.3	252.3	257.1	262.5
165°	231.5	231.1	232.0	234.8	237.1	239.9	244.1	247.4	250.1	253.4	257.6
167.5°	235.5	234.9	235.7	237.5	239.2	240.9	244.0	246.7	248.0	250.1	252.7
170°	238.1	237.1	237.6	239.0	239.9	241.3	243.6	246.0	246.9	248.3	250.1
172.5°	239.5	239.0	238.7	240.1	240.7	241.7	243.3	244.8	245.4	246.1	247.5
175°	241.3	240.8	240.4	241.3	241.3	241.7	242.7	243.6	243.2	243.6	244.1
177.5°	242.1	241.4	241.0	241.7	241.7	241.7	242.1	242.9	242.1	241.7	242.1
180°	241.7	241.7	241.7	241.7	241.7	241.7	241.7	241.7	241.7	241.7	241.7



TEST NUMBER: P331392-930

CATALOG NUMBER: SA2XXDIP-C865D530U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1
2.5°	1120.3	1122.3	1124.1	1124.9	1124.5	1124.1	1123.8	1123.4
5°	1112.7	1114.7	1116.6	1117.3	1116.9	1116.4	1115.9	1115.4
7.5°	1100.2	1102.1	1104.1	1104.7	1104.2	1103.7	1103.2	1102.6
10°	1088.9	1090.9	1092.8	1093.4	1092.7	1091.9	1091.2	1090.5
12.5°	1075.7	1077.0	1078.4	1078.8	1078.2	1077.7	1077.2	1076.7
15°	1052.4	1053.4	1054.3	1054.2	1053.0	1051.8	1050.6	1049.4
17.5°	1024.7	1025.9	1027.0	1027.0	1025.8	1024.7	1023.5	1022.4
20°	1003.2	1004.0	1004.7	1004.5	1003.6	1002.7	1001.7	1000.7
22.5°	980.5	980.6	980.7	980.6	979.9	979.3	978.8	978.2
25°	943.3	943.7	944.2	944.2	943.7	943.3	942.8	942.3
27.5°	906.7	906.0	905.2	904.3	903.1	902.0	900.8	899.7
30°	878.1	877.4	876.7	875.8	874.9	873.9	872.9	872.0
32.5°	850.1	848.8	847.5	846.4	845.5	844.5	843.5	842.5
35°	805.3	803.8	802.4	801.0	799.9	798.7	797.4	796.2
37.5°	760.3	758.5	756.7	755.2	754.1	752.9	751.8	750.6
40°	729.2	727.0	724.9	723.3	722.4	721.4	720.4	719.4
42.5°	698.5	696.1	693.8	691.9	690.6	689.3	687.9	686.6
45°	651.4	648.7	646.1	644.3	643.4	642.4	641.4	640.5
47.5°	602.4	599.7	596.9	594.8	593.4	592.0	590.6	589.2
50°	571.0	567.6	564.3	562.0	560.8	559.5	558.4	557.2
52.5°	538.3	535.6	532.8	530.6	529.0	527.4	525.9	524.2
55°	489.8	486.8	484.0	481.9	480.7	479.5	478.3	477.1
57.5°	439.2	436.3	433.5	431.6	430.7	429.8	428.9	428.0
60°	405.9	403.2	400.6	398.8	398.1	397.4	396.6	396.0
62.5°	374.1	371.7	369.2	367.6	366.6	365.7	364.8	363.9
65°	325.6	323.5	321.3	319.6	318.5	317.2	316.0	314.8
67.5°	277.7	276.0	274.3	273.0	272.1	271.1	270.1	269.1
70°	246.5	244.8	243.2	241.8	240.9	239.9	239.0	238.0
72.5°	217.1	215.4	213.8	212.5	211.7	211.0	210.2	209.5
75°	171.3	169.8	168.4	168.0	168.4	168.9	169.3	169.8
77.5°	130.4	129.6	128.9	128.2	127.5	126.9	126.2	125.5
80°	103.5	102.8	102.1	101.4	100.9	100.5	100.0	99.5
82.5°	77.1	76.2	75.3	74.8	74.7	74.6	74.5	74.4
85°	40.8	40.0	39.3	38.8	38.6	38.3	38.1	37.8
87.5°	13.9	13.2	12.8	12.5	12.3	12.1	11.9	11.7
90°	14.8	13.9	14.8	15.3	15.3	15.3	15.3	15.3
92.5°	40.5	34.8	30.9	28.0	27.6	26.2	26.5	25.8
95°	121.8	93.4	73.9	63.7	57.6	54.0	52.5	53.0
97.5°	284.3	232.6	182.3	148.7	126.5	115.0	108.3	104.4
100°	424.5	366.9	303.1	246.9	208.3	188.3	174.8	166.5
102.5°	516.4	503.4	456.8	397.1	355.2	321.1	304.3	292.9
105°	564.9	617.4	623.5	608.1	579.4	550.5	530.5	524.0
107.5°	529.9	609.1	657.5	680.0	683.5	682.0	678.0	669.4
110°	499.9	583.0	642.5	680.7	700.7	709.6	713.7	713.2



TEST NUMBER: P331392-930

CATALOG NUMBER: SA2XXDIP-C865D530U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	472.3	552.2	615.8	659.5	687.3	702.1	710.0	712.5
115°	438.5	510.1	571.0	618.9	651.8	673.3	685.3	689.5
117.5°	412.9	475.8	531.1	576.0	609.7	632.3	645.0	648.5
120°	400.3	458.0	507.3	549.6	582.1	604.0	617.4	622.1
122.5°	390.3	443.1	489.8	528.0	557.2	578.7	590.7	594.6
125°	375.7	423.5	464.5	499.4	526.4	544.0	555.6	559.4
127.5°	361.3	404.6	443.2	475.4	498.9	515.4	525.5	528.5
130°	352.0	392.0	428.7	459.3	482.2	498.0	507.3	510.9
132.5°	343.1	380.1	413.8	442.6	465.0	480.9	489.4	492.8
135°	330.6	361.3	392.0	418.0	438.0	453.3	461.7	463.6
137.5°	320.7	346.3	370.6	393.4	411.6	424.8	432.1	434.9
140°	314.3	336.6	358.0	378.5	393.4	405.4	412.4	415.2
142.5°	309.1	328.1	346.5	363.6	377.7	388.7	394.9	395.5
145°	301.7	317.1	331.5	345.0	356.1	364.0	368.7	370.1
147.5°	296.1	308.2	319.4	329.3	338.5	344.8	348.0	348.8
150°	292.0	302.2	312.0	320.3	327.3	332.9	335.7	336.1
152.5°	287.9	297.4	305.7	312.9	318.4	323.3	325.3	325.4
155°	282.3	289.7	296.6	301.7	306.9	310.1	312.0	311.0
157.5°	275.7	281.8	287.7	291.7	295.3	298.1	298.9	298.9
160°	271.5	276.6	281.8	285.0	288.3	290.6	291.1	291.1
162.5°	267.4	271.8	276.2	278.7	281.9	283.6	284.0	283.6
165°	261.3	264.6	267.8	269.7	271.5	273.4	273.4	273.0
167.5°	255.4	258.0	260.2	261.9	262.7	263.7	263.7	263.1
170°	252.5	253.9	255.8	256.7	257.1	258.5	258.0	257.1
172.5°	249.2	250.1	251.6	252.2	252.7	253.3	252.8	252.3
175°	245.5	246.0	246.5	246.9	246.9	247.4	246.9	246.0
177.5°	242.9	242.9	243.3	243.3	243.3	243.3	242.9	242.1
180°	241.7	241.7	241.7	241.7	241.7	241.7	241.7	241.7

(END OF REPORT)