

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331714-935

Luminaire Tested: **SA2XXRDIP-C865D530U935-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331714-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C865D530U935-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 530 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4417.9 lumens
Efficiency: N/A
Efficacy: 90.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 48.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331714-935
CATALOG NUMBER: SA2XXRDIP-C865D530U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331714-935

CATALOG NUMBER: SA2XXRDIP-C865D530U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20									
RC	80					70					50					30					10				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0				
RCR	0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64	59						
	1	100	96	92	89	93	90	87	84	78	76	74	68	66	64	58	56	55	51						
	2	92	85	79	74	85	79	74	70	69	65	62	60	57	55	51	49	47	43						
	3	84	75	68	62	78	70	64	59	62	57	53	54	50	47	46	43	41	37						
	4	77	67	59	53	72	63	56	51	55	50	45	48	44	41	42	38	36	33						
	5	71	60	52	46	66	56	49	44	50	44	40	43	39	36	38	34	32	29						
	6	66	54	46	40	61	51	44	38	45	39	35	40	35	32	34	31	28	25						
	7	61	49	41	36	57	46	39	34	41	35	31	36	32	28	32	28	25	23						
	8	57	45	37	32	53	42	35	30	38	32	28	33	29	25	29	26	23	21						
	9	53	41	33	28	50	39	32	27	35	29	25	31	26	23	27	23	21	19						
	10	50	38	31	26	46	36	29	25	32	27	23	28	24	21	25	22	19	17						

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	20384	20384	20384
5°	20462	20128	20238
10°	20305	19799	19630
15°	20072	19211	18658
20°	19747	18374	17452
25°	19417	17423	16283
30°	18957	16444	14783
35°	18510	15380	13466
40°	18061	14280	11944
45°	17532	13045	10565
50°	16990	11796	9211
55°	16434	10452	7910
60°	15791	9038	6568
65°	15060	7595	5979
70°	14186	6255	5500
75°	13119	5702	5128
80°	11576	5095	4677
85°	9114	4020	4020



TEST NUMBER: P331714-935

CATALOG NUMBER: SA2XXRDIP-C865D530U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	118.2	2.7
10°-20°	324.5	7.3
20°-30°	455.6	10.3
30°-40°	496.8	11.2
40°-50°	456.8	10.3
50°-60°	358.8	8.1
60°-70°	233.9	5.3
70°-80°	120.6	2.7
80°-90°	32.8	0.7
90°-100°	20.7	0.5
100°-110°	76.0	1.7
110°-120°	203.0	4.6
120°-130°	335.2	7.6
130°-140°	356.5	8.1
140°-150°	331.3	7.5
150°-160°	266.4	6.0
160°-170°	171.7	3.9
170°-180°	59.1	1.3
0°-30°	898.3	20.3
0°-40°	1395.1	31.6
0°-60°	2210.7	50.0
0°-90°	2598.1	58.8
90°-120°	299.7	6.8
90°-150°	1322.7	29.9
90°-180°	1820.0	41.2
0°-180°	4417.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1262	1262	1262	1262	1262	
5°	1262	1256	1242	1251	1249	120
15°	1201	1187	1149	1128	1116	338
25°	1090	1051	978	933	914	501
35°	939	878	780	711	683	587
45°	768	689	571	493	463	593
55°	584	493	371	305	281	521
65°	394	301	199	162	156	391
75°	210	133	91	84	82	223
85°	49	26	22	22	22	58
90°	0	5	9	11	12	3
95°	29	15	18	20	19	36
105°	137	143	27	32	34	146
115°	258	266	277	79	37	254
125°	365	371	380	383	384	326
135°	452	459	463	468	467	349
145°	524	524	532	534	532	328
155°	577	574	579	581	578	266
165°	608	606	607	610	607	172
175°	622	619	620	623	619	59
180°	621	621	621	621	621	



TEST NUMBER: P331714-935

CATALOG NUMBER: SA2XXRDIP-C865D530U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1262.5	1262.5	1262.5	1262.5	1262.5	1262.5	1262.5	1262.5	1262.5	1262.5	1262.5
2.5°	1267.0	1266.0	1265.0	1263.9	1263.0	1261.4	1259.1	1256.9	1254.6	1252.4	1254.5
5°	1262.5	1261.2	1259.9	1258.6	1257.4	1255.1	1251.8	1248.5	1245.2	1241.9	1244.1
7.5°	1249.4	1247.8	1246.3	1244.7	1243.1	1240.4	1236.6	1232.7	1228.8	1224.9	1225.6
10°	1238.5	1236.7	1234.9	1233.1	1231.3	1228.0	1222.9	1217.8	1212.7	1207.6	1206.9
12.5°	1224.8	1222.5	1220.4	1218.2	1216.0	1211.7	1205.1	1198.7	1192.1	1185.7	1184.3
15°	1200.8	1198.0	1195.2	1192.4	1189.6	1183.9	1175.3	1166.7	1158.0	1149.3	1144.5
17.5°	1171.3	1167.0	1162.8	1158.5	1154.3	1146.6	1135.5	1124.4	1113.4	1102.3	1096.6
20°	1149.3	1144.3	1139.2	1134.1	1129.0	1120.2	1107.4	1094.8	1082.1	1069.4	1063.0
22.5°	1125.6	1119.9	1114.2	1108.5	1102.9	1092.9	1078.5	1064.2	1049.9	1035.5	1027.3
25°	1089.9	1081.8	1073.7	1065.6	1057.5	1045.0	1028.2	1011.5	994.7	978.0	967.6
27.5°	1047.0	1038.1	1029.3	1020.5	1011.7	997.8	978.9	960.0	941.1	922.2	910.1
30°	1016.8	1007.2	997.6	987.9	978.3	963.3	943.0	922.6	902.3	882.0	869.1
32.5°	987.6	976.3	965.0	953.7	942.5	926.5	905.8	885.0	864.4	843.6	828.9
35°	939.1	926.2	913.3	900.3	887.3	869.7	847.3	825.0	802.7	780.3	764.3
37.5°	890.7	876.5	862.3	848.0	833.8	814.8	791.0	767.2	743.4	719.5	701.9
40°	856.9	841.6	826.4	811.1	795.9	776.0	751.4	726.8	702.1	677.5	659.4
42.5°	822.2	806.1	790.1	774.0	757.9	737.2	711.8	686.3	660.9	635.4	616.8
45°	767.8	750.7	733.7	716.7	699.7	677.9	651.3	624.6	597.9	571.3	553.2
47.5°	714.7	696.7	678.7	660.6	642.7	619.8	592.4	564.8	537.3	509.8	491.9
50°	676.4	658.3	640.3	622.2	604.2	581.3	553.4	525.4	497.5	469.6	452.0
52.5°	638.9	620.0	601.2	582.4	563.5	540.4	513.2	485.8	458.5	431.2	414.2
55°	583.8	564.0	544.2	524.4	504.6	481.0	453.6	426.1	398.7	371.3	356.1
57.5°	527.4	507.0	486.7	466.4	446.2	422.8	396.4	370.1	343.7	317.4	303.4
60°	489.0	468.6	448.4	428.1	407.8	384.5	358.3	332.2	306.1	279.9	267.0
62.5°	451.5	431.2	410.9	390.5	370.2	347.7	322.7	297.8	272.9	247.9	235.6
65°	394.2	373.6	353.0	332.4	311.9	290.2	267.3	244.5	221.6	198.8	190.2
67.5°	338.9	318.5	298.1	277.6	257.2	236.7	216.2	195.6	175.0	154.5	150.5
70°	300.5	280.7	260.9	241.1	221.3	202.6	185.1	167.6	150.1	132.5	130.0
72.5°	263.9	245.0	225.9	207.0	188.0	171.4	157.4	143.3	129.2	115.2	113.0
75°	210.3	192.4	174.7	156.9	139.1	126.0	117.3	108.7	100.0	91.4	89.6
77.5°	157.5	141.8	126.2	110.6	95.1	85.2	81.0	76.9	72.8	68.5	67.5
80°	124.5	111.6	98.7	85.7	72.8	65.0	62.4	59.9	57.3	54.8	53.8
82.5°	94.4	84.3	74.1	64.1	54.0	48.0	46.3	44.6	42.9	41.2	40.6
85°	49.2	43.8	38.5	33.1	27.8	24.8	24.0	23.2	22.5	21.7	21.7
87.5°	14.7	13.3	11.9	10.5	9.1	8.4	8.6	8.8	9.0	9.1	9.0
90°	0.4	1.5	2.7	3.7	4.8	5.8	6.6	7.4	8.2	9.0	9.5
92.5°	9.0	9.0	8.9	8.8	8.7	8.9	9.2	9.6	10.0	10.4	10.7
95°	29.2	25.9	22.6	19.3	16.0	14.7	15.4	16.1	16.8	17.6	18.0
97.5°	57.9	48.6	39.4	30.1	20.8	17.0	18.6	20.2	21.9	23.4	23.8
100°	79.6	65.9	52.2	38.5	24.8	18.9	20.5	22.2	23.9	25.6	26.4
102.5°	103.2	100.4	97.5	94.5	91.7	83.1	69.0	54.8	40.6	26.3	27.4
105°	136.6	139.6	142.6	145.6	148.6	136.5	109.2	82.0	54.7	27.4	28.5
107.5°	174.6	177.0	179.4	181.8	184.3	169.1	136.5	103.8	71.0	38.4	37.3
110°	199.1	201.1	203.3	205.3	207.4	194.1	165.2	136.4	107.5	78.6	68.6



TEST NUMBER: P331714-935

CATALOG NUMBER: SA2XXRDIP-C865D530U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	222.1	223.9	225.8	227.6	229.5	226.9	219.7	212.6	205.4	198.4	161.9
115°	258.4	260.0	261.7	263.5	265.2	267.3	269.8	272.2	274.7	277.2	231.0
117.5°	290.8	292.7	294.6	296.5	298.4	300.2	302.0	303.7	305.4	307.0	295.9
120°	314.5	316.0	317.5	319.0	320.6	322.2	324.0	325.8	327.5	329.3	330.5
122.5°	334.7	336.2	337.9	339.4	341.0	342.8	344.7	346.6	348.6	350.6	351.3
125°	365.3	366.6	367.9	369.2	370.5	372.1	374.0	375.9	377.8	379.7	380.4
127.5°	393.0	394.5	396.0	397.4	398.8	400.3	401.7	403.1	404.5	406.0	406.9
130°	410.7	412.2	413.9	415.5	417.1	418.4	419.6	420.6	421.7	422.8	424.0
132.5°	428.7	430.0	431.4	432.7	434.1	435.3	436.4	437.6	438.6	439.7	440.7
135°	452.0	453.7	455.2	456.8	458.4	459.7	460.5	461.5	462.4	463.2	464.3
137.5°	475.7	476.7	477.9	479.0	480.1	481.2	482.2	483.3	484.2	485.3	486.3
140°	491.1	491.9	492.8	493.5	494.3	495.2	496.4	497.5	498.5	499.6	500.6
142.5°	504.0	504.8	505.5	506.2	507.0	507.9	509.2	510.4	511.7	513.0	513.8
145°	524.3	524.3	524.2	524.1	524.0	524.8	526.5	528.1	529.9	531.6	532.3
147.5°	542.1	541.7	541.3	541.0	540.5	541.2	542.9	544.6	546.2	547.9	548.5
150°	553.5	552.8	552.2	551.5	550.8	551.2	552.8	554.4	556.0	557.6	558.2
152.5°	563.3	562.5	561.7	560.9	560.2	560.5	562.1	563.6	565.1	566.6	567.2
155°	577.4	576.5	575.6	574.7	573.8	573.9	575.1	576.4	577.6	578.8	579.4
157.5°	588.4	587.7	586.9	586.2	585.4	585.5	586.3	587.1	588.0	588.8	589.4
160°	595.0	594.3	593.7	593.1	592.5	592.5	593.1	593.7	594.3	595.0	595.6
162.5°	600.6	600.0	599.4	598.8	598.3	598.2	598.7	599.3	599.8	600.3	601.0
165°	608.4	607.8	607.2	606.6	606.0	605.9	606.1	606.4	606.7	607.0	607.8
167.5°	614.2	613.5	612.9	612.3	611.7	611.6	611.8	612.2	612.4	612.7	613.4
170°	617.3	616.8	616.2	615.6	615.0	614.8	615.0	615.2	615.4	615.6	616.3
172.5°	619.6	619.0	618.4	617.8	617.2	616.9	617.2	617.3	617.5	617.8	618.5
175°	622.3	621.6	621.0	620.3	619.5	619.3	619.5	619.7	619.8	620.1	620.8
177.5°	622.8	622.2	621.6	621.1	620.5	620.3	620.4	620.4	620.5	620.6	621.2
180°	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0



TEST NUMBER: P331714-935

CATALOG NUMBER: SA2XXRDIP-C865D530U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1262.5	1262.5	1262.5	1262.5	1262.5	1262.5	1262.5	1262.5
2.5°	1256.5	1258.5	1260.5	1261.4	1260.9	1260.5	1260.2	1259.7
5°	1246.5	1248.7	1251.0	1251.8	1251.0	1250.3	1249.5	1248.7
7.5°	1226.3	1226.9	1227.6	1227.3	1226.0	1224.7	1223.3	1222.0
10°	1206.1	1205.3	1204.5	1203.4	1201.9	1200.4	1198.9	1197.3
12.5°	1182.9	1181.6	1180.2	1178.3	1175.7	1173.2	1170.6	1168.1
15°	1139.7	1134.9	1130.1	1126.4	1123.9	1121.3	1118.8	1116.2
17.5°	1090.8	1085.0	1079.3	1074.3	1069.9	1065.6	1061.2	1056.8
20°	1056.7	1050.3	1044.0	1038.0	1032.4	1026.8	1021.2	1015.7
22.5°	1019.3	1011.1	1002.9	996.7	992.6	988.3	984.2	980.1
25°	957.2	946.8	936.3	929.2	925.4	921.6	917.8	914.0
27.5°	897.9	885.8	873.7	864.6	858.6	852.5	846.4	840.4
30°	856.1	843.2	830.2	820.3	813.5	806.6	799.8	792.9
32.5°	814.1	799.3	784.5	773.9	767.5	761.0	754.6	748.1
35°	748.3	732.4	716.4	705.6	700.0	694.4	688.8	683.2
37.5°	684.3	666.7	649.1	637.1	630.7	624.2	617.9	611.5
40°	641.4	623.5	605.4	593.1	586.5	579.9	573.3	566.7
42.5°	598.2	579.5	560.9	548.4	542.0	535.6	529.2	522.8
45°	535.2	517.2	499.1	487.1	481.0	474.9	468.8	462.7
47.5°	473.9	456.0	438.1	426.4	420.9	415.3	409.7	404.2
50°	434.5	417.0	399.5	388.1	382.7	377.4	372.0	366.7
52.5°	397.4	380.5	363.5	352.7	347.7	342.8	337.9	332.9
55°	340.9	325.6	310.4	300.3	295.5	290.7	285.9	281.0
57.5°	289.5	275.5	261.6	252.5	248.5	244.4	240.3	236.3
60°	254.0	241.1	228.1	219.6	215.5	211.5	207.4	203.4
62.5°	223.3	210.9	198.5	191.1	188.7	186.3	183.8	181.4
65°	181.5	172.9	164.3	159.5	158.8	158.1	157.3	156.5
67.5°	146.5	142.6	138.6	136.2	135.4	134.6	133.8	133.0
70°	127.4	124.9	122.3	120.6	119.6	118.6	117.5	116.5
72.5°	110.9	108.7	106.6	105.3	104.6	104.0	103.4	102.8
75°	87.8	86.1	84.3	83.3	83.0	82.7	82.5	82.2
77.5°	66.6	65.5	64.5	63.8	63.4	62.9	62.6	62.2
80°	52.8	51.8	50.8	50.3	50.3	50.3	50.3	50.3
82.5°	40.0	39.3	38.7	38.4	38.4	38.4	38.4	38.4
85°	21.7	21.7	21.7	21.7	21.7	21.7	21.7	21.7
87.5°	8.9	8.8	8.7	8.7	8.7	8.8	8.8	8.8
90°	10.0	10.5	11.0	11.4	11.5	11.7	12.0	12.1
92.5°	10.9	11.2	11.5	11.6	11.8	11.9	12.1	12.1
95°	18.5	19.0	19.5	19.7	19.6	19.5	19.5	19.3
97.5°	24.3	24.6	25.1	25.3	25.4	25.6	25.7	25.8
100°	27.2	28.0	28.8	29.3	29.5	29.7	29.9	30.1
102.5°	28.4	29.4	30.5	31.2	31.4	31.7	31.9	32.3
105°	29.6	30.7	31.8	32.5	33.0	33.3	33.8	34.2
107.5°	36.2	35.0	33.9	33.6	33.9	34.4	34.7	35.1
110°	58.6	48.6	38.7	33.9	34.3	34.7	35.1	35.5



TEST NUMBER: P331714-935

CATALOG NUMBER: SA2XXRDIP-C865D530U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	125.4	89.0	52.6	34.6	34.9	35.2	35.6	35.8
115°	184.8	138.5	92.3	65.6	58.4	51.2	44.0	36.9
117.5°	284.7	273.5	262.3	245.0	221.3	197.7	174.1	150.4
120°	331.7	332.9	334.2	328.0	314.5	301.1	287.6	274.1
122.5°	352.0	352.8	353.4	352.5	349.9	347.2	344.7	342.0
125°	381.1	381.8	382.5	383.0	383.3	383.6	383.9	384.2
127.5°	407.9	409.0	410.0	410.5	410.6	410.7	410.7	410.8
130°	425.0	426.1	427.2	427.7	427.6	427.5	427.4	427.3
132.5°	441.6	442.6	443.5	443.8	443.8	443.7	443.6	443.5
135°	465.3	466.2	467.3	467.7	467.4	467.3	467.1	466.8
137.5°	487.2	488.2	489.2	489.5	489.1	488.8	488.5	488.2
140°	501.4	502.3	503.3	503.4	502.9	502.5	502.0	501.4
142.5°	514.6	515.4	516.3	516.4	515.9	515.4	514.9	514.4
145°	533.0	533.6	534.3	534.4	534.0	533.5	533.0	532.4
147.5°	549.0	549.5	550.0	550.0	549.7	549.2	548.8	548.4
150°	558.8	559.4	560.0	560.1	559.6	559.0	558.5	558.1
152.5°	567.8	568.4	569.0	568.9	568.3	567.7	567.0	566.4
155°	580.0	580.6	581.2	581.0	580.2	579.5	578.7	577.8
157.5°	590.1	590.8	591.5	591.5	590.6	589.9	589.1	588.3
160°	596.1	596.7	597.3	597.3	596.6	595.9	595.1	594.4
162.5°	601.7	602.4	603.0	603.0	602.1	601.2	600.4	599.5
165°	608.5	609.2	609.8	609.8	609.2	608.5	607.8	607.0
167.5°	614.1	614.8	615.5	615.4	614.5	613.6	612.7	611.8
170°	617.0	617.7	618.4	618.3	617.3	616.5	615.6	614.7
172.5°	619.1	619.8	620.5	620.4	619.6	618.6	617.8	616.8
175°	621.5	622.2	622.8	622.8	621.7	620.7	619.7	618.7
177.5°	621.7	622.3	622.8	622.8	622.1	621.3	620.6	619.9
180°	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0

(END OF REPORT)