

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331429-840

Luminaire Tested: **SA2XXDIP-C1005D530U840-4F0-1E-UDD-A**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331429-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C1005D530U840-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 530 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6578.9 lumens
Efficiency: N/A
Efficacy: 119.4 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 55.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331429-840

CATALOG NUMBER: SA2XXDIP-C1005D530U840-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331429-840

CATALOG NUMBER: SA2XXDIP-C1005D530U840-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	68				
1	102	98	94	91	96	93	90	87	83	80	78	73	72	70	65	64	62	58				
2	94	87	81	75	88	82	77	72	73	69	66	65	62	59	58	56	53	50				
3	86	77	69	64	81	73	66	61	65	60	56	58	54	51	52	49	46	43				
4	79	68	61	55	74	65	58	53	58	53	48	52	48	44	47	43	40	37				
5	73	61	53	47	69	58	51	46	53	47	42	47	43	39	43	39	36	33				
6	67	55	47	42	64	53	46	40	48	42	37	43	38	35	39	35	32	29				
7	63	50	42	37	59	48	41	36	44	38	33	40	35	31	36	32	29	26				
8	58	46	38	33	55	44	37	32	40	34	30	36	31	28	33	29	26	24				
9	55	42	35	30	52	40	34	29	37	31	27	34	29	25	31	26	24	22				
10	51	39	32	27	48	37	31	26	34	29	25	31	26	23	28	24	22	20				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	32513	32513	32513	32513
5°	36451	32725	29000	32725
10°	41769	32455	25097	32455
15°	46208	31861	22173	31861
20°	45505	31223	20213	31223
25°	41031	30375	18971	30375
30°	33907	29015	18066	29015
35°	24711	27595	17420	27595
40°	19736	25918	17062	25918
45°	17249	23980	16575	23980
50°	16211	22102	16252	22102
55°	14945	20194	15817	20194
60°	13695	18167	15145	18167
65°	12478	16351	14487	16351
70°	11325	14578	13520	14578
75°	10044	12601	11977	12601
80°	8638	10432	9642	10432
85°	7744	7744	5743	7744



TEST NUMBER: P331429-840

CATALOG NUMBER: SA2XXDIP-C1005D530U840-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	191.8	2.9
10°-20°	557.5	8.5
20°-30°	809.1	12.3
30°-40°	853.9	13.0
40°-50°	756.0	11.5
50°-60°	603.3	9.2
60°-70°	410.1	6.2
70°-80°	210.2	3.2
80°-90°	52.5	0.8
90°-100°	24.3	0.4
100°-110°	89.1	1.4
110°-120°	238.2	3.6
120°-130°	393.1	6.0
130°-140°	418.1	6.4
140°-150°	388.6	5.9
150°-160°	312.4	4.7
160°-170°	201.3	3.1
170°-180°	69.3	1.1
0°-30°	1558.5	23.7
0°-40°	2412.3	36.7
0°-60°	3771.7	57.3
0°-90°	4444.5	67.6
90°-120°	351.5	5.3
90°-150°	1551.4	23.6
90°-180°	2134.0	32.4
0°-180°	6578.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	2014	2014	2014	2014	2014	
5°	2249	2019	1789	2019	2249	225
15°	2764	1906	1326	1906	2764	763
25°	2303	1705	1065	1705	2303	1041
35°	1254	1400	884	1400	1254	815
45°	755	1050	726	1050	755	594
55°	531	717	562	717	531	476
65°	327	428	379	428	327	325
75°	161	202	192	202	161	172
85°	42	42	31	42	42	46
90°	14	0	14	0	14	8
95°	23	34	23	34	23	21
105°	40	160	40	160	40	42
115°	43	303	43	303	43	108
125°	451	428	451	428	451	390
135°	548	530	548	530	548	422
145°	624	615	624	615	624	391
155°	678	677	678	677	678	313
165°	712	714	712	714	712	201
175°	726	730	726	730	726	69
180°	728	728	728	728	728	



TEST NUMBER: P331429-840
 CATALOG NUMBER: SA2XXDIP-C1005D530U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7
2.5°	2106.6	2107.2	2108.4	2098.5	2097.3	2097.3	2088.6	2081.2	2072.5	2060.7	2062.0
5°	2249.0	2257.5	2260.6	2251.3	2237.4	2235.8	2222.7	2201.0	2180.9	2164.6	2153.0
7.5°	2418.9	2422.4	2414.8	2402.6	2392.2	2373.6	2349.1	2325.1	2291.6	2260.8	2237.9
10°	2547.7	2552.3	2539.2	2521.4	2506.7	2485.1	2449.4	2413.1	2368.9	2326.4	2292.3
12.5°	2645.5	2657.0	2640.1	2637.8	2612.6	2582.8	2540.4	2522.0	2459.9	2400.7	2364.2
15°	2764.4	2763.6	2765.2	2750.5	2731.9	2727.2	2682.4	2633.6	2546.2	2511.3	2450.9
17.5°	2730.1	2741.8	2747.2	2747.0	2746.6	2743.7	2729.3	2698.5	2654.6	2598.2	2528.5
20°	2648.4	2663.8	2666.1	2683.9	2694.0	2707.1	2712.6	2704.0	2677.0	2629.8	2569.4
22.5°	2522.0	2526.4	2533.7	2561.3	2583.1	2616.2	2633.3	2661.9	2651.6	2628.5	2578.1
25°	2303.2	2295.4	2322.5	2336.4	2386.7	2439.3	2477.3	2519.1	2556.3	2578.7	2563.9
27.5°	2040.3	2028.7	2069.3	2106.3	2147.2	2204.1	2263.2	2333.0	2391.1	2463.7	2488.6
30°	1818.7	1825.6	1864.3	1903.8	1965.7	2046.2	2112.7	2189.4	2272.2	2353.5	2409.9
32.5°	1579.7	1606.5	1630.9	1691.4	1746.0	1835.7	1933.2	2029.0	2132.3	2224.7	2312.2
35°	1253.7	1284.6	1318.8	1362.8	1439.5	1528.4	1623.7	1752.9	1893.8	2019.9	2123.6
37.5°	1055.3	1050.4	1069.9	1101.8	1163.8	1235.7	1345.2	1472.9	1638.7	1787.0	1933.2
40°	936.4	933.3	947.3	976.6	1023.9	1076.5	1172.5	1284.6	1438.7	1619.8	1793.9
42.5°	854.7	856.6	864.3	885.0	917.4	960.7	1032.6	1128.0	1269.1	1439.7	1626.8
45°	755.4	760.7	769.3	779.3	797.9	833.5	873.7	941.9	1053.3	1195.7	1379.9
47.5°	683.8	684.0	692.7	701.5	712.5	732.6	765.4	808.1	886.8	1002.7	1161.0
50°	645.4	640.1	646.2	653.2	664.8	678.7	700.3	740.6	793.2	886.9	1019.3
52.5°	598.3	598.5	604.1	606.7	617.1	631.1	650.9	678.7	726.4	799.6	908.4
55°	530.9	534.7	537.9	542.5	551.8	561.9	577.3	595.9	633.1	688.0	768.5
57.5°	467.5	468.7	471.8	480.6	486.5	495.7	510.5	527.4	551.5	592.2	652.7
60°	424.1	424.1	430.3	434.1	441.9	451.2	462.8	479.1	500.7	534.0	582.8
62.5°	384.5	383.8	386.4	392.6	398.6	407.3	418.8	432.6	453.0	482.6	522.7
65°	326.6	325.1	329.7	331.2	337.4	346.0	355.3	369.9	386.2	407.9	443.4
67.5°	270.8	272.8	275.2	278.1	281.6	290.5	296.7	307.1	320.8	338.8	362.9
70°	239.9	239.9	239.9	242.3	246.9	251.6	257.7	266.2	279.4	294.9	316.5
72.5°	205.2	207.7	210.2	208.8	214.7	217.4	224.9	229.7	242.3	252.2	271.4
75°	161.0	161.0	161.0	164.8	167.1	169.5	174.1	178.7	185.0	197.3	207.4
77.5°	120.1	119.8	120.6	121.5	124.0	126.7	128.2	132.3	138.0	143.8	152.3
80°	92.9	94.4	95.2	96.7	96.7	98.3	99.1	104.5	108.4	112.2	117.6
82.5°	71.8	72.1	72.3	72.6	73.2	74.1	76.1	77.9	79.3	82.5	86.6
85°	41.8	41.0	41.0	42.5	41.8	41.8	43.3	44.8	44.8	45.6	48.0
87.5°	19.0	18.9	19.5	18.8	18.8	19.3	19.2	18.5	19.0	19.5	19.9
90°	14.2	14.0	13.7	13.5	13.3	12.9	12.3	11.7	11.1	10.5	9.6
92.5°	14.2	14.1	13.9	13.8	13.6	13.4	13.1	12.8	12.5	12.2	11.7
95°	22.6	22.8	22.9	23.0	23.1	22.9	22.3	21.7	21.1	20.6	19.7
97.5°	30.3	30.1	30.0	29.8	29.7	29.4	28.9	28.5	28.0	27.5	25.7
100°	35.3	35.0	34.8	34.6	34.3	33.8	32.8	31.9	31.0	30.0	28.1
102.5°	37.9	37.5	37.2	36.9	36.6	35.7	34.5	33.3	32.1	30.9	47.6
105°	40.1	39.6	39.1	38.7	38.2	37.3	36.1	34.7	33.4	32.1	64.1
107.5°	41.2	40.7	40.3	39.8	39.4	39.8	41.1	42.4	43.7	45.0	83.3
110°	41.6	41.2	40.7	40.2	39.8	45.3	57.1	68.8	80.5	92.2	126.0



TEST NUMBER: P331429-840

CATALOG NUMBER: SA2XXDIP-C1005D530U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	42.0	41.7	41.3	40.9	40.6	61.7	104.4	147.1	189.9	232.7	241.0
115°	43.2	51.6	60.1	68.5	77.0	108.3	162.5	216.7	270.9	325.2	322.2
117.5°	176.4	204.2	231.9	259.5	287.3	307.7	320.8	334.0	347.1	360.1	358.2
120°	321.4	337.3	353.1	368.9	384.8	391.9	390.5	389.1	387.7	386.3	384.2
122.5°	401.1	404.2	407.3	410.4	413.4	414.5	413.7	412.8	412.0	411.2	408.9
125°	450.6	450.3	449.9	449.6	449.2	448.6	447.8	447.0	446.2	445.4	443.1
127.5°	481.8	481.7	481.7	481.6	481.5	480.9	479.7	478.5	477.3	476.2	474.4
130°	501.2	501.3	501.4	501.5	501.7	501.1	499.8	498.5	497.3	495.9	494.6
132.5°	520.2	520.3	520.4	520.5	520.6	520.2	519.1	518.0	516.8	515.7	514.4
135°	547.5	547.9	548.1	548.3	548.6	548.1	546.8	545.7	544.5	543.3	542.3
137.5°	572.6	573.0	573.3	573.7	574.1	573.8	572.6	571.5	570.4	569.2	567.9
140°	588.1	588.8	589.4	589.9	590.5	590.3	589.2	588.1	587.1	586.0	584.7
142.5°	603.3	603.9	604.5	605.1	605.7	605.5	604.5	603.6	602.6	601.7	600.2
145°	624.5	625.1	625.7	626.3	626.8	626.7	625.9	625.1	624.3	623.5	621.5
147.5°	643.2	643.7	644.2	644.7	645.1	645.1	644.5	643.9	643.3	642.7	640.7
150°	654.6	655.1	655.7	656.3	656.9	656.8	656.1	655.4	654.7	654.0	652.2
152.5°	664.3	665.0	665.8	666.6	667.3	667.4	666.7	666.0	665.3	664.6	662.8
155°	677.7	678.7	679.6	680.5	681.5	681.7	681.0	680.2	679.5	678.8	677.4
157.5°	690.0	690.9	691.9	692.8	693.8	693.8	693.0	692.2	691.4	690.6	689.6
160°	697.2	698.0	698.9	699.7	700.5	700.5	699.8	699.1	698.5	697.8	697.1
162.5°	703.2	704.2	705.2	706.2	707.2	707.3	706.5	705.7	704.9	704.1	703.5
165°	712.0	712.9	713.7	714.5	715.3	715.3	714.5	713.7	712.9	712.0	711.7
167.5°	717.6	718.6	719.7	720.7	721.9	722.0	721.1	720.2	719.4	718.6	718.3
170°	720.9	722.1	723.1	724.1	725.2	725.3	724.5	723.7	722.9	722.1	721.8
172.5°	723.5	724.6	725.6	726.7	727.7	727.8	727.0	726.2	725.4	724.6	724.3
175°	725.7	726.9	728.0	729.2	730.4	730.5	729.7	728.9	728.1	727.3	727.0
177.5°	727.1	727.9	728.7	729.6	730.4	730.5	729.9	729.2	728.6	727.9	727.8
180°	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3



TEST NUMBER: P331429-840

CATALOG NUMBER: SA2XXDIP-C1005D530U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7
2.5°	2066.4	2061.4	2058.3	2047.2	2037.2	2027.3	2024.3	2025.5	2011.9	1998.8	1993.3
5°	2146.9	2131.3	2116.7	2095.8	2071.0	2043.9	2029.9	2019.1	1992.1	1962.7	1945.6
7.5°	2219.0	2196.9	2168.5	2129.2	2093.1	2050.5	2023.5	1999.4	1959.8	1918.3	1893.0
10°	2262.9	2232.7	2196.4	2148.4	2104.3	2052.4	2016.0	1979.6	1933.2	1883.7	1852.7
12.5°	2300.7	2260.0	2224.2	2162.6	2110.4	2045.6	2002.5	1951.2	1902.3	1843.4	1813.1
15°	2390.7	2315.5	2247.5	2177.8	2113.5	2023.0	1975.0	1906.1	1841.9	1769.2	1734.3
17.5°	2460.1	2375.7	2268.5	2180.0	2105.1	2004.8	1934.3	1851.8	1775.8	1692.7	1645.4
20°	2499.7	2403.0	2287.6	2182.4	2092.6	1978.1	1901.5	1817.2	1728.2	1634.5	1583.5
22.5°	2523.2	2421.6	2307.5	2173.1	2067.9	1956.4	1860.0	1767.6	1677.4	1576.3	1522.8
25°	2530.7	2437.8	2317.1	2165.5	2036.9	1910.8	1794.7	1705.0	1595.8	1501.4	1423.2
27.5°	2493.9	2427.3	2311.2	2150.8	2001.1	1853.7	1724.2	1622.6	1507.4	1404.9	1326.4
30°	2448.6	2409.9	2296.9	2136.0	1972.7	1814.0	1671.6	1556.3	1441.8	1338.1	1257.6
32.5°	2378.7	2370.4	2271.0	2115.0	1942.4	1763.9	1616.6	1500.0	1373.1	1271.2	1194.5
35°	2241.3	2278.4	2215.7	2067.9	1885.2	1692.5	1533.1	1400.0	1268.5	1170.9	1098.9
37.5°	2057.1	2149.3	2132.9	1999.0	1808.2	1614.9	1438.9	1299.7	1174.4	1075.9	1005.3
40°	1930.2	2047.8	2064.8	1946.4	1753.7	1554.8	1368.3	1229.7	1107.4	1017.7	946.4
42.5°	1793.9	1931.4	1978.1	1883.2	1694.3	1491.7	1305.1	1161.6	1040.6	953.3	890.2
45°	1565.6	1747.5	1831.9	1777.7	1595.1	1387.7	1195.7	1050.2	940.3	858.3	809.5
47.5°	1352.2	1551.0	1664.4	1645.2	1484.7	1279.3	1089.5	949.9	842.9	777.5	733.9
50°	1201.1	1405.4	1542.4	1548.6	1405.4	1201.8	1011.5	879.9	781.6	720.5	684.9
52.5°	1069.9	1264.9	1414.2	1447.0	1316.9	1121.4	941.5	810.6	724.1	667.9	636.0
55°	898.5	1063.4	1229.0	1289.3	1184.9	999.2	832.7	717.4	636.1	597.4	569.6
57.5°	747.0	884.4	1037.3	1104.1	1039.7	880.7	724.7	624.5	558.7	524.7	503.3
60°	667.1	775.5	911.7	991.4	935.6	794.1	657.8	562.6	508.5	478.3	458.2
62.5°	592.8	688.8	804.0	876.9	846.5	713.0	591.0	507.0	460.2	431.8	417.3
65°	489.1	564.9	654.0	721.2	701.1	599.8	500.0	428.0	390.8	368.4	356.8
67.5°	402.7	457.6	519.3	578.2	562.0	490.2	410.0	354.0	326.3	306.9	299.9
70°	348.3	390.0	445.0	492.2	479.1	420.2	356.8	308.8	284.8	268.5	261.6
72.5°	296.3	330.6	372.5	411.1	402.2	353.4	300.4	264.2	245.8	230.8	225.1
75°	223.7	249.9	275.5	301.0	298.7	260.8	229.8	202.0	187.3	175.7	173.4
77.5°	165.1	179.9	197.2	212.4	208.1	186.5	162.2	146.2	135.4	127.6	126.4
80°	126.1	134.6	147.0	157.8	152.5	143.2	123.8	112.2	104.5	96.7	93.6
82.5°	91.5	100.0	107.4	113.3	109.2	100.5	88.6	80.7	76.0	70.7	69.5
85°	48.0	52.6	55.7	57.3	55.7	50.3	44.8	41.8	38.0	35.6	34.8
87.5°	20.3	20.1	19.9	20.9	18.8	18.6	15.9	13.7	13.3	13.0	12.0
90°	8.7	7.8	6.8	5.7	4.3	3.1	1.8	0.5	1.8	3.1	4.3
92.5°	11.3	10.8	10.4	10.2	10.3	10.4	10.5	10.6	10.5	10.4	10.3
95°	18.9	18.1	17.3	18.8	22.6	26.6	30.4	34.2	30.4	26.6	22.6
97.5°	23.7	21.8	19.9	24.4	35.3	46.3	57.1	68.0	57.1	46.3	35.3
100°	26.1	24.0	22.1	29.1	45.1	61.2	77.3	93.3	77.3	61.2	45.1
102.5°	64.2	80.9	97.5	107.6	110.9	114.3	117.8	121.1	117.8	114.3	110.9
105°	96.1	128.1	160.1	174.3	170.8	167.2	163.7	160.2	163.7	167.2	170.8
107.5°	121.7	160.1	198.3	216.1	213.3	210.5	207.6	204.8	207.6	210.5	213.3
110°	160.0	193.8	227.6	243.3	240.9	238.4	235.9	233.5	235.9	238.4	240.9



TEST NUMBER: P331429-840

CATALOG NUMBER: SA2XXDIP-C1005D530U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	249.3	257.7	266.1	269.1	267.0	264.8	262.7	260.4	262.7	264.8	267.0
115°	319.3	316.4	313.5	311.0	309.0	307.0	305.0	303.1	305.0	307.0	309.0
117.5°	356.2	354.2	352.1	350.0	347.8	345.6	343.4	341.1	343.4	345.6	347.8
120°	382.1	380.0	377.9	376.0	374.2	372.4	370.6	368.9	370.6	372.4	374.2
122.5°	406.6	404.2	402.0	399.9	398.1	396.3	394.4	392.5	394.4	396.3	398.1
125°	440.9	438.7	436.5	434.5	433.0	431.5	430.0	428.5	430.0	431.5	433.0
127.5°	472.8	471.1	469.5	467.8	466.1	464.4	462.7	461.0	462.7	464.4	466.1
130°	493.3	492.1	490.8	489.2	487.4	485.4	483.5	481.7	483.5	485.4	487.4
132.5°	513.2	511.9	510.6	509.2	507.6	505.9	504.3	502.8	504.3	505.9	507.6
135°	541.3	540.2	539.2	537.7	535.8	533.9	532.1	530.2	532.1	533.9	535.8
137.5°	566.8	565.6	564.4	563.1	561.8	560.5	559.2	558.0	559.2	560.5	561.8
140°	583.5	582.2	580.9	579.8	578.9	577.9	576.9	576.0	576.9	577.9	578.9
142.5°	598.6	597.2	595.7	594.6	593.7	592.9	592.1	591.2	592.1	592.9	593.7
145°	619.5	617.5	615.5	614.6	614.7	614.8	614.9	615.0	614.9	614.8	614.7
147.5°	638.7	636.7	634.8	634.0	634.5	634.9	635.3	635.8	635.3	634.9	634.5
150°	650.3	648.4	646.5	646.0	646.8	647.6	648.4	649.2	648.4	647.6	646.8
152.5°	661.1	659.2	657.4	657.0	657.9	658.8	659.7	660.7	659.7	658.8	657.9
155°	676.0	674.6	673.2	673.0	674.1	675.1	676.2	677.2	676.2	675.1	674.1
157.5°	688.6	687.6	686.7	686.6	687.5	688.4	689.3	690.1	689.3	688.4	687.5
160°	696.4	695.7	695.0	695.0	695.7	696.4	697.1	697.8	697.1	696.4	695.7
162.5°	702.9	702.3	701.7	701.8	702.4	703.1	703.8	704.5	703.8	703.1	702.4
165°	711.2	710.9	710.6	710.7	711.4	712.2	712.9	713.6	712.9	712.2	711.4
167.5°	718.0	717.6	717.3	717.5	718.2	718.9	719.6	720.3	719.6	718.9	718.2
170°	721.5	721.3	721.0	721.3	722.1	722.8	723.5	724.1	723.5	722.8	722.1
172.5°	724.1	723.9	723.6	723.9	724.6	725.3	726.0	726.7	726.0	725.3	724.6
175°	726.8	726.6	726.4	726.6	727.5	728.3	729.1	729.9	729.1	728.3	727.5
177.5°	727.7	727.6	727.5	727.8	728.5	729.1	729.8	730.4	729.8	729.1	728.5
180°	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3



TEST NUMBER: P331429-840

CATALOG NUMBER: SA2XXDIP-C1005D530U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7
2.5°	1987.1	1983.4	1970.3	1963.6	1952.5	1941.9	1935.1	1938.2	1940.7	1939.4	1937.5
5°	1930.2	1915.4	1893.0	1873.6	1859.7	1834.2	1823.3	1818.0	1813.3	1807.9	1802.4
7.5°	1862.3	1839.2	1807.0	1779.4	1753.3	1721.6	1703.5	1692.7	1681.5	1669.3	1658.5
10°	1814.0	1781.5	1747.5	1708.8	1677.9	1649.2	1623.7	1606.6	1591.1	1576.5	1565.6
12.5°	1763.3	1725.9	1683.7	1630.8	1596.7	1555.7	1551.9	1521.9	1497.6	1488.5	1475.8
15°	1682.4	1629.8	1576.5	1513.8	1486.7	1449.6	1426.3	1403.1	1382.2	1367.5	1363.6
17.5°	1590.7	1522.6	1469.5	1424.4	1380.1	1342.0	1320.6	1302.0	1284.9	1265.2	1262.5
20°	1520.8	1461.9	1403.9	1364.4	1318.8	1280.0	1253.7	1235.2	1220.4	1208.8	1198.8
22.5°	1454.5	1390.1	1337.0	1293.8	1248.8	1217.5	1196.8	1178.8	1166.6	1153.8	1144.3
25°	1348.2	1297.9	1239.8	1191.0	1153.9	1133.8	1116.7	1101.3	1093.6	1085.0	1074.2
27.5°	1255.2	1199.2	1144.9	1107.1	1074.5	1056.7	1044.6	1034.1	1026.8	1021.9	1015.7
30°	1189.5	1133.0	1090.5	1053.3	1026.2	1008.5	1000.7	994.5	985.9	982.9	979.8
32.5°	1126.3	1075.4	1039.1	1006.8	981.0	969.4	962.3	956.7	950.1	947.0	940.8
35°	1037.0	994.5	958.9	941.1	920.2	910.1	904.7	897.0	890.8	887.7	886.9
37.5°	953.0	916.0	892.6	869.7	860.9	854.7	847.3	842.0	840.2	839.7	838.9
40°	898.5	868.3	847.5	828.9	825.0	815.7	809.5	804.9	804.9	805.7	804.9
42.5°	849.0	821.9	803.4	787.4	782.8	777.3	771.1	770.8	772.0	774.7	772.0
45°	774.0	754.6	741.4	733.7	725.2	719.7	718.9	721.2	722.1	722.9	725.2
47.5°	704.9	692.1	680.1	671.6	667.9	666.9	666.0	670.0	673.8	675.2	678.7
50°	664.0	649.3	639.2	633.8	630.8	629.1	630.8	635.4	638.4	642.4	644.7
52.5°	618.2	607.8	600.9	596.7	595.4	596.4	596.7	602.0	606.9	608.3	609.4
55°	554.9	547.1	545.6	538.7	541.7	541.0	544.8	548.0	552.6	557.2	558.0
57.5°	491.7	485.5	481.4	482.0	482.9	486.4	489.6	495.0	500.0	504.9	505.3
60°	449.7	446.6	444.2	444.2	445.8	450.4	454.2	459.7	462.8	465.9	468.2
62.5°	411.2	408.2	405.9	407.1	411.1	413.8	418.4	421.3	424.4	427.5	428.6
65°	350.6	349.0	351.3	352.9	353.7	357.6	362.9	365.3	368.4	369.9	375.4
67.5°	294.7	295.0	294.7	296.9	301.3	302.3	307.4	312.9	313.5	316.4	319.9
70°	256.9	258.5	260.0	261.6	265.5	267.0	270.8	273.2	276.3	278.6	280.9
72.5°	222.3	222.6	224.1	223.8	227.0	230.5	233.7	236.0	239.1	242.1	244.4
75°	171.1	171.1	172.6	173.4	177.2	181.1	180.4	181.9	185.0	188.0	189.7
77.5°	124.9	123.2	124.9	125.7	126.9	130.2	130.8	133.0	136.5	135.4	137.1
80°	95.2	92.9	95.2	95.9	95.9	99.9	99.9	101.4	103.7	101.4	103.7
82.5°	68.0	66.9	68.6	68.8	70.0	70.1	71.4	71.7	74.0	72.9	74.0
85°	34.0	33.3	34.0	33.3	34.0	34.8	34.8	34.0	34.0	35.6	33.3
87.5°	11.6	11.3	10.8	11.0	10.6	10.2	9.7	9.8	9.9	8.8	8.9
90°	5.7	6.8	7.8	8.7	9.6	10.5	11.1	11.7	12.3	12.9	13.3
92.5°	10.2	10.4	10.8	11.3	11.7	12.2	12.5	12.8	13.1	13.4	13.6
95°	18.8	17.3	18.1	18.9	19.7	20.6	21.1	21.7	22.3	22.9	23.1
97.5°	24.4	19.9	21.8	23.7	25.7	27.5	28.0	28.5	28.9	29.4	29.7
100°	29.1	22.1	24.0	26.1	28.1	30.0	31.0	31.9	32.8	33.8	34.3
102.5°	107.6	97.5	80.9	64.2	47.6	30.9	32.1	33.3	34.5	35.7	36.6
105°	174.3	160.1	128.1	96.1	64.1	32.1	33.4	34.7	36.1	37.3	38.2
107.5°	216.1	198.3	160.1	121.7	83.3	45.0	43.7	42.4	41.1	39.8	39.4
110°	243.3	227.6	193.8	160.0	126.0	92.2	80.5	68.8	57.1	45.3	39.8



TEST NUMBER: P331429-840

CATALOG NUMBER: SA2XXDIP-C1005D530U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	269.1	266.1	257.7	249.3	241.0	232.7	189.9	147.1	104.4	61.7	40.6
115°	311.0	313.5	316.4	319.3	322.2	325.2	270.9	216.7	162.5	108.3	77.0
117.5°	350.0	352.1	354.2	356.2	358.2	360.1	347.1	334.0	320.8	307.7	287.3
120°	376.0	377.9	380.0	382.1	384.2	386.3	387.7	389.1	390.5	391.9	384.8
122.5°	399.9	402.0	404.2	406.6	408.9	411.2	412.0	412.8	413.7	414.5	413.4
125°	434.5	436.5	438.7	440.9	443.1	445.4	446.2	447.0	447.8	448.6	449.2
127.5°	467.8	469.5	471.1	472.8	474.4	476.2	477.3	478.5	479.7	480.9	481.5
130°	489.2	490.8	492.1	493.3	494.6	495.9	497.3	498.5	499.8	501.1	501.7
132.5°	509.2	510.6	511.9	513.2	514.4	515.7	516.8	518.0	519.1	520.2	520.6
135°	537.7	539.2	540.2	541.3	542.3	543.3	544.5	545.7	546.8	548.1	548.6
137.5°	563.1	564.4	565.6	566.8	567.9	569.2	570.4	571.5	572.6	573.8	574.1
140°	579.8	580.9	582.2	583.5	584.7	586.0	587.1	588.1	589.2	590.3	590.5
142.5°	594.6	595.7	597.2	598.6	600.2	601.7	602.6	603.6	604.5	605.5	605.7
145°	614.6	615.5	617.5	619.5	621.5	623.5	624.3	625.1	625.9	626.7	626.8
147.5°	634.0	634.8	636.7	638.7	640.7	642.7	643.3	643.9	644.5	645.1	645.1
150°	646.0	646.5	648.4	650.3	652.2	654.0	654.7	655.4	656.1	656.8	656.9
152.5°	657.0	657.4	659.2	661.1	662.8	664.6	665.3	666.0	666.7	667.4	667.3
155°	673.0	673.2	674.6	676.0	677.4	678.8	679.5	680.2	681.0	681.7	681.5
157.5°	686.6	686.7	687.6	688.6	689.6	690.6	691.4	692.2	693.0	693.8	693.8
160°	695.0	695.0	695.7	696.4	697.1	697.8	698.5	699.1	699.8	700.5	700.5
162.5°	701.8	701.7	702.3	702.9	703.5	704.1	704.9	705.7	706.5	707.3	707.2
165°	710.7	710.6	710.9	711.2	711.7	712.0	712.9	713.7	714.5	715.3	715.3
167.5°	717.5	717.3	717.6	718.0	718.3	718.6	719.4	720.2	721.1	722.0	721.9
170°	721.3	721.0	721.3	721.5	721.8	722.1	722.9	723.7	724.5	725.3	725.2
172.5°	723.9	723.6	723.9	724.1	724.3	724.6	725.4	726.2	727.0	727.8	727.7
175°	726.6	726.4	726.6	726.8	727.0	727.3	728.1	728.9	729.7	730.5	730.4
177.5°	727.8	727.5	727.6	727.7	727.8	727.9	728.6	729.2	729.9	730.5	730.4
180°	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3



TEST NUMBER: P331429-840

CATALOG NUMBER: SA2XXDIP-C1005D530U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7
2.5°	1931.4	1930.2	1930.2	1924.6	1930.2	1930.2	1931.4	1937.5	1939.4	1940.7	1938.2
5°	1791.6	1789.3	1785.4	1789.3	1785.4	1789.3	1791.6	1802.4	1807.9	1813.3	1818.0
7.5°	1653.4	1644.1	1642.7	1633.6	1642.7	1644.1	1653.4	1658.5	1669.3	1681.5	1692.7
10°	1552.5	1546.3	1545.5	1530.8	1545.5	1546.3	1552.5	1565.6	1576.5	1591.1	1606.6
12.5°	1475.7	1460.9	1463.8	1455.2	1463.8	1460.9	1475.7	1475.8	1488.5	1497.6	1521.9
15°	1342.7	1342.7	1339.7	1326.5	1339.7	1342.7	1342.7	1363.6	1367.5	1382.2	1403.1
17.5°	1247.3	1245.7	1238.3	1241.9	1238.3	1245.7	1247.3	1262.5	1265.2	1284.9	1302.0
20°	1190.2	1185.7	1176.4	1176.4	1176.4	1185.7	1190.2	1198.8	1208.8	1220.4	1235.2
22.5°	1136.4	1136.1	1126.2	1129.3	1126.2	1136.1	1136.4	1144.3	1153.8	1166.6	1178.8
25°	1073.4	1067.2	1062.6	1064.9	1062.6	1067.2	1073.4	1074.2	1085.0	1093.6	1101.3
27.5°	1013.7	1010.3	1010.0	1003.6	1010.0	1010.3	1013.7	1015.7	1021.9	1026.8	1034.1
30°	979.0	971.3	972.8	969.0	972.8	971.3	979.0	979.8	982.9	985.9	994.5
32.5°	939.4	936.5	935.0	931.8	935.0	936.5	939.4	940.8	947.0	950.1	956.7
35°	885.3	886.2	882.2	883.8	882.2	886.2	885.3	886.9	887.7	890.8	897.0
37.5°	838.2	840.6	838.8	839.2	838.8	840.6	838.2	838.9	839.7	840.2	842.0
40°	807.2	807.2	807.2	809.5	807.2	807.2	807.2	804.9	805.7	804.9	804.9
42.5°	777.5	776.3	775.0	774.9	775.0	776.3	777.5	772.0	774.7	772.0	770.8
45°	726.7	729.0	729.8	725.9	729.8	729.0	726.7	725.2	722.9	722.1	721.2
47.5°	680.8	681.1	680.8	684.2	680.8	681.1	680.8	678.7	675.2	673.8	670.0
50°	648.5	647.0	648.5	647.0	648.5	647.0	648.5	644.7	642.4	638.4	635.4
52.5°	614.5	614.8	613.9	613.6	613.9	614.8	614.5	609.4	608.3	606.9	602.0
55°	561.1	562.6	561.9	561.9	561.9	562.6	561.1	558.0	557.2	552.6	548.0
57.5°	505.8	507.3	508.3	504.9	508.3	507.3	505.8	505.3	504.9	500.0	495.0
60°	467.5	471.3	470.5	469.0	470.5	471.3	467.5	468.2	465.9	462.8	459.7
62.5°	432.1	433.5	433.4	433.1	433.4	433.5	432.1	428.6	427.5	424.4	421.3
65°	377.7	379.2	376.9	379.2	376.9	379.2	377.7	375.4	369.9	368.4	365.3
67.5°	319.0	319.5	321.1	322.2	321.1	319.5	319.0	319.9	316.4	313.5	312.9
70°	282.5	281.8	284.1	286.4	284.1	281.8	282.5	280.9	278.6	276.3	273.2
72.5°	244.1	245.8	245.0	246.7	245.0	245.8	244.1	244.4	242.1	239.1	236.0
75°	188.0	190.4	189.7	192.0	189.7	190.4	188.0	189.7	188.0	185.0	181.9
77.5°	135.9	136.2	135.9	137.1	135.9	136.2	135.9	137.1	135.4	136.5	133.0
80°	103.7	102.2	100.6	103.7	100.6	102.2	103.7	103.7	101.4	103.7	101.4
82.5°	72.1	73.0	71.5	71.5	71.5	73.0	72.1	74.0	72.9	74.0	71.7
85°	33.3	32.5	31.0	31.0	31.0	32.5	33.3	33.3	35.6	34.0	34.0
87.5°	8.9	8.3	8.4	7.8	8.4	8.3	8.9	8.9	8.8	9.9	9.8
90°	13.5	13.7	14.0	14.2	14.0	13.7	13.5	13.3	12.9	12.3	11.7
92.5°	13.8	13.9	14.1	14.2	14.1	13.9	13.8	13.6	13.4	13.1	12.8
95°	23.0	22.9	22.8	22.6	22.8	22.9	23.0	23.1	22.9	22.3	21.7
97.5°	29.8	30.0	30.1	30.3	30.1	30.0	29.8	29.7	29.4	28.9	28.5
100°	34.6	34.8	35.0	35.3	35.0	34.8	34.6	34.3	33.8	32.8	31.9
102.5°	36.9	37.2	37.5	37.9	37.5	37.2	36.9	36.6	35.7	34.5	33.3
105°	38.7	39.1	39.6	40.1	39.6	39.1	38.7	38.2	37.3	36.1	34.7
107.5°	39.8	40.3	40.7	41.2	40.7	40.3	39.8	39.4	39.8	41.1	42.4
110°	40.2	40.7	41.2	41.6	41.2	40.7	40.2	39.8	45.3	57.1	68.8



TEST NUMBER: P331429-840

CATALOG NUMBER: SA2XXDIP-C1005D530U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	40.9	41.3	41.7	42.0	41.7	41.3	40.9	40.6	61.7	104.4	147.1
115°	68.5	60.1	51.6	43.2	51.6	60.1	68.5	77.0	108.3	162.5	216.7
117.5°	259.5	231.9	204.2	176.4	204.2	231.9	259.5	287.3	307.7	320.8	334.0
120°	368.9	353.1	337.3	321.4	337.3	353.1	368.9	384.8	391.9	390.5	389.1
122.5°	410.4	407.3	404.2	401.1	404.2	407.3	410.4	413.4	414.5	413.7	412.8
125°	449.6	449.9	450.3	450.6	450.3	449.9	449.6	449.2	448.6	447.8	447.0
127.5°	481.6	481.7	481.7	481.8	481.7	481.7	481.6	481.5	480.9	479.7	478.5
130°	501.5	501.4	501.3	501.2	501.3	501.4	501.5	501.7	501.1	499.8	498.5
132.5°	520.5	520.4	520.3	520.2	520.3	520.4	520.5	520.6	520.2	519.1	518.0
135°	548.3	548.1	547.9	547.5	547.9	548.1	548.3	548.6	548.1	546.8	545.7
137.5°	573.7	573.3	573.0	572.6	573.0	573.3	573.7	574.1	573.8	572.6	571.5
140°	589.9	589.4	588.8	588.1	588.8	589.4	589.9	590.5	590.3	589.2	588.1
142.5°	605.1	604.5	603.9	603.3	603.9	604.5	605.1	605.7	605.5	604.5	603.6
145°	626.3	625.7	625.1	624.5	625.1	625.7	626.3	626.8	626.7	625.9	625.1
147.5°	644.7	644.2	643.7	643.2	643.7	644.2	644.7	645.1	645.1	644.5	643.9
150°	656.3	655.7	655.1	654.6	655.1	655.7	656.3	656.9	656.8	656.1	655.4
152.5°	666.6	665.8	665.0	664.3	665.0	665.8	666.6	667.3	667.4	666.7	666.0
155°	680.5	679.6	678.7	677.7	678.7	679.6	680.5	681.5	681.7	681.0	680.2
157.5°	692.8	691.9	690.9	690.0	690.9	691.9	692.8	693.8	693.8	693.0	692.2
160°	699.7	698.9	698.0	697.2	698.0	698.9	699.7	700.5	700.5	699.8	699.1
162.5°	706.2	705.2	704.2	703.2	704.2	705.2	706.2	707.2	707.3	706.5	705.7
165°	714.5	713.7	712.9	712.0	712.9	713.7	714.5	715.3	715.3	714.5	713.7
167.5°	720.7	719.7	718.6	717.6	718.6	719.7	720.7	721.9	722.0	721.1	720.2
170°	724.1	723.1	722.1	720.9	722.1	723.1	724.1	725.2	725.3	724.5	723.7
172.5°	726.7	725.6	724.6	723.5	724.6	725.6	726.7	727.7	727.8	727.0	726.2
175°	729.2	728.0	726.9	725.7	726.9	728.0	729.2	730.4	730.5	729.7	728.9
177.5°	729.6	728.7	727.9	727.1	727.9	728.7	729.6	730.4	730.5	729.9	729.2
180°	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3



TEST NUMBER: P331429-840

CATALOG NUMBER: SA2XXDIP-C1005D530U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7
2.5°	1935.1	1941.9	1952.5	1963.6	1970.3	1983.4	1987.1	1993.3	1998.8	2011.9	2025.5
5°	1823.3	1834.2	1859.7	1873.6	1893.0	1915.4	1930.2	1945.6	1962.7	1992.1	2019.1
7.5°	1703.5	1721.6	1753.3	1779.4	1807.0	1839.2	1862.3	1893.0	1918.3	1959.8	1999.4
10°	1623.7	1649.2	1677.9	1708.8	1747.5	1781.5	1814.0	1852.7	1883.7	1933.2	1979.6
12.5°	1551.9	1555.7	1596.7	1630.8	1683.7	1725.9	1763.3	1813.1	1843.4	1902.3	1951.2
15°	1426.3	1449.6	1486.7	1513.8	1576.5	1629.8	1682.4	1734.3	1769.2	1841.9	1906.1
17.5°	1320.6	1342.0	1380.1	1424.4	1469.5	1522.6	1590.7	1645.4	1692.7	1775.8	1851.8
20°	1253.7	1280.0	1318.8	1364.4	1403.9	1461.9	1520.8	1583.5	1634.5	1728.2	1817.2
22.5°	1196.8	1217.5	1248.8	1293.8	1337.0	1390.1	1454.5	1522.8	1576.3	1677.4	1767.6
25°	1116.7	1133.8	1153.9	1191.0	1239.8	1297.9	1348.2	1423.2	1501.4	1595.8	1705.0
27.5°	1044.6	1056.7	1074.5	1107.1	1144.9	1199.2	1255.2	1326.4	1404.9	1507.4	1622.6
30°	1000.7	1008.5	1026.2	1053.3	1090.5	1133.0	1189.5	1257.6	1338.1	1441.8	1556.3
32.5°	962.3	969.4	981.0	1006.8	1039.1	1075.4	1126.3	1194.5	1271.2	1373.1	1500.0
35°	904.7	910.1	920.2	941.1	958.9	994.5	1037.0	1098.9	1170.9	1268.5	1400.0
37.5°	847.3	854.7	860.9	869.7	892.6	916.0	953.0	1005.3	1075.9	1174.4	1299.7
40°	809.5	815.7	825.0	828.9	847.5	868.3	898.5	946.4	1017.7	1107.4	1229.7
42.5°	771.1	777.3	782.8	787.4	803.4	821.9	849.0	890.2	953.3	1040.6	1161.6
45°	718.9	719.7	725.2	733.7	741.4	754.6	774.0	809.5	858.3	940.3	1050.2
47.5°	666.0	666.9	667.9	671.6	680.1	692.1	704.9	733.9	777.5	842.9	949.9
50°	630.8	629.1	630.8	633.8	639.2	649.3	664.0	684.9	720.5	781.6	879.9
52.5°	596.7	596.4	595.4	596.7	600.9	607.8	618.2	636.0	667.9	724.1	810.6
55°	544.8	541.0	541.7	538.7	545.6	547.1	554.9	569.6	597.4	636.1	717.4
57.5°	489.6	486.4	482.9	482.0	481.4	485.5	491.7	503.3	524.7	558.7	624.5
60°	454.2	450.4	445.8	444.2	444.2	446.6	449.7	458.2	478.3	508.5	562.6
62.5°	418.4	413.8	411.1	407.1	405.9	408.2	411.2	417.3	431.8	460.2	507.0
65°	362.9	357.6	353.7	352.9	351.3	349.0	350.6	356.8	368.4	390.8	428.0
67.5°	307.4	302.3	301.3	296.9	294.7	295.0	294.7	299.9	306.9	326.3	354.0
70°	270.8	267.0	265.5	261.6	260.0	258.5	256.9	261.6	268.5	284.8	308.8
72.5°	233.7	230.5	227.0	223.8	224.1	222.6	222.3	225.1	230.8	245.8	264.2
75°	180.4	181.1	177.2	173.4	172.6	171.1	171.1	173.4	175.7	187.3	202.0
77.5°	130.8	130.2	126.9	125.7	124.9	123.2	124.9	126.4	127.6	135.4	146.2
80°	99.9	99.9	95.9	95.9	95.2	92.9	95.2	93.6	96.7	104.5	112.2
82.5°	71.4	70.1	70.0	68.8	68.6	66.9	68.0	69.5	70.7	76.0	80.7
85°	34.8	34.8	34.0	33.3	34.0	33.3	34.0	34.8	35.6	38.0	41.8
87.5°	9.7	10.2	10.6	11.0	10.8	11.3	11.6	12.0	13.0	13.3	13.7
90°	11.1	10.5	9.6	8.7	7.8	6.8	5.7	4.3	3.1	1.8	0.5
92.5°	12.5	12.2	11.7	11.3	10.8	10.4	10.2	10.3	10.4	10.5	10.6
95°	21.1	20.6	19.7	18.9	18.1	17.3	18.8	22.6	26.6	30.4	34.2
97.5°	28.0	27.5	25.7	23.7	21.8	19.9	24.4	35.3	46.3	57.1	68.0
100°	31.0	30.0	28.1	26.1	24.0	22.1	29.1	45.1	61.2	77.3	93.3
102.5°	32.1	30.9	47.6	64.2	80.9	97.5	107.6	110.9	114.3	117.8	121.1
105°	33.4	32.1	64.1	96.1	128.1	160.1	174.3	170.8	167.2	163.7	160.2
107.5°	43.7	45.0	83.3	121.7	160.1	198.3	216.1	213.3	210.5	207.6	204.8
110°	80.5	92.2	126.0	160.0	193.8	227.6	243.3	240.9	238.4	235.9	233.5



TEST NUMBER: P331429-840

CATALOG NUMBER: SA2XXDIP-C1005D530U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	189.9	232.7	241.0	249.3	257.7	266.1	269.1	267.0	264.8	262.7	260.4
115°	270.9	325.2	322.2	319.3	316.4	313.5	311.0	309.0	307.0	305.0	303.1
117.5°	347.1	360.1	358.2	356.2	354.2	352.1	350.0	347.8	345.6	343.4	341.1
120°	387.7	386.3	384.2	382.1	380.0	377.9	376.0	374.2	372.4	370.6	368.9
122.5°	412.0	411.2	408.9	406.6	404.2	402.0	399.9	398.1	396.3	394.4	392.5
125°	446.2	445.4	443.1	440.9	438.7	436.5	434.5	433.0	431.5	430.0	428.5
127.5°	477.3	476.2	474.4	472.8	471.1	469.5	467.8	466.1	464.4	462.7	461.0
130°	497.3	495.9	494.6	493.3	492.1	490.8	489.2	487.4	485.4	483.5	481.7
132.5°	516.8	515.7	514.4	513.2	511.9	510.6	509.2	507.6	505.9	504.3	502.8
135°	544.5	543.3	542.3	541.3	540.2	539.2	537.7	535.8	533.9	532.1	530.2
137.5°	570.4	569.2	567.9	566.8	565.6	564.4	563.1	561.8	560.5	559.2	558.0
140°	587.1	586.0	584.7	583.5	582.2	580.9	579.8	578.9	577.9	576.9	576.0
142.5°	602.6	601.7	600.2	598.6	597.2	595.7	594.6	593.7	592.9	592.1	591.2
145°	624.3	623.5	621.5	619.5	617.5	615.5	614.6	614.7	614.8	614.9	615.0
147.5°	643.3	642.7	640.7	638.7	636.7	634.8	634.0	634.5	634.9	635.3	635.8
150°	654.7	654.0	652.2	650.3	648.4	646.5	646.0	646.8	647.6	648.4	649.2
152.5°	665.3	664.6	662.8	661.1	659.2	657.4	657.0	657.9	658.8	659.7	660.7
155°	679.5	678.8	677.4	676.0	674.6	673.2	673.0	674.1	675.1	676.2	677.2
157.5°	691.4	690.6	689.6	688.6	687.6	686.7	686.6	687.5	688.4	689.3	690.1
160°	698.5	697.8	697.1	696.4	695.7	695.0	695.0	695.7	696.4	697.1	697.8
162.5°	704.9	704.1	703.5	702.9	702.3	701.7	701.8	702.4	703.1	703.8	704.5
165°	712.9	712.0	711.7	711.2	710.9	710.6	710.7	711.4	712.2	712.9	713.6
167.5°	719.4	718.6	718.3	718.0	717.6	717.3	717.5	718.2	718.9	719.6	720.3
170°	722.9	722.1	721.8	721.5	721.3	721.0	721.3	722.1	722.8	723.5	724.1
172.5°	725.4	724.6	724.3	724.1	723.9	723.6	723.9	724.6	725.3	726.0	726.7
175°	728.1	727.3	727.0	726.8	726.6	726.4	726.6	727.5	728.3	729.1	729.9
177.5°	728.6	727.9	727.8	727.7	727.6	727.5	727.8	728.5	729.1	729.8	730.4
180°	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3



TEST NUMBER: P331429-840

CATALOG NUMBER: SA2XXDIP-C1005D530U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7
2.5°	2024.3	2027.3	2037.2	2047.2	2058.3	2061.4	2066.4	2062.0	2060.7	2072.5	2081.2
5°	2029.9	2043.9	2071.0	2095.8	2116.7	2131.3	2146.9	2153.0	2164.6	2180.9	2201.0
7.5°	2023.5	2050.5	2093.1	2129.2	2168.5	2196.9	2219.0	2237.9	2260.8	2291.6	2325.1
10°	2016.0	2052.4	2104.3	2148.4	2196.4	2232.7	2262.9	2292.3	2326.4	2368.9	2413.1
12.5°	2002.5	2045.6	2110.4	2162.6	2224.2	2260.0	2300.7	2364.2	2400.7	2459.9	2522.0
15°	1975.0	2023.0	2113.5	2177.8	2247.5	2315.5	2390.7	2450.9	2511.3	2546.2	2633.6
17.5°	1934.3	2004.8	2105.1	2180.0	2268.5	2375.7	2460.1	2528.5	2598.2	2654.6	2698.5
20°	1901.5	1978.1	2092.6	2182.4	2287.6	2403.0	2499.7	2569.4	2629.8	2677.0	2704.0
22.5°	1860.0	1956.4	2067.9	2173.1	2307.5	2421.6	2523.2	2578.1	2628.5	2651.6	2661.9
25°	1794.7	1910.8	2036.9	2165.5	2317.1	2437.8	2530.7	2563.9	2578.7	2556.3	2519.1
27.5°	1724.2	1853.7	2001.1	2150.8	2311.2	2427.3	2493.9	2488.6	2463.7	2391.1	2333.0
30°	1671.6	1814.0	1972.7	2136.0	2296.9	2409.9	2448.6	2409.9	2353.5	2272.2	2189.4
32.5°	1616.6	1763.9	1942.4	2115.0	2271.0	2370.4	2378.7	2312.2	2224.7	2132.3	2029.0
35°	1533.1	1692.5	1885.2	2067.9	2215.7	2278.4	2241.3	2123.6	2019.9	1893.8	1752.9
37.5°	1438.9	1614.9	1808.2	1999.0	2132.9	2149.3	2057.1	1933.2	1787.0	1638.7	1472.9
40°	1368.3	1554.8	1753.7	1946.4	2064.8	2047.8	1930.2	1793.9	1619.8	1438.7	1284.6
42.5°	1305.1	1491.7	1694.3	1883.2	1978.1	1931.4	1793.9	1626.8	1439.7	1269.1	1128.0
45°	1195.7	1387.7	1595.1	1777.7	1831.9	1747.5	1565.6	1379.9	1195.7	1053.3	941.9
47.5°	1089.5	1279.3	1484.7	1645.2	1664.4	1551.0	1352.2	1161.0	1002.7	886.8	808.1
50°	1011.5	1201.8	1405.4	1548.6	1542.4	1405.4	1201.1	1019.3	886.9	793.2	740.6
52.5°	941.5	1121.4	1316.9	1447.0	1414.2	1264.9	1069.9	908.4	799.6	726.4	678.7
55°	832.7	999.2	1184.9	1289.3	1229.0	1063.4	898.5	768.5	688.0	633.1	595.9
57.5°	724.7	880.7	1039.7	1104.1	1037.3	884.4	747.0	652.7	592.2	551.5	527.4
60°	657.8	794.1	935.6	991.4	911.7	775.5	667.1	582.8	534.0	500.7	479.1
62.5°	591.0	713.0	846.5	876.9	804.0	688.8	592.8	522.7	482.6	453.0	432.6
65°	500.0	599.8	701.1	721.2	654.0	564.9	489.1	443.4	407.9	386.2	369.9
67.5°	410.0	490.2	562.0	578.2	519.3	457.6	402.7	362.9	338.8	320.8	307.1
70°	356.8	420.2	479.1	492.2	445.0	390.0	348.3	316.5	294.9	279.4	266.2
72.5°	300.4	353.4	402.2	411.1	372.5	330.6	296.3	271.4	252.2	242.3	229.7
75°	229.8	260.8	298.7	301.0	275.5	249.9	223.7	207.4	197.3	185.0	178.7
77.5°	162.2	186.5	208.1	212.4	197.2	179.9	165.1	152.3	143.8	138.0	132.3
80°	123.8	143.2	152.5	157.8	147.0	134.6	126.1	117.6	112.2	108.4	104.5
82.5°	88.6	100.5	109.2	113.3	107.4	100.0	91.5	86.6	82.5	79.3	77.9
85°	44.8	50.3	55.7	57.3	55.7	52.6	48.0	48.0	45.6	44.8	44.8
87.5°	15.9	18.6	18.8	20.9	19.9	20.1	20.3	19.9	19.5	19.0	18.5
90°	1.8	3.1	4.3	5.7	6.8	7.8	8.7	9.6	10.5	11.1	11.7
92.5°	10.5	10.4	10.3	10.2	10.4	10.8	11.3	11.7	12.2	12.5	12.8
95°	30.4	26.6	22.6	18.8	17.3	18.1	18.9	19.7	20.6	21.1	21.7
97.5°	57.1	46.3	35.3	24.4	19.9	21.8	23.7	25.7	27.5	28.0	28.5
100°	77.3	61.2	45.1	29.1	22.1	24.0	26.1	28.1	30.0	31.0	31.9
102.5°	117.8	114.3	110.9	107.6	97.5	80.9	64.2	47.6	30.9	32.1	33.3
105°	163.7	167.2	170.8	174.3	160.1	128.1	96.1	64.1	32.1	33.4	34.7
107.5°	207.6	210.5	213.3	216.1	198.3	160.1	121.7	83.3	45.0	43.7	42.4
110°	235.9	238.4	240.9	243.3	227.6	193.8	160.0	126.0	92.2	80.5	68.8



TEST NUMBER: P331429-840

CATALOG NUMBER: SA2XXDIP-C1005D530U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	262.7	264.8	267.0	269.1	266.1	257.7	249.3	241.0	232.7	189.9	147.1
115°	305.0	307.0	309.0	311.0	313.5	316.4	319.3	322.2	325.2	270.9	216.7
117.5°	343.4	345.6	347.8	350.0	352.1	354.2	356.2	358.2	360.1	347.1	334.0
120°	370.6	372.4	374.2	376.0	377.9	380.0	382.1	384.2	386.3	387.7	389.1
122.5°	394.4	396.3	398.1	399.9	402.0	404.2	406.6	408.9	411.2	412.0	412.8
125°	430.0	431.5	433.0	434.5	436.5	438.7	440.9	443.1	445.4	446.2	447.0
127.5°	462.7	464.4	466.1	467.8	469.5	471.1	472.8	474.4	476.2	477.3	478.5
130°	483.5	485.4	487.4	489.2	490.8	492.1	493.3	494.6	495.9	497.3	498.5
132.5°	504.3	505.9	507.6	509.2	510.6	511.9	513.2	514.4	515.7	516.8	518.0
135°	532.1	533.9	535.8	537.7	539.2	540.2	541.3	542.3	543.3	544.5	545.7
137.5°	559.2	560.5	561.8	563.1	564.4	565.6	566.8	567.9	569.2	570.4	571.5
140°	576.9	577.9	578.9	579.8	580.9	582.2	583.5	584.7	586.0	587.1	588.1
142.5°	592.1	592.9	593.7	594.6	595.7	597.2	598.6	600.2	601.7	602.6	603.6
145°	614.9	614.8	614.7	614.6	615.5	617.5	619.5	621.5	623.5	624.3	625.1
147.5°	635.3	634.9	634.5	634.0	634.8	636.7	638.7	640.7	642.7	643.3	643.9
150°	648.4	647.6	646.8	646.0	646.5	648.4	650.3	652.2	654.0	654.7	655.4
152.5°	659.7	658.8	657.9	657.0	657.4	659.2	661.1	662.8	664.6	665.3	666.0
155°	676.2	675.1	674.1	673.0	673.2	674.6	676.0	677.4	678.8	679.5	680.2
157.5°	689.3	688.4	687.5	686.6	686.7	687.6	688.6	689.6	690.6	691.4	692.2
160°	697.1	696.4	695.7	695.0	695.0	695.7	696.4	697.1	697.8	698.5	699.1
162.5°	703.8	703.1	702.4	701.8	701.7	702.3	702.9	703.5	704.1	704.9	705.7
165°	712.9	712.2	711.4	710.7	710.6	710.9	711.2	711.7	712.0	712.9	713.7
167.5°	719.6	718.9	718.2	717.5	717.3	717.6	718.0	718.3	718.6	719.4	720.2
170°	723.5	722.8	722.1	721.3	721.0	721.3	721.5	721.8	722.1	722.9	723.7
172.5°	726.0	725.3	724.6	723.9	723.6	723.9	724.1	724.3	724.6	725.4	726.2
175°	729.1	728.3	727.5	726.6	726.4	726.6	726.8	727.0	727.3	728.1	728.9
177.5°	729.8	729.1	728.5	727.8	727.5	727.6	727.7	727.8	727.9	728.6	729.2
180°	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3



TEST NUMBER: P331429-840

CATALOG NUMBER: SA2XXDIP-C1005D530U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7
2.5°	2088.6	2097.3	2097.3	2098.5	2108.4	2107.2	2106.6
5°	2222.7	2235.8	2237.4	2251.3	2260.6	2257.5	2249.0
7.5°	2349.1	2373.6	2392.2	2402.6	2414.8	2422.4	2418.9
10°	2449.4	2485.1	2506.7	2521.4	2539.2	2552.3	2547.7
12.5°	2540.4	2582.8	2612.6	2637.8	2640.1	2657.0	2645.5
15°	2682.4	2727.2	2731.9	2750.5	2765.2	2763.6	2764.4
17.5°	2729.3	2743.7	2746.6	2747.0	2747.2	2741.8	2730.1
20°	2712.6	2707.1	2694.0	2683.9	2666.1	2663.8	2648.4
22.5°	2633.3	2616.2	2583.1	2561.3	2533.7	2526.4	2522.0
25°	2477.3	2439.3	2386.7	2336.4	2322.5	2295.4	2303.2
27.5°	2263.2	2204.1	2147.2	2106.3	2069.3	2028.7	2040.3
30°	2112.7	2046.2	1965.7	1903.8	1864.3	1825.6	1818.7
32.5°	1933.2	1835.7	1746.0	1691.4	1630.9	1606.5	1579.7
35°	1623.7	1528.4	1439.5	1362.8	1318.8	1284.6	1253.7
37.5°	1345.2	1235.7	1163.8	1101.8	1069.9	1050.4	1055.3
40°	1172.5	1076.5	1023.9	976.6	947.3	933.3	936.4
42.5°	1032.6	960.7	917.4	885.0	864.3	856.6	854.7
45°	873.7	833.5	797.9	779.3	769.3	760.7	755.4
47.5°	765.4	732.6	712.5	701.5	692.7	684.0	683.8
50°	700.3	678.7	664.8	653.2	646.2	640.1	645.4
52.5°	650.9	631.1	617.1	606.7	604.1	598.5	598.3
55°	577.3	561.9	551.8	542.5	537.9	534.7	530.9
57.5°	510.5	495.7	486.5	480.6	471.8	468.7	467.5
60°	462.8	451.2	441.9	434.1	430.3	424.1	424.1
62.5°	418.8	407.3	398.6	392.6	386.4	383.8	384.5
65°	355.3	346.0	337.4	331.2	329.7	325.1	326.6
67.5°	296.7	290.5	281.6	278.1	275.2	272.8	270.8
70°	257.7	251.6	246.9	242.3	239.9	239.9	239.9
72.5°	224.9	217.4	214.7	208.8	210.2	207.7	205.2
75°	174.1	169.5	167.1	164.8	161.0	161.0	161.0
77.5°	128.2	126.7	124.0	121.5	120.6	119.8	120.1
80°	99.1	98.3	96.7	96.7	95.2	94.4	92.9
82.5°	76.1	74.1	73.2	72.6	72.3	72.1	71.8
85°	43.3	41.8	41.8	42.5	41.0	41.0	41.8
87.5°	19.2	19.3	18.8	18.8	19.5	18.9	19.0
90°	12.3	12.9	13.3	13.5	13.7	14.0	14.2
92.5°	13.1	13.4	13.6	13.8	13.9	14.1	14.2
95°	22.3	22.9	23.1	23.0	22.9	22.8	22.6
97.5°	28.9	29.4	29.7	29.8	30.0	30.1	30.3
100°	32.8	33.8	34.3	34.6	34.8	35.0	35.3
102.5°	34.5	35.7	36.6	36.9	37.2	37.5	37.9
105°	36.1	37.3	38.2	38.7	39.1	39.6	40.1
107.5°	41.1	39.8	39.4	39.8	40.3	40.7	41.2
110°	57.1	45.3	39.8	40.2	40.7	41.2	41.6



TEST NUMBER: P331429-840

CATALOG NUMBER: SA2XXDIP-C1005D530U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	104.4	61.7	40.6	40.9	41.3	41.7	42.0
115°	162.5	108.3	77.0	68.5	60.1	51.6	43.2
117.5°	320.8	307.7	287.3	259.5	231.9	204.2	176.4
120°	390.5	391.9	384.8	368.9	353.1	337.3	321.4
122.5°	413.7	414.5	413.4	410.4	407.3	404.2	401.1
125°	447.8	448.6	449.2	449.6	449.9	450.3	450.6
127.5°	479.7	480.9	481.5	481.6	481.7	481.7	481.8
130°	499.8	501.1	501.7	501.5	501.4	501.3	501.2
132.5°	519.1	520.2	520.6	520.5	520.4	520.3	520.2
135°	546.8	548.1	548.6	548.3	548.1	547.9	547.5
137.5°	572.6	573.8	574.1	573.7	573.3	573.0	572.6
140°	589.2	590.3	590.5	589.9	589.4	588.8	588.1
142.5°	604.5	605.5	605.7	605.1	604.5	603.9	603.3
145°	625.9	626.7	626.8	626.3	625.7	625.1	624.5
147.5°	644.5	645.1	645.1	644.7	644.2	643.7	643.2
150°	656.1	656.8	656.9	656.3	655.7	655.1	654.6
152.5°	666.7	667.4	667.3	666.6	665.8	665.0	664.3
155°	681.0	681.7	681.5	680.5	679.6	678.7	677.7
157.5°	693.0	693.8	693.8	692.8	691.9	690.9	690.0
160°	699.8	700.5	700.5	699.7	698.9	698.0	697.2
162.5°	706.5	707.3	707.2	706.2	705.2	704.2	703.2
165°	714.5	715.3	715.3	714.5	713.7	712.9	712.0
167.5°	721.1	722.0	721.9	720.7	719.7	718.6	717.6
170°	724.5	725.3	725.2	724.1	723.1	722.1	720.9
172.5°	727.0	727.8	727.7	726.7	725.6	724.6	723.5
175°	729.7	730.5	730.4	729.2	728.0	726.9	725.7
177.5°	729.9	730.5	730.4	729.6	728.7	727.9	727.1
180°	728.3	728.3	728.3	728.3	728.3	728.3	728.3

(END OF REPORT)