

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331435-840

Luminaire Tested: **SA2XXDIP-C1005D530U840-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331435-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C1005D530U840-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 530 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6231.2 lumens
Efficiency: N/A
Efficacy: 113.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 55.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331435-840
CATALOG NUMBER: SA2XXDIP-C1005D530U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331435-840

CATALOG NUMBER: SA2XXDIP-C1005D530U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	71	71	71	66
1	101	97	93	89	95	91	88	85	81	78	76	71	69	67	62	61	60	55
2	92	85	78	73	87	80	74	70	71	67	63	63	59	56	55	52	50	46
3	84	74	67	61	79	70	64	58	63	57	53	55	51	48	49	46	43	39
4	77	66	58	52	72	62	55	49	56	50	45	49	45	41	44	40	37	34
5	71	59	51	44	66	56	48	43	50	44	39	44	39	36	39	35	32	29
6	65	53	45	39	61	50	43	37	45	39	34	40	35	31	36	32	28	26
7	61	48	40	34	57	45	38	33	41	35	30	37	32	28	33	28	25	23
8	56	44	36	30	53	41	34	29	37	31	27	34	28	25	30	26	23	20
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	28	24	20	18
10	49	37	29	24	46	35	28	24	32	26	22	29	24	20	26	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	25987	25987	25987
5°	26086	25710	25861
10°	25932	25450	25576
15°	25611	25120	25095
20°	25156	24624	24598
25°	24704	24015	24015
30°	24121	23457	23256
35°	23580	22787	22450
40°	22898	22118	21692
45°	22229	21450	20922
50°	21499	20760	20022
55°	20738	19952	19212
60°	19888	18991	18290
65°	18980	18032	17207
70°	17825	16877	16074
75°	16220	15540	15159
80°	14393	13966	13240
85°	11745	11189	10022



TEST NUMBER: P331435-840

CATALOG NUMBER: SA2XXDIP-C1005D530U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	151.3	2.4
10°-20°	425.9	6.8
20°-30°	626.0	10.0
30°-40°	727.1	11.7
40°-50°	726.3	11.7
50°-60°	633.4	10.2
60°-70°	468.3	7.5
70°-80°	265.3	4.3
80°-90°	73.1	1.2
90°-100°	24.3	0.4
100°-110°	89.1	1.4
110°-120°	238.2	3.8
120°-130°	393.1	6.3
130°-140°	418.1	6.7
140°-150°	388.6	6.2
150°-160°	312.4	5.0
160°-170°	201.3	3.2
170°-180°	69.3	1.1
0°-30°	1203.2	19.3
0°-40°	1930.3	31.0
0°-60°	3290.0	52.8
0°-90°	4096.7	65.7
90°-120°	351.5	5.6
90°-150°	1551.4	24.9
90°-180°	2134.0	34.2
0°-180°	6231.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1610	1610	1610	1610	1610	
5°	1610	1603	1586	1598	1596	153
15°	1532	1522	1503	1508	1501	431
25°	1387	1374	1348	1351	1348	638
35°	1196	1180	1156	1147	1139	747
45°	974	962	939	923	916	751
55°	737	727	709	691	682	658
65°	497	487	472	458	450	491
75°	260	257	249	241	243	278
85°	63	62	60	56	54	73
90°	0	6	10	13	14	5
95°	34	18	21	23	23	42
105°	160	167	32	38	40	171
115°	303	312	325	93	43	298
125°	428	436	445	449	451	382
135°	530	538	543	548	548	409
145°	615	615	624	627	624	385
155°	677	673	679	682	678	312
165°	714	711	712	715	712	202
175°	730	726	727	730	726	69
180°	728	728	728	728	728	



TEST NUMBER: P331435-840

CATALOG NUMBER: SA2XXDIP-C1005D530U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1609.5	1609.5	1609.5	1609.5	1609.5	1609.5	1609.5	1609.5	1609.5	1609.5	1609.5
2.5°	1617.0	1615.6	1614.3	1612.9	1611.4	1609.3	1606.3	1603.3	1600.2	1597.2	1599.9
5°	1609.5	1608.2	1606.8	1605.4	1604.1	1601.4	1597.7	1593.9	1590.1	1586.3	1589.1
7.5°	1595.3	1593.2	1591.0	1588.9	1586.8	1583.8	1579.9	1576.1	1572.3	1568.4	1571.1
10°	1581.7	1579.3	1576.9	1574.5	1572.1	1568.8	1564.7	1560.5	1556.4	1552.3	1555.1
12.5°	1563.2	1560.9	1558.8	1556.7	1554.6	1551.5	1547.3	1543.2	1539.1	1535.0	1536.9
15°	1532.2	1530.1	1528.0	1526.0	1523.9	1520.7	1516.2	1511.7	1507.2	1502.8	1504.2
17.5°	1492.6	1490.5	1488.4	1486.3	1484.3	1481.0	1476.4	1471.9	1467.3	1462.9	1464.4
20°	1464.1	1462.0	1460.0	1457.8	1455.8	1452.4	1447.5	1442.8	1437.9	1433.1	1434.1
22.5°	1435.6	1432.7	1429.9	1426.9	1424.0	1420.4	1415.8	1411.3	1406.7	1402.2	1402.4
25°	1386.7	1383.9	1381.2	1378.5	1375.7	1371.4	1365.5	1359.7	1353.8	1348.0	1348.7
27.5°	1331.0	1328.5	1326.1	1323.5	1321.1	1317.6	1312.9	1308.3	1303.7	1299.1	1298.1
30°	1293.8	1291.1	1288.3	1285.6	1282.8	1278.9	1273.7	1268.6	1263.4	1258.2	1257.2
32.5°	1254.3	1252.0	1249.8	1247.6	1245.4	1241.6	1236.2	1230.7	1225.3	1219.8	1218.0
35°	1196.3	1192.9	1189.4	1186.0	1182.6	1178.1	1172.6	1167.1	1161.6	1156.1	1154.1
37.5°	1131.0	1128.0	1125.0	1122.0	1118.9	1114.7	1109.1	1103.7	1098.1	1092.7	1090.0
40°	1086.4	1083.7	1081.0	1078.2	1075.4	1071.4	1065.8	1060.4	1054.8	1049.4	1046.2
42.5°	1043.1	1040.4	1037.6	1034.9	1032.1	1027.9	1022.5	1016.9	1011.5	1005.9	1002.6
45°	973.5	971.1	968.7	966.2	963.8	960.1	954.9	949.8	944.6	939.4	935.6
47.5°	904.1	901.9	899.6	897.4	895.0	891.2	885.9	880.5	875.1	869.8	865.8
50°	855.9	854.1	852.4	850.7	849.0	845.7	840.9	836.1	831.2	826.5	821.6
52.5°	808.8	806.6	804.3	802.0	799.7	796.3	791.7	787.2	782.7	778.2	774.2
55°	736.7	734.6	732.6	730.5	728.4	725.3	721.2	717.1	713.0	708.8	704.7
57.5°	664.3	662.6	661.0	659.3	657.6	654.6	650.1	645.5	641.0	636.4	632.4
60°	615.9	614.6	613.2	611.9	610.5	607.3	602.6	597.7	592.9	588.1	584.3
62.5°	569.0	566.7	564.5	562.3	560.1	557.1	553.4	549.8	546.0	542.3	538.8
65°	496.8	494.7	492.7	490.6	488.6	485.7	482.3	478.9	475.4	472.0	469.0
67.5°	423.4	421.8	420.1	418.5	416.9	414.4	411.3	408.3	405.2	402.1	399.7
70°	377.6	376.3	374.9	373.5	372.1	369.9	366.8	363.7	360.6	357.5	355.1
72.5°	330.5	329.2	327.8	326.5	325.1	323.4	321.4	319.4	317.4	315.4	313.0
75°	260.0	259.3	258.6	257.9	257.2	256.0	254.3	252.6	250.9	249.1	247.1
77.5°	196.8	195.7	194.5	193.4	192.2	191.3	190.6	189.9	189.1	188.5	187.4
80°	154.8	154.4	154.1	153.7	153.4	152.9	152.2	151.5	150.8	150.2	149.1
82.5°	115.1	115.1	115.0	114.9	114.8	114.6	114.2	113.8	113.4	113.0	111.7
85°	63.4	63.1	62.8	62.4	62.1	61.7	61.4	61.0	60.7	60.4	59.3
87.5°	22.4	22.1	21.8	21.5	21.2	20.9	20.5	20.2	19.8	19.5	18.8
90°	0.5	1.8	3.1	4.3	5.7	6.8	7.8	8.7	9.6	10.5	11.1
92.5°	10.6	10.5	10.4	10.3	10.2	10.4	10.8	11.3	11.7	12.2	12.5
95°	34.2	30.4	26.6	22.6	18.8	17.3	18.1	18.9	19.7	20.6	21.1
97.5°	68.0	57.1	46.3	35.3	24.4	19.9	21.8	23.7	25.7	27.5	28.0
100°	93.3	77.3	61.2	45.1	29.1	22.1	24.0	26.1	28.1	30.0	31.0
102.5°	121.1	117.8	114.3	110.9	107.6	97.5	80.9	64.2	47.6	30.9	32.1
105°	160.2	163.7	167.2	170.8	174.3	160.1	128.1	96.1	64.1	32.1	33.4
107.5°	204.8	207.6	210.5	213.3	216.1	198.3	160.1	121.7	83.3	45.0	43.7
110°	233.5	235.9	238.4	240.9	243.3	227.6	193.8	160.0	126.0	92.2	80.5



TEST NUMBER: P331435-840

CATALOG NUMBER: SA2XXDIP-C1005D530U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	260.4	262.7	264.8	267.0	269.1	266.1	257.7	249.3	241.0	232.7	189.9
115°	303.1	305.0	307.0	309.0	311.0	313.5	316.4	319.3	322.2	325.2	270.9
117.5°	341.1	343.4	345.6	347.8	350.0	352.1	354.2	356.2	358.2	360.1	347.1
120°	368.9	370.6	372.4	374.2	376.0	377.9	380.0	382.1	384.2	386.3	387.7
122.5°	392.5	394.4	396.3	398.1	399.9	402.0	404.2	406.6	408.9	411.2	412.0
125°	428.5	430.0	431.5	433.0	434.5	436.5	438.7	440.9	443.1	445.4	446.2
127.5°	461.0	462.7	464.4	466.1	467.8	469.5	471.1	472.8	474.4	476.2	477.3
130°	481.7	483.5	485.4	487.4	489.2	490.8	492.1	493.3	494.6	495.9	497.3
132.5°	502.8	504.3	505.9	507.6	509.2	510.6	511.9	513.2	514.4	515.7	516.8
135°	530.2	532.1	533.9	535.8	537.7	539.2	540.2	541.3	542.3	543.3	544.5
137.5°	558.0	559.2	560.5	561.8	563.1	564.4	565.6	566.8	567.9	569.2	570.4
140°	576.0	576.9	577.9	578.9	579.8	580.9	582.2	583.5	584.7	586.0	587.1
142.5°	591.2	592.1	592.9	593.7	594.6	595.7	597.2	598.6	600.2	601.7	602.6
145°	615.0	614.9	614.8	614.7	614.6	615.5	617.5	619.5	621.5	623.5	624.3
147.5°	635.8	635.3	634.9	634.5	634.0	634.8	636.7	638.7	640.7	642.7	643.3
150°	649.2	648.4	647.6	646.8	646.0	646.5	648.4	650.3	652.2	654.0	654.7
152.5°	660.7	659.7	658.8	657.9	657.0	657.4	659.2	661.1	662.8	664.6	665.3
155°	677.2	676.2	675.1	674.1	673.0	673.2	674.6	676.0	677.4	678.8	679.5
157.5°	690.1	689.3	688.4	687.5	686.6	686.7	687.6	688.6	689.6	690.6	691.4
160°	697.8	697.1	696.4	695.7	695.0	695.0	695.7	696.4	697.1	697.8	698.5
162.5°	704.5	703.8	703.1	702.4	701.8	701.7	702.3	702.9	703.5	704.1	704.9
165°	713.6	712.9	712.2	711.4	710.7	710.6	710.9	711.2	711.7	712.0	712.9
167.5°	720.3	719.6	718.9	718.2	717.5	717.3	717.6	718.0	718.3	718.6	719.4
170°	724.1	723.5	722.8	722.1	721.3	721.0	721.3	721.5	721.8	722.1	722.9
172.5°	726.7	726.0	725.3	724.6	723.9	723.6	723.9	724.1	724.3	724.6	725.4
175°	729.9	729.1	728.3	727.5	726.6	726.4	726.6	726.8	727.0	727.3	728.1
177.5°	730.4	729.8	729.1	728.5	727.8	727.5	727.6	727.7	727.8	727.9	728.6
180°	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3



TEST NUMBER: P331435-840

CATALOG NUMBER: SA2XXDIP-C1005D530U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1609.5	1609.5	1609.5	1609.5	1609.5	1609.5	1609.5	1609.5
2.5°	1602.7	1605.4	1608.2	1609.3	1608.7	1608.2	1607.6	1607.1
5°	1591.9	1594.6	1597.3	1598.4	1597.7	1597.0	1596.3	1595.6
7.5°	1573.9	1576.6	1579.4	1580.4	1579.6	1578.9	1578.1	1577.4
10°	1557.8	1560.5	1563.3	1564.2	1563.2	1562.1	1561.0	1560.0
12.5°	1538.8	1540.8	1542.7	1543.3	1542.5	1541.8	1541.0	1540.2
15°	1505.5	1506.9	1508.2	1508.1	1506.4	1504.7	1503.0	1501.3
17.5°	1466.0	1467.6	1469.2	1469.2	1467.4	1465.8	1464.2	1462.5
20°	1435.2	1436.2	1437.2	1437.0	1435.7	1434.3	1433.0	1431.6
22.5°	1402.6	1402.8	1403.0	1402.7	1401.9	1401.1	1400.2	1399.4
25°	1349.4	1350.1	1350.8	1350.8	1350.1	1349.4	1348.7	1348.0
27.5°	1297.1	1296.0	1294.9	1293.6	1292.0	1290.3	1288.7	1287.1
30°	1256.2	1255.2	1254.2	1252.9	1251.5	1250.1	1248.8	1247.4
32.5°	1216.2	1214.3	1212.4	1210.8	1209.4	1208.1	1206.7	1205.3
35°	1152.0	1149.9	1147.8	1146.0	1144.3	1142.6	1140.7	1139.0
37.5°	1087.5	1085.0	1082.5	1080.4	1078.7	1077.0	1075.4	1073.8
40°	1043.1	1040.1	1036.9	1034.7	1033.3	1032.0	1030.6	1029.2
42.5°	999.3	995.8	992.5	989.9	988.0	986.0	984.1	982.1
45°	931.9	928.1	924.3	921.7	920.3	919.0	917.6	916.3
47.5°	861.8	857.8	853.8	850.8	848.8	846.9	844.9	842.8
50°	816.8	812.0	807.2	804.0	802.2	800.5	798.8	797.1
52.5°	770.2	766.2	762.2	759.1	756.8	754.6	752.2	750.0
55°	700.5	696.4	692.4	689.4	687.7	686.0	684.3	682.5
57.5°	628.2	624.2	620.2	617.4	616.2	614.9	613.6	612.3
60°	580.6	576.7	573.0	570.6	569.6	568.6	567.4	566.4
62.5°	535.3	531.8	528.3	525.8	524.5	523.2	521.9	520.6
65°	465.9	462.7	459.7	457.3	455.6	453.8	452.1	450.4
67.5°	397.3	394.9	392.4	390.5	389.2	387.8	386.5	385.1
70°	352.6	350.3	347.9	346.0	344.6	343.3	341.8	340.5
72.5°	310.6	308.2	305.8	304.1	303.0	301.8	300.7	299.6
75°	245.1	243.0	241.0	240.2	241.0	241.6	242.3	243.0
77.5°	186.4	185.4	184.4	183.4	182.4	181.5	180.5	179.6
80°	148.0	147.0	146.0	145.1	144.4	143.8	143.1	142.4
82.5°	110.4	109.1	107.8	107.0	106.8	106.7	106.6	106.4
85°	58.3	57.3	56.2	55.5	55.2	54.8	54.5	54.1
87.5°	18.0	17.3	16.6	16.2	16.0	15.7	15.5	15.2
90°	11.7	12.3	12.9	13.3	13.5	13.7	14.0	14.2
92.5°	12.8	13.1	13.4	13.6	13.8	13.9	14.1	14.2
95°	21.7	22.3	22.9	23.1	23.0	22.9	22.8	22.6
97.5°	28.5	28.9	29.4	29.7	29.8	30.0	30.1	30.3
100°	31.9	32.8	33.8	34.3	34.6	34.8	35.0	35.3
102.5°	33.3	34.5	35.7	36.6	36.9	37.2	37.5	37.9
105°	34.7	36.1	37.3	38.2	38.7	39.1	39.6	40.1
107.5°	42.4	41.1	39.8	39.4	39.8	40.3	40.7	41.2
110°	68.8	57.1	45.3	39.8	40.2	40.7	41.2	41.6



TEST NUMBER: P331435-840

CATALOG NUMBER: SA2XXDIP-C1005D530U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	147.1	104.4	61.7	40.6	40.9	41.3	41.7	42.0
115°	216.7	162.5	108.3	77.0	68.5	60.1	51.6	43.2
117.5°	334.0	320.8	307.7	287.3	259.5	231.9	204.2	176.4
120°	389.1	390.5	391.9	384.8	368.9	353.1	337.3	321.4
122.5°	412.8	413.7	414.5	413.4	410.4	407.3	404.2	401.1
125°	447.0	447.8	448.6	449.2	449.6	449.9	450.3	450.6
127.5°	478.5	479.7	480.9	481.5	481.6	481.7	481.7	481.8
130°	498.5	499.8	501.1	501.7	501.5	501.4	501.3	501.2
132.5°	518.0	519.1	520.2	520.6	520.5	520.4	520.3	520.2
135°	545.7	546.8	548.1	548.6	548.3	548.1	547.9	547.5
137.5°	571.5	572.6	573.8	574.1	573.7	573.3	573.0	572.6
140°	588.1	589.2	590.3	590.5	589.9	589.4	588.8	588.1
142.5°	603.6	604.5	605.5	605.7	605.1	604.5	603.9	603.3
145°	625.1	625.9	626.7	626.8	626.3	625.7	625.1	624.5
147.5°	643.9	644.5	645.1	645.1	644.7	644.2	643.7	643.2
150°	655.4	656.1	656.8	656.9	656.3	655.7	655.1	654.6
152.5°	666.0	666.7	667.4	667.3	666.6	665.8	665.0	664.3
155°	680.2	681.0	681.7	681.5	680.5	679.6	678.7	677.7
157.5°	692.2	693.0	693.8	693.8	692.8	691.9	690.9	690.0
160°	699.1	699.8	700.5	700.5	699.7	698.9	698.0	697.2
162.5°	705.7	706.5	707.3	707.2	706.2	705.2	704.2	703.2
165°	713.7	714.5	715.3	715.3	714.5	713.7	712.9	712.0
167.5°	720.2	721.1	722.0	721.9	720.7	719.7	718.6	717.6
170°	723.7	724.5	725.3	725.2	724.1	723.1	722.1	720.9
172.5°	726.2	727.0	727.8	727.7	726.7	725.6	724.6	723.5
175°	728.9	729.7	730.5	730.4	729.2	728.0	726.9	725.7
177.5°	729.2	729.9	730.5	730.4	729.6	728.7	727.9	727.1
180°	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3

(END OF REPORT)