

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331754-930

Luminaire Tested: **SA2XXRDIP-C1005D925U930-4F0-1E-UDD-A1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331754-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C1005D925U930-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 925 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5807.3 lumens
Efficiency: N/A
Efficacy: 86.9 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 66.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331754-930

CATALOG NUMBER: SA2XXRDIP-C1005D925U930-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331754-930

CATALOG NUMBER: SA2XXRDIP-C1005D925U930-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	54
1	99	95	92	88	92	89	86	83	76	74	72	64	63	61	54	53	52	47
2	91	84	79	74	84	79	74	69	68	64	61	58	55	53	48	47	45	41
3	84	75	68	63	78	70	64	59	61	56	52	52	48	46	44	41	39	35
4	77	67	60	54	71	63	56	51	54	49	45	47	43	40	40	37	35	31
5	71	60	53	47	66	56	50	44	49	44	40	43	39	35	36	33	31	28
6	66	54	47	41	61	51	44	39	45	39	35	39	35	32	33	30	28	25
7	61	50	42	37	57	47	40	35	41	36	32	36	31	28	31	28	25	23
8	57	45	38	33	53	43	36	31	38	32	28	33	29	26	29	25	23	21
9	53	42	34	30	50	39	33	28	35	30	26	31	26	23	27	23	21	19
10	50	38	31	27	47	36	30	26	32	27	24	28	24	21	25	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	29032	29032	29032	29032
5°	32423	29214	25901	29214
10°	35974	29009	22453	29009
15°	37742	28583	17690	28583
20°	32720	27953	15309	27953
25°	21458	27091	13668	27091
30°	14443	26045	12370	26045
35°	11698	24727	11158	24727
40°	10404	23294	10323	23294
45°	9417	21614	9216	21614
50°	8568	19947	8538	19947
55°	8056	18097	7949	18097
60°	6736	16401	6659	16401
65°	5681	14896	6445	14896
70°	5249	13303	6076	13303
75°	4916	11578	5608	11578
80°	4537	9530	4993	9530
85°	4168	7521	4390	7521



TEST NUMBER: P331754-930

CATALOG NUMBER: SA2XXRDIP-C1005D925U930-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	170.4	2.9
10°-20°	474.9	8.2
20°-30°	612.0	10.5
30°-40°	581.6	10.0
40°-50°	498.2	8.6
50°-60°	379.4	6.5
60°-70°	239.9	4.1
70°-80°	119.8	2.1
80°-90°	35.0	0.6
90°-100°	61.1	1.1
100°-110°	189.8	3.3
110°-120°	324.3	5.6
120°-130°	426.5	7.3
130°-140°	478.7	8.2
140°-150°	469.4	8.1
150°-160°	393.7	6.8
160°-170°	261.1	4.5
170°-180°	91.3	1.6
0°-30°	1257.4	21.7
0°-40°	1839.0	31.7
0°-60°	2716.7	46.8
0°-90°	3111.4	53.6
90°-120°	575.2	9.9
90°-150°	1949.8	33.6
90°-180°	2696.0	46.4
0°-180°	5807.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1798	1798	1798	1798	1798	
5°	2000	1802	1598	1802	2000	197
15°	2258	1710	1058	1710	2258	609
25°	1204	1521	767	1521	1204	572
35°	594	1254	566	1254	594	380
45°	412	947	404	947	412	319
55°	286	643	282	643	286	251
65°	149	390	169	390	149	151
75°	79	186	90	186	79	84
85°	22	41	24	41	22	25
90°	28	1	28	1	28	13
95°	50	42	50	42	50	56
105°	181	175	181	175	181	190
115°	326	326	326	326	326	321
125°	475	474	475	474	475	424
135°	620	613	620	613	620	477
145°	752	744	752	744	752	469
155°	857	850	857	850	857	394
165°	926	925	926	925	926	261
175°	959	962	959	962	959	91
180°	964	964	964	964	964	



TEST NUMBER: P331754-930

CATALOG NUMBER: SA2XXRDIP-C1005D925U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1
2.5°	1871.0	1872.6	1874.0	1870.5	1870.5	1867.5	1861.1	1856.0	1842.1	1840.0	1840.0
5°	2000.5	1999.3	2001.7	1993.7	1982.4	1979.9	1968.1	1952.4	1936.2	1918.1	1914.3
7.5°	2129.2	2127.4	2122.3	2121.0	2112.4	2093.4	2074.4	2054.0	2027.0	2000.7	1987.4
10°	2194.2	2214.8	2202.3	2180.4	2184.8	2155.5	2139.8	2113.0	2090.5	2051.1	2042.4
12.5°	2258.1	2266.3	2262.3	2249.9	2244.3	2223.9	2202.8	2179.5	2138.0	2102.6	2071.8
15°	2257.9	2269.8	2272.9	2269.1	2272.3	2271.0	2259.8	2240.4	2204.2	2165.4	2131.7
17.5°	2091.2	2099.5	2119.9	2133.8	2151.3	2188.3	2206.5	2213.7	2208.3	2186.2	2162.4
20°	1904.3	1890.5	1948.0	1977.4	2002.4	2064.8	2118.6	2139.2	2172.3	2171.7	2165.4
22.5°	1639.4	1642.7	1697.1	1732.0	1805.0	1867.4	1928.7	2006.3	2070.4	2112.7	2137.5
25°	1204.5	1228.3	1282.6	1330.2	1411.4	1527.5	1633.1	1755.6	1871.2	1962.4	2049.3
27.5°	904.7	906.4	949.5	993.4	1041.6	1136.9	1269.7	1416.0	1580.8	1716.8	1873.2
30°	774.7	770.9	789.0	816.0	857.2	930.9	1030.9	1174.6	1338.9	1543.8	1726.2
32.5°	682.7	683.0	696.6	716.5	750.7	800.5	868.9	985.6	1140.9	1342.4	1556.3
35°	593.5	592.9	602.9	617.3	631.6	663.5	710.4	771.6	878.4	1066.5	1285.2
37.5°	529.5	532.3	537.2	546.2	562.1	579.8	607.9	649.0	725.1	836.3	1020.1
40°	493.6	494.8	501.7	509.2	518.5	532.3	555.4	588.6	644.2	732.9	867.2
42.5°	460.6	461.9	466.7	473.7	481.1	494.8	514.0	542.6	587.7	656.9	767.7
45°	412.4	412.4	416.7	419.9	428.0	440.4	456.1	479.8	511.0	562.3	636.0
47.5°	367.1	367.2	370.1	375.5	380.6	390.4	405.7	425.1	447.8	487.5	550.4
50°	341.1	341.8	343.6	348.0	351.1	359.9	371.8	388.6	412.4	443.0	495.5
52.5°	320.2	319.8	322.1	324.0	326.1	332.4	341.3	356.1	377.3	404.0	447.4
55°	286.2	283.6	287.4	290.5	292.4	294.9	299.9	309.2	327.3	349.8	382.4
57.5°	243.7	242.6	245.3	248.2	254.0	260.8	265.1	271.0	280.4	296.5	328.7
60°	208.6	208.6	214.3	216.1	223.1	231.8	240.5	245.6	254.9	265.5	289.3
62.5°	177.7	178.2	180.8	182.7	186.5	197.3	209.5	220.5	229.4	239.5	255.3
65°	148.7	149.9	149.9	151.2	153.7	156.2	161.2	169.9	185.6	199.9	211.8
67.5°	126.2	126.6	126.9	128.2	128.8	131.6	133.5	137.5	141.0	154.7	169.4
70°	111.2	113.1	112.4	113.7	114.3	115.6	118.1	119.9	125.6	128.7	137.5
72.5°	97.2	98.6	98.5	99.2	100.9	101.1	103.1	104.9	108.6	111.2	115.9
75°	78.8	78.1	78.8	80.0	80.6	81.2	81.2	83.7	85.6	88.1	91.2
77.5°	60.7	61.4	61.2	61.4	61.5	62.6	62.5	63.6	65.5	66.7	68.2
80°	48.8	49.3	48.8	49.3	50.0	50.6	50.0	50.6	52.5	53.7	53.7
82.5°	37.7	37.8	38.2	38.4	38.5	38.6	39.5	39.6	41.0	40.8	41.3
85°	22.5	21.9	21.9	21.9	22.5	23.2	22.5	22.5	23.2	23.2	23.2
87.5°	13.5	14.0	13.9	13.9	13.9	13.9	13.9	14.5	14.1	14.7	13.4
90°	27.6	27.5	27.3	27.1	26.9	27.1	27.4	27.7	28.1	28.5	24.5
92.5°	26.3	26.3	26.3	26.3	26.3	26.2	26.1	26.0	25.9	25.8	24.9
95°	50.5	50.8	51.2	51.5	51.9	52.1	52.1	52.1	52.1	52.1	51.7
97.5°	87.4	87.4	87.5	87.5	87.6	87.6	87.6	87.6	87.6	87.6	86.8
100°	111.5	111.6	111.9	112.0	112.2	112.3	112.3	112.3	112.3	112.3	111.8
102.5°	138.8	139.0	139.2	139.3	139.5	139.6	139.4	139.3	139.1	139.0	138.3
105°	180.6	180.6	180.6	180.6	180.6	180.4	180.1	179.7	179.4	179.0	178.6
107.5°	220.0	220.9	221.7	222.5	223.3	223.6	223.6	223.4	223.2	223.1	223.1
110°	250.6	251.1	251.7	252.3	252.7	253.1	253.1	253.1	253.1	253.1	253.1



TEST NUMBER: P331754-930

CATALOG NUMBER: SA2XXRDIP-C1005D925U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	279.9	280.3	280.7	281.1	281.4	281.9	282.3	282.7	283.2	283.6	283.8
115°	325.5	326.0	326.5	327.1	327.6	328.0	328.2	328.3	328.6	328.7	329.1
117.5°	368.9	369.4	370.0	370.6	371.0	371.5	372.0	372.4	372.8	373.3	374.3
120°	399.5	400.1	400.6	401.1	401.7	401.9	401.9	401.9	401.9	401.9	403.4
122.5°	429.4	429.8	430.2	430.6	431.0	431.5	431.9	432.3	432.8	433.2	434.2
125°	475.2	475.3	475.5	475.7	475.9	476.2	476.8	477.4	477.8	478.4	479.0
127.5°	516.8	517.4	518.0	518.5	519.1	519.8	520.4	521.1	521.7	522.4	523.0
130°	546.7	547.5	548.2	548.9	549.7	550.2	550.6	550.9	551.3	551.6	552.0
132.5°	575.4	576.0	576.6	577.2	577.7	578.4	579.2	580.0	580.8	581.6	581.5
135°	620.0	620.5	621.1	621.6	622.2	622.5	622.7	622.9	623.1	623.2	622.9
137.5°	660.3	661.0	661.8	662.5	663.2	663.7	663.8	664.0	664.1	664.2	663.8
140°	688.4	689.1	689.7	690.5	691.2	691.6	691.6	691.6	691.6	691.6	690.7
142.5°	713.7	714.4	715.2	715.9	716.6	716.9	716.7	716.6	716.5	716.3	715.7
145°	751.8	752.5	753.3	754.0	754.7	755.0	754.8	754.6	754.4	754.2	753.2
147.5°	785.8	786.5	787.2	787.9	788.6	788.7	788.3	787.9	787.5	787.1	786.4
150°	808.0	808.5	809.0	809.6	810.1	810.1	809.6	809.0	808.5	808.0	807.2
152.5°	828.8	829.5	830.1	830.8	831.5	831.5	830.8	830.1	829.5	828.8	827.9
155°	856.7	857.3	857.9	858.3	858.9	858.8	857.9	857.0	856.1	855.1	854.6
157.5°	880.8	881.7	882.6	883.5	884.3	884.1	882.9	881.7	880.4	879.2	878.9
160°	895.8	896.5	897.2	898.0	898.7	898.5	897.4	896.3	895.3	894.1	894.0
162.5°	908.8	909.7	910.5	911.4	912.3	912.1	910.9	909.6	908.4	907.2	907.0
165°	925.9	926.8	927.7	928.6	929.5	929.4	928.1	926.8	925.5	924.3	924.3
167.5°	939.9	940.9	941.8	942.7	943.6	943.5	942.2	940.9	939.7	938.4	938.5
170°	947.1	948.1	949.3	950.3	951.4	951.3	950.1	948.8	947.5	946.2	946.4
172.5°	952.9	954.0	955.1	956.2	957.2	957.2	955.9	954.6	953.4	952.1	952.3
175°	959.3	960.3	961.4	962.5	963.6	963.5	962.2	961.0	959.7	958.5	958.8
177.5°	962.2	963.0	963.9	964.8	965.6	965.6	964.8	963.9	963.0	962.2	962.5
180°	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2



TEST NUMBER: P331754-930

CATALOG NUMBER: SA2XXRDIP-C1005D925U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1
2.5°	1841.1	1837.0	1833.6	1824.6	1820.1	1810.0	1808.6	1808.1	1795.1	1782.6	1779.1
5°	1904.3	1894.3	1879.3	1861.8	1843.7	1825.0	1812.5	1802.5	1777.4	1753.7	1740.0
7.5°	1968.1	1946.5	1920.7	1887.6	1859.9	1829.0	1806.0	1785.3	1749.9	1715.9	1693.0
10°	2015.5	1980.5	1946.1	1900.5	1864.9	1829.9	1797.5	1769.4	1729.3	1684.4	1652.5
12.5°	2045.0	2006.5	1959.2	1914.6	1868.4	1824.0	1780.5	1744.3	1697.4	1650.9	1613.1
15°	2084.9	2043.6	1986.2	1922.4	1863.0	1805.0	1755.0	1710.0	1648.8	1593.2	1546.9
17.5°	2117.5	2060.8	1999.0	1925.3	1856.6	1782.7	1718.4	1660.9	1592.8	1525.7	1471.2
20°	2127.9	2071.8	2000.5	1926.8	1845.6	1758.8	1689.4	1626.9	1553.8	1480.7	1418.2
22.5°	2121.5	2077.7	1998.5	1910.3	1827.1	1736.3	1657.9	1585.4	1504.3	1429.7	1357.2
25°	2077.4	2062.4	1987.4	1891.2	1796.2	1690.6	1600.0	1520.7	1428.2	1348.3	1269.5
27.5°	1974.5	2006.9	1960.4	1857.9	1752.3	1639.2	1537.3	1447.0	1351.0	1261.0	1182.6
30°	1875.6	1949.9	1929.9	1834.9	1716.9	1605.7	1491.3	1397.0	1294.5	1202.1	1124.6
32.5°	1740.1	1863.0	1882.4	1803.0	1680.9	1558.7	1438.8	1345.0	1238.0	1140.6	1065.1
35°	1524.4	1708.1	1792.4	1741.9	1619.4	1487.6	1363.8	1254.5	1147.0	1050.8	975.9
37.5°	1267.1	1517.4	1657.9	1661.5	1549.1	1412.0	1277.2	1168.7	1058.7	964.3	883.2
40°	1100.2	1371.3	1554.4	1595.1	1500.1	1352.0	1215.8	1105.2	997.8	905.3	812.2
42.5°	950.3	1220.4	1445.4	1516.0	1440.6	1293.6	1156.8	1041.2	936.8	849.3	754.2
45°	768.5	1004.6	1252.6	1378.8	1337.0	1200.8	1056.5	946.6	848.4	772.8	681.6
47.5°	648.2	814.7	1054.8	1225.4	1224.7	1100.3	958.4	853.0	762.1	691.2	617.4
50°	579.8	724.7	927.8	1121.4	1137.7	1033.4	898.4	794.1	709.1	634.8	575.4
52.5°	518.3	637.7	820.4	1006.0	1052.2	961.9	831.0	734.6	652.2	583.8	533.0
55°	438.0	530.4	669.1	842.8	912.8	849.1	732.9	642.9	576.0	518.5	474.8
57.5°	370.5	439.9	551.1	691.0	772.5	732.4	636.5	563.5	506.2	454.2	419.7
60°	328.0	384.8	479.2	596.1	686.0	657.9	576.0	507.9	459.2	414.3	381.7
62.5°	288.0	336.9	417.8	512.6	595.0	583.4	516.6	459.4	416.7	375.8	348.2
65°	231.8	267.4	330.5	404.9	471.1	476.7	428.6	389.9	351.7	319.3	294.9
67.5°	184.6	207.8	252.3	314.9	364.5	382.2	352.9	323.3	293.0	267.9	246.8
70°	155.6	174.3	206.8	257.4	303.0	321.7	304.9	281.8	255.5	234.9	216.8
72.5°	126.0	144.3	168.3	205.5	244.5	264.8	258.9	242.3	221.0	203.9	186.8
75°	95.0	100.6	116.8	141.9	172.4	190.0	194.3	185.6	168.7	155.6	145.5
77.5°	70.2	73.6	81.4	94.5	114.5	130.0	136.5	135.4	123.8	116.2	106.8
80°	56.3	58.1	61.9	67.5	82.5	98.1	102.5	102.5	94.3	91.2	81.9
82.5°	42.7	44.1	46.4	49.5	56.5	70.1	75.0	76.0	70.8	66.7	59.4
85°	24.4	23.7	25.0	26.9	28.1	31.9	39.4	40.6	39.4	34.3	32.4
87.5°	12.6	12.3	11.5	10.4	10.4	10.5	12.6	14.7	13.1	12.1	11.5
90°	20.5	16.6	12.6	9.5	7.3	5.1	3.0	0.8	3.0	5.1	7.3
92.5°	24.0	23.1	22.1	20.9	19.2	17.7	16.1	14.5	16.1	17.7	19.2
95°	51.4	51.0	50.6	49.6	47.7	45.9	44.1	42.3	44.1	45.9	47.7
97.5°	86.2	85.5	84.8	83.6	82.1	80.5	78.9	77.3	78.9	80.5	82.1
100°	111.2	110.6	110.1	109.1	107.7	106.2	104.8	103.3	104.8	106.2	107.7
102.5°	137.6	136.9	136.2	135.3	134.1	133.0	131.8	130.7	131.8	133.0	134.1
105°	178.3	177.9	177.6	177.1	176.6	176.0	175.5	175.0	175.5	176.0	176.6
107.5°	223.1	223.1	223.1	222.7	221.9	221.1	220.3	219.5	220.3	221.1	221.9
110°	253.1	253.1	253.1	252.5	251.4	250.3	249.2	248.2	249.2	250.3	251.4



TEST NUMBER: P331754-930

CATALOG NUMBER: SA2XXRDIP-C1005D925U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	283.9	284.1	284.2	283.7	282.7	281.6	280.5	279.4	280.5	281.6	282.7
115°	329.5	329.8	330.1	329.8	328.7	327.6	326.5	325.5	326.5	327.6	328.7
117.5°	375.3	376.3	377.3	377.2	375.7	374.2	372.8	371.4	372.8	374.2	375.7
120°	404.8	406.3	407.7	407.7	406.3	404.8	403.4	401.9	403.4	404.8	406.3
122.5°	435.2	436.2	437.2	436.8	435.1	433.4	431.6	429.9	431.6	433.4	435.1
125°	479.5	480.0	480.6	480.0	478.4	476.8	475.2	473.5	475.2	476.8	478.4
127.5°	523.7	524.3	525.0	524.2	522.2	520.2	518.0	516.0	518.0	520.2	522.2
130°	552.4	552.7	553.1	552.1	549.8	547.4	545.0	542.7	545.0	547.4	549.8
132.5°	581.5	581.4	581.3	580.3	578.4	576.5	574.5	572.7	574.5	576.5	578.4
135°	622.5	622.2	621.8	620.6	618.6	616.6	614.7	612.7	614.7	616.6	618.6
137.5°	663.3	662.8	662.3	661.3	659.7	658.0	656.4	654.8	656.4	658.0	659.7
140°	689.7	688.8	687.9	686.7	685.1	683.5	681.8	680.2	681.8	683.5	685.1
142.5°	715.1	714.4	713.9	712.7	711.1	709.5	707.8	706.2	707.8	709.5	711.1
145°	752.0	751.0	749.9	748.7	747.5	746.2	744.9	743.6	744.9	746.2	747.5
147.5°	785.6	785.0	784.2	783.1	781.5	780.1	778.5	777.0	778.5	780.1	781.5
150°	806.5	805.8	805.0	804.1	803.1	801.9	800.9	799.8	800.9	801.9	803.1
152.5°	827.0	826.1	825.3	824.3	823.2	822.1	821.1	819.9	821.1	822.1	823.2
155°	854.0	853.5	853.0	852.4	851.9	851.3	850.8	850.3	850.8	851.3	851.9
157.5°	878.6	878.2	877.9	877.6	877.2	876.9	876.4	876.1	876.4	876.9	877.2
160°	893.8	893.6	893.5	893.2	892.8	892.4	892.1	891.8	892.1	892.4	892.8
162.5°	906.9	906.7	906.4	906.4	906.3	906.2	906.1	906.0	906.1	906.2	906.3
165°	924.3	924.3	924.3	924.4	924.5	924.7	925.0	925.1	925.0	924.7	924.5
167.5°	938.5	938.6	938.6	938.9	939.4	940.0	940.5	941.0	940.5	940.0	939.4
170°	946.6	946.8	947.0	947.3	947.9	948.4	948.9	949.5	948.9	948.4	947.9
172.5°	952.4	952.7	952.8	953.2	953.7	954.3	954.8	955.4	954.8	954.3	953.7
175°	959.2	959.5	959.9	960.3	960.9	961.4	962.0	962.5	962.0	961.4	960.9
177.5°	962.8	963.0	963.4	963.7	964.2	964.6	965.0	965.5	965.0	964.6	964.2
180°	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2



TEST NUMBER: P331754-930

CATALOG NUMBER: SA2XXRDIP-C1005D925U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1
2.5°	1772.6	1769.1	1762.6	1752.6	1746.6	1736.1	1729.1	1733.1	1734.1	1733.1	1732.1
5°	1725.0	1711.9	1693.8	1676.3	1660.0	1642.5	1632.6	1628.2	1619.4	1614.4	1611.9
7.5°	1667.4	1644.8	1619.2	1588.7	1562.8	1535.7	1521.8	1514.9	1497.1	1487.4	1478.8
10°	1624.4	1588.8	1563.2	1523.2	1498.8	1463.2	1438.8	1439.5	1415.1	1401.3	1391.4
12.5°	1577.0	1537.8	1495.2	1459.2	1425.4	1396.8	1367.3	1355.5	1329.7	1316.4	1289.4
15°	1498.2	1452.6	1407.6	1358.9	1324.5	1280.2	1237.7	1185.9	1143.9	1107.7	1097.7
17.5°	1412.3	1355.8	1310.7	1253.4	1194.6	1120.0	1070.7	1040.6	1015.4	996.3	982.0
20°	1353.2	1295.8	1247.7	1161.5	1082.1	1031.5	995.2	972.2	945.9	925.3	914.0
22.5°	1291.3	1231.3	1165.7	1069.5	1007.6	967.0	934.7	908.2	890.4	874.3	864.1
25°	1203.3	1137.7	1029.6	963.4	913.4	870.9	848.4	832.2	813.4	791.6	781.6
27.5°	1110.4	1006.0	928.4	879.1	831.4	803.8	783.6	759.4	742.6	732.7	722.4
30°	1040.9	936.5	876.0	822.2	788.5	757.8	734.1	720.4	704.1	687.2	680.4
32.5°	963.4	880.0	822.0	777.2	743.0	716.9	698.1	675.9	664.1	653.8	639.4
35°	867.2	804.0	751.0	714.8	682.2	661.0	639.1	626.0	604.8	596.1	590.4
37.5°	785.7	731.0	691.4	653.1	627.4	603.9	590.5	569.6	560.4	548.3	536.5
40°	739.7	686.0	647.9	616.6	587.9	570.4	553.5	536.7	522.9	517.3	503.0
42.5°	692.8	649.0	610.9	576.7	557.4	538.9	517.6	505.2	491.0	481.8	473.0
45°	627.9	589.1	556.7	528.6	507.3	488.0	474.2	453.6	445.5	427.4	419.9
47.5°	571.0	534.9	503.9	477.2	456.5	443.8	423.7	407.6	394.6	383.5	373.9
50°	530.4	500.4	470.4	446.7	428.0	409.9	389.2	381.1	361.1	355.5	349.8
52.5°	493.4	465.0	437.5	414.3	395.5	377.9	359.7	349.1	335.7	330.0	325.9
55°	441.7	414.3	388.0	367.4	348.6	330.5	319.3	306.1	299.9	295.5	290.5
57.5°	389.7	365.0	344.9	324.0	305.2	290.7	277.8	269.9	263.4	257.6	251.7
60°	356.8	333.0	314.9	295.5	276.1	264.2	254.3	244.9	237.4	228.7	226.2
62.5°	321.7	301.0	284.4	265.5	248.7	237.8	228.3	219.4	210.4	197.7	194.2
65°	273.6	257.4	239.9	224.3	209.3	198.7	184.9	175.0	171.2	169.9	169.3
67.5°	230.2	214.8	199.8	183.8	170.2	160.3	153.4	151.8	149.2	148.5	146.7
70°	201.2	186.8	171.8	156.8	143.7	141.9	139.3	136.8	133.7	132.5	131.2
72.5°	175.2	160.3	145.3	133.3	127.7	125.3	122.9	120.3	118.2	117.0	116.2
75°	134.4	120.6	110.6	106.2	103.1	101.2	97.4	95.6	94.3	92.5	91.8
77.5°	96.7	88.9	84.4	81.6	78.4	76.3	74.2	72.3	71.0	70.6	69.6
80°	73.7	70.0	66.9	63.1	61.9	59.4	58.7	56.8	57.5	55.6	55.6
82.5°	57.2	52.5	49.9	48.1	46.9	44.8	44.3	43.4	43.5	42.1	42.1
85°	29.4	28.1	26.9	25.6	25.6	23.7	24.4	23.7	23.7	22.5	21.9
87.5°	11.4	11.5	11.3	12.1	12.9	13.2	13.1	12.6	12.5	12.4	11.9
90°	9.5	12.6	16.6	20.5	24.5	28.5	28.1	27.7	27.4	27.1	26.9
92.5°	20.9	22.1	23.1	24.0	24.9	25.8	25.9	26.0	26.1	26.2	26.3
95°	49.6	50.6	51.0	51.4	51.7	52.1	52.1	52.1	52.1	52.1	51.9
97.5°	83.6	84.8	85.5	86.2	86.8	87.6	87.6	87.6	87.6	87.6	87.6
100°	109.1	110.1	110.6	111.2	111.8	112.3	112.3	112.3	112.3	112.3	112.2
102.5°	135.3	136.2	136.9	137.6	138.3	139.0	139.1	139.3	139.4	139.6	139.5
105°	177.1	177.6	177.9	178.3	178.6	179.0	179.4	179.7	180.1	180.4	180.6
107.5°	222.7	223.1	223.1	223.1	223.1	223.1	223.2	223.4	223.6	223.6	223.3
110°	252.5	253.1	253.1	253.1	253.1	253.1	253.1	253.1	253.1	253.1	252.7



TEST NUMBER: P331754-930

CATALOG NUMBER: SA2XXRDIP-C1005D925U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	283.7	284.2	284.1	283.9	283.8	283.6	283.2	282.7	282.3	281.9	281.4
115°	329.8	330.1	329.8	329.5	329.1	328.7	328.6	328.3	328.2	328.0	327.6
117.5°	377.2	377.3	376.3	375.3	374.3	373.3	372.8	372.4	372.0	371.5	371.0
120°	407.7	407.7	406.3	404.8	403.4	401.9	401.9	401.9	401.9	401.9	401.7
122.5°	436.8	437.2	436.2	435.2	434.2	433.2	432.8	432.3	431.9	431.5	431.0
125°	480.0	480.6	480.0	479.5	479.0	478.4	477.8	477.4	476.8	476.2	475.9
127.5°	524.2	525.0	524.3	523.7	523.0	522.4	521.7	521.1	520.4	519.8	519.1
130°	552.1	553.1	552.7	552.4	552.0	551.6	551.3	550.9	550.6	550.2	549.7
132.5°	580.3	581.3	581.4	581.5	581.5	581.6	580.8	580.0	579.2	578.4	577.7
135°	620.6	621.8	622.2	622.5	622.9	623.2	623.1	622.9	622.7	622.5	622.2
137.5°	661.3	662.3	662.8	663.3	663.8	664.2	664.1	664.0	663.8	663.7	663.2
140°	686.7	687.9	688.8	689.7	690.7	691.6	691.6	691.6	691.6	691.6	691.2
142.5°	712.7	713.9	714.4	715.1	715.7	716.3	716.5	716.6	716.7	716.9	716.6
145°	748.7	749.9	751.0	752.0	753.2	754.2	754.4	754.6	754.8	755.0	754.7
147.5°	783.1	784.2	785.0	785.6	786.4	787.1	787.5	787.9	788.3	788.7	788.6
150°	804.1	805.0	805.8	806.5	807.2	808.0	808.5	809.0	809.6	810.1	810.1
152.5°	824.3	825.3	826.1	827.0	827.9	828.8	829.5	830.1	830.8	831.5	831.5
155°	852.4	853.0	853.5	854.0	854.6	855.1	856.1	857.0	857.9	858.8	858.9
157.5°	877.6	877.9	878.2	878.6	878.9	879.2	880.4	881.7	882.9	884.1	884.3
160°	893.2	893.5	893.6	893.8	894.0	894.1	895.3	896.3	897.4	898.5	898.7
162.5°	906.4	906.4	906.7	906.9	907.0	907.2	908.4	909.6	910.9	912.1	912.3
165°	924.4	924.3	924.3	924.3	924.3	924.3	925.5	926.8	928.1	929.4	929.5
167.5°	938.9	938.6	938.6	938.5	938.5	938.4	939.7	940.9	942.2	943.5	943.6
170°	947.3	947.0	946.8	946.6	946.4	946.2	947.5	948.8	950.1	951.3	951.4
172.5°	953.2	952.8	952.7	952.4	952.3	952.1	953.4	954.6	955.9	957.2	957.2
175°	960.3	959.9	959.5	959.2	958.8	958.5	959.7	961.0	962.2	963.5	963.6
177.5°	963.7	963.4	963.0	962.8	962.5	962.2	963.0	963.9	964.8	965.6	965.6
180°	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2



TEST NUMBER: P331754-930

CATALOG NUMBER: SA2XXRDIP-C1005D925U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1
2.5°	1726.6	1727.6	1726.2	1727.1	1726.2	1727.6	1726.6	1732.1	1733.1	1734.1	1733.1
5°	1608.7	1601.2	1600.0	1598.1	1600.0	1601.2	1608.7	1611.9	1614.4	1619.4	1628.2
7.5°	1468.1	1467.0	1463.9	1459.5	1463.9	1467.0	1468.1	1478.8	1487.4	1497.1	1514.9
10°	1377.6	1374.5	1373.9	1369.5	1373.9	1374.5	1377.6	1391.4	1401.3	1415.1	1439.5
12.5°	1271.6	1251.6	1249.4	1238.5	1249.4	1251.6	1271.6	1289.4	1316.4	1329.7	1355.5
15°	1082.7	1079.0	1066.5	1058.3	1066.5	1079.0	1082.7	1097.7	1107.7	1143.9	1185.9
17.5°	974.8	962.5	958.6	956.9	958.6	962.5	974.8	982.0	996.3	1015.4	1040.6
20°	905.3	894.1	892.2	891.0	892.2	894.1	905.3	914.0	925.3	945.9	972.2
22.5°	857.3	845.5	840.7	836.9	840.7	845.5	857.3	864.1	874.3	890.4	908.2
25°	775.3	770.9	768.5	767.2	768.5	770.9	775.3	781.6	791.6	813.4	832.2
27.5°	711.3	701.6	699.8	696.5	699.8	701.6	711.3	722.4	732.7	742.6	759.4
30°	674.7	671.6	667.2	663.5	667.2	671.6	674.7	680.4	687.2	704.1	720.4
32.5°	631.8	629.2	625.3	623.5	625.3	629.2	631.8	639.4	653.8	664.1	675.9
35°	584.2	575.4	571.7	566.1	571.7	575.4	584.2	590.4	596.1	604.8	626.0
37.5°	533.8	529.2	523.9	525.8	523.9	529.2	533.8	536.5	548.3	560.4	569.6
40°	494.8	491.7	490.5	489.8	490.5	491.7	494.8	503.0	517.3	522.9	536.7
42.5°	463.8	455.2	451.9	451.8	451.9	455.2	463.8	473.0	481.8	491.0	505.2
45°	416.7	408.6	403.0	403.6	403.0	408.6	416.7	419.9	427.4	445.5	453.6
47.5°	368.5	368.3	364.8	365.8	364.8	368.3	368.5	373.9	383.5	394.6	407.6
50°	345.5	341.8	339.2	339.9	339.2	341.8	345.5	349.8	355.5	361.1	381.1
52.5°	323.5	320.2	318.3	320.9	318.3	320.2	323.5	325.9	330.0	335.7	349.1
55°	287.4	283.6	283.0	282.4	283.0	283.6	287.4	290.5	295.5	299.9	306.1
57.5°	247.0	244.5	240.8	239.1	240.8	244.5	247.0	251.7	257.6	263.4	269.9
60°	218.0	213.0	206.8	206.2	206.8	213.0	218.0	226.2	228.7	237.4	244.9
62.5°	191.5	190.5	189.3	189.1	189.3	190.5	191.5	194.2	197.7	210.4	219.4
65°	168.0	167.5	168.0	168.7	168.0	167.5	168.0	169.3	169.9	171.2	175.0
67.5°	146.4	145.3	144.2	144.7	144.2	145.3	146.4	146.7	148.5	149.2	151.8
70°	130.0	129.3	128.7	128.7	128.7	129.3	130.0	131.2	132.5	133.7	136.8
72.5°	114.0	113.8	113.2	112.7	113.2	113.8	114.0	116.2	117.0	118.2	120.3
75°	91.2	89.9	89.9	89.9	89.9	89.9	91.2	91.8	92.5	94.3	95.6
77.5°	69.5	68.8	68.2	67.8	68.2	68.8	69.5	69.6	70.6	71.0	72.3
80°	55.0	54.4	53.7	53.7	53.7	54.4	55.0	55.6	55.6	57.5	56.8
82.5°	42.0	41.3	41.3	40.8	41.3	41.3	42.0	42.1	42.1	43.5	43.4
85°	22.5	23.2	22.5	23.7	22.5	23.2	22.5	21.9	22.5	23.7	23.7
87.5°	11.9	11.5	12.0	11.5	12.0	11.5	11.9	11.9	12.4	12.5	12.6
90°	27.1	27.3	27.5	27.6	27.5	27.3	27.1	26.9	27.1	27.4	27.7
92.5°	26.3	26.3	26.3	26.3	26.3	26.3	26.3	26.3	26.2	26.1	26.0
95°	51.5	51.2	50.8	50.5	50.8	51.2	51.5	51.9	52.1	52.1	52.1
97.5°	87.5	87.5	87.4	87.4	87.4	87.5	87.5	87.6	87.6	87.6	87.6
100°	112.0	111.9	111.6	111.5	111.6	111.9	112.0	112.2	112.3	112.3	112.3
102.5°	139.3	139.2	139.0	138.8	139.0	139.2	139.3	139.5	139.6	139.4	139.3
105°	180.6	180.6	180.6	180.6	180.6	180.6	180.6	180.6	180.4	180.1	179.7
107.5°	222.5	221.7	220.9	220.0	220.9	221.7	222.5	223.3	223.6	223.6	223.4
110°	252.3	251.7	251.1	250.6	251.1	251.7	252.3	252.7	253.1	253.1	253.1



TEST NUMBER: P331754-930

CATALOG NUMBER: SA2XXRDIP-C1005D925U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	281.1	280.7	280.3	279.9	280.3	280.7	281.1	281.4	281.9	282.3	282.7
115°	327.1	326.5	326.0	325.5	326.0	326.5	327.1	327.6	328.0	328.2	328.3
117.5°	370.6	370.0	369.4	368.9	369.4	370.0	370.6	371.0	371.5	372.0	372.4
120°	401.1	400.6	400.1	399.5	400.1	400.6	401.1	401.7	401.9	401.9	401.9
122.5°	430.6	430.2	429.8	429.4	429.8	430.2	430.6	431.0	431.5	431.9	432.3
125°	475.7	475.5	475.3	475.2	475.3	475.5	475.7	475.9	476.2	476.8	477.4
127.5°	518.5	518.0	517.4	516.8	517.4	518.0	518.5	519.1	519.8	520.4	521.1
130°	548.9	548.2	547.5	546.7	547.5	548.2	548.9	549.7	550.2	550.6	550.9
132.5°	577.2	576.6	576.0	575.4	576.0	576.6	577.2	577.7	578.4	579.2	580.0
135°	621.6	621.1	620.5	620.0	620.5	621.1	621.6	622.2	622.5	622.7	622.9
137.5°	662.5	661.8	661.0	660.3	661.0	661.8	662.5	663.2	663.7	663.8	664.0
140°	690.5	689.7	689.1	688.4	689.1	689.7	690.5	691.2	691.6	691.6	691.6
142.5°	715.9	715.2	714.4	713.7	714.4	715.2	715.9	716.6	716.9	716.7	716.6
145°	754.0	753.3	752.5	751.8	752.5	753.3	754.0	754.7	755.0	754.8	754.6
147.5°	787.9	787.2	786.5	785.8	786.5	787.2	787.9	788.6	788.7	788.3	787.9
150°	809.6	809.0	808.5	808.0	808.5	809.0	809.6	810.1	810.1	809.6	809.0
152.5°	830.8	830.1	829.5	828.8	829.5	830.1	830.8	831.5	831.5	830.8	830.1
155°	858.3	857.9	857.3	856.7	857.3	857.9	858.3	858.9	858.8	857.9	857.0
157.5°	883.5	882.6	881.7	880.8	881.7	882.6	883.5	884.3	884.1	882.9	881.7
160°	898.0	897.2	896.5	895.8	896.5	897.2	898.0	898.7	898.5	897.4	896.3
162.5°	911.4	910.5	909.7	908.8	909.7	910.5	911.4	912.3	912.1	910.9	909.6
165°	928.6	927.7	926.8	925.9	926.8	927.7	928.6	929.5	929.4	928.1	926.8
167.5°	942.7	941.8	940.9	939.9	940.9	941.8	942.7	943.6	943.5	942.2	940.9
170°	950.3	949.3	948.1	947.1	948.1	949.3	950.3	951.4	951.3	950.1	948.8
172.5°	956.2	955.1	954.0	952.9	954.0	955.1	956.2	957.2	957.2	955.9	954.6
175°	962.5	961.4	960.3	959.3	960.3	961.4	962.5	963.6	963.5	962.2	961.0
177.5°	964.8	963.9	963.0	962.2	963.0	963.9	964.8	965.6	965.6	964.8	963.9
180°	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2



TEST NUMBER: P331754-930

CATALOG NUMBER: SA2XXRDIP-C1005D925U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1
2.5°	1729.1	1736.1	1746.6	1752.6	1762.6	1769.1	1772.6	1779.1	1782.6	1795.1	1808.1
5°	1632.6	1642.5	1660.0	1676.3	1693.8	1711.9	1725.0	1740.0	1753.7	1777.4	1802.5
7.5°	1521.8	1535.7	1562.8	1588.7	1619.2	1644.8	1667.4	1693.0	1715.9	1749.9	1785.3
10°	1438.8	1463.2	1498.8	1523.2	1563.2	1588.8	1624.4	1652.5	1684.4	1729.3	1769.4
12.5°	1367.3	1396.8	1425.4	1459.2	1495.2	1537.8	1577.0	1613.1	1650.9	1697.4	1744.3
15°	1237.7	1280.2	1324.5	1358.9	1407.6	1452.6	1498.2	1546.9	1593.2	1648.8	1710.0
17.5°	1070.7	1120.0	1194.6	1253.4	1310.7	1355.8	1412.3	1471.2	1525.7	1592.8	1660.9
20°	995.2	1031.5	1082.1	1161.5	1247.7	1295.8	1353.2	1418.2	1480.7	1553.8	1626.9
22.5°	934.7	967.0	1007.6	1069.5	1165.7	1231.3	1291.3	1357.2	1429.7	1504.3	1585.4
25°	848.4	870.9	913.4	963.4	1029.6	1137.7	1203.3	1269.5	1348.3	1428.2	1520.7
27.5°	783.6	803.8	831.4	879.1	928.4	1006.0	1110.4	1182.6	1261.0	1351.0	1447.0
30°	734.1	757.8	788.5	822.2	876.0	936.5	1040.9	1124.6	1202.1	1294.5	1397.0
32.5°	698.1	716.9	743.0	777.2	822.0	880.0	963.4	1065.1	1140.6	1238.0	1345.0
35°	639.1	661.0	682.2	714.8	751.0	804.0	867.2	975.9	1050.8	1147.0	1254.5
37.5°	590.5	603.9	627.4	653.1	691.4	731.0	785.7	883.2	964.3	1058.7	1168.7
40°	553.5	570.4	587.9	616.6	647.9	686.0	739.7	812.2	905.3	997.8	1105.2
42.5°	517.6	538.9	557.4	576.7	610.9	649.0	692.8	754.2	849.3	936.8	1041.2
45°	474.2	488.0	507.3	528.6	556.7	589.1	627.9	681.6	772.8	848.4	946.6
47.5°	423.7	443.8	456.5	477.2	503.9	534.9	571.0	617.4	691.2	762.1	853.0
50°	389.2	409.9	428.0	446.7	470.4	500.4	530.4	575.4	634.8	709.1	794.1
52.5°	359.7	377.9	395.5	414.3	437.5	465.0	493.4	533.0	583.8	652.2	734.6
55°	319.3	330.5	348.6	367.4	388.0	414.3	441.7	474.8	518.5	576.0	642.9
57.5°	277.8	290.7	305.2	324.0	344.9	365.0	389.7	419.7	454.2	506.2	563.5
60°	254.3	264.2	276.1	295.5	314.9	333.0	356.8	381.7	414.3	459.2	507.9
62.5°	228.3	237.8	248.7	265.5	284.4	301.0	321.7	348.2	375.8	416.7	459.4
65°	184.9	198.7	209.3	224.3	239.9	257.4	273.6	294.9	319.3	351.7	389.9
67.5°	153.4	160.3	170.2	183.8	199.8	214.8	230.2	246.8	267.9	293.0	323.3
70°	139.3	141.9	143.7	156.8	171.8	186.8	201.2	216.8	234.9	255.5	281.8
72.5°	122.9	125.3	127.7	133.3	145.3	160.3	175.2	186.8	203.9	221.0	242.3
75°	97.4	101.2	103.1	106.2	110.6	120.6	134.4	145.5	155.6	168.7	185.6
77.5°	74.2	76.3	78.4	81.6	84.4	88.9	96.7	106.8	116.2	123.8	135.4
80°	58.7	59.4	61.9	63.1	66.9	70.0	73.7	81.9	91.2	94.3	102.5
82.5°	44.3	44.8	46.9	48.1	49.9	52.5	57.2	59.4	66.7	70.8	76.0
85°	24.4	23.7	25.6	25.6	26.9	28.1	29.4	32.4	34.3	39.4	40.6
87.5°	13.1	13.2	12.9	12.1	11.3	11.5	11.4	11.5	12.1	13.1	14.7
90°	28.1	28.5	24.5	20.5	16.6	12.6	9.5	7.3	5.1	3.0	0.8
92.5°	25.9	25.8	24.9	24.0	23.1	22.1	20.9	19.2	17.7	16.1	14.5
95°	52.1	52.1	51.7	51.4	51.0	50.6	49.6	47.7	45.9	44.1	42.3
97.5°	87.6	87.6	86.8	86.2	85.5	84.8	83.6	82.1	80.5	78.9	77.3
100°	112.3	112.3	111.8	111.2	110.6	110.1	109.1	107.7	106.2	104.8	103.3
102.5°	139.1	139.0	138.3	137.6	136.9	136.2	135.3	134.1	133.0	131.8	130.7
105°	179.4	179.0	178.6	178.3	177.9	177.6	177.1	176.6	176.0	175.5	175.0
107.5°	223.2	223.1	223.1	223.1	223.1	223.1	222.7	221.9	221.1	220.3	219.5
110°	253.1	253.1	253.1	253.1	253.1	253.1	252.5	251.4	250.3	249.2	248.2



TEST NUMBER: P331754-930

CATALOG NUMBER: SA2XXRDIP-C1005D925U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	283.2	283.6	283.8	283.9	284.1	284.2	283.7	282.7	281.6	280.5	279.4
115°	328.6	328.7	329.1	329.5	329.8	330.1	329.8	328.7	327.6	326.5	325.5
117.5°	372.8	373.3	374.3	375.3	376.3	377.3	377.2	375.7	374.2	372.8	371.4
120°	401.9	401.9	403.4	404.8	406.3	407.7	407.7	406.3	404.8	403.4	401.9
122.5°	432.8	433.2	434.2	435.2	436.2	437.2	436.8	435.1	433.4	431.6	429.9
125°	477.8	478.4	479.0	479.5	480.0	480.6	480.0	478.4	476.8	475.2	473.5
127.5°	521.7	522.4	523.0	523.7	524.3	525.0	524.2	522.2	520.2	518.0	516.0
130°	551.3	551.6	552.0	552.4	552.7	553.1	552.1	549.8	547.4	545.0	542.7
132.5°	580.8	581.6	581.5	581.5	581.4	581.3	580.3	578.4	576.5	574.5	572.7
135°	623.1	623.2	622.9	622.5	622.2	621.8	620.6	618.6	616.6	614.7	612.7
137.5°	664.1	664.2	663.8	663.3	662.8	662.3	661.3	659.7	658.0	656.4	654.8
140°	691.6	691.6	690.7	689.7	688.8	687.9	686.7	685.1	683.5	681.8	680.2
142.5°	716.5	716.3	715.7	715.1	714.4	713.9	712.7	711.1	709.5	707.8	706.2
145°	754.4	754.2	753.2	752.0	751.0	749.9	748.7	747.5	746.2	744.9	743.6
147.5°	787.5	787.1	786.4	785.6	785.0	784.2	783.1	781.5	780.1	778.5	777.0
150°	808.5	808.0	807.2	806.5	805.8	805.0	804.1	803.1	801.9	800.9	799.8
152.5°	829.5	828.8	827.9	827.0	826.1	825.3	824.3	823.2	822.1	821.1	819.9
155°	856.1	855.1	854.6	854.0	853.5	853.0	852.4	851.9	851.3	850.8	850.3
157.5°	880.4	879.2	878.9	878.6	878.2	877.9	877.6	877.2	876.9	876.4	876.1
160°	895.3	894.1	894.0	893.8	893.6	893.5	893.2	892.8	892.4	892.1	891.8
162.5°	908.4	907.2	907.0	906.9	906.7	906.4	906.4	906.3	906.2	906.1	906.0
165°	925.5	924.3	924.3	924.3	924.3	924.3	924.4	924.5	924.7	925.0	925.1
167.5°	939.7	938.4	938.5	938.5	938.6	938.6	938.9	939.4	940.0	940.5	941.0
170°	947.5	946.2	946.4	946.6	946.8	947.0	947.3	947.9	948.4	948.9	949.5
172.5°	953.4	952.1	952.3	952.4	952.7	952.8	953.2	953.7	954.3	954.8	955.4
175°	959.7	958.5	958.8	959.2	959.5	959.9	960.3	960.9	961.4	962.0	962.5
177.5°	963.0	962.2	962.5	962.8	963.0	963.4	963.7	964.2	964.6	965.0	965.5
180°	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2



TEST NUMBER: P331754-930

CATALOG NUMBER: SA2XXRDIP-C1005D925U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1
2.5°	1808.6	1810.0	1820.1	1824.6	1833.6	1837.0	1841.1	1840.0	1840.0	1842.1	1856.0
5°	1812.5	1825.0	1843.7	1861.8	1879.3	1894.3	1904.3	1914.3	1918.1	1936.2	1952.4
7.5°	1806.0	1829.0	1859.9	1887.6	1920.7	1946.5	1968.1	1987.4	2000.7	2027.0	2054.0
10°	1797.5	1829.9	1864.9	1900.5	1946.1	1980.5	2015.5	2042.4	2051.1	2090.5	2113.0
12.5°	1780.5	1824.0	1868.4	1914.6	1959.2	2006.5	2045.0	2071.8	2102.6	2138.0	2179.5
15°	1755.0	1805.0	1863.0	1922.4	1986.2	2043.6	2084.9	2131.7	2165.4	2204.2	2240.4
17.5°	1718.4	1782.7	1856.6	1925.3	1999.0	2060.8	2117.5	2162.4	2186.2	2208.3	2213.7
20°	1689.4	1758.8	1845.6	1926.8	2000.5	2071.8	2127.9	2165.4	2171.7	2172.3	2139.2
22.5°	1657.9	1736.3	1827.1	1910.3	1998.5	2077.7	2121.5	2137.5	2112.7	2070.4	2006.3
25°	1600.0	1690.6	1796.2	1891.2	1987.4	2062.4	2077.4	2049.3	1962.4	1871.2	1755.6
27.5°	1537.3	1639.2	1752.3	1857.9	1960.4	2006.9	1974.5	1873.2	1716.8	1580.8	1416.0
30°	1491.3	1605.7	1716.9	1834.9	1929.9	1949.9	1875.6	1726.2	1543.8	1338.9	1174.6
32.5°	1438.8	1558.7	1680.9	1803.0	1882.4	1863.0	1740.1	1556.3	1342.4	1140.9	985.6
35°	1363.8	1487.6	1619.4	1741.9	1792.4	1708.1	1524.4	1285.2	1066.5	878.4	771.6
37.5°	1277.2	1412.0	1549.1	1661.5	1657.9	1517.4	1267.1	1020.1	836.3	725.1	649.0
40°	1215.8	1352.0	1500.1	1595.1	1554.4	1371.3	1100.2	867.2	732.9	644.2	588.6
42.5°	1156.8	1293.6	1440.6	1516.0	1445.4	1220.4	950.3	767.7	656.9	587.7	542.6
45°	1056.5	1200.8	1337.0	1378.8	1252.6	1004.6	768.5	636.0	562.3	511.0	479.8
47.5°	958.4	1100.3	1224.7	1225.4	1054.8	814.7	648.2	550.4	487.5	447.8	425.1
50°	898.4	1033.4	1137.7	1121.4	927.8	724.7	579.8	495.5	443.0	412.4	388.6
52.5°	831.0	961.9	1052.2	1006.0	820.4	637.7	518.3	447.4	404.0	377.3	356.1
55°	732.9	849.1	912.8	842.8	669.1	530.4	438.0	382.4	349.8	327.3	309.2
57.5°	636.5	732.4	772.5	691.0	551.1	439.9	370.5	328.7	296.5	280.4	271.0
60°	576.0	657.9	686.0	596.1	479.2	384.8	328.0	289.3	265.5	254.9	245.6
62.5°	516.6	583.4	595.0	512.6	417.8	336.9	288.0	255.3	239.5	229.4	220.5
65°	428.6	476.7	471.1	404.9	330.5	267.4	231.8	211.8	199.9	185.6	169.9
67.5°	352.9	382.2	364.5	314.9	252.3	207.8	184.6	169.4	154.7	141.0	137.5
70°	304.9	321.7	303.0	257.4	206.8	174.3	155.6	137.5	128.7	125.6	119.9
72.5°	258.9	264.8	244.5	205.5	168.3	144.3	126.0	115.9	111.2	108.6	104.9
75°	194.3	190.0	172.4	141.9	116.8	100.6	95.0	91.2	88.1	85.6	83.7
77.5°	136.5	130.0	114.5	94.5	81.4	73.6	70.2	68.2	66.7	65.5	63.6
80°	102.5	98.1	82.5	67.5	61.9	58.1	56.3	53.7	53.7	52.5	50.6
82.5°	75.0	70.1	56.5	49.5	46.4	44.1	42.7	41.3	40.8	41.0	39.6
85°	39.4	31.9	28.1	26.9	25.0	23.7	24.4	23.2	23.2	23.2	22.5
87.5°	12.6	10.5	10.4	10.4	11.5	12.3	12.6	13.4	14.7	14.1	14.5
90°	3.0	5.1	7.3	9.5	12.6	16.6	20.5	24.5	28.5	28.1	27.7
92.5°	16.1	17.7	19.2	20.9	22.1	23.1	24.0	24.9	25.8	25.9	26.0
95°	44.1	45.9	47.7	49.6	50.6	51.0	51.4	51.7	52.1	52.1	52.1
97.5°	78.9	80.5	82.1	83.6	84.8	85.5	86.2	86.8	87.6	87.6	87.6
100°	104.8	106.2	107.7	109.1	110.1	110.6	111.2	111.8	112.3	112.3	112.3
102.5°	131.8	133.0	134.1	135.3	136.2	136.9	137.6	138.3	139.0	139.1	139.3
105°	175.5	176.0	176.6	177.1	177.6	177.9	178.3	178.6	179.0	179.4	179.7
107.5°	220.3	221.1	221.9	222.7	223.1	223.1	223.1	223.1	223.1	223.2	223.4
110°	249.2	250.3	251.4	252.5	253.1	253.1	253.1	253.1	253.1	253.1	253.1



TEST NUMBER: P331754-930

CATALOG NUMBER: SA2XXRDIP-C1005D925U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	280.5	281.6	282.7	283.7	284.2	284.1	283.9	283.8	283.6	283.2	282.7
115°	326.5	327.6	328.7	329.8	330.1	329.8	329.5	329.1	328.7	328.6	328.3
117.5°	372.8	374.2	375.7	377.2	377.3	376.3	375.3	374.3	373.3	372.8	372.4
120°	403.4	404.8	406.3	407.7	407.7	406.3	404.8	403.4	401.9	401.9	401.9
122.5°	431.6	433.4	435.1	436.8	437.2	436.2	435.2	434.2	433.2	432.8	432.3
125°	475.2	476.8	478.4	480.0	480.6	480.0	479.5	479.0	478.4	477.8	477.4
127.5°	518.0	520.2	522.2	524.2	525.0	524.3	523.7	523.0	522.4	521.7	521.1
130°	545.0	547.4	549.8	552.1	553.1	552.7	552.4	552.0	551.6	551.3	550.9
132.5°	574.5	576.5	578.4	580.3	581.3	581.4	581.5	581.5	581.6	580.8	580.0
135°	614.7	616.6	618.6	620.6	621.8	622.2	622.5	622.9	623.2	623.1	622.9
137.5°	656.4	658.0	659.7	661.3	662.3	662.8	663.3	663.8	664.2	664.1	664.0
140°	681.8	683.5	685.1	686.7	687.9	688.8	689.7	690.7	691.6	691.6	691.6
142.5°	707.8	709.5	711.1	712.7	713.9	714.4	715.1	715.7	716.3	716.5	716.6
145°	744.9	746.2	747.5	748.7	749.9	751.0	752.0	753.2	754.2	754.4	754.6
147.5°	778.5	780.1	781.5	783.1	784.2	785.0	785.6	786.4	787.1	787.5	787.9
150°	800.9	801.9	803.1	804.1	805.0	805.8	806.5	807.2	808.0	808.5	809.0
152.5°	821.1	822.1	823.2	824.3	825.3	826.1	827.0	827.9	828.8	829.5	830.1
155°	850.8	851.3	851.9	852.4	853.0	853.5	854.0	854.6	855.1	856.1	857.0
157.5°	876.4	876.9	877.2	877.6	877.9	878.2	878.6	878.9	879.2	880.4	881.7
160°	892.1	892.4	892.8	893.2	893.5	893.6	893.8	894.0	894.1	895.3	896.3
162.5°	906.1	906.2	906.3	906.4	906.4	906.7	906.9	907.0	907.2	908.4	909.6
165°	925.0	924.7	924.5	924.4	924.3	924.3	924.3	924.3	924.3	925.5	926.8
167.5°	940.5	940.0	939.4	938.9	938.6	938.6	938.5	938.5	938.4	939.7	940.9
170°	948.9	948.4	947.9	947.3	947.0	946.8	946.6	946.4	946.2	947.5	948.8
172.5°	954.8	954.3	953.7	953.2	952.8	952.7	952.4	952.3	952.1	953.4	954.6
175°	962.0	961.4	960.9	960.3	959.9	959.5	959.2	958.8	958.5	959.7	961.0
177.5°	965.0	964.6	964.2	963.7	963.4	963.0	962.8	962.5	962.2	963.0	963.9
180°	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2	964.2



TEST NUMBER: P331754-930

CATALOG NUMBER: SA2XXRDIP-C1005D925U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1
2.5°	1861.1	1867.5	1870.5	1870.5	1874.0	1872.6	1871.0
5°	1968.1	1979.9	1982.4	1993.7	2001.7	1999.3	2000.5
7.5°	2074.4	2093.4	2112.4	2121.0	2122.3	2127.4	2129.2
10°	2139.8	2155.5	2184.8	2180.4	2202.3	2214.8	2194.2
12.5°	2202.8	2223.9	2244.3	2249.9	2262.3	2266.3	2258.1
15°	2259.8	2271.0	2272.3	2269.1	2272.9	2269.8	2257.9
17.5°	2206.5	2188.3	2151.3	2133.8	2119.9	2099.5	2091.2
20°	2118.6	2064.8	2002.4	1977.4	1948.0	1890.5	1904.3
22.5°	1928.7	1867.4	1805.0	1732.0	1697.1	1642.7	1639.4
25°	1633.1	1527.5	1411.4	1330.2	1282.6	1228.3	1204.5
27.5°	1269.7	1136.9	1041.6	993.4	949.5	906.4	904.7
30°	1030.9	930.9	857.2	816.0	789.0	770.9	774.7
32.5°	868.9	800.5	750.7	716.5	696.6	683.0	682.7
35°	710.4	663.5	631.6	617.3	602.9	592.9	593.5
37.5°	607.9	579.8	562.1	546.2	537.2	532.3	529.5
40°	555.4	532.3	518.5	509.2	501.7	494.8	493.6
42.5°	514.0	494.8	481.1	473.7	466.7	461.9	460.6
45°	456.1	440.4	428.0	419.9	416.7	412.4	412.4
47.5°	405.7	390.4	380.6	375.5	370.1	367.2	367.1
50°	371.8	359.9	351.1	348.0	343.6	341.8	341.1
52.5°	341.3	332.4	326.1	324.0	322.1	319.8	320.2
55°	299.9	294.9	292.4	290.5	287.4	283.6	286.2
57.5°	265.1	260.8	254.0	248.2	245.3	242.6	243.7
60°	240.5	231.8	223.1	216.1	214.3	208.6	208.6
62.5°	209.5	197.3	186.5	182.7	180.8	178.2	177.7
65°	161.2	156.2	153.7	151.2	149.9	149.9	148.7
67.5°	133.5	131.6	128.8	128.2	126.9	126.6	126.2
70°	118.1	115.6	114.3	113.7	112.4	113.1	111.2
72.5°	103.1	101.1	100.9	99.2	98.5	98.6	97.2
75°	81.2	81.2	80.6	80.0	78.8	78.1	78.8
77.5°	62.5	62.6	61.5	61.4	61.2	61.4	60.7
80°	50.0	50.6	50.0	49.3	48.8	49.3	48.8
82.5°	39.5	38.6	38.5	38.4	38.2	37.8	37.7
85°	22.5	23.2	22.5	21.9	21.9	21.9	22.5
87.5°	13.9	13.9	13.9	13.9	13.9	14.0	13.5
90°	27.4	27.1	26.9	27.1	27.3	27.5	27.6
92.5°	26.1	26.2	26.3	26.3	26.3	26.3	26.3
95°	52.1	52.1	51.9	51.5	51.2	50.8	50.5
97.5°	87.6	87.6	87.6	87.5	87.5	87.4	87.4
100°	112.3	112.3	112.2	112.0	111.9	111.6	111.5
102.5°	139.4	139.6	139.5	139.3	139.2	139.0	138.8
105°	180.1	180.4	180.6	180.6	180.6	180.6	180.6
107.5°	223.6	223.6	223.3	222.5	221.7	220.9	220.0
110°	253.1	253.1	252.7	252.3	251.7	251.1	250.6



TEST NUMBER: P331754-930

CATALOG NUMBER: SA2XXRDIP-C1005D925U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	282.3	281.9	281.4	281.1	280.7	280.3	279.9
115°	328.2	328.0	327.6	327.1	326.5	326.0	325.5
117.5°	372.0	371.5	371.0	370.6	370.0	369.4	368.9
120°	401.9	401.9	401.7	401.1	400.6	400.1	399.5
122.5°	431.9	431.5	431.0	430.6	430.2	429.8	429.4
125°	476.8	476.2	475.9	475.7	475.5	475.3	475.2
127.5°	520.4	519.8	519.1	518.5	518.0	517.4	516.8
130°	550.6	550.2	549.7	548.9	548.2	547.5	546.7
132.5°	579.2	578.4	577.7	577.2	576.6	576.0	575.4
135°	622.7	622.5	622.2	621.6	621.1	620.5	620.0
137.5°	663.8	663.7	663.2	662.5	661.8	661.0	660.3
140°	691.6	691.6	691.2	690.5	689.7	689.1	688.4
142.5°	716.7	716.9	716.6	715.9	715.2	714.4	713.7
145°	754.8	755.0	754.7	754.0	753.3	752.5	751.8
147.5°	788.3	788.7	788.6	787.9	787.2	786.5	785.8
150°	809.6	810.1	810.1	809.6	809.0	808.5	808.0
152.5°	830.8	831.5	831.5	830.8	830.1	829.5	828.8
155°	857.9	858.8	858.9	858.3	857.9	857.3	856.7
157.5°	882.9	884.1	884.3	883.5	882.6	881.7	880.8
160°	897.4	898.5	898.7	898.0	897.2	896.5	895.8
162.5°	910.9	912.1	912.3	911.4	910.5	909.7	908.8
165°	928.1	929.4	929.5	928.6	927.7	926.8	925.9
167.5°	942.2	943.5	943.6	942.7	941.8	940.9	939.9
170°	950.1	951.3	951.4	950.3	949.3	948.1	947.1
172.5°	955.9	957.2	957.2	956.2	955.1	954.0	952.9
175°	962.2	963.5	963.6	962.5	961.4	960.3	959.3
177.5°	964.8	965.6	965.6	964.8	963.9	963.0	962.2
180°	964.2	964.2	964.2	964.2	964.2	964.2	964.2

(END OF REPORT)