

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331438-840

Luminaire Tested: **SA2XXDIP-C1005D725U840-4F0-1E-UDD-A**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331438-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXDIP-C1005D725U840-4F0-1E-UDD-A  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 725 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7370.8 lumens  
Efficiency: N/A  
Efficacy: 121.4 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 60.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331438-840  
CATALOG NUMBER: SA2XXDIP-C1005D725U840-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P331438-840

CATALOG NUMBER: SA2XXDIP-C1005D725U840-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20				
RC	80					70					50					30				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	66	66	66	60		
1	101	96	93	89	94	90	87	84	79	77	74	69	67	65	59	58	57	52		
2	92	85	79	74	86	80	75	70	70	66	63	61	58	55	53	50	49	44		
3	84	75	68	62	79	71	64	59	62	57	53	54	51	48	47	44	42	38		
4	78	67	59	53	72	63	56	51	56	50	46	49	45	41	42	39	37	33		
5	72	60	52	46	67	57	50	44	50	45	40	44	40	36	39	35	32	29		
6	66	54	46	40	62	51	44	39	46	40	35	40	36	32	35	32	29	26		
7	61	49	41	36	57	47	39	34	41	36	31	37	32	29	32	29	26	23		
8	57	45	37	32	53	43	36	31	38	32	28	34	29	26	30	26	23	21		
9	53	41	34	29	50	39	32	28	35	29	25	31	27	23	28	24	21	19		
10	50	38	31	26	47	36	29	25	32	27	23	29	24	21	26	22	19	18		

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	32513	32513	32513	32513
5°	36451	32725	29000	32725
10°	41769	32455	25097	32455
15°	46208	31861	22173	31861
20°	45505	31223	20213	31223
25°	41031	30375	18971	30375
30°	33907	29015	18066	29015
35°	24711	27595	17420	27595
40°	19736	25918	17062	25918
45°	17249	23980	16575	23980
50°	16211	22102	16252	22102
55°	14945	20194	15817	20194
60°	13695	18167	15145	18167
65°	12478	16351	14487	16351
70°	11325	14578	13520	14578
75°	10044	12601	11977	12601
80°	8638	10432	9642	10432
85°	7744	7744	5743	7744



TEST NUMBER: P331438-840

CATALOG NUMBER: SA2XXDIP-C1005D725U840-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	191.8	2.6
10°-20°	557.5	7.6
20°-30°	809.1	11.0
30°-40°	853.9	11.6
40°-50°	756.0	10.3
50°-60°	603.3	8.2
60°-70°	410.1	5.6
70°-80°	210.2	2.9
80°-90°	53.1	0.7
90°-100°	33.3	0.5
100°-110°	122.1	1.7
110°-120°	326.4	4.4
120°-130°	538.9	7.3
130°-140°	573.1	7.8
140°-150°	532.7	7.2
150°-160°	428.3	5.8
160°-170°	276.0	3.7
170°-180°	95.0	1.3
0°-30°	1558.5	21.1
0°-40°	2412.3	32.7
0°-60°	3771.7	51.2
0°-90°	4445.1	60.3
90°-120°	481.9	6.5
90°-150°	2126.5	28.8
90°-180°	2926.0	39.7
0°-180°	7370.8	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	2014	2014	2014	2014	2014	
5°	2249	2019	1789	2019	2249	225
15°	2764	1906	1326	1906	2764	763
25°	2303	1705	1065	1705	2303	1041
35°	1254	1400	884	1400	1254	815
45°	755	1050	726	1050	755	594
55°	531	717	562	717	531	476
65°	327	428	379	428	327	325
75°	161	202	192	202	161	172
85°	42	42	31	42	42	46
90°	20	1	20	1	20	11
95°	31	47	31	47	31	29
105°	55	220	55	220	55	57
115°	59	415	59	415	59	148
125°	618	587	618	587	618	534
135°	750	727	750	727	750	578
145°	856	843	856	843	856	535
155°	929	928	929	928	929	429
165°	976	978	976	978	976	276
175°	995	1000	995	1000	995	95
180°	998	998	998	998	998	



TEST NUMBER: P331438-840  
 CATALOG NUMBER: SA2XXDIP-C1005D725U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7
2.5°	2106.6	2107.2	2108.4	2098.5	2097.3	2097.3	2088.6	2081.2	2072.5	2060.7	2062.0
5°	2249.0	2257.5	2260.6	2251.3	2237.4	2235.8	2222.7	2201.0	2180.9	2164.6	2153.0
7.5°	2418.9	2422.4	2414.8	2402.6	2392.2	2373.6	2349.1	2325.1	2291.6	2260.8	2237.9
10°	2547.7	2552.3	2539.2	2521.4	2506.7	2485.1	2449.4	2413.1	2368.9	2326.4	2292.3
12.5°	2645.5	2657.0	2640.1	2637.8	2612.6	2582.8	2540.4	2522.0	2459.9	2400.7	2364.2
15°	2764.4	2763.6	2765.2	2750.5	2731.9	2727.2	2682.4	2633.6	2546.2	2511.3	2450.9
17.5°	2730.1	2741.8	2747.2	2747.0	2746.6	2743.7	2729.3	2698.5	2654.6	2598.2	2528.5
20°	2648.4	2663.8	2666.1	2683.9	2694.0	2707.1	2712.6	2704.0	2677.0	2629.8	2569.4
22.5°	2522.0	2526.4	2533.7	2561.3	2583.1	2616.2	2633.3	2661.9	2651.6	2628.5	2578.1
25°	2303.2	2295.4	2322.5	2336.4	2386.7	2439.3	2477.3	2519.1	2556.3	2578.7	2563.9
27.5°	2040.3	2028.7	2069.3	2106.3	2147.2	2204.1	2263.2	2333.0	2391.1	2463.7	2488.6
30°	1818.7	1825.6	1864.3	1903.8	1965.7	2046.2	2112.7	2189.4	2272.2	2353.5	2409.9
32.5°	1579.7	1606.5	1630.9	1691.4	1746.0	1835.7	1933.2	2029.0	2132.3	2224.7	2312.2
35°	1253.7	1284.6	1318.8	1362.8	1439.5	1528.4	1623.7	1752.9	1893.8	2019.9	2123.6
37.5°	1055.3	1050.4	1069.9	1101.8	1163.8	1235.7	1345.2	1472.9	1638.7	1787.0	1933.2
40°	936.4	933.3	947.3	976.6	1023.9	1076.5	1172.5	1284.6	1438.7	1619.8	1793.9
42.5°	854.7	856.6	864.3	885.0	917.4	960.7	1032.6	1128.0	1269.1	1439.7	1626.8
45°	755.4	760.7	769.3	779.3	797.9	833.5	873.7	941.9	1053.3	1195.7	1379.9
47.5°	683.8	684.0	692.7	701.5	712.5	732.6	765.4	808.1	886.8	1002.7	1161.0
50°	645.4	640.1	646.2	653.2	664.8	678.7	700.3	740.6	793.2	886.9	1019.3
52.5°	598.3	598.5	604.1	606.7	617.1	631.1	650.9	678.7	726.4	799.6	908.4
55°	530.9	534.7	537.9	542.5	551.8	561.9	577.3	595.9	633.1	688.0	768.5
57.5°	467.5	468.7	471.8	480.6	486.5	495.7	510.5	527.4	551.5	592.2	652.7
60°	424.1	424.1	430.3	434.1	441.9	451.2	462.8	479.1	500.7	534.0	582.8
62.5°	384.5	383.8	386.4	392.6	398.6	407.3	418.8	432.6	453.0	482.6	522.7
65°	326.6	325.1	329.7	331.2	337.4	346.0	355.3	369.9	386.2	407.9	443.4
67.5°	270.8	272.8	275.2	278.1	281.6	290.5	296.7	307.1	320.8	338.8	362.9
70°	239.9	239.9	239.9	242.3	246.9	251.6	257.7	266.2	279.4	294.9	316.5
72.5°	205.2	207.7	210.2	208.8	214.7	217.4	224.9	229.7	242.3	252.2	271.4
75°	161.0	161.0	161.0	164.8	167.1	169.5	174.1	178.7	185.0	197.3	207.4
77.5°	120.1	119.8	120.6	121.5	124.0	126.7	128.2	132.3	138.0	143.8	152.3
80°	92.9	94.4	95.2	96.7	96.7	98.3	99.1	104.5	108.4	112.2	117.6
82.5°	71.8	72.1	72.3	72.6	73.2	74.1	76.1	77.9	79.3	82.5	86.6
85°	41.8	41.0	41.0	42.5	41.8	41.8	43.3	44.8	44.8	45.6	48.0
87.5°	20.0	19.9	20.5	19.8	19.7	20.3	20.1	19.3	19.8	20.2	20.6
90°	19.5	19.2	18.9	18.6	18.2	17.7	16.9	16.1	15.2	14.4	13.1
92.5°	19.5	19.3	19.1	18.9	18.8	18.4	18.0	17.6	17.2	16.8	16.2
95°	31.1	31.2	31.4	31.5	31.7	31.4	30.6	29.8	29.0	28.2	27.1
97.5°	41.5	41.3	41.1	40.9	40.7	40.3	39.6	39.0	38.4	37.7	35.1
100°	48.4	48.1	47.8	47.5	47.2	46.4	45.0	43.7	42.4	41.2	38.5
102.5°	51.9	51.4	51.0	50.5	50.1	49.0	47.4	45.6	44.0	42.3	65.1
105°	54.9	54.2	53.6	53.0	52.3	51.1	49.4	47.6	45.8	44.0	87.9
107.5°	56.5	55.8	55.2	54.5	53.9	54.5	56.2	58.1	59.9	61.7	114.2
110°	57.1	56.5	55.7	55.1	54.5	62.2	78.3	94.3	110.4	126.4	172.8



TEST NUMBER: P331438-840

CATALOG NUMBER: SA2XXDIP-C1005D725U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	57.7	57.2	56.7	56.1	55.5	84.6	143.2	201.8	260.3	318.8	330.3
115°	59.3	70.8	82.3	93.9	105.4	148.5	222.8	297.1	371.4	445.8	441.7
117.5°	241.9	279.8	317.8	355.8	393.7	421.7	439.7	457.8	475.7	493.7	490.9
120°	440.7	462.3	484.0	505.6	527.4	537.2	535.3	533.4	531.4	529.5	526.6
122.5°	549.9	554.1	558.3	562.5	566.7	568.3	567.0	565.9	564.7	563.6	560.5
125°	617.6	617.1	616.7	616.2	615.7	614.9	613.8	612.7	611.6	610.5	607.3
127.5°	660.5	660.4	660.2	660.1	660.0	659.1	657.5	655.9	654.3	652.6	650.4
130°	687.0	687.1	687.3	687.5	687.6	686.8	685.1	683.3	681.6	679.7	678.0
132.5°	713.0	713.2	713.4	713.5	713.7	713.0	711.4	709.9	708.4	706.9	705.2
135°	750.5	750.8	751.2	751.5	751.8	751.2	749.6	748.0	746.4	744.8	743.4
137.5°	784.8	785.4	785.9	786.5	787.0	786.5	784.9	783.4	781.7	780.2	778.5
140°	806.2	807.0	807.8	808.6	809.4	809.1	807.6	806.2	804.8	803.3	801.5
142.5°	827.0	827.8	828.6	829.4	830.2	829.9	828.6	827.3	826.0	824.7	822.6
145°	856.1	856.9	857.7	858.5	859.2	859.1	858.0	856.9	855.8	854.5	851.8
147.5°	881.6	882.3	882.9	883.6	884.3	884.2	883.4	882.5	881.7	880.9	878.2
150°	897.2	898.0	898.8	899.6	900.4	900.3	899.4	898.4	897.5	896.5	893.9
152.5°	910.5	911.6	912.6	913.7	914.7	914.8	913.8	912.8	911.9	910.9	908.5
155°	929.0	930.3	931.6	932.8	934.1	934.3	933.3	932.4	931.4	930.4	928.5
157.5°	945.9	947.2	948.4	949.7	950.9	951.0	949.9	948.8	947.8	946.6	945.2
160°	955.7	956.8	958.0	959.1	960.2	960.3	959.4	958.4	957.5	956.4	955.4
162.5°	963.8	965.2	966.5	968.0	969.4	969.5	968.4	967.2	966.2	965.1	964.3
165°	975.9	977.0	978.2	979.4	980.5	980.5	979.4	978.2	977.0	975.9	975.4
167.5°	983.6	985.0	986.5	988.0	989.4	989.6	988.5	987.3	986.1	985.0	984.6
170°	988.3	989.7	991.1	992.6	994.0	994.2	993.0	991.9	990.8	989.7	989.4
172.5°	991.7	993.1	994.6	996.0	997.4	997.6	996.5	995.4	994.3	993.1	992.8
175°	994.7	996.3	997.9	999.6	1001.2	1001.4	1000.3	999.2	998.0	996.9	996.5
177.5°	996.6	997.7	999.0	1000.1	1001.3	1001.4	1000.5	999.6	998.7	997.7	997.6
180°	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4



TEST NUMBER: P331438-840

CATALOG NUMBER: SA2XXDIP-C1005D725U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7
2.5°	2066.4	2061.4	2058.3	2047.2	2037.2	2027.3	2024.3	2025.5	2011.9	1998.8	1993.3
5°	2146.9	2131.3	2116.7	2095.8	2071.0	2043.9	2029.9	2019.1	1992.1	1962.7	1945.6
7.5°	2219.0	2196.9	2168.5	2129.2	2093.1	2050.5	2023.5	1999.4	1959.8	1918.3	1893.0
10°	2262.9	2232.7	2196.4	2148.4	2104.3	2052.4	2016.0	1979.6	1933.2	1883.7	1852.7
12.5°	2300.7	2260.0	2224.2	2162.6	2110.4	2045.6	2002.5	1951.2	1902.3	1843.4	1813.1
15°	2390.7	2315.5	2247.5	2177.8	2113.5	2023.0	1975.0	1906.1	1841.9	1769.2	1734.3
17.5°	2460.1	2375.7	2268.5	2180.0	2105.1	2004.8	1934.3	1851.8	1775.8	1692.7	1645.4
20°	2499.7	2403.0	2287.6	2182.4	2092.6	1978.1	1901.5	1817.2	1728.2	1634.5	1583.5
22.5°	2523.2	2421.6	2307.5	2173.1	2067.9	1956.4	1860.0	1767.6	1677.4	1576.3	1522.8
25°	2530.7	2437.8	2317.1	2165.5	2036.9	1910.8	1794.7	1705.0	1595.8	1501.4	1423.2
27.5°	2493.9	2427.3	2311.2	2150.8	2001.1	1853.7	1724.2	1622.6	1507.4	1404.9	1326.4
30°	2448.6	2409.9	2296.9	2136.0	1972.7	1814.0	1671.6	1556.3	1441.8	1338.1	1257.6
32.5°	2378.7	2370.4	2271.0	2115.0	1942.4	1763.9	1616.6	1500.0	1373.1	1271.2	1194.5
35°	2241.3	2278.4	2215.7	2067.9	1885.2	1692.5	1533.1	1400.0	1268.5	1170.9	1098.9
37.5°	2057.1	2149.3	2132.9	1999.0	1808.2	1614.9	1438.9	1299.7	1174.4	1075.9	1005.3
40°	1930.2	2047.8	2064.8	1946.4	1753.7	1554.8	1368.3	1229.7	1107.4	1017.7	946.4
42.5°	1793.9	1931.4	1978.1	1883.2	1694.3	1491.7	1305.1	1161.6	1040.6	953.3	890.2
45°	1565.6	1747.5	1831.9	1777.7	1595.1	1387.7	1195.7	1050.2	940.3	858.3	809.5
47.5°	1352.2	1551.0	1664.4	1645.2	1484.7	1279.3	1089.5	949.9	842.9	777.5	733.9
50°	1201.1	1405.4	1542.4	1548.6	1405.4	1201.8	1011.5	879.9	781.6	720.5	684.9
52.5°	1069.9	1264.9	1414.2	1447.0	1316.9	1121.4	941.5	810.6	724.1	667.9	636.0
55°	898.5	1063.4	1229.0	1289.3	1184.9	999.2	832.7	717.4	636.1	597.4	569.6
57.5°	747.0	884.4	1037.3	1104.1	1039.7	880.7	724.7	624.5	558.7	524.7	503.3
60°	667.1	775.5	911.7	991.4	935.6	794.1	657.8	562.6	508.5	478.3	458.2
62.5°	592.8	688.8	804.0	876.9	846.5	713.0	591.0	507.0	460.2	431.8	417.3
65°	489.1	564.9	654.0	721.2	701.1	599.8	500.0	428.0	390.8	368.4	356.8
67.5°	402.7	457.6	519.3	578.2	562.0	490.2	410.0	354.0	326.3	306.9	299.9
70°	348.3	390.0	445.0	492.2	479.1	420.2	356.8	308.8	284.8	268.5	261.6
72.5°	296.3	330.6	372.5	411.1	402.2	353.4	300.4	264.2	245.8	230.8	225.1
75°	223.7	249.9	275.5	301.0	298.7	260.8	229.8	202.0	187.3	175.7	173.4
77.5°	165.1	179.9	197.2	212.4	208.1	186.5	162.2	146.2	135.4	127.6	126.4
80°	126.1	134.6	147.0	157.8	152.5	143.2	123.8	112.2	104.5	96.7	93.6
82.5°	91.5	100.0	107.4	113.3	109.2	100.5	88.6	80.7	76.0	70.7	69.5
85°	48.0	52.6	55.7	57.3	55.7	50.3	44.8	41.8	38.0	35.6	34.8
87.5°	20.9	20.7	20.4	21.4	19.2	18.8	16.0	13.7	13.5	13.2	12.3
90°	11.9	10.6	9.3	7.8	6.1	4.2	2.5	0.7	2.5	4.2	6.1
92.5°	15.5	14.8	14.2	13.9	14.1	14.2	14.4	14.5	14.4	14.2	14.1
95°	26.0	24.8	23.6	25.8	31.1	36.4	41.7	47.0	41.7	36.4	31.1
97.5°	32.5	29.9	27.3	33.4	48.4	63.3	78.3	93.2	78.3	63.3	48.4
100°	35.7	33.0	30.3	39.9	61.9	83.9	105.8	127.8	105.8	83.9	61.9
102.5°	88.0	110.8	133.6	147.3	152.1	156.7	161.4	166.0	161.4	156.7	152.1
105°	131.7	175.5	219.3	238.8	234.1	229.2	224.4	219.6	224.4	229.2	234.1
107.5°	166.8	219.3	272.0	296.3	292.4	288.5	284.6	280.7	284.6	288.5	292.4
110°	219.2	265.6	311.9	333.5	330.1	326.8	323.4	320.0	323.4	326.8	330.1





TEST NUMBER: P331438-840

CATALOG NUMBER: SA2XXDIP-C1005D725U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	341.7	353.3	364.7	368.9	366.0	362.9	360.0	357.0	360.0	362.9	366.0
115°	437.7	433.6	429.7	426.3	423.5	420.8	418.1	415.4	418.1	420.8	423.5
117.5°	488.2	485.4	482.6	479.7	476.7	473.6	470.6	467.6	470.6	473.6	476.7
120°	523.7	520.9	518.0	515.3	512.9	510.5	508.1	505.6	508.1	510.5	512.9
122.5°	557.3	554.2	551.0	548.2	545.6	543.1	540.6	538.1	540.6	543.1	545.6
125°	604.3	601.3	598.2	595.6	593.6	591.5	589.4	587.3	589.4	591.5	593.6
127.5°	648.0	645.8	643.5	641.2	638.8	636.6	634.3	632.0	634.3	636.6	638.8
130°	676.2	674.5	672.7	670.6	667.9	665.4	662.9	660.2	662.9	665.4	667.9
132.5°	703.4	701.7	699.8	697.9	695.7	693.6	691.4	689.1	691.4	693.6	695.7
135°	741.8	740.4	739.0	737.0	734.5	731.8	729.3	726.7	729.3	731.8	734.5
137.5°	776.9	775.3	773.7	771.9	770.1	768.3	766.5	764.8	766.5	768.3	770.1
140°	799.8	798.0	796.3	794.7	793.5	792.1	790.8	789.6	790.8	792.1	793.5
142.5°	820.6	818.6	816.6	815.0	813.9	812.7	811.5	810.4	811.5	812.7	813.9
145°	849.1	846.4	843.6	842.4	842.5	842.7	842.8	843.0	842.8	842.7	842.5
147.5°	875.5	872.8	870.1	869.1	869.7	870.3	870.9	871.5	870.9	870.3	869.7
150°	891.3	888.8	886.3	885.4	886.7	887.8	888.9	890.0	888.9	887.8	886.7
152.5°	906.1	903.6	901.2	900.6	901.8	903.1	904.3	905.5	904.3	903.1	901.8
155°	926.6	924.6	922.7	922.5	923.9	925.3	926.9	928.3	926.9	925.3	923.9
157.5°	943.9	942.6	941.2	941.2	942.4	943.6	944.8	946.0	944.8	943.6	942.4
160°	954.5	953.5	952.6	952.6	953.5	954.5	955.4	956.4	955.4	954.5	953.5
162.5°	963.4	962.6	961.8	961.8	962.8	963.8	964.7	965.7	964.7	963.8	962.8
165°	975.0	974.5	974.0	974.2	975.2	976.2	977.1	978.2	977.1	976.2	975.2
167.5°	984.1	983.7	983.2	983.5	984.5	985.4	986.4	987.3	986.4	985.4	984.5
170°	989.1	988.8	988.4	988.8	989.7	990.7	991.6	992.6	991.6	990.7	989.7
172.5°	992.5	992.2	991.9	992.2	993.1	994.1	995.0	996.0	995.0	994.1	993.1
175°	996.2	995.9	995.6	996.0	997.1	998.3	999.4	1000.5	999.4	998.3	997.1
177.5°	997.5	997.3	997.2	997.6	998.6	999.5	1000.4	1001.3	1000.4	999.5	998.6
180°	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4



TEST NUMBER: P331438-840  
 CATALOG NUMBER: SA2XXDIP-C1005D725U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7
2.5°	1987.1	1983.4	1970.3	1963.6	1952.5	1941.9	1935.1	1938.2	1940.7	1939.4	1937.5
5°	1930.2	1915.4	1893.0	1873.6	1859.7	1834.2	1823.3	1818.0	1813.3	1807.9	1802.4
7.5°	1862.3	1839.2	1807.0	1779.4	1753.3	1721.6	1703.5	1692.7	1681.5	1669.3	1658.5
10°	1814.0	1781.5	1747.5	1708.8	1677.9	1649.2	1623.7	1606.6	1591.1	1576.5	1565.6
12.5°	1763.3	1725.9	1683.7	1630.8	1596.7	1555.7	1551.9	1521.9	1497.6	1488.5	1475.8
15°	1682.4	1629.8	1576.5	1513.8	1486.7	1449.6	1426.3	1403.1	1382.2	1367.5	1363.6
17.5°	1590.7	1522.6	1469.5	1424.4	1380.1	1342.0	1320.6	1302.0	1284.9	1265.2	1262.5
20°	1520.8	1461.9	1403.9	1364.4	1318.8	1280.0	1253.7	1235.2	1220.4	1208.8	1198.8
22.5°	1454.5	1390.1	1337.0	1293.8	1248.8	1217.5	1196.8	1178.8	1166.6	1153.8	1144.3
25°	1348.2	1297.9	1239.8	1191.0	1153.9	1133.8	1116.7	1101.3	1093.6	1085.0	1074.2
27.5°	1255.2	1199.2	1144.9	1107.1	1074.5	1056.7	1044.6	1034.1	1026.8	1021.9	1015.7
30°	1189.5	1133.0	1090.5	1053.3	1026.2	1008.5	1000.7	994.5	985.9	982.9	979.8
32.5°	1126.3	1075.4	1039.1	1006.8	981.0	969.4	962.3	956.7	950.1	947.0	940.8
35°	1037.0	994.5	958.9	941.1	920.2	910.1	904.7	897.0	890.8	887.7	886.9
37.5°	953.0	916.0	892.6	869.7	860.9	854.7	847.3	842.0	840.2	839.7	838.9
40°	898.5	868.3	847.5	828.9	825.0	815.7	809.5	804.9	804.9	805.7	804.9
42.5°	849.0	821.9	803.4	787.4	782.8	777.3	771.1	770.8	772.0	774.7	772.0
45°	774.0	754.6	741.4	733.7	725.2	719.7	718.9	721.2	722.1	722.9	725.2
47.5°	704.9	692.1	680.1	671.6	667.9	666.9	666.0	670.0	673.8	675.2	678.7
50°	664.0	649.3	639.2	633.8	630.8	629.1	630.8	635.4	638.4	642.4	644.7
52.5°	618.2	607.8	600.9	596.7	595.4	596.4	596.7	602.0	606.9	608.3	609.4
55°	554.9	547.1	545.6	538.7	541.7	541.0	544.8	548.0	552.6	557.2	558.0
57.5°	491.7	485.5	481.4	482.0	482.9	486.4	489.6	495.0	500.0	504.9	505.3
60°	449.7	446.6	444.2	444.2	445.8	450.4	454.2	459.7	462.8	465.9	468.2
62.5°	411.2	408.2	405.9	407.1	411.1	413.8	418.4	421.3	424.4	427.5	428.6
65°	350.6	349.0	351.3	352.9	353.7	357.6	362.9	365.3	368.4	369.9	375.4
67.5°	294.7	295.0	294.7	296.9	301.3	302.3	307.4	312.9	313.5	316.4	319.9
70°	256.9	258.5	260.0	261.6	265.5	267.0	270.8	273.2	276.3	278.6	280.9
72.5°	222.3	222.6	224.1	223.8	227.0	230.5	233.7	236.0	239.1	242.1	244.4
75°	171.1	171.1	172.6	173.4	177.2	181.1	180.4	181.9	185.0	188.0	189.7
77.5°	124.9	123.2	124.9	125.7	126.9	130.2	130.8	133.0	136.5	135.4	137.1
80°	95.2	92.9	95.2	95.9	95.9	99.9	99.9	101.4	103.7	101.4	103.7
82.5°	68.0	66.9	68.6	68.8	70.0	70.1	71.4	71.7	74.0	72.9	74.0
85°	34.0	33.3	34.0	33.3	34.0	34.8	34.8	34.0	34.0	35.6	33.3
87.5°	12.1	11.8	11.4	11.6	11.3	10.9	10.5	10.6	10.8	9.7	9.8
90°	7.8	9.3	10.6	11.9	13.1	14.4	15.2	16.1	16.9	17.7	18.2
92.5°	13.9	14.2	14.8	15.5	16.2	16.8	17.2	17.6	18.0	18.4	18.8
95°	25.8	23.6	24.8	26.0	27.1	28.2	29.0	29.8	30.6	31.4	31.7
97.5°	33.4	27.3	29.9	32.5	35.1	37.7	38.4	39.0	39.6	40.3	40.7
100°	39.9	30.3	33.0	35.7	38.5	41.2	42.4	43.7	45.0	46.4	47.2
102.5°	147.3	133.6	110.8	88.0	65.1	42.3	44.0	45.6	47.4	49.0	50.1
105°	238.8	219.3	175.5	131.7	87.9	44.0	45.8	47.6	49.4	51.1	52.3
107.5°	296.3	272.0	219.3	166.8	114.2	61.7	59.9	58.1	56.2	54.5	53.9
110°	333.5	311.9	265.6	219.2	172.8	126.4	110.4	94.3	78.3	62.2	54.5



TEST NUMBER: P331438-840

CATALOG NUMBER: SA2XXDIP-C1005D725U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	368.9	364.7	353.3	341.7	330.3	318.8	260.3	201.8	143.2	84.6	55.5
115°	426.3	429.7	433.6	437.7	441.7	445.8	371.4	297.1	222.8	148.5	105.4
117.5°	479.7	482.6	485.4	488.2	490.9	493.7	475.7	457.8	439.7	421.7	393.7
120°	515.3	518.0	520.9	523.7	526.6	529.5	531.4	533.4	535.3	537.2	527.4
122.5°	548.2	551.0	554.2	557.3	560.5	563.6	564.7	565.9	567.0	568.3	566.7
125°	595.6	598.2	601.3	604.3	607.3	610.5	611.6	612.7	613.8	614.9	615.7
127.5°	641.2	643.5	645.8	648.0	650.4	652.6	654.3	655.9	657.5	659.1	660.0
130°	670.6	672.7	674.5	676.2	678.0	679.7	681.6	683.3	685.1	686.8	687.6
132.5°	697.9	699.8	701.7	703.4	705.2	706.9	708.4	709.9	711.4	713.0	713.7
135°	737.0	739.0	740.4	741.8	743.4	744.8	746.4	748.0	749.6	751.2	751.8
137.5°	771.9	773.7	775.3	776.9	778.5	780.2	781.7	783.4	784.9	786.5	787.0
140°	794.7	796.3	798.0	799.8	801.5	803.3	804.8	806.2	807.6	809.1	809.4
142.5°	815.0	816.6	818.6	820.6	822.6	824.7	826.0	827.3	828.6	829.9	830.2
145°	842.4	843.6	846.4	849.1	851.8	854.5	855.8	856.9	858.0	859.1	859.2
147.5°	869.1	870.1	872.8	875.5	878.2	880.9	881.7	882.5	883.4	884.2	884.3
150°	885.4	886.3	888.8	891.3	893.9	896.5	897.5	898.4	899.4	900.3	900.4
152.5°	900.6	901.2	903.6	906.1	908.5	910.9	911.9	912.8	913.8	914.8	914.7
155°	922.5	922.7	924.6	926.6	928.5	930.4	931.4	932.4	933.3	934.3	934.1
157.5°	941.2	941.2	942.6	943.9	945.2	946.6	947.8	948.8	949.9	951.0	950.9
160°	952.6	952.6	953.5	954.5	955.4	956.4	957.5	958.4	959.4	960.3	960.2
162.5°	961.8	961.8	962.6	963.4	964.3	965.1	966.2	967.2	968.4	969.5	969.4
165°	974.2	974.0	974.5	975.0	975.4	975.9	977.0	978.2	979.4	980.5	980.5
167.5°	983.5	983.2	983.7	984.1	984.6	985.0	986.1	987.3	988.5	989.6	989.4
170°	988.8	988.4	988.8	989.1	989.4	989.7	990.8	991.9	993.0	994.2	994.0
172.5°	992.2	991.9	992.2	992.5	992.8	993.1	994.3	995.4	996.5	997.6	997.4
175°	996.0	995.6	995.9	996.2	996.5	996.9	998.0	999.2	1000.3	1001.4	1001.2
177.5°	997.6	997.2	997.3	997.5	997.6	997.7	998.7	999.6	1000.5	1001.4	1001.3
180°	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4



TEST NUMBER: P331438-840

CATALOG NUMBER: SA2XXDIP-C1005D725U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7
2.5°	1931.4	1930.2	1930.2	1924.6	1930.2	1930.2	1931.4	1937.5	1939.4	1940.7	1938.2
5°	1791.6	1789.3	1785.4	1789.3	1785.4	1789.3	1791.6	1802.4	1807.9	1813.3	1818.0
7.5°	1653.4	1644.1	1642.7	1633.6	1642.7	1644.1	1653.4	1658.5	1669.3	1681.5	1692.7
10°	1552.5	1546.3	1545.5	1530.8	1545.5	1546.3	1552.5	1565.6	1576.5	1591.1	1606.6
12.5°	1475.7	1460.9	1463.8	1455.2	1463.8	1460.9	1475.7	1475.8	1488.5	1497.6	1521.9
15°	1342.7	1342.7	1339.7	1326.5	1339.7	1342.7	1342.7	1363.6	1367.5	1382.2	1403.1
17.5°	1247.3	1245.7	1238.3	1241.9	1238.3	1245.7	1247.3	1262.5	1265.2	1284.9	1302.0
20°	1190.2	1185.7	1176.4	1176.4	1176.4	1185.7	1190.2	1198.8	1208.8	1220.4	1235.2
22.5°	1136.4	1136.1	1126.2	1129.3	1126.2	1136.1	1136.4	1144.3	1153.8	1166.6	1178.8
25°	1073.4	1067.2	1062.6	1064.9	1062.6	1067.2	1073.4	1074.2	1085.0	1093.6	1101.3
27.5°	1013.7	1010.3	1010.0	1003.6	1010.0	1010.3	1013.7	1015.7	1021.9	1026.8	1034.1
30°	979.0	971.3	972.8	969.0	972.8	971.3	979.0	979.8	982.9	985.9	994.5
32.5°	939.4	936.5	935.0	931.8	935.0	936.5	939.4	940.8	947.0	950.1	956.7
35°	885.3	886.2	882.2	883.8	882.2	886.2	885.3	886.9	887.7	890.8	897.0
37.5°	838.2	840.6	838.8	839.2	838.8	840.6	838.2	838.9	839.7	840.2	842.0
40°	807.2	807.2	807.2	809.5	807.2	807.2	807.2	804.9	805.7	804.9	804.9
42.5°	777.5	776.3	775.0	774.9	775.0	776.3	777.5	772.0	774.7	772.0	770.8
45°	726.7	729.0	729.8	725.9	729.8	729.0	726.7	725.2	722.9	722.1	721.2
47.5°	680.8	681.1	680.8	684.2	680.8	681.1	680.8	678.7	675.2	673.8	670.0
50°	648.5	647.0	648.5	647.0	648.5	647.0	648.5	644.7	642.4	638.4	635.4
52.5°	614.5	614.8	613.9	613.6	613.9	614.8	614.5	609.4	608.3	606.9	602.0
55°	561.1	562.6	561.9	561.9	561.9	562.6	561.1	558.0	557.2	552.6	548.0
57.5°	505.8	507.3	508.3	504.9	508.3	507.3	505.8	505.3	504.9	500.0	495.0
60°	467.5	471.3	470.5	469.0	470.5	471.3	467.5	468.2	465.9	462.8	459.7
62.5°	432.1	433.5	433.4	433.1	433.4	433.5	432.1	428.6	427.5	424.4	421.3
65°	377.7	379.2	376.9	379.2	376.9	379.2	377.7	375.4	369.9	368.4	365.3
67.5°	319.0	319.5	321.1	322.2	321.1	319.5	319.0	319.9	316.4	313.5	312.9
70°	282.5	281.8	284.1	286.4	284.1	281.8	282.5	280.9	278.6	276.3	273.2
72.5°	244.1	245.8	245.0	246.7	245.0	245.8	244.1	244.4	242.1	239.1	236.0
75°	188.0	190.4	189.7	192.0	189.7	190.4	188.0	189.7	188.0	185.0	181.9
77.5°	135.9	136.2	135.9	137.1	135.9	136.2	135.9	137.1	135.4	136.5	133.0
80°	103.7	102.2	100.6	103.7	100.6	102.2	103.7	103.7	101.4	103.7	101.4
82.5°	72.1	73.0	71.5	71.5	71.5	73.0	72.1	74.0	72.9	74.0	71.7
85°	33.3	32.5	31.0	31.0	31.0	32.5	33.3	33.3	35.6	34.0	34.0
87.5°	9.9	9.4	9.4	8.9	9.4	9.4	9.9	9.8	9.7	10.8	10.6
90°	18.6	18.9	19.2	19.5	19.2	18.9	18.6	18.2	17.7	16.9	16.1
92.5°	18.9	19.1	19.3	19.5	19.3	19.1	18.9	18.8	18.4	18.0	17.6
95°	31.5	31.4	31.2	31.1	31.2	31.4	31.5	31.7	31.4	30.6	29.8
97.5°	40.9	41.1	41.3	41.5	41.3	41.1	40.9	40.7	40.3	39.6	39.0
100°	47.5	47.8	48.1	48.4	48.1	47.8	47.5	47.2	46.4	45.0	43.7
102.5°	50.5	51.0	51.4	51.9	51.4	51.0	50.5	50.1	49.0	47.4	45.6
105°	53.0	53.6	54.2	54.9	54.2	53.6	53.0	52.3	51.1	49.4	47.6
107.5°	54.5	55.2	55.8	56.5	55.8	55.2	54.5	53.9	54.5	56.2	58.1
110°	55.1	55.7	56.5	57.1	56.5	55.7	55.1	54.5	62.2	78.3	94.3



TEST NUMBER: P331438-840

CATALOG NUMBER: SA2XXDIP-C1005D725U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	56.1	56.7	57.2	57.7	57.2	56.7	56.1	55.5	84.6	143.2	201.8
115°	93.9	82.3	70.8	59.3	70.8	82.3	93.9	105.4	148.5	222.8	297.1
117.5°	355.8	317.8	279.8	241.9	279.8	317.8	355.8	393.7	421.7	439.7	457.8
120°	505.6	484.0	462.3	440.7	462.3	484.0	505.6	527.4	537.2	535.3	533.4
122.5°	562.5	558.3	554.1	549.9	554.1	558.3	562.5	566.7	568.3	567.0	565.9
125°	616.2	616.7	617.1	617.6	617.1	616.7	616.2	615.7	614.9	613.8	612.7
127.5°	660.1	660.2	660.4	660.5	660.4	660.2	660.1	660.0	659.1	657.5	655.9
130°	687.5	687.3	687.1	687.0	687.1	687.3	687.5	687.6	686.8	685.1	683.3
132.5°	713.5	713.4	713.2	713.0	713.2	713.4	713.5	713.7	713.0	711.4	709.9
135°	751.5	751.2	750.8	750.5	750.8	751.2	751.5	751.8	751.2	749.6	748.0
137.5°	786.5	785.9	785.4	784.8	785.4	785.9	786.5	787.0	786.5	784.9	783.4
140°	808.6	807.8	807.0	806.2	807.0	807.8	808.6	809.4	809.1	807.6	806.2
142.5°	829.4	828.6	827.8	827.0	827.8	828.6	829.4	830.2	829.9	828.6	827.3
145°	858.5	857.7	856.9	856.1	856.9	857.7	858.5	859.2	859.1	858.0	856.9
147.5°	883.6	882.9	882.3	881.6	882.3	882.9	883.6	884.3	884.2	883.4	882.5
150°	899.6	898.8	898.0	897.2	898.0	898.8	899.6	900.4	900.3	899.4	898.4
152.5°	913.7	912.6	911.6	910.5	911.6	912.6	913.7	914.7	914.8	913.8	912.8
155°	932.8	931.6	930.3	929.0	930.3	931.6	932.8	934.1	934.3	933.3	932.4
157.5°	949.7	948.4	947.2	945.9	947.2	948.4	949.7	950.9	951.0	949.9	948.8
160°	959.1	958.0	956.8	955.7	956.8	958.0	959.1	960.2	960.3	959.4	958.4
162.5°	968.0	966.5	965.2	963.8	965.2	966.5	968.0	969.4	969.5	968.4	967.2
165°	979.4	978.2	977.0	975.9	977.0	978.2	979.4	980.5	980.5	979.4	978.2
167.5°	988.0	986.5	985.0	983.6	985.0	986.5	988.0	989.4	989.6	988.5	987.3
170°	992.6	991.1	989.7	988.3	989.7	991.1	992.6	994.0	994.2	993.0	991.9
172.5°	996.0	994.6	993.1	991.7	993.1	994.6	996.0	997.4	997.6	996.5	995.4
175°	999.6	997.9	996.3	994.7	996.3	997.9	999.6	1001.2	1001.4	1000.3	999.2
177.5°	1000.1	999.0	997.7	996.6	997.7	999.0	1000.1	1001.3	1001.4	1000.5	999.6
180°	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4



TEST NUMBER: P331438-840

CATALOG NUMBER: SA2XXDIP-C1005D725U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7
2.5°	1935.1	1941.9	1952.5	1963.6	1970.3	1983.4	1987.1	1993.3	1998.8	2011.9	2025.5
5°	1823.3	1834.2	1859.7	1873.6	1893.0	1915.4	1930.2	1945.6	1962.7	1992.1	2019.1
7.5°	1703.5	1721.6	1753.3	1779.4	1807.0	1839.2	1862.3	1893.0	1918.3	1959.8	1999.4
10°	1623.7	1649.2	1677.9	1708.8	1747.5	1781.5	1814.0	1852.7	1883.7	1933.2	1979.6
12.5°	1551.9	1555.7	1596.7	1630.8	1683.7	1725.9	1763.3	1813.1	1843.4	1902.3	1951.2
15°	1426.3	1449.6	1486.7	1513.8	1576.5	1629.8	1682.4	1734.3	1769.2	1841.9	1906.1
17.5°	1320.6	1342.0	1380.1	1424.4	1469.5	1522.6	1590.7	1645.4	1692.7	1775.8	1851.8
20°	1253.7	1280.0	1318.8	1364.4	1403.9	1461.9	1520.8	1583.5	1634.5	1728.2	1817.2
22.5°	1196.8	1217.5	1248.8	1293.8	1337.0	1390.1	1454.5	1522.8	1576.3	1677.4	1767.6
25°	1116.7	1133.8	1153.9	1191.0	1239.8	1297.9	1348.2	1423.2	1501.4	1595.8	1705.0
27.5°	1044.6	1056.7	1074.5	1107.1	1144.9	1199.2	1255.2	1326.4	1404.9	1507.4	1622.6
30°	1000.7	1008.5	1026.2	1053.3	1090.5	1133.0	1189.5	1257.6	1338.1	1441.8	1556.3
32.5°	962.3	969.4	981.0	1006.8	1039.1	1075.4	1126.3	1194.5	1271.2	1373.1	1500.0
35°	904.7	910.1	920.2	941.1	958.9	994.5	1037.0	1098.9	1170.9	1268.5	1400.0
37.5°	847.3	854.7	860.9	869.7	892.6	916.0	953.0	1005.3	1075.9	1174.4	1299.7
40°	809.5	815.7	825.0	828.9	847.5	868.3	898.5	946.4	1017.7	1107.4	1229.7
42.5°	771.1	777.3	782.8	787.4	803.4	821.9	849.0	890.2	953.3	1040.6	1161.6
45°	718.9	719.7	725.2	733.7	741.4	754.6	774.0	809.5	858.3	940.3	1050.2
47.5°	666.0	666.9	667.9	671.6	680.1	692.1	704.9	733.9	777.5	842.9	949.9
50°	630.8	629.1	630.8	633.8	639.2	649.3	664.0	684.9	720.5	781.6	879.9
52.5°	596.7	596.4	595.4	596.7	600.9	607.8	618.2	636.0	667.9	724.1	810.6
55°	544.8	541.0	541.7	538.7	545.6	547.1	554.9	569.6	597.4	636.1	717.4
57.5°	489.6	486.4	482.9	482.0	481.4	485.5	491.7	503.3	524.7	558.7	624.5
60°	454.2	450.4	445.8	444.2	444.2	446.6	449.7	458.2	478.3	508.5	562.6
62.5°	418.4	413.8	411.1	407.1	405.9	408.2	411.2	417.3	431.8	460.2	507.0
65°	362.9	357.6	353.7	352.9	351.3	349.0	350.6	356.8	368.4	390.8	428.0
67.5°	307.4	302.3	301.3	296.9	294.7	295.0	294.7	299.9	306.9	326.3	354.0
70°	270.8	267.0	265.5	261.6	260.0	258.5	256.9	261.6	268.5	284.8	308.8
72.5°	233.7	230.5	227.0	223.8	224.1	222.6	222.3	225.1	230.8	245.8	264.2
75°	180.4	181.1	177.2	173.4	172.6	171.1	171.1	173.4	175.7	187.3	202.0
77.5°	130.8	130.2	126.9	125.7	124.9	123.2	124.9	126.4	127.6	135.4	146.2
80°	99.9	99.9	95.9	95.9	95.2	92.9	95.2	93.6	96.7	104.5	112.2
82.5°	71.4	70.1	70.0	68.8	68.6	66.9	68.0	69.5	70.7	76.0	80.7
85°	34.8	34.8	34.0	33.3	34.0	33.3	34.0	34.8	35.6	38.0	41.8
87.5°	10.5	10.9	11.3	11.6	11.4	11.8	12.1	12.3	13.2	13.5	13.7
90°	15.2	14.4	13.1	11.9	10.6	9.3	7.8	6.1	4.2	2.5	0.7
92.5°	17.2	16.8	16.2	15.5	14.8	14.2	13.9	14.1	14.2	14.4	14.5
95°	29.0	28.2	27.1	26.0	24.8	23.6	25.8	31.1	36.4	41.7	47.0
97.5°	38.4	37.7	35.1	32.5	29.9	27.3	33.4	48.4	63.3	78.3	93.2
100°	42.4	41.2	38.5	35.7	33.0	30.3	39.9	61.9	83.9	105.8	127.8
102.5°	44.0	42.3	65.1	88.0	110.8	133.6	147.3	152.1	156.7	161.4	166.0
105°	45.8	44.0	87.9	131.7	175.5	219.3	238.8	234.1	229.2	224.4	219.6
107.5°	59.9	61.7	114.2	166.8	219.3	272.0	296.3	292.4	288.5	284.6	280.7
110°	110.4	126.4	172.8	219.2	265.6	311.9	333.5	330.1	326.8	323.4	320.0



TEST NUMBER: P331438-840

CATALOG NUMBER: SA2XXDIP-C1005D725U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	260.3	318.8	330.3	341.7	353.3	364.7	368.9	366.0	362.9	360.0	357.0
115°	371.4	445.8	441.7	437.7	433.6	429.7	426.3	423.5	420.8	418.1	415.4
117.5°	475.7	493.7	490.9	488.2	485.4	482.6	479.7	476.7	473.6	470.6	467.6
120°	531.4	529.5	526.6	523.7	520.9	518.0	515.3	512.9	510.5	508.1	505.6
122.5°	564.7	563.6	560.5	557.3	554.2	551.0	548.2	545.6	543.1	540.6	538.1
125°	611.6	610.5	607.3	604.3	601.3	598.2	595.6	593.6	591.5	589.4	587.3
127.5°	654.3	652.6	650.4	648.0	645.8	643.5	641.2	638.8	636.6	634.3	632.0
130°	681.6	679.7	678.0	676.2	674.5	672.7	670.6	667.9	665.4	662.9	660.2
132.5°	708.4	706.9	705.2	703.4	701.7	699.8	697.9	695.7	693.6	691.4	689.1
135°	746.4	744.8	743.4	741.8	740.4	739.0	737.0	734.5	731.8	729.3	726.7
137.5°	781.7	780.2	778.5	776.9	775.3	773.7	771.9	770.1	768.3	766.5	764.8
140°	804.8	803.3	801.5	799.8	798.0	796.3	794.7	793.5	792.1	790.8	789.6
142.5°	826.0	824.7	822.6	820.6	818.6	816.6	815.0	813.9	812.7	811.5	810.4
145°	855.8	854.5	851.8	849.1	846.4	843.6	842.4	842.5	842.7	842.8	843.0
147.5°	881.7	880.9	878.2	875.5	872.8	870.1	869.1	869.7	870.3	870.9	871.5
150°	897.5	896.5	893.9	891.3	888.8	886.3	885.4	886.7	887.8	888.9	890.0
152.5°	911.9	910.9	908.5	906.1	903.6	901.2	900.6	901.8	903.1	904.3	905.5
155°	931.4	930.4	928.5	926.6	924.6	922.7	922.5	923.9	925.3	926.9	928.3
157.5°	947.8	946.6	945.2	943.9	942.6	941.2	941.2	942.4	943.6	944.8	946.0
160°	957.5	956.4	955.4	954.5	953.5	952.6	952.6	953.5	954.5	955.4	956.4
162.5°	966.2	965.1	964.3	963.4	962.6	961.8	961.8	962.8	963.8	964.7	965.7
165°	977.0	975.9	975.4	975.0	974.5	974.0	974.2	975.2	976.2	977.1	978.2
167.5°	986.1	985.0	984.6	984.1	983.7	983.2	983.5	984.5	985.4	986.4	987.3
170°	990.8	989.7	989.4	989.1	988.8	988.4	988.8	989.7	990.7	991.6	992.6
172.5°	994.3	993.1	992.8	992.5	992.2	991.9	992.2	993.1	994.1	995.0	996.0
175°	998.0	996.9	996.5	996.2	995.9	995.6	996.0	997.1	998.3	999.4	1000.5
177.5°	998.7	997.7	997.6	997.5	997.3	997.2	997.6	998.6	999.5	1000.4	1001.3
180°	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4



TEST NUMBER: P331438-840  
 CATALOG NUMBER: SA2XXDIP-C1005D725U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7
2.5°	2024.3	2027.3	2037.2	2047.2	2058.3	2061.4	2066.4	2062.0	2060.7	2072.5	2081.2
5°	2029.9	2043.9	2071.0	2095.8	2116.7	2131.3	2146.9	2153.0	2164.6	2180.9	2201.0
7.5°	2023.5	2050.5	2093.1	2129.2	2168.5	2196.9	2219.0	2237.9	2260.8	2291.6	2325.1
10°	2016.0	2052.4	2104.3	2148.4	2196.4	2232.7	2262.9	2292.3	2326.4	2368.9	2413.1
12.5°	2002.5	2045.6	2110.4	2162.6	2224.2	2260.0	2300.7	2364.2	2400.7	2459.9	2522.0
15°	1975.0	2023.0	2113.5	2177.8	2247.5	2315.5	2390.7	2450.9	2511.3	2546.2	2633.6
17.5°	1934.3	2004.8	2105.1	2180.0	2268.5	2375.7	2460.1	2528.5	2598.2	2654.6	2698.5
20°	1901.5	1978.1	2092.6	2182.4	2287.6	2403.0	2499.7	2569.4	2629.8	2677.0	2704.0
22.5°	1860.0	1956.4	2067.9	2173.1	2307.5	2421.6	2523.2	2578.1	2628.5	2651.6	2661.9
25°	1794.7	1910.8	2036.9	2165.5	2317.1	2437.8	2530.7	2563.9	2578.7	2556.3	2519.1
27.5°	1724.2	1853.7	2001.1	2150.8	2311.2	2427.3	2493.9	2488.6	2463.7	2391.1	2333.0
30°	1671.6	1814.0	1972.7	2136.0	2296.9	2409.9	2448.6	2409.9	2353.5	2272.2	2189.4
32.5°	1616.6	1763.9	1942.4	2115.0	2271.0	2370.4	2378.7	2312.2	2224.7	2132.3	2029.0
35°	1533.1	1692.5	1885.2	2067.9	2215.7	2278.4	2241.3	2123.6	2019.9	1893.8	1752.9
37.5°	1438.9	1614.9	1808.2	1999.0	2132.9	2149.3	2057.1	1933.2	1787.0	1638.7	1472.9
40°	1368.3	1554.8	1753.7	1946.4	2064.8	2047.8	1930.2	1793.9	1619.8	1438.7	1284.6
42.5°	1305.1	1491.7	1694.3	1883.2	1978.1	1931.4	1793.9	1626.8	1439.7	1269.1	1128.0
45°	1195.7	1387.7	1595.1	1777.7	1831.9	1747.5	1565.6	1379.9	1195.7	1053.3	941.9
47.5°	1089.5	1279.3	1484.7	1645.2	1664.4	1551.0	1352.2	1161.0	1002.7	886.8	808.1
50°	1011.5	1201.8	1405.4	1548.6	1542.4	1405.4	1201.1	1019.3	886.9	793.2	740.6
52.5°	941.5	1121.4	1316.9	1447.0	1414.2	1264.9	1069.9	908.4	799.6	726.4	678.7
55°	832.7	999.2	1184.9	1289.3	1229.0	1063.4	898.5	768.5	688.0	633.1	595.9
57.5°	724.7	880.7	1039.7	1104.1	1037.3	884.4	747.0	652.7	592.2	551.5	527.4
60°	657.8	794.1	935.6	991.4	911.7	775.5	667.1	582.8	534.0	500.7	479.1
62.5°	591.0	713.0	846.5	876.9	804.0	688.8	592.8	522.7	482.6	453.0	432.6
65°	500.0	599.8	701.1	721.2	654.0	564.9	489.1	443.4	407.9	386.2	369.9
67.5°	410.0	490.2	562.0	578.2	519.3	457.6	402.7	362.9	338.8	320.8	307.1
70°	356.8	420.2	479.1	492.2	445.0	390.0	348.3	316.5	294.9	279.4	266.2
72.5°	300.4	353.4	402.2	411.1	372.5	330.6	296.3	271.4	252.2	242.3	229.7
75°	229.8	260.8	298.7	301.0	275.5	249.9	223.7	207.4	197.3	185.0	178.7
77.5°	162.2	186.5	208.1	212.4	197.2	179.9	165.1	152.3	143.8	138.0	132.3
80°	123.8	143.2	152.5	157.8	147.0	134.6	126.1	117.6	112.2	108.4	104.5
82.5°	88.6	100.5	109.2	113.3	107.4	100.0	91.5	86.6	82.5	79.3	77.9
85°	44.8	50.3	55.7	57.3	55.7	52.6	48.0	48.0	45.6	44.8	44.8
87.5°	16.0	18.8	19.2	21.4	20.4	20.7	20.9	20.6	20.2	19.8	19.3
90°	2.5	4.2	6.1	7.8	9.3	10.6	11.9	13.1	14.4	15.2	16.1
92.5°	14.4	14.2	14.1	13.9	14.2	14.8	15.5	16.2	16.8	17.2	17.6
95°	41.7	36.4	31.1	25.8	23.6	24.8	26.0	27.1	28.2	29.0	29.8
97.5°	78.3	63.3	48.4	33.4	27.3	29.9	32.5	35.1	37.7	38.4	39.0
100°	105.8	83.9	61.9	39.9	30.3	33.0	35.7	38.5	41.2	42.4	43.7
102.5°	161.4	156.7	152.1	147.3	133.6	110.8	88.0	65.1	42.3	44.0	45.6
105°	224.4	229.2	234.1	238.8	219.3	175.5	131.7	87.9	44.0	45.8	47.6
107.5°	284.6	288.5	292.4	296.3	272.0	219.3	166.8	114.2	61.7	59.9	58.1
110°	323.4	326.8	330.1	333.5	311.9	265.6	219.2	172.8	126.4	110.4	94.3





TEST NUMBER: P331438-840

CATALOG NUMBER: SA2XXDIP-C1005D725U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	360.0	362.9	366.0	368.9	364.7	353.3	341.7	330.3	318.8	260.3	201.8
115°	418.1	420.8	423.5	426.3	429.7	433.6	437.7	441.7	445.8	371.4	297.1
117.5°	470.6	473.6	476.7	479.7	482.6	485.4	488.2	490.9	493.7	475.7	457.8
120°	508.1	510.5	512.9	515.3	518.0	520.9	523.7	526.6	529.5	531.4	533.4
122.5°	540.6	543.1	545.6	548.2	551.0	554.2	557.3	560.5	563.6	564.7	565.9
125°	589.4	591.5	593.6	595.6	598.2	601.3	604.3	607.3	610.5	611.6	612.7
127.5°	634.3	636.6	638.8	641.2	643.5	645.8	648.0	650.4	652.6	654.3	655.9
130°	662.9	665.4	667.9	670.6	672.7	674.5	676.2	678.0	679.7	681.6	683.3
132.5°	691.4	693.6	695.7	697.9	699.8	701.7	703.4	705.2	706.9	708.4	709.9
135°	729.3	731.8	734.5	737.0	739.0	740.4	741.8	743.4	744.8	746.4	748.0
137.5°	766.5	768.3	770.1	771.9	773.7	775.3	776.9	778.5	780.2	781.7	783.4
140°	790.8	792.1	793.5	794.7	796.3	798.0	799.8	801.5	803.3	804.8	806.2
142.5°	811.5	812.7	813.9	815.0	816.6	818.6	820.6	822.6	824.7	826.0	827.3
145°	842.8	842.7	842.5	842.4	843.6	846.4	849.1	851.8	854.5	855.8	856.9
147.5°	870.9	870.3	869.7	869.1	870.1	872.8	875.5	878.2	880.9	881.7	882.5
150°	888.9	887.8	886.7	885.4	886.3	888.8	891.3	893.9	896.5	897.5	898.4
152.5°	904.3	903.1	901.8	900.6	901.2	903.6	906.1	908.5	910.9	911.9	912.8
155°	926.9	925.3	923.9	922.5	922.7	924.6	926.6	928.5	930.4	931.4	932.4
157.5°	944.8	943.6	942.4	941.2	941.2	942.6	943.9	945.2	946.6	947.8	948.8
160°	955.4	954.5	953.5	952.6	952.6	953.5	954.5	955.4	956.4	957.5	958.4
162.5°	964.7	963.8	962.8	961.8	961.8	962.6	963.4	964.3	965.1	966.2	967.2
165°	977.1	976.2	975.2	974.2	974.0	974.5	975.0	975.4	975.9	977.0	978.2
167.5°	986.4	985.4	984.5	983.5	983.2	983.7	984.1	984.6	985.0	986.1	987.3
170°	991.6	990.7	989.7	988.8	988.4	988.8	989.1	989.4	989.7	990.8	991.9
172.5°	995.0	994.1	993.1	992.2	991.9	992.2	992.5	992.8	993.1	994.3	995.4
175°	999.4	998.3	997.1	996.0	995.6	995.9	996.2	996.5	996.9	998.0	999.2
177.5°	1000.4	999.5	998.6	997.6	997.2	997.3	997.5	997.6	997.7	998.7	999.6
180°	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4



TEST NUMBER: P331438-840

CATALOG NUMBER: SA2XXDIP-C1005D725U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7
2.5°	2088.6	2097.3	2097.3	2098.5	2108.4	2107.2	2106.6
5°	2222.7	2235.8	2237.4	2251.3	2260.6	2257.5	2249.0
7.5°	2349.1	2373.6	2392.2	2402.6	2414.8	2422.4	2418.9
10°	2449.4	2485.1	2506.7	2521.4	2539.2	2552.3	2547.7
12.5°	2540.4	2582.8	2612.6	2637.8	2640.1	2657.0	2645.5
15°	2682.4	2727.2	2731.9	2750.5	2765.2	2763.6	2764.4
17.5°	2729.3	2743.7	2746.6	2747.0	2747.2	2741.8	2730.1
20°	2712.6	2707.1	2694.0	2683.9	2666.1	2663.8	2648.4
22.5°	2633.3	2616.2	2583.1	2561.3	2533.7	2526.4	2522.0
25°	2477.3	2439.3	2386.7	2336.4	2322.5	2295.4	2303.2
27.5°	2263.2	2204.1	2147.2	2106.3	2069.3	2028.7	2040.3
30°	2112.7	2046.2	1965.7	1903.8	1864.3	1825.6	1818.7
32.5°	1933.2	1835.7	1746.0	1691.4	1630.9	1606.5	1579.7
35°	1623.7	1528.4	1439.5	1362.8	1318.8	1284.6	1253.7
37.5°	1345.2	1235.7	1163.8	1101.8	1069.9	1050.4	1055.3
40°	1172.5	1076.5	1023.9	976.6	947.3	933.3	936.4
42.5°	1032.6	960.7	917.4	885.0	864.3	856.6	854.7
45°	873.7	833.5	797.9	779.3	769.3	760.7	755.4
47.5°	765.4	732.6	712.5	701.5	692.7	684.0	683.8
50°	700.3	678.7	664.8	653.2	646.2	640.1	645.4
52.5°	650.9	631.1	617.1	606.7	604.1	598.5	598.3
55°	577.3	561.9	551.8	542.5	537.9	534.7	530.9
57.5°	510.5	495.7	486.5	480.6	471.8	468.7	467.5
60°	462.8	451.2	441.9	434.1	430.3	424.1	424.1
62.5°	418.8	407.3	398.6	392.6	386.4	383.8	384.5
65°	355.3	346.0	337.4	331.2	329.7	325.1	326.6
67.5°	296.7	290.5	281.6	278.1	275.2	272.8	270.8
70°	257.7	251.6	246.9	242.3	239.9	239.9	239.9
72.5°	224.9	217.4	214.7	208.8	210.2	207.7	205.2
75°	174.1	169.5	167.1	164.8	161.0	161.0	161.0
77.5°	128.2	126.7	124.0	121.5	120.6	119.8	120.1
80°	99.1	98.3	96.7	96.7	95.2	94.4	92.9
82.5°	76.1	74.1	73.2	72.6	72.3	72.1	71.8
85°	43.3	41.8	41.8	42.5	41.0	41.0	41.8
87.5°	20.1	20.3	19.7	19.8	20.5	19.9	20.0
90°	16.9	17.7	18.2	18.6	18.9	19.2	19.5
92.5°	18.0	18.4	18.8	18.9	19.1	19.3	19.5
95°	30.6	31.4	31.7	31.5	31.4	31.2	31.1
97.5°	39.6	40.3	40.7	40.9	41.1	41.3	41.5
100°	45.0	46.4	47.2	47.5	47.8	48.1	48.4
102.5°	47.4	49.0	50.1	50.5	51.0	51.4	51.9
105°	49.4	51.1	52.3	53.0	53.6	54.2	54.9
107.5°	56.2	54.5	53.9	54.5	55.2	55.8	56.5
110°	78.3	62.2	54.5	55.1	55.7	56.5	57.1



TEST NUMBER: P331438-840

CATALOG NUMBER: SA2XXDIP-C1005D725U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	143.2	84.6	55.5	56.1	56.7	57.2	57.7
115°	222.8	148.5	105.4	93.9	82.3	70.8	59.3
117.5°	439.7	421.7	393.7	355.8	317.8	279.8	241.9
120°	535.3	537.2	527.4	505.6	484.0	462.3	440.7
122.5°	567.0	568.3	566.7	562.5	558.3	554.1	549.9
125°	613.8	614.9	615.7	616.2	616.7	617.1	617.6
127.5°	657.5	659.1	660.0	660.1	660.2	660.4	660.5
130°	685.1	686.8	687.6	687.5	687.3	687.1	687.0
132.5°	711.4	713.0	713.7	713.5	713.4	713.2	713.0
135°	749.6	751.2	751.8	751.5	751.2	750.8	750.5
137.5°	784.9	786.5	787.0	786.5	785.9	785.4	784.8
140°	807.6	809.1	809.4	808.6	807.8	807.0	806.2
142.5°	828.6	829.9	830.2	829.4	828.6	827.8	827.0
145°	858.0	859.1	859.2	858.5	857.7	856.9	856.1
147.5°	883.4	884.2	884.3	883.6	882.9	882.3	881.6
150°	899.4	900.3	900.4	899.6	898.8	898.0	897.2
152.5°	913.8	914.8	914.7	913.7	912.6	911.6	910.5
155°	933.3	934.3	934.1	932.8	931.6	930.3	929.0
157.5°	949.9	951.0	950.9	949.7	948.4	947.2	945.9
160°	959.4	960.3	960.2	959.1	958.0	956.8	955.7
162.5°	968.4	969.5	969.4	968.0	966.5	965.2	963.8
165°	979.4	980.5	980.5	979.4	978.2	977.0	975.9
167.5°	988.5	989.6	989.4	988.0	986.5	985.0	983.6
170°	993.0	994.2	994.0	992.6	991.1	989.7	988.3
172.5°	996.5	997.6	997.4	996.0	994.6	993.1	991.7
175°	1000.3	1001.4	1001.2	999.6	997.9	996.3	994.7
177.5°	1000.5	1001.4	1001.3	1000.1	999.0	997.7	996.6
180°	998.4	998.4	998.4	998.4	998.4	998.4	998.4

(END OF REPORT)