

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331620-930

Luminaire Tested: **SA2XXRDIP-C290D330U930-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331620-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C290D330U930-4F0-1E-UDD-F4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 330 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1885.5 lumens
Efficiency: N/A
Efficacy: 92.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 20.3
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331620-930
CATALOG NUMBER: SA2XXRDIP-C290D330U930-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331620-930

CATALOG NUMBER: SA2XXRDIP-C290D330U930-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	45
1	97	93	89	86	89	85	82	79	71	69	67	58	56	55	46	45	44	38
2	89	82	76	71	81	75	70	66	63	59	56	51	49	47	41	39	38	33
3	81	72	65	59	74	66	60	55	56	51	48	46	43	40	37	34	33	28
4	74	64	56	51	68	59	52	47	50	45	41	41	38	35	33	31	28	25
5	68	57	49	44	63	53	46	41	45	39	35	37	33	30	30	27	25	22
6	63	51	44	38	58	48	41	36	40	35	31	34	30	27	27	25	22	19
7	58	47	39	33	54	43	36	31	37	31	28	31	27	24	25	22	20	17
8	54	42	35	30	50	39	33	28	34	28	25	28	24	21	23	20	18	16
9	51	39	31	27	46	36	30	25	31	26	22	26	22	19	21	19	16	14
10	47	36	29	24	43	33	27	23	28	23	20	24	20	17	20	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6608	6608	6608
5°	6634	6525	6561
10°	6583	6419	6365
15°	6506	6228	6048
20°	6402	5957	5658
25°	6296	5649	5279
30°	6145	5330	4793
35°	6000	4987	4366
40°	5855	4628	3872
45°	5683	4229	3425
50°	5506	3823	2987
55°	5326	3386	2567
60°	5118	2929	2131
65°	4883	2460	1937
70°	4598	2030	1780
75°	4255	1847	1666
80°	3756	1655	1516
85°	2946	1297	1297



TEST NUMBER: P331620-930

CATALOG NUMBER: SA2XXRDIP-C290D330U930-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	38.3	2.0
10°-20°	105.2	5.6
20°-30°	147.7	7.8
30°-40°	161.1	8.5
40°-50°	148.1	7.9
50°-60°	116.3	6.2
60°-70°	75.8	4.0
70°-80°	39.1	2.1
80°-90°	11.5	0.6
90°-100°	59.9	3.2
100°-110°	203.2	10.8
110°-120°	215.9	11.5
120°-130°	177.7	9.4
130°-140°	142.7	7.6
140°-150°	107.9	5.7
150°-160°	75.8	4.0
160°-170°	44.6	2.4
170°-180°	14.5	0.8
0°-30°	291.2	15.4
0°-40°	452.3	24.0
0°-60°	716.7	38.0
0°-90°	843.1	44.7
90°-120°	479.1	25.4
90°-150°	907.4	48.1
90°-180°	1042.0	55.3
0°-180°	1885.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	409	409	409	409	409	
5°	409	407	403	406	405	39
15°	389	385	373	366	362	110
25°	353	341	317	302	296	162
35°	304	285	253	230	222	190
45°	249	223	185	160	150	192
55°	189	160	120	99	91	169
65°	128	98	64	52	51	127
75°	68	43	30	27	27	72
85°	16	8	7	7	7	19
90°	0	4	10	9	10	1
95°	10	25	113	43	33	11
105°	35	53	213	382	325	37
115°	62	78	179	369	427	61
125°	86	102	172	299	347	77
135°	101	121	170	251	287	78
145°	116	133	169	210	229	73
155°	132	142	164	185	193	61
165°	144	148	157	166	169	40
175°	150	150	151	153	152	14
180°	150	150	150	150	150	



TEST NUMBER: P331620-930

CATALOG NUMBER: SA2XXRDIP-C290D330U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	409.3	409.3	409.3	409.3	409.3	409.3	409.3	409.3	409.3	409.3	409.3
2.5°	410.7	410.4	410.1	409.8	409.4	408.9	408.1	407.5	406.8	406.0	406.7
5°	409.3	408.9	408.5	408.1	407.6	406.8	405.8	404.7	403.7	402.6	403.3
7.5°	405.0	404.6	404.0	403.5	403.0	402.1	400.9	399.6	398.4	397.1	397.3
10°	401.5	400.9	400.3	399.7	399.2	398.0	396.4	394.8	393.1	391.5	391.3
12.5°	397.1	396.3	395.6	394.9	394.2	392.8	390.7	388.6	386.5	384.3	383.9
15°	389.2	388.3	387.4	386.5	385.6	383.8	381.0	378.2	375.4	372.6	371.0
17.5°	379.7	378.3	376.9	375.5	374.1	371.7	368.1	364.5	360.9	357.3	355.5
20°	372.6	371.0	369.3	367.6	366.0	363.1	359.0	354.9	350.8	346.7	344.6
22.5°	364.9	363.1	361.2	359.4	357.5	354.2	349.6	345.0	340.4	335.7	333.0
25°	353.4	350.7	348.1	345.4	342.8	338.8	333.3	327.9	322.5	317.1	313.6
27.5°	339.4	336.6	333.7	330.8	327.9	323.4	317.3	311.2	305.1	299.0	295.1
30°	329.6	326.5	323.3	320.2	317.2	312.3	305.7	299.1	292.5	285.9	281.8
32.5°	320.2	316.5	312.8	309.2	305.5	300.4	293.7	286.9	280.2	273.5	268.7
35°	304.4	300.3	296.0	291.9	287.6	281.9	274.7	267.4	260.2	253.0	247.8
37.5°	288.8	284.1	279.5	274.9	270.3	264.2	256.4	248.7	241.0	233.3	227.6
40°	277.8	272.9	267.9	262.9	258.0	251.6	243.6	235.6	227.6	219.6	213.8
42.5°	266.5	261.3	256.1	250.9	245.7	239.0	230.7	222.5	214.3	206.0	200.0
45°	248.9	243.4	237.8	232.4	226.8	219.7	211.1	202.4	193.8	185.2	179.4
47.5°	231.7	225.8	220.0	214.2	208.3	201.0	192.0	183.1	174.1	165.3	159.5
50°	219.2	213.4	207.6	201.7	195.9	188.4	179.4	170.3	161.3	152.2	146.5
52.5°	207.1	201.0	194.9	188.8	182.7	175.2	166.3	157.5	148.6	139.7	134.3
55°	189.2	182.9	176.4	170.0	163.5	156.0	147.0	138.1	129.2	120.3	115.4
57.5°	171.0	164.4	157.8	151.2	144.6	137.1	128.5	120.0	111.5	102.9	98.3
60°	158.5	152.0	145.4	138.8	132.2	124.7	116.2	107.7	99.2	90.7	86.5
62.5°	146.3	139.8	133.2	126.6	120.0	112.7	104.6	96.5	88.5	80.4	76.4
65°	127.8	121.1	114.5	107.8	101.1	94.1	86.7	79.2	71.8	64.4	61.6
67.5°	109.8	103.2	96.6	90.0	83.4	76.7	70.0	63.4	56.7	50.1	48.8
70°	97.4	91.0	84.5	78.2	71.7	65.7	60.0	54.3	48.7	43.0	42.2
72.5°	85.5	79.4	73.2	67.1	60.9	55.6	51.0	46.5	41.9	37.3	36.6
75°	68.2	62.4	56.7	50.9	45.1	40.8	38.0	35.2	32.4	29.6	29.0
77.5°	51.0	46.0	40.9	35.9	30.8	27.6	26.3	24.9	23.6	22.3	21.9
80°	40.4	36.2	32.0	27.8	23.6	21.0	20.2	19.4	18.6	17.8	17.4
82.5°	30.6	27.3	24.1	20.8	17.5	15.6	15.0	14.4	13.9	13.4	13.1
85°	15.9	14.2	12.5	10.8	9.0	8.0	7.7	7.5	7.3	7.0	7.0
87.5°	4.8	4.5	4.2	3.8	3.3	3.3	3.5	3.9	4.2	4.3	4.2
90°	0.3	1.1	2.3	2.9	3.4	4.3	5.8	7.7	9.5	9.8	9.5
92.5°	3.5	5.1	7.2	8.4	10.4	13.0	19.6	28.8	36.9	37.4	31.6
95°	10.1	11.3	14.1	16.7	21.3	28.2	41.5	66.5	100.0	112.9	98.8
97.5°	16.4	17.9	21.0	24.9	30.2	38.1	54.7	89.7	145.2	192.7	202.2
100°	22.2	23.1	25.6	30.2	36.0	44.1	59.4	94.5	156.7	227.6	269.0
102.5°	27.5	28.1	30.7	35.3	41.3	49.4	63.5	94.7	152.3	228.7	293.9
105°	35.1	36.3	38.3	42.6	49.0	57.1	70.6	96.2	143.7	213.4	290.1
107.5°	43.5	44.4	46.3	50.3	56.6	64.7	77.9	100.2	139.5	197.1	264.8
110°	49.0	50.1	51.9	55.6	61.6	70.0	82.7	103.4	138.6	189.2	248.9



TEST NUMBER: P331620-930

CATALOG NUMBER: SA2XXRDIP-C290D330U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	54.1	55.2	57.2	60.7	66.4	75.1	87.3	106.9	138.8	184.2	237.8
115°	62.0	63.3	65.1	68.6	74.4	82.1	94.5	112.0	140.0	178.6	224.1
117.5°	70.1	71.3	73.0	76.1	81.6	89.7	101.1	117.6	142.1	175.9	215.5
120°	75.2	76.3	78.1	80.6	86.4	94.5	105.7	121.3	143.5	174.3	210.8
122.5°	80.1	81.0	82.7	85.5	91.2	99.5	110.1	124.5	145.0	173.3	206.9
125°	86.4	87.3	89.0	92.5	98.2	106.3	116.7	129.6	147.5	171.7	201.4
127.5°	91.5	92.6	95.1	98.9	104.4	112.7	122.8	134.4	149.9	170.7	196.2
130°	94.5	95.6	98.5	102.6	108.4	116.3	126.5	137.4	151.8	170.2	192.7
132.5°	97.3	98.7	101.7	106.0	112.0	120.1	129.7	140.4	153.7	170.0	190.0
135°	101.4	102.6	106.0	110.3	117.0	125.0	134.3	144.3	155.9	169.7	186.1
137.5°	105.3	106.7	110.1	114.8	121.3	128.8	137.9	147.3	157.8	169.6	183.4
140°	108.4	109.5	112.9	117.6	123.8	131.3	140.0	149.0	158.7	169.4	181.7
142.5°	111.3	112.3	115.4	120.1	126.2	133.2	141.6	150.3	159.4	169.4	180.2
145°	115.8	117.0	119.8	124.2	130.0	136.2	144.1	152.1	160.1	168.8	178.1
147.5°	120.7	121.5	124.3	128.2	133.1	138.7	146.0	153.1	160.4	167.8	175.9
150°	123.8	124.7	127.0	130.8	135.1	140.3	146.9	153.5	160.1	167.1	174.0
152.5°	127.1	127.5	129.8	133.1	137.2	141.9	147.8	153.8	159.7	165.9	172.4
155°	131.7	131.9	133.6	136.8	140.0	144.3	149.2	154.1	159.0	163.9	169.4
157.5°	135.4	135.7	137.1	139.9	142.4	146.0	150.2	154.1	157.7	161.8	166.6
160°	137.9	138.3	139.4	141.7	144.1	147.2	150.7	154.1	157.0	160.5	164.4
162.5°	140.6	140.3	141.5	143.3	145.4	147.9	150.9	153.8	156.3	159.3	162.7
165°	143.5	143.2	143.7	145.4	146.9	148.6	151.2	153.3	155.0	157.0	159.6
167.5°	145.9	145.5	146.0	147.2	148.2	149.3	151.2	152.9	153.7	155.0	156.6
170°	147.5	146.9	147.2	148.1	148.6	149.5	150.9	152.4	153.0	153.8	155.0
172.5°	148.4	148.1	147.9	148.8	149.1	149.8	150.7	151.7	152.1	152.5	153.4
175°	149.5	149.2	149.0	149.5	149.5	149.8	150.3	150.9	150.7	150.9	151.2
177.5°	150.0	149.5	149.4	149.8	149.8	149.8	150.0	150.5	150.0	149.8	150.0
180°	149.8	149.8	149.8	149.8	149.8	149.8	149.8	149.8	149.8	149.8	149.8



TEST NUMBER: P331620-930

CATALOG NUMBER: SA2XXRDIP-C290D330U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	409.3	409.3	409.3	409.3	409.3	409.3	409.3	409.3
2.5°	407.3	408.0	408.6	408.9	408.8	408.6	408.5	408.4
5°	404.1	404.8	405.5	405.8	405.5	405.3	405.0	404.8
7.5°	397.5	397.8	397.9	397.9	397.5	397.0	396.6	396.2
10°	391.0	390.8	390.5	390.1	389.6	389.1	388.7	388.2
12.5°	383.5	383.0	382.6	382.0	381.2	380.3	379.5	378.7
15°	369.5	367.9	366.3	365.2	364.4	363.5	362.6	361.8
17.5°	353.6	351.7	349.9	348.3	346.8	345.4	344.0	342.6
20°	342.6	340.5	338.4	336.5	334.7	332.9	331.1	329.3
22.5°	330.4	327.8	325.1	323.1	321.7	320.4	319.0	317.7
25°	310.3	306.9	303.5	301.3	300.0	298.7	297.5	296.3
27.5°	291.1	287.1	283.2	280.3	278.3	276.4	274.4	272.5
30°	277.5	273.4	269.1	266.0	263.7	261.5	259.3	257.1
32.5°	263.9	259.1	254.3	250.9	248.8	246.7	244.6	242.6
35°	242.6	237.4	232.2	228.7	226.9	225.1	223.3	221.5
37.5°	221.8	216.1	210.4	206.5	204.5	202.4	200.3	198.2
40°	208.0	202.1	196.2	192.2	190.1	188.0	185.8	183.7
42.5°	193.9	187.8	181.8	177.8	175.7	173.7	171.5	169.5
45°	173.5	167.6	161.8	157.9	156.0	153.9	152.0	150.0
47.5°	153.6	147.8	142.0	138.2	136.4	134.6	132.8	131.0
50°	140.9	135.2	129.5	125.8	124.1	122.4	120.6	118.9
52.5°	128.8	123.4	117.9	114.3	112.8	111.1	109.5	107.9
55°	110.5	105.6	100.6	97.3	95.8	94.2	92.7	91.2
57.5°	93.8	89.3	84.8	81.9	80.6	79.2	77.9	76.6
60°	82.3	78.2	73.9	71.2	69.9	68.6	67.3	66.0
62.5°	72.4	68.4	64.4	62.0	61.1	60.4	59.6	58.8
65°	58.9	56.0	53.2	51.7	51.4	51.2	51.0	50.7
67.5°	47.5	46.2	44.9	44.2	43.9	43.6	43.4	43.1
70°	41.3	40.5	39.7	39.1	38.7	38.4	38.1	37.7
72.5°	36.0	35.2	34.6	34.2	33.9	33.8	33.5	33.3
75°	28.5	27.9	27.3	27.0	26.9	26.8	26.7	26.7
77.5°	21.5	21.2	20.9	20.7	20.5	20.4	20.3	20.1
80°	17.1	16.8	16.5	16.3	16.3	16.3	16.3	16.3
82.5°	13.0	12.7	12.6	12.5	12.5	12.5	12.5	12.5
85°	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0
87.5°	4.1	3.9	3.9	4.0	4.0	4.0	4.0	4.0
90°	9.2	8.6	9.2	9.5	9.5	9.5	9.5	9.5
92.5°	25.1	21.5	19.2	17.4	17.1	16.2	16.4	16.0
95°	75.5	57.9	45.8	39.5	35.7	33.4	32.5	32.9
97.5°	176.1	144.1	112.9	92.1	78.4	71.3	67.1	64.7
100°	263.0	227.3	187.8	153.0	129.1	116.7	108.4	103.1
102.5°	319.9	311.9	283.0	246.1	220.0	198.9	188.5	181.5
105°	350.0	382.5	386.3	376.8	358.9	341.0	328.6	324.7
107.5°	328.3	377.4	407.3	421.3	423.5	422.6	420.0	414.7
110°	309.7	361.3	398.1	421.8	434.1	439.6	442.2	441.9



TEST NUMBER: P331620-930

CATALOG NUMBER: SA2XXRDIP-C290D330U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	292.6	342.1	381.5	408.6	425.8	435.0	439.9	441.4
115°	271.7	316.0	353.8	383.4	403.9	417.1	424.6	427.2
117.5°	255.8	294.8	329.1	356.9	377.7	391.8	399.6	401.8
120°	248.0	283.7	314.3	340.5	360.7	374.2	382.5	385.5
122.5°	241.8	274.5	303.5	327.1	345.2	358.6	366.0	368.4
125°	232.8	262.4	287.8	309.4	326.1	337.0	344.2	346.6
127.5°	223.8	250.7	274.6	294.5	309.1	319.4	325.5	327.4
130°	218.1	242.9	265.6	284.6	298.7	308.5	314.3	316.6
132.5°	212.5	235.5	256.4	274.3	288.1	297.9	303.2	305.3
135°	204.8	223.8	242.9	258.9	271.3	280.9	286.1	287.2
137.5°	198.7	214.6	229.7	243.7	255.0	263.2	267.7	269.5
140°	194.7	208.6	221.8	234.5	243.7	251.2	255.5	257.2
142.5°	191.5	203.3	214.7	225.3	234.0	240.8	244.7	245.0
145°	186.9	196.5	205.4	213.8	220.6	225.6	228.4	229.3
147.5°	183.4	190.9	197.9	204.0	209.7	213.6	215.6	216.1
150°	180.9	187.3	193.3	198.4	202.8	206.3	208.0	208.3
152.5°	178.4	184.3	189.4	193.9	197.3	200.2	201.5	201.6
155°	174.9	179.4	183.8	186.9	190.1	192.2	193.3	192.7
157.5°	170.8	174.6	178.2	180.8	183.0	184.7	185.2	185.2
160°	168.2	171.4	174.6	176.6	178.6	180.0	180.3	180.3
162.5°	165.7	168.4	171.1	172.7	174.7	175.7	175.9	175.7
165°	161.9	163.9	165.9	167.1	168.2	169.4	169.4	169.1
167.5°	158.2	159.8	161.2	162.2	162.7	163.4	163.3	163.0
170°	156.5	157.3	158.4	159.0	159.3	160.1	159.9	159.3
172.5°	154.3	155.0	155.9	156.2	156.5	156.9	156.6	156.3
175°	152.1	152.4	152.7	153.0	153.0	153.3	153.0	152.4
177.5°	150.5	150.5	150.7	150.7	150.7	150.7	150.5	150.0
180°	149.8	149.8	149.8	149.8	149.8	149.8	149.8	149.8

(END OF REPORT)