

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331453-840

Luminaire Tested: **SA2XXDIP-C1005D925U840-4F0-1E-UDD-F**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331453-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXDIP-C1005D925U840-4F0-1E-UDD-F  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 925 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7833.4 lumens  
Efficiency: N/A  
Efficacy: 117.3 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 66.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331453-840  
CATALOG NUMBER: SA2XXDIP-C1005D925U840-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P331453-840

CATALOG NUMBER: SA2XXDIP-C1005D925U840-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	58	58	58	52
1	98	94	90	87	91	87	84	81	74	72	69	62	61	59	51	50	49	44
2	90	82	76	71	83	76	71	66	65	61	58	55	52	49	45	43	41	37
3	82	72	65	59	75	67	61	55	57	52	48	48	45	42	40	38	35	31
4	75	64	56	50	69	59	52	47	51	46	41	43	39	36	36	33	30	27
5	69	57	49	43	63	53	46	40	46	40	36	39	34	31	32	29	27	23
6	63	51	43	37	58	48	40	35	41	35	31	35	31	27	29	26	23	20
7	58	46	38	33	54	43	36	31	37	32	27	32	27	24	27	23	21	18
8	54	42	34	29	50	39	32	27	34	28	24	29	25	21	25	21	19	16
9	51	38	31	26	47	36	29	24	31	26	22	27	22	19	23	19	17	15
10	47	35	28	23	44	33	26	22	29	23	20	25	21	17	21	18	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	25987	25987	25987
5°	26086	25710	25861
10°	25932	25450	25576
15°	25611	25120	25095
20°	25156	24624	24598
25°	24704	24015	24015
30°	24121	23457	23256
35°	23580	22787	22450
40°	22898	22118	21692
45°	22229	21450	20922
50°	21499	20760	20022
55°	20738	19952	19212
60°	19888	18991	18290
65°	18980	18032	17207
70°	17825	16877	16074
75°	16220	15540	15159
80°	14393	13966	13240
85°	11745	11189	10022



TEST NUMBER: P331453-840

CATALOG NUMBER: SA2XXDIP-C1005D925U840-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	151.3	1.9
10°-20°	425.9	5.4
20°-30°	626.0	8.0
30°-40°	727.1	9.3
40°-50°	726.3	9.3
50°-60°	633.4	8.1
60°-70°	468.3	6.0
70°-80°	265.3	3.4
80°-90°	74.5	1.0
90°-100°	42.5	0.5
100°-110°	155.9	2.0
110°-120°	416.8	5.3
120°-130°	688.0	8.8
130°-140°	731.7	9.3
140°-150°	680.1	8.7
150°-160°	546.8	7.0
160°-170°	352.3	4.5
170°-180°	121.3	1.5
0°-30°	1203.2	15.4
0°-40°	1930.3	24.6
0°-60°	3290.0	42.0
0°-90°	4098.1	52.3
90°-120°	615.2	7.9
90°-150°	2714.9	34.7
90°-180°	3735.0	47.7
0°-180°	7833.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1610	1610	1610	1610	1610	
5°	1610	1603	1586	1598	1596	153
15°	1532	1522	1503	1508	1501	431
25°	1387	1374	1348	1351	1348	638
35°	1196	1180	1156	1147	1139	747
45°	974	962	939	923	916	751
55°	737	727	709	691	682	658
65°	497	487	472	458	450	491
75°	260	257	249	241	243	278
85°	63	62	60	56	54	73
90°	1	11	18	23	25	6
95°	60	32	36	40	40	73
105°	280	292	56	66	70	300
115°	530	546	569	162	76	522
125°	750	762	779	786	789	668
135°	928	942	951	960	958	716
145°	1076	1076	1091	1097	1093	673
155°	1185	1178	1188	1193	1186	546
165°	1249	1244	1246	1252	1246	353
175°	1277	1271	1273	1278	1270	122
180°	1275	1275	1275	1275	1275	



TEST NUMBER: P331453-840

CATALOG NUMBER: SA2XXDIP-C1005D925U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1609.5	1609.5	1609.5	1609.5	1609.5	1609.5	1609.5	1609.5	1609.5	1609.5	1609.5
2.5°	1617.0	1615.6	1614.3	1612.9	1611.4	1609.3	1606.3	1603.3	1600.2	1597.2	1599.9
5°	1609.5	1608.2	1606.8	1605.4	1604.1	1601.4	1597.7	1593.9	1590.1	1586.3	1589.1
7.5°	1595.3	1593.2	1591.0	1588.9	1586.8	1583.8	1579.9	1576.1	1572.3	1568.4	1571.1
10°	1581.7	1579.3	1576.9	1574.5	1572.1	1568.8	1564.7	1560.5	1556.4	1552.3	1555.1
12.5°	1563.2	1560.9	1558.8	1556.7	1554.6	1551.5	1547.3	1543.2	1539.1	1535.0	1536.9
15°	1532.2	1530.1	1528.0	1526.0	1523.9	1520.7	1516.2	1511.7	1507.2	1502.8	1504.2
17.5°	1492.6	1490.5	1488.4	1486.3	1484.3	1481.0	1476.4	1471.9	1467.3	1462.9	1464.4
20°	1464.1	1462.0	1460.0	1457.8	1455.8	1452.4	1447.5	1442.8	1437.9	1433.1	1434.1
22.5°	1435.6	1432.7	1429.9	1426.9	1424.0	1420.4	1415.8	1411.3	1406.7	1402.2	1402.4
25°	1386.7	1383.9	1381.2	1378.5	1375.7	1371.4	1365.5	1359.7	1353.8	1348.0	1348.7
27.5°	1331.0	1328.5	1326.1	1323.5	1321.1	1317.6	1312.9	1308.3	1303.7	1299.1	1298.1
30°	1293.8	1291.1	1288.3	1285.6	1282.8	1278.9	1273.7	1268.6	1263.4	1258.2	1257.2
32.5°	1254.3	1252.0	1249.8	1247.6	1245.4	1241.6	1236.2	1230.7	1225.3	1219.8	1218.0
35°	1196.3	1192.9	1189.4	1186.0	1182.6	1178.1	1172.6	1167.1	1161.6	1156.1	1154.1
37.5°	1131.0	1128.0	1125.0	1122.0	1118.9	1114.7	1109.1	1103.7	1098.1	1092.7	1090.0
40°	1086.4	1083.7	1081.0	1078.2	1075.4	1071.4	1065.8	1060.4	1054.8	1049.4	1046.2
42.5°	1043.1	1040.4	1037.6	1034.9	1032.1	1027.9	1022.5	1016.9	1011.5	1005.9	1002.6
45°	973.5	971.1	968.7	966.2	963.8	960.1	954.9	949.8	944.6	939.4	935.6
47.5°	904.1	901.9	899.6	897.4	895.0	891.2	885.9	880.5	875.1	869.8	865.8
50°	855.9	854.1	852.4	850.7	849.0	845.7	840.9	836.1	831.2	826.5	821.6
52.5°	808.8	806.6	804.3	802.0	799.7	796.3	791.7	787.2	782.7	778.2	774.2
55°	736.7	734.6	732.6	730.5	728.4	725.3	721.2	717.1	713.0	708.8	704.7
57.5°	664.3	662.6	661.0	659.3	657.6	654.6	650.1	645.5	641.0	636.4	632.4
60°	615.9	614.6	613.2	611.9	610.5	607.3	602.6	597.7	592.9	588.1	584.3
62.5°	569.0	566.7	564.5	562.3	560.1	557.1	553.4	549.8	546.0	542.3	538.8
65°	496.8	494.7	492.7	490.6	488.6	485.7	482.3	478.9	475.4	472.0	469.0
67.5°	423.4	421.8	420.1	418.5	416.9	414.4	411.3	408.3	405.2	402.1	399.7
70°	377.6	376.3	374.9	373.5	372.1	369.9	366.8	363.7	360.6	357.5	355.1
72.5°	330.5	329.2	327.8	326.5	325.1	323.4	321.4	319.4	317.4	315.4	313.0
75°	260.0	259.3	258.6	257.9	257.2	256.0	254.3	252.6	250.9	249.1	247.1
77.5°	196.8	195.7	194.5	193.4	192.2	191.3	190.6	189.9	189.1	188.5	187.4
80°	154.8	154.4	154.1	153.7	153.4	152.9	152.2	151.5	150.8	150.2	149.1
82.5°	115.1	115.1	115.0	114.9	114.8	114.6	114.2	113.8	113.4	113.0	111.7
85°	63.4	63.1	62.8	62.4	62.1	61.7	61.4	61.0	60.7	60.4	59.3
87.5°	22.5	22.4	22.3	22.2	22.1	21.9	21.7	21.5	21.2	21.0	20.4
90°	0.9	3.1	5.5	7.7	9.9	11.9	13.5	15.1	16.8	18.5	19.5
92.5°	18.6	18.4	18.2	18.0	17.8	18.1	19.0	19.8	20.6	21.4	21.9
95°	60.0	53.2	46.5	39.7	32.9	30.2	31.7	33.1	34.5	36.0	37.0
97.5°	119.0	99.9	80.9	61.8	42.7	34.8	38.2	41.5	44.8	48.2	49.0
100°	163.3	135.1	107.0	79.0	50.9	38.7	42.1	45.6	49.1	52.6	54.2
102.5°	212.0	206.0	200.1	194.1	188.1	170.7	141.5	112.3	83.2	54.0	56.1
105°	280.3	286.5	292.7	298.8	305.0	280.0	224.1	168.1	112.2	56.2	58.5
107.5°	358.4	363.3	368.3	373.2	378.3	347.2	280.0	213.0	145.8	78.8	76.4
110°	408.6	412.9	417.2	421.5	425.8	398.3	339.1	279.8	220.7	161.4	140.9



TEST NUMBER: P331453-840

CATALOG NUMBER: SA2XXDIP-C1005D925U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	455.8	459.6	463.4	467.3	471.0	465.6	451.0	436.4	421.7	407.1	332.3
115°	530.3	533.8	537.2	540.8	544.2	548.6	553.7	558.9	563.9	569.1	474.1
117.5°	596.9	600.8	604.7	608.6	612.5	616.2	619.8	623.3	626.8	630.3	607.3
120°	645.6	648.6	651.8	654.8	657.9	661.3	665.0	668.6	672.4	676.0	678.5
122.5°	686.9	690.1	693.4	696.6	699.8	703.5	707.5	711.6	715.6	719.6	721.0
125°	749.8	752.5	755.2	757.8	760.5	763.8	767.7	771.5	775.5	779.3	780.8
127.5°	806.8	809.8	812.7	815.7	818.6	821.5	824.5	827.4	830.3	833.2	835.3
130°	843.0	846.3	849.5	852.8	856.1	858.9	861.1	863.3	865.7	867.9	870.1
132.5°	879.9	882.6	885.4	888.3	891.0	893.5	895.9	898.1	900.3	902.5	904.5
135°	927.9	931.1	934.4	937.7	941.0	943.5	945.3	947.3	949.1	950.9	952.9
137.5°	976.3	978.7	981.0	983.2	985.5	987.7	989.8	991.9	994.0	996.1	998.0
140°	1008.0	1009.8	1011.4	1013.0	1014.6	1016.6	1018.9	1021.1	1023.4	1025.6	1027.4
142.5°	1034.6	1036.1	1037.6	1039.1	1040.6	1042.6	1045.1	1047.7	1050.4	1052.9	1054.6
145°	1076.3	1076.1	1075.9	1075.7	1075.5	1077.1	1080.7	1084.1	1087.6	1091.1	1092.5
147.5°	1112.7	1111.9	1111.2	1110.3	1109.5	1110.9	1114.3	1117.8	1121.3	1124.7	1125.7
150°	1136.3	1134.9	1133.4	1132.0	1130.5	1131.5	1134.8	1138.0	1141.3	1144.6	1145.8
152.5°	1156.2	1154.6	1153.0	1151.4	1149.8	1150.5	1153.7	1156.8	1159.9	1163.1	1164.3
155°	1185.2	1183.4	1181.4	1179.6	1177.8	1178.1	1180.5	1183.1	1185.5	1187.9	1189.1
157.5°	1207.8	1206.3	1204.8	1203.2	1201.6	1201.7	1203.5	1205.2	1206.9	1208.6	1210.0
160°	1221.1	1219.9	1218.7	1217.4	1216.2	1216.2	1217.4	1218.7	1219.9	1221.1	1222.3
162.5°	1232.9	1231.7	1230.5	1229.2	1228.0	1227.9	1229.0	1230.0	1231.1	1232.2	1233.6
165°	1248.8	1247.6	1246.4	1245.1	1243.9	1243.5	1244.2	1244.8	1245.5	1246.1	1247.5
167.5°	1260.6	1259.4	1258.2	1256.9	1255.7	1255.4	1256.0	1256.5	1257.1	1257.7	1259.1
170°	1267.3	1266.0	1264.8	1263.5	1262.3	1261.9	1262.3	1262.7	1263.1	1263.5	1265.0
172.5°	1271.6	1270.4	1269.2	1268.0	1266.8	1266.4	1266.8	1267.2	1267.6	1268.0	1269.4
175°	1277.4	1276.0	1274.6	1273.0	1271.6	1271.1	1271.5	1271.9	1272.3	1272.7	1274.2
177.5°	1278.3	1277.2	1276.1	1274.9	1273.7	1273.2	1273.4	1273.5	1273.7	1273.8	1275.1
180°	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7



TEST NUMBER: P331453-840

CATALOG NUMBER: SA2XXDIP-C1005D925U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1609.5	1609.5	1609.5	1609.5	1609.5	1609.5	1609.5	1609.5
2.5°	1602.7	1605.4	1608.2	1609.3	1608.7	1608.2	1607.6	1607.1
5°	1591.9	1594.6	1597.3	1598.4	1597.7	1597.0	1596.3	1595.6
7.5°	1573.9	1576.6	1579.4	1580.4	1579.6	1578.9	1578.1	1577.4
10°	1557.8	1560.5	1563.3	1564.2	1563.2	1562.1	1561.0	1560.0
12.5°	1538.8	1540.8	1542.7	1543.3	1542.5	1541.8	1541.0	1540.2
15°	1505.5	1506.9	1508.2	1508.1	1506.4	1504.7	1503.0	1501.3
17.5°	1466.0	1467.6	1469.2	1469.2	1467.4	1465.8	1464.2	1462.5
20°	1435.2	1436.2	1437.2	1437.0	1435.7	1434.3	1433.0	1431.6
22.5°	1402.6	1402.8	1403.0	1402.7	1401.9	1401.1	1400.2	1399.4
25°	1349.4	1350.1	1350.8	1350.8	1350.1	1349.4	1348.7	1348.0
27.5°	1297.1	1296.0	1294.9	1293.6	1292.0	1290.3	1288.7	1287.1
30°	1256.2	1255.2	1254.2	1252.9	1251.5	1250.1	1248.8	1247.4
32.5°	1216.2	1214.3	1212.4	1210.8	1209.4	1208.1	1206.7	1205.3
35°	1152.0	1149.9	1147.8	1146.0	1144.3	1142.6	1140.7	1139.0
37.5°	1087.5	1085.0	1082.5	1080.4	1078.7	1077.0	1075.4	1073.8
40°	1043.1	1040.1	1036.9	1034.7	1033.3	1032.0	1030.6	1029.2
42.5°	999.3	995.8	992.5	989.9	988.0	986.0	984.1	982.1
45°	931.9	928.1	924.3	921.7	920.3	919.0	917.6	916.3
47.5°	861.8	857.8	853.8	850.8	848.8	846.9	844.9	842.8
50°	816.8	812.0	807.2	804.0	802.2	800.5	798.8	797.1
52.5°	770.2	766.2	762.2	759.1	756.8	754.6	752.2	750.0
55°	700.5	696.4	692.4	689.4	687.7	686.0	684.3	682.5
57.5°	628.2	624.2	620.2	617.4	616.2	614.9	613.6	612.3
60°	580.6	576.7	573.0	570.6	569.6	568.6	567.4	566.4
62.5°	535.3	531.8	528.3	525.8	524.5	523.2	521.9	520.6
65°	465.9	462.7	459.7	457.3	455.6	453.8	452.1	450.4
67.5°	397.3	394.9	392.4	390.5	389.2	387.8	386.5	385.1
70°	352.6	350.3	347.9	346.0	344.6	343.3	341.8	340.5
72.5°	310.6	308.2	305.8	304.1	303.0	301.8	300.7	299.6
75°	245.1	243.0	241.0	240.2	241.0	241.6	242.3	243.0
77.5°	186.4	185.4	184.4	183.4	182.4	181.5	180.5	179.6
80°	148.0	147.0	146.0	145.1	144.4	143.8	143.1	142.4
82.5°	110.4	109.1	107.8	107.0	106.8	106.7	106.6	106.4
85°	58.3	57.3	56.2	55.5	55.2	54.8	54.5	54.1
87.5°	19.8	19.2	18.6	18.2	18.0	17.8	17.6	17.4
90°	20.5	21.5	22.5	23.2	23.6	24.0	24.5	24.9
92.5°	22.4	23.0	23.5	23.9	24.1	24.4	24.6	24.9
95°	38.0	39.1	40.1	40.5	40.3	40.1	39.9	39.7
97.5°	49.8	50.6	51.4	51.9	52.2	52.4	52.7	52.9
100°	55.8	57.5	59.2	60.2	60.6	61.0	61.4	61.8
102.5°	58.3	60.5	62.6	63.9	64.5	65.0	65.6	66.2
105°	60.8	63.0	65.2	66.9	67.7	68.5	69.3	70.1
107.5°	74.1	71.9	69.6	68.9	69.7	70.5	71.3	72.1
110°	120.4	99.9	79.4	69.6	70.4	71.2	72.0	72.9





TEST NUMBER: P331453-840

CATALOG NUMBER: SA2XXDIP-C1005D925U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	257.6	182.8	108.1	71.0	71.6	72.3	72.9	73.6
115°	379.3	284.4	189.5	134.6	119.9	105.1	90.4	75.6
117.5°	584.4	561.5	538.5	502.7	454.2	405.8	357.3	308.8
120°	681.0	683.5	685.9	673.3	645.6	617.9	590.3	562.6
122.5°	722.6	724.0	725.5	723.6	718.2	712.8	707.4	702.1
125°	782.2	783.7	785.1	786.1	786.7	787.3	788.0	788.6
127.5°	837.4	839.5	841.6	842.6	842.8	842.9	843.0	843.1
130°	872.4	874.6	876.9	878.0	877.8	877.5	877.3	877.1
132.5°	906.5	908.4	910.3	911.1	910.9	910.7	910.5	910.3
135°	955.0	957.0	959.1	959.9	959.5	959.1	958.7	958.3
137.5°	1000.1	1002.1	1004.1	1004.8	1004.1	1003.4	1002.7	1002.0
140°	1029.3	1031.2	1033.0	1033.4	1032.4	1031.4	1030.4	1029.3
142.5°	1056.2	1057.9	1059.7	1060.0	1058.9	1057.9	1056.9	1055.8
145°	1094.0	1095.4	1096.8	1097.0	1096.0	1095.0	1094.0	1093.0
147.5°	1126.8	1127.8	1128.9	1129.0	1128.1	1127.3	1126.4	1125.6
150°	1147.0	1148.3	1149.5	1149.6	1148.6	1147.5	1146.5	1145.5
152.5°	1165.5	1166.7	1167.9	1167.9	1166.5	1165.2	1163.9	1162.5
155°	1190.4	1191.6	1192.9	1192.7	1191.0	1189.3	1187.7	1186.1
157.5°	1211.3	1212.7	1214.2	1214.1	1212.4	1210.8	1209.2	1207.7
160°	1223.6	1224.9	1226.1	1226.0	1224.5	1223.0	1221.6	1220.2
162.5°	1235.0	1236.4	1237.8	1237.6	1235.9	1234.1	1232.3	1230.5
165°	1248.9	1250.3	1251.7	1251.7	1250.3	1248.9	1247.5	1246.1
167.5°	1260.5	1261.9	1263.4	1263.1	1261.3	1259.5	1257.7	1255.8
170°	1266.5	1267.9	1269.3	1269.1	1267.3	1265.4	1263.5	1261.7
172.5°	1270.8	1272.3	1273.7	1273.5	1271.6	1269.8	1268.0	1266.2
175°	1275.7	1277.1	1278.5	1278.2	1276.2	1274.1	1272.0	1270.0
177.5°	1276.2	1277.4	1278.5	1278.3	1276.9	1275.4	1273.8	1272.4
180°	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7

(END OF REPORT)