

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331245-840

Luminaire Tested: **SA2XXDIP-C290D330U840-4F0-1E-UDD-D4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331245-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C290D330U840-4F0-1E-UDD-D4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, DROP SATIN WHITE DIFFUSER
UPLIGHT 330 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2500.4 lumens
Efficiency: N/A
Efficacy: 123.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.08')
CIE Type: General Diffuse


Input Watts (W): 20.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331245-840

CATALOG NUMBER: SA2XXDIP-C290D330U840-4F0-1E-UDD-D4

Luminous Intensity Polar Plot





TEST NUMBER: P331245-840

CATALOG NUMBER: SA2XXDIP-C290D330U840-4F0-1E-UDD-D4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	50	50	50	43
1	95	90	86	82	86	82	79	75	68	65	62	54	52	51	42	41	39	34
2	86	78	71	66	78	71	65	61	59	54	51	47	44	41	36	34	32	27
3	78	68	60	54	71	62	55	50	51	46	42	41	37	34	32	29	27	22
4	71	60	52	45	64	55	48	42	45	40	35	36	32	29	28	25	23	19
5	65	53	45	39	59	49	41	36	40	35	30	32	28	25	25	22	20	16
6	60	47	39	33	54	44	36	31	36	30	26	29	25	22	23	19	17	14
7	55	43	35	29	50	39	32	27	33	27	23	26	22	19	21	17	15	12
8	51	39	31	25	47	36	29	24	30	24	20	24	20	17	19	16	13	11
9	48	35	28	22	43	32	26	21	27	22	18	22	18	15	17	14	12	10
10	44	32	25	20	40	30	23	19	25	20	16	20	16	13	16	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5112	5112	5112
5°	5137	4921	4901
10°	5105	4774	4722
15°	5033	4621	4531
20°	4944	4456	4348
25°	4857	4297	4181
30°	4733	4133	4015
35°	4608	3975	3898
40°	4476	3840	3780
45°	4351	3721	3681
50°	4218	3612	3581
55°	4076	3496	3482
60°	3902	3373	3374
65°	3723	3232	3247
70°	3523	3079	3110
75°	3270	2929	2984
80°	2861	2776	2858
85°	2484	2642	2759



TEST NUMBER: P331245-840

CATALOG NUMBER: SA2XXDIP-C290D330U840-4F0-1E-UDD-D4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	30.0	1.2
10°-20°	86.0	3.4
20°-30°	130.3	5.2
30°-40°	158.8	6.3
40°-50°	170.8	6.8
50°-60°	165.9	6.6
60°-70°	144.8	5.8
70°-80°	111.5	4.5
80°-90°	76.5	3.1
90°-100°	125.7	5.0
100°-110°	289.4	11.6
110°-120°	292.3	11.7
120°-130°	234.0	9.4
130°-140°	182.6	7.3
140°-150°	134.6	5.4
150°-160°	93.9	3.8
160°-170°	55.3	2.2
170°-180°	18.0	0.7
0°-30°	246.3	9.9
0°-40°	405.1	16.2
0°-60°	741.7	29.7
0°-90°	1074.5	43.0
90°-120°	707.4	28.3
90°-150°	1258.7	50.3
90°-180°	1426.0	57.0
0°-180°	2500.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	317	317	317	317	317	
5°	318	316	313	316	316	30
15°	303	304	304	308	307	85
25°	275	278	283	288	289	127
35°	237	245	254	263	267	148
45°	194	207	223	237	242	150
55°	149	166	190	205	212	133
65°	102	125	151	170	176	101
75°	56	82	112	130	137	60
85°	17	45	74	93	100	18
90°	5	36	73	90	96	4
95°	16	56	193	122	116	16
105°	46	82	304	528	463	49
115°	79	105	249	497	576	78
125°	108	128	228	397	461	96
135°	126	151	215	325	374	98
145°	143	165	209	262	289	90
155°	163	176	203	230	239	75
165°	178	183	194	206	209	50
175°	185	185	187	189	189	18
180°	186	186	186	186	186	



TEST NUMBER: P331245-840

CATALOG NUMBER: SA2XXDIP-C290D330U840-4F0-1E-UDD-D4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	316.6	316.6	316.6	316.6	316.6	316.6	316.6	316.6	316.6	316.6	316.6
2.5°	318.4	318.1	317.9	317.6	317.4	317.0	316.4	315.9	315.3	314.7	315.1
5°	317.5	317.2	316.9	316.6	316.2	315.8	315.2	314.6	314.0	313.4	314.0
7.5°	314.6	314.4	314.2	314.0	313.8	313.5	313.0	312.6	312.0	311.5	312.4
10°	312.5	312.3	312.0	311.8	311.6	311.3	311.0	310.7	310.4	310.1	310.9
12.5°	308.7	308.8	308.8	308.9	308.9	308.8	308.6	308.4	308.1	307.9	308.7
15°	302.8	303.0	303.2	303.4	303.6	303.7	303.7	303.7	303.7	303.7	304.6
17.5°	295.1	295.5	295.9	296.4	296.8	297.2	297.5	297.8	298.1	298.5	299.4
20°	289.9	290.4	290.9	291.4	292.0	292.5	292.9	293.3	293.7	294.1	295.2
22.5°	284.5	285.0	285.6	286.2	286.8	287.4	287.9	288.5	289.1	289.6	290.7
25°	275.3	276.0	276.7	277.4	278.1	278.9	279.8	280.7	281.7	282.6	283.8
27.5°	264.3	265.4	266.6	267.7	268.9	270.0	271.0	272.2	273.3	274.4	275.9
30°	256.9	258.2	259.5	260.8	262.2	263.6	264.9	266.2	267.5	268.8	270.4
32.5°	248.8	250.3	251.8	253.3	254.8	256.3	257.9	259.4	261.1	262.6	264.5
35°	237.2	238.9	240.7	242.4	244.1	245.9	247.9	249.8	251.8	253.7	255.9
37.5°	224.5	226.5	228.5	230.6	232.5	234.8	237.3	239.7	242.3	244.8	247.3
40°	216.1	218.3	220.6	222.8	225.0	227.5	230.2	233.1	235.8	238.5	241.2
42.5°	208.0	210.3	212.5	214.7	217.0	219.6	222.9	226.0	229.1	232.3	235.2
45°	194.5	197.2	200.1	202.8	205.5	208.6	212.3	215.8	219.3	223.0	226.1
47.5°	181.2	184.2	187.2	190.2	193.2	196.8	201.0	205.1	209.3	213.5	216.8
50°	172.1	175.2	178.3	181.5	184.7	188.5	193.2	197.7	202.3	206.9	210.4
52.5°	163.2	166.5	169.9	173.2	176.5	180.6	185.4	190.3	195.1	200.0	203.5
55°	149.1	152.8	156.4	160.1	163.8	168.2	173.6	178.8	184.2	189.5	193.2
57.5°	135.1	139.3	143.4	147.5	151.7	156.4	161.9	167.2	172.7	178.1	182.1
60°	125.2	129.7	134.0	138.4	142.8	147.8	153.7	159.5	165.3	171.1	175.0
62.5°	116.4	121.0	125.5	130.1	134.6	139.8	145.6	151.4	157.2	163.1	167.1
65°	101.8	106.8	111.8	116.8	121.8	127.3	133.3	139.4	145.4	151.4	155.6
67.5°	88.5	93.7	98.9	104.1	109.4	115.0	121.2	127.3	133.5	139.7	143.9
70°	78.9	84.2	89.5	94.8	100.1	105.9	112.2	118.6	124.9	131.2	135.6
72.5°	70.1	75.5	81.0	86.4	92.0	97.9	104.3	110.7	117.1	123.5	127.8
75°	56.5	62.1	67.9	73.5	79.3	85.3	91.9	98.5	104.9	111.5	115.8
77.5°	43.2	49.2	55.1	61.1	67.2	73.4	80.1	86.6	93.3	99.9	104.3
80°	34.4	40.6	46.9	53.0	59.3	65.7	72.3	79.0	85.5	92.2	96.4
82.5°	27.1	33.2	39.4	45.4	51.6	58.1	64.7	71.5	78.2	84.8	89.2
85°	16.6	22.8	29.2	35.4	41.8	48.2	54.7	61.3	67.8	74.3	78.6
87.5°	9.1	15.3	21.7	28.0	34.1	40.7	47.6	54.5	61.5	68.2	72.2
90°	4.9	11.9	19.3	25.9	32.5	39.8	48.1	57.2	65.8	72.7	76.4
92.5°	8.6	16.0	24.0	31.2	39.1	48.4	62.7	80.3	96.7	103.6	100.4
95°	16.2	22.4	30.7	38.8	49.3	63.2	85.7	122.9	170.5	192.6	179.0
97.5°	23.5	29.7	37.8	46.9	57.8	72.5	99.0	148.1	222.8	287.6	303.1
100°	30.7	35.5	42.5	52.0	62.9	77.7	102.3	151.5	234.3	327.8	382.9
102.5°	36.9	41.1	47.8	57.0	67.8	82.3	105.3	149.6	226.4	326.6	411.1
105°	45.8	50.2	55.6	63.9	74.7	88.9	111.0	148.0	212.2	303.9	402.3
107.5°	56.0	59.5	64.3	71.6	81.7	95.5	116.8	149.7	203.4	279.8	367.1
110°	62.5	65.9	70.2	76.9	86.3	100.2	120.9	151.6	200.2	267.9	345.1



TEST NUMBER: P331245-840

CATALOG NUMBER: SA2XXDIP-C290D330U840-4F0-1E-UDD-D4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	68.8	71.9	76.0	82.1	91.0	104.9	124.8	153.8	198.0	259.0	328.8
115°	78.6	81.5	84.7	90.1	98.4	110.9	130.8	157.1	196.3	248.7	308.2
117.5°	88.3	90.4	93.2	97.8	105.3	117.9	136.3	161.0	195.5	241.7	293.7
120°	94.5	96.3	98.9	102.5	110.1	122.3	140.3	163.6	195.2	237.4	285.6
122.5°	100.5	101.8	104.1	107.8	115.0	127.3	144.2	165.9	195.2	234.1	278.4
125°	108.0	109.1	111.2	115.4	122.6	134.2	150.4	169.7	195.0	228.2	267.7
127.5°	114.2	115.5	118.5	123.1	129.9	141.4	156.4	173.5	195.4	223.8	257.8
130°	118.0	119.3	122.7	127.6	134.7	145.7	160.3	176.0	196.0	221.0	251.3
132.5°	121.4	123.0	126.7	131.9	139.3	150.0	163.6	178.5	196.5	218.4	245.5
135°	126.0	127.4	131.8	137.1	145.3	155.8	168.2	181.8	197.0	215.2	237.7
137.5°	130.9	132.6	136.8	142.6	150.7	160.2	171.9	184.0	197.4	212.5	231.4
140°	134.6	135.9	140.2	145.7	153.5	162.8	173.7	185.0	197.3	210.8	227.7
142.5°	138.4	139.4	143.3	148.9	156.3	165.0	175.5	186.3	197.6	210.0	224.6
145°	143.4	144.9	148.5	153.8	161.0	168.7	178.4	188.4	198.3	209.0	221.2
147.5°	149.5	150.5	153.9	158.9	164.8	171.8	180.9	189.7	198.6	207.8	217.9
150°	153.4	154.5	157.3	162.0	167.3	173.8	182.0	190.2	198.3	206.9	215.5
152.5°	157.4	157.9	160.8	164.8	170.0	175.7	183.1	190.5	197.8	205.5	213.5
155°	163.1	163.4	165.5	169.5	173.4	178.7	184.8	190.9	196.9	203.0	209.8
157.5°	167.7	168.1	169.9	173.3	176.4	180.9	186.0	190.9	195.3	200.5	206.3
160°	170.9	171.3	172.7	175.5	178.4	182.4	186.6	190.9	194.5	198.7	203.7
162.5°	174.1	173.8	175.3	177.5	180.2	183.2	186.9	190.6	193.6	197.3	201.5
165°	177.7	177.3	178.0	180.2	182.0	184.1	187.3	189.9	192.0	194.5	197.6
167.5°	180.7	180.3	180.9	182.3	183.6	184.9	187.2	189.3	190.4	192.0	194.0
170°	182.7	182.0	182.4	183.4	184.1	185.2	186.9	188.7	189.5	190.6	192.0
172.5°	183.8	183.4	183.2	184.3	184.7	185.5	186.7	187.9	188.3	188.8	190.0
175°	185.2	184.8	184.5	185.2	185.2	185.5	186.2	186.9	186.6	186.9	187.3
177.5°	185.8	185.2	185.0	185.5	185.5	185.5	185.8	186.4	185.8	185.5	185.8
180°	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5



TEST NUMBER: P331245-840

CATALOG NUMBER: SA2XXDIP-C290D330U840-4F0-1E-UDD-D4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	316.6	316.6	316.6	316.6	316.6	316.6	316.6	316.6
2.5°	315.5	315.9	316.3	316.5	316.3	316.1	316.0	315.8
5°	314.6	315.2	315.8	316.0	315.9	315.8	315.7	315.6
7.5°	313.1	313.8	314.6	314.9	314.8	314.7	314.6	314.5
10°	311.7	312.6	313.4	313.8	313.7	313.6	313.5	313.4
12.5°	309.5	310.3	311.1	311.5	311.4	311.3	311.2	311.1
15°	305.5	306.5	307.4	307.8	307.7	307.6	307.5	307.4
17.5°	300.4	301.3	302.3	302.8	302.8	302.8	302.8	302.8
20°	296.3	297.4	298.5	299.1	299.1	299.1	299.1	299.1
22.5°	292.0	293.1	294.2	294.8	295.0	295.1	295.3	295.5
25°	285.1	286.3	287.5	288.2	288.5	288.8	289.1	289.4
27.5°	277.4	279.0	280.5	281.4	281.7	281.9	282.1	282.4
30°	272.1	273.8	275.4	276.3	276.6	276.9	277.2	277.5
32.5°	266.3	268.2	270.1	271.4	271.9	272.5	273.0	273.5
35°	258.2	260.4	262.7	264.2	264.9	265.6	266.3	267.0
37.5°	249.7	252.3	254.8	256.4	257.1	257.9	258.6	259.3
40°	243.9	246.5	249.1	251.0	251.9	252.8	253.7	254.6
42.5°	238.1	241.0	243.9	245.8	246.7	247.6	248.5	249.4
45°	229.2	232.5	235.6	237.7	238.7	239.7	240.8	241.8
47.5°	220.2	223.4	226.7	228.9	230.0	231.2	232.3	233.4
50°	213.8	217.3	220.8	223.1	224.2	225.3	226.4	227.5
52.5°	207.0	210.6	214.1	216.5	217.7	218.9	220.2	221.3
55°	196.8	200.5	204.2	206.6	207.9	209.3	210.7	212.0
57.5°	186.0	190.0	193.9	196.5	197.9	199.2	200.6	202.0
60°	178.8	182.8	186.6	189.2	190.7	192.1	193.6	195.0
62.5°	171.3	175.4	179.6	182.3	183.6	184.9	186.3	187.6
65°	159.8	163.9	168.1	170.9	172.2	173.5	174.8	176.1
67.5°	148.0	152.3	156.5	159.4	160.7	162.1	163.5	164.9
70°	140.0	144.3	148.8	151.6	152.8	154.0	155.2	156.4
72.5°	132.1	136.4	140.7	143.6	145.0	146.5	148.0	149.5
75°	120.3	124.6	129.1	131.9	133.2	134.5	135.8	137.1
77.5°	108.7	113.0	117.3	120.3	121.7	123.1	124.5	125.9
80°	100.8	105.0	109.4	112.2	113.6	115.0	116.4	117.9
82.5°	93.4	97.8	102.0	104.8	106.1	107.6	108.9	110.2
85°	82.9	87.2	91.5	94.3	95.7	97.1	98.6	100.0
87.5°	76.3	80.3	84.6	87.5	88.8	90.0	91.3	92.6
90°	80.1	83.5	88.3	91.3	92.5	93.7	94.9	96.1
92.5°	96.3	95.9	96.9	97.4	98.3	98.4	99.9	100.5
95°	154.0	136.1	125.0	119.7	116.2	114.6	114.8	116.3
97.5°	274.5	238.6	203.8	180.5	164.6	157.0	153.1	151.3
100°	379.2	338.7	293.6	252.9	224.4	210.2	201.0	195.6
102.5°	447.0	440.7	408.6	365.3	334.2	309.1	297.3	289.7
105°	480.1	524.0	532.2	522.8	501.8	480.8	466.6	462.7
107.5°	449.2	513.4	553.9	573.5	577.3	577.2	575.3	569.9
110°	423.6	490.7	539.7	571.1	587.5	595.5	599.8	600.6



TEST NUMBER: P331245-840

CATALOG NUMBER: SA2XXDIP-C290D330U840-4F0-1E-UDD-D4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	399.9	464.4	516.5	552.3	574.7	587.2	594.4	597.4
115°	370.1	428.1	478.0	516.7	543.2	560.8	571.2	575.5
117.5°	346.7	398.0	443.4	479.9	506.8	525.1	535.9	539.7
120°	334.5	381.6	422.2	456.8	482.8	500.7	512.2	516.8
122.5°	324.4	367.7	406.3	437.5	460.9	478.4	488.5	492.4
125°	309.4	348.9	383.0	411.6	433.2	447.8	457.6	461.4
127.5°	294.6	330.4	362.5	388.9	407.9	421.5	430.1	433.2
130°	285.1	318.2	348.9	374.1	392.3	405.3	413.2	416.9
132.5°	275.9	306.6	334.9	358.6	376.7	389.6	397.0	400.3
135°	263.1	288.7	314.4	335.9	352.0	364.7	371.8	374.1
137.5°	252.2	273.8	294.4	313.1	327.7	338.5	344.9	347.7
140°	245.4	264.2	282.2	299.0	311.0	320.9	326.9	329.6
142.5°	240.0	255.9	271.2	285.4	296.7	305.7	311.0	311.9
145°	232.8	245.2	256.8	267.7	276.8	283.4	287.5	289.0
147.5°	227.4	236.7	245.5	253.2	260.4	265.6	268.2	269.1
150°	224.1	232.0	239.4	245.8	251.2	255.5	257.6	258.0
152.5°	221.0	228.2	234.6	240.1	244.4	248.0	249.6	249.7
155°	216.6	222.3	227.6	231.6	235.5	238.0	239.4	238.7
157.5°	211.6	216.3	220.8	223.9	226.6	228.7	229.3	229.3
160°	208.3	212.3	216.2	218.7	221.3	223.0	223.4	223.4
162.5°	205.2	208.6	212.0	213.9	216.4	217.6	217.9	217.6
165°	200.6	203.0	205.5	206.9	208.3	209.8	209.8	209.4
167.5°	196.0	197.9	199.7	201.0	201.6	202.4	202.3	201.9
170°	193.8	194.8	196.2	196.9	197.3	198.3	198.0	197.3
172.5°	191.2	192.0	193.1	193.5	193.9	194.4	194.0	193.6
175°	188.4	188.7	189.1	189.5	189.5	189.9	189.5	188.7
177.5°	186.4	186.4	186.7	186.7	186.7	186.7	186.4	185.8
180°	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5

(END OF REPORT)