

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331624-930

Luminaire Tested: **SA2XXRDIP-C290D530U930-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331624-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C290D530U930-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 530 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2566.4 lumens
Efficiency: N/A
Efficacy: 100.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 25.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331624-930
CATALOG NUMBER: SA2XXRDIP-C290D530U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331624-930

CATALOG NUMBER: SA2XXRDIP-C290D530U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40	33
1	94	90	86	83	85	81	78	76	65	63	61	50	49	47	36	35	35	28
2	86	79	73	68	77	71	67	62	57	54	51	44	42	40	32	31	30	24
3	79	70	63	57	71	63	57	52	51	47	43	39	37	34	29	27	26	21
4	72	62	54	49	65	56	50	45	45	41	37	35	32	30	26	24	22	18
5	66	55	47	42	59	50	43	38	41	36	32	32	28	26	23	21	20	16
6	61	49	42	36	55	45	38	33	37	32	28	29	25	23	21	19	17	14
7	56	45	37	32	51	41	34	29	33	28	25	26	23	20	20	17	16	13
8	52	40	33	28	47	37	30	26	30	25	22	24	20	18	18	16	14	11
9	49	37	30	25	44	34	27	23	28	23	20	22	19	16	17	14	13	10
10	45	34	27	22	41	31	25	21	26	21	18	20	17	15	16	13	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6608	6608	6608
5°	6634	6525	6561
10°	6583	6419	6365
15°	6506	6228	6048
20°	6402	5957	5658
25°	6296	5649	5279
30°	6145	5330	4793
35°	6000	4987	4366
40°	5855	4628	3872
45°	5683	4229	3425
50°	5506	3823	2987
55°	5326	3386	2567
60°	5118	2929	2131
65°	4883	2460	1937
70°	4598	2030	1780
75°	4255	1847	1666
80°	3756	1655	1516
85°	2946	1297	1297



TEST NUMBER: P331624-930

CATALOG NUMBER: SA2XXRDIP-C290D530U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	38.3	1.5
10°-20°	105.2	4.1
20°-30°	147.7	5.8
30°-40°	161.1	6.3
40°-50°	148.1	5.8
50°-60°	116.3	4.5
60°-70°	75.8	3.0
70°-80°	39.1	1.5
80°-90°	11.6	0.5
90°-100°	19.6	0.8
100°-110°	71.9	2.8
110°-120°	192.3	7.5
120°-130°	317.4	12.4
130°-140°	337.5	13.2
140°-150°	313.7	12.2
150°-160°	252.2	9.8
160°-170°	162.5	6.3
170°-180°	55.9	2.2
0°-30°	291.2	11.3
0°-40°	452.3	17.6
0°-60°	716.7	27.9
0°-90°	843.2	32.9
90°-120°	283.8	11.1
90°-150°	1252.5	48.8
90°-180°	1723.0	67.1
0°-180°	2566.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	409	409	409	409	409	
5°	409	407	403	406	405	39
15°	389	385	373	366	362	110
25°	353	341	317	302	296	162
35°	304	285	253	230	222	190
45°	249	223	185	160	150	192
55°	189	160	120	99	91	169
65°	128	98	64	52	51	127
75°	68	43	30	27	27	72
85°	16	8	7	7	7	19
90°	0	5	8	11	12	2
95°	28	15	17	19	18	34
105°	129	135	26	30	32	138
115°	245	252	262	75	35	241
125°	346	352	360	362	364	308
135°	428	435	439	443	442	330
145°	496	497	503	506	504	310
155°	547	543	548	550	547	252
165°	576	574	575	578	575	163
175°	589	586	587	590	586	56
180°	588	588	588	588	588	



TEST NUMBER: P331624-930

CATALOG NUMBER: SA2XXRDIP-C290D530U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	409.3	409.3	409.3	409.3	409.3	409.3	409.3	409.3	409.3	409.3	409.3
2.5°	410.7	410.4	410.1	409.8	409.4	408.9	408.1	407.5	406.8	406.0	406.7
5°	409.3	408.9	408.5	408.1	407.6	406.8	405.8	404.7	403.7	402.6	403.3
7.5°	405.0	404.6	404.0	403.5	403.0	402.1	400.9	399.6	398.4	397.1	397.3
10°	401.5	400.9	400.3	399.7	399.2	398.0	396.4	394.8	393.1	391.5	391.3
12.5°	397.1	396.3	395.6	394.9	394.2	392.8	390.7	388.6	386.5	384.3	383.9
15°	389.2	388.3	387.4	386.5	385.6	383.8	381.0	378.2	375.4	372.6	371.0
17.5°	379.7	378.3	376.9	375.5	374.1	371.7	368.1	364.5	360.9	357.3	355.5
20°	372.6	371.0	369.3	367.6	366.0	363.1	359.0	354.9	350.8	346.7	344.6
22.5°	364.9	363.1	361.2	359.4	357.5	354.2	349.6	345.0	340.4	335.7	333.0
25°	353.4	350.7	348.1	345.4	342.8	338.8	333.3	327.9	322.5	317.1	313.6
27.5°	339.4	336.6	333.7	330.8	327.9	323.4	317.3	311.2	305.1	299.0	295.1
30°	329.6	326.5	323.3	320.2	317.2	312.3	305.7	299.1	292.5	285.9	281.8
32.5°	320.2	316.5	312.8	309.2	305.5	300.4	293.7	286.9	280.2	273.5	268.7
35°	304.4	300.3	296.0	291.9	287.6	281.9	274.7	267.4	260.2	253.0	247.8
37.5°	288.8	284.1	279.5	274.9	270.3	264.2	256.4	248.7	241.0	233.3	227.6
40°	277.8	272.9	267.9	262.9	258.0	251.6	243.6	235.6	227.6	219.6	213.8
42.5°	266.5	261.3	256.1	250.9	245.7	239.0	230.7	222.5	214.3	206.0	200.0
45°	248.9	243.4	237.8	232.4	226.8	219.7	211.1	202.4	193.8	185.2	179.4
47.5°	231.7	225.8	220.0	214.2	208.3	201.0	192.0	183.1	174.1	165.3	159.5
50°	219.2	213.4	207.6	201.7	195.9	188.4	179.4	170.3	161.3	152.2	146.5
52.5°	207.1	201.0	194.9	188.8	182.7	175.2	166.3	157.5	148.6	139.7	134.3
55°	189.2	182.9	176.4	170.0	163.5	156.0	147.0	138.1	129.2	120.3	115.4
57.5°	171.0	164.4	157.8	151.2	144.6	137.1	128.5	120.0	111.5	102.9	98.3
60°	158.5	152.0	145.4	138.8	132.2	124.7	116.2	107.7	99.2	90.7	86.5
62.5°	146.3	139.8	133.2	126.6	120.0	112.7	104.6	96.5	88.5	80.4	76.4
65°	127.8	121.1	114.5	107.8	101.1	94.1	86.7	79.2	71.8	64.4	61.6
67.5°	109.8	103.2	96.6	90.0	83.4	76.7	70.0	63.4	56.7	50.1	48.8
70°	97.4	91.0	84.5	78.2	71.7	65.7	60.0	54.3	48.7	43.0	42.2
72.5°	85.5	79.4	73.2	67.1	60.9	55.6	51.0	46.5	41.9	37.3	36.6
75°	68.2	62.4	56.7	50.9	45.1	40.8	38.0	35.2	32.4	29.6	29.0
77.5°	51.0	46.0	40.9	35.9	30.8	27.6	26.3	24.9	23.6	22.3	21.9
80°	40.4	36.2	32.0	27.8	23.6	21.0	20.2	19.4	18.6	17.8	17.4
82.5°	30.6	27.3	24.1	20.8	17.5	15.6	15.0	14.4	13.9	13.4	13.1
85°	15.9	14.2	12.5	10.8	9.0	8.0	7.7	7.5	7.3	7.0	7.0
87.5°	4.8	4.5	4.2	3.8	3.6	3.5	3.6	3.8	3.9	4.1	4.1
90°	0.4	1.5	2.5	3.5	4.6	5.5	6.3	7.0	7.7	8.5	9.0
92.5°	8.6	8.5	8.4	8.3	8.2	8.4	8.7	9.1	9.5	9.9	10.1
95°	27.6	24.5	21.4	18.3	15.2	13.9	14.6	15.2	15.9	16.6	17.0
97.5°	54.9	46.1	37.3	28.5	19.7	16.1	17.6	19.2	20.7	22.2	22.6
100°	75.3	62.4	49.4	36.4	23.5	17.9	19.4	21.0	22.7	24.2	25.0
102.5°	97.8	95.1	92.3	89.5	86.8	84.7	82.3	80.6	79.4	78.6	78.1
105°	129.3	132.2	135.0	137.9	140.7	143.2	145.4	147.2	148.6	149.5	150.0
107.5°	165.3	167.6	169.9	172.2	174.5	176.5	178.1	179.3	180.1	180.5	180.7
110°	188.5	190.5	192.5	194.4	196.4	198.1	199.4	200.3	200.8	201.0	201.1



TEST NUMBER: P331624-930

CATALOG NUMBER: SA2XXRDIP-C290D530U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	210.3	212.1	213.8	215.6	217.3	214.8	208.1	201.3	194.5	187.8	153.3
115°	244.7	246.2	247.9	249.5	251.1	253.1	255.4	257.8	260.2	262.5	218.7
117.5°	275.4	277.2	279.0	280.8	282.6	284.3	285.9	287.6	289.2	290.7	280.2
120°	297.8	299.2	300.7	302.1	303.5	305.1	306.8	308.5	310.1	311.9	313.0
122.5°	316.9	318.4	319.9	321.4	322.9	324.6	326.4	328.2	330.1	332.0	332.6
125°	345.9	347.2	348.4	349.6	350.8	352.4	354.2	356.0	357.8	359.5	360.2
127.5°	372.2	373.6	375.0	376.3	377.6	379.0	380.3	381.7	383.0	384.4	385.3
130°	388.9	390.4	391.9	393.5	394.9	396.2	397.3	398.3	399.3	400.4	401.5
132.5°	405.9	407.2	408.5	409.8	411.1	412.2	413.3	414.3	415.3	416.4	417.3
135°	428.0	429.6	431.0	432.6	434.1	435.3	436.1	437.0	437.8	438.6	439.6
137.5°	450.5	451.4	452.5	453.6	454.6	455.7	456.6	457.6	458.5	459.5	460.5
140°	465.0	465.8	466.6	467.3	468.1	469.0	470.0	471.1	472.1	473.1	474.0
142.5°	477.3	478.0	478.7	479.3	480.0	480.9	482.2	483.3	484.5	485.8	486.5
145°	496.5	496.4	496.4	496.3	496.2	496.9	498.6	500.1	501.7	503.4	504.0
147.5°	513.3	512.9	512.6	512.3	511.8	512.5	514.0	515.7	517.2	518.9	519.3
150°	524.2	523.5	522.9	522.2	521.5	522.0	523.5	525.0	526.5	528.0	528.6
152.5°	533.4	532.6	531.9	531.2	530.4	530.8	532.2	533.7	535.1	536.5	537.1
155°	546.7	545.9	545.0	544.2	543.3	543.5	544.6	545.8	546.9	548.0	548.6
157.5°	557.2	556.5	555.8	555.1	554.3	554.4	555.1	556.0	556.8	557.6	558.2
160°	563.4	562.8	562.2	561.7	561.1	561.1	561.7	562.2	562.8	563.4	563.9
162.5°	568.8	568.2	567.6	567.0	566.6	566.5	567.0	567.4	567.9	568.4	569.1
165°	576.1	575.5	574.9	574.4	573.8	573.7	574.0	574.2	574.5	574.8	575.5
167.5°	581.6	581.0	580.4	579.8	579.3	579.1	579.4	579.7	579.9	580.2	580.8
170°	584.6	584.1	583.5	582.9	582.4	582.1	582.4	582.5	582.7	582.9	583.6
172.5°	586.7	586.1	585.5	585.0	584.4	584.2	584.4	584.6	584.7	585.0	585.6
175°	589.3	588.6	588.0	587.3	586.6	586.4	586.6	586.8	586.9	587.2	587.8
177.5°	589.7	589.2	588.6	588.2	587.6	587.3	587.4	587.5	587.6	587.7	588.2
180°	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0



TEST NUMBER: P331624-930

CATALOG NUMBER: SA2XXRDIP-C290D530U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	409.3	409.3	409.3	409.3	409.3	409.3	409.3	409.3
2.5°	407.3	408.0	408.6	408.9	408.8	408.6	408.5	408.4
5°	404.1	404.8	405.5	405.8	405.5	405.3	405.0	404.8
7.5°	397.5	397.8	397.9	397.9	397.5	397.0	396.6	396.2
10°	391.0	390.8	390.5	390.1	389.6	389.1	388.7	388.2
12.5°	383.5	383.0	382.6	382.0	381.2	380.3	379.5	378.7
15°	369.5	367.9	366.3	365.2	364.4	363.5	362.6	361.8
17.5°	353.6	351.7	349.9	348.3	346.8	345.4	344.0	342.6
20°	342.6	340.5	338.4	336.5	334.7	332.9	331.1	329.3
22.5°	330.4	327.8	325.1	323.1	321.7	320.4	319.0	317.7
25°	310.3	306.9	303.5	301.3	300.0	298.7	297.5	296.3
27.5°	291.1	287.1	283.2	280.3	278.3	276.4	274.4	272.5
30°	277.5	273.4	269.1	266.0	263.7	261.5	259.3	257.1
32.5°	263.9	259.1	254.3	250.9	248.8	246.7	244.6	242.6
35°	242.6	237.4	232.2	228.7	226.9	225.1	223.3	221.5
37.5°	221.8	216.1	210.4	206.5	204.5	202.4	200.3	198.2
40°	208.0	202.1	196.2	192.2	190.1	188.0	185.8	183.7
42.5°	193.9	187.8	181.8	177.8	175.7	173.7	171.5	169.5
45°	173.5	167.6	161.8	157.9	156.0	153.9	152.0	150.0
47.5°	153.6	147.8	142.0	138.2	136.4	134.6	132.8	131.0
50°	140.9	135.2	129.5	125.8	124.1	122.4	120.6	118.9
52.5°	128.8	123.4	117.9	114.3	112.8	111.1	109.5	107.9
55°	110.5	105.6	100.6	97.3	95.8	94.2	92.7	91.2
57.5°	93.8	89.3	84.8	81.9	80.6	79.2	77.9	76.6
60°	82.3	78.2	73.9	71.2	69.9	68.6	67.3	66.0
62.5°	72.4	68.4	64.4	62.0	61.1	60.4	59.6	58.8
65°	58.9	56.0	53.2	51.7	51.4	51.2	51.0	50.7
67.5°	47.5	46.2	44.9	44.2	43.9	43.6	43.4	43.1
70°	41.3	40.5	39.7	39.1	38.7	38.4	38.1	37.7
72.5°	36.0	35.2	34.6	34.2	33.9	33.8	33.5	33.3
75°	28.5	27.9	27.3	27.0	26.9	26.8	26.7	26.7
77.5°	21.5	21.2	20.9	20.7	20.5	20.4	20.3	20.1
80°	17.1	16.8	16.5	16.3	16.3	16.3	16.3	16.3
82.5°	13.0	12.7	12.6	12.5	12.5	12.5	12.5	12.5
85°	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0
87.5°	4.2	4.2	4.2	4.2	4.2	4.3	4.3	4.4
90°	9.5	9.9	10.4	10.8	10.9	11.1	11.3	11.5
92.5°	10.4	10.6	10.8	11.0	11.2	11.3	11.4	11.5
95°	17.5	18.0	18.5	18.7	18.6	18.5	18.4	18.3
97.5°	23.0	23.3	23.7	24.0	24.1	24.2	24.3	24.5
100°	25.8	26.5	27.3	27.7	28.0	28.1	28.3	28.5
102.5°	26.9	27.9	28.9	29.5	29.8	30.0	30.2	30.6
105°	28.0	29.1	30.1	30.8	31.2	31.6	32.0	32.4
107.5°	34.2	33.2	32.1	31.8	32.1	32.5	32.9	33.3
110°	55.5	46.1	36.6	32.1	32.4	32.9	33.3	33.6



TEST NUMBER: P331624-930

CATALOG NUMBER: SA2XXRDIP-C290D530U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	118.8	84.3	49.8	32.8	33.0	33.3	33.7	33.9
115°	175.0	131.2	87.4	62.1	55.3	48.5	41.7	34.9
117.5°	269.6	259.0	248.4	232.0	209.5	187.2	164.9	142.4
120°	314.1	315.3	316.4	310.6	297.8	285.1	272.3	259.5
122.5°	333.3	334.0	334.7	333.8	331.3	328.8	326.4	323.8
125°	360.9	361.5	362.2	362.6	363.0	363.2	363.5	363.8
127.5°	386.3	387.3	388.2	388.7	388.8	388.9	388.9	389.0
130°	402.4	403.5	404.6	405.0	404.9	404.8	404.7	404.6
132.5°	418.2	419.1	420.0	420.3	420.2	420.1	420.0	420.0
135°	440.6	441.5	442.5	442.9	442.6	442.5	442.3	442.1
137.5°	461.4	462.3	463.3	463.5	463.2	462.8	462.6	462.3
140°	474.8	475.6	476.5	476.7	476.2	475.8	475.3	474.8
142.5°	487.3	488.0	488.9	489.0	488.5	488.0	487.5	487.1
145°	504.7	505.3	506.0	506.1	505.6	505.2	504.7	504.2
147.5°	519.8	520.3	520.8	520.8	520.5	520.1	519.7	519.3
150°	529.1	529.7	530.3	530.4	529.9	529.4	528.9	528.5
152.5°	537.7	538.3	538.8	538.7	538.2	537.5	536.9	536.3
155°	549.2	549.8	550.3	550.2	549.4	548.7	548.0	547.1
157.5°	558.8	559.5	560.1	560.1	559.3	558.6	557.8	557.1
160°	564.4	565.0	565.6	565.6	564.9	564.3	563.5	562.9
162.5°	569.7	570.4	571.0	571.0	570.1	569.3	568.5	567.7
165°	576.2	576.8	577.5	577.5	576.8	576.2	575.5	574.8
167.5°	581.5	582.2	582.9	582.8	581.9	581.1	580.2	579.4
170°	584.2	584.9	585.5	585.5	584.6	583.8	582.9	582.0
172.5°	586.3	586.9	587.6	587.5	586.7	585.8	585.0	584.1
175°	588.5	589.1	589.8	589.7	588.7	587.7	586.9	585.9
177.5°	588.7	589.3	589.8	589.7	589.1	588.3	587.7	587.0
180°	588.0	588.0	588.0	588.0	588.0	588.0	588.0	588.0

(END OF REPORT)