

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331630-930

Luminaire Tested: **SA2XXRDIP-C290D725U930-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331630-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C290D725U930-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 725 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3205.7 lumens
Efficiency: N/A
Efficacy: 102.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331630-930

CATALOG NUMBER: SA2XXRDIP-C290D725U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331630-930

CATALOG NUMBER: SA2XXRDIP-C290D725U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	70	70	70	52	52	52	34	34	34	26
1	93	89	85	82	83	79	76	73	62	60	58	46	44	43	31	30	29	23
2	85	78	72	67	75	70	65	61	54	51	48	40	38	36	27	26	25	19
3	77	68	62	56	69	61	56	51	48	44	41	36	33	31	24	23	22	17
4	71	61	53	47	63	54	48	43	43	38	35	32	29	27	22	20	19	15
5	65	54	46	41	58	49	42	37	38	34	30	29	26	23	20	18	17	13
6	60	48	41	35	53	44	37	32	34	30	26	26	23	20	18	16	15	11
7	55	44	36	31	49	39	33	28	31	26	23	24	20	18	17	15	13	10
8	51	39	32	27	46	36	29	25	28	24	20	22	18	16	15	13	12	9
9	48	36	29	24	42	33	26	22	26	21	18	20	17	14	14	12	11	8
10	44	33	26	21	40	30	24	20	24	19	16	18	15	13	13	11	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6608	6608	6608
5°	6634	6525	6561
10°	6583	6419	6365
15°	6506	6228	6048
20°	6402	5957	5658
25°	6296	5649	5279
30°	6145	5330	4793
35°	6000	4987	4366
40°	5855	4628	3872
45°	5683	4229	3425
50°	5506	3823	2987
55°	5326	3386	2567
60°	5118	2929	2131
65°	4883	2460	1937
70°	4598	2030	1780
75°	4255	1847	1666
80°	3756	1655	1516
85°	2946	1297	1297



TEST NUMBER: P331630-930

CATALOG NUMBER: SA2XXRDIP-C290D725U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	38.3	1.2
10°-20°	105.2	3.3
20°-30°	147.7	4.6
30°-40°	161.1	5.0
40°-50°	148.1	4.6
50°-60°	116.3	3.6
60°-70°	75.8	2.4
70°-80°	39.1	1.2
80°-90°	12.1	0.4
90°-100°	26.9	0.8
100°-110°	98.6	3.1
110°-120°	263.5	8.2
120°-130°	435.0	13.6
130°-140°	462.7	14.4
140°-150°	430.0	13.4
150°-160°	345.7	10.8
160°-170°	222.8	6.9
170°-180°	76.7	2.4
0°-30°	291.2	9.1
0°-40°	452.3	14.1
0°-60°	716.7	22.4
0°-90°	843.7	26.3
90°-120°	389.0	12.1
90°-150°	1716.8	53.6
90°-180°	2362.0	73.7
0°-180°	3205.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	409	409	409	409	409	
5°	409	407	403	406	405	39
15°	389	385	373	366	362	110
25°	353	341	317	302	296	162
35°	304	285	253	230	222	190
45°	249	223	185	160	150	192
55°	189	160	120	99	91	169
65°	128	98	64	52	51	127
75°	68	43	30	27	27	72
85°	16	8	7	7	7	19
90°	1	7	12	14	16	2
95°	38	20	23	26	25	46
105°	177	185	36	42	44	189
115°	335	346	360	102	48	330
125°	474	482	493	497	499	423
135°	587	596	601	607	606	453
145°	681	681	690	694	691	426
155°	749	745	751	754	750	345
165°	790	786	788	792	788	223
175°	808	804	805	808	803	77
180°	806	806	806	806	806	



TEST NUMBER: P331630-930

CATALOG NUMBER: SA2XXRDIP-C290D725U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	409.3	409.3	409.3	409.3	409.3	409.3	409.3	409.3	409.3	409.3	409.3
2.5°	410.7	410.4	410.1	409.8	409.4	408.9	408.1	407.5	406.8	406.0	406.7
5°	409.3	408.9	408.5	408.1	407.6	406.8	405.8	404.7	403.7	402.6	403.3
7.5°	405.0	404.6	404.0	403.5	403.0	402.1	400.9	399.6	398.4	397.1	397.3
10°	401.5	400.9	400.3	399.7	399.2	398.0	396.4	394.8	393.1	391.5	391.3
12.5°	397.1	396.3	395.6	394.9	394.2	392.8	390.7	388.6	386.5	384.3	383.9
15°	389.2	388.3	387.4	386.5	385.6	383.8	381.0	378.2	375.4	372.6	371.0
17.5°	379.7	378.3	376.9	375.5	374.1	371.7	368.1	364.5	360.9	357.3	355.5
20°	372.6	371.0	369.3	367.6	366.0	363.1	359.0	354.9	350.8	346.7	344.6
22.5°	364.9	363.1	361.2	359.4	357.5	354.2	349.6	345.0	340.4	335.7	333.0
25°	353.4	350.7	348.1	345.4	342.8	338.8	333.3	327.9	322.5	317.1	313.6
27.5°	339.4	336.6	333.7	330.8	327.9	323.4	317.3	311.2	305.1	299.0	295.1
30°	329.6	326.5	323.3	320.2	317.2	312.3	305.7	299.1	292.5	285.9	281.8
32.5°	320.2	316.5	312.8	309.2	305.5	300.4	293.7	286.9	280.2	273.5	268.7
35°	304.4	300.3	296.0	291.9	287.6	281.9	274.7	267.4	260.2	253.0	247.8
37.5°	288.8	284.1	279.5	274.9	270.3	264.2	256.4	248.7	241.0	233.3	227.6
40°	277.8	272.9	267.9	262.9	258.0	251.6	243.6	235.6	227.6	219.6	213.8
42.5°	266.5	261.3	256.1	250.9	245.7	239.0	230.7	222.5	214.3	206.0	200.0
45°	248.9	243.4	237.8	232.4	226.8	219.7	211.1	202.4	193.8	185.2	179.4
47.5°	231.7	225.8	220.0	214.2	208.3	201.0	192.0	183.1	174.1	165.3	159.5
50°	219.2	213.4	207.6	201.7	195.9	188.4	179.4	170.3	161.3	152.2	146.5
52.5°	207.1	201.0	194.9	188.8	182.7	175.2	166.3	157.5	148.6	139.7	134.3
55°	189.2	182.9	176.4	170.0	163.5	156.0	147.0	138.1	129.2	120.3	115.4
57.5°	171.0	164.4	157.8	151.2	144.6	137.1	128.5	120.0	111.5	102.9	98.3
60°	158.5	152.0	145.4	138.8	132.2	124.7	116.2	107.7	99.2	90.7	86.5
62.5°	146.3	139.8	133.2	126.6	120.0	112.7	104.6	96.5	88.5	80.4	76.4
65°	127.8	121.1	114.5	107.8	101.1	94.1	86.7	79.2	71.8	64.4	61.6
67.5°	109.8	103.2	96.6	90.0	83.4	76.7	70.0	63.4	56.7	50.1	48.8
70°	97.4	91.0	84.5	78.2	71.7	65.7	60.0	54.3	48.7	43.0	42.2
72.5°	85.5	79.4	73.2	67.1	60.9	55.6	51.0	46.5	41.9	37.3	36.6
75°	68.2	62.4	56.7	50.9	45.1	40.8	38.0	35.2	32.4	29.6	29.0
77.5°	51.0	46.0	40.9	35.9	30.8	27.6	26.3	24.9	23.6	22.3	21.9
80°	40.4	36.2	32.0	27.8	23.6	21.0	20.2	19.4	18.6	17.8	17.4
82.5°	30.6	27.3	24.1	20.8	17.5	15.6	15.0	14.4	13.9	13.4	13.1
85°	15.9	14.2	12.5	10.8	9.0	8.0	7.7	7.5	7.3	7.0	7.0
87.5°	4.9	4.6	4.4	4.2	3.9	3.9	4.1	4.3	4.5	4.7	4.7
90°	0.6	2.0	3.4	4.9	6.3	7.5	8.6	9.6	10.6	11.7	12.3
92.5°	11.7	11.7	11.5	11.4	11.3	11.5	12.0	12.5	13.0	13.5	13.9
95°	37.9	33.7	29.4	25.1	20.8	19.1	20.1	21.0	21.9	22.7	23.4
97.5°	75.3	63.2	51.1	39.1	27.0	22.0	24.1	26.3	28.4	30.4	31.0
100°	103.2	85.4	67.8	50.0	32.2	24.5	26.7	28.9	31.1	33.3	34.2
102.5°	134.0	130.3	126.5	122.8	119.0	107.9	89.4	71.0	52.6	34.2	35.5
105°	177.3	181.2	185.1	189.0	192.8	177.1	141.7	106.3	70.9	35.5	37.0
107.5°	226.7	229.8	232.9	236.0	239.2	219.6	177.1	134.7	92.2	49.8	48.3
110°	258.4	261.1	263.8	266.5	269.2	251.8	214.4	177.0	139.5	102.1	89.1



TEST NUMBER: P331630-930

CATALOG NUMBER: SA2XXRDIP-C290D725U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	288.2	290.7	293.0	295.5	297.8	294.4	285.2	275.9	266.7	257.4	210.2
115°	335.3	337.5	339.7	341.9	344.1	346.9	350.1	353.4	356.6	359.9	299.9
117.5°	377.5	379.9	382.4	384.8	387.3	389.6	391.9	394.1	396.3	398.6	384.1
120°	408.2	410.2	412.1	414.1	416.0	418.2	420.5	422.8	425.2	427.5	429.0
122.5°	434.4	436.4	438.5	440.5	442.5	444.8	447.4	450.0	452.5	455.0	455.9
125°	474.2	475.8	477.5	479.2	480.9	483.0	485.4	487.9	490.3	492.8	493.7
127.5°	510.2	512.1	514.0	515.8	517.6	519.5	521.4	523.2	525.1	526.8	528.2
130°	533.0	535.2	537.2	539.2	541.4	543.1	544.5	545.9	547.4	548.8	550.2
132.5°	556.4	558.2	559.9	561.7	563.5	565.0	566.5	567.9	569.3	570.7	571.9
135°	586.7	588.8	590.8	593.0	595.0	596.6	597.8	598.9	600.1	601.3	602.6
137.5°	617.4	618.8	620.3	621.7	623.2	624.6	625.9	627.2	628.5	629.9	631.1
140°	637.5	638.5	639.5	640.6	641.6	642.9	644.2	645.7	647.1	648.6	649.7
142.5°	654.3	655.2	656.2	657.0	657.9	659.3	660.9	662.5	664.1	665.8	666.8
145°	680.6	680.4	680.4	680.2	680.1	681.1	683.3	685.5	687.7	689.9	690.9
147.5°	703.6	703.1	702.6	702.1	701.6	702.5	704.7	706.8	709.0	711.2	711.8
150°	718.5	717.6	716.7	715.8	714.9	715.5	717.5	719.6	721.7	723.7	724.6
152.5°	731.1	730.1	729.1	728.1	727.1	727.6	729.5	731.5	733.4	735.4	736.2
155°	749.4	748.3	747.1	745.9	744.8	744.9	746.5	748.0	749.6	751.1	752.0
157.5°	763.8	762.8	761.8	760.8	759.9	759.9	761.0	762.1	763.1	764.3	765.2
160°	772.2	771.4	770.6	769.8	769.1	769.1	769.8	770.6	771.4	772.2	773.0
162.5°	779.7	778.9	778.1	777.3	776.5	776.5	777.1	777.8	778.5	779.2	780.1
165°	789.7	788.9	788.1	787.3	786.5	786.4	786.8	787.2	787.5	787.9	788.8
167.5°	797.1	796.4	795.6	794.8	794.0	793.8	794.2	794.5	794.9	795.2	796.1
170°	801.4	800.5	799.8	799.0	798.3	797.9	798.3	798.5	798.7	799.0	799.9
172.5°	804.1	803.3	802.6	801.8	801.0	800.8	801.0	801.3	801.5	801.8	802.7
175°	807.7	806.8	805.9	805.0	804.1	803.8	804.0	804.3	804.5	804.9	805.8
177.5°	808.4	807.6	806.9	806.2	805.4	805.1	805.2	805.4	805.4	805.5	806.2
180°	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0



TEST NUMBER: P331630-930

CATALOG NUMBER: SA2XXRDIP-C290D725U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	409.3	409.3	409.3	409.3	409.3	409.3	409.3	409.3
2.5°	407.3	408.0	408.6	408.9	408.8	408.6	408.5	408.4
5°	404.1	404.8	405.5	405.8	405.5	405.3	405.0	404.8
7.5°	397.5	397.8	397.9	397.9	397.5	397.0	396.6	396.2
10°	391.0	390.8	390.5	390.1	389.6	389.1	388.7	388.2
12.5°	383.5	383.0	382.6	382.0	381.2	380.3	379.5	378.7
15°	369.5	367.9	366.3	365.2	364.4	363.5	362.6	361.8
17.5°	353.6	351.7	349.9	348.3	346.8	345.4	344.0	342.6
20°	342.6	340.5	338.4	336.5	334.7	332.9	331.1	329.3
22.5°	330.4	327.8	325.1	323.1	321.7	320.4	319.0	317.7
25°	310.3	306.9	303.5	301.3	300.0	298.7	297.5	296.3
27.5°	291.1	287.1	283.2	280.3	278.3	276.4	274.4	272.5
30°	277.5	273.4	269.1	266.0	263.7	261.5	259.3	257.1
32.5°	263.9	259.1	254.3	250.9	248.8	246.7	244.6	242.6
35°	242.6	237.4	232.2	228.7	226.9	225.1	223.3	221.5
37.5°	221.8	216.1	210.4	206.5	204.5	202.4	200.3	198.2
40°	208.0	202.1	196.2	192.2	190.1	188.0	185.8	183.7
42.5°	193.9	187.8	181.8	177.8	175.7	173.7	171.5	169.5
45°	173.5	167.6	161.8	157.9	156.0	153.9	152.0	150.0
47.5°	153.6	147.8	142.0	138.2	136.4	134.6	132.8	131.0
50°	140.9	135.2	129.5	125.8	124.1	122.4	120.6	118.9
52.5°	128.8	123.4	117.9	114.3	112.8	111.1	109.5	107.9
55°	110.5	105.6	100.6	97.3	95.8	94.2	92.7	91.2
57.5°	93.8	89.3	84.8	81.9	80.6	79.2	77.9	76.6
60°	82.3	78.2	73.9	71.2	69.9	68.6	67.3	66.0
62.5°	72.4	68.4	64.4	62.0	61.1	60.4	59.6	58.8
65°	58.9	56.0	53.2	51.7	51.4	51.2	51.0	50.7
67.5°	47.5	46.2	44.9	44.2	43.9	43.6	43.4	43.1
70°	41.3	40.5	39.7	39.1	38.7	38.4	38.1	37.7
72.5°	36.0	35.2	34.6	34.2	33.9	33.8	33.5	33.3
75°	28.5	27.9	27.3	27.0	26.9	26.8	26.7	26.7
77.5°	21.5	21.2	20.9	20.7	20.5	20.4	20.3	20.1
80°	17.1	16.8	16.5	16.3	16.3	16.3	16.3	16.3
82.5°	13.0	12.7	12.6	12.5	12.5	12.5	12.5	12.5
85°	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0
87.5°	4.8	4.9	5.0	5.1	5.1	5.1	5.1	5.2
90°	13.0	13.6	14.3	14.7	15.0	15.2	15.5	15.7
92.5°	14.2	14.5	14.8	15.2	15.2	15.4	15.6	15.7
95°	24.1	24.7	25.4	25.6	25.4	25.4	25.2	25.1
97.5°	31.5	32.0	32.5	32.9	33.0	33.2	33.3	33.5
100°	35.3	36.4	37.4	38.1	38.3	38.6	38.8	39.1
102.5°	36.9	38.2	39.5	40.4	40.8	41.2	41.5	41.9
105°	38.4	39.9	41.3	42.2	42.8	43.3	43.8	44.4
107.5°	46.9	45.4	44.0	43.5	44.0	44.6	45.1	45.6
110°	76.1	63.2	50.2	44.0	44.5	45.0	45.6	46.1



TEST NUMBER: P331630-930

CATALOG NUMBER: SA2XXRDIP-C290D725U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	162.9	115.6	68.3	44.8	45.3	45.7	46.1	46.6
115°	239.9	179.9	119.8	85.1	75.8	66.4	57.2	47.9
117.5°	369.6	355.0	340.5	317.9	287.2	256.6	225.9	195.3
120°	430.6	432.2	433.7	425.7	408.2	390.8	373.2	355.8
122.5°	456.9	457.8	458.8	457.5	454.1	450.7	447.4	443.9
125°	494.6	495.5	496.4	497.1	497.5	497.9	498.2	498.6
127.5°	529.5	530.8	532.1	532.9	533.0	533.0	533.1	533.2
130°	551.6	553.1	554.5	555.1	555.1	554.9	554.7	554.6
132.5°	573.2	574.4	575.6	576.2	576.0	575.9	575.8	575.6
135°	603.9	605.2	606.5	607.0	606.7	606.5	606.2	605.9
137.5°	632.4	633.7	635.0	635.4	635.0	634.5	634.1	633.6
140°	650.9	652.0	653.2	653.5	652.8	652.2	651.5	650.9
142.5°	667.9	669.0	670.0	670.3	669.6	669.0	668.3	667.6
145°	691.8	692.7	693.6	693.7	693.1	692.4	691.8	691.1
147.5°	712.5	713.2	713.9	714.0	713.4	712.8	712.3	711.8
150°	725.3	726.1	726.8	726.9	726.3	725.6	725.0	724.3
152.5°	736.9	737.8	738.6	738.5	737.7	736.8	736.0	735.1
155°	752.8	753.5	754.3	754.2	753.1	752.1	751.1	750.0
157.5°	766.0	766.9	767.8	767.7	766.7	765.6	764.7	763.7
160°	773.7	774.5	775.3	775.2	774.3	773.4	772.5	771.6
162.5°	780.9	781.8	782.7	782.6	781.5	780.3	779.3	778.1
165°	789.7	790.7	791.6	791.6	790.7	789.7	788.8	787.9
167.5°	797.1	798.0	798.9	798.7	797.6	796.5	795.2	794.1
170°	800.8	801.7	802.7	802.5	801.4	800.1	799.0	797.9
172.5°	803.6	804.5	805.4	805.3	804.1	803.0	801.8	800.6
175°	806.7	807.6	808.5	808.3	807.0	805.7	804.4	803.1
177.5°	807.0	807.7	808.5	808.4	807.4	806.5	805.5	804.6
180°	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0

(END OF REPORT)