

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331328-840

Luminaire Tested: **SA2XXDIP-C485D1080U840-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331328-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXDIP-C485D1080U840-4F0-1E-UDD-F1  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1080 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5887.9 lumens  
Efficiency: N/A  
Efficacy: 119.2 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 49.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331328-840  
CATALOG NUMBER: SA2XXDIP-C485D1080U840-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P331328-840

CATALOG NUMBER: SA2XXDIP-C485D1080U840-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	34
1	94	90	86	83	85	81	78	75	65	63	61	50	49	47	37	36	35	29
2	86	78	73	67	77	71	66	62	57	53	50	44	42	40	32	31	29	24
3	78	69	62	56	70	62	56	51	50	46	42	39	36	33	28	27	25	20
4	71	61	53	47	64	55	49	44	45	40	36	35	31	29	25	23	22	17
5	65	54	46	40	59	49	42	37	40	35	31	31	28	25	23	21	19	15
6	60	48	41	35	54	44	37	32	36	31	27	28	24	22	21	18	16	13
7	56	44	36	31	50	40	33	28	32	27	24	25	22	19	19	16	15	12
8	52	40	32	27	46	36	29	25	29	24	21	23	20	17	17	15	13	11
9	48	36	29	24	43	33	26	22	27	22	19	21	18	15	16	14	12	10
10	45	33	26	21	40	30	24	20	25	20	17	20	16	14	15	12	11	9

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	12665	12665	12665
5°	12713	12530	12603
10°	12637	12403	12463
15°	12481	12242	12227
20°	12259	12000	11986
25°	12039	11703	11703
30°	11757	11432	11332
35°	11491	11105	10941
40°	11160	10779	10570
45°	10832	10453	10195
50°	10477	10115	9756
55°	10106	9723	9362
60°	9691	9255	8913
65°	9249	8787	8382
70°	8686	8224	7832
75°	7904	7573	7392
80°	7011	6797	6453
85°	5724	5446	4891



TEST NUMBER: P331328-840

CATALOG NUMBER: SA2XXDIP-C485D1080U840-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	73.8	1.3
10°-20°	207.5	3.5
20°-30°	305.0	5.2
30°-40°	354.3	6.0
40°-50°	354.0	6.0
50°-60°	308.7	5.2
60°-70°	228.2	3.9
70°-80°	129.3	2.2
80°-90°	40.3	0.7
90°-100°	88.1	1.5
100°-110°	273.6	4.6
110°-120°	467.6	7.9
120°-130°	614.9	10.4
130°-140°	690.2	11.7
140°-150°	676.7	11.5
150°-160°	567.6	9.6
160°-170°	376.5	6.4
170°-180°	131.6	2.2
0°-30°	586.3	10.0
0°-40°	940.7	16.0
0°-60°	1603.3	27.2
0°-90°	2001.1	34.0
90°-120°	829.3	14.1
90°-150°	2811.1	47.7
90°-180°	3887.0	66.0
0°-180°	5887.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	784	784	784	784	784	
5°	784	781	773	779	778	74
15°	747	742	732	735	732	210
25°	676	669	657	658	657	311
35°	583	575	563	559	555	364
45°	474	469	458	450	446	366
55°	359	354	345	337	333	321
65°	242	237	230	223	219	239
75°	127	125	121	117	118	135
85°	31	30	29	27	26	35
90°	1	16	41	39	40	5
95°	61	72	75	75	73	70
105°	252	256	258	260	260	266
115°	469	476	474	473	469	464
125°	683	692	690	686	685	610
135°	883	896	899	897	894	682
145°	1072	1080	1087	1088	1084	670
155°	1226	1229	1233	1238	1235	564
165°	1334	1333	1333	1340	1335	376
175°	1388	1384	1382	1389	1383	132
180°	1390	1390	1390	1390	1390	



TEST NUMBER: P331328-840

CATALOG NUMBER: SA2XXDIP-C485D1080U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	784.4	784.4	784.4	784.4	784.4	784.4	784.4	784.4	784.4	784.4	784.4
2.5°	788.0	787.3	786.7	786.0	785.3	784.3	782.7	781.3	779.8	778.3	779.7
5°	784.4	783.7	783.0	782.3	781.7	780.4	778.6	776.8	774.9	773.1	774.4
7.5°	777.4	776.4	775.4	774.3	773.3	771.8	769.9	768.1	766.2	764.3	765.7
10°	770.8	769.6	768.4	767.3	766.1	764.5	762.4	760.5	758.5	756.5	757.8
12.5°	761.7	760.7	759.6	758.6	757.6	756.1	754.1	752.0	750.0	748.0	748.9
15°	746.7	745.7	744.7	743.7	742.7	741.0	738.8	736.7	734.5	732.4	733.0
17.5°	727.3	726.4	725.4	724.4	723.4	721.8	719.5	717.3	715.1	712.9	713.7
20°	713.5	712.5	711.4	710.4	709.4	707.8	705.4	703.1	700.7	698.4	698.9
22.5°	699.6	698.2	696.8	695.4	694.0	692.2	689.9	687.7	685.5	683.3	683.4
25°	675.8	674.4	673.1	671.8	670.4	668.3	665.5	662.6	659.7	656.9	657.2
27.5°	648.6	647.4	646.2	645.0	643.8	642.1	639.9	637.5	635.3	633.1	632.6
30°	630.6	629.1	627.8	626.5	625.1	623.2	620.7	618.2	615.7	613.2	612.7
32.5°	611.2	610.2	609.0	607.9	606.9	605.0	602.4	599.8	597.1	594.5	593.6
35°	583.0	581.3	579.7	577.9	576.3	574.1	571.5	568.8	566.0	563.4	562.4
37.5°	551.2	549.7	548.3	546.7	545.2	543.2	540.5	537.9	535.1	532.5	531.2
40°	529.5	528.1	526.7	525.4	524.1	522.1	519.4	516.7	514.0	511.4	509.9
42.5°	508.4	507.0	505.6	504.3	503.0	501.0	498.3	495.6	492.9	490.2	488.6
45°	474.4	473.2	472.0	470.9	469.7	467.9	465.3	462.8	460.3	457.8	456.0
47.5°	440.6	439.5	438.4	437.3	436.2	434.3	431.7	429.1	426.5	423.8	421.9
50°	417.1	416.3	415.4	414.5	413.7	412.1	409.8	407.5	405.1	402.7	400.4
52.5°	394.2	393.0	391.9	390.8	389.7	388.1	385.9	383.6	381.4	379.2	377.3
55°	359.0	358.0	357.0	356.0	355.0	353.5	351.4	349.4	347.4	345.4	343.5
57.5°	323.7	322.9	322.0	321.3	320.5	319.0	316.8	314.6	312.4	310.1	308.1
60°	300.1	299.5	298.8	298.1	297.5	296.0	293.7	291.2	288.9	286.6	284.8
62.5°	277.2	276.2	275.1	274.0	273.0	271.6	269.7	267.9	266.1	264.3	262.6
65°	242.1	241.1	240.0	239.0	238.1	236.7	235.1	233.4	231.7	230.0	228.5
67.5°	206.3	205.5	204.7	203.9	203.1	202.0	200.5	198.9	197.4	195.9	194.8
70°	184.0	183.4	182.7	182.0	181.4	180.3	178.7	177.2	175.7	174.2	173.1
72.5°	161.1	160.5	159.8	159.1	158.4	157.6	156.6	155.6	154.7	153.7	152.5
75°	126.7	126.3	126.0	125.7	125.3	124.8	123.9	123.1	122.3	121.4	120.4
77.5°	95.9	95.3	94.8	94.2	93.6	93.2	92.9	92.5	92.2	91.9	91.4
80°	75.4	75.2	75.1	74.9	74.7	74.5	74.1	73.8	73.5	73.1	72.6
82.5°	56.1	56.0	56.0	56.0	55.9	55.8	55.6	55.4	55.2	55.0	54.4
85°	30.9	30.8	30.6	30.4	30.3	30.1	29.9	29.8	29.6	29.4	28.9
87.5°	11.1	11.4	11.8	12.1	12.5	13.1	14.0	14.9	15.8	16.7	16.2
90°	1.2	4.3	7.5	10.6	13.7	18.1	23.8	29.6	35.3	41.1	40.5
92.5°	20.9	23.1	25.4	27.8	30.1	31.9	33.2	34.6	36.0	37.3	37.4
95°	61.0	63.6	66.2	68.8	71.4	73.0	73.5	74.0	74.5	75.0	75.0
97.5°	111.5	113.7	116.0	118.4	120.6	122.3	123.2	124.2	125.2	126.2	126.2
100°	149.0	151.1	153.2	155.2	157.3	158.8	159.6	160.3	161.1	161.9	161.9
102.5°	188.4	190.1	191.8	193.4	195.1	196.4	197.4	198.3	199.3	200.4	200.6
105°	252.2	253.0	253.8	254.6	255.3	256.0	256.5	257.0	257.5	258.0	258.6
107.5°	316.5	317.6	318.8	319.9	321.0	321.6	321.6	321.6	321.6	321.6	321.8
110°	357.8	359.3	360.9	362.4	364.1	364.9	364.9	364.9	364.9	364.9	364.9



TEST NUMBER: P331328-840

CATALOG NUMBER: SA2XXDIP-C485D1080U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	402.8	404.3	406.0	407.5	409.1	409.8	409.5	409.3	409.1	408.9	408.3
115°	469.2	470.8	472.3	473.9	475.4	475.9	475.4	474.9	474.4	473.9	473.6
117.5°	535.3	537.5	539.6	541.6	543.7	544.0	542.6	541.1	539.7	538.2	537.6
120°	579.5	581.6	583.7	585.7	587.8	587.8	585.7	583.7	581.6	579.5	579.5
122.5°	619.9	622.4	624.8	627.3	629.9	630.4	628.9	627.4	626.0	624.5	623.9
125°	682.7	685.1	687.4	689.7	692.1	692.9	692.1	691.4	690.5	689.7	688.9
127.5°	744.0	746.9	749.9	752.9	755.8	756.9	755.9	755.0	754.1	753.1	752.1
130°	782.4	785.8	789.2	792.5	796.0	797.4	796.9	796.4	795.9	795.4	794.8
132.5°	825.6	828.4	831.1	833.8	836.7	838.1	838.2	838.3	838.4	838.5	837.4
135°	883.3	886.2	889.1	891.9	894.7	896.5	897.0	897.5	898.1	898.6	898.3
137.5°	944.0	946.4	948.8	951.1	953.4	954.9	955.6	956.3	956.9	957.7	957.5
140°	980.7	983.0	985.3	987.7	990.1	991.9	993.2	994.5	995.8	997.0	997.0
142.5°	1018.2	1020.6	1022.9	1025.2	1027.5	1029.2	1030.1	1031.0	1031.9	1032.8	1033.0
145°	1072.2	1074.0	1075.8	1077.6	1079.4	1081.2	1082.7	1084.3	1085.8	1087.4	1087.6
147.5°	1120.2	1122.5	1124.6	1126.8	1129.0	1130.6	1131.7	1132.8	1133.8	1134.8	1135.4
150°	1153.1	1154.7	1156.2	1157.8	1159.3	1160.6	1161.7	1162.8	1163.8	1164.9	1165.6
152.5°	1182.1	1183.8	1185.3	1186.9	1188.4	1189.8	1191.1	1192.3	1193.7	1194.9	1195.9
155°	1225.9	1226.6	1227.4	1228.2	1229.0	1229.7	1230.5	1231.3	1232.1	1232.8	1234.2
157.5°	1263.1	1263.6	1264.1	1264.7	1265.3	1265.7	1266.2	1266.7	1267.1	1267.6	1269.4
160°	1285.7	1286.2	1286.7	1287.2	1287.8	1288.1	1288.4	1288.7	1288.9	1289.2	1290.7
162.5°	1306.3	1306.4	1306.5	1306.6	1306.8	1306.9	1307.2	1307.4	1307.7	1308.0	1309.7
165°	1333.7	1333.5	1333.2	1332.9	1332.7	1332.6	1332.6	1332.6	1332.6	1332.6	1334.4
167.5°	1356.8	1355.9	1355.1	1354.4	1353.6	1353.2	1353.1	1353.1	1353.0	1353.0	1354.8
170°	1369.0	1368.2	1367.4	1366.5	1365.8	1365.3	1365.0	1364.7	1364.5	1364.2	1366.0
172.5°	1377.4	1376.6	1375.8	1375.0	1374.2	1373.7	1373.5	1373.2	1372.9	1372.7	1374.5
175°	1387.8	1386.9	1386.1	1385.3	1384.6	1383.9	1383.4	1382.9	1382.4	1381.8	1383.7
177.5°	1391.9	1391.3	1390.7	1390.1	1389.5	1388.9	1388.5	1388.1	1387.7	1387.3	1388.5
180°	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1



TEST NUMBER: P331328-840

CATALOG NUMBER: SA2XXDIP-C485D1080U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	784.4	784.4	784.4	784.4	784.4	784.4	784.4	784.4
2.5°	781.0	782.3	783.7	784.3	784.0	783.7	783.5	783.2
5°	775.8	777.1	778.4	778.9	778.6	778.2	777.9	777.6
7.5°	767.0	768.3	769.7	770.1	769.8	769.4	769.0	768.7
10°	759.1	760.5	761.8	762.2	761.7	761.2	760.7	760.2
12.5°	749.9	750.8	751.7	752.0	751.6	751.3	750.9	750.5
15°	733.7	734.4	735.0	734.9	734.1	733.3	732.5	731.5
17.5°	714.4	715.2	716.0	715.9	715.1	714.4	713.6	712.8
20°	699.4	699.9	700.4	700.3	699.6	698.9	698.3	697.6
22.5°	683.5	683.6	683.7	683.6	683.2	682.8	682.4	682.0
25°	657.6	657.9	658.2	658.2	657.9	657.6	657.2	656.9
27.5°	632.1	631.6	631.1	630.5	629.7	628.8	628.0	627.2
30°	612.2	611.7	611.2	610.6	609.9	609.3	608.5	607.8
32.5°	592.7	591.8	590.9	590.1	589.4	588.8	588.0	587.3
35°	561.4	560.4	559.4	558.5	557.6	556.7	555.9	555.1
37.5°	530.0	528.8	527.6	526.4	525.6	524.8	524.0	523.3
40°	508.4	506.9	505.3	504.2	503.5	502.9	502.2	501.5
42.5°	487.0	485.3	483.6	482.4	481.4	480.5	479.6	478.6
45°	454.1	452.3	450.4	449.2	448.5	447.9	447.2	446.5
47.5°	420.0	418.0	416.1	414.7	413.6	412.7	411.7	410.7
50°	398.1	395.7	393.3	391.7	390.9	390.1	389.2	388.4
52.5°	375.4	373.3	371.4	369.9	368.8	367.7	366.6	365.5
55°	341.4	339.4	337.4	336.0	335.1	334.3	333.5	332.6
57.5°	306.2	304.2	302.3	300.9	300.2	299.6	299.0	298.3
60°	282.9	281.0	279.2	278.0	277.5	277.0	276.5	276.0
62.5°	260.8	259.1	257.4	256.3	255.6	255.0	254.4	253.7
65°	227.0	225.5	224.0	222.8	222.0	221.2	220.4	219.4
67.5°	193.6	192.4	191.3	190.4	189.7	188.9	188.3	187.6
70°	171.9	170.7	169.6	168.6	167.9	167.2	166.6	165.9
72.5°	151.4	150.2	149.1	148.1	147.6	147.0	146.5	146.0
75°	119.4	118.5	117.4	117.0	117.4	117.8	118.1	118.5
77.5°	90.9	90.4	89.9	89.4	88.9	88.5	88.0	87.5
80°	72.1	71.6	71.2	70.7	70.4	70.1	69.7	69.4
82.5°	53.8	53.1	52.5	52.1	52.1	52.0	51.9	51.9
85°	28.4	27.9	27.4	27.1	26.9	26.8	26.6	26.4
87.5°	15.7	15.1	14.6	14.3	14.2	14.1	14.1	14.0
90°	40.0	39.5	39.0	38.9	39.1	39.4	39.6	39.9
92.5°	37.5	37.6	37.8	37.8	37.9	37.9	38.0	38.0
95°	75.0	75.0	75.0	74.8	74.3	73.8	73.2	72.7
97.5°	126.2	126.2	126.2	126.2	126.1	126.1	126.0	126.0
100°	161.9	161.9	161.9	161.8	161.5	161.3	161.0	160.7
102.5°	200.8	201.0	201.2	201.2	200.9	200.7	200.4	200.2
105°	259.1	259.6	260.1	260.4	260.4	260.4	260.4	260.4
107.5°	322.0	322.2	322.4	321.9	320.8	319.6	318.4	317.2
110°	364.9	364.9	364.9	364.5	363.7	362.8	362.0	361.3





TEST NUMBER: P331328-840

CATALOG NUMBER: SA2XXDIP-C485D1080U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	407.7	407.1	406.5	405.9	405.3	404.7	404.1	403.5
115°	473.4	473.1	472.8	472.3	471.6	470.8	470.0	469.2
117.5°	536.9	536.3	535.7	535.0	534.2	533.4	532.6	531.9
120°	579.5	579.5	579.5	579.1	578.3	577.5	576.7	575.9
122.5°	623.3	622.7	622.0	621.5	620.9	620.3	619.8	619.1
125°	688.2	687.4	686.6	686.1	685.8	685.6	685.3	685.1
127.5°	751.2	750.2	749.3	748.4	747.6	746.8	746.0	745.1
130°	794.3	793.8	793.2	792.4	791.4	790.3	789.3	788.3
132.5°	836.2	835.1	833.9	832.9	832.1	831.2	830.4	829.6
135°	898.1	897.8	897.5	897.0	896.2	895.4	894.6	893.8
137.5°	957.3	957.0	956.8	956.2	955.1	954.1	953.1	952.0
140°	997.0	997.0	997.0	996.5	995.5	994.5	993.4	992.4
142.5°	1033.2	1033.4	1033.6	1033.2	1032.1	1031.1	1030.1	1029.0
145°	1087.9	1088.2	1088.4	1088.0	1087.0	1086.0	1084.9	1083.9
147.5°	1136.0	1136.5	1137.1	1136.9	1135.9	1134.9	1133.9	1133.0
150°	1166.4	1167.2	1168.0	1168.0	1167.2	1166.4	1165.6	1164.9
152.5°	1196.9	1197.8	1198.8	1198.8	1197.8	1196.9	1195.9	1194.9
155°	1235.5	1236.8	1238.1	1238.3	1237.6	1236.8	1236.0	1235.2
157.5°	1271.1	1272.9	1274.7	1275.0	1273.6	1272.4	1271.2	1269.9
160°	1292.3	1293.8	1295.5	1295.7	1294.6	1293.6	1292.5	1291.5
162.5°	1311.5	1313.2	1315.0	1315.2	1314.0	1312.8	1311.5	1310.3
165°	1336.3	1338.1	1339.9	1340.1	1338.9	1337.6	1336.3	1334.9
167.5°	1356.7	1358.5	1360.3	1360.5	1359.2	1357.8	1356.5	1355.1
170°	1367.9	1369.7	1371.5	1371.7	1370.1	1368.6	1367.0	1365.4
172.5°	1376.3	1378.2	1380.0	1380.1	1378.6	1377.0	1375.4	1373.8
175°	1385.5	1387.4	1389.2	1389.3	1387.8	1386.1	1384.6	1383.0
177.5°	1389.8	1391.0	1392.2	1392.2	1391.0	1389.8	1388.5	1387.3
180°	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1

(END OF REPORT)