

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331329-840

Luminaire Tested: **SA2XXDIP-C485D1080U840-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331329-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C485D1080U840-4F0-1E-UDD-F4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1080 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6246.0 lumens
Efficiency: N/A
Efficacy: 126.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 49.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331329-840

CATALOG NUMBER: SA2XXDIP-C485D1080U840-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331329-840

CATALOG NUMBER: SA2XXDIP-C485D1080U840-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	73	73	73	56	56	56	40	40	40	32
1	94	90	86	82	84	81	78	75	64	62	60	49	48	46	35	34	33	27
2	85	78	72	67	77	70	65	61	56	53	50	43	41	39	31	29	28	23
3	78	69	62	56	70	62	56	51	50	45	42	38	35	33	27	25	24	19
4	71	61	53	47	64	55	48	43	44	39	35	34	31	28	24	22	21	16
5	65	54	46	40	58	49	42	37	39	34	30	30	27	24	22	20	18	14
6	60	48	40	35	54	44	37	32	35	30	26	27	24	21	20	18	16	13
7	55	43	36	30	50	39	33	28	32	27	23	25	21	19	18	16	14	11
8	51	39	32	27	46	36	29	25	29	24	20	23	19	16	17	14	12	10
9	48	36	29	24	43	33	26	22	26	22	18	21	17	15	15	13	11	9
10	44	33	26	21	40	30	24	19	24	20	16	19	16	13	14	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12665	12665	12665
5°	12713	12530	12603
10°	12637	12403	12463
15°	12481	12242	12227
20°	12259	12000	11986
25°	12039	11703	11703
30°	11757	11432	11332
35°	11491	11105	10941
40°	11160	10779	10570
45°	10832	10453	10195
50°	10477	10115	9756
55°	10106	9723	9362
60°	9691	9255	8913
65°	9249	8787	8382
70°	8686	8224	7832
75°	7904	7573	7392
80°	7011	6797	6453
85°	5724	5446	4891



TEST NUMBER: P331329-840

CATALOG NUMBER: SA2XXDIP-C485D1080U840-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.8	1.2
10°-20°	207.5	3.3
20°-30°	305.0	4.9
30°-40°	354.3	5.7
40°-50°	354.0	5.7
50°-60°	308.7	4.9
60°-70°	228.2	3.7
70°-80°	129.3	2.1
80°-90°	40.2	0.6
90°-100°	243.9	3.9
100°-110°	827.7	13.3
110°-120°	879.3	14.1
120°-130°	723.9	11.6
130°-140°	581.3	9.3
140°-150°	439.3	7.0
150°-160°	308.7	4.9
160°-170°	181.7	2.9
170°-180°	59.1	0.9
0°-30°	586.3	9.4
0°-40°	940.7	15.1
0°-60°	1603.3	25.7
0°-90°	2001.0	32.0
90°-120°	1951.0	31.2
90°-150°	3695.4	59.2
90°-180°	4245.0	68.0
0°-180°	6246.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	784	784	784	784	784	
5°	784	781	773	779	778	74
15°	747	742	732	735	732	210
25°	676	669	657	658	657	311
35°	583	575	563	559	555	364
45°	474	469	458	450	446	366
55°	359	354	345	337	333	321
65°	242	237	230	223	219	239
75°	127	125	121	117	118	135
85°	31	30	29	27	26	35
90°	1	16	40	38	39	4
95°	41	101	460	174	134	44
105°	143	216	869	1554	1322	152
115°	252	319	727	1501	1740	250
125°	352	416	699	1216	1411	312
135°	413	493	691	1022	1170	319
145°	472	542	687	854	934	296
155°	536	579	668	755	785	247
165°	584	602	639	678	689	165
175°	609	609	615	622	621	58
180°	610	610	610	610	610	



TEST NUMBER: P331329-840

CATALOG NUMBER: SA2XXDIP-C485D1080U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	784.4	784.4	784.4	784.4	784.4	784.4	784.4	784.4	784.4	784.4	784.4
2.5°	788.0	787.3	786.7	786.0	785.3	784.3	782.7	781.3	779.8	778.3	779.7
5°	784.4	783.7	783.0	782.3	781.7	780.4	778.6	776.8	774.9	773.1	774.4
7.5°	777.4	776.4	775.4	774.3	773.3	771.8	769.9	768.1	766.2	764.3	765.7
10°	770.8	769.6	768.4	767.3	766.1	764.5	762.4	760.5	758.5	756.5	757.8
12.5°	761.7	760.7	759.6	758.6	757.6	756.1	754.1	752.0	750.0	748.0	748.9
15°	746.7	745.7	744.7	743.7	742.7	741.0	738.8	736.7	734.5	732.4	733.0
17.5°	727.3	726.4	725.4	724.4	723.4	721.8	719.5	717.3	715.1	712.9	713.7
20°	713.5	712.5	711.4	710.4	709.4	707.8	705.4	703.1	700.7	698.4	698.9
22.5°	699.6	698.2	696.8	695.4	694.0	692.2	689.9	687.7	685.5	683.3	683.4
25°	675.8	674.4	673.1	671.8	670.4	668.3	665.5	662.6	659.7	656.9	657.2
27.5°	648.6	647.4	646.2	645.0	643.8	642.1	639.9	637.5	635.3	633.1	632.6
30°	630.6	629.1	627.8	626.5	625.1	623.2	620.7	618.2	615.7	613.2	612.7
32.5°	611.2	610.2	609.0	607.9	606.9	605.0	602.4	599.8	597.1	594.5	593.6
35°	583.0	581.3	579.7	577.9	576.3	574.1	571.5	568.8	566.0	563.4	562.4
37.5°	551.2	549.7	548.3	546.7	545.2	543.2	540.5	537.9	535.1	532.5	531.2
40°	529.5	528.1	526.7	525.4	524.1	522.1	519.4	516.7	514.0	511.4	509.9
42.5°	508.4	507.0	505.6	504.3	503.0	501.0	498.3	495.6	492.9	490.2	488.6
45°	474.4	473.2	472.0	470.9	469.7	467.9	465.3	462.8	460.3	457.8	456.0
47.5°	440.6	439.5	438.4	437.3	436.2	434.3	431.7	429.1	426.5	423.8	421.9
50°	417.1	416.3	415.4	414.5	413.7	412.1	409.8	407.5	405.1	402.7	400.4
52.5°	394.2	393.0	391.9	390.8	389.7	388.1	385.9	383.6	381.4	379.2	377.3
55°	359.0	358.0	357.0	356.0	355.0	353.5	351.4	349.4	347.4	345.4	343.5
57.5°	323.7	322.9	322.0	321.3	320.5	319.0	316.8	314.6	312.4	310.1	308.1
60°	300.1	299.5	298.8	298.1	297.5	296.0	293.7	291.2	288.9	286.6	284.8
62.5°	277.2	276.2	275.1	274.0	273.0	271.6	269.7	267.9	266.1	264.3	262.6
65°	242.1	241.1	240.0	239.0	238.1	236.7	235.1	233.4	231.7	230.0	228.5
67.5°	206.3	205.5	204.7	203.9	203.1	202.0	200.5	198.9	197.4	195.9	194.8
70°	184.0	183.4	182.7	182.0	181.4	180.3	178.7	177.2	175.7	174.2	173.1
72.5°	161.1	160.5	159.8	159.1	158.4	157.6	156.6	155.6	154.7	153.7	152.5
75°	126.7	126.3	126.0	125.7	125.3	124.8	123.9	123.1	122.3	121.4	120.4
77.5°	95.9	95.3	94.8	94.2	93.6	93.2	92.9	92.5	92.2	91.9	91.4
80°	75.4	75.2	75.1	74.9	74.7	74.5	74.1	73.8	73.5	73.1	72.6
82.5°	56.1	56.0	56.0	56.0	55.9	55.8	55.6	55.4	55.2	55.0	54.4
85°	30.9	30.8	30.6	30.4	30.3	30.1	29.9	29.8	29.6	29.4	28.9
87.5°	11.1	11.5	12.2	12.4	12.6	13.0	13.9	15.3	16.5	16.5	15.8
90°	1.2	4.6	9.4	11.7	14.0	17.6	23.4	31.7	38.7	39.9	38.7
92.5°	14.3	20.6	29.1	34.2	42.2	53.2	79.8	117.0	150.4	152.5	128.9
95°	41.1	45.7	57.5	68.1	86.8	114.9	169.0	270.9	407.1	459.9	402.4
97.5°	66.9	73.2	85.6	101.6	123.2	155.1	222.9	365.1	591.3	785.1	823.5
100°	90.3	93.8	104.4	123.2	146.6	179.5	241.7	384.8	638.1	926.8	1095.7
102.5°	111.9	114.5	125.0	143.8	168.2	201.1	258.5	385.8	620.4	931.5	1197.1
105°	143.1	147.8	156.0	173.6	199.4	232.3	287.4	391.8	585.4	869.3	1181.3
107.5°	176.9	180.7	188.6	204.8	230.5	263.5	317.0	408.0	568.0	802.6	1078.3
110°	199.4	204.1	211.2	226.4	251.1	285.1	336.7	421.1	564.3	770.7	1013.6



TEST NUMBER: P331329-840

CATALOG NUMBER: SA2XXDIP-C485D1080U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	220.0	224.8	232.8	247.0	270.7	305.7	355.5	435.3	565.2	750.1	968.6
115°	252.3	258.1	265.1	279.2	302.7	334.4	384.8	456.4	570.2	727.3	912.7
117.5°	285.6	290.2	297.3	309.7	332.2	365.1	411.7	478.9	578.6	716.3	877.5
120°	306.2	310.8	317.9	328.5	351.9	384.8	430.5	493.9	584.2	709.7	858.7
122.5°	325.9	329.6	336.7	348.2	371.6	405.5	448.4	507.1	590.8	706.0	842.7
125°	351.9	355.5	362.5	376.6	400.0	432.9	475.1	528.0	600.7	699.2	820.0
127.5°	372.5	377.3	387.2	402.6	425.2	458.9	500.0	547.3	610.8	695.2	798.9
130°	384.8	389.5	401.2	417.7	441.1	473.9	515.0	559.6	618.2	693.3	784.9
132.5°	396.1	401.7	414.3	431.7	456.2	489.0	528.2	571.8	625.7	692.4	773.6
135°	412.9	417.7	431.7	449.3	476.3	509.2	546.6	587.7	634.7	690.9	757.8
137.5°	428.9	434.5	448.6	467.4	494.1	524.6	561.7	600.0	642.7	690.7	746.8
140°	441.1	445.8	459.9	478.7	504.4	534.9	570.2	606.5	646.4	689.8	740.2
142.5°	453.3	457.1	470.2	489.0	513.8	542.5	576.7	612.2	649.2	689.8	733.7
145°	471.6	476.3	488.1	505.6	529.1	554.9	586.5	619.5	652.3	687.4	725.0
147.5°	491.3	494.8	506.0	522.3	541.8	564.7	594.5	623.4	653.2	683.3	716.1
150°	504.4	508.0	517.4	532.6	550.2	571.3	598.3	625.3	652.3	680.4	708.5
152.5°	517.6	519.3	528.6	542.0	558.7	577.8	602.1	626.2	650.4	675.7	702.0
155°	536.1	537.2	544.3	557.2	570.2	587.7	607.6	627.6	647.5	667.5	689.8
157.5°	551.6	552.8	558.5	569.7	580.0	594.8	611.7	627.6	642.2	659.0	678.3
160°	561.9	563.1	567.7	577.1	586.5	599.5	613.6	627.6	639.3	653.5	669.8
162.5°	572.3	571.6	576.2	583.7	592.2	602.3	614.5	626.7	636.5	648.7	662.4
165°	584.2	583.1	585.4	592.4	598.3	605.3	615.9	624.1	631.2	639.3	649.9
167.5°	594.1	592.7	594.8	599.3	603.5	607.9	615.6	622.5	625.7	631.2	637.7
170°	600.7	598.3	599.5	603.0	605.3	608.8	614.7	620.6	622.9	626.4	631.2
172.5°	604.4	603.0	602.3	605.8	607.2	609.8	613.8	617.7	619.1	620.9	624.6
175°	608.8	607.6	606.5	608.8	608.8	610.1	612.4	614.7	613.6	614.7	615.9
177.5°	611.0	609.0	608.1	610.1	610.1	610.1	611.0	612.9	611.0	610.1	611.0
180°	610.1	610.1	610.1	610.1	610.1	610.1	610.1	610.1	610.1	610.1	610.1



TEST NUMBER: P331329-840

CATALOG NUMBER: SA2XXDIP-C485D1080U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	784.4	784.4	784.4	784.4	784.4	784.4	784.4	784.4
2.5°	781.0	782.3	783.7	784.3	784.0	783.7	783.5	783.2
5°	775.8	777.1	778.4	778.9	778.6	778.2	777.9	777.6
7.5°	767.0	768.3	769.7	770.1	769.8	769.4	769.0	768.7
10°	759.1	760.5	761.8	762.2	761.7	761.2	760.7	760.2
12.5°	749.9	750.8	751.7	752.0	751.6	751.3	750.9	750.5
15°	733.7	734.4	735.0	734.9	734.1	733.3	732.5	731.5
17.5°	714.4	715.2	716.0	715.9	715.1	714.4	713.6	712.8
20°	699.4	699.9	700.4	700.3	699.6	698.9	698.3	697.6
22.5°	683.5	683.6	683.7	683.6	683.2	682.8	682.4	682.0
25°	657.6	657.9	658.2	658.2	657.9	657.6	657.2	656.9
27.5°	632.1	631.6	631.1	630.5	629.7	628.8	628.0	627.2
30°	612.2	611.7	611.2	610.6	609.9	609.3	608.5	607.8
32.5°	592.7	591.8	590.9	590.1	589.4	588.8	588.0	587.3
35°	561.4	560.4	559.4	558.5	557.6	556.7	555.9	555.1
37.5°	530.0	528.8	527.6	526.4	525.6	524.8	524.0	523.3
40°	508.4	506.9	505.3	504.2	503.5	502.9	502.2	501.5
42.5°	487.0	485.3	483.6	482.4	481.4	480.5	479.6	478.6
45°	454.1	452.3	450.4	449.2	448.5	447.9	447.2	446.5
47.5°	420.0	418.0	416.1	414.7	413.6	412.7	411.7	410.7
50°	398.1	395.7	393.3	391.7	390.9	390.1	389.2	388.4
52.5°	375.4	373.3	371.4	369.9	368.8	367.7	366.6	365.5
55°	341.4	339.4	337.4	336.0	335.1	334.3	333.5	332.6
57.5°	306.2	304.2	302.3	300.9	300.2	299.6	299.0	298.3
60°	282.9	281.0	279.2	278.0	277.5	277.0	276.5	276.0
62.5°	260.8	259.1	257.4	256.3	255.6	255.0	254.4	253.7
65°	227.0	225.5	224.0	222.8	222.0	221.2	220.4	219.4
67.5°	193.6	192.4	191.3	190.4	189.7	188.9	188.3	187.6
70°	171.9	170.7	169.6	168.6	167.9	167.2	166.6	165.9
72.5°	151.4	150.2	149.1	148.1	147.6	147.0	146.5	146.0
75°	119.4	118.5	117.4	117.0	117.4	117.8	118.1	118.5
77.5°	90.9	90.4	89.9	89.4	88.9	88.5	88.0	87.5
80°	72.1	71.6	71.2	70.7	70.4	70.1	69.7	69.4
82.5°	53.8	53.1	52.5	52.1	52.1	52.0	51.9	51.9
85°	28.4	27.9	27.4	27.1	26.9	26.8	26.6	26.4
87.5°	15.1	14.2	14.3	14.3	14.1	14.0	13.9	13.7
90°	37.6	35.2	37.6	38.7	38.7	38.7	38.7	38.7
92.5°	102.3	87.8	77.9	70.6	69.7	65.9	66.9	65.0
95°	307.4	235.8	186.5	160.7	145.4	136.1	132.6	133.7
97.5°	717.2	586.8	459.9	375.2	319.1	290.2	273.1	263.3
100°	1071.1	925.6	764.9	622.9	525.5	475.1	441.1	420.0
102.5°	1302.9	1270.0	1152.5	1002.1	896.3	810.2	767.7	739.1
105°	1425.3	1557.9	1573.2	1534.5	1461.7	1389.0	1338.6	1322.1
107.5°	1337.2	1536.8	1658.8	1715.6	1724.7	1720.7	1710.6	1688.8
110°	1261.1	1471.1	1621.2	1717.5	1767.9	1790.2	1800.8	1799.6



TEST NUMBER: P331329-840

CATALOG NUMBER: SA2XXDIP-C485D1080U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	1191.6	1393.2	1553.7	1664.0	1734.1	1771.4	1791.4	1797.7
115°	1106.3	1287.0	1440.6	1561.5	1644.8	1698.7	1729.2	1739.8
117.5°	1042.0	1200.6	1340.0	1453.3	1538.2	1595.2	1627.4	1636.3
120°	1010.1	1155.5	1279.9	1386.6	1468.7	1523.9	1557.9	1569.6
122.5°	984.7	1118.0	1235.8	1332.2	1405.8	1460.1	1490.4	1500.2
125°	947.9	1068.7	1171.9	1259.9	1328.0	1372.6	1401.9	1411.3
127.5°	911.5	1020.9	1118.2	1199.4	1258.8	1300.5	1325.9	1333.4
130°	888.1	989.0	1081.7	1159.0	1216.6	1256.5	1279.9	1289.3
132.5°	865.6	959.0	1044.1	1116.8	1173.4	1213.3	1234.9	1243.2
135°	834.0	911.5	989.0	1054.6	1105.1	1143.8	1164.9	1169.6
137.5°	809.0	873.7	935.2	992.5	1038.4	1071.8	1090.4	1097.3
140°	793.0	849.4	903.3	954.9	992.5	1023.0	1040.6	1047.6
142.5°	779.9	827.8	874.2	917.4	953.0	980.8	996.4	997.8
145°	761.3	800.1	836.5	870.5	898.6	918.6	930.3	933.8
147.5°	747.1	777.6	806.0	830.8	854.0	870.0	878.0	880.1
150°	736.7	762.5	787.2	808.3	825.9	840.0	847.0	848.2
152.5°	726.4	750.3	771.2	789.5	803.3	815.6	820.7	820.9
155°	712.1	730.8	748.4	761.3	774.3	782.4	787.2	784.9
157.5°	695.4	711.1	725.9	736.0	745.2	751.9	754.1	754.1
160°	685.1	698.0	710.9	719.1	727.3	733.2	734.4	734.4
162.5°	674.8	685.8	696.8	703.2	711.3	715.4	716.5	715.6
165°	659.3	667.5	675.7	680.4	685.1	689.8	689.8	688.6
167.5°	644.5	650.9	656.5	660.8	662.8	665.4	665.2	663.8
170°	637.0	640.6	645.2	647.5	648.7	652.3	651.1	648.7
172.5°	628.5	631.2	634.9	636.3	637.5	639.1	637.9	636.5
175°	619.5	620.6	621.8	622.9	622.9	624.1	622.9	620.6
177.5°	612.9	612.9	613.8	613.8	613.8	613.8	612.9	611.0
180°	610.1	610.1	610.1	610.1	610.1	610.1	610.1	610.1

(END OF REPORT)