

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331660-930

Luminaire Tested: **SA2XXRDIP-C485D725U930-4F0-1E-UDD-F**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331660-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXRDIP-C485D725U930-4F0-1E-UDD-F  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 725 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3747.8 lumens  
Efficiency: N/A  
Efficacy: 97.6 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 38.4  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331660-930  
CATALOG NUMBER: SA2XXRDIP-C485D725U930-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P331660-930

CATALOG NUMBER: SA2XXRDIP-C485D725U930-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	37				37
1	95	91	87	84	86	83	80	77	67	65	63	53	51	50	40	39	38				32	
2	87	80	74	69	79	73	68	64	59	56	53	47	44	42	35	34	32				27	
3	80	71	64	58	72	64	58	54	53	48	45	42	39	36	32	30	28				23	
4	73	63	55	49	66	57	51	46	47	42	38	37	34	31	28	26	24				20	
5	67	56	48	42	61	51	44	39	42	37	33	34	30	27	26	23	22				18	
6	62	50	42	37	56	46	39	34	38	33	29	30	27	24	23	21	19				16	
7	57	45	38	32	52	42	35	30	34	29	26	28	24	21	21	19	17				14	
8	53	41	34	29	48	38	31	27	31	26	23	25	22	19	20	17	15				13	
9	49	38	30	25	45	35	28	24	29	24	20	23	20	17	18	16	14				12	
10	46	34	27	23	42	32	26	21	27	22	18	22	18	16	17	15	13				11	

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	10863	10863	10863
5°	10904	10728	10786
10°	10822	10552	10462
15°	10696	10238	9944
20°	10524	9792	9301
25°	10349	9285	8678
30°	10103	8764	7879
35°	9865	8198	7177
40°	9624	7611	6365
45°	9344	6951	5631
50°	9053	6285	4908
55°	8757	5571	4217
60°	8415	4818	3500
65°	8027	4046	3186
70°	7558	3333	2932
75°	6987	3038	2739
80°	6174	2715	2492
85°	4854	2149	2149



TEST NUMBER: P331660-930

CATALOG NUMBER: SA2XXRDIP-C485D725U930-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	63.0	1.7
10°-20°	172.9	4.6
20°-30°	242.8	6.5
30°-40°	264.8	7.1
40°-50°	243.5	6.5
50°-60°	191.2	5.1
60°-70°	124.7	3.3
70°-80°	64.3	1.7
80°-90°	18.7	0.5
90°-100°	26.9	0.7
100°-110°	98.6	2.6
110°-120°	263.5	7.0
120°-130°	435.0	11.6
130°-140°	462.7	12.3
140°-150°	430.0	11.5
150°-160°	345.7	9.2
160°-170°	222.8	5.9
170°-180°	76.7	2.0
0°-30°	478.7	12.8
0°-40°	743.5	19.8
0°-60°	1178.2	31.4
0°-90°	1385.8	37.0
90°-120°	389.0	10.4
90°-150°	1716.8	45.8
90°-180°	2362.0	63.0
0°-180°	3747.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	673	673	673	673	673	
5°	673	670	662	667	666	64
15°	640	632	612	601	595	180
25°	581	560	521	497	487	267
35°	500	468	416	379	364	313
45°	409	367	304	263	247	316
55°	311	263	198	163	150	278
65°	210	160	106	86	83	208
75°	112	71	49	45	44	119
85°	26	14	12	12	12	31
90°	1	7	12	14	16	3
95°	38	20	23	26	25	46
105°	177	185	36	42	44	189
115°	335	346	360	102	48	330
125°	474	482	493	497	499	423
135°	587	596	601	607	606	453
145°	681	681	690	694	691	426
155°	749	745	751	754	750	345
165°	790	786	788	792	788	223
175°	808	804	805	808	803	77
180°	806	806	806	806	806	



TEST NUMBER: P331660-930

CATALOG NUMBER: SA2XXRDIP-C485D725U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	672.8	672.8	672.8	672.8	672.8	672.8	672.8	672.8	672.8	672.8	672.8
2.5°	675.2	674.7	674.2	673.6	673.1	672.2	671.1	669.8	668.6	667.5	668.5
5°	672.8	672.1	671.5	670.8	670.1	668.9	667.2	665.4	663.7	661.9	663.1
7.5°	665.9	665.0	664.2	663.3	662.5	661.0	659.0	657.0	654.9	652.9	653.2
10°	660.1	659.1	658.1	657.2	656.2	654.4	651.8	649.0	646.3	643.6	643.2
12.5°	652.7	651.6	650.4	649.2	648.1	645.8	642.3	638.9	635.4	631.9	631.2
15°	639.9	638.5	637.0	635.4	634.0	631.0	626.3	621.7	617.2	612.5	610.0
17.5°	624.3	622.0	619.7	617.4	615.1	611.1	605.2	599.2	593.4	587.4	584.4
20°	612.5	609.8	607.2	604.5	601.7	597.0	590.2	583.4	576.7	569.9	566.6
22.5°	599.9	596.9	593.8	590.8	587.7	582.4	574.8	567.1	559.5	551.9	547.6
25°	580.9	576.6	572.3	567.9	563.5	556.9	548.0	539.1	530.1	521.2	515.7
27.5°	558.0	553.3	548.5	543.9	539.2	531.7	521.7	511.6	501.6	491.5	485.0
30°	541.9	536.8	531.7	526.5	521.4	513.4	502.6	491.7	480.9	470.1	463.2
32.5°	526.4	520.3	514.3	508.3	502.3	493.7	482.7	471.7	460.6	449.6	441.7
35°	500.5	493.6	486.7	479.8	472.9	463.5	451.6	439.7	427.8	415.9	407.3
37.5°	474.7	467.1	459.5	451.9	444.4	434.2	421.6	408.9	396.2	383.5	374.1
40°	456.6	448.6	440.4	432.4	424.2	413.6	400.5	387.3	374.2	361.1	351.5
42.5°	438.1	429.6	421.0	412.5	404.0	392.9	379.4	365.7	352.2	338.7	328.7
45°	409.2	400.1	391.0	382.0	372.9	361.3	347.1	332.9	318.6	304.4	294.8
47.5°	380.9	371.3	361.7	352.1	342.5	330.4	315.7	301.0	286.3	271.7	262.1
50°	360.4	350.8	341.3	331.7	322.0	309.8	294.9	280.1	265.1	250.2	240.9
52.5°	340.5	330.4	320.4	310.4	300.4	288.0	273.5	258.9	244.3	229.8	220.8
55°	311.1	300.6	290.0	279.5	269.0	256.3	241.7	227.1	212.5	197.9	189.8
57.5°	281.0	270.3	259.4	248.6	237.7	225.3	211.3	197.2	183.2	169.2	161.7
60°	260.6	249.8	239.0	228.1	217.3	205.0	191.0	177.1	163.1	149.2	142.3
62.5°	240.6	229.8	219.0	208.1	197.3	185.3	172.0	158.7	145.4	132.2	125.6
65°	210.1	199.1	188.2	177.2	166.2	154.7	142.5	130.3	118.1	105.9	101.3
67.5°	180.6	169.7	158.8	148.0	137.1	126.1	115.2	104.3	93.3	82.3	80.2
70°	160.1	149.6	139.0	128.5	117.9	107.9	98.7	89.3	80.0	70.6	69.3
72.5°	140.6	130.5	120.4	110.3	100.2	91.4	83.9	76.4	68.9	61.4	60.3
75°	112.0	102.6	93.1	83.6	74.1	67.1	62.5	57.9	53.3	48.7	47.8
77.5°	83.9	75.6	67.3	58.9	50.7	45.4	43.2	41.0	38.7	36.5	36.0
80°	66.4	59.4	52.6	45.7	38.7	34.7	33.3	32.0	30.6	29.2	28.7
82.5°	50.3	44.9	39.5	34.2	28.8	25.6	24.7	23.7	22.8	21.9	21.6
85°	26.2	23.3	20.5	17.7	14.8	13.2	12.8	12.4	12.0	11.6	11.6
87.5°	7.9	7.3	6.8	6.2	5.6	5.4	5.6	5.8	6.0	6.2	6.3
90°	0.6	2.0	3.4	4.9	6.3	7.5	8.6	9.6	10.6	11.7	12.3
92.5°	11.7	11.7	11.5	11.4	11.3	11.5	12.0	12.5	13.0	13.5	13.9
95°	37.9	33.7	29.4	25.1	20.8	19.1	20.1	21.0	21.9	22.7	23.4
97.5°	75.3	63.2	51.1	39.1	27.0	22.0	24.1	26.3	28.4	30.4	31.0
100°	103.2	85.4	67.8	50.0	32.2	24.5	26.7	28.9	31.1	33.3	34.2
102.5°	134.0	130.3	126.5	122.8	119.0	107.9	89.4	71.0	52.6	34.2	35.5
105°	177.3	181.2	185.1	189.0	192.8	177.1	141.7	106.3	70.9	35.5	37.0
107.5°	226.7	229.8	232.9	236.0	239.2	219.6	177.1	134.7	92.2	49.8	48.3
110°	258.4	261.1	263.8	266.5	269.2	251.8	214.4	177.0	139.5	102.1	89.1



TEST NUMBER: P331660-930

CATALOG NUMBER: SA2XXRDIP-C485D725U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	288.2	290.7	293.0	295.5	297.8	294.4	285.2	275.9	266.7	257.4	210.2
115°	335.3	337.5	339.7	341.9	344.1	346.9	350.1	353.4	356.6	359.9	299.9
117.5°	377.5	379.9	382.4	384.8	387.3	389.6	391.9	394.1	396.3	398.6	384.1
120°	408.2	410.2	412.1	414.1	416.0	418.2	420.5	422.8	425.2	427.5	429.0
122.5°	434.4	436.4	438.5	440.5	442.5	444.8	447.4	450.0	452.5	455.0	455.9
125°	474.2	475.8	477.5	479.2	480.9	483.0	485.4	487.9	490.3	492.8	493.7
127.5°	510.2	512.1	514.0	515.8	517.6	519.5	521.4	523.2	525.1	526.8	528.2
130°	533.0	535.2	537.2	539.2	541.4	543.1	544.5	545.9	547.4	548.8	550.2
132.5°	556.4	558.2	559.9	561.7	563.5	565.0	566.5	567.9	569.3	570.7	571.9
135°	586.7	588.8	590.8	593.0	595.0	596.6	597.8	598.9	600.1	601.3	602.6
137.5°	617.4	618.8	620.3	621.7	623.2	624.6	625.9	627.2	628.5	629.9	631.1
140°	637.5	638.5	639.5	640.6	641.6	642.9	644.2	645.7	647.1	648.6	649.7
142.5°	654.3	655.2	656.2	657.0	657.9	659.3	660.9	662.5	664.1	665.8	666.8
145°	680.6	680.4	680.4	680.2	680.1	681.1	683.3	685.5	687.7	689.9	690.9
147.5°	703.6	703.1	702.6	702.1	701.6	702.5	704.7	706.8	709.0	711.2	711.8
150°	718.5	717.6	716.7	715.8	714.9	715.5	717.5	719.6	721.7	723.7	724.6
152.5°	731.1	730.1	729.1	728.1	727.1	727.6	729.5	731.5	733.4	735.4	736.2
155°	749.4	748.3	747.1	745.9	744.8	744.9	746.5	748.0	749.6	751.1	752.0
157.5°	763.8	762.8	761.8	760.8	759.9	759.9	761.0	762.1	763.1	764.3	765.2
160°	772.2	771.4	770.6	769.8	769.1	769.1	769.8	770.6	771.4	772.2	773.0
162.5°	779.7	778.9	778.1	777.3	776.5	776.5	777.1	777.8	778.5	779.2	780.1
165°	789.7	788.9	788.1	787.3	786.5	786.4	786.8	787.2	787.5	787.9	788.8
167.5°	797.1	796.4	795.6	794.8	794.0	793.8	794.2	794.5	794.9	795.2	796.1
170°	801.4	800.5	799.8	799.0	798.3	797.9	798.3	798.5	798.7	799.0	799.9
172.5°	804.1	803.3	802.6	801.8	801.0	800.8	801.0	801.3	801.5	801.8	802.7
175°	807.7	806.8	805.9	805.0	804.1	803.8	804.0	804.3	804.5	804.9	805.8
177.5°	808.4	807.6	806.9	806.2	805.4	805.1	805.2	805.4	805.4	805.5	806.2
180°	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0



TEST NUMBER: P331660-930

CATALOG NUMBER: SA2XXRDIP-C485D725U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	672.8	672.8	672.8	672.8	672.8	672.8	672.8	672.8
2.5°	669.6	670.7	671.8	672.2	672.1	671.8	671.6	671.4
5°	664.3	665.5	666.8	667.2	666.8	666.3	665.9	665.5
7.5°	653.5	653.9	654.3	654.1	653.4	652.6	652.0	651.3
10°	642.8	642.4	642.0	641.4	640.6	639.8	639.0	638.1
12.5°	630.5	629.7	629.0	627.9	626.6	625.3	623.9	622.6
15°	607.4	604.9	602.3	600.3	598.9	597.6	596.2	594.9
17.5°	581.3	578.3	575.2	572.5	570.2	567.9	565.6	563.2
20°	563.1	559.8	556.4	553.2	550.2	547.2	544.3	541.3
22.5°	543.2	538.8	534.5	531.2	529.0	526.8	524.6	522.3
25°	510.1	504.6	499.0	495.2	493.2	491.1	489.2	487.1
27.5°	478.6	472.1	465.6	460.8	457.5	454.4	451.1	447.9
30°	456.2	449.4	442.5	437.2	433.5	429.9	426.2	422.6
32.5°	433.8	426.0	418.1	412.5	409.0	405.6	402.1	398.7
35°	398.8	390.3	381.8	376.0	373.1	370.1	367.1	364.1
37.5°	364.7	355.3	345.9	339.5	336.1	332.7	329.3	325.9
40°	341.9	332.2	322.6	316.1	312.6	309.1	305.5	302.0
42.5°	318.8	308.8	299.0	292.3	288.9	285.4	282.0	278.6
45°	285.2	275.7	266.0	259.6	256.3	253.1	249.8	246.6
47.5°	252.6	243.0	233.5	227.2	224.3	221.4	218.3	215.4
50°	231.5	222.3	212.9	206.8	204.0	201.1	198.3	195.4
52.5°	211.7	202.8	193.7	187.9	185.3	182.7	180.0	177.4
55°	181.6	173.5	165.4	160.0	157.5	154.9	152.4	149.8
57.5°	154.3	146.8	139.4	134.6	132.4	130.3	128.1	125.9
60°	135.3	128.5	121.6	117.1	114.9	112.7	110.6	108.4
62.5°	119.0	112.4	105.8	101.9	100.6	99.3	98.0	96.7
65°	96.8	92.1	87.6	85.0	84.6	84.2	83.8	83.4
67.5°	78.1	76.0	73.9	72.6	72.2	71.7	71.3	70.8
70°	67.9	66.6	65.2	64.2	63.8	63.2	62.6	62.1
72.5°	59.1	58.0	56.8	56.1	55.8	55.4	55.1	54.8
75°	46.8	45.9	44.9	44.4	44.3	44.1	43.9	43.9
77.5°	35.5	34.9	34.4	34.0	33.8	33.6	33.3	33.1
80°	28.1	27.6	27.1	26.8	26.8	26.8	26.8	26.8
82.5°	21.3	21.0	20.6	20.5	20.5	20.5	20.5	20.5
85°	11.6	11.6	11.6	11.6	11.6	11.6	11.6	11.6
87.5°	6.3	6.3	6.3	6.4	6.4	6.4	6.5	6.5
90°	13.0	13.6	14.3	14.7	15.0	15.2	15.5	15.7
92.5°	14.2	14.5	14.8	15.2	15.2	15.4	15.6	15.7
95°	24.1	24.7	25.4	25.6	25.4	25.4	25.2	25.1
97.5°	31.5	32.0	32.5	32.9	33.0	33.2	33.3	33.5
100°	35.3	36.4	37.4	38.1	38.3	38.6	38.8	39.1
102.5°	36.9	38.2	39.5	40.4	40.8	41.2	41.5	41.9
105°	38.4	39.9	41.3	42.2	42.8	43.3	43.8	44.4
107.5°	46.9	45.4	44.0	43.5	44.0	44.6	45.1	45.6
110°	76.1	63.2	50.2	44.0	44.5	45.0	45.6	46.1





TEST NUMBER: P331660-930

CATALOG NUMBER: SA2XXRDIP-C485D725U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	162.9	115.6	68.3	44.8	45.3	45.7	46.1	46.6
115°	239.9	179.9	119.8	85.1	75.8	66.4	57.2	47.9
117.5°	369.6	355.0	340.5	317.9	287.2	256.6	225.9	195.3
120°	430.6	432.2	433.7	425.7	408.2	390.8	373.2	355.8
122.5°	456.9	457.8	458.8	457.5	454.1	450.7	447.4	443.9
125°	494.6	495.5	496.4	497.1	497.5	497.9	498.2	498.6
127.5°	529.5	530.8	532.1	532.9	533.0	533.0	533.1	533.2
130°	551.6	553.1	554.5	555.1	555.1	554.9	554.7	554.6
132.5°	573.2	574.4	575.6	576.2	576.0	575.9	575.8	575.6
135°	603.9	605.2	606.5	607.0	606.7	606.5	606.2	605.9
137.5°	632.4	633.7	635.0	635.4	635.0	634.5	634.1	633.6
140°	650.9	652.0	653.2	653.5	652.8	652.2	651.5	650.9
142.5°	667.9	669.0	670.0	670.3	669.6	669.0	668.3	667.6
145°	691.8	692.7	693.6	693.7	693.1	692.4	691.8	691.1
147.5°	712.5	713.2	713.9	714.0	713.4	712.8	712.3	711.8
150°	725.3	726.1	726.8	726.9	726.3	725.6	725.0	724.3
152.5°	736.9	737.8	738.6	738.5	737.7	736.8	736.0	735.1
155°	752.8	753.5	754.3	754.2	753.1	752.1	751.1	750.0
157.5°	766.0	766.9	767.8	767.7	766.7	765.6	764.7	763.7
160°	773.7	774.5	775.3	775.2	774.3	773.4	772.5	771.6
162.5°	780.9	781.8	782.7	782.6	781.5	780.3	779.3	778.1
165°	789.7	790.7	791.6	791.6	790.7	789.7	788.8	787.9
167.5°	797.1	798.0	798.9	798.7	797.6	796.5	795.2	794.1
170°	800.8	801.7	802.7	802.5	801.4	800.1	799.0	797.9
172.5°	803.6	804.5	805.4	805.3	804.1	803.0	801.8	800.6
175°	806.7	807.6	808.5	808.3	807.0	805.7	804.4	803.1
177.5°	807.0	807.7	808.5	808.4	807.4	806.5	805.5	804.6
180°	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0

(END OF REPORT)