

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331679-930

Luminaire Tested: **SA2XXRDIP-C675D330U930-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331679-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXRDIP-C675D330U930-4F0-1E-UDD-F1  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 330 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2847.3 lumens  
Efficiency: N/A  
Efficacy: 81.4 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 35  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331679-930  
CATALOG NUMBER: SA2XXRDIP-C675D330U930-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P331679-930

CATALOG NUMBER: SA2XXRDIP-C675D330U930-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	111	111	111	111	105	105	105	105	92	92	92	81	81	81	71	71	71	66				
1	102	98	94	91	96	92	89	86	82	80	77	73	71	69	64	63	61	57				
2	94	86	80	75	88	82	76	72	73	69	65	65	62	59	57	55	53	49				
3	86	76	69	64	81	72	66	61	65	60	56	58	54	51	51	48	46	42				
4	79	68	60	54	74	65	58	52	58	52	48	52	47	44	46	43	40	37				
5	73	61	53	47	68	58	51	45	52	46	42	47	42	39	42	38	35	32				
6	67	55	47	41	63	53	45	40	47	41	37	43	38	34	38	34	31	29				
7	62	50	42	37	59	48	41	35	43	37	33	39	34	31	35	31	28	26				
8	58	46	38	33	55	44	37	32	40	34	30	36	31	27	32	28	25	23				
9	54	42	35	30	51	40	33	29	37	31	27	33	28	25	30	26	23	21				
10	51	39	32	27	48	37	30	26	34	28	24	31	26	23	28	24	21	19				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	14849	14849	14849
5°	14906	14663	14744
10°	14791	14423	14300
15°	14621	13996	13593
20°	14387	13385	12713
25°	14145	12691	11863
30°	13811	11979	10769
35°	13484	11203	9810
40°	13156	10404	8701
45°	12771	9501	7695
50°	12376	8593	6712
55°	11972	7614	5762
60°	11502	6584	4782
65°	10968	5532	4359
70°	10334	4556	4008
75°	9551	4155	3737
80°	8433	3710	3403
85°	6632	2927	2927



TEST NUMBER: P331679-930

CATALOG NUMBER: SA2XXRDIP-C675D330U930-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	86.1	3.0
10°-20°	236.4	8.3
20°-30°	331.9	11.7
30°-40°	361.9	12.7
40°-50°	332.8	11.7
50°-60°	261.4	9.2
60°-70°	170.4	6.0
70°-80°	87.9	3.1
80°-90°	24.2	0.8
90°-100°	21.6	0.8
100°-110°	67.2	2.4
110°-120°	114.8	4.0
120°-130°	151.0	5.3
130°-140°	169.5	6.0
140°-150°	166.2	5.8
150°-160°	139.4	4.9
160°-170°	92.4	3.2
170°-180°	32.3	1.1
0°-30°	654.4	23.0
0°-40°	1016.3	35.7
0°-60°	1610.5	56.6
0°-90°	1892.9	66.5
90°-120°	203.6	7.2
90°-150°	690.3	24.2
90°-180°	954.0	33.5
0°-180°	2847.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	920	920	920	920	920	
5°	920	915	905	912	910	87
15°	875	864	837	822	813	246
25°	794	766	712	680	666	365
35°	684	640	568	518	498	428
45°	559	502	416	359	337	432
55°	425	359	270	222	205	380
65°	287	219	145	118	114	285
75°	153	96	67	61	60	162
85°	36	19	16	16	16	42
90°	0	4	10	10	10	2
95°	15	18	18	18	18	17
105°	62	63	63	64	64	65
115°	115	117	116	116	115	114
125°	168	170	169	168	168	150
135°	217	220	221	220	220	168
145°	263	265	267	267	266	164
155°	301	302	303	304	303	138
165°	328	327	327	329	328	92
175°	341	340	339	341	340	32
180°	341	341	341	341	341	



TEST NUMBER: P331679-930

CATALOG NUMBER: SA2XXRDIP-C675D330U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	919.7	919.7	919.7	919.7	919.7	919.7	919.7	919.7	919.7	919.7	919.7
2.5°	923.0	922.3	921.5	920.8	920.1	918.8	917.2	915.6	914.0	912.4	913.9
5°	919.7	918.8	917.9	916.9	916.0	914.4	911.9	909.5	907.1	904.7	906.4
7.5°	910.2	909.1	907.9	906.8	905.6	903.6	900.8	898.1	895.2	892.4	892.8
10°	902.2	900.9	899.6	898.3	897.0	894.5	890.8	887.1	883.5	879.7	879.2
12.5°	892.2	890.6	889.0	887.5	885.8	882.7	878.0	873.3	868.5	863.7	862.7
15°	874.7	872.7	870.7	868.6	866.6	862.4	856.1	849.9	843.6	837.3	833.8
17.5°	853.3	850.2	847.1	843.9	840.8	835.3	827.2	819.1	811.1	803.0	798.8
20°	837.3	833.6	829.9	826.2	822.5	816.0	806.7	797.5	788.3	779.0	774.4
22.5°	819.9	815.9	811.7	807.6	803.4	796.1	785.7	775.3	764.8	754.4	748.4
25°	794.0	788.1	782.2	776.2	770.4	761.2	749.1	736.9	724.6	712.4	704.8
27.5°	762.7	756.3	749.8	743.4	736.9	726.8	713.1	699.4	685.6	671.8	663.0
30°	740.8	733.7	726.7	719.7	712.7	701.7	686.9	672.1	657.3	642.5	633.1
32.5°	719.4	711.2	703.0	694.8	686.6	674.9	659.8	644.7	629.7	614.6	603.8
35°	684.1	674.7	665.3	655.8	646.5	633.6	617.3	601.0	584.7	568.4	556.8
37.5°	648.9	638.5	628.1	617.8	607.4	593.5	576.3	558.9	541.5	524.2	511.4
40°	624.2	613.1	602.0	590.9	579.8	565.3	547.4	529.5	511.5	493.6	480.5
42.5°	598.9	587.3	575.5	563.9	552.2	537.0	518.5	500.0	481.4	462.9	449.3
45°	559.3	546.9	534.5	522.1	509.7	493.8	474.4	455.0	435.5	416.1	403.0
47.5°	520.7	507.5	494.4	481.3	468.1	451.6	431.5	411.5	391.4	371.4	358.3
50°	492.7	479.6	466.4	453.3	440.2	423.5	403.1	382.8	362.4	342.1	329.3
52.5°	465.5	451.7	438.0	424.3	410.5	393.7	373.8	353.9	334.0	314.1	301.8
55°	425.3	410.9	396.5	382.0	367.6	350.4	330.4	310.5	290.5	270.5	259.4
57.5°	384.2	369.4	354.6	339.8	325.0	308.0	288.8	269.6	250.4	231.2	221.0
60°	356.2	341.4	326.6	311.9	297.0	280.1	261.1	242.0	223.0	203.9	194.4
62.5°	328.9	314.1	299.3	284.5	269.7	253.2	235.1	217.0	198.8	180.6	171.6
65°	287.1	272.1	257.1	242.2	227.2	211.4	194.8	178.1	161.4	144.8	138.5
67.5°	246.9	232.0	217.1	202.3	187.4	172.4	157.4	142.5	127.5	112.5	109.7
70°	218.9	204.5	190.0	175.6	161.2	147.6	134.9	122.1	109.3	96.5	94.7
72.5°	192.2	178.4	164.6	150.7	136.9	124.9	114.6	104.4	94.2	83.9	82.3
75°	153.1	140.2	127.3	114.3	101.3	91.7	85.4	79.2	72.9	66.6	65.3
77.5°	114.7	103.3	92.0	80.6	69.3	62.0	59.0	56.0	53.0	50.0	49.2
80°	90.7	81.3	71.8	62.5	53.0	47.4	45.5	43.6	41.8	39.9	39.2
82.5°	68.7	61.4	54.1	46.6	39.3	35.0	33.8	32.4	31.2	30.0	29.5
85°	35.8	31.9	28.0	24.1	20.2	18.0	17.4	17.0	16.4	15.8	15.8
87.5°	10.7	9.7	8.6	7.6	6.6	6.2	6.5	6.8	7.1	7.3	7.2
90°	0.3	1.1	1.8	2.6	3.3	4.5	5.9	7.3	8.6	10.1	9.9
92.5°	5.1	5.7	6.3	6.8	7.4	7.8	8.2	8.5	8.8	9.1	9.2
95°	15.0	15.7	16.2	16.9	17.5	17.9	18.0	18.2	18.3	18.4	18.4
97.5°	27.4	28.0	28.5	29.0	29.6	30.0	30.2	30.5	30.7	31.0	31.0
100°	36.6	37.1	37.6	38.2	38.6	39.0	39.1	39.4	39.5	39.8	39.8
102.5°	46.2	46.6	47.0	47.5	47.9	48.3	48.4	48.7	48.9	49.2	49.2
105°	62.0	62.1	62.3	62.5	62.7	62.9	63.0	63.1	63.3	63.3	63.5
107.5°	77.7	78.0	78.3	78.6	78.8	79.0	79.0	79.0	79.0	79.0	79.0
110°	87.9	88.2	88.6	89.0	89.4	89.6	89.6	89.6	89.6	89.6	89.6



TEST NUMBER: P331679-930

CATALOG NUMBER: SA2XXRDIP-C675D330U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	98.9	99.3	99.7	100.0	100.4	100.6	100.5	100.5	100.4	100.4	100.3
115°	115.2	115.6	116.0	116.3	116.8	116.9	116.8	116.6	116.5	116.3	116.3
117.5°	131.4	132.0	132.5	133.0	133.5	133.6	133.2	132.9	132.5	132.2	132.0
120°	142.3	142.8	143.3	143.8	144.3	144.3	143.8	143.3	142.8	142.3	142.3
122.5°	152.2	152.8	153.4	154.0	154.7	154.8	154.4	154.1	153.7	153.4	153.2
125°	167.6	168.2	168.8	169.3	169.9	170.2	169.9	169.7	169.6	169.3	169.2
127.5°	182.7	183.4	184.2	184.8	185.6	185.8	185.6	185.4	185.2	184.9	184.7
130°	192.2	193.0	193.8	194.6	195.4	195.8	195.7	195.6	195.4	195.3	195.2
132.5°	202.8	203.4	204.1	204.7	205.5	205.8	205.8	205.9	205.9	205.9	205.6
135°	216.9	217.6	218.3	219.0	219.7	220.1	220.3	220.4	220.5	220.6	220.5
137.5°	231.8	232.4	232.9	233.6	234.2	234.5	234.6	234.8	235.0	235.1	235.1
140°	240.8	241.4	242.0	242.6	243.1	243.5	243.9	244.2	244.5	244.8	244.8
142.5°	250.1	250.6	251.2	251.8	252.3	252.7	252.9	253.2	253.4	253.6	253.6
145°	263.3	263.7	264.2	264.6	265.1	265.5	265.9	266.3	266.6	267.0	267.1
147.5°	275.1	275.7	276.1	276.7	277.2	277.6	277.9	278.2	278.4	278.7	278.8
150°	283.2	283.6	283.9	284.3	284.7	285.0	285.3	285.5	285.8	286.0	286.3
152.5°	290.3	290.7	291.1	291.5	291.8	292.2	292.4	292.8	293.1	293.4	293.7
155°	301.0	301.2	301.4	301.6	301.7	302.0	302.1	302.3	302.6	302.7	303.0
157.5°	310.1	310.3	310.4	310.5	310.7	310.8	311.0	311.0	311.1	311.3	311.7
160°	315.7	315.8	315.9	316.1	316.2	316.3	316.3	316.4	316.5	316.6	316.9
162.5°	320.7	320.8	320.8	320.8	320.9	320.9	321.0	321.1	321.1	321.1	321.6
165°	327.5	327.4	327.3	327.3	327.3	327.2	327.2	327.2	327.2	327.2	327.7
167.5°	333.1	333.0	332.8	332.6	332.4	332.3	332.2	332.2	332.2	332.2	332.6
170°	336.1	336.0	335.7	335.6	335.4	335.3	335.2	335.1	335.1	335.0	335.4
172.5°	338.2	338.0	337.9	337.6	337.5	337.3	337.3	337.2	337.1	337.0	337.5
175°	340.8	340.6	340.4	340.1	340.0	339.8	339.7	339.6	339.4	339.3	339.7
177.5°	341.8	341.6	341.4	341.4	341.2	341.0	341.0	340.9	340.7	340.6	341.0
180°	341.4	341.4	341.4	341.4	341.4	341.4	341.4	341.4	341.4	341.4	341.4



TEST NUMBER: P331679-930

CATALOG NUMBER: SA2XXRDIP-C675D330U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	919.7	919.7	919.7	919.7	919.7	919.7	919.7	919.7
2.5°	915.3	916.8	918.3	918.8	918.6	918.3	918.0	917.7
5°	908.0	909.7	911.3	911.9	911.3	910.8	910.3	909.7
7.5°	893.3	893.8	894.3	894.1	893.1	892.2	891.2	890.2
10°	878.6	878.1	877.5	876.7	875.5	874.5	873.3	872.2
12.5°	861.8	860.8	859.7	858.3	856.5	854.7	852.8	850.9
15°	830.3	826.7	823.2	820.5	818.7	816.8	815.0	813.2
17.5°	794.7	790.4	786.3	782.6	779.4	776.2	773.1	769.9
20°	769.8	765.2	760.5	756.2	752.1	748.0	744.0	739.9
22.5°	742.5	736.5	730.6	726.1	723.0	720.0	717.0	714.0
25°	697.2	689.7	682.1	676.9	674.2	671.4	668.6	665.9
27.5°	654.1	645.3	636.5	629.8	625.4	621.0	616.6	612.2
30°	623.7	614.2	604.8	597.6	592.6	587.6	582.6	577.6
32.5°	593.0	582.3	571.5	563.8	559.1	554.4	549.7	545.0
35°	545.2	533.5	521.9	514.0	509.9	505.8	501.8	497.7
37.5°	498.5	485.7	472.9	464.1	459.4	454.8	450.1	445.5
40°	467.2	454.1	441.0	432.0	427.2	422.4	417.6	412.8
42.5°	435.8	422.2	408.6	399.5	394.8	390.2	385.6	380.8
45°	389.9	376.7	363.6	354.8	350.4	345.9	341.5	337.0
47.5°	345.3	332.2	319.1	310.6	306.6	302.6	298.5	294.5
50°	316.6	303.8	291.1	282.7	278.8	274.9	271.1	267.2
52.5°	289.5	277.1	264.8	256.9	253.3	249.7	246.1	242.6
55°	248.3	237.2	226.1	218.8	215.3	211.7	208.2	204.7
57.5°	210.8	200.7	190.5	183.9	181.0	178.1	175.0	172.1
60°	185.1	175.6	166.2	160.0	157.0	154.1	151.1	148.1
62.5°	162.7	153.6	144.6	139.3	137.5	135.7	134.0	132.2
65°	132.2	126.0	119.7	116.3	115.7	115.1	114.5	114.1
67.5°	106.7	103.9	101.0	99.2	98.7	98.1	97.5	96.9
70°	92.9	91.0	89.1	87.9	87.1	86.3	85.6	84.9
72.5°	80.8	79.2	77.7	76.7	76.2	75.8	75.3	74.9
75°	64.0	62.7	61.4	60.7	60.5	60.3	60.1	59.9
77.5°	48.4	47.7	47.0	46.5	46.1	45.9	45.6	45.2
80°	38.5	37.7	37.0	36.6	36.6	36.6	36.6	36.6
82.5°	29.1	28.6	28.2	28.0	28.0	28.0	28.0	28.0
85°	15.8	15.8	15.8	15.8	15.8	15.8	15.8	15.8
87.5°	7.0	6.8	6.7	6.6	6.6	6.6	6.6	6.6
90°	9.9	9.7	9.5	9.5	9.6	9.7	9.7	9.8
92.5°	9.2	9.2	9.3	9.3	9.3	9.3	9.3	9.3
95°	18.4	18.4	18.4	18.3	18.3	18.1	18.0	17.9
97.5°	31.0	31.0	31.0	31.0	31.0	31.0	31.0	30.9
100°	39.8	39.8	39.8	39.7	39.6	39.6	39.5	39.5
102.5°	49.3	49.3	49.4	49.4	49.3	49.2	49.2	49.2
105°	63.6	63.8	63.9	63.9	63.9	63.9	63.9	63.9
107.5°	79.1	79.2	79.2	79.1	78.8	78.5	78.2	77.9
110°	89.6	89.6	89.6	89.5	89.3	89.1	88.9	88.7





TEST NUMBER: P331679-930  
CATALOG NUMBER: SA2XXRDIP-C675D330U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	100.1	100.0	99.8	99.6	99.5	99.4	99.2	99.1
115°	116.3	116.2	116.1	116.0	115.8	115.6	115.4	115.2
117.5°	131.8	131.7	131.5	131.3	131.2	131.0	130.8	130.6
120°	142.3	142.3	142.3	142.2	142.0	141.8	141.6	141.5
122.5°	153.0	152.9	152.7	152.6	152.5	152.3	152.1	152.1
125°	169.0	168.8	168.6	168.4	168.4	168.4	168.3	168.2
127.5°	184.5	184.3	184.0	183.8	183.6	183.4	183.2	183.0
130°	195.0	194.9	194.8	194.6	194.4	194.0	193.8	193.6
132.5°	205.3	205.0	204.8	204.6	204.3	204.2	203.9	203.7
135°	220.5	220.5	220.4	220.3	220.0	219.9	219.7	219.5
137.5°	235.1	235.0	235.0	234.8	234.6	234.3	234.1	233.7
140°	244.8	244.8	244.8	244.7	244.4	244.2	243.9	243.7
142.5°	253.7	253.7	253.8	253.7	253.5	253.2	252.9	252.7
145°	267.2	267.2	267.3	267.2	266.9	266.7	266.4	266.1
147.5°	278.9	279.1	279.2	279.2	278.9	278.7	278.4	278.2
150°	286.4	286.6	286.8	286.8	286.6	286.4	286.3	286.0
152.5°	293.9	294.2	294.4	294.4	294.2	293.9	293.7	293.4
155°	303.4	303.7	304.0	304.1	303.9	303.7	303.5	303.3
157.5°	312.1	312.6	313.0	313.1	312.7	312.4	312.2	311.9
160°	317.3	317.7	318.1	318.1	317.9	317.6	317.4	317.2
162.5°	322.0	322.5	322.9	322.9	322.7	322.4	322.0	321.7
165°	328.1	328.6	329.0	329.1	328.7	328.4	328.1	327.8
167.5°	333.1	333.5	334.0	334.1	333.8	333.4	333.0	332.7
170°	335.9	336.3	336.8	336.8	336.5	336.1	335.7	335.3
172.5°	337.9	338.4	338.8	338.9	338.5	338.1	337.8	337.4
175°	340.2	340.6	341.1	341.1	340.8	340.4	340.0	339.6
177.5°	341.3	341.5	341.9	341.9	341.5	341.3	341.0	340.6
180°	341.4	341.4	341.4	341.4	341.4	341.4	341.4	341.4

(END OF REPORT)