

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331683-930

Luminaire Tested: **SA2XXRDIP-C675D530U930-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331683-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXRDIP-C675D530U930-4F0-1E-UDD-A4  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 530 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3754.6 lumens  
Efficiency: N/A  
Efficacy: 93.2 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 40.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331683-930  
CATALOG NUMBER: SA2XXRDIP-C675D530U930-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P331683-930

CATALOG NUMBER: SA2XXRDIP-C675D530U930-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55
1	100	96	92	89	93	89	86	83	77	75	73	66	64	62	55	54	53	48
2	92	85	79	74	85	79	74	70	68	65	62	59	56	54	50	48	46	42
3	84	75	68	63	78	70	64	59	61	57	53	53	49	46	45	42	40	37
4	78	67	60	54	72	63	56	51	55	50	46	48	44	41	41	38	36	32
5	72	61	53	47	67	57	50	45	50	44	40	43	39	36	37	34	32	29
6	66	55	47	42	62	52	45	40	45	40	36	40	35	32	34	31	28	26
7	62	50	42	37	57	47	40	35	42	36	32	36	32	29	32	28	26	23
8	57	46	38	33	54	43	36	32	38	33	29	34	29	26	29	26	23	21
9	54	42	35	30	50	40	33	29	35	30	26	31	27	24	27	24	21	19
10	50	39	32	27	47	37	30	26	33	28	24	29	25	22	25	22	20	18

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	19339	19339	19339	19339
5°	21598	19460	17253	19460
10°	23963	19323	14955	19323
15°	25142	19041	11784	19041
20°	21795	18620	10198	18620
25°	14295	18045	9103	18045
30°	9622	17350	8240	17350
35°	7792	16472	7433	16472
40°	6930	15517	6877	15517
45°	6272	14397	6140	14397
50°	5707	13288	5687	13288
55°	5365	12056	5295	12056
60°	4489	10924	4434	10924
65°	3786	9922	4290	9922
70°	3498	8861	4050	8861
75°	3269	7711	3737	7711
80°	3013	6341	3329	6341
85°	2779	5020	2927	5020



TEST NUMBER: P331683-930

CATALOG NUMBER: SA2XXRDIP-C675D530U930-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	113.5	3.0
10°-20°	316.4	8.4
20°-30°	407.7	10.9
30°-40°	387.4	10.3
40°-50°	331.9	8.8
50°-60°	252.7	6.7
60°-70°	159.8	4.3
70°-80°	79.8	2.1
80°-90°	22.9	0.6
90°-100°	96.7	2.6
100°-110°	328.1	8.7
110°-120°	348.5	9.3
120°-130°	286.9	7.6
130°-140°	230.4	6.1
140°-150°	174.1	4.6
150°-160°	122.4	3.3
160°-170°	72.0	1.9
170°-180°	23.4	0.6
0°-30°	837.6	22.3
0°-40°	1225.0	32.6
0°-60°	1809.6	48.2
0°-90°	2072.1	55.2
90°-120°	773.2	20.6
90°-150°	1464.6	39.0
90°-180°	1682.0	44.8
0°-180°	3754.6	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1198	1198	1198	1198	1198	
5°	1333	1201	1064	1201	1333	132
15°	1504	1139	705	1139	1504	406
25°	802	1013	511	1013	802	381
35°	395	836	377	836	395	253
45°	275	630	269	630	275	213
55°	191	428	188	428	191	167
65°	99	260	112	260	99	101
75°	52	124	60	124	52	56
85°	15	27	16	27	15	16
90°	15	0	15	0	15	9
95°	53	16	53	16	53	69
105°	524	57	524	57	524	507
115°	690	100	690	100	690	675
125°	559	140	559	140	559	505
135°	464	164	464	164	464	360
145°	370	187	370	187	370	235
155°	311	212	311	212	311	145
165°	273	232	273	232	273	78
175°	246	241	246	241	246	24
180°	242	242	242	242	242	



TEST NUMBER: P331683-930

CATALOG NUMBER: SA2XXRDIP-C675D530U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8
2.5°	1246.3	1247.3	1248.4	1246.0	1246.0	1244.0	1239.7	1236.4	1227.0	1225.7	1225.7
5°	1332.6	1331.7	1333.4	1328.0	1320.5	1318.8	1310.9	1300.6	1289.7	1277.7	1275.1
7.5°	1418.3	1417.1	1413.7	1412.8	1407.0	1394.5	1381.8	1368.2	1350.2	1332.7	1323.9
10°	1461.6	1475.4	1467.0	1452.5	1455.4	1435.8	1425.4	1407.5	1392.5	1366.3	1360.5
12.5°	1504.2	1509.6	1507.0	1498.7	1494.9	1481.4	1467.4	1451.8	1424.2	1400.6	1380.1
15°	1504.1	1512.0	1514.0	1511.6	1513.6	1512.8	1505.3	1492.4	1468.3	1442.4	1420.0
17.5°	1393.0	1398.5	1412.2	1421.4	1433.1	1457.7	1469.8	1474.6	1471.0	1456.3	1440.5
20°	1268.5	1259.3	1297.6	1317.2	1333.8	1375.4	1411.2	1425.0	1447.0	1446.6	1442.4
22.5°	1092.0	1094.2	1130.5	1153.7	1202.3	1243.9	1284.7	1336.4	1379.1	1407.3	1423.8
25°	802.4	818.2	854.4	886.1	940.1	1017.6	1087.9	1169.5	1246.4	1307.2	1365.1
27.5°	602.6	603.8	632.5	661.7	693.8	757.2	845.8	943.2	1053.0	1143.5	1247.7
30°	516.1	513.6	525.6	543.6	571.0	620.1	686.6	782.4	891.9	1028.3	1149.9
32.5°	454.8	454.9	464.1	477.3	500.1	533.2	578.8	656.6	760.0	894.2	1036.7
35°	395.3	394.9	401.6	411.2	420.8	442.0	473.2	514.0	585.1	710.4	856.1
37.5°	352.8	354.6	357.8	363.8	374.4	386.2	405.0	432.4	483.0	557.1	679.6
40°	328.8	329.6	334.2	339.2	345.4	354.6	370.0	392.0	429.1	488.2	577.6
42.5°	306.8	307.6	310.9	315.5	320.4	329.6	342.3	361.4	391.4	437.6	511.4
45°	274.7	274.7	277.6	279.6	285.1	293.4	303.8	319.6	340.5	374.5	423.6
47.5°	244.5	244.6	246.5	250.1	253.6	260.0	270.3	283.2	298.3	324.7	366.6
50°	227.2	227.6	228.9	231.8	233.9	239.7	247.6	258.9	274.7	295.1	330.0
52.5°	213.3	213.0	214.6	215.8	217.3	221.4	227.3	237.3	251.4	269.1	298.1
55°	190.6	188.9	191.4	193.6	194.8	196.4	199.7	206.0	218.1	233.1	254.7
57.5°	162.3	161.7	163.4	165.3	169.3	173.7	176.5	180.5	186.8	197.5	219.0
60°	139.0	139.0	142.8	144.0	148.5	154.4	160.2	163.5	169.8	176.8	192.7
62.5°	118.4	118.7	120.4	121.7	124.3	131.4	139.6	146.9	152.8	159.6	170.1
65°	99.1	99.9	99.9	100.7	102.4	104.0	107.4	113.2	123.6	133.1	141.0
67.5°	84.1	84.3	84.5	85.4	85.9	87.6	88.9	91.6	94.0	103.1	112.8
70°	74.1	75.3	74.9	75.7	76.1	77.0	78.7	79.9	83.6	85.8	91.6
72.5°	64.7	65.6	65.6	66.1	67.2	67.3	68.6	70.0	72.3	74.1	77.2
75°	52.4	52.0	52.4	53.2	53.6	54.1	54.1	55.8	57.0	58.7	60.7
77.5°	40.4	40.8	40.8	40.8	40.9	41.7	41.6	42.4	43.6	44.4	45.4
80°	32.4	32.9	32.4	32.9	33.3	33.7	33.3	33.7	35.0	35.8	35.8
82.5°	25.1	25.2	25.4	25.5	25.6	25.7	26.3	26.4	27.3	27.1	27.5
85°	15.0	14.6	14.6	14.6	15.0	15.4	15.0	15.0	15.4	15.4	15.4
87.5°	8.4	8.7	8.7	8.7	8.7	8.6	8.5	9.0	8.7	9.1	8.7
90°	15.3	15.3	15.3	15.3	15.3	14.8	13.9	14.8	15.3	15.8	15.3
92.5°	25.8	26.5	26.2	27.6	28.0	30.9	34.8	40.5	51.0	60.4	59.6
95°	53.0	52.5	54.0	57.6	63.7	73.9	93.4	121.8	159.5	182.3	161.3
97.5°	104.4	108.3	115.0	126.5	148.7	182.3	232.6	284.3	326.4	311.1	234.3
100°	166.5	174.8	188.3	208.3	246.9	303.1	366.9	424.5	434.2	367.3	252.9
102.5°	292.9	304.3	321.1	355.2	397.1	456.8	503.4	516.4	474.4	369.2	245.9
105°	524.0	530.5	550.5	579.4	608.1	623.5	617.4	564.9	468.2	344.5	232.0
107.5°	669.4	678.0	682.0	683.5	680.0	657.5	609.1	529.9	427.4	318.1	225.1
110°	713.2	713.7	709.6	700.7	680.7	642.5	583.0	499.9	401.7	305.5	223.6



TEST NUMBER: P331683-930

CATALOG NUMBER: SA2XXRDIP-C675D530U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	712.5	710.0	702.1	687.3	659.5	615.8	552.2	472.3	383.8	297.3	224.0
115°	689.5	685.3	673.3	651.8	618.9	571.0	510.1	438.5	361.7	288.3	226.0
117.5°	648.5	645.0	632.3	609.7	576.0	531.1	475.8	412.9	347.8	283.9	229.3
120°	622.1	617.4	604.0	582.1	549.6	507.3	458.0	400.3	340.4	281.3	231.5
122.5°	594.6	590.7	578.7	557.2	528.0	489.8	443.1	390.3	334.0	279.8	234.2
125°	559.4	555.6	544.0	526.4	499.4	464.5	423.5	375.7	325.0	277.1	238.1
127.5°	528.5	525.5	515.4	498.9	475.4	443.2	404.6	361.3	316.7	275.6	242.1
130°	510.9	507.3	498.0	482.2	459.3	428.7	392.0	352.0	311.0	274.8	245.0
132.5°	492.8	489.4	480.9	465.0	442.6	413.8	380.1	343.1	306.6	274.4	248.0
135°	463.6	461.7	453.3	438.0	418.0	392.0	361.3	330.6	300.4	273.9	251.5
137.5°	434.9	432.1	424.8	411.6	393.4	370.6	346.3	320.7	296.0	273.8	254.7
140°	415.2	412.4	405.4	393.4	378.5	358.0	336.6	314.3	293.4	273.4	256.2
142.5°	395.5	394.9	388.7	377.7	363.6	346.5	328.1	309.1	290.8	273.4	257.3
145°	370.1	368.7	364.0	356.1	345.0	331.5	317.1	301.7	287.3	272.5	258.5
147.5°	348.8	348.0	344.8	338.5	329.3	319.4	308.2	296.1	283.8	270.8	258.9
150°	336.1	335.7	332.9	327.3	320.3	312.0	302.2	292.0	280.9	269.7	258.5
152.5°	325.4	325.3	323.3	318.4	312.9	305.7	297.4	287.9	278.3	267.8	257.8
155°	311.0	312.0	310.1	306.9	301.7	296.6	289.7	282.3	273.4	264.6	256.7
157.5°	298.9	298.9	298.1	295.3	291.7	287.7	281.8	275.7	268.8	261.2	254.5
160°	291.1	291.1	290.6	288.3	285.0	281.8	276.6	271.5	265.5	259.0	253.4
162.5°	283.6	284.0	283.6	281.9	278.7	276.2	271.8	267.4	262.5	257.1	252.3
165°	273.0	273.4	273.4	271.5	269.7	267.8	264.6	261.3	257.6	253.4	250.1
167.5°	263.1	263.7	263.7	262.7	261.9	260.2	258.0	255.4	252.7	250.1	248.0
170°	257.1	258.0	258.5	257.1	256.7	255.8	253.9	252.5	250.1	248.3	246.9
172.5°	252.3	252.8	253.3	252.7	252.2	251.6	250.1	249.2	247.5	246.1	245.4
175°	246.0	246.9	247.4	246.9	246.9	246.5	246.0	245.5	244.1	243.6	243.2
177.5°	242.1	242.9	243.3	243.3	243.3	243.3	242.9	242.9	242.1	241.7	242.1
180°	241.7	241.7	241.7	241.7	241.7	241.7	241.7	241.7	241.7	241.7	241.7



TEST NUMBER: P331683-930

CATALOG NUMBER: SA2XXRDIP-C675D530U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8
2.5°	1226.4	1223.7	1221.4	1215.4	1212.4	1205.7	1204.8	1204.4	1195.7	1187.4	1185.1
5°	1268.5	1261.8	1251.8	1240.2	1228.1	1215.6	1207.3	1200.7	1184.0	1168.2	1159.0
7.5°	1310.9	1296.7	1279.4	1257.4	1238.9	1218.3	1203.0	1189.3	1165.6	1143.0	1127.7
10°	1342.6	1319.2	1296.4	1266.0	1242.3	1219.0	1197.3	1178.6	1151.9	1122.0	1100.7
12.5°	1362.2	1336.6	1305.0	1275.3	1244.6	1215.0	1186.0	1162.0	1130.7	1099.7	1074.5
15°	1388.8	1361.3	1323.0	1280.6	1241.0	1202.3	1169.1	1139.1	1098.3	1061.3	1030.5
17.5°	1410.5	1372.7	1331.5	1282.5	1236.7	1187.5	1144.6	1106.4	1060.9	1016.3	980.0
20°	1417.5	1380.1	1332.6	1283.4	1229.4	1171.5	1125.4	1083.7	1035.0	986.3	944.7
22.5°	1413.2	1384.1	1331.2	1272.5	1217.1	1156.5	1104.3	1056.1	1002.1	952.4	904.1
25°	1383.8	1373.8	1323.9	1259.7	1196.5	1126.2	1065.8	1012.9	951.4	898.1	845.6
27.5°	1315.2	1336.8	1305.9	1237.6	1167.3	1091.8	1024.0	963.8	899.9	840.0	787.7
30°	1249.4	1298.9	1285.6	1222.3	1143.6	1069.6	993.4	930.6	862.3	800.7	749.1
32.5°	1159.1	1241.0	1253.9	1201.0	1119.7	1038.3	958.5	895.9	824.7	759.8	709.5
35°	1015.5	1137.8	1194.0	1160.3	1078.7	990.9	908.5	835.7	764.1	700.0	650.0
37.5°	844.1	1010.7	1104.3	1106.8	1031.8	940.5	850.8	778.5	705.2	642.3	588.3
40°	732.9	913.5	1035.4	1062.5	999.2	900.6	809.8	736.2	664.6	603.0	541.0
42.5°	633.0	812.9	962.9	1009.9	959.6	861.6	770.6	693.6	624.0	565.7	502.4
45°	511.9	669.2	834.5	918.5	890.6	799.9	703.8	630.5	565.2	514.8	454.0
47.5°	431.8	542.7	702.5	816.3	815.8	733.0	638.4	568.3	507.7	460.5	411.2
50°	386.2	482.7	618.0	747.1	757.8	688.4	598.4	529.0	472.4	422.8	383.3
52.5°	345.3	424.9	546.4	670.1	700.9	640.7	553.5	489.3	434.4	388.9	355.0
55°	291.7	353.4	445.7	561.4	608.1	565.6	488.2	428.3	383.7	345.4	316.3
57.5°	246.8	293.0	367.1	460.3	514.5	487.9	424.0	375.3	337.2	302.6	279.6
60°	218.5	256.3	319.2	397.1	457.0	438.2	383.7	338.3	305.9	275.9	254.3
62.5°	191.8	224.4	278.3	341.4	396.4	388.7	344.1	306.1	277.6	250.3	232.0
65°	154.4	178.1	220.1	269.7	313.8	317.6	285.5	259.7	234.3	212.6	196.4
67.5°	122.9	138.4	168.0	209.8	242.8	254.6	235.1	215.3	195.2	178.5	164.4
70°	103.6	116.1	137.8	171.5	201.9	214.3	203.1	187.7	170.2	156.5	144.4
72.5°	84.0	96.1	112.1	136.8	162.9	176.3	172.4	161.4	147.2	135.8	124.4
75°	63.3	67.0	77.9	94.5	114.9	126.5	129.5	123.6	112.3	103.6	96.9
77.5°	46.8	49.0	54.2	62.9	76.2	86.7	90.9	90.3	82.5	77.4	71.2
80°	37.4	38.7	41.2	44.9	55.0	65.3	68.2	68.2	62.9	60.7	54.5
82.5°	28.5	29.4	30.9	32.9	37.6	46.7	50.0	50.6	47.2	44.4	39.5
85°	16.2	15.8	16.6	17.9	18.8	21.2	26.3	27.1	26.3	22.9	21.6
87.5°	8.2	7.8	7.4	6.8	6.9	7.1	8.4	9.8	8.7	8.1	7.6
90°	12.6	9.3	7.0	5.5	4.6	3.8	1.9	0.5	1.9	3.8	4.6
92.5°	46.4	31.6	21.1	16.7	13.6	11.5	8.2	5.7	8.2	11.5	13.6
95°	107.4	66.9	45.6	34.4	27.0	22.7	18.1	16.3	18.1	22.7	27.0
97.5°	144.7	88.4	61.5	48.8	40.3	33.9	29.0	26.5	29.0	33.9	40.3
100°	152.5	95.8	71.2	58.1	48.8	41.4	37.2	35.8	37.2	41.4	48.8
102.5°	152.9	102.5	79.7	66.7	57.0	49.6	45.4	44.4	45.4	49.6	57.0
105°	155.3	113.9	92.0	79.0	68.8	61.8	58.6	56.7	58.6	61.8	68.8
107.5°	161.7	125.6	104.4	91.3	81.2	74.8	71.6	70.1	71.6	74.8	81.2
110°	166.9	133.5	113.0	99.5	89.8	83.7	80.9	79.0	80.9	83.7	89.8





TEST NUMBER: P331683-930

CATALOG NUMBER: SA2XXRDIP-C675D530U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	172.5	140.9	121.2	107.3	97.9	92.2	89.1	87.2	89.1	92.2	97.9
115°	180.8	152.5	132.5	119.9	110.6	105.1	102.3	100.0	102.3	105.1	110.6
117.5°	189.8	163.2	144.7	131.7	122.8	117.8	115.0	113.2	115.0	117.8	122.8
120°	195.8	170.6	152.5	139.5	130.2	126.0	123.2	121.3	123.2	126.0	130.2
122.5°	201.0	177.7	160.7	147.3	138.0	133.5	130.7	129.1	130.7	133.5	138.0
125°	209.2	188.3	171.5	158.6	149.3	143.7	140.9	139.5	140.9	143.7	149.3
127.5°	217.0	198.2	181.9	168.5	159.6	153.4	149.5	147.7	149.5	153.4	159.6
130°	221.8	204.2	187.8	174.8	165.5	159.0	154.3	152.5	154.3	159.0	165.5
132.5°	226.7	209.3	193.8	180.8	171.1	164.2	159.2	156.9	159.2	164.2	171.1
135°	232.9	216.7	201.8	188.7	178.1	171.1	165.5	163.6	165.5	171.1	178.1
137.5°	237.7	222.7	207.9	195.8	185.2	177.8	172.2	170.0	172.2	177.8	185.2
140°	240.4	226.0	212.1	199.9	189.7	182.3	176.7	174.8	176.7	182.3	189.7
142.5°	242.6	228.6	215.0	203.7	193.8	186.4	181.2	179.7	181.2	186.4	193.8
145°	245.5	232.4	219.9	209.7	200.4	193.4	188.7	186.9	188.7	193.4	200.4
147.5°	247.1	235.6	223.8	214.7	207.0	200.6	196.1	194.7	196.1	200.6	207.0
150°	247.9	237.1	226.4	218.1	211.1	205.0	201.3	199.9	201.3	205.0	211.1
152.5°	248.2	238.6	229.0	221.4	214.8	209.5	205.8	205.1	205.8	209.5	214.8
155°	248.7	240.8	232.9	226.0	220.9	215.7	213.0	212.5	213.0	215.7	220.9
157.5°	248.7	242.4	235.7	229.9	225.8	221.4	219.1	218.6	219.1	221.4	225.8
160°	248.7	243.2	237.6	232.4	228.8	225.0	223.1	222.7	223.1	225.0	228.8
162.5°	248.3	243.5	238.7	234.7	231.4	228.4	226.5	226.8	226.5	228.4	231.4
165°	247.4	244.1	239.9	237.1	234.8	232.0	231.1	231.5	231.1	232.0	234.8
167.5°	246.7	244.0	240.9	239.2	237.5	235.7	234.9	235.5	234.9	235.7	237.5
170°	246.0	243.6	241.3	239.9	239.0	237.6	237.1	238.1	237.1	237.6	239.0
172.5°	244.8	243.3	241.7	240.7	240.1	238.7	239.0	239.5	239.0	238.7	240.1
175°	243.6	242.7	241.7	241.3	241.3	240.4	240.8	241.3	240.8	240.4	241.3
177.5°	242.9	242.1	241.7	241.7	241.7	241.0	241.4	242.1	241.4	241.0	241.7
180°	241.7	241.7	241.7	241.7	241.7	241.7	241.7	241.7	241.7	241.7	241.7



TEST NUMBER: P331683-930

CATALOG NUMBER: SA2XXRDIP-C675D530U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8
2.5°	1180.8	1178.4	1174.1	1167.4	1163.4	1156.4	1151.8	1154.5	1155.1	1154.5	1153.8
5°	1149.1	1140.3	1128.2	1116.6	1105.8	1094.1	1087.4	1084.5	1078.7	1075.4	1073.7
7.5°	1110.7	1095.6	1078.6	1058.3	1041.0	1023.0	1013.7	1009.1	997.2	990.8	985.0
10°	1082.1	1058.3	1041.3	1014.6	998.4	974.7	958.5	958.9	942.6	933.4	926.8
12.5°	1050.4	1024.3	996.0	972.0	949.4	930.4	910.9	902.9	885.7	876.9	858.9
15°	998.0	967.6	937.7	905.1	882.3	852.7	824.4	789.9	762.0	737.8	731.2
17.5°	940.7	903.1	873.0	834.9	795.7	746.0	713.2	693.2	676.4	663.7	654.1
20°	901.4	863.2	831.1	773.6	720.8	687.1	663.0	647.6	630.1	616.4	608.9
22.5°	860.1	820.2	776.5	712.4	671.2	644.2	622.6	605.0	593.1	582.4	575.6
25°	801.5	757.8	685.8	641.7	608.5	580.2	565.2	554.3	541.8	527.3	520.7
27.5°	739.6	670.1	618.4	585.6	553.8	535.4	522.0	505.8	494.6	488.1	481.2
30°	693.3	623.9	583.5	547.7	525.2	504.8	489.0	479.9	469.0	457.8	453.2
32.5°	641.7	586.2	547.6	517.7	494.9	477.5	465.0	450.2	442.4	435.5	425.9
35°	577.6	535.7	500.3	476.1	454.4	440.3	425.7	417.0	402.8	397.1	393.3
37.5°	523.3	486.9	460.6	435.0	417.9	402.3	393.4	379.4	373.3	365.3	357.3
40°	492.8	457.0	431.5	410.7	391.6	379.9	368.8	357.5	348.3	344.6	335.0
42.5°	461.5	432.4	406.9	384.1	371.3	359.0	344.8	336.6	327.0	321.0	315.0
45°	418.2	392.5	370.8	352.0	337.9	325.1	315.8	302.1	296.8	284.6	279.6
47.5°	380.3	356.3	335.7	317.9	304.0	295.6	282.3	271.5	262.9	255.4	249.1
50°	353.4	333.4	313.4	297.6	285.1	273.0	259.3	253.9	240.5	236.8	233.1
52.5°	328.7	309.7	291.4	275.9	263.4	251.7	239.6	232.5	223.6	219.8	217.1
55°	294.2	275.9	258.4	244.7	232.2	220.1	212.6	203.9	199.7	196.8	193.6
57.5°	259.6	243.1	229.8	215.8	203.3	193.7	185.0	179.8	175.5	171.6	167.6
60°	237.7	221.8	209.8	196.8	183.9	176.0	169.4	163.1	158.2	152.3	150.7
62.5°	214.3	200.5	189.5	176.8	165.7	158.4	152.1	146.2	140.1	131.7	129.3
65°	182.3	171.5	159.8	149.4	139.4	132.3	123.2	116.5	114.1	113.2	112.8
67.5°	153.4	143.1	133.1	122.5	113.3	106.8	102.2	101.1	99.4	98.9	97.8
70°	134.0	124.4	114.5	104.4	95.7	94.5	92.8	91.2	89.0	88.2	87.4
72.5°	116.7	106.8	96.8	88.8	85.0	83.5	81.9	80.1	78.8	77.9	77.4
75°	89.4	80.3	73.7	70.8	68.6	67.4	64.9	63.7	62.9	61.6	61.1
77.5°	64.4	59.3	56.2	54.4	52.2	50.9	49.4	48.2	47.3	47.0	46.4
80°	49.1	46.6	44.5	42.1	41.2	39.5	39.1	37.9	38.3	37.0	37.0
82.5°	38.2	35.0	33.2	32.0	31.2	29.9	29.4	28.9	28.9	28.0	28.0
85°	19.6	18.8	17.9	17.0	17.0	15.8	16.2	15.8	15.8	15.0	14.6
87.5°	7.4	7.4	7.2	7.8	8.4	8.2	8.1	7.7	7.4	7.7	7.4
90°	5.5	7.0	9.3	12.6	15.3	15.8	15.3	14.8	13.9	14.8	15.3
92.5°	16.7	21.1	31.6	46.4	59.6	60.4	51.0	40.5	34.8	30.9	28.0
95°	34.4	45.6	66.9	107.4	161.3	182.3	159.5	121.8	93.4	73.9	63.7
97.5°	48.8	61.5	88.4	144.7	234.3	311.1	326.4	284.3	232.6	182.3	148.7
100°	58.1	71.2	95.8	152.5	252.9	367.3	434.2	424.5	366.9	303.1	246.9
102.5°	66.7	79.7	102.5	152.9	245.9	369.2	474.4	516.4	503.4	456.8	397.1
105°	79.0	92.0	113.9	155.3	232.0	344.5	468.2	564.9	617.4	623.5	608.1
107.5°	91.3	104.4	125.6	161.7	225.1	318.1	427.4	529.9	609.1	657.5	680.0
110°	99.5	113.0	133.5	166.9	223.6	305.5	401.7	499.9	583.0	642.5	680.7



TEST NUMBER: P331683-930

CATALOG NUMBER: SA2XXRDIP-C675D530U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	107.3	121.2	140.9	172.5	224.0	297.3	383.8	472.3	552.2	615.8	659.5
115°	119.9	132.5	152.5	180.8	226.0	288.3	361.7	438.5	510.1	571.0	618.9
117.5°	131.7	144.7	163.2	189.8	229.3	283.9	347.8	412.9	475.8	531.1	576.0
120°	139.5	152.5	170.6	195.8	231.5	281.3	340.4	400.3	458.0	507.3	549.6
122.5°	147.3	160.7	177.7	201.0	234.2	279.8	334.0	390.3	443.1	489.8	528.0
125°	158.6	171.5	188.3	209.2	238.1	277.1	325.0	375.7	423.5	464.5	499.4
127.5°	168.5	181.9	198.2	217.0	242.1	275.6	316.7	361.3	404.6	443.2	475.4
130°	174.8	187.8	204.2	221.8	245.0	274.8	311.0	352.0	392.0	428.7	459.3
132.5°	180.8	193.8	209.3	226.7	248.0	274.4	306.6	343.1	380.1	413.8	442.6
135°	188.7	201.8	216.7	232.9	251.5	273.9	300.4	330.6	361.3	392.0	418.0
137.5°	195.8	207.9	222.7	237.7	254.7	273.8	296.0	320.7	346.3	370.6	393.4
140°	199.9	212.1	226.0	240.4	256.2	273.4	293.4	314.3	336.6	358.0	378.5
142.5°	203.7	215.0	228.6	242.6	257.3	273.4	290.8	309.1	328.1	346.5	363.6
145°	209.7	219.9	232.4	245.5	258.5	272.5	287.3	301.7	317.1	331.5	345.0
147.5°	214.7	223.8	235.6	247.1	258.9	270.8	283.8	296.1	308.2	319.4	329.3
150°	218.1	226.4	237.1	247.9	258.5	269.7	280.9	292.0	302.2	312.0	320.3
152.5°	221.4	229.0	238.6	248.2	257.8	267.8	278.3	287.9	297.4	305.7	312.9
155°	226.0	232.9	240.8	248.7	256.7	264.6	273.4	282.3	289.7	296.6	301.7
157.5°	229.9	235.7	242.4	248.7	254.5	261.2	268.8	275.7	281.8	287.7	291.7
160°	232.4	237.6	243.2	248.7	253.4	259.0	265.5	271.5	276.6	281.8	285.0
162.5°	234.7	238.7	243.5	248.3	252.3	257.1	262.5	267.4	271.8	276.2	278.7
165°	237.1	239.9	244.1	247.4	250.1	253.4	257.6	261.3	264.6	267.8	269.7
167.5°	239.2	240.9	244.0	246.7	248.0	250.1	252.7	255.4	258.0	260.2	261.9
170°	239.9	241.3	243.6	246.0	246.9	248.3	250.1	252.5	253.9	255.8	256.7
172.5°	240.7	241.7	243.3	244.8	245.4	246.1	247.5	249.2	250.1	251.6	252.2
175°	241.3	241.7	242.7	243.6	243.2	243.6	244.1	245.5	246.0	246.5	246.9
177.5°	241.7	241.7	242.1	242.9	242.1	241.7	242.1	242.9	242.9	243.3	243.3
180°	241.7	241.7	241.7	241.7	241.7	241.7	241.7	241.7	241.7	241.7	241.7



TEST NUMBER: P331683-930

CATALOG NUMBER: SA2XXRDIP-C675D530U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8
2.5°	1150.1	1150.8	1149.8	1150.5	1149.8	1150.8	1150.1	1153.8	1154.5	1155.1	1154.5
5°	1071.6	1066.7	1065.8	1064.5	1065.8	1066.7	1071.6	1073.7	1075.4	1078.7	1084.5
7.5°	978.0	977.1	975.1	972.2	975.1	977.1	978.0	985.0	990.8	997.2	1009.1
10°	917.6	915.6	915.2	912.2	915.2	915.6	917.6	926.8	933.4	942.6	958.9
12.5°	847.1	833.6	832.3	825.0	832.3	833.6	847.1	858.9	876.9	885.7	902.9
15°	721.2	718.8	710.4	705.0	710.4	718.8	721.2	731.2	737.8	762.0	789.9
17.5°	649.3	641.2	638.5	637.4	638.5	641.2	649.3	654.1	663.7	676.4	693.2
20°	603.0	595.6	594.3	593.5	594.3	595.6	603.0	608.9	616.4	630.1	647.6
22.5°	571.0	563.2	560.0	557.5	560.0	563.2	571.0	575.6	582.4	593.1	605.0
25°	516.5	513.6	511.9	511.0	511.9	513.6	516.5	520.7	527.3	541.8	554.3
27.5°	473.8	467.3	466.1	464.0	466.1	467.3	473.8	481.2	488.1	494.6	505.8
30°	449.5	447.4	444.5	442.0	444.5	447.4	449.5	453.2	457.8	469.0	479.9
32.5°	420.9	419.1	416.5	415.3	416.5	419.1	420.9	425.9	435.5	442.4	450.2
35°	389.1	383.3	380.8	377.1	380.8	383.3	389.1	393.3	397.1	402.8	417.0
37.5°	355.6	352.5	349.0	350.3	349.0	352.5	355.6	357.3	365.3	373.3	379.4
40°	329.6	327.5	326.7	326.3	326.7	327.5	329.6	335.0	344.6	348.3	357.5
42.5°	309.0	303.2	301.1	301.0	301.1	303.2	309.0	315.0	321.0	327.0	336.6
45°	277.6	272.1	268.4	268.9	268.4	272.1	277.6	279.6	284.6	296.8	302.1
47.5°	245.5	245.3	243.0	243.7	243.0	245.3	245.5	249.1	255.4	262.9	271.5
50°	230.2	227.6	226.0	226.4	226.0	227.6	230.2	233.1	236.8	240.5	253.9
52.5°	215.5	213.4	212.0	213.8	212.0	213.4	215.5	217.1	219.8	223.6	232.5
55°	191.4	188.9	188.5	188.1	188.5	188.9	191.4	193.6	196.8	199.7	203.9
57.5°	164.5	162.9	160.4	159.3	160.4	162.9	164.5	167.6	171.6	175.5	179.8
60°	145.2	141.9	137.8	137.3	137.8	141.9	145.2	150.7	152.3	158.2	163.1
62.5°	127.6	126.9	126.1	126.0	126.1	126.9	127.6	129.3	131.7	140.1	146.2
65°	111.9	111.5	111.9	112.3	111.9	111.5	111.9	112.8	113.2	114.1	116.5
67.5°	97.6	96.8	96.0	96.4	96.0	96.8	97.6	97.8	98.9	99.4	101.1
70°	86.6	86.2	85.8	85.8	85.8	86.2	86.6	87.4	88.2	89.0	91.2
72.5°	75.9	75.8	75.4	75.1	75.4	75.8	75.9	77.4	77.9	78.8	80.1
75°	60.7	59.9	59.9	59.9	59.9	59.9	60.7	61.1	61.6	62.9	63.7
77.5°	46.3	45.9	45.4	45.1	45.4	45.9	46.3	46.4	47.0	47.3	48.2
80°	36.6	36.2	35.8	35.8	35.8	36.2	36.6	37.0	37.0	38.3	37.9
82.5°	28.0	27.6	27.5	27.1	27.5	27.6	28.0	28.0	28.0	28.9	28.9
85°	15.0	15.4	15.0	15.8	15.0	15.4	15.0	14.6	15.0	15.8	15.8
87.5°	7.4	7.1	7.4	7.1	7.4	7.1	7.4	7.4	7.7	7.4	7.7
90°	15.3	15.3	15.3	15.3	15.3	15.3	15.3	15.3	14.8	13.9	14.8
92.5°	27.6	26.2	26.5	25.8	26.5	26.2	27.6	28.0	30.9	34.8	40.5
95°	57.6	54.0	52.5	53.0	52.5	54.0	57.6	63.7	73.9	93.4	121.8
97.5°	126.5	115.0	108.3	104.4	108.3	115.0	126.5	148.7	182.3	232.6	284.3
100°	208.3	188.3	174.8	166.5	174.8	188.3	208.3	246.9	303.1	366.9	424.5
102.5°	355.2	321.1	304.3	292.9	304.3	321.1	355.2	397.1	456.8	503.4	516.4
105°	579.4	550.5	530.5	524.0	530.5	550.5	579.4	608.1	623.5	617.4	564.9
107.5°	683.5	682.0	678.0	669.4	678.0	682.0	683.5	680.0	657.5	609.1	529.9
110°	700.7	709.6	713.7	713.2	713.7	709.6	700.7	680.7	642.5	583.0	499.9



TEST NUMBER: P331683-930

CATALOG NUMBER: SA2XXRDIP-C675D530U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	687.3	702.1	710.0	712.5	710.0	702.1	687.3	659.5	615.8	552.2	472.3
115°	651.8	673.3	685.3	689.5	685.3	673.3	651.8	618.9	571.0	510.1	438.5
117.5°	609.7	632.3	645.0	648.5	645.0	632.3	609.7	576.0	531.1	475.8	412.9
120°	582.1	604.0	617.4	622.1	617.4	604.0	582.1	549.6	507.3	458.0	400.3
122.5°	557.2	578.7	590.7	594.6	590.7	578.7	557.2	528.0	489.8	443.1	390.3
125°	526.4	544.0	555.6	559.4	555.6	544.0	526.4	499.4	464.5	423.5	375.7
127.5°	498.9	515.4	525.5	528.5	525.5	515.4	498.9	475.4	443.2	404.6	361.3
130°	482.2	498.0	507.3	510.9	507.3	498.0	482.2	459.3	428.7	392.0	352.0
132.5°	465.0	480.9	489.4	492.8	489.4	480.9	465.0	442.6	413.8	380.1	343.1
135°	438.0	453.3	461.7	463.6	461.7	453.3	438.0	418.0	392.0	361.3	330.6
137.5°	411.6	424.8	432.1	434.9	432.1	424.8	411.6	393.4	370.6	346.3	320.7
140°	393.4	405.4	412.4	415.2	412.4	405.4	393.4	378.5	358.0	336.6	314.3
142.5°	377.7	388.7	394.9	395.5	394.9	388.7	377.7	363.6	346.5	328.1	309.1
145°	356.1	364.0	368.7	370.1	368.7	364.0	356.1	345.0	331.5	317.1	301.7
147.5°	338.5	344.8	348.0	348.8	348.0	344.8	338.5	329.3	319.4	308.2	296.1
150°	327.3	332.9	335.7	336.1	335.7	332.9	327.3	320.3	312.0	302.2	292.0
152.5°	318.4	323.3	325.3	325.4	325.3	323.3	318.4	312.9	305.7	297.4	287.9
155°	306.9	310.1	312.0	311.0	312.0	310.1	306.9	301.7	296.6	289.7	282.3
157.5°	295.3	298.1	298.9	298.9	298.9	298.1	295.3	291.7	287.7	281.8	275.7
160°	288.3	290.6	291.1	291.1	291.1	290.6	288.3	285.0	281.8	276.6	271.5
162.5°	281.9	283.6	284.0	283.6	284.0	283.6	281.9	278.7	276.2	271.8	267.4
165°	271.5	273.4	273.4	273.0	273.4	273.4	271.5	269.7	267.8	264.6	261.3
167.5°	262.7	263.7	263.7	263.1	263.7	263.7	262.7	261.9	260.2	258.0	255.4
170°	257.1	258.5	258.0	257.1	258.0	258.5	257.1	256.7	255.8	253.9	252.5
172.5°	252.7	253.3	252.8	252.3	252.8	253.3	252.7	252.2	251.6	250.1	249.2
175°	246.9	247.4	246.9	246.0	246.9	247.4	246.9	246.9	246.5	246.0	245.5
177.5°	243.3	243.3	242.9	242.1	242.9	243.3	243.3	243.3	243.3	242.9	242.9
180°	241.7	241.7	241.7	241.7	241.7	241.7	241.7	241.7	241.7	241.7	241.7



TEST NUMBER: P331683-930

CATALOG NUMBER: SA2XXRDIP-C675D530U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8
2.5°	1151.8	1156.4	1163.4	1167.4	1174.1	1178.4	1180.8	1185.1	1187.4	1195.7	1204.4
5°	1087.4	1094.1	1105.8	1116.6	1128.2	1140.3	1149.1	1159.0	1168.2	1184.0	1200.7
7.5°	1013.7	1023.0	1041.0	1058.3	1078.6	1095.6	1110.7	1127.7	1143.0	1165.6	1189.3
10°	958.5	974.7	998.4	1014.6	1041.3	1058.3	1082.1	1100.7	1122.0	1151.9	1178.6
12.5°	910.9	930.4	949.4	972.0	996.0	1024.3	1050.4	1074.5	1099.7	1130.7	1162.0
15°	824.4	852.7	882.3	905.1	937.7	967.6	998.0	1030.5	1061.3	1098.3	1139.1
17.5°	713.2	746.0	795.7	834.9	873.0	903.1	940.7	980.0	1016.3	1060.9	1106.4
20°	663.0	687.1	720.8	773.6	831.1	863.2	901.4	944.7	986.3	1035.0	1083.7
22.5°	622.6	644.2	671.2	712.4	776.5	820.2	860.1	904.1	952.4	1002.1	1056.1
25°	565.2	580.2	608.5	641.7	685.8	757.8	801.5	845.6	898.1	951.4	1012.9
27.5°	522.0	535.4	553.8	585.6	618.4	670.1	739.6	787.7	840.0	899.9	963.8
30°	489.0	504.8	525.2	547.7	583.5	623.9	693.3	749.1	800.7	862.3	930.6
32.5°	465.0	477.5	494.9	517.7	547.6	586.2	641.7	709.5	759.8	824.7	895.9
35°	425.7	440.3	454.4	476.1	500.3	535.7	577.6	650.0	700.0	764.1	835.7
37.5°	393.4	402.3	417.9	435.0	460.6	486.9	523.3	588.3	642.3	705.2	778.5
40°	368.8	379.9	391.6	410.7	431.5	457.0	492.8	541.0	603.0	664.6	736.2
42.5°	344.8	359.0	371.3	384.1	406.9	432.4	461.5	502.4	565.7	624.0	693.6
45°	315.8	325.1	337.9	352.0	370.8	392.5	418.2	454.0	514.8	565.2	630.5
47.5°	282.3	295.6	304.0	317.9	335.7	356.3	380.3	411.2	460.5	507.7	568.3
50°	259.3	273.0	285.1	297.6	313.4	333.4	353.4	383.3	422.8	472.4	529.0
52.5°	239.6	251.7	263.4	275.9	291.4	309.7	328.7	355.0	388.9	434.4	489.3
55°	212.6	220.1	232.2	244.7	258.4	275.9	294.2	316.3	345.4	383.7	428.3
57.5°	185.0	193.7	203.3	215.8	229.8	243.1	259.6	279.6	302.6	337.2	375.3
60°	169.4	176.0	183.9	196.8	209.8	221.8	237.7	254.3	275.9	305.9	338.3
62.5°	152.1	158.4	165.7	176.8	189.5	200.5	214.3	232.0	250.3	277.6	306.1
65°	123.2	132.3	139.4	149.4	159.8	171.5	182.3	196.4	212.6	234.3	259.7
67.5°	102.2	106.8	113.3	122.5	133.1	143.1	153.4	164.4	178.5	195.2	215.3
70°	92.8	94.5	95.7	104.4	114.5	124.4	134.0	144.4	156.5	170.2	187.7
72.5°	81.9	83.5	85.0	88.8	96.8	106.8	116.7	124.4	135.8	147.2	161.4
75°	64.9	67.4	68.6	70.8	73.7	80.3	89.4	96.9	103.6	112.3	123.6
77.5°	49.4	50.9	52.2	54.4	56.2	59.3	64.4	71.2	77.4	82.5	90.3
80°	39.1	39.5	41.2	42.1	44.5	46.6	49.1	54.5	60.7	62.9	68.2
82.5°	29.4	29.9	31.2	32.0	33.2	35.0	38.2	39.5	44.4	47.2	50.6
85°	16.2	15.8	17.0	17.0	17.9	18.8	19.6	21.6	22.9	26.3	27.1
87.5°	8.1	8.2	8.4	7.8	7.2	7.4	7.4	7.6	8.1	8.7	9.8
90°	15.3	15.8	15.3	12.6	9.3	7.0	5.5	4.6	3.8	1.9	0.5
92.5°	51.0	60.4	59.6	46.4	31.6	21.1	16.7	13.6	11.5	8.2	5.7
95°	159.5	182.3	161.3	107.4	66.9	45.6	34.4	27.0	22.7	18.1	16.3
97.5°	326.4	311.1	234.3	144.7	88.4	61.5	48.8	40.3	33.9	29.0	26.5
100°	434.2	367.3	252.9	152.5	95.8	71.2	58.1	48.8	41.4	37.2	35.8
102.5°	474.4	369.2	245.9	152.9	102.5	79.7	66.7	57.0	49.6	45.4	44.4
105°	468.2	344.5	232.0	155.3	113.9	92.0	79.0	68.8	61.8	58.6	56.7
107.5°	427.4	318.1	225.1	161.7	125.6	104.4	91.3	81.2	74.8	71.6	70.1
110°	401.7	305.5	223.6	166.9	133.5	113.0	99.5	89.8	83.7	80.9	79.0



TEST NUMBER: P331683-930

CATALOG NUMBER: SA2XXRDIP-C675D530U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	383.8	297.3	224.0	172.5	140.9	121.2	107.3	97.9	92.2	89.1	87.2
115°	361.7	288.3	226.0	180.8	152.5	132.5	119.9	110.6	105.1	102.3	100.0
117.5°	347.8	283.9	229.3	189.8	163.2	144.7	131.7	122.8	117.8	115.0	113.2
120°	340.4	281.3	231.5	195.8	170.6	152.5	139.5	130.2	126.0	123.2	121.3
122.5°	334.0	279.8	234.2	201.0	177.7	160.7	147.3	138.0	133.5	130.7	129.1
125°	325.0	277.1	238.1	209.2	188.3	171.5	158.6	149.3	143.7	140.9	139.5
127.5°	316.7	275.6	242.1	217.0	198.2	181.9	168.5	159.6	153.4	149.5	147.7
130°	311.0	274.8	245.0	221.8	204.2	187.8	174.8	165.5	159.0	154.3	152.5
132.5°	306.6	274.4	248.0	226.7	209.3	193.8	180.8	171.1	164.2	159.2	156.9
135°	300.4	273.9	251.5	232.9	216.7	201.8	188.7	178.1	171.1	165.5	163.6
137.5°	296.0	273.8	254.7	237.7	222.7	207.9	195.8	185.2	177.8	172.2	170.0
140°	293.4	273.4	256.2	240.4	226.0	212.1	199.9	189.7	182.3	176.7	174.8
142.5°	290.8	273.4	257.3	242.6	228.6	215.0	203.7	193.8	186.4	181.2	179.7
145°	287.3	272.5	258.5	245.5	232.4	219.9	209.7	200.4	193.4	188.7	186.9
147.5°	283.8	270.8	258.9	247.1	235.6	223.8	214.7	207.0	200.6	196.1	194.7
150°	280.9	269.7	258.5	247.9	237.1	226.4	218.1	211.1	205.0	201.3	199.9
152.5°	278.3	267.8	257.8	248.2	238.6	229.0	221.4	214.8	209.5	205.8	205.1
155°	273.4	264.6	256.7	248.7	240.8	232.9	226.0	220.9	215.7	213.0	212.5
157.5°	268.8	261.2	254.5	248.7	242.4	235.7	229.9	225.8	221.4	219.1	218.6
160°	265.5	259.0	253.4	248.7	243.2	237.6	232.4	228.8	225.0	223.1	222.7
162.5°	262.5	257.1	252.3	248.3	243.5	238.7	234.7	231.4	228.4	226.5	226.8
165°	257.6	253.4	250.1	247.4	244.1	239.9	237.1	234.8	232.0	231.1	231.5
167.5°	252.7	250.1	248.0	246.7	244.0	240.9	239.2	237.5	235.7	234.9	235.5
170°	250.1	248.3	246.9	246.0	243.6	241.3	239.9	239.0	237.6	237.1	238.1
172.5°	247.5	246.1	245.4	244.8	243.3	241.7	240.7	240.1	238.7	239.0	239.5
175°	244.1	243.6	243.2	243.6	242.7	241.7	241.3	241.3	240.4	240.8	241.3
177.5°	242.1	241.7	242.1	242.9	242.1	241.7	241.7	241.7	241.0	241.4	242.1
180°	241.7	241.7	241.7	241.7	241.7	241.7	241.7	241.7	241.7	241.7	241.7



TEST NUMBER: P331683-930

CATALOG NUMBER: SA2XXRDIP-C675D530U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8
2.5°	1204.8	1205.7	1212.4	1215.4	1221.4	1223.7	1226.4	1225.7	1225.7	1227.0	1236.4
5°	1207.3	1215.6	1228.1	1240.2	1251.8	1261.8	1268.5	1275.1	1277.7	1289.7	1300.6
7.5°	1203.0	1218.3	1238.9	1257.4	1279.4	1296.7	1310.9	1323.9	1332.7	1350.2	1368.2
10°	1197.3	1219.0	1242.3	1266.0	1296.4	1319.2	1342.6	1360.5	1366.3	1392.5	1407.5
12.5°	1186.0	1215.0	1244.6	1275.3	1305.0	1336.6	1362.2	1380.1	1400.6	1424.2	1451.8
15°	1169.1	1202.3	1241.0	1280.6	1323.0	1361.3	1388.8	1420.0	1442.4	1468.3	1492.4
17.5°	1144.6	1187.5	1236.7	1282.5	1331.5	1372.7	1410.5	1440.5	1456.3	1471.0	1474.6
20°	1125.4	1171.5	1229.4	1283.4	1332.6	1380.1	1417.5	1442.4	1446.6	1447.0	1425.0
22.5°	1104.3	1156.5	1217.1	1272.5	1331.2	1384.1	1413.2	1423.8	1407.3	1379.1	1336.4
25°	1065.8	1126.2	1196.5	1259.7	1323.9	1373.8	1383.8	1365.1	1307.2	1246.4	1169.5
27.5°	1024.0	1091.8	1167.3	1237.6	1305.9	1336.8	1315.2	1247.7	1143.5	1053.0	943.2
30°	993.4	1069.6	1143.6	1222.3	1285.6	1298.9	1249.4	1149.9	1028.3	891.9	782.4
32.5°	958.5	1038.3	1119.7	1201.0	1253.9	1241.0	1159.1	1036.7	894.2	760.0	656.6
35°	908.5	990.9	1078.7	1160.3	1194.0	1137.8	1015.5	856.1	710.4	585.1	514.0
37.5°	850.8	940.5	1031.8	1106.8	1104.3	1010.7	844.1	679.6	557.1	483.0	432.4
40°	809.8	900.6	999.2	1062.5	1035.4	913.5	732.9	577.6	488.2	429.1	392.0
42.5°	770.6	861.6	959.6	1009.9	962.9	812.9	633.0	511.4	437.6	391.4	361.4
45°	703.8	799.9	890.6	918.5	834.5	669.2	511.9	423.6	374.5	340.5	319.6
47.5°	638.4	733.0	815.8	816.3	702.5	542.7	431.8	366.6	324.7	298.3	283.2
50°	598.4	688.4	757.8	747.1	618.0	482.7	386.2	330.0	295.1	274.7	258.9
52.5°	553.5	640.7	700.9	670.1	546.4	424.9	345.3	298.1	269.1	251.4	237.3
55°	488.2	565.6	608.1	561.4	445.7	353.4	291.7	254.7	233.1	218.1	206.0
57.5°	424.0	487.9	514.5	460.3	367.1	293.0	246.8	219.0	197.5	186.8	180.5
60°	383.7	438.2	457.0	397.1	319.2	256.3	218.5	192.7	176.8	169.8	163.5
62.5°	344.1	388.7	396.4	341.4	278.3	224.4	191.8	170.1	159.6	152.8	146.9
65°	285.5	317.6	313.8	269.7	220.1	178.1	154.4	141.0	133.1	123.6	113.2
67.5°	235.1	254.6	242.8	209.8	168.0	138.4	122.9	112.8	103.1	94.0	91.6
70°	203.1	214.3	201.9	171.5	137.8	116.1	103.6	91.6	85.8	83.6	79.9
72.5°	172.4	176.3	162.9	136.8	112.1	96.1	84.0	77.2	74.1	72.3	70.0
75°	129.5	126.5	114.9	94.5	77.9	67.0	63.3	60.7	58.7	57.0	55.8
77.5°	90.9	86.7	76.2	62.9	54.2	49.0	46.8	45.4	44.4	43.6	42.4
80°	68.2	65.3	55.0	44.9	41.2	38.7	37.4	35.8	35.8	35.0	33.7
82.5°	50.0	46.7	37.6	32.9	30.9	29.4	28.5	27.5	27.1	27.3	26.4
85°	26.3	21.2	18.8	17.9	16.6	15.8	16.2	15.4	15.4	15.4	15.0
87.5°	8.4	7.1	6.9	6.8	7.4	7.8	8.2	8.7	9.1	8.7	9.0
90°	1.9	3.8	4.6	5.5	7.0	9.3	12.6	15.3	15.8	15.3	14.8
92.5°	8.2	11.5	13.6	16.7	21.1	31.6	46.4	59.6	60.4	51.0	40.5
95°	18.1	22.7	27.0	34.4	45.6	66.9	107.4	161.3	182.3	159.5	121.8
97.5°	29.0	33.9	40.3	48.8	61.5	88.4	144.7	234.3	311.1	326.4	284.3
100°	37.2	41.4	48.8	58.1	71.2	95.8	152.5	252.9	367.3	434.2	424.5
102.5°	45.4	49.6	57.0	66.7	79.7	102.5	152.9	245.9	369.2	474.4	516.4
105°	58.6	61.8	68.8	79.0	92.0	113.9	155.3	232.0	344.5	468.2	564.9
107.5°	71.6	74.8	81.2	91.3	104.4	125.6	161.7	225.1	318.1	427.4	529.9
110°	80.9	83.7	89.8	99.5	113.0	133.5	166.9	223.6	305.5	401.7	499.9





TEST NUMBER: P331683-930

CATALOG NUMBER: SA2XXRDIP-C675D530U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	89.1	92.2	97.9	107.3	121.2	140.9	172.5	224.0	297.3	383.8	472.3
115°	102.3	105.1	110.6	119.9	132.5	152.5	180.8	226.0	288.3	361.7	438.5
117.5°	115.0	117.8	122.8	131.7	144.7	163.2	189.8	229.3	283.9	347.8	412.9
120°	123.2	126.0	130.2	139.5	152.5	170.6	195.8	231.5	281.3	340.4	400.3
122.5°	130.7	133.5	138.0	147.3	160.7	177.7	201.0	234.2	279.8	334.0	390.3
125°	140.9	143.7	149.3	158.6	171.5	188.3	209.2	238.1	277.1	325.0	375.7
127.5°	149.5	153.4	159.6	168.5	181.9	198.2	217.0	242.1	275.6	316.7	361.3
130°	154.3	159.0	165.5	174.8	187.8	204.2	221.8	245.0	274.8	311.0	352.0
132.5°	159.2	164.2	171.1	180.8	193.8	209.3	226.7	248.0	274.4	306.6	343.1
135°	165.5	171.1	178.1	188.7	201.8	216.7	232.9	251.5	273.9	300.4	330.6
137.5°	172.2	177.8	185.2	195.8	207.9	222.7	237.7	254.7	273.8	296.0	320.7
140°	176.7	182.3	189.7	199.9	212.1	226.0	240.4	256.2	273.4	293.4	314.3
142.5°	181.2	186.4	193.8	203.7	215.0	228.6	242.6	257.3	273.4	290.8	309.1
145°	188.7	193.4	200.4	209.7	219.9	232.4	245.5	258.5	272.5	287.3	301.7
147.5°	196.1	200.6	207.0	214.7	223.8	235.6	247.1	258.9	270.8	283.8	296.1
150°	201.3	205.0	211.1	218.1	226.4	237.1	247.9	258.5	269.7	280.9	292.0
152.5°	205.8	209.5	214.8	221.4	229.0	238.6	248.2	257.8	267.8	278.3	287.9
155°	213.0	215.7	220.9	226.0	232.9	240.8	248.7	256.7	264.6	273.4	282.3
157.5°	219.1	221.4	225.8	229.9	235.7	242.4	248.7	254.5	261.2	268.8	275.7
160°	223.1	225.0	228.8	232.4	237.6	243.2	248.7	253.4	259.0	265.5	271.5
162.5°	226.5	228.4	231.4	234.7	238.7	243.5	248.3	252.3	257.1	262.5	267.4
165°	231.1	232.0	234.8	237.1	239.9	244.1	247.4	250.1	253.4	257.6	261.3
167.5°	234.9	235.7	237.5	239.2	240.9	244.0	246.7	248.0	250.1	252.7	255.4
170°	237.1	237.6	239.0	239.9	241.3	243.6	246.0	246.9	248.3	250.1	252.5
172.5°	239.0	238.7	240.1	240.7	241.7	243.3	244.8	245.4	246.1	247.5	249.2
175°	240.8	240.4	241.3	241.3	241.7	242.7	243.6	243.2	243.6	244.1	245.5
177.5°	241.4	241.0	241.7	241.7	241.7	242.1	242.9	242.1	241.7	242.1	242.9
180°	241.7	241.7	241.7	241.7	241.7	241.7	241.7	241.7	241.7	241.7	241.7



TEST NUMBER: P331683-930  
 CATALOG NUMBER: SA2XXRDIP-C675D530U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8	1197.8
2.5°	1239.7	1244.0	1246.0	1246.0	1248.4	1247.3	1246.3
5°	1310.9	1318.8	1320.5	1328.0	1333.4	1331.7	1332.6
7.5°	1381.8	1394.5	1407.0	1412.8	1413.7	1417.1	1418.3
10°	1425.4	1435.8	1455.4	1452.5	1467.0	1475.4	1461.6
12.5°	1467.4	1481.4	1494.9	1498.7	1507.0	1509.6	1504.2
15°	1505.3	1512.8	1513.6	1511.6	1514.0	1512.0	1504.1
17.5°	1469.8	1457.7	1433.1	1421.4	1412.2	1398.5	1393.0
20°	1411.2	1375.4	1333.8	1317.2	1297.6	1259.3	1268.5
22.5°	1284.7	1243.9	1202.3	1153.7	1130.5	1094.2	1092.0
25°	1087.9	1017.6	940.1	886.1	854.4	818.2	802.4
27.5°	845.8	757.2	693.8	661.7	632.5	603.8	602.6
30°	686.6	620.1	571.0	543.6	525.6	513.6	516.1
32.5°	578.8	533.2	500.1	477.3	464.1	454.9	454.8
35°	473.2	442.0	420.8	411.2	401.6	394.9	395.3
37.5°	405.0	386.2	374.4	363.8	357.8	354.6	352.8
40°	370.0	354.6	345.4	339.2	334.2	329.6	328.8
42.5°	342.3	329.6	320.4	315.5	310.9	307.6	306.8
45°	303.8	293.4	285.1	279.6	277.6	274.7	274.7
47.5°	270.3	260.0	253.6	250.1	246.5	244.6	244.5
50°	247.6	239.7	233.9	231.8	228.9	227.6	227.2
52.5°	227.3	221.4	217.3	215.8	214.6	213.0	213.3
55°	199.7	196.4	194.8	193.6	191.4	188.9	190.6
57.5°	176.5	173.7	169.3	165.3	163.4	161.7	162.3
60°	160.2	154.4	148.5	144.0	142.8	139.0	139.0
62.5°	139.6	131.4	124.3	121.7	120.4	118.7	118.4
65°	107.4	104.0	102.4	100.7	99.9	99.9	99.1
67.5°	88.9	87.6	85.9	85.4	84.5	84.3	84.1
70°	78.7	77.0	76.1	75.7	74.9	75.3	74.1
72.5°	68.6	67.3	67.2	66.1	65.6	65.6	64.7
75°	54.1	54.1	53.6	53.2	52.4	52.0	52.4
77.5°	41.6	41.7	40.9	40.8	40.8	40.8	40.4
80°	33.3	33.7	33.3	32.9	32.4	32.9	32.4
82.5°	26.3	25.7	25.6	25.5	25.4	25.2	25.1
85°	15.0	15.4	15.0	14.6	14.6	14.6	15.0
87.5°	8.5	8.6	8.7	8.7	8.7	8.7	8.4
90°	13.9	14.8	15.3	15.3	15.3	15.3	15.3
92.5°	34.8	30.9	28.0	27.6	26.2	26.5	25.8
95°	93.4	73.9	63.7	57.6	54.0	52.5	53.0
97.5°	232.6	182.3	148.7	126.5	115.0	108.3	104.4
100°	366.9	303.1	246.9	208.3	188.3	174.8	166.5
102.5°	503.4	456.8	397.1	355.2	321.1	304.3	292.9
105°	617.4	623.5	608.1	579.4	550.5	530.5	524.0
107.5°	609.1	657.5	680.0	683.5	682.0	678.0	669.4
110°	583.0	642.5	680.7	700.7	709.6	713.7	713.2



TEST NUMBER: P331683-930

CATALOG NUMBER: SA2XXRDIP-C675D530U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	552.2	615.8	659.5	687.3	702.1	710.0	712.5
115°	510.1	571.0	618.9	651.8	673.3	685.3	689.5
117.5°	475.8	531.1	576.0	609.7	632.3	645.0	648.5
120°	458.0	507.3	549.6	582.1	604.0	617.4	622.1
122.5°	443.1	489.8	528.0	557.2	578.7	590.7	594.6
125°	423.5	464.5	499.4	526.4	544.0	555.6	559.4
127.5°	404.6	443.2	475.4	498.9	515.4	525.5	528.5
130°	392.0	428.7	459.3	482.2	498.0	507.3	510.9
132.5°	380.1	413.8	442.6	465.0	480.9	489.4	492.8
135°	361.3	392.0	418.0	438.0	453.3	461.7	463.6
137.5°	346.3	370.6	393.4	411.6	424.8	432.1	434.9
140°	336.6	358.0	378.5	393.4	405.4	412.4	415.2
142.5°	328.1	346.5	363.6	377.7	388.7	394.9	395.5
145°	317.1	331.5	345.0	356.1	364.0	368.7	370.1
147.5°	308.2	319.4	329.3	338.5	344.8	348.0	348.8
150°	302.2	312.0	320.3	327.3	332.9	335.7	336.1
152.5°	297.4	305.7	312.9	318.4	323.3	325.3	325.4
155°	289.7	296.6	301.7	306.9	310.1	312.0	311.0
157.5°	281.8	287.7	291.7	295.3	298.1	298.9	298.9
160°	276.6	281.8	285.0	288.3	290.6	291.1	291.1
162.5°	271.8	276.2	278.7	281.9	283.6	284.0	283.6
165°	264.6	267.8	269.7	271.5	273.4	273.4	273.0
167.5°	258.0	260.2	261.9	262.7	263.7	263.7	263.1
170°	253.9	255.8	256.7	257.1	258.5	258.0	257.1
172.5°	250.1	251.6	252.2	252.7	253.3	252.8	252.3
175°	246.0	246.5	246.9	246.9	247.4	246.9	246.0
177.5°	242.9	243.3	243.3	243.3	243.3	242.9	242.1
180°	241.7	241.7	241.7	241.7	241.7	241.7	241.7

(END OF REPORT)