

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331690-930

Luminaire Tested: **SA2XXRDIP-C675D725U930-4F0-1E-UDD-F**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331690-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXRDIP-C675D725U930-4F0-1E-UDD-F  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 725 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4255.5 lumens  
Efficiency: N/A  
Efficacy: 92.7 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 45.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331690-930  
CATALOG NUMBER: SA2XXRDIP-C675D725U930-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P331690-930

CATALOG NUMBER: SA2XXRDIP-C675D725U930-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	44				44
1	97	93	89	86	89	85	82	79	71	69	67	58	56	55	46	45	44				38	
2	89	82	76	71	81	75	70	66	63	59	56	51	49	47	41	39	38				33	
3	81	72	65	59	74	66	60	55	56	51	47	46	43	40	37	34	33				28	
4	74	64	56	51	68	59	52	47	50	45	41	41	37	35	33	30	28				25	
5	68	57	49	44	63	53	46	41	45	39	35	37	33	30	30	27	25				22	
6	63	51	44	38	58	48	41	36	40	35	31	34	30	27	27	24	22				19	
7	58	47	39	33	54	43	36	31	37	31	28	31	27	24	25	22	20				17	
8	54	42	35	30	50	39	33	28	34	28	25	28	24	21	23	20	18				16	
9	51	39	31	27	46	36	29	25	31	26	22	26	22	19	21	18	16				14	
10	47	36	29	24	43	33	27	23	28	23	20	24	20	17	20	17	15				13	

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	14849	14849	14849
5°	14906	14663	14744
10°	14791	14423	14300
15°	14621	13996	13593
20°	14387	13385	12713
25°	14145	12691	11863
30°	13811	11979	10769
35°	13484	11203	9810
40°	13156	10404	8701
45°	12771	9501	7695
50°	12376	8593	6712
55°	11972	7614	5762
60°	11502	6584	4782
65°	10968	5532	4359
70°	10334	4556	4008
75°	9551	4155	3737
80°	8433	3710	3403
85°	6632	2927	2927



TEST NUMBER: P331690-930

CATALOG NUMBER: SA2XXRDIP-C675D725U930-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	86.1	2.0
10°-20°	236.4	5.6
20°-30°	331.9	7.8
30°-40°	361.9	8.5
40°-50°	332.8	7.8
50°-60°	261.4	6.1
60°-70°	170.4	4.0
70°-80°	87.9	2.1
80°-90°	24.8	0.6
90°-100°	26.9	0.6
100°-110°	98.6	2.3
110°-120°	263.5	6.2
120°-130°	435.0	10.2
130°-140°	462.7	10.9
140°-150°	430.0	10.1
150°-160°	345.7	8.1
160°-170°	222.8	5.2
170°-180°	76.7	1.8
0°-30°	654.4	15.4
0°-40°	1016.3	23.9
0°-60°	1610.5	37.8
0°-90°	1893.5	44.5
90°-120°	389.0	9.1
90°-150°	1716.8	40.3
90°-180°	2362.0	55.5
0°-180°	4255.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	920	920	920	920	920	
5°	920	915	905	912	910	87
15°	875	864	837	822	813	246
25°	794	766	712	680	666	365
35°	684	640	568	518	498	428
45°	559	502	416	359	337	432
55°	425	359	270	222	205	380
65°	287	219	145	118	114	285
75°	153	96	67	61	60	162
85°	36	19	16	16	16	42
90°	1	7	12	14	16	3
95°	38	20	23	26	25	46
105°	177	185	36	42	44	189
115°	335	346	360	102	48	330
125°	474	482	493	497	499	423
135°	587	596	601	607	606	453
145°	681	681	690	694	691	426
155°	749	745	751	754	750	345
165°	790	786	788	792	788	223
175°	808	804	805	808	803	77
180°	806	806	806	806	806	



TEST NUMBER: P331690-930

CATALOG NUMBER: SA2XXRDIP-C675D725U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	919.7	919.7	919.7	919.7	919.7	919.7	919.7	919.7	919.7	919.7	919.7
2.5°	923.0	922.3	921.5	920.8	920.1	918.8	917.2	915.6	914.0	912.4	913.9
5°	919.7	918.8	917.9	916.9	916.0	914.4	911.9	909.5	907.1	904.7	906.4
7.5°	910.2	909.1	907.9	906.8	905.6	903.6	900.8	898.1	895.2	892.4	892.8
10°	902.2	900.9	899.6	898.3	897.0	894.5	890.8	887.1	883.5	879.7	879.2
12.5°	892.2	890.6	889.0	887.5	885.8	882.7	878.0	873.3	868.5	863.7	862.7
15°	874.7	872.7	870.7	868.6	866.6	862.4	856.1	849.9	843.6	837.3	833.8
17.5°	853.3	850.2	847.1	843.9	840.8	835.3	827.2	819.1	811.1	803.0	798.8
20°	837.3	833.6	829.9	826.2	822.5	816.0	806.7	797.5	788.3	779.0	774.4
22.5°	819.9	815.9	811.7	807.6	803.4	796.1	785.7	775.3	764.8	754.4	748.4
25°	794.0	788.1	782.2	776.2	770.4	761.2	749.1	736.9	724.6	712.4	704.8
27.5°	762.7	756.3	749.8	743.4	736.9	726.8	713.1	699.4	685.6	671.8	663.0
30°	740.8	733.7	726.7	719.7	712.7	701.7	686.9	672.1	657.3	642.5	633.1
32.5°	719.4	711.2	703.0	694.8	686.6	674.9	659.8	644.7	629.7	614.6	603.8
35°	684.1	674.7	665.3	655.8	646.5	633.6	617.3	601.0	584.7	568.4	556.8
37.5°	648.9	638.5	628.1	617.8	607.4	593.5	576.3	558.9	541.5	524.2	511.4
40°	624.2	613.1	602.0	590.9	579.8	565.3	547.4	529.5	511.5	493.6	480.5
42.5°	598.9	587.3	575.5	563.9	552.2	537.0	518.5	500.0	481.4	462.9	449.3
45°	559.3	546.9	534.5	522.1	509.7	493.8	474.4	455.0	435.5	416.1	403.0
47.5°	520.7	507.5	494.4	481.3	468.1	451.6	431.5	411.5	391.4	371.4	358.3
50°	492.7	479.6	466.4	453.3	440.2	423.5	403.1	382.8	362.4	342.1	329.3
52.5°	465.5	451.7	438.0	424.3	410.5	393.7	373.8	353.9	334.0	314.1	301.8
55°	425.3	410.9	396.5	382.0	367.6	350.4	330.4	310.5	290.5	270.5	259.4
57.5°	384.2	369.4	354.6	339.8	325.0	308.0	288.8	269.6	250.4	231.2	221.0
60°	356.2	341.4	326.6	311.9	297.0	280.1	261.1	242.0	223.0	203.9	194.4
62.5°	328.9	314.1	299.3	284.5	269.7	253.2	235.1	217.0	198.8	180.6	171.6
65°	287.1	272.1	257.1	242.2	227.2	211.4	194.8	178.1	161.4	144.8	138.5
67.5°	246.9	232.0	217.1	202.3	187.4	172.4	157.4	142.5	127.5	112.5	109.7
70°	218.9	204.5	190.0	175.6	161.2	147.6	134.9	122.1	109.3	96.5	94.7
72.5°	192.2	178.4	164.6	150.7	136.9	124.9	114.6	104.4	94.2	83.9	82.3
75°	153.1	140.2	127.3	114.3	101.3	91.7	85.4	79.2	72.9	66.6	65.3
77.5°	114.7	103.3	92.0	80.6	69.3	62.0	59.0	56.0	53.0	50.0	49.2
80°	90.7	81.3	71.8	62.5	53.0	47.4	45.5	43.6	41.8	39.9	39.2
82.5°	68.7	61.4	54.1	46.6	39.3	35.0	33.8	32.4	31.2	30.0	29.5
85°	35.8	31.9	28.0	24.1	20.2	18.0	17.4	17.0	16.4	15.8	15.8
87.5°	10.8	9.9	9.0	8.1	7.2	6.8	7.0	7.3	7.4	7.7	7.7
90°	0.6	2.0	3.4	4.9	6.3	7.5	8.6	9.6	10.6	11.7	12.3
92.5°	11.7	11.7	11.5	11.4	11.3	11.5	12.0	12.5	13.0	13.5	13.9
95°	37.9	33.7	29.4	25.1	20.8	19.1	20.1	21.0	21.9	22.7	23.4
97.5°	75.3	63.2	51.1	39.1	27.0	22.0	24.1	26.3	28.4	30.4	31.0
100°	103.2	85.4	67.8	50.0	32.2	24.5	26.7	28.9	31.1	33.3	34.2
102.5°	134.0	130.3	126.5	122.8	119.0	107.9	89.4	71.0	52.6	34.2	35.5
105°	177.3	181.2	185.1	189.0	192.8	177.1	141.7	106.3	70.9	35.5	37.0
107.5°	226.7	229.8	232.9	236.0	239.2	219.6	177.1	134.7	92.2	49.8	48.3
110°	258.4	261.1	263.8	266.5	269.2	251.8	214.4	177.0	139.5	102.1	89.1



TEST NUMBER: P331690-930

CATALOG NUMBER: SA2XXRDIP-C675D725U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	288.2	290.7	293.0	295.5	297.8	294.4	285.2	275.9	266.7	257.4	210.2
115°	335.3	337.5	339.7	341.9	344.1	346.9	350.1	353.4	356.6	359.9	299.9
117.5°	377.5	379.9	382.4	384.8	387.3	389.6	391.9	394.1	396.3	398.6	384.1
120°	408.2	410.2	412.1	414.1	416.0	418.2	420.5	422.8	425.2	427.5	429.0
122.5°	434.4	436.4	438.5	440.5	442.5	444.8	447.4	450.0	452.5	455.0	455.9
125°	474.2	475.8	477.5	479.2	480.9	483.0	485.4	487.9	490.3	492.8	493.7
127.5°	510.2	512.1	514.0	515.8	517.6	519.5	521.4	523.2	525.1	526.8	528.2
130°	533.0	535.2	537.2	539.2	541.4	543.1	544.5	545.9	547.4	548.8	550.2
132.5°	556.4	558.2	559.9	561.7	563.5	565.0	566.5	567.9	569.3	570.7	571.9
135°	586.7	588.8	590.8	593.0	595.0	596.6	597.8	598.9	600.1	601.3	602.6
137.5°	617.4	618.8	620.3	621.7	623.2	624.6	625.9	627.2	628.5	629.9	631.1
140°	637.5	638.5	639.5	640.6	641.6	642.9	644.2	645.7	647.1	648.6	649.7
142.5°	654.3	655.2	656.2	657.0	657.9	659.3	660.9	662.5	664.1	665.8	666.8
145°	680.6	680.4	680.4	680.2	680.1	681.1	683.3	685.5	687.7	689.9	690.9
147.5°	703.6	703.1	702.6	702.1	701.6	702.5	704.7	706.8	709.0	711.2	711.8
150°	718.5	717.6	716.7	715.8	714.9	715.5	717.5	719.6	721.7	723.7	724.6
152.5°	731.1	730.1	729.1	728.1	727.1	727.6	729.5	731.5	733.4	735.4	736.2
155°	749.4	748.3	747.1	745.9	744.8	744.9	746.5	748.0	749.6	751.1	752.0
157.5°	763.8	762.8	761.8	760.8	759.9	759.9	761.0	762.1	763.1	764.3	765.2
160°	772.2	771.4	770.6	769.8	769.1	769.1	769.8	770.6	771.4	772.2	773.0
162.5°	779.7	778.9	778.1	777.3	776.5	776.5	777.1	777.8	778.5	779.2	780.1
165°	789.7	788.9	788.1	787.3	786.5	786.4	786.8	787.2	787.5	787.9	788.8
167.5°	797.1	796.4	795.6	794.8	794.0	793.8	794.2	794.5	794.9	795.2	796.1
170°	801.4	800.5	799.8	799.0	798.3	797.9	798.3	798.5	798.7	799.0	799.9
172.5°	804.1	803.3	802.6	801.8	801.0	800.8	801.0	801.3	801.5	801.8	802.7
175°	807.7	806.8	805.9	805.0	804.1	803.8	804.0	804.3	804.5	804.9	805.8
177.5°	808.4	807.6	806.9	806.2	805.4	805.1	805.2	805.4	805.4	805.5	806.2
180°	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0



TEST NUMBER: P331690-930

CATALOG NUMBER: SA2XXRDIP-C675D725U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	919.7	919.7	919.7	919.7	919.7	919.7	919.7	919.7
2.5°	915.3	916.8	918.3	918.8	918.6	918.3	918.0	917.7
5°	908.0	909.7	911.3	911.9	911.3	910.8	910.3	909.7
7.5°	893.3	893.8	894.3	894.1	893.1	892.2	891.2	890.2
10°	878.6	878.1	877.5	876.7	875.5	874.5	873.3	872.2
12.5°	861.8	860.8	859.7	858.3	856.5	854.7	852.8	850.9
15°	830.3	826.7	823.2	820.5	818.7	816.8	815.0	813.2
17.5°	794.7	790.4	786.3	782.6	779.4	776.2	773.1	769.9
20°	769.8	765.2	760.5	756.2	752.1	748.0	744.0	739.9
22.5°	742.5	736.5	730.6	726.1	723.0	720.0	717.0	714.0
25°	697.2	689.7	682.1	676.9	674.2	671.4	668.6	665.9
27.5°	654.1	645.3	636.5	629.8	625.4	621.0	616.6	612.2
30°	623.7	614.2	604.8	597.6	592.6	587.6	582.6	577.6
32.5°	593.0	582.3	571.5	563.8	559.1	554.4	549.7	545.0
35°	545.2	533.5	521.9	514.0	509.9	505.8	501.8	497.7
37.5°	498.5	485.7	472.9	464.1	459.4	454.8	450.1	445.5
40°	467.2	454.1	441.0	432.0	427.2	422.4	417.6	412.8
42.5°	435.8	422.2	408.6	399.5	394.8	390.2	385.6	380.8
45°	389.9	376.7	363.6	354.8	350.4	345.9	341.5	337.0
47.5°	345.3	332.2	319.1	310.6	306.6	302.6	298.5	294.5
50°	316.6	303.8	291.1	282.7	278.8	274.9	271.1	267.2
52.5°	289.5	277.1	264.8	256.9	253.3	249.7	246.1	242.6
55°	248.3	237.2	226.1	218.8	215.3	211.7	208.2	204.7
57.5°	210.8	200.7	190.5	183.9	181.0	178.1	175.0	172.1
60°	185.1	175.6	166.2	160.0	157.0	154.1	151.1	148.1
62.5°	162.7	153.6	144.6	139.3	137.5	135.7	134.0	132.2
65°	132.2	126.0	119.7	116.3	115.7	115.1	114.5	114.1
67.5°	106.7	103.9	101.0	99.2	98.7	98.1	97.5	96.9
70°	92.9	91.0	89.1	87.9	87.1	86.3	85.6	84.9
72.5°	80.8	79.2	77.7	76.7	76.2	75.8	75.3	74.9
75°	64.0	62.7	61.4	60.7	60.5	60.3	60.1	59.9
77.5°	48.4	47.7	47.0	46.5	46.1	45.9	45.6	45.2
80°	38.5	37.7	37.0	36.6	36.6	36.6	36.6	36.6
82.5°	29.1	28.6	28.2	28.0	28.0	28.0	28.0	28.0
85°	15.8	15.8	15.8	15.8	15.8	15.8	15.8	15.8
87.5°	7.6	7.6	7.6	7.6	7.7	7.7	7.7	7.8
90°	13.0	13.6	14.3	14.7	15.0	15.2	15.5	15.7
92.5°	14.2	14.5	14.8	15.2	15.2	15.4	15.6	15.7
95°	24.1	24.7	25.4	25.6	25.4	25.4	25.2	25.1
97.5°	31.5	32.0	32.5	32.9	33.0	33.2	33.3	33.5
100°	35.3	36.4	37.4	38.1	38.3	38.6	38.8	39.1
102.5°	36.9	38.2	39.5	40.4	40.8	41.2	41.5	41.9
105°	38.4	39.9	41.3	42.2	42.8	43.3	43.8	44.4
107.5°	46.9	45.4	44.0	43.5	44.0	44.6	45.1	45.6
110°	76.1	63.2	50.2	44.0	44.5	45.0	45.6	46.1





TEST NUMBER: P331690-930

CATALOG NUMBER: SA2XXRDIP-C675D725U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	162.9	115.6	68.3	44.8	45.3	45.7	46.1	46.6
115°	239.9	179.9	119.8	85.1	75.8	66.4	57.2	47.9
117.5°	369.6	355.0	340.5	317.9	287.2	256.6	225.9	195.3
120°	430.6	432.2	433.7	425.7	408.2	390.8	373.2	355.8
122.5°	456.9	457.8	458.8	457.5	454.1	450.7	447.4	443.9
125°	494.6	495.5	496.4	497.1	497.5	497.9	498.2	498.6
127.5°	529.5	530.8	532.1	532.9	533.0	533.0	533.1	533.2
130°	551.6	553.1	554.5	555.1	555.1	554.9	554.7	554.6
132.5°	573.2	574.4	575.6	576.2	576.0	575.9	575.8	575.6
135°	603.9	605.2	606.5	607.0	606.7	606.5	606.2	605.9
137.5°	632.4	633.7	635.0	635.4	635.0	634.5	634.1	633.6
140°	650.9	652.0	653.2	653.5	652.8	652.2	651.5	650.9
142.5°	667.9	669.0	670.0	670.3	669.6	669.0	668.3	667.6
145°	691.8	692.7	693.6	693.7	693.1	692.4	691.8	691.1
147.5°	712.5	713.2	713.9	714.0	713.4	712.8	712.3	711.8
150°	725.3	726.1	726.8	726.9	726.3	725.6	725.0	724.3
152.5°	736.9	737.8	738.6	738.5	737.7	736.8	736.0	735.1
155°	752.8	753.5	754.3	754.2	753.1	752.1	751.1	750.0
157.5°	766.0	766.9	767.8	767.7	766.7	765.6	764.7	763.7
160°	773.7	774.5	775.3	775.2	774.3	773.4	772.5	771.6
162.5°	780.9	781.8	782.7	782.6	781.5	780.3	779.3	778.1
165°	789.7	790.7	791.6	791.6	790.7	789.7	788.8	787.9
167.5°	797.1	798.0	798.9	798.7	797.6	796.5	795.2	794.1
170°	800.8	801.7	802.7	802.5	801.4	800.1	799.0	797.9
172.5°	803.6	804.5	805.4	805.3	804.1	803.0	801.8	800.6
175°	806.7	807.6	808.5	808.3	807.0	805.7	804.4	803.1
177.5°	807.0	807.7	808.5	808.4	807.4	806.5	805.5	804.6
180°	806.0	806.0	806.0	806.0	806.0	806.0	806.0	806.0

(END OF REPORT)