

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331692-930

Luminaire Tested: **SA2XXRDIP-C675D725U930-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331692-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C675D725U930-4F0-1E-UDD-F4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 725 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4200.7 lumens
Efficiency: N/A
Efficacy: 91.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45.9
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331692-930

CATALOG NUMBER: SA2XXRDIP-C675D725U930-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331692-930

CATALOG NUMBER: SA2XXRDIP-C675D725U930-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	45				
1	97	93	89	86	89	85	82	79	71	69	67	58	57	55	46	45	44	39				
2	89	82	76	71	81	75	70	66	63	59	56	52	49	47	41	40	38	33				
3	81	72	65	60	74	67	60	56	56	51	48	46	43	40	37	35	33	29				
4	75	64	57	51	68	59	53	47	50	45	41	41	38	35	33	31	29	25				
5	69	57	49	44	63	53	46	41	45	40	36	37	33	30	30	27	25	22				
6	63	52	44	38	58	48	41	36	41	35	31	34	30	27	28	25	22	20				
7	59	47	39	34	54	43	36	32	37	32	28	31	27	24	25	22	20	17				
8	54	42	35	30	50	39	33	28	34	28	25	28	24	21	23	20	18	16				
9	51	39	32	27	47	36	30	25	31	26	22	26	22	19	22	19	16	14				
10	47	36	29	24	44	33	27	23	29	24	20	24	20	18	20	17	15	13				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14849	14849	14849
5°	14906	14663	14744
10°	14791	14423	14300
15°	14621	13996	13593
20°	14387	13385	12713
25°	14145	12691	11863
30°	13811	11979	10769
35°	13484	11203	9810
40°	13156	10404	8701
45°	12771	9501	7695
50°	12376	8593	6712
55°	11972	7614	5762
60°	11502	6584	4782
65°	10968	5532	4359
70°	10334	4556	4008
75°	9551	4155	3737
80°	8433	3710	3403
85°	6632	2927	2927



TEST NUMBER: P331692-930

CATALOG NUMBER: SA2XXRDIP-C675D725U930-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.1	2.0
10°-20°	236.4	5.6
20°-30°	331.9	7.9
30°-40°	361.9	8.6
40°-50°	332.8	7.9
50°-60°	261.4	6.2
60°-70°	170.4	4.1
70°-80°	87.9	2.1
80°-90°	25.8	0.6
90°-100°	132.5	3.2
100°-110°	449.7	10.7
110°-120°	477.7	11.4
120°-130°	393.2	9.4
130°-140°	315.8	7.5
140°-150°	238.6	5.7
150°-160°	167.7	4.0
160°-170°	98.7	2.4
170°-180°	32.1	0.8
0°-30°	654.4	15.6
0°-40°	1016.3	24.2
0°-60°	1610.5	38.3
0°-90°	1894.5	45.1
90°-120°	1059.9	25.2
90°-150°	2007.6	47.8
90°-180°	2306.0	54.9
0°-180°	4200.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	920	920	920	920	920	
5°	920	915	905	912	910	87
15°	875	864	837	822	813	246
25°	794	766	712	680	666	365
35°	684	640	568	518	498	428
45°	559	502	416	359	337	432
55°	425	359	270	222	205	380
65°	287	219	145	118	114	285
75°	153	96	67	61	60	162
85°	36	19	16	16	16	42
90°	1	9	22	21	21	3
95°	22	55	250	94	73	24
105°	78	117	472	844	718	83
115°	137	173	395	815	945	136
125°	191	226	380	661	767	170
135°	224	268	375	555	635	173
145°	256	294	374	464	507	161
155°	291	314	363	410	426	134
165°	317	327	347	368	374	89
175°	331	331	334	338	337	31
180°	331	331	331	331	331	



TEST NUMBER: P331692-930

CATALOG NUMBER: SA2XXRDIP-C675D725U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	919.7	919.7	919.7	919.7	919.7	919.7	919.7	919.7	919.7	919.7	919.7
2.5°	923.0	922.3	921.5	920.8	920.1	918.8	917.2	915.6	914.0	912.4	913.9
5°	919.7	918.8	917.9	916.9	916.0	914.4	911.9	909.5	907.1	904.7	906.4
7.5°	910.2	909.1	907.9	906.8	905.6	903.6	900.8	898.1	895.2	892.4	892.8
10°	902.2	900.9	899.6	898.3	897.0	894.5	890.8	887.1	883.5	879.7	879.2
12.5°	892.2	890.6	889.0	887.5	885.8	882.7	878.0	873.3	868.5	863.7	862.7
15°	874.7	872.7	870.7	868.6	866.6	862.4	856.1	849.9	843.6	837.3	833.8
17.5°	853.3	850.2	847.1	843.9	840.8	835.3	827.2	819.1	811.1	803.0	798.8
20°	837.3	833.6	829.9	826.2	822.5	816.0	806.7	797.5	788.3	779.0	774.4
22.5°	819.9	815.9	811.7	807.6	803.4	796.1	785.7	775.3	764.8	754.4	748.4
25°	794.0	788.1	782.2	776.2	770.4	761.2	749.1	736.9	724.6	712.4	704.8
27.5°	762.7	756.3	749.8	743.4	736.9	726.8	713.1	699.4	685.6	671.8	663.0
30°	740.8	733.7	726.7	719.7	712.7	701.7	686.9	672.1	657.3	642.5	633.1
32.5°	719.4	711.2	703.0	694.8	686.6	674.9	659.8	644.7	629.7	614.6	603.8
35°	684.1	674.7	665.3	655.8	646.5	633.6	617.3	601.0	584.7	568.4	556.8
37.5°	648.9	638.5	628.1	617.8	607.4	593.5	576.3	558.9	541.5	524.2	511.4
40°	624.2	613.1	602.0	590.9	579.8	565.3	547.4	529.5	511.5	493.6	480.5
42.5°	598.9	587.3	575.5	563.9	552.2	537.0	518.5	500.0	481.4	462.9	449.3
45°	559.3	546.9	534.5	522.1	509.7	493.8	474.4	455.0	435.5	416.1	403.0
47.5°	520.7	507.5	494.4	481.3	468.1	451.6	431.5	411.5	391.4	371.4	358.3
50°	492.7	479.6	466.4	453.3	440.2	423.5	403.1	382.8	362.4	342.1	329.3
52.5°	465.5	451.7	438.0	424.3	410.5	393.7	373.8	353.9	334.0	314.1	301.8
55°	425.3	410.9	396.5	382.0	367.6	350.4	330.4	310.5	290.5	270.5	259.4
57.5°	384.2	369.4	354.6	339.8	325.0	308.0	288.8	269.6	250.4	231.2	221.0
60°	356.2	341.4	326.6	311.9	297.0	280.1	261.1	242.0	223.0	203.9	194.4
62.5°	328.9	314.1	299.3	284.5	269.7	253.2	235.1	217.0	198.8	180.6	171.6
65°	287.1	272.1	257.1	242.2	227.2	211.4	194.8	178.1	161.4	144.8	138.5
67.5°	246.9	232.0	217.1	202.3	187.4	172.4	157.4	142.5	127.5	112.5	109.7
70°	218.9	204.5	190.0	175.6	161.2	147.6	134.9	122.1	109.3	96.5	94.7
72.5°	192.2	178.4	164.6	150.7	136.9	124.9	114.6	104.4	94.2	83.9	82.3
75°	153.1	140.2	127.3	114.3	101.3	91.7	85.4	79.2	72.9	66.6	65.3
77.5°	114.7	103.3	92.0	80.6	69.3	62.0	59.0	56.0	53.0	50.0	49.2
80°	90.7	81.3	71.8	62.5	53.0	47.4	45.5	43.6	41.8	39.9	39.2
82.5°	68.7	61.4	54.1	46.6	39.3	35.0	33.8	32.4	31.2	30.0	29.5
85°	35.8	31.9	28.0	24.1	20.2	18.0	17.4	17.0	16.4	15.8	15.8
87.5°	10.8	9.9	9.3	8.4	7.4	7.3	7.9	8.8	9.5	9.6	9.4
90°	0.7	2.5	5.1	6.4	7.7	9.5	12.7	17.2	21.0	21.7	21.0
92.5°	7.7	11.3	15.8	18.6	22.9	28.9	43.4	63.6	81.7	82.8	70.0
95°	22.3	24.9	31.2	36.9	47.1	62.5	91.8	147.2	221.2	249.8	218.6
97.5°	36.4	39.8	46.6	55.2	66.9	84.2	121.1	198.4	321.2	426.5	447.4
100°	49.1	51.0	56.7	66.9	79.7	97.5	131.3	209.0	346.7	503.4	595.3
102.5°	60.8	62.2	67.9	78.1	91.4	109.3	140.5	209.5	337.0	506.1	650.3
105°	77.8	80.3	84.8	94.3	108.4	126.2	156.1	212.9	318.0	472.2	641.8
107.5°	96.1	98.2	102.5	111.3	125.1	143.2	172.2	221.7	308.6	436.0	585.8
110°	108.4	110.9	114.7	123.0	136.4	154.9	182.9	228.8	306.6	418.7	550.7



TEST NUMBER: P331692-930

CATALOG NUMBER: SA2XXRDIP-C675D725U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	119.5	122.1	126.5	134.2	147.1	166.1	193.1	236.4	307.0	407.5	526.2
115°	137.1	140.2	144.1	151.6	164.4	181.6	209.0	247.9	309.7	395.2	495.9
117.5°	155.2	157.7	161.5	168.3	180.5	198.4	223.7	260.2	314.3	389.1	476.7
120°	166.3	168.9	172.7	178.5	191.2	209.0	233.9	268.3	317.4	385.6	466.5
122.5°	177.1	179.1	182.9	189.1	201.9	220.3	243.6	275.5	321.0	383.5	457.9
125°	191.2	193.1	196.9	204.6	217.4	235.1	258.1	286.8	326.3	379.8	445.5
127.5°	202.4	205.0	210.3	218.7	231.0	249.3	271.7	297.3	331.8	377.6	434.0
130°	209.0	211.6	217.9	226.9	239.6	257.5	279.8	304.0	335.9	376.7	426.4
132.5°	215.2	218.3	225.1	234.6	247.8	265.6	286.9	310.6	340.0	376.2	420.3
135°	224.4	226.9	234.6	244.1	258.8	276.6	297.0	319.3	344.8	375.4	411.7
137.5°	233.0	236.0	243.7	253.9	268.5	285.0	305.2	326.0	349.1	375.3	405.7
140°	239.6	242.1	249.8	260.0	274.0	290.7	309.7	329.5	351.1	374.7	402.2
142.5°	246.2	248.3	255.4	265.6	279.2	294.7	313.3	332.6	352.7	374.7	398.6
145°	256.2	258.8	265.1	274.7	287.4	301.4	318.7	336.5	354.3	373.5	393.9
147.5°	266.9	268.8	274.9	283.7	294.3	306.8	323.0	338.7	354.9	371.2	389.1
150°	274.0	276.0	281.0	289.3	298.9	310.4	325.1	339.7	354.3	369.7	384.9
152.5°	281.2	282.1	287.1	294.4	303.5	314.0	327.1	340.2	353.4	367.1	381.4
155°	291.2	291.9	295.7	302.7	309.7	319.3	330.1	341.0	351.8	362.6	374.7
157.5°	299.7	300.3	303.4	309.5	315.1	323.1	332.3	341.0	348.9	358.1	368.5
160°	305.2	305.9	308.4	313.6	318.7	325.6	333.3	341.0	347.3	355.0	363.9
162.5°	310.9	310.5	313.1	317.2	321.7	327.2	333.9	340.5	345.8	352.5	359.8
165°	317.4	316.7	318.0	321.9	325.1	328.9	334.6	339.1	342.9	347.3	353.1
167.5°	322.8	322.0	323.1	325.5	327.8	330.3	334.4	338.2	340.0	342.9	346.4
170°	326.3	325.1	325.6	327.6	328.9	330.8	333.9	337.1	338.4	340.3	342.9
172.5°	328.3	327.6	327.2	329.1	329.9	331.3	333.5	335.6	336.4	337.3	339.3
175°	330.8	330.1	329.5	330.8	330.8	331.4	332.6	333.9	333.3	333.9	334.6
177.5°	331.9	330.9	330.4	331.4	331.4	331.4	331.9	333.0	331.9	331.4	331.9
180°	331.4	331.4	331.4	331.4	331.4	331.4	331.4	331.4	331.4	331.4	331.4



TEST NUMBER: P331692-930

CATALOG NUMBER: SA2XXRDIP-C675D725U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	919.7	919.7	919.7	919.7	919.7	919.7	919.7	919.7
2.5°	915.3	916.8	918.3	918.8	918.6	918.3	918.0	917.7
5°	908.0	909.7	911.3	911.9	911.3	910.8	910.3	909.7
7.5°	893.3	893.8	894.3	894.1	893.1	892.2	891.2	890.2
10°	878.6	878.1	877.5	876.7	875.5	874.5	873.3	872.2
12.5°	861.8	860.8	859.7	858.3	856.5	854.7	852.8	850.9
15°	830.3	826.7	823.2	820.5	818.7	816.8	815.0	813.2
17.5°	794.7	790.4	786.3	782.6	779.4	776.2	773.1	769.9
20°	769.8	765.2	760.5	756.2	752.1	748.0	744.0	739.9
22.5°	742.5	736.5	730.6	726.1	723.0	720.0	717.0	714.0
25°	697.2	689.7	682.1	676.9	674.2	671.4	668.6	665.9
27.5°	654.1	645.3	636.5	629.8	625.4	621.0	616.6	612.2
30°	623.7	614.2	604.8	597.6	592.6	587.6	582.6	577.6
32.5°	593.0	582.3	571.5	563.8	559.1	554.4	549.7	545.0
35°	545.2	533.5	521.9	514.0	509.9	505.8	501.8	497.7
37.5°	498.5	485.7	472.9	464.1	459.4	454.8	450.1	445.5
40°	467.2	454.1	441.0	432.0	427.2	422.4	417.6	412.8
42.5°	435.8	422.2	408.6	399.5	394.8	390.2	385.6	380.8
45°	389.9	376.7	363.6	354.8	350.4	345.9	341.5	337.0
47.5°	345.3	332.2	319.1	310.6	306.6	302.6	298.5	294.5
50°	316.6	303.8	291.1	282.7	278.8	274.9	271.1	267.2
52.5°	289.5	277.1	264.8	256.9	253.3	249.7	246.1	242.6
55°	248.3	237.2	226.1	218.8	215.3	211.7	208.2	204.7
57.5°	210.8	200.7	190.5	183.9	181.0	178.1	175.0	172.1
60°	185.1	175.6	166.2	160.0	157.0	154.1	151.1	148.1
62.5°	162.7	153.6	144.6	139.3	137.5	135.7	134.0	132.2
65°	132.2	126.0	119.7	116.3	115.7	115.1	114.5	114.1
67.5°	106.7	103.9	101.0	99.2	98.7	98.1	97.5	96.9
70°	92.9	91.0	89.1	87.9	87.1	86.3	85.6	84.9
72.5°	80.8	79.2	77.7	76.7	76.2	75.8	75.3	74.9
75°	64.0	62.7	61.4	60.7	60.5	60.3	60.1	59.9
77.5°	48.4	47.7	47.0	46.5	46.1	45.9	45.6	45.2
80°	38.5	37.7	37.0	36.6	36.6	36.6	36.6	36.6
82.5°	29.1	28.6	28.2	28.0	28.0	28.0	28.0	28.0
85°	15.8	15.8	15.8	15.8	15.8	15.8	15.8	15.8
87.5°	9.1	8.7	8.8	8.9	8.9	8.9	8.9	8.9
90°	20.4	19.2	20.4	21.0	21.0	21.0	21.0	21.0
92.5°	55.6	47.7	42.3	38.4	37.8	35.8	36.4	35.3
95°	167.0	128.1	101.3	87.3	79.0	73.9	72.0	72.6
97.5°	389.6	318.8	249.8	203.8	173.3	157.7	148.4	143.0
100°	581.9	502.9	415.6	338.4	285.5	258.1	239.6	228.1
102.5°	707.8	690.0	626.1	544.4	486.9	440.1	417.0	401.5
105°	774.4	846.4	854.7	833.6	794.1	754.6	727.2	718.3
107.5°	726.4	834.9	901.2	932.1	937.0	934.8	929.4	917.5
110°	685.1	799.2	880.8	933.0	960.4	972.6	978.3	977.6



TEST NUMBER: P331692-930

CATALOG NUMBER: SA2XXRDIP-C675D725U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	647.4	756.8	844.1	904.0	942.1	962.4	973.2	976.6
115°	601.0	699.1	782.6	848.2	893.5	922.8	939.4	945.2
117.5°	566.1	652.2	728.0	789.5	835.7	866.7	884.1	888.9
120°	548.7	627.8	695.3	753.3	797.9	827.9	846.4	852.7
122.5°	535.0	607.4	671.3	723.7	763.8	793.2	809.7	815.0
125°	514.9	580.6	636.7	684.4	721.5	745.7	761.6	766.7
127.5°	495.2	554.6	607.5	651.6	683.9	706.5	720.3	724.4
130°	482.4	537.3	587.6	629.7	660.9	682.6	695.3	700.4
132.5°	470.2	521.0	567.2	606.7	637.5	659.1	670.8	675.4
135°	453.1	495.2	537.3	572.9	600.4	621.4	632.8	635.4
137.5°	439.5	474.7	508.1	539.2	564.2	582.3	592.3	596.1
140°	430.8	461.5	490.7	518.8	539.2	555.7	565.3	569.2
142.5°	423.7	449.7	474.9	498.4	517.8	532.8	541.4	542.1
145°	413.6	434.6	454.4	472.9	488.2	499.0	505.4	507.3
147.5°	405.9	422.4	437.8	451.3	464.0	472.6	477.0	478.1
150°	400.2	414.3	427.6	439.1	448.7	456.3	460.2	460.8
152.5°	394.6	407.6	419.0	428.9	436.4	443.0	445.9	446.0
155°	386.9	397.1	406.6	413.6	420.6	425.1	427.6	426.4
157.5°	377.8	386.4	394.4	399.8	404.8	408.5	409.7	409.7
160°	372.2	379.2	386.2	390.7	395.2	398.4	398.9	398.9
162.5°	366.6	372.6	378.5	382.0	386.5	388.7	389.3	388.7
165°	358.2	362.6	367.1	369.7	372.2	374.7	374.7	374.1
167.5°	350.2	353.6	356.6	359.0	360.1	361.5	361.3	360.6
170°	346.1	348.0	350.5	351.8	352.5	354.3	353.7	352.5
172.5°	341.4	342.9	345.0	345.7	346.3	347.2	346.6	345.8
175°	336.5	337.1	337.8	338.4	338.4	339.1	338.4	337.1
177.5°	333.0	333.0	333.5	333.5	333.5	333.5	333.0	331.9
180°	331.4	331.4	331.4	331.4	331.4	331.4	331.4	331.4

(END OF REPORT)