

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331320-840

Luminaire Tested: **SA2XXDIP-C485D925U840-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331320-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C485D925U840-4F0-1E-UDD-F4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 925 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5647.2 lumens
Efficiency: N/A
Efficacy: 126.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 44.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331320-840

CATALOG NUMBER: SA2XXDIP-C485D925U840-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331320-840

CATALOG NUMBER: SA2XXDIP-C485D925U840-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	43	43	43	35
1	95	90	86	83	85	82	79	76	66	64	62	51	50	48	38	37	36	30
2	86	79	73	68	78	71	66	62	58	54	51	45	43	40	33	32	30	25
3	78	69	62	56	71	63	57	52	51	46	43	40	37	34	29	27	26	21
4	72	61	53	48	65	56	49	44	45	40	36	35	32	29	26	24	22	18
5	66	54	46	41	59	50	43	37	40	35	31	32	28	25	24	21	19	16
6	60	49	41	35	54	44	37	32	36	31	27	29	25	22	21	19	17	14
7	56	44	36	31	50	40	33	28	33	28	24	26	22	19	20	17	15	12
8	52	40	32	27	47	36	30	25	30	25	21	24	20	17	18	15	14	11
9	48	36	29	24	43	33	27	22	27	22	19	22	18	15	17	14	12	10
10	45	33	26	21	41	30	24	20	25	20	17	20	16	14	15	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12665	12665	12665
5°	12713	12530	12603
10°	12637	12403	12463
15°	12481	12242	12227
20°	12259	12000	11986
25°	12039	11703	11703
30°	11757	11432	11332
35°	11491	11105	10941
40°	11160	10779	10570
45°	10832	10453	10195
50°	10477	10115	9756
55°	10106	9723	9362
60°	9691	9255	8913
65°	9249	8787	8382
70°	8686	8224	7832
75°	7904	7573	7392
80°	7011	6797	6453
85°	5724	5446	4891



TEST NUMBER: P331320-840

CATALOG NUMBER: SA2XXDIP-C485D925U840-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.8	1.3
10°-20°	207.5	3.7
20°-30°	305.0	5.4
30°-40°	354.3	6.3
40°-50°	354.0	6.3
50°-60°	308.7	5.5
60°-70°	228.2	4.0
70°-80°	129.3	2.3
80°-90°	39.5	0.7
90°-100°	209.6	3.7
100°-110°	711.1	12.6
110°-120°	755.5	13.4
120°-130°	621.9	11.0
130°-140°	499.4	8.8
140°-150°	377.4	6.7
150°-160°	265.2	4.7
160°-170°	156.1	2.8
170°-180°	50.8	0.9
0°-30°	586.3	10.4
0°-40°	940.7	16.7
0°-60°	1603.3	28.4
0°-90°	2000.2	35.4
90°-120°	1676.1	29.7
90°-150°	3174.8	56.2
90°-180°	3647.0	64.6
0°-180°	5647.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	784	784	784	784	784	
5°	784	781	773	779	778	74
15°	747	742	732	735	732	210
25°	676	669	657	658	657	311
35°	583	575	563	559	555	364
45°	474	469	458	450	446	366
55°	359	354	345	337	333	321
65°	242	237	230	223	219	239
75°	127	125	121	117	118	135
85°	31	30	29	27	26	35
90°	1	14	34	33	33	3
95°	35	87	395	149	115	37
105°	123	185	747	1335	1136	131
115°	217	274	625	1290	1495	215
125°	302	358	601	1045	1212	268
135°	355	423	594	878	1005	274
145°	405	466	591	733	802	254
155°	461	497	574	649	674	212
165°	502	517	549	583	592	141
175°	523	524	528	535	533	50
180°	524	524	524	524	524	



TEST NUMBER: P331320-840

CATALOG NUMBER: SA2XXDIP-C485D925U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	784.4	784.4	784.4	784.4	784.4	784.4	784.4	784.4	784.4	784.4	784.4
2.5°	788.0	787.3	786.7	786.0	785.3	784.3	782.7	781.3	779.8	778.3	779.7
5°	784.4	783.7	783.0	782.3	781.7	780.4	778.6	776.8	774.9	773.1	774.4
7.5°	777.4	776.4	775.4	774.3	773.3	771.8	769.9	768.1	766.2	764.3	765.7
10°	770.8	769.6	768.4	767.3	766.1	764.5	762.4	760.5	758.5	756.5	757.8
12.5°	761.7	760.7	759.6	758.6	757.6	756.1	754.1	752.0	750.0	748.0	748.9
15°	746.7	745.7	744.7	743.7	742.7	741.0	738.8	736.7	734.5	732.4	733.0
17.5°	727.3	726.4	725.4	724.4	723.4	721.8	719.5	717.3	715.1	712.9	713.7
20°	713.5	712.5	711.4	710.4	709.4	707.8	705.4	703.1	700.7	698.4	698.9
22.5°	699.6	698.2	696.8	695.4	694.0	692.2	689.9	687.7	685.5	683.3	683.4
25°	675.8	674.4	673.1	671.8	670.4	668.3	665.5	662.6	659.7	656.9	657.2
27.5°	648.6	647.4	646.2	645.0	643.8	642.1	639.9	637.5	635.3	633.1	632.6
30°	630.6	629.1	627.8	626.5	625.1	623.2	620.7	618.2	615.7	613.2	612.7
32.5°	611.2	610.2	609.0	607.9	606.9	605.0	602.4	599.8	597.1	594.5	593.6
35°	583.0	581.3	579.7	577.9	576.3	574.1	571.5	568.8	566.0	563.4	562.4
37.5°	551.2	549.7	548.3	546.7	545.2	543.2	540.5	537.9	535.1	532.5	531.2
40°	529.5	528.1	526.7	525.4	524.1	522.1	519.4	516.7	514.0	511.4	509.9
42.5°	508.4	507.0	505.6	504.3	503.0	501.0	498.3	495.6	492.9	490.2	488.6
45°	474.4	473.2	472.0	470.9	469.7	467.9	465.3	462.8	460.3	457.8	456.0
47.5°	440.6	439.5	438.4	437.3	436.2	434.3	431.7	429.1	426.5	423.8	421.9
50°	417.1	416.3	415.4	414.5	413.7	412.1	409.8	407.5	405.1	402.7	400.4
52.5°	394.2	393.0	391.9	390.8	389.7	388.1	385.9	383.6	381.4	379.2	377.3
55°	359.0	358.0	357.0	356.0	355.0	353.5	351.4	349.4	347.4	345.4	343.5
57.5°	323.7	322.9	322.0	321.3	320.5	319.0	316.8	314.6	312.4	310.1	308.1
60°	300.1	299.5	298.8	298.1	297.5	296.0	293.7	291.2	288.9	286.6	284.8
62.5°	277.2	276.2	275.1	274.0	273.0	271.6	269.7	267.9	266.1	264.3	262.6
65°	242.1	241.1	240.0	239.0	238.1	236.7	235.1	233.4	231.7	230.0	228.5
67.5°	206.3	205.5	204.7	203.9	203.1	202.0	200.5	198.9	197.4	195.9	194.8
70°	184.0	183.4	182.7	182.0	181.4	180.3	178.7	177.2	175.7	174.2	173.1
72.5°	161.1	160.5	159.8	159.1	158.4	157.6	156.6	155.6	154.7	153.7	152.5
75°	126.7	126.3	126.0	125.7	125.3	124.8	123.9	123.1	122.3	121.4	120.4
77.5°	95.9	95.3	94.8	94.2	93.6	93.2	92.9	92.5	92.2	91.9	91.4
80°	75.4	75.2	75.1	74.9	74.7	74.5	74.1	73.8	73.5	73.1	72.6
82.5°	56.1	56.0	56.0	56.0	55.9	55.8	55.6	55.4	55.2	55.0	54.4
85°	30.9	30.8	30.6	30.4	30.3	30.1	29.9	29.8	29.6	29.4	28.9
87.5°	11.1	11.4	11.9	12.1	12.2	12.5	13.3	14.4	15.3	15.3	14.7
90°	1.0	4.0	8.1	10.1	12.1	15.1	20.2	27.2	33.2	34.2	33.2
92.5°	12.3	17.8	25.0	29.4	36.3	45.7	68.6	100.6	129.2	131.0	110.7
95°	35.2	39.3	49.4	58.5	74.6	98.8	145.1	232.8	349.7	395.1	345.7
97.5°	57.5	62.9	73.6	87.3	105.8	133.2	191.5	313.7	508.0	674.5	707.5
100°	77.6	80.6	89.7	105.8	126.0	154.2	207.6	330.6	548.3	796.2	941.4
102.5°	96.1	98.4	107.4	123.6	144.5	172.8	222.2	331.4	533.0	800.2	1028.4
105°	123.0	127.0	134.0	149.2	171.4	199.5	246.9	336.6	502.9	746.8	1014.9
107.5°	152.0	155.2	162.1	176.0	197.9	226.4	272.4	350.5	488.0	689.6	926.5
110°	171.4	175.4	181.4	194.5	215.7	244.9	289.2	361.8	484.8	662.2	870.8



TEST NUMBER: P331320-840

CATALOG NUMBER: SA2XXDIP-C485D925U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	189.0	193.1	200.0	212.3	232.6	262.7	305.4	374.0	485.5	644.4	832.1
115°	216.7	221.8	227.8	239.8	260.0	287.2	330.6	392.0	489.8	624.9	784.2
117.5°	245.3	249.3	255.4	266.1	285.4	313.7	353.8	411.4	497.1	615.4	753.9
120°	263.1	267.1	273.2	282.2	302.4	330.6	369.9	424.3	501.9	609.8	737.8
122.5°	280.0	283.2	289.2	299.1	319.3	348.3	385.2	435.6	507.6	606.5	724.1
125°	302.4	305.4	311.4	323.6	343.7	371.9	408.2	453.5	516.0	600.7	704.5
127.5°	320.1	324.2	332.5	345.9	365.3	394.3	429.6	470.3	524.7	597.2	686.4
130°	330.6	334.6	344.7	358.8	379.0	407.2	442.4	480.8	531.2	595.6	674.3
132.5°	340.2	345.1	356.0	370.9	391.8	420.1	453.7	491.2	537.6	594.8	664.6
135°	354.8	358.8	370.9	386.0	409.2	437.4	469.7	504.9	545.2	593.6	651.1
137.5°	368.5	373.3	385.4	401.5	424.5	450.7	482.6	515.4	552.1	593.4	641.6
140°	379.0	383.0	395.1	411.2	433.4	459.6	489.8	521.1	555.3	592.6	636.0
142.5°	389.4	392.6	403.9	420.1	441.4	466.1	495.4	525.9	557.7	592.6	630.4
145°	405.2	409.2	419.3	434.4	454.5	476.8	503.9	532.2	560.4	590.6	622.9
147.5°	422.1	425.2	434.7	448.7	465.4	485.2	510.8	535.6	561.2	587.0	615.2
150°	433.4	436.4	444.4	457.6	472.7	490.8	514.0	537.1	560.4	584.6	608.7
152.5°	444.6	446.1	454.1	465.6	480.0	496.4	517.3	538.0	558.8	580.6	603.1
155°	460.6	461.6	467.7	478.8	489.8	504.9	522.1	539.2	556.3	573.5	592.6
157.5°	473.9	474.9	479.8	489.4	498.3	511.0	525.5	539.2	551.7	566.2	582.8
160°	482.8	483.8	487.8	495.8	503.9	515.0	527.1	539.2	549.3	561.4	575.5
162.5°	491.6	491.0	495.0	501.5	508.8	517.5	528.0	538.4	546.8	557.3	569.1
165°	501.9	500.9	502.9	509.0	514.0	520.1	529.2	536.2	542.2	549.3	558.4
167.5°	510.4	509.2	511.0	514.8	518.5	522.3	529.0	534.8	537.6	542.2	547.9
170°	516.0	514.0	515.0	518.1	520.1	523.1	528.2	533.2	535.2	538.2	542.2
172.5°	519.3	518.1	517.5	520.5	521.7	523.9	527.4	530.8	532.0	533.4	536.6
175°	523.1	522.1	521.1	523.1	523.1	524.1	526.1	528.2	527.1	528.2	529.2
177.5°	524.9	523.3	522.5	524.1	524.1	524.1	524.9	526.5	524.9	524.1	524.9
180°	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1



TEST NUMBER: P331320-840

CATALOG NUMBER: SA2XXDIP-C485D925U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	784.4	784.4	784.4	784.4	784.4	784.4	784.4	784.4
2.5°	781.0	782.3	783.7	784.3	784.0	783.7	783.5	783.2
5°	775.8	777.1	778.4	778.9	778.6	778.2	777.9	777.6
7.5°	767.0	768.3	769.7	770.1	769.8	769.4	769.0	768.7
10°	759.1	760.5	761.8	762.2	761.7	761.2	760.7	760.2
12.5°	749.9	750.8	751.7	752.0	751.6	751.3	750.9	750.5
15°	733.7	734.4	735.0	734.9	734.1	733.3	732.5	731.5
17.5°	714.4	715.2	716.0	715.9	715.1	714.4	713.6	712.8
20°	699.4	699.9	700.4	700.3	699.6	698.9	698.3	697.6
22.5°	683.5	683.6	683.7	683.6	683.2	682.8	682.4	682.0
25°	657.6	657.9	658.2	658.2	657.9	657.6	657.2	656.9
27.5°	632.1	631.6	631.1	630.5	629.7	628.8	628.0	627.2
30°	612.2	611.7	611.2	610.6	609.9	609.3	608.5	607.8
32.5°	592.7	591.8	590.9	590.1	589.4	588.8	588.0	587.3
35°	561.4	560.4	559.4	558.5	557.6	556.7	555.9	555.1
37.5°	530.0	528.8	527.6	526.4	525.6	524.8	524.0	523.3
40°	508.4	506.9	505.3	504.2	503.5	502.9	502.2	501.5
42.5°	487.0	485.3	483.6	482.4	481.4	480.5	479.6	478.6
45°	454.1	452.3	450.4	449.2	448.5	447.9	447.2	446.5
47.5°	420.0	418.0	416.1	414.7	413.6	412.7	411.7	410.7
50°	398.1	395.7	393.3	391.7	390.9	390.1	389.2	388.4
52.5°	375.4	373.3	371.4	369.9	368.8	367.7	366.6	365.5
55°	341.4	339.4	337.4	336.0	335.1	334.3	333.5	332.6
57.5°	306.2	304.2	302.3	300.9	300.2	299.6	299.0	298.3
60°	282.9	281.0	279.2	278.0	277.5	277.0	276.5	276.0
62.5°	260.8	259.1	257.4	256.3	255.6	255.0	254.4	253.7
65°	227.0	225.5	224.0	222.8	222.0	221.2	220.4	219.4
67.5°	193.6	192.4	191.3	190.4	189.7	188.9	188.3	187.6
70°	171.9	170.7	169.6	168.6	167.9	167.2	166.6	165.9
72.5°	151.4	150.2	149.1	148.1	147.6	147.0	146.5	146.0
75°	119.4	118.5	117.4	117.0	117.4	117.8	118.1	118.5
77.5°	90.9	90.4	89.9	89.4	88.9	88.5	88.0	87.5
80°	72.1	71.6	71.2	70.7	70.4	70.1	69.7	69.4
82.5°	53.8	53.1	52.5	52.1	52.1	52.0	51.9	51.9
85°	28.4	27.9	27.4	27.1	26.9	26.8	26.6	26.4
87.5°	14.1	13.3	13.3	13.2	13.1	12.9	12.8	12.7
90°	32.2	30.2	32.2	33.2	33.2	33.2	33.2	33.2
92.5°	87.9	75.4	67.0	60.7	59.9	56.7	57.5	55.8
95°	264.1	202.6	160.3	138.0	125.0	116.9	113.9	114.9
97.5°	616.2	504.1	395.1	322.3	274.2	249.3	234.6	226.2
100°	920.2	795.2	657.1	535.2	451.5	408.2	379.0	360.8
102.5°	1119.3	1091.2	990.2	860.9	770.0	696.0	659.5	635.0
105°	1224.6	1338.5	1351.6	1318.3	1255.8	1193.4	1149.9	1135.9
107.5°	1148.8	1320.3	1425.1	1473.9	1481.8	1478.3	1469.7	1451.0
110°	1083.5	1263.8	1392.9	1475.5	1518.8	1538.0	1547.1	1546.1



TEST NUMBER: P331320-840

CATALOG NUMBER: SA2XXDIP-C485D925U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	1023.8	1197.0	1334.8	1429.6	1489.9	1521.9	1539.0	1544.5
115°	950.4	1105.6	1237.7	1341.5	1413.0	1459.4	1485.6	1494.7
117.5°	895.1	1031.5	1151.1	1248.6	1321.5	1370.5	1398.2	1405.7
120°	867.8	992.8	1099.5	1191.3	1261.8	1309.2	1338.5	1348.6
122.5°	846.0	960.5	1061.7	1144.6	1207.8	1254.4	1280.4	1288.9
125°	814.4	918.2	1006.8	1082.5	1140.9	1179.2	1204.4	1212.4
127.5°	783.2	877.1	960.7	1030.5	1081.5	1117.3	1139.1	1145.6
130°	763.0	849.6	929.3	995.8	1045.2	1079.4	1099.5	1107.6
132.5°	743.6	823.8	897.0	959.5	1008.0	1042.4	1060.9	1068.1
135°	716.6	783.2	849.6	906.1	949.4	982.7	1000.8	1004.8
137.5°	695.0	750.6	803.4	852.6	892.2	920.8	936.8	942.8
140°	681.4	729.7	776.1	820.4	852.6	878.9	894.0	900.0
142.5°	670.0	711.1	751.0	788.2	818.8	842.6	856.1	857.3
145°	654.1	687.4	718.6	747.8	772.0	789.2	799.2	802.2
147.5°	641.8	668.0	692.4	713.8	733.8	747.4	754.3	756.1
150°	633.0	655.1	676.3	694.4	709.5	721.6	727.7	728.7
152.5°	624.1	644.6	662.6	678.3	690.1	700.6	705.1	705.3
155°	611.8	627.9	643.0	654.1	665.2	672.3	676.3	674.3
157.5°	597.4	611.0	623.7	632.4	640.2	646.0	647.8	647.8
160°	588.5	599.7	610.8	617.8	624.9	630.0	631.0	631.0
162.5°	579.8	589.2	598.6	604.1	611.2	614.6	615.6	614.8
165°	566.4	573.5	580.6	584.6	588.5	592.6	592.6	591.6
167.5°	553.7	559.2	564.0	567.6	569.5	571.7	571.5	570.3
170°	547.2	550.3	554.3	556.3	557.3	560.4	559.4	557.3
172.5°	540.0	542.2	545.4	546.6	547.6	549.1	548.1	546.8
175°	532.2	533.2	534.2	535.2	535.2	536.2	535.2	533.2
177.5°	526.5	526.5	527.4	527.4	527.4	527.4	526.5	524.9
180°	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1

(END OF REPORT)