

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331368-840

Luminaire Tested: **SA2XXDIP-C675D1080U840-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331368-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C675D1080U840-4F0-1E-UDD-A4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1080 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7209.8 lumens
Efficiency: N/A
Efficacy: 126.7 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 56.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331368-840
CATALOG NUMBER: SA2XXDIP-C675D1080U840-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331368-840

CATALOG NUMBER: SA2XXDIP-C675D1080U840-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	105	105	105	105	96	96	96	96	78	78	78	63	63	63	48	48	48	41				41
1	96	92	88	85	88	84	81	78	69	67	65	56	54	53	43	42	41				35	
2	88	81	75	70	80	74	69	65	61	58	54	49	47	45	38	37	35				30	
3	80	71	64	59	73	65	59	55	54	50	46	44	41	38	34	32	30				26	
4	74	63	56	50	67	58	52	47	48	44	40	39	36	33	31	29	27				23	
5	68	57	49	43	62	52	45	40	43	38	34	35	32	29	28	25	23				20	
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	26	23	21				18	
7	58	46	38	33	53	42	36	31	36	31	27	29	26	23	23	21	19				16	
8	54	42	34	29	49	39	32	27	33	27	24	27	23	20	22	19	17				14	
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	20	17	15				13	
10	47	35	28	23	43	32	26	22	28	23	19	23	19	17	19	16	14				12	

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	21658	21658	21658	21658
5°	24280	21797	19316	21797
10°	27824	21620	16718	21620
15°	30780	21224	14770	21224
20°	30311	20797	13464	20797
25°	27332	20232	12636	20232
30°	22585	19328	12033	19328
35°	16462	18382	11606	18382
40°	13148	17266	11367	17266
45°	11488	15972	11040	15972
50°	10798	14722	10826	14722
55°	9956	13453	10536	13453
60°	9122	12103	10091	12103
65°	8309	10892	9650	10892
70°	7544	9711	9007	9711
75°	6687	8390	7973	8390
80°	5755	6946	6425	6946
85°	5169	5169	3816	5169



TEST NUMBER: P331368-840

CATALOG NUMBER: SA2XXDIP-C675D1080U840-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	127.7	1.8
10°-20°	371.4	5.2
20°-30°	539.0	7.5
30°-40°	568.8	7.9
40°-50°	503.6	7.0
50°-60°	401.9	5.6
60°-70°	273.2	3.8
70°-80°	140.0	1.9
80°-90°	39.3	0.5
90°-100°	243.9	3.4
100°-110°	827.7	11.5
110°-120°	879.3	12.2
120°-130°	723.9	10.0
130°-140°	581.3	8.1
140°-150°	439.3	6.1
150°-160°	308.7	4.3
160°-170°	181.7	2.5
170°-180°	59.1	0.8
0°-30°	1038.1	14.4
0°-40°	1606.9	22.3
0°-60°	2512.4	34.8
0°-90°	2964.8	41.1
90°-120°	1951.0	27.1
90°-150°	3695.4	51.3
90°-180°	4245.0	58.9
0°-180°	7209.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1341	1341	1341	1341	1341	
5°	1498	1345	1192	1345	1498	150
15°	1841	1270	884	1270	1841	508
25°	1534	1136	709	1136	1534	693
35°	835	933	589	933	835	543
45°	503	700	484	700	503	396
55°	354	478	374	478	354	317
65°	218	285	253	285	218	216
75°	107	134	128	134	107	115
85°	28	28	21	28	28	32
90°	39	1	39	1	39	22
95°	134	41	134	41	134	174
105°	1322	143	1322	143	1322	1279
115°	1740	252	1740	252	1740	1704
125°	1411	352	1411	352	1411	1275
135°	1170	413	1170	413	1170	909
145°	934	472	934	472	934	593
155°	785	536	785	536	785	366
165°	689	584	689	584	689	197
175°	621	609	621	609	621	60
180°	610	610	610	610	610	



TEST NUMBER: P331368-840

CATALOG NUMBER: SA2XXDIP-C675D1080U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1403.2	1403.6	1404.5	1397.9	1397.0	1397.0	1391.3	1386.3	1380.6	1372.7	1373.5
5°	1498.1	1503.8	1505.8	1499.6	1490.4	1489.3	1480.6	1466.1	1452.7	1441.9	1434.2
7.5°	1611.3	1613.6	1608.5	1600.3	1593.5	1581.1	1564.8	1548.8	1526.4	1505.9	1490.7
10°	1697.1	1700.2	1691.4	1679.6	1669.8	1655.4	1631.6	1607.4	1578.0	1549.6	1526.9
12.5°	1762.2	1769.9	1758.7	1757.1	1740.3	1720.5	1692.2	1680.0	1638.6	1599.1	1574.8
15°	1841.4	1840.9	1842.0	1832.2	1819.8	1816.6	1786.8	1754.3	1696.1	1672.8	1632.6
17.5°	1818.6	1826.3	1830.0	1829.9	1829.6	1827.7	1818.1	1797.6	1768.4	1730.7	1684.3
20°	1764.1	1774.4	1775.9	1787.9	1794.5	1803.3	1806.9	1801.2	1783.2	1751.7	1711.5
22.5°	1680.0	1682.8	1687.7	1706.2	1720.7	1742.6	1754.1	1773.2	1766.3	1750.9	1717.3
25°	1534.2	1529.0	1547.1	1556.3	1589.8	1624.9	1650.2	1678.0	1702.7	1717.7	1707.9
27.5°	1359.1	1351.4	1378.4	1403.0	1430.3	1468.2	1507.6	1554.1	1592.8	1641.1	1657.7
30°	1211.4	1216.1	1241.9	1268.2	1309.4	1363.0	1407.3	1458.4	1513.6	1567.7	1605.3
32.5°	1052.3	1070.2	1086.4	1126.7	1163.0	1222.8	1287.8	1351.6	1420.4	1481.9	1540.1
35°	835.2	855.8	878.5	907.9	958.9	1018.1	1081.6	1167.6	1261.5	1345.5	1414.6
37.5°	703.0	699.6	712.7	733.9	775.3	823.0	896.1	981.2	1091.6	1190.3	1287.8
40°	623.8	621.7	631.0	650.6	682.1	717.1	781.0	855.8	958.4	1078.9	1195.0
42.5°	569.4	570.6	575.7	589.6	611.1	640.0	687.8	751.4	845.4	959.0	1083.6
45°	503.1	506.8	512.4	519.2	531.5	555.2	582.0	627.4	701.7	796.5	919.2
47.5°	455.6	455.7	461.4	467.3	474.6	488.0	509.9	538.3	590.7	667.9	773.4
50°	429.9	426.4	430.5	435.0	442.8	452.1	466.6	493.3	528.4	590.8	678.9
52.5°	398.6	398.7	402.4	404.1	411.1	420.3	433.5	452.1	483.8	532.6	605.1
55°	353.7	356.2	358.3	361.3	367.6	374.3	384.6	397.0	421.7	458.3	511.9
57.5°	311.3	312.1	314.3	320.1	324.1	330.2	340.0	351.2	367.4	394.5	434.7
60°	282.5	282.5	286.6	289.2	294.4	300.5	308.3	319.1	333.6	355.7	388.2
62.5°	256.1	255.7	257.3	261.6	265.5	271.2	279.0	288.2	301.7	321.4	348.2
65°	217.5	216.5	219.6	220.7	224.8	230.5	236.6	246.4	257.2	271.7	295.4
67.5°	180.5	181.7	183.3	185.3	187.5	193.5	197.6	204.6	213.7	225.7	241.8
70°	159.8	159.8	159.8	161.4	164.4	167.5	171.7	177.3	186.1	196.4	210.9
72.5°	136.7	138.4	140.0	139.1	143.0	144.8	149.8	153.0	161.4	167.9	180.8
75°	107.2	107.2	107.2	109.8	111.4	112.9	116.0	119.1	123.2	131.5	138.1
77.5°	80.0	79.8	80.3	80.9	82.6	84.4	85.3	88.2	92.0	95.7	101.5
80°	61.9	62.9	63.4	64.4	64.4	65.4	65.9	69.6	72.2	74.7	78.4
82.5°	47.9	48.1	48.2	48.4	48.8	49.4	50.7	51.9	52.8	54.9	57.8
85°	27.9	27.4	27.4	28.4	27.9	27.9	28.9	29.9	29.9	30.4	31.9
87.5°	18.5	18.5	18.9	18.5	18.5	18.7	18.2	18.3	18.9	19.5	19.7
90°	38.7	38.7	38.7	38.7	38.7	37.6	35.2	37.6	38.7	39.9	38.7
92.5°	65.0	66.9	65.9	69.7	70.6	77.9	87.8	102.3	128.9	152.5	150.4
95°	133.7	132.6	136.1	145.4	160.7	186.5	235.8	307.4	402.4	459.9	407.1
97.5°	263.3	273.1	290.2	319.1	375.2	459.9	586.8	717.2	823.5	785.1	591.3
100°	420.0	441.1	475.1	525.5	622.9	764.9	925.6	1071.1	1095.7	926.8	638.1
102.5°	739.1	767.7	810.2	896.3	1002.1	1152.5	1270.0	1302.9	1197.1	931.5	620.4
105°	1322.1	1338.6	1389.0	1461.7	1534.5	1573.2	1557.9	1425.3	1181.3	869.3	585.4
107.5°	1688.8	1710.6	1720.7	1724.7	1715.6	1658.8	1536.8	1337.2	1078.3	802.6	568.0
110°	1799.6	1800.8	1790.2	1767.9	1717.5	1621.2	1471.1	1261.1	1013.6	770.7	564.3



TEST NUMBER: P331368-840

CATALOG NUMBER: SA2XXDIP-C675D1080U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1797.7	1791.4	1771.4	1734.1	1664.0	1553.7	1393.2	1191.6	968.6	750.1	565.2
115°	1739.8	1729.2	1698.7	1644.8	1561.5	1440.6	1287.0	1106.3	912.7	727.3	570.2
117.5°	1636.3	1627.4	1595.2	1538.2	1453.3	1340.0	1200.6	1042.0	877.5	716.3	578.6
120°	1569.6	1557.9	1523.9	1468.7	1386.6	1279.9	1155.5	1010.1	858.7	709.7	584.2
122.5°	1500.2	1490.4	1460.1	1405.8	1332.2	1235.8	1118.0	984.7	842.7	706.0	590.8
125°	1411.3	1401.9	1372.6	1328.0	1259.9	1171.9	1068.7	947.9	820.0	699.2	600.7
127.5°	1333.4	1325.9	1300.5	1258.8	1199.4	1118.2	1020.9	911.5	798.9	695.2	610.8
130°	1289.3	1279.9	1256.5	1216.6	1159.0	1081.7	989.0	888.1	784.9	693.3	618.2
132.5°	1243.2	1234.9	1213.3	1173.4	1116.8	1044.1	959.0	865.6	773.6	692.4	625.7
135°	1169.6	1164.9	1143.8	1105.1	1054.6	989.0	911.5	834.0	757.8	690.9	634.7
137.5°	1097.3	1090.4	1071.8	1038.4	992.5	935.2	873.7	809.0	746.8	690.7	642.7
140°	1047.6	1040.6	1023.0	992.5	954.9	903.3	849.4	793.0	740.2	689.8	646.4
142.5°	997.8	996.4	980.8	953.0	917.4	874.2	827.8	779.9	733.7	689.8	649.2
145°	933.8	930.3	918.6	898.6	870.5	836.5	800.1	761.3	725.0	687.4	652.3
147.5°	880.1	878.0	870.0	854.0	830.8	806.0	777.6	747.1	716.1	683.3	653.2
150°	848.2	847.0	840.0	825.9	808.3	787.2	762.5	736.7	708.5	680.4	652.3
152.5°	820.9	820.7	815.6	803.3	789.5	771.2	750.3	726.4	702.0	675.7	650.4
155°	784.9	787.2	782.4	774.3	761.3	748.4	730.8	712.1	689.8	667.5	647.5
157.5°	754.1	754.1	751.9	745.2	736.0	725.9	711.1	695.4	678.3	659.0	642.2
160°	734.4	734.4	733.2	727.3	719.1	710.9	698.0	685.1	669.8	653.5	639.3
162.5°	715.6	716.5	715.4	711.3	703.2	696.8	685.8	674.8	662.4	648.7	636.5
165°	688.6	689.8	689.8	685.1	680.4	675.7	667.5	659.3	649.9	639.3	631.2
167.5°	663.8	665.2	665.4	662.8	660.8	656.5	650.9	644.5	637.7	631.2	625.7
170°	648.7	651.1	652.3	648.7	647.5	645.2	640.6	637.0	631.2	626.4	622.9
172.5°	636.5	637.9	639.1	637.5	636.3	634.9	631.2	628.5	624.6	620.9	619.1
175°	620.6	622.9	624.1	622.9	622.9	621.8	620.6	619.5	615.9	614.7	613.6
177.5°	611.0	612.9	613.8	613.8	613.8	613.8	612.9	612.9	611.0	610.1	611.0
180°	610.1	610.1	610.1	610.1	610.1	610.1	610.1	610.1	610.1	610.1	610.1



TEST NUMBER: P331368-840

CATALOG NUMBER: SA2XXDIP-C675D1080U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1376.4	1373.1	1371.1	1363.6	1357.1	1350.5	1348.4	1349.2	1340.2	1331.5	1327.8
5°	1430.1	1419.8	1410.0	1396.0	1379.6	1361.5	1352.2	1344.9	1327.0	1307.4	1296.1
7.5°	1478.1	1463.4	1444.5	1418.3	1394.3	1365.9	1347.9	1331.9	1305.5	1277.9	1260.9
10°	1507.4	1487.2	1463.0	1431.1	1401.7	1367.2	1342.9	1318.7	1287.8	1254.8	1234.2
12.5°	1532.6	1505.4	1481.6	1440.6	1405.8	1362.6	1333.8	1299.7	1267.2	1228.0	1207.8
15°	1592.5	1542.5	1497.0	1450.7	1407.9	1347.6	1315.7	1269.7	1226.9	1178.5	1155.3
17.5°	1638.7	1582.6	1511.1	1452.1	1402.2	1335.4	1288.5	1233.6	1183.0	1127.5	1096.0
20°	1665.2	1600.6	1523.9	1453.8	1393.9	1317.7	1266.7	1210.4	1151.1	1088.7	1054.7
22.5°	1680.8	1613.1	1537.1	1447.5	1377.5	1303.2	1239.0	1177.4	1117.3	1050.1	1014.3
25°	1685.8	1623.9	1543.5	1442.4	1356.9	1272.8	1195.5	1135.7	1063.0	1000.1	948.1
27.5°	1661.2	1616.9	1539.5	1432.7	1333.0	1234.8	1148.6	1080.9	1004.1	935.8	883.5
30°	1631.1	1605.3	1530.0	1422.8	1314.0	1208.4	1113.5	1036.7	960.4	891.3	837.7
32.5°	1584.5	1578.9	1512.8	1408.8	1293.8	1175.0	1076.8	999.2	914.6	846.8	795.7
35°	1493.0	1517.7	1475.9	1377.5	1255.8	1127.4	1021.3	932.6	845.0	780.0	732.1
37.5°	1370.3	1431.7	1420.8	1331.6	1204.5	1075.7	958.5	865.8	782.2	716.7	669.6
40°	1285.7	1364.0	1375.4	1296.6	1168.2	1035.7	911.4	819.2	737.7	677.9	630.5
42.5°	1195.0	1286.6	1317.7	1254.5	1128.5	993.6	869.4	773.8	693.2	635.0	593.0
45°	1042.9	1164.1	1220.2	1184.2	1062.5	924.3	796.5	699.5	626.3	571.7	539.3
47.5°	900.7	1033.1	1108.6	1095.9	989.0	852.1	725.8	632.8	561.5	517.9	488.8
50°	800.1	936.1	1027.4	1031.6	936.1	800.6	673.8	586.1	520.7	480.0	456.3
52.5°	712.7	842.5	942.1	963.9	877.2	747.0	627.2	540.0	482.3	444.8	423.6
55°	598.5	708.3	818.6	858.9	789.2	665.5	554.7	477.9	423.7	398.0	379.4
57.5°	497.6	589.2	691.1	735.5	692.6	586.6	482.7	416.1	372.1	349.5	335.3
60°	444.3	516.5	607.2	660.4	623.3	529.0	438.2	374.8	338.7	318.6	305.2
62.5°	394.9	458.8	535.5	584.1	563.9	474.9	393.6	337.7	306.5	287.6	278.0
65°	325.8	376.4	435.7	480.5	467.1	399.5	333.1	285.1	260.3	245.4	237.6
67.5°	268.3	304.8	345.9	385.2	374.4	326.5	273.2	235.8	217.3	204.5	199.9
70°	232.0	259.8	296.4	327.9	319.1	279.9	237.6	205.7	189.8	178.8	174.2
72.5°	197.3	220.3	248.1	273.9	267.9	235.4	200.2	176.0	163.7	153.7	149.9
75°	149.0	166.5	183.5	200.6	198.9	173.7	153.1	134.5	124.7	117.0	115.4
77.5°	110.0	119.8	131.4	141.5	138.7	124.2	108.1	97.5	90.2	85.0	84.2
80°	84.0	89.7	98.0	105.1	101.6	95.3	82.5	74.7	69.6	64.4	62.4
82.5°	60.9	66.7	71.6	75.4	72.7	67.0	59.0	53.7	50.6	47.2	46.3
85°	31.9	35.0	37.2	38.2	37.2	33.5	29.9	27.9	25.2	23.7	23.2
87.5°	18.7	17.1	15.9	16.1	14.3	13.8	11.2	9.3	9.6	10.1	9.8
90°	31.7	23.4	17.6	14.0	11.7	9.4	4.6	1.2	4.6	9.4	11.7
92.5°	117.0	79.8	53.2	42.2	34.2	29.1	20.6	14.3	20.6	29.1	34.2
95°	270.9	169.0	114.9	86.8	68.1	57.5	45.7	41.1	45.7	57.5	68.1
97.5°	365.1	222.9	155.1	123.2	101.6	85.6	73.2	66.9	73.2	85.6	101.6
100°	384.8	241.7	179.5	146.6	123.2	104.4	93.8	90.3	93.8	104.4	123.2
102.5°	385.8	258.5	201.1	168.2	143.8	125.0	114.5	111.9	114.5	125.0	143.8
105°	391.8	287.4	232.3	199.4	173.6	156.0	147.8	143.1	147.8	156.0	173.6
107.5°	408.0	317.0	263.5	230.5	204.8	188.6	180.7	176.9	180.7	188.6	204.8
110°	421.1	336.7	285.1	251.1	226.4	211.2	204.1	199.4	204.1	211.2	226.4



TEST NUMBER: P331368-840

CATALOG NUMBER: SA2XXDIP-C675D1080U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	435.3	355.5	305.7	270.7	247.0	232.8	224.8	220.0	224.8	232.8	247.0
115°	456.4	384.8	334.4	302.7	279.2	265.1	258.1	252.3	258.1	265.1	279.2
117.5°	478.9	411.7	365.1	332.2	309.7	297.3	290.2	285.6	290.2	297.3	309.7
120°	493.9	430.5	384.8	351.9	328.5	317.9	310.8	306.2	310.8	317.9	328.5
122.5°	507.1	448.4	405.5	371.6	348.2	336.7	329.6	325.9	329.6	336.7	348.2
125°	528.0	475.1	432.9	400.0	376.6	362.5	355.5	351.9	355.5	362.5	376.6
127.5°	547.3	500.0	458.9	425.2	402.6	387.2	377.3	372.5	377.3	387.2	402.6
130°	559.6	515.0	473.9	441.1	417.7	401.2	389.5	384.8	389.5	401.2	417.7
132.5°	571.8	528.2	489.0	456.2	431.7	414.3	401.7	396.1	401.7	414.3	431.7
135°	587.7	546.6	509.2	476.3	449.3	431.7	417.7	412.9	417.7	431.7	449.3
137.5°	600.0	561.7	524.6	494.1	467.4	448.6	434.5	428.9	434.5	448.6	467.4
140°	606.5	570.2	534.9	504.4	478.7	459.9	445.8	441.1	445.8	459.9	478.7
142.5°	612.2	576.7	542.5	513.8	489.0	470.2	457.1	453.3	457.1	470.2	489.0
145°	619.5	586.5	554.9	529.1	505.6	488.1	476.3	471.6	476.3	488.1	505.6
147.5°	623.4	594.5	564.7	541.8	522.3	506.0	494.8	491.3	494.8	506.0	522.3
150°	625.3	598.3	571.3	550.2	532.6	517.4	508.0	504.4	508.0	517.4	532.6
152.5°	626.2	602.1	577.8	558.7	542.0	528.6	519.3	517.6	519.3	528.6	542.0
155°	627.6	607.6	587.7	570.2	557.2	544.3	537.2	536.1	537.2	544.3	557.2
157.5°	627.6	611.7	594.8	580.0	569.7	558.5	552.8	551.6	552.8	558.5	569.7
160°	627.6	613.6	599.5	586.5	577.1	567.7	563.1	561.9	563.1	567.7	577.1
162.5°	626.7	614.5	602.3	592.2	583.7	576.2	571.6	572.3	571.6	576.2	583.7
165°	624.1	615.9	605.3	598.3	592.4	585.4	583.1	584.2	583.1	585.4	592.4
167.5°	622.5	615.6	607.9	603.5	599.3	594.8	592.7	594.1	592.7	594.8	599.3
170°	620.6	614.7	608.8	605.3	603.0	599.5	598.3	600.7	598.3	599.5	603.0
172.5°	617.7	613.8	609.8	607.2	605.8	602.3	603.0	604.4	603.0	602.3	605.8
175°	614.7	612.4	610.1	608.8	608.8	606.5	607.6	608.8	607.6	606.5	608.8
177.5°	612.9	611.0	610.1	610.1	610.1	608.1	609.0	611.0	609.0	608.1	610.1
180°	610.1	610.1	610.1	610.1	610.1	610.1	610.1	610.1	610.1	610.1	610.1



TEST NUMBER: P331368-840
 CATALOG NUMBER: SA2XXDIP-C675D1080U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1323.6	1321.2	1312.5	1308.0	1300.5	1293.5	1289.0	1291.1	1292.7	1291.9	1290.6
5°	1285.7	1275.9	1260.9	1248.1	1238.8	1221.7	1214.6	1210.9	1207.9	1204.3	1200.6
7.5°	1240.5	1225.1	1203.7	1185.3	1167.9	1146.8	1134.8	1127.5	1120.1	1112.0	1104.8
10°	1208.4	1186.7	1164.1	1138.2	1117.6	1098.5	1081.6	1070.3	1060.0	1050.2	1042.9
12.5°	1174.6	1149.6	1121.6	1086.3	1063.6	1036.3	1033.7	1013.7	997.6	991.6	983.1
15°	1120.7	1085.7	1050.2	1008.4	990.3	965.5	950.1	934.6	920.7	910.9	908.4
17.5°	1059.6	1014.2	978.9	948.9	919.3	893.9	879.7	867.3	855.9	842.7	841.0
20°	1013.0	973.8	935.1	908.9	878.5	852.6	835.2	822.7	812.9	805.3	798.5
22.5°	968.9	925.9	890.6	861.8	831.8	811.0	797.2	785.3	777.1	768.5	762.2
25°	898.1	864.5	825.9	793.3	768.6	755.3	743.9	733.6	728.4	722.8	715.6
27.5°	836.1	798.8	762.7	737.5	715.8	703.9	695.8	688.8	684.0	680.6	676.6
30°	792.3	754.7	726.4	701.7	683.6	671.8	666.6	662.5	656.8	654.7	652.7
32.5°	750.3	716.4	692.2	670.7	653.5	645.7	641.0	637.3	632.9	630.8	626.6
35°	690.7	662.5	638.7	626.8	613.0	606.2	602.7	597.4	593.4	591.3	590.8
37.5°	634.8	610.2	594.6	579.4	573.5	569.4	564.4	560.9	559.7	559.4	558.9
40°	598.5	578.5	564.5	552.1	549.6	543.3	539.3	536.1	536.1	536.6	536.1
42.5°	565.5	547.4	535.2	524.5	521.5	517.8	513.6	513.4	514.3	516.0	514.3
45°	515.5	502.6	493.8	488.7	483.0	479.4	478.9	480.5	481.0	481.5	483.0
47.5°	469.5	461.0	453.0	447.4	444.8	444.2	443.6	446.4	448.8	449.7	452.1
50°	442.3	432.5	425.9	422.2	420.1	419.1	420.1	423.2	425.3	427.9	429.4
52.5°	411.8	404.9	400.2	397.5	396.7	397.3	397.5	401.0	404.2	405.2	406.0
55°	369.6	364.5	363.5	358.8	360.8	360.3	362.9	365.0	368.1	371.1	371.7
57.5°	327.6	323.5	320.6	321.0	321.6	324.0	326.1	329.7	333.1	336.3	336.6
60°	299.5	297.4	295.9	295.9	296.9	300.0	302.7	306.2	308.3	310.3	311.8
62.5°	274.0	271.9	270.3	271.1	273.9	275.7	278.7	280.6	282.7	284.8	285.5
65°	233.5	232.5	234.1	235.1	235.6	238.1	241.8	243.3	245.4	246.4	250.0
67.5°	196.3	196.5	196.3	197.7	200.8	201.4	204.8	208.3	208.7	210.8	213.1
70°	171.2	172.2	173.2	174.2	176.8	177.8	180.5	182.0	184.0	185.6	187.1
72.5°	148.0	148.2	149.3	149.1	151.3	153.5	155.7	157.2	159.3	161.3	162.8
75°	113.9	113.9	114.9	115.4	118.1	120.7	120.1	121.2	123.2	125.2	126.3
77.5°	83.2	82.1	83.2	83.7	84.5	86.7	87.2	88.6	90.9	90.2	91.4
80°	63.4	61.9	63.4	63.9	63.9	66.6	66.6	67.6	69.1	67.6	69.1
82.5°	45.2	44.5	45.6	45.7	46.6	46.7	47.6	47.8	49.3	48.6	49.3
85°	22.7	22.2	22.7	22.2	22.7	23.2	23.2	22.7	22.7	23.7	22.2
87.5°	9.8	10.1	10.9	12.5	13.5	13.3	12.7	12.4	12.0	11.6	11.9
90°	14.0	17.6	23.4	31.7	38.7	39.9	38.7	37.6	35.2	37.6	38.7
92.5°	42.2	53.2	79.8	117.0	150.4	152.5	128.9	102.3	87.8	77.9	70.6
95°	86.8	114.9	169.0	270.9	407.1	459.9	402.4	307.4	235.8	186.5	160.7
97.5°	123.2	155.1	222.9	365.1	591.3	785.1	823.5	717.2	586.8	459.9	375.2
100°	146.6	179.5	241.7	384.8	638.1	926.8	1095.7	1071.1	925.6	764.9	622.9
102.5°	168.2	201.1	258.5	385.8	620.4	931.5	1197.1	1302.9	1270.0	1152.5	1002.1
105°	199.4	232.3	287.4	391.8	585.4	869.3	1181.3	1425.3	1557.9	1573.2	1534.5
107.5°	230.5	263.5	317.0	408.0	568.0	802.6	1078.3	1337.2	1536.8	1658.8	1715.6
110°	251.1	285.1	336.7	421.1	564.3	770.7	1013.6	1261.1	1471.1	1621.2	1717.5



TEST NUMBER: P331368-840

CATALOG NUMBER: SA2XXDIP-C675D1080U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	270.7	305.7	355.5	435.3	565.2	750.1	968.6	1191.6	1393.2	1553.7	1664.0
115°	302.7	334.4	384.8	456.4	570.2	727.3	912.7	1106.3	1287.0	1440.6	1561.5
117.5°	332.2	365.1	411.7	478.9	578.6	716.3	877.5	1042.0	1200.6	1340.0	1453.3
120°	351.9	384.8	430.5	493.9	584.2	709.7	858.7	1010.1	1155.5	1279.9	1386.6
122.5°	371.6	405.5	448.4	507.1	590.8	706.0	842.7	984.7	1118.0	1235.8	1332.2
125°	400.0	432.9	475.1	528.0	600.7	699.2	820.0	947.9	1068.7	1171.9	1259.9
127.5°	425.2	458.9	500.0	547.3	610.8	695.2	798.9	911.5	1020.9	1118.2	1199.4
130°	441.1	473.9	515.0	559.6	618.2	693.3	784.9	888.1	989.0	1081.7	1159.0
132.5°	456.2	489.0	528.2	571.8	625.7	692.4	773.6	865.6	959.0	1044.1	1116.8
135°	476.3	509.2	546.6	587.7	634.7	690.9	757.8	834.0	911.5	989.0	1054.6
137.5°	494.1	524.6	561.7	600.0	642.7	690.7	746.8	809.0	873.7	935.2	992.5
140°	504.4	534.9	570.2	606.5	646.4	689.8	740.2	793.0	849.4	903.3	954.9
142.5°	513.8	542.5	576.7	612.2	649.2	689.8	733.7	779.9	827.8	874.2	917.4
145°	529.1	554.9	586.5	619.5	652.3	687.4	725.0	761.3	800.1	836.5	870.5
147.5°	541.8	564.7	594.5	623.4	653.2	683.3	716.1	747.1	777.6	806.0	830.8
150°	550.2	571.3	598.3	625.3	652.3	680.4	708.5	736.7	762.5	787.2	808.3
152.5°	558.7	577.8	602.1	626.2	650.4	675.7	702.0	726.4	750.3	771.2	789.5
155°	570.2	587.7	607.6	627.6	647.5	667.5	689.8	712.1	730.8	748.4	761.3
157.5°	580.0	594.8	611.7	627.6	642.2	659.0	678.3	695.4	711.1	725.9	736.0
160°	586.5	599.5	613.6	627.6	639.3	653.5	669.8	685.1	698.0	710.9	719.1
162.5°	592.2	602.3	614.5	626.7	636.5	648.7	662.4	674.8	685.8	696.8	703.2
165°	598.3	605.3	615.9	624.1	631.2	639.3	649.9	659.3	667.5	675.7	680.4
167.5°	603.5	607.9	615.6	622.5	625.7	631.2	637.7	644.5	650.9	656.5	660.8
170°	605.3	608.8	614.7	620.6	622.9	626.4	631.2	637.0	640.6	645.2	647.5
172.5°	607.2	609.8	613.8	617.7	619.1	620.9	624.6	628.5	631.2	634.9	636.3
175°	608.8	610.1	612.4	614.7	613.6	614.7	615.9	619.5	620.6	621.8	622.9
177.5°	610.1	610.1	611.0	612.9	611.0	610.1	611.0	612.9	612.9	613.8	613.8
180°	610.1	610.1	610.1	610.1	610.1	610.1	610.1	610.1	610.1	610.1	610.1



TEST NUMBER: P331368-840

CATALOG NUMBER: SA2XXDIP-C675D1080U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1286.6	1285.7	1285.7	1282.0	1285.7	1285.7	1286.6	1290.6	1291.9	1292.7	1291.1
5°	1193.5	1191.8	1189.3	1191.8	1189.3	1191.8	1193.5	1200.6	1204.3	1207.9	1210.9
7.5°	1101.4	1095.2	1094.3	1088.1	1094.3	1095.2	1101.4	1104.8	1112.0	1120.1	1127.5
10°	1034.1	1030.0	1029.5	1019.7	1029.5	1030.0	1034.1	1042.9	1050.2	1060.0	1070.3
12.5°	983.0	973.1	975.0	969.4	975.0	973.1	983.0	983.1	991.6	997.6	1013.7
15°	894.4	894.4	892.3	883.6	892.3	894.4	894.4	908.4	910.9	920.7	934.6
17.5°	830.8	829.8	824.9	827.3	824.9	829.8	830.8	841.0	842.7	855.9	867.3
20°	792.8	789.8	783.6	783.6	783.6	789.8	792.8	798.5	805.3	812.9	822.7
22.5°	757.0	756.8	750.2	752.2	750.2	756.8	757.0	762.2	768.5	777.1	785.3
25°	715.0	710.9	707.8	709.3	707.8	710.9	715.0	715.6	722.8	728.4	733.6
27.5°	675.2	673.0	672.8	668.5	672.8	673.0	675.2	676.6	680.6	684.0	688.8
30°	652.2	647.0	648.0	645.4	648.0	647.0	652.2	652.7	654.7	656.8	662.5
32.5°	625.7	623.9	622.9	620.7	622.9	623.9	625.7	626.6	630.8	632.9	637.3
35°	589.8	590.3	587.7	588.8	587.7	590.3	589.8	590.8	591.3	593.4	597.4
37.5°	558.4	560.0	558.8	559.1	558.8	560.0	558.4	558.9	559.4	559.7	560.9
40°	537.7	537.7	537.7	539.3	537.7	537.7	537.7	536.1	536.6	536.1	536.1
42.5°	517.9	517.1	516.2	516.1	516.2	517.1	517.9	514.3	516.0	514.3	513.4
45°	484.0	485.6	486.1	483.5	486.1	485.6	484.0	483.0	481.5	481.0	480.5
47.5°	453.4	453.6	453.4	455.8	453.4	453.6	453.4	452.1	449.7	448.8	446.4
50°	432.0	431.0	432.0	431.0	432.0	431.0	432.0	429.4	427.9	425.3	423.2
52.5°	409.3	409.5	408.9	408.7	408.9	409.5	409.3	406.0	405.2	404.2	401.0
55°	373.8	374.8	374.3	374.3	374.3	374.8	373.8	371.7	371.1	368.1	365.0
57.5°	337.0	337.9	338.6	336.3	338.6	337.9	337.0	336.6	336.3	333.1	329.7
60°	311.3	314.0	313.5	312.5	313.5	314.0	311.3	311.8	310.3	308.3	306.2
62.5°	287.9	288.8	288.7	288.5	288.7	288.8	287.9	285.5	284.8	282.7	280.6
65°	251.6	252.6	251.1	252.6	251.1	252.6	251.6	250.0	246.4	245.4	243.3
67.5°	212.5	212.8	214.0	214.7	214.0	212.8	212.5	213.1	210.8	208.7	208.3
70°	188.1	187.6	189.1	190.8	189.1	187.6	188.1	187.1	185.6	184.0	182.0
72.5°	162.6	163.7	163.2	164.3	163.2	163.7	162.6	162.8	161.3	159.3	157.2
75°	125.2	126.8	126.3	127.8	126.3	126.8	125.2	126.3	125.2	123.2	121.2
77.5°	90.5	90.7	90.5	91.4	90.5	90.7	90.5	91.4	90.2	90.9	88.6
80°	69.1	68.1	67.1	69.1	67.1	68.1	69.1	69.1	67.6	69.1	67.6
82.5°	48.1	48.7	47.7	47.7	47.7	48.7	48.1	49.3	48.6	49.3	47.8
85°	22.2	21.6	20.6	20.6	20.6	21.6	22.2	22.2	23.7	22.7	22.7
87.5°	11.9	11.4	11.4	11.0	11.4	11.4	11.9	11.9	11.6	12.0	12.4
90°	38.7	38.7	38.7	38.7	38.7	38.7	38.7	38.7	37.6	35.2	37.6
92.5°	69.7	65.9	66.9	65.0	66.9	65.9	69.7	70.6	77.9	87.8	102.3
95°	145.4	136.1	132.6	133.7	132.6	136.1	145.4	160.7	186.5	235.8	307.4
97.5°	319.1	290.2	273.1	263.3	273.1	290.2	319.1	375.2	459.9	586.8	717.2
100°	525.5	475.1	441.1	420.0	441.1	475.1	525.5	622.9	764.9	925.6	1071.1
102.5°	896.3	810.2	767.7	739.1	767.7	810.2	896.3	1002.1	1152.5	1270.0	1302.9
105°	1461.7	1389.0	1338.6	1322.1	1338.6	1389.0	1461.7	1534.5	1573.2	1557.9	1425.3
107.5°	1724.7	1720.7	1710.6	1688.8	1710.6	1720.7	1724.7	1715.6	1658.8	1536.8	1337.2
110°	1767.9	1790.2	1800.8	1799.6	1800.8	1790.2	1767.9	1717.5	1621.2	1471.1	1261.1



TEST NUMBER: P331368-840

CATALOG NUMBER: SA2XXDIP-C675D1080U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1734.1	1771.4	1791.4	1797.7	1791.4	1771.4	1734.1	1664.0	1553.7	1393.2	1191.6
115°	1644.8	1698.7	1729.2	1739.8	1729.2	1698.7	1644.8	1561.5	1440.6	1287.0	1106.3
117.5°	1538.2	1595.2	1627.4	1636.3	1627.4	1595.2	1538.2	1453.3	1340.0	1200.6	1042.0
120°	1468.7	1523.9	1557.9	1569.6	1557.9	1523.9	1468.7	1386.6	1279.9	1155.5	1010.1
122.5°	1405.8	1460.1	1490.4	1500.2	1490.4	1460.1	1405.8	1332.2	1235.8	1118.0	984.7
125°	1328.0	1372.6	1401.9	1411.3	1401.9	1372.6	1328.0	1259.9	1171.9	1068.7	947.9
127.5°	1258.8	1300.5	1325.9	1333.4	1325.9	1300.5	1258.8	1199.4	1118.2	1020.9	911.5
130°	1216.6	1256.5	1279.9	1289.3	1279.9	1256.5	1216.6	1159.0	1081.7	989.0	888.1
132.5°	1173.4	1213.3	1234.9	1243.2	1234.9	1213.3	1173.4	1116.8	1044.1	959.0	865.6
135°	1105.1	1143.8	1164.9	1169.6	1164.9	1143.8	1105.1	1054.6	989.0	911.5	834.0
137.5°	1038.4	1071.8	1090.4	1097.3	1090.4	1071.8	1038.4	992.5	935.2	873.7	809.0
140°	992.5	1023.0	1040.6	1047.6	1040.6	1023.0	992.5	954.9	903.3	849.4	793.0
142.5°	953.0	980.8	996.4	997.8	996.4	980.8	953.0	917.4	874.2	827.8	779.9
145°	898.6	918.6	930.3	933.8	930.3	918.6	898.6	870.5	836.5	800.1	761.3
147.5°	854.0	870.0	878.0	880.1	878.0	870.0	854.0	830.8	806.0	777.6	747.1
150°	825.9	840.0	847.0	848.2	847.0	840.0	825.9	808.3	787.2	762.5	736.7
152.5°	803.3	815.6	820.7	820.9	820.7	815.6	803.3	789.5	771.2	750.3	726.4
155°	774.3	782.4	787.2	784.9	787.2	782.4	774.3	761.3	748.4	730.8	712.1
157.5°	745.2	751.9	754.1	754.1	754.1	751.9	745.2	736.0	725.9	711.1	695.4
160°	727.3	733.2	734.4	734.4	734.4	733.2	727.3	719.1	710.9	698.0	685.1
162.5°	711.3	715.4	716.5	715.6	716.5	715.4	711.3	703.2	696.8	685.8	674.8
165°	685.1	689.8	689.8	688.6	689.8	689.8	685.1	680.4	675.7	667.5	659.3
167.5°	662.8	665.4	665.2	663.8	665.2	665.4	662.8	660.8	656.5	650.9	644.5
170°	648.7	652.3	651.1	648.7	651.1	652.3	648.7	647.5	645.2	640.6	637.0
172.5°	637.5	639.1	637.9	636.5	637.9	639.1	637.5	636.3	634.9	631.2	628.5
175°	622.9	624.1	622.9	620.6	622.9	624.1	622.9	622.9	621.8	620.6	619.5
177.5°	613.8	613.8	612.9	611.0	612.9	613.8	613.8	613.8	613.8	612.9	612.9
180°	610.1	610.1	610.1	610.1	610.1	610.1	610.1	610.1	610.1	610.1	610.1



TEST NUMBER: P331368-840

CATALOG NUMBER: SA2XXDIP-C675D1080U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1289.0	1293.5	1300.5	1308.0	1312.5	1321.2	1323.6	1327.8	1331.5	1340.2	1349.2
5°	1214.6	1221.7	1238.8	1248.1	1260.9	1275.9	1285.7	1296.1	1307.4	1327.0	1344.9
7.5°	1134.8	1146.8	1167.9	1185.3	1203.7	1225.1	1240.5	1260.9	1277.9	1305.5	1331.9
10°	1081.6	1098.5	1117.6	1138.2	1164.1	1186.7	1208.4	1234.2	1254.8	1287.8	1318.7
12.5°	1033.7	1036.3	1063.6	1086.3	1121.6	1149.6	1174.6	1207.8	1228.0	1267.2	1299.7
15°	950.1	965.5	990.3	1008.4	1050.2	1085.7	1120.7	1155.3	1178.5	1226.9	1269.7
17.5°	879.7	893.9	919.3	948.9	978.9	1014.2	1059.6	1096.0	1127.5	1183.0	1233.6
20°	835.2	852.6	878.5	908.9	935.1	973.8	1013.0	1054.7	1088.7	1151.1	1210.4
22.5°	797.2	811.0	831.8	861.8	890.6	925.9	968.9	1014.3	1050.1	1117.3	1177.4
25°	743.9	755.3	768.6	793.3	825.9	864.5	898.1	948.1	1000.1	1063.0	1135.7
27.5°	695.8	703.9	715.8	737.5	762.7	798.8	836.1	883.5	935.8	1004.1	1080.9
30°	666.6	671.8	683.6	701.7	726.4	754.7	792.3	837.7	891.3	960.4	1036.7
32.5°	641.0	645.7	653.5	670.7	692.2	716.4	750.3	795.7	846.8	914.6	999.2
35°	602.7	606.2	613.0	626.8	638.7	662.5	690.7	732.1	780.0	845.0	932.6
37.5°	564.4	569.4	573.5	579.4	594.6	610.2	634.8	669.6	716.7	782.2	865.8
40°	539.3	543.3	549.6	552.1	564.5	578.5	598.5	630.5	677.9	737.7	819.2
42.5°	513.6	517.8	521.5	524.5	535.2	547.4	565.5	593.0	635.0	693.2	773.8
45°	478.9	479.4	483.0	488.7	493.8	502.6	515.5	539.3	571.7	626.3	699.5
47.5°	443.6	444.2	444.8	447.4	453.0	461.0	469.5	488.8	517.9	561.5	632.8
50°	420.1	419.1	420.1	422.2	425.9	432.5	442.3	456.3	480.0	520.7	586.1
52.5°	397.5	397.3	396.7	397.5	400.2	404.9	411.8	423.6	444.8	482.3	540.0
55°	362.9	360.3	360.8	358.8	363.5	364.5	369.6	379.4	398.0	423.7	477.9
57.5°	326.1	324.0	321.6	321.0	320.6	323.5	327.6	335.3	349.5	372.1	416.1
60°	302.7	300.0	296.9	295.9	295.9	297.4	299.5	305.2	318.6	338.7	374.8
62.5°	278.7	275.7	273.9	271.1	270.3	271.9	274.0	278.0	287.6	306.5	337.7
65°	241.8	238.1	235.6	235.1	234.1	232.5	233.5	237.6	245.4	260.3	285.1
67.5°	204.8	201.4	200.8	197.7	196.3	196.5	196.3	199.9	204.5	217.3	235.8
70°	180.5	177.8	176.8	174.2	173.2	172.2	171.2	174.2	178.8	189.8	205.7
72.5°	155.7	153.5	151.3	149.1	149.3	148.2	148.0	149.9	153.7	163.7	176.0
75°	120.1	120.7	118.1	115.4	114.9	113.9	113.9	115.4	117.0	124.7	134.5
77.5°	87.2	86.7	84.5	83.7	83.2	82.1	83.2	84.2	85.0	90.2	97.5
80°	66.6	66.6	63.9	63.9	63.4	61.9	63.4	62.4	64.4	69.6	74.7
82.5°	47.6	46.7	46.6	45.7	45.6	44.5	45.2	46.3	47.2	50.6	53.7
85°	23.2	23.2	22.7	22.2	22.7	22.2	22.7	23.2	23.7	25.2	27.9
87.5°	12.7	13.3	13.5	12.5	10.9	10.1	9.8	9.8	10.1	9.6	9.3
90°	38.7	39.9	38.7	31.7	23.4	17.6	14.0	11.7	9.4	4.6	1.2
92.5°	128.9	152.5	150.4	117.0	79.8	53.2	42.2	34.2	29.1	20.6	14.3
95°	402.4	459.9	407.1	270.9	169.0	114.9	86.8	68.1	57.5	45.7	41.1
97.5°	823.5	785.1	591.3	365.1	222.9	155.1	123.2	101.6	85.6	73.2	66.9
100°	1095.7	926.8	638.1	384.8	241.7	179.5	146.6	123.2	104.4	93.8	90.3
102.5°	1197.1	931.5	620.4	385.8	258.5	201.1	168.2	143.8	125.0	114.5	111.9
105°	1181.3	869.3	585.4	391.8	287.4	232.3	199.4	173.6	156.0	147.8	143.1
107.5°	1078.3	802.6	568.0	408.0	317.0	263.5	230.5	204.8	188.6	180.7	176.9
110°	1013.6	770.7	564.3	421.1	336.7	285.1	251.1	226.4	211.2	204.1	199.4



TEST NUMBER: P331368-840

CATALOG NUMBER: SA2XXDIP-C675D1080U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	968.6	750.1	565.2	435.3	355.5	305.7	270.7	247.0	232.8	224.8	220.0
115°	912.7	727.3	570.2	456.4	384.8	334.4	302.7	279.2	265.1	258.1	252.3
117.5°	877.5	716.3	578.6	478.9	411.7	365.1	332.2	309.7	297.3	290.2	285.6
120°	858.7	709.7	584.2	493.9	430.5	384.8	351.9	328.5	317.9	310.8	306.2
122.5°	842.7	706.0	590.8	507.1	448.4	405.5	371.6	348.2	336.7	329.6	325.9
125°	820.0	699.2	600.7	528.0	475.1	432.9	400.0	376.6	362.5	355.5	351.9
127.5°	798.9	695.2	610.8	547.3	500.0	458.9	425.2	402.6	387.2	377.3	372.5
130°	784.9	693.3	618.2	559.6	515.0	473.9	441.1	417.7	401.2	389.5	384.8
132.5°	773.6	692.4	625.7	571.8	528.2	489.0	456.2	431.7	414.3	401.7	396.1
135°	757.8	690.9	634.7	587.7	546.6	509.2	476.3	449.3	431.7	417.7	412.9
137.5°	746.8	690.7	642.7	600.0	561.7	524.6	494.1	467.4	448.6	434.5	428.9
140°	740.2	689.8	646.4	606.5	570.2	534.9	504.4	478.7	459.9	445.8	441.1
142.5°	733.7	689.8	649.2	612.2	576.7	542.5	513.8	489.0	470.2	457.1	453.3
145°	725.0	687.4	652.3	619.5	586.5	554.9	529.1	505.6	488.1	476.3	471.6
147.5°	716.1	683.3	653.2	623.4	594.5	564.7	541.8	522.3	506.0	494.8	491.3
150°	708.5	680.4	652.3	625.3	598.3	571.3	550.2	532.6	517.4	508.0	504.4
152.5°	702.0	675.7	650.4	626.2	602.1	577.8	558.7	542.0	528.6	519.3	517.6
155°	689.8	667.5	647.5	627.6	607.6	587.7	570.2	557.2	544.3	537.2	536.1
157.5°	678.3	659.0	642.2	627.6	611.7	594.8	580.0	569.7	558.5	552.8	551.6
160°	669.8	653.5	639.3	627.6	613.6	599.5	586.5	577.1	567.7	563.1	561.9
162.5°	662.4	648.7	636.5	626.7	614.5	602.3	592.2	583.7	576.2	571.6	572.3
165°	649.9	639.3	631.2	624.1	615.9	605.3	598.3	592.4	585.4	583.1	584.2
167.5°	637.7	631.2	625.7	622.5	615.6	607.9	603.5	599.3	594.8	592.7	594.1
170°	631.2	626.4	622.9	620.6	614.7	608.8	605.3	603.0	599.5	598.3	600.7
172.5°	624.6	620.9	619.1	617.7	613.8	609.8	607.2	605.8	602.3	603.0	604.4
175°	615.9	614.7	613.6	614.7	612.4	610.1	608.8	608.8	606.5	607.6	608.8
177.5°	611.0	610.1	611.0	612.9	611.0	610.1	610.1	610.1	608.1	609.0	611.0
180°	610.1	610.1	610.1	610.1	610.1	610.1	610.1	610.1	610.1	610.1	610.1



TEST NUMBER: P331368-840

CATALOG NUMBER: SA2XXDIP-C675D1080U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1348.4	1350.5	1357.1	1363.6	1371.1	1373.1	1376.4	1373.5	1372.7	1380.6	1386.3
5°	1352.2	1361.5	1379.6	1396.0	1410.0	1419.8	1430.1	1434.2	1441.9	1452.7	1466.1
7.5°	1347.9	1365.9	1394.3	1418.3	1444.5	1463.4	1478.1	1490.7	1505.9	1526.4	1548.8
10°	1342.9	1367.2	1401.7	1431.1	1463.0	1487.2	1507.4	1526.9	1549.6	1578.0	1607.4
12.5°	1333.8	1362.6	1405.8	1440.6	1481.6	1505.4	1532.6	1574.8	1599.1	1638.6	1680.0
15°	1315.7	1347.6	1407.9	1450.7	1497.0	1542.5	1592.5	1632.6	1672.8	1696.1	1754.3
17.5°	1288.5	1335.4	1402.2	1452.1	1511.1	1582.6	1638.7	1684.3	1730.7	1768.4	1797.6
20°	1266.7	1317.7	1393.9	1453.8	1523.9	1600.6	1665.2	1711.5	1751.7	1783.2	1801.2
22.5°	1239.0	1303.2	1377.5	1447.5	1537.1	1613.1	1680.8	1717.3	1750.9	1766.3	1773.2
25°	1195.5	1272.8	1356.9	1442.4	1543.5	1623.9	1685.8	1707.9	1717.7	1702.7	1678.0
27.5°	1148.6	1234.8	1333.0	1432.7	1539.5	1616.9	1661.2	1657.7	1641.1	1592.8	1554.1
30°	1113.5	1208.4	1314.0	1422.8	1530.0	1605.3	1631.1	1605.3	1567.7	1513.6	1458.4
32.5°	1076.8	1175.0	1293.8	1408.8	1512.8	1578.9	1584.5	1540.1	1481.9	1420.4	1351.6
35°	1021.3	1127.4	1255.8	1377.5	1475.9	1517.7	1493.0	1414.6	1345.5	1261.5	1167.6
37.5°	958.5	1075.7	1204.5	1331.6	1420.8	1431.7	1370.3	1287.8	1190.3	1091.6	981.2
40°	911.4	1035.7	1168.2	1296.6	1375.4	1364.0	1285.7	1195.0	1078.9	958.4	855.8
42.5°	869.4	993.6	1128.5	1254.5	1317.7	1286.6	1195.0	1083.6	959.0	845.4	751.4
45°	796.5	924.3	1062.5	1184.2	1220.2	1164.1	1042.9	919.2	796.5	701.7	627.4
47.5°	725.8	852.1	989.0	1095.9	1108.6	1033.1	900.7	773.4	667.9	590.7	538.3
50°	673.8	800.6	936.1	1031.6	1027.4	936.1	800.1	678.9	590.8	528.4	493.3
52.5°	627.2	747.0	877.2	963.9	942.1	842.5	712.7	605.1	532.6	483.8	452.1
55°	554.7	665.5	789.2	858.9	818.6	708.3	598.5	511.9	458.3	421.7	397.0
57.5°	482.7	586.6	692.6	735.5	691.1	589.2	497.6	434.7	394.5	367.4	351.2
60°	438.2	529.0	623.3	660.4	607.2	516.5	444.3	388.2	355.7	333.6	319.1
62.5°	393.6	474.9	563.9	584.1	535.5	458.8	394.9	348.2	321.4	301.7	288.2
65°	333.1	399.5	467.1	480.5	435.7	376.4	325.8	295.4	271.7	257.2	246.4
67.5°	273.2	326.5	374.4	385.2	345.9	304.8	268.3	241.8	225.7	213.7	204.6
70°	237.6	279.9	319.1	327.9	296.4	259.8	232.0	210.9	196.4	186.1	177.3
72.5°	200.2	235.4	267.9	273.9	248.1	220.3	197.3	180.8	167.9	161.4	153.0
75°	153.1	173.7	198.9	200.6	183.5	166.5	149.0	138.1	131.5	123.2	119.1
77.5°	108.1	124.2	138.7	141.5	131.4	119.8	110.0	101.5	95.7	92.0	88.2
80°	82.5	95.3	101.6	105.1	98.0	89.7	84.0	78.4	74.7	72.2	69.6
82.5°	59.0	67.0	72.7	75.4	71.6	66.7	60.9	57.8	54.9	52.8	51.9
85°	29.9	33.5	37.2	38.2	37.2	35.0	31.9	31.9	30.4	29.9	29.9
87.5°	11.2	13.8	14.3	16.1	15.9	17.1	18.7	19.7	19.5	18.9	18.3
90°	4.6	9.4	11.7	14.0	17.6	23.4	31.7	38.7	39.9	38.7	37.6
92.5°	20.6	29.1	34.2	42.2	53.2	79.8	117.0	150.4	152.5	128.9	102.3
95°	45.7	57.5	68.1	86.8	114.9	169.0	270.9	407.1	459.9	402.4	307.4
97.5°	73.2	85.6	101.6	123.2	155.1	222.9	365.1	591.3	785.1	823.5	717.2
100°	93.8	104.4	123.2	146.6	179.5	241.7	384.8	638.1	926.8	1095.7	1071.1
102.5°	114.5	125.0	143.8	168.2	201.1	258.5	385.8	620.4	931.5	1197.1	1302.9
105°	147.8	156.0	173.6	199.4	232.3	287.4	391.8	585.4	869.3	1181.3	1425.3
107.5°	180.7	188.6	204.8	230.5	263.5	317.0	408.0	568.0	802.6	1078.3	1337.2
110°	204.1	211.2	226.4	251.1	285.1	336.7	421.1	564.3	770.7	1013.6	1261.1



TEST NUMBER: P331368-840

CATALOG NUMBER: SA2XXDIP-C675D1080U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	224.8	232.8	247.0	270.7	305.7	355.5	435.3	565.2	750.1	968.6	1191.6
115°	258.1	265.1	279.2	302.7	334.4	384.8	456.4	570.2	727.3	912.7	1106.3
117.5°	290.2	297.3	309.7	332.2	365.1	411.7	478.9	578.6	716.3	877.5	1042.0
120°	310.8	317.9	328.5	351.9	384.8	430.5	493.9	584.2	709.7	858.7	1010.1
122.5°	329.6	336.7	348.2	371.6	405.5	448.4	507.1	590.8	706.0	842.7	984.7
125°	355.5	362.5	376.6	400.0	432.9	475.1	528.0	600.7	699.2	820.0	947.9
127.5°	377.3	387.2	402.6	425.2	458.9	500.0	547.3	610.8	695.2	798.9	911.5
130°	389.5	401.2	417.7	441.1	473.9	515.0	559.6	618.2	693.3	784.9	888.1
132.5°	401.7	414.3	431.7	456.2	489.0	528.2	571.8	625.7	692.4	773.6	865.6
135°	417.7	431.7	449.3	476.3	509.2	546.6	587.7	634.7	690.9	757.8	834.0
137.5°	434.5	448.6	467.4	494.1	524.6	561.7	600.0	642.7	690.7	746.8	809.0
140°	445.8	459.9	478.7	504.4	534.9	570.2	606.5	646.4	689.8	740.2	793.0
142.5°	457.1	470.2	489.0	513.8	542.5	576.7	612.2	649.2	689.8	733.7	779.9
145°	476.3	488.1	505.6	529.1	554.9	586.5	619.5	652.3	687.4	725.0	761.3
147.5°	494.8	506.0	522.3	541.8	564.7	594.5	623.4	653.2	683.3	716.1	747.1
150°	508.0	517.4	532.6	550.2	571.3	598.3	625.3	652.3	680.4	708.5	736.7
152.5°	519.3	528.6	542.0	558.7	577.8	602.1	626.2	650.4	675.7	702.0	726.4
155°	537.2	544.3	557.2	570.2	587.7	607.6	627.6	647.5	667.5	689.8	712.1
157.5°	552.8	558.5	569.7	580.0	594.8	611.7	627.6	642.2	659.0	678.3	695.4
160°	563.1	567.7	577.1	586.5	599.5	613.6	627.6	639.3	653.5	669.8	685.1
162.5°	571.6	576.2	583.7	592.2	602.3	614.5	626.7	636.5	648.7	662.4	674.8
165°	583.1	585.4	592.4	598.3	605.3	615.9	624.1	631.2	639.3	649.9	659.3
167.5°	592.7	594.8	599.3	603.5	607.9	615.6	622.5	625.7	631.2	637.7	644.5
170°	598.3	599.5	603.0	605.3	608.8	614.7	620.6	622.9	626.4	631.2	637.0
172.5°	603.0	602.3	605.8	607.2	609.8	613.8	617.7	619.1	620.9	624.6	628.5
175°	607.6	606.5	608.8	608.8	610.1	612.4	614.7	613.6	614.7	615.9	619.5
177.5°	609.0	608.1	610.1	610.1	610.1	611.0	612.9	611.0	610.1	611.0	612.9
180°	610.1	610.1	610.1	610.1	610.1	610.1	610.1	610.1	610.1	610.1	610.1



TEST NUMBER: P331368-840

CATALOG NUMBER: SA2XXDIP-C675D1080U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1391.3	1397.0	1397.0	1397.9	1404.5	1403.6	1403.2
5°	1480.6	1489.3	1490.4	1499.6	1505.8	1503.8	1498.1
7.5°	1564.8	1581.1	1593.5	1600.3	1608.5	1613.6	1611.3
10°	1631.6	1655.4	1669.8	1679.6	1691.4	1700.2	1697.1
12.5°	1692.2	1720.5	1740.3	1757.1	1758.7	1769.9	1762.2
15°	1786.8	1816.6	1819.8	1832.2	1842.0	1840.9	1841.4
17.5°	1818.1	1827.7	1829.6	1829.9	1830.0	1826.3	1818.6
20°	1806.9	1803.3	1794.5	1787.9	1775.9	1774.4	1764.1
22.5°	1754.1	1742.6	1720.7	1706.2	1687.7	1682.8	1680.0
25°	1650.2	1624.9	1589.8	1556.3	1547.1	1529.0	1534.2
27.5°	1507.6	1468.2	1430.3	1403.0	1378.4	1351.4	1359.1
30°	1407.3	1363.0	1309.4	1268.2	1241.9	1216.1	1211.4
32.5°	1287.8	1222.8	1163.0	1126.7	1086.4	1070.2	1052.3
35°	1081.6	1018.1	958.9	907.9	878.5	855.8	835.2
37.5°	896.1	823.0	775.3	733.9	712.7	699.6	703.0
40°	781.0	717.1	682.1	650.6	631.0	621.7	623.8
42.5°	687.8	640.0	611.1	589.6	575.7	570.6	569.4
45°	582.0	555.2	531.5	519.2	512.4	506.8	503.1
47.5°	509.9	488.0	474.6	467.3	461.4	455.7	455.6
50°	466.6	452.1	442.8	435.0	430.5	426.4	429.9
52.5°	433.5	420.3	411.1	404.1	402.4	398.7	398.6
55°	384.6	374.3	367.6	361.3	358.3	356.2	353.7
57.5°	340.0	330.2	324.1	320.1	314.3	312.1	311.3
60°	308.3	300.5	294.4	289.2	286.6	282.5	282.5
62.5°	279.0	271.2	265.5	261.6	257.3	255.7	256.1
65°	236.6	230.5	224.8	220.7	219.6	216.5	217.5
67.5°	197.6	193.5	187.5	185.3	183.3	181.7	180.5
70°	171.7	167.5	164.4	161.4	159.8	159.8	159.8
72.5°	149.8	144.8	143.0	139.1	140.0	138.4	136.7
75°	116.0	112.9	111.4	109.8	107.2	107.2	107.2
77.5°	85.3	84.4	82.6	80.9	80.3	79.8	80.0
80°	65.9	65.4	64.4	64.4	63.4	62.9	61.9
82.5°	50.7	49.4	48.8	48.4	48.2	48.1	47.9
85°	28.9	27.9	27.9	28.4	27.4	27.4	27.9
87.5°	18.2	18.7	18.5	18.5	18.9	18.5	18.5
90°	35.2	37.6	38.7	38.7	38.7	38.7	38.7
92.5°	87.8	77.9	70.6	69.7	65.9	66.9	65.0
95°	235.8	186.5	160.7	145.4	136.1	132.6	133.7
97.5°	586.8	459.9	375.2	319.1	290.2	273.1	263.3
100°	925.6	764.9	622.9	525.5	475.1	441.1	420.0
102.5°	1270.0	1152.5	1002.1	896.3	810.2	767.7	739.1
105°	1557.9	1573.2	1534.5	1461.7	1389.0	1338.6	1322.1
107.5°	1536.8	1658.8	1715.6	1724.7	1720.7	1710.6	1688.8
110°	1471.1	1621.2	1717.5	1767.9	1790.2	1800.8	1799.6



TEST NUMBER: P331368-840

CATALOG NUMBER: SA2XXDIP-C675D1080U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1393.2	1553.7	1664.0	1734.1	1771.4	1791.4	1797.7
115°	1287.0	1440.6	1561.5	1644.8	1698.7	1729.2	1739.8
117.5°	1200.6	1340.0	1453.3	1538.2	1595.2	1627.4	1636.3
120°	1155.5	1279.9	1386.6	1468.7	1523.9	1557.9	1569.6
122.5°	1118.0	1235.8	1332.2	1405.8	1460.1	1490.4	1500.2
125°	1068.7	1171.9	1259.9	1328.0	1372.6	1401.9	1411.3
127.5°	1020.9	1118.2	1199.4	1258.8	1300.5	1325.9	1333.4
130°	989.0	1081.7	1159.0	1216.6	1256.5	1279.9	1289.3
132.5°	959.0	1044.1	1116.8	1173.4	1213.3	1234.9	1243.2
135°	911.5	989.0	1054.6	1105.1	1143.8	1164.9	1169.6
137.5°	873.7	935.2	992.5	1038.4	1071.8	1090.4	1097.3
140°	849.4	903.3	954.9	992.5	1023.0	1040.6	1047.6
142.5°	827.8	874.2	917.4	953.0	980.8	996.4	997.8
145°	800.1	836.5	870.5	898.6	918.6	930.3	933.8
147.5°	777.6	806.0	830.8	854.0	870.0	878.0	880.1
150°	762.5	787.2	808.3	825.9	840.0	847.0	848.2
152.5°	750.3	771.2	789.5	803.3	815.6	820.7	820.9
155°	730.8	748.4	761.3	774.3	782.4	787.2	784.9
157.5°	711.1	725.9	736.0	745.2	751.9	754.1	754.1
160°	698.0	710.9	719.1	727.3	733.2	734.4	734.4
162.5°	685.8	696.8	703.2	711.3	715.4	716.5	715.6
165°	667.5	675.7	680.4	685.1	689.8	689.8	688.6
167.5°	650.9	656.5	660.8	662.8	665.4	665.2	663.8
170°	640.6	645.2	647.5	648.7	652.3	651.1	648.7
172.5°	631.2	634.9	636.3	637.5	639.1	637.9	636.5
175°	620.6	621.8	622.9	622.9	624.1	622.9	620.6
177.5°	612.9	613.8	613.8	613.8	613.8	612.9	611.0
180°	610.1	610.1	610.1	610.1	610.1	610.1	610.1

(END OF REPORT)