

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331330-840

Luminaire Tested: **SA2XXDIP-C675D330U840-4F0-1E-UDD-A**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331330-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C675D330U840-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 330 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4282.9 lumens
Efficiency: N/A
Efficacy: 122.4 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 35
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331330-840
CATALOG NUMBER: SA2XXDIP-C675D330U840-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331330-840

CATALOG NUMBER: SA2XXDIP-C675D330U840-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	112	112	112	112	106	106	106	106	94	94	94	83	83	83	74	74	74	69				
1	103	99	95	91	97	93	90	87	83	81	79	74	73	71	66	65	64	60				
2	94	87	81	76	89	82	77	73	74	70	66	66	63	60	59	57	55	51				
3	86	77	70	64	81	73	67	61	66	61	57	59	55	52	53	50	47	44				
4	79	69	61	55	75	65	58	53	59	53	49	53	49	45	48	44	41	38				
5	73	62	54	48	69	59	51	46	53	47	43	48	43	40	43	40	36	34				
6	68	56	48	42	64	53	46	40	48	42	38	44	39	35	40	36	32	30				
7	63	51	43	37	59	48	41	36	44	38	34	40	35	31	36	32	29	27				
8	59	46	39	33	55	44	37	32	41	35	30	37	32	28	34	29	26	24				
9	55	43	35	30	52	41	34	29	37	31	27	34	29	26	31	27	24	22				
10	51	39	32	27	49	38	31	26	35	29	25	32	27	23	29	25	22	20				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	21658	21658	21658	21658
5°	24280	21797	19316	21797
10°	27824	21620	16718	21620
15°	30780	21224	14770	21224
20°	30311	20797	13464	20797
25°	27332	20232	12636	20232
30°	22585	19328	12033	19328
35°	16462	18382	11606	18382
40°	13148	17266	11367	17266
45°	11488	15972	11040	15972
50°	10798	14722	10826	14722
55°	9956	13453	10536	13453
60°	9122	12103	10091	12103
65°	8309	10892	9650	10892
70°	7544	9711	9007	9711
75°	6687	8390	7973	8390
80°	5755	6946	6425	6946
85°	5169	5169	3816	5169



TEST NUMBER: P331330-840

CATALOG NUMBER: SA2XXDIP-C675D330U840-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	127.7	3.0
10°-20°	371.4	8.7
20°-30°	539.0	12.6
30°-40°	568.8	13.3
40°-50°	503.6	11.8
50°-60°	401.9	9.4
60°-70°	273.2	6.4
70°-80°	140.0	3.3
80°-90°	34.9	0.8
90°-100°	15.1	0.4
100°-110°	55.2	1.3
110°-120°	147.6	3.4
120°-130°	243.6	5.7
130°-140°	259.0	6.0
140°-150°	240.8	5.6
150°-160°	193.6	4.5
160°-170°	124.7	2.9
170°-180°	42.9	1.0
0°-30°	1038.1	24.2
0°-40°	1606.9	37.5
0°-60°	2512.4	58.7
0°-90°	2960.5	69.1
90°-120°	217.8	5.1
90°-150°	961.2	22.4
90°-180°	1322.0	30.9
0°-180°	4282.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1341	1341	1341	1341	1341	
5°	1498	1345	1192	1345	1498	150
15°	1841	1270	884	1270	1841	508
25°	1534	1136	709	1136	1534	693
35°	835	933	589	933	835	543
45°	503	700	484	700	503	396
55°	354	478	374	478	354	317
65°	218	285	253	285	218	216
75°	107	134	128	134	107	115
85°	28	28	21	28	28	31
90°	9	0	9	0	9	5
95°	14	21	14	21	14	13
105°	25	99	25	99	25	26
115°	27	188	27	188	27	67
125°	279	266	279	266	279	242
135°	339	328	339	328	339	261
145°	387	381	387	381	387	242
155°	420	420	420	420	420	194
165°	441	442	441	442	441	125
175°	450	452	450	452	450	43
180°	451	451	451	451	451	



TEST NUMBER: P331330-840

CATALOG NUMBER: SA2XXDIP-C675D330U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1403.2	1403.6	1404.5	1397.9	1397.0	1397.0	1391.3	1386.3	1380.6	1372.7	1373.5
5°	1498.1	1503.8	1505.8	1499.6	1490.4	1489.3	1480.6	1466.1	1452.7	1441.9	1434.2
7.5°	1611.3	1613.6	1608.5	1600.3	1593.5	1581.1	1564.8	1548.8	1526.4	1505.9	1490.7
10°	1697.1	1700.2	1691.4	1679.6	1669.8	1655.4	1631.6	1607.4	1578.0	1549.6	1526.9
12.5°	1762.2	1769.9	1758.7	1757.1	1740.3	1720.5	1692.2	1680.0	1638.6	1599.1	1574.8
15°	1841.4	1840.9	1842.0	1832.2	1819.8	1816.6	1786.8	1754.3	1696.1	1672.8	1632.6
17.5°	1818.6	1826.3	1830.0	1829.9	1829.6	1827.7	1818.1	1797.6	1768.4	1730.7	1684.3
20°	1764.1	1774.4	1775.9	1787.9	1794.5	1803.3	1806.9	1801.2	1783.2	1751.7	1711.5
22.5°	1680.0	1682.8	1687.7	1706.2	1720.7	1742.6	1754.1	1773.2	1766.3	1750.9	1717.3
25°	1534.2	1529.0	1547.1	1556.3	1589.8	1624.9	1650.2	1678.0	1702.7	1717.7	1707.9
27.5°	1359.1	1351.4	1378.4	1403.0	1430.3	1468.2	1507.6	1554.1	1592.8	1641.1	1657.7
30°	1211.4	1216.1	1241.9	1268.2	1309.4	1363.0	1407.3	1458.4	1513.6	1567.7	1605.3
32.5°	1052.3	1070.2	1086.4	1126.7	1163.0	1222.8	1287.8	1351.6	1420.4	1481.9	1540.1
35°	835.2	855.8	878.5	907.9	958.9	1018.1	1081.6	1167.6	1261.5	1345.5	1414.6
37.5°	703.0	699.6	712.7	733.9	775.3	823.0	896.1	981.2	1091.6	1190.3	1287.8
40°	623.8	621.7	631.0	650.6	682.1	717.1	781.0	855.8	958.4	1078.9	1195.0
42.5°	569.4	570.6	575.7	589.6	611.1	640.0	687.8	751.4	845.4	959.0	1083.6
45°	503.1	506.8	512.4	519.2	531.5	555.2	582.0	627.4	701.7	796.5	919.2
47.5°	455.6	455.7	461.4	467.3	474.6	488.0	509.9	538.3	590.7	667.9	773.4
50°	429.9	426.4	430.5	435.0	442.8	452.1	466.6	493.3	528.4	590.8	678.9
52.5°	398.6	398.7	402.4	404.1	411.1	420.3	433.5	452.1	483.8	532.6	605.1
55°	353.7	356.2	358.3	361.3	367.6	374.3	384.6	397.0	421.7	458.3	511.9
57.5°	311.3	312.1	314.3	320.1	324.1	330.2	340.0	351.2	367.4	394.5	434.7
60°	282.5	282.5	286.6	289.2	294.4	300.5	308.3	319.1	333.6	355.7	388.2
62.5°	256.1	255.7	257.3	261.6	265.5	271.2	279.0	288.2	301.7	321.4	348.2
65°	217.5	216.5	219.6	220.7	224.8	230.5	236.6	246.4	257.2	271.7	295.4
67.5°	180.5	181.7	183.3	185.3	187.5	193.5	197.6	204.6	213.7	225.7	241.8
70°	159.8	159.8	159.8	161.4	164.4	167.5	171.7	177.3	186.1	196.4	210.9
72.5°	136.7	138.4	140.0	139.1	143.0	144.8	149.8	153.0	161.4	167.9	180.8
75°	107.2	107.2	107.2	109.8	111.4	112.9	116.0	119.1	123.2	131.5	138.1
77.5°	80.0	79.8	80.3	80.9	82.6	84.4	85.3	88.2	92.0	95.7	101.5
80°	61.9	62.9	63.4	64.4	64.4	65.4	65.9	69.6	72.2	74.7	78.4
82.5°	47.9	48.1	48.2	48.4	48.8	49.4	50.7	51.9	52.8	54.9	57.8
85°	27.9	27.4	27.4	28.4	27.9	27.9	28.9	29.9	29.9	30.4	31.9
87.5°	12.5	12.4	12.8	12.4	12.3	12.7	12.6	12.2	12.5	12.8	13.1
90°	8.8	8.7	8.5	8.4	8.3	8.0	7.6	7.3	6.9	6.6	6.0
92.5°	8.8	8.7	8.7	8.6	8.5	8.3	8.2	8.0	7.8	7.6	7.3
95°	14.0	14.1	14.1	14.2	14.3	14.1	13.8	13.4	13.1	12.7	12.2
97.5°	18.8	18.7	18.6	18.5	18.4	18.2	17.9	17.7	17.4	17.1	15.9
100°	21.9	21.7	21.6	21.4	21.3	20.9	20.4	19.8	19.2	18.6	17.4
102.5°	23.4	23.2	23.0	22.8	22.6	22.1	21.4	20.6	19.9	19.1	29.5
105°	24.8	24.5	24.2	23.9	23.6	23.1	22.3	21.5	20.7	19.9	39.7
107.5°	25.5	25.2	24.9	24.6	24.3	24.6	25.4	26.3	27.1	27.9	51.6
110°	25.8	25.5	25.2	24.9	24.6	28.1	35.3	42.6	49.9	57.2	78.1



TEST NUMBER: P331330-840

CATALOG NUMBER: SA2XXDIP-C675D330U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	26.1	25.9	25.5	25.3	25.1	38.3	64.7	91.2	117.6	144.1	149.3
115°	26.8	32.0	37.3	42.4	47.7	67.1	100.7	134.3	167.8	201.5	199.7
117.5°	109.4	126.5	143.7	160.9	178.0	190.7	198.7	206.9	215.0	223.2	221.9
120°	199.1	208.9	218.7	228.5	238.3	242.8	242.0	241.1	240.2	239.3	238.0
122.5°	248.5	250.4	252.4	254.3	256.1	256.8	256.3	255.8	255.3	254.8	253.4
125°	279.1	278.9	278.7	278.5	278.3	277.9	277.4	276.9	276.4	275.9	274.5
127.5°	298.5	298.4	298.4	298.4	298.3	297.9	297.2	296.5	295.7	295.0	294.0
130°	310.5	310.6	310.6	310.7	310.8	310.4	309.6	308.8	308.0	307.3	306.5
132.5°	322.2	322.3	322.4	322.4	322.6	322.2	321.5	320.9	320.2	319.5	318.7
135°	339.2	339.4	339.5	339.7	339.8	339.5	338.8	338.1	337.4	336.7	336.0
137.5°	354.8	355.0	355.3	355.5	355.7	355.5	354.8	354.1	353.4	352.6	351.9
140°	364.4	364.8	365.2	365.5	365.9	365.7	365.1	364.4	363.8	363.0	362.3
142.5°	373.8	374.2	374.6	374.9	375.3	375.2	374.6	374.0	373.3	372.7	371.8
145°	386.9	387.3	387.7	388.0	388.4	388.3	387.8	387.3	386.8	386.3	385.1
147.5°	398.5	398.8	399.1	399.4	399.7	399.7	399.3	398.9	398.5	398.2	397.0
150°	405.6	405.9	406.3	406.7	407.0	407.0	406.5	406.1	405.7	405.3	404.0
152.5°	411.5	412.0	412.5	412.9	413.4	413.4	413.0	412.6	412.1	411.7	410.6
155°	419.9	420.5	421.1	421.6	422.2	422.3	421.8	421.4	421.0	420.5	419.7
157.5°	427.6	428.1	428.7	429.2	429.8	429.8	429.4	428.9	428.4	427.9	427.3
160°	432.0	432.5	433.0	433.5	434.0	434.0	433.6	433.2	432.7	432.3	431.9
162.5°	435.7	436.3	436.9	437.5	438.2	438.2	437.7	437.2	436.8	436.3	435.9
165°	441.1	441.6	442.1	442.6	443.1	443.1	442.6	442.1	441.6	441.1	440.9
167.5°	444.5	445.2	445.9	446.6	447.2	447.3	446.8	446.3	445.8	445.2	445.0
170°	446.7	447.4	448.0	448.7	449.3	449.4	448.9	448.4	447.9	447.4	447.2
172.5°	448.3	448.9	449.6	450.2	450.9	450.9	450.4	449.9	449.4	448.9	448.8
175°	449.6	450.3	451.1	451.8	452.5	452.6	452.1	451.6	451.1	450.6	450.5
177.5°	450.5	451.0	451.5	452.0	452.5	452.6	452.2	451.8	451.4	451.0	450.9
180°	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2



TEST NUMBER: P331330-840

CATALOG NUMBER: SA2XXDIP-C675D330U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1376.4	1373.1	1371.1	1363.6	1357.1	1350.5	1348.4	1349.2	1340.2	1331.5	1327.8
5°	1430.1	1419.8	1410.0	1396.0	1379.6	1361.5	1352.2	1344.9	1327.0	1307.4	1296.1
7.5°	1478.1	1463.4	1444.5	1418.3	1394.3	1365.9	1347.9	1331.9	1305.5	1277.9	1260.9
10°	1507.4	1487.2	1463.0	1431.1	1401.7	1367.2	1342.9	1318.7	1287.8	1254.8	1234.2
12.5°	1532.6	1505.4	1481.6	1440.6	1405.8	1362.6	1333.8	1299.7	1267.2	1228.0	1207.8
15°	1592.5	1542.5	1497.0	1450.7	1407.9	1347.6	1315.7	1269.7	1226.9	1178.5	1155.3
17.5°	1638.7	1582.6	1511.1	1452.1	1402.2	1335.4	1288.5	1233.6	1183.0	1127.5	1096.0
20°	1665.2	1600.6	1523.9	1453.8	1393.9	1317.7	1266.7	1210.4	1151.1	1088.7	1054.7
22.5°	1680.8	1613.1	1537.1	1447.5	1377.5	1303.2	1239.0	1177.4	1117.3	1050.1	1014.3
25°	1685.8	1623.9	1543.5	1442.4	1356.9	1272.8	1195.5	1135.7	1063.0	1000.1	948.1
27.5°	1661.2	1616.9	1539.5	1432.7	1333.0	1234.8	1148.6	1080.9	1004.1	935.8	883.5
30°	1631.1	1605.3	1530.0	1422.8	1314.0	1208.4	1113.5	1036.7	960.4	891.3	837.7
32.5°	1584.5	1578.9	1512.8	1408.8	1293.8	1175.0	1076.8	999.2	914.6	846.8	795.7
35°	1493.0	1517.7	1475.9	1377.5	1255.8	1127.4	1021.3	932.6	845.0	780.0	732.1
37.5°	1370.3	1431.7	1420.8	1331.6	1204.5	1075.7	958.5	865.8	782.2	716.7	669.6
40°	1285.7	1364.0	1375.4	1296.6	1168.2	1035.7	911.4	819.2	737.7	677.9	630.5
42.5°	1195.0	1286.6	1317.7	1254.5	1128.5	993.6	869.4	773.8	693.2	635.0	593.0
45°	1042.9	1164.1	1220.2	1184.2	1062.5	924.3	796.5	699.5	626.3	571.7	539.3
47.5°	900.7	1033.1	1108.6	1095.9	989.0	852.1	725.8	632.8	561.5	517.9	488.8
50°	800.1	936.1	1027.4	1031.6	936.1	800.6	673.8	586.1	520.7	480.0	456.3
52.5°	712.7	842.5	942.1	963.9	877.2	747.0	627.2	540.0	482.3	444.8	423.6
55°	598.5	708.3	818.6	858.9	789.2	665.5	554.7	477.9	423.7	398.0	379.4
57.5°	497.6	589.2	691.1	735.5	692.6	586.6	482.7	416.1	372.1	349.5	335.3
60°	444.3	516.5	607.2	660.4	623.3	529.0	438.2	374.8	338.7	318.6	305.2
62.5°	394.9	458.8	535.5	584.1	563.9	474.9	393.6	337.7	306.5	287.6	278.0
65°	325.8	376.4	435.7	480.5	467.1	399.5	333.1	285.1	260.3	245.4	237.6
67.5°	268.3	304.8	345.9	385.2	374.4	326.5	273.2	235.8	217.3	204.5	199.9
70°	232.0	259.8	296.4	327.9	319.1	279.9	237.6	205.7	189.8	178.8	174.2
72.5°	197.3	220.3	248.1	273.9	267.9	235.4	200.2	176.0	163.7	153.7	149.9
75°	149.0	166.5	183.5	200.6	198.9	173.7	153.1	134.5	124.7	117.0	115.4
77.5°	110.0	119.8	131.4	141.5	138.7	124.2	108.1	97.5	90.2	85.0	84.2
80°	84.0	89.7	98.0	105.1	101.6	95.3	82.5	74.7	69.6	64.4	62.4
82.5°	60.9	66.7	71.6	75.4	72.7	67.0	59.0	53.7	50.6	47.2	46.3
85°	31.9	35.0	37.2	38.2	37.2	33.5	29.9	27.9	25.2	23.7	23.2
87.5°	13.4	13.3	13.2	13.9	12.5	12.3	10.5	9.1	8.9	8.6	8.0
90°	5.4	4.7	4.2	3.5	2.7	1.9	1.1	0.3	1.1	1.9	2.7
92.5°	7.0	6.7	6.5	6.3	6.4	6.5	6.6	6.6	6.6	6.5	6.4
95°	11.7	11.2	10.7	11.6	14.0	16.5	18.8	21.2	18.8	16.5	14.0
97.5°	14.6	13.5	12.3	15.1	21.9	28.6	35.3	42.1	35.3	28.6	21.9
100°	16.2	14.9	13.6	18.1	28.0	37.9	47.9	57.8	47.9	37.9	28.0
102.5°	39.8	50.1	60.4	66.7	68.8	70.8	72.9	75.0	72.9	70.8	68.8
105°	59.6	79.4	99.2	108.0	105.8	103.6	101.4	99.3	101.4	103.6	105.8
107.5°	75.4	99.2	122.9	133.9	132.2	130.4	128.7	126.8	128.7	130.4	132.2
110°	99.1	120.1	141.0	150.8	149.3	147.7	146.1	144.6	146.1	147.7	149.3



TEST NUMBER: P331330-840

CATALOG NUMBER: SA2XXDIP-C675D330U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	154.5	159.7	164.8	166.7	165.4	164.1	162.7	161.4	162.7	164.1	165.4
115°	197.8	196.0	194.2	192.7	191.5	190.3	188.9	187.7	188.9	190.3	191.5
117.5°	220.7	219.4	218.1	216.8	215.5	214.1	212.7	211.4	212.7	214.1	215.5
120°	236.7	235.4	234.1	232.9	231.9	230.8	229.6	228.5	229.6	230.8	231.9
122.5°	251.9	250.4	249.0	247.8	246.6	245.5	244.4	243.2	244.4	245.5	246.6
125°	273.2	271.8	270.4	269.2	268.3	267.3	266.4	265.5	266.4	267.3	268.3
127.5°	293.0	291.9	290.8	289.8	288.8	287.7	286.7	285.6	286.7	287.7	288.8
130°	305.7	304.9	304.1	303.1	301.9	300.7	299.6	298.4	299.6	300.7	301.9
132.5°	317.9	317.1	316.3	315.5	314.5	313.5	312.5	311.5	312.5	313.5	314.5
135°	335.4	334.7	334.1	333.2	331.9	330.8	329.6	328.5	329.6	330.8	331.9
137.5°	351.1	350.4	349.7	348.9	348.1	347.3	346.5	345.7	346.5	347.3	348.1
140°	361.5	360.7	359.9	359.2	358.6	358.0	357.5	356.9	357.5	358.0	358.6
142.5°	370.9	370.0	369.1	368.4	367.9	367.3	366.8	366.3	366.8	367.3	367.9
145°	383.8	382.5	381.3	380.7	380.8	380.9	381.0	381.0	381.0	380.9	380.8
147.5°	395.8	394.5	393.2	392.8	393.0	393.3	393.6	393.9	393.6	393.3	393.0
150°	402.9	401.7	400.6	400.2	400.7	401.2	401.7	402.2	401.7	401.2	400.7
152.5°	409.5	408.4	407.3	407.1	407.6	408.2	408.8	409.3	408.8	408.2	407.6
155°	418.8	418.0	417.1	417.0	417.6	418.3	418.9	419.6	418.9	418.3	417.6
157.5°	426.7	426.1	425.5	425.4	426.0	426.5	427.1	427.6	427.1	426.5	426.0
160°	431.4	431.0	430.6	430.6	431.0	431.4	431.9	432.3	431.9	431.4	431.0
162.5°	435.5	435.0	434.7	434.7	435.2	435.7	436.1	436.5	436.1	435.7	435.2
165°	440.7	440.5	440.3	440.4	440.8	441.2	441.7	442.1	441.7	441.2	440.8
167.5°	444.8	444.6	444.4	444.5	444.9	445.5	445.9	446.3	445.9	445.5	444.9
170°	447.1	446.9	446.8	446.9	447.4	447.8	448.2	448.7	448.2	447.8	447.4
172.5°	448.6	448.5	448.3	448.5	448.9	449.3	449.8	450.2	449.8	449.3	448.9
175°	450.3	450.2	450.0	450.2	450.7	451.2	451.7	452.2	451.7	451.2	450.7
177.5°	450.9	450.8	450.8	450.9	451.3	451.7	452.1	452.5	452.1	451.7	451.3
180°	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2



TEST NUMBER: P331330-840

CATALOG NUMBER: SA2XXDIP-C675D330U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1323.6	1321.2	1312.5	1308.0	1300.5	1293.5	1289.0	1291.1	1292.7	1291.9	1290.6
5°	1285.7	1275.9	1260.9	1248.1	1238.8	1221.7	1214.6	1210.9	1207.9	1204.3	1200.6
7.5°	1240.5	1225.1	1203.7	1185.3	1167.9	1146.8	1134.8	1127.5	1120.1	1112.0	1104.8
10°	1208.4	1186.7	1164.1	1138.2	1117.6	1098.5	1081.6	1070.3	1060.0	1050.2	1042.9
12.5°	1174.6	1149.6	1121.6	1086.3	1063.6	1036.3	1033.7	1013.7	997.6	991.6	983.1
15°	1120.7	1085.7	1050.2	1008.4	990.3	965.5	950.1	934.6	920.7	910.9	908.4
17.5°	1059.6	1014.2	978.9	948.9	919.3	893.9	879.7	867.3	855.9	842.7	841.0
20°	1013.0	973.8	935.1	908.9	878.5	852.6	835.2	822.7	812.9	805.3	798.5
22.5°	968.9	925.9	890.6	861.8	831.8	811.0	797.2	785.3	777.1	768.5	762.2
25°	898.1	864.5	825.9	793.3	768.6	755.3	743.9	733.6	728.4	722.8	715.6
27.5°	836.1	798.8	762.7	737.5	715.8	703.9	695.8	688.8	684.0	680.6	676.6
30°	792.3	754.7	726.4	701.7	683.6	671.8	666.6	662.5	656.8	654.7	652.7
32.5°	750.3	716.4	692.2	670.7	653.5	645.7	641.0	637.3	632.9	630.8	626.6
35°	690.7	662.5	638.7	626.8	613.0	606.2	602.7	597.4	593.4	591.3	590.8
37.5°	634.8	610.2	594.6	579.4	573.5	569.4	564.4	560.9	559.7	559.4	558.9
40°	598.5	578.5	564.5	552.1	549.6	543.3	539.3	536.1	536.1	536.6	536.1
42.5°	565.5	547.4	535.2	524.5	521.5	517.8	513.6	513.4	514.3	516.0	514.3
45°	515.5	502.6	493.8	488.7	483.0	479.4	478.9	480.5	481.0	481.5	483.0
47.5°	469.5	461.0	453.0	447.4	444.8	444.2	443.6	446.4	448.8	449.7	452.1
50°	442.3	432.5	425.9	422.2	420.1	419.1	420.1	423.2	425.3	427.9	429.4
52.5°	411.8	404.9	400.2	397.5	396.7	397.3	397.5	401.0	404.2	405.2	406.0
55°	369.6	364.5	363.5	358.8	360.8	360.3	362.9	365.0	368.1	371.1	371.7
57.5°	327.6	323.5	320.6	321.0	321.6	324.0	326.1	329.7	333.1	336.3	336.6
60°	299.5	297.4	295.9	295.9	296.9	300.0	302.7	306.2	308.3	310.3	311.8
62.5°	274.0	271.9	270.3	271.1	273.9	275.7	278.7	280.6	282.7	284.8	285.5
65°	233.5	232.5	234.1	235.1	235.6	238.1	241.8	243.3	245.4	246.4	250.0
67.5°	196.3	196.5	196.3	197.7	200.8	201.4	204.8	208.3	208.7	210.8	213.1
70°	171.2	172.2	173.2	174.2	176.8	177.8	180.5	182.0	184.0	185.6	187.1
72.5°	148.0	148.2	149.3	149.1	151.3	153.5	155.7	157.2	159.3	161.3	162.8
75°	113.9	113.9	114.9	115.4	118.1	120.7	120.1	121.2	123.2	125.2	126.3
77.5°	83.2	82.1	83.2	83.7	84.5	86.7	87.2	88.6	90.9	90.2	91.4
80°	63.4	61.9	63.4	63.9	63.9	66.6	66.6	67.6	69.1	67.6	69.1
82.5°	45.2	44.5	45.6	45.7	46.6	46.7	47.6	47.8	49.3	48.6	49.3
85°	22.7	22.2	22.7	22.2	22.7	23.2	23.2	22.7	22.7	23.7	22.2
87.5°	7.7	7.5	7.2	7.3	7.0	6.7	6.4	6.4	6.5	5.8	5.8
90°	3.5	4.2	4.7	5.4	6.0	6.6	6.9	7.3	7.6	8.0	8.3
92.5°	6.3	6.5	6.7	7.0	7.3	7.6	7.8	8.0	8.2	8.3	8.5
95°	11.6	10.7	11.2	11.7	12.2	12.7	13.1	13.4	13.8	14.1	14.3
97.5°	15.1	12.3	13.5	14.6	15.9	17.1	17.4	17.7	17.9	18.2	18.4
100°	18.1	13.6	14.9	16.2	17.4	18.6	19.2	19.8	20.4	20.9	21.3
102.5°	66.7	60.4	50.1	39.8	29.5	19.1	19.9	20.6	21.4	22.1	22.6
105°	108.0	99.2	79.4	59.6	39.7	19.9	20.7	21.5	22.3	23.1	23.6
107.5°	133.9	122.9	99.2	75.4	51.6	27.9	27.1	26.3	25.4	24.6	24.3
110°	150.8	141.0	120.1	99.1	78.1	57.2	49.9	42.6	35.3	28.1	24.6



TEST NUMBER: P331330-840

CATALOG NUMBER: SA2XXDIP-C675D330U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	166.7	164.8	159.7	154.5	149.3	144.1	117.6	91.2	64.7	38.3	25.1
115°	192.7	194.2	196.0	197.8	199.7	201.5	167.8	134.3	100.7	67.1	47.7
117.5°	216.8	218.1	219.4	220.7	221.9	223.2	215.0	206.9	198.7	190.7	178.0
120°	232.9	234.1	235.4	236.7	238.0	239.3	240.2	241.1	242.0	242.8	238.3
122.5°	247.8	249.0	250.4	251.9	253.4	254.8	255.3	255.8	256.3	256.8	256.1
125°	269.2	270.4	271.8	273.2	274.5	275.9	276.4	276.9	277.4	277.9	278.3
127.5°	289.8	290.8	291.9	293.0	294.0	295.0	295.7	296.5	297.2	297.9	298.3
130°	303.1	304.1	304.9	305.7	306.5	307.3	308.0	308.8	309.6	310.4	310.8
132.5°	315.5	316.3	317.1	317.9	318.7	319.5	320.2	320.9	321.5	322.2	322.6
135°	333.2	334.1	334.7	335.4	336.0	336.7	337.4	338.1	338.8	339.5	339.8
137.5°	348.9	349.7	350.4	351.1	351.9	352.6	353.4	354.1	354.8	355.5	355.7
140°	359.2	359.9	360.7	361.5	362.3	363.0	363.8	364.4	365.1	365.7	365.9
142.5°	368.4	369.1	370.0	370.9	371.8	372.7	373.3	374.0	374.6	375.2	375.3
145°	380.7	381.3	382.5	383.8	385.1	386.3	386.8	387.3	387.8	388.3	388.4
147.5°	392.8	393.2	394.5	395.8	397.0	398.2	398.5	398.9	399.3	399.7	399.7
150°	400.2	400.6	401.7	402.9	404.0	405.3	405.7	406.1	406.5	407.0	407.0
152.5°	407.1	407.3	408.4	409.5	410.6	411.7	412.1	412.6	413.0	413.4	413.4
155°	417.0	417.1	418.0	418.8	419.7	420.5	421.0	421.4	421.8	422.3	422.2
157.5°	425.4	425.5	426.1	426.7	427.3	427.9	428.4	428.9	429.4	429.8	429.8
160°	430.6	430.6	431.0	431.4	431.9	432.3	432.7	433.2	433.6	434.0	434.0
162.5°	434.7	434.7	435.0	435.5	435.9	436.3	436.8	437.2	437.7	438.2	438.2
165°	440.4	440.3	440.5	440.7	440.9	441.1	441.6	442.1	442.6	443.1	443.1
167.5°	444.5	444.4	444.6	444.8	445.0	445.2	445.8	446.3	446.8	447.3	447.2
170°	446.9	446.8	446.9	447.1	447.2	447.4	447.9	448.4	448.9	449.4	449.3
172.5°	448.5	448.3	448.5	448.6	448.8	448.9	449.4	449.9	450.4	450.9	450.9
175°	450.2	450.0	450.2	450.3	450.5	450.6	451.1	451.6	452.1	452.6	452.5
177.5°	450.9	450.8	450.8	450.9	450.9	451.0	451.4	451.8	452.2	452.6	452.5
180°	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2



TEST NUMBER: P331330-840

CATALOG NUMBER: SA2XXDIP-C675D330U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1286.6	1285.7	1285.7	1282.0	1285.7	1285.7	1286.6	1290.6	1291.9	1292.7	1291.1
5°	1193.5	1191.8	1189.3	1191.8	1189.3	1191.8	1193.5	1200.6	1204.3	1207.9	1210.9
7.5°	1101.4	1095.2	1094.3	1088.1	1094.3	1095.2	1101.4	1104.8	1112.0	1120.1	1127.5
10°	1034.1	1030.0	1029.5	1019.7	1029.5	1030.0	1034.1	1042.9	1050.2	1060.0	1070.3
12.5°	983.0	973.1	975.0	969.4	975.0	973.1	983.0	983.1	991.6	997.6	1013.7
15°	894.4	894.4	892.3	883.6	892.3	894.4	894.4	908.4	910.9	920.7	934.6
17.5°	830.8	829.8	824.9	827.3	824.9	829.8	830.8	841.0	842.7	855.9	867.3
20°	792.8	789.8	783.6	783.6	783.6	789.8	792.8	798.5	805.3	812.9	822.7
22.5°	757.0	756.8	750.2	752.2	750.2	756.8	757.0	762.2	768.5	777.1	785.3
25°	715.0	710.9	707.8	709.3	707.8	710.9	715.0	715.6	722.8	728.4	733.6
27.5°	675.2	673.0	672.8	668.5	672.8	673.0	675.2	676.6	680.6	684.0	688.8
30°	652.2	647.0	648.0	645.4	648.0	647.0	652.2	652.7	654.7	656.8	662.5
32.5°	625.7	623.9	622.9	620.7	622.9	623.9	625.7	626.6	630.8	632.9	637.3
35°	589.8	590.3	587.7	588.8	587.7	590.3	589.8	590.8	591.3	593.4	597.4
37.5°	558.4	560.0	558.8	559.1	558.8	560.0	558.4	558.9	559.4	559.7	560.9
40°	537.7	537.7	537.7	539.3	537.7	537.7	537.7	536.1	536.6	536.1	536.1
42.5°	517.9	517.1	516.2	516.1	516.2	517.1	517.9	514.3	516.0	514.3	513.4
45°	484.0	485.6	486.1	483.5	486.1	485.6	484.0	483.0	481.5	481.0	480.5
47.5°	453.4	453.6	453.4	455.8	453.4	453.6	453.4	452.1	449.7	448.8	446.4
50°	432.0	431.0	432.0	431.0	432.0	431.0	432.0	429.4	427.9	425.3	423.2
52.5°	409.3	409.5	408.9	408.7	408.9	409.5	409.3	406.0	405.2	404.2	401.0
55°	373.8	374.8	374.3	374.3	374.3	374.8	373.8	371.7	371.1	368.1	365.0
57.5°	337.0	337.9	338.6	336.3	338.6	337.9	337.0	336.6	336.3	333.1	329.7
60°	311.3	314.0	313.5	312.5	313.5	314.0	311.3	311.8	310.3	308.3	306.2
62.5°	287.9	288.8	288.7	288.5	288.7	288.8	287.9	285.5	284.8	282.7	280.6
65°	251.6	252.6	251.1	252.6	251.1	252.6	251.6	250.0	246.4	245.4	243.3
67.5°	212.5	212.8	214.0	214.7	214.0	212.8	212.5	213.1	210.8	208.7	208.3
70°	188.1	187.6	189.1	190.8	189.1	187.6	188.1	187.1	185.6	184.0	182.0
72.5°	162.6	163.7	163.2	164.3	163.2	163.7	162.6	162.8	161.3	159.3	157.2
75°	125.2	126.8	126.3	127.8	126.3	126.8	125.2	126.3	125.2	123.2	121.2
77.5°	90.5	90.7	90.5	91.4	90.5	90.7	90.5	91.4	90.2	90.9	88.6
80°	69.1	68.1	67.1	69.1	67.1	68.1	69.1	69.1	67.6	69.1	67.6
82.5°	48.1	48.7	47.7	47.7	47.7	48.7	48.1	49.3	48.6	49.3	47.8
85°	22.2	21.6	20.6	20.6	20.6	21.6	22.2	22.2	23.7	22.7	22.7
87.5°	5.8	5.5	5.5	5.0	5.5	5.5	5.8	5.8	5.8	6.5	6.4
90°	8.4	8.5	8.7	8.8	8.7	8.5	8.4	8.3	8.0	7.6	7.3
92.5°	8.6	8.7	8.7	8.8	8.7	8.7	8.6	8.5	8.3	8.2	8.0
95°	14.2	14.1	14.1	14.0	14.1	14.1	14.2	14.3	14.1	13.8	13.4
97.5°	18.5	18.6	18.7	18.8	18.7	18.6	18.5	18.4	18.2	17.9	17.7
100°	21.4	21.6	21.7	21.9	21.7	21.6	21.4	21.3	20.9	20.4	19.8
102.5°	22.8	23.0	23.2	23.4	23.2	23.0	22.8	22.6	22.1	21.4	20.6
105°	23.9	24.2	24.5	24.8	24.5	24.2	23.9	23.6	23.1	22.3	21.5
107.5°	24.6	24.9	25.2	25.5	25.2	24.9	24.6	24.3	24.6	25.4	26.3
110°	24.9	25.2	25.5	25.8	25.5	25.2	24.9	24.6	28.1	35.3	42.6



TEST NUMBER: P331330-840

CATALOG NUMBER: SA2XXDIP-C675D330U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	25.3	25.5	25.9	26.1	25.9	25.5	25.3	25.1	38.3	64.7	91.2
115°	42.4	37.3	32.0	26.8	32.0	37.3	42.4	47.7	67.1	100.7	134.3
117.5°	160.9	143.7	126.5	109.4	126.5	143.7	160.9	178.0	190.7	198.7	206.9
120°	228.5	218.7	208.9	199.1	208.9	218.7	228.5	238.3	242.8	242.0	241.1
122.5°	254.3	252.4	250.4	248.5	250.4	252.4	254.3	256.1	256.8	256.3	255.8
125°	278.5	278.7	278.9	279.1	278.9	278.7	278.5	278.3	277.9	277.4	276.9
127.5°	298.4	298.4	298.4	298.5	298.4	298.4	298.4	298.3	297.9	297.2	296.5
130°	310.7	310.6	310.6	310.5	310.6	310.6	310.7	310.8	310.4	309.6	308.8
132.5°	322.4	322.4	322.3	322.2	322.3	322.4	322.4	322.6	322.2	321.5	320.9
135°	339.7	339.5	339.4	339.2	339.4	339.5	339.7	339.8	339.5	338.8	338.1
137.5°	355.5	355.3	355.0	354.8	355.0	355.3	355.5	355.7	355.5	354.8	354.1
140°	365.5	365.2	364.8	364.4	364.8	365.2	365.5	365.9	365.7	365.1	364.4
142.5°	374.9	374.6	374.2	373.8	374.2	374.6	374.9	375.3	375.2	374.6	374.0
145°	388.0	387.7	387.3	386.9	387.3	387.7	388.0	388.4	388.3	387.8	387.3
147.5°	399.4	399.1	398.8	398.5	398.8	399.1	399.4	399.7	399.7	399.3	398.9
150°	406.7	406.3	405.9	405.6	405.9	406.3	406.7	407.0	407.0	406.5	406.1
152.5°	412.9	412.5	412.0	411.5	412.0	412.5	412.9	413.4	413.4	413.0	412.6
155°	421.6	421.1	420.5	419.9	420.5	421.1	421.6	422.2	422.3	421.8	421.4
157.5°	429.2	428.7	428.1	427.6	428.1	428.7	429.2	429.8	429.8	429.4	428.9
160°	433.5	433.0	432.5	432.0	432.5	433.0	433.5	434.0	434.0	433.6	433.2
162.5°	437.5	436.9	436.3	435.7	436.3	436.9	437.5	438.2	438.2	437.7	437.2
165°	442.6	442.1	441.6	441.1	441.6	442.1	442.6	443.1	443.1	442.6	442.1
167.5°	446.6	445.9	445.2	444.5	445.2	445.9	446.6	447.2	447.3	446.8	446.3
170°	448.7	448.0	447.4	446.7	447.4	448.0	448.7	449.3	449.4	448.9	448.4
172.5°	450.2	449.6	448.9	448.3	448.9	449.6	450.2	450.9	450.9	450.4	449.9
175°	451.8	451.1	450.3	449.6	450.3	451.1	451.8	452.5	452.6	452.1	451.6
177.5°	452.0	451.5	451.0	450.5	451.0	451.5	452.0	452.5	452.6	452.2	451.8
180°	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2



TEST NUMBER: P331330-840

CATALOG NUMBER: SA2XXDIP-C675D330U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1289.0	1293.5	1300.5	1308.0	1312.5	1321.2	1323.6	1327.8	1331.5	1340.2	1349.2
5°	1214.6	1221.7	1238.8	1248.1	1260.9	1275.9	1285.7	1296.1	1307.4	1327.0	1344.9
7.5°	1134.8	1146.8	1167.9	1185.3	1203.7	1225.1	1240.5	1260.9	1277.9	1305.5	1331.9
10°	1081.6	1098.5	1117.6	1138.2	1164.1	1186.7	1208.4	1234.2	1254.8	1287.8	1318.7
12.5°	1033.7	1036.3	1063.6	1086.3	1121.6	1149.6	1174.6	1207.8	1228.0	1267.2	1299.7
15°	950.1	965.5	990.3	1008.4	1050.2	1085.7	1120.7	1155.3	1178.5	1226.9	1269.7
17.5°	879.7	893.9	919.3	948.9	978.9	1014.2	1059.6	1096.0	1127.5	1183.0	1233.6
20°	835.2	852.6	878.5	908.9	935.1	973.8	1013.0	1054.7	1088.7	1151.1	1210.4
22.5°	797.2	811.0	831.8	861.8	890.6	925.9	968.9	1014.3	1050.1	1117.3	1177.4
25°	743.9	755.3	768.6	793.3	825.9	864.5	898.1	948.1	1000.1	1063.0	1135.7
27.5°	695.8	703.9	715.8	737.5	762.7	798.8	836.1	883.5	935.8	1004.1	1080.9
30°	666.6	671.8	683.6	701.7	726.4	754.7	792.3	837.7	891.3	960.4	1036.7
32.5°	641.0	645.7	653.5	670.7	692.2	716.4	750.3	795.7	846.8	914.6	999.2
35°	602.7	606.2	613.0	626.8	638.7	662.5	690.7	732.1	780.0	845.0	932.6
37.5°	564.4	569.4	573.5	579.4	594.6	610.2	634.8	669.6	716.7	782.2	865.8
40°	539.3	543.3	549.6	552.1	564.5	578.5	598.5	630.5	677.9	737.7	819.2
42.5°	513.6	517.8	521.5	524.5	535.2	547.4	565.5	593.0	635.0	693.2	773.8
45°	478.9	479.4	483.0	488.7	493.8	502.6	515.5	539.3	571.7	626.3	699.5
47.5°	443.6	444.2	444.8	447.4	453.0	461.0	469.5	488.8	517.9	561.5	632.8
50°	420.1	419.1	420.1	422.2	425.9	432.5	442.3	456.3	480.0	520.7	586.1
52.5°	397.5	397.3	396.7	397.5	400.2	404.9	411.8	423.6	444.8	482.3	540.0
55°	362.9	360.3	360.8	358.8	363.5	364.5	369.6	379.4	398.0	423.7	477.9
57.5°	326.1	324.0	321.6	321.0	320.6	323.5	327.6	335.3	349.5	372.1	416.1
60°	302.7	300.0	296.9	295.9	295.9	297.4	299.5	305.2	318.6	338.7	374.8
62.5°	278.7	275.7	273.9	271.1	270.3	271.9	274.0	278.0	287.6	306.5	337.7
65°	241.8	238.1	235.6	235.1	234.1	232.5	233.5	237.6	245.4	260.3	285.1
67.5°	204.8	201.4	200.8	197.7	196.3	196.5	196.3	199.9	204.5	217.3	235.8
70°	180.5	177.8	176.8	174.2	173.2	172.2	171.2	174.2	178.8	189.8	205.7
72.5°	155.7	153.5	151.3	149.1	149.3	148.2	148.0	149.9	153.7	163.7	176.0
75°	120.1	120.7	118.1	115.4	114.9	113.9	113.9	115.4	117.0	124.7	134.5
77.5°	87.2	86.7	84.5	83.7	83.2	82.1	83.2	84.2	85.0	90.2	97.5
80°	66.6	66.6	63.9	63.9	63.4	61.9	63.4	62.4	64.4	69.6	74.7
82.5°	47.6	46.7	46.6	45.7	45.6	44.5	45.2	46.3	47.2	50.6	53.7
85°	23.2	23.2	22.7	22.2	22.7	22.2	22.7	23.2	23.7	25.2	27.9
87.5°	6.4	6.7	7.0	7.3	7.2	7.5	7.7	8.0	8.6	8.9	9.1
90°	6.9	6.6	6.0	5.4	4.7	4.2	3.5	2.7	1.9	1.1	0.3
92.5°	7.8	7.6	7.3	7.0	6.7	6.5	6.3	6.4	6.5	6.6	6.6
95°	13.1	12.7	12.2	11.7	11.2	10.7	11.6	14.0	16.5	18.8	21.2
97.5°	17.4	17.1	15.9	14.6	13.5	12.3	15.1	21.9	28.6	35.3	42.1
100°	19.2	18.6	17.4	16.2	14.9	13.6	18.1	28.0	37.9	47.9	57.8
102.5°	19.9	19.1	29.5	39.8	50.1	60.4	66.7	68.8	70.8	72.9	75.0
105°	20.7	19.9	39.7	59.6	79.4	99.2	108.0	105.8	103.6	101.4	99.3
107.5°	27.1	27.9	51.6	75.4	99.2	122.9	133.9	132.2	130.4	128.7	126.8
110°	49.9	57.2	78.1	99.1	120.1	141.0	150.8	149.3	147.7	146.1	144.6



TEST NUMBER: P331330-840

CATALOG NUMBER: SA2XXDIP-C675D330U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	117.6	144.1	149.3	154.5	159.7	164.8	166.7	165.4	164.1	162.7	161.4
115°	167.8	201.5	199.7	197.8	196.0	194.2	192.7	191.5	190.3	188.9	187.7
117.5°	215.0	223.2	221.9	220.7	219.4	218.1	216.8	215.5	214.1	212.7	211.4
120°	240.2	239.3	238.0	236.7	235.4	234.1	232.9	231.9	230.8	229.6	228.5
122.5°	255.3	254.8	253.4	251.9	250.4	249.0	247.8	246.6	245.5	244.4	243.2
125°	276.4	275.9	274.5	273.2	271.8	270.4	269.2	268.3	267.3	266.4	265.5
127.5°	295.7	295.0	294.0	293.0	291.9	290.8	289.8	288.8	287.7	286.7	285.6
130°	308.0	307.3	306.5	305.7	304.9	304.1	303.1	301.9	300.7	299.6	298.4
132.5°	320.2	319.5	318.7	317.9	317.1	316.3	315.5	314.5	313.5	312.5	311.5
135°	337.4	336.7	336.0	335.4	334.7	334.1	333.2	331.9	330.8	329.6	328.5
137.5°	353.4	352.6	351.9	351.1	350.4	349.7	348.9	348.1	347.3	346.5	345.7
140°	363.8	363.0	362.3	361.5	360.7	359.9	359.2	358.6	358.0	357.5	356.9
142.5°	373.3	372.7	371.8	370.9	370.0	369.1	368.4	367.9	367.3	366.8	366.3
145°	386.8	386.3	385.1	383.8	382.5	381.3	380.7	380.8	380.9	381.0	381.0
147.5°	398.5	398.2	397.0	395.8	394.5	393.2	392.8	393.0	393.3	393.6	393.9
150°	405.7	405.3	404.0	402.9	401.7	400.6	400.2	400.7	401.2	401.7	402.2
152.5°	412.1	411.7	410.6	409.5	408.4	407.3	407.1	407.6	408.2	408.8	409.3
155°	421.0	420.5	419.7	418.8	418.0	417.1	417.0	417.6	418.3	418.9	419.6
157.5°	428.4	427.9	427.3	426.7	426.1	425.5	425.4	426.0	426.5	427.1	427.6
160°	432.7	432.3	431.9	431.4	431.0	430.6	430.6	431.0	431.4	431.9	432.3
162.5°	436.8	436.3	435.9	435.5	435.0	434.7	434.7	435.2	435.7	436.1	436.5
165°	441.6	441.1	440.9	440.7	440.5	440.3	440.4	440.8	441.2	441.7	442.1
167.5°	445.8	445.2	445.0	444.8	444.6	444.4	444.5	444.9	445.5	445.9	446.3
170°	447.9	447.4	447.2	447.1	446.9	446.8	446.9	447.4	447.8	448.2	448.7
172.5°	449.4	448.9	448.8	448.6	448.5	448.3	448.5	448.9	449.3	449.8	450.2
175°	451.1	450.6	450.5	450.3	450.2	450.0	450.2	450.7	451.2	451.7	452.2
177.5°	451.4	451.0	450.9	450.9	450.8	450.8	450.9	451.3	451.7	452.1	452.5
180°	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2



TEST NUMBER: P331330-840

CATALOG NUMBER: SA2XXDIP-C675D330U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1348.4	1350.5	1357.1	1363.6	1371.1	1373.1	1376.4	1373.5	1372.7	1380.6	1386.3
5°	1352.2	1361.5	1379.6	1396.0	1410.0	1419.8	1430.1	1434.2	1441.9	1452.7	1466.1
7.5°	1347.9	1365.9	1394.3	1418.3	1444.5	1463.4	1478.1	1490.7	1505.9	1526.4	1548.8
10°	1342.9	1367.2	1401.7	1431.1	1463.0	1487.2	1507.4	1526.9	1549.6	1578.0	1607.4
12.5°	1333.8	1362.6	1405.8	1440.6	1481.6	1505.4	1532.6	1574.8	1599.1	1638.6	1680.0
15°	1315.7	1347.6	1407.9	1450.7	1497.0	1542.5	1592.5	1632.6	1672.8	1696.1	1754.3
17.5°	1288.5	1335.4	1402.2	1452.1	1511.1	1582.6	1638.7	1684.3	1730.7	1768.4	1797.6
20°	1266.7	1317.7	1393.9	1453.8	1523.9	1600.6	1665.2	1711.5	1751.7	1783.2	1801.2
22.5°	1239.0	1303.2	1377.5	1447.5	1537.1	1613.1	1680.8	1717.3	1750.9	1766.3	1773.2
25°	1195.5	1272.8	1356.9	1442.4	1543.5	1623.9	1685.8	1707.9	1717.7	1702.7	1678.0
27.5°	1148.6	1234.8	1333.0	1432.7	1539.5	1616.9	1661.2	1657.7	1641.1	1592.8	1554.1
30°	1113.5	1208.4	1314.0	1422.8	1530.0	1605.3	1631.1	1605.3	1567.7	1513.6	1458.4
32.5°	1076.8	1175.0	1293.8	1408.8	1512.8	1578.9	1584.5	1540.1	1481.9	1420.4	1351.6
35°	1021.3	1127.4	1255.8	1377.5	1475.9	1517.7	1493.0	1414.6	1345.5	1261.5	1167.6
37.5°	958.5	1075.7	1204.5	1331.6	1420.8	1431.7	1370.3	1287.8	1190.3	1091.6	981.2
40°	911.4	1035.7	1168.2	1296.6	1375.4	1364.0	1285.7	1195.0	1078.9	958.4	855.8
42.5°	869.4	993.6	1128.5	1254.5	1317.7	1286.6	1195.0	1083.6	959.0	845.4	751.4
45°	796.5	924.3	1062.5	1184.2	1220.2	1164.1	1042.9	919.2	796.5	701.7	627.4
47.5°	725.8	852.1	989.0	1095.9	1108.6	1033.1	900.7	773.4	667.9	590.7	538.3
50°	673.8	800.6	936.1	1031.6	1027.4	936.1	800.1	678.9	590.8	528.4	493.3
52.5°	627.2	747.0	877.2	963.9	942.1	842.5	712.7	605.1	532.6	483.8	452.1
55°	554.7	665.5	789.2	858.9	818.6	708.3	598.5	511.9	458.3	421.7	397.0
57.5°	482.7	586.6	692.6	735.5	691.1	589.2	497.6	434.7	394.5	367.4	351.2
60°	438.2	529.0	623.3	660.4	607.2	516.5	444.3	388.2	355.7	333.6	319.1
62.5°	393.6	474.9	563.9	584.1	535.5	458.8	394.9	348.2	321.4	301.7	288.2
65°	333.1	399.5	467.1	480.5	435.7	376.4	325.8	295.4	271.7	257.2	246.4
67.5°	273.2	326.5	374.4	385.2	345.9	304.8	268.3	241.8	225.7	213.7	204.6
70°	237.6	279.9	319.1	327.9	296.4	259.8	232.0	210.9	196.4	186.1	177.3
72.5°	200.2	235.4	267.9	273.9	248.1	220.3	197.3	180.8	167.9	161.4	153.0
75°	153.1	173.7	198.9	200.6	183.5	166.5	149.0	138.1	131.5	123.2	119.1
77.5°	108.1	124.2	138.7	141.5	131.4	119.8	110.0	101.5	95.7	92.0	88.2
80°	82.5	95.3	101.6	105.1	98.0	89.7	84.0	78.4	74.7	72.2	69.6
82.5°	59.0	67.0	72.7	75.4	71.6	66.7	60.9	57.8	54.9	52.8	51.9
85°	29.9	33.5	37.2	38.2	37.2	35.0	31.9	31.9	30.4	29.9	29.9
87.5°	10.5	12.3	12.5	13.9	13.2	13.3	13.4	13.1	12.8	12.5	12.2
90°	1.1	1.9	2.7	3.5	4.2	4.7	5.4	6.0	6.6	6.9	7.3
92.5°	6.6	6.5	6.4	6.3	6.5	6.7	7.0	7.3	7.6	7.8	8.0
95°	18.8	16.5	14.0	11.6	10.7	11.2	11.7	12.2	12.7	13.1	13.4
97.5°	35.3	28.6	21.9	15.1	12.3	13.5	14.6	15.9	17.1	17.4	17.7
100°	47.9	37.9	28.0	18.1	13.6	14.9	16.2	17.4	18.6	19.2	19.8
102.5°	72.9	70.8	68.8	66.7	60.4	50.1	39.8	29.5	19.1	19.9	20.6
105°	101.4	103.6	105.8	108.0	99.2	79.4	59.6	39.7	19.9	20.7	21.5
107.5°	128.7	130.4	132.2	133.9	122.9	99.2	75.4	51.6	27.9	27.1	26.3
110°	146.1	147.7	149.3	150.8	141.0	120.1	99.1	78.1	57.2	49.9	42.6



TEST NUMBER: P331330-840

CATALOG NUMBER: SA2XXDIP-C675D330U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	162.7	164.1	165.4	166.7	164.8	159.7	154.5	149.3	144.1	117.6	91.2
115°	188.9	190.3	191.5	192.7	194.2	196.0	197.8	199.7	201.5	167.8	134.3
117.5°	212.7	214.1	215.5	216.8	218.1	219.4	220.7	221.9	223.2	215.0	206.9
120°	229.6	230.8	231.9	232.9	234.1	235.4	236.7	238.0	239.3	240.2	241.1
122.5°	244.4	245.5	246.6	247.8	249.0	250.4	251.9	253.4	254.8	255.3	255.8
125°	266.4	267.3	268.3	269.2	270.4	271.8	273.2	274.5	275.9	276.4	276.9
127.5°	286.7	287.7	288.8	289.8	290.8	291.9	293.0	294.0	295.0	295.7	296.5
130°	299.6	300.7	301.9	303.1	304.1	304.9	305.7	306.5	307.3	308.0	308.8
132.5°	312.5	313.5	314.5	315.5	316.3	317.1	317.9	318.7	319.5	320.2	320.9
135°	329.6	330.8	331.9	333.2	334.1	334.7	335.4	336.0	336.7	337.4	338.1
137.5°	346.5	347.3	348.1	348.9	349.7	350.4	351.1	351.9	352.6	353.4	354.1
140°	357.5	358.0	358.6	359.2	359.9	360.7	361.5	362.3	363.0	363.8	364.4
142.5°	366.8	367.3	367.9	368.4	369.1	370.0	370.9	371.8	372.7	373.3	374.0
145°	381.0	380.9	380.8	380.7	381.3	382.5	383.8	385.1	386.3	386.8	387.3
147.5°	393.6	393.3	393.0	392.8	393.2	394.5	395.8	397.0	398.2	398.5	398.9
150°	401.7	401.2	400.7	400.2	400.6	401.7	402.9	404.0	405.3	405.7	406.1
152.5°	408.8	408.2	407.6	407.1	407.3	408.4	409.5	410.6	411.7	412.1	412.6
155°	418.9	418.3	417.6	417.0	417.1	418.0	418.8	419.7	420.5	421.0	421.4
157.5°	427.1	426.5	426.0	425.4	425.5	426.1	426.7	427.3	427.9	428.4	428.9
160°	431.9	431.4	431.0	430.6	430.6	431.0	431.4	431.9	432.3	432.7	433.2
162.5°	436.1	435.7	435.2	434.7	434.7	435.0	435.5	435.9	436.3	436.8	437.2
165°	441.7	441.2	440.8	440.4	440.3	440.5	440.7	440.9	441.1	441.6	442.1
167.5°	445.9	445.5	444.9	444.5	444.4	444.6	444.8	445.0	445.2	445.8	446.3
170°	448.2	447.8	447.4	446.9	446.8	446.9	447.1	447.2	447.4	447.9	448.4
172.5°	449.8	449.3	448.9	448.5	448.3	448.5	448.6	448.8	448.9	449.4	449.9
175°	451.7	451.2	450.7	450.2	450.0	450.2	450.3	450.5	450.6	451.1	451.6
177.5°	452.1	451.7	451.3	450.9	450.8	450.8	450.9	450.9	451.0	451.4	451.8
180°	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2



TEST NUMBER: P331330-840
 CATALOG NUMBER: SA2XXDIP-C675D330U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1391.3	1397.0	1397.0	1397.9	1404.5	1403.6	1403.2
5°	1480.6	1489.3	1490.4	1499.6	1505.8	1503.8	1498.1
7.5°	1564.8	1581.1	1593.5	1600.3	1608.5	1613.6	1611.3
10°	1631.6	1655.4	1669.8	1679.6	1691.4	1700.2	1697.1
12.5°	1692.2	1720.5	1740.3	1757.1	1758.7	1769.9	1762.2
15°	1786.8	1816.6	1819.8	1832.2	1842.0	1840.9	1841.4
17.5°	1818.1	1827.7	1829.6	1829.9	1830.0	1826.3	1818.6
20°	1806.9	1803.3	1794.5	1787.9	1775.9	1774.4	1764.1
22.5°	1754.1	1742.6	1720.7	1706.2	1687.7	1682.8	1680.0
25°	1650.2	1624.9	1589.8	1556.3	1547.1	1529.0	1534.2
27.5°	1507.6	1468.2	1430.3	1403.0	1378.4	1351.4	1359.1
30°	1407.3	1363.0	1309.4	1268.2	1241.9	1216.1	1211.4
32.5°	1287.8	1222.8	1163.0	1126.7	1086.4	1070.2	1052.3
35°	1081.6	1018.1	958.9	907.9	878.5	855.8	835.2
37.5°	896.1	823.0	775.3	733.9	712.7	699.6	703.0
40°	781.0	717.1	682.1	650.6	631.0	621.7	623.8
42.5°	687.8	640.0	611.1	589.6	575.7	570.6	569.4
45°	582.0	555.2	531.5	519.2	512.4	506.8	503.1
47.5°	509.9	488.0	474.6	467.3	461.4	455.7	455.6
50°	466.6	452.1	442.8	435.0	430.5	426.4	429.9
52.5°	433.5	420.3	411.1	404.1	402.4	398.7	398.6
55°	384.6	374.3	367.6	361.3	358.3	356.2	353.7
57.5°	340.0	330.2	324.1	320.1	314.3	312.1	311.3
60°	308.3	300.5	294.4	289.2	286.6	282.5	282.5
62.5°	279.0	271.2	265.5	261.6	257.3	255.7	256.1
65°	236.6	230.5	224.8	220.7	219.6	216.5	217.5
67.5°	197.6	193.5	187.5	185.3	183.3	181.7	180.5
70°	171.7	167.5	164.4	161.4	159.8	159.8	159.8
72.5°	149.8	144.8	143.0	139.1	140.0	138.4	136.7
75°	116.0	112.9	111.4	109.8	107.2	107.2	107.2
77.5°	85.3	84.4	82.6	80.9	80.3	79.8	80.0
80°	65.9	65.4	64.4	64.4	63.4	62.9	61.9
82.5°	50.7	49.4	48.8	48.4	48.2	48.1	47.9
85°	28.9	27.9	27.9	28.4	27.4	27.4	27.9
87.5°	12.6	12.7	12.3	12.4	12.8	12.4	12.5
90°	7.6	8.0	8.3	8.4	8.5	8.7	8.8
92.5°	8.2	8.3	8.5	8.6	8.7	8.7	8.8
95°	13.8	14.1	14.3	14.2	14.1	14.1	14.0
97.5°	17.9	18.2	18.4	18.5	18.6	18.7	18.8
100°	20.4	20.9	21.3	21.4	21.6	21.7	21.9
102.5°	21.4	22.1	22.6	22.8	23.0	23.2	23.4
105°	22.3	23.1	23.6	23.9	24.2	24.5	24.8
107.5°	25.4	24.6	24.3	24.6	24.9	25.2	25.5
110°	35.3	28.1	24.6	24.9	25.2	25.5	25.8



TEST NUMBER: P331330-840

CATALOG NUMBER: SA2XXDIP-C675D330U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	64.7	38.3	25.1	25.3	25.5	25.9	26.1
115°	100.7	67.1	47.7	42.4	37.3	32.0	26.8
117.5°	198.7	190.7	178.0	160.9	143.7	126.5	109.4
120°	242.0	242.8	238.3	228.5	218.7	208.9	199.1
122.5°	256.3	256.8	256.1	254.3	252.4	250.4	248.5
125°	277.4	277.9	278.3	278.5	278.7	278.9	279.1
127.5°	297.2	297.9	298.3	298.4	298.4	298.4	298.5
130°	309.6	310.4	310.8	310.7	310.6	310.6	310.5
132.5°	321.5	322.2	322.6	322.4	322.4	322.3	322.2
135°	338.8	339.5	339.8	339.7	339.5	339.4	339.2
137.5°	354.8	355.5	355.7	355.5	355.3	355.0	354.8
140°	365.1	365.7	365.9	365.5	365.2	364.8	364.4
142.5°	374.6	375.2	375.3	374.9	374.6	374.2	373.8
145°	387.8	388.3	388.4	388.0	387.7	387.3	386.9
147.5°	399.3	399.7	399.7	399.4	399.1	398.8	398.5
150°	406.5	407.0	407.0	406.7	406.3	405.9	405.6
152.5°	413.0	413.4	413.4	412.9	412.5	412.0	411.5
155°	421.8	422.3	422.2	421.6	421.1	420.5	419.9
157.5°	429.4	429.8	429.8	429.2	428.7	428.1	427.6
160°	433.6	434.0	434.0	433.5	433.0	432.5	432.0
162.5°	437.7	438.2	438.2	437.5	436.9	436.3	435.7
165°	442.6	443.1	443.1	442.6	442.1	441.6	441.1
167.5°	446.8	447.3	447.2	446.6	445.9	445.2	444.5
170°	448.9	449.4	449.3	448.7	448.0	447.4	446.7
172.5°	450.4	450.9	450.9	450.2	449.6	448.9	448.3
175°	452.1	452.6	452.5	451.8	451.1	450.3	449.6
177.5°	452.2	452.6	452.5	452.0	451.5	451.0	450.5
180°	451.2	451.2	451.2	451.2	451.2	451.2	451.2

(END OF REPORT)