

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331698-930

Luminaire Tested: **SA2XXRDIP-C675D925U930-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331698-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C675D925U930-4F0-1E-UDD-F4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 925 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4839.7 lumens
Efficiency: N/A
Efficacy: 93.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 52
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331698-930
CATALOG NUMBER: SA2XXRDIP-C675D925U930-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331698-930

CATALOG NUMBER: SA2XXRDIP-C675D925U930-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46	39				
1	96	92	88	85	87	83	80	78	68	66	64	54	53	51	41	40	40	34				
2	87	80	75	70	79	73	68	64	60	57	54	48	46	44	37	35	34	29				
3	80	71	64	58	73	65	59	54	53	49	45	43	40	37	33	31	29	25				
4	73	63	55	50	66	58	51	46	48	43	39	38	35	32	30	27	26	22				
5	67	56	48	43	61	52	45	40	43	38	34	35	31	28	27	24	23	19				
6	62	51	43	37	56	46	40	35	39	33	30	31	28	25	25	22	20	17				
7	57	46	38	33	52	42	35	30	35	30	26	29	25	22	22	20	18	15				
8	53	41	34	29	49	38	32	27	32	27	23	26	22	20	21	18	16	14				
9	50	38	31	26	45	35	29	24	29	24	21	24	20	18	19	17	15	12				
10	46	35	28	23	42	32	26	22	27	22	19	22	19	16	18	15	13	11				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14849	14849	14849
5°	14906	14663	14744
10°	14791	14423	14300
15°	14621	13996	13593
20°	14387	13385	12713
25°	14145	12691	11863
30°	13811	11979	10769
35°	13484	11203	9810
40°	13156	10404	8701
45°	12771	9501	7695
50°	12376	8593	6712
55°	11972	7614	5762
60°	11502	6584	4782
65°	10968	5532	4359
70°	10334	4556	4008
75°	9551	4155	3737
80°	8433	3710	3403
85°	6632	2927	2927



TEST NUMBER: P331698-930

CATALOG NUMBER: SA2XXRDIP-C675D925U930-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.1	1.8
10°-20°	236.4	4.9
20°-30°	331.9	6.9
30°-40°	361.9	7.5
40°-50°	332.8	6.9
50°-60°	261.4	5.4
60°-70°	170.4	3.5
70°-80°	87.9	1.8
80°-90°	26.6	0.5
90°-100°	169.2	3.5
100°-110°	574.1	11.9
110°-120°	609.9	12.6
120°-130°	502.1	10.4
130°-140°	403.2	8.3
140°-150°	304.7	6.3
150°-160°	214.1	4.4
160°-170°	126.0	2.6
170°-180°	41.0	0.8
0°-30°	654.4	13.5
0°-40°	1016.3	21.0
0°-60°	1610.5	33.3
0°-90°	1895.3	39.2
90°-120°	1353.2	28.0
90°-150°	2563.1	53.0
90°-180°	2944.0	60.8
0°-180°	4839.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	920	920	920	920	920	
5°	920	915	905	912	910	87
15°	875	864	837	822	813	246
25°	794	766	712	680	666	365
35°	684	640	568	518	498	428
45°	559	502	416	359	337	432
55°	425	359	270	222	205	380
65°	287	219	145	118	114	285
75°	153	96	67	61	60	162
85°	36	19	16	16	16	42
90°	1	11	28	26	27	3
95°	28	70	319	120	93	30
105°	99	150	603	1078	917	106
115°	175	221	504	1041	1207	173
125°	244	289	485	843	979	217
135°	286	342	479	709	811	221
145°	327	376	477	592	648	205
155°	372	402	463	524	544	171
165°	405	417	443	470	478	114
175°	422	423	426	432	430	40
180°	423	423	423	423	423	



TEST NUMBER: P331698-930

CATALOG NUMBER: SA2XXRDIP-C675D925U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	919.7	919.7	919.7	919.7	919.7	919.7	919.7	919.7	919.7	919.7	919.7
2.5°	923.0	922.3	921.5	920.8	920.1	918.8	917.2	915.6	914.0	912.4	913.9
5°	919.7	918.8	917.9	916.9	916.0	914.4	911.9	909.5	907.1	904.7	906.4
7.5°	910.2	909.1	907.9	906.8	905.6	903.6	900.8	898.1	895.2	892.4	892.8
10°	902.2	900.9	899.6	898.3	897.0	894.5	890.8	887.1	883.5	879.7	879.2
12.5°	892.2	890.6	889.0	887.5	885.8	882.7	878.0	873.3	868.5	863.7	862.7
15°	874.7	872.7	870.7	868.6	866.6	862.4	856.1	849.9	843.6	837.3	833.8
17.5°	853.3	850.2	847.1	843.9	840.8	835.3	827.2	819.1	811.1	803.0	798.8
20°	837.3	833.6	829.9	826.2	822.5	816.0	806.7	797.5	788.3	779.0	774.4
22.5°	819.9	815.9	811.7	807.6	803.4	796.1	785.7	775.3	764.8	754.4	748.4
25°	794.0	788.1	782.2	776.2	770.4	761.2	749.1	736.9	724.6	712.4	704.8
27.5°	762.7	756.3	749.8	743.4	736.9	726.8	713.1	699.4	685.6	671.8	663.0
30°	740.8	733.7	726.7	719.7	712.7	701.7	686.9	672.1	657.3	642.5	633.1
32.5°	719.4	711.2	703.0	694.8	686.6	674.9	659.8	644.7	629.7	614.6	603.8
35°	684.1	674.7	665.3	655.8	646.5	633.6	617.3	601.0	584.7	568.4	556.8
37.5°	648.9	638.5	628.1	617.8	607.4	593.5	576.3	558.9	541.5	524.2	511.4
40°	624.2	613.1	602.0	590.9	579.8	565.3	547.4	529.5	511.5	493.6	480.5
42.5°	598.9	587.3	575.5	563.9	552.2	537.0	518.5	500.0	481.4	462.9	449.3
45°	559.3	546.9	534.5	522.1	509.7	493.8	474.4	455.0	435.5	416.1	403.0
47.5°	520.7	507.5	494.4	481.3	468.1	451.6	431.5	411.5	391.4	371.4	358.3
50°	492.7	479.6	466.4	453.3	440.2	423.5	403.1	382.8	362.4	342.1	329.3
52.5°	465.5	451.7	438.0	424.3	410.5	393.7	373.8	353.9	334.0	314.1	301.8
55°	425.3	410.9	396.5	382.0	367.6	350.4	330.4	310.5	290.5	270.5	259.4
57.5°	384.2	369.4	354.6	339.8	325.0	308.0	288.8	269.6	250.4	231.2	221.0
60°	356.2	341.4	326.6	311.9	297.0	280.1	261.1	242.0	223.0	203.9	194.4
62.5°	328.9	314.1	299.3	284.5	269.7	253.2	235.1	217.0	198.8	180.6	171.6
65°	287.1	272.1	257.1	242.2	227.2	211.4	194.8	178.1	161.4	144.8	138.5
67.5°	246.9	232.0	217.1	202.3	187.4	172.4	157.4	142.5	127.5	112.5	109.7
70°	218.9	204.5	190.0	175.6	161.2	147.6	134.9	122.1	109.3	96.5	94.7
72.5°	192.2	178.4	164.6	150.7	136.9	124.9	114.6	104.4	94.2	83.9	82.3
75°	153.1	140.2	127.3	114.3	101.3	91.7	85.4	79.2	72.9	66.6	65.3
77.5°	114.7	103.3	92.0	80.6	69.3	62.0	59.0	56.0	53.0	50.0	49.2
80°	90.7	81.3	71.8	62.5	53.0	47.4	45.5	43.6	41.8	39.9	39.2
82.5°	68.7	61.4	54.1	46.6	39.3	35.0	33.8	32.4	31.2	30.0	29.5
85°	35.8	31.9	28.0	24.1	20.2	18.0	17.4	17.0	16.4	15.8	15.8
87.5°	10.8	10.1	9.6	8.7	7.9	7.7	8.6	9.7	10.7	10.8	10.5
90°	0.8	3.3	6.5	8.2	9.8	12.2	16.3	21.9	26.8	27.6	26.8
92.5°	9.9	14.3	20.2	23.7	29.3	36.9	55.4	81.2	104.3	105.7	89.4
95°	28.5	31.7	39.9	47.2	60.3	79.7	117.2	187.9	282.3	318.9	279.1
97.5°	46.4	50.8	59.4	70.4	85.4	107.5	154.6	253.2	410.1	544.5	571.2
100°	62.6	65.1	72.4	85.4	101.7	124.5	167.6	266.9	442.6	642.8	760.0
102.5°	77.6	79.4	86.7	99.8	116.7	139.5	179.4	267.6	430.3	646.0	830.3
105°	99.3	102.6	108.2	120.4	138.4	161.1	199.3	271.7	406.0	602.9	819.4
107.5°	122.7	125.3	130.9	142.1	159.8	182.8	219.9	283.0	394.0	556.8	748.0
110°	138.4	141.6	146.4	157.0	174.1	197.7	233.5	292.1	391.4	534.6	703.0



TEST NUMBER: P331698-930

CATALOG NUMBER: SA2XXRDIP-C675D925U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	152.6	155.9	161.4	171.4	187.8	212.1	246.5	301.9	392.0	520.2	671.8
115°	175.0	179.0	183.9	193.6	209.9	231.9	266.9	316.5	395.4	504.5	633.1
117.5°	198.0	201.3	206.2	214.8	230.4	253.2	285.6	332.2	401.3	496.8	608.6
120°	212.4	215.6	220.5	227.8	244.1	266.9	298.6	342.6	405.2	492.3	595.7
122.5°	226.1	228.6	233.5	241.5	257.8	281.2	311.0	351.6	409.8	489.7	584.6
125°	244.1	246.5	251.4	261.2	277.4	300.3	329.5	366.2	416.6	484.9	568.8
127.5°	258.4	261.7	268.5	279.2	294.9	318.3	346.8	379.7	423.6	482.2	554.2
130°	266.9	270.1	278.3	289.7	306.0	328.7	357.2	388.2	428.8	480.9	544.4
132.5°	274.7	278.6	287.4	299.5	316.3	339.2	366.3	396.6	434.0	480.2	536.5
135°	286.4	289.7	299.5	311.6	330.4	353.1	379.2	407.6	440.2	479.2	525.6
137.5°	297.5	301.4	311.1	324.2	342.8	363.9	389.6	416.1	445.7	479.1	518.0
140°	306.0	309.2	318.9	332.0	349.9	371.0	395.4	420.7	448.3	478.4	513.5
142.5°	314.4	317.0	326.1	339.2	356.4	376.3	400.0	424.6	450.3	478.4	508.9
145°	327.1	330.4	338.5	350.7	367.0	384.9	406.8	429.7	452.4	476.8	502.9
147.5°	340.8	343.2	351.0	362.2	375.8	391.8	412.4	432.4	453.1	473.9	496.7
150°	349.9	352.3	358.8	369.4	381.6	396.2	415.0	433.7	452.4	472.0	491.5
152.5°	359.0	360.1	366.6	375.9	387.5	400.8	417.6	434.3	451.1	468.7	486.9
155°	371.9	372.7	377.6	386.5	395.4	407.6	421.5	435.3	449.1	463.0	478.4
157.5°	382.6	383.4	387.3	395.1	402.3	412.5	424.3	435.3	445.4	457.1	470.5
160°	389.8	390.6	393.8	400.3	406.8	415.8	425.6	435.3	443.4	453.2	464.6
162.5°	396.9	396.4	399.7	404.9	410.7	417.8	426.2	434.6	441.5	450.0	459.4
165°	405.2	404.4	406.0	410.9	415.0	419.9	427.2	432.9	437.7	443.4	450.8
167.5°	412.1	411.1	412.5	415.6	418.6	421.7	427.1	431.8	434.0	437.7	442.3
170°	416.6	415.0	415.8	418.2	419.9	422.3	426.4	430.5	432.1	434.5	437.7
172.5°	419.2	418.2	417.8	420.2	421.2	423.0	425.7	428.5	429.5	430.6	433.3
175°	422.3	421.5	420.7	422.3	422.3	423.1	424.8	426.4	425.6	426.4	427.2
177.5°	423.8	422.5	421.8	423.1	423.1	423.1	423.8	425.1	423.8	423.1	423.8
180°	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1



TEST NUMBER: P331698-930
 CATALOG NUMBER: SA2XXRDIP-C675D925U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	919.7	919.7	919.7	919.7	919.7	919.7	919.7	919.7
2.5°	915.3	916.8	918.3	918.8	918.6	918.3	918.0	917.7
5°	908.0	909.7	911.3	911.9	911.3	910.8	910.3	909.7
7.5°	893.3	893.8	894.3	894.1	893.1	892.2	891.2	890.2
10°	878.6	878.1	877.5	876.7	875.5	874.5	873.3	872.2
12.5°	861.8	860.8	859.7	858.3	856.5	854.7	852.8	850.9
15°	830.3	826.7	823.2	820.5	818.7	816.8	815.0	813.2
17.5°	794.7	790.4	786.3	782.6	779.4	776.2	773.1	769.9
20°	769.8	765.2	760.5	756.2	752.1	748.0	744.0	739.9
22.5°	742.5	736.5	730.6	726.1	723.0	720.0	717.0	714.0
25°	697.2	689.7	682.1	676.9	674.2	671.4	668.6	665.9
27.5°	654.1	645.3	636.5	629.8	625.4	621.0	616.6	612.2
30°	623.7	614.2	604.8	597.6	592.6	587.6	582.6	577.6
32.5°	593.0	582.3	571.5	563.8	559.1	554.4	549.7	545.0
35°	545.2	533.5	521.9	514.0	509.9	505.8	501.8	497.7
37.5°	498.5	485.7	472.9	464.1	459.4	454.8	450.1	445.5
40°	467.2	454.1	441.0	432.0	427.2	422.4	417.6	412.8
42.5°	435.8	422.2	408.6	399.5	394.8	390.2	385.6	380.8
45°	389.9	376.7	363.6	354.8	350.4	345.9	341.5	337.0
47.5°	345.3	332.2	319.1	310.6	306.6	302.6	298.5	294.5
50°	316.6	303.8	291.1	282.7	278.8	274.9	271.1	267.2
52.5°	289.5	277.1	264.8	256.9	253.3	249.7	246.1	242.6
55°	248.3	237.2	226.1	218.8	215.3	211.7	208.2	204.7
57.5°	210.8	200.7	190.5	183.9	181.0	178.1	175.0	172.1
60°	185.1	175.6	166.2	160.0	157.0	154.1	151.1	148.1
62.5°	162.7	153.6	144.6	139.3	137.5	135.7	134.0	132.2
65°	132.2	126.0	119.7	116.3	115.7	115.1	114.5	114.1
67.5°	106.7	103.9	101.0	99.2	98.7	98.1	97.5	96.9
70°	92.9	91.0	89.1	87.9	87.1	86.3	85.6	84.9
72.5°	80.8	79.2	77.7	76.7	76.2	75.8	75.3	74.9
75°	64.0	62.7	61.4	60.7	60.5	60.3	60.1	59.9
77.5°	48.4	47.7	47.0	46.5	46.1	45.9	45.6	45.2
80°	38.5	37.7	37.0	36.6	36.6	36.6	36.6	36.6
82.5°	29.1	28.6	28.2	28.0	28.0	28.0	28.0	28.0
85°	15.8	15.8	15.8	15.8	15.8	15.8	15.8	15.8
87.5°	10.3	9.8	9.9	10.0	10.0	10.0	10.0	10.0
90°	26.0	24.4	26.0	26.8	26.8	26.8	26.8	26.8
92.5°	70.9	60.9	54.1	49.0	48.3	45.7	46.4	45.1
95°	213.2	163.5	129.4	111.5	100.9	94.4	92.0	92.8
97.5°	497.5	407.0	318.9	260.2	221.4	201.3	189.4	182.6
100°	742.9	642.0	530.5	432.1	364.5	329.5	306.0	291.3
102.5°	903.7	880.9	799.4	695.0	621.7	561.9	532.5	512.7
105°	988.6	1080.6	1091.2	1064.3	1013.8	963.4	928.4	917.0
107.5°	927.5	1065.9	1150.6	1189.9	1196.3	1193.5	1186.5	1171.4
110°	874.7	1020.3	1124.5	1191.2	1226.2	1241.7	1249.0	1248.2



TEST NUMBER: P331698-930

CATALOG NUMBER: SA2XXRDIP-C675D925U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	826.6	966.4	1077.7	1154.1	1202.8	1228.7	1242.5	1246.9
115°	767.3	892.6	999.2	1083.0	1140.8	1178.2	1199.4	1206.7
117.5°	722.7	832.7	929.4	1008.0	1066.9	1106.4	1128.8	1134.9
120°	700.6	801.5	887.7	961.8	1018.7	1057.0	1080.6	1088.8
122.5°	683.0	775.4	857.1	924.1	975.1	1012.7	1033.7	1040.6
125°	657.5	741.3	812.9	873.9	921.1	952.0	972.3	978.8
127.5°	632.3	708.1	775.6	831.9	873.1	902.0	919.7	924.9
130°	616.0	685.9	750.2	804.0	843.8	871.5	887.7	894.2
132.5°	600.3	665.1	724.1	774.6	813.8	841.6	856.5	862.3
135°	578.5	632.3	685.9	731.5	766.5	793.4	808.0	811.2
137.5°	561.1	606.0	648.7	688.4	720.3	743.4	756.3	761.2
140°	550.1	589.1	626.6	662.3	688.4	709.6	721.8	726.6
142.5°	541.0	574.1	606.3	636.3	661.0	680.3	691.1	692.1
145°	528.1	555.0	580.2	603.7	623.3	637.2	645.2	647.7
147.5°	518.1	539.3	559.0	576.3	592.4	603.4	608.9	610.4
150°	511.0	528.9	546.0	560.6	572.8	582.6	587.5	588.3
152.5°	503.9	520.4	534.9	547.6	557.2	565.7	569.2	569.4
155°	493.9	507.0	519.1	528.1	537.0	542.7	546.0	544.4
157.5°	482.3	493.3	503.5	510.5	516.8	521.5	523.0	523.0
160°	475.2	484.1	493.1	498.8	504.5	508.6	509.4	509.4
162.5°	468.1	475.6	483.3	487.7	493.4	496.2	497.0	496.4
165°	457.3	463.0	468.7	472.0	475.2	478.4	478.4	477.6
167.5°	447.0	451.4	455.3	458.3	459.7	461.5	461.4	460.4
170°	441.8	444.3	447.5	449.1	450.0	452.4	451.6	450.0
172.5°	435.9	437.7	440.3	441.3	442.1	443.3	442.5	441.5
175°	429.7	430.5	431.3	432.1	432.1	432.9	432.1	430.5
177.5°	425.1	425.1	425.7	425.7	425.7	425.7	425.1	423.8
180°	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1

(END OF REPORT)