

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331332-840

Luminaire Tested: **SA2XXDIP-C675D330U840-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331332-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXDIP-C675D330U840-4F0-1E-UDD-A4  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 330 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4252.2 lumens  
Efficiency: N/A  
Efficacy: 121.5 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 35  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331332-840  
CATALOG NUMBER: SA2XXDIP-C675D330U840-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P331332-840

CATALOG NUMBER: SA2XXDIP-C675D330U840-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	94	94	94	84	84	84	74	74	74	70
1	103	99	95	91	97	93	90	87	84	81	79	75	73	71	67	65	64	60
2	94	87	81	76	89	83	77	73	74	70	66	67	63	61	59	57	55	51
3	86	77	70	64	82	73	67	62	66	61	57	59	55	52	53	50	48	44
4	79	69	61	55	75	65	58	53	59	54	49	53	49	45	48	45	42	39
5	73	62	54	48	69	59	52	46	53	47	43	48	44	40	44	40	37	34
6	68	56	48	42	64	53	46	41	49	42	38	44	39	35	40	36	33	30
7	63	51	43	37	60	49	41	36	44	38	34	40	35	32	37	33	29	27
8	59	46	39	33	56	44	37	32	41	35	30	37	32	28	34	30	27	24
9	55	43	35	30	52	41	34	29	37	32	27	34	29	26	31	27	24	22
10	51	39	32	27	49	38	31	26	35	29	25	32	27	24	29	25	22	20

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	21658	21658	21658	21658
5°	24280	21797	19316	21797
10°	27824	21620	16718	21620
15°	30780	21224	14770	21224
20°	30311	20797	13464	20797
25°	27332	20232	12636	20232
30°	22585	19328	12033	19328
35°	16462	18382	11606	18382
40°	13148	17266	11367	17266
45°	11488	15972	11040	15972
50°	10798	14722	10826	14722
55°	9956	13453	10536	13453
60°	9122	12103	10091	12103
65°	8309	10892	9650	10892
70°	7544	9711	9007	9711
75°	6687	8390	7973	8390
80°	5755	6946	6425	6946
85°	5169	5169	3816	5169



TEST NUMBER: P331332-840

CATALOG NUMBER: SA2XXDIP-C675D330U840-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	127.7	3.0
10°-20°	371.4	8.7
20°-30°	539.0	12.7
30°-40°	568.8	13.4
40°-50°	503.6	11.8
50°-60°	401.9	9.5
60°-70°	273.2	6.4
70°-80°	140.0	3.3
80°-90°	35.4	0.8
90°-100°	74.2	1.7
100°-110°	251.8	5.9
110°-120°	267.5	6.3
120°-130°	220.2	5.2
130°-140°	176.8	4.2
140°-150°	133.6	3.1
150°-160°	93.9	2.2
160°-170°	55.3	1.3
170°-180°	18.0	0.4
0°-30°	1038.1	24.4
0°-40°	1606.9	37.8
0°-60°	2512.4	59.1
0°-90°	2961.0	69.6
90°-120°	593.4	14.0
90°-150°	1124.0	26.4
90°-180°	1291.0	30.4
0°-180°	4252.2	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1341	1341	1341	1341	1341	
5°	1498	1345	1192	1345	1498	150
15°	1841	1270	884	1270	1841	508
25°	1534	1136	709	1136	1534	693
35°	835	933	589	933	835	543
45°	503	700	484	700	503	396
55°	354	478	374	478	354	317
65°	218	285	253	285	218	216
75°	107	134	128	134	107	115
85°	28	28	21	28	28	31
90°	12	0	12	0	12	8
95°	41	12	41	12	41	53
105°	402	44	402	44	402	389
115°	529	77	529	77	529	518
125°	429	107	429	107	429	388
135°	356	126	356	126	356	276
145°	284	143	284	143	284	180
155°	239	163	239	163	239	111
165°	209	178	209	178	209	60
175°	189	185	189	185	189	18
180°	186	186	186	186	186	



TEST NUMBER: P331332-840

CATALOG NUMBER: SA2XXDIP-C675D330U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1403.2	1403.6	1404.5	1397.9	1397.0	1397.0	1391.3	1386.3	1380.6	1372.7	1373.5
5°	1498.1	1503.8	1505.8	1499.6	1490.4	1489.3	1480.6	1466.1	1452.7	1441.9	1434.2
7.5°	1611.3	1613.6	1608.5	1600.3	1593.5	1581.1	1564.8	1548.8	1526.4	1505.9	1490.7
10°	1697.1	1700.2	1691.4	1679.6	1669.8	1655.4	1631.6	1607.4	1578.0	1549.6	1526.9
12.5°	1762.2	1769.9	1758.7	1757.1	1740.3	1720.5	1692.2	1680.0	1638.6	1599.1	1574.8
15°	1841.4	1840.9	1842.0	1832.2	1819.8	1816.6	1786.8	1754.3	1696.1	1672.8	1632.6
17.5°	1818.6	1826.3	1830.0	1829.9	1829.6	1827.7	1818.1	1797.6	1768.4	1730.7	1684.3
20°	1764.1	1774.4	1775.9	1787.9	1794.5	1803.3	1806.9	1801.2	1783.2	1751.7	1711.5
22.5°	1680.0	1682.8	1687.7	1706.2	1720.7	1742.6	1754.1	1773.2	1766.3	1750.9	1717.3
25°	1534.2	1529.0	1547.1	1556.3	1589.8	1624.9	1650.2	1678.0	1702.7	1717.7	1707.9
27.5°	1359.1	1351.4	1378.4	1403.0	1430.3	1468.2	1507.6	1554.1	1592.8	1641.1	1657.7
30°	1211.4	1216.1	1241.9	1268.2	1309.4	1363.0	1407.3	1458.4	1513.6	1567.7	1605.3
32.5°	1052.3	1070.2	1086.4	1126.7	1163.0	1222.8	1287.8	1351.6	1420.4	1481.9	1540.1
35°	835.2	855.8	878.5	907.9	958.9	1018.1	1081.6	1167.6	1261.5	1345.5	1414.6
37.5°	703.0	699.6	712.7	733.9	775.3	823.0	896.1	981.2	1091.6	1190.3	1287.8
40°	623.8	621.7	631.0	650.6	682.1	717.1	781.0	855.8	958.4	1078.9	1195.0
42.5°	569.4	570.6	575.7	589.6	611.1	640.0	687.8	751.4	845.4	959.0	1083.6
45°	503.1	506.8	512.4	519.2	531.5	555.2	582.0	627.4	701.7	796.5	919.2
47.5°	455.6	455.7	461.4	467.3	474.6	488.0	509.9	538.3	590.7	667.9	773.4
50°	429.9	426.4	430.5	435.0	442.8	452.1	466.6	493.3	528.4	590.8	678.9
52.5°	398.6	398.7	402.4	404.1	411.1	420.3	433.5	452.1	483.8	532.6	605.1
55°	353.7	356.2	358.3	361.3	367.6	374.3	384.6	397.0	421.7	458.3	511.9
57.5°	311.3	312.1	314.3	320.1	324.1	330.2	340.0	351.2	367.4	394.5	434.7
60°	282.5	282.5	286.6	289.2	294.4	300.5	308.3	319.1	333.6	355.7	388.2
62.5°	256.1	255.7	257.3	261.6	265.5	271.2	279.0	288.2	301.7	321.4	348.2
65°	217.5	216.5	219.6	220.7	224.8	230.5	236.6	246.4	257.2	271.7	295.4
67.5°	180.5	181.7	183.3	185.3	187.5	193.5	197.6	204.6	213.7	225.7	241.8
70°	159.8	159.8	159.8	161.4	164.4	167.5	171.7	177.3	186.1	196.4	210.9
72.5°	136.7	138.4	140.0	139.1	143.0	144.8	149.8	153.0	161.4	167.9	180.8
75°	107.2	107.2	107.2	109.8	111.4	112.9	116.0	119.1	123.2	131.5	138.1
77.5°	80.0	79.8	80.3	80.9	82.6	84.4	85.3	88.2	92.0	95.7	101.5
80°	61.9	62.9	63.4	64.4	64.4	65.4	65.9	69.6	72.2	74.7	78.4
82.5°	47.9	48.1	48.2	48.4	48.8	49.4	50.7	51.9	52.8	54.9	57.8
85°	27.9	27.4	27.4	28.4	27.9	27.9	28.9	29.9	29.9	30.4	31.9
87.5°	13.1	13.1	13.5	13.1	13.1	13.4	13.2	13.0	13.5	13.9	14.3
90°	11.8	11.8	11.8	11.8	11.8	11.4	10.7	11.4	11.8	12.1	11.8
92.5°	19.8	20.3	20.1	21.2	21.5	23.7	26.7	31.1	39.2	46.4	45.7
95°	40.7	40.3	41.4	44.2	48.9	56.8	71.7	93.5	122.4	139.9	123.8
97.5°	80.1	83.1	88.3	97.0	114.1	139.9	178.4	218.1	250.4	238.7	179.9
100°	127.7	134.2	144.5	159.9	189.5	232.7	281.6	325.8	333.3	281.9	194.1
102.5°	224.8	233.5	246.4	272.6	304.8	350.5	386.3	396.3	364.1	283.3	188.6
105°	402.1	407.1	422.4	444.5	466.8	478.5	473.8	433.5	359.3	264.4	178.0
107.5°	513.7	520.3	523.4	524.6	521.8	504.5	467.5	406.7	328.0	244.1	172.8
110°	547.3	547.8	544.5	537.8	522.4	493.1	447.5	383.5	308.3	234.4	171.7



TEST NUMBER: P331332-840

CATALOG NUMBER: SA2XXDIP-C675D330U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	546.7	544.8	538.8	527.5	506.1	472.5	423.7	362.4	294.6	228.1	171.9
115°	529.2	525.9	516.6	500.3	474.9	438.2	391.4	336.5	277.6	221.3	173.4
117.5°	497.7	494.9	485.2	467.9	442.0	407.6	365.2	316.9	266.9	217.8	176.0
120°	477.5	473.8	463.5	446.8	421.7	389.3	351.4	307.2	261.2	215.9	177.7
122.5°	456.3	453.3	444.1	427.6	405.2	375.9	340.0	299.5	256.3	214.7	179.7
125°	429.3	426.4	417.5	403.9	383.2	356.5	325.1	288.3	249.4	212.7	182.7
127.5°	405.6	403.2	395.6	382.8	364.8	340.1	310.5	277.2	243.0	211.5	185.7
130°	392.1	389.3	382.1	370.0	352.5	329.0	300.8	270.1	238.7	210.9	188.0
132.5°	378.2	375.6	369.0	356.9	339.7	317.6	291.6	263.3	235.3	210.6	190.4
135°	355.8	354.4	347.9	336.1	320.7	300.8	277.2	253.7	230.5	210.2	193.1
137.5°	333.8	331.6	326.0	315.9	301.8	284.5	265.8	246.1	227.1	210.1	195.5
140°	318.6	316.5	311.1	301.8	290.4	274.8	258.3	241.2	225.1	209.8	196.6
142.5°	303.5	303.1	298.3	289.8	279.0	265.9	251.8	237.2	223.2	209.8	197.4
145°	284.0	283.0	279.4	273.3	264.8	254.4	243.4	231.6	220.6	209.0	198.3
147.5°	267.7	267.0	264.6	259.7	252.7	245.1	236.5	227.2	217.8	207.8	198.6
150°	258.0	257.6	255.5	251.2	245.8	239.4	232.0	224.1	215.5	206.9	198.3
152.5°	249.7	249.6	248.0	244.4	240.1	234.6	228.2	221.0	213.5	205.5	197.8
155°	238.7	239.4	238.0	235.5	231.6	227.6	222.3	216.6	209.8	203.0	196.9
157.5°	229.3	229.3	228.7	226.6	223.9	220.8	216.3	211.6	206.3	200.5	195.3
160°	223.4	223.4	223.0	221.3	218.7	216.2	212.3	208.3	203.7	198.7	194.5
162.5°	217.6	217.9	217.6	216.4	213.9	212.0	208.6	205.2	201.5	197.3	193.6
165°	209.4	209.8	209.8	208.3	206.9	205.5	203.0	200.6	197.6	194.5	192.0
167.5°	201.9	202.3	202.4	201.6	201.0	199.7	197.9	196.0	194.0	192.0	190.4
170°	197.3	198.0	198.3	197.3	196.9	196.2	194.8	193.8	192.0	190.6	189.5
172.5°	193.6	194.0	194.4	193.9	193.5	193.1	192.0	191.2	190.0	188.8	188.3
175°	188.7	189.5	189.9	189.5	189.5	189.1	188.7	188.4	187.3	186.9	186.6
177.5°	185.8	186.4	186.7	186.7	186.7	186.7	186.4	186.4	185.8	185.5	185.8
180°	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5



TEST NUMBER: P331332-840

CATALOG NUMBER: SA2XXDIP-C675D330U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1376.4	1373.1	1371.1	1363.6	1357.1	1350.5	1348.4	1349.2	1340.2	1331.5	1327.8
5°	1430.1	1419.8	1410.0	1396.0	1379.6	1361.5	1352.2	1344.9	1327.0	1307.4	1296.1
7.5°	1478.1	1463.4	1444.5	1418.3	1394.3	1365.9	1347.9	1331.9	1305.5	1277.9	1260.9
10°	1507.4	1487.2	1463.0	1431.1	1401.7	1367.2	1342.9	1318.7	1287.8	1254.8	1234.2
12.5°	1532.6	1505.4	1481.6	1440.6	1405.8	1362.6	1333.8	1299.7	1267.2	1228.0	1207.8
15°	1592.5	1542.5	1497.0	1450.7	1407.9	1347.6	1315.7	1269.7	1226.9	1178.5	1155.3
17.5°	1638.7	1582.6	1511.1	1452.1	1402.2	1335.4	1288.5	1233.6	1183.0	1127.5	1096.0
20°	1665.2	1600.6	1523.9	1453.8	1393.9	1317.7	1266.7	1210.4	1151.1	1088.7	1054.7
22.5°	1680.8	1613.1	1537.1	1447.5	1377.5	1303.2	1239.0	1177.4	1117.3	1050.1	1014.3
25°	1685.8	1623.9	1543.5	1442.4	1356.9	1272.8	1195.5	1135.7	1063.0	1000.1	948.1
27.5°	1661.2	1616.9	1539.5	1432.7	1333.0	1234.8	1148.6	1080.9	1004.1	935.8	883.5
30°	1631.1	1605.3	1530.0	1422.8	1314.0	1208.4	1113.5	1036.7	960.4	891.3	837.7
32.5°	1584.5	1578.9	1512.8	1408.8	1293.8	1175.0	1076.8	999.2	914.6	846.8	795.7
35°	1493.0	1517.7	1475.9	1377.5	1255.8	1127.4	1021.3	932.6	845.0	780.0	732.1
37.5°	1370.3	1431.7	1420.8	1331.6	1204.5	1075.7	958.5	865.8	782.2	716.7	669.6
40°	1285.7	1364.0	1375.4	1296.6	1168.2	1035.7	911.4	819.2	737.7	677.9	630.5
42.5°	1195.0	1286.6	1317.7	1254.5	1128.5	993.6	869.4	773.8	693.2	635.0	593.0
45°	1042.9	1164.1	1220.2	1184.2	1062.5	924.3	796.5	699.5	626.3	571.7	539.3
47.5°	900.7	1033.1	1108.6	1095.9	989.0	852.1	725.8	632.8	561.5	517.9	488.8
50°	800.1	936.1	1027.4	1031.6	936.1	800.6	673.8	586.1	520.7	480.0	456.3
52.5°	712.7	842.5	942.1	963.9	877.2	747.0	627.2	540.0	482.3	444.8	423.6
55°	598.5	708.3	818.6	858.9	789.2	665.5	554.7	477.9	423.7	398.0	379.4
57.5°	497.6	589.2	691.1	735.5	692.6	586.6	482.7	416.1	372.1	349.5	335.3
60°	444.3	516.5	607.2	660.4	623.3	529.0	438.2	374.8	338.7	318.6	305.2
62.5°	394.9	458.8	535.5	584.1	563.9	474.9	393.6	337.7	306.5	287.6	278.0
65°	325.8	376.4	435.7	480.5	467.1	399.5	333.1	285.1	260.3	245.4	237.6
67.5°	268.3	304.8	345.9	385.2	374.4	326.5	273.2	235.8	217.3	204.5	199.9
70°	232.0	259.8	296.4	327.9	319.1	279.9	237.6	205.7	189.8	178.8	174.2
72.5°	197.3	220.3	248.1	273.9	267.9	235.4	200.2	176.0	163.7	153.7	149.9
75°	149.0	166.5	183.5	200.6	198.9	173.7	153.1	134.5	124.7	117.0	115.4
77.5°	110.0	119.8	131.4	141.5	138.7	124.2	108.1	97.5	90.2	85.0	84.2
80°	84.0	89.7	98.0	105.1	101.6	95.3	82.5	74.7	69.6	64.4	62.4
82.5°	60.9	66.7	71.6	75.4	72.7	67.0	59.0	53.7	50.6	47.2	46.3
85°	31.9	35.0	37.2	38.2	37.2	33.5	29.9	27.9	25.2	23.7	23.2
87.5°	14.3	13.8	13.4	14.0	12.6	12.5	10.6	9.2	9.0	8.8	8.2
90°	9.6	7.2	5.4	4.2	3.5	2.8	1.4	0.4	1.4	2.8	3.5
92.5°	35.6	24.2	16.2	12.8	10.4	8.9	6.3	4.3	6.3	8.9	10.4
95°	82.4	51.4	34.9	26.4	20.7	17.5	13.9	12.5	13.9	17.5	20.7
97.5°	111.1	67.8	47.2	37.5	30.9	26.1	22.2	20.3	22.2	26.1	30.9
100°	117.0	73.5	54.6	44.6	37.5	31.7	28.6	27.5	28.6	31.7	37.5
102.5°	117.3	78.7	61.2	51.2	43.7	38.1	34.8	34.0	34.8	38.1	43.7
105°	119.2	87.5	70.7	60.7	52.8	47.5	44.9	43.5	44.9	47.5	52.8
107.5°	124.1	96.4	80.2	70.1	62.3	57.4	54.9	53.8	54.9	57.4	62.3
110°	128.1	102.4	86.7	76.3	68.9	64.2	62.1	60.7	62.1	64.2	68.9





TEST NUMBER: P331332-840

CATALOG NUMBER: SA2XXDIP-C675D330U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	132.4	108.2	93.0	82.3	75.1	70.8	68.4	67.0	68.4	70.8	75.1
115°	138.8	117.0	101.7	92.1	84.9	80.7	78.5	76.7	78.5	80.7	84.9
117.5°	145.6	125.2	111.1	101.1	94.2	90.4	88.3	86.8	88.3	90.4	94.2
120°	150.3	131.0	117.0	107.0	99.9	96.7	94.5	93.1	94.5	96.7	99.9
122.5°	154.2	136.3	123.3	113.0	105.9	102.4	100.3	99.2	100.3	102.4	105.9
125°	160.6	144.5	131.7	121.7	114.5	110.3	108.2	107.0	108.2	110.3	114.5
127.5°	166.5	152.1	139.6	129.3	122.5	117.8	114.7	113.3	114.7	117.8	122.5
130°	170.2	156.6	144.1	134.2	127.0	122.0	118.5	117.0	118.5	122.0	127.0
132.5°	173.9	160.7	148.8	138.8	131.3	126.0	122.2	120.5	122.2	126.0	131.3
135°	178.7	166.3	154.8	144.9	136.6	131.3	127.0	125.6	127.0	131.3	136.6
137.5°	182.5	170.9	159.6	150.3	142.2	136.4	132.2	130.5	132.2	136.4	142.2
140°	184.5	173.4	162.7	153.4	145.6	139.9	135.6	134.2	135.6	139.9	145.6
142.5°	186.2	175.4	165.0	156.3	148.8	143.0	139.1	137.8	139.1	143.0	148.8
145°	188.4	178.4	168.7	161.0	153.8	148.5	144.9	143.4	144.9	148.5	153.8
147.5°	189.7	180.9	171.8	164.8	158.9	153.9	150.5	149.5	150.5	153.9	158.9
150°	190.2	182.0	173.8	167.3	162.0	157.3	154.5	153.4	154.5	157.3	162.0
152.5°	190.5	183.1	175.7	170.0	164.8	160.8	157.9	157.4	157.9	160.8	164.8
155°	190.9	184.8	178.7	173.4	169.5	165.5	163.4	163.1	163.4	165.5	169.5
157.5°	190.9	186.0	180.9	176.4	173.3	169.9	168.1	167.7	168.1	169.9	173.3
160°	190.9	186.6	182.4	178.4	175.5	172.7	171.3	170.9	171.3	172.7	175.5
162.5°	190.6	186.9	183.2	180.2	177.5	175.3	173.8	174.1	173.8	175.3	177.5
165°	189.9	187.3	184.1	182.0	180.2	178.0	177.3	177.7	177.3	178.0	180.2
167.5°	189.3	187.2	184.9	183.6	182.3	180.9	180.3	180.7	180.3	180.9	182.3
170°	188.7	186.9	185.2	184.1	183.4	182.4	182.0	182.7	182.0	182.4	183.4
172.5°	187.9	186.7	185.5	184.7	184.3	183.2	183.4	183.8	183.4	183.2	184.3
175°	186.9	186.2	185.5	185.2	185.2	184.5	184.8	185.2	184.8	184.5	185.2
177.5°	186.4	185.8	185.5	185.5	185.5	185.0	185.2	185.8	185.2	185.0	185.5
180°	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5



TEST NUMBER: P331332-840

CATALOG NUMBER: SA2XXDIP-C675D330U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1323.6	1321.2	1312.5	1308.0	1300.5	1293.5	1289.0	1291.1	1292.7	1291.9	1290.6
5°	1285.7	1275.9	1260.9	1248.1	1238.8	1221.7	1214.6	1210.9	1207.9	1204.3	1200.6
7.5°	1240.5	1225.1	1203.7	1185.3	1167.9	1146.8	1134.8	1127.5	1120.1	1112.0	1104.8
10°	1208.4	1186.7	1164.1	1138.2	1117.6	1098.5	1081.6	1070.3	1060.0	1050.2	1042.9
12.5°	1174.6	1149.6	1121.6	1086.3	1063.6	1036.3	1033.7	1013.7	997.6	991.6	983.1
15°	1120.7	1085.7	1050.2	1008.4	990.3	965.5	950.1	934.6	920.7	910.9	908.4
17.5°	1059.6	1014.2	978.9	948.9	919.3	893.9	879.7	867.3	855.9	842.7	841.0
20°	1013.0	973.8	935.1	908.9	878.5	852.6	835.2	822.7	812.9	805.3	798.5
22.5°	968.9	925.9	890.6	861.8	831.8	811.0	797.2	785.3	777.1	768.5	762.2
25°	898.1	864.5	825.9	793.3	768.6	755.3	743.9	733.6	728.4	722.8	715.6
27.5°	836.1	798.8	762.7	737.5	715.8	703.9	695.8	688.8	684.0	680.6	676.6
30°	792.3	754.7	726.4	701.7	683.6	671.8	666.6	662.5	656.8	654.7	652.7
32.5°	750.3	716.4	692.2	670.7	653.5	645.7	641.0	637.3	632.9	630.8	626.6
35°	690.7	662.5	638.7	626.8	613.0	606.2	602.7	597.4	593.4	591.3	590.8
37.5°	634.8	610.2	594.6	579.4	573.5	569.4	564.4	560.9	559.7	559.4	558.9
40°	598.5	578.5	564.5	552.1	549.6	543.3	539.3	536.1	536.1	536.6	536.1
42.5°	565.5	547.4	535.2	524.5	521.5	517.8	513.6	513.4	514.3	516.0	514.3
45°	515.5	502.6	493.8	488.7	483.0	479.4	478.9	480.5	481.0	481.5	483.0
47.5°	469.5	461.0	453.0	447.4	444.8	444.2	443.6	446.4	448.8	449.7	452.1
50°	442.3	432.5	425.9	422.2	420.1	419.1	420.1	423.2	425.3	427.9	429.4
52.5°	411.8	404.9	400.2	397.5	396.7	397.3	397.5	401.0	404.2	405.2	406.0
55°	369.6	364.5	363.5	358.8	360.8	360.3	362.9	365.0	368.1	371.1	371.7
57.5°	327.6	323.5	320.6	321.0	321.6	324.0	326.1	329.7	333.1	336.3	336.6
60°	299.5	297.4	295.9	295.9	296.9	300.0	302.7	306.2	308.3	310.3	311.8
62.5°	274.0	271.9	270.3	271.1	273.9	275.7	278.7	280.6	282.7	284.8	285.5
65°	233.5	232.5	234.1	235.1	235.6	238.1	241.8	243.3	245.4	246.4	250.0
67.5°	196.3	196.5	196.3	197.7	200.8	201.4	204.8	208.3	208.7	210.8	213.1
70°	171.2	172.2	173.2	174.2	176.8	177.8	180.5	182.0	184.0	185.6	187.1
72.5°	148.0	148.2	149.3	149.1	151.3	153.5	155.7	157.2	159.3	161.3	162.8
75°	113.9	113.9	114.9	115.4	118.1	120.7	120.1	121.2	123.2	125.2	126.3
77.5°	83.2	82.1	83.2	83.7	84.5	86.7	87.2	88.6	90.9	90.2	91.4
80°	63.4	61.9	63.4	63.9	63.9	66.6	66.6	67.6	69.1	67.6	69.1
82.5°	45.2	44.5	45.6	45.7	46.6	46.7	47.6	47.8	49.3	48.6	49.3
85°	22.7	22.2	22.7	22.2	22.7	23.2	23.2	22.7	22.7	23.7	22.2
87.5°	7.9	7.7	7.6	8.1	8.1	7.8	7.3	7.3	7.1	6.4	6.5
90°	4.2	5.4	7.2	9.6	11.8	12.1	11.8	11.4	10.7	11.4	11.8
92.5°	12.8	16.2	24.2	35.6	45.7	46.4	39.2	31.1	26.7	23.7	21.5
95°	26.4	34.9	51.4	82.4	123.8	139.9	122.4	93.5	71.7	56.8	48.9
97.5°	37.5	47.2	67.8	111.1	179.9	238.7	250.4	218.1	178.4	139.9	114.1
100°	44.6	54.6	73.5	117.0	194.1	281.9	333.3	325.8	281.6	232.7	189.5
102.5°	51.2	61.2	78.7	117.3	188.6	283.3	364.1	396.3	386.3	350.5	304.8
105°	60.7	70.7	87.5	119.2	178.0	264.4	359.3	433.5	473.8	478.5	466.8
107.5°	70.1	80.2	96.4	124.1	172.8	244.1	328.0	406.7	467.5	504.5	521.8
110°	76.3	86.7	102.4	128.1	171.7	234.4	308.3	383.5	447.5	493.1	522.4



TEST NUMBER: P331332-840

CATALOG NUMBER: SA2XXDIP-C675D330U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	82.3	93.0	108.2	132.4	171.9	228.1	294.6	362.4	423.7	472.5	506.1
115°	92.1	101.7	117.0	138.8	173.4	221.3	277.6	336.5	391.4	438.2	474.9
117.5°	101.1	111.1	125.2	145.6	176.0	217.8	266.9	316.9	365.2	407.6	442.0
120°	107.0	117.0	131.0	150.3	177.7	215.9	261.2	307.2	351.4	389.3	421.7
122.5°	113.0	123.3	136.3	154.2	179.7	214.7	256.3	299.5	340.0	375.9	405.2
125°	121.7	131.7	144.5	160.6	182.7	212.7	249.4	288.3	325.1	356.5	383.2
127.5°	129.3	139.6	152.1	166.5	185.7	211.5	243.0	277.2	310.5	340.1	364.8
130°	134.2	144.1	156.6	170.2	188.0	210.9	238.7	270.1	300.8	329.0	352.5
132.5°	138.8	148.8	160.7	173.9	190.4	210.6	235.3	263.3	291.6	317.6	339.7
135°	144.9	154.8	166.3	178.7	193.1	210.2	230.5	253.7	277.2	300.8	320.7
137.5°	150.3	159.6	170.9	182.5	195.5	210.1	227.1	246.1	265.8	284.5	301.8
140°	153.4	162.7	173.4	184.5	196.6	209.8	225.1	241.2	258.3	274.8	290.4
142.5°	156.3	165.0	175.4	186.2	197.4	209.8	223.2	237.2	251.8	265.9	279.0
145°	161.0	168.7	178.4	188.4	198.3	209.0	220.6	231.6	243.4	254.4	264.8
147.5°	164.8	171.8	180.9	189.7	198.6	207.8	217.8	227.2	236.5	245.1	252.7
150°	167.3	173.8	182.0	190.2	198.3	206.9	215.5	224.1	232.0	239.4	245.8
152.5°	170.0	175.7	183.1	190.5	197.8	205.5	213.5	221.0	228.2	234.6	240.1
155°	173.4	178.7	184.8	190.9	196.9	203.0	209.8	216.6	222.3	227.6	231.6
157.5°	176.4	180.9	186.0	190.9	195.3	200.5	206.3	211.6	216.3	220.8	223.9
160°	178.4	182.4	186.6	190.9	194.5	198.7	203.7	208.3	212.3	216.2	218.7
162.5°	180.2	183.2	186.9	190.6	193.6	197.3	201.5	205.2	208.6	212.0	213.9
165°	182.0	184.1	187.3	189.9	192.0	194.5	197.6	200.6	203.0	205.5	206.9
167.5°	183.6	184.9	187.2	189.3	190.4	192.0	194.0	196.0	197.9	199.7	201.0
170°	184.1	185.2	186.9	188.7	189.5	190.6	192.0	193.8	194.8	196.2	196.9
172.5°	184.7	185.5	186.7	187.9	188.3	188.8	190.0	191.2	192.0	193.1	193.5
175°	185.2	185.5	186.2	186.9	186.6	186.9	187.3	188.4	188.7	189.1	189.5
177.5°	185.5	185.5	185.8	186.4	185.8	185.5	185.8	186.4	186.4	186.7	186.7
180°	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5



TEST NUMBER: P331332-840

CATALOG NUMBER: SA2XXDIP-C675D330U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1286.6	1285.7	1285.7	1282.0	1285.7	1285.7	1286.6	1290.6	1291.9	1292.7	1291.1
5°	1193.5	1191.8	1189.3	1191.8	1189.3	1191.8	1193.5	1200.6	1204.3	1207.9	1210.9
7.5°	1101.4	1095.2	1094.3	1088.1	1094.3	1095.2	1101.4	1104.8	1112.0	1120.1	1127.5
10°	1034.1	1030.0	1029.5	1019.7	1029.5	1030.0	1034.1	1042.9	1050.2	1060.0	1070.3
12.5°	983.0	973.1	975.0	969.4	975.0	973.1	983.0	983.1	991.6	997.6	1013.7
15°	894.4	894.4	892.3	883.6	892.3	894.4	894.4	908.4	910.9	920.7	934.6
17.5°	830.8	829.8	824.9	827.3	824.9	829.8	830.8	841.0	842.7	855.9	867.3
20°	792.8	789.8	783.6	783.6	783.6	789.8	792.8	798.5	805.3	812.9	822.7
22.5°	757.0	756.8	750.2	752.2	750.2	756.8	757.0	762.2	768.5	777.1	785.3
25°	715.0	710.9	707.8	709.3	707.8	710.9	715.0	715.6	722.8	728.4	733.6
27.5°	675.2	673.0	672.8	668.5	672.8	673.0	675.2	676.6	680.6	684.0	688.8
30°	652.2	647.0	648.0	645.4	648.0	647.0	652.2	652.7	654.7	656.8	662.5
32.5°	625.7	623.9	622.9	620.7	622.9	623.9	625.7	626.6	630.8	632.9	637.3
35°	589.8	590.3	587.7	588.8	587.7	590.3	589.8	590.8	591.3	593.4	597.4
37.5°	558.4	560.0	558.8	559.1	558.8	560.0	558.4	558.9	559.4	559.7	560.9
40°	537.7	537.7	537.7	539.3	537.7	537.7	537.7	536.1	536.6	536.1	536.1
42.5°	517.9	517.1	516.2	516.1	516.2	517.1	517.9	514.3	516.0	514.3	513.4
45°	484.0	485.6	486.1	483.5	486.1	485.6	484.0	483.0	481.5	481.0	480.5
47.5°	453.4	453.6	453.4	455.8	453.4	453.6	453.4	452.1	449.7	448.8	446.4
50°	432.0	431.0	432.0	431.0	432.0	431.0	432.0	429.4	427.9	425.3	423.2
52.5°	409.3	409.5	408.9	408.7	408.9	409.5	409.3	406.0	405.2	404.2	401.0
55°	373.8	374.8	374.3	374.3	374.3	374.8	373.8	371.7	371.1	368.1	365.0
57.5°	337.0	337.9	338.6	336.3	338.6	337.9	337.0	336.6	336.3	333.1	329.7
60°	311.3	314.0	313.5	312.5	313.5	314.0	311.3	311.8	310.3	308.3	306.2
62.5°	287.9	288.8	288.7	288.5	288.7	288.8	287.9	285.5	284.8	282.7	280.6
65°	251.6	252.6	251.1	252.6	251.1	252.6	251.6	250.0	246.4	245.4	243.3
67.5°	212.5	212.8	214.0	214.7	214.0	212.8	212.5	213.1	210.8	208.7	208.3
70°	188.1	187.6	189.1	190.8	189.1	187.6	188.1	187.1	185.6	184.0	182.0
72.5°	162.6	163.7	163.2	164.3	163.2	163.7	162.6	162.8	161.3	159.3	157.2
75°	125.2	126.8	126.3	127.8	126.3	126.8	125.2	126.3	125.2	123.2	121.2
77.5°	90.5	90.7	90.5	91.4	90.5	90.7	90.5	91.4	90.2	90.9	88.6
80°	69.1	68.1	67.1	69.1	67.1	68.1	69.1	69.1	67.6	69.1	67.6
82.5°	48.1	48.7	47.7	47.7	47.7	48.7	48.1	49.3	48.6	49.3	47.8
85°	22.2	21.6	20.6	20.6	20.6	21.6	22.2	22.2	23.7	22.7	22.7
87.5°	6.5	6.1	6.1	5.7	6.1	6.1	6.5	6.5	6.4	7.1	7.3
90°	11.8	11.8	11.8	11.8	11.8	11.8	11.8	11.8	11.4	10.7	11.4
92.5°	21.2	20.1	20.3	19.8	20.3	20.1	21.2	21.5	23.7	26.7	31.1
95°	44.2	41.4	40.3	40.7	40.3	41.4	44.2	48.9	56.8	71.7	93.5
97.5°	97.0	88.3	83.1	80.1	83.1	88.3	97.0	114.1	139.9	178.4	218.1
100°	159.9	144.5	134.2	127.7	134.2	144.5	159.9	189.5	232.7	281.6	325.8
102.5°	272.6	246.4	233.5	224.8	233.5	246.4	272.6	304.8	350.5	386.3	396.3
105°	444.5	422.4	407.1	402.1	407.1	422.4	444.5	466.8	478.5	473.8	433.5
107.5°	524.6	523.4	520.3	513.7	520.3	523.4	524.6	521.8	504.5	467.5	406.7
110°	537.8	544.5	547.8	547.3	547.8	544.5	537.8	522.4	493.1	447.5	383.5



TEST NUMBER: P331332-840

CATALOG NUMBER: SA2XXDIP-C675D330U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	527.5	538.8	544.8	546.7	544.8	538.8	527.5	506.1	472.5	423.7	362.4
115°	500.3	516.6	525.9	529.2	525.9	516.6	500.3	474.9	438.2	391.4	336.5
117.5°	467.9	485.2	494.9	497.7	494.9	485.2	467.9	442.0	407.6	365.2	316.9
120°	446.8	463.5	473.8	477.5	473.8	463.5	446.8	421.7	389.3	351.4	307.2
122.5°	427.6	444.1	453.3	456.3	453.3	444.1	427.6	405.2	375.9	340.0	299.5
125°	403.9	417.5	426.4	429.3	426.4	417.5	403.9	383.2	356.5	325.1	288.3
127.5°	382.8	395.6	403.2	405.6	403.2	395.6	382.8	364.8	340.1	310.5	277.2
130°	370.0	382.1	389.3	392.1	389.3	382.1	370.0	352.5	329.0	300.8	270.1
132.5°	356.9	369.0	375.6	378.2	375.6	369.0	356.9	339.7	317.6	291.6	263.3
135°	336.1	347.9	354.4	355.8	354.4	347.9	336.1	320.7	300.8	277.2	253.7
137.5°	315.9	326.0	331.6	333.8	331.6	326.0	315.9	301.8	284.5	265.8	246.1
140°	301.8	311.1	316.5	318.6	316.5	311.1	301.8	290.4	274.8	258.3	241.2
142.5°	289.8	298.3	303.1	303.5	303.1	298.3	289.8	279.0	265.9	251.8	237.2
145°	273.3	279.4	283.0	284.0	283.0	279.4	273.3	264.8	254.4	243.4	231.6
147.5°	259.7	264.6	267.0	267.7	267.0	264.6	259.7	252.7	245.1	236.5	227.2
150°	251.2	255.5	257.6	258.0	257.6	255.5	251.2	245.8	239.4	232.0	224.1
152.5°	244.4	248.0	249.6	249.7	249.6	248.0	244.4	240.1	234.6	228.2	221.0
155°	235.5	238.0	239.4	238.7	239.4	238.0	235.5	231.6	227.6	222.3	216.6
157.5°	226.6	228.7	229.3	229.3	229.3	228.7	226.6	223.9	220.8	216.3	211.6
160°	221.3	223.0	223.4	223.4	223.4	223.0	221.3	218.7	216.2	212.3	208.3
162.5°	216.4	217.6	217.9	217.6	217.9	217.6	216.4	213.9	212.0	208.6	205.2
165°	208.3	209.8	209.8	209.4	209.8	209.8	208.3	206.9	205.5	203.0	200.6
167.5°	201.6	202.4	202.3	201.9	202.3	202.4	201.6	201.0	199.7	197.9	196.0
170°	197.3	198.3	198.0	197.3	198.0	198.3	197.3	196.9	196.2	194.8	193.8
172.5°	193.9	194.4	194.0	193.6	194.0	194.4	193.9	193.5	193.1	192.0	191.2
175°	189.5	189.9	189.5	188.7	189.5	189.9	189.5	189.5	189.1	188.7	188.4
177.5°	186.7	186.7	186.4	185.8	186.4	186.7	186.7	186.7	186.7	186.4	186.4
180°	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5



TEST NUMBER: P331332-840

CATALOG NUMBER: SA2XXDIP-C675D330U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1289.0	1293.5	1300.5	1308.0	1312.5	1321.2	1323.6	1327.8	1331.5	1340.2	1349.2
5°	1214.6	1221.7	1238.8	1248.1	1260.9	1275.9	1285.7	1296.1	1307.4	1327.0	1344.9
7.5°	1134.8	1146.8	1167.9	1185.3	1203.7	1225.1	1240.5	1260.9	1277.9	1305.5	1331.9
10°	1081.6	1098.5	1117.6	1138.2	1164.1	1186.7	1208.4	1234.2	1254.8	1287.8	1318.7
12.5°	1033.7	1036.3	1063.6	1086.3	1121.6	1149.6	1174.6	1207.8	1228.0	1267.2	1299.7
15°	950.1	965.5	990.3	1008.4	1050.2	1085.7	1120.7	1155.3	1178.5	1226.9	1269.7
17.5°	879.7	893.9	919.3	948.9	978.9	1014.2	1059.6	1096.0	1127.5	1183.0	1233.6
20°	835.2	852.6	878.5	908.9	935.1	973.8	1013.0	1054.7	1088.7	1151.1	1210.4
22.5°	797.2	811.0	831.8	861.8	890.6	925.9	968.9	1014.3	1050.1	1117.3	1177.4
25°	743.9	755.3	768.6	793.3	825.9	864.5	898.1	948.1	1000.1	1063.0	1135.7
27.5°	695.8	703.9	715.8	737.5	762.7	798.8	836.1	883.5	935.8	1004.1	1080.9
30°	666.6	671.8	683.6	701.7	726.4	754.7	792.3	837.7	891.3	960.4	1036.7
32.5°	641.0	645.7	653.5	670.7	692.2	716.4	750.3	795.7	846.8	914.6	999.2
35°	602.7	606.2	613.0	626.8	638.7	662.5	690.7	732.1	780.0	845.0	932.6
37.5°	564.4	569.4	573.5	579.4	594.6	610.2	634.8	669.6	716.7	782.2	865.8
40°	539.3	543.3	549.6	552.1	564.5	578.5	598.5	630.5	677.9	737.7	819.2
42.5°	513.6	517.8	521.5	524.5	535.2	547.4	565.5	593.0	635.0	693.2	773.8
45°	478.9	479.4	483.0	488.7	493.8	502.6	515.5	539.3	571.7	626.3	699.5
47.5°	443.6	444.2	444.8	447.4	453.0	461.0	469.5	488.8	517.9	561.5	632.8
50°	420.1	419.1	420.1	422.2	425.9	432.5	442.3	456.3	480.0	520.7	586.1
52.5°	397.5	397.3	396.7	397.5	400.2	404.9	411.8	423.6	444.8	482.3	540.0
55°	362.9	360.3	360.8	358.8	363.5	364.5	369.6	379.4	398.0	423.7	477.9
57.5°	326.1	324.0	321.6	321.0	320.6	323.5	327.6	335.3	349.5	372.1	416.1
60°	302.7	300.0	296.9	295.9	295.9	297.4	299.5	305.2	318.6	338.7	374.8
62.5°	278.7	275.7	273.9	271.1	270.3	271.9	274.0	278.0	287.6	306.5	337.7
65°	241.8	238.1	235.6	235.1	234.1	232.5	233.5	237.6	245.4	260.3	285.1
67.5°	204.8	201.4	200.8	197.7	196.3	196.5	196.3	199.9	204.5	217.3	235.8
70°	180.5	177.8	176.8	174.2	173.2	172.2	171.2	174.2	178.8	189.8	205.7
72.5°	155.7	153.5	151.3	149.1	149.3	148.2	148.0	149.9	153.7	163.7	176.0
75°	120.1	120.7	118.1	115.4	114.9	113.9	113.9	115.4	117.0	124.7	134.5
77.5°	87.2	86.7	84.5	83.7	83.2	82.1	83.2	84.2	85.0	90.2	97.5
80°	66.6	66.6	63.9	63.9	63.4	61.9	63.4	62.4	64.4	69.6	74.7
82.5°	47.6	46.7	46.6	45.7	45.6	44.5	45.2	46.3	47.2	50.6	53.7
85°	23.2	23.2	22.7	22.2	22.7	22.2	22.7	23.2	23.7	25.2	27.9
87.5°	7.3	7.8	8.1	8.1	7.6	7.7	7.9	8.2	8.8	9.0	9.2
90°	11.8	12.1	11.8	9.6	7.2	5.4	4.2	3.5	2.8	1.4	0.4
92.5°	39.2	46.4	45.7	35.6	24.2	16.2	12.8	10.4	8.9	6.3	4.3
95°	122.4	139.9	123.8	82.4	51.4	34.9	26.4	20.7	17.5	13.9	12.5
97.5°	250.4	238.7	179.9	111.1	67.8	47.2	37.5	30.9	26.1	22.2	20.3
100°	333.3	281.9	194.1	117.0	73.5	54.6	44.6	37.5	31.7	28.6	27.5
102.5°	364.1	283.3	188.6	117.3	78.7	61.2	51.2	43.7	38.1	34.8	34.0
105°	359.3	264.4	178.0	119.2	87.5	70.7	60.7	52.8	47.5	44.9	43.5
107.5°	328.0	244.1	172.8	124.1	96.4	80.2	70.1	62.3	57.4	54.9	53.8
110°	308.3	234.4	171.7	128.1	102.4	86.7	76.3	68.9	64.2	62.1	60.7



TEST NUMBER: P331332-840

CATALOG NUMBER: SA2XXDIP-C675D330U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	294.6	228.1	171.9	132.4	108.2	93.0	82.3	75.1	70.8	68.4	67.0
115°	277.6	221.3	173.4	138.8	117.0	101.7	92.1	84.9	80.7	78.5	76.7
117.5°	266.9	217.8	176.0	145.6	125.2	111.1	101.1	94.2	90.4	88.3	86.8
120°	261.2	215.9	177.7	150.3	131.0	117.0	107.0	99.9	96.7	94.5	93.1
122.5°	256.3	214.7	179.7	154.2	136.3	123.3	113.0	105.9	102.4	100.3	99.2
125°	249.4	212.7	182.7	160.6	144.5	131.7	121.7	114.5	110.3	108.2	107.0
127.5°	243.0	211.5	185.7	166.5	152.1	139.6	129.3	122.5	117.8	114.7	113.3
130°	238.7	210.9	188.0	170.2	156.6	144.1	134.2	127.0	122.0	118.5	117.0
132.5°	235.3	210.6	190.4	173.9	160.7	148.8	138.8	131.3	126.0	122.2	120.5
135°	230.5	210.2	193.1	178.7	166.3	154.8	144.9	136.6	131.3	127.0	125.6
137.5°	227.1	210.1	195.5	182.5	170.9	159.6	150.3	142.2	136.4	132.2	130.5
140°	225.1	209.8	196.6	184.5	173.4	162.7	153.4	145.6	139.9	135.6	134.2
142.5°	223.2	209.8	197.4	186.2	175.4	165.0	156.3	148.8	143.0	139.1	137.8
145°	220.6	209.0	198.3	188.4	178.4	168.7	161.0	153.8	148.5	144.9	143.4
147.5°	217.8	207.8	198.6	189.7	180.9	171.8	164.8	158.9	153.9	150.5	149.5
150°	215.5	206.9	198.3	190.2	182.0	173.8	167.3	162.0	157.3	154.5	153.4
152.5°	213.5	205.5	197.8	190.5	183.1	175.7	170.0	164.8	160.8	157.9	157.4
155°	209.8	203.0	196.9	190.9	184.8	178.7	173.4	169.5	165.5	163.4	163.1
157.5°	206.3	200.5	195.3	190.9	186.0	180.9	176.4	173.3	169.9	168.1	167.7
160°	203.7	198.7	194.5	190.9	186.6	182.4	178.4	175.5	172.7	171.3	170.9
162.5°	201.5	197.3	193.6	190.6	186.9	183.2	180.2	177.5	175.3	173.8	174.1
165°	197.6	194.5	192.0	189.9	187.3	184.1	182.0	180.2	178.0	177.3	177.7
167.5°	194.0	192.0	190.4	189.3	187.2	184.9	183.6	182.3	180.9	180.3	180.7
170°	192.0	190.6	189.5	188.7	186.9	185.2	184.1	183.4	182.4	182.0	182.7
172.5°	190.0	188.8	188.3	187.9	186.7	185.5	184.7	184.3	183.2	183.4	183.8
175°	187.3	186.9	186.6	186.9	186.2	185.5	185.2	185.2	184.5	184.8	185.2
177.5°	185.8	185.5	185.8	186.4	185.8	185.5	185.5	185.5	185.0	185.2	185.8
180°	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5



TEST NUMBER: P331332-840  
 CATALOG NUMBER: SA2XXDIP-C675D330U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1348.4	1350.5	1357.1	1363.6	1371.1	1373.1	1376.4	1373.5	1372.7	1380.6	1386.3
5°	1352.2	1361.5	1379.6	1396.0	1410.0	1419.8	1430.1	1434.2	1441.9	1452.7	1466.1
7.5°	1347.9	1365.9	1394.3	1418.3	1444.5	1463.4	1478.1	1490.7	1505.9	1526.4	1548.8
10°	1342.9	1367.2	1401.7	1431.1	1463.0	1487.2	1507.4	1526.9	1549.6	1578.0	1607.4
12.5°	1333.8	1362.6	1405.8	1440.6	1481.6	1505.4	1532.6	1574.8	1599.1	1638.6	1680.0
15°	1315.7	1347.6	1407.9	1450.7	1497.0	1542.5	1592.5	1632.6	1672.8	1696.1	1754.3
17.5°	1288.5	1335.4	1402.2	1452.1	1511.1	1582.6	1638.7	1684.3	1730.7	1768.4	1797.6
20°	1266.7	1317.7	1393.9	1453.8	1523.9	1600.6	1665.2	1711.5	1751.7	1783.2	1801.2
22.5°	1239.0	1303.2	1377.5	1447.5	1537.1	1613.1	1680.8	1717.3	1750.9	1766.3	1773.2
25°	1195.5	1272.8	1356.9	1442.4	1543.5	1623.9	1685.8	1707.9	1717.7	1702.7	1678.0
27.5°	1148.6	1234.8	1333.0	1432.7	1539.5	1616.9	1661.2	1657.7	1641.1	1592.8	1554.1
30°	1113.5	1208.4	1314.0	1422.8	1530.0	1605.3	1631.1	1605.3	1567.7	1513.6	1458.4
32.5°	1076.8	1175.0	1293.8	1408.8	1512.8	1578.9	1584.5	1540.1	1481.9	1420.4	1351.6
35°	1021.3	1127.4	1255.8	1377.5	1475.9	1517.7	1493.0	1414.6	1345.5	1261.5	1167.6
37.5°	958.5	1075.7	1204.5	1331.6	1420.8	1431.7	1370.3	1287.8	1190.3	1091.6	981.2
40°	911.4	1035.7	1168.2	1296.6	1375.4	1364.0	1285.7	1195.0	1078.9	958.4	855.8
42.5°	869.4	993.6	1128.5	1254.5	1317.7	1286.6	1195.0	1083.6	959.0	845.4	751.4
45°	796.5	924.3	1062.5	1184.2	1220.2	1164.1	1042.9	919.2	796.5	701.7	627.4
47.5°	725.8	852.1	989.0	1095.9	1108.6	1033.1	900.7	773.4	667.9	590.7	538.3
50°	673.8	800.6	936.1	1031.6	1027.4	936.1	800.1	678.9	590.8	528.4	493.3
52.5°	627.2	747.0	877.2	963.9	942.1	842.5	712.7	605.1	532.6	483.8	452.1
55°	554.7	665.5	789.2	858.9	818.6	708.3	598.5	511.9	458.3	421.7	397.0
57.5°	482.7	586.6	692.6	735.5	691.1	589.2	497.6	434.7	394.5	367.4	351.2
60°	438.2	529.0	623.3	660.4	607.2	516.5	444.3	388.2	355.7	333.6	319.1
62.5°	393.6	474.9	563.9	584.1	535.5	458.8	394.9	348.2	321.4	301.7	288.2
65°	333.1	399.5	467.1	480.5	435.7	376.4	325.8	295.4	271.7	257.2	246.4
67.5°	273.2	326.5	374.4	385.2	345.9	304.8	268.3	241.8	225.7	213.7	204.6
70°	237.6	279.9	319.1	327.9	296.4	259.8	232.0	210.9	196.4	186.1	177.3
72.5°	200.2	235.4	267.9	273.9	248.1	220.3	197.3	180.8	167.9	161.4	153.0
75°	153.1	173.7	198.9	200.6	183.5	166.5	149.0	138.1	131.5	123.2	119.1
77.5°	108.1	124.2	138.7	141.5	131.4	119.8	110.0	101.5	95.7	92.0	88.2
80°	82.5	95.3	101.6	105.1	98.0	89.7	84.0	78.4	74.7	72.2	69.6
82.5°	59.0	67.0	72.7	75.4	71.6	66.7	60.9	57.8	54.9	52.8	51.9
85°	29.9	33.5	37.2	38.2	37.2	35.0	31.9	31.9	30.4	29.9	29.9
87.5°	10.6	12.5	12.6	14.0	13.4	13.8	14.3	14.3	13.9	13.5	13.0
90°	1.4	2.8	3.5	4.2	5.4	7.2	9.6	11.8	12.1	11.8	11.4
92.5°	6.3	8.9	10.4	12.8	16.2	24.2	35.6	45.7	46.4	39.2	31.1
95°	13.9	17.5	20.7	26.4	34.9	51.4	82.4	123.8	139.9	122.4	93.5
97.5°	22.2	26.1	30.9	37.5	47.2	67.8	111.1	179.9	238.7	250.4	218.1
100°	28.6	31.7	37.5	44.6	54.6	73.5	117.0	194.1	281.9	333.3	325.8
102.5°	34.8	38.1	43.7	51.2	61.2	78.7	117.3	188.6	283.3	364.1	396.3
105°	44.9	47.5	52.8	60.7	70.7	87.5	119.2	178.0	264.4	359.3	433.5
107.5°	54.9	57.4	62.3	70.1	80.2	96.4	124.1	172.8	244.1	328.0	406.7
110°	62.1	64.2	68.9	76.3	86.7	102.4	128.1	171.7	234.4	308.3	383.5





TEST NUMBER: P331332-840

CATALOG NUMBER: SA2XXDIP-C675D330U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	68.4	70.8	75.1	82.3	93.0	108.2	132.4	171.9	228.1	294.6	362.4
115°	78.5	80.7	84.9	92.1	101.7	117.0	138.8	173.4	221.3	277.6	336.5
117.5°	88.3	90.4	94.2	101.1	111.1	125.2	145.6	176.0	217.8	266.9	316.9
120°	94.5	96.7	99.9	107.0	117.0	131.0	150.3	177.7	215.9	261.2	307.2
122.5°	100.3	102.4	105.9	113.0	123.3	136.3	154.2	179.7	214.7	256.3	299.5
125°	108.2	110.3	114.5	121.7	131.7	144.5	160.6	182.7	212.7	249.4	288.3
127.5°	114.7	117.8	122.5	129.3	139.6	152.1	166.5	185.7	211.5	243.0	277.2
130°	118.5	122.0	127.0	134.2	144.1	156.6	170.2	188.0	210.9	238.7	270.1
132.5°	122.2	126.0	131.3	138.8	148.8	160.7	173.9	190.4	210.6	235.3	263.3
135°	127.0	131.3	136.6	144.9	154.8	166.3	178.7	193.1	210.2	230.5	253.7
137.5°	132.2	136.4	142.2	150.3	159.6	170.9	182.5	195.5	210.1	227.1	246.1
140°	135.6	139.9	145.6	153.4	162.7	173.4	184.5	196.6	209.8	225.1	241.2
142.5°	139.1	143.0	148.8	156.3	165.0	175.4	186.2	197.4	209.8	223.2	237.2
145°	144.9	148.5	153.8	161.0	168.7	178.4	188.4	198.3	209.0	220.6	231.6
147.5°	150.5	153.9	158.9	164.8	171.8	180.9	189.7	198.6	207.8	217.8	227.2
150°	154.5	157.3	162.0	167.3	173.8	182.0	190.2	198.3	206.9	215.5	224.1
152.5°	157.9	160.8	164.8	170.0	175.7	183.1	190.5	197.8	205.5	213.5	221.0
155°	163.4	165.5	169.5	173.4	178.7	184.8	190.9	196.9	203.0	209.8	216.6
157.5°	168.1	169.9	173.3	176.4	180.9	186.0	190.9	195.3	200.5	206.3	211.6
160°	171.3	172.7	175.5	178.4	182.4	186.6	190.9	194.5	198.7	203.7	208.3
162.5°	173.8	175.3	177.5	180.2	183.2	186.9	190.6	193.6	197.3	201.5	205.2
165°	177.3	178.0	180.2	182.0	184.1	187.3	189.9	192.0	194.5	197.6	200.6
167.5°	180.3	180.9	182.3	183.6	184.9	187.2	189.3	190.4	192.0	194.0	196.0
170°	182.0	182.4	183.4	184.1	185.2	186.9	188.7	189.5	190.6	192.0	193.8
172.5°	183.4	183.2	184.3	184.7	185.5	186.7	187.9	188.3	188.8	190.0	191.2
175°	184.8	184.5	185.2	185.2	185.5	186.2	186.9	186.6	186.9	187.3	188.4
177.5°	185.2	185.0	185.5	185.5	185.5	185.8	186.4	185.8	185.5	185.8	186.4
180°	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5



TEST NUMBER: P331332-840

CATALOG NUMBER: SA2XXDIP-C675D330U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1391.3	1397.0	1397.0	1397.9	1404.5	1403.6	1403.2
5°	1480.6	1489.3	1490.4	1499.6	1505.8	1503.8	1498.1
7.5°	1564.8	1581.1	1593.5	1600.3	1608.5	1613.6	1611.3
10°	1631.6	1655.4	1669.8	1679.6	1691.4	1700.2	1697.1
12.5°	1692.2	1720.5	1740.3	1757.1	1758.7	1769.9	1762.2
15°	1786.8	1816.6	1819.8	1832.2	1842.0	1840.9	1841.4
17.5°	1818.1	1827.7	1829.6	1829.9	1830.0	1826.3	1818.6
20°	1806.9	1803.3	1794.5	1787.9	1775.9	1774.4	1764.1
22.5°	1754.1	1742.6	1720.7	1706.2	1687.7	1682.8	1680.0
25°	1650.2	1624.9	1589.8	1556.3	1547.1	1529.0	1534.2
27.5°	1507.6	1468.2	1430.3	1403.0	1378.4	1351.4	1359.1
30°	1407.3	1363.0	1309.4	1268.2	1241.9	1216.1	1211.4
32.5°	1287.8	1222.8	1163.0	1126.7	1086.4	1070.2	1052.3
35°	1081.6	1018.1	958.9	907.9	878.5	855.8	835.2
37.5°	896.1	823.0	775.3	733.9	712.7	699.6	703.0
40°	781.0	717.1	682.1	650.6	631.0	621.7	623.8
42.5°	687.8	640.0	611.1	589.6	575.7	570.6	569.4
45°	582.0	555.2	531.5	519.2	512.4	506.8	503.1
47.5°	509.9	488.0	474.6	467.3	461.4	455.7	455.6
50°	466.6	452.1	442.8	435.0	430.5	426.4	429.9
52.5°	433.5	420.3	411.1	404.1	402.4	398.7	398.6
55°	384.6	374.3	367.6	361.3	358.3	356.2	353.7
57.5°	340.0	330.2	324.1	320.1	314.3	312.1	311.3
60°	308.3	300.5	294.4	289.2	286.6	282.5	282.5
62.5°	279.0	271.2	265.5	261.6	257.3	255.7	256.1
65°	236.6	230.5	224.8	220.7	219.6	216.5	217.5
67.5°	197.6	193.5	187.5	185.3	183.3	181.7	180.5
70°	171.7	167.5	164.4	161.4	159.8	159.8	159.8
72.5°	149.8	144.8	143.0	139.1	140.0	138.4	136.7
75°	116.0	112.9	111.4	109.8	107.2	107.2	107.2
77.5°	85.3	84.4	82.6	80.9	80.3	79.8	80.0
80°	65.9	65.4	64.4	64.4	63.4	62.9	61.9
82.5°	50.7	49.4	48.8	48.4	48.2	48.1	47.9
85°	28.9	27.9	27.9	28.4	27.4	27.4	27.9
87.5°	13.2	13.4	13.1	13.1	13.5	13.1	13.1
90°	10.7	11.4	11.8	11.8	11.8	11.8	11.8
92.5°	26.7	23.7	21.5	21.2	20.1	20.3	19.8
95°	71.7	56.8	48.9	44.2	41.4	40.3	40.7
97.5°	178.4	139.9	114.1	97.0	88.3	83.1	80.1
100°	281.6	232.7	189.5	159.9	144.5	134.2	127.7
102.5°	386.3	350.5	304.8	272.6	246.4	233.5	224.8
105°	473.8	478.5	466.8	444.5	422.4	407.1	402.1
107.5°	467.5	504.5	521.8	524.6	523.4	520.3	513.7
110°	447.5	493.1	522.4	537.8	544.5	547.8	547.3



TEST NUMBER: P331332-840

CATALOG NUMBER: SA2XXDIP-C675D330U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	423.7	472.5	506.1	527.5	538.8	544.8	546.7
115°	391.4	438.2	474.9	500.3	516.6	525.9	529.2
117.5°	365.2	407.6	442.0	467.9	485.2	494.9	497.7
120°	351.4	389.3	421.7	446.8	463.5	473.8	477.5
122.5°	340.0	375.9	405.2	427.6	444.1	453.3	456.3
125°	325.1	356.5	383.2	403.9	417.5	426.4	429.3
127.5°	310.5	340.1	364.8	382.8	395.6	403.2	405.6
130°	300.8	329.0	352.5	370.0	382.1	389.3	392.1
132.5°	291.6	317.6	339.7	356.9	369.0	375.6	378.2
135°	277.2	300.8	320.7	336.1	347.9	354.4	355.8
137.5°	265.8	284.5	301.8	315.9	326.0	331.6	333.8
140°	258.3	274.8	290.4	301.8	311.1	316.5	318.6
142.5°	251.8	265.9	279.0	289.8	298.3	303.1	303.5
145°	243.4	254.4	264.8	273.3	279.4	283.0	284.0
147.5°	236.5	245.1	252.7	259.7	264.6	267.0	267.7
150°	232.0	239.4	245.8	251.2	255.5	257.6	258.0
152.5°	228.2	234.6	240.1	244.4	248.0	249.6	249.7
155°	222.3	227.6	231.6	235.5	238.0	239.4	238.7
157.5°	216.3	220.8	223.9	226.6	228.7	229.3	229.3
160°	212.3	216.2	218.7	221.3	223.0	223.4	223.4
162.5°	208.6	212.0	213.9	216.4	217.6	217.9	217.6
165°	203.0	205.5	206.9	208.3	209.8	209.8	209.4
167.5°	197.9	199.7	201.0	201.6	202.4	202.3	201.9
170°	194.8	196.2	196.9	197.3	198.3	198.0	197.3
172.5°	192.0	193.1	193.5	193.9	194.4	194.0	193.6
175°	188.7	189.1	189.5	189.5	189.9	189.5	188.7
177.5°	186.4	186.7	186.7	186.7	186.7	186.4	185.8
180°	185.5	185.5	185.5	185.5	185.5	185.5	185.5

(END OF REPORT)