

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331710-930

Luminaire Tested: **SA2XXRDIP-C865D330U930-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331710-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C865D330U930-4F0-1E-UDD-F4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 330 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3502.5 lumens
Efficiency: N/A
Efficacy: 80.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 43.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331710-930
CATALOG NUMBER: SA2XXRDIP-C865D330U930-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331710-930

CATALOG NUMBER: SA2XXRDIP-C865D330U930-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	95	95	95	84	84	84	75	75	75	70
1	103	99	95	92	97	94	90	87	84	82	79	75	73	72	67	66	64	60
2	94	87	81	76	89	83	77	73	74	70	67	67	64	61	60	57	55	52
3	87	77	70	64	82	73	67	62	66	61	57	60	56	52	54	51	48	45
4	80	69	61	55	75	66	59	53	59	54	49	54	49	45	48	45	42	39
5	73	62	54	48	69	59	52	46	54	48	43	49	44	40	44	40	37	34
6	68	56	48	42	64	53	46	41	49	43	38	44	39	35	40	36	33	30
7	63	51	43	37	60	49	41	36	44	38	34	41	35	32	37	33	30	27
8	59	46	39	33	56	44	37	32	41	35	30	37	32	29	34	30	27	25
9	55	43	35	30	52	41	34	29	38	32	28	35	30	26	32	27	24	22
10	52	39	32	27	49	38	31	27	35	29	25	32	27	24	29	25	22	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	19302	19302	19302
5°	19376	19060	19164
10°	19226	18748	18589
15°	19005	18191	17668
20°	18699	17399	16526
25°	18387	16498	15419
30°	17952	15571	13998
35°	17527	14564	12751
40°	17102	13523	11310
45°	16600	12353	10003
50°	16088	11170	8721
55°	15564	9897	7491
60°	14951	8561	6219
65°	14258	7194	5662
70°	13430	5925	5207
75°	12420	5402	4860
80°	10962	4826	4426
85°	8633	3798	3798



TEST NUMBER: P331710-930

CATALOG NUMBER: SA2XXRDIP-C865D330U930-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	111.9	3.2
10°-20°	307.2	8.8
20°-30°	431.5	12.3
30°-40°	470.5	13.4
40°-50°	432.6	12.4
50°-60°	339.7	9.7
60°-70°	221.5	6.3
70°-80°	114.2	3.3
80°-90°	31.0	0.9
90°-100°	59.9	1.7
100°-110°	203.2	5.8
110°-120°	215.9	6.2
120°-130°	177.7	5.1
130°-140°	142.7	4.1
140°-150°	107.9	3.1
150°-160°	75.8	2.2
160°-170°	44.6	1.3
170°-180°	14.5	0.4
0°-30°	850.6	24.3
0°-40°	1321.1	37.7
0°-60°	2093.4	59.8
0°-90°	2460.1	70.2
90°-120°	479.1	13.7
90°-150°	907.4	25.9
90°-180°	1042.0	29.8
0°-180°	3502.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1196	1196	1196	1196	1196	
5°	1196	1190	1176	1185	1182	113
15°	1137	1124	1088	1068	1057	320
25°	1032	995	926	883	866	474
35°	889	832	739	673	647	556
45°	727	652	541	467	438	561
55°	553	467	352	289	266	494
65°	373	285	188	153	148	370
75°	199	126	87	79	78	211
85°	47	25	20	20	20	55
90°	0	4	10	9	10	2
95°	10	25	113	43	33	11
105°	35	53	213	382	325	37
115°	62	78	179	369	427	61
125°	86	102	172	299	347	77
135°	101	121	170	251	287	78
145°	116	133	169	210	229	73
155°	132	142	164	185	193	61
165°	144	148	157	166	169	40
175°	150	150	151	153	152	14
180°	150	150	150	150	150	



TEST NUMBER: P331710-930

CATALOG NUMBER: SA2XXRDIP-C865D330U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1195.5	1195.5	1195.5	1195.5	1195.5	1195.5	1195.5	1195.5	1195.5	1195.5	1195.5
2.5°	1199.8	1198.8	1197.8	1196.9	1196.0	1194.4	1192.3	1190.2	1188.1	1185.9	1187.9
5°	1195.5	1194.3	1193.0	1191.8	1190.7	1188.5	1185.4	1182.3	1179.1	1176.0	1178.1
7.5°	1183.1	1181.6	1180.1	1178.7	1177.1	1174.6	1170.9	1167.3	1163.6	1159.9	1160.6
10°	1172.7	1171.0	1169.4	1167.7	1166.0	1162.8	1158.0	1153.2	1148.3	1143.5	1142.8
12.5°	1159.8	1157.6	1155.6	1153.6	1151.4	1147.4	1141.2	1135.1	1128.9	1122.7	1121.4
15°	1137.0	1134.4	1131.7	1129.1	1126.4	1121.0	1112.9	1104.7	1096.5	1088.3	1083.8
17.5°	1109.1	1105.1	1101.1	1097.0	1093.0	1085.7	1075.2	1064.7	1054.3	1043.7	1038.4
20°	1088.3	1083.5	1078.7	1073.9	1069.1	1060.7	1048.6	1036.7	1024.7	1012.6	1006.6
22.5°	1065.8	1060.5	1055.1	1049.7	1044.3	1034.9	1021.2	1007.7	994.2	980.6	972.8
25°	1032.1	1024.4	1016.7	1009.0	1001.4	989.5	973.6	957.8	941.9	926.1	916.2
27.5°	991.4	983.0	974.7	966.3	958.0	944.9	926.9	909.1	891.1	873.3	861.8
30°	962.9	953.7	944.6	935.5	926.3	912.2	892.9	873.7	854.4	835.2	823.0
32.5°	935.1	924.5	913.8	903.1	892.4	877.3	857.7	838.0	818.5	798.8	784.9
35°	889.2	877.0	864.8	852.5	840.2	823.5	802.3	781.2	760.1	738.9	723.7
37.5°	843.4	830.0	816.5	803.0	789.5	771.5	749.0	726.4	703.9	681.3	664.6
40°	811.4	797.0	782.5	768.1	753.7	734.8	711.5	688.2	664.9	641.6	624.4
42.5°	778.5	763.3	748.1	733.0	717.7	698.1	674.0	649.9	625.8	601.7	584.1
45°	727.0	710.9	694.8	678.7	662.6	641.9	616.7	591.4	566.1	541.0	523.8
47.5°	676.8	659.7	642.7	625.6	608.5	586.9	560.9	534.8	508.7	482.7	465.8
50°	640.5	623.4	606.3	589.2	572.2	550.4	524.0	497.5	471.1	444.7	428.0
52.5°	605.0	587.1	569.3	551.5	533.6	511.8	485.9	460.0	434.1	408.3	392.2
55°	552.9	534.1	515.4	496.6	477.8	455.4	429.5	403.5	377.6	351.6	337.2
57.5°	499.4	480.1	460.9	441.6	422.5	400.4	375.4	350.4	325.5	300.5	287.3
60°	463.0	443.8	424.6	405.4	386.1	364.1	339.3	314.5	289.8	265.1	252.8
62.5°	427.5	408.3	389.1	369.8	350.6	329.2	305.6	282.0	258.4	234.7	223.1
65°	373.2	353.8	334.3	314.8	295.4	274.8	253.2	231.5	209.9	188.3	180.1
67.5°	320.9	301.6	282.3	262.9	243.5	224.1	204.7	185.2	165.8	146.3	142.5
70°	284.5	265.8	247.0	228.3	209.5	191.8	175.3	158.7	142.1	125.5	123.1
72.5°	249.9	232.0	213.9	196.0	178.0	162.3	149.0	135.7	122.4	109.1	107.0
75°	199.1	182.2	165.4	148.5	131.8	119.3	111.0	102.9	94.7	86.6	84.9
77.5°	149.1	134.3	119.5	104.8	90.0	80.7	76.7	72.8	68.9	64.9	63.9
80°	117.9	105.7	93.4	81.1	68.9	61.6	59.1	56.7	54.3	51.9	51.0
82.5°	89.4	79.8	70.2	60.7	51.1	45.5	43.9	42.2	40.6	39.0	38.4
85°	46.6	41.5	36.4	31.4	26.3	23.5	22.7	22.0	21.3	20.5	20.5
87.5°	13.9	12.6	11.3	9.8	8.4	7.8	8.1	8.5	8.8	8.9	8.6
90°	0.3	1.1	2.3	2.9	3.4	4.3	5.8	7.7	9.5	9.8	9.5
92.5°	3.5	5.1	7.2	8.4	10.4	13.0	19.6	28.8	36.9	37.4	31.6
95°	10.1	11.3	14.1	16.7	21.3	28.2	41.5	66.5	100.0	112.9	98.8
97.5°	16.4	17.9	21.0	24.9	30.2	38.1	54.7	89.7	145.2	192.7	202.2
100°	22.2	23.1	25.6	30.2	36.0	44.1	59.4	94.5	156.7	227.6	269.0
102.5°	27.5	28.1	30.7	35.3	41.3	49.4	63.5	94.7	152.3	228.7	293.9
105°	35.1	36.3	38.3	42.6	49.0	57.1	70.6	96.2	143.7	213.4	290.1
107.5°	43.5	44.4	46.3	50.3	56.6	64.7	77.9	100.2	139.5	197.1	264.8
110°	49.0	50.1	51.9	55.6	61.6	70.0	82.7	103.4	138.6	189.2	248.9



TEST NUMBER: P331710-930

CATALOG NUMBER: SA2XXRDIP-C865D330U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	54.1	55.2	57.2	60.7	66.4	75.1	87.3	106.9	138.8	184.2	237.8
115°	62.0	63.3	65.1	68.6	74.4	82.1	94.5	112.0	140.0	178.6	224.1
117.5°	70.1	71.3	73.0	76.1	81.6	89.7	101.1	117.6	142.1	175.9	215.5
120°	75.2	76.3	78.1	80.6	86.4	94.5	105.7	121.3	143.5	174.3	210.8
122.5°	80.1	81.0	82.7	85.5	91.2	99.5	110.1	124.5	145.0	173.3	206.9
125°	86.4	87.3	89.0	92.5	98.2	106.3	116.7	129.6	147.5	171.7	201.4
127.5°	91.5	92.6	95.1	98.9	104.4	112.7	122.8	134.4	149.9	170.7	196.2
130°	94.5	95.6	98.5	102.6	108.4	116.3	126.5	137.4	151.8	170.2	192.7
132.5°	97.3	98.7	101.7	106.0	112.0	120.1	129.7	140.4	153.7	170.0	190.0
135°	101.4	102.6	106.0	110.3	117.0	125.0	134.3	144.3	155.9	169.7	186.1
137.5°	105.3	106.7	110.1	114.8	121.3	128.8	137.9	147.3	157.8	169.6	183.4
140°	108.4	109.5	112.9	117.6	123.8	131.3	140.0	149.0	158.7	169.4	181.7
142.5°	111.3	112.3	115.4	120.1	126.2	133.2	141.6	150.3	159.4	169.4	180.2
145°	115.8	117.0	119.8	124.2	130.0	136.2	144.1	152.1	160.1	168.8	178.1
147.5°	120.7	121.5	124.3	128.2	133.1	138.7	146.0	153.1	160.4	167.8	175.9
150°	123.8	124.7	127.0	130.8	135.1	140.3	146.9	153.5	160.1	167.1	174.0
152.5°	127.1	127.5	129.8	133.1	137.2	141.9	147.8	153.8	159.7	165.9	172.4
155°	131.7	131.9	133.6	136.8	140.0	144.3	149.2	154.1	159.0	163.9	169.4
157.5°	135.4	135.7	137.1	139.9	142.4	146.0	150.2	154.1	157.7	161.8	166.6
160°	137.9	138.3	139.4	141.7	144.1	147.2	150.7	154.1	157.0	160.5	164.4
162.5°	140.6	140.3	141.5	143.3	145.4	147.9	150.9	153.8	156.3	159.3	162.7
165°	143.5	143.2	143.7	145.4	146.9	148.6	151.2	153.3	155.0	157.0	159.6
167.5°	145.9	145.5	146.0	147.2	148.2	149.3	151.2	152.9	153.7	155.0	156.6
170°	147.5	146.9	147.2	148.1	148.6	149.5	150.9	152.4	153.0	153.8	155.0
172.5°	148.4	148.1	147.9	148.8	149.1	149.8	150.7	151.7	152.1	152.5	153.4
175°	149.5	149.2	149.0	149.5	149.5	149.8	150.3	150.9	150.7	150.9	151.2
177.5°	150.0	149.5	149.4	149.8	149.8	149.8	150.0	150.5	150.0	149.8	150.0
180°	149.8	149.8	149.8	149.8	149.8	149.8	149.8	149.8	149.8	149.8	149.8



TEST NUMBER: P331710-930

CATALOG NUMBER: SA2XXRDIP-C865D330U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1195.5	1195.5	1195.5	1195.5	1195.5	1195.5	1195.5	1195.5
2.5°	1189.8	1191.7	1193.6	1194.4	1194.0	1193.6	1193.3	1192.9
5°	1180.3	1182.4	1184.6	1185.4	1184.6	1183.9	1183.2	1182.4
7.5°	1161.2	1161.8	1162.5	1162.1	1160.9	1159.7	1158.4	1157.2
10°	1142.1	1141.3	1140.6	1139.5	1138.1	1136.7	1135.2	1133.8
12.5°	1120.1	1118.8	1117.5	1115.7	1113.3	1110.9	1108.5	1106.1
15°	1079.2	1074.6	1070.1	1066.6	1064.2	1061.8	1059.4	1057.0
17.5°	1032.9	1027.4	1022.1	1017.2	1013.1	1009.0	1004.9	1000.7
20°	1000.6	994.6	988.6	982.9	977.6	972.3	967.0	961.8
22.5°	965.2	957.4	949.7	943.8	939.9	935.9	932.0	928.1
25°	906.4	896.5	886.6	879.9	876.3	872.7	869.1	865.5
27.5°	850.3	838.8	827.3	818.7	813.0	807.2	801.5	795.8
30°	810.7	798.4	786.1	776.7	770.3	763.8	757.3	750.8
32.5°	770.9	756.8	742.9	732.8	726.8	720.6	714.5	708.4
35°	708.6	693.5	678.3	668.1	662.8	657.5	652.2	646.9
37.5°	648.0	631.3	614.7	603.2	597.2	591.1	585.1	579.0
40°	607.4	590.4	573.2	561.6	555.4	549.1	542.8	536.6
42.5°	566.5	548.8	531.2	519.3	513.2	507.2	501.1	495.0
45°	506.8	489.8	472.6	461.2	455.4	449.7	443.9	438.1
47.5°	448.7	431.8	414.8	403.7	398.5	393.2	388.0	382.8
50°	411.5	394.8	378.3	367.5	362.4	357.3	352.3	347.2
52.5°	376.3	360.3	344.2	333.9	329.2	324.6	319.9	315.3
55°	322.8	308.3	293.9	284.4	279.8	275.2	270.7	266.1
57.5°	274.1	260.9	247.7	239.1	235.3	231.4	227.6	223.7
60°	240.5	228.3	216.0	208.0	204.1	200.2	196.4	192.6
62.5°	211.4	199.7	188.0	181.0	178.7	176.4	174.1	171.8
65°	171.9	163.7	155.6	151.1	150.3	149.7	149.0	148.2
67.5°	138.8	135.0	131.3	129.0	128.2	127.4	126.7	126.0
70°	120.7	118.3	115.9	114.2	113.2	112.3	111.3	110.3
72.5°	105.0	103.0	100.9	99.7	99.1	98.5	97.9	97.3
75°	83.2	81.5	79.8	78.8	78.6	78.4	78.1	77.9
77.5°	63.0	62.0	61.1	60.4	60.0	59.6	59.3	58.9
80°	50.0	49.1	48.1	47.6	47.6	47.6	47.6	47.6
82.5°	37.8	37.2	36.6	36.4	36.4	36.4	36.4	36.4
85°	20.5	20.5	20.5	20.5	20.5	20.5	20.5	20.5
87.5°	8.4	8.1	8.0	8.0	8.0	8.0	8.0	8.0
90°	9.2	8.6	9.2	9.5	9.5	9.5	9.5	9.5
92.5°	25.1	21.5	19.2	17.4	17.1	16.2	16.4	16.0
95°	75.5	57.9	45.8	39.5	35.7	33.4	32.5	32.9
97.5°	176.1	144.1	112.9	92.1	78.4	71.3	67.1	64.7
100°	263.0	227.3	187.8	153.0	129.1	116.7	108.4	103.1
102.5°	319.9	311.9	283.0	246.1	220.0	198.9	188.5	181.5
105°	350.0	382.5	386.3	376.8	358.9	341.0	328.6	324.7
107.5°	328.3	377.4	407.3	421.3	423.5	422.6	420.0	414.7
110°	309.7	361.3	398.1	421.8	434.1	439.6	442.2	441.9



TEST NUMBER: P331710-930

CATALOG NUMBER: SA2XXRDIP-C865D330U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	292.6	342.1	381.5	408.6	425.8	435.0	439.9	441.4
115°	271.7	316.0	353.8	383.4	403.9	417.1	424.6	427.2
117.5°	255.8	294.8	329.1	356.9	377.7	391.8	399.6	401.8
120°	248.0	283.7	314.3	340.5	360.7	374.2	382.5	385.5
122.5°	241.8	274.5	303.5	327.1	345.2	358.6	366.0	368.4
125°	232.8	262.4	287.8	309.4	326.1	337.0	344.2	346.6
127.5°	223.8	250.7	274.6	294.5	309.1	319.4	325.5	327.4
130°	218.1	242.9	265.6	284.6	298.7	308.5	314.3	316.6
132.5°	212.5	235.5	256.4	274.3	288.1	297.9	303.2	305.3
135°	204.8	223.8	242.9	258.9	271.3	280.9	286.1	287.2
137.5°	198.7	214.6	229.7	243.7	255.0	263.2	267.7	269.5
140°	194.7	208.6	221.8	234.5	243.7	251.2	255.5	257.2
142.5°	191.5	203.3	214.7	225.3	234.0	240.8	244.7	245.0
145°	186.9	196.5	205.4	213.8	220.6	225.6	228.4	229.3
147.5°	183.4	190.9	197.9	204.0	209.7	213.6	215.6	216.1
150°	180.9	187.3	193.3	198.4	202.8	206.3	208.0	208.3
152.5°	178.4	184.3	189.4	193.9	197.3	200.2	201.5	201.6
155°	174.9	179.4	183.8	186.9	190.1	192.2	193.3	192.7
157.5°	170.8	174.6	178.2	180.8	183.0	184.7	185.2	185.2
160°	168.2	171.4	174.6	176.6	178.6	180.0	180.3	180.3
162.5°	165.7	168.4	171.1	172.7	174.7	175.7	175.9	175.7
165°	161.9	163.9	165.9	167.1	168.2	169.4	169.4	169.1
167.5°	158.2	159.8	161.2	162.2	162.7	163.4	163.3	163.0
170°	156.5	157.3	158.4	159.0	159.3	160.1	159.9	159.3
172.5°	154.3	155.0	155.9	156.2	156.5	156.9	156.6	156.3
175°	152.1	152.4	152.7	153.0	153.0	153.3	153.0	152.4
177.5°	150.5	150.5	150.7	150.7	150.7	150.7	150.5	150.0
180°	149.8	149.8	149.8	149.8	149.8	149.8	149.8	149.8

(END OF REPORT)