

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331339-840

Luminaire Tested: **SA2XXDIP-C675D530U840-4F0-1E-UDD-A**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331339-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXDIP-C675D530U840-4F0-1E-UDD-A  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 530 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5095.6 lumens  
Efficiency: N/A  
Efficacy: 126.4 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 40.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331339-840  
CATALOG NUMBER: SA2XXDIP-C675D530U840-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P331339-840

CATALOG NUMBER: SA2XXDIP-C675D530U840-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	64	64	64	58
1	100	96	92	89	93	90	86	84	78	76	73	67	65	64	57	56	55	50
2	92	84	79	74	85	79	74	69	69	65	62	60	57	54	51	49	47	43
3	84	75	68	62	78	70	64	59	61	56	53	53	50	46	46	43	41	37
4	77	67	59	53	72	63	56	50	55	50	45	48	44	40	41	38	36	32
5	71	60	52	46	66	56	49	44	49	44	39	43	39	35	37	34	31	28
6	66	54	46	40	61	51	44	38	45	39	35	39	35	31	34	31	28	25
7	61	49	41	35	57	46	39	34	41	35	31	36	31	28	31	28	25	23
8	57	45	37	32	53	42	35	30	37	32	28	33	28	25	29	25	23	20
9	53	41	33	28	49	39	32	27	34	29	25	31	26	23	27	23	21	19
10	50	38	30	26	46	36	29	25	32	26	23	28	24	21	25	21	19	17

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	21658	21658	21658	21658
5°	24280	21797	19316	21797
10°	27824	21620	16718	21620
15°	30780	21224	14770	21224
20°	30311	20797	13464	20797
25°	27332	20232	12636	20232
30°	22585	19328	12033	19328
35°	16462	18382	11606	18382
40°	13148	17266	11367	17266
45°	11488	15972	11040	15972
50°	10798	14722	10826	14722
55°	9956	13453	10536	13453
60°	9122	12103	10091	12103
65°	8309	10892	9650	10892
70°	7544	9711	9007	9711
75°	6687	8390	7973	8390
80°	5755	6946	6425	6946
85°	5169	5169	3816	5169



TEST NUMBER: P331339-840

CATALOG NUMBER: SA2XXDIP-C675D530U840-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	127.7	2.5
10°-20°	371.4	7.3
20°-30°	539.0	10.6
30°-40°	568.8	11.2
40°-50°	503.6	9.9
50°-60°	401.9	7.9
60°-70°	273.2	5.4
70°-80°	140.0	2.7
80°-90°	35.6	0.7
90°-100°	24.3	0.5
100°-110°	89.1	1.7
110°-120°	238.2	4.7
120°-130°	393.1	7.7
130°-140°	418.1	8.2
140°-150°	388.6	7.6
150°-160°	312.4	6.1
160°-170°	201.3	4.0
170°-180°	69.3	1.4
0°-30°	1038.1	20.4
0°-40°	1606.9	31.5
0°-60°	2512.4	49.3
0°-90°	2961.2	58.1
90°-120°	351.5	6.9
90°-150°	1551.4	30.4
90°-180°	2134.0	41.9
0°-180°	5095.6	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1341	1341	1341	1341	1341	
5°	1498	1345	1192	1345	1498	150
15°	1841	1270	884	1270	1841	508
25°	1534	1136	709	1136	1534	693
35°	835	933	589	933	835	543
45°	503	700	484	700	503	396
55°	354	478	374	478	354	317
65°	218	285	253	285	218	216
75°	107	134	128	134	107	115
85°	28	28	21	28	28	31
90°	14	0	14	0	14	8
95°	23	34	23	34	23	21
105°	40	160	40	160	40	42
115°	43	303	43	303	43	108
125°	451	428	451	428	451	390
135°	548	530	548	530	548	422
145°	624	615	624	615	624	391
155°	678	677	678	677	678	313
165°	712	714	712	714	712	201
175°	726	730	726	730	726	69
180°	728	728	728	728	728	



TEST NUMBER: P331339-840

CATALOG NUMBER: SA2XXDIP-C675D530U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1403.2	1403.6	1404.5	1397.9	1397.0	1397.0	1391.3	1386.3	1380.6	1372.7	1373.5
5°	1498.1	1503.8	1505.8	1499.6	1490.4	1489.3	1480.6	1466.1	1452.7	1441.9	1434.2
7.5°	1611.3	1613.6	1608.5	1600.3	1593.5	1581.1	1564.8	1548.8	1526.4	1505.9	1490.7
10°	1697.1	1700.2	1691.4	1679.6	1669.8	1655.4	1631.6	1607.4	1578.0	1549.6	1526.9
12.5°	1762.2	1769.9	1758.7	1757.1	1740.3	1720.5	1692.2	1680.0	1638.6	1599.1	1574.8
15°	1841.4	1840.9	1842.0	1832.2	1819.8	1816.6	1786.8	1754.3	1696.1	1672.8	1632.6
17.5°	1818.6	1826.3	1830.0	1829.9	1829.6	1827.7	1818.1	1797.6	1768.4	1730.7	1684.3
20°	1764.1	1774.4	1775.9	1787.9	1794.5	1803.3	1806.9	1801.2	1783.2	1751.7	1711.5
22.5°	1680.0	1682.8	1687.7	1706.2	1720.7	1742.6	1754.1	1773.2	1766.3	1750.9	1717.3
25°	1534.2	1529.0	1547.1	1556.3	1589.8	1624.9	1650.2	1678.0	1702.7	1717.7	1707.9
27.5°	1359.1	1351.4	1378.4	1403.0	1430.3	1468.2	1507.6	1554.1	1592.8	1641.1	1657.7
30°	1211.4	1216.1	1241.9	1268.2	1309.4	1363.0	1407.3	1458.4	1513.6	1567.7	1605.3
32.5°	1052.3	1070.2	1086.4	1126.7	1163.0	1222.8	1287.8	1351.6	1420.4	1481.9	1540.1
35°	835.2	855.8	878.5	907.9	958.9	1018.1	1081.6	1167.6	1261.5	1345.5	1414.6
37.5°	703.0	699.6	712.7	733.9	775.3	823.0	896.1	981.2	1091.6	1190.3	1287.8
40°	623.8	621.7	631.0	650.6	682.1	717.1	781.0	855.8	958.4	1078.9	1195.0
42.5°	569.4	570.6	575.7	589.6	611.1	640.0	687.8	751.4	845.4	959.0	1083.6
45°	503.1	506.8	512.4	519.2	531.5	555.2	582.0	627.4	701.7	796.5	919.2
47.5°	455.6	455.7	461.4	467.3	474.6	488.0	509.9	538.3	590.7	667.9	773.4
50°	429.9	426.4	430.5	435.0	442.8	452.1	466.6	493.3	528.4	590.8	678.9
52.5°	398.6	398.7	402.4	404.1	411.1	420.3	433.5	452.1	483.8	532.6	605.1
55°	353.7	356.2	358.3	361.3	367.6	374.3	384.6	397.0	421.7	458.3	511.9
57.5°	311.3	312.1	314.3	320.1	324.1	330.2	340.0	351.2	367.4	394.5	434.7
60°	282.5	282.5	286.6	289.2	294.4	300.5	308.3	319.1	333.6	355.7	388.2
62.5°	256.1	255.7	257.3	261.6	265.5	271.2	279.0	288.2	301.7	321.4	348.2
65°	217.5	216.5	219.6	220.7	224.8	230.5	236.6	246.4	257.2	271.7	295.4
67.5°	180.5	181.7	183.3	185.3	187.5	193.5	197.6	204.6	213.7	225.7	241.8
70°	159.8	159.8	159.8	161.4	164.4	167.5	171.7	177.3	186.1	196.4	210.9
72.5°	136.7	138.4	140.0	139.1	143.0	144.8	149.8	153.0	161.4	167.9	180.8
75°	107.2	107.2	107.2	109.8	111.4	112.9	116.0	119.1	123.2	131.5	138.1
77.5°	80.0	79.8	80.3	80.9	82.6	84.4	85.3	88.2	92.0	95.7	101.5
80°	61.9	62.9	63.4	64.4	64.4	65.4	65.9	69.6	72.2	74.7	78.4
82.5°	47.9	48.1	48.2	48.4	48.8	49.4	50.7	51.9	52.8	54.9	57.8
85°	27.9	27.4	27.4	28.4	27.9	27.9	28.9	29.9	29.9	30.4	31.9
87.5°	13.5	13.5	13.9	13.4	13.4	13.7	13.6	13.0	13.3	13.6	13.8
90°	14.2	14.0	13.7	13.5	13.3	12.9	12.3	11.7	11.1	10.5	9.6
92.5°	14.2	14.1	13.9	13.8	13.6	13.4	13.1	12.8	12.5	12.2	11.7
95°	22.6	22.8	22.9	23.0	23.1	22.9	22.3	21.7	21.1	20.6	19.7
97.5°	30.3	30.1	30.0	29.8	29.7	29.4	28.9	28.5	28.0	27.5	25.7
100°	35.3	35.0	34.8	34.6	34.3	33.8	32.8	31.9	31.0	30.0	28.1
102.5°	37.9	37.5	37.2	36.9	36.6	35.7	34.5	33.3	32.1	30.9	47.6
105°	40.1	39.6	39.1	38.7	38.2	37.3	36.1	34.7	33.4	32.1	64.1
107.5°	41.2	40.7	40.3	39.8	39.4	39.8	41.1	42.4	43.7	45.0	83.3
110°	41.6	41.2	40.7	40.2	39.8	45.3	57.1	68.8	80.5	92.2	126.0



TEST NUMBER: P331339-840

CATALOG NUMBER: SA2XXDIP-C675D530U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	42.0	41.7	41.3	40.9	40.6	61.7	104.4	147.1	189.9	232.7	241.0
115°	43.2	51.6	60.1	68.5	77.0	108.3	162.5	216.7	270.9	325.2	322.2
117.5°	176.4	204.2	231.9	259.5	287.3	307.7	320.8	334.0	347.1	360.1	358.2
120°	321.4	337.3	353.1	368.9	384.8	391.9	390.5	389.1	387.7	386.3	384.2
122.5°	401.1	404.2	407.3	410.4	413.4	414.5	413.7	412.8	412.0	411.2	408.9
125°	450.6	450.3	449.9	449.6	449.2	448.6	447.8	447.0	446.2	445.4	443.1
127.5°	481.8	481.7	481.7	481.6	481.5	480.9	479.7	478.5	477.3	476.2	474.4
130°	501.2	501.3	501.4	501.5	501.7	501.1	499.8	498.5	497.3	495.9	494.6
132.5°	520.2	520.3	520.4	520.5	520.6	520.2	519.1	518.0	516.8	515.7	514.4
135°	547.5	547.9	548.1	548.3	548.6	548.1	546.8	545.7	544.5	543.3	542.3
137.5°	572.6	573.0	573.3	573.7	574.1	573.8	572.6	571.5	570.4	569.2	567.9
140°	588.1	588.8	589.4	589.9	590.5	590.3	589.2	588.1	587.1	586.0	584.7
142.5°	603.3	603.9	604.5	605.1	605.7	605.5	604.5	603.6	602.6	601.7	600.2
145°	624.5	625.1	625.7	626.3	626.8	626.7	625.9	625.1	624.3	623.5	621.5
147.5°	643.2	643.7	644.2	644.7	645.1	645.1	644.5	643.9	643.3	642.7	640.7
150°	654.6	655.1	655.7	656.3	656.9	656.8	656.1	655.4	654.7	654.0	652.2
152.5°	664.3	665.0	665.8	666.6	667.3	667.4	666.7	666.0	665.3	664.6	662.8
155°	677.7	678.7	679.6	680.5	681.5	681.7	681.0	680.2	679.5	678.8	677.4
157.5°	690.0	690.9	691.9	692.8	693.8	693.8	693.0	692.2	691.4	690.6	689.6
160°	697.2	698.0	698.9	699.7	700.5	700.5	699.8	699.1	698.5	697.8	697.1
162.5°	703.2	704.2	705.2	706.2	707.2	707.3	706.5	705.7	704.9	704.1	703.5
165°	712.0	712.9	713.7	714.5	715.3	715.3	714.5	713.7	712.9	712.0	711.7
167.5°	717.6	718.6	719.7	720.7	721.9	722.0	721.1	720.2	719.4	718.6	718.3
170°	720.9	722.1	723.1	724.1	725.2	725.3	724.5	723.7	722.9	722.1	721.8
172.5°	723.5	724.6	725.6	726.7	727.7	727.8	727.0	726.2	725.4	724.6	724.3
175°	725.7	726.9	728.0	729.2	730.4	730.5	729.7	728.9	728.1	727.3	727.0
177.5°	727.1	727.9	728.7	729.6	730.4	730.5	729.9	729.2	728.6	727.9	727.8
180°	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3



TEST NUMBER: P331339-840

CATALOG NUMBER: SA2XXDIP-C675D530U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1376.4	1373.1	1371.1	1363.6	1357.1	1350.5	1348.4	1349.2	1340.2	1331.5	1327.8
5°	1430.1	1419.8	1410.0	1396.0	1379.6	1361.5	1352.2	1344.9	1327.0	1307.4	1296.1
7.5°	1478.1	1463.4	1444.5	1418.3	1394.3	1365.9	1347.9	1331.9	1305.5	1277.9	1260.9
10°	1507.4	1487.2	1463.0	1431.1	1401.7	1367.2	1342.9	1318.7	1287.8	1254.8	1234.2
12.5°	1532.6	1505.4	1481.6	1440.6	1405.8	1362.6	1333.8	1299.7	1267.2	1228.0	1207.8
15°	1592.5	1542.5	1497.0	1450.7	1407.9	1347.6	1315.7	1269.7	1226.9	1178.5	1155.3
17.5°	1638.7	1582.6	1511.1	1452.1	1402.2	1335.4	1288.5	1233.6	1183.0	1127.5	1096.0
20°	1665.2	1600.6	1523.9	1453.8	1393.9	1317.7	1266.7	1210.4	1151.1	1088.7	1054.7
22.5°	1680.8	1613.1	1537.1	1447.5	1377.5	1303.2	1239.0	1177.4	1117.3	1050.1	1014.3
25°	1685.8	1623.9	1543.5	1442.4	1356.9	1272.8	1195.5	1135.7	1063.0	1000.1	948.1
27.5°	1661.2	1616.9	1539.5	1432.7	1333.0	1234.8	1148.6	1080.9	1004.1	935.8	883.5
30°	1631.1	1605.3	1530.0	1422.8	1314.0	1208.4	1113.5	1036.7	960.4	891.3	837.7
32.5°	1584.5	1578.9	1512.8	1408.8	1293.8	1175.0	1076.8	999.2	914.6	846.8	795.7
35°	1493.0	1517.7	1475.9	1377.5	1255.8	1127.4	1021.3	932.6	845.0	780.0	732.1
37.5°	1370.3	1431.7	1420.8	1331.6	1204.5	1075.7	958.5	865.8	782.2	716.7	669.6
40°	1285.7	1364.0	1375.4	1296.6	1168.2	1035.7	911.4	819.2	737.7	677.9	630.5
42.5°	1195.0	1286.6	1317.7	1254.5	1128.5	993.6	869.4	773.8	693.2	635.0	593.0
45°	1042.9	1164.1	1220.2	1184.2	1062.5	924.3	796.5	699.5	626.3	571.7	539.3
47.5°	900.7	1033.1	1108.6	1095.9	989.0	852.1	725.8	632.8	561.5	517.9	488.8
50°	800.1	936.1	1027.4	1031.6	936.1	800.6	673.8	586.1	520.7	480.0	456.3
52.5°	712.7	842.5	942.1	963.9	877.2	747.0	627.2	540.0	482.3	444.8	423.6
55°	598.5	708.3	818.6	858.9	789.2	665.5	554.7	477.9	423.7	398.0	379.4
57.5°	497.6	589.2	691.1	735.5	692.6	586.6	482.7	416.1	372.1	349.5	335.3
60°	444.3	516.5	607.2	660.4	623.3	529.0	438.2	374.8	338.7	318.6	305.2
62.5°	394.9	458.8	535.5	584.1	563.9	474.9	393.6	337.7	306.5	287.6	278.0
65°	325.8	376.4	435.7	480.5	467.1	399.5	333.1	285.1	260.3	245.4	237.6
67.5°	268.3	304.8	345.9	385.2	374.4	326.5	273.2	235.8	217.3	204.5	199.9
70°	232.0	259.8	296.4	327.9	319.1	279.9	237.6	205.7	189.8	178.8	174.2
72.5°	197.3	220.3	248.1	273.9	267.9	235.4	200.2	176.0	163.7	153.7	149.9
75°	149.0	166.5	183.5	200.6	198.9	173.7	153.1	134.5	124.7	117.0	115.4
77.5°	110.0	119.8	131.4	141.5	138.7	124.2	108.1	97.5	90.2	85.0	84.2
80°	84.0	89.7	98.0	105.1	101.6	95.3	82.5	74.7	69.6	64.4	62.4
82.5°	60.9	66.7	71.6	75.4	72.7	67.0	59.0	53.7	50.6	47.2	46.3
85°	31.9	35.0	37.2	38.2	37.2	33.5	29.9	27.9	25.2	23.7	23.2
87.5°	14.1	13.9	13.7	14.3	12.8	12.6	10.7	9.2	9.0	8.9	8.3
90°	8.7	7.8	6.8	5.7	4.3	3.1	1.8	0.5	1.8	3.1	4.3
92.5°	11.3	10.8	10.4	10.2	10.3	10.4	10.5	10.6	10.5	10.4	10.3
95°	18.9	18.1	17.3	18.8	22.6	26.6	30.4	34.2	30.4	26.6	22.6
97.5°	23.7	21.8	19.9	24.4	35.3	46.3	57.1	68.0	57.1	46.3	35.3
100°	26.1	24.0	22.1	29.1	45.1	61.2	77.3	93.3	77.3	61.2	45.1
102.5°	64.2	80.9	97.5	107.6	110.9	114.3	117.8	121.1	117.8	114.3	110.9
105°	96.1	128.1	160.1	174.3	170.8	167.2	163.7	160.2	163.7	167.2	170.8
107.5°	121.7	160.1	198.3	216.1	213.3	210.5	207.6	204.8	207.6	210.5	213.3
110°	160.0	193.8	227.6	243.3	240.9	238.4	235.9	233.5	235.9	238.4	240.9





TEST NUMBER: P331339-840

CATALOG NUMBER: SA2XXDIP-C675D530U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	249.3	257.7	266.1	269.1	267.0	264.8	262.7	260.4	262.7	264.8	267.0
115°	319.3	316.4	313.5	311.0	309.0	307.0	305.0	303.1	305.0	307.0	309.0
117.5°	356.2	354.2	352.1	350.0	347.8	345.6	343.4	341.1	343.4	345.6	347.8
120°	382.1	380.0	377.9	376.0	374.2	372.4	370.6	368.9	370.6	372.4	374.2
122.5°	406.6	404.2	402.0	399.9	398.1	396.3	394.4	392.5	394.4	396.3	398.1
125°	440.9	438.7	436.5	434.5	433.0	431.5	430.0	428.5	430.0	431.5	433.0
127.5°	472.8	471.1	469.5	467.8	466.1	464.4	462.7	461.0	462.7	464.4	466.1
130°	493.3	492.1	490.8	489.2	487.4	485.4	483.5	481.7	483.5	485.4	487.4
132.5°	513.2	511.9	510.6	509.2	507.6	505.9	504.3	502.8	504.3	505.9	507.6
135°	541.3	540.2	539.2	537.7	535.8	533.9	532.1	530.2	532.1	533.9	535.8
137.5°	566.8	565.6	564.4	563.1	561.8	560.5	559.2	558.0	559.2	560.5	561.8
140°	583.5	582.2	580.9	579.8	578.9	577.9	576.9	576.0	576.9	577.9	578.9
142.5°	598.6	597.2	595.7	594.6	593.7	592.9	592.1	591.2	592.1	592.9	593.7
145°	619.5	617.5	615.5	614.6	614.7	614.8	614.9	615.0	614.9	614.8	614.7
147.5°	638.7	636.7	634.8	634.0	634.5	634.9	635.3	635.8	635.3	634.9	634.5
150°	650.3	648.4	646.5	646.0	646.8	647.6	648.4	649.2	648.4	647.6	646.8
152.5°	661.1	659.2	657.4	657.0	657.9	658.8	659.7	660.7	659.7	658.8	657.9
155°	676.0	674.6	673.2	673.0	674.1	675.1	676.2	677.2	676.2	675.1	674.1
157.5°	688.6	687.6	686.7	686.6	687.5	688.4	689.3	690.1	689.3	688.4	687.5
160°	696.4	695.7	695.0	695.0	695.7	696.4	697.1	697.8	697.1	696.4	695.7
162.5°	702.9	702.3	701.7	701.8	702.4	703.1	703.8	704.5	703.8	703.1	702.4
165°	711.2	710.9	710.6	710.7	711.4	712.2	712.9	713.6	712.9	712.2	711.4
167.5°	718.0	717.6	717.3	717.5	718.2	718.9	719.6	720.3	719.6	718.9	718.2
170°	721.5	721.3	721.0	721.3	722.1	722.8	723.5	724.1	723.5	722.8	722.1
172.5°	724.1	723.9	723.6	723.9	724.6	725.3	726.0	726.7	726.0	725.3	724.6
175°	726.8	726.6	726.4	726.6	727.5	728.3	729.1	729.9	729.1	728.3	727.5
177.5°	727.7	727.6	727.5	727.8	728.5	729.1	729.8	730.4	729.8	729.1	728.5
180°	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3



TEST NUMBER: P331339-840

CATALOG NUMBER: SA2XXDIP-C675D530U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1323.6	1321.2	1312.5	1308.0	1300.5	1293.5	1289.0	1291.1	1292.7	1291.9	1290.6
5°	1285.7	1275.9	1260.9	1248.1	1238.8	1221.7	1214.6	1210.9	1207.9	1204.3	1200.6
7.5°	1240.5	1225.1	1203.7	1185.3	1167.9	1146.8	1134.8	1127.5	1120.1	1112.0	1104.8
10°	1208.4	1186.7	1164.1	1138.2	1117.6	1098.5	1081.6	1070.3	1060.0	1050.2	1042.9
12.5°	1174.6	1149.6	1121.6	1086.3	1063.6	1036.3	1033.7	1013.7	997.6	991.6	983.1
15°	1120.7	1085.7	1050.2	1008.4	990.3	965.5	950.1	934.6	920.7	910.9	908.4
17.5°	1059.6	1014.2	978.9	948.9	919.3	893.9	879.7	867.3	855.9	842.7	841.0
20°	1013.0	973.8	935.1	908.9	878.5	852.6	835.2	822.7	812.9	805.3	798.5
22.5°	968.9	925.9	890.6	861.8	831.8	811.0	797.2	785.3	777.1	768.5	762.2
25°	898.1	864.5	825.9	793.3	768.6	755.3	743.9	733.6	728.4	722.8	715.6
27.5°	836.1	798.8	762.7	737.5	715.8	703.9	695.8	688.8	684.0	680.6	676.6
30°	792.3	754.7	726.4	701.7	683.6	671.8	666.6	662.5	656.8	654.7	652.7
32.5°	750.3	716.4	692.2	670.7	653.5	645.7	641.0	637.3	632.9	630.8	626.6
35°	690.7	662.5	638.7	626.8	613.0	606.2	602.7	597.4	593.4	591.3	590.8
37.5°	634.8	610.2	594.6	579.4	573.5	569.4	564.4	560.9	559.7	559.4	558.9
40°	598.5	578.5	564.5	552.1	549.6	543.3	539.3	536.1	536.1	536.6	536.1
42.5°	565.5	547.4	535.2	524.5	521.5	517.8	513.6	513.4	514.3	516.0	514.3
45°	515.5	502.6	493.8	488.7	483.0	479.4	478.9	480.5	481.0	481.5	483.0
47.5°	469.5	461.0	453.0	447.4	444.8	444.2	443.6	446.4	448.8	449.7	452.1
50°	442.3	432.5	425.9	422.2	420.1	419.1	420.1	423.2	425.3	427.9	429.4
52.5°	411.8	404.9	400.2	397.5	396.7	397.3	397.5	401.0	404.2	405.2	406.0
55°	369.6	364.5	363.5	358.8	360.8	360.3	362.9	365.0	368.1	371.1	371.7
57.5°	327.6	323.5	320.6	321.0	321.6	324.0	326.1	329.7	333.1	336.3	336.6
60°	299.5	297.4	295.9	295.9	296.9	300.0	302.7	306.2	308.3	310.3	311.8
62.5°	274.0	271.9	270.3	271.1	273.9	275.7	278.7	280.6	282.7	284.8	285.5
65°	233.5	232.5	234.1	235.1	235.6	238.1	241.8	243.3	245.4	246.4	250.0
67.5°	196.3	196.5	196.3	197.7	200.8	201.4	204.8	208.3	208.7	210.8	213.1
70°	171.2	172.2	173.2	174.2	176.8	177.8	180.5	182.0	184.0	185.6	187.1
72.5°	148.0	148.2	149.3	149.1	151.3	153.5	155.7	157.2	159.3	161.3	162.8
75°	113.9	113.9	114.9	115.4	118.1	120.7	120.1	121.2	123.2	125.2	126.3
77.5°	83.2	82.1	83.2	83.7	84.5	86.7	87.2	88.6	90.9	90.2	91.4
80°	63.4	61.9	63.4	63.9	63.9	66.6	66.6	67.6	69.1	67.6	69.1
82.5°	45.2	44.5	45.6	45.7	46.6	46.7	47.6	47.8	49.3	48.6	49.3
85°	22.7	22.2	22.7	22.2	22.7	23.2	23.2	22.7	22.7	23.7	22.2
87.5°	8.2	8.0	7.8	7.9	7.7	7.5	7.2	7.3	7.4	6.7	6.8
90°	5.7	6.8	7.8	8.7	9.6	10.5	11.1	11.7	12.3	12.9	13.3
92.5°	10.2	10.4	10.8	11.3	11.7	12.2	12.5	12.8	13.1	13.4	13.6
95°	18.8	17.3	18.1	18.9	19.7	20.6	21.1	21.7	22.3	22.9	23.1
97.5°	24.4	19.9	21.8	23.7	25.7	27.5	28.0	28.5	28.9	29.4	29.7
100°	29.1	22.1	24.0	26.1	28.1	30.0	31.0	31.9	32.8	33.8	34.3
102.5°	107.6	97.5	80.9	64.2	47.6	30.9	32.1	33.3	34.5	35.7	36.6
105°	174.3	160.1	128.1	96.1	64.1	32.1	33.4	34.7	36.1	37.3	38.2
107.5°	216.1	198.3	160.1	121.7	83.3	45.0	43.7	42.4	41.1	39.8	39.4
110°	243.3	227.6	193.8	160.0	126.0	92.2	80.5	68.8	57.1	45.3	39.8



TEST NUMBER: P331339-840

CATALOG NUMBER: SA2XXDIP-C675D530U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	269.1	266.1	257.7	249.3	241.0	232.7	189.9	147.1	104.4	61.7	40.6
115°	311.0	313.5	316.4	319.3	322.2	325.2	270.9	216.7	162.5	108.3	77.0
117.5°	350.0	352.1	354.2	356.2	358.2	360.1	347.1	334.0	320.8	307.7	287.3
120°	376.0	377.9	380.0	382.1	384.2	386.3	387.7	389.1	390.5	391.9	384.8
122.5°	399.9	402.0	404.2	406.6	408.9	411.2	412.0	412.8	413.7	414.5	413.4
125°	434.5	436.5	438.7	440.9	443.1	445.4	446.2	447.0	447.8	448.6	449.2
127.5°	467.8	469.5	471.1	472.8	474.4	476.2	477.3	478.5	479.7	480.9	481.5
130°	489.2	490.8	492.1	493.3	494.6	495.9	497.3	498.5	499.8	501.1	501.7
132.5°	509.2	510.6	511.9	513.2	514.4	515.7	516.8	518.0	519.1	520.2	520.6
135°	537.7	539.2	540.2	541.3	542.3	543.3	544.5	545.7	546.8	548.1	548.6
137.5°	563.1	564.4	565.6	566.8	567.9	569.2	570.4	571.5	572.6	573.8	574.1
140°	579.8	580.9	582.2	583.5	584.7	586.0	587.1	588.1	589.2	590.3	590.5
142.5°	594.6	595.7	597.2	598.6	600.2	601.7	602.6	603.6	604.5	605.5	605.7
145°	614.6	615.5	617.5	619.5	621.5	623.5	624.3	625.1	625.9	626.7	626.8
147.5°	634.0	634.8	636.7	638.7	640.7	642.7	643.3	643.9	644.5	645.1	645.1
150°	646.0	646.5	648.4	650.3	652.2	654.0	654.7	655.4	656.1	656.8	656.9
152.5°	657.0	657.4	659.2	661.1	662.8	664.6	665.3	666.0	666.7	667.4	667.3
155°	673.0	673.2	674.6	676.0	677.4	678.8	679.5	680.2	681.0	681.7	681.5
157.5°	686.6	686.7	687.6	688.6	689.6	690.6	691.4	692.2	693.0	693.8	693.8
160°	695.0	695.0	695.7	696.4	697.1	697.8	698.5	699.1	699.8	700.5	700.5
162.5°	701.8	701.7	702.3	702.9	703.5	704.1	704.9	705.7	706.5	707.3	707.2
165°	710.7	710.6	710.9	711.2	711.7	712.0	712.9	713.7	714.5	715.3	715.3
167.5°	717.5	717.3	717.6	718.0	718.3	718.6	719.4	720.2	721.1	722.0	721.9
170°	721.3	721.0	721.3	721.5	721.8	722.1	722.9	723.7	724.5	725.3	725.2
172.5°	723.9	723.6	723.9	724.1	724.3	724.6	725.4	726.2	727.0	727.8	727.7
175°	726.6	726.4	726.6	726.8	727.0	727.3	728.1	728.9	729.7	730.5	730.4
177.5°	727.8	727.5	727.6	727.7	727.8	727.9	728.6	729.2	729.9	730.5	730.4
180°	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3



TEST NUMBER: P331339-840

CATALOG NUMBER: SA2XXDIP-C675D530U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1286.6	1285.7	1285.7	1282.0	1285.7	1285.7	1286.6	1290.6	1291.9	1292.7	1291.1
5°	1193.5	1191.8	1189.3	1191.8	1189.3	1191.8	1193.5	1200.6	1204.3	1207.9	1210.9
7.5°	1101.4	1095.2	1094.3	1088.1	1094.3	1095.2	1101.4	1104.8	1112.0	1120.1	1127.5
10°	1034.1	1030.0	1029.5	1019.7	1029.5	1030.0	1034.1	1042.9	1050.2	1060.0	1070.3
12.5°	983.0	973.1	975.0	969.4	975.0	973.1	983.0	983.1	991.6	997.6	1013.7
15°	894.4	894.4	892.3	883.6	892.3	894.4	894.4	908.4	910.9	920.7	934.6
17.5°	830.8	829.8	824.9	827.3	824.9	829.8	830.8	841.0	842.7	855.9	867.3
20°	792.8	789.8	783.6	783.6	783.6	789.8	792.8	798.5	805.3	812.9	822.7
22.5°	757.0	756.8	750.2	752.2	750.2	756.8	757.0	762.2	768.5	777.1	785.3
25°	715.0	710.9	707.8	709.3	707.8	710.9	715.0	715.6	722.8	728.4	733.6
27.5°	675.2	673.0	672.8	668.5	672.8	673.0	675.2	676.6	680.6	684.0	688.8
30°	652.2	647.0	648.0	645.4	648.0	647.0	652.2	652.7	654.7	656.8	662.5
32.5°	625.7	623.9	622.9	620.7	622.9	623.9	625.7	626.6	630.8	632.9	637.3
35°	589.8	590.3	587.7	588.8	587.7	590.3	589.8	590.8	591.3	593.4	597.4
37.5°	558.4	560.0	558.8	559.1	558.8	560.0	558.4	558.9	559.4	559.7	560.9
40°	537.7	537.7	537.7	539.3	537.7	537.7	537.7	536.1	536.6	536.1	536.1
42.5°	517.9	517.1	516.2	516.1	516.2	517.1	517.9	514.3	516.0	514.3	513.4
45°	484.0	485.6	486.1	483.5	486.1	485.6	484.0	483.0	481.5	481.0	480.5
47.5°	453.4	453.6	453.4	455.8	453.4	453.6	453.4	452.1	449.7	448.8	446.4
50°	432.0	431.0	432.0	431.0	432.0	431.0	432.0	429.4	427.9	425.3	423.2
52.5°	409.3	409.5	408.9	408.7	408.9	409.5	409.3	406.0	405.2	404.2	401.0
55°	373.8	374.8	374.3	374.3	374.3	374.8	373.8	371.7	371.1	368.1	365.0
57.5°	337.0	337.9	338.6	336.3	338.6	337.9	337.0	336.6	336.3	333.1	329.7
60°	311.3	314.0	313.5	312.5	313.5	314.0	311.3	311.8	310.3	308.3	306.2
62.5°	287.9	288.8	288.7	288.5	288.7	288.8	287.9	285.5	284.8	282.7	280.6
65°	251.6	252.6	251.1	252.6	251.1	252.6	251.6	250.0	246.4	245.4	243.3
67.5°	212.5	212.8	214.0	214.7	214.0	212.8	212.5	213.1	210.8	208.7	208.3
70°	188.1	187.6	189.1	190.8	189.1	187.6	188.1	187.1	185.6	184.0	182.0
72.5°	162.6	163.7	163.2	164.3	163.2	163.7	162.6	162.8	161.3	159.3	157.2
75°	125.2	126.8	126.3	127.8	126.3	126.8	125.2	126.3	125.2	123.2	121.2
77.5°	90.5	90.7	90.5	91.4	90.5	90.7	90.5	91.4	90.2	90.9	88.6
80°	69.1	68.1	67.1	69.1	67.1	68.1	69.1	69.1	67.6	69.1	67.6
82.5°	48.1	48.7	47.7	47.7	47.7	48.7	48.1	49.3	48.6	49.3	47.8
85°	22.2	21.6	20.6	20.6	20.6	21.6	22.2	22.2	23.7	22.7	22.7
87.5°	6.9	6.5	6.5	6.2	6.5	6.5	6.9	6.8	6.7	7.4	7.3
90°	13.5	13.7	14.0	14.2	14.0	13.7	13.5	13.3	12.9	12.3	11.7
92.5°	13.8	13.9	14.1	14.2	14.1	13.9	13.8	13.6	13.4	13.1	12.8
95°	23.0	22.9	22.8	22.6	22.8	22.9	23.0	23.1	22.9	22.3	21.7
97.5°	29.8	30.0	30.1	30.3	30.1	30.0	29.8	29.7	29.4	28.9	28.5
100°	34.6	34.8	35.0	35.3	35.0	34.8	34.6	34.3	33.8	32.8	31.9
102.5°	36.9	37.2	37.5	37.9	37.5	37.2	36.9	36.6	35.7	34.5	33.3
105°	38.7	39.1	39.6	40.1	39.6	39.1	38.7	38.2	37.3	36.1	34.7
107.5°	39.8	40.3	40.7	41.2	40.7	40.3	39.8	39.4	39.8	41.1	42.4
110°	40.2	40.7	41.2	41.6	41.2	40.7	40.2	39.8	45.3	57.1	68.8



TEST NUMBER: P331339-840

CATALOG NUMBER: SA2XXDIP-C675D530U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	40.9	41.3	41.7	42.0	41.7	41.3	40.9	40.6	61.7	104.4	147.1
115°	68.5	60.1	51.6	43.2	51.6	60.1	68.5	77.0	108.3	162.5	216.7
117.5°	259.5	231.9	204.2	176.4	204.2	231.9	259.5	287.3	307.7	320.8	334.0
120°	368.9	353.1	337.3	321.4	337.3	353.1	368.9	384.8	391.9	390.5	389.1
122.5°	410.4	407.3	404.2	401.1	404.2	407.3	410.4	413.4	414.5	413.7	412.8
125°	449.6	449.9	450.3	450.6	450.3	449.9	449.6	449.2	448.6	447.8	447.0
127.5°	481.6	481.7	481.7	481.8	481.7	481.7	481.6	481.5	480.9	479.7	478.5
130°	501.5	501.4	501.3	501.2	501.3	501.4	501.5	501.7	501.1	499.8	498.5
132.5°	520.5	520.4	520.3	520.2	520.3	520.4	520.5	520.6	520.2	519.1	518.0
135°	548.3	548.1	547.9	547.5	547.9	548.1	548.3	548.6	548.1	546.8	545.7
137.5°	573.7	573.3	573.0	572.6	573.0	573.3	573.7	574.1	573.8	572.6	571.5
140°	589.9	589.4	588.8	588.1	588.8	589.4	589.9	590.5	590.3	589.2	588.1
142.5°	605.1	604.5	603.9	603.3	603.9	604.5	605.1	605.7	605.5	604.5	603.6
145°	626.3	625.7	625.1	624.5	625.1	625.7	626.3	626.8	626.7	625.9	625.1
147.5°	644.7	644.2	643.7	643.2	643.7	644.2	644.7	645.1	645.1	644.5	643.9
150°	656.3	655.7	655.1	654.6	655.1	655.7	656.3	656.9	656.8	656.1	655.4
152.5°	666.6	665.8	665.0	664.3	665.0	665.8	666.6	667.3	667.4	666.7	666.0
155°	680.5	679.6	678.7	677.7	678.7	679.6	680.5	681.5	681.7	681.0	680.2
157.5°	692.8	691.9	690.9	690.0	690.9	691.9	692.8	693.8	693.8	693.0	692.2
160°	699.7	698.9	698.0	697.2	698.0	698.9	699.7	700.5	700.5	699.8	699.1
162.5°	706.2	705.2	704.2	703.2	704.2	705.2	706.2	707.2	707.3	706.5	705.7
165°	714.5	713.7	712.9	712.0	712.9	713.7	714.5	715.3	715.3	714.5	713.7
167.5°	720.7	719.7	718.6	717.6	718.6	719.7	720.7	721.9	722.0	721.1	720.2
170°	724.1	723.1	722.1	720.9	722.1	723.1	724.1	725.2	725.3	724.5	723.7
172.5°	726.7	725.6	724.6	723.5	724.6	725.6	726.7	727.7	727.8	727.0	726.2
175°	729.2	728.0	726.9	725.7	726.9	728.0	729.2	730.4	730.5	729.7	728.9
177.5°	729.6	728.7	727.9	727.1	727.9	728.7	729.6	730.4	730.5	729.9	729.2
180°	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3



TEST NUMBER: P331339-840

CATALOG NUMBER: SA2XXDIP-C675D530U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1289.0	1293.5	1300.5	1308.0	1312.5	1321.2	1323.6	1327.8	1331.5	1340.2	1349.2
5°	1214.6	1221.7	1238.8	1248.1	1260.9	1275.9	1285.7	1296.1	1307.4	1327.0	1344.9
7.5°	1134.8	1146.8	1167.9	1185.3	1203.7	1225.1	1240.5	1260.9	1277.9	1305.5	1331.9
10°	1081.6	1098.5	1117.6	1138.2	1164.1	1186.7	1208.4	1234.2	1254.8	1287.8	1318.7
12.5°	1033.7	1036.3	1063.6	1086.3	1121.6	1149.6	1174.6	1207.8	1228.0	1267.2	1299.7
15°	950.1	965.5	990.3	1008.4	1050.2	1085.7	1120.7	1155.3	1178.5	1226.9	1269.7
17.5°	879.7	893.9	919.3	948.9	978.9	1014.2	1059.6	1096.0	1127.5	1183.0	1233.6
20°	835.2	852.6	878.5	908.9	935.1	973.8	1013.0	1054.7	1088.7	1151.1	1210.4
22.5°	797.2	811.0	831.8	861.8	890.6	925.9	968.9	1014.3	1050.1	1117.3	1177.4
25°	743.9	755.3	768.6	793.3	825.9	864.5	898.1	948.1	1000.1	1063.0	1135.7
27.5°	695.8	703.9	715.8	737.5	762.7	798.8	836.1	883.5	935.8	1004.1	1080.9
30°	666.6	671.8	683.6	701.7	726.4	754.7	792.3	837.7	891.3	960.4	1036.7
32.5°	641.0	645.7	653.5	670.7	692.2	716.4	750.3	795.7	846.8	914.6	999.2
35°	602.7	606.2	613.0	626.8	638.7	662.5	690.7	732.1	780.0	845.0	932.6
37.5°	564.4	569.4	573.5	579.4	594.6	610.2	634.8	669.6	716.7	782.2	865.8
40°	539.3	543.3	549.6	552.1	564.5	578.5	598.5	630.5	677.9	737.7	819.2
42.5°	513.6	517.8	521.5	524.5	535.2	547.4	565.5	593.0	635.0	693.2	773.8
45°	478.9	479.4	483.0	488.7	493.8	502.6	515.5	539.3	571.7	626.3	699.5
47.5°	443.6	444.2	444.8	447.4	453.0	461.0	469.5	488.8	517.9	561.5	632.8
50°	420.1	419.1	420.1	422.2	425.9	432.5	442.3	456.3	480.0	520.7	586.1
52.5°	397.5	397.3	396.7	397.5	400.2	404.9	411.8	423.6	444.8	482.3	540.0
55°	362.9	360.3	360.8	358.8	363.5	364.5	369.6	379.4	398.0	423.7	477.9
57.5°	326.1	324.0	321.6	321.0	320.6	323.5	327.6	335.3	349.5	372.1	416.1
60°	302.7	300.0	296.9	295.9	295.9	297.4	299.5	305.2	318.6	338.7	374.8
62.5°	278.7	275.7	273.9	271.1	270.3	271.9	274.0	278.0	287.6	306.5	337.7
65°	241.8	238.1	235.6	235.1	234.1	232.5	233.5	237.6	245.4	260.3	285.1
67.5°	204.8	201.4	200.8	197.7	196.3	196.5	196.3	199.9	204.5	217.3	235.8
70°	180.5	177.8	176.8	174.2	173.2	172.2	171.2	174.2	178.8	189.8	205.7
72.5°	155.7	153.5	151.3	149.1	149.3	148.2	148.0	149.9	153.7	163.7	176.0
75°	120.1	120.7	118.1	115.4	114.9	113.9	113.9	115.4	117.0	124.7	134.5
77.5°	87.2	86.7	84.5	83.7	83.2	82.1	83.2	84.2	85.0	90.2	97.5
80°	66.6	66.6	63.9	63.9	63.4	61.9	63.4	62.4	64.4	69.6	74.7
82.5°	47.6	46.7	46.6	45.7	45.6	44.5	45.2	46.3	47.2	50.6	53.7
85°	23.2	23.2	22.7	22.2	22.7	22.2	22.7	23.2	23.7	25.2	27.9
87.5°	7.2	7.5	7.7	7.9	7.8	8.0	8.2	8.3	8.9	9.0	9.2
90°	11.1	10.5	9.6	8.7	7.8	6.8	5.7	4.3	3.1	1.8	0.5
92.5°	12.5	12.2	11.7	11.3	10.8	10.4	10.2	10.3	10.4	10.5	10.6
95°	21.1	20.6	19.7	18.9	18.1	17.3	18.8	22.6	26.6	30.4	34.2
97.5°	28.0	27.5	25.7	23.7	21.8	19.9	24.4	35.3	46.3	57.1	68.0
100°	31.0	30.0	28.1	26.1	24.0	22.1	29.1	45.1	61.2	77.3	93.3
102.5°	32.1	30.9	47.6	64.2	80.9	97.5	107.6	110.9	114.3	117.8	121.1
105°	33.4	32.1	64.1	96.1	128.1	160.1	174.3	170.8	167.2	163.7	160.2
107.5°	43.7	45.0	83.3	121.7	160.1	198.3	216.1	213.3	210.5	207.6	204.8
110°	80.5	92.2	126.0	160.0	193.8	227.6	243.3	240.9	238.4	235.9	233.5



TEST NUMBER: P331339-840

CATALOG NUMBER: SA2XXDIP-C675D530U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	189.9	232.7	241.0	249.3	257.7	266.1	269.1	267.0	264.8	262.7	260.4
115°	270.9	325.2	322.2	319.3	316.4	313.5	311.0	309.0	307.0	305.0	303.1
117.5°	347.1	360.1	358.2	356.2	354.2	352.1	350.0	347.8	345.6	343.4	341.1
120°	387.7	386.3	384.2	382.1	380.0	377.9	376.0	374.2	372.4	370.6	368.9
122.5°	412.0	411.2	408.9	406.6	404.2	402.0	399.9	398.1	396.3	394.4	392.5
125°	446.2	445.4	443.1	440.9	438.7	436.5	434.5	433.0	431.5	430.0	428.5
127.5°	477.3	476.2	474.4	472.8	471.1	469.5	467.8	466.1	464.4	462.7	461.0
130°	497.3	495.9	494.6	493.3	492.1	490.8	489.2	487.4	485.4	483.5	481.7
132.5°	516.8	515.7	514.4	513.2	511.9	510.6	509.2	507.6	505.9	504.3	502.8
135°	544.5	543.3	542.3	541.3	540.2	539.2	537.7	535.8	533.9	532.1	530.2
137.5°	570.4	569.2	567.9	566.8	565.6	564.4	563.1	561.8	560.5	559.2	558.0
140°	587.1	586.0	584.7	583.5	582.2	580.9	579.8	578.9	577.9	576.9	576.0
142.5°	602.6	601.7	600.2	598.6	597.2	595.7	594.6	593.7	592.9	592.1	591.2
145°	624.3	623.5	621.5	619.5	617.5	615.5	614.6	614.7	614.8	614.9	615.0
147.5°	643.3	642.7	640.7	638.7	636.7	634.8	634.0	634.5	634.9	635.3	635.8
150°	654.7	654.0	652.2	650.3	648.4	646.5	646.0	646.8	647.6	648.4	649.2
152.5°	665.3	664.6	662.8	661.1	659.2	657.4	657.0	657.9	658.8	659.7	660.7
155°	679.5	678.8	677.4	676.0	674.6	673.2	673.0	674.1	675.1	676.2	677.2
157.5°	691.4	690.6	689.6	688.6	687.6	686.7	686.6	687.5	688.4	689.3	690.1
160°	698.5	697.8	697.1	696.4	695.7	695.0	695.0	695.7	696.4	697.1	697.8
162.5°	704.9	704.1	703.5	702.9	702.3	701.7	701.8	702.4	703.1	703.8	704.5
165°	712.9	712.0	711.7	711.2	710.9	710.6	710.7	711.4	712.2	712.9	713.6
167.5°	719.4	718.6	718.3	718.0	717.6	717.3	717.5	718.2	718.9	719.6	720.3
170°	722.9	722.1	721.8	721.5	721.3	721.0	721.3	722.1	722.8	723.5	724.1
172.5°	725.4	724.6	724.3	724.1	723.9	723.6	723.9	724.6	725.3	726.0	726.7
175°	728.1	727.3	727.0	726.8	726.6	726.4	726.6	727.5	728.3	729.1	729.9
177.5°	728.6	727.9	727.8	727.7	727.6	727.5	727.8	728.5	729.1	729.8	730.4
180°	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3



TEST NUMBER: P331339-840

CATALOG NUMBER: SA2XXDIP-C675D530U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1348.4	1350.5	1357.1	1363.6	1371.1	1373.1	1376.4	1373.5	1372.7	1380.6	1386.3
5°	1352.2	1361.5	1379.6	1396.0	1410.0	1419.8	1430.1	1434.2	1441.9	1452.7	1466.1
7.5°	1347.9	1365.9	1394.3	1418.3	1444.5	1463.4	1478.1	1490.7	1505.9	1526.4	1548.8
10°	1342.9	1367.2	1401.7	1431.1	1463.0	1487.2	1507.4	1526.9	1549.6	1578.0	1607.4
12.5°	1333.8	1362.6	1405.8	1440.6	1481.6	1505.4	1532.6	1574.8	1599.1	1638.6	1680.0
15°	1315.7	1347.6	1407.9	1450.7	1497.0	1542.5	1592.5	1632.6	1672.8	1696.1	1754.3
17.5°	1288.5	1335.4	1402.2	1452.1	1511.1	1582.6	1638.7	1684.3	1730.7	1768.4	1797.6
20°	1266.7	1317.7	1393.9	1453.8	1523.9	1600.6	1665.2	1711.5	1751.7	1783.2	1801.2
22.5°	1239.0	1303.2	1377.5	1447.5	1537.1	1613.1	1680.8	1717.3	1750.9	1766.3	1773.2
25°	1195.5	1272.8	1356.9	1442.4	1543.5	1623.9	1685.8	1707.9	1717.7	1702.7	1678.0
27.5°	1148.6	1234.8	1333.0	1432.7	1539.5	1616.9	1661.2	1657.7	1641.1	1592.8	1554.1
30°	1113.5	1208.4	1314.0	1422.8	1530.0	1605.3	1631.1	1605.3	1567.7	1513.6	1458.4
32.5°	1076.8	1175.0	1293.8	1408.8	1512.8	1578.9	1584.5	1540.1	1481.9	1420.4	1351.6
35°	1021.3	1127.4	1255.8	1377.5	1475.9	1517.7	1493.0	1414.6	1345.5	1261.5	1167.6
37.5°	958.5	1075.7	1204.5	1331.6	1420.8	1431.7	1370.3	1287.8	1190.3	1091.6	981.2
40°	911.4	1035.7	1168.2	1296.6	1375.4	1364.0	1285.7	1195.0	1078.9	958.4	855.8
42.5°	869.4	993.6	1128.5	1254.5	1317.7	1286.6	1195.0	1083.6	959.0	845.4	751.4
45°	796.5	924.3	1062.5	1184.2	1220.2	1164.1	1042.9	919.2	796.5	701.7	627.4
47.5°	725.8	852.1	989.0	1095.9	1108.6	1033.1	900.7	773.4	667.9	590.7	538.3
50°	673.8	800.6	936.1	1031.6	1027.4	936.1	800.1	678.9	590.8	528.4	493.3
52.5°	627.2	747.0	877.2	963.9	942.1	842.5	712.7	605.1	532.6	483.8	452.1
55°	554.7	665.5	789.2	858.9	818.6	708.3	598.5	511.9	458.3	421.7	397.0
57.5°	482.7	586.6	692.6	735.5	691.1	589.2	497.6	434.7	394.5	367.4	351.2
60°	438.2	529.0	623.3	660.4	607.2	516.5	444.3	388.2	355.7	333.6	319.1
62.5°	393.6	474.9	563.9	584.1	535.5	458.8	394.9	348.2	321.4	301.7	288.2
65°	333.1	399.5	467.1	480.5	435.7	376.4	325.8	295.4	271.7	257.2	246.4
67.5°	273.2	326.5	374.4	385.2	345.9	304.8	268.3	241.8	225.7	213.7	204.6
70°	237.6	279.9	319.1	327.9	296.4	259.8	232.0	210.9	196.4	186.1	177.3
72.5°	200.2	235.4	267.9	273.9	248.1	220.3	197.3	180.8	167.9	161.4	153.0
75°	153.1	173.7	198.9	200.6	183.5	166.5	149.0	138.1	131.5	123.2	119.1
77.5°	108.1	124.2	138.7	141.5	131.4	119.8	110.0	101.5	95.7	92.0	88.2
80°	82.5	95.3	101.6	105.1	98.0	89.7	84.0	78.4	74.7	72.2	69.6
82.5°	59.0	67.0	72.7	75.4	71.6	66.7	60.9	57.8	54.9	52.8	51.9
85°	29.9	33.5	37.2	38.2	37.2	35.0	31.9	31.9	30.4	29.9	29.9
87.5°	10.7	12.6	12.8	14.3	13.7	13.9	14.1	13.8	13.6	13.3	13.0
90°	1.8	3.1	4.3	5.7	6.8	7.8	8.7	9.6	10.5	11.1	11.7
92.5°	10.5	10.4	10.3	10.2	10.4	10.8	11.3	11.7	12.2	12.5	12.8
95°	30.4	26.6	22.6	18.8	17.3	18.1	18.9	19.7	20.6	21.1	21.7
97.5°	57.1	46.3	35.3	24.4	19.9	21.8	23.7	25.7	27.5	28.0	28.5
100°	77.3	61.2	45.1	29.1	22.1	24.0	26.1	28.1	30.0	31.0	31.9
102.5°	117.8	114.3	110.9	107.6	97.5	80.9	64.2	47.6	30.9	32.1	33.3
105°	163.7	167.2	170.8	174.3	160.1	128.1	96.1	64.1	32.1	33.4	34.7
107.5°	207.6	210.5	213.3	216.1	198.3	160.1	121.7	83.3	45.0	43.7	42.4
110°	235.9	238.4	240.9	243.3	227.6	193.8	160.0	126.0	92.2	80.5	68.8





TEST NUMBER: P331339-840

CATALOG NUMBER: SA2XXDIP-C675D530U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	262.7	264.8	267.0	269.1	266.1	257.7	249.3	241.0	232.7	189.9	147.1
115°	305.0	307.0	309.0	311.0	313.5	316.4	319.3	322.2	325.2	270.9	216.7
117.5°	343.4	345.6	347.8	350.0	352.1	354.2	356.2	358.2	360.1	347.1	334.0
120°	370.6	372.4	374.2	376.0	377.9	380.0	382.1	384.2	386.3	387.7	389.1
122.5°	394.4	396.3	398.1	399.9	402.0	404.2	406.6	408.9	411.2	412.0	412.8
125°	430.0	431.5	433.0	434.5	436.5	438.7	440.9	443.1	445.4	446.2	447.0
127.5°	462.7	464.4	466.1	467.8	469.5	471.1	472.8	474.4	476.2	477.3	478.5
130°	483.5	485.4	487.4	489.2	490.8	492.1	493.3	494.6	495.9	497.3	498.5
132.5°	504.3	505.9	507.6	509.2	510.6	511.9	513.2	514.4	515.7	516.8	518.0
135°	532.1	533.9	535.8	537.7	539.2	540.2	541.3	542.3	543.3	544.5	545.7
137.5°	559.2	560.5	561.8	563.1	564.4	565.6	566.8	567.9	569.2	570.4	571.5
140°	576.9	577.9	578.9	579.8	580.9	582.2	583.5	584.7	586.0	587.1	588.1
142.5°	592.1	592.9	593.7	594.6	595.7	597.2	598.6	600.2	601.7	602.6	603.6
145°	614.9	614.8	614.7	614.6	615.5	617.5	619.5	621.5	623.5	624.3	625.1
147.5°	635.3	634.9	634.5	634.0	634.8	636.7	638.7	640.7	642.7	643.3	643.9
150°	648.4	647.6	646.8	646.0	646.5	648.4	650.3	652.2	654.0	654.7	655.4
152.5°	659.7	658.8	657.9	657.0	657.4	659.2	661.1	662.8	664.6	665.3	666.0
155°	676.2	675.1	674.1	673.0	673.2	674.6	676.0	677.4	678.8	679.5	680.2
157.5°	689.3	688.4	687.5	686.6	686.7	687.6	688.6	689.6	690.6	691.4	692.2
160°	697.1	696.4	695.7	695.0	695.0	695.7	696.4	697.1	697.8	698.5	699.1
162.5°	703.8	703.1	702.4	701.8	701.7	702.3	702.9	703.5	704.1	704.9	705.7
165°	712.9	712.2	711.4	710.7	710.6	710.9	711.2	711.7	712.0	712.9	713.7
167.5°	719.6	718.9	718.2	717.5	717.3	717.6	718.0	718.3	718.6	719.4	720.2
170°	723.5	722.8	722.1	721.3	721.0	721.3	721.5	721.8	722.1	722.9	723.7
172.5°	726.0	725.3	724.6	723.9	723.6	723.9	724.1	724.3	724.6	725.4	726.2
175°	729.1	728.3	727.5	726.6	726.4	726.6	726.8	727.0	727.3	728.1	728.9
177.5°	729.8	729.1	728.5	727.8	727.5	727.6	727.7	727.8	727.9	728.6	729.2
180°	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3



TEST NUMBER: P331339-840

CATALOG NUMBER: SA2XXDIP-C675D530U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1391.3	1397.0	1397.0	1397.9	1404.5	1403.6	1403.2
5°	1480.6	1489.3	1490.4	1499.6	1505.8	1503.8	1498.1
7.5°	1564.8	1581.1	1593.5	1600.3	1608.5	1613.6	1611.3
10°	1631.6	1655.4	1669.8	1679.6	1691.4	1700.2	1697.1
12.5°	1692.2	1720.5	1740.3	1757.1	1758.7	1769.9	1762.2
15°	1786.8	1816.6	1819.8	1832.2	1842.0	1840.9	1841.4
17.5°	1818.1	1827.7	1829.6	1829.9	1830.0	1826.3	1818.6
20°	1806.9	1803.3	1794.5	1787.9	1775.9	1774.4	1764.1
22.5°	1754.1	1742.6	1720.7	1706.2	1687.7	1682.8	1680.0
25°	1650.2	1624.9	1589.8	1556.3	1547.1	1529.0	1534.2
27.5°	1507.6	1468.2	1430.3	1403.0	1378.4	1351.4	1359.1
30°	1407.3	1363.0	1309.4	1268.2	1241.9	1216.1	1211.4
32.5°	1287.8	1222.8	1163.0	1126.7	1086.4	1070.2	1052.3
35°	1081.6	1018.1	958.9	907.9	878.5	855.8	835.2
37.5°	896.1	823.0	775.3	733.9	712.7	699.6	703.0
40°	781.0	717.1	682.1	650.6	631.0	621.7	623.8
42.5°	687.8	640.0	611.1	589.6	575.7	570.6	569.4
45°	582.0	555.2	531.5	519.2	512.4	506.8	503.1
47.5°	509.9	488.0	474.6	467.3	461.4	455.7	455.6
50°	466.6	452.1	442.8	435.0	430.5	426.4	429.9
52.5°	433.5	420.3	411.1	404.1	402.4	398.7	398.6
55°	384.6	374.3	367.6	361.3	358.3	356.2	353.7
57.5°	340.0	330.2	324.1	320.1	314.3	312.1	311.3
60°	308.3	300.5	294.4	289.2	286.6	282.5	282.5
62.5°	279.0	271.2	265.5	261.6	257.3	255.7	256.1
65°	236.6	230.5	224.8	220.7	219.6	216.5	217.5
67.5°	197.6	193.5	187.5	185.3	183.3	181.7	180.5
70°	171.7	167.5	164.4	161.4	159.8	159.8	159.8
72.5°	149.8	144.8	143.0	139.1	140.0	138.4	136.7
75°	116.0	112.9	111.4	109.8	107.2	107.2	107.2
77.5°	85.3	84.4	82.6	80.9	80.3	79.8	80.0
80°	65.9	65.4	64.4	64.4	63.4	62.9	61.9
82.5°	50.7	49.4	48.8	48.4	48.2	48.1	47.9
85°	28.9	27.9	27.9	28.4	27.4	27.4	27.9
87.5°	13.6	13.7	13.4	13.4	13.9	13.5	13.5
90°	12.3	12.9	13.3	13.5	13.7	14.0	14.2
92.5°	13.1	13.4	13.6	13.8	13.9	14.1	14.2
95°	22.3	22.9	23.1	23.0	22.9	22.8	22.6
97.5°	28.9	29.4	29.7	29.8	30.0	30.1	30.3
100°	32.8	33.8	34.3	34.6	34.8	35.0	35.3
102.5°	34.5	35.7	36.6	36.9	37.2	37.5	37.9
105°	36.1	37.3	38.2	38.7	39.1	39.6	40.1
107.5°	41.1	39.8	39.4	39.8	40.3	40.7	41.2
110°	57.1	45.3	39.8	40.2	40.7	41.2	41.6



TEST NUMBER: P331339-840

CATALOG NUMBER: SA2XXDIP-C675D530U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	104.4	61.7	40.6	40.9	41.3	41.7	42.0
115°	162.5	108.3	77.0	68.5	60.1	51.6	43.2
117.5°	320.8	307.7	287.3	259.5	231.9	204.2	176.4
120°	390.5	391.9	384.8	368.9	353.1	337.3	321.4
122.5°	413.7	414.5	413.4	410.4	407.3	404.2	401.1
125°	447.8	448.6	449.2	449.6	449.9	450.3	450.6
127.5°	479.7	480.9	481.5	481.6	481.7	481.7	481.8
130°	499.8	501.1	501.7	501.5	501.4	501.3	501.2
132.5°	519.1	520.2	520.6	520.5	520.4	520.3	520.2
135°	546.8	548.1	548.6	548.3	548.1	547.9	547.5
137.5°	572.6	573.8	574.1	573.7	573.3	573.0	572.6
140°	589.2	590.3	590.5	589.9	589.4	588.8	588.1
142.5°	604.5	605.5	605.7	605.1	604.5	603.9	603.3
145°	625.9	626.7	626.8	626.3	625.7	625.1	624.5
147.5°	644.5	645.1	645.1	644.7	644.2	643.7	643.2
150°	656.1	656.8	656.9	656.3	655.7	655.1	654.6
152.5°	666.7	667.4	667.3	666.6	665.8	665.0	664.3
155°	681.0	681.7	681.5	680.5	679.6	678.7	677.7
157.5°	693.0	693.8	693.8	692.8	691.9	690.9	690.0
160°	699.8	700.5	700.5	699.7	698.9	698.0	697.2
162.5°	706.5	707.3	707.2	706.2	705.2	704.2	703.2
165°	714.5	715.3	715.3	714.5	713.7	712.9	712.0
167.5°	721.1	722.0	721.9	720.7	719.7	718.6	717.6
170°	724.5	725.3	725.2	724.1	723.1	722.1	720.9
172.5°	727.0	727.8	727.7	726.7	725.6	724.6	723.5
175°	729.7	730.5	730.4	729.2	728.0	726.9	725.7
177.5°	729.9	730.5	730.4	729.6	728.7	727.9	727.1
180°	728.3	728.3	728.3	728.3	728.3	728.3	728.3

(END OF REPORT)