

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331347-840

Luminaire Tested: **SA2XXDIP-C675D530U840-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331347-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C675D530U840-4F0-1E-UDD-F4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 530 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4814.4 lumens
Efficiency: N/A
Efficacy: 119.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 40.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331347-840
CATALOG NUMBER: SA2XXDIP-C675D530U840-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331347-840

CATALOG NUMBER: SA2XXDIP-C675D530U840-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	57
1	99	95	91	87	92	88	85	82	76	74	72	65	63	62	55	54	53	48
2	90	83	77	71	84	77	72	67	67	63	59	57	54	52	48	46	44	40
3	82	73	65	60	76	68	62	56	59	54	50	51	47	44	43	40	38	34
4	75	65	57	50	70	60	53	48	53	47	43	45	41	37	38	35	33	29
5	69	58	49	43	64	54	47	41	47	41	37	41	36	32	35	31	28	25
6	64	52	43	38	59	48	41	36	42	36	32	37	32	28	31	28	25	22
7	59	47	39	33	55	44	37	31	38	33	28	33	29	25	29	25	22	20
8	55	42	35	29	51	40	33	28	35	29	25	31	26	23	26	23	20	18
9	51	39	31	26	48	37	30	25	32	27	23	28	24	20	24	21	18	16
10	48	36	28	23	45	34	27	22	30	24	20	26	22	18	23	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17312	17312	17312
5°	17378	17126	17227
10°	17274	16952	17038
15°	17060	16732	16715
20°	16756	16402	16385
25°	16456	15998	15998
30°	16067	15627	15491
35°	15707	15179	14954
40°	15253	14731	14450
45°	14805	14289	13935
50°	14320	13828	13335
55°	13813	13292	12797
60°	13249	12649	12184
65°	12642	12015	11461
70°	11877	11240	10707
75°	10805	10356	10100
80°	9586	9298	8815
85°	7836	7447	6688



TEST NUMBER: P331347-840

CATALOG NUMBER: SA2XXDIP-C675D530U840-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.8	2.1
10°-20°	283.7	5.9
20°-30°	417.0	8.7
30°-40°	484.3	10.1
40°-50°	483.8	10.0
50°-60°	421.9	8.8
60°-70°	312.0	6.5
70°-80°	176.7	3.7
80°-90°	50.2	1.0
90°-100°	119.7	2.5
100°-110°	406.3	8.4
110°-120°	431.7	9.0
120°-130°	355.4	7.4
130°-140°	285.4	5.9
140°-150°	215.7	4.5
150°-160°	151.6	3.1
160°-170°	89.2	1.9
170°-180°	29.0	0.6
0°-30°	801.5	16.6
0°-40°	1285.8	26.7
0°-60°	2191.5	45.5
0°-90°	2730.4	56.7
90°-120°	957.8	19.9
90°-150°	1814.1	37.7
90°-180°	2084.0	43.3
0°-180°	4814.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1072	1072	1072	1072	1072	
5°	1072	1068	1057	1064	1063	102
15°	1021	1014	1001	1005	1000	287
25°	924	915	898	900	898	425
35°	797	786	770	764	759	497
45°	648	641	626	615	610	500
55°	491	484	472	460	455	439
65°	331	324	314	305	300	327
75°	173	171	166	160	162	185
85°	42	41	40	37	36	48
90°	1	8	20	19	19	3
95°	20	50	226	85	66	21
105°	70	106	427	763	649	75
115°	124	156	357	737	854	123
125°	173	204	343	597	693	153
135°	203	242	339	502	574	157
145°	232	266	338	419	458	145
155°	263	284	328	371	385	121
165°	287	295	314	333	338	81
175°	299	299	302	306	305	28
180°	299	299	299	299	299	



TEST NUMBER: P331347-840

CATALOG NUMBER: SA2XXDIP-C675D530U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1072.2	1072.2	1072.2	1072.2	1072.2	1072.2	1072.2	1072.2	1072.2	1072.2	1072.2
2.5°	1077.1	1076.2	1075.3	1074.4	1073.5	1072.0	1070.0	1067.9	1065.9	1063.9	1065.7
5°	1072.2	1071.3	1070.4	1069.4	1068.5	1066.8	1064.3	1061.8	1059.2	1056.7	1058.5
7.5°	1062.7	1061.3	1059.9	1058.4	1057.0	1055.0	1052.5	1049.9	1047.3	1044.7	1046.5
10°	1053.6	1052.0	1050.4	1048.7	1047.2	1045.0	1042.3	1039.6	1036.7	1034.0	1035.8
12.5°	1041.3	1039.9	1038.3	1036.9	1035.5	1033.5	1030.7	1027.9	1025.2	1022.5	1023.8
15°	1020.6	1019.3	1017.8	1016.5	1015.1	1012.9	1010.0	1006.9	1004.0	1001.0	1002.0
17.5°	994.2	992.8	991.5	990.1	988.8	986.5	983.5	980.5	977.4	974.4	975.5
20°	975.2	973.9	972.5	971.1	969.8	967.5	964.2	961.1	957.9	954.6	955.3
22.5°	956.2	954.3	952.4	950.5	948.6	946.1	943.1	940.1	937.1	934.0	934.1
25°	923.7	921.9	920.1	918.2	916.4	913.5	909.6	905.7	901.8	898.0	898.4
27.5°	886.6	884.9	883.3	881.6	880.0	877.7	874.5	871.5	868.4	865.4	864.6
30°	861.8	860.0	858.2	856.4	854.5	851.9	848.5	845.1	841.6	838.2	837.5
32.5°	835.5	833.9	832.5	831.0	829.6	827.1	823.4	819.8	816.2	812.5	811.3
35°	796.9	794.7	792.3	790.0	787.7	784.8	781.1	777.4	773.8	770.1	768.7
37.5°	753.4	751.3	749.3	747.3	745.4	742.5	738.8	735.2	731.5	727.8	726.1
40°	723.7	721.9	720.0	718.2	716.4	713.7	709.9	706.3	702.7	698.9	696.9
42.5°	694.9	693.0	691.2	689.3	687.5	684.8	681.1	677.4	673.8	670.1	667.8
45°	648.4	646.8	645.2	643.7	642.1	639.5	636.1	632.7	629.2	625.8	623.3
47.5°	602.3	600.8	599.3	597.7	596.2	593.7	590.1	586.5	583.0	579.4	576.7
50°	570.1	569.0	567.8	566.6	565.5	563.3	560.2	556.9	553.7	550.5	547.3
52.5°	538.8	537.2	535.7	534.2	532.7	530.5	527.5	524.4	521.4	518.4	515.7
55°	490.7	489.4	488.0	486.6	485.2	483.1	480.4	477.7	474.9	472.2	469.4
57.5°	442.4	441.4	440.3	439.2	438.1	436.1	433.0	430.0	427.0	423.9	421.2
60°	410.3	409.4	408.5	407.6	406.7	404.6	401.4	398.2	395.0	391.7	389.2
62.5°	379.0	377.5	376.1	374.6	373.1	371.1	368.7	366.2	363.8	361.2	358.9
65°	330.9	329.5	328.2	326.8	325.4	323.6	321.3	319.0	316.7	314.5	312.4
67.5°	282.1	280.9	279.8	278.7	277.6	276.1	274.0	272.0	269.9	267.8	266.2
70°	251.6	250.6	249.7	248.8	247.9	246.4	244.3	242.3	240.2	238.1	236.5
72.5°	220.3	219.2	218.3	217.4	216.5	215.4	214.1	212.8	211.5	210.1	208.5
75°	173.2	172.7	172.3	171.8	171.4	170.6	169.5	168.2	167.1	166.0	164.6
77.5°	131.2	130.4	129.6	128.8	128.1	127.4	126.9	126.4	126.0	125.5	124.9
80°	103.1	102.9	102.6	102.4	102.2	101.8	101.4	100.9	100.5	100.0	99.3
82.5°	76.7	76.6	76.6	76.5	76.5	76.3	76.0	75.8	75.5	75.2	74.4
85°	42.3	42.0	41.8	41.6	41.3	41.1	40.9	40.7	40.4	40.2	39.5
87.5°	14.9	14.9	15.0	14.9	14.7	14.7	14.9	15.3	15.8	15.5	14.8
90°	0.6	2.3	4.6	5.8	6.9	8.7	11.5	15.6	19.0	19.6	19.0
92.5°	7.1	10.1	14.2	16.9	20.7	26.2	39.2	57.5	73.8	74.8	63.2
95°	20.2	22.4	28.2	33.4	42.6	56.5	82.9	133.0	199.9	225.8	197.5
97.5°	32.8	36.0	42.0	49.9	60.5	76.1	109.5	179.3	290.2	385.4	404.2
100°	44.3	46.0	51.3	60.5	72.0	88.2	118.7	188.9	313.3	454.9	537.9
102.5°	54.9	56.2	61.4	70.6	82.6	98.7	126.9	189.3	304.6	457.3	587.6
105°	70.3	72.6	76.5	85.2	97.9	114.0	141.1	192.4	287.4	426.8	580.0
107.5°	86.8	88.7	92.6	100.6	113.1	129.4	155.6	200.3	278.8	394.0	529.4
110°	97.9	100.2	103.7	111.2	123.2	140.0	165.3	206.7	277.0	378.4	497.6



TEST NUMBER: P331347-840

CATALOG NUMBER: SA2XXDIP-C675D530U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	108.1	110.4	114.2	121.3	132.9	150.1	174.5	213.7	277.5	368.2	475.4
115°	123.8	126.7	130.2	137.0	148.6	164.1	188.9	224.0	279.9	357.1	448.1
117.5°	140.2	142.5	145.9	152.1	163.1	179.3	202.2	235.1	284.1	351.6	430.8
120°	150.3	152.6	156.0	161.3	172.8	188.9	211.4	242.5	286.8	348.4	421.6
122.5°	160.0	161.9	165.3	171.0	182.5	199.0	220.2	248.9	290.0	346.6	413.7
125°	172.8	174.5	177.9	184.9	196.4	212.5	233.3	259.1	294.9	343.3	402.5
127.5°	182.9	185.2	190.1	197.6	208.7	225.3	245.5	268.7	299.8	341.3	392.2
130°	188.9	191.2	196.9	205.0	216.5	232.7	252.9	274.7	303.5	340.3	385.3
132.5°	194.4	197.2	203.4	212.0	223.9	240.0	259.2	280.7	307.2	339.9	379.7
135°	202.7	205.0	212.0	220.6	233.8	249.9	268.4	288.5	311.5	339.2	372.0
137.5°	210.6	213.3	220.3	229.4	242.6	257.5	275.8	294.5	315.5	339.1	366.6
140°	216.5	218.8	225.8	235.0	247.6	262.7	279.9	297.7	317.3	338.6	363.5
142.5°	222.6	224.4	230.9	240.0	252.3	266.3	283.2	300.5	318.7	338.6	360.2
145°	231.6	233.8	239.5	248.2	259.7	272.4	287.9	304.1	320.2	337.5	355.9
147.5°	241.2	242.9	248.4	256.4	266.0	277.2	291.9	306.1	320.6	335.4	351.5
150°	247.6	249.3	254.0	261.5	270.1	280.4	293.7	307.0	320.2	334.1	347.9
152.5°	254.1	254.9	259.5	266.1	274.3	283.7	295.6	307.4	319.3	331.7	344.7
155°	263.2	263.8	267.2	273.6	279.9	288.5	298.3	308.1	317.9	327.7	338.6
157.5°	270.7	271.4	274.2	279.6	284.8	292.0	300.2	308.1	315.3	323.6	333.0
160°	275.9	276.4	278.7	283.4	287.9	294.3	301.2	308.1	313.9	320.8	328.8
162.5°	280.9	280.5	282.9	286.6	290.7	295.7	301.6	307.6	312.5	318.5	325.2
165°	286.8	286.2	287.4	290.8	293.7	297.2	302.4	306.4	309.8	313.9	319.0
167.5°	291.6	290.9	292.0	294.2	296.3	298.4	302.3	305.6	307.2	309.8	313.1
170°	294.9	293.7	294.3	296.0	297.2	298.9	301.7	304.7	305.8	307.5	309.8
172.5°	296.7	296.0	295.7	297.4	298.1	299.3	301.3	303.3	304.0	304.8	306.6
175°	298.9	298.3	297.7	298.9	298.9	299.4	300.6	301.7	301.2	301.7	302.4
177.5°	299.9	299.0	298.5	299.4	299.4	299.4	299.9	300.8	299.9	299.4	299.9
180°	299.4	299.4	299.4	299.4	299.4	299.4	299.4	299.4	299.4	299.4	299.4



TEST NUMBER: P331347-840

CATALOG NUMBER: SA2XXDIP-C675D530U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1072.2	1072.2	1072.2	1072.2	1072.2	1072.2	1072.2	1072.2
2.5°	1067.5	1069.4	1071.3	1072.0	1071.6	1071.3	1070.9	1070.6
5°	1060.4	1062.2	1064.0	1064.7	1064.3	1063.8	1063.4	1062.9
7.5°	1048.4	1050.3	1052.1	1052.7	1052.2	1051.8	1051.3	1050.8
10°	1037.6	1039.6	1041.4	1041.9	1041.3	1040.6	1039.9	1039.2
12.5°	1025.0	1026.3	1027.6	1027.9	1027.4	1027.0	1026.5	1026.0
15°	1002.9	1003.8	1004.7	1004.6	1003.4	1002.3	1001.2	1000.0
17.5°	976.5	977.5	978.7	978.7	977.5	976.4	975.3	974.2
20°	956.0	956.7	957.4	957.3	956.3	955.4	954.5	953.6
22.5°	934.3	934.4	934.5	934.3	933.8	933.2	932.7	932.2
25°	898.9	899.3	899.8	899.8	899.3	898.9	898.4	898.0
27.5°	863.9	863.3	862.6	861.7	860.6	859.5	858.4	857.3
30°	836.8	836.1	835.4	834.6	833.6	832.7	831.8	830.9
32.5°	810.1	808.9	807.6	806.6	805.7	804.8	803.8	802.8
35°	767.4	766.0	764.6	763.4	762.2	761.0	759.9	758.7
37.5°	724.5	722.8	721.0	719.6	718.5	717.4	716.4	715.3
40°	694.9	692.8	690.7	689.2	688.3	687.4	686.5	685.6
42.5°	665.6	663.4	661.2	659.3	658.0	656.8	655.5	654.2
45°	620.8	618.2	615.7	614.0	613.1	612.2	611.3	610.3
47.5°	574.1	571.4	568.8	566.7	565.4	564.1	562.8	561.5
50°	544.1	540.9	537.7	535.5	534.3	533.2	532.1	530.9
52.5°	513.0	510.4	507.8	505.6	504.1	502.6	501.1	499.6
55°	466.7	463.9	461.2	459.2	458.1	457.0	455.8	454.6
57.5°	418.5	415.8	413.1	411.3	410.4	409.6	408.7	407.8
60°	386.7	384.2	381.6	380.1	379.4	378.7	378.0	377.3
62.5°	356.6	354.3	351.9	350.3	349.4	348.5	347.7	346.8
65°	310.3	308.2	306.2	304.6	303.5	302.3	301.1	300.0
67.5°	264.6	263.1	261.5	260.1	259.2	258.3	257.4	256.5
70°	234.9	233.4	231.8	230.5	229.5	228.6	227.7	226.8
72.5°	206.9	205.3	203.7	202.5	201.8	201.1	200.4	199.5
75°	163.2	161.9	160.5	160.1	160.5	161.0	161.4	161.9
77.5°	124.2	123.5	122.8	122.2	121.5	120.9	120.3	119.6
80°	98.7	98.0	97.3	96.6	96.2	95.7	95.3	94.8
82.5°	73.5	72.6	71.8	71.3	71.2	71.1	71.0	70.9
85°	38.9	38.2	37.5	37.0	36.8	36.6	36.4	36.1
87.5°	14.1	13.3	13.0	12.8	12.6	12.4	12.2	12.0
90°	18.4	17.3	18.4	19.0	19.0	19.0	19.0	19.0
92.5°	50.2	43.1	38.3	34.6	34.2	32.4	32.8	31.9
95°	150.9	115.7	91.6	78.9	71.4	66.9	65.0	65.6
97.5°	352.1	288.1	225.8	184.2	156.6	142.5	134.1	129.3
100°	525.8	454.4	375.5	305.8	258.0	233.3	216.5	206.2
102.5°	639.6	623.5	565.8	491.9	440.0	397.7	376.9	362.8
105°	699.7	764.8	772.3	753.3	717.6	681.9	657.1	649.0
107.5°	656.4	754.5	814.4	842.2	846.7	844.8	839.8	829.1
110°	619.1	722.2	795.9	843.1	867.9	878.9	884.0	883.4



TEST NUMBER: P331347-840

CATALOG NUMBER: SA2XXDIP-C675D530U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	585.0	684.0	762.8	816.9	851.3	869.6	879.4	882.5
115°	543.1	631.8	707.2	766.6	807.4	833.9	848.9	854.0
117.5°	511.5	589.4	657.8	713.5	755.2	783.2	798.9	803.2
120°	495.8	567.2	628.3	680.8	721.0	748.1	764.8	770.5
122.5°	483.4	548.9	606.6	654.0	690.1	716.8	731.6	736.5
125°	465.3	524.6	575.3	618.5	652.0	673.8	688.2	692.9
127.5°	447.5	501.2	549.0	588.9	617.9	638.4	650.9	654.6
130°	436.0	485.5	531.0	569.0	597.2	616.8	628.3	632.9
132.5°	425.0	470.8	512.6	548.3	576.0	595.6	606.2	610.4
135°	409.5	447.5	485.5	517.8	542.5	561.5	571.9	574.2
137.5°	397.2	429.0	459.1	487.3	509.8	526.1	535.2	538.7
140°	389.3	417.0	443.4	468.8	487.3	502.2	510.8	514.3
142.5°	382.8	406.4	429.2	450.4	467.9	481.5	489.2	489.9
145°	373.8	392.7	410.6	427.4	441.1	450.9	456.7	458.4
147.5°	366.8	381.7	395.7	407.9	419.3	427.1	431.0	432.0
150°	361.6	374.4	386.5	396.8	405.5	412.3	415.8	416.4
152.5°	356.6	368.4	378.6	387.6	394.4	400.4	402.9	403.0
155°	349.6	358.8	367.4	373.8	380.1	384.2	386.5	385.3
157.5°	341.4	349.1	356.4	361.3	365.8	369.2	370.2	370.2
160°	336.3	342.6	349.0	353.0	357.1	359.9	360.5	360.5
162.5°	331.2	336.7	342.1	345.2	349.2	351.2	351.7	351.3
165°	323.7	327.7	331.7	334.1	336.3	338.6	338.6	338.1
167.5°	316.4	319.5	322.2	324.4	325.4	326.7	326.6	325.9
170°	312.8	314.5	316.8	317.9	318.5	320.2	319.6	318.5
172.5°	308.6	309.8	311.6	312.4	313.0	313.8	313.2	312.5
175°	304.1	304.7	305.3	305.8	305.8	306.4	305.8	304.7
177.5°	300.8	300.8	301.3	301.3	301.3	301.3	300.8	299.9
180°	299.4	299.4	299.4	299.4	299.4	299.4	299.4	299.4

(END OF REPORT)