

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331718-930

Luminaire Tested: **SA2XXRDIP-C865D725U930-4F0-1E-UDD-A1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331718-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C865D725U930-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 725 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4805.3 lumens
Efficiency: N/A
Efficacy: 88.3 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 54.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331718-930
CATALOG NUMBER: SA2XXRDIP-C865D725U930-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331718-930

CATALOG NUMBER: SA2XXRDIP-C865D725U930-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	56				56
1	100	96	92	89	93	89	86	84	77	75	73	66	65	63	56	55	54	49				49
2	92	85	79	74	85	79	74	70	69	65	62	59	56	54	50	48	47	42				42
3	84	75	69	63	78	71	65	60	62	57	53	53	50	47	45	43	41	37				37
4	78	68	60	54	72	63	57	52	55	50	46	48	44	41	41	38	36	33				33
5	72	61	53	47	67	57	50	45	50	45	41	44	40	36	38	35	32	29				29
6	67	55	47	42	62	52	45	40	46	40	36	40	36	32	35	31	29	26				26
7	62	50	42	37	58	47	40	35	42	36	32	37	32	29	32	29	26	24				24
8	58	46	38	33	54	43	37	32	38	33	29	34	30	26	30	26	24	22				22
9	54	42	35	30	50	40	33	29	36	30	26	31	27	24	28	24	22	20				20
10	51	39	32	27	47	37	30	26	33	28	24	29	25	22	26	22	20	18				18

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	25137	25137	25137	25137
5°	28075	25293	22428	25293
10°	31147	25117	19441	25117
15°	32679	24749	15318	24749
20°	28331	24204	13254	24204
25°	18579	23457	11834	23457
30°	12506	22551	10711	22551
35°	10129	21409	9660	21409
40°	9008	20168	8939	20168
45°	8152	18712	7978	18712
50°	7420	17269	7390	17269
55°	6975	15671	6883	15671
60°	5835	14202	5767	14202
65°	4917	12894	5578	12894
70°	4546	11514	5264	11514
75°	4255	10025	4860	10025
80°	3924	8247	4333	8247
85°	3612	6502	3798	6502



TEST NUMBER: P331718-930

CATALOG NUMBER: SA2XXRDIP-C865D725U930-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	147.6	3.1
10°-20°	411.2	8.6
20°-30°	529.9	11.0
30°-40°	503.6	10.5
40°-50°	431.4	9.0
50°-60°	328.5	6.8
60°-70°	207.7	4.3
70°-80°	103.7	2.2
80°-90°	30.0	0.6
90°-100°	47.9	1.0
100°-110°	148.6	3.1
110°-120°	254.0	5.3
120°-130°	334.1	7.0
130°-140°	375.0	7.8
140°-150°	367.7	7.7
150°-160°	308.4	6.4
160°-170°	204.5	4.3
170°-180°	71.5	1.5
0°-30°	1088.7	22.7
0°-40°	1592.3	33.1
0°-60°	2352.3	49.0
0°-90°	2693.7	56.1
90°-120°	450.5	9.4
90°-150°	1527.2	31.8
90°-180°	2112.0	44.0
0°-180°	4805.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1557	1557	1557	1557	1557	
5°	1732	1561	1384	1561	1732	171
15°	1955	1481	916	1481	1955	527
25°	1043	1317	664	1317	1043	495
35°	514	1086	490	1086	514	329
45°	357	820	349	820	357	276
55°	248	557	244	557	248	217
65°	129	338	146	338	129	131
75°	68	161	78	161	68	72
85°	20	35	20	35	20	21
90°	22	1	22	1	22	10
95°	40	33	40	33	40	44
105°	142	137	142	137	142	149
115°	255	255	255	255	255	252
125°	372	371	372	371	372	332
135°	486	480	486	480	486	374
145°	589	582	589	582	589	368
155°	671	666	671	666	671	309
165°	725	725	725	725	725	205
175°	751	754	751	754	751	71
180°	755	755	755	755	755	



TEST NUMBER: P331718-930

CATALOG NUMBER: SA2XXRDIP-C865D725U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9
2.5°	1620.1	1621.4	1622.7	1619.6	1619.6	1617.1	1611.4	1607.1	1595.0	1593.3	1593.3
5°	1732.2	1731.0	1733.2	1726.2	1716.4	1714.3	1704.1	1690.5	1676.4	1660.8	1657.5
7.5°	1843.6	1841.9	1837.6	1836.5	1829.0	1812.7	1796.1	1778.5	1755.1	1732.3	1720.8
10°	1899.8	1917.7	1906.9	1887.9	1891.7	1866.3	1852.8	1829.5	1810.0	1776.0	1768.4
12.5°	1955.3	1962.3	1958.8	1948.1	1943.3	1925.6	1907.3	1887.1	1851.1	1820.6	1793.9
15°	1955.0	1965.3	1968.0	1964.8	1967.5	1966.4	1956.6	1939.8	1908.5	1874.9	1845.8
17.5°	1810.7	1817.9	1835.6	1847.5	1862.7	1894.8	1910.6	1916.7	1912.0	1892.9	1872.3
20°	1648.9	1637.0	1686.7	1712.1	1733.7	1787.9	1834.4	1852.3	1880.9	1880.4	1874.9
22.5°	1419.4	1422.3	1469.5	1499.7	1562.8	1616.9	1670.0	1737.2	1792.6	1829.3	1850.7
25°	1042.9	1063.6	1110.6	1151.7	1222.1	1322.7	1414.1	1520.1	1620.2	1699.2	1774.3
27.5°	783.3	784.8	822.1	860.1	901.9	984.3	1099.4	1226.0	1368.7	1486.5	1621.9
30°	670.8	667.6	683.2	706.5	742.2	806.0	892.6	1017.0	1159.3	1336.7	1494.7
32.5°	591.2	591.3	603.2	620.4	650.0	693.1	752.4	853.5	987.9	1162.3	1347.5
35°	513.9	513.4	522.0	534.4	546.9	574.5	615.1	668.1	760.6	923.4	1112.7
37.5°	458.5	460.9	465.1	472.9	486.7	502.0	526.4	562.0	627.9	724.1	883.3
40°	427.4	428.4	434.4	440.9	449.0	460.9	480.9	509.6	557.7	634.5	750.8
42.5°	398.8	399.9	404.1	410.2	416.5	428.4	445.0	469.8	508.8	568.8	664.7
45°	357.0	357.0	360.9	363.5	370.6	381.4	394.9	415.5	442.5	486.9	550.7
47.5°	317.9	318.0	320.5	325.1	329.5	338.0	351.3	368.1	387.8	422.1	476.6
50°	295.4	295.9	297.5	301.3	304.0	311.6	321.9	336.5	357.0	383.5	429.0
52.5°	277.2	276.9	278.9	280.5	282.4	287.8	295.5	308.3	326.8	349.8	387.4
55°	247.8	245.6	248.8	251.5	253.2	255.4	259.7	267.7	283.5	303.0	331.1
57.5°	211.0	210.1	212.4	214.8	220.0	225.8	229.5	234.6	242.8	256.7	284.6
60°	180.7	180.7	185.6	187.2	193.1	200.7	208.3	212.6	220.7	229.9	250.5
62.5°	153.8	154.3	156.5	158.2	161.5	170.8	181.4	190.9	198.6	207.4	221.0
65°	128.7	129.8	129.8	130.9	133.1	135.3	139.6	147.2	160.7	173.1	183.4
67.5°	109.3	109.6	109.9	111.0	111.5	113.9	115.7	119.0	122.1	134.0	146.7
70°	96.3	97.9	97.3	98.5	99.0	100.0	102.2	103.9	108.8	111.5	119.0
72.5°	84.1	85.4	85.3	85.9	87.3	87.6	89.3	90.9	94.0	96.3	100.4
75°	68.2	67.6	68.2	69.2	69.8	70.4	70.4	72.5	74.1	76.3	79.0
77.5°	52.6	53.2	53.0	53.2	53.2	54.2	54.1	55.0	56.7	57.8	59.1
80°	42.2	42.7	42.2	42.7	43.3	43.8	43.3	43.8	45.4	46.6	46.6
82.5°	32.7	32.8	33.1	33.2	33.3	33.4	34.2	34.3	35.5	35.3	35.7
85°	19.5	18.9	18.9	18.9	19.5	20.0	19.5	19.5	20.0	20.0	20.0
87.5°	11.3	11.7	11.7	11.6	11.6	11.6	11.7	12.1	11.7	12.2	11.2
90°	21.7	21.5	21.4	21.3	21.1	21.2	21.4	21.8	22.0	22.3	19.2
92.5°	20.6	20.6	20.6	20.5	20.5	20.5	20.5	20.4	20.3	20.3	19.6
95°	39.5	39.8	40.1	40.4	40.7	40.8	40.8	40.8	40.8	40.8	40.5
97.5°	68.4	68.5	68.5	68.6	68.6	68.6	68.6	68.6	68.6	68.6	68.0
100°	87.3	87.5	87.6	87.7	87.9	88.0	88.0	88.0	88.0	88.0	87.5
102.5°	108.7	108.8	109.0	109.2	109.3	109.3	109.2	109.1	108.9	108.8	108.3
105°	141.5	141.5	141.5	141.5	141.5	141.4	141.0	140.8	140.5	140.2	139.9
107.5°	172.4	173.0	173.7	174.3	175.0	175.2	175.0	175.0	174.9	174.7	174.7
110°	196.2	196.7	197.1	197.5	198.0	198.2	198.2	198.2	198.2	198.2	198.2



TEST NUMBER: P331718-930

CATALOG NUMBER: SA2XXRDIP-C865D725U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	219.2	219.6	219.8	220.1	220.5	220.8	221.1	221.4	221.8	222.2	222.3
115°	254.9	255.4	255.8	256.2	256.6	256.9	257.1	257.1	257.3	257.5	257.7
117.5°	288.9	289.3	289.8	290.2	290.7	291.0	291.4	291.7	292.0	292.4	293.2
120°	312.9	313.3	313.7	314.1	314.6	314.8	314.8	314.8	314.8	314.8	315.9
122.5°	336.4	336.6	337.0	337.3	337.6	337.9	338.3	338.6	338.9	339.2	340.1
125°	372.2	372.3	372.4	372.6	372.8	373.0	373.4	373.9	374.3	374.7	375.1
127.5°	404.8	405.3	405.7	406.2	406.6	407.1	407.6	408.1	408.6	409.1	409.6
130°	428.3	428.8	429.4	429.9	430.5	431.0	431.2	431.5	431.8	432.1	432.4
132.5°	450.7	451.1	451.6	452.0	452.5	453.1	453.6	454.3	454.9	455.5	455.4
135°	485.6	486.0	486.5	486.9	487.3	487.5	487.7	487.9	488.0	488.1	487.9
137.5°	517.2	517.8	518.4	518.9	519.5	519.8	519.9	520.1	520.2	520.2	519.9
140°	539.2	539.7	540.3	540.9	541.4	541.7	541.7	541.7	541.7	541.7	541.0
142.5°	559.1	559.6	560.1	560.7	561.3	561.5	561.4	561.3	561.2	561.1	560.6
145°	588.8	589.4	590.0	590.5	591.1	591.3	591.2	591.0	590.9	590.8	589.9
147.5°	615.5	616.0	616.5	617.1	617.7	617.8	617.4	617.1	616.8	616.5	616.0
150°	632.8	633.2	633.7	634.1	634.5	634.5	634.1	633.7	633.2	632.8	632.3
152.5°	649.1	649.6	650.2	650.8	651.3	651.3	650.8	650.2	649.6	649.1	648.4
155°	671.1	671.5	671.9	672.3	672.8	672.6	671.9	671.2	670.5	669.8	669.4
157.5°	689.9	690.6	691.3	691.9	692.6	692.5	691.5	690.6	689.6	688.6	688.4
160°	701.6	702.2	702.8	703.4	703.9	703.8	703.0	702.1	701.2	700.3	700.3
162.5°	711.8	712.5	713.2	713.9	714.5	714.4	713.5	712.5	711.5	710.5	710.5
165°	725.2	725.9	726.6	727.3	728.1	727.9	726.9	725.9	725.0	723.9	723.9
167.5°	736.2	736.9	737.7	738.4	739.2	739.0	738.0	737.0	736.1	735.0	735.1
170°	741.8	742.7	743.5	744.4	745.2	745.1	744.1	743.1	742.2	741.1	741.3
172.5°	746.4	747.2	748.0	748.9	749.7	749.7	748.7	747.7	746.7	745.8	745.9
175°	751.4	752.2	753.0	753.9	754.7	754.6	753.7	752.7	751.7	750.7	751.0
177.5°	753.7	754.3	755.0	755.7	756.4	756.4	755.7	755.0	754.3	753.7	753.8
180°	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1



TEST NUMBER: P331718-930

CATALOG NUMBER: SA2XXRDIP-C865D725U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9
2.5°	1594.1	1590.6	1587.6	1579.8	1575.9	1567.2	1565.9	1565.5	1554.3	1543.4	1540.4
5°	1648.9	1640.2	1627.2	1612.1	1596.4	1580.1	1569.3	1560.6	1539.0	1518.5	1506.6
7.5°	1704.1	1685.4	1663.0	1634.3	1610.5	1583.6	1563.7	1545.8	1515.2	1485.7	1465.9
10°	1745.1	1714.8	1685.1	1645.6	1614.8	1584.5	1556.3	1532.0	1497.4	1458.4	1430.9
12.5°	1770.7	1737.3	1696.3	1657.7	1617.8	1579.2	1541.6	1510.3	1469.7	1429.5	1396.6
15°	1805.2	1769.4	1719.7	1664.5	1613.2	1562.8	1519.6	1480.6	1427.6	1379.4	1339.4
17.5°	1833.4	1784.3	1730.9	1667.0	1607.5	1543.6	1487.8	1438.1	1379.1	1321.0	1273.8
20°	1842.5	1793.8	1732.2	1668.3	1598.0	1522.8	1462.7	1408.7	1345.3	1282.1	1228.0
22.5°	1836.9	1799.0	1730.4	1654.0	1582.0	1503.3	1435.5	1372.7	1302.5	1238.0	1175.2
25°	1798.7	1785.7	1720.8	1637.4	1555.3	1463.9	1385.4	1316.7	1236.6	1167.4	1099.2
27.5°	1709.7	1737.6	1697.5	1608.7	1517.3	1419.3	1331.1	1252.9	1169.8	1091.8	1023.9
30°	1624.0	1688.3	1671.0	1588.8	1486.5	1390.2	1291.3	1209.6	1120.9	1040.8	973.7
32.5°	1506.7	1613.0	1629.9	1561.1	1455.4	1349.6	1245.9	1164.6	1072.0	987.6	922.2
35°	1320.0	1479.0	1552.0	1508.2	1402.2	1288.0	1180.9	1086.2	993.2	909.9	845.0
37.5°	1097.1	1313.8	1435.5	1438.6	1341.2	1222.5	1106.0	1011.9	916.7	834.9	764.7
40°	952.6	1187.4	1345.9	1381.0	1298.9	1170.6	1052.7	956.9	863.9	783.8	703.3
42.5°	822.8	1056.7	1251.6	1312.7	1247.3	1120.0	1001.7	901.6	811.1	735.4	653.1
45°	665.4	869.8	1084.6	1193.9	1157.6	1039.8	914.8	819.5	734.6	669.2	590.2
47.5°	561.3	705.4	913.2	1061.0	1060.4	952.8	829.8	738.7	659.8	598.5	534.6
50°	502.0	627.5	803.3	971.0	985.0	894.7	777.9	687.5	614.0	549.6	498.2
52.5°	448.7	552.2	710.3	871.1	911.1	832.8	719.5	636.1	564.7	505.5	461.5
55°	379.2	459.3	579.4	729.8	790.4	735.2	634.5	556.7	498.8	449.0	411.2
57.5°	320.8	380.8	477.2	598.3	668.9	634.1	551.1	487.9	438.3	393.3	363.4
60°	284.0	333.2	414.9	516.1	593.9	569.6	498.8	439.8	397.6	358.7	330.5
62.5°	249.4	291.7	361.7	443.8	515.2	505.2	447.3	397.8	360.9	325.3	301.5
65°	200.7	231.5	286.2	350.6	407.9	412.8	371.1	337.5	304.6	276.5	255.4
67.5°	159.8	179.9	218.4	272.6	315.6	330.9	305.5	279.9	253.7	232.0	213.7
70°	134.7	150.9	179.0	222.9	262.4	278.6	264.0	243.9	221.3	203.4	187.7
72.5°	109.2	125.0	145.7	177.9	211.7	229.3	224.2	209.8	191.4	176.6	161.8
75°	82.3	87.1	101.2	122.8	149.3	164.4	168.3	160.7	146.0	134.7	126.0
77.5°	60.8	63.8	70.4	81.8	99.1	112.6	118.1	117.2	107.2	100.6	92.5
80°	48.7	50.3	53.6	58.5	71.4	85.0	88.7	88.7	81.7	79.0	70.8
82.5°	37.0	38.2	40.1	42.8	48.9	60.7	64.9	65.8	61.3	57.8	51.4
85°	21.1	20.5	21.6	23.2	24.4	27.6	34.1	35.1	34.1	29.8	28.1
87.5°	10.6	10.4	9.8	8.8	9.0	9.0	10.8	12.6	11.3	10.4	9.8
90°	16.1	13.0	9.9	7.4	5.7	4.1	2.4	0.7	2.4	4.1	5.7
92.5°	18.8	18.0	17.3	16.3	15.1	13.9	12.6	11.3	12.6	13.9	15.1
95°	40.2	39.9	39.6	38.8	37.4	36.0	34.6	33.1	34.6	36.0	37.4
97.5°	67.5	66.9	66.4	65.6	64.2	63.0	61.8	60.6	61.8	63.0	64.2
100°	87.1	86.7	86.3	85.4	84.3	83.2	82.1	81.0	82.1	83.2	84.3
102.5°	107.8	107.2	106.7	106.0	105.1	104.2	103.2	102.3	103.2	104.2	105.1
105°	139.7	139.3	139.1	138.7	138.3	137.9	137.5	137.1	137.5	137.9	138.3
107.5°	174.7	174.7	174.7	174.4	173.8	173.2	172.6	171.9	172.6	173.2	173.8
110°	198.2	198.2	198.2	197.8	196.9	196.1	195.2	194.4	195.2	196.1	196.9



TEST NUMBER: P331718-930

CATALOG NUMBER: SA2XXRDIP-C865D725U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	222.4	222.5	222.6	222.3	221.4	220.5	219.7	218.8	219.7	220.5	221.4
115°	258.0	258.3	258.6	258.3	257.5	256.6	255.8	254.9	255.8	256.6	257.5
117.5°	294.0	294.7	295.5	295.4	294.2	293.1	292.0	290.8	292.0	293.1	294.2
120°	317.1	318.2	319.4	319.4	318.2	317.1	315.9	314.8	315.9	317.1	318.2
122.5°	340.9	341.7	342.4	342.2	340.8	339.5	338.1	336.7	338.1	339.5	340.8
125°	375.5	376.0	376.4	376.0	374.7	373.4	372.2	370.9	372.2	373.4	374.7
127.5°	410.2	410.7	411.2	410.6	409.0	407.4	405.8	404.1	405.8	407.4	409.0
130°	432.6	432.9	433.2	432.4	430.6	428.8	426.9	425.1	426.9	428.8	430.6
132.5°	455.4	455.3	455.3	454.5	453.0	451.5	450.0	448.5	450.0	451.5	453.0
135°	487.5	487.3	487.0	486.1	484.5	483.0	481.4	479.9	481.4	483.0	484.5
137.5°	519.5	519.2	518.8	518.0	516.7	515.4	514.1	512.9	514.1	515.4	516.7
140°	540.3	539.6	538.8	537.9	536.5	535.3	534.0	532.8	534.0	535.3	536.5
142.5°	560.1	559.6	559.1	558.2	557.0	555.7	554.4	553.2	554.4	555.7	557.0
145°	589.1	588.2	587.3	586.4	585.5	584.5	583.4	582.4	583.4	584.5	585.5
147.5°	615.4	614.8	614.2	613.3	612.1	611.0	609.8	608.6	609.8	611.0	612.1
150°	631.7	631.1	630.6	629.8	629.0	628.1	627.3	626.5	627.3	628.1	629.0
152.5°	647.8	647.1	646.4	645.6	644.8	643.9	643.1	642.2	643.1	643.9	644.8
155°	669.0	668.5	668.1	667.6	667.2	666.8	666.3	665.9	666.3	666.8	667.2
157.5°	688.1	687.9	687.6	687.4	687.1	686.8	686.5	686.2	686.5	686.8	687.1
160°	700.1	699.9	699.8	699.6	699.3	699.0	698.7	698.5	698.7	699.0	699.3
162.5°	710.3	710.1	710.0	709.9	709.8	709.8	709.7	709.6	709.7	709.8	709.8
165°	723.9	723.9	723.9	724.0	724.1	724.3	724.5	724.6	724.5	724.3	724.1
167.5°	735.1	735.2	735.2	735.4	735.8	736.2	736.6	737.0	736.6	736.2	735.8
170°	741.4	741.6	741.7	742.0	742.4	742.8	743.3	743.7	743.3	742.8	742.4
172.5°	746.0	746.2	746.3	746.6	747.0	747.5	747.9	748.3	747.9	747.5	747.0
175°	751.3	751.5	751.9	752.2	752.6	753.0	753.5	753.9	753.5	753.0	752.6
177.5°	754.1	754.3	754.6	754.8	755.1	755.5	755.9	756.2	755.9	755.5	755.1
180°	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1



TEST NUMBER: P331718-930

CATALOG NUMBER: SA2XXRDIP-C865D725U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9
2.5°	1534.8	1531.8	1526.2	1517.5	1512.3	1503.2	1497.1	1500.6	1501.5	1500.6	1499.7
5°	1493.5	1482.2	1466.6	1451.4	1437.3	1422.2	1413.5	1409.7	1402.2	1397.8	1395.7
7.5°	1443.7	1424.2	1401.9	1375.6	1353.2	1329.7	1317.7	1311.7	1296.2	1287.8	1280.4
10°	1406.5	1375.7	1353.5	1318.8	1297.8	1266.9	1245.9	1246.3	1225.2	1213.3	1204.7
12.5°	1365.4	1331.5	1294.6	1263.5	1234.1	1209.3	1184.0	1173.6	1151.3	1139.8	1116.4
15°	1297.2	1257.8	1218.8	1176.6	1146.8	1108.4	1071.6	1026.7	990.5	959.1	950.5
17.5°	1222.8	1173.9	1134.8	1085.2	1034.3	969.7	927.1	901.0	879.1	862.6	850.3
20°	1171.7	1121.9	1080.3	1005.7	936.9	893.2	861.8	841.7	819.0	801.2	791.4
22.5°	1118.0	1066.1	1009.3	926.0	872.5	837.3	809.3	786.4	770.9	757.0	748.1
25°	1041.9	985.0	891.5	834.1	790.8	754.1	734.6	720.6	704.3	685.4	676.7
27.5°	961.4	871.1	803.9	761.2	719.9	696.0	678.5	657.5	642.9	634.5	625.4
30°	901.2	810.9	758.4	711.9	682.7	656.2	635.6	623.7	609.7	595.1	589.1
32.5°	834.1	762.0	711.7	672.9	643.3	620.7	604.5	585.2	575.0	566.1	553.6
35°	750.8	696.2	650.2	618.9	590.8	572.3	553.4	542.0	523.7	516.1	511.2
37.5°	680.3	632.9	598.6	565.5	543.2	522.9	511.3	493.3	485.3	474.7	464.5
40°	640.5	593.9	561.0	533.9	509.1	493.9	479.3	464.7	452.8	447.9	435.5
42.5°	599.8	562.0	529.0	499.3	482.7	466.6	448.2	437.4	425.1	417.2	409.5
45°	543.6	510.1	482.0	457.6	439.3	422.5	410.6	392.7	385.7	370.0	363.5
47.5°	494.3	463.2	436.3	413.2	395.3	384.3	366.9	352.9	341.7	332.1	323.7
50°	459.3	433.3	407.3	386.8	370.6	354.9	337.0	330.0	312.7	307.8	303.0
52.5°	427.2	402.6	378.8	358.7	342.4	327.2	311.4	302.3	290.6	285.8	282.2
55°	382.5	358.7	335.9	318.0	301.8	286.2	276.5	265.1	259.7	255.8	251.5
57.5°	337.5	316.0	298.6	280.5	264.2	251.8	240.5	233.7	228.0	223.1	217.9
60°	308.9	288.3	272.6	255.8	239.1	228.9	220.1	212.1	205.5	198.0	195.8
62.5°	278.6	260.7	246.2	229.9	215.3	205.9	197.6	190.0	182.2	171.1	168.1
65°	236.9	222.9	207.7	194.2	181.2	172.0	160.1	151.5	148.2	147.2	146.6
67.5°	199.3	186.0	173.0	159.1	147.3	138.8	132.7	131.4	129.1	128.5	127.0
70°	174.1	161.8	148.8	135.7	124.4	122.8	120.7	118.5	115.8	114.7	113.6
72.5°	151.6	138.8	125.8	115.4	110.6	108.5	106.3	104.2	102.3	101.3	100.6
75°	116.3	104.4	95.7	92.0	89.3	87.6	84.4	82.8	81.7	80.1	79.5
77.5°	83.7	77.0	73.1	70.7	67.8	66.1	64.2	62.6	61.5	61.1	60.3
80°	63.8	60.6	57.9	54.6	53.6	51.4	50.9	49.2	49.7	48.2	48.2
82.5°	49.6	45.4	43.1	41.7	40.6	38.8	38.3	37.5	37.7	36.4	36.4
85°	25.4	24.4	23.2	22.2	22.2	20.5	21.1	20.5	20.5	19.5	18.9
87.5°	9.7	9.8	9.5	10.1	10.8	10.9	10.9	10.4	10.4	10.3	9.9
90°	7.4	9.9	13.0	16.1	19.2	22.3	22.0	21.8	21.4	21.2	21.1
92.5°	16.3	17.3	18.0	18.8	19.6	20.3	20.3	20.4	20.5	20.5	20.5
95°	38.8	39.6	39.9	40.2	40.5	40.8	40.8	40.8	40.8	40.8	40.7
97.5°	65.6	66.4	66.9	67.5	68.0	68.6	68.6	68.6	68.6	68.6	68.6
100°	85.4	86.3	86.7	87.1	87.5	88.0	88.0	88.0	88.0	88.0	87.9
102.5°	106.0	106.7	107.2	107.8	108.3	108.8	108.9	109.1	109.2	109.3	109.3
105°	138.7	139.1	139.3	139.7	139.9	140.2	140.5	140.8	141.0	141.4	141.5
107.5°	174.4	174.7	174.7	174.7	174.7	174.7	174.9	175.0	175.0	175.2	175.0
110°	197.8	198.2	198.2	198.2	198.2	198.2	198.2	198.2	198.2	198.2	198.0



TEST NUMBER: P331718-930

CATALOG NUMBER: SA2XXRDIP-C865D725U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	222.3	222.6	222.5	222.4	222.3	222.2	221.8	221.4	221.1	220.8	220.5
115°	258.3	258.6	258.3	258.0	257.7	257.5	257.3	257.1	257.1	256.9	256.6
117.5°	295.4	295.5	294.7	294.0	293.2	292.4	292.0	291.7	291.4	291.0	290.7
120°	319.4	319.4	318.2	317.1	315.9	314.8	314.8	314.8	314.8	314.8	314.6
122.5°	342.2	342.4	341.7	340.9	340.1	339.2	338.9	338.6	338.3	337.9	337.6
125°	376.0	376.4	376.0	375.5	375.1	374.7	374.3	373.9	373.4	373.0	372.8
127.5°	410.6	411.2	410.7	410.2	409.6	409.1	408.6	408.1	407.6	407.1	406.6
130°	432.4	433.2	432.9	432.6	432.4	432.1	431.8	431.5	431.2	431.0	430.5
132.5°	454.5	455.3	455.3	455.4	455.4	455.5	454.9	454.3	453.6	453.1	452.5
135°	486.1	487.0	487.3	487.5	487.9	488.1	488.0	487.9	487.7	487.5	487.3
137.5°	518.0	518.8	519.2	519.5	519.9	520.2	520.2	520.1	519.9	519.8	519.5
140°	537.9	538.8	539.6	540.3	541.0	541.7	541.7	541.7	541.7	541.7	541.4
142.5°	558.2	559.1	559.6	560.1	560.6	561.1	561.2	561.3	561.4	561.5	561.3
145°	586.4	587.3	588.2	589.1	589.9	590.8	590.9	591.0	591.2	591.3	591.1
147.5°	613.3	614.2	614.8	615.4	616.0	616.5	616.8	617.1	617.4	617.8	617.7
150°	629.8	630.6	631.1	631.7	632.3	632.8	633.2	633.7	634.1	634.5	634.5
152.5°	645.6	646.4	647.1	647.8	648.4	649.1	649.6	650.2	650.8	651.3	651.3
155°	667.6	668.1	668.5	669.0	669.4	669.8	670.5	671.2	671.9	672.6	672.8
157.5°	687.4	687.6	687.9	688.1	688.4	688.6	689.6	690.6	691.5	692.5	692.6
160°	699.6	699.8	699.9	700.1	700.3	700.3	701.2	702.1	703.0	703.8	703.9
162.5°	709.9	710.0	710.1	710.3	710.5	710.5	711.5	712.5	713.5	714.4	714.5
165°	724.0	723.9	723.9	723.9	723.9	723.9	725.0	725.9	726.9	727.9	728.1
167.5°	735.4	735.2	735.2	735.1	735.1	735.0	736.1	737.0	738.0	739.0	739.2
170°	742.0	741.7	741.6	741.4	741.3	741.1	742.2	743.1	744.1	745.1	745.2
172.5°	746.6	746.3	746.2	746.0	745.9	745.8	746.7	747.7	748.7	749.7	749.7
175°	752.2	751.9	751.5	751.3	751.0	750.7	751.7	752.7	753.7	754.6	754.7
177.5°	754.8	754.6	754.3	754.1	753.8	753.7	754.3	755.0	755.7	756.4	756.4
180°	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1



TEST NUMBER: P331718-930
 CATALOG NUMBER: SA2XXRDIP-C865D725U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9
2.5°	1495.0	1495.8	1494.5	1495.4	1494.5	1495.8	1495.0	1499.7	1500.6	1501.5	1500.6
5°	1392.9	1386.5	1385.4	1383.8	1385.4	1386.5	1392.9	1395.7	1397.8	1402.2	1409.7
7.5°	1271.1	1270.2	1267.5	1263.7	1267.5	1270.2	1271.1	1280.4	1287.8	1296.2	1311.7
10°	1192.8	1190.1	1189.6	1185.8	1189.6	1190.1	1192.8	1204.7	1213.3	1225.2	1246.3
12.5°	1101.1	1083.6	1081.8	1072.4	1081.8	1083.6	1101.1	1116.4	1139.8	1151.3	1173.6
15°	937.5	934.3	923.4	916.4	923.4	934.3	937.5	950.5	959.1	990.5	1026.7
17.5°	844.0	833.4	830.1	828.5	830.1	833.4	844.0	850.3	862.6	879.1	901.0
20°	783.8	774.1	772.5	771.4	772.5	774.1	783.8	791.4	801.2	819.0	841.7
22.5°	742.3	732.1	727.9	724.6	727.9	732.1	742.3	748.1	757.0	770.9	786.4
25°	671.3	667.6	665.4	664.3	665.4	667.6	671.3	676.7	685.4	704.3	720.6
27.5°	615.8	607.5	605.8	603.1	605.8	607.5	615.8	625.4	634.5	642.9	657.5
30°	584.2	581.6	577.7	574.5	577.7	581.6	584.2	589.1	595.1	609.7	623.7
32.5°	547.0	544.8	541.4	539.9	541.4	544.8	547.0	553.6	566.1	575.0	585.2
35°	505.8	498.2	495.0	490.1	495.0	498.2	505.8	511.2	516.1	523.7	542.0
37.5°	462.2	458.2	453.6	455.3	453.6	458.2	462.2	464.5	474.7	485.3	493.3
40°	428.4	425.7	424.7	424.1	424.7	425.7	428.4	435.5	447.9	452.8	464.7
42.5°	401.6	394.1	391.3	391.2	391.3	394.1	401.6	409.5	417.2	425.1	437.4
45°	360.9	353.8	348.9	349.4	348.9	353.8	360.9	363.5	370.0	385.7	392.7
47.5°	319.0	318.9	315.8	316.8	315.8	318.9	319.0	323.7	332.1	341.7	352.9
50°	299.1	295.9	293.8	294.2	293.8	295.9	299.1	303.0	307.8	312.7	330.0
52.5°	280.1	277.3	275.6	277.9	275.6	277.3	280.1	282.2	285.8	290.6	302.3
55°	248.8	245.6	245.1	244.5	245.1	245.6	248.8	251.5	255.8	259.7	265.1
57.5°	213.9	211.7	208.5	207.1	208.5	211.7	213.9	217.9	223.1	228.0	233.7
60°	188.8	184.5	179.0	178.6	179.0	184.5	188.8	195.8	198.0	205.5	212.1
62.5°	165.8	165.0	163.9	163.8	163.9	165.0	165.8	168.1	171.1	182.2	190.0
65°	145.5	145.0	145.5	146.0	145.5	145.0	145.5	146.6	147.2	148.2	151.5
67.5°	126.8	125.8	124.8	125.3	124.8	125.8	126.8	127.0	128.5	129.1	131.4
70°	112.5	111.9	111.5	111.5	111.5	111.9	112.5	113.6	114.7	115.8	118.5
72.5°	98.7	98.6	98.0	97.6	98.0	98.6	98.7	100.6	101.3	102.3	104.2
75°	79.0	77.9	77.9	77.9	77.9	77.9	79.0	79.5	80.1	81.7	82.8
77.5°	60.2	59.6	59.1	58.6	59.1	59.6	60.2	60.3	61.1	61.5	62.6
80°	47.6	47.0	46.6	46.6	46.6	47.0	47.6	48.2	48.2	49.7	49.2
82.5°	36.4	35.8	35.7	35.3	35.7	35.8	36.4	36.4	36.4	37.7	37.5
85°	19.5	20.0	19.5	20.5	19.5	20.0	19.5	18.9	19.5	20.5	20.5
87.5°	9.9	9.5	9.9	9.5	9.9	9.5	9.9	9.9	10.3	10.4	10.4
90°	21.3	21.4	21.5	21.7	21.5	21.4	21.3	21.1	21.2	21.4	21.8
92.5°	20.5	20.6	20.6	20.6	20.6	20.6	20.5	20.5	20.5	20.5	20.4
95°	40.4	40.1	39.8	39.5	39.8	40.1	40.4	40.7	40.8	40.8	40.8
97.5°	68.6	68.5	68.5	68.4	68.5	68.5	68.6	68.6	68.6	68.6	68.6
100°	87.7	87.6	87.5	87.3	87.5	87.6	87.7	87.9	88.0	88.0	88.0
102.5°	109.2	109.0	108.8	108.7	108.8	109.0	109.2	109.3	109.3	109.2	109.1
105°	141.5	141.5	141.5	141.5	141.5	141.5	141.5	141.5	141.4	141.0	140.8
107.5°	174.3	173.7	173.0	172.4	173.0	173.7	174.3	175.0	175.2	175.0	175.0
110°	197.5	197.1	196.7	196.2	196.7	197.1	197.5	198.0	198.2	198.2	198.2



TEST NUMBER: P331718-930

CATALOG NUMBER: SA2XXRDIP-C865D725U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	220.1	219.8	219.6	219.2	219.6	219.8	220.1	220.5	220.8	221.1	221.4
115°	256.2	255.8	255.4	254.9	255.4	255.8	256.2	256.6	256.9	257.1	257.1
117.5°	290.2	289.8	289.3	288.9	289.3	289.8	290.2	290.7	291.0	291.4	291.7
120°	314.1	313.7	313.3	312.9	313.3	313.7	314.1	314.6	314.8	314.8	314.8
122.5°	337.3	337.0	336.6	336.4	336.6	337.0	337.3	337.6	337.9	338.3	338.6
125°	372.6	372.4	372.3	372.2	372.3	372.4	372.6	372.8	373.0	373.4	373.9
127.5°	406.2	405.7	405.3	404.8	405.3	405.7	406.2	406.6	407.1	407.6	408.1
130°	429.9	429.4	428.8	428.3	428.8	429.4	429.9	430.5	431.0	431.2	431.5
132.5°	452.0	451.6	451.1	450.7	451.1	451.6	452.0	452.5	453.1	453.6	454.3
135°	486.9	486.5	486.0	485.6	486.0	486.5	486.9	487.3	487.5	487.7	487.9
137.5°	518.9	518.4	517.8	517.2	517.8	518.4	518.9	519.5	519.8	519.9	520.1
140°	540.9	540.3	539.7	539.2	539.7	540.3	540.9	541.4	541.7	541.7	541.7
142.5°	560.7	560.1	559.6	559.1	559.6	560.1	560.7	561.3	561.5	561.4	561.3
145°	590.5	590.0	589.4	588.8	589.4	590.0	590.5	591.1	591.3	591.2	591.0
147.5°	617.1	616.5	616.0	615.5	616.0	616.5	617.1	617.7	617.8	617.4	617.1
150°	634.1	633.7	633.2	632.8	633.2	633.7	634.1	634.5	634.5	634.1	633.7
152.5°	650.8	650.2	649.6	649.1	649.6	650.2	650.8	651.3	651.3	650.8	650.2
155°	672.3	671.9	671.5	671.1	671.5	671.9	672.3	672.8	672.6	671.9	671.2
157.5°	691.9	691.3	690.6	689.9	690.6	691.3	691.9	692.6	692.5	691.5	690.6
160°	703.4	702.8	702.2	701.6	702.2	702.8	703.4	703.9	703.8	703.0	702.1
162.5°	713.9	713.2	712.5	711.8	712.5	713.2	713.9	714.5	714.4	713.5	712.5
165°	727.3	726.6	725.9	725.2	725.9	726.6	727.3	728.1	727.9	726.9	725.9
167.5°	738.4	737.7	736.9	736.2	736.9	737.7	738.4	739.2	739.0	738.0	737.0
170°	744.4	743.5	742.7	741.8	742.7	743.5	744.4	745.2	745.1	744.1	743.1
172.5°	748.9	748.0	747.2	746.4	747.2	748.0	748.9	749.7	749.7	748.7	747.7
175°	753.9	753.0	752.2	751.4	752.2	753.0	753.9	754.7	754.6	753.7	752.7
177.5°	755.7	755.0	754.3	753.7	754.3	755.0	755.7	756.4	756.4	755.7	755.0
180°	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1



TEST NUMBER: P331718-930
 CATALOG NUMBER: SA2XXRDIP-C865D725U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9
2.5°	1497.1	1503.2	1512.3	1517.5	1526.2	1531.8	1534.8	1540.4	1543.4	1554.3	1565.5
5°	1413.5	1422.2	1437.3	1451.4	1466.6	1482.2	1493.5	1506.6	1518.5	1539.0	1560.6
7.5°	1317.7	1329.7	1353.2	1375.6	1401.9	1424.2	1443.7	1465.9	1485.7	1515.2	1545.8
10°	1245.9	1266.9	1297.8	1318.8	1353.5	1375.7	1406.5	1430.9	1458.4	1497.4	1532.0
12.5°	1184.0	1209.3	1234.1	1263.5	1294.6	1331.5	1365.4	1396.6	1429.5	1469.7	1510.3
15°	1071.6	1108.4	1146.8	1176.6	1218.8	1257.8	1297.2	1339.4	1379.4	1427.6	1480.6
17.5°	927.1	969.7	1034.3	1085.2	1134.8	1173.9	1222.8	1273.8	1321.0	1379.1	1438.1
20°	861.8	893.2	936.9	1005.7	1080.3	1121.9	1171.7	1228.0	1282.1	1345.3	1408.7
22.5°	809.3	837.3	872.5	926.0	1009.3	1066.1	1118.0	1175.2	1238.0	1302.5	1372.7
25°	734.6	754.1	790.8	834.1	891.5	985.0	1041.9	1099.2	1167.4	1236.6	1316.7
27.5°	678.5	696.0	719.9	761.2	803.9	871.1	961.4	1023.9	1091.8	1169.8	1252.9
30°	635.6	656.2	682.7	711.9	758.4	810.9	901.2	973.7	1040.8	1120.9	1209.6
32.5°	604.5	620.7	643.3	672.9	711.7	762.0	834.1	922.2	987.6	1072.0	1164.6
35°	553.4	572.3	590.8	618.9	650.2	696.2	750.8	845.0	909.9	993.2	1086.2
37.5°	511.3	522.9	543.2	565.5	598.6	632.9	680.3	764.7	834.9	916.7	1011.9
40°	479.3	493.9	509.1	533.9	561.0	593.9	640.5	703.3	783.8	863.9	956.9
42.5°	448.2	466.6	482.7	499.3	529.0	562.0	599.8	653.1	735.4	811.1	901.6
45°	410.6	422.5	439.3	457.6	482.0	510.1	543.6	590.2	669.2	734.6	819.5
47.5°	366.9	384.3	395.3	413.2	436.3	463.2	494.3	534.6	598.5	659.8	738.7
50°	337.0	354.9	370.6	386.8	407.3	433.3	459.3	498.2	549.6	614.0	687.5
52.5°	311.4	327.2	342.4	358.7	378.8	402.6	427.2	461.5	505.5	564.7	636.1
55°	276.5	286.2	301.8	318.0	335.9	358.7	382.5	411.2	449.0	498.8	556.7
57.5°	240.5	251.8	264.2	280.5	298.6	316.0	337.5	363.4	393.3	438.3	487.9
60°	220.1	228.9	239.1	255.8	272.6	288.3	308.9	330.5	358.7	397.6	439.8
62.5°	197.6	205.9	215.3	229.9	246.2	260.7	278.6	301.5	325.3	360.9	397.8
65°	160.1	172.0	181.2	194.2	207.7	222.9	236.9	255.4	276.5	304.6	337.5
67.5°	132.7	138.8	147.3	159.1	173.0	186.0	199.3	213.7	232.0	253.7	279.9
70°	120.7	122.8	124.4	135.7	148.8	161.8	174.1	187.7	203.4	221.3	243.9
72.5°	106.3	108.5	110.6	115.4	125.8	138.8	151.6	161.8	176.6	191.4	209.8
75°	84.4	87.6	89.3	92.0	95.7	104.4	116.3	126.0	134.7	146.0	160.7
77.5°	64.2	66.1	67.8	70.7	73.1	77.0	83.7	92.5	100.6	107.2	117.2
80°	50.9	51.4	53.6	54.6	57.9	60.6	63.8	70.8	79.0	81.7	88.7
82.5°	38.3	38.8	40.6	41.7	43.1	45.4	49.6	51.4	57.8	61.3	65.8
85°	21.1	20.5	22.2	22.2	23.2	24.4	25.4	28.1	29.8	34.1	35.1
87.5°	10.9	10.9	10.8	10.1	9.5	9.8	9.7	9.8	10.4	11.3	12.6
90°	22.0	22.3	19.2	16.1	13.0	9.9	7.4	5.7	4.1	2.4	0.7
92.5°	20.3	20.3	19.6	18.8	18.0	17.3	16.3	15.1	13.9	12.6	11.3
95°	40.8	40.8	40.5	40.2	39.9	39.6	38.8	37.4	36.0	34.6	33.1
97.5°	68.6	68.6	68.0	67.5	66.9	66.4	65.6	64.2	63.0	61.8	60.6
100°	88.0	88.0	87.5	87.1	86.7	86.3	85.4	84.3	83.2	82.1	81.0
102.5°	108.9	108.8	108.3	107.8	107.2	106.7	106.0	105.1	104.2	103.2	102.3
105°	140.5	140.2	139.9	139.7	139.3	139.1	138.7	138.3	137.9	137.5	137.1
107.5°	174.9	174.7	174.7	174.7	174.7	174.7	174.4	173.8	173.2	172.6	171.9
110°	198.2	198.2	198.2	198.2	198.2	198.2	197.8	196.9	196.1	195.2	194.4



TEST NUMBER: P331718-930
 CATALOG NUMBER: SA2XXRDIP-C865D725U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	221.8	222.2	222.3	222.4	222.5	222.6	222.3	221.4	220.5	219.7	218.8
115°	257.3	257.5	257.7	258.0	258.3	258.6	258.3	257.5	256.6	255.8	254.9
117.5°	292.0	292.4	293.2	294.0	294.7	295.5	295.4	294.2	293.1	292.0	290.8
120°	314.8	314.8	315.9	317.1	318.2	319.4	319.4	318.2	317.1	315.9	314.8
122.5°	338.9	339.2	340.1	340.9	341.7	342.4	342.2	340.8	339.5	338.1	336.7
125°	374.3	374.7	375.1	375.5	376.0	376.4	376.0	374.7	373.4	372.2	370.9
127.5°	408.6	409.1	409.6	410.2	410.7	411.2	410.6	409.0	407.4	405.8	404.1
130°	431.8	432.1	432.4	432.6	432.9	433.2	432.4	430.6	428.8	426.9	425.1
132.5°	454.9	455.5	455.4	455.4	455.3	455.3	454.5	453.0	451.5	450.0	448.5
135°	488.0	488.1	487.9	487.5	487.3	487.0	486.1	484.5	483.0	481.4	479.9
137.5°	520.2	520.2	519.9	519.5	519.2	518.8	518.0	516.7	515.4	514.1	512.9
140°	541.7	541.7	541.0	540.3	539.6	538.8	537.9	536.5	535.3	534.0	532.8
142.5°	561.2	561.1	560.6	560.1	559.6	559.1	558.2	557.0	555.7	554.4	553.2
145°	590.9	590.8	589.9	589.1	588.2	587.3	586.4	585.5	584.5	583.4	582.4
147.5°	616.8	616.5	616.0	615.4	614.8	614.2	613.3	612.1	611.0	609.8	608.6
150°	633.2	632.8	632.3	631.7	631.1	630.6	629.8	629.0	628.1	627.3	626.5
152.5°	649.6	649.1	648.4	647.8	647.1	646.4	645.6	644.8	643.9	643.1	642.2
155°	670.5	669.8	669.4	669.0	668.5	668.1	667.6	667.2	666.8	666.3	665.9
157.5°	689.6	688.6	688.4	688.1	687.9	687.6	687.4	687.1	686.8	686.5	686.2
160°	701.2	700.3	700.3	700.1	699.9	699.8	699.6	699.3	699.0	698.7	698.5
162.5°	711.5	710.5	710.5	710.3	710.1	710.0	709.9	709.8	709.8	709.7	709.6
165°	725.0	723.9	723.9	723.9	723.9	723.9	724.0	724.1	724.3	724.5	724.6
167.5°	736.1	735.0	735.1	735.1	735.2	735.2	735.4	735.8	736.2	736.6	737.0
170°	742.2	741.1	741.3	741.4	741.6	741.7	742.0	742.4	742.8	743.3	743.7
172.5°	746.7	745.8	745.9	746.0	746.2	746.3	746.6	747.0	747.5	747.9	748.3
175°	751.7	750.7	751.0	751.3	751.5	751.9	752.2	752.6	753.0	753.5	753.9
177.5°	754.3	753.7	753.8	754.1	754.3	754.6	754.8	755.1	755.5	755.9	756.2
180°	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1



TEST NUMBER: P331718-930

CATALOG NUMBER: SA2XXRDIP-C865D725U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9
2.5°	1565.9	1567.2	1575.9	1579.8	1587.6	1590.6	1594.1	1593.3	1593.3	1595.0	1607.1
5°	1569.3	1580.1	1596.4	1612.1	1627.2	1640.2	1648.9	1657.5	1660.8	1676.4	1690.5
7.5°	1563.7	1583.6	1610.5	1634.3	1663.0	1685.4	1704.1	1720.8	1732.3	1755.1	1778.5
10°	1556.3	1584.5	1614.8	1645.6	1685.1	1714.8	1745.1	1768.4	1776.0	1810.0	1829.5
12.5°	1541.6	1579.2	1617.8	1657.7	1696.3	1737.3	1770.7	1793.9	1820.6	1851.1	1887.1
15°	1519.6	1562.8	1613.2	1664.5	1719.7	1769.4	1805.2	1845.8	1874.9	1908.5	1939.8
17.5°	1487.8	1543.6	1607.5	1667.0	1730.9	1784.3	1833.4	1872.3	1892.9	1912.0	1916.7
20°	1462.7	1522.8	1598.0	1668.3	1732.2	1793.8	1842.5	1874.9	1880.4	1880.9	1852.3
22.5°	1435.5	1503.3	1582.0	1654.0	1730.4	1799.0	1836.9	1850.7	1829.3	1792.6	1737.2
25°	1385.4	1463.9	1555.3	1637.4	1720.8	1785.7	1798.7	1774.3	1699.2	1620.2	1520.1
27.5°	1331.1	1419.3	1517.3	1608.7	1697.5	1737.6	1709.7	1621.9	1486.5	1368.7	1226.0
30°	1291.3	1390.2	1486.5	1588.8	1671.0	1688.3	1624.0	1494.7	1336.7	1159.3	1017.0
32.5°	1245.9	1349.6	1455.4	1561.1	1629.9	1613.0	1506.7	1347.5	1162.3	987.9	853.5
35°	1180.9	1288.0	1402.2	1508.2	1552.0	1479.0	1320.0	1112.7	923.4	760.6	668.1
37.5°	1106.0	1222.5	1341.2	1438.6	1435.5	1313.8	1097.1	883.3	724.1	627.9	562.0
40°	1052.7	1170.6	1298.9	1381.0	1345.9	1187.4	952.6	750.8	634.5	557.7	509.6
42.5°	1001.7	1120.0	1247.3	1312.7	1251.6	1056.7	822.8	664.7	568.8	508.8	469.8
45°	914.8	1039.8	1157.6	1193.9	1084.6	869.8	665.4	550.7	486.9	442.5	415.5
47.5°	829.8	952.8	1060.4	1061.0	913.2	705.4	561.3	476.6	422.1	387.8	368.1
50°	777.9	894.7	985.0	971.0	803.3	627.5	502.0	429.0	383.5	357.0	336.5
52.5°	719.5	832.8	911.1	871.1	710.3	552.2	448.7	387.4	349.8	326.8	308.3
55°	634.5	735.2	790.4	729.8	579.4	459.3	379.2	331.1	303.0	283.5	267.7
57.5°	551.1	634.1	668.9	598.3	477.2	380.8	320.8	284.6	256.7	242.8	234.6
60°	498.8	569.6	593.9	516.1	414.9	333.2	284.0	250.5	229.9	220.7	212.6
62.5°	447.3	505.2	515.2	443.8	361.7	291.7	249.4	221.0	207.4	198.6	190.9
65°	371.1	412.8	407.9	350.6	286.2	231.5	200.7	183.4	173.1	160.7	147.2
67.5°	305.5	330.9	315.6	272.6	218.4	179.9	159.8	146.7	134.0	122.1	119.0
70°	264.0	278.6	262.4	222.9	179.0	150.9	134.7	119.0	111.5	108.8	103.9
72.5°	224.2	229.3	211.7	177.9	145.7	125.0	109.2	100.4	96.3	94.0	90.9
75°	168.3	164.4	149.3	122.8	101.2	87.1	82.3	79.0	76.3	74.1	72.5
77.5°	118.1	112.6	99.1	81.8	70.4	63.8	60.8	59.1	57.8	56.7	55.0
80°	88.7	85.0	71.4	58.5	53.6	50.3	48.7	46.6	46.6	45.4	43.8
82.5°	64.9	60.7	48.9	42.8	40.1	38.2	37.0	35.7	35.3	35.5	34.3
85°	34.1	27.6	24.4	23.2	21.6	20.5	21.1	20.0	20.0	20.0	19.5
87.5°	10.8	9.0	9.0	8.8	9.8	10.4	10.6	11.2	12.2	11.7	12.1
90°	2.4	4.1	5.7	7.4	9.9	13.0	16.1	19.2	22.3	22.0	21.8
92.5°	12.6	13.9	15.1	16.3	17.3	18.0	18.8	19.6	20.3	20.3	20.4
95°	34.6	36.0	37.4	38.8	39.6	39.9	40.2	40.5	40.8	40.8	40.8
97.5°	61.8	63.0	64.2	65.6	66.4	66.9	67.5	68.0	68.6	68.6	68.6
100°	82.1	83.2	84.3	85.4	86.3	86.7	87.1	87.5	88.0	88.0	88.0
102.5°	103.2	104.2	105.1	106.0	106.7	107.2	107.8	108.3	108.8	108.9	109.1
105°	137.5	137.9	138.3	138.7	139.1	139.3	139.7	139.9	140.2	140.5	140.8
107.5°	172.6	173.2	173.8	174.4	174.7	174.7	174.7	174.7	174.7	174.9	175.0
110°	195.2	196.1	196.9	197.8	198.2	198.2	198.2	198.2	198.2	198.2	198.2



TEST NUMBER: P331718-930

CATALOG NUMBER: SA2XXRDIP-C865D725U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	219.7	220.5	221.4	222.3	222.6	222.5	222.4	222.3	222.2	221.8	221.4
115°	255.8	256.6	257.5	258.3	258.6	258.3	258.0	257.7	257.5	257.3	257.1
117.5°	292.0	293.1	294.2	295.4	295.5	294.7	294.0	293.2	292.4	292.0	291.7
120°	315.9	317.1	318.2	319.4	319.4	318.2	317.1	315.9	314.8	314.8	314.8
122.5°	338.1	339.5	340.8	342.2	342.4	341.7	340.9	340.1	339.2	338.9	338.6
125°	372.2	373.4	374.7	376.0	376.4	376.0	375.5	375.1	374.7	374.3	373.9
127.5°	405.8	407.4	409.0	410.6	411.2	410.7	410.2	409.6	409.1	408.6	408.1
130°	426.9	428.8	430.6	432.4	433.2	432.9	432.6	432.4	432.1	431.8	431.5
132.5°	450.0	451.5	453.0	454.5	455.3	455.3	455.4	455.4	455.5	454.9	454.3
135°	481.4	483.0	484.5	486.1	487.0	487.3	487.5	487.9	488.1	488.0	487.9
137.5°	514.1	515.4	516.7	518.0	518.8	519.2	519.5	519.9	520.2	520.2	520.1
140°	534.0	535.3	536.5	537.9	538.8	539.6	540.3	541.0	541.7	541.7	541.7
142.5°	554.4	555.7	557.0	558.2	559.1	559.6	560.1	560.6	561.1	561.2	561.3
145°	583.4	584.5	585.5	586.4	587.3	588.2	589.1	589.9	590.8	590.9	591.0
147.5°	609.8	611.0	612.1	613.3	614.2	614.8	615.4	616.0	616.5	616.8	617.1
150°	627.3	628.1	629.0	629.8	630.6	631.1	631.7	632.3	632.8	633.2	633.7
152.5°	643.1	643.9	644.8	645.6	646.4	647.1	647.8	648.4	649.1	649.6	650.2
155°	666.3	666.8	667.2	667.6	668.1	668.5	669.0	669.4	669.8	670.5	671.2
157.5°	686.5	686.8	687.1	687.4	687.6	687.9	688.1	688.4	688.6	689.6	690.6
160°	698.7	699.0	699.3	699.6	699.8	699.9	700.1	700.3	700.3	701.2	702.1
162.5°	709.7	709.8	709.8	709.9	710.0	710.1	710.3	710.5	710.5	711.5	712.5
165°	724.5	724.3	724.1	724.0	723.9	723.9	723.9	723.9	723.9	725.0	725.9
167.5°	736.6	736.2	735.8	735.4	735.2	735.2	735.1	735.1	735.0	736.1	737.0
170°	743.3	742.8	742.4	742.0	741.7	741.6	741.4	741.3	741.1	742.2	743.1
172.5°	747.9	747.5	747.0	746.6	746.3	746.2	746.0	745.9	745.8	746.7	747.7
175°	753.5	753.0	752.6	752.2	751.9	751.5	751.3	751.0	750.7	751.7	752.7
177.5°	755.9	755.5	755.1	754.8	754.6	754.3	754.1	753.8	753.7	754.3	755.0
180°	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1	755.1



TEST NUMBER: P331718-930

CATALOG NUMBER: SA2XXRDIP-C865D725U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9
2.5°	1611.4	1617.1	1619.6	1619.6	1622.7	1621.4	1620.1
5°	1704.1	1714.3	1716.4	1726.2	1733.2	1731.0	1732.2
7.5°	1796.1	1812.7	1829.0	1836.5	1837.6	1841.9	1843.6
10°	1852.8	1866.3	1891.7	1887.9	1906.9	1917.7	1899.8
12.5°	1907.3	1925.6	1943.3	1948.1	1958.8	1962.3	1955.3
15°	1956.6	1966.4	1967.5	1964.8	1968.0	1965.3	1955.0
17.5°	1910.6	1894.8	1862.7	1847.5	1835.6	1817.9	1810.7
20°	1834.4	1787.9	1733.7	1712.1	1686.7	1637.0	1648.9
22.5°	1670.0	1616.9	1562.8	1499.7	1469.5	1422.3	1419.4
25°	1414.1	1322.7	1222.1	1151.7	1110.6	1063.6	1042.9
27.5°	1099.4	984.3	901.9	860.1	822.1	784.8	783.3
30°	892.6	806.0	742.2	706.5	683.2	667.6	670.8
32.5°	752.4	693.1	650.0	620.4	603.2	591.3	591.2
35°	615.1	574.5	546.9	534.4	522.0	513.4	513.9
37.5°	526.4	502.0	486.7	472.9	465.1	460.9	458.5
40°	480.9	460.9	449.0	440.9	434.4	428.4	427.4
42.5°	445.0	428.4	416.5	410.2	404.1	399.9	398.8
45°	394.9	381.4	370.6	363.5	360.9	357.0	357.0
47.5°	351.3	338.0	329.5	325.1	320.5	318.0	317.9
50°	321.9	311.6	304.0	301.3	297.5	295.9	295.4
52.5°	295.5	287.8	282.4	280.5	278.9	276.9	277.2
55°	259.7	255.4	253.2	251.5	248.8	245.6	247.8
57.5°	229.5	225.8	220.0	214.8	212.4	210.1	211.0
60°	208.3	200.7	193.1	187.2	185.6	180.7	180.7
62.5°	181.4	170.8	161.5	158.2	156.5	154.3	153.8
65°	139.6	135.3	133.1	130.9	129.8	129.8	128.7
67.5°	115.7	113.9	111.5	111.0	109.9	109.6	109.3
70°	102.2	100.0	99.0	98.5	97.3	97.9	96.3
72.5°	89.3	87.6	87.3	85.9	85.3	85.4	84.1
75°	70.4	70.4	69.8	69.2	68.2	67.6	68.2
77.5°	54.1	54.2	53.2	53.2	53.0	53.2	52.6
80°	43.3	43.8	43.3	42.7	42.2	42.7	42.2
82.5°	34.2	33.4	33.3	33.2	33.1	32.8	32.7
85°	19.5	20.0	19.5	18.9	18.9	18.9	19.5
87.5°	11.7	11.6	11.6	11.6	11.7	11.7	11.3
90°	21.4	21.2	21.1	21.3	21.4	21.5	21.7
92.5°	20.5	20.5	20.5	20.5	20.6	20.6	20.6
95°	40.8	40.8	40.7	40.4	40.1	39.8	39.5
97.5°	68.6	68.6	68.6	68.6	68.5	68.5	68.4
100°	88.0	88.0	87.9	87.7	87.6	87.5	87.3
102.5°	109.2	109.3	109.3	109.2	109.0	108.8	108.7
105°	141.0	141.4	141.5	141.5	141.5	141.5	141.5
107.5°	175.0	175.2	175.0	174.3	173.7	173.0	172.4
110°	198.2	198.2	198.0	197.5	197.1	196.7	196.2



TEST NUMBER: P331718-930

CATALOG NUMBER: SA2XXRDIP-C865D725U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	221.1	220.8	220.5	220.1	219.8	219.6	219.2
115°	257.1	256.9	256.6	256.2	255.8	255.4	254.9
117.5°	291.4	291.0	290.7	290.2	289.8	289.3	288.9
120°	314.8	314.8	314.6	314.1	313.7	313.3	312.9
122.5°	338.3	337.9	337.6	337.3	337.0	336.6	336.4
125°	373.4	373.0	372.8	372.6	372.4	372.3	372.2
127.5°	407.6	407.1	406.6	406.2	405.7	405.3	404.8
130°	431.2	431.0	430.5	429.9	429.4	428.8	428.3
132.5°	453.6	453.1	452.5	452.0	451.6	451.1	450.7
135°	487.7	487.5	487.3	486.9	486.5	486.0	485.6
137.5°	519.9	519.8	519.5	518.9	518.4	517.8	517.2
140°	541.7	541.7	541.4	540.9	540.3	539.7	539.2
142.5°	561.4	561.5	561.3	560.7	560.1	559.6	559.1
145°	591.2	591.3	591.1	590.5	590.0	589.4	588.8
147.5°	617.4	617.8	617.7	617.1	616.5	616.0	615.5
150°	634.1	634.5	634.5	634.1	633.7	633.2	632.8
152.5°	650.8	651.3	651.3	650.8	650.2	649.6	649.1
155°	671.9	672.6	672.8	672.3	671.9	671.5	671.1
157.5°	691.5	692.5	692.6	691.9	691.3	690.6	689.9
160°	703.0	703.8	703.9	703.4	702.8	702.2	701.6
162.5°	713.5	714.4	714.5	713.9	713.2	712.5	711.8
165°	726.9	727.9	728.1	727.3	726.6	725.9	725.2
167.5°	738.0	739.0	739.2	738.4	737.7	736.9	736.2
170°	744.1	745.1	745.2	744.4	743.5	742.7	741.8
172.5°	748.7	749.7	749.7	748.9	748.0	747.2	746.4
175°	753.7	754.6	754.7	753.9	753.0	752.2	751.4
177.5°	755.7	756.4	756.4	755.7	755.0	754.3	753.7
180°	755.1	755.1	755.1	755.1	755.1	755.1	755.1

(END OF REPORT)