

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331363-840

Luminaire Tested: **SA2XXDIP-C675D925U840-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331363-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C675D925U840-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 925 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6466.2 lumens
Efficiency: N/A
Efficacy: 124.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 52
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331363-840
CATALOG NUMBER: SA2XXDIP-C675D925U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331363-840

CATALOG NUMBER: SA2XXDIP-C675D925U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49	42
1	96	92	88	84	88	84	81	78	69	67	65	56	54	53	43	42	41	36
2	87	80	74	69	80	73	68	64	61	57	54	49	46	44	38	36	35	30
3	80	70	63	57	73	65	58	53	53	49	45	43	40	37	34	32	30	25
4	73	62	54	48	66	57	50	45	47	42	38	39	35	32	30	28	26	22
5	67	55	47	41	61	51	44	39	42	37	33	35	31	28	27	24	22	19
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	25	22	20	17
7	57	45	37	31	52	41	34	29	35	29	25	28	24	21	22	20	17	15
8	53	41	33	28	48	37	31	26	32	26	22	26	22	19	21	18	16	13
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12
10	46	34	27	22	42	31	25	21	27	22	18	22	18	15	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17312	17312	17312
5°	17378	17126	17227
10°	17274	16952	17038
15°	17060	16732	16715
20°	16756	16402	16385
25°	16456	15998	15998
30°	16067	15627	15491
35°	15707	15179	14954
40°	15253	14731	14450
45°	14805	14289	13935
50°	14320	13828	13335
55°	13813	13292	12797
60°	13249	12649	12184
65°	12642	12015	11461
70°	11877	11240	10707
75°	10805	10356	10100
80°	9586	9298	8815
85°	7836	7447	6688



TEST NUMBER: P331363-840

CATALOG NUMBER: SA2XXDIP-C675D925U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.8	1.6
10°-20°	283.7	4.4
20°-30°	417.0	6.4
30°-40°	484.3	7.5
40°-50°	483.8	7.5
50°-60°	421.9	6.5
60°-70°	312.0	4.8
70°-80°	176.7	2.7
80°-90°	50.6	0.8
90°-100°	42.5	0.7
100°-110°	155.9	2.4
110°-120°	416.8	6.4
120°-130°	688.0	10.6
130°-140°	731.7	11.3
140°-150°	680.1	10.5
150°-160°	546.8	8.5
160°-170°	352.3	5.4
170°-180°	121.3	1.9
0°-30°	801.5	12.4
0°-40°	1285.8	19.9
0°-60°	2191.5	33.9
0°-90°	2730.9	42.2
90°-120°	615.2	9.5
90°-150°	2714.9	42.0
90°-180°	3735.0	57.8
0°-180°	6466.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1072	1072	1072	1072	1072	
5°	1072	1068	1057	1064	1063	102
15°	1021	1014	1001	1005	1000	287
25°	924	915	898	900	898	425
35°	797	786	770	764	759	497
45°	648	641	626	615	610	500
55°	491	484	472	460	455	439
65°	331	324	314	305	300	327
75°	173	171	166	160	162	185
85°	42	41	40	37	36	48
90°	1	11	18	23	25	5
95°	60	32	36	40	40	73
105°	280	292	56	66	70	300
115°	530	546	569	162	76	522
125°	750	762	779	786	789	668
135°	928	942	951	960	958	716
145°	1076	1076	1091	1097	1093	673
155°	1185	1178	1188	1193	1186	546
165°	1249	1244	1246	1252	1246	353
175°	1277	1271	1273	1278	1270	122
180°	1275	1275	1275	1275	1275	



TEST NUMBER: P331363-840

CATALOG NUMBER: SA2XXDIP-C675D925U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1072.2	1072.2	1072.2	1072.2	1072.2	1072.2	1072.2	1072.2	1072.2	1072.2	1072.2
2.5°	1077.1	1076.2	1075.3	1074.4	1073.5	1072.0	1070.0	1067.9	1065.9	1063.9	1065.7
5°	1072.2	1071.3	1070.4	1069.4	1068.5	1066.8	1064.3	1061.8	1059.2	1056.7	1058.5
7.5°	1062.7	1061.3	1059.9	1058.4	1057.0	1055.0	1052.5	1049.9	1047.3	1044.7	1046.5
10°	1053.6	1052.0	1050.4	1048.7	1047.2	1045.0	1042.3	1039.6	1036.7	1034.0	1035.8
12.5°	1041.3	1039.9	1038.3	1036.9	1035.5	1033.5	1030.7	1027.9	1025.2	1022.5	1023.8
15°	1020.6	1019.3	1017.8	1016.5	1015.1	1012.9	1010.0	1006.9	1004.0	1001.0	1002.0
17.5°	994.2	992.8	991.5	990.1	988.8	986.5	983.5	980.5	977.4	974.4	975.5
20°	975.2	973.9	972.5	971.1	969.8	967.5	964.2	961.1	957.9	954.6	955.3
22.5°	956.2	954.3	952.4	950.5	948.6	946.1	943.1	940.1	937.1	934.0	934.1
25°	923.7	921.9	920.1	918.2	916.4	913.5	909.6	905.7	901.8	898.0	898.4
27.5°	886.6	884.9	883.3	881.6	880.0	877.7	874.5	871.5	868.4	865.4	864.6
30°	861.8	860.0	858.2	856.4	854.5	851.9	848.5	845.1	841.6	838.2	837.5
32.5°	835.5	833.9	832.5	831.0	829.6	827.1	823.4	819.8	816.2	812.5	811.3
35°	796.9	794.7	792.3	790.0	787.7	784.8	781.1	777.4	773.8	770.1	768.7
37.5°	753.4	751.3	749.3	747.3	745.4	742.5	738.8	735.2	731.5	727.8	726.1
40°	723.7	721.9	720.0	718.2	716.4	713.7	709.9	706.3	702.7	698.9	696.9
42.5°	694.9	693.0	691.2	689.3	687.5	684.8	681.1	677.4	673.8	670.1	667.8
45°	648.4	646.8	645.2	643.7	642.1	639.5	636.1	632.7	629.2	625.8	623.3
47.5°	602.3	600.8	599.3	597.7	596.2	593.7	590.1	586.5	583.0	579.4	576.7
50°	570.1	569.0	567.8	566.6	565.5	563.3	560.2	556.9	553.7	550.5	547.3
52.5°	538.8	537.2	535.7	534.2	532.7	530.5	527.5	524.4	521.4	518.4	515.7
55°	490.7	489.4	488.0	486.6	485.2	483.1	480.4	477.7	474.9	472.2	469.4
57.5°	442.4	441.4	440.3	439.2	438.1	436.1	433.0	430.0	427.0	423.9	421.2
60°	410.3	409.4	408.5	407.6	406.7	404.6	401.4	398.2	395.0	391.7	389.2
62.5°	379.0	377.5	376.1	374.6	373.1	371.1	368.7	366.2	363.8	361.2	358.9
65°	330.9	329.5	328.2	326.8	325.4	323.6	321.3	319.0	316.7	314.5	312.4
67.5°	282.1	280.9	279.8	278.7	277.6	276.1	274.0	272.0	269.9	267.8	266.2
70°	251.6	250.6	249.7	248.8	247.9	246.4	244.3	242.3	240.2	238.1	236.5
72.5°	220.3	219.2	218.3	217.4	216.5	215.4	214.1	212.8	211.5	210.1	208.5
75°	173.2	172.7	172.3	171.8	171.4	170.6	169.5	168.2	167.1	166.0	164.6
77.5°	131.2	130.4	129.6	128.8	128.1	127.4	126.9	126.4	126.0	125.5	124.9
80°	103.1	102.9	102.6	102.4	102.2	101.8	101.4	100.9	100.5	100.0	99.3
82.5°	76.7	76.6	76.6	76.5	76.5	76.3	76.0	75.8	75.5	75.2	74.4
85°	42.3	42.0	41.8	41.6	41.3	41.1	40.9	40.7	40.4	40.2	39.5
87.5°	15.0	15.1	15.1	15.2	15.3	15.3	15.3	15.3	15.2	15.2	14.8
90°	0.9	3.1	5.5	7.7	9.9	11.9	13.5	15.1	16.8	18.5	19.5
92.5°	18.6	18.4	18.2	18.0	17.8	18.1	19.0	19.8	20.6	21.4	21.9
95°	60.0	53.2	46.5	39.7	32.9	30.2	31.7	33.1	34.5	36.0	37.0
97.5°	119.0	99.9	80.9	61.8	42.7	34.8	38.2	41.5	44.8	48.2	49.0
100°	163.3	135.1	107.0	79.0	50.9	38.7	42.1	45.6	49.1	52.6	54.2
102.5°	212.0	206.0	200.1	194.1	188.1	170.7	141.5	112.3	83.2	54.0	56.1
105°	280.3	286.5	292.7	298.8	305.0	280.0	224.1	168.1	112.2	56.2	58.5
107.5°	358.4	363.3	368.3	373.2	378.3	347.2	280.0	213.0	145.8	78.8	76.4
110°	408.6	412.9	417.2	421.5	425.8	398.3	339.1	279.8	220.7	161.4	140.9



TEST NUMBER: P331363-840

CATALOG NUMBER: SA2XXDIP-C675D925U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	455.8	459.6	463.4	467.3	471.0	465.6	451.0	436.4	421.7	407.1	332.3
115°	530.3	533.8	537.2	540.8	544.2	548.6	553.7	558.9	563.9	569.1	474.1
117.5°	596.9	600.8	604.7	608.6	612.5	616.2	619.8	623.3	626.8	630.3	607.3
120°	645.6	648.6	651.8	654.8	657.9	661.3	665.0	668.6	672.4	676.0	678.5
122.5°	686.9	690.1	693.4	696.6	699.8	703.5	707.5	711.6	715.6	719.6	721.0
125°	749.8	752.5	755.2	757.8	760.5	763.8	767.7	771.5	775.5	779.3	780.8
127.5°	806.8	809.8	812.7	815.7	818.6	821.5	824.5	827.4	830.3	833.2	835.3
130°	843.0	846.3	849.5	852.8	856.1	858.9	861.1	863.3	865.7	867.9	870.1
132.5°	879.9	882.6	885.4	888.3	891.0	893.5	895.9	898.1	900.3	902.5	904.5
135°	927.9	931.1	934.4	937.7	941.0	943.5	945.3	947.3	949.1	950.9	952.9
137.5°	976.3	978.7	981.0	983.2	985.5	987.7	989.8	991.9	994.0	996.1	998.0
140°	1008.0	1009.8	1011.4	1013.0	1014.6	1016.6	1018.9	1021.1	1023.4	1025.6	1027.4
142.5°	1034.6	1036.1	1037.6	1039.1	1040.6	1042.6	1045.1	1047.7	1050.4	1052.9	1054.6
145°	1076.3	1076.1	1075.9	1075.7	1075.5	1077.1	1080.7	1084.1	1087.6	1091.1	1092.5
147.5°	1112.7	1111.9	1111.2	1110.3	1109.5	1110.9	1114.3	1117.8	1121.3	1124.7	1125.7
150°	1136.3	1134.9	1133.4	1132.0	1130.5	1131.5	1134.8	1138.0	1141.3	1144.6	1145.8
152.5°	1156.2	1154.6	1153.0	1151.4	1149.8	1150.5	1153.7	1156.8	1159.9	1163.1	1164.3
155°	1185.2	1183.4	1181.4	1179.6	1177.8	1178.1	1180.5	1183.1	1185.5	1187.9	1189.1
157.5°	1207.8	1206.3	1204.8	1203.2	1201.6	1201.7	1203.5	1205.2	1206.9	1208.6	1210.0
160°	1221.1	1219.9	1218.7	1217.4	1216.2	1216.2	1217.4	1218.7	1219.9	1221.1	1222.3
162.5°	1232.9	1231.7	1230.5	1229.2	1228.0	1227.9	1229.0	1230.0	1231.1	1232.2	1233.6
165°	1248.8	1247.6	1246.4	1245.1	1243.9	1243.5	1244.2	1244.8	1245.5	1246.1	1247.5
167.5°	1260.6	1259.4	1258.2	1256.9	1255.7	1255.4	1256.0	1256.5	1257.1	1257.7	1259.1
170°	1267.3	1266.0	1264.8	1263.5	1262.3	1261.9	1262.3	1262.7	1263.1	1263.5	1265.0
172.5°	1271.6	1270.4	1269.2	1268.0	1266.8	1266.4	1266.8	1267.2	1267.6	1268.0	1269.4
175°	1277.4	1276.0	1274.6	1273.0	1271.6	1271.1	1271.5	1271.9	1272.3	1272.7	1274.2
177.5°	1278.3	1277.2	1276.1	1274.9	1273.7	1273.2	1273.4	1273.5	1273.7	1273.8	1275.1
180°	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7



TEST NUMBER: P331363-840

CATALOG NUMBER: SA2XXDIP-C675D925U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1072.2	1072.2	1072.2	1072.2	1072.2	1072.2	1072.2	1072.2
2.5°	1067.5	1069.4	1071.3	1072.0	1071.6	1071.3	1070.9	1070.6
5°	1060.4	1062.2	1064.0	1064.7	1064.3	1063.8	1063.4	1062.9
7.5°	1048.4	1050.3	1052.1	1052.7	1052.2	1051.8	1051.3	1050.8
10°	1037.6	1039.6	1041.4	1041.9	1041.3	1040.6	1039.9	1039.2
12.5°	1025.0	1026.3	1027.6	1027.9	1027.4	1027.0	1026.5	1026.0
15°	1002.9	1003.8	1004.7	1004.6	1003.4	1002.3	1001.2	1000.0
17.5°	976.5	977.5	978.7	978.7	977.5	976.4	975.3	974.2
20°	956.0	956.7	957.4	957.3	956.3	955.4	954.5	953.6
22.5°	934.3	934.4	934.5	934.3	933.8	933.2	932.7	932.2
25°	898.9	899.3	899.8	899.8	899.3	898.9	898.4	898.0
27.5°	863.9	863.3	862.6	861.7	860.6	859.5	858.4	857.3
30°	836.8	836.1	835.4	834.6	833.6	832.7	831.8	830.9
32.5°	810.1	808.9	807.6	806.6	805.7	804.8	803.8	802.8
35°	767.4	766.0	764.6	763.4	762.2	761.0	759.9	758.7
37.5°	724.5	722.8	721.0	719.6	718.5	717.4	716.4	715.3
40°	694.9	692.8	690.7	689.2	688.3	687.4	686.5	685.6
42.5°	665.6	663.4	661.2	659.3	658.0	656.8	655.5	654.2
45°	620.8	618.2	615.7	614.0	613.1	612.2	611.3	610.3
47.5°	574.1	571.4	568.8	566.7	565.4	564.1	562.8	561.5
50°	544.1	540.9	537.7	535.5	534.3	533.2	532.1	530.9
52.5°	513.0	510.4	507.8	505.6	504.1	502.6	501.1	499.6
55°	466.7	463.9	461.2	459.2	458.1	457.0	455.8	454.6
57.5°	418.5	415.8	413.1	411.3	410.4	409.6	408.7	407.8
60°	386.7	384.2	381.6	380.1	379.4	378.7	378.0	377.3
62.5°	356.6	354.3	351.9	350.3	349.4	348.5	347.7	346.8
65°	310.3	308.2	306.2	304.6	303.5	302.3	301.1	300.0
67.5°	264.6	263.1	261.5	260.1	259.2	258.3	257.4	256.5
70°	234.9	233.4	231.8	230.5	229.5	228.6	227.7	226.8
72.5°	206.9	205.3	203.7	202.5	201.8	201.1	200.4	199.5
75°	163.2	161.9	160.5	160.1	160.5	161.0	161.4	161.9
77.5°	124.2	123.5	122.8	122.2	121.5	120.9	120.3	119.6
80°	98.7	98.0	97.3	96.6	96.2	95.7	95.3	94.8
82.5°	73.5	72.6	71.8	71.3	71.2	71.1	71.0	70.9
85°	38.9	38.2	37.5	37.0	36.8	36.6	36.4	36.1
87.5°	14.5	14.2	13.8	13.6	13.5	13.4	13.3	13.2
90°	20.5	21.5	22.5	23.2	23.6	24.0	24.5	24.9
92.5°	22.4	23.0	23.5	23.9	24.1	24.4	24.6	24.9
95°	38.0	39.1	40.1	40.5	40.3	40.1	39.9	39.7
97.5°	49.8	50.6	51.4	51.9	52.2	52.4	52.7	52.9
100°	55.8	57.5	59.2	60.2	60.6	61.0	61.4	61.8
102.5°	58.3	60.5	62.6	63.9	64.5	65.0	65.6	66.2
105°	60.8	63.0	65.2	66.9	67.7	68.5	69.3	70.1
107.5°	74.1	71.9	69.6	68.9	69.7	70.5	71.3	72.1
110°	120.4	99.9	79.4	69.6	70.4	71.2	72.0	72.9



TEST NUMBER: P331363-840

CATALOG NUMBER: SA2XXDIP-C675D925U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	257.6	182.8	108.1	71.0	71.6	72.3	72.9	73.6
115°	379.3	284.4	189.5	134.6	119.9	105.1	90.4	75.6
117.5°	584.4	561.5	538.5	502.7	454.2	405.8	357.3	308.8
120°	681.0	683.5	685.9	673.3	645.6	617.9	590.3	562.6
122.5°	722.6	724.0	725.5	723.6	718.2	712.8	707.4	702.1
125°	782.2	783.7	785.1	786.1	786.7	787.3	788.0	788.6
127.5°	837.4	839.5	841.6	842.6	842.8	842.9	843.0	843.1
130°	872.4	874.6	876.9	878.0	877.8	877.5	877.3	877.1
132.5°	906.5	908.4	910.3	911.1	910.9	910.7	910.5	910.3
135°	955.0	957.0	959.1	959.9	959.5	959.1	958.7	958.3
137.5°	1000.1	1002.1	1004.1	1004.8	1004.1	1003.4	1002.7	1002.0
140°	1029.3	1031.2	1033.0	1033.4	1032.4	1031.4	1030.4	1029.3
142.5°	1056.2	1057.9	1059.7	1060.0	1058.9	1057.9	1056.9	1055.8
145°	1094.0	1095.4	1096.8	1097.0	1096.0	1095.0	1094.0	1093.0
147.5°	1126.8	1127.8	1128.9	1129.0	1128.1	1127.3	1126.4	1125.6
150°	1147.0	1148.3	1149.5	1149.6	1148.6	1147.5	1146.5	1145.5
152.5°	1165.5	1166.7	1167.9	1167.9	1166.5	1165.2	1163.9	1162.5
155°	1190.4	1191.6	1192.9	1192.7	1191.0	1189.3	1187.7	1186.1
157.5°	1211.3	1212.7	1214.2	1214.1	1212.4	1210.8	1209.2	1207.7
160°	1223.6	1224.9	1226.1	1226.0	1224.5	1223.0	1221.6	1220.2
162.5°	1235.0	1236.4	1237.8	1237.6	1235.9	1234.1	1232.3	1230.5
165°	1248.9	1250.3	1251.7	1251.7	1250.3	1248.9	1247.5	1246.1
167.5°	1260.5	1261.9	1263.4	1263.1	1261.3	1259.5	1257.7	1255.8
170°	1266.5	1267.9	1269.3	1269.1	1267.3	1265.4	1263.5	1261.7
172.5°	1270.8	1272.3	1273.7	1273.5	1271.6	1269.8	1268.0	1266.2
175°	1275.7	1277.1	1278.5	1278.2	1276.2	1274.1	1272.0	1270.0
177.5°	1276.2	1277.4	1278.5	1278.3	1276.9	1275.4	1273.8	1272.4
180°	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7

(END OF REPORT)