

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331419-840

Luminaire Tested: **SA2XXDIP-C865D1080U840-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331419-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C865D1080U840-4F0-1E-UDD-F4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1080 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7796.1 lumens
Efficiency: N/A
Efficacy: 119.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 65.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331419-840
CATALOG NUMBER: SA2XXDIP-C865D1080U840-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331419-840

CATALOG NUMBER: SA2XXDIP-C865D1080U840-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	46				46
1	97	92	89	85	89	85	82	79	71	68	66	58	56	55	46	45	44				38	
2	88	81	75	69	81	74	69	65	62	58	55	51	48	46	40	39	37				32	
3	80	71	64	58	73	65	59	54	55	50	46	45	42	39	36	33	31				27	
4	74	63	55	49	67	58	51	46	49	43	39	40	36	33	32	29	27				23	
5	67	56	48	42	62	52	44	39	43	38	34	36	32	29	29	26	24				20	
6	62	50	42	36	57	46	39	34	39	34	30	32	28	25	26	23	21				18	
7	57	45	37	32	53	42	35	30	35	30	26	30	25	22	24	21	18				16	
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	17				14	
9	50	37	30	25	45	35	28	24	30	24	21	25	21	18	20	17	15				13	
10	46	34	27	22	42	32	25	21	27	22	19	23	19	16	19	16	14				12	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	22501	22501	22501
5°	22587	22261	22392
10°	22453	22035	22146
15°	22176	21750	21727
20°	21782	21321	21297
25°	21389	20794	20794
30°	20885	20310	20137
35°	20416	19730	19438
40°	19827	19150	18782
45°	19244	18573	18114
50°	18613	17975	17334
55°	17954	17275	16636
60°	17221	16443	15839
65°	16435	15614	14896
70°	15437	14611	13917
75°	14042	13456	13125
80°	12459	12087	11464
85°	10170	9689	8688



TEST NUMBER: P331419-840

CATALOG NUMBER: SA2XXDIP-C865D1080U840-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	131.0	1.7
10°-20°	368.7	4.7
20°-30°	542.0	7.0
30°-40°	629.6	8.1
40°-50°	628.9	8.1
50°-60°	548.4	7.0
60°-70°	405.5	5.2
70°-80°	229.7	2.9
80°-90°	67.3	0.9
90°-100°	243.9	3.1
100°-110°	827.7	10.6
110°-120°	879.3	11.3
120°-130°	723.9	9.3
130°-140°	581.3	7.5
140°-150°	439.3	5.6
150°-160°	308.7	4.0
160°-170°	181.7	2.3
170°-180°	59.1	0.8
0°-30°	1041.8	13.4
0°-40°	1671.3	21.4
0°-60°	2848.6	36.5
0°-90°	3551.1	45.5
90°-120°	1951.0	25.0
90°-150°	3695.4	47.4
90°-180°	4245.0	54.5
0°-180°	7796.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1394	1394	1394	1394	1394	
5°	1394	1388	1374	1384	1382	132
15°	1327	1318	1301	1306	1300	373
25°	1201	1189	1167	1170	1167	552
35°	1036	1022	1001	993	986	646
45°	843	833	813	799	793	650
55°	638	629	614	598	591	570
65°	430	422	409	397	390	425
75°	225	222	216	208	210	240
85°	55	54	52	48	47	63
90°	1	16	40	38	39	5
95°	41	101	460	174	134	44
105°	143	216	869	1554	1322	152
115°	252	319	727	1501	1740	250
125°	352	416	699	1216	1411	312
135°	413	493	691	1022	1170	319
145°	472	542	687	854	934	296
155°	536	579	668	755	785	247
165°	584	602	639	678	689	165
175°	609	609	615	622	621	58
180°	610	610	610	610	610	



TEST NUMBER: P331419-840

CATALOG NUMBER: SA2XXDIP-C865D1080U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1393.6	1393.6	1393.6	1393.6	1393.6	1393.6	1393.6	1393.6	1393.6	1393.6	1393.6
2.5°	1400.1	1398.9	1397.7	1396.5	1395.3	1393.4	1390.8	1388.2	1385.5	1382.9	1385.3
5°	1393.6	1392.4	1391.3	1390.1	1388.9	1386.6	1383.4	1380.1	1376.8	1373.5	1375.9
7.5°	1381.3	1379.5	1377.7	1375.7	1373.9	1371.3	1368.0	1364.6	1361.3	1358.0	1360.4
10°	1369.5	1367.5	1365.3	1363.2	1361.2	1358.4	1354.7	1351.2	1347.7	1344.0	1346.5
12.5°	1353.4	1351.6	1349.8	1347.9	1346.0	1343.3	1339.8	1336.2	1332.6	1329.1	1330.7
15°	1326.7	1324.8	1323.0	1321.3	1319.5	1316.7	1312.8	1308.9	1305.0	1301.2	1302.3
17.5°	1292.3	1290.5	1288.8	1287.0	1285.2	1282.3	1278.4	1274.4	1270.5	1266.6	1268.0
20°	1267.7	1265.9	1264.1	1262.3	1260.5	1257.6	1253.3	1249.2	1245.1	1240.9	1241.7
22.5°	1243.0	1240.5	1238.0	1235.5	1233.0	1229.8	1225.9	1221.9	1218.0	1214.1	1214.3
25°	1200.6	1198.3	1195.9	1193.6	1191.1	1187.4	1182.3	1177.3	1172.3	1167.2	1167.8
27.5°	1152.5	1150.3	1148.1	1146.0	1143.9	1140.7	1136.8	1132.8	1128.8	1124.8	1124.0
30°	1120.2	1117.9	1115.5	1113.2	1110.8	1107.3	1102.9	1098.4	1093.9	1089.4	1088.5
32.5°	1086.0	1084.1	1082.2	1080.3	1078.3	1075.0	1070.4	1065.6	1061.0	1056.2	1054.6
35°	1035.8	1032.9	1029.9	1026.9	1023.9	1020.1	1015.3	1010.6	1005.7	1001.0	999.3
37.5°	979.3	976.6	974.0	971.4	968.9	965.1	960.4	955.6	950.8	946.0	943.8
40°	940.7	938.4	935.9	933.5	931.2	927.6	922.8	918.1	913.3	908.6	905.8
42.5°	903.2	900.8	898.4	896.1	893.6	890.1	885.3	880.6	875.8	871.0	868.1
45°	842.8	840.8	838.7	836.7	834.6	831.2	826.8	822.3	817.9	813.4	810.1
47.5°	782.8	780.9	778.9	777.0	775.0	771.6	767.0	762.3	757.7	753.1	749.6
50°	741.0	739.5	738.1	736.6	735.1	732.3	728.1	723.9	719.7	715.6	711.4
52.5°	700.3	698.3	696.4	694.4	692.5	689.5	685.6	681.7	677.7	673.8	670.3
55°	637.8	636.1	634.3	632.5	630.7	628.0	624.5	620.9	617.3	613.7	610.2
57.5°	575.1	573.7	572.3	570.9	569.5	566.7	562.8	558.9	554.9	551.0	547.5
60°	533.3	532.1	531.0	529.8	528.6	525.9	521.7	517.6	513.4	509.2	505.9
62.5°	492.6	490.7	488.8	486.9	484.9	482.4	479.2	475.9	472.7	469.6	466.6
65°	430.2	428.4	426.6	424.7	423.0	420.6	417.7	414.7	411.7	408.7	406.1
67.5°	366.7	365.2	363.8	362.3	360.9	358.9	356.2	353.5	350.8	348.1	346.1
70°	327.0	325.8	324.6	323.4	322.2	320.2	317.6	314.9	312.3	309.5	307.5
72.5°	286.2	285.1	283.9	282.7	281.4	280.0	278.3	276.6	274.8	273.1	271.0
75°	225.1	224.5	223.9	223.4	222.8	221.7	220.3	218.7	217.2	215.7	214.0
77.5°	170.5	169.5	168.4	167.4	166.4	165.6	165.0	164.4	163.8	163.2	162.3
80°	134.0	133.7	133.4	133.1	132.8	132.4	131.8	131.2	130.6	130.0	129.1
82.5°	99.7	99.7	99.6	99.5	99.5	99.3	98.9	98.6	98.2	97.9	96.6
85°	54.9	54.6	54.3	54.0	53.7	53.4	53.1	52.8	52.5	52.3	51.4
87.5°	19.5	19.8	20.2	20.2	20.2	20.4	21.1	22.3	23.2	23.0	22.0
90°	1.2	4.6	9.4	11.7	14.0	17.6	23.4	31.7	38.7	39.9	38.7
92.5°	14.3	20.6	29.1	34.2	42.2	53.2	79.8	117.0	150.4	152.5	128.9
95°	41.1	45.7	57.5	68.1	86.8	114.9	169.0	270.9	407.1	459.9	402.4
97.5°	66.9	73.2	85.6	101.6	123.2	155.1	222.9	365.1	591.3	785.1	823.5
100°	90.3	93.8	104.4	123.2	146.6	179.5	241.7	384.8	638.1	926.8	1095.7
102.5°	111.9	114.5	125.0	143.8	168.2	201.1	258.5	385.8	620.4	931.5	1197.1
105°	143.1	147.8	156.0	173.6	199.4	232.3	287.4	391.8	585.4	869.3	1181.3
107.5°	176.9	180.7	188.6	204.8	230.5	263.5	317.0	408.0	568.0	802.6	1078.3
110°	199.4	204.1	211.2	226.4	251.1	285.1	336.7	421.1	564.3	770.7	1013.6



TEST NUMBER: P331419-840

CATALOG NUMBER: SA2XXDIP-C865D1080U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	220.0	224.8	232.8	247.0	270.7	305.7	355.5	435.3	565.2	750.1	968.6
115°	252.3	258.1	265.1	279.2	302.7	334.4	384.8	456.4	570.2	727.3	912.7
117.5°	285.6	290.2	297.3	309.7	332.2	365.1	411.7	478.9	578.6	716.3	877.5
120°	306.2	310.8	317.9	328.5	351.9	384.8	430.5	493.9	584.2	709.7	858.7
122.5°	325.9	329.6	336.7	348.2	371.6	405.5	448.4	507.1	590.8	706.0	842.7
125°	351.9	355.5	362.5	376.6	400.0	432.9	475.1	528.0	600.7	699.2	820.0
127.5°	372.5	377.3	387.2	402.6	425.2	458.9	500.0	547.3	610.8	695.2	798.9
130°	384.8	389.5	401.2	417.7	441.1	473.9	515.0	559.6	618.2	693.3	784.9
132.5°	396.1	401.7	414.3	431.7	456.2	489.0	528.2	571.8	625.7	692.4	773.6
135°	412.9	417.7	431.7	449.3	476.3	509.2	546.6	587.7	634.7	690.9	757.8
137.5°	428.9	434.5	448.6	467.4	494.1	524.6	561.7	600.0	642.7	690.7	746.8
140°	441.1	445.8	459.9	478.7	504.4	534.9	570.2	606.5	646.4	689.8	740.2
142.5°	453.3	457.1	470.2	489.0	513.8	542.5	576.7	612.2	649.2	689.8	733.7
145°	471.6	476.3	488.1	505.6	529.1	554.9	586.5	619.5	652.3	687.4	725.0
147.5°	491.3	494.8	506.0	522.3	541.8	564.7	594.5	623.4	653.2	683.3	716.1
150°	504.4	508.0	517.4	532.6	550.2	571.3	598.3	625.3	652.3	680.4	708.5
152.5°	517.6	519.3	528.6	542.0	558.7	577.8	602.1	626.2	650.4	675.7	702.0
155°	536.1	537.2	544.3	557.2	570.2	587.7	607.6	627.6	647.5	667.5	689.8
157.5°	551.6	552.8	558.5	569.7	580.0	594.8	611.7	627.6	642.2	659.0	678.3
160°	561.9	563.1	567.7	577.1	586.5	599.5	613.6	627.6	639.3	653.5	669.8
162.5°	572.3	571.6	576.2	583.7	592.2	602.3	614.5	626.7	636.5	648.7	662.4
165°	584.2	583.1	585.4	592.4	598.3	605.3	615.9	624.1	631.2	639.3	649.9
167.5°	594.1	592.7	594.8	599.3	603.5	607.9	615.6	622.5	625.7	631.2	637.7
170°	600.7	598.3	599.5	603.0	605.3	608.8	614.7	620.6	622.9	626.4	631.2
172.5°	604.4	603.0	602.3	605.8	607.2	609.8	613.8	617.7	619.1	620.9	624.6
175°	608.8	607.6	606.5	608.8	608.8	610.1	612.4	614.7	613.6	614.7	615.9
177.5°	611.0	609.0	608.1	610.1	610.1	610.1	611.0	612.9	611.0	610.1	611.0
180°	610.1	610.1	610.1	610.1	610.1	610.1	610.1	610.1	610.1	610.1	610.1



TEST NUMBER: P331419-840
 CATALOG NUMBER: SA2XXDIP-C865D1080U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1393.6	1393.6	1393.6	1393.6	1393.6	1393.6	1393.6	1393.6
2.5°	1387.7	1390.1	1392.4	1393.4	1392.9	1392.4	1392.0	1391.5
5°	1378.3	1380.7	1383.1	1383.9	1383.4	1382.8	1382.2	1381.6
7.5°	1362.7	1365.1	1367.6	1368.4	1367.8	1367.1	1366.4	1365.7
10°	1348.8	1351.2	1353.6	1354.3	1353.4	1352.5	1351.6	1350.8
12.5°	1332.4	1334.0	1335.7	1336.3	1335.5	1334.9	1334.2	1333.6
15°	1303.5	1304.7	1306.0	1305.8	1304.3	1302.8	1301.3	1299.8
17.5°	1269.3	1270.7	1272.1	1272.0	1270.6	1269.2	1267.8	1266.4
20°	1242.6	1243.5	1244.5	1244.3	1243.1	1241.9	1240.7	1239.5
22.5°	1214.5	1214.6	1214.8	1214.6	1213.8	1213.0	1212.3	1211.6
25°	1168.4	1168.9	1169.5	1169.5	1168.9	1168.4	1167.8	1167.2
27.5°	1123.1	1122.2	1121.3	1120.1	1118.6	1117.2	1115.8	1114.4
30°	1087.6	1086.8	1085.9	1084.8	1083.7	1082.5	1081.3	1080.1
32.5°	1053.0	1051.4	1049.8	1048.3	1047.2	1046.0	1044.8	1043.6
35°	997.4	995.6	993.9	992.2	990.8	989.3	987.7	986.2
37.5°	941.7	939.5	937.3	935.4	934.0	932.6	931.2	929.7
40°	903.2	900.5	897.9	895.9	894.7	893.5	892.3	891.1
42.5°	865.2	862.2	859.4	857.1	855.4	853.7	852.0	850.4
45°	806.9	803.5	800.3	798.1	796.9	795.7	794.5	793.3
47.5°	746.2	742.8	739.3	736.7	735.0	733.3	731.5	729.8
50°	707.2	703.1	698.9	696.1	694.6	693.1	691.7	690.1
52.5°	666.8	663.4	659.9	657.2	655.3	653.3	651.4	649.3
55°	606.6	603.0	599.5	596.9	595.4	593.9	592.5	591.0
57.5°	544.0	540.5	536.9	534.6	533.5	532.4	531.3	530.1
60°	502.7	499.4	496.1	494.0	493.1	492.2	491.3	490.5
62.5°	463.4	460.4	457.4	455.3	454.1	453.0	451.9	450.8
65°	403.3	400.7	398.0	395.9	394.5	392.9	391.4	389.9
67.5°	344.0	341.8	339.8	338.2	337.0	335.8	334.6	333.4
70°	305.4	303.3	301.2	299.5	298.4	297.2	296.0	294.8
72.5°	268.9	266.8	264.8	263.3	262.3	261.4	260.3	259.4
75°	212.2	210.4	208.6	208.0	208.6	209.2	209.7	210.4
77.5°	161.5	160.6	159.7	158.8	157.9	157.1	156.3	155.4
80°	128.2	127.3	126.4	125.6	125.0	124.5	123.9	123.3
82.5°	95.5	94.4	93.3	92.7	92.5	92.4	92.3	92.2
85°	50.5	49.6	48.7	48.1	47.8	47.5	47.2	46.9
87.5°	21.1	19.9	19.7	19.4	19.2	19.0	18.7	18.5
90°	37.6	35.2	37.6	38.7	38.7	38.7	38.7	38.7
92.5°	102.3	87.8	77.9	70.6	69.7	65.9	66.9	65.0
95°	307.4	235.8	186.5	160.7	145.4	136.1	132.6	133.7
97.5°	717.2	586.8	459.9	375.2	319.1	290.2	273.1	263.3
100°	1071.1	925.6	764.9	622.9	525.5	475.1	441.1	420.0
102.5°	1302.9	1270.0	1152.5	1002.1	896.3	810.2	767.7	739.1
105°	1425.3	1557.9	1573.2	1534.5	1461.7	1389.0	1338.6	1322.1
107.5°	1337.2	1536.8	1658.8	1715.6	1724.7	1720.7	1710.6	1688.8
110°	1261.1	1471.1	1621.2	1717.5	1767.9	1790.2	1800.8	1799.6



TEST NUMBER: P331419-840

CATALOG NUMBER: SA2XXDIP-C865D1080U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	1191.6	1393.2	1553.7	1664.0	1734.1	1771.4	1791.4	1797.7
115°	1106.3	1287.0	1440.6	1561.5	1644.8	1698.7	1729.2	1739.8
117.5°	1042.0	1200.6	1340.0	1453.3	1538.2	1595.2	1627.4	1636.3
120°	1010.1	1155.5	1279.9	1386.6	1468.7	1523.9	1557.9	1569.6
122.5°	984.7	1118.0	1235.8	1332.2	1405.8	1460.1	1490.4	1500.2
125°	947.9	1068.7	1171.9	1259.9	1328.0	1372.6	1401.9	1411.3
127.5°	911.5	1020.9	1118.2	1199.4	1258.8	1300.5	1325.9	1333.4
130°	888.1	989.0	1081.7	1159.0	1216.6	1256.5	1279.9	1289.3
132.5°	865.6	959.0	1044.1	1116.8	1173.4	1213.3	1234.9	1243.2
135°	834.0	911.5	989.0	1054.6	1105.1	1143.8	1164.9	1169.6
137.5°	809.0	873.7	935.2	992.5	1038.4	1071.8	1090.4	1097.3
140°	793.0	849.4	903.3	954.9	992.5	1023.0	1040.6	1047.6
142.5°	779.9	827.8	874.2	917.4	953.0	980.8	996.4	997.8
145°	761.3	800.1	836.5	870.5	898.6	918.6	930.3	933.8
147.5°	747.1	777.6	806.0	830.8	854.0	870.0	878.0	880.1
150°	736.7	762.5	787.2	808.3	825.9	840.0	847.0	848.2
152.5°	726.4	750.3	771.2	789.5	803.3	815.6	820.7	820.9
155°	712.1	730.8	748.4	761.3	774.3	782.4	787.2	784.9
157.5°	695.4	711.1	725.9	736.0	745.2	751.9	754.1	754.1
160°	685.1	698.0	710.9	719.1	727.3	733.2	734.4	734.4
162.5°	674.8	685.8	696.8	703.2	711.3	715.4	716.5	715.6
165°	659.3	667.5	675.7	680.4	685.1	689.8	689.8	688.6
167.5°	644.5	650.9	656.5	660.8	662.8	665.4	665.2	663.8
170°	637.0	640.6	645.2	647.5	648.7	652.3	651.1	648.7
172.5°	628.5	631.2	634.9	636.3	637.5	639.1	637.9	636.5
175°	619.5	620.6	621.8	622.9	622.9	624.1	622.9	620.6
177.5°	612.9	612.9	613.8	613.8	613.8	613.8	612.9	611.0
180°	610.1	610.1	610.1	610.1	610.1	610.1	610.1	610.1

(END OF REPORT)