

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331436

Luminaire Tested: **SA2XXDIP-C1005D530U835-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331436
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C1005D530U835-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 530 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5947.1 lumens
Efficiency: N/A
Efficacy: 107.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 55.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331436
CATALOG NUMBER: SA2XXDIP-C1005D530U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331436

CATALOG NUMBER: SA2XXDIP-C1005D530U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	111	111	111	111	105	105	105	105	93	93	93	83	83	83	73	73	73	68				
1	102	97	93	90	96	92	89	85	82	79	77	73	71	69	64	63	62	57				
2	93	85	79	73	87	81	75	70	72	68	64	64	61	58	57	54	52	48				
3	85	75	67	61	80	71	64	59	64	58	54	57	52	49	50	47	44	41				
4	78	66	58	52	73	63	56	50	57	51	46	51	46	42	45	41	38	35				
5	71	59	51	45	67	56	49	43	51	44	40	45	40	36	41	36	33	30				
6	66	53	45	39	62	51	43	37	46	39	35	41	36	32	37	33	29	27				
7	61	48	40	34	57	46	38	33	42	35	31	37	32	28	34	29	26	24				
8	57	44	36	30	53	42	35	29	38	32	27	34	29	25	31	27	23	21				
9	53	40	32	27	50	38	31	26	35	29	25	32	27	23	29	24	21	19				
10	49	37	30	25	47	35	28	24	32	26	22	29	24	21	27	22	19	17				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	25733	25733	25733
5°	25832	25459	25608
10°	25678	25201	25327
15°	25361	24874	24849
20°	24911	24383	24357
25°	24464	23779	23779
30°	23886	23228	23029
35°	23349	22565	22231
40°	22675	21901	21479
45°	22012	21240	20717
50°	21288	20557	19826
55°	20535	19758	19023
60°	19695	18807	18112
65°	18793	17857	17039
70°	17651	16711	15918
75°	16064	15390	15009
80°	14254	13826	13110
85°	11634	11078	9930



TEST NUMBER: P331436

CATALOG NUMBER: SA2XXDIP-C1005D530U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	149.9	2.5
10°-20°	421.7	7.1
20°-30°	619.8	10.4
30°-40°	720.0	12.1
40°-50°	719.2	12.1
50°-60°	627.2	10.5
60°-70°	463.8	7.8
70°-80°	262.7	4.4
80°-90°	73.3	1.2
90°-100°	42.8	0.7
100°-110°	133.0	2.2
110°-120°	227.3	3.8
120°-130°	298.9	5.0
130°-140°	335.5	5.6
140°-150°	329.0	5.5
150°-160°	275.9	4.6
160°-170°	183.0	3.1
170°-180°	64.0	1.1
0°-30°	1191.4	20.0
0°-40°	1911.4	32.1
0°-60°	3257.9	54.8
0°-90°	4057.6	68.2
90°-120°	403.1	6.8
90°-150°	1366.6	23.0
90°-180°	1889.0	31.8
0°-180°	5947.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1594	1594	1594	1594	1594	
5°	1594	1587	1571	1582	1580	151
15°	1517	1507	1488	1493	1487	427
25°	1373	1360	1335	1338	1335	631
35°	1185	1169	1145	1136	1128	739
45°	964	953	930	914	907	744
55°	730	720	702	684	676	652
65°	492	482	467	454	446	486
75°	258	254	247	238	241	275
85°	63	61	60	55	54	72
90°	1	8	20	19	19	5
95°	30	35	36	36	35	34
105°	123	124	126	127	127	129
115°	228	231	230	230	228	226
125°	332	337	335	334	333	296
135°	429	435	437	436	434	332
145°	521	525	529	529	527	325
155°	596	598	599	602	600	274
165°	648	648	648	651	649	183
175°	675	673	672	675	672	64
180°	676	676	676	676	676	



TEST NUMBER: P331436

CATALOG NUMBER: SA2XXDIP-C1005D530U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8
2.5°	1601.2	1599.8	1598.5	1597.1	1595.7	1593.6	1590.6	1587.6	1584.6	1581.6	1584.3
5°	1593.8	1592.5	1591.1	1589.7	1588.4	1585.8	1582.1	1578.3	1574.6	1570.8	1573.6
7.5°	1579.7	1577.6	1575.5	1573.4	1571.3	1568.3	1564.5	1560.7	1556.9	1553.1	1555.8
10°	1566.2	1563.9	1561.5	1559.1	1556.7	1553.5	1549.4	1545.3	1541.2	1537.1	1539.9
12.5°	1547.9	1545.7	1543.6	1541.5	1539.4	1536.3	1532.2	1528.1	1524.1	1520.0	1521.9
15°	1517.2	1515.2	1513.1	1511.1	1509.0	1505.8	1501.4	1496.9	1492.5	1488.1	1489.5
17.5°	1478.0	1475.9	1473.9	1471.8	1469.8	1466.5	1462.0	1457.5	1453.0	1448.6	1450.1
20°	1449.8	1447.7	1445.7	1443.6	1441.6	1438.2	1433.4	1428.7	1423.9	1419.1	1420.1
22.5°	1421.6	1418.7	1415.9	1413.0	1410.1	1406.5	1402.0	1397.5	1393.0	1388.5	1388.7
25°	1373.2	1370.4	1367.7	1365.0	1362.3	1358.0	1352.2	1346.4	1340.6	1334.8	1335.5
27.5°	1318.0	1315.5	1313.1	1310.6	1308.2	1304.7	1300.1	1295.5	1291.0	1286.4	1285.4
30°	1281.2	1278.5	1275.7	1273.0	1270.3	1266.4	1261.3	1256.2	1251.1	1245.9	1244.9
32.5°	1242.0	1239.8	1237.6	1235.4	1233.2	1229.5	1224.1	1218.7	1213.3	1207.9	1206.1
35°	1184.6	1181.2	1177.8	1174.4	1171.0	1166.6	1161.1	1155.7	1150.3	1144.8	1142.8
37.5°	1120.0	1117.0	1114.0	1111.0	1108.0	1103.8	1098.3	1092.9	1087.4	1082.0	1079.4
40°	1075.8	1073.1	1070.4	1067.7	1064.9	1060.9	1055.4	1050.0	1044.5	1039.1	1036.0
42.5°	1032.9	1030.2	1027.5	1024.8	1022.0	1017.9	1012.5	1007.0	1001.6	996.1	992.8
45°	964.0	961.6	959.2	956.8	954.4	950.7	945.6	940.5	935.4	930.2	926.5
47.5°	895.3	893.1	890.8	888.6	886.3	882.5	877.2	871.9	866.6	861.3	857.3
50°	847.5	845.8	844.1	842.4	840.7	837.4	832.7	827.9	823.1	818.4	813.6
52.5°	800.9	798.7	796.4	794.2	791.9	788.5	784.0	779.5	775.1	770.6	766.6
55°	729.5	727.4	725.4	723.4	721.3	718.2	714.2	710.1	706.0	701.9	697.8
57.5°	657.8	656.1	654.5	652.9	651.2	648.2	643.7	639.2	634.7	630.2	626.2
60°	609.9	608.6	607.2	605.9	604.5	601.4	596.7	591.9	587.1	582.4	578.6
62.5°	563.4	561.2	559.0	556.8	554.6	551.7	548.0	544.4	540.7	537.0	533.5
65°	491.9	489.9	487.9	485.8	483.8	481.0	477.6	474.2	470.8	467.4	464.4
67.5°	419.3	417.7	416.0	414.4	412.8	410.4	407.3	404.3	401.2	398.2	395.8
70°	373.9	372.6	371.2	369.9	368.5	366.3	363.2	360.1	357.1	354.0	351.6
72.5°	327.3	326.0	324.6	323.3	321.9	320.2	318.3	316.3	314.3	312.3	309.9
75°	257.5	256.8	256.1	255.4	254.7	253.5	251.8	250.1	248.4	246.7	244.7
77.5°	194.9	193.8	192.6	191.5	190.3	189.4	188.7	188.0	187.3	186.7	185.6
80°	153.3	152.9	152.6	152.2	151.9	151.4	150.7	150.0	149.3	148.7	147.6
82.5°	114.0	114.0	113.9	113.8	113.7	113.5	113.1	112.7	112.3	111.9	110.6
85°	62.8	62.5	62.2	61.8	61.5	61.1	60.8	60.4	60.1	59.8	58.7
87.5°	22.2	21.9	21.7	21.5	21.2	21.1	21.1	21.1	21.1	21.2	20.3
90°	0.6	2.1	3.6	5.1	6.7	8.8	11.6	14.4	17.2	20.0	19.7
92.5°	10.2	11.3	12.4	13.5	14.6	15.5	16.2	16.8	17.5	18.1	18.2
95°	29.7	30.9	32.2	33.5	34.7	35.5	35.7	36.0	36.2	36.5	36.5
97.5°	54.2	55.3	56.4	57.5	58.6	59.4	59.9	60.4	60.9	61.4	61.4
100°	72.4	73.4	74.4	75.5	76.5	77.2	77.6	77.9	78.3	78.7	78.7
102.5°	91.6	92.4	93.2	94.0	94.8	95.5	96.0	96.4	96.9	97.4	97.5
105°	122.6	123.0	123.4	123.7	124.1	124.4	124.7	124.9	125.2	125.5	125.7
107.5°	153.9	154.4	155.0	155.5	156.1	156.4	156.4	156.4	156.4	156.4	156.5
110°	173.9	174.7	175.4	176.2	177.0	177.3	177.3	177.3	177.3	177.3	177.3



TEST NUMBER: P331436

CATALOG NUMBER: SA2XXDIP-C1005D530U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	195.8	196.6	197.3	198.1	198.9	199.2	199.1	199.0	198.9	198.8	198.5
115°	228.1	228.9	229.6	230.4	231.1	231.4	231.1	230.9	230.6	230.4	230.3
117.5°	260.3	261.3	262.3	263.3	264.3	264.5	263.8	263.0	262.3	261.6	261.3
120°	281.7	282.7	283.7	284.7	285.8	285.8	284.7	283.7	282.7	281.7	281.7
122.5°	301.3	302.5	303.8	305.0	306.2	306.4	305.7	305.0	304.3	303.6	303.3
125°	331.9	333.0	334.2	335.3	336.4	336.8	336.4	336.1	335.7	335.3	334.9
127.5°	361.6	363.1	364.5	366.0	367.4	367.9	367.5	367.0	366.6	366.1	365.6
130°	380.4	382.0	383.6	385.3	386.9	387.6	387.4	387.1	386.9	386.6	386.4
132.5°	401.3	402.7	404.0	405.4	406.7	407.4	407.5	407.5	407.6	407.6	407.1
135°	429.4	430.8	432.2	433.6	435.0	435.8	436.0	436.3	436.6	436.8	436.7
137.5°	458.9	460.1	461.2	462.4	463.5	464.2	464.6	464.9	465.2	465.5	465.4
140°	476.7	477.9	479.0	480.1	481.3	482.2	482.8	483.4	484.1	484.7	484.7
142.5°	495.0	496.1	497.3	498.4	499.5	500.3	500.8	501.2	501.6	502.0	502.1
145°	521.2	522.1	523.0	523.9	524.8	525.6	526.3	527.1	527.9	528.6	528.7
147.5°	544.6	545.6	546.7	547.8	548.8	549.6	550.1	550.6	551.1	551.7	551.9
150°	560.6	561.3	562.1	562.8	563.6	564.2	564.7	565.2	565.7	566.3	566.6
152.5°	574.7	575.5	576.2	577.0	577.7	578.4	579.0	579.6	580.2	580.9	581.3
155°	595.9	596.3	596.7	597.0	597.4	597.8	598.2	598.6	598.9	599.3	600.0
157.5°	614.0	614.3	614.5	614.8	615.1	615.3	615.5	615.8	616.0	616.2	617.1
160°	625.0	625.2	625.5	625.7	626.0	626.2	626.3	626.4	626.6	626.7	627.5
162.5°	635.0	635.1	635.1	635.2	635.2	635.3	635.4	635.6	635.7	635.8	636.7
165°	648.4	648.2	648.1	648.0	647.9	647.8	647.8	647.8	647.8	647.8	648.7
167.5°	659.5	659.2	658.8	658.4	658.0	657.8	657.8	657.8	657.7	657.7	658.6
170°	665.5	665.1	664.7	664.3	664.0	663.7	663.6	663.4	663.3	663.2	664.1
172.5°	669.6	669.2	668.8	668.4	668.1	667.8	667.7	667.6	667.4	667.3	668.2
175°	674.6	674.2	673.8	673.5	673.1	672.8	672.5	672.3	672.0	671.7	672.6
177.5°	676.7	676.3	676.0	675.7	675.4	675.2	675.0	674.8	674.6	674.4	675.0
180°	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7



TEST NUMBER: P331436

CATALOG NUMBER: SA2XXDIP-C1005D530U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8	1593.8
2.5°	1587.0	1589.7	1592.5	1593.6	1593.0	1592.5	1591.9	1591.4
5°	1576.3	1579.0	1581.7	1582.8	1582.1	1581.4	1580.7	1580.0
7.5°	1558.5	1561.2	1564.0	1565.0	1564.2	1563.5	1562.7	1562.0
10°	1542.6	1545.3	1548.0	1548.9	1547.9	1546.8	1545.8	1544.8
12.5°	1523.8	1525.7	1527.6	1528.2	1527.4	1526.7	1525.9	1525.2
15°	1490.8	1492.2	1493.5	1493.4	1491.7	1490.0	1488.3	1486.6
17.5°	1451.7	1453.3	1454.8	1454.8	1453.1	1451.5	1449.9	1448.2
20°	1421.2	1422.2	1423.2	1423.0	1421.7	1420.3	1419.0	1417.6
22.5°	1388.9	1389.1	1389.3	1389.0	1388.2	1387.4	1386.5	1385.7
25°	1336.2	1336.9	1337.6	1337.6	1336.9	1336.2	1335.5	1334.8
27.5°	1284.4	1283.3	1282.3	1281.0	1279.4	1277.7	1276.1	1274.5
30°	1243.9	1242.9	1241.9	1240.7	1239.3	1237.9	1236.6	1235.2
32.5°	1204.3	1202.4	1200.6	1199.0	1197.6	1196.3	1194.9	1193.5
35°	1140.7	1138.7	1136.6	1134.8	1133.1	1131.4	1129.6	1127.9
37.5°	1076.9	1074.4	1071.9	1069.8	1068.2	1066.5	1064.9	1063.3
40°	1032.9	1029.9	1026.8	1024.6	1023.2	1021.9	1020.5	1019.1
42.5°	989.5	986.1	982.8	980.2	978.3	976.4	974.5	972.5
45°	922.8	919.0	915.3	912.7	911.3	910.0	908.6	907.3
47.5°	853.4	849.4	845.5	842.5	840.5	838.6	836.6	834.6
50°	808.8	804.1	799.3	796.1	794.4	792.7	791.0	789.3
52.5°	762.7	758.7	754.8	751.7	749.4	747.2	744.9	742.7
55°	693.7	689.6	685.6	682.7	681.0	679.3	677.6	675.8
57.5°	622.1	618.1	614.1	611.4	610.2	608.9	607.6	606.3
60°	574.9	571.1	567.4	565.0	564.0	563.0	561.9	560.9
62.5°	530.1	526.6	523.1	520.7	519.4	518.1	516.8	515.5
65°	461.3	458.2	455.2	452.8	451.1	449.4	447.7	446.0
67.5°	393.4	391.0	388.6	386.7	385.4	384.0	382.7	381.3
70°	349.2	346.9	344.5	342.6	341.2	339.9	338.5	337.2
72.5°	307.6	305.2	302.8	301.1	300.0	298.9	297.8	296.7
75°	242.7	240.6	238.6	237.9	238.6	239.2	239.9	240.6
77.5°	184.6	183.6	182.6	181.6	180.6	179.7	178.7	177.8
80°	146.6	145.6	144.6	143.7	143.0	142.4	141.7	141.0
82.5°	109.3	108.0	106.7	106.0	105.8	105.7	105.6	105.4
85°	57.7	56.7	55.7	55.0	54.7	54.3	54.0	53.6
87.5°	19.4	18.6	17.7	17.1	16.9	16.6	16.4	16.1
90°	19.5	19.2	18.9	18.9	19.0	19.1	19.3	19.4
92.5°	18.2	18.3	18.3	18.4	18.4	18.4	18.5	18.5
95°	36.5	36.5	36.5	36.4	36.1	35.9	35.6	35.4
97.5°	61.4	61.4	61.4	61.3	61.3	61.3	61.3	61.2
100°	78.7	78.7	78.7	78.6	78.5	78.4	78.3	78.1
102.5°	97.6	97.7	97.8	97.8	97.7	97.5	97.4	97.3
105°	126.0	126.2	126.5	126.6	126.6	126.6	126.6	126.6
107.5°	156.6	156.7	156.8	156.5	155.9	155.4	154.8	154.2
110°	177.3	177.3	177.3	177.2	176.8	176.4	176.0	175.6



TEST NUMBER: P331436

CATALOG NUMBER: SA2XXDIP-C1005D530U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	198.2	197.9	197.6	197.3	197.0	196.7	196.4	196.2
115°	230.1	230.0	229.9	229.6	229.2	228.9	228.5	228.1
117.5°	261.0	260.7	260.4	260.1	259.7	259.3	258.9	258.5
120°	281.7	281.7	281.7	281.5	281.1	280.8	280.4	280.0
122.5°	303.0	302.7	302.4	302.1	301.8	301.5	301.3	301.0
125°	334.5	334.2	333.8	333.5	333.4	333.3	333.1	333.0
127.5°	365.2	364.7	364.3	363.8	363.4	363.0	362.6	362.2
130°	386.1	385.9	385.6	385.2	384.7	384.2	383.7	383.2
132.5°	406.5	405.9	405.4	404.9	404.5	404.1	403.7	403.3
135°	436.6	436.4	436.3	436.0	435.7	435.3	434.9	434.5
137.5°	465.3	465.2	465.1	464.8	464.3	463.8	463.3	462.8
140°	484.7	484.7	484.7	484.5	483.9	483.4	482.9	482.4
142.5°	502.2	502.3	502.4	502.2	501.7	501.2	500.7	500.2
145°	528.9	529.0	529.1	528.9	528.4	527.9	527.4	526.9
147.5°	552.2	552.5	552.8	552.7	552.2	551.7	551.2	550.7
150°	567.0	567.4	567.8	567.8	567.4	567.0	566.6	566.3
152.5°	581.8	582.3	582.8	582.8	582.3	581.8	581.3	580.9
155°	600.6	601.2	601.9	602.0	601.6	601.2	600.8	600.5
157.5°	617.9	618.8	619.7	619.8	619.2	618.6	618.0	617.3
160°	628.2	629.0	629.7	629.9	629.4	628.9	628.3	627.8
162.5°	637.5	638.4	639.3	639.4	638.8	638.2	637.6	637.0
165°	649.6	650.5	651.3	651.5	650.8	650.2	649.6	648.9
167.5°	659.5	660.4	661.3	661.4	660.7	660.1	659.4	658.7
170°	665.0	665.9	666.7	666.8	666.0	665.3	664.5	663.8
172.5°	669.1	670.0	670.8	670.9	670.2	669.4	668.6	667.9
175°	673.5	674.4	675.3	675.4	674.6	673.8	673.1	672.3
177.5°	675.6	676.2	676.8	676.8	676.2	675.6	675.0	674.4
180°	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7

(END OF REPORT)