

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331390-840

Luminaire Tested: **SA2XXDIP-C865D530U840-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331390-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C865D530U840-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 530 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5681.8 lumens
Efficiency: N/A
Efficacy: 116.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 48.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331390-840
CATALOG NUMBER: SA2XXDIP-C865D530U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331390-840

CATALOG NUMBER: SA2XXDIP-C865D530U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	68	68	68	68	68	68	62																
1	101	96	92	89	94	90	87	84	79	77	74	69	67	65	60	58	57	60	58	57	53																
2	92	84	78	72	86	79	73	69	69	65	61	61	57	55	53	50	48	53	50	48	44																
3	84	74	66	60	78	70	63	57	61	56	52	54	50	46	47	44	41	47	44	41	37																
4	77	65	57	51	71	62	54	49	54	49	44	48	43	40	42	38	35	42	38	35	32																
5	70	58	50	44	66	55	48	42	49	43	38	43	38	34	38	34	31	38	34	31	28																
6	65	52	44	38	61	50	42	37	44	38	33	39	34	30	34	30	27	34	30	27	24																
7	60	47	39	34	56	45	37	32	40	34	29	35	30	27	31	27	24	31	27	24	22																
8	56	43	35	30	52	41	34	29	37	31	26	32	28	24	29	25	22	29	25	22	19																
9	52	39	32	27	49	37	30	26	34	28	24	30	25	22	26	22	20	26	22	20	18																
10	49	36	29	24	46	34	28	23	31	25	21	28	23	20	25	21	18	25	21	18	16																

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	22501	22501	22501
5°	22587	22261	22392
10°	22453	22035	22146
15°	22176	21750	21727
20°	21782	21321	21297
25°	21389	20794	20794
30°	20885	20310	20137
35°	20416	19730	19438
40°	19827	19150	18782
45°	19244	18573	18114
50°	18613	17975	17334
55°	17954	17275	16636
60°	17221	16443	15839
65°	16435	15614	14896
70°	15437	14611	13917
75°	14042	13456	13125
80°	12459	12087	11464
85°	10170	9689	8688



TEST NUMBER: P331390-840

CATALOG NUMBER: SA2XXDIP-C865D530U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	131.0	2.3
10°-20°	368.7	6.5
20°-30°	542.0	9.5
30°-40°	629.6	11.1
40°-50°	628.9	11.1
50°-60°	548.4	9.7
60°-70°	405.5	7.1
70°-80°	229.7	4.0
80°-90°	63.6	1.1
90°-100°	24.3	0.4
100°-110°	89.1	1.6
110°-120°	238.2	4.2
120°-130°	393.1	6.9
130°-140°	418.1	7.4
140°-150°	388.6	6.8
150°-160°	312.4	5.5
160°-170°	201.3	3.5
170°-180°	69.3	1.2
0°-30°	1041.8	18.3
0°-40°	1671.3	29.4
0°-60°	2848.6	50.1
0°-90°	3547.4	62.4
90°-120°	351.5	6.2
90°-150°	1551.4	27.3
90°-180°	2134.0	37.6
0°-180°	5681.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1394	1394	1394	1394	1394	
5°	1394	1388	1374	1384	1382	132
15°	1327	1318	1301	1306	1300	373
25°	1201	1189	1167	1170	1167	552
35°	1036	1022	1001	993	986	646
45°	843	833	813	799	793	650
55°	638	629	614	598	591	570
65°	430	422	409	397	390	425
75°	225	222	216	208	210	240
85°	55	54	52	48	47	63
90°	0	6	10	13	14	4
95°	34	18	21	23	23	42
105°	160	167	32	38	40	171
115°	303	312	325	93	43	298
125°	428	436	445	449	451	382
135°	530	538	543	548	548	409
145°	615	615	624	627	624	385
155°	677	673	679	682	678	312
165°	714	711	712	715	712	202
175°	730	726	727	730	726	69
180°	728	728	728	728	728	



TEST NUMBER: P331390-840

CATALOG NUMBER: SA2XXDIP-C865D530U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1393.6	1393.6	1393.6	1393.6	1393.6	1393.6	1393.6	1393.6	1393.6	1393.6	1393.6
2.5°	1400.1	1398.9	1397.7	1396.5	1395.3	1393.4	1390.8	1388.2	1385.5	1382.9	1385.3
5°	1393.6	1392.4	1391.3	1390.1	1388.9	1386.6	1383.4	1380.1	1376.8	1373.5	1375.9
7.5°	1381.3	1379.5	1377.7	1375.7	1373.9	1371.3	1368.0	1364.6	1361.3	1358.0	1360.4
10°	1369.5	1367.5	1365.3	1363.2	1361.2	1358.4	1354.7	1351.2	1347.7	1344.0	1346.5
12.5°	1353.4	1351.6	1349.8	1347.9	1346.0	1343.3	1339.8	1336.2	1332.6	1329.1	1330.7
15°	1326.7	1324.8	1323.0	1321.3	1319.5	1316.7	1312.8	1308.9	1305.0	1301.2	1302.3
17.5°	1292.3	1290.5	1288.8	1287.0	1285.2	1282.3	1278.4	1274.4	1270.5	1266.6	1268.0
20°	1267.7	1265.9	1264.1	1262.3	1260.5	1257.6	1253.3	1249.2	1245.1	1240.9	1241.7
22.5°	1243.0	1240.5	1238.0	1235.5	1233.0	1229.8	1225.9	1221.9	1218.0	1214.1	1214.3
25°	1200.6	1198.3	1195.9	1193.6	1191.1	1187.4	1182.3	1177.3	1172.3	1167.2	1167.8
27.5°	1152.5	1150.3	1148.1	1146.0	1143.9	1140.7	1136.8	1132.8	1128.8	1124.8	1124.0
30°	1120.2	1117.9	1115.5	1113.2	1110.8	1107.3	1102.9	1098.4	1093.9	1089.4	1088.5
32.5°	1086.0	1084.1	1082.2	1080.3	1078.3	1075.0	1070.4	1065.6	1061.0	1056.2	1054.6
35°	1035.8	1032.9	1029.9	1026.9	1023.9	1020.1	1015.3	1010.6	1005.7	1001.0	999.3
37.5°	979.3	976.6	974.0	971.4	968.9	965.1	960.4	955.6	950.8	946.0	943.8
40°	940.7	938.4	935.9	933.5	931.2	927.6	922.8	918.1	913.3	908.6	905.8
42.5°	903.2	900.8	898.4	896.1	893.6	890.1	885.3	880.6	875.8	871.0	868.1
45°	842.8	840.8	838.7	836.7	834.6	831.2	826.8	822.3	817.9	813.4	810.1
47.5°	782.8	780.9	778.9	777.0	775.0	771.6	767.0	762.3	757.7	753.1	749.6
50°	741.0	739.5	738.1	736.6	735.1	732.3	728.1	723.9	719.7	715.6	711.4
52.5°	700.3	698.3	696.4	694.4	692.5	689.5	685.6	681.7	677.7	673.8	670.3
55°	637.8	636.1	634.3	632.5	630.7	628.0	624.5	620.9	617.3	613.7	610.2
57.5°	575.1	573.7	572.3	570.9	569.5	566.7	562.8	558.9	554.9	551.0	547.5
60°	533.3	532.1	531.0	529.8	528.6	525.9	521.7	517.6	513.4	509.2	505.9
62.5°	492.6	490.7	488.8	486.9	484.9	482.4	479.2	475.9	472.7	469.6	466.6
65°	430.2	428.4	426.6	424.7	423.0	420.6	417.7	414.7	411.7	408.7	406.1
67.5°	366.7	365.2	363.8	362.3	360.9	358.9	356.2	353.5	350.8	348.1	346.1
70°	327.0	325.8	324.6	323.4	322.2	320.2	317.6	314.9	312.3	309.5	307.5
72.5°	286.2	285.1	283.9	282.7	281.4	280.0	278.3	276.6	274.8	273.1	271.0
75°	225.1	224.5	223.9	223.4	222.8	221.7	220.3	218.7	217.2	215.7	214.0
77.5°	170.5	169.5	168.4	167.4	166.4	165.6	165.0	164.4	163.8	163.2	162.3
80°	134.0	133.7	133.4	133.1	132.8	132.4	131.8	131.2	130.6	130.0	129.1
82.5°	99.7	99.7	99.6	99.5	99.5	99.3	98.9	98.6	98.2	97.9	96.6
85°	54.9	54.6	54.3	54.0	53.7	53.4	53.1	52.8	52.5	52.3	51.4
87.5°	19.4	19.2	19.0	18.8	18.5	18.3	18.0	17.7	17.4	17.1	16.6
90°	0.5	1.8	3.1	4.3	5.7	6.8	7.8	8.7	9.6	10.5	11.1
92.5°	10.6	10.5	10.4	10.3	10.2	10.4	10.8	11.3	11.7	12.2	12.5
95°	34.2	30.4	26.6	22.6	18.8	17.3	18.1	18.9	19.7	20.6	21.1
97.5°	68.0	57.1	46.3	35.3	24.4	19.9	21.8	23.7	25.7	27.5	28.0
100°	93.3	77.3	61.2	45.1	29.1	22.1	24.0	26.1	28.1	30.0	31.0
102.5°	121.1	117.8	114.3	110.9	107.6	97.5	80.9	64.2	47.6	30.9	32.1
105°	160.2	163.7	167.2	170.8	174.3	160.1	128.1	96.1	64.1	32.1	33.4
107.5°	204.8	207.6	210.5	213.3	216.1	198.3	160.1	121.7	83.3	45.0	43.7
110°	233.5	235.9	238.4	240.9	243.3	227.6	193.8	160.0	126.0	92.2	80.5



TEST NUMBER: P331390-840

CATALOG NUMBER: SA2XXDIP-C865D530U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	260.4	262.7	264.8	267.0	269.1	266.1	257.7	249.3	241.0	232.7	189.9
115°	303.1	305.0	307.0	309.0	311.0	313.5	316.4	319.3	322.2	325.2	270.9
117.5°	341.1	343.4	345.6	347.8	350.0	352.1	354.2	356.2	358.2	360.1	347.1
120°	368.9	370.6	372.4	374.2	376.0	377.9	380.0	382.1	384.2	386.3	387.7
122.5°	392.5	394.4	396.3	398.1	399.9	402.0	404.2	406.6	408.9	411.2	412.0
125°	428.5	430.0	431.5	433.0	434.5	436.5	438.7	440.9	443.1	445.4	446.2
127.5°	461.0	462.7	464.4	466.1	467.8	469.5	471.1	472.8	474.4	476.2	477.3
130°	481.7	483.5	485.4	487.4	489.2	490.8	492.1	493.3	494.6	495.9	497.3
132.5°	502.8	504.3	505.9	507.6	509.2	510.6	511.9	513.2	514.4	515.7	516.8
135°	530.2	532.1	533.9	535.8	537.7	539.2	540.2	541.3	542.3	543.3	544.5
137.5°	558.0	559.2	560.5	561.8	563.1	564.4	565.6	566.8	567.9	569.2	570.4
140°	576.0	576.9	577.9	578.9	579.8	580.9	582.2	583.5	584.7	586.0	587.1
142.5°	591.2	592.1	592.9	593.7	594.6	595.7	597.2	598.6	600.2	601.7	602.6
145°	615.0	614.9	614.8	614.7	614.6	615.5	617.5	619.5	621.5	623.5	624.3
147.5°	635.8	635.3	634.9	634.5	634.0	634.8	636.7	638.7	640.7	642.7	643.3
150°	649.2	648.4	647.6	646.8	646.0	646.5	648.4	650.3	652.2	654.0	654.7
152.5°	660.7	659.7	658.8	657.9	657.0	657.4	659.2	661.1	662.8	664.6	665.3
155°	677.2	676.2	675.1	674.1	673.0	673.2	674.6	676.0	677.4	678.8	679.5
157.5°	690.1	689.3	688.4	687.5	686.6	686.7	687.6	688.6	689.6	690.6	691.4
160°	697.8	697.1	696.4	695.7	695.0	695.0	695.7	696.4	697.1	697.8	698.5
162.5°	704.5	703.8	703.1	702.4	701.8	701.7	702.3	702.9	703.5	704.1	704.9
165°	713.6	712.9	712.2	711.4	710.7	710.6	710.9	711.2	711.7	712.0	712.9
167.5°	720.3	719.6	718.9	718.2	717.5	717.3	717.6	718.0	718.3	718.6	719.4
170°	724.1	723.5	722.8	722.1	721.3	721.0	721.3	721.5	721.8	722.1	722.9
172.5°	726.7	726.0	725.3	724.6	723.9	723.6	723.9	724.1	724.3	724.6	725.4
175°	729.9	729.1	728.3	727.5	726.6	726.4	726.6	726.8	727.0	727.3	728.1
177.5°	730.4	729.8	729.1	728.5	727.8	727.5	727.6	727.7	727.8	727.9	728.6
180°	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3



TEST NUMBER: P331390-840

CATALOG NUMBER: SA2XXDIP-C865D530U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1393.6	1393.6	1393.6	1393.6	1393.6	1393.6	1393.6	1393.6
2.5°	1387.7	1390.1	1392.4	1393.4	1392.9	1392.4	1392.0	1391.5
5°	1378.3	1380.7	1383.1	1383.9	1383.4	1382.8	1382.2	1381.6
7.5°	1362.7	1365.1	1367.6	1368.4	1367.8	1367.1	1366.4	1365.7
10°	1348.8	1351.2	1353.6	1354.3	1353.4	1352.5	1351.6	1350.8
12.5°	1332.4	1334.0	1335.7	1336.3	1335.5	1334.9	1334.2	1333.6
15°	1303.5	1304.7	1306.0	1305.8	1304.3	1302.8	1301.3	1299.8
17.5°	1269.3	1270.7	1272.1	1272.0	1270.6	1269.2	1267.8	1266.4
20°	1242.6	1243.5	1244.5	1244.3	1243.1	1241.9	1240.7	1239.5
22.5°	1214.5	1214.6	1214.8	1214.6	1213.8	1213.0	1212.3	1211.6
25°	1168.4	1168.9	1169.5	1169.5	1168.9	1168.4	1167.8	1167.2
27.5°	1123.1	1122.2	1121.3	1120.1	1118.6	1117.2	1115.8	1114.4
30°	1087.6	1086.8	1085.9	1084.8	1083.7	1082.5	1081.3	1080.1
32.5°	1053.0	1051.4	1049.8	1048.3	1047.2	1046.0	1044.8	1043.6
35°	997.4	995.6	993.9	992.2	990.8	989.3	987.7	986.2
37.5°	941.7	939.5	937.3	935.4	934.0	932.6	931.2	929.7
40°	903.2	900.5	897.9	895.9	894.7	893.5	892.3	891.1
42.5°	865.2	862.2	859.4	857.1	855.4	853.7	852.0	850.4
45°	806.9	803.5	800.3	798.1	796.9	795.7	794.5	793.3
47.5°	746.2	742.8	739.3	736.7	735.0	733.3	731.5	729.8
50°	707.2	703.1	698.9	696.1	694.6	693.1	691.7	690.1
52.5°	666.8	663.4	659.9	657.2	655.3	653.3	651.4	649.3
55°	606.6	603.0	599.5	596.9	595.4	593.9	592.5	591.0
57.5°	544.0	540.5	536.9	534.6	533.5	532.4	531.3	530.1
60°	502.7	499.4	496.1	494.0	493.1	492.2	491.3	490.5
62.5°	463.4	460.4	457.4	455.3	454.1	453.0	451.9	450.8
65°	403.3	400.7	398.0	395.9	394.5	392.9	391.4	389.9
67.5°	344.0	341.8	339.8	338.2	337.0	335.8	334.6	333.4
70°	305.4	303.3	301.2	299.5	298.4	297.2	296.0	294.8
72.5°	268.9	266.8	264.8	263.3	262.3	261.4	260.3	259.4
75°	212.2	210.4	208.6	208.0	208.6	209.2	209.7	210.4
77.5°	161.5	160.6	159.7	158.8	157.9	157.1	156.3	155.4
80°	128.2	127.3	126.4	125.6	125.0	124.5	123.9	123.3
82.5°	95.5	94.4	93.3	92.7	92.5	92.4	92.3	92.2
85°	50.5	49.6	48.7	48.1	47.8	47.5	47.2	46.9
87.5°	16.0	15.3	14.7	14.3	14.1	13.9	13.7	13.5
90°	11.7	12.3	12.9	13.3	13.5	13.7	14.0	14.2
92.5°	12.8	13.1	13.4	13.6	13.8	13.9	14.1	14.2
95°	21.7	22.3	22.9	23.1	23.0	22.9	22.8	22.6
97.5°	28.5	28.9	29.4	29.7	29.8	30.0	30.1	30.3
100°	31.9	32.8	33.8	34.3	34.6	34.8	35.0	35.3
102.5°	33.3	34.5	35.7	36.6	36.9	37.2	37.5	37.9
105°	34.7	36.1	37.3	38.2	38.7	39.1	39.6	40.1
107.5°	42.4	41.1	39.8	39.4	39.8	40.3	40.7	41.2
110°	68.8	57.1	45.3	39.8	40.2	40.7	41.2	41.6



TEST NUMBER: P331390-840

CATALOG NUMBER: SA2XXDIP-C865D530U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	147.1	104.4	61.7	40.6	40.9	41.3	41.7	42.0
115°	216.7	162.5	108.3	77.0	68.5	60.1	51.6	43.2
117.5°	334.0	320.8	307.7	287.3	259.5	231.9	204.2	176.4
120°	389.1	390.5	391.9	384.8	368.9	353.1	337.3	321.4
122.5°	412.8	413.7	414.5	413.4	410.4	407.3	404.2	401.1
125°	447.0	447.8	448.6	449.2	449.6	449.9	450.3	450.6
127.5°	478.5	479.7	480.9	481.5	481.6	481.7	481.7	481.8
130°	498.5	499.8	501.1	501.7	501.5	501.4	501.3	501.2
132.5°	518.0	519.1	520.2	520.6	520.5	520.4	520.3	520.2
135°	545.7	546.8	548.1	548.6	548.3	548.1	547.9	547.5
137.5°	571.5	572.6	573.8	574.1	573.7	573.3	573.0	572.6
140°	588.1	589.2	590.3	590.5	589.9	589.4	588.8	588.1
142.5°	603.6	604.5	605.5	605.7	605.1	604.5	603.9	603.3
145°	625.1	625.9	626.7	626.8	626.3	625.7	625.1	624.5
147.5°	643.9	644.5	645.1	645.1	644.7	644.2	643.7	643.2
150°	655.4	656.1	656.8	656.9	656.3	655.7	655.1	654.6
152.5°	666.0	666.7	667.4	667.3	666.6	665.8	665.0	664.3
155°	680.2	681.0	681.7	681.5	680.5	679.6	678.7	677.7
157.5°	692.2	693.0	693.8	693.8	692.8	691.9	690.9	690.0
160°	699.1	699.8	700.5	700.5	699.7	698.9	698.0	697.2
162.5°	705.7	706.5	707.3	707.2	706.2	705.2	704.2	703.2
165°	713.7	714.5	715.3	715.3	714.5	713.7	712.9	712.0
167.5°	720.2	721.1	722.0	721.9	720.7	719.7	718.6	717.6
170°	723.7	724.5	725.3	725.2	724.1	723.1	722.1	720.9
172.5°	726.2	727.0	727.8	727.7	726.7	725.6	724.6	723.5
175°	728.9	729.7	730.5	730.4	729.2	728.0	726.9	725.7
177.5°	729.2	729.9	730.5	730.4	729.6	728.7	727.9	727.1
180°	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3

(END OF REPORT)