

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331391-840

Luminaire Tested: **SA2XXDIP-C865D530U840-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331391-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C865D530U840-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 530 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5456.5 lumens
Efficiency: N/A
Efficacy: 111.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 48.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331391-840
CATALOG NUMBER: SA2XXDIP-C865D530U840-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331391-840

CATALOG NUMBER: SA2XXDIP-C865D530U840-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	92	92	92	80	80	80	70	70	70	65
1	101	97	93	89	95	91	88	84	80	78	75	71	69	67	62	60	59	55
2	92	84	78	73	86	80	74	69	71	66	62	62	59	56	54	52	50	46
3	84	74	67	61	79	70	63	58	62	57	53	55	51	47	48	45	42	39
4	77	66	58	51	72	62	55	49	55	50	45	49	44	41	43	40	37	33
5	71	59	50	44	66	56	48	42	50	44	39	44	39	35	39	35	32	29
6	65	53	44	39	61	50	42	37	45	39	34	40	35	31	35	31	28	25
7	60	48	40	34	57	45	38	33	41	35	30	36	31	27	32	28	25	23
8	56	43	36	30	53	41	34	29	37	31	27	33	28	25	30	26	22	20
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	27	23	20	18
10	49	37	29	24	46	35	28	23	32	26	22	28	24	20	25	21	18	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	22501	22501	22501
5°	22587	22261	22392
10°	22453	22035	22146
15°	22176	21750	21727
20°	21782	21321	21297
25°	21389	20794	20794
30°	20885	20310	20137
35°	20416	19730	19438
40°	19827	19150	18782
45°	19244	18573	18114
50°	18613	17975	17334
55°	17954	17275	16636
60°	17221	16443	15839
65°	16435	15614	14896
70°	15437	14611	13917
75°	14042	13456	13125
80°	12459	12087	11464
85°	10170	9689	8688



TEST NUMBER: P331391-840

CATALOG NUMBER: SA2XXDIP-C865D530U840-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	131.0	2.4
10°-20°	368.7	6.8
20°-30°	542.0	9.9
30°-40°	629.6	11.5
40°-50°	628.9	11.5
50°-60°	548.4	10.1
60°-70°	405.5	7.4
70°-80°	229.7	4.2
80°-90°	64.5	1.2
90°-100°	43.3	0.8
100°-110°	134.3	2.5
110°-120°	229.6	4.2
120°-130°	301.9	5.5
130°-140°	338.8	6.2
140°-150°	332.2	6.1
150°-160°	278.7	5.1
160°-170°	184.8	3.4
170°-180°	64.6	1.2
0°-30°	1041.8	19.1
0°-40°	1671.3	30.6
0°-60°	2848.6	52.2
0°-90°	3548.3	65.0
90°-120°	407.1	7.5
90°-150°	1380.1	25.3
90°-180°	1908.0	35.0
0°-180°	5456.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1394	1394	1394	1394	1394	
5°	1394	1388	1374	1384	1382	132
15°	1327	1318	1301	1306	1300	373
25°	1201	1189	1167	1170	1167	552
35°	1036	1022	1001	993	986	646
45°	843	833	813	799	793	650
55°	638	629	614	598	591	570
65°	430	422	409	397	390	425
75°	225	222	216	208	210	240
85°	55	54	52	48	47	63
90°	1	8	20	19	20	4
95°	30	35	37	37	36	34
105°	124	125	127	128	128	131
115°	230	234	233	232	230	228
125°	335	340	339	337	336	299
135°	434	440	441	440	439	335
145°	526	530	534	534	532	329
155°	602	604	605	608	606	277
165°	655	654	654	658	655	185
175°	681	680	678	682	679	65
180°	682	682	682	682	682	



TEST NUMBER: P331391-840

CATALOG NUMBER: SA2XXDIP-C865D530U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1393.6	1393.6	1393.6	1393.6	1393.6	1393.6	1393.6	1393.6	1393.6	1393.6	1393.6
2.5°	1400.1	1398.9	1397.7	1396.5	1395.3	1393.4	1390.8	1388.2	1385.5	1382.9	1385.3
5°	1393.6	1392.4	1391.3	1390.1	1388.9	1386.6	1383.4	1380.1	1376.8	1373.5	1375.9
7.5°	1381.3	1379.5	1377.7	1375.7	1373.9	1371.3	1368.0	1364.6	1361.3	1358.0	1360.4
10°	1369.5	1367.5	1365.3	1363.2	1361.2	1358.4	1354.7	1351.2	1347.7	1344.0	1346.5
12.5°	1353.4	1351.6	1349.8	1347.9	1346.0	1343.3	1339.8	1336.2	1332.6	1329.1	1330.7
15°	1326.7	1324.8	1323.0	1321.3	1319.5	1316.7	1312.8	1308.9	1305.0	1301.2	1302.3
17.5°	1292.3	1290.5	1288.8	1287.0	1285.2	1282.3	1278.4	1274.4	1270.5	1266.6	1268.0
20°	1267.7	1265.9	1264.1	1262.3	1260.5	1257.6	1253.3	1249.2	1245.1	1240.9	1241.7
22.5°	1243.0	1240.5	1238.0	1235.5	1233.0	1229.8	1225.9	1221.9	1218.0	1214.1	1214.3
25°	1200.6	1198.3	1195.9	1193.6	1191.1	1187.4	1182.3	1177.3	1172.3	1167.2	1167.8
27.5°	1152.5	1150.3	1148.1	1146.0	1143.9	1140.7	1136.8	1132.8	1128.8	1124.8	1124.0
30°	1120.2	1117.9	1115.5	1113.2	1110.8	1107.3	1102.9	1098.4	1093.9	1089.4	1088.5
32.5°	1086.0	1084.1	1082.2	1080.3	1078.3	1075.0	1070.4	1065.6	1061.0	1056.2	1054.6
35°	1035.8	1032.9	1029.9	1026.9	1023.9	1020.1	1015.3	1010.6	1005.7	1001.0	999.3
37.5°	979.3	976.6	974.0	971.4	968.9	965.1	960.4	955.6	950.8	946.0	943.8
40°	940.7	938.4	935.9	933.5	931.2	927.6	922.8	918.1	913.3	908.6	905.8
42.5°	903.2	900.8	898.4	896.1	893.6	890.1	885.3	880.6	875.8	871.0	868.1
45°	842.8	840.8	838.7	836.7	834.6	831.2	826.8	822.3	817.9	813.4	810.1
47.5°	782.8	780.9	778.9	777.0	775.0	771.6	767.0	762.3	757.7	753.1	749.6
50°	741.0	739.5	738.1	736.6	735.1	732.3	728.1	723.9	719.7	715.6	711.4
52.5°	700.3	698.3	696.4	694.4	692.5	689.5	685.6	681.7	677.7	673.8	670.3
55°	637.8	636.1	634.3	632.5	630.7	628.0	624.5	620.9	617.3	613.7	610.2
57.5°	575.1	573.7	572.3	570.9	569.5	566.7	562.8	558.9	554.9	551.0	547.5
60°	533.3	532.1	531.0	529.8	528.6	525.9	521.7	517.6	513.4	509.2	505.9
62.5°	492.6	490.7	488.8	486.9	484.9	482.4	479.2	475.9	472.7	469.6	466.6
65°	430.2	428.4	426.6	424.7	423.0	420.6	417.7	414.7	411.7	408.7	406.1
67.5°	366.7	365.2	363.8	362.3	360.9	358.9	356.2	353.5	350.8	348.1	346.1
70°	327.0	325.8	324.6	323.4	322.2	320.2	317.6	314.9	312.3	309.5	307.5
72.5°	286.2	285.1	283.9	282.7	281.4	280.0	278.3	276.6	274.8	273.1	271.0
75°	225.1	224.5	223.9	223.4	222.8	221.7	220.3	218.7	217.2	215.7	214.0
77.5°	170.5	169.5	168.4	167.4	166.4	165.6	165.0	164.4	163.8	163.2	162.3
80°	134.0	133.7	133.4	133.1	132.8	132.4	131.8	131.2	130.6	130.0	129.1
82.5°	99.7	99.7	99.6	99.5	99.5	99.3	98.9	98.6	98.2	97.9	96.6
85°	54.9	54.6	54.3	54.0	53.7	53.4	53.1	52.8	52.5	52.3	51.4
87.5°	19.4	19.3	19.1	18.9	18.8	18.7	18.8	18.9	19.0	19.1	18.3
90°	0.6	2.1	3.6	5.2	6.8	8.9	11.7	14.5	17.4	20.2	19.9
92.5°	10.3	11.4	12.5	13.6	14.7	15.7	16.4	17.0	17.7	18.3	18.4
95°	30.0	31.2	32.5	33.8	35.0	35.9	36.1	36.4	36.6	36.9	36.9
97.5°	54.7	55.8	57.0	58.1	59.2	60.0	60.5	61.0	61.5	62.0	62.0
100°	73.1	74.1	75.1	76.2	77.3	78.0	78.4	78.7	79.1	79.5	79.5
102.5°	92.5	93.3	94.1	94.9	95.7	96.4	96.9	97.4	97.9	98.4	98.5
105°	123.8	124.2	124.6	124.9	125.3	125.6	125.9	126.1	126.4	126.7	126.9
107.5°	155.4	155.9	156.5	157.0	157.6	157.9	157.9	157.9	157.9	157.9	158.0
110°	175.6	176.4	177.1	177.9	178.7	179.0	179.0	179.0	179.0	179.0	179.0



TEST NUMBER: P331391-840

CATALOG NUMBER: SA2XXDIP-C865D530U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	197.7	198.5	199.2	200.1	200.9	201.2	201.1	201.0	200.9	200.8	200.5
115°	230.4	231.2	231.9	232.7	233.4	233.7	233.4	233.2	232.9	232.7	232.6
117.5°	262.9	263.9	264.9	265.9	266.9	267.1	266.4	265.6	264.9	264.2	263.9
120°	284.5	285.5	286.5	287.5	288.6	288.6	287.5	286.5	285.5	284.5	284.5
122.5°	304.3	305.5	306.8	308.0	309.2	309.4	308.7	308.0	307.3	306.6	306.3
125°	335.2	336.3	337.5	338.6	339.7	340.1	339.7	339.4	339.0	338.6	338.2
127.5°	365.2	366.7	368.1	369.6	371.0	371.5	371.1	370.6	370.2	369.7	369.2
130°	384.2	385.8	387.4	389.1	390.7	391.4	391.2	390.9	390.7	390.4	390.2
132.5°	405.3	406.7	408.0	409.4	410.7	411.4	411.5	411.5	411.6	411.6	411.1
135°	433.6	435.0	436.5	437.9	439.3	440.1	440.3	440.6	440.9	441.1	441.0
137.5°	463.4	464.6	465.7	467.0	468.1	468.8	469.2	469.5	469.8	470.1	470.0
140°	481.4	482.6	483.7	484.8	486.0	487.0	487.6	488.2	488.9	489.5	489.5
142.5°	499.9	501.0	502.2	503.3	504.4	505.2	505.7	506.1	506.5	507.0	507.1
145°	526.3	527.3	528.2	529.1	530.0	530.8	531.5	532.3	533.1	533.8	533.9
147.5°	550.0	551.0	552.1	553.2	554.2	555.0	555.5	556.0	556.5	557.1	557.3
150°	566.1	566.8	567.6	568.4	569.2	569.8	570.3	570.8	571.3	571.9	572.2
152.5°	580.4	581.2	581.9	582.7	583.4	584.1	584.7	585.3	585.9	586.6	587.0
155°	601.8	602.2	602.6	602.9	603.3	603.7	604.1	604.5	604.8	605.2	605.9
157.5°	620.1	620.4	620.6	620.9	621.2	621.4	621.6	621.9	622.1	622.3	623.2
160°	631.2	631.4	631.7	631.9	632.2	632.4	632.5	632.6	632.8	632.9	633.7
162.5°	641.3	641.4	641.4	641.5	641.5	641.6	641.7	641.9	642.0	642.1	643.0
165°	654.8	654.6	654.5	654.4	654.3	654.2	654.2	654.2	654.2	654.2	655.1
167.5°	666.0	665.7	665.3	664.9	664.5	664.3	664.3	664.3	664.2	664.2	665.1
170°	672.1	671.7	671.3	670.9	670.6	670.2	670.1	669.9	669.8	669.7	670.7
172.5°	676.2	675.8	675.4	675.0	674.7	674.4	674.3	674.2	674.0	673.9	674.8
175°	681.3	680.9	680.4	680.1	679.7	679.4	679.1	678.9	678.6	678.3	679.2
177.5°	683.4	683.0	682.7	682.4	682.1	681.9	681.7	681.5	681.3	681.1	681.7
180°	682.4	682.4	682.4	682.4	682.4	682.4	682.4	682.4	682.4	682.4	682.4



TEST NUMBER: P331391-840

CATALOG NUMBER: SA2XXDIP-C865D530U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1393.6	1393.6	1393.6	1393.6	1393.6	1393.6	1393.6	1393.6
2.5°	1387.7	1390.1	1392.4	1393.4	1392.9	1392.4	1392.0	1391.5
5°	1378.3	1380.7	1383.1	1383.9	1383.4	1382.8	1382.2	1381.6
7.5°	1362.7	1365.1	1367.6	1368.4	1367.8	1367.1	1366.4	1365.7
10°	1348.8	1351.2	1353.6	1354.3	1353.4	1352.5	1351.6	1350.8
12.5°	1332.4	1334.0	1335.7	1336.3	1335.5	1334.9	1334.2	1333.6
15°	1303.5	1304.7	1306.0	1305.8	1304.3	1302.8	1301.3	1299.8
17.5°	1269.3	1270.7	1272.1	1272.0	1270.6	1269.2	1267.8	1266.4
20°	1242.6	1243.5	1244.5	1244.3	1243.1	1241.9	1240.7	1239.5
22.5°	1214.5	1214.6	1214.8	1214.6	1213.8	1213.0	1212.3	1211.6
25°	1168.4	1168.9	1169.5	1169.5	1168.9	1168.4	1167.8	1167.2
27.5°	1123.1	1122.2	1121.3	1120.1	1118.6	1117.2	1115.8	1114.4
30°	1087.6	1086.8	1085.9	1084.8	1083.7	1082.5	1081.3	1080.1
32.5°	1053.0	1051.4	1049.8	1048.3	1047.2	1046.0	1044.8	1043.6
35°	997.4	995.6	993.9	992.2	990.8	989.3	987.7	986.2
37.5°	941.7	939.5	937.3	935.4	934.0	932.6	931.2	929.7
40°	903.2	900.5	897.9	895.9	894.7	893.5	892.3	891.1
42.5°	865.2	862.2	859.4	857.1	855.4	853.7	852.0	850.4
45°	806.9	803.5	800.3	798.1	796.9	795.7	794.5	793.3
47.5°	746.2	742.8	739.3	736.7	735.0	733.3	731.5	729.8
50°	707.2	703.1	698.9	696.1	694.6	693.1	691.7	690.1
52.5°	666.8	663.4	659.9	657.2	655.3	653.3	651.4	649.3
55°	606.6	603.0	599.5	596.9	595.4	593.9	592.5	591.0
57.5°	544.0	540.5	536.9	534.6	533.5	532.4	531.3	530.1
60°	502.7	499.4	496.1	494.0	493.1	492.2	491.3	490.5
62.5°	463.4	460.4	457.4	455.3	454.1	453.0	451.9	450.8
65°	403.3	400.7	398.0	395.9	394.5	392.9	391.4	389.9
67.5°	344.0	341.8	339.8	338.2	337.0	335.8	334.6	333.4
70°	305.4	303.3	301.2	299.5	298.4	297.2	296.0	294.8
72.5°	268.9	266.8	264.8	263.3	262.3	261.4	260.3	259.4
75°	212.2	210.4	208.6	208.0	208.6	209.2	209.7	210.4
77.5°	161.5	160.6	159.7	158.8	157.9	157.1	156.3	155.4
80°	128.2	127.3	126.4	125.6	125.0	124.5	123.9	123.3
82.5°	95.5	94.4	93.3	92.7	92.5	92.4	92.3	92.2
85°	50.5	49.6	48.7	48.1	47.8	47.5	47.2	46.9
87.5°	17.5	16.8	16.0	15.5	15.2	15.0	14.8	14.6
90°	19.7	19.4	19.1	19.1	19.2	19.3	19.5	19.6
92.5°	18.4	18.5	18.5	18.6	18.6	18.6	18.7	18.7
95°	36.9	36.9	36.9	36.8	36.5	36.3	36.0	35.7
97.5°	62.0	62.0	62.0	61.9	61.9	61.9	61.9	61.8
100°	79.5	79.5	79.5	79.4	79.3	79.2	79.1	78.9
102.5°	98.6	98.7	98.8	98.8	98.7	98.5	98.4	98.3
105°	127.2	127.4	127.7	127.8	127.8	127.8	127.8	127.8
107.5°	158.1	158.2	158.3	158.0	157.4	156.9	156.3	155.7
110°	179.0	179.0	179.0	178.9	178.5	178.1	177.7	177.3



TEST NUMBER: P331391-840

CATALOG NUMBER: SA2XXDIP-C865D530U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	200.2	199.9	199.5	199.2	198.9	198.6	198.3	198.1
115°	232.4	232.3	232.2	231.9	231.5	231.2	230.8	230.4
117.5°	263.6	263.3	263.0	262.7	262.3	261.9	261.5	261.1
120°	284.5	284.5	284.5	284.3	283.9	283.6	283.2	282.8
122.5°	306.0	305.7	305.4	305.1	304.8	304.5	304.3	304.0
125°	337.8	337.5	337.1	336.8	336.7	336.6	336.4	336.3
127.5°	368.8	368.3	367.9	367.4	367.0	366.6	366.2	365.8
130°	389.9	389.7	389.4	389.0	388.5	388.0	387.5	387.0
132.5°	410.5	409.9	409.4	408.9	408.5	408.1	407.7	407.3
135°	440.9	440.7	440.6	440.3	440.0	439.6	439.2	438.8
137.5°	469.9	469.8	469.7	469.4	468.9	468.4	467.9	467.4
140°	489.5	489.5	489.5	489.3	488.7	488.2	487.7	487.2
142.5°	507.2	507.3	507.4	507.2	506.6	506.1	505.6	505.1
145°	534.1	534.2	534.3	534.1	533.6	533.1	532.6	532.1
147.5°	557.6	558.0	558.3	558.2	557.6	557.1	556.6	556.1
150°	572.6	573.0	573.4	573.4	573.0	572.6	572.2	571.9
152.5°	587.5	588.0	588.5	588.5	588.0	587.5	587.0	586.6
155°	606.5	607.1	607.8	607.9	607.5	607.1	606.7	606.4
157.5°	624.0	624.9	625.8	625.9	625.3	624.7	624.1	623.4
160°	634.4	635.2	635.9	636.1	635.6	635.1	634.5	634.0
162.5°	643.8	644.7	645.6	645.7	645.1	644.5	643.9	643.3
165°	656.0	656.9	657.7	657.9	657.2	656.6	656.0	655.3
167.5°	666.0	666.9	667.8	667.9	667.2	666.6	665.9	665.2
170°	671.6	672.5	673.3	673.4	672.6	671.9	671.1	670.3
172.5°	675.7	676.6	677.4	677.5	676.8	676.0	675.2	674.5
175°	680.1	681.1	682.0	682.1	681.3	680.4	679.7	678.9
177.5°	682.3	682.9	683.5	683.5	682.9	682.3	681.7	681.1
180°	682.4	682.4	682.4	682.4	682.4	682.4	682.4	682.4

(END OF REPORT)