

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331402-840

Luminaire Tested: **SA2XXDIP-C865D925U840-4F0-1E-UDD-A**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331402-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C865D925U840-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 925 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7585.1 lumens
Efficiency: N/A
Efficacy: 125.4 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 60.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331402-840
CATALOG NUMBER: SA2XXDIP-C865D925U840-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331402-840

CATALOG NUMBER: SA2XXDIP-C865D925U840-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51
1	98	94	91	87	91	87	84	81	74	72	70	62	60	59	51	50	49	44
2	90	83	77	72	83	77	72	67	66	62	59	55	52	50	45	44	42	37
3	82	73	66	61	76	68	62	57	58	54	50	49	46	43	41	38	36	32
4	76	65	58	52	70	61	54	49	52	47	43	44	40	37	37	34	32	28
5	70	58	50	45	64	54	47	42	47	41	37	40	36	33	33	30	28	25
6	64	53	45	39	59	49	42	37	42	37	33	36	32	29	30	27	25	22
7	60	48	40	34	55	45	38	33	39	33	29	33	29	26	28	25	22	20
8	55	43	36	31	51	41	34	29	35	30	26	30	26	23	26	23	20	18
9	52	40	32	27	48	37	31	26	32	27	23	28	24	21	24	21	18	16
10	48	36	29	25	45	34	28	24	30	25	21	26	22	19	22	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	28150	28150	28150	28150
5°	31561	28336	25109	28336
10°	36166	28103	21730	28103
15°	40010	27587	19198	27587
20°	39400	27034	17500	27034
25°	35527	26298	16425	26298
30°	29358	25124	15642	25124
35°	21396	23893	15084	23893
40°	17089	22443	14773	22443
45°	14933	20763	14351	20763
50°	14039	19138	14071	19138
55°	12940	17486	13695	17486
60°	11858	15733	13114	15733
65°	10804	14155	12542	14155
70°	9805	12623	11703	12623
75°	8696	10911	10368	10911
80°	7476	9028	8350	9028
85°	6706	6706	4965	6706



TEST NUMBER: P331402-840

CATALOG NUMBER: SA2XXDIP-C865D925U840-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	166.1	2.2
10°-20°	482.7	6.4
20°-30°	700.6	9.2
30°-40°	739.3	9.7
40°-50°	654.6	8.6
50°-60°	522.4	6.9
60°-70°	355.1	4.7
70°-80°	182.0	2.4
80°-90°	47.0	0.6
90°-100°	42.5	0.6
100°-110°	155.9	2.1
110°-120°	416.8	5.5
120°-130°	688.0	9.1
130°-140°	731.7	9.6
140°-150°	680.1	9.0
150°-160°	546.8	7.2
160°-170°	352.3	4.6
170°-180°	121.3	1.6
0°-30°	1349.4	17.8
0°-40°	2088.7	27.5
0°-60°	3265.7	43.1
0°-90°	3849.8	50.8
90°-120°	615.2	8.1
90°-150°	2714.9	35.8
90°-180°	3735.0	49.2
0°-180°	7585.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1744	1744	1744	1744	1744	
5°	1947	1748	1549	1748	1947	194
15°	2394	1650	1148	1650	2394	660
25°	1994	1476	922	1476	1994	901
35°	1086	1212	765	1212	1086	706
45°	654	909	628	909	654	514
55°	460	621	486	621	460	412
65°	283	370	328	370	283	281
75°	139	175	166	175	139	149
85°	36	36	27	36	36	40
90°	25	1	25	1	25	13
95°	40	60	40	60	40	37
105°	70	280	70	280	70	73
115°	76	530	76	530	76	189
125°	789	750	789	750	789	682
135°	958	928	958	928	958	739
145°	1093	1076	1093	1076	1093	683
155°	1186	1185	1186	1185	1186	547
165°	1246	1249	1246	1249	1246	352
175°	1270	1277	1270	1277	1270	121
180°	1275	1275	1275	1275	1275	



TEST NUMBER: P331402-840

CATALOG NUMBER: SA2XXDIP-C865D925U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5
2.5°	1824.0	1824.5	1825.6	1817.1	1815.9	1815.9	1808.5	1802.0	1794.5	1784.3	1785.4
5°	1947.3	1954.7	1957.3	1949.3	1937.2	1935.9	1924.5	1905.7	1888.3	1874.2	1864.2
7.5°	2094.5	2097.4	2090.8	2080.2	2071.2	2055.2	2034.0	2013.3	1984.2	1957.5	1937.6
10°	2205.9	2210.0	2198.6	2183.1	2170.4	2151.6	2120.8	2089.3	2051.1	2014.3	1984.8
12.5°	2290.7	2300.6	2285.9	2283.9	2262.1	2236.3	2199.7	2183.7	2130.0	2078.6	2047.0
15°	2393.6	2392.9	2394.3	2381.5	2365.4	2361.4	2322.6	2280.4	2204.6	2174.4	2122.2
17.5°	2363.8	2374.0	2378.7	2378.5	2378.1	2375.6	2363.2	2336.5	2298.6	2249.7	2189.3
20°	2293.1	2306.4	2308.5	2323.9	2332.6	2344.0	2348.6	2341.3	2317.8	2276.9	2224.7
22.5°	2183.7	2187.5	2193.7	2217.8	2236.6	2265.2	2280.1	2304.8	2295.8	2275.9	2232.2
25°	1994.2	1987.5	2010.9	2023.0	2066.6	2112.1	2145.0	2181.1	2213.3	2232.7	2220.0
27.5°	1766.7	1756.6	1791.7	1823.7	1859.1	1908.4	1959.6	2020.0	2070.3	2133.1	2154.7
30°	1574.7	1580.7	1614.3	1648.4	1702.0	1771.7	1829.4	1895.7	1967.4	2037.7	2086.7
32.5°	1367.8	1391.0	1412.2	1464.5	1511.8	1589.4	1673.9	1756.9	1846.2	1926.2	2002.0
35°	1085.5	1112.4	1141.9	1180.0	1246.4	1323.4	1405.8	1517.7	1639.7	1749.0	1838.8
37.5°	913.7	909.5	926.3	953.9	1007.6	1069.9	1164.8	1275.4	1418.9	1547.2	1673.9
40°	810.8	808.1	820.2	845.7	886.6	932.1	1015.2	1112.4	1245.7	1402.5	1553.3
42.5°	740.0	741.6	748.3	766.3	794.4	831.8	894.0	976.7	1098.8	1246.5	1408.6
45°	654.0	658.7	666.1	674.8	690.8	721.6	756.5	815.5	912.0	1035.3	1194.8
47.5°	592.1	592.2	599.8	607.3	616.9	634.3	662.7	699.7	767.8	868.2	1005.3
50°	558.9	554.2	559.6	565.5	575.6	587.6	606.4	641.3	686.8	767.9	882.5
52.5°	518.2	518.3	523.1	525.3	534.3	546.4	563.5	587.6	628.9	692.4	786.6
55°	459.7	463.0	465.7	469.7	477.8	486.5	499.9	515.9	548.2	595.7	665.4
57.5°	404.8	405.8	408.5	416.2	421.2	429.3	442.0	456.6	477.5	512.7	565.1
60°	367.2	367.2	372.5	375.9	382.6	390.6	400.7	414.8	433.5	462.3	504.6
62.5°	333.0	332.3	334.5	340.0	345.1	352.6	362.6	374.6	392.2	417.9	452.6
65°	282.8	281.4	285.5	286.8	292.2	299.5	307.6	320.3	334.4	353.1	384.0
67.5°	234.5	236.1	238.3	240.9	243.8	251.6	256.9	265.9	277.8	293.4	314.3
70°	207.7	207.7	207.7	209.7	213.8	217.8	223.2	230.6	241.9	255.3	274.1
72.5°	177.7	179.9	182.0	180.8	185.9	188.3	194.7	198.8	209.7	218.3	234.9
75°	139.4	139.4	139.4	142.7	144.7	146.7	150.8	154.8	160.2	170.9	179.6
77.5°	104.0	103.7	104.4	105.2	107.3	109.8	111.0	114.6	119.6	124.5	131.9
80°	80.4	81.8	82.4	83.7	83.7	85.1	85.7	90.5	93.8	97.1	101.9
82.5°	62.2	62.4	62.6	62.8	63.4	64.2	65.9	67.5	68.6	71.4	75.0
85°	36.2	35.5	35.5	36.9	36.2	36.2	37.6	38.9	38.9	39.5	41.5
87.5°	18.9	18.9	19.3	18.7	18.6	19.0	18.8	18.1	18.4	18.7	18.9
90°	24.9	24.5	24.0	23.6	23.2	22.5	21.5	20.5	19.5	18.5	16.8
92.5°	24.9	24.6	24.4	24.1	23.9	23.5	23.0	22.4	21.9	21.4	20.6
95°	39.7	39.9	40.1	40.3	40.5	40.1	39.1	38.0	37.0	36.0	34.5
97.5°	52.9	52.7	52.4	52.2	51.9	51.4	50.6	49.8	49.0	48.2	44.8
100°	61.8	61.4	61.0	60.6	60.2	59.2	57.5	55.8	54.2	52.6	49.1
102.5°	66.2	65.6	65.0	64.5	63.9	62.6	60.5	58.3	56.1	54.0	83.2
105°	70.1	69.3	68.5	67.7	66.9	65.2	63.0	60.8	58.5	56.2	112.2
107.5°	72.1	71.3	70.5	69.7	68.9	69.6	71.9	74.1	76.4	78.8	145.8
110°	72.9	72.0	71.2	70.4	69.6	79.4	99.9	120.4	140.9	161.4	220.7



TEST NUMBER: P331402-840

CATALOG NUMBER: SA2XXDIP-C865D925U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	73.6	72.9	72.3	71.6	71.0	108.1	182.8	257.6	332.3	407.1	421.7
115°	75.6	90.4	105.1	119.9	134.6	189.5	284.4	379.3	474.1	569.1	563.9
117.5°	308.8	357.3	405.8	454.2	502.7	538.5	561.5	584.4	607.3	630.3	626.8
120°	562.6	590.3	617.9	645.6	673.3	685.9	683.5	681.0	678.5	676.0	672.4
122.5°	702.1	707.4	712.8	718.2	723.6	725.5	724.0	722.6	721.0	719.6	715.6
125°	788.6	788.0	787.3	786.7	786.1	785.1	783.7	782.2	780.8	779.3	775.5
127.5°	843.1	843.0	842.9	842.8	842.6	841.6	839.5	837.4	835.3	833.2	830.3
130°	877.1	877.3	877.5	877.8	878.0	876.9	874.6	872.4	870.1	867.9	865.7
132.5°	910.3	910.5	910.7	910.9	911.1	910.3	908.4	906.5	904.5	902.5	900.3
135°	958.3	958.7	959.1	959.5	959.9	959.1	957.0	955.0	952.9	950.9	949.1
137.5°	1002.0	1002.7	1003.4	1004.1	1004.8	1004.1	1002.1	1000.1	998.0	996.1	994.0
140°	1029.3	1030.4	1031.4	1032.4	1033.4	1033.0	1031.2	1029.3	1027.4	1025.6	1023.4
142.5°	1055.8	1056.9	1057.9	1058.9	1060.0	1059.7	1057.9	1056.2	1054.6	1052.9	1050.4
145°	1093.0	1094.0	1095.0	1096.0	1097.0	1096.8	1095.4	1094.0	1092.5	1091.1	1087.6
147.5°	1125.6	1126.4	1127.3	1128.1	1129.0	1128.9	1127.8	1126.8	1125.7	1124.7	1121.3
150°	1145.5	1146.5	1147.5	1148.6	1149.6	1149.5	1148.3	1147.0	1145.8	1144.6	1141.3
152.5°	1162.5	1163.9	1165.2	1166.5	1167.9	1167.9	1166.7	1165.5	1164.3	1163.1	1159.9
155°	1186.1	1187.7	1189.3	1191.0	1192.7	1192.9	1191.6	1190.4	1189.1	1187.9	1185.5
157.5°	1207.7	1209.2	1210.8	1212.4	1214.1	1214.2	1212.7	1211.3	1210.0	1208.6	1206.9
160°	1220.2	1221.6	1223.0	1224.5	1226.0	1226.1	1224.9	1223.6	1222.3	1221.1	1219.9
162.5°	1230.5	1232.3	1234.1	1235.9	1237.6	1237.8	1236.4	1235.0	1233.6	1232.2	1231.1
165°	1246.1	1247.5	1248.9	1250.3	1251.7	1251.7	1250.3	1248.9	1247.5	1246.1	1245.5
167.5°	1255.8	1257.7	1259.5	1261.3	1263.1	1263.4	1261.9	1260.5	1259.1	1257.7	1257.1
170°	1261.7	1263.5	1265.4	1267.3	1269.1	1269.3	1267.9	1266.5	1265.0	1263.5	1263.1
172.5°	1266.2	1268.0	1269.8	1271.6	1273.5	1273.7	1272.3	1270.8	1269.4	1268.0	1267.6
175°	1270.0	1272.0	1274.1	1276.2	1278.2	1278.5	1277.1	1275.7	1274.2	1272.7	1272.3
177.5°	1272.4	1273.8	1275.4	1276.9	1278.3	1278.5	1277.4	1276.2	1275.1	1273.8	1273.7
180°	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7



TEST NUMBER: P331402-840

CATALOG NUMBER: SA2XXDIP-C865D925U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5
2.5°	1789.2	1784.8	1782.2	1772.5	1763.9	1755.3	1752.7	1753.7	1742.0	1730.7	1725.9
5°	1858.9	1845.4	1832.7	1814.6	1793.2	1769.7	1757.7	1748.3	1724.8	1699.4	1684.7
7.5°	1921.3	1902.1	1877.6	1843.6	1812.3	1775.4	1752.0	1731.2	1697.0	1661.0	1639.0
10°	1959.3	1933.2	1901.7	1860.2	1822.0	1777.1	1745.6	1714.1	1673.9	1631.0	1604.2
12.5°	1992.1	1956.8	1925.8	1872.5	1827.4	1771.2	1733.8	1689.4	1647.1	1596.2	1569.9
15°	2069.9	2004.9	1945.9	1885.6	1830.0	1751.6	1710.1	1650.4	1594.8	1531.9	1501.7
17.5°	2130.1	2057.1	1964.2	1887.5	1822.6	1735.9	1674.9	1603.4	1537.6	1465.6	1424.6
20°	2164.4	2080.6	1980.7	1889.7	1811.9	1712.7	1646.4	1573.4	1496.3	1415.2	1371.0
22.5°	2184.7	2096.7	1997.9	1881.6	1790.5	1693.9	1610.5	1530.5	1452.4	1364.8	1318.5
25°	2191.2	2110.8	2006.3	1874.9	1763.7	1654.5	1554.0	1476.2	1381.7	1300.0	1232.3
27.5°	2159.3	2101.6	2001.1	1862.3	1732.7	1605.0	1493.0	1404.9	1305.3	1216.5	1148.4
30°	2120.2	2086.7	1988.8	1849.5	1708.1	1570.7	1447.4	1347.6	1248.4	1158.6	1088.9
32.5°	2059.6	2052.3	1966.3	1831.2	1681.8	1527.3	1399.7	1298.8	1188.9	1100.7	1034.2
35°	1940.6	1972.8	1918.4	1790.5	1632.3	1465.5	1327.5	1212.2	1098.3	1013.8	951.5
37.5°	1781.1	1861.0	1846.7	1730.8	1565.6	1398.3	1245.9	1125.4	1016.8	931.6	870.4
40°	1671.2	1773.0	1787.8	1685.3	1518.4	1346.3	1184.8	1064.8	958.9	881.2	819.5
42.5°	1553.3	1672.2	1712.7	1630.6	1466.9	1291.5	1130.0	1005.8	901.0	825.5	770.7
45°	1355.6	1513.1	1586.1	1539.2	1381.1	1201.4	1035.3	909.3	814.2	743.2	700.9
47.5°	1170.7	1342.8	1441.1	1424.5	1285.5	1107.6	943.3	822.4	729.8	673.2	635.4
50°	1040.0	1216.9	1335.4	1340.9	1216.9	1040.7	875.9	761.9	676.8	623.9	593.0
52.5°	926.3	1095.2	1224.6	1252.9	1140.2	971.0	815.3	701.9	626.9	578.2	550.7
55°	778.0	920.7	1064.1	1116.4	1025.9	865.1	721.0	621.2	550.8	517.4	493.2
57.5°	646.8	765.8	898.2	955.9	900.2	762.5	627.4	540.8	483.6	454.3	435.9
60°	577.6	671.5	789.4	858.4	810.1	687.5	569.6	487.2	440.3	414.1	396.7
62.5°	513.3	596.4	696.1	759.2	733.0	617.3	511.7	438.9	398.4	374.0	361.3
65°	423.5	489.2	566.2	624.5	607.1	519.3	432.9	370.5	338.4	318.9	308.9
67.5°	348.7	396.2	449.6	500.7	486.7	424.4	355.0	306.5	282.6	265.8	259.7
70°	301.5	337.7	385.3	426.2	414.8	363.9	308.9	267.4	246.6	232.6	226.5
72.5°	256.5	286.3	322.6	356.0	348.3	306.0	260.1	228.7	212.8	199.9	194.9
75°	193.7	216.4	238.5	260.6	258.6	225.8	199.0	174.9	162.2	152.1	150.1
77.5°	143.0	155.7	170.8	183.9	180.3	161.5	140.5	126.6	117.2	110.6	109.5
80°	109.3	116.6	127.3	136.7	132.0	124.0	107.2	97.1	90.5	83.7	81.1
82.5°	79.2	86.5	93.0	98.1	94.5	86.9	76.6	69.8	65.8	61.2	60.2
85°	41.5	45.5	48.3	49.6	48.3	43.5	38.9	36.2	32.8	30.8	30.2
87.5°	19.1	18.8	18.5	19.2	17.1	16.7	14.0	12.0	11.9	11.8	11.2
90°	15.1	13.5	11.9	9.9	7.7	5.5	3.1	0.9	3.1	5.5	7.7
92.5°	19.8	19.0	18.1	17.8	18.0	18.2	18.4	18.6	18.4	18.2	18.0
95°	33.1	31.7	30.2	32.9	39.7	46.5	53.2	60.0	53.2	46.5	39.7
97.5°	41.5	38.2	34.8	42.7	61.8	80.9	99.9	119.0	99.9	80.9	61.8
100°	45.6	42.1	38.7	50.9	79.0	107.0	135.1	163.3	135.1	107.0	79.0
102.5°	112.3	141.5	170.7	188.1	194.1	200.1	206.0	212.0	206.0	200.1	194.1
105°	168.1	224.1	280.0	305.0	298.8	292.7	286.5	280.3	286.5	292.7	298.8
107.5°	213.0	280.0	347.2	378.3	373.2	368.3	363.3	358.4	363.3	368.3	373.2
110°	279.8	339.1	398.3	425.8	421.5	417.2	412.9	408.6	412.9	417.2	421.5



TEST NUMBER: P331402-840

CATALOG NUMBER: SA2XXDIP-C865D925U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	436.4	451.0	465.6	471.0	467.3	463.4	459.6	455.8	459.6	463.4	467.3
115°	558.9	553.7	548.6	544.2	540.8	537.2	533.8	530.3	533.8	537.2	540.8
117.5°	623.3	619.8	616.2	612.5	608.6	604.7	600.8	596.9	600.8	604.7	608.6
120°	668.6	665.0	661.3	657.9	654.8	651.8	648.6	645.6	648.6	651.8	654.8
122.5°	711.6	707.5	703.5	699.8	696.6	693.4	690.1	686.9	690.1	693.4	696.6
125°	771.5	767.7	763.8	760.5	757.8	755.2	752.5	749.8	752.5	755.2	757.8
127.5°	827.4	824.5	821.5	818.6	815.7	812.7	809.8	806.8	809.8	812.7	815.7
130°	863.3	861.1	858.9	856.1	852.8	849.5	846.3	843.0	846.3	849.5	852.8
132.5°	898.1	895.9	893.5	891.0	888.3	885.4	882.6	879.9	882.6	885.4	888.3
135°	947.3	945.3	943.5	941.0	937.7	934.4	931.1	927.9	931.1	934.4	937.7
137.5°	991.9	989.8	987.7	985.5	983.2	981.0	978.7	976.3	978.7	981.0	983.2
140°	1021.1	1018.9	1016.6	1014.6	1013.0	1011.4	1009.8	1008.0	1009.8	1011.4	1013.0
142.5°	1047.7	1045.1	1042.6	1040.6	1039.1	1037.6	1036.1	1034.6	1036.1	1037.6	1039.1
145°	1084.1	1080.7	1077.1	1075.5	1075.7	1075.9	1076.1	1076.3	1076.1	1075.9	1075.7
147.5°	1117.8	1114.3	1110.9	1109.5	1110.3	1111.2	1111.9	1112.7	1111.9	1111.2	1110.3
150°	1138.0	1134.8	1131.5	1130.5	1132.0	1133.4	1134.9	1136.3	1134.9	1133.4	1132.0
152.5°	1156.8	1153.7	1150.5	1149.8	1151.4	1153.0	1154.6	1156.2	1154.6	1153.0	1151.4
155°	1183.1	1180.5	1178.1	1177.8	1179.6	1181.4	1183.4	1185.2	1183.4	1181.4	1179.6
157.5°	1205.2	1203.5	1201.7	1201.6	1203.2	1204.8	1206.3	1207.8	1206.3	1204.8	1203.2
160°	1218.7	1217.4	1216.2	1216.2	1217.4	1218.7	1219.9	1221.1	1219.9	1218.7	1217.4
162.5°	1230.0	1229.0	1227.9	1228.0	1229.2	1230.5	1231.7	1232.9	1231.7	1230.5	1229.2
165°	1244.8	1244.2	1243.5	1243.9	1245.1	1246.4	1247.6	1248.8	1247.6	1246.4	1245.1
167.5°	1256.5	1256.0	1255.4	1255.7	1256.9	1258.2	1259.4	1260.6	1259.4	1258.2	1256.9
170°	1262.7	1262.3	1261.9	1262.3	1263.5	1264.8	1266.0	1267.3	1266.0	1264.8	1263.5
172.5°	1267.2	1266.8	1266.4	1266.8	1268.0	1269.2	1270.4	1271.6	1270.4	1269.2	1268.0
175°	1271.9	1271.5	1271.1	1271.6	1273.0	1274.6	1276.0	1277.4	1276.0	1274.6	1273.0
177.5°	1273.5	1273.4	1273.2	1273.7	1274.9	1276.1	1277.2	1278.3	1277.2	1276.1	1274.9
180°	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7



TEST NUMBER: P331402-840

CATALOG NUMBER: SA2XXDIP-C865D925U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5
2.5°	1720.5	1717.3	1706.1	1700.2	1690.5	1681.4	1675.5	1678.2	1680.3	1679.2	1677.7
5°	1671.2	1658.5	1639.0	1622.2	1610.2	1588.1	1578.7	1574.1	1570.0	1565.3	1560.6
7.5°	1612.6	1592.5	1564.5	1540.7	1518.1	1490.7	1475.0	1465.6	1456.0	1445.4	1436.0
10°	1570.7	1542.6	1513.1	1479.6	1452.8	1427.9	1405.8	1391.1	1377.8	1364.9	1355.6
12.5°	1526.7	1494.3	1457.8	1412.0	1382.5	1347.1	1343.6	1317.7	1296.8	1288.9	1277.9
15°	1456.8	1411.2	1364.9	1310.7	1287.3	1255.1	1235.0	1214.9	1196.8	1184.1	1180.7
17.5°	1377.4	1318.4	1272.3	1233.3	1194.9	1162.0	1143.5	1127.4	1112.5	1095.5	1093.2
20°	1316.8	1265.8	1215.6	1181.3	1141.9	1108.3	1085.5	1069.4	1056.7	1046.7	1037.9
22.5°	1259.4	1203.7	1157.6	1120.2	1081.3	1054.2	1036.2	1020.7	1010.1	999.0	990.8
25°	1167.3	1123.8	1073.5	1031.3	999.1	981.7	966.9	953.5	946.8	939.5	930.1
27.5°	1086.7	1038.3	991.4	958.7	930.4	914.9	904.5	895.3	889.1	884.7	879.4
30°	1030.0	981.0	944.1	912.0	888.6	873.1	866.5	861.1	853.7	851.0	848.4
32.5°	975.2	931.2	899.7	871.8	849.4	839.4	833.2	828.4	822.6	819.9	814.6
35°	898.0	861.1	830.2	814.9	796.8	788.0	783.4	776.7	771.2	768.6	767.9
37.5°	825.2	793.1	772.8	753.1	745.4	740.0	733.7	729.0	727.4	727.0	726.4
40°	778.0	751.8	733.8	717.7	714.3	706.3	700.9	696.9	696.9	697.6	696.9
42.5°	735.1	711.7	695.7	681.8	677.8	673.1	667.7	667.4	668.5	670.8	668.5
45°	670.0	653.4	642.0	635.2	627.8	623.2	622.5	624.5	625.2	625.9	627.8
47.5°	610.4	599.2	588.9	581.5	578.2	577.4	576.6	580.2	583.4	584.6	587.6
50°	574.9	562.2	553.5	548.8	546.1	544.8	546.1	550.2	552.8	556.1	558.2
52.5°	535.2	526.2	520.3	516.6	515.5	516.3	516.6	521.2	525.5	526.6	527.7
55°	480.5	473.7	472.4	466.4	469.1	468.4	471.7	474.4	478.5	482.5	483.1
57.5°	425.8	420.4	416.8	417.4	418.2	421.1	423.9	428.6	432.9	437.2	437.6
60°	389.3	386.7	384.7	384.7	386.0	390.0	393.3	398.0	400.7	403.4	405.4
62.5°	356.1	353.5	351.4	352.4	356.0	358.4	362.2	364.8	367.5	370.1	371.1
65°	303.6	302.3	304.3	305.6	306.2	309.6	314.3	316.3	318.9	320.3	325.0
67.5°	255.2	255.4	255.2	257.0	260.9	261.8	266.2	270.8	271.4	274.0	277.0
70°	222.5	223.8	225.2	226.5	229.8	231.2	234.5	236.5	239.2	241.3	243.3
72.5°	192.5	192.7	194.1	193.8	196.6	199.5	202.4	204.4	207.0	209.6	211.6
75°	148.0	148.0	149.5	150.1	153.5	156.8	156.1	157.4	160.2	162.8	164.2
77.5°	108.2	106.6	108.2	108.9	109.9	112.7	113.2	115.1	118.2	117.2	118.8
80°	82.4	80.4	82.4	83.1	83.1	86.4	86.4	87.8	89.8	87.8	89.8
82.5°	58.9	57.9	59.4	59.5	60.6	60.7	61.8	62.0	64.0	63.1	64.0
85°	29.5	28.8	29.5	28.8	29.5	30.2	30.2	29.5	29.5	30.8	28.8
87.5°	11.1	10.9	10.7	11.1	10.9	10.7	10.3	10.5	10.7	9.9	10.0
90°	9.9	11.9	13.5	15.1	16.8	18.5	19.5	20.5	21.5	22.5	23.2
92.5°	17.8	18.1	19.0	19.8	20.6	21.4	21.9	22.4	23.0	23.5	23.9
95°	32.9	30.2	31.7	33.1	34.5	36.0	37.0	38.0	39.1	40.1	40.5
97.5°	42.7	34.8	38.2	41.5	44.8	48.2	49.0	49.8	50.6	51.4	51.9
100°	50.9	38.7	42.1	45.6	49.1	52.6	54.2	55.8	57.5	59.2	60.2
102.5°	188.1	170.7	141.5	112.3	83.2	54.0	56.1	58.3	60.5	62.6	63.9
105°	305.0	280.0	224.1	168.1	112.2	56.2	58.5	60.8	63.0	65.2	66.9
107.5°	378.3	347.2	280.0	213.0	145.8	78.8	76.4	74.1	71.9	69.6	68.9
110°	425.8	398.3	339.1	279.8	220.7	161.4	140.9	120.4	99.9	79.4	69.6



TEST NUMBER: P331402-840

CATALOG NUMBER: SA2XXDIP-C865D925U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	471.0	465.6	451.0	436.4	421.7	407.1	332.3	257.6	182.8	108.1	71.0
115°	544.2	548.6	553.7	558.9	563.9	569.1	474.1	379.3	284.4	189.5	134.6
117.5°	612.5	616.2	619.8	623.3	626.8	630.3	607.3	584.4	561.5	538.5	502.7
120°	657.9	661.3	665.0	668.6	672.4	676.0	678.5	681.0	683.5	685.9	673.3
122.5°	699.8	703.5	707.5	711.6	715.6	719.6	721.0	722.6	724.0	725.5	723.6
125°	760.5	763.8	767.7	771.5	775.5	779.3	780.8	782.2	783.7	785.1	786.1
127.5°	818.6	821.5	824.5	827.4	830.3	833.2	835.3	837.4	839.5	841.6	842.6
130°	856.1	858.9	861.1	863.3	865.7	867.9	870.1	872.4	874.6	876.9	878.0
132.5°	891.0	893.5	895.9	898.1	900.3	902.5	904.5	906.5	908.4	910.3	911.1
135°	941.0	943.5	945.3	947.3	949.1	950.9	952.9	955.0	957.0	959.1	959.9
137.5°	985.5	987.7	989.8	991.9	994.0	996.1	998.0	1000.1	1002.1	1004.1	1004.8
140°	1014.6	1016.6	1018.9	1021.1	1023.4	1025.6	1027.4	1029.3	1031.2	1033.0	1033.4
142.5°	1040.6	1042.6	1045.1	1047.7	1050.4	1052.9	1054.6	1056.2	1057.9	1059.7	1060.0
145°	1075.5	1077.1	1080.7	1084.1	1087.6	1091.1	1092.5	1094.0	1095.4	1096.8	1097.0
147.5°	1109.5	1110.9	1114.3	1117.8	1121.3	1124.7	1125.7	1126.8	1127.8	1128.9	1129.0
150°	1130.5	1131.5	1134.8	1138.0	1141.3	1144.6	1145.8	1147.0	1148.3	1149.5	1149.6
152.5°	1149.8	1150.5	1153.7	1156.8	1159.9	1163.1	1164.3	1165.5	1166.7	1167.9	1167.9
155°	1177.8	1178.1	1180.5	1183.1	1185.5	1187.9	1189.1	1190.4	1191.6	1192.9	1192.7
157.5°	1201.6	1201.7	1203.5	1205.2	1206.9	1208.6	1210.0	1211.3	1212.7	1214.2	1214.1
160°	1216.2	1216.2	1217.4	1218.7	1219.9	1221.1	1222.3	1223.6	1224.9	1226.1	1226.0
162.5°	1228.0	1227.9	1229.0	1230.0	1231.1	1232.2	1233.6	1235.0	1236.4	1237.8	1237.6
165°	1243.9	1243.5	1244.2	1244.8	1245.5	1246.1	1247.5	1248.9	1250.3	1251.7	1251.7
167.5°	1255.7	1255.4	1256.0	1256.5	1257.1	1257.7	1259.1	1260.5	1261.9	1263.4	1263.1
170°	1262.3	1261.9	1262.3	1262.7	1263.1	1263.5	1265.0	1266.5	1267.9	1269.3	1269.1
172.5°	1266.8	1266.4	1266.8	1267.2	1267.6	1268.0	1269.4	1270.8	1272.3	1273.7	1273.5
175°	1271.6	1271.1	1271.5	1271.9	1272.3	1272.7	1274.2	1275.7	1277.1	1278.5	1278.2
177.5°	1273.7	1273.2	1273.4	1273.5	1273.7	1273.8	1275.1	1276.2	1277.4	1278.5	1278.3
180°	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7



TEST NUMBER: P331402-840

CATALOG NUMBER: SA2XXDIP-C865D925U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5
2.5°	1672.2	1671.2	1671.2	1666.4	1671.2	1671.2	1672.2	1677.7	1679.2	1680.3	1678.2
5°	1551.3	1549.2	1545.9	1549.2	1545.9	1549.2	1551.3	1560.6	1565.3	1570.0	1574.1
7.5°	1431.6	1423.5	1422.3	1414.4	1422.3	1423.5	1431.6	1436.0	1445.4	1456.0	1465.6
10°	1344.2	1338.9	1338.2	1325.4	1338.2	1338.9	1344.2	1355.6	1364.9	1377.8	1391.1
12.5°	1277.8	1264.9	1267.4	1260.0	1267.4	1264.9	1277.8	1277.9	1288.9	1296.8	1317.7
15°	1162.7	1162.7	1159.9	1148.5	1159.9	1162.7	1162.7	1180.7	1184.1	1196.8	1214.9
17.5°	1079.9	1078.5	1072.2	1075.4	1072.2	1078.5	1079.9	1093.2	1095.5	1112.5	1127.4
20°	1030.6	1026.6	1018.5	1018.5	1018.5	1026.6	1030.6	1037.9	1046.7	1056.7	1069.4
22.5°	984.0	983.7	975.1	977.8	975.1	983.7	984.0	990.8	999.0	1010.1	1020.7
25°	929.4	924.0	920.1	922.0	920.1	924.0	929.4	930.1	939.5	946.8	953.5
27.5°	877.7	874.7	874.4	869.0	874.4	874.7	877.7	879.4	884.7	889.1	895.3
30°	847.7	841.0	842.3	839.0	842.3	841.0	847.7	848.4	851.0	853.7	861.1
32.5°	813.3	810.9	809.6	806.8	809.6	810.9	813.3	814.6	819.9	822.6	828.4
35°	766.6	767.3	763.9	765.3	763.9	767.3	766.6	767.9	768.6	771.2	776.7
37.5°	725.7	727.8	726.3	726.7	726.3	727.8	725.7	726.4	727.0	727.4	729.0
40°	698.9	698.9	698.9	700.9	698.9	698.9	698.9	696.9	697.6	696.9	696.9
42.5°	673.2	672.1	671.1	670.9	671.1	672.1	673.2	668.5	670.8	668.5	667.4
45°	629.2	631.3	631.9	628.5	631.9	631.3	629.2	627.8	625.9	625.2	624.5
47.5°	589.5	589.7	589.5	592.4	589.5	589.7	589.5	587.6	584.6	583.4	580.2
50°	561.6	560.2	561.6	560.2	561.6	560.2	561.6	558.2	556.1	552.8	550.2
52.5°	532.1	532.3	531.5	531.3	531.5	532.3	532.1	527.7	526.6	525.5	521.2
55°	485.8	487.2	486.5	486.5	486.5	487.2	485.8	483.1	482.5	478.5	474.4
57.5°	438.0	439.2	440.1	437.2	440.1	439.2	438.0	437.6	437.2	432.9	428.6
60°	404.8	408.1	407.4	406.1	407.4	408.1	404.8	405.4	403.4	400.7	398.0
62.5°	374.2	375.4	375.3	375.0	375.3	375.4	374.2	371.1	370.1	367.5	364.8
65°	327.0	328.3	326.3	328.3	326.3	328.3	327.0	325.0	320.3	318.9	316.3
67.5°	276.2	276.6	278.1	279.0	278.1	276.6	276.2	277.0	274.0	271.4	270.8
70°	244.6	243.9	245.9	247.9	245.9	243.9	244.6	243.3	241.3	239.2	236.5
72.5°	211.4	212.8	212.2	213.6	212.2	212.8	211.4	211.6	209.6	207.0	204.4
75°	162.8	164.8	164.2	166.2	164.2	164.8	162.8	164.2	162.8	160.2	157.4
77.5°	117.6	118.0	117.6	118.8	117.6	118.0	117.6	118.8	117.2	118.2	115.1
80°	89.8	88.5	87.2	89.8	87.2	88.5	89.8	89.8	87.8	89.8	87.8
82.5°	62.4	63.2	61.9	61.9	61.9	63.2	62.4	64.0	63.1	64.0	62.0
85°	28.8	28.2	26.8	26.8	26.8	28.2	28.8	28.8	30.8	29.5	29.5
87.5°	10.1	9.6	9.7	9.3	9.7	9.6	10.1	10.0	9.9	10.7	10.5
90°	23.6	24.0	24.5	24.9	24.5	24.0	23.6	23.2	22.5	21.5	20.5
92.5°	24.1	24.4	24.6	24.9	24.6	24.4	24.1	23.9	23.5	23.0	22.4
95°	40.3	40.1	39.9	39.7	39.9	40.1	40.3	40.5	40.1	39.1	38.0
97.5°	52.2	52.4	52.7	52.9	52.7	52.4	52.2	51.9	51.4	50.6	49.8
100°	60.6	61.0	61.4	61.8	61.4	61.0	60.6	60.2	59.2	57.5	55.8
102.5°	64.5	65.0	65.6	66.2	65.6	65.0	64.5	63.9	62.6	60.5	58.3
105°	67.7	68.5	69.3	70.1	69.3	68.5	67.7	66.9	65.2	63.0	60.8
107.5°	69.7	70.5	71.3	72.1	71.3	70.5	69.7	68.9	69.6	71.9	74.1
110°	70.4	71.2	72.0	72.9	72.0	71.2	70.4	69.6	79.4	99.9	120.4



TEST NUMBER: P331402-840
 CATALOG NUMBER: SA2XXDIP-C865D925U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	71.6	72.3	72.9	73.6	72.9	72.3	71.6	71.0	108.1	182.8	257.6
115°	119.9	105.1	90.4	75.6	90.4	105.1	119.9	134.6	189.5	284.4	379.3
117.5°	454.2	405.8	357.3	308.8	357.3	405.8	454.2	502.7	538.5	561.5	584.4
120°	645.6	617.9	590.3	562.6	590.3	617.9	645.6	673.3	685.9	683.5	681.0
122.5°	718.2	712.8	707.4	702.1	707.4	712.8	718.2	723.6	725.5	724.0	722.6
125°	786.7	787.3	788.0	788.6	788.0	787.3	786.7	786.1	785.1	783.7	782.2
127.5°	842.8	842.9	843.0	843.1	843.0	842.9	842.8	842.6	841.6	839.5	837.4
130°	877.8	877.5	877.3	877.1	877.3	877.5	877.8	878.0	876.9	874.6	872.4
132.5°	910.9	910.7	910.5	910.3	910.5	910.7	910.9	911.1	910.3	908.4	906.5
135°	959.5	959.1	958.7	958.3	958.7	959.1	959.5	959.9	959.1	957.0	955.0
137.5°	1004.1	1003.4	1002.7	1002.0	1002.7	1003.4	1004.1	1004.8	1004.1	1002.1	1000.1
140°	1032.4	1031.4	1030.4	1029.3	1030.4	1031.4	1032.4	1033.4	1033.0	1031.2	1029.3
142.5°	1058.9	1057.9	1056.9	1055.8	1056.9	1057.9	1058.9	1060.0	1059.7	1057.9	1056.2
145°	1096.0	1095.0	1094.0	1093.0	1094.0	1095.0	1096.0	1097.0	1096.8	1095.4	1094.0
147.5°	1128.1	1127.3	1126.4	1125.6	1126.4	1127.3	1128.1	1129.0	1128.9	1127.8	1126.8
150°	1148.6	1147.5	1146.5	1145.5	1146.5	1147.5	1148.6	1149.6	1149.5	1148.3	1147.0
152.5°	1166.5	1165.2	1163.9	1162.5	1163.9	1165.2	1166.5	1167.9	1167.9	1166.7	1165.5
155°	1191.0	1189.3	1187.7	1186.1	1187.7	1189.3	1191.0	1192.7	1192.9	1191.6	1190.4
157.5°	1212.4	1210.8	1209.2	1207.7	1209.2	1210.8	1212.4	1214.1	1214.2	1212.7	1211.3
160°	1224.5	1223.0	1221.6	1220.2	1221.6	1223.0	1224.5	1226.0	1226.1	1224.9	1223.6
162.5°	1235.9	1234.1	1232.3	1230.5	1232.3	1234.1	1235.9	1237.6	1237.8	1236.4	1235.0
165°	1250.3	1248.9	1247.5	1246.1	1247.5	1248.9	1250.3	1251.7	1251.7	1250.3	1248.9
167.5°	1261.3	1259.5	1257.7	1255.8	1257.7	1259.5	1261.3	1263.1	1263.4	1261.9	1260.5
170°	1267.3	1265.4	1263.5	1261.7	1263.5	1265.4	1267.3	1269.1	1269.3	1267.9	1266.5
172.5°	1271.6	1269.8	1268.0	1266.2	1268.0	1269.8	1271.6	1273.5	1273.7	1272.3	1270.8
175°	1276.2	1274.1	1272.0	1270.0	1272.0	1274.1	1276.2	1278.2	1278.5	1277.1	1275.7
177.5°	1276.9	1275.4	1273.8	1272.4	1273.8	1275.4	1276.9	1278.3	1278.5	1277.4	1276.2
180°	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7



TEST NUMBER: P331402-840
 CATALOG NUMBER: SA2XXDIP-C865D925U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5
2.5°	1675.5	1681.4	1690.5	1700.2	1706.1	1717.3	1720.5	1725.9	1730.7	1742.0	1753.7
5°	1578.7	1588.1	1610.2	1622.2	1639.0	1658.5	1671.2	1684.7	1699.4	1724.8	1748.3
7.5°	1475.0	1490.7	1518.1	1540.7	1564.5	1592.5	1612.6	1639.0	1661.0	1697.0	1731.2
10°	1405.8	1427.9	1452.8	1479.6	1513.1	1542.6	1570.7	1604.2	1631.0	1673.9	1714.1
12.5°	1343.6	1347.1	1382.5	1412.0	1457.8	1494.3	1526.7	1569.9	1596.2	1647.1	1689.4
15°	1235.0	1255.1	1287.3	1310.7	1364.9	1411.2	1456.8	1501.7	1531.9	1594.8	1650.4
17.5°	1143.5	1162.0	1194.9	1233.3	1272.3	1318.4	1377.4	1424.6	1465.6	1537.6	1603.4
20°	1085.5	1108.3	1141.9	1181.3	1215.6	1265.8	1316.8	1371.0	1415.2	1496.3	1573.4
22.5°	1036.2	1054.2	1081.3	1120.2	1157.6	1203.7	1259.4	1318.5	1364.8	1452.4	1530.5
25°	966.9	981.7	999.1	1031.3	1073.5	1123.8	1167.3	1232.3	1300.0	1381.7	1476.2
27.5°	904.5	914.9	930.4	958.7	991.4	1038.3	1086.7	1148.4	1216.5	1305.3	1404.9
30°	866.5	873.1	888.6	912.0	944.1	981.0	1030.0	1088.9	1158.6	1248.4	1347.6
32.5°	833.2	839.4	849.4	871.8	899.7	931.2	975.2	1034.2	1100.7	1188.9	1298.8
35°	783.4	788.0	796.8	814.9	830.2	861.1	898.0	951.5	1013.8	1098.3	1212.2
37.5°	733.7	740.0	745.4	753.1	772.8	793.1	825.2	870.4	931.6	1016.8	1125.4
40°	700.9	706.3	714.3	717.7	733.8	751.8	778.0	819.5	881.2	958.9	1064.8
42.5°	667.7	673.1	677.8	681.8	695.7	711.7	735.1	770.7	825.5	901.0	1005.8
45°	622.5	623.2	627.8	635.2	642.0	653.4	670.0	700.9	743.2	814.2	909.3
47.5°	576.6	577.4	578.2	581.5	588.9	599.2	610.4	635.4	673.2	729.8	822.4
50°	546.1	544.8	546.1	548.8	553.5	562.2	574.9	593.0	623.9	676.8	761.9
52.5°	516.6	516.3	515.5	516.6	520.3	526.2	535.2	550.7	578.2	626.9	701.9
55°	471.7	468.4	469.1	466.4	472.4	473.7	480.5	493.2	517.4	550.8	621.2
57.5°	423.9	421.1	418.2	417.4	416.8	420.4	425.8	435.9	454.3	483.6	540.8
60°	393.3	390.0	386.0	384.7	384.7	386.7	389.3	396.7	414.1	440.3	487.2
62.5°	362.2	358.4	356.0	352.4	351.4	353.5	356.1	361.3	374.0	398.4	438.9
65°	314.3	309.6	306.2	305.6	304.3	302.3	303.6	308.9	318.9	338.4	370.5
67.5°	266.2	261.8	260.9	257.0	255.2	255.4	255.2	259.7	265.8	282.6	306.5
70°	234.5	231.2	229.8	226.5	225.2	223.8	222.5	226.5	232.6	246.6	267.4
72.5°	202.4	199.5	196.6	193.8	194.1	192.7	192.5	194.9	199.9	212.8	228.7
75°	156.1	156.8	153.5	150.1	149.5	148.0	148.0	150.1	152.1	162.2	174.9
77.5°	113.2	112.7	109.9	108.9	108.2	106.6	108.2	109.5	110.6	117.2	126.6
80°	86.4	86.4	83.1	83.1	82.4	80.4	82.4	81.1	83.7	90.5	97.1
82.5°	61.8	60.7	60.6	59.5	59.4	57.9	58.9	60.2	61.2	65.8	69.8
85°	30.2	30.2	29.5	28.8	29.5	28.8	29.5	30.2	30.8	32.8	36.2
87.5°	10.3	10.7	10.9	11.1	10.7	10.9	11.1	11.2	11.8	11.9	12.0
90°	19.5	18.5	16.8	15.1	13.5	11.9	9.9	7.7	5.5	3.1	0.9
92.5°	21.9	21.4	20.6	19.8	19.0	18.1	17.8	18.0	18.2	18.4	18.6
95°	37.0	36.0	34.5	33.1	31.7	30.2	32.9	39.7	46.5	53.2	60.0
97.5°	49.0	48.2	44.8	41.5	38.2	34.8	42.7	61.8	80.9	99.9	119.0
100°	54.2	52.6	49.1	45.6	42.1	38.7	50.9	79.0	107.0	135.1	163.3
102.5°	56.1	54.0	83.2	112.3	141.5	170.7	188.1	194.1	200.1	206.0	212.0
105°	58.5	56.2	112.2	168.1	224.1	280.0	305.0	298.8	292.7	286.5	280.3
107.5°	76.4	78.8	145.8	213.0	280.0	347.2	378.3	373.2	368.3	363.3	358.4
110°	140.9	161.4	220.7	279.8	339.1	398.3	425.8	421.5	417.2	412.9	408.6



TEST NUMBER: P331402-840
 CATALOG NUMBER: SA2XXDIP-C865D925U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	332.3	407.1	421.7	436.4	451.0	465.6	471.0	467.3	463.4	459.6	455.8
115°	474.1	569.1	563.9	558.9	553.7	548.6	544.2	540.8	537.2	533.8	530.3
117.5°	607.3	630.3	626.8	623.3	619.8	616.2	612.5	608.6	604.7	600.8	596.9
120°	678.5	676.0	672.4	668.6	665.0	661.3	657.9	654.8	651.8	648.6	645.6
122.5°	721.0	719.6	715.6	711.6	707.5	703.5	699.8	696.6	693.4	690.1	686.9
125°	780.8	779.3	775.5	771.5	767.7	763.8	760.5	757.8	755.2	752.5	749.8
127.5°	835.3	833.2	830.3	827.4	824.5	821.5	818.6	815.7	812.7	809.8	806.8
130°	870.1	867.9	865.7	863.3	861.1	858.9	856.1	852.8	849.5	846.3	843.0
132.5°	904.5	902.5	900.3	898.1	895.9	893.5	891.0	888.3	885.4	882.6	879.9
135°	952.9	950.9	949.1	947.3	945.3	943.5	941.0	937.7	934.4	931.1	927.9
137.5°	998.0	996.1	994.0	991.9	989.8	987.7	985.5	983.2	981.0	978.7	976.3
140°	1027.4	1025.6	1023.4	1021.1	1018.9	1016.6	1014.6	1013.0	1011.4	1009.8	1008.0
142.5°	1054.6	1052.9	1050.4	1047.7	1045.1	1042.6	1040.6	1039.1	1037.6	1036.1	1034.6
145°	1092.5	1091.1	1087.6	1084.1	1080.7	1077.1	1075.5	1075.7	1075.9	1076.1	1076.3
147.5°	1125.7	1124.7	1121.3	1117.8	1114.3	1110.9	1109.5	1110.3	1111.2	1111.9	1112.7
150°	1145.8	1144.6	1141.3	1138.0	1134.8	1131.5	1130.5	1132.0	1133.4	1134.9	1136.3
152.5°	1164.3	1163.1	1159.9	1156.8	1153.7	1150.5	1149.8	1151.4	1153.0	1154.6	1156.2
155°	1189.1	1187.9	1185.5	1183.1	1180.5	1178.1	1177.8	1179.6	1181.4	1183.4	1185.2
157.5°	1210.0	1208.6	1206.9	1205.2	1203.5	1201.7	1201.6	1203.2	1204.8	1206.3	1207.8
160°	1222.3	1221.1	1219.9	1218.7	1217.4	1216.2	1216.2	1217.4	1218.7	1219.9	1221.1
162.5°	1233.6	1232.2	1231.1	1230.0	1229.0	1227.9	1228.0	1229.2	1230.5	1231.7	1232.9
165°	1247.5	1246.1	1245.5	1244.8	1244.2	1243.5	1243.9	1245.1	1246.4	1247.6	1248.8
167.5°	1259.1	1257.7	1257.1	1256.5	1256.0	1255.4	1255.7	1256.9	1258.2	1259.4	1260.6
170°	1265.0	1263.5	1263.1	1262.7	1262.3	1261.9	1262.3	1263.5	1264.8	1266.0	1267.3
172.5°	1269.4	1268.0	1267.6	1267.2	1266.8	1266.4	1266.8	1268.0	1269.2	1270.4	1271.6
175°	1274.2	1272.7	1272.3	1271.9	1271.5	1271.1	1271.6	1273.0	1274.6	1276.0	1277.4
177.5°	1275.1	1273.8	1273.7	1273.5	1273.4	1273.2	1273.7	1274.9	1276.1	1277.2	1278.3
180°	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7



TEST NUMBER: P331402-840

CATALOG NUMBER: SA2XXDIP-C865D925U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5
2.5°	1752.7	1755.3	1763.9	1772.5	1782.2	1784.8	1789.2	1785.4	1784.3	1794.5	1802.0
5°	1757.7	1769.7	1793.2	1814.6	1832.7	1845.4	1858.9	1864.2	1874.2	1888.3	1905.7
7.5°	1752.0	1775.4	1812.3	1843.6	1877.6	1902.1	1921.3	1937.6	1957.5	1984.2	2013.3
10°	1745.6	1777.1	1822.0	1860.2	1901.7	1933.2	1959.3	1984.8	2014.3	2051.1	2089.3
12.5°	1733.8	1771.2	1827.4	1872.5	1925.8	1956.8	1992.1	2047.0	2078.6	2130.0	2183.7
15°	1710.1	1751.6	1830.0	1885.6	1945.9	2004.9	2069.9	2122.2	2174.4	2204.6	2280.4
17.5°	1674.9	1735.9	1822.6	1887.5	1964.2	2057.1	2130.1	2189.3	2249.7	2298.6	2336.5
20°	1646.4	1712.7	1811.9	1889.7	1980.7	2080.6	2164.4	2224.7	2276.9	2317.8	2341.3
22.5°	1610.5	1693.9	1790.5	1881.6	1997.9	2096.7	2184.7	2232.2	2275.9	2295.8	2304.8
25°	1554.0	1654.5	1763.7	1874.9	2006.3	2110.8	2191.2	2220.0	2232.7	2213.3	2181.1
27.5°	1493.0	1605.0	1732.7	1862.3	2001.1	2101.6	2159.3	2154.7	2133.1	2070.3	2020.0
30°	1447.4	1570.7	1708.1	1849.5	1988.8	2086.7	2120.2	2086.7	2037.7	1967.4	1895.7
32.5°	1399.7	1527.3	1681.8	1831.2	1966.3	2052.3	2059.6	2002.0	1926.2	1846.2	1756.9
35°	1327.5	1465.5	1632.3	1790.5	1918.4	1972.8	1940.6	1838.8	1749.0	1639.7	1517.7
37.5°	1245.9	1398.3	1565.6	1730.8	1846.7	1861.0	1781.1	1673.9	1547.2	1418.9	1275.4
40°	1184.8	1346.3	1518.4	1685.3	1787.8	1773.0	1671.2	1553.3	1402.5	1245.7	1112.4
42.5°	1130.0	1291.5	1466.9	1630.6	1712.7	1672.2	1553.3	1408.6	1246.5	1098.8	976.7
45°	1035.3	1201.4	1381.1	1539.2	1586.1	1513.1	1355.6	1194.8	1035.3	912.0	815.5
47.5°	943.3	1107.6	1285.5	1424.5	1441.1	1342.8	1170.7	1005.3	868.2	767.8	699.7
50°	875.9	1040.7	1216.9	1340.9	1335.4	1216.9	1040.0	882.5	767.9	686.8	641.3
52.5°	815.3	971.0	1140.2	1252.9	1224.6	1095.2	926.3	786.6	692.4	628.9	587.6
55°	721.0	865.1	1025.9	1116.4	1064.1	920.7	778.0	665.4	595.7	548.2	515.9
57.5°	627.4	762.5	900.2	955.9	898.2	765.8	646.8	565.1	512.7	477.5	456.6
60°	569.6	687.5	810.1	858.4	789.4	671.5	577.6	504.6	462.3	433.5	414.8
62.5°	511.7	617.3	733.0	759.2	696.1	596.4	513.3	452.6	417.9	392.2	374.6
65°	432.9	519.3	607.1	624.5	566.2	489.2	423.5	384.0	353.1	334.4	320.3
67.5°	355.0	424.4	486.7	500.7	449.6	396.2	348.7	314.3	293.4	277.8	265.9
70°	308.9	363.9	414.8	426.2	385.3	337.7	301.5	274.1	255.3	241.9	230.6
72.5°	260.1	306.0	348.3	356.0	322.6	286.3	256.5	234.9	218.3	209.7	198.8
75°	199.0	225.8	258.6	260.6	238.5	216.4	193.7	179.6	170.9	160.2	154.8
77.5°	140.5	161.5	180.3	183.9	170.8	155.7	143.0	131.9	124.5	119.6	114.6
80°	107.2	124.0	132.0	136.7	127.3	116.6	109.3	101.9	97.1	93.8	90.5
82.5°	76.6	86.9	94.5	98.1	93.0	86.5	79.2	75.0	71.4	68.6	67.5
85°	38.9	43.5	48.3	49.6	48.3	45.5	41.5	41.5	39.5	38.9	38.9
87.5°	14.0	16.7	17.1	19.2	18.5	18.8	19.1	18.9	18.7	18.4	18.1
90°	3.1	5.5	7.7	9.9	11.9	13.5	15.1	16.8	18.5	19.5	20.5
92.5°	18.4	18.2	18.0	17.8	18.1	19.0	19.8	20.6	21.4	21.9	22.4
95°	53.2	46.5	39.7	32.9	30.2	31.7	33.1	34.5	36.0	37.0	38.0
97.5°	99.9	80.9	61.8	42.7	34.8	38.2	41.5	44.8	48.2	49.0	49.8
100°	135.1	107.0	79.0	50.9	38.7	42.1	45.6	49.1	52.6	54.2	55.8
102.5°	206.0	200.1	194.1	188.1	170.7	141.5	112.3	83.2	54.0	56.1	58.3
105°	286.5	292.7	298.8	305.0	280.0	224.1	168.1	112.2	56.2	58.5	60.8
107.5°	363.3	368.3	373.2	378.3	347.2	280.0	213.0	145.8	78.8	76.4	74.1
110°	412.9	417.2	421.5	425.8	398.3	339.1	279.8	220.7	161.4	140.9	120.4



TEST NUMBER: P331402-840
 CATALOG NUMBER: SA2XXDIP-C865D925U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	459.6	463.4	467.3	471.0	465.6	451.0	436.4	421.7	407.1	332.3	257.6
115°	533.8	537.2	540.8	544.2	548.6	553.7	558.9	563.9	569.1	474.1	379.3
117.5°	600.8	604.7	608.6	612.5	616.2	619.8	623.3	626.8	630.3	607.3	584.4
120°	648.6	651.8	654.8	657.9	661.3	665.0	668.6	672.4	676.0	678.5	681.0
122.5°	690.1	693.4	696.6	699.8	703.5	707.5	711.6	715.6	719.6	721.0	722.6
125°	752.5	755.2	757.8	760.5	763.8	767.7	771.5	775.5	779.3	780.8	782.2
127.5°	809.8	812.7	815.7	818.6	821.5	824.5	827.4	830.3	833.2	835.3	837.4
130°	846.3	849.5	852.8	856.1	858.9	861.1	863.3	865.7	867.9	870.1	872.4
132.5°	882.6	885.4	888.3	891.0	893.5	895.9	898.1	900.3	902.5	904.5	906.5
135°	931.1	934.4	937.7	941.0	943.5	945.3	947.3	949.1	950.9	952.9	955.0
137.5°	978.7	981.0	983.2	985.5	987.7	989.8	991.9	994.0	996.1	998.0	1000.1
140°	1009.8	1011.4	1013.0	1014.6	1016.6	1018.9	1021.1	1023.4	1025.6	1027.4	1029.3
142.5°	1036.1	1037.6	1039.1	1040.6	1042.6	1045.1	1047.7	1050.4	1052.9	1054.6	1056.2
145°	1076.1	1075.9	1075.7	1075.5	1077.1	1080.7	1084.1	1087.6	1091.1	1092.5	1094.0
147.5°	1111.9	1111.2	1110.3	1109.5	1110.9	1114.3	1117.8	1121.3	1124.7	1125.7	1126.8
150°	1134.9	1133.4	1132.0	1130.5	1131.5	1134.8	1138.0	1141.3	1144.6	1145.8	1147.0
152.5°	1154.6	1153.0	1151.4	1149.8	1150.5	1153.7	1156.8	1159.9	1163.1	1164.3	1165.5
155°	1183.4	1181.4	1179.6	1177.8	1178.1	1180.5	1183.1	1185.5	1187.9	1189.1	1190.4
157.5°	1206.3	1204.8	1203.2	1201.6	1201.7	1203.5	1205.2	1206.9	1208.6	1210.0	1211.3
160°	1219.9	1218.7	1217.4	1216.2	1216.2	1217.4	1218.7	1219.9	1221.1	1222.3	1223.6
162.5°	1231.7	1230.5	1229.2	1228.0	1227.9	1229.0	1230.0	1231.1	1232.2	1233.6	1235.0
165°	1247.6	1246.4	1245.1	1243.9	1243.5	1244.2	1244.8	1245.5	1246.1	1247.5	1248.9
167.5°	1259.4	1258.2	1256.9	1255.7	1255.4	1256.0	1256.5	1257.1	1257.7	1259.1	1260.5
170°	1266.0	1264.8	1263.5	1262.3	1261.9	1262.3	1262.7	1263.1	1263.5	1265.0	1266.5
172.5°	1270.4	1269.2	1268.0	1266.8	1266.4	1266.8	1267.2	1267.6	1268.0	1269.4	1270.8
175°	1276.0	1274.6	1273.0	1271.6	1271.1	1271.5	1271.9	1272.3	1272.7	1274.2	1275.7
177.5°	1277.2	1276.1	1274.9	1273.7	1273.2	1273.4	1273.5	1273.7	1273.8	1275.1	1276.2
180°	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7



TEST NUMBER: P331402-840
 CATALOG NUMBER: SA2XXDIP-C865D925U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5
2.5°	1808.5	1815.9	1815.9	1817.1	1825.6	1824.5	1824.0
5°	1924.5	1935.9	1937.2	1949.3	1957.3	1954.7	1947.3
7.5°	2034.0	2055.2	2071.2	2080.2	2090.8	2097.4	2094.5
10°	2120.8	2151.6	2170.4	2183.1	2198.6	2210.0	2205.9
12.5°	2199.7	2236.3	2262.1	2283.9	2285.9	2300.6	2290.7
15°	2322.6	2361.4	2365.4	2381.5	2394.3	2392.9	2393.6
17.5°	2363.2	2375.6	2378.1	2378.5	2378.7	2374.0	2363.8
20°	2348.6	2344.0	2332.6	2323.9	2308.5	2306.4	2293.1
22.5°	2280.1	2265.2	2236.6	2217.8	2193.7	2187.5	2183.7
25°	2145.0	2112.1	2066.6	2023.0	2010.9	1987.5	1994.2
27.5°	1959.6	1908.4	1859.1	1823.7	1791.7	1756.6	1766.7
30°	1829.4	1771.7	1702.0	1648.4	1614.3	1580.7	1574.7
32.5°	1673.9	1589.4	1511.8	1464.5	1412.2	1391.0	1367.8
35°	1405.8	1323.4	1246.4	1180.0	1141.9	1112.4	1085.5
37.5°	1164.8	1069.9	1007.6	953.9	926.3	909.5	913.7
40°	1015.2	932.1	886.6	845.7	820.2	808.1	810.8
42.5°	894.0	831.8	794.4	766.3	748.3	741.6	740.0
45°	756.5	721.6	690.8	674.8	666.1	658.7	654.0
47.5°	662.7	634.3	616.9	607.3	599.8	592.2	592.1
50°	606.4	587.6	575.6	565.5	559.6	554.2	558.9
52.5°	563.5	546.4	534.3	525.3	523.1	518.3	518.2
55°	499.9	486.5	477.8	469.7	465.7	463.0	459.7
57.5°	442.0	429.3	421.2	416.2	408.5	405.8	404.8
60°	400.7	390.6	382.6	375.9	372.5	367.2	367.2
62.5°	362.6	352.6	345.1	340.0	334.5	332.3	333.0
65°	307.6	299.5	292.2	286.8	285.5	281.4	282.8
67.5°	256.9	251.6	243.8	240.9	238.3	236.1	234.5
70°	223.2	217.8	213.8	209.7	207.7	207.7	207.7
72.5°	194.7	188.3	185.9	180.8	182.0	179.9	177.7
75°	150.8	146.7	144.7	142.7	139.4	139.4	139.4
77.5°	111.0	109.8	107.3	105.2	104.4	103.7	104.0
80°	85.7	85.1	83.7	83.7	82.4	81.8	80.4
82.5°	65.9	64.2	63.4	62.8	62.6	62.4	62.2
85°	37.6	36.2	36.2	36.9	35.5	35.5	36.2
87.5°	18.8	19.0	18.6	18.7	19.3	18.9	18.9
90°	21.5	22.5	23.2	23.6	24.0	24.5	24.9
92.5°	23.0	23.5	23.9	24.1	24.4	24.6	24.9
95°	39.1	40.1	40.5	40.3	40.1	39.9	39.7
97.5°	50.6	51.4	51.9	52.2	52.4	52.7	52.9
100°	57.5	59.2	60.2	60.6	61.0	61.4	61.8
102.5°	60.5	62.6	63.9	64.5	65.0	65.6	66.2
105°	63.0	65.2	66.9	67.7	68.5	69.3	70.1
107.5°	71.9	69.6	68.9	69.7	70.5	71.3	72.1
110°	99.9	79.4	69.6	70.4	71.2	72.0	72.9



TEST NUMBER: P331402-840
 CATALOG NUMBER: SA2XXDIP-C865D925U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	182.8	108.1	71.0	71.6	72.3	72.9	73.6
115°	284.4	189.5	134.6	119.9	105.1	90.4	75.6
117.5°	561.5	538.5	502.7	454.2	405.8	357.3	308.8
120°	683.5	685.9	673.3	645.6	617.9	590.3	562.6
122.5°	724.0	725.5	723.6	718.2	712.8	707.4	702.1
125°	783.7	785.1	786.1	786.7	787.3	788.0	788.6
127.5°	839.5	841.6	842.6	842.8	842.9	843.0	843.1
130°	874.6	876.9	878.0	877.8	877.5	877.3	877.1
132.5°	908.4	910.3	911.1	910.9	910.7	910.5	910.3
135°	957.0	959.1	959.9	959.5	959.1	958.7	958.3
137.5°	1002.1	1004.1	1004.8	1004.1	1003.4	1002.7	1002.0
140°	1031.2	1033.0	1033.4	1032.4	1031.4	1030.4	1029.3
142.5°	1057.9	1059.7	1060.0	1058.9	1057.9	1056.9	1055.8
145°	1095.4	1096.8	1097.0	1096.0	1095.0	1094.0	1093.0
147.5°	1127.8	1128.9	1129.0	1128.1	1127.3	1126.4	1125.6
150°	1148.3	1149.5	1149.6	1148.6	1147.5	1146.5	1145.5
152.5°	1166.7	1167.9	1167.9	1166.5	1165.2	1163.9	1162.5
155°	1191.6	1192.9	1192.7	1191.0	1189.3	1187.7	1186.1
157.5°	1212.7	1214.2	1214.1	1212.4	1210.8	1209.2	1207.7
160°	1224.9	1226.1	1226.0	1224.5	1223.0	1221.6	1220.2
162.5°	1236.4	1237.8	1237.6	1235.9	1234.1	1232.3	1230.5
165°	1250.3	1251.7	1251.7	1250.3	1248.9	1247.5	1246.1
167.5°	1261.9	1263.4	1263.1	1261.3	1259.5	1257.7	1255.8
170°	1267.9	1269.3	1269.1	1267.3	1265.4	1263.5	1261.7
172.5°	1272.3	1273.7	1273.5	1271.6	1269.8	1268.0	1266.2
175°	1277.1	1278.5	1278.2	1276.2	1274.1	1272.0	1270.0
177.5°	1277.4	1278.5	1278.3	1276.9	1275.4	1273.8	1272.4
180°	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7

(END OF REPORT)