

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331404-840

Luminaire Tested: **SA2XXDIP-C865D925U840-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331404-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXDIP-C865D925U840-4F0-1E-UDD-A4  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 865 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 925 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7498.4 lumens  
Efficiency: N/A  
Efficacy: 123.9 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 60.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331404-840  
CATALOG NUMBER: SA2XXDIP-C865D925U840-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P331404-840

CATALOG NUMBER: SA2XXDIP-C865D925U840-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51
1	99	94	91	87	91	87	84	81	74	72	70	62	61	59	51	50	49	44
2	90	83	77	72	83	77	72	68	66	62	59	55	53	50	46	44	42	38
3	83	73	66	61	76	68	62	57	58	54	50	49	46	43	41	39	37	33
4	76	65	58	52	70	61	54	49	52	47	43	44	41	37	37	34	32	28
5	70	58	51	45	64	55	48	42	47	42	37	40	36	33	34	31	28	25
6	64	53	45	39	59	49	42	37	43	37	33	36	32	29	31	28	25	22
7	60	48	40	34	55	45	38	33	39	33	29	33	29	26	28	25	22	20
8	55	43	36	31	51	41	34	29	35	30	26	31	26	23	26	23	20	18
9	52	40	32	27	48	37	31	26	33	27	24	28	24	21	24	21	18	16
10	48	37	29	25	45	34	28	24	30	25	21	26	22	19	22	19	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	28150	28150	28150	28150
5°	31561	28336	25109	28336
10°	36166	28103	21730	28103
15°	40010	27587	19198	27587
20°	39400	27034	17500	27034
25°	35527	26298	16425	26298
30°	29358	25124	15642	25124
35°	21396	23893	15084	23893
40°	17089	22443	14773	22443
45°	14933	20763	14351	20763
50°	14039	19138	14071	19138
55°	12940	17486	13695	17486
60°	11858	15733	13114	15733
65°	10804	14155	12542	14155
70°	9805	12623	11703	12623
75°	8696	10911	10368	10911
80°	7476	9028	8350	9028
85°	6706	6706	4965	6706



TEST NUMBER: P331404-840

CATALOG NUMBER: SA2XXDIP-C865D925U840-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	166.1	2.2
10°-20°	482.7	6.4
20°-30°	700.6	9.3
30°-40°	739.3	9.9
40°-50°	654.6	8.7
50°-60°	522.4	7.0
60°-70°	355.1	4.7
70°-80°	182.0	2.4
80°-90°	48.6	0.6
90°-100°	209.6	2.8
100°-110°	711.1	9.5
110°-120°	755.5	10.1
120°-130°	621.9	8.3
130°-140°	499.4	6.7
140°-150°	377.4	5.0
150°-160°	265.2	3.5
160°-170°	156.1	2.1
170°-180°	50.8	0.7
0°-30°	1349.4	18.0
0°-40°	2088.7	27.9
0°-60°	3265.7	43.6
0°-90°	3851.4	51.4
90°-120°	1676.1	22.4
90°-150°	3174.8	42.3
90°-180°	3647.0	48.6
0°-180°	7498.4	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1744	1744	1744	1744	1744	
5°	1947	1748	1549	1748	1947	194
15°	2394	1650	1148	1650	2394	660
25°	1994	1476	922	1476	1994	901
35°	1086	1212	765	1212	1086	706
45°	654	909	628	909	654	514
55°	460	621	486	621	460	412
65°	283	370	328	370	283	281
75°	139	175	166	175	139	149
85°	36	36	27	36	36	40
90°	33	1	33	1	33	20
95°	115	35	115	35	115	149
105°	1136	123	1136	123	1136	1099
115°	1495	217	1495	217	1495	1464
125°	1212	302	1212	302	1212	1096
135°	1005	355	1005	355	1005	781
145°	802	405	802	405	802	510
155°	674	461	674	461	674	315
165°	592	502	592	502	592	169
175°	533	523	533	523	533	52
180°	524	524	524	524	524	



TEST NUMBER: P331404-840

CATALOG NUMBER: SA2XXDIP-C865D925U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5
2.5°	1824.0	1824.5	1825.6	1817.1	1815.9	1815.9	1808.5	1802.0	1794.5	1784.3	1785.4
5°	1947.3	1954.7	1957.3	1949.3	1937.2	1935.9	1924.5	1905.7	1888.3	1874.2	1864.2
7.5°	2094.5	2097.4	2090.8	2080.2	2071.2	2055.2	2034.0	2013.3	1984.2	1957.5	1937.6
10°	2205.9	2210.0	2198.6	2183.1	2170.4	2151.6	2120.8	2089.3	2051.1	2014.3	1984.8
12.5°	2290.7	2300.6	2285.9	2283.9	2262.1	2236.3	2199.7	2183.7	2130.0	2078.6	2047.0
15°	2393.6	2392.9	2394.3	2381.5	2365.4	2361.4	2322.6	2280.4	2204.6	2174.4	2122.2
17.5°	2363.8	2374.0	2378.7	2378.5	2378.1	2375.6	2363.2	2336.5	2298.6	2249.7	2189.3
20°	2293.1	2306.4	2308.5	2323.9	2332.6	2344.0	2348.6	2341.3	2317.8	2276.9	2224.7
22.5°	2183.7	2187.5	2193.7	2217.8	2236.6	2265.2	2280.1	2304.8	2295.8	2275.9	2232.2
25°	1994.2	1987.5	2010.9	2023.0	2066.6	2112.1	2145.0	2181.1	2213.3	2232.7	2220.0
27.5°	1766.7	1756.6	1791.7	1823.7	1859.1	1908.4	1959.6	2020.0	2070.3	2133.1	2154.7
30°	1574.7	1580.7	1614.3	1648.4	1702.0	1771.7	1829.4	1895.7	1967.4	2037.7	2086.7
32.5°	1367.8	1391.0	1412.2	1464.5	1511.8	1589.4	1673.9	1756.9	1846.2	1926.2	2002.0
35°	1085.5	1112.4	1141.9	1180.0	1246.4	1323.4	1405.8	1517.7	1639.7	1749.0	1838.8
37.5°	913.7	909.5	926.3	953.9	1007.6	1069.9	1164.8	1275.4	1418.9	1547.2	1673.9
40°	810.8	808.1	820.2	845.7	886.6	932.1	1015.2	1112.4	1245.7	1402.5	1553.3
42.5°	740.0	741.6	748.3	766.3	794.4	831.8	894.0	976.7	1098.8	1246.5	1408.6
45°	654.0	658.7	666.1	674.8	690.8	721.6	756.5	815.5	912.0	1035.3	1194.8
47.5°	592.1	592.2	599.8	607.3	616.9	634.3	662.7	699.7	767.8	868.2	1005.3
50°	558.9	554.2	559.6	565.5	575.6	587.6	606.4	641.3	686.8	767.9	882.5
52.5°	518.2	518.3	523.1	525.3	534.3	546.4	563.5	587.6	628.9	692.4	786.6
55°	459.7	463.0	465.7	469.7	477.8	486.5	499.9	515.9	548.2	595.7	665.4
57.5°	404.8	405.8	408.5	416.2	421.2	429.3	442.0	456.6	477.5	512.7	565.1
60°	367.2	367.2	372.5	375.9	382.6	390.6	400.7	414.8	433.5	462.3	504.6
62.5°	333.0	332.3	334.5	340.0	345.1	352.6	362.6	374.6	392.2	417.9	452.6
65°	282.8	281.4	285.5	286.8	292.2	299.5	307.6	320.3	334.4	353.1	384.0
67.5°	234.5	236.1	238.3	240.9	243.8	251.6	256.9	265.9	277.8	293.4	314.3
70°	207.7	207.7	207.7	209.7	213.8	217.8	223.2	230.6	241.9	255.3	274.1
72.5°	177.7	179.9	182.0	180.8	185.9	188.3	194.7	198.8	209.7	218.3	234.9
75°	139.4	139.4	139.4	142.7	144.7	146.7	150.8	154.8	160.2	170.9	179.6
77.5°	104.0	103.7	104.4	105.2	107.3	109.8	111.0	114.6	119.6	124.5	131.9
80°	80.4	81.8	82.4	83.7	83.7	85.1	85.7	90.5	93.8	97.1	101.9
82.5°	62.2	62.4	62.6	62.8	63.4	64.2	65.9	67.5	68.6	71.4	75.0
85°	36.2	35.5	35.5	36.9	36.2	36.2	37.6	38.9	38.9	39.5	41.5
87.5°	20.6	20.6	21.1	20.6	20.6	20.9	20.5	20.4	21.1	21.9	22.2
90°	33.2	33.2	33.2	33.2	33.2	32.2	30.2	32.2	33.2	34.2	33.2
92.5°	55.8	57.5	56.7	59.9	60.7	67.0	75.4	87.9	110.7	131.0	129.2
95°	114.9	113.9	116.9	125.0	138.0	160.3	202.6	264.1	345.7	395.1	349.7
97.5°	226.2	234.6	249.3	274.2	322.3	395.1	504.1	616.2	707.5	674.5	508.0
100°	360.8	379.0	408.2	451.5	535.2	657.1	795.2	920.2	941.4	796.2	548.3
102.5°	635.0	659.5	696.0	770.0	860.9	990.2	1091.2	1119.3	1028.4	800.2	533.0
105°	1135.9	1149.9	1193.4	1255.8	1318.3	1351.6	1338.5	1224.6	1014.9	746.8	502.9
107.5°	1451.0	1469.7	1478.3	1481.8	1473.9	1425.1	1320.3	1148.8	926.5	689.6	488.0
110°	1546.1	1547.1	1538.0	1518.8	1475.5	1392.9	1263.8	1083.5	870.8	662.2	484.8



TEST NUMBER: P331404-840

CATALOG NUMBER: SA2XXDIP-C865D925U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1544.5	1539.0	1521.9	1489.9	1429.6	1334.8	1197.0	1023.8	832.1	644.4	485.5
115°	1494.7	1485.6	1459.4	1413.0	1341.5	1237.7	1105.6	950.4	784.2	624.9	489.8
117.5°	1405.7	1398.2	1370.5	1321.5	1248.6	1151.1	1031.5	895.1	753.9	615.4	497.1
120°	1348.6	1338.5	1309.2	1261.8	1191.3	1099.5	992.8	867.8	737.8	609.8	501.9
122.5°	1288.9	1280.4	1254.4	1207.8	1144.6	1061.7	960.5	846.0	724.1	606.5	507.6
125°	1212.4	1204.4	1179.2	1140.9	1082.5	1006.8	918.2	814.4	704.5	600.7	516.0
127.5°	1145.6	1139.1	1117.3	1081.5	1030.5	960.7	877.1	783.2	686.4	597.2	524.7
130°	1107.6	1099.5	1079.4	1045.2	995.8	929.3	849.6	763.0	674.3	595.6	531.2
132.5°	1068.1	1060.9	1042.4	1008.0	959.5	897.0	823.8	743.6	664.6	594.8	537.6
135°	1004.8	1000.8	982.7	949.4	906.1	849.6	783.2	716.6	651.1	593.6	545.2
137.5°	942.8	936.8	920.8	892.2	852.6	803.4	750.6	695.0	641.6	593.4	552.1
140°	900.0	894.0	878.9	852.6	820.4	776.1	729.7	681.4	636.0	592.6	555.3
142.5°	857.3	856.1	842.6	818.8	788.2	751.0	711.1	670.0	630.4	592.6	557.7
145°	802.2	799.2	789.2	772.0	747.8	718.6	687.4	654.1	622.9	590.6	560.4
147.5°	756.1	754.3	747.4	733.8	713.8	692.4	668.0	641.8	615.2	587.0	561.2
150°	728.7	727.7	721.6	709.5	694.4	676.3	655.1	633.0	608.7	584.6	560.4
152.5°	705.3	705.1	700.6	690.1	678.3	662.6	644.6	624.1	603.1	580.6	558.8
155°	674.3	676.3	672.3	665.2	654.1	643.0	627.9	611.8	592.6	573.5	556.3
157.5°	647.8	647.8	646.0	640.2	632.4	623.7	611.0	597.4	582.8	566.2	551.7
160°	631.0	631.0	630.0	624.9	617.8	610.8	599.7	588.5	575.5	561.4	549.3
162.5°	614.8	615.6	614.6	611.2	604.1	598.6	589.2	579.8	569.1	557.3	546.8
165°	591.6	592.6	592.6	588.5	584.6	580.6	573.5	566.4	558.4	549.3	542.2
167.5°	570.3	571.5	571.7	569.5	567.6	564.0	559.2	553.7	547.9	542.2	537.6
170°	557.3	559.4	560.4	557.3	556.3	554.3	550.3	547.2	542.2	538.2	535.2
172.5°	546.8	548.1	549.1	547.6	546.6	545.4	542.2	540.0	536.6	533.4	532.0
175°	533.2	535.2	536.2	535.2	535.2	534.2	533.2	532.2	529.2	528.2	527.1
177.5°	524.9	526.5	527.4	527.4	527.4	527.4	526.5	526.5	524.9	524.1	524.9
180°	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1



TEST NUMBER: P331404-840

CATALOG NUMBER: SA2XXDIP-C865D925U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5
2.5°	1789.2	1784.8	1782.2	1772.5	1763.9	1755.3	1752.7	1753.7	1742.0	1730.7	1725.9
5°	1858.9	1845.4	1832.7	1814.6	1793.2	1769.7	1757.7	1748.3	1724.8	1699.4	1684.7
7.5°	1921.3	1902.1	1877.6	1843.6	1812.3	1775.4	1752.0	1731.2	1697.0	1661.0	1639.0
10°	1959.3	1933.2	1901.7	1860.2	1822.0	1777.1	1745.6	1714.1	1673.9	1631.0	1604.2
12.5°	1992.1	1956.8	1925.8	1872.5	1827.4	1771.2	1733.8	1689.4	1647.1	1596.2	1569.9
15°	2069.9	2004.9	1945.9	1885.6	1830.0	1751.6	1710.1	1650.4	1594.8	1531.9	1501.7
17.5°	2130.1	2057.1	1964.2	1887.5	1822.6	1735.9	1674.9	1603.4	1537.6	1465.6	1424.6
20°	2164.4	2080.6	1980.7	1889.7	1811.9	1712.7	1646.4	1573.4	1496.3	1415.2	1371.0
22.5°	2184.7	2096.7	1997.9	1881.6	1790.5	1693.9	1610.5	1530.5	1452.4	1364.8	1318.5
25°	2191.2	2110.8	2006.3	1874.9	1763.7	1654.5	1554.0	1476.2	1381.7	1300.0	1232.3
27.5°	2159.3	2101.6	2001.1	1862.3	1732.7	1605.0	1493.0	1404.9	1305.3	1216.5	1148.4
30°	2120.2	2086.7	1988.8	1849.5	1708.1	1570.7	1447.4	1347.6	1248.4	1158.6	1088.9
32.5°	2059.6	2052.3	1966.3	1831.2	1681.8	1527.3	1399.7	1298.8	1188.9	1100.7	1034.2
35°	1940.6	1972.8	1918.4	1790.5	1632.3	1465.5	1327.5	1212.2	1098.3	1013.8	951.5
37.5°	1781.1	1861.0	1846.7	1730.8	1565.6	1398.3	1245.9	1125.4	1016.8	931.6	870.4
40°	1671.2	1773.0	1787.8	1685.3	1518.4	1346.3	1184.8	1064.8	958.9	881.2	819.5
42.5°	1553.3	1672.2	1712.7	1630.6	1466.9	1291.5	1130.0	1005.8	901.0	825.5	770.7
45°	1355.6	1513.1	1586.1	1539.2	1381.1	1201.4	1035.3	909.3	814.2	743.2	700.9
47.5°	1170.7	1342.8	1441.1	1424.5	1285.5	1107.6	943.3	822.4	729.8	673.2	635.4
50°	1040.0	1216.9	1335.4	1340.9	1216.9	1040.7	875.9	761.9	676.8	623.9	593.0
52.5°	926.3	1095.2	1224.6	1252.9	1140.2	971.0	815.3	701.9	626.9	578.2	550.7
55°	778.0	920.7	1064.1	1116.4	1025.9	865.1	721.0	621.2	550.8	517.4	493.2
57.5°	646.8	765.8	898.2	955.9	900.2	762.5	627.4	540.8	483.6	454.3	435.9
60°	577.6	671.5	789.4	858.4	810.1	687.5	569.6	487.2	440.3	414.1	396.7
62.5°	513.3	596.4	696.1	759.2	733.0	617.3	511.7	438.9	398.4	374.0	361.3
65°	423.5	489.2	566.2	624.5	607.1	519.3	432.9	370.5	338.4	318.9	308.9
67.5°	348.7	396.2	449.6	500.7	486.7	424.4	355.0	306.5	282.6	265.8	259.7
70°	301.5	337.7	385.3	426.2	414.8	363.9	308.9	267.4	246.6	232.6	226.5
72.5°	256.5	286.3	322.6	356.0	348.3	306.0	260.1	228.7	212.8	199.9	194.9
75°	193.7	216.4	238.5	260.6	258.6	225.8	199.0	174.9	162.2	152.1	150.1
77.5°	143.0	155.7	170.8	183.9	180.3	161.5	140.5	126.6	117.2	110.6	109.5
80°	109.3	116.6	127.3	136.7	132.0	124.0	107.2	97.1	90.5	83.7	81.1
82.5°	79.2	86.5	93.0	98.1	94.5	86.9	76.6	69.8	65.8	61.2	60.2
85°	41.5	45.5	48.3	49.6	48.3	43.5	38.9	36.2	32.8	30.8	30.2
87.5°	21.5	20.1	19.1	19.6	17.6	17.2	14.2	12.0	12.0	12.3	11.7
90°	27.2	20.2	15.1	12.1	10.1	8.1	4.0	1.0	4.0	8.1	10.1
92.5°	100.6	68.6	45.7	36.3	29.4	25.0	17.8	12.3	17.8	25.0	29.4
95°	232.8	145.1	98.8	74.6	58.5	49.4	39.3	35.2	39.3	49.4	58.5
97.5°	313.7	191.5	133.2	105.8	87.3	73.6	62.9	57.5	62.9	73.6	87.3
100°	330.6	207.6	154.2	126.0	105.8	89.7	80.6	77.6	80.6	89.7	105.8
102.5°	331.4	222.2	172.8	144.5	123.6	107.4	98.4	96.1	98.4	107.4	123.6
105°	336.6	246.9	199.5	171.4	149.2	134.0	127.0	123.0	127.0	134.0	149.2
107.5°	350.5	272.4	226.4	197.9	176.0	162.1	155.2	152.0	155.2	162.1	176.0
110°	361.8	289.2	244.9	215.7	194.5	181.4	175.4	171.4	175.4	181.4	194.5





TEST NUMBER: P331404-840

CATALOG NUMBER: SA2XXDIP-C865D925U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	374.0	305.4	262.7	232.6	212.3	200.0	193.1	189.0	193.1	200.0	212.3
115°	392.0	330.6	287.2	260.0	239.8	227.8	221.8	216.7	221.8	227.8	239.8
117.5°	411.4	353.8	313.7	285.4	266.1	255.4	249.3	245.3	249.3	255.4	266.1
120°	424.3	369.9	330.6	302.4	282.2	273.2	267.1	263.1	267.1	273.2	282.2
122.5°	435.6	385.2	348.3	319.3	299.1	289.2	283.2	280.0	283.2	289.2	299.1
125°	453.5	408.2	371.9	343.7	323.6	311.4	305.4	302.4	305.4	311.4	323.6
127.5°	470.3	429.6	394.3	365.3	345.9	332.5	324.2	320.1	324.2	332.5	345.9
130°	480.8	442.4	407.2	379.0	358.8	344.7	334.6	330.6	334.6	344.7	358.8
132.5°	491.2	453.7	420.1	391.8	370.9	356.0	345.1	340.2	345.1	356.0	370.9
135°	504.9	469.7	437.4	409.2	386.0	370.9	358.8	354.8	358.8	370.9	386.0
137.5°	515.4	482.6	450.7	424.5	401.5	385.4	373.3	368.5	373.3	385.4	401.5
140°	521.1	489.8	459.6	433.4	411.2	395.1	383.0	379.0	383.0	395.1	411.2
142.5°	525.9	495.4	466.1	441.4	420.1	403.9	392.6	389.4	392.6	403.9	420.1
145°	532.2	503.9	476.8	454.5	434.4	419.3	409.2	405.2	409.2	419.3	434.4
147.5°	535.6	510.8	485.2	465.4	448.7	434.7	425.2	422.1	425.2	434.7	448.7
150°	537.1	514.0	490.8	472.7	457.6	444.4	436.4	433.4	436.4	444.4	457.6
152.5°	538.0	517.3	496.4	480.0	465.6	454.1	446.1	444.6	446.1	454.1	465.6
155°	539.2	522.1	504.9	489.8	478.8	467.7	461.6	460.6	461.6	467.7	478.8
157.5°	539.2	525.5	511.0	498.3	489.4	479.8	474.9	473.9	474.9	479.8	489.4
160°	539.2	527.1	515.0	503.9	495.8	487.8	483.8	482.8	483.8	487.8	495.8
162.5°	538.4	528.0	517.5	508.8	501.5	495.0	491.0	491.6	491.0	495.0	501.5
165°	536.2	529.2	520.1	514.0	509.0	502.9	500.9	501.9	500.9	502.9	509.0
167.5°	534.8	529.0	522.3	518.5	514.8	511.0	509.2	510.4	509.2	511.0	514.8
170°	533.2	528.2	523.1	520.1	518.1	515.0	514.0	516.0	514.0	515.0	518.1
172.5°	530.8	527.4	523.9	521.7	520.5	517.5	518.1	519.3	518.1	517.5	520.5
175°	528.2	526.1	524.1	523.1	523.1	521.1	522.1	523.1	522.1	521.1	523.1
177.5°	526.5	524.9	524.1	524.1	524.1	522.5	523.3	524.9	523.3	522.5	524.1
180°	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1



TEST NUMBER: P331404-840

CATALOG NUMBER: SA2XXDIP-C865D925U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5
2.5°	1720.5	1717.3	1706.1	1700.2	1690.5	1681.4	1675.5	1678.2	1680.3	1679.2	1677.7
5°	1671.2	1658.5	1639.0	1622.2	1610.2	1588.1	1578.7	1574.1	1570.0	1565.3	1560.6
7.5°	1612.6	1592.5	1564.5	1540.7	1518.1	1490.7	1475.0	1465.6	1456.0	1445.4	1436.0
10°	1570.7	1542.6	1513.1	1479.6	1452.8	1427.9	1405.8	1391.1	1377.8	1364.9	1355.6
12.5°	1526.7	1494.3	1457.8	1412.0	1382.5	1347.1	1343.6	1317.7	1296.8	1288.9	1277.9
15°	1456.8	1411.2	1364.9	1310.7	1287.3	1255.1	1235.0	1214.9	1196.8	1184.1	1180.7
17.5°	1377.4	1318.4	1272.3	1233.3	1194.9	1162.0	1143.5	1127.4	1112.5	1095.5	1093.2
20°	1316.8	1265.8	1215.6	1181.3	1141.9	1108.3	1085.5	1069.4	1056.7	1046.7	1037.9
22.5°	1259.4	1203.7	1157.6	1120.2	1081.3	1054.2	1036.2	1020.7	1010.1	999.0	990.8
25°	1167.3	1123.8	1073.5	1031.3	999.1	981.7	966.9	953.5	946.8	939.5	930.1
27.5°	1086.7	1038.3	991.4	958.7	930.4	914.9	904.5	895.3	889.1	884.7	879.4
30°	1030.0	981.0	944.1	912.0	888.6	873.1	866.5	861.1	853.7	851.0	848.4
32.5°	975.2	931.2	899.7	871.8	849.4	839.4	833.2	828.4	822.6	819.9	814.6
35°	898.0	861.1	830.2	814.9	796.8	788.0	783.4	776.7	771.2	768.6	767.9
37.5°	825.2	793.1	772.8	753.1	745.4	740.0	733.7	729.0	727.4	727.0	726.4
40°	778.0	751.8	733.8	717.7	714.3	706.3	700.9	696.9	696.9	697.6	696.9
42.5°	735.1	711.7	695.7	681.8	677.8	673.1	667.7	667.4	668.5	670.8	668.5
45°	670.0	653.4	642.0	635.2	627.8	623.2	622.5	624.5	625.2	625.9	627.8
47.5°	610.4	599.2	588.9	581.5	578.2	577.4	576.6	580.2	583.4	584.6	587.6
50°	574.9	562.2	553.5	548.8	546.1	544.8	546.1	550.2	552.8	556.1	558.2
52.5°	535.2	526.2	520.3	516.6	515.5	516.3	516.6	521.2	525.5	526.6	527.7
55°	480.5	473.7	472.4	466.4	469.1	468.4	471.7	474.4	478.5	482.5	483.1
57.5°	425.8	420.4	416.8	417.4	418.2	421.1	423.9	428.6	432.9	437.2	437.6
60°	389.3	386.7	384.7	384.7	386.0	390.0	393.3	398.0	400.7	403.4	405.4
62.5°	356.1	353.5	351.4	352.4	356.0	358.4	362.2	364.8	367.5	370.1	371.1
65°	303.6	302.3	304.3	305.6	306.2	309.6	314.3	316.3	318.9	320.3	325.0
67.5°	255.2	255.4	255.2	257.0	260.9	261.8	266.2	270.8	271.4	274.0	277.0
70°	222.5	223.8	225.2	226.5	229.8	231.2	234.5	236.5	239.2	241.3	243.3
72.5°	192.5	192.7	194.1	193.8	196.6	199.5	202.4	204.4	207.0	209.6	211.6
75°	148.0	148.0	149.5	150.1	153.5	156.8	156.1	157.4	160.2	162.8	164.2
77.5°	108.2	106.6	108.2	108.9	109.9	112.7	113.2	115.1	118.2	117.2	118.8
80°	82.4	80.4	82.4	83.1	83.1	86.4	86.4	87.8	89.8	87.8	89.8
82.5°	58.9	57.9	59.4	59.5	60.6	60.7	61.8	62.0	64.0	63.1	64.0
85°	29.5	28.8	29.5	28.8	29.5	30.2	30.2	29.5	29.5	30.8	28.8
87.5°	11.5	11.6	12.1	13.5	14.1	13.8	13.1	12.9	12.5	11.8	12.0
90°	12.1	15.1	20.2	27.2	33.2	34.2	33.2	32.2	30.2	32.2	33.2
92.5°	36.3	45.7	68.6	100.6	129.2	131.0	110.7	87.9	75.4	67.0	60.7
95°	74.6	98.8	145.1	232.8	349.7	395.1	345.7	264.1	202.6	160.3	138.0
97.5°	105.8	133.2	191.5	313.7	508.0	674.5	707.5	616.2	504.1	395.1	322.3
100°	126.0	154.2	207.6	330.6	548.3	796.2	941.4	920.2	795.2	657.1	535.2
102.5°	144.5	172.8	222.2	331.4	533.0	800.2	1028.4	1119.3	1091.2	990.2	860.9
105°	171.4	199.5	246.9	336.6	502.9	746.8	1014.9	1224.6	1338.5	1351.6	1318.3
107.5°	197.9	226.4	272.4	350.5	488.0	689.6	926.5	1148.8	1320.3	1425.1	1473.9
110°	215.7	244.9	289.2	361.8	484.8	662.2	870.8	1083.5	1263.8	1392.9	1475.5



TEST NUMBER: P331404-840

CATALOG NUMBER: SA2XXDIP-C865D925U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	232.6	262.7	305.4	374.0	485.5	644.4	832.1	1023.8	1197.0	1334.8	1429.6
115°	260.0	287.2	330.6	392.0	489.8	624.9	784.2	950.4	1105.6	1237.7	1341.5
117.5°	285.4	313.7	353.8	411.4	497.1	615.4	753.9	895.1	1031.5	1151.1	1248.6
120°	302.4	330.6	369.9	424.3	501.9	609.8	737.8	867.8	992.8	1099.5	1191.3
122.5°	319.3	348.3	385.2	435.6	507.6	606.5	724.1	846.0	960.5	1061.7	1144.6
125°	343.7	371.9	408.2	453.5	516.0	600.7	704.5	814.4	918.2	1006.8	1082.5
127.5°	365.3	394.3	429.6	470.3	524.7	597.2	686.4	783.2	877.1	960.7	1030.5
130°	379.0	407.2	442.4	480.8	531.2	595.6	674.3	763.0	849.6	929.3	995.8
132.5°	391.8	420.1	453.7	491.2	537.6	594.8	664.6	743.6	823.8	897.0	959.5
135°	409.2	437.4	469.7	504.9	545.2	593.6	651.1	716.6	783.2	849.6	906.1
137.5°	424.5	450.7	482.6	515.4	552.1	593.4	641.6	695.0	750.6	803.4	852.6
140°	433.4	459.6	489.8	521.1	555.3	592.6	636.0	681.4	729.7	776.1	820.4
142.5°	441.4	466.1	495.4	525.9	557.7	592.6	630.4	670.0	711.1	751.0	788.2
145°	454.5	476.8	503.9	532.2	560.4	590.6	622.9	654.1	687.4	718.6	747.8
147.5°	465.4	485.2	510.8	535.6	561.2	587.0	615.2	641.8	668.0	692.4	713.8
150°	472.7	490.8	514.0	537.1	560.4	584.6	608.7	633.0	655.1	676.3	694.4
152.5°	480.0	496.4	517.3	538.0	558.8	580.6	603.1	624.1	644.6	662.6	678.3
155°	489.8	504.9	522.1	539.2	556.3	573.5	592.6	611.8	627.9	643.0	654.1
157.5°	498.3	511.0	525.5	539.2	551.7	566.2	582.8	597.4	611.0	623.7	632.4
160°	503.9	515.0	527.1	539.2	549.3	561.4	575.5	588.5	599.7	610.8	617.8
162.5°	508.8	517.5	528.0	538.4	546.8	557.3	569.1	579.8	589.2	598.6	604.1
165°	514.0	520.1	529.2	536.2	542.2	549.3	558.4	566.4	573.5	580.6	584.6
167.5°	518.5	522.3	529.0	534.8	537.6	542.2	547.9	553.7	559.2	564.0	567.6
170°	520.1	523.1	528.2	533.2	535.2	538.2	542.2	547.2	550.3	554.3	556.3
172.5°	521.7	523.9	527.4	530.8	532.0	533.4	536.6	540.0	542.2	545.4	546.6
175°	523.1	524.1	526.1	528.2	527.1	528.2	529.2	532.2	533.2	534.2	535.2
177.5°	524.1	524.1	524.9	526.5	524.9	524.1	524.9	526.5	526.5	527.4	527.4
180°	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1



TEST NUMBER: P331404-840  
 CATALOG NUMBER: SA2XXDIP-C865D925U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5
2.5°	1672.2	1671.2	1671.2	1666.4	1671.2	1671.2	1672.2	1677.7	1679.2	1680.3	1678.2
5°	1551.3	1549.2	1545.9	1549.2	1545.9	1549.2	1551.3	1560.6	1565.3	1570.0	1574.1
7.5°	1431.6	1423.5	1422.3	1414.4	1422.3	1423.5	1431.6	1436.0	1445.4	1456.0	1465.6
10°	1344.2	1338.9	1338.2	1325.4	1338.2	1338.9	1344.2	1355.6	1364.9	1377.8	1391.1
12.5°	1277.8	1264.9	1267.4	1260.0	1267.4	1264.9	1277.8	1277.9	1288.9	1296.8	1317.7
15°	1162.7	1162.7	1159.9	1148.5	1159.9	1162.7	1162.7	1180.7	1184.1	1196.8	1214.9
17.5°	1079.9	1078.5	1072.2	1075.4	1072.2	1078.5	1079.9	1093.2	1095.5	1112.5	1127.4
20°	1030.6	1026.6	1018.5	1018.5	1018.5	1026.6	1030.6	1037.9	1046.7	1056.7	1069.4
22.5°	984.0	983.7	975.1	977.8	975.1	983.7	984.0	990.8	999.0	1010.1	1020.7
25°	929.4	924.0	920.1	922.0	920.1	924.0	929.4	930.1	939.5	946.8	953.5
27.5°	877.7	874.7	874.4	869.0	874.4	874.7	877.7	879.4	884.7	889.1	895.3
30°	847.7	841.0	842.3	839.0	842.3	841.0	847.7	848.4	851.0	853.7	861.1
32.5°	813.3	810.9	809.6	806.8	809.6	810.9	813.3	814.6	819.9	822.6	828.4
35°	766.6	767.3	763.9	765.3	763.9	767.3	766.6	767.9	768.6	771.2	776.7
37.5°	725.7	727.8	726.3	726.7	726.3	727.8	725.7	726.4	727.0	727.4	729.0
40°	698.9	698.9	698.9	700.9	698.9	698.9	698.9	696.9	697.6	696.9	696.9
42.5°	673.2	672.1	671.1	670.9	671.1	672.1	673.2	668.5	670.8	668.5	667.4
45°	629.2	631.3	631.9	628.5	631.9	631.3	629.2	627.8	625.9	625.2	624.5
47.5°	589.5	589.7	589.5	592.4	589.5	589.7	589.5	587.6	584.6	583.4	580.2
50°	561.6	560.2	561.6	560.2	561.6	560.2	561.6	558.2	556.1	552.8	550.2
52.5°	532.1	532.3	531.5	531.3	531.5	532.3	532.1	527.7	526.6	525.5	521.2
55°	485.8	487.2	486.5	486.5	486.5	487.2	485.8	483.1	482.5	478.5	474.4
57.5°	438.0	439.2	440.1	437.2	440.1	439.2	438.0	437.6	437.2	432.9	428.6
60°	404.8	408.1	407.4	406.1	407.4	408.1	404.8	405.4	403.4	400.7	398.0
62.5°	374.2	375.4	375.3	375.0	375.3	375.4	374.2	371.1	370.1	367.5	364.8
65°	327.0	328.3	326.3	328.3	326.3	328.3	327.0	325.0	320.3	318.9	316.3
67.5°	276.2	276.6	278.1	279.0	278.1	276.6	276.2	277.0	274.0	271.4	270.8
70°	244.6	243.9	245.9	247.9	245.9	243.9	244.6	243.3	241.3	239.2	236.5
72.5°	211.4	212.8	212.2	213.6	212.2	212.8	211.4	211.6	209.6	207.0	204.4
75°	162.8	164.8	164.2	166.2	164.2	164.8	162.8	164.2	162.8	160.2	157.4
77.5°	117.6	118.0	117.6	118.8	117.6	118.0	117.6	118.8	117.2	118.2	115.1
80°	89.8	88.5	87.2	89.8	87.2	88.5	89.8	89.8	87.8	89.8	87.8
82.5°	62.4	63.2	61.9	61.9	61.9	63.2	62.4	64.0	63.1	64.0	62.0
85°	28.8	28.2	26.8	26.8	26.8	28.2	28.8	28.8	30.8	29.5	29.5
87.5°	12.0	11.5	11.5	10.9	11.5	11.5	12.0	12.0	11.8	12.5	12.9
90°	33.2	33.2	33.2	33.2	33.2	33.2	33.2	33.2	32.2	30.2	32.2
92.5°	59.9	56.7	57.5	55.8	57.5	56.7	59.9	60.7	67.0	75.4	87.9
95°	125.0	116.9	113.9	114.9	113.9	116.9	125.0	138.0	160.3	202.6	264.1
97.5°	274.2	249.3	234.6	226.2	234.6	249.3	274.2	322.3	395.1	504.1	616.2
100°	451.5	408.2	379.0	360.8	379.0	408.2	451.5	535.2	657.1	795.2	920.2
102.5°	770.0	696.0	659.5	635.0	659.5	696.0	770.0	860.9	990.2	1091.2	1119.3
105°	1255.8	1193.4	1149.9	1135.9	1149.9	1193.4	1255.8	1318.3	1351.6	1338.5	1224.6
107.5°	1481.8	1478.3	1469.7	1451.0	1469.7	1478.3	1481.8	1473.9	1425.1	1320.3	1148.8
110°	1518.8	1538.0	1547.1	1546.1	1547.1	1538.0	1518.8	1475.5	1392.9	1263.8	1083.5



TEST NUMBER: P331404-840

CATALOG NUMBER: SA2XXDIP-C865D925U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1489.9	1521.9	1539.0	1544.5	1539.0	1521.9	1489.9	1429.6	1334.8	1197.0	1023.8
115°	1413.0	1459.4	1485.6	1494.7	1485.6	1459.4	1413.0	1341.5	1237.7	1105.6	950.4
117.5°	1321.5	1370.5	1398.2	1405.7	1398.2	1370.5	1321.5	1248.6	1151.1	1031.5	895.1
120°	1261.8	1309.2	1338.5	1348.6	1338.5	1309.2	1261.8	1191.3	1099.5	992.8	867.8
122.5°	1207.8	1254.4	1280.4	1288.9	1280.4	1254.4	1207.8	1144.6	1061.7	960.5	846.0
125°	1140.9	1179.2	1204.4	1212.4	1204.4	1179.2	1140.9	1082.5	1006.8	918.2	814.4
127.5°	1081.5	1117.3	1139.1	1145.6	1139.1	1117.3	1081.5	1030.5	960.7	877.1	783.2
130°	1045.2	1079.4	1099.5	1107.6	1099.5	1079.4	1045.2	995.8	929.3	849.6	763.0
132.5°	1008.0	1042.4	1060.9	1068.1	1060.9	1042.4	1008.0	959.5	897.0	823.8	743.6
135°	949.4	982.7	1000.8	1004.8	1000.8	982.7	949.4	906.1	849.6	783.2	716.6
137.5°	892.2	920.8	936.8	942.8	936.8	920.8	892.2	852.6	803.4	750.6	695.0
140°	852.6	878.9	894.0	900.0	894.0	878.9	852.6	820.4	776.1	729.7	681.4
142.5°	818.8	842.6	856.1	857.3	856.1	842.6	818.8	788.2	751.0	711.1	670.0
145°	772.0	789.2	799.2	802.2	799.2	789.2	772.0	747.8	718.6	687.4	654.1
147.5°	733.8	747.4	754.3	756.1	754.3	747.4	733.8	713.8	692.4	668.0	641.8
150°	709.5	721.6	727.7	728.7	727.7	721.6	709.5	694.4	676.3	655.1	633.0
152.5°	690.1	700.6	705.1	705.3	705.1	700.6	690.1	678.3	662.6	644.6	624.1
155°	665.2	672.3	676.3	674.3	676.3	672.3	665.2	654.1	643.0	627.9	611.8
157.5°	640.2	646.0	647.8	647.8	647.8	646.0	640.2	632.4	623.7	611.0	597.4
160°	624.9	630.0	631.0	631.0	631.0	630.0	624.9	617.8	610.8	599.7	588.5
162.5°	611.2	614.6	615.6	614.8	615.6	614.6	611.2	604.1	598.6	589.2	579.8
165°	588.5	592.6	592.6	591.6	592.6	592.6	588.5	584.6	580.6	573.5	566.4
167.5°	569.5	571.7	571.5	570.3	571.5	571.7	569.5	567.6	564.0	559.2	553.7
170°	557.3	560.4	559.4	557.3	559.4	560.4	557.3	556.3	554.3	550.3	547.2
172.5°	547.6	549.1	548.1	546.8	548.1	549.1	547.6	546.6	545.4	542.2	540.0
175°	535.2	536.2	535.2	533.2	535.2	536.2	535.2	535.2	534.2	533.2	532.2
177.5°	527.4	527.4	526.5	524.9	526.5	527.4	527.4	527.4	527.4	526.5	526.5
180°	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1



TEST NUMBER: P331404-840

CATALOG NUMBER: SA2XXDIP-C865D925U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5
2.5°	1675.5	1681.4	1690.5	1700.2	1706.1	1717.3	1720.5	1725.9	1730.7	1742.0	1753.7
5°	1578.7	1588.1	1610.2	1622.2	1639.0	1658.5	1671.2	1684.7	1699.4	1724.8	1748.3
7.5°	1475.0	1490.7	1518.1	1540.7	1564.5	1592.5	1612.6	1639.0	1661.0	1697.0	1731.2
10°	1405.8	1427.9	1452.8	1479.6	1513.1	1542.6	1570.7	1604.2	1631.0	1673.9	1714.1
12.5°	1343.6	1347.1	1382.5	1412.0	1457.8	1494.3	1526.7	1569.9	1596.2	1647.1	1689.4
15°	1235.0	1255.1	1287.3	1310.7	1364.9	1411.2	1456.8	1501.7	1531.9	1594.8	1650.4
17.5°	1143.5	1162.0	1194.9	1233.3	1272.3	1318.4	1377.4	1424.6	1465.6	1537.6	1603.4
20°	1085.5	1108.3	1141.9	1181.3	1215.6	1265.8	1316.8	1371.0	1415.2	1496.3	1573.4
22.5°	1036.2	1054.2	1081.3	1120.2	1157.6	1203.7	1259.4	1318.5	1364.8	1452.4	1530.5
25°	966.9	981.7	999.1	1031.3	1073.5	1123.8	1167.3	1232.3	1300.0	1381.7	1476.2
27.5°	904.5	914.9	930.4	958.7	991.4	1038.3	1086.7	1148.4	1216.5	1305.3	1404.9
30°	866.5	873.1	888.6	912.0	944.1	981.0	1030.0	1088.9	1158.6	1248.4	1347.6
32.5°	833.2	839.4	849.4	871.8	899.7	931.2	975.2	1034.2	1100.7	1188.9	1298.8
35°	783.4	788.0	796.8	814.9	830.2	861.1	898.0	951.5	1013.8	1098.3	1212.2
37.5°	733.7	740.0	745.4	753.1	772.8	793.1	825.2	870.4	931.6	1016.8	1125.4
40°	700.9	706.3	714.3	717.7	733.8	751.8	778.0	819.5	881.2	958.9	1064.8
42.5°	667.7	673.1	677.8	681.8	695.7	711.7	735.1	770.7	825.5	901.0	1005.8
45°	622.5	623.2	627.8	635.2	642.0	653.4	670.0	700.9	743.2	814.2	909.3
47.5°	576.6	577.4	578.2	581.5	588.9	599.2	610.4	635.4	673.2	729.8	822.4
50°	546.1	544.8	546.1	548.8	553.5	562.2	574.9	593.0	623.9	676.8	761.9
52.5°	516.6	516.3	515.5	516.6	520.3	526.2	535.2	550.7	578.2	626.9	701.9
55°	471.7	468.4	469.1	466.4	472.4	473.7	480.5	493.2	517.4	550.8	621.2
57.5°	423.9	421.1	418.2	417.4	416.8	420.4	425.8	435.9	454.3	483.6	540.8
60°	393.3	390.0	386.0	384.7	384.7	386.7	389.3	396.7	414.1	440.3	487.2
62.5°	362.2	358.4	356.0	352.4	351.4	353.5	356.1	361.3	374.0	398.4	438.9
65°	314.3	309.6	306.2	305.6	304.3	302.3	303.6	308.9	318.9	338.4	370.5
67.5°	266.2	261.8	260.9	257.0	255.2	255.4	255.2	259.7	265.8	282.6	306.5
70°	234.5	231.2	229.8	226.5	225.2	223.8	222.5	226.5	232.6	246.6	267.4
72.5°	202.4	199.5	196.6	193.8	194.1	192.7	192.5	194.9	199.9	212.8	228.7
75°	156.1	156.8	153.5	150.1	149.5	148.0	148.0	150.1	152.1	162.2	174.9
77.5°	113.2	112.7	109.9	108.9	108.2	106.6	108.2	109.5	110.6	117.2	126.6
80°	86.4	86.4	83.1	83.1	82.4	80.4	82.4	81.1	83.7	90.5	97.1
82.5°	61.8	60.7	60.6	59.5	59.4	57.9	58.9	60.2	61.2	65.8	69.8
85°	30.2	30.2	29.5	28.8	29.5	28.8	29.5	30.2	30.8	32.8	36.2
87.5°	13.1	13.8	14.1	13.5	12.1	11.6	11.5	11.7	12.3	12.0	12.0
90°	33.2	34.2	33.2	27.2	20.2	15.1	12.1	10.1	8.1	4.0	1.0
92.5°	110.7	131.0	129.2	100.6	68.6	45.7	36.3	29.4	25.0	17.8	12.3
95°	345.7	395.1	349.7	232.8	145.1	98.8	74.6	58.5	49.4	39.3	35.2
97.5°	707.5	674.5	508.0	313.7	191.5	133.2	105.8	87.3	73.6	62.9	57.5
100°	941.4	796.2	548.3	330.6	207.6	154.2	126.0	105.8	89.7	80.6	77.6
102.5°	1028.4	800.2	533.0	331.4	222.2	172.8	144.5	123.6	107.4	98.4	96.1
105°	1014.9	746.8	502.9	336.6	246.9	199.5	171.4	149.2	134.0	127.0	123.0
107.5°	926.5	689.6	488.0	350.5	272.4	226.4	197.9	176.0	162.1	155.2	152.0
110°	870.8	662.2	484.8	361.8	289.2	244.9	215.7	194.5	181.4	175.4	171.4



TEST NUMBER: P331404-840

CATALOG NUMBER: SA2XXDIP-C865D925U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	832.1	644.4	485.5	374.0	305.4	262.7	232.6	212.3	200.0	193.1	189.0
115°	784.2	624.9	489.8	392.0	330.6	287.2	260.0	239.8	227.8	221.8	216.7
117.5°	753.9	615.4	497.1	411.4	353.8	313.7	285.4	266.1	255.4	249.3	245.3
120°	737.8	609.8	501.9	424.3	369.9	330.6	302.4	282.2	273.2	267.1	263.1
122.5°	724.1	606.5	507.6	435.6	385.2	348.3	319.3	299.1	289.2	283.2	280.0
125°	704.5	600.7	516.0	453.5	408.2	371.9	343.7	323.6	311.4	305.4	302.4
127.5°	686.4	597.2	524.7	470.3	429.6	394.3	365.3	345.9	332.5	324.2	320.1
130°	674.3	595.6	531.2	480.8	442.4	407.2	379.0	358.8	344.7	334.6	330.6
132.5°	664.6	594.8	537.6	491.2	453.7	420.1	391.8	370.9	356.0	345.1	340.2
135°	651.1	593.6	545.2	504.9	469.7	437.4	409.2	386.0	370.9	358.8	354.8
137.5°	641.6	593.4	552.1	515.4	482.6	450.7	424.5	401.5	385.4	373.3	368.5
140°	636.0	592.6	555.3	521.1	489.8	459.6	433.4	411.2	395.1	383.0	379.0
142.5°	630.4	592.6	557.7	525.9	495.4	466.1	441.4	420.1	403.9	392.6	389.4
145°	622.9	590.6	560.4	532.2	503.9	476.8	454.5	434.4	419.3	409.2	405.2
147.5°	615.2	587.0	561.2	535.6	510.8	485.2	465.4	448.7	434.7	425.2	422.1
150°	608.7	584.6	560.4	537.1	514.0	490.8	472.7	457.6	444.4	436.4	433.4
152.5°	603.1	580.6	558.8	538.0	517.3	496.4	480.0	465.6	454.1	446.1	444.6
155°	592.6	573.5	556.3	539.2	522.1	504.9	489.8	478.8	467.7	461.6	460.6
157.5°	582.8	566.2	551.7	539.2	525.5	511.0	498.3	489.4	479.8	474.9	473.9
160°	575.5	561.4	549.3	539.2	527.1	515.0	503.9	495.8	487.8	483.8	482.8
162.5°	569.1	557.3	546.8	538.4	528.0	517.5	508.8	501.5	495.0	491.0	491.6
165°	558.4	549.3	542.2	536.2	529.2	520.1	514.0	509.0	502.9	500.9	501.9
167.5°	547.9	542.2	537.6	534.8	529.0	522.3	518.5	514.8	511.0	509.2	510.4
170°	542.2	538.2	535.2	533.2	528.2	523.1	520.1	518.1	515.0	514.0	516.0
172.5°	536.6	533.4	532.0	530.8	527.4	523.9	521.7	520.5	517.5	518.1	519.3
175°	529.2	528.2	527.1	528.2	526.1	524.1	523.1	523.1	521.1	522.1	523.1
177.5°	524.9	524.1	524.9	526.5	524.9	524.1	524.1	524.1	522.5	523.3	524.9
180°	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1





TEST NUMBER: P331404-840

CATALOG NUMBER: SA2XXDIP-C865D925U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5
2.5°	1752.7	1755.3	1763.9	1772.5	1782.2	1784.8	1789.2	1785.4	1784.3	1794.5	1802.0
5°	1757.7	1769.7	1793.2	1814.6	1832.7	1845.4	1858.9	1864.2	1874.2	1888.3	1905.7
7.5°	1752.0	1775.4	1812.3	1843.6	1877.6	1902.1	1921.3	1937.6	1957.5	1984.2	2013.3
10°	1745.6	1777.1	1822.0	1860.2	1901.7	1933.2	1959.3	1984.8	2014.3	2051.1	2089.3
12.5°	1733.8	1771.2	1827.4	1872.5	1925.8	1956.8	1992.1	2047.0	2078.6	2130.0	2183.7
15°	1710.1	1751.6	1830.0	1885.6	1945.9	2004.9	2069.9	2122.2	2174.4	2204.6	2280.4
17.5°	1674.9	1735.9	1822.6	1887.5	1964.2	2057.1	2130.1	2189.3	2249.7	2298.6	2336.5
20°	1646.4	1712.7	1811.9	1889.7	1980.7	2080.6	2164.4	2224.7	2276.9	2317.8	2341.3
22.5°	1610.5	1693.9	1790.5	1881.6	1997.9	2096.7	2184.7	2232.2	2275.9	2295.8	2304.8
25°	1554.0	1654.5	1763.7	1874.9	2006.3	2110.8	2191.2	2220.0	2232.7	2213.3	2181.1
27.5°	1493.0	1605.0	1732.7	1862.3	2001.1	2101.6	2159.3	2154.7	2133.1	2070.3	2020.0
30°	1447.4	1570.7	1708.1	1849.5	1988.8	2086.7	2120.2	2086.7	2037.7	1967.4	1895.7
32.5°	1399.7	1527.3	1681.8	1831.2	1966.3	2052.3	2059.6	2002.0	1926.2	1846.2	1756.9
35°	1327.5	1465.5	1632.3	1790.5	1918.4	1972.8	1940.6	1838.8	1749.0	1639.7	1517.7
37.5°	1245.9	1398.3	1565.6	1730.8	1846.7	1861.0	1781.1	1673.9	1547.2	1418.9	1275.4
40°	1184.8	1346.3	1518.4	1685.3	1787.8	1773.0	1671.2	1553.3	1402.5	1245.7	1112.4
42.5°	1130.0	1291.5	1466.9	1630.6	1712.7	1672.2	1553.3	1408.6	1246.5	1098.8	976.7
45°	1035.3	1201.4	1381.1	1539.2	1586.1	1513.1	1355.6	1194.8	1035.3	912.0	815.5
47.5°	943.3	1107.6	1285.5	1424.5	1441.1	1342.8	1170.7	1005.3	868.2	767.8	699.7
50°	875.9	1040.7	1216.9	1340.9	1335.4	1216.9	1040.0	882.5	767.9	686.8	641.3
52.5°	815.3	971.0	1140.2	1252.9	1224.6	1095.2	926.3	786.6	692.4	628.9	587.6
55°	721.0	865.1	1025.9	1116.4	1064.1	920.7	778.0	665.4	595.7	548.2	515.9
57.5°	627.4	762.5	900.2	955.9	898.2	765.8	646.8	565.1	512.7	477.5	456.6
60°	569.6	687.5	810.1	858.4	789.4	671.5	577.6	504.6	462.3	433.5	414.8
62.5°	511.7	617.3	733.0	759.2	696.1	596.4	513.3	452.6	417.9	392.2	374.6
65°	432.9	519.3	607.1	624.5	566.2	489.2	423.5	384.0	353.1	334.4	320.3
67.5°	355.0	424.4	486.7	500.7	449.6	396.2	348.7	314.3	293.4	277.8	265.9
70°	308.9	363.9	414.8	426.2	385.3	337.7	301.5	274.1	255.3	241.9	230.6
72.5°	260.1	306.0	348.3	356.0	322.6	286.3	256.5	234.9	218.3	209.7	198.8
75°	199.0	225.8	258.6	260.6	238.5	216.4	193.7	179.6	170.9	160.2	154.8
77.5°	140.5	161.5	180.3	183.9	170.8	155.7	143.0	131.9	124.5	119.6	114.6
80°	107.2	124.0	132.0	136.7	127.3	116.6	109.3	101.9	97.1	93.8	90.5
82.5°	76.6	86.9	94.5	98.1	93.0	86.5	79.2	75.0	71.4	68.6	67.5
85°	38.9	43.5	48.3	49.6	48.3	45.5	41.5	41.5	39.5	38.9	38.9
87.5°	14.2	17.2	17.6	19.6	19.1	20.1	21.5	22.2	21.9	21.1	20.4
90°	4.0	8.1	10.1	12.1	15.1	20.2	27.2	33.2	34.2	33.2	32.2
92.5°	17.8	25.0	29.4	36.3	45.7	68.6	100.6	129.2	131.0	110.7	87.9
95°	39.3	49.4	58.5	74.6	98.8	145.1	232.8	349.7	395.1	345.7	264.1
97.5°	62.9	73.6	87.3	105.8	133.2	191.5	313.7	508.0	674.5	707.5	616.2
100°	80.6	89.7	105.8	126.0	154.2	207.6	330.6	548.3	796.2	941.4	920.2
102.5°	98.4	107.4	123.6	144.5	172.8	222.2	331.4	533.0	800.2	1028.4	1119.3
105°	127.0	134.0	149.2	171.4	199.5	246.9	336.6	502.9	746.8	1014.9	1224.6
107.5°	155.2	162.1	176.0	197.9	226.4	272.4	350.5	488.0	689.6	926.5	1148.8
110°	175.4	181.4	194.5	215.7	244.9	289.2	361.8	484.8	662.2	870.8	1083.5





TEST NUMBER: P331404-840

CATALOG NUMBER: SA2XXDIP-C865D925U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	193.1	200.0	212.3	232.6	262.7	305.4	374.0	485.5	644.4	832.1	1023.8
115°	221.8	227.8	239.8	260.0	287.2	330.6	392.0	489.8	624.9	784.2	950.4
117.5°	249.3	255.4	266.1	285.4	313.7	353.8	411.4	497.1	615.4	753.9	895.1
120°	267.1	273.2	282.2	302.4	330.6	369.9	424.3	501.9	609.8	737.8	867.8
122.5°	283.2	289.2	299.1	319.3	348.3	385.2	435.6	507.6	606.5	724.1	846.0
125°	305.4	311.4	323.6	343.7	371.9	408.2	453.5	516.0	600.7	704.5	814.4
127.5°	324.2	332.5	345.9	365.3	394.3	429.6	470.3	524.7	597.2	686.4	783.2
130°	334.6	344.7	358.8	379.0	407.2	442.4	480.8	531.2	595.6	674.3	763.0
132.5°	345.1	356.0	370.9	391.8	420.1	453.7	491.2	537.6	594.8	664.6	743.6
135°	358.8	370.9	386.0	409.2	437.4	469.7	504.9	545.2	593.6	651.1	716.6
137.5°	373.3	385.4	401.5	424.5	450.7	482.6	515.4	552.1	593.4	641.6	695.0
140°	383.0	395.1	411.2	433.4	459.6	489.8	521.1	555.3	592.6	636.0	681.4
142.5°	392.6	403.9	420.1	441.4	466.1	495.4	525.9	557.7	592.6	630.4	670.0
145°	409.2	419.3	434.4	454.5	476.8	503.9	532.2	560.4	590.6	622.9	654.1
147.5°	425.2	434.7	448.7	465.4	485.2	510.8	535.6	561.2	587.0	615.2	641.8
150°	436.4	444.4	457.6	472.7	490.8	514.0	537.1	560.4	584.6	608.7	633.0
152.5°	446.1	454.1	465.6	480.0	496.4	517.3	538.0	558.8	580.6	603.1	624.1
155°	461.6	467.7	478.8	489.8	504.9	522.1	539.2	556.3	573.5	592.6	611.8
157.5°	474.9	479.8	489.4	498.3	511.0	525.5	539.2	551.7	566.2	582.8	597.4
160°	483.8	487.8	495.8	503.9	515.0	527.1	539.2	549.3	561.4	575.5	588.5
162.5°	491.0	495.0	501.5	508.8	517.5	528.0	538.4	546.8	557.3	569.1	579.8
165°	500.9	502.9	509.0	514.0	520.1	529.2	536.2	542.2	549.3	558.4	566.4
167.5°	509.2	511.0	514.8	518.5	522.3	529.0	534.8	537.6	542.2	547.9	553.7
170°	514.0	515.0	518.1	520.1	523.1	528.2	533.2	535.2	538.2	542.2	547.2
172.5°	518.1	517.5	520.5	521.7	523.9	527.4	530.8	532.0	533.4	536.6	540.0
175°	522.1	521.1	523.1	523.1	524.1	526.1	528.2	527.1	528.2	529.2	532.2
177.5°	523.3	522.5	524.1	524.1	524.1	524.9	526.5	524.9	524.1	524.9	526.5
180°	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1	524.1



TEST NUMBER: P331404-840

CATALOG NUMBER: SA2XXDIP-C865D925U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5
2.5°	1808.5	1815.9	1815.9	1817.1	1825.6	1824.5	1824.0
5°	1924.5	1935.9	1937.2	1949.3	1957.3	1954.7	1947.3
7.5°	2034.0	2055.2	2071.2	2080.2	2090.8	2097.4	2094.5
10°	2120.8	2151.6	2170.4	2183.1	2198.6	2210.0	2205.9
12.5°	2199.7	2236.3	2262.1	2283.9	2285.9	2300.6	2290.7
15°	2322.6	2361.4	2365.4	2381.5	2394.3	2392.9	2393.6
17.5°	2363.2	2375.6	2378.1	2378.5	2378.7	2374.0	2363.8
20°	2348.6	2344.0	2332.6	2323.9	2308.5	2306.4	2293.1
22.5°	2280.1	2265.2	2236.6	2217.8	2193.7	2187.5	2183.7
25°	2145.0	2112.1	2066.6	2023.0	2010.9	1987.5	1994.2
27.5°	1959.6	1908.4	1859.1	1823.7	1791.7	1756.6	1766.7
30°	1829.4	1771.7	1702.0	1648.4	1614.3	1580.7	1574.7
32.5°	1673.9	1589.4	1511.8	1464.5	1412.2	1391.0	1367.8
35°	1405.8	1323.4	1246.4	1180.0	1141.9	1112.4	1085.5
37.5°	1164.8	1069.9	1007.6	953.9	926.3	909.5	913.7
40°	1015.2	932.1	886.6	845.7	820.2	808.1	810.8
42.5°	894.0	831.8	794.4	766.3	748.3	741.6	740.0
45°	756.5	721.6	690.8	674.8	666.1	658.7	654.0
47.5°	662.7	634.3	616.9	607.3	599.8	592.2	592.1
50°	606.4	587.6	575.6	565.5	559.6	554.2	558.9
52.5°	563.5	546.4	534.3	525.3	523.1	518.3	518.2
55°	499.9	486.5	477.8	469.7	465.7	463.0	459.7
57.5°	442.0	429.3	421.2	416.2	408.5	405.8	404.8
60°	400.7	390.6	382.6	375.9	372.5	367.2	367.2
62.5°	362.6	352.6	345.1	340.0	334.5	332.3	333.0
65°	307.6	299.5	292.2	286.8	285.5	281.4	282.8
67.5°	256.9	251.6	243.8	240.9	238.3	236.1	234.5
70°	223.2	217.8	213.8	209.7	207.7	207.7	207.7
72.5°	194.7	188.3	185.9	180.8	182.0	179.9	177.7
75°	150.8	146.7	144.7	142.7	139.4	139.4	139.4
77.5°	111.0	109.8	107.3	105.2	104.4	103.7	104.0
80°	85.7	85.1	83.7	83.7	82.4	81.8	80.4
82.5°	65.9	64.2	63.4	62.8	62.6	62.4	62.2
85°	37.6	36.2	36.2	36.9	35.5	35.5	36.2
87.5°	20.5	20.9	20.6	20.6	21.1	20.6	20.6
90°	30.2	32.2	33.2	33.2	33.2	33.2	33.2
92.5°	75.4	67.0	60.7	59.9	56.7	57.5	55.8
95°	202.6	160.3	138.0	125.0	116.9	113.9	114.9
97.5°	504.1	395.1	322.3	274.2	249.3	234.6	226.2
100°	795.2	657.1	535.2	451.5	408.2	379.0	360.8
102.5°	1091.2	990.2	860.9	770.0	696.0	659.5	635.0
105°	1338.5	1351.6	1318.3	1255.8	1193.4	1149.9	1135.9
107.5°	1320.3	1425.1	1473.9	1481.8	1478.3	1469.7	1451.0
110°	1263.8	1392.9	1475.5	1518.8	1538.0	1547.1	1546.1



TEST NUMBER: P331404-840

CATALOG NUMBER: SA2XXDIP-C865D925U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	1197.0	1334.8	1429.6	1489.9	1521.9	1539.0	1544.5
115°	1105.6	1237.7	1341.5	1413.0	1459.4	1485.6	1494.7
117.5°	1031.5	1151.1	1248.6	1321.5	1370.5	1398.2	1405.7
120°	992.8	1099.5	1191.3	1261.8	1309.2	1338.5	1348.6
122.5°	960.5	1061.7	1144.6	1207.8	1254.4	1280.4	1288.9
125°	918.2	1006.8	1082.5	1140.9	1179.2	1204.4	1212.4
127.5°	877.1	960.7	1030.5	1081.5	1117.3	1139.1	1145.6
130°	849.6	929.3	995.8	1045.2	1079.4	1099.5	1107.6
132.5°	823.8	897.0	959.5	1008.0	1042.4	1060.9	1068.1
135°	783.2	849.6	906.1	949.4	982.7	1000.8	1004.8
137.5°	750.6	803.4	852.6	892.2	920.8	936.8	942.8
140°	729.7	776.1	820.4	852.6	878.9	894.0	900.0
142.5°	711.1	751.0	788.2	818.8	842.6	856.1	857.3
145°	687.4	718.6	747.8	772.0	789.2	799.2	802.2
147.5°	668.0	692.4	713.8	733.8	747.4	754.3	756.1
150°	655.1	676.3	694.4	709.5	721.6	727.7	728.7
152.5°	644.6	662.6	678.3	690.1	700.6	705.1	705.3
155°	627.9	643.0	654.1	665.2	672.3	676.3	674.3
157.5°	611.0	623.7	632.4	640.2	646.0	647.8	647.8
160°	599.7	610.8	617.8	624.9	630.0	631.0	631.0
162.5°	589.2	598.6	604.1	611.2	614.6	615.6	614.8
165°	573.5	580.6	584.6	588.5	592.6	592.6	591.6
167.5°	559.2	564.0	567.6	569.5	571.7	571.5	570.3
170°	550.3	554.3	556.3	557.3	560.4	559.4	557.3
172.5°	542.2	545.4	546.6	547.6	549.1	548.1	546.8
175°	533.2	534.2	535.2	535.2	536.2	535.2	533.2
177.5°	526.5	527.4	527.4	527.4	527.4	526.5	524.9
180°	524.1	524.1	524.1	524.1	524.1	524.1	524.1

(END OF REPORT)