

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331265

Luminaire Tested: **SA2XXDIP-C290D725U835-4F0-1E-UDD-F1**

Issue Date: 10/7/2019


Test Information

Test Method: LM-79-08
Report Number: P331265
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C290D725U835-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 725 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3795.6 lumens
Efficiency: N/A
Efficacy: 121.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331265
CATALOG NUMBER: SA2XXDIP-C290D725U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331265

CATALOG NUMBER: SA2XXDIP-C290D725U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	92	92	92	92	73	73	73	56	56	56	39	39	39	32
1	94	89	86	82	84	81	77	75	64	62	60	49	47	46	35	34	33	27
2	85	78	72	67	76	70	65	61	56	53	50	43	40	38	31	29	28	22
3	78	69	61	56	70	62	56	51	49	45	42	38	35	32	27	25	24	19
4	71	61	53	47	64	55	48	43	44	39	35	34	30	28	24	22	20	16
5	65	54	46	40	58	49	42	37	39	34	30	30	27	24	22	20	18	14
6	60	48	40	35	54	44	37	32	35	30	26	27	24	21	20	17	16	12
7	55	43	36	30	50	39	33	28	32	27	23	25	21	18	18	16	14	11
8	51	39	32	27	46	36	29	25	29	24	20	23	19	16	16	14	12	10
9	48	36	28	24	43	33	26	22	26	22	18	21	17	15	15	13	11	9
10	44	33	26	21	40	30	24	19	24	20	16	19	16	13	14	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7627	7627	7627
5°	7656	7546	7592
10°	7612	7470	7507
15°	7517	7373	7366
20°	7383	7228	7220
25°	7251	7049	7049
30°	7081	6885	6825
35°	6922	6688	6589
40°	6721	6492	6367
45°	6524	6295	6140
50°	6310	6094	5878
55°	6086	5858	5638
60°	5838	5574	5370
65°	5570	5295	5051
70°	5231	4952	4716
75°	4760	4560	4448
80°	4221	4100	3887
85°	3446	3279	2946



TEST NUMBER: P331265

CATALOG NUMBER: SA2XXDIP-C290D725U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.4	1.2
10°-20°	125.0	3.3
20°-30°	183.7	4.8
30°-40°	213.4	5.6
40°-50°	213.2	5.6
50°-60°	185.9	4.9
60°-70°	137.5	3.6
70°-80°	77.9	2.1
80°-90°	24.6	0.6
90°-100°	58.7	1.5
100°-110°	182.3	4.8
110°-120°	311.6	8.2
120°-130°	409.8	10.8
130°-140°	459.9	12.1
140°-150°	450.9	11.9
150°-160°	378.2	10.0
160°-170°	250.9	6.6
170°-180°	87.7	2.3
0°-30°	353.2	9.3
0°-40°	566.6	14.9
0°-60°	965.7	25.4
0°-90°	1205.6	31.8
90°-120°	552.6	14.6
90°-150°	1873.2	49.4
90°-180°	2590.0	68.2
0°-180°	3795.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	472	472	472	472	472	
5°	472	470	466	469	468	45
15°	450	447	441	443	441	127
25°	407	403	396	396	396	187
35°	351	346	339	337	334	219
45°	286	282	276	271	269	220
55°	216	213	208	203	200	193
65°	146	143	139	135	132	144
75°	76	75	73	71	71	82
85°	19	18	18	16	16	21
90°	1	11	27	26	27	3
95°	41	48	50	50	48	47
105°	168	170	172	173	174	177
115°	313	317	316	315	313	309
125°	455	461	460	457	456	406
135°	589	597	599	598	596	454
145°	714	720	725	725	722	446
155°	817	819	822	825	823	376
165°	889	888	888	893	890	251
175°	925	922	921	926	922	88
180°	926	926	926	926	926	



TEST NUMBER: P331265

CATALOG NUMBER: SA2XXDIP-C290D725U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	472.4	472.4	472.4	472.4	472.4	472.4	472.4	472.4	472.4	472.4	472.4
2.5°	474.6	474.2	473.8	473.4	473.0	472.4	471.5	470.6	469.7	468.8	469.6
5°	472.4	472.0	471.6	471.2	470.8	470.1	469.0	467.9	466.7	465.6	466.4
7.5°	468.3	467.6	467.0	466.4	465.8	464.9	463.8	462.6	461.5	460.4	461.2
10°	464.3	463.6	462.9	462.2	461.4	460.5	459.3	458.1	456.9	455.6	456.4
12.5°	458.8	458.2	457.6	456.9	456.3	455.4	454.2	453.0	451.8	450.6	451.1
15°	449.7	449.1	448.5	447.9	447.3	446.4	445.0	443.7	442.4	441.1	441.5
17.5°	438.1	437.5	436.9	436.3	435.7	434.7	433.4	432.0	430.7	429.4	429.8
20°	429.7	429.1	428.5	427.9	427.3	426.3	424.9	423.5	422.1	420.7	421.0
22.5°	421.4	420.5	419.7	418.8	418.0	416.9	415.6	414.2	412.9	411.6	411.6
25°	407.0	406.2	405.4	404.6	403.8	402.5	400.8	399.1	397.4	395.7	395.9
27.5°	390.7	390.0	389.2	388.5	387.8	386.7	385.4	384.0	382.7	381.3	381.0
30°	379.8	379.0	378.2	377.4	376.5	375.4	373.9	372.4	370.8	369.3	369.0
32.5°	368.1	367.5	366.9	366.2	365.6	364.4	362.8	361.3	359.7	358.1	357.5
35°	351.2	350.1	349.1	348.1	347.1	345.8	344.2	342.6	341.0	339.3	338.7
37.5°	332.0	331.1	330.2	329.3	328.4	327.2	325.6	324.0	322.3	320.7	320.0
40°	318.9	318.1	317.3	316.5	315.7	314.5	312.8	311.2	309.6	308.0	307.1
42.5°	306.2	305.4	304.6	303.8	303.0	301.7	300.1	298.5	296.9	295.3	294.3
45°	285.7	285.0	284.3	283.6	282.9	281.8	280.3	278.8	277.3	275.7	274.6
47.5°	265.4	264.7	264.1	263.4	262.7	261.6	260.0	258.5	256.9	255.3	254.1
50°	251.2	250.7	250.2	249.7	249.2	248.2	246.8	245.4	244.0	242.6	241.2
52.5°	237.4	236.7	236.1	235.4	234.7	233.7	232.4	231.1	229.7	228.4	227.2
55°	216.2	215.6	215.0	214.4	213.8	212.9	211.7	210.5	209.3	208.1	206.8
57.5°	195.0	194.5	194.0	193.5	193.0	192.1	190.8	189.5	188.1	186.8	185.6
60°	180.8	180.4	180.0	179.6	179.2	178.3	176.9	175.5	174.0	172.6	171.5
62.5°	167.0	166.3	165.7	165.1	164.4	163.5	162.4	161.4	160.3	159.2	158.1
65°	145.8	145.2	144.6	144.0	143.4	142.6	141.6	140.6	139.6	138.6	137.6
67.5°	124.3	123.8	123.3	122.8	122.4	121.7	120.7	119.8	118.9	118.0	117.3
70°	110.8	110.4	110.0	109.6	109.2	108.6	107.7	106.8	105.8	104.9	104.2
72.5°	97.0	96.6	96.2	95.8	95.4	94.9	94.3	93.8	93.2	92.6	91.9
75°	76.3	76.1	75.9	75.7	75.5	75.2	74.7	74.1	73.6	73.1	72.5
77.5°	57.8	57.4	57.1	56.8	56.4	56.1	55.9	55.7	55.5	55.3	55.0
80°	45.4	45.3	45.2	45.1	45.0	44.9	44.7	44.5	44.3	44.1	43.8
82.5°	33.8	33.8	33.8	33.7	33.7	33.6	33.5	33.4	33.3	33.2	32.8
85°	18.6	18.5	18.4	18.3	18.2	18.1	18.0	17.9	17.8	17.7	17.4
87.5°	6.7	7.0	7.2	7.5	7.7	8.1	8.8	9.4	10.0	10.6	10.2
90°	0.8	2.9	5.0	7.0	9.1	12.1	15.9	19.7	23.5	27.4	27.0
92.5°	13.9	15.4	17.0	18.5	20.0	21.2	22.1	23.0	24.0	24.9	24.9
95°	40.6	42.4	44.1	45.9	47.6	48.6	49.0	49.3	49.7	50.0	50.0
97.5°	74.3	75.8	77.3	78.8	80.4	81.5	82.1	82.8	83.4	84.1	84.1
100°	99.3	100.7	102.0	103.4	104.8	105.8	106.3	106.8	107.3	107.9	107.9
102.5°	125.5	126.6	127.8	128.9	130.0	130.9	131.5	132.2	132.8	133.5	133.6
105°	168.1	168.6	169.1	169.6	170.1	170.6	170.9	171.3	171.6	172.0	172.3
107.5°	210.9	211.7	212.4	213.2	213.9	214.3	214.3	214.3	214.3	214.3	214.5
110°	238.4	239.4	240.5	241.5	242.6	243.1	243.1	243.1	243.1	243.1	243.1



TEST NUMBER: P331265

CATALOG NUMBER: SA2XXDIP-C290D725U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	268.4	269.5	270.5	271.5	272.6	273.0	272.9	272.8	272.6	272.5	272.1
115°	312.7	313.7	314.7	315.8	316.8	317.2	316.8	316.5	316.1	315.8	315.6
117.5°	356.7	358.1	359.5	360.9	362.3	362.5	361.5	360.6	359.6	358.6	358.2
120°	386.1	387.5	388.9	390.3	391.7	391.7	390.3	388.9	387.5	386.1	386.1
122.5°	413.0	414.7	416.4	418.0	419.7	420.0	419.1	418.1	417.1	416.1	415.7
125°	454.9	456.5	458.0	459.6	461.2	461.7	461.2	460.6	460.1	459.6	459.1
127.5°	495.7	497.7	499.7	501.7	503.6	504.3	503.7	503.1	502.4	501.8	501.2
130°	521.4	523.6	525.9	528.1	530.4	531.3	531.0	530.6	530.3	530.0	529.6
132.5°	550.1	552.0	553.8	555.6	557.5	558.4	558.5	558.6	558.6	558.7	558.0
135°	588.6	590.5	592.4	594.3	596.2	597.3	597.7	598.0	598.4	598.7	598.6
137.5°	629.1	630.6	632.2	633.8	635.3	636.3	636.8	637.2	637.7	638.1	638.0
140°	653.5	655.0	656.6	658.1	659.7	660.9	661.8	662.7	663.5	664.4	664.4
142.5°	678.5	680.0	681.6	683.2	684.7	685.8	686.4	687.0	687.6	688.2	688.3
145°	714.4	715.6	716.9	718.1	719.3	720.4	721.5	722.5	723.5	724.6	724.8
147.5°	746.5	747.9	749.4	750.8	752.3	753.4	754.1	754.8	755.5	756.2	756.5
150°	768.4	769.4	770.4	771.5	772.5	773.4	774.1	774.8	775.5	776.2	776.7
152.5°	787.7	788.8	789.8	790.9	791.9	792.8	793.7	794.5	795.3	796.2	796.8
155°	816.8	817.3	817.9	818.4	818.9	819.4	819.9	820.5	821.0	821.5	822.4
157.5°	841.7	842.0	842.4	842.7	843.1	843.4	843.7	844.0	844.3	844.6	845.8
160°	856.7	857.0	857.4	857.7	858.1	858.3	858.5	858.7	858.9	859.0	860.1
162.5°	870.4	870.5	870.6	870.6	870.7	870.8	871.0	871.2	871.4	871.5	872.7
165°	888.7	888.6	888.4	888.2	888.0	887.9	887.9	887.9	887.9	887.9	889.2
167.5°	904.0	903.5	903.0	902.5	902.0	901.7	901.7	901.6	901.6	901.5	902.8
170°	912.2	911.7	911.1	910.6	910.1	909.7	909.6	909.4	909.2	909.0	910.3
172.5°	917.8	917.3	916.8	916.2	915.7	915.4	915.2	915.0	914.9	914.7	915.9
175°	924.7	924.2	923.6	923.1	922.6	922.2	921.8	921.5	921.1	920.8	922.0
177.5°	927.5	927.1	926.7	926.2	925.8	925.5	925.2	924.9	924.6	924.4	925.2
180°	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2



TEST NUMBER: P331265

CATALOG NUMBER: SA2XXDIP-C290D725U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	472.4	472.4	472.4	472.4	472.4	472.4	472.4	472.4
2.5°	470.4	471.2	472.0	472.4	472.2	472.0	471.9	471.7
5°	467.3	468.1	468.9	469.2	469.0	468.8	468.6	468.4
7.5°	462.0	462.8	463.6	463.9	463.7	463.4	463.2	463.0
10°	457.3	458.1	458.9	459.1	458.8	458.5	458.2	457.9
12.5°	451.7	452.2	452.8	453.0	452.8	452.5	452.3	452.1
15°	441.9	442.3	442.7	442.7	442.2	441.7	441.2	440.7
17.5°	430.3	430.8	431.2	431.2	430.7	430.3	429.8	429.3
20°	421.3	421.6	421.9	421.8	421.4	421.0	420.6	420.2
22.5°	411.7	411.8	411.8	411.7	411.5	411.2	411.0	410.8
25°	396.1	396.3	396.5	396.5	396.3	396.1	395.9	395.7
27.5°	380.7	380.4	380.1	379.7	379.2	378.7	378.3	377.8
30°	368.7	368.4	368.1	367.8	367.4	367.0	366.6	366.1
32.5°	357.0	356.4	355.9	355.4	355.0	354.6	354.2	353.8
35°	338.1	337.5	336.9	336.4	335.9	335.4	334.9	334.3
37.5°	319.2	318.5	317.7	317.1	316.6	316.1	315.7	315.2
40°	306.2	305.3	304.4	303.7	303.3	302.9	302.5	302.1
42.5°	293.3	292.3	291.3	290.5	290.0	289.4	288.9	288.3
45°	273.5	272.4	271.3	270.5	270.1	269.7	269.3	268.9
47.5°	253.0	251.8	250.6	249.7	249.2	248.6	248.0	247.4
50°	239.8	238.3	236.9	236.0	235.5	235.0	234.5	234.0
52.5°	226.1	224.9	223.7	222.8	222.1	221.5	220.8	220.1
55°	205.6	204.4	203.2	202.4	201.9	201.3	200.8	200.3
57.5°	184.4	183.2	182.0	181.2	180.9	180.5	180.1	179.7
60°	170.4	169.3	168.2	167.5	167.2	166.9	166.6	166.3
62.5°	157.1	156.1	155.1	154.4	154.0	153.6	153.2	152.8
65°	136.7	135.8	134.9	134.2	133.7	133.2	132.7	132.2
67.5°	116.6	115.9	115.2	114.6	114.2	113.8	113.4	113.0
70°	103.5	102.8	102.1	101.6	101.2	100.7	100.3	99.9
72.5°	91.2	90.5	89.8	89.2	88.9	88.6	88.3	87.9
75°	71.9	71.3	70.7	70.5	70.7	70.9	71.1	71.3
77.5°	54.7	54.4	54.1	53.8	53.5	53.3	53.0	52.7
80°	43.5	43.2	42.9	42.6	42.4	42.2	42.0	41.8
82.5°	32.4	32.0	31.6	31.4	31.4	31.3	31.3	31.3
85°	17.1	16.8	16.5	16.3	16.2	16.1	16.0	15.9
87.5°	9.9	9.6	9.3	9.1	9.1	9.0	9.0	8.9
90°	26.7	26.3	26.0	25.9	26.1	26.2	26.4	26.6
92.5°	25.0	25.1	25.1	25.2	25.2	25.3	25.3	25.3
95°	50.0	50.0	50.0	49.9	49.5	49.2	48.8	48.5
97.5°	84.1	84.1	84.1	84.1	84.1	84.0	84.0	83.9
100°	107.9	107.9	107.9	107.8	107.6	107.4	107.3	107.1
102.5°	133.8	133.9	134.1	134.0	133.9	133.7	133.5	133.3
105°	172.7	173.0	173.4	173.5	173.5	173.5	173.5	173.5
107.5°	214.6	214.7	214.9	214.6	213.8	213.0	212.2	211.4
110°	243.1	243.1	243.1	242.8	242.3	241.8	241.3	240.7



TEST NUMBER: P331265

CATALOG NUMBER: SA2XXDIP-C290D725U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	271.6	271.2	270.8	270.4	270.0	269.6	269.3	268.9
115°	315.4	315.3	315.1	314.7	314.2	313.7	313.2	312.7
117.5°	357.8	357.4	356.9	356.5	356.0	355.4	354.9	354.4
120°	386.1	386.1	386.1	385.9	385.3	384.8	384.3	383.8
122.5°	415.3	414.9	414.5	414.1	413.7	413.3	412.9	412.6
125°	458.6	458.0	457.5	457.2	457.0	456.8	456.7	456.5
127.5°	500.6	499.9	499.3	498.7	498.2	497.6	497.1	496.5
130°	529.3	528.9	528.6	528.0	527.3	526.7	526.0	525.3
132.5°	557.2	556.4	555.7	555.0	554.4	553.9	553.3	552.8
135°	598.4	598.2	598.0	597.7	597.2	596.7	596.1	595.6
137.5°	637.9	637.7	637.6	637.2	636.5	635.8	635.1	634.4
140°	664.4	664.4	664.4	664.0	663.4	662.7	662.0	661.3
142.5°	688.4	688.6	688.7	688.4	687.7	687.0	686.4	685.7
145°	724.9	725.1	725.3	725.0	724.3	723.6	722.9	722.2
147.5°	756.9	757.3	757.7	757.6	756.9	756.2	755.6	754.9
150°	777.2	777.7	778.3	778.3	777.7	777.2	776.7	776.2
152.5°	797.5	798.2	798.8	798.8	798.2	797.5	796.8	796.2
155°	823.2	824.1	825.0	825.2	824.6	824.1	823.6	823.1
157.5°	847.0	848.2	849.4	849.5	848.7	847.9	847.0	846.2
160°	861.1	862.2	863.2	863.4	862.7	862.0	861.3	860.6
162.5°	873.9	875.1	876.3	876.4	875.6	874.8	873.9	873.1
165°	890.4	891.6	892.8	893.0	892.1	891.2	890.4	889.5
167.5°	904.0	905.2	906.4	906.6	905.7	904.8	903.9	903.0
170°	911.5	912.7	913.9	914.0	913.0	911.9	910.9	909.8
172.5°	917.1	918.3	919.5	919.6	918.6	917.5	916.5	915.5
175°	923.2	924.4	925.6	925.7	924.7	923.6	922.6	921.6
177.5°	926.0	926.9	927.7	927.7	926.9	926.0	925.2	924.4
180°	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2

(END OF REPORT)