

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331267

Luminaire Tested: **SA2XXDIP-C290D925U835-4F0-1E-UDD-A**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331267
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C290D925U835-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 925 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5006.0 lumens
Efficiency: N/A
Efficacy: 134.2 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 37.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331267
CATALOG NUMBER: SA2XXDIP-C290D925U835-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331267

CATALOG NUMBER: SA2XXDIP-C290D925U835-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	91	91	91	91	70	70	70	51	51	51	34	34	34	26
1	93	89	85	82	83	79	76	73	62	60	58	45	44	43	31	30	29	22
2	85	78	72	67	75	69	65	61	54	51	48	40	38	36	27	26	25	19
3	77	68	61	56	69	61	55	51	48	44	41	36	33	31	24	23	22	17
4	71	61	53	47	63	54	48	43	43	38	35	32	29	27	22	20	19	14
5	65	54	46	41	58	48	42	37	38	34	30	29	26	23	20	18	16	13
6	60	48	41	35	53	43	37	32	34	30	26	26	23	20	18	16	15	11
7	55	44	36	31	49	39	33	28	31	26	23	24	20	18	16	15	13	10
8	51	39	32	27	46	36	29	25	28	24	20	22	18	16	15	13	12	9
9	47	36	29	24	42	32	26	22	26	21	18	20	17	14	14	12	11	8
10	44	33	26	21	40	30	24	20	24	19	16	18	15	13	13	11	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9544	9544	9544	9544
5°	10699	9606	8512	9606
10°	12260	9527	7366	9527
15°	13563	9352	6509	9352
20°	13357	9165	5933	9165
25°	12043	8915	5569	8915
30°	9952	8516	5302	8516
35°	7253	8099	5113	8099
40°	5794	7609	5008	7609
45°	5062	7040	4866	7040
50°	4760	6488	4770	6488
55°	4386	5928	4642	5928
60°	4020	5331	4447	5331
65°	3664	4798	4252	4798
70°	3323	4277	3970	4277
75°	2951	3699	3512	3699
80°	2538	3059	2827	3059
85°	2279	2279	1686	2279



TEST NUMBER: P331267

CATALOG NUMBER: SA2XXDIP-C290D925U835-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.3	1.1
10°-20°	163.7	3.3
20°-30°	237.5	4.7
30°-40°	250.6	5.0
40°-50°	221.9	4.4
50°-60°	177.1	3.5
60°-70°	120.4	2.4
70°-80°	61.7	1.2
80°-90°	18.0	0.4
90°-100°	42.1	0.8
100°-110°	154.4	3.1
110°-120°	412.7	8.2
120°-130°	681.3	13.6
130°-140°	724.5	14.5
140°-150°	673.4	13.5
150°-160°	541.4	10.8
160°-170°	348.9	7.0
170°-180°	120.1	2.4
0°-30°	457.5	9.1
0°-40°	708.1	14.1
0°-60°	1107.1	22.1
0°-90°	1307.2	26.1
90°-120°	609.2	12.2
90°-150°	2688.4	53.7
90°-180°	3699.0	73.9
0°-180°	5006.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	591	591	591	591	591	
5°	660	593	525	593	660	66
15°	811	560	389	560	811	224
25°	676	500	313	500	676	306
35°	368	411	259	411	368	239
45°	222	308	213	308	222	174
55°	156	211	165	211	156	140
65°	96	126	111	126	96	95
75°	47	59	56	59	47	51
85°	12	12	9	12	12	14
90°	25	1	25	1	25	11
95°	39	59	39	59	39	37
105°	69	278	69	278	69	72
115°	75	525	75	525	75	188
125°	781	742	781	742	781	676
135°	949	919	949	919	949	731
145°	1082	1066	1082	1066	1082	677
155°	1174	1174	1174	1174	1174	542
165°	1234	1237	1234	1237	1234	348
175°	1258	1265	1258	1265	1258	120
180°	1262	1262	1262	1262	1262	



TEST NUMBER: P331267

CATALOG NUMBER: SA2XXDIP-C290D925U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1
2.5°	618.3	618.5	618.9	616.0	615.6	615.6	613.1	610.9	608.3	604.9	605.3
5°	660.1	662.6	663.5	660.8	656.7	656.3	652.4	646.1	640.1	635.4	632.0
7.5°	710.0	711.0	708.8	705.2	702.2	696.7	689.5	682.5	672.6	663.6	656.9
10°	747.8	749.2	745.3	740.1	735.8	729.4	719.0	708.3	695.4	682.9	672.9
12.5°	776.5	779.9	774.9	774.3	766.9	758.1	745.7	740.3	722.1	704.7	693.9
15°	811.4	811.2	811.7	807.3	801.9	800.5	787.4	773.0	747.4	737.1	719.4
17.5°	801.3	804.8	806.4	806.3	806.2	805.3	801.1	792.1	779.2	762.6	742.2
20°	777.4	781.9	782.6	787.8	790.8	794.6	796.2	793.7	785.8	771.9	754.2
22.5°	740.3	741.6	743.7	751.8	758.2	767.9	772.9	781.4	778.3	771.5	756.7
25°	676.0	673.8	681.7	685.8	700.6	716.0	727.2	739.4	750.3	756.9	752.6
27.5°	598.9	595.5	607.4	618.3	630.2	647.0	664.3	684.8	701.8	723.2	730.5
30°	533.8	535.9	547.2	558.8	577.0	600.6	620.2	642.6	667.0	690.8	707.4
32.5°	463.7	471.5	478.7	496.5	512.5	538.8	567.5	595.6	625.9	653.0	678.7
35°	368.0	377.1	387.1	400.0	422.5	448.6	476.6	514.5	555.9	592.9	623.3
37.5°	309.8	308.3	314.0	323.4	341.6	362.7	394.9	432.3	481.0	524.5	567.5
40°	274.9	274.0	278.0	286.7	300.5	316.0	344.2	377.1	422.3	475.5	526.6
42.5°	250.9	251.4	253.7	259.8	269.3	282.0	303.1	331.1	372.5	422.6	477.5
45°	221.7	223.3	225.8	228.8	234.2	244.7	256.5	276.5	309.2	351.0	405.0
47.5°	200.7	200.8	203.3	205.9	209.1	215.0	224.7	237.2	260.3	294.3	340.8
50°	189.5	187.9	189.7	191.7	195.1	199.2	205.6	217.4	232.8	260.3	299.2
52.5°	175.6	175.7	177.3	178.1	181.1	185.2	191.0	199.2	213.2	234.7	266.6
55°	155.8	157.0	157.9	159.2	162.0	164.9	169.5	174.9	185.8	201.9	225.6
57.5°	137.2	137.6	138.5	141.1	142.8	145.5	149.8	154.8	161.9	173.8	191.6
60°	124.5	124.5	126.3	127.4	129.7	132.4	135.8	140.6	147.0	156.7	171.1
62.5°	112.9	112.7	113.4	115.3	117.0	119.5	122.9	127.0	133.0	141.7	153.4
65°	95.9	95.4	96.8	97.2	99.0	101.5	104.3	108.6	113.4	119.7	130.2
67.5°	79.5	80.1	80.8	81.6	82.6	85.3	87.1	90.1	94.2	99.5	106.5
70°	70.4	70.4	70.4	71.1	72.5	73.8	75.6	78.1	82.0	86.5	92.9
72.5°	60.2	61.0	61.7	61.3	63.0	63.8	66.0	67.4	71.1	74.0	79.6
75°	47.3	47.3	47.3	48.4	49.1	49.7	51.1	52.5	54.3	57.9	60.9
77.5°	35.3	35.2	35.4	35.7	36.4	37.2	37.6	38.8	40.5	42.2	44.7
80°	27.3	27.7	27.9	28.4	28.4	28.8	29.1	30.7	31.8	32.9	34.5
82.5°	21.1	21.2	21.2	21.3	21.5	21.8	22.4	22.9	23.3	24.2	25.4
85°	12.3	12.0	12.0	12.5	12.3	12.3	12.7	13.2	13.2	13.4	14.1
87.5°	9.7	9.6	9.7	9.4	9.3	9.4	9.2	8.8	8.8	8.7	8.6
90°	24.7	24.3	23.8	23.4	23.0	22.3	21.3	20.3	19.3	18.3	16.6
92.5°	24.7	24.4	24.2	23.9	23.7	23.3	22.8	22.2	21.7	21.2	20.4
95°	39.3	39.5	39.7	39.9	40.1	39.7	38.7	37.6	36.6	35.6	34.2
97.5°	52.4	52.2	51.9	51.7	51.4	50.9	50.1	49.3	48.5	47.7	44.4
100°	61.2	60.8	60.4	60.0	59.6	58.6	56.9	55.3	53.7	52.1	48.6
102.5°	65.6	65.0	64.4	63.9	63.3	62.0	59.9	57.7	55.6	53.5	48.2
105°	69.4	68.6	67.8	67.0	66.2	64.6	62.4	60.2	57.9	55.7	48.1
107.5°	71.4	70.6	69.8	69.0	68.2	68.9	71.2	73.4	75.7	78.0	144.4
110°	72.2	71.3	70.5	69.7	68.9	78.6	98.9	119.2	139.5	159.8	218.5



TEST NUMBER: P331267

CATALOG NUMBER: SA2XXDIP-C290D925U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	72.9	72.2	71.6	70.9	70.3	107.0	181.0	255.1	329.1	403.1	417.6
115°	74.9	89.5	104.1	118.7	133.3	187.6	281.6	375.6	469.5	563.5	558.4
117.5°	305.8	353.8	401.8	449.8	497.8	533.2	556.0	578.7	601.4	624.1	620.7
120°	557.1	584.5	611.9	639.3	666.7	679.2	676.8	674.3	671.9	669.4	665.8
122.5°	695.2	700.5	705.8	711.2	716.5	718.4	716.9	715.5	714.0	712.6	708.6
125°	780.9	780.3	779.6	779.0	778.4	777.4	776.0	774.6	773.2	771.7	767.9
127.5°	834.9	834.8	834.7	834.6	834.4	833.4	831.3	829.2	827.1	825.1	822.2
130°	868.5	868.7	868.9	869.2	869.4	868.3	866.1	863.9	861.6	859.4	857.2
132.5°	901.4	901.6	901.8	902.0	902.2	901.4	899.5	897.6	895.7	893.7	891.5
135°	948.9	949.3	949.7	950.1	950.5	949.7	947.7	945.7	943.6	941.6	939.8
137.5°	992.2	992.9	993.6	994.3	995.0	994.3	992.3	990.3	988.3	986.4	984.3
140°	1019.2	1020.3	1021.3	1022.3	1023.3	1022.9	1021.1	1019.2	1017.4	1015.6	1013.4
142.5°	1045.5	1046.6	1047.6	1048.6	1049.6	1049.3	1047.6	1045.9	1044.3	1042.6	1040.1
145°	1082.3	1083.3	1084.3	1085.3	1086.3	1086.1	1084.7	1083.3	1081.8	1080.4	1077.0
147.5°	1114.6	1115.4	1116.3	1117.1	1118.0	1117.9	1116.8	1115.8	1114.7	1113.7	1110.3
150°	1134.3	1135.3	1136.3	1137.4	1138.4	1138.3	1137.1	1135.8	1134.6	1133.4	1130.2
152.5°	1151.1	1152.5	1153.8	1155.1	1156.5	1156.5	1155.3	1154.1	1152.9	1151.7	1148.6
155°	1174.5	1176.1	1177.7	1179.4	1181.0	1181.2	1180.0	1178.8	1177.5	1176.3	1173.9
157.5°	1195.9	1197.4	1199.0	1200.6	1202.2	1202.3	1200.9	1199.5	1198.2	1196.8	1195.1
160°	1208.3	1209.7	1211.1	1212.5	1214.0	1214.1	1212.9	1211.6	1210.4	1209.2	1208.0
162.5°	1218.5	1220.3	1222.0	1223.8	1225.5	1225.7	1224.3	1222.9	1221.5	1220.2	1219.1
165°	1233.9	1235.3	1236.7	1238.1	1239.5	1239.5	1238.1	1236.7	1235.3	1233.9	1233.3
167.5°	1243.5	1245.4	1247.2	1249.0	1250.8	1251.1	1249.6	1248.2	1246.8	1245.4	1244.8
170°	1249.4	1251.2	1253.0	1254.9	1256.7	1256.9	1255.5	1254.1	1252.6	1251.2	1250.8
172.5°	1253.8	1255.6	1257.4	1259.2	1261.1	1261.3	1259.9	1258.4	1257.0	1255.6	1255.2
175°	1257.6	1259.6	1261.7	1263.7	1265.7	1266.0	1264.6	1263.2	1261.8	1260.3	1259.9
177.5°	1260.0	1261.4	1262.9	1264.4	1265.8	1266.0	1264.9	1263.7	1262.6	1261.4	1261.3
180°	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2



TEST NUMBER: P331267

CATALOG NUMBER: SA2XXDIP-C290D925U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1
2.5°	606.5	605.1	604.2	600.9	598.0	595.1	594.2	594.5	590.5	586.7	585.1
5°	630.2	625.6	621.3	615.2	607.9	599.9	595.9	592.7	584.7	576.1	571.1
7.5°	651.3	644.8	636.5	625.0	614.4	601.9	593.9	586.9	575.3	563.1	555.6
10°	664.2	655.4	644.7	630.6	617.7	602.4	591.8	581.1	567.5	552.9	543.8
12.5°	675.3	663.4	652.9	634.8	619.5	600.4	587.8	572.7	558.4	541.1	532.2
15°	701.7	679.7	659.7	639.2	620.4	593.8	579.7	559.5	540.7	519.3	509.1
17.5°	722.1	697.3	665.9	639.9	617.9	588.4	567.8	543.6	521.3	496.9	483.0
20°	733.7	705.3	671.5	640.6	614.3	580.6	558.1	533.4	507.3	479.8	464.8
22.5°	740.6	710.8	677.3	637.9	607.0	574.3	546.0	518.8	492.4	462.7	447.0
25°	742.8	715.6	680.1	635.6	597.9	560.9	526.8	500.4	468.4	440.7	417.8
27.5°	732.0	712.5	678.4	631.3	587.4	544.1	506.1	476.3	442.5	412.4	389.3
30°	718.7	707.4	674.2	627.0	579.0	532.5	490.7	456.8	423.2	392.8	369.1
32.5°	698.2	695.8	666.6	620.8	570.1	517.8	474.5	440.3	403.0	373.1	350.6
35°	657.9	668.8	650.4	607.0	553.4	496.8	450.0	410.9	372.3	343.7	322.6
37.5°	603.8	630.9	626.1	586.8	530.7	474.0	422.3	381.5	344.7	315.8	295.1
40°	566.5	601.1	606.1	571.3	514.8	456.4	401.6	361.0	325.1	298.7	277.8
42.5°	526.6	566.9	580.6	552.8	497.3	437.8	383.1	341.0	305.4	279.8	261.3
45°	459.6	512.9	537.7	521.8	468.2	407.3	351.0	308.3	276.0	251.9	237.6
47.5°	396.9	455.2	488.5	482.9	435.8	375.5	319.8	278.8	247.4	228.2	215.4
50°	352.6	412.5	452.7	454.6	412.5	352.8	296.9	258.3	229.4	211.5	201.0
52.5°	314.0	371.3	415.1	424.8	386.5	329.2	276.4	237.9	212.5	196.0	186.7
55°	263.7	312.1	360.7	378.5	347.8	293.3	244.4	210.6	186.7	175.4	167.2
57.5°	219.3	259.6	304.5	324.1	305.2	258.5	212.7	183.3	164.0	154.0	147.7
60°	195.8	227.6	267.6	291.0	274.6	233.1	193.1	165.1	149.2	140.4	134.5
62.5°	174.0	202.2	236.0	257.4	248.5	209.3	173.5	148.8	135.1	126.8	122.5
65°	143.6	165.8	192.0	211.7	205.8	176.1	146.7	125.6	114.7	108.1	104.7
67.5°	118.2	134.3	152.4	169.7	165.0	143.9	120.4	103.9	95.8	90.1	88.0
70°	102.2	114.5	130.6	144.5	140.6	123.4	104.7	90.6	83.6	78.8	76.8
72.5°	87.0	97.0	109.4	120.7	118.1	103.7	88.2	77.6	72.1	67.7	66.1
75°	65.7	73.4	80.9	88.4	87.7	76.6	67.5	59.3	55.0	51.6	50.9
77.5°	48.5	52.8	57.9	62.3	61.1	54.7	47.6	42.9	39.8	37.5	37.1
80°	37.0	39.5	43.2	46.3	44.8	42.0	36.3	32.9	30.7	28.4	27.5
82.5°	26.9	29.3	31.5	33.3	32.0	29.5	26.0	23.7	22.3	20.8	20.4
85°	14.1	15.4	16.4	16.8	16.4	14.8	13.2	12.3	11.1	10.4	10.2
87.5°	8.5	8.1	7.8	7.8	6.8	6.3	5.2	4.2	4.4	4.7	4.8
90°	15.0	13.4	11.8	9.8	7.6	5.4	3.1	0.9	3.1	5.4	7.6
92.5°	19.6	18.8	17.9	17.6	17.8	18.0	18.2	18.4	18.2	18.0	17.8
95°	32.8	31.4	29.9	32.6	39.3	46.0	52.7	59.4	52.7	46.0	39.3
97.5°	41.1	37.8	34.5	42.3	61.2	80.1	98.9	117.8	98.9	80.1	61.2
100°	45.2	41.7	38.3	50.4	78.2	106.0	133.8	161.7	133.8	106.0	78.2
102.5°	111.2	140.1	169.0	186.3	192.2	198.1	204.0	209.9	204.0	198.1	192.2
105°	166.5	221.9	277.3	302.0	295.9	289.8	283.7	277.6	283.7	289.8	295.9
107.5°	210.9	277.3	343.8	374.6	369.6	364.7	359.8	354.9	359.8	364.7	369.6
110°	277.1	335.8	394.4	421.6	417.4	413.1	408.9	404.6	408.9	413.1	417.4



TEST NUMBER: P331267

CATALOG NUMBER: SA2XXDIP-C290D925U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	432.1	446.6	461.1	466.4	462.7	458.9	455.1	451.3	455.1	458.9	462.7
115°	553.4	548.3	543.2	538.9	535.5	532.0	528.6	525.1	528.6	532.0	535.5
117.5°	617.2	613.7	610.2	606.5	602.7	598.8	594.9	591.1	594.9	598.8	602.7
120°	662.1	658.5	654.8	651.5	648.4	645.4	642.3	639.3	642.3	645.4	648.4
122.5°	704.6	700.6	696.6	693.0	689.8	686.6	683.4	680.2	683.4	686.6	689.8
125°	764.0	760.2	756.3	753.1	750.4	747.8	745.1	742.5	745.1	747.8	750.4
127.5°	819.3	816.4	813.5	810.6	807.7	804.8	801.9	798.9	801.9	804.8	807.7
130°	854.9	852.7	850.5	847.7	844.5	841.2	838.0	834.8	838.0	841.2	844.5
132.5°	889.3	887.1	884.8	882.3	879.6	876.8	874.0	871.3	874.0	876.8	879.6
135°	938.0	936.1	934.3	931.8	928.5	925.3	922.0	918.8	922.0	925.3	928.5
137.5°	982.2	980.1	978.1	975.9	973.6	971.4	969.1	966.8	969.1	971.4	973.6
140°	1011.1	1008.9	1006.7	1004.7	1003.1	1001.5	999.9	998.2	999.9	1001.5	1003.1
142.5°	1037.5	1034.9	1032.4	1030.4	1028.9	1027.5	1026.0	1024.5	1026.0	1027.5	1028.9
145°	1073.5	1070.1	1066.6	1065.0	1065.2	1065.4	1065.6	1065.8	1065.6	1065.4	1065.2
147.5°	1106.9	1103.4	1100.0	1098.7	1099.5	1100.3	1101.0	1101.8	1101.0	1100.3	1099.5
150°	1126.9	1123.7	1120.4	1119.5	1120.9	1122.3	1123.8	1125.2	1123.8	1122.3	1120.9
152.5°	1145.5	1142.4	1139.3	1138.6	1140.2	1141.7	1143.3	1144.9	1143.3	1141.7	1140.2
155°	1171.5	1169.0	1166.6	1166.3	1168.1	1169.9	1171.8	1173.6	1171.8	1169.9	1168.1
157.5°	1193.4	1191.7	1190.0	1189.9	1191.4	1193.0	1194.5	1196.0	1194.5	1193.0	1191.4
160°	1206.8	1205.5	1204.3	1204.3	1205.5	1206.8	1208.0	1209.2	1208.0	1206.8	1205.5
162.5°	1218.0	1217.0	1215.9	1216.0	1217.2	1218.5	1219.7	1220.9	1219.7	1218.5	1217.2
165°	1232.6	1232.0	1231.4	1231.7	1232.9	1234.2	1235.4	1236.6	1235.4	1234.2	1232.9
167.5°	1244.2	1243.7	1243.1	1243.4	1244.6	1245.9	1247.1	1248.3	1247.1	1245.9	1244.6
170°	1250.4	1250.0	1249.6	1250.0	1251.2	1252.4	1253.6	1254.9	1253.6	1252.4	1251.2
172.5°	1254.8	1254.4	1254.0	1254.4	1255.6	1256.8	1258.0	1259.2	1258.0	1256.8	1255.6
175°	1259.5	1259.1	1258.7	1259.2	1260.6	1262.1	1263.5	1264.9	1263.5	1262.1	1260.6
177.5°	1261.1	1261.0	1260.8	1261.3	1262.4	1263.6	1264.7	1265.8	1264.7	1263.6	1262.4
180°	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2



TEST NUMBER: P331267

CATALOG NUMBER: SA2XXDIP-C290D925U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1
2.5°	583.3	582.2	578.4	576.4	573.1	570.0	568.0	568.9	569.6	569.3	568.7
5°	566.5	562.2	555.6	550.0	545.9	538.4	535.2	533.6	532.2	530.7	529.1
7.5°	546.6	539.8	530.4	522.3	514.7	505.3	500.0	496.9	493.6	490.0	486.8
10°	532.5	522.9	512.9	501.6	492.5	484.1	476.6	471.6	467.0	462.7	459.6
12.5°	517.6	506.6	494.2	478.7	468.7	456.6	455.5	446.7	439.6	436.9	433.2
15°	493.9	478.4	462.7	444.3	436.4	425.5	418.7	411.8	405.7	401.4	400.3
17.5°	466.9	446.9	431.3	418.1	405.1	393.9	387.6	382.2	377.1	371.4	370.6
20°	446.4	429.1	412.1	400.5	387.1	375.7	368.0	362.6	358.2	354.8	351.9
22.5°	426.9	408.0	392.4	379.8	366.6	357.4	351.3	346.0	342.4	338.7	335.9
25°	395.7	381.0	363.9	349.6	338.7	332.8	327.8	323.3	321.0	318.5	315.3
27.5°	368.4	352.0	336.1	325.0	315.4	310.2	306.6	303.5	301.4	299.9	298.1
30°	349.2	332.6	320.1	309.2	301.2	296.0	293.7	291.9	289.4	288.5	287.6
32.5°	330.6	315.7	305.0	295.5	288.0	284.5	282.5	280.8	278.9	278.0	276.1
35°	304.4	291.9	281.5	276.2	270.1	267.1	265.6	263.3	261.5	260.6	260.3
37.5°	279.7	268.9	262.0	255.3	252.7	250.9	248.7	247.2	246.6	246.5	246.2
40°	263.7	254.9	248.7	243.3	242.2	239.4	237.6	236.3	236.3	236.5	236.3
42.5°	249.2	241.2	235.8	231.1	229.8	228.2	226.3	226.3	226.6	227.4	226.6
45°	227.2	221.5	217.6	215.4	212.9	211.3	211.0	211.7	211.9	212.2	212.9
47.5°	206.9	203.1	199.6	197.1	196.0	195.8	195.5	196.7	197.8	198.2	199.2
50°	194.9	190.6	187.6	186.0	185.1	184.7	185.1	186.5	187.4	188.5	189.2
52.5°	181.5	178.4	176.4	175.1	174.8	175.1	175.1	176.7	178.1	178.6	178.9
55°	162.9	160.6	160.2	158.1	159.0	158.8	159.9	160.8	162.2	163.6	163.8
57.5°	144.3	142.5	141.3	141.5	141.8	142.8	143.7	145.3	146.7	148.2	148.3
60°	132.0	131.1	130.4	130.4	130.8	132.2	133.3	134.9	135.8	136.8	137.4
62.5°	120.7	119.8	119.1	119.5	120.7	121.5	122.8	123.7	124.6	125.5	125.8
65°	102.9	102.5	103.1	103.6	103.8	104.9	106.5	107.2	108.1	108.6	110.2
67.5°	86.5	86.6	86.5	87.1	88.5	88.7	90.2	91.8	92.0	92.9	93.9
70°	75.4	75.9	76.3	76.8	77.9	78.4	79.5	80.2	81.1	81.8	82.5
72.5°	65.2	65.3	65.8	65.7	66.7	67.6	68.6	69.3	70.2	71.1	71.7
75°	50.2	50.2	50.7	50.9	52.0	53.2	52.9	53.4	54.3	55.2	55.7
77.5°	36.7	36.2	36.7	36.9	37.3	38.2	38.4	39.0	40.1	39.8	40.3
80°	27.9	27.3	27.9	28.2	28.2	29.3	29.3	29.8	30.4	29.8	30.4
82.5°	19.9	19.6	20.1	20.2	20.5	20.6	20.9	21.0	21.7	21.4	21.7
85°	10.0	9.8	10.0	9.8	10.0	10.2	10.2	10.0	10.0	10.4	9.8
87.5°	5.1	5.3	5.4	5.7	5.9	6.0	6.0	6.2	6.4	6.3	6.4
90°	9.8	11.8	13.4	15.0	16.6	18.3	19.3	20.3	21.3	22.3	23.0
92.5°	17.6	17.9	18.8	19.6	20.4	21.2	21.7	22.2	22.8	23.3	23.7
95°	32.6	29.9	31.4	32.8	34.2	35.6	36.6	37.6	38.7	39.7	40.1
97.5°	42.3	34.5	37.8	41.1	44.4	47.7	48.5	49.3	50.1	50.9	51.4
100°	50.4	38.3	41.7	45.2	48.6	52.1	53.7	55.3	56.9	58.6	59.6
102.5°	186.3	169.0	140.1	111.2	82.4	53.5	55.6	57.7	59.9	62.0	63.3
105°	302.0	277.3	221.9	166.5	111.1	55.7	57.9	60.2	62.4	64.6	66.2
107.5°	374.6	343.8	277.3	210.9	144.4	78.0	75.7	73.4	71.2	68.9	68.2
110°	421.6	394.4	335.8	277.1	218.5	159.8	139.5	119.2	98.9	78.6	68.9



TEST NUMBER: P331267

CATALOG NUMBER: SA2XXDIP-C290D925U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	466.4	461.1	446.6	432.1	417.6	403.1	329.1	255.1	181.0	107.0	70.3
115°	538.9	543.2	548.3	553.4	558.4	563.5	469.5	375.6	281.6	187.6	133.3
117.5°	606.5	610.2	613.7	617.2	620.7	624.1	601.4	578.7	556.0	533.2	497.8
120°	651.5	654.8	658.5	662.1	665.8	669.4	671.9	674.3	676.8	679.2	666.7
122.5°	693.0	696.6	700.6	704.6	708.6	712.6	714.0	715.5	716.9	718.4	716.5
125°	753.1	756.3	760.2	764.0	767.9	771.7	773.2	774.6	776.0	777.4	778.4
127.5°	810.6	813.5	816.4	819.3	822.2	825.1	827.1	829.2	831.3	833.4	834.4
130°	847.7	850.5	852.7	854.9	857.2	859.4	861.6	863.9	866.1	868.3	869.4
132.5°	882.3	884.8	887.1	889.3	891.5	893.7	895.7	897.6	899.5	901.4	902.2
135°	931.8	934.3	936.1	938.0	939.8	941.6	943.6	945.7	947.7	949.7	950.5
137.5°	975.9	978.1	980.1	982.2	984.3	986.4	988.3	990.3	992.3	994.3	995.0
140°	1004.7	1006.7	1008.9	1011.1	1013.4	1015.6	1017.4	1019.2	1021.1	1022.9	1023.3
142.5°	1030.4	1032.4	1034.9	1037.5	1040.1	1042.6	1044.3	1045.9	1047.6	1049.3	1049.6
145°	1065.0	1066.6	1070.1	1073.5	1077.0	1080.4	1081.8	1083.3	1084.7	1086.1	1086.3
147.5°	1098.7	1100.0	1103.4	1106.9	1110.3	1113.7	1114.7	1115.8	1116.8	1117.9	1118.0
150°	1119.5	1120.4	1123.7	1126.9	1130.2	1133.4	1134.6	1135.8	1137.1	1138.3	1138.4
152.5°	1138.6	1139.3	1142.4	1145.5	1148.6	1151.7	1152.9	1154.1	1155.3	1156.5	1156.5
155°	1166.3	1166.6	1169.0	1171.5	1173.9	1176.3	1177.5	1178.8	1180.0	1181.2	1181.0
157.5°	1189.9	1190.0	1191.7	1193.4	1195.1	1196.8	1198.2	1199.5	1200.9	1202.3	1202.2
160°	1204.3	1204.3	1205.5	1206.8	1208.0	1209.2	1210.4	1211.6	1212.9	1214.1	1214.0
162.5°	1216.0	1215.9	1217.0	1218.0	1219.1	1220.2	1221.5	1222.9	1224.3	1225.7	1225.5
165°	1231.7	1231.4	1232.0	1232.6	1233.3	1233.9	1235.3	1236.7	1238.1	1239.5	1239.5
167.5°	1243.4	1243.1	1243.7	1244.2	1244.8	1245.4	1246.8	1248.2	1249.6	1251.1	1250.8
170°	1250.0	1249.6	1250.0	1250.4	1250.8	1251.2	1252.6	1254.1	1255.5	1256.9	1256.7
172.5°	1254.4	1254.0	1254.4	1254.8	1255.2	1255.6	1257.0	1258.4	1259.9	1261.3	1261.1
175°	1259.2	1258.7	1259.1	1259.5	1259.9	1260.3	1261.8	1263.2	1264.6	1266.0	1265.7
177.5°	1261.3	1260.8	1261.0	1261.1	1261.3	1261.4	1262.6	1263.7	1264.9	1266.0	1265.8
180°	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2



TEST NUMBER: P331267

CATALOG NUMBER: SA2XXDIP-C290D925U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1
2.5°	566.9	566.5	566.5	564.9	566.5	566.5	566.9	568.7	569.3	569.6	568.9
5°	525.9	525.2	524.1	525.2	524.1	525.2	525.9	529.1	530.7	532.2	533.6
7.5°	485.3	482.6	482.2	479.5	482.2	482.6	485.3	486.8	490.0	493.6	496.9
10°	455.7	453.9	453.6	449.3	453.6	453.9	455.7	459.6	462.7	467.0	471.6
12.5°	433.2	428.8	429.7	427.2	429.7	428.8	433.2	433.2	436.9	439.6	446.7
15°	394.1	394.1	393.2	389.4	393.2	394.1	394.1	400.3	401.4	405.7	411.8
17.5°	366.1	365.6	363.5	364.6	363.5	365.6	366.1	370.6	371.4	377.1	382.2
20°	349.4	348.0	345.3	345.3	345.3	348.0	349.4	351.9	354.8	358.2	362.6
22.5°	333.6	333.5	330.6	331.5	330.6	333.5	333.6	335.9	338.7	342.4	346.0
25°	315.1	313.3	311.9	312.6	311.9	313.3	315.1	315.3	318.5	321.0	323.3
27.5°	297.5	296.5	296.4	294.6	296.4	296.5	297.5	298.1	299.9	301.4	303.5
30°	287.4	285.1	285.5	284.4	285.5	285.1	287.4	287.6	288.5	289.4	291.9
32.5°	275.7	274.9	274.5	273.5	274.5	274.9	275.7	276.1	278.0	278.9	280.8
35°	259.9	260.1	259.0	259.4	259.0	260.1	259.9	260.3	260.6	261.5	263.3
37.5°	246.0	246.7	246.2	246.3	246.2	246.7	246.0	246.2	246.5	246.6	247.2
40°	236.9	236.9	236.9	237.6	236.9	236.9	236.9	236.3	236.5	236.3	236.3
42.5°	228.2	227.8	227.5	227.4	227.5	227.8	228.2	226.6	227.4	226.6	226.3
45°	213.3	214.0	214.2	213.1	214.2	214.0	213.3	212.9	212.2	211.9	211.7
47.5°	199.8	199.9	199.8	200.8	199.8	199.9	199.8	199.2	198.2	197.8	196.7
50°	190.4	189.9	190.4	189.9	190.4	189.9	190.4	189.2	188.5	187.4	186.5
52.5°	180.4	180.5	180.2	180.1	180.2	180.5	180.4	178.9	178.6	178.1	176.7
55°	164.7	165.1	164.9	164.9	164.9	165.1	164.7	163.8	163.6	162.2	160.8
57.5°	148.5	148.9	149.2	148.2	149.2	148.9	148.5	148.3	148.2	146.7	145.3
60°	137.2	138.3	138.1	137.7	138.1	138.3	137.2	137.4	136.8	135.8	134.9
62.5°	126.8	127.3	127.2	127.1	127.2	127.3	126.8	125.8	125.5	124.6	123.7
65°	110.9	111.3	110.6	111.3	110.6	111.3	110.9	110.2	108.6	108.1	107.2
67.5°	93.6	93.8	94.3	94.6	94.3	93.8	93.6	93.9	92.9	92.0	91.8
70°	82.9	82.7	83.4	84.1	83.4	82.7	82.9	82.5	81.8	81.1	80.2
72.5°	71.6	72.1	71.9	72.4	71.9	72.1	71.6	71.7	71.1	70.2	69.3
75°	55.2	55.9	55.7	56.3	55.7	55.9	55.2	55.7	55.2	54.3	53.4
77.5°	39.9	40.0	39.9	40.3	39.9	40.0	39.9	40.3	39.8	40.1	39.0
80°	30.4	30.0	29.5	30.4	29.5	30.0	30.4	30.4	29.8	30.4	29.8
82.5°	21.2	21.4	21.0	21.0	21.0	21.4	21.2	21.7	21.4	21.7	21.0
85°	9.8	9.5	9.1	9.1	9.1	9.5	9.8	9.8	10.4	10.0	10.0
87.5°	6.5	6.4	6.5	6.4	6.5	6.4	6.5	6.4	6.3	6.4	6.2
90°	23.4	23.8	24.3	24.7	24.3	23.8	23.4	23.0	22.3	21.3	20.3
92.5°	23.9	24.2	24.4	24.7	24.4	24.2	23.9	23.7	23.3	22.8	22.2
95°	39.9	39.7	39.5	39.3	39.5	39.7	39.9	40.1	39.7	38.7	37.6
97.5°	51.7	51.9	52.2	52.4	52.2	51.9	51.7	51.4	50.9	50.1	49.3
100°	60.0	60.4	60.8	61.2	60.8	60.4	60.0	59.6	58.6	56.9	55.3
102.5°	63.9	64.4	65.0	65.6	65.0	64.4	63.9	63.3	62.0	59.9	57.7
105°	67.0	67.8	68.6	69.4	68.6	67.8	67.0	66.2	64.6	62.4	60.2
107.5°	69.0	69.8	70.6	71.4	70.6	69.8	69.0	68.2	68.9	71.2	73.4
110°	69.7	70.5	71.3	72.2	71.3	70.5	69.7	68.9	78.6	98.9	119.2



TEST NUMBER: P331267

CATALOG NUMBER: SA2XXDIP-C290D925U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	70.9	71.6	72.2	72.9	72.2	71.6	70.9	70.3	107.0	181.0	255.1
115°	118.7	104.1	89.5	74.9	89.5	104.1	118.7	133.3	187.6	281.6	375.6
117.5°	449.8	401.8	353.8	305.8	353.8	401.8	449.8	497.8	533.2	556.0	578.7
120°	639.3	611.9	584.5	557.1	584.5	611.9	639.3	666.7	679.2	676.8	674.3
122.5°	711.2	705.8	700.5	695.2	700.5	705.8	711.2	716.5	718.4	716.9	715.5
125°	779.0	779.6	780.3	780.9	780.3	779.6	779.0	778.4	777.4	776.0	774.6
127.5°	834.6	834.7	834.8	834.9	834.8	834.7	834.6	834.4	833.4	831.3	829.2
130°	869.2	868.9	868.7	868.5	868.7	868.9	869.2	869.4	868.3	866.1	863.9
132.5°	902.0	901.8	901.6	901.4	901.6	901.8	902.0	902.2	901.4	899.5	897.6
135°	950.1	949.7	949.3	948.9	949.3	949.7	950.1	950.5	949.7	947.7	945.7
137.5°	994.3	993.6	992.9	992.2	992.9	993.6	994.3	995.0	994.3	992.3	990.3
140°	1022.3	1021.3	1020.3	1019.2	1020.3	1021.3	1022.3	1023.3	1022.9	1021.1	1019.2
142.5°	1048.6	1047.6	1046.6	1045.5	1046.6	1047.6	1048.6	1049.6	1049.3	1047.6	1045.9
145°	1085.3	1084.3	1083.3	1082.3	1083.3	1084.3	1085.3	1086.3	1086.1	1084.7	1083.3
147.5°	1117.1	1116.3	1115.4	1114.6	1115.4	1116.3	1117.1	1118.0	1117.9	1116.8	1115.8
150°	1137.4	1136.3	1135.3	1134.3	1135.3	1136.3	1137.4	1138.4	1138.3	1137.1	1135.8
152.5°	1155.1	1153.8	1152.5	1151.1	1152.5	1153.8	1155.1	1156.5	1156.5	1155.3	1154.1
155°	1179.4	1177.7	1176.1	1174.5	1176.1	1177.7	1179.4	1181.0	1181.2	1180.0	1178.8
157.5°	1200.6	1199.0	1197.4	1195.9	1197.4	1199.0	1200.6	1202.2	1202.3	1200.9	1199.5
160°	1212.5	1211.1	1209.7	1208.3	1209.7	1211.1	1212.5	1214.0	1214.1	1212.9	1211.6
162.5°	1223.8	1222.0	1220.3	1218.5	1220.3	1222.0	1223.8	1225.5	1225.7	1224.3	1222.9
165°	1238.1	1236.7	1235.3	1233.9	1235.3	1236.7	1238.1	1239.5	1239.5	1238.1	1236.7
167.5°	1249.0	1247.2	1245.4	1243.5	1245.4	1247.2	1249.0	1250.8	1251.1	1249.6	1248.2
170°	1254.9	1253.0	1251.2	1249.4	1251.2	1253.0	1254.9	1256.7	1256.9	1255.5	1254.1
172.5°	1259.2	1257.4	1255.6	1253.8	1255.6	1257.4	1259.2	1261.1	1261.3	1259.9	1258.4
175°	1263.7	1261.7	1259.6	1257.6	1259.6	1261.7	1263.7	1265.7	1266.0	1264.6	1263.2
177.5°	1264.4	1262.9	1261.4	1260.0	1261.4	1262.9	1264.4	1265.8	1266.0	1264.9	1263.7
180°	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2



TEST NUMBER: P331267
 CATALOG NUMBER: SA2XXDIP-C290D925U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1
2.5°	568.0	570.0	573.1	576.4	578.4	582.2	583.3	585.1	586.7	590.5	594.5
5°	535.2	538.4	545.9	550.0	555.6	562.2	566.5	571.1	576.1	584.7	592.7
7.5°	500.0	505.3	514.7	522.3	530.4	539.8	546.6	555.6	563.1	575.3	586.9
10°	476.6	484.1	492.5	501.6	512.9	522.9	532.5	543.8	552.9	567.5	581.1
12.5°	455.5	456.6	468.7	478.7	494.2	506.6	517.6	532.2	541.1	558.4	572.7
15°	418.7	425.5	436.4	444.3	462.7	478.4	493.9	509.1	519.3	540.7	559.5
17.5°	387.6	393.9	405.1	418.1	431.3	446.9	466.9	483.0	496.9	521.3	543.6
20°	368.0	375.7	387.1	400.5	412.1	429.1	446.4	464.8	479.8	507.3	533.4
22.5°	351.3	357.4	366.6	379.8	392.4	408.0	426.9	447.0	462.7	492.4	518.8
25°	327.8	332.8	338.7	349.6	363.9	381.0	395.7	417.8	440.7	468.4	500.4
27.5°	306.6	310.2	315.4	325.0	336.1	352.0	368.4	389.3	412.4	442.5	476.3
30°	293.7	296.0	301.2	309.2	320.1	332.6	349.2	369.1	392.8	423.2	456.8
32.5°	282.5	284.5	288.0	295.5	305.0	315.7	330.6	350.6	373.1	403.0	440.3
35°	265.6	267.1	270.1	276.2	281.5	291.9	304.4	322.6	343.7	372.3	410.9
37.5°	248.7	250.9	252.7	255.3	262.0	268.9	279.7	295.1	315.8	344.7	381.5
40°	237.6	239.4	242.2	243.3	248.7	254.9	263.7	277.8	298.7	325.1	361.0
42.5°	226.3	228.2	229.8	231.1	235.8	241.2	249.2	261.3	279.8	305.4	341.0
45°	211.0	211.3	212.9	215.4	217.6	221.5	227.2	237.6	251.9	276.0	308.3
47.5°	195.5	195.8	196.0	197.1	199.6	203.1	206.9	215.4	228.2	247.4	278.8
50°	185.1	184.7	185.1	186.0	187.6	190.6	194.9	201.0	211.5	229.4	258.3
52.5°	175.1	175.1	174.8	175.1	176.4	178.4	181.5	186.7	196.0	212.5	237.9
55°	159.9	158.8	159.0	158.1	160.2	160.6	162.9	167.2	175.4	186.7	210.6
57.5°	143.7	142.8	141.8	141.5	141.3	142.5	144.3	147.7	154.0	164.0	183.3
60°	133.3	132.2	130.8	130.4	130.4	131.1	132.0	134.5	140.4	149.2	165.1
62.5°	122.8	121.5	120.7	119.5	119.1	119.8	120.7	122.5	126.8	135.1	148.8
65°	106.5	104.9	103.8	103.6	103.1	102.5	102.9	104.7	108.1	114.7	125.6
67.5°	90.2	88.7	88.5	87.1	86.5	86.6	86.5	88.0	90.1	95.8	103.9
70°	79.5	78.4	77.9	76.8	76.3	75.9	75.4	76.8	78.8	83.6	90.6
72.5°	68.6	67.6	66.7	65.7	65.8	65.3	65.2	66.1	67.7	72.1	77.6
75°	52.9	53.2	52.0	50.9	50.7	50.2	50.2	50.9	51.6	55.0	59.3
77.5°	38.4	38.2	37.3	36.9	36.7	36.2	36.7	37.1	37.5	39.8	42.9
80°	29.3	29.3	28.2	28.2	27.9	27.3	27.9	27.5	28.4	30.7	32.9
82.5°	20.9	20.6	20.5	20.2	20.1	19.6	19.9	20.4	20.8	22.3	23.7
85°	10.2	10.2	10.0	9.8	10.0	9.8	10.0	10.2	10.4	11.1	12.3
87.5°	6.0	6.0	5.9	5.7	5.4	5.3	5.1	4.8	4.7	4.4	4.2
90°	19.3	18.3	16.6	15.0	13.4	11.8	9.8	7.6	5.4	3.1	0.9
92.5°	21.7	21.2	20.4	19.6	18.8	17.9	17.6	17.8	18.0	18.2	18.4
95°	36.6	35.6	34.2	32.8	31.4	29.9	32.6	39.3	46.0	52.7	59.4
97.5°	48.5	47.7	44.4	41.1	37.8	34.5	42.3	61.2	80.1	98.9	117.8
100°	53.7	52.1	48.6	45.2	41.7	38.3	50.4	78.2	106.0	133.8	161.7
102.5°	55.6	53.5	82.4	111.2	140.1	169.0	186.3	192.2	198.1	204.0	209.9
105°	57.9	55.7	111.1	166.5	221.9	277.3	302.0	295.9	289.8	283.7	277.6
107.5°	75.7	78.0	144.4	210.9	277.3	343.8	374.6	369.6	364.7	359.8	354.9
110°	139.5	159.8	218.5	277.1	335.8	394.4	421.6	417.4	413.1	408.9	404.6



TEST NUMBER: P331267

CATALOG NUMBER: SA2XXDIP-C290D925U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	329.1	403.1	417.6	432.1	446.6	461.1	466.4	462.7	458.9	455.1	451.3
115°	469.5	563.5	558.4	553.4	548.3	543.2	538.9	535.5	532.0	528.6	525.1
117.5°	601.4	624.1	620.7	617.2	613.7	610.2	606.5	602.7	598.8	594.9	591.1
120°	671.9	669.4	665.8	662.1	658.5	654.8	651.5	648.4	645.4	642.3	639.3
122.5°	714.0	712.6	708.6	704.6	700.6	696.6	693.0	689.8	686.6	683.4	680.2
125°	773.2	771.7	767.9	764.0	760.2	756.3	753.1	750.4	747.8	745.1	742.5
127.5°	827.1	825.1	822.2	819.3	816.4	813.5	810.6	807.7	804.8	801.9	798.9
130°	861.6	859.4	857.2	854.9	852.7	850.5	847.7	844.5	841.2	838.0	834.8
132.5°	895.7	893.7	891.5	889.3	887.1	884.8	882.3	879.6	876.8	874.0	871.3
135°	943.6	941.6	939.8	938.0	936.1	934.3	931.8	928.5	925.3	922.0	918.8
137.5°	988.3	986.4	984.3	982.2	980.1	978.1	975.9	973.6	971.4	969.1	966.8
140°	1017.4	1015.6	1013.4	1011.1	1008.9	1006.7	1004.7	1003.1	1001.5	999.9	998.2
142.5°	1044.3	1042.6	1040.1	1037.5	1034.9	1032.4	1030.4	1028.9	1027.5	1026.0	1024.5
145°	1081.8	1080.4	1077.0	1073.5	1070.1	1066.6	1065.0	1065.2	1065.4	1065.6	1065.8
147.5°	1114.7	1113.7	1110.3	1106.9	1103.4	1100.0	1098.7	1099.5	1100.3	1101.0	1101.8
150°	1134.6	1133.4	1130.2	1126.9	1123.7	1120.4	1119.5	1120.9	1122.3	1123.8	1125.2
152.5°	1152.9	1151.7	1148.6	1145.5	1142.4	1139.3	1138.6	1140.2	1141.7	1143.3	1144.9
155°	1177.5	1176.3	1173.9	1171.5	1169.0	1166.6	1166.3	1168.1	1169.9	1171.8	1173.6
157.5°	1198.2	1196.8	1195.1	1193.4	1191.7	1190.0	1189.9	1191.4	1193.0	1194.5	1196.0
160°	1210.4	1209.2	1208.0	1206.8	1205.5	1204.3	1204.3	1205.5	1206.8	1208.0	1209.2
162.5°	1221.5	1220.2	1219.1	1218.0	1217.0	1215.9	1216.0	1217.2	1218.5	1219.7	1220.9
165°	1235.3	1233.9	1233.3	1232.6	1232.0	1231.4	1231.7	1232.9	1234.2	1235.4	1236.6
167.5°	1246.8	1245.4	1244.8	1244.2	1243.7	1243.1	1243.4	1244.6	1245.9	1247.1	1248.3
170°	1252.6	1251.2	1250.8	1250.4	1250.0	1249.6	1250.0	1251.2	1252.4	1253.6	1254.9
172.5°	1257.0	1255.6	1255.2	1254.8	1254.4	1254.0	1254.4	1255.6	1256.8	1258.0	1259.2
175°	1261.8	1260.3	1259.9	1259.5	1259.1	1258.7	1259.2	1260.6	1262.1	1263.5	1264.9
177.5°	1262.6	1261.4	1261.3	1261.1	1261.0	1260.8	1261.3	1262.4	1263.6	1264.7	1265.8
180°	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2



TEST NUMBER: P331267

CATALOG NUMBER: SA2XXDIP-C290D925U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1
2.5°	594.2	595.1	598.0	600.9	604.2	605.1	606.5	605.3	604.9	608.3	610.9
5°	595.9	599.9	607.9	615.2	621.3	625.6	630.2	632.0	635.4	640.1	646.1
7.5°	593.9	601.9	614.4	625.0	636.5	644.8	651.3	656.9	663.6	672.6	682.5
10°	591.8	602.4	617.7	630.6	644.7	655.4	664.2	672.9	682.9	695.4	708.3
12.5°	587.8	600.4	619.5	634.8	652.9	663.4	675.3	693.9	704.7	722.1	740.3
15°	579.7	593.8	620.4	639.2	659.7	679.7	701.7	719.4	737.1	747.4	773.0
17.5°	567.8	588.4	617.9	639.9	665.9	697.3	722.1	742.2	762.6	779.2	792.1
20°	558.1	580.6	614.3	640.6	671.5	705.3	733.7	754.2	771.9	785.8	793.7
22.5°	546.0	574.3	607.0	637.9	677.3	710.8	740.6	756.7	771.5	778.3	781.4
25°	526.8	560.9	597.9	635.6	680.1	715.6	742.8	752.6	756.9	750.3	739.4
27.5°	506.1	544.1	587.4	631.3	678.4	712.5	732.0	730.5	723.2	701.8	684.8
30°	490.7	532.5	579.0	627.0	674.2	707.4	718.7	707.4	690.8	667.0	642.6
32.5°	474.5	517.8	570.1	620.8	666.6	695.8	698.2	678.7	653.0	625.9	595.6
35°	450.0	496.8	553.4	607.0	650.4	668.8	657.9	623.3	592.9	555.9	514.5
37.5°	422.3	474.0	530.7	586.8	626.1	630.9	603.8	567.5	524.5	481.0	432.3
40°	401.6	456.4	514.8	571.3	606.1	601.1	566.5	526.6	475.5	422.3	377.1
42.5°	383.1	437.8	497.3	552.8	580.6	566.9	526.6	477.5	422.6	372.5	331.1
45°	351.0	407.3	468.2	521.8	537.7	512.9	459.6	405.0	351.0	309.2	276.5
47.5°	319.8	375.5	435.8	482.9	488.5	455.2	396.9	340.8	294.3	260.3	237.2
50°	296.9	352.8	412.5	454.6	452.7	412.5	352.6	299.2	260.3	232.8	217.4
52.5°	276.4	329.2	386.5	424.8	415.1	371.3	314.0	266.6	234.7	213.2	199.2
55°	244.4	293.3	347.8	378.5	360.7	312.1	263.7	225.6	201.9	185.8	174.9
57.5°	212.7	258.5	305.2	324.1	304.5	259.6	219.3	191.6	173.8	161.9	154.8
60°	193.1	233.1	274.6	291.0	267.6	227.6	195.8	171.1	156.7	147.0	140.6
62.5°	173.5	209.3	248.5	257.4	236.0	202.2	174.0	153.4	141.7	133.0	127.0
65°	146.7	176.1	205.8	211.7	192.0	165.8	143.6	130.2	119.7	113.4	108.6
67.5°	120.4	143.9	165.0	169.7	152.4	134.3	118.2	106.5	99.5	94.2	90.1
70°	104.7	123.4	140.6	144.5	130.6	114.5	102.2	92.9	86.5	82.0	78.1
72.5°	88.2	103.7	118.1	120.7	109.4	97.0	87.0	79.6	74.0	71.1	67.4
75°	67.5	76.6	87.7	88.4	80.9	73.4	65.7	60.9	57.9	54.3	52.5
77.5°	47.6	54.7	61.1	62.3	57.9	52.8	48.5	44.7	42.2	40.5	38.8
80°	36.3	42.0	44.8	46.3	43.2	39.5	37.0	34.5	32.9	31.8	30.7
82.5°	26.0	29.5	32.0	33.3	31.5	29.3	26.9	25.4	24.2	23.3	22.9
85°	13.2	14.8	16.4	16.8	16.4	15.4	14.1	14.1	13.4	13.2	13.2
87.5°	5.2	6.3	6.8	7.8	7.8	8.1	8.5	8.6	8.7	8.8	8.8
90°	3.1	5.4	7.6	9.8	11.8	13.4	15.0	16.6	18.3	19.3	20.3
92.5°	18.2	18.0	17.8	17.6	17.9	18.8	19.6	20.4	21.2	21.7	22.2
95°	52.7	46.0	39.3	32.6	29.9	31.4	32.8	34.2	35.6	36.6	37.6
97.5°	98.9	80.1	61.2	42.3	34.5	37.8	41.1	44.4	47.7	48.5	49.3
100°	133.8	106.0	78.2	50.4	38.3	41.7	45.2	48.6	52.1	53.7	55.3
102.5°	204.0	198.1	192.2	186.3	169.0	140.1	111.2	82.4	53.5	55.6	57.7
105°	283.7	289.8	295.9	302.0	277.3	221.9	166.5	111.1	55.7	57.9	60.2
107.5°	359.8	364.7	369.6	374.6	343.8	277.3	210.9	144.4	78.0	75.7	73.4
110°	408.9	413.1	417.4	421.6	394.4	335.8	277.1	218.5	159.8	139.5	119.2



TEST NUMBER: P331267

CATALOG NUMBER: SA2XXDIP-C290D925U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	455.1	458.9	462.7	466.4	461.1	446.6	432.1	417.6	403.1	329.1	255.1
115°	528.6	532.0	535.5	538.9	543.2	548.3	553.4	558.4	563.5	469.5	375.6
117.5°	594.9	598.8	602.7	606.5	610.2	613.7	617.2	620.7	624.1	601.4	578.7
120°	642.3	645.4	648.4	651.5	654.8	658.5	662.1	665.8	669.4	671.9	674.3
122.5°	683.4	686.6	689.8	693.0	696.6	700.6	704.6	708.6	712.6	714.0	715.5
125°	745.1	747.8	750.4	753.1	756.3	760.2	764.0	767.9	771.7	773.2	774.6
127.5°	801.9	804.8	807.7	810.6	813.5	816.4	819.3	822.2	825.1	827.1	829.2
130°	838.0	841.2	844.5	847.7	850.5	852.7	854.9	857.2	859.4	861.6	863.9
132.5°	874.0	876.8	879.6	882.3	884.8	887.1	889.3	891.5	893.7	895.7	897.6
135°	922.0	925.3	928.5	931.8	934.3	936.1	938.0	939.8	941.6	943.6	945.7
137.5°	969.1	971.4	973.6	975.9	978.1	980.1	982.2	984.3	986.4	988.3	990.3
140°	999.9	1001.5	1003.1	1004.7	1006.7	1008.9	1011.1	1013.4	1015.6	1017.4	1019.2
142.5°	1026.0	1027.5	1028.9	1030.4	1032.4	1034.9	1037.5	1040.1	1042.6	1044.3	1045.9
145°	1065.6	1065.4	1065.2	1065.0	1066.6	1070.1	1073.5	1077.0	1080.4	1081.8	1083.3
147.5°	1101.0	1100.3	1099.5	1098.7	1100.0	1103.4	1106.9	1110.3	1113.7	1114.7	1115.8
150°	1123.8	1122.3	1120.9	1119.5	1120.4	1123.7	1126.9	1130.2	1133.4	1134.6	1135.8
152.5°	1143.3	1141.7	1140.2	1138.6	1139.3	1142.4	1145.5	1148.6	1151.7	1152.9	1154.1
155°	1171.8	1169.9	1168.1	1166.3	1166.6	1169.0	1171.5	1173.9	1176.3	1177.5	1178.8
157.5°	1194.5	1193.0	1191.4	1189.9	1190.0	1191.7	1193.4	1195.1	1196.8	1198.2	1199.5
160°	1208.0	1206.8	1205.5	1204.3	1204.3	1205.5	1206.8	1208.0	1209.2	1210.4	1211.6
162.5°	1219.7	1218.5	1217.2	1216.0	1215.9	1217.0	1218.0	1219.1	1220.2	1221.5	1222.9
165°	1235.4	1234.2	1232.9	1231.7	1231.4	1232.0	1232.6	1233.3	1233.9	1235.3	1236.7
167.5°	1247.1	1245.9	1244.6	1243.4	1243.1	1243.7	1244.2	1244.8	1245.4	1246.8	1248.2
170°	1253.6	1252.4	1251.2	1250.0	1249.6	1250.0	1250.4	1250.8	1251.2	1252.6	1254.1
172.5°	1258.0	1256.8	1255.6	1254.4	1254.0	1254.4	1254.8	1255.2	1255.6	1257.0	1258.4
175°	1263.5	1262.1	1260.6	1259.2	1258.7	1259.1	1259.5	1259.9	1260.3	1261.8	1263.2
177.5°	1264.7	1263.6	1262.4	1261.3	1260.8	1261.0	1261.1	1261.3	1261.4	1262.6	1263.7
180°	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2



TEST NUMBER: P331267

CATALOG NUMBER: SA2XXDIP-C290D925U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	591.1	591.1	591.1	591.1	591.1	591.1	591.1
2.5°	613.1	615.6	615.6	616.0	618.9	618.5	618.3
5°	652.4	656.3	656.7	660.8	663.5	662.6	660.1
7.5°	689.5	696.7	702.2	705.2	708.8	711.0	710.0
10°	719.0	729.4	735.8	740.1	745.3	749.2	747.8
12.5°	745.7	758.1	766.9	774.3	774.9	779.9	776.5
15°	787.4	800.5	801.9	807.3	811.7	811.2	811.4
17.5°	801.1	805.3	806.2	806.3	806.4	804.8	801.3
20°	796.2	794.6	790.8	787.8	782.6	781.9	777.4
22.5°	772.9	767.9	758.2	751.8	743.7	741.6	740.3
25°	727.2	716.0	700.6	685.8	681.7	673.8	676.0
27.5°	664.3	647.0	630.2	618.3	607.4	595.5	598.9
30°	620.2	600.6	577.0	558.8	547.2	535.9	533.8
32.5°	567.5	538.8	512.5	496.5	478.7	471.5	463.7
35°	476.6	448.6	422.5	400.0	387.1	377.1	368.0
37.5°	394.9	362.7	341.6	323.4	314.0	308.3	309.8
40°	344.2	316.0	300.5	286.7	278.0	274.0	274.9
42.5°	303.1	282.0	269.3	259.8	253.7	251.4	250.9
45°	256.5	244.7	234.2	228.8	225.8	223.3	221.7
47.5°	224.7	215.0	209.1	205.9	203.3	200.8	200.7
50°	205.6	199.2	195.1	191.7	189.7	187.9	189.5
52.5°	191.0	185.2	181.1	178.1	177.3	175.7	175.6
55°	169.5	164.9	162.0	159.2	157.9	157.0	155.8
57.5°	149.8	145.5	142.8	141.1	138.5	137.6	137.2
60°	135.8	132.4	129.7	127.4	126.3	124.5	124.5
62.5°	122.9	119.5	117.0	115.3	113.4	112.7	112.9
65°	104.3	101.5	99.0	97.2	96.8	95.4	95.9
67.5°	87.1	85.3	82.6	81.6	80.8	80.1	79.5
70°	75.6	73.8	72.5	71.1	70.4	70.4	70.4
72.5°	66.0	63.8	63.0	61.3	61.7	61.0	60.2
75°	51.1	49.7	49.1	48.4	47.3	47.3	47.3
77.5°	37.6	37.2	36.4	35.7	35.4	35.2	35.3
80°	29.1	28.8	28.4	28.4	27.9	27.7	27.3
82.5°	22.4	21.8	21.5	21.3	21.2	21.2	21.1
85°	12.7	12.3	12.3	12.5	12.0	12.0	12.3
87.5°	9.2	9.4	9.3	9.4	9.7	9.6	9.7
90°	21.3	22.3	23.0	23.4	23.8	24.3	24.7
92.5°	22.8	23.3	23.7	23.9	24.2	24.4	24.7
95°	38.7	39.7	40.1	39.9	39.7	39.5	39.3
97.5°	50.1	50.9	51.4	51.7	51.9	52.2	52.4
100°	56.9	58.6	59.6	60.0	60.4	60.8	61.2
102.5°	59.9	62.0	63.3	63.9	64.4	65.0	65.6
105°	62.4	64.6	66.2	67.0	67.8	68.6	69.4
107.5°	71.2	68.9	68.2	69.0	69.8	70.6	71.4
110°	98.9	78.6	68.9	69.7	70.5	71.3	72.2



TEST NUMBER: P331267

CATALOG NUMBER: SA2XXDIP-C290D925U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	181.0	107.0	70.3	70.9	71.6	72.2	72.9
115°	281.6	187.6	133.3	118.7	104.1	89.5	74.9
117.5°	556.0	533.2	497.8	449.8	401.8	353.8	305.8
120°	676.8	679.2	666.7	639.3	611.9	584.5	557.1
122.5°	716.9	718.4	716.5	711.2	705.8	700.5	695.2
125°	776.0	777.4	778.4	779.0	779.6	780.3	780.9
127.5°	831.3	833.4	834.4	834.6	834.7	834.8	834.9
130°	866.1	868.3	869.4	869.2	868.9	868.7	868.5
132.5°	899.5	901.4	902.2	902.0	901.8	901.6	901.4
135°	947.7	949.7	950.5	950.1	949.7	949.3	948.9
137.5°	992.3	994.3	995.0	994.3	993.6	992.9	992.2
140°	1021.1	1022.9	1023.3	1022.3	1021.3	1020.3	1019.2
142.5°	1047.6	1049.3	1049.6	1048.6	1047.6	1046.6	1045.5
145°	1084.7	1086.1	1086.3	1085.3	1084.3	1083.3	1082.3
147.5°	1116.8	1117.9	1118.0	1117.1	1116.3	1115.4	1114.6
150°	1137.1	1138.3	1138.4	1137.4	1136.3	1135.3	1134.3
152.5°	1155.3	1156.5	1156.5	1155.1	1153.8	1152.5	1151.1
155°	1180.0	1181.2	1181.0	1179.4	1177.7	1176.1	1174.5
157.5°	1200.9	1202.3	1202.2	1200.6	1199.0	1197.4	1195.9
160°	1212.9	1214.1	1214.0	1212.5	1211.1	1209.7	1208.3
162.5°	1224.3	1225.7	1225.5	1223.8	1222.0	1220.3	1218.5
165°	1238.1	1239.5	1239.5	1238.1	1236.7	1235.3	1233.9
167.5°	1249.6	1251.1	1250.8	1249.0	1247.2	1245.4	1243.5
170°	1255.5	1256.9	1256.7	1254.9	1253.0	1251.2	1249.4
172.5°	1259.9	1261.3	1261.1	1259.2	1257.4	1255.6	1253.8
175°	1264.6	1266.0	1265.7	1263.7	1261.7	1259.6	1257.6
177.5°	1264.9	1266.0	1265.8	1264.4	1262.9	1261.4	1260.0
180°	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2

(END OF REPORT)