

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331285

Luminaire Tested: **SA2XXDIP-C485D330U835-4F0-1E-UDD-A**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331285
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C485D330U835-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 330 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3454.4 lumens
Efficiency: N/A
Efficacy: 125.6 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 27.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331285
CATALOG NUMBER: SA2XXDIP-C485D330U835-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331285

CATALOG NUMBER: SA2XXDIP-C485D330U835-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	62				
1	101	97	93	90	95	91	88	85	80	77	75	70	68	66	60	59	58	53				
2	93	85	79	74	87	80	75	71	71	67	63	62	59	56	54	52	50	46				
3	85	76	68	63	79	71	65	60	63	58	54	55	52	48	48	45	43	39				
4	78	67	60	54	73	64	57	51	56	51	47	50	45	42	44	40	38	34				
5	72	60	52	46	67	57	50	45	51	45	41	45	40	37	40	36	33	30				
6	66	55	47	41	62	52	44	39	46	40	36	41	36	33	36	32	30	27				
7	62	49	42	36	58	47	40	35	42	36	32	37	33	29	33	29	27	24				
8	57	45	37	32	54	43	36	31	39	33	29	34	30	26	31	27	24	22				
9	54	41	34	29	50	39	33	28	35	30	26	32	27	24	28	25	22	20				
10	50	38	31	26	47	36	30	25	33	27	23	30	25	22	26	23	20	18				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15689	15689	15689	15689
5°	17590	15793	13994	15793
10°	20156	15662	12111	15662
15°	22298	15375	10700	15375
20°	21959	15067	9754	15067
25°	19800	14656	9155	14656
30°	16362	14001	8718	14001
35°	11925	13316	8406	13316
40°	9525	12507	8233	12507
45°	8323	11572	7999	11572
50°	7824	10665	7842	10665
55°	7212	9745	7631	9745
60°	6610	8767	7308	8767
65°	6021	7889	6991	7889
70°	5467	7034	6524	7034
75°	4847	6082	5777	6082
80°	4166	5040	4649	5040
85°	3742	3742	2760	3742



TEST NUMBER: P331285

CATALOG NUMBER: SA2XXDIP-C485D330U835-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	92.5	2.7
10°-20°	269.0	7.8
20°-30°	390.5	11.3
30°-40°	412.0	11.9
40°-50°	364.8	10.6
50°-60°	291.1	8.4
60°-70°	197.9	5.7
70°-80°	101.5	2.9
80°-90°	25.6	0.7
90°-100°	14.9	0.4
100°-110°	54.7	1.6
110°-120°	146.1	4.2
120°-130°	241.2	7.0
130°-140°	256.5	7.4
140°-150°	238.4	6.9
150°-160°	191.7	5.5
160°-170°	123.5	3.6
170°-180°	42.5	1.2
0°-30°	752.0	21.8
0°-40°	1164.1	33.7
0°-60°	1820.1	52.7
0°-90°	2145.0	62.1
90°-120°	215.7	6.2
90°-150°	951.8	27.6
90°-180°	1309.0	37.9
0°-180°	3454.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	972	972	972	972	972	
5°	1085	974	863	974	1085	108
15°	1334	920	640	920	1334	368
25°	1111	823	514	823	1111	502
35°	605	676	426	676	605	393
45°	364	507	350	507	364	287
55°	256	346	271	346	256	230
65°	158	206	183	206	158	157
75°	78	98	93	98	78	83
85°	20	20	15	20	20	22
90°	9	0	9	0	9	5
95°	14	21	14	21	14	13
105°	25	98	25	98	25	26
115°	26	186	26	186	26	66
125°	276	263	276	263	276	239
135°	336	325	336	325	336	259
145°	383	377	383	377	383	240
155°	416	416	416	416	416	192
165°	437	438	437	438	437	123
175°	445	448	445	448	445	42
180°	447	447	447	447	447	



TEST NUMBER: P331285

CATALOG NUMBER: SA2XXDIP-C485D330U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7
2.5°	1016.6	1016.9	1017.4	1012.7	1012.1	1012.1	1007.9	1004.3	1000.1	994.4	995.0
5°	1085.3	1089.4	1090.9	1086.4	1079.7	1078.9	1072.6	1062.1	1052.4	1044.6	1039.0
7.5°	1167.3	1168.9	1165.3	1159.4	1154.4	1145.4	1133.6	1122.0	1105.8	1090.9	1079.9
10°	1229.4	1231.7	1225.3	1216.7	1209.6	1199.2	1182.0	1164.4	1143.2	1122.6	1106.2
12.5°	1276.6	1282.2	1274.0	1272.9	1260.7	1246.4	1225.9	1217.0	1187.1	1158.5	1140.8
15°	1334.0	1333.6	1334.4	1327.3	1318.3	1316.1	1294.4	1270.9	1228.7	1211.9	1182.7
17.5°	1317.4	1323.1	1325.7	1325.6	1325.4	1324.0	1317.0	1302.2	1281.0	1253.8	1220.2
20°	1278.0	1285.4	1286.6	1295.2	1300.0	1306.4	1309.0	1304.9	1291.8	1269.0	1239.9
22.5°	1217.0	1219.1	1222.6	1236.0	1246.5	1262.4	1270.7	1284.5	1279.5	1268.4	1244.1
25°	1111.4	1107.7	1120.7	1127.5	1151.7	1177.1	1195.4	1215.6	1233.5	1244.4	1237.3
27.5°	984.6	979.0	998.6	1016.4	1036.1	1063.6	1092.1	1125.8	1153.8	1188.9	1200.9
30°	877.6	881.0	899.7	918.7	948.6	987.4	1019.5	1056.5	1096.5	1135.7	1162.9
32.5°	762.3	775.2	787.0	816.2	842.5	885.8	932.9	979.1	1029.0	1073.5	1115.7
35°	605.0	619.9	636.4	657.7	694.6	737.6	783.5	845.9	913.9	974.7	1024.8
37.5°	509.2	506.9	516.3	531.7	561.6	596.3	649.1	710.8	790.8	862.3	932.9
40°	451.9	450.4	457.1	471.3	494.1	519.5	565.8	619.9	694.3	781.6	865.7
42.5°	412.4	413.3	417.1	427.1	442.7	463.6	498.3	544.4	612.4	694.7	785.0
45°	364.5	367.1	371.2	376.1	385.0	402.2	421.6	454.5	508.3	577.0	665.9
47.5°	330.0	330.1	334.2	338.5	343.8	353.5	369.4	390.0	427.9	483.9	560.3
50°	311.5	308.8	311.8	315.2	320.8	327.5	338.0	357.4	382.8	428.0	491.8
52.5°	288.8	288.8	291.5	292.8	297.8	304.5	314.1	327.5	350.5	385.9	438.4
55°	256.2	258.1	259.6	261.8	266.3	271.1	278.6	287.6	305.5	332.0	370.8
57.5°	225.6	226.2	227.7	231.9	234.8	239.2	246.3	254.5	266.1	285.8	315.0
60°	204.7	204.7	207.6	209.5	213.2	217.7	223.3	231.2	241.6	257.7	281.2
62.5°	185.5	185.2	186.4	189.5	192.3	196.5	202.1	208.8	218.6	232.9	252.2
65°	157.6	156.9	159.1	159.8	162.8	166.9	171.4	178.5	186.4	196.8	214.0
67.5°	130.7	131.6	132.8	134.2	135.9	140.2	143.2	148.2	154.8	163.5	175.2
70°	115.8	115.8	115.8	116.9	119.1	121.4	124.4	128.5	134.8	142.3	152.7
72.5°	99.0	100.2	101.4	100.8	103.6	104.9	108.5	110.8	116.9	121.7	130.9
75°	77.7	77.7	77.7	79.5	80.7	81.8	84.0	86.3	89.3	95.2	100.1
77.5°	58.0	57.8	58.2	58.6	59.8	61.2	61.8	63.9	66.6	69.4	73.5
80°	44.8	45.6	45.9	46.7	46.7	47.4	47.8	50.4	52.3	54.2	56.8
82.5°	34.7	34.8	34.9	35.0	35.3	35.8	36.7	37.6	38.2	39.8	41.8
85°	20.2	19.8	19.8	20.5	20.2	20.2	20.9	21.7	21.7	22.0	23.2
87.5°	9.5	9.5	9.8	9.4	9.4	9.6	9.6	9.2	9.4	9.7	9.8
90°	8.7	8.6	8.4	8.3	8.2	7.9	7.5	7.2	6.8	6.5	5.9
92.5°	8.7	8.6	8.6	8.5	8.4	8.2	8.1	7.9	7.7	7.5	7.2
95°	13.9	14.0	14.0	14.1	14.2	14.0	13.7	13.3	13.0	12.6	12.1
97.5°	18.6	18.5	18.4	18.3	18.2	18.0	17.7	17.5	17.2	16.9	15.7
100°	21.7	21.5	21.4	21.2	21.1	20.7	20.2	19.6	19.0	18.4	17.2
102.5°	23.2	23.0	22.8	22.6	22.4	21.9	21.2	20.4	19.7	18.9	29.2
105°	24.6	24.3	24.0	23.7	23.4	22.9	22.1	21.3	20.5	19.7	39.3
107.5°	25.3	25.0	24.7	24.4	24.1	24.4	25.2	26.0	26.8	27.6	51.1
110°	25.5	25.3	25.0	24.7	24.4	27.8	35.0	42.2	49.4	56.6	77.3



TEST NUMBER: P331285

CATALOG NUMBER: SA2XXDIP-C485D330U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	25.8	25.6	25.3	25.1	24.9	37.9	64.1	90.3	116.5	142.7	147.8
115°	26.5	31.7	36.9	42.0	47.2	66.4	99.7	133.0	166.2	199.5	197.7
117.5°	108.3	125.3	142.3	159.3	176.3	188.8	196.8	204.9	212.9	221.0	219.7
120°	197.2	206.9	216.6	226.3	236.0	240.4	239.6	238.7	237.9	237.0	235.7
122.5°	246.1	248.0	249.9	251.8	253.6	254.3	253.8	253.3	252.8	252.3	250.9
125°	276.4	276.2	276.0	275.8	275.6	275.2	274.7	274.2	273.7	273.2	271.8
127.5°	295.6	295.5	295.5	295.5	295.4	295.0	294.3	293.6	292.8	292.1	291.1
130°	307.5	307.6	307.6	307.7	307.8	307.4	306.6	305.8	305.0	304.3	303.5
132.5°	319.1	319.2	319.3	319.3	319.4	319.1	318.4	317.8	317.1	316.4	315.6
135°	335.9	336.1	336.2	336.4	336.5	336.2	335.5	334.8	334.1	333.4	332.7
137.5°	351.3	351.5	351.8	352.0	352.2	352.0	351.3	350.6	349.9	349.2	348.5
140°	360.8	361.2	361.6	361.9	362.3	362.1	361.5	360.8	360.2	359.5	358.8
142.5°	370.1	370.5	370.9	371.2	371.6	371.5	370.9	370.3	369.7	369.1	368.2
145°	383.1	383.5	383.9	384.2	384.6	384.5	384.0	383.5	383.0	382.5	381.3
147.5°	394.6	394.9	395.2	395.5	395.8	395.8	395.4	395.0	394.6	394.3	393.1
150°	401.6	401.9	402.3	402.7	403.0	403.0	402.5	402.1	401.7	401.3	400.1
152.5°	407.5	408.0	408.5	408.9	409.4	409.4	409.0	408.6	408.1	407.7	406.6
155°	415.8	416.4	417.0	417.5	418.1	418.2	417.7	417.3	416.9	416.4	415.6
157.5°	423.4	423.9	424.5	425.0	425.6	425.6	425.2	424.7	424.2	423.7	423.1
160°	427.8	428.3	428.8	429.3	429.8	429.8	429.4	429.0	428.5	428.1	427.7
162.5°	431.4	432.0	432.6	433.2	433.9	433.9	433.4	432.9	432.5	432.0	431.6
165°	436.8	437.3	437.8	438.3	438.8	438.8	438.3	437.8	437.3	436.8	436.6
167.5°	440.2	440.9	441.5	442.2	442.8	442.9	442.4	441.9	441.4	440.9	440.7
170°	442.3	443.0	443.6	444.3	444.9	445.0	444.5	444.0	443.5	443.0	442.8
172.5°	443.9	444.5	445.2	445.8	446.5	446.5	446.0	445.5	445.0	444.5	444.4
175°	445.2	445.9	446.7	447.4	448.1	448.2	447.7	447.2	446.7	446.2	446.1
177.5°	446.1	446.6	447.1	447.6	448.1	448.2	447.8	447.4	447.0	446.6	446.5
180°	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8



TEST NUMBER: P331285

CATALOG NUMBER: SA2XXDIP-C485D330U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7
2.5°	997.1	994.7	993.2	987.9	983.1	978.3	976.8	977.4	970.8	964.6	961.9
5°	1036.0	1028.5	1021.4	1011.3	999.4	986.3	979.6	974.4	961.3	947.1	938.9
7.5°	1070.8	1060.1	1046.4	1027.5	1010.1	989.5	976.4	964.9	945.7	925.7	913.5
10°	1092.0	1077.4	1059.9	1036.7	1015.4	990.4	972.9	955.3	932.9	909.0	894.1
12.5°	1110.2	1090.6	1073.3	1043.6	1018.4	987.1	966.3	941.6	918.0	889.6	874.9
15°	1153.6	1117.4	1084.5	1050.9	1019.9	976.2	953.1	919.8	888.8	853.7	836.9
17.5°	1187.1	1146.4	1094.7	1052.0	1015.8	967.4	933.4	893.6	856.9	816.8	794.0
20°	1206.3	1159.6	1103.9	1053.2	1009.8	954.6	917.6	876.9	833.9	788.7	764.1
22.5°	1217.6	1168.6	1113.5	1048.7	997.9	944.1	897.6	853.0	809.4	760.7	734.8
25°	1221.2	1176.4	1118.1	1044.9	982.9	922.1	866.0	822.7	770.1	724.5	686.8
27.5°	1203.4	1171.3	1115.3	1037.9	965.7	894.5	832.1	783.0	727.4	678.0	640.0
30°	1181.6	1162.9	1108.4	1030.7	951.9	875.4	806.7	751.0	695.8	645.7	606.9
32.5°	1147.9	1143.8	1095.9	1020.6	937.3	851.2	780.1	723.8	662.6	613.4	576.4
35°	1081.5	1099.5	1069.2	997.9	909.7	816.8	739.8	675.6	612.1	565.0	530.3
37.5°	992.7	1037.2	1029.3	964.6	872.5	779.3	694.3	627.2	566.7	519.2	485.1
40°	931.4	988.2	996.4	939.2	846.3	750.3	660.3	593.4	534.4	491.1	456.7
42.5°	865.7	932.0	954.6	908.8	817.6	719.8	629.8	560.6	502.2	460.0	429.6
45°	755.5	843.3	884.0	857.8	769.7	669.6	577.0	506.8	453.8	414.2	390.6
47.5°	652.5	748.4	803.2	793.9	716.4	617.3	525.8	458.4	406.8	375.2	354.1
50°	579.6	678.2	744.3	747.3	678.2	580.0	488.1	424.6	377.2	347.7	330.5
52.5°	516.3	610.4	682.5	698.3	635.5	541.1	454.3	391.2	349.4	322.3	306.9
55°	433.6	513.1	593.1	622.2	571.8	482.1	401.8	346.2	307.0	288.3	274.9
57.5°	360.5	426.8	500.6	532.8	501.7	425.0	349.7	301.4	269.6	253.2	242.9
60°	321.9	374.2	439.9	478.4	451.5	383.2	317.4	271.5	245.4	230.8	221.1
62.5°	286.1	332.4	387.9	423.1	408.5	344.0	285.2	244.6	222.1	208.4	201.4
65°	236.0	272.6	315.6	348.1	338.4	289.4	241.3	206.5	188.6	177.8	172.2
67.5°	194.3	220.8	250.6	279.0	271.2	236.5	197.9	170.8	157.4	148.1	144.8
70°	168.1	188.2	214.7	237.5	231.2	202.8	172.2	149.0	137.4	129.6	126.2
72.5°	143.0	159.5	179.8	198.4	194.1	170.5	145.0	127.5	118.6	111.4	108.6
75°	107.9	120.6	133.0	145.3	144.2	125.9	110.9	97.5	90.4	84.8	83.7
77.5°	79.7	86.8	95.2	102.5	100.5	90.0	78.3	70.6	65.4	61.6	61.0
80°	60.9	65.0	71.0	76.2	73.6	69.1	59.8	54.2	50.4	46.7	45.2
82.5°	44.1	48.3	51.8	54.7	52.7	48.5	42.7	38.9	36.7	34.1	33.5
85°	23.2	25.4	26.9	27.6	26.9	24.3	21.7	20.2	18.3	17.2	16.8
87.5°	10.0	9.9	9.8	10.3	9.2	9.0	7.7	6.6	6.5	6.4	5.9
90°	5.3	4.7	4.2	3.5	2.7	1.9	1.1	0.3	1.1	1.9	2.7
92.5°	6.9	6.6	6.4	6.2	6.3	6.4	6.5	6.5	6.5	6.4	6.3
95°	11.6	11.1	10.6	11.5	13.9	16.3	18.6	21.0	18.6	16.3	13.9
97.5°	14.5	13.4	12.2	15.0	21.7	28.3	35.0	41.7	35.0	28.3	21.7
100°	16.0	14.8	13.5	17.9	27.7	37.5	47.4	57.2	47.4	37.5	27.7
102.5°	39.4	49.6	59.8	66.0	68.1	70.1	72.2	74.3	72.2	70.1	68.1
105°	59.0	78.6	98.2	106.9	104.8	102.6	100.4	98.3	100.4	102.6	104.8
107.5°	74.7	98.2	121.7	132.6	130.9	129.1	127.4	125.6	127.4	129.1	130.9
110°	98.1	118.9	139.6	149.3	147.8	146.3	144.7	143.2	144.7	146.3	147.8



TEST NUMBER: P331285

CATALOG NUMBER: SA2XXDIP-C485D330U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	153.0	158.1	163.2	165.1	163.8	162.5	161.1	159.8	161.1	162.5	163.8
115°	195.9	194.1	192.3	190.8	189.6	188.4	187.1	185.9	187.1	188.4	189.6
117.5°	218.5	217.3	216.0	214.7	213.4	212.0	210.6	209.3	210.6	212.0	213.4
120°	234.4	233.1	231.8	230.6	229.6	228.5	227.4	226.3	227.4	228.5	229.6
122.5°	249.4	248.0	246.6	245.4	244.2	243.1	242.0	240.8	242.0	243.1	244.2
125°	270.5	269.1	267.8	266.6	265.7	264.7	263.8	262.9	263.8	264.7	265.7
127.5°	290.1	289.0	288.0	287.0	286.0	284.9	283.9	282.8	283.9	284.9	286.0
130°	302.7	301.9	301.1	300.1	299.0	297.8	296.7	295.5	296.7	297.8	299.0
132.5°	314.8	314.0	313.2	312.4	311.4	310.4	309.4	308.5	309.4	310.4	311.4
135°	332.1	331.4	330.8	329.9	328.7	327.6	326.4	325.3	326.4	327.6	328.7
137.5°	347.7	347.0	346.3	345.5	344.7	343.9	343.1	342.3	343.1	343.9	344.7
140°	358.0	357.2	356.4	355.7	355.1	354.5	354.0	353.4	354.0	354.5	355.1
142.5°	367.3	366.4	365.5	364.8	364.3	363.7	363.2	362.7	363.2	363.7	364.3
145°	380.1	378.8	377.6	377.0	377.1	377.2	377.3	377.3	377.3	377.2	377.1
147.5°	391.9	390.6	389.4	389.0	389.2	389.5	389.8	390.1	389.8	389.5	389.2
150°	399.0	397.8	396.7	396.3	396.8	397.3	397.8	398.3	397.8	397.3	396.8
152.5°	405.5	404.4	403.3	403.1	403.6	404.2	404.8	405.3	404.8	404.2	403.6
155°	414.7	413.9	413.0	412.9	413.5	414.2	414.8	415.5	414.8	414.2	413.5
157.5°	422.5	421.9	421.3	421.2	421.8	422.3	422.9	423.4	422.9	422.3	421.8
160°	427.2	426.8	426.4	426.4	426.8	427.2	427.7	428.1	427.7	427.2	426.8
162.5°	431.2	430.8	430.5	430.5	430.9	431.4	431.8	432.2	431.8	431.4	430.9
165°	436.4	436.2	436.0	436.1	436.5	436.9	437.4	437.8	437.4	436.9	436.5
167.5°	440.5	440.3	440.1	440.2	440.6	441.1	441.5	441.9	441.5	441.1	440.6
170°	442.7	442.5	442.4	442.5	443.0	443.4	443.8	444.3	443.8	443.4	443.0
172.5°	444.2	444.1	443.9	444.1	444.5	444.9	445.4	445.8	445.4	444.9	444.5
175°	445.9	445.8	445.6	445.8	446.3	446.8	447.3	447.8	447.3	446.8	446.3
177.5°	446.5	446.4	446.4	446.5	446.9	447.3	447.7	448.1	447.7	447.3	446.9
180°	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8



TEST NUMBER: P331285

CATALOG NUMBER: SA2XXDIP-C485D330U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7
2.5°	958.9	957.1	950.8	947.5	942.2	937.1	933.8	935.3	936.5	935.9	935.0
5°	931.4	924.3	913.5	904.1	897.4	885.1	879.9	877.3	875.0	872.4	869.8
7.5°	898.7	887.5	872.0	858.7	846.1	830.8	822.1	816.8	811.4	805.5	800.3
10°	875.4	859.7	843.3	824.6	809.7	795.8	783.5	775.3	767.8	760.7	755.5
12.5°	850.9	832.8	812.5	787.0	770.5	750.7	748.9	734.4	722.7	718.3	712.2
15°	811.9	786.5	760.7	730.5	717.4	699.5	688.3	677.1	667.0	659.9	658.0
17.5°	767.6	734.7	709.1	687.4	666.0	647.6	637.3	628.3	620.0	610.5	609.3
20°	733.8	705.5	677.5	658.4	636.4	617.7	605.0	596.0	588.9	583.3	578.5
22.5°	701.9	670.8	645.2	624.3	602.6	587.5	577.5	568.9	563.0	556.8	552.2
25°	650.6	626.3	598.3	574.8	556.8	547.1	538.9	531.4	527.7	523.6	518.4
27.5°	605.7	578.7	552.5	534.3	518.5	509.9	504.1	499.0	495.5	493.1	490.1
30°	574.0	546.7	526.2	508.3	495.2	486.6	482.9	479.9	475.8	474.3	472.8
32.5°	543.5	519.0	501.4	485.9	473.4	467.8	464.4	461.7	458.5	457.0	454.0
35°	500.4	479.9	462.7	454.1	444.0	439.2	436.6	432.8	429.9	428.4	428.0
37.5°	459.9	442.0	430.7	419.7	415.4	412.4	408.9	406.3	405.4	405.2	404.8
40°	433.6	419.0	408.9	400.0	398.1	393.6	390.6	388.4	388.4	388.8	388.4
42.5°	409.7	396.6	387.7	380.0	377.8	375.1	372.1	372.0	372.6	373.8	372.6
45°	373.5	364.1	357.8	354.0	349.9	347.3	346.9	348.1	348.4	348.8	349.9
47.5°	340.1	333.9	328.2	324.1	322.3	321.8	321.4	323.3	325.1	325.8	327.5
50°	320.4	313.3	308.5	305.9	304.4	303.6	304.4	306.6	308.1	310.0	311.1
52.5°	298.3	293.3	290.0	287.9	287.3	287.8	287.9	290.5	292.9	293.5	294.1
55°	267.8	264.0	263.3	259.9	261.4	261.0	262.9	264.4	266.6	268.9	269.3
57.5°	237.3	234.3	232.3	232.6	233.0	234.7	236.2	238.9	241.3	243.6	243.9
60°	217.0	215.5	214.4	214.4	215.1	217.4	219.2	221.8	223.3	224.8	225.9
62.5°	198.5	197.0	195.8	196.4	198.4	199.7	201.9	203.3	204.8	206.3	206.8
65°	169.2	168.4	169.6	170.3	170.7	172.5	175.2	176.3	177.8	178.5	181.1
67.5°	142.2	142.4	142.2	143.3	145.4	145.9	148.3	151.0	151.3	152.7	154.4
70°	124.0	124.7	125.5	126.2	128.1	128.8	130.7	131.8	133.3	134.4	135.6
72.5°	107.3	107.4	108.2	108.0	109.6	111.2	112.8	113.9	115.4	116.8	117.9
75°	82.5	82.5	83.3	83.7	85.5	87.4	87.0	87.8	89.3	90.8	91.5
77.5°	60.3	59.5	60.3	60.6	61.2	62.8	63.1	64.2	65.9	65.4	66.2
80°	45.9	44.8	45.9	46.3	46.3	48.2	48.2	48.9	50.0	48.9	50.0
82.5°	32.8	32.3	33.1	33.2	33.8	33.8	34.4	34.6	35.7	35.2	35.7
85°	16.4	16.1	16.4	16.1	16.4	16.8	16.8	16.4	16.4	17.2	16.1
87.5°	5.8	5.6	5.4	5.5	5.4	5.2	5.0	5.0	5.1	4.6	4.6
90°	3.5	4.2	4.7	5.3	5.9	6.5	6.8	7.2	7.5	7.9	8.2
92.5°	6.2	6.4	6.6	6.9	7.2	7.5	7.7	7.9	8.1	8.2	8.4
95°	11.5	10.6	11.1	11.6	12.1	12.6	13.0	13.3	13.7	14.0	14.2
97.5°	15.0	12.2	13.4	14.5	15.7	16.9	17.2	17.5	17.7	18.0	18.2
100°	17.9	13.5	14.8	16.0	17.2	18.4	19.0	19.6	20.2	20.7	21.1
102.5°	66.0	59.8	49.6	39.4	29.2	18.9	19.7	20.4	21.2	21.9	22.4
105°	106.9	98.2	78.6	59.0	39.3	19.7	20.5	21.3	22.1	22.9	23.4
107.5°	132.6	121.7	98.2	74.7	51.1	27.6	26.8	26.0	25.2	24.4	24.1
110°	149.3	139.6	118.9	98.1	77.3	56.6	49.4	42.2	35.0	27.8	24.4



TEST NUMBER: P331285

CATALOG NUMBER: SA2XXDIP-C485D330U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	165.1	163.2	158.1	153.0	147.8	142.7	116.5	90.3	64.1	37.9	24.9
115°	190.8	192.3	194.1	195.9	197.7	199.5	166.2	133.0	99.7	66.4	47.2
117.5°	214.7	216.0	217.3	218.5	219.7	221.0	212.9	204.9	196.8	188.8	176.3
120°	230.6	231.8	233.1	234.4	235.7	237.0	237.9	238.7	239.6	240.4	236.0
122.5°	245.4	246.6	248.0	249.4	250.9	252.3	252.8	253.3	253.8	254.3	253.6
125°	266.6	267.8	269.1	270.5	271.8	273.2	273.7	274.2	274.7	275.2	275.6
127.5°	287.0	288.0	289.0	290.1	291.1	292.1	292.8	293.6	294.3	295.0	295.4
130°	300.1	301.1	301.9	302.7	303.5	304.3	305.0	305.8	306.6	307.4	307.8
132.5°	312.4	313.2	314.0	314.8	315.6	316.4	317.1	317.8	318.4	319.1	319.4
135°	329.9	330.8	331.4	332.1	332.7	333.4	334.1	334.8	335.5	336.2	336.5
137.5°	345.5	346.3	347.0	347.7	348.5	349.2	349.9	350.6	351.3	352.0	352.2
140°	355.7	356.4	357.2	358.0	358.8	359.5	360.2	360.8	361.5	362.1	362.3
142.5°	364.8	365.5	366.4	367.3	368.2	369.1	369.7	370.3	370.9	371.5	371.6
145°	377.0	377.6	378.8	380.1	381.3	382.5	383.0	383.5	384.0	384.5	384.6
147.5°	389.0	389.4	390.6	391.9	393.1	394.3	394.6	395.0	395.4	395.8	395.8
150°	396.3	396.7	397.8	399.0	400.1	401.3	401.7	402.1	402.5	403.0	403.0
152.5°	403.1	403.3	404.4	405.5	406.6	407.7	408.1	408.6	409.0	409.4	409.4
155°	412.9	413.0	413.9	414.7	415.6	416.4	416.9	417.3	417.7	418.2	418.1
157.5°	421.2	421.3	421.9	422.5	423.1	423.7	424.2	424.7	425.2	425.6	425.6
160°	426.4	426.4	426.8	427.2	427.7	428.1	428.5	429.0	429.4	429.8	429.8
162.5°	430.5	430.5	430.8	431.2	431.6	432.0	432.5	432.9	433.4	433.9	433.9
165°	436.1	436.0	436.2	436.4	436.6	436.8	437.3	437.8	438.3	438.8	438.8
167.5°	440.2	440.1	440.3	440.5	440.7	440.9	441.4	441.9	442.4	442.9	442.8
170°	442.5	442.4	442.5	442.7	442.8	443.0	443.5	444.0	444.5	445.0	444.9
172.5°	444.1	443.9	444.1	444.2	444.4	444.5	445.0	445.5	446.0	446.5	446.5
175°	445.8	445.6	445.8	445.9	446.1	446.2	446.7	447.2	447.7	448.2	448.1
177.5°	446.5	446.4	446.4	446.5	446.5	446.6	447.0	447.4	447.8	448.2	448.1
180°	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8



TEST NUMBER: P331285

CATALOG NUMBER: SA2XXDIP-C485D330U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7
2.5°	932.0	931.4	931.4	928.7	931.4	931.4	932.0	935.0	935.9	936.5	935.3
5°	864.6	863.4	861.6	863.4	861.6	863.4	864.6	869.8	872.4	875.0	877.3
7.5°	797.9	793.4	792.7	788.3	792.7	793.4	797.9	800.3	805.5	811.4	816.8
10°	749.2	746.2	745.8	738.7	745.8	746.2	749.2	755.5	760.7	767.8	775.3
12.5°	712.1	704.9	706.4	702.3	706.4	704.9	712.1	712.2	718.3	722.7	734.4
15°	647.9	647.9	646.5	640.1	646.5	647.9	647.9	658.0	659.9	667.0	677.1
17.5°	601.9	601.1	597.5	599.3	597.5	601.1	601.9	609.3	610.5	620.0	628.3
20°	574.4	572.1	567.7	567.7	567.7	572.1	574.4	578.5	583.3	588.9	596.0
22.5°	548.4	548.2	543.5	545.0	543.5	548.2	548.4	552.2	556.8	563.0	568.9
25°	518.0	515.0	512.8	513.9	512.8	515.0	518.0	518.4	523.6	527.7	531.4
27.5°	489.2	487.5	487.4	484.3	487.4	487.5	489.2	490.1	493.1	495.5	499.0
30°	472.4	468.7	469.4	467.6	469.4	468.7	472.4	472.8	474.3	475.8	479.9
32.5°	453.3	452.0	451.2	449.6	451.2	452.0	453.3	454.0	457.0	458.5	461.7
35°	427.2	427.6	425.7	426.5	425.7	427.6	427.2	428.0	428.4	429.9	432.8
37.5°	404.5	405.7	404.8	405.0	404.8	405.7	404.5	404.8	405.2	405.4	406.3
40°	389.5	389.5	389.5	390.6	389.5	389.5	389.5	388.4	388.8	388.4	388.4
42.5°	375.2	374.6	374.0	373.9	374.0	374.6	375.2	372.6	373.8	372.6	372.0
45°	350.7	351.8	352.2	350.3	352.2	351.8	350.7	349.9	348.8	348.4	348.1
47.5°	328.5	328.6	328.5	330.1	328.5	328.6	328.5	327.5	325.8	325.1	323.3
50°	313.0	312.2	313.0	312.2	313.0	312.2	313.0	311.1	310.0	308.1	306.6
52.5°	296.5	296.7	296.2	296.1	296.2	296.7	296.5	294.1	293.5	292.9	290.5
55°	270.8	271.5	271.1	271.1	271.1	271.5	270.8	269.3	268.9	266.6	264.4
57.5°	244.1	244.8	245.3	243.6	245.3	244.8	244.1	243.9	243.6	241.3	238.9
60°	225.6	227.4	227.1	226.3	227.1	227.4	225.6	225.9	224.8	223.3	221.8
62.5°	208.5	209.2	209.1	209.0	209.1	209.2	208.5	206.8	206.3	204.8	203.3
65°	182.2	183.0	181.9	183.0	181.9	183.0	182.2	181.1	178.5	177.8	176.3
67.5°	153.9	154.2	155.0	155.5	155.0	154.2	153.9	154.4	152.7	151.3	151.0
70°	136.3	135.9	137.1	138.2	137.1	135.9	136.3	135.6	134.4	133.3	131.8
72.5°	117.8	118.6	118.2	119.1	118.2	118.6	117.8	117.9	116.8	115.4	113.9
75°	90.8	91.9	91.5	92.6	91.5	91.9	90.8	91.5	90.8	89.3	87.8
77.5°	65.6	65.7	65.6	66.2	65.6	65.7	65.6	66.2	65.4	65.9	64.2
80°	50.0	49.3	48.5	50.0	48.5	49.3	50.0	50.0	48.9	50.0	48.9
82.5°	34.8	35.3	34.5	34.5	34.5	35.3	34.8	35.7	35.2	35.7	34.6
85°	16.1	15.7	14.9	14.9	14.9	15.7	16.1	16.1	17.2	16.4	16.4
87.5°	4.6	4.4	4.4	4.1	4.4	4.4	4.6	4.6	4.6	5.1	5.0
90°	8.3	8.4	8.6	8.7	8.6	8.4	8.3	8.2	7.9	7.5	7.2
92.5°	8.5	8.6	8.6	8.7	8.6	8.6	8.5	8.4	8.2	8.1	7.9
95°	14.1	14.0	14.0	13.9	14.0	14.0	14.1	14.2	14.0	13.7	13.3
97.5°	18.3	18.4	18.5	18.6	18.5	18.4	18.3	18.2	18.0	17.7	17.5
100°	21.2	21.4	21.5	21.7	21.5	21.4	21.2	21.1	20.7	20.2	19.6
102.5°	22.6	22.8	23.0	23.2	23.0	22.8	22.6	22.4	21.9	21.2	20.4
105°	23.7	24.0	24.3	24.6	24.3	24.0	23.7	23.4	22.9	22.1	21.3
107.5°	24.4	24.7	25.0	25.3	25.0	24.7	24.4	24.1	24.4	25.2	26.0
110°	24.7	25.0	25.3	25.5	25.3	25.0	24.7	24.4	27.8	35.0	42.2



TEST NUMBER: P331285

CATALOG NUMBER: SA2XXDIP-C485D330U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	25.1	25.3	25.6	25.8	25.6	25.3	25.1	24.9	37.9	64.1	90.3
115°	42.0	36.9	31.7	26.5	31.7	36.9	42.0	47.2	66.4	99.7	133.0
117.5°	159.3	142.3	125.3	108.3	125.3	142.3	159.3	176.3	188.8	196.8	204.9
120°	226.3	216.6	206.9	197.2	206.9	216.6	226.3	236.0	240.4	239.6	238.7
122.5°	251.8	249.9	248.0	246.1	248.0	249.9	251.8	253.6	254.3	253.8	253.3
125°	275.8	276.0	276.2	276.4	276.2	276.0	275.8	275.6	275.2	274.7	274.2
127.5°	295.5	295.5	295.5	295.6	295.5	295.5	295.5	295.4	295.0	294.3	293.6
130°	307.7	307.6	307.6	307.5	307.6	307.6	307.7	307.8	307.4	306.6	305.8
132.5°	319.3	319.3	319.2	319.1	319.2	319.3	319.3	319.4	319.1	318.4	317.8
135°	336.4	336.2	336.1	335.9	336.1	336.2	336.4	336.5	336.2	335.5	334.8
137.5°	352.0	351.8	351.5	351.3	351.5	351.8	352.0	352.2	352.0	351.3	350.6
140°	361.9	361.6	361.2	360.8	361.2	361.6	361.9	362.3	362.1	361.5	360.8
142.5°	371.2	370.9	370.5	370.1	370.5	370.9	371.2	371.6	371.5	370.9	370.3
145°	384.2	383.9	383.5	383.1	383.5	383.9	384.2	384.6	384.5	384.0	383.5
147.5°	395.5	395.2	394.9	394.6	394.9	395.2	395.5	395.8	395.8	395.4	395.0
150°	402.7	402.3	401.9	401.6	401.9	402.3	402.7	403.0	403.0	402.5	402.1
152.5°	408.9	408.5	408.0	407.5	408.0	408.5	408.9	409.4	409.4	409.0	408.6
155°	417.5	417.0	416.4	415.8	416.4	417.0	417.5	418.1	418.2	417.7	417.3
157.5°	425.0	424.5	423.9	423.4	423.9	424.5	425.0	425.6	425.6	425.2	424.7
160°	429.3	428.8	428.3	427.8	428.3	428.8	429.3	429.8	429.8	429.4	429.0
162.5°	433.2	432.6	432.0	431.4	432.0	432.6	433.2	433.9	433.9	433.4	432.9
165°	438.3	437.8	437.3	436.8	437.3	437.8	438.3	438.8	438.8	438.3	437.8
167.5°	442.2	441.5	440.9	440.2	440.9	441.5	442.2	442.8	442.9	442.4	441.9
170°	444.3	443.6	443.0	442.3	443.0	443.6	444.3	444.9	445.0	444.5	444.0
172.5°	445.8	445.2	444.5	443.9	444.5	445.2	445.8	446.5	446.5	446.0	445.5
175°	447.4	446.7	445.9	445.2	445.9	446.7	447.4	448.1	448.2	447.7	447.2
177.5°	447.6	447.1	446.6	446.1	446.6	447.1	447.6	448.1	448.2	447.8	447.4
180°	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8



TEST NUMBER: P331285

CATALOG NUMBER: SA2XXDIP-C485D330U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7
2.5°	933.8	937.1	942.2	947.5	950.8	957.1	958.9	961.9	964.6	970.8	977.4
5°	879.9	885.1	897.4	904.1	913.5	924.3	931.4	938.9	947.1	961.3	974.4
7.5°	822.1	830.8	846.1	858.7	872.0	887.5	898.7	913.5	925.7	945.7	964.9
10°	783.5	795.8	809.7	824.6	843.3	859.7	875.4	894.1	909.0	932.9	955.3
12.5°	748.9	750.7	770.5	787.0	812.5	832.8	850.9	874.9	889.6	918.0	941.6
15°	688.3	699.5	717.4	730.5	760.7	786.5	811.9	836.9	853.7	888.8	919.8
17.5°	637.3	647.6	666.0	687.4	709.1	734.7	767.6	794.0	816.8	856.9	893.6
20°	605.0	617.7	636.4	658.4	677.5	705.5	733.8	764.1	788.7	833.9	876.9
22.5°	577.5	587.5	602.6	624.3	645.2	670.8	701.9	734.8	760.7	809.4	853.0
25°	538.9	547.1	556.8	574.8	598.3	626.3	650.6	686.8	724.5	770.1	822.7
27.5°	504.1	509.9	518.5	534.3	552.5	578.7	605.7	640.0	678.0	727.4	783.0
30°	482.9	486.6	495.2	508.3	526.2	546.7	574.0	606.9	645.7	695.8	751.0
32.5°	464.4	467.8	473.4	485.9	501.4	519.0	543.5	576.4	613.4	662.6	723.8
35°	436.6	439.2	444.0	454.1	462.7	479.9	500.4	530.3	565.0	612.1	675.6
37.5°	408.9	412.4	415.4	419.7	430.7	442.0	459.9	485.1	519.2	566.7	627.2
40°	390.6	393.6	398.1	400.0	408.9	419.0	433.6	456.7	491.1	534.4	593.4
42.5°	372.1	375.1	377.8	380.0	387.7	396.6	409.7	429.6	460.0	502.2	560.6
45°	346.9	347.3	349.9	354.0	357.8	364.1	373.5	390.6	414.2	453.8	506.8
47.5°	321.4	321.8	322.3	324.1	328.2	333.9	340.1	354.1	375.2	406.8	458.4
50°	304.4	303.6	304.4	305.9	308.5	313.3	320.4	330.5	347.7	377.2	424.6
52.5°	287.9	287.8	287.3	287.9	290.0	293.3	298.3	306.9	322.3	349.4	391.2
55°	262.9	261.0	261.4	259.9	263.3	264.0	267.8	274.9	288.3	307.0	346.2
57.5°	236.2	234.7	233.0	232.6	232.3	234.3	237.3	242.9	253.2	269.6	301.4
60°	219.2	217.4	215.1	214.4	214.4	215.5	217.0	221.1	230.8	245.4	271.5
62.5°	201.9	199.7	198.4	196.4	195.8	197.0	198.5	201.4	208.4	222.1	244.6
65°	175.2	172.5	170.7	170.3	169.6	168.4	169.2	172.2	177.8	188.6	206.5
67.5°	148.3	145.9	145.4	143.3	142.2	142.4	142.2	144.8	148.1	157.4	170.8
70°	130.7	128.8	128.1	126.2	125.5	124.7	124.0	126.2	129.6	137.4	149.0
72.5°	112.8	111.2	109.6	108.0	108.2	107.4	107.3	108.6	111.4	118.6	127.5
75°	87.0	87.4	85.5	83.7	83.3	82.5	82.5	83.7	84.8	90.4	97.5
77.5°	63.1	62.8	61.2	60.6	60.3	59.5	60.3	61.0	61.6	65.4	70.6
80°	48.2	48.2	46.3	46.3	45.9	44.8	45.9	45.2	46.7	50.4	54.2
82.5°	34.4	33.8	33.8	33.2	33.1	32.3	32.8	33.5	34.1	36.7	38.9
85°	16.8	16.8	16.4	16.1	16.4	16.1	16.4	16.8	17.2	18.3	20.2
87.5°	5.0	5.2	5.4	5.5	5.4	5.6	5.8	5.9	6.4	6.5	6.6
90°	6.8	6.5	5.9	5.3	4.7	4.2	3.5	2.7	1.9	1.1	0.3
92.5°	7.7	7.5	7.2	6.9	6.6	6.4	6.2	6.3	6.4	6.5	6.5
95°	13.0	12.6	12.1	11.6	11.1	10.6	11.5	13.9	16.3	18.6	21.0
97.5°	17.2	16.9	15.7	14.5	13.4	12.2	15.0	21.7	28.3	35.0	41.7
100°	19.0	18.4	17.2	16.0	14.8	13.5	17.9	27.7	37.5	47.4	57.2
102.5°	19.7	18.9	29.2	39.4	49.6	59.8	66.0	68.1	70.1	72.2	74.3
105°	20.5	19.7	39.3	59.0	78.6	98.2	106.9	104.8	102.6	100.4	98.3
107.5°	26.8	27.6	51.1	74.7	98.2	121.7	132.6	130.9	129.1	127.4	125.6
110°	49.4	56.6	77.3	98.1	118.9	139.6	149.3	147.8	146.3	144.7	143.2



TEST NUMBER: P331285

CATALOG NUMBER: SA2XXDIP-C485D330U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	116.5	142.7	147.8	153.0	158.1	163.2	165.1	163.8	162.5	161.1	159.8
115°	166.2	199.5	197.7	195.9	194.1	192.3	190.8	189.6	188.4	187.1	185.9
117.5°	212.9	221.0	219.7	218.5	217.3	216.0	214.7	213.4	212.0	210.6	209.3
120°	237.9	237.0	235.7	234.4	233.1	231.8	230.6	229.6	228.5	227.4	226.3
122.5°	252.8	252.3	250.9	249.4	248.0	246.6	245.4	244.2	243.1	242.0	240.8
125°	273.7	273.2	271.8	270.5	269.1	267.8	266.6	265.7	264.7	263.8	262.9
127.5°	292.8	292.1	291.1	290.1	289.0	288.0	287.0	286.0	284.9	283.9	282.8
130°	305.0	304.3	303.5	302.7	301.9	301.1	300.1	299.0	297.8	296.7	295.5
132.5°	317.1	316.4	315.6	314.8	314.0	313.2	312.4	311.4	310.4	309.4	308.5
135°	334.1	333.4	332.7	332.1	331.4	330.8	329.9	328.7	327.6	326.4	325.3
137.5°	349.9	349.2	348.5	347.7	347.0	346.3	345.5	344.7	343.9	343.1	342.3
140°	360.2	359.5	358.8	358.0	357.2	356.4	355.7	355.1	354.5	354.0	353.4
142.5°	369.7	369.1	368.2	367.3	366.4	365.5	364.8	364.3	363.7	363.2	362.7
145°	383.0	382.5	381.3	380.1	378.8	377.6	377.0	377.1	377.2	377.3	377.3
147.5°	394.6	394.3	393.1	391.9	390.6	389.4	389.0	389.2	389.5	389.8	390.1
150°	401.7	401.3	400.1	399.0	397.8	396.7	396.3	396.8	397.3	397.8	398.3
152.5°	408.1	407.7	406.6	405.5	404.4	403.3	403.1	403.6	404.2	404.8	405.3
155°	416.9	416.4	415.6	414.7	413.9	413.0	412.9	413.5	414.2	414.8	415.5
157.5°	424.2	423.7	423.1	422.5	421.9	421.3	421.2	421.8	422.3	422.9	423.4
160°	428.5	428.1	427.7	427.2	426.8	426.4	426.4	426.8	427.2	427.7	428.1
162.5°	432.5	432.0	431.6	431.2	430.8	430.5	430.5	430.9	431.4	431.8	432.2
165°	437.3	436.8	436.6	436.4	436.2	436.0	436.1	436.5	436.9	437.4	437.8
167.5°	441.4	440.9	440.7	440.5	440.3	440.1	440.2	440.6	441.1	441.5	441.9
170°	443.5	443.0	442.8	442.7	442.5	442.4	442.5	443.0	443.4	443.8	444.3
172.5°	445.0	444.5	444.4	444.2	444.1	443.9	444.1	444.5	444.9	445.4	445.8
175°	446.7	446.2	446.1	445.9	445.8	445.6	445.8	446.3	446.8	447.3	447.8
177.5°	447.0	446.6	446.5	446.5	446.4	446.4	446.5	446.9	447.3	447.7	448.1
180°	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8



TEST NUMBER: P331285

CATALOG NUMBER: SA2XXDIP-C485D330U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7
2.5°	976.8	978.3	983.1	987.9	993.2	994.7	997.1	995.0	994.4	1000.1	1004.3
5°	979.6	986.3	999.4	1011.3	1021.4	1028.5	1036.0	1039.0	1044.6	1052.4	1062.1
7.5°	976.4	989.5	1010.1	1027.5	1046.4	1060.1	1070.8	1079.9	1090.9	1105.8	1122.0
10°	972.9	990.4	1015.4	1036.7	1059.9	1077.4	1092.0	1106.2	1122.6	1143.2	1164.4
12.5°	966.3	987.1	1018.4	1043.6	1073.3	1090.6	1110.2	1140.8	1158.5	1187.1	1217.0
15°	953.1	976.2	1019.9	1050.9	1084.5	1117.4	1153.6	1182.7	1211.9	1228.7	1270.9
17.5°	933.4	967.4	1015.8	1052.0	1094.7	1146.4	1187.1	1220.2	1253.8	1281.0	1302.2
20°	917.6	954.6	1009.8	1053.2	1103.9	1159.6	1206.3	1239.9	1269.0	1291.8	1304.9
22.5°	897.6	944.1	997.9	1048.7	1113.5	1168.6	1217.6	1244.1	1268.4	1279.5	1284.5
25°	866.0	922.1	982.9	1044.9	1118.1	1176.4	1221.2	1237.3	1244.4	1233.5	1215.6
27.5°	832.1	894.5	965.7	1037.9	1115.3	1171.3	1203.4	1200.9	1188.9	1153.8	1125.8
30°	806.7	875.4	951.9	1030.7	1108.4	1162.9	1181.6	1162.9	1135.7	1096.5	1056.5
32.5°	780.1	851.2	937.3	1020.6	1095.9	1143.8	1147.9	1115.7	1073.5	1029.0	979.1
35°	739.8	816.8	909.7	997.9	1069.2	1099.5	1081.5	1024.8	974.7	913.9	845.9
37.5°	694.3	779.3	872.5	964.6	1029.3	1037.2	992.7	932.9	862.3	790.8	710.8
40°	660.3	750.3	846.3	939.2	996.4	988.2	931.4	865.7	781.6	694.3	619.9
42.5°	629.8	719.8	817.6	908.8	954.6	932.0	865.7	785.0	694.7	612.4	544.4
45°	577.0	669.6	769.7	857.8	884.0	843.3	755.5	665.9	577.0	508.3	454.5
47.5°	525.8	617.3	716.4	793.9	803.2	748.4	652.5	560.3	483.9	427.9	390.0
50°	488.1	580.0	678.2	747.3	744.3	678.2	579.6	491.8	428.0	382.8	357.4
52.5°	454.3	541.1	635.5	698.3	682.5	610.4	516.3	438.4	385.9	350.5	327.5
55°	401.8	482.1	571.8	622.2	593.1	513.1	433.6	370.8	332.0	305.5	287.6
57.5°	349.7	425.0	501.7	532.8	500.6	426.8	360.5	315.0	285.8	266.1	254.5
60°	317.4	383.2	451.5	478.4	439.9	374.2	321.9	281.2	257.7	241.6	231.2
62.5°	285.2	344.0	408.5	423.1	387.9	332.4	286.1	252.2	232.9	218.6	208.8
65°	241.3	289.4	338.4	348.1	315.6	272.6	236.0	214.0	196.8	186.4	178.5
67.5°	197.9	236.5	271.2	279.0	250.6	220.8	194.3	175.2	163.5	154.8	148.2
70°	172.2	202.8	231.2	237.5	214.7	188.2	168.1	152.7	142.3	134.8	128.5
72.5°	145.0	170.5	194.1	198.4	179.8	159.5	143.0	130.9	121.7	116.9	110.8
75°	110.9	125.9	144.2	145.3	133.0	120.6	107.9	100.1	95.2	89.3	86.3
77.5°	78.3	90.0	100.5	102.5	95.2	86.8	79.7	73.5	69.4	66.6	63.9
80°	59.8	69.1	73.6	76.2	71.0	65.0	60.9	56.8	54.2	52.3	50.4
82.5°	42.7	48.5	52.7	54.7	51.8	48.3	44.1	41.8	39.8	38.2	37.6
85°	21.7	24.3	26.9	27.6	26.9	25.4	23.2	23.2	22.0	21.7	21.7
87.5°	7.7	9.0	9.2	10.3	9.8	9.9	10.0	9.8	9.7	9.4	9.2
90°	1.1	1.9	2.7	3.5	4.2	4.7	5.3	5.9	6.5	6.8	7.2
92.5°	6.5	6.4	6.3	6.2	6.4	6.6	6.9	7.2	7.5	7.7	7.9
95°	18.6	16.3	13.9	11.5	10.6	11.1	11.6	12.1	12.6	13.0	13.3
97.5°	35.0	28.3	21.7	15.0	12.2	13.4	14.5	15.7	16.9	17.2	17.5
100°	47.4	37.5	27.7	17.9	13.5	14.8	16.0	17.2	18.4	19.0	19.6
102.5°	72.2	70.1	68.1	66.0	59.8	49.6	39.4	29.2	18.9	19.7	20.4
105°	100.4	102.6	104.8	106.9	98.2	78.6	59.0	39.3	19.7	20.5	21.3
107.5°	127.4	129.1	130.9	132.6	121.7	98.2	74.7	51.1	27.6	26.8	26.0
110°	144.7	146.3	147.8	149.3	139.6	118.9	98.1	77.3	56.6	49.4	42.2



TEST NUMBER: P331285

CATALOG NUMBER: SA2XXDIP-C485D330U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	161.1	162.5	163.8	165.1	163.2	158.1	153.0	147.8	142.7	116.5	90.3
115°	187.1	188.4	189.6	190.8	192.3	194.1	195.9	197.7	199.5	166.2	133.0
117.5°	210.6	212.0	213.4	214.7	216.0	217.3	218.5	219.7	221.0	212.9	204.9
120°	227.4	228.5	229.6	230.6	231.8	233.1	234.4	235.7	237.0	237.9	238.7
122.5°	242.0	243.1	244.2	245.4	246.6	248.0	249.4	250.9	252.3	252.8	253.3
125°	263.8	264.7	265.7	266.6	267.8	269.1	270.5	271.8	273.2	273.7	274.2
127.5°	283.9	284.9	286.0	287.0	288.0	289.0	290.1	291.1	292.1	292.8	293.6
130°	296.7	297.8	299.0	300.1	301.1	301.9	302.7	303.5	304.3	305.0	305.8
132.5°	309.4	310.4	311.4	312.4	313.2	314.0	314.8	315.6	316.4	317.1	317.8
135°	326.4	327.6	328.7	329.9	330.8	331.4	332.1	332.7	333.4	334.1	334.8
137.5°	343.1	343.9	344.7	345.5	346.3	347.0	347.7	348.5	349.2	349.9	350.6
140°	354.0	354.5	355.1	355.7	356.4	357.2	358.0	358.8	359.5	360.2	360.8
142.5°	363.2	363.7	364.3	364.8	365.5	366.4	367.3	368.2	369.1	369.7	370.3
145°	377.3	377.2	377.1	377.0	377.6	378.8	380.1	381.3	382.5	383.0	383.5
147.5°	389.8	389.5	389.2	389.0	389.4	390.6	391.9	393.1	394.3	394.6	395.0
150°	397.8	397.3	396.8	396.3	396.7	397.8	399.0	400.1	401.3	401.7	402.1
152.5°	404.8	404.2	403.6	403.1	403.3	404.4	405.5	406.6	407.7	408.1	408.6
155°	414.8	414.2	413.5	412.9	413.0	413.9	414.7	415.6	416.4	416.9	417.3
157.5°	422.9	422.3	421.8	421.2	421.3	421.9	422.5	423.1	423.7	424.2	424.7
160°	427.7	427.2	426.8	426.4	426.4	426.8	427.2	427.7	428.1	428.5	429.0
162.5°	431.8	431.4	430.9	430.5	430.5	430.8	431.2	431.6	432.0	432.5	432.9
165°	437.4	436.9	436.5	436.1	436.0	436.2	436.4	436.6	436.8	437.3	437.8
167.5°	441.5	441.1	440.6	440.2	440.1	440.3	440.5	440.7	440.9	441.4	441.9
170°	443.8	443.4	443.0	442.5	442.4	442.5	442.7	442.8	443.0	443.5	444.0
172.5°	445.4	444.9	444.5	444.1	443.9	444.1	444.2	444.4	444.5	445.0	445.5
175°	447.3	446.8	446.3	445.8	445.6	445.8	445.9	446.1	446.2	446.7	447.2
177.5°	447.7	447.3	446.9	446.5	446.4	446.4	446.5	446.5	446.6	447.0	447.4
180°	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8



TEST NUMBER: P331285
 CATALOG NUMBER: SA2XXDIP-C485D330U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	971.7	971.7	971.7	971.7	971.7	971.7	971.7
2.5°	1007.9	1012.1	1012.1	1012.7	1017.4	1016.9	1016.6
5°	1072.6	1078.9	1079.7	1086.4	1090.9	1089.4	1085.3
7.5°	1133.6	1145.4	1154.4	1159.4	1165.3	1168.9	1167.3
10°	1182.0	1199.2	1209.6	1216.7	1225.3	1231.7	1229.4
12.5°	1225.9	1246.4	1260.7	1272.9	1274.0	1282.2	1276.6
15°	1294.4	1316.1	1318.3	1327.3	1334.4	1333.6	1334.0
17.5°	1317.0	1324.0	1325.4	1325.6	1325.7	1323.1	1317.4
20°	1309.0	1306.4	1300.0	1295.2	1286.6	1285.4	1278.0
22.5°	1270.7	1262.4	1246.5	1236.0	1222.6	1219.1	1217.0
25°	1195.4	1177.1	1151.7	1127.5	1120.7	1107.7	1111.4
27.5°	1092.1	1063.6	1036.1	1016.4	998.6	979.0	984.6
30°	1019.5	987.4	948.6	918.7	899.7	881.0	877.6
32.5°	932.9	885.8	842.5	816.2	787.0	775.2	762.3
35°	783.5	737.6	694.6	657.7	636.4	619.9	605.0
37.5°	649.1	596.3	561.6	531.7	516.3	506.9	509.2
40°	565.8	519.5	494.1	471.3	457.1	450.4	451.9
42.5°	498.3	463.6	442.7	427.1	417.1	413.3	412.4
45°	421.6	402.2	385.0	376.1	371.2	367.1	364.5
47.5°	369.4	353.5	343.8	338.5	334.2	330.1	330.0
50°	338.0	327.5	320.8	315.2	311.8	308.8	311.5
52.5°	314.1	304.5	297.8	292.8	291.5	288.8	288.8
55°	278.6	271.1	266.3	261.8	259.6	258.1	256.2
57.5°	246.3	239.2	234.8	231.9	227.7	226.2	225.6
60°	223.3	217.7	213.2	209.5	207.6	204.7	204.7
62.5°	202.1	196.5	192.3	189.5	186.4	185.2	185.5
65°	171.4	166.9	162.8	159.8	159.1	156.9	157.6
67.5°	143.2	140.2	135.9	134.2	132.8	131.6	130.7
70°	124.4	121.4	119.1	116.9	115.8	115.8	115.8
72.5°	108.5	104.9	103.6	100.8	101.4	100.2	99.0
75°	84.0	81.8	80.7	79.5	77.7	77.7	77.7
77.5°	61.8	61.2	59.8	58.6	58.2	57.8	58.0
80°	47.8	47.4	46.7	46.7	45.9	45.6	44.8
82.5°	36.7	35.8	35.3	35.0	34.9	34.8	34.7
85°	20.9	20.2	20.2	20.5	19.8	19.8	20.2
87.5°	9.6	9.6	9.4	9.4	9.8	9.5	9.5
90°	7.5	7.9	8.2	8.3	8.4	8.6	8.7
92.5°	8.1	8.2	8.4	8.5	8.6	8.6	8.7
95°	13.7	14.0	14.2	14.1	14.0	14.0	13.9
97.5°	17.7	18.0	18.2	18.3	18.4	18.5	18.6
100°	20.2	20.7	21.1	21.2	21.4	21.5	21.7
102.5°	21.2	21.9	22.4	22.6	22.8	23.0	23.2
105°	22.1	22.9	23.4	23.7	24.0	24.3	24.6
107.5°	25.2	24.4	24.1	24.4	24.7	25.0	25.3
110°	35.0	27.8	24.4	24.7	25.0	25.3	25.5



TEST NUMBER: P331285

CATALOG NUMBER: SA2XXDIP-C485D330U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	64.1	37.9	24.9	25.1	25.3	25.6	25.8
115°	99.7	66.4	47.2	42.0	36.9	31.7	26.5
117.5°	196.8	188.8	176.3	159.3	142.3	125.3	108.3
120°	239.6	240.4	236.0	226.3	216.6	206.9	197.2
122.5°	253.8	254.3	253.6	251.8	249.9	248.0	246.1
125°	274.7	275.2	275.6	275.8	276.0	276.2	276.4
127.5°	294.3	295.0	295.4	295.5	295.5	295.5	295.6
130°	306.6	307.4	307.8	307.7	307.6	307.6	307.5
132.5°	318.4	319.1	319.4	319.3	319.3	319.2	319.1
135°	335.5	336.2	336.5	336.4	336.2	336.1	335.9
137.5°	351.3	352.0	352.2	352.0	351.8	351.5	351.3
140°	361.5	362.1	362.3	361.9	361.6	361.2	360.8
142.5°	370.9	371.5	371.6	371.2	370.9	370.5	370.1
145°	384.0	384.5	384.6	384.2	383.9	383.5	383.1
147.5°	395.4	395.8	395.8	395.5	395.2	394.9	394.6
150°	402.5	403.0	403.0	402.7	402.3	401.9	401.6
152.5°	409.0	409.4	409.4	408.9	408.5	408.0	407.5
155°	417.7	418.2	418.1	417.5	417.0	416.4	415.8
157.5°	425.2	425.6	425.6	425.0	424.5	423.9	423.4
160°	429.4	429.8	429.8	429.3	428.8	428.3	427.8
162.5°	433.4	433.9	433.9	433.2	432.6	432.0	431.4
165°	438.3	438.8	438.8	438.3	437.8	437.3	436.8
167.5°	442.4	442.9	442.8	442.2	441.5	440.9	440.2
170°	444.5	445.0	444.9	444.3	443.6	443.0	442.3
172.5°	446.0	446.5	446.5	445.8	445.2	444.5	443.9
175°	447.7	448.2	448.1	447.4	446.7	445.9	445.2
177.5°	447.8	448.2	448.1	447.6	447.1	446.6	446.1
180°	446.8	446.8	446.8	446.8	446.8	446.8	446.8

(END OF REPORT)