

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331620-840

Luminaire Tested: **SA2XXRDIP-C290D330U840-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331620-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C290D330U840-4F0-1E-UDD-F4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 330 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2335.4 lumens
Efficiency: N/A
Efficacy: 115.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 20.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331620-840
CATALOG NUMBER: SA2XXRDIP-C290D330U840-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331620-840

CATALOG NUMBER: SA2XXRDIP-C290D330U840-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	45				45
1	97	93	89	86	89	85	82	79	71	69	67	58	56	55	46	45	44	38				38
2	89	82	76	71	81	75	70	66	63	59	56	51	49	47	41	39	38	33				33
3	81	72	65	59	74	66	60	55	56	51	48	46	43	40	37	34	33	28				28
4	74	64	56	51	68	59	52	47	50	45	41	41	38	35	33	31	28	25				25
5	68	57	49	44	63	53	46	41	45	39	35	37	33	30	30	27	25	22				22
6	63	51	44	38	58	48	41	36	40	35	31	34	30	27	27	25	22	19				19
7	58	47	39	33	54	43	36	31	37	31	28	31	27	24	25	22	20	17				17
8	54	42	35	30	50	39	33	28	34	28	25	28	24	21	23	20	18	16				16
9	51	39	31	27	46	36	30	25	31	26	22	26	22	19	21	19	16	14				14
10	47	36	29	24	43	33	27	23	28	23	20	24	20	17	20	17	15	13				13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8186	8186	8186
5°	8217	8083	8126
10°	8153	7950	7883
15°	8058	7714	7492
20°	7930	7378	7009
25°	7798	6996	6538
30°	7612	6604	5936
35°	7433	6177	5409
40°	7253	5735	4795
45°	7040	5236	4242
50°	6822	4735	3697
55°	6598	4197	3178
60°	6339	3630	2638
65°	6044	3049	2399
70°	5698	2511	2209
75°	5265	2289	2059
80°	4649	2046	1878
85°	3649	1612	1612



TEST NUMBER: P331620-840

CATALOG NUMBER: SA2XXRDIP-C290D330U840-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.4	2.0
10°-20°	130.3	5.6
20°-30°	183.0	7.8
30°-40°	199.5	8.5
40°-50°	183.4	7.9
50°-60°	144.1	6.2
60°-70°	93.9	4.0
70°-80°	48.4	2.1
80°-90°	14.2	0.6
90°-100°	74.2	3.2
100°-110°	251.8	10.8
110°-120°	267.5	11.5
120°-130°	220.2	9.4
130°-140°	176.8	7.6
140°-150°	133.6	5.7
150°-160°	93.9	4.0
160°-170°	55.3	2.4
170°-180°	18.0	0.8
0°-30°	360.7	15.4
0°-40°	560.2	24.0
0°-60°	887.7	38.0
0°-90°	1044.3	44.7
90°-120°	593.4	25.4
90°-150°	1124.0	48.1
90°-180°	1291.0	55.3
0°-180°	2335.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	507	507	507	507	507	
5°	507	504	499	502	501	48
15°	482	476	462	453	448	136
25°	438	422	393	375	367	201
35°	377	353	313	285	274	236
45°	308	277	229	198	186	238
55°	234	198	149	123	113	209
65°	158	121	80	65	63	157
75°	84	53	37	34	33	89
85°	20	11	9	9	9	23
90°	0	5	12	12	12	2
95°	12	31	140	53	41	13
105°	44	66	264	473	402	46
115°	77	97	221	457	529	76
125°	107	127	213	370	429	95
135°	126	150	210	311	356	97
145°	143	165	209	260	284	90
155°	163	176	203	230	239	75
165°	178	183	194	206	209	50
175°	185	185	187	189	189	18
180°	186	186	186	186	186	



TEST NUMBER: P331620-840

CATALOG NUMBER: SA2XXRDIP-C290D330U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	507.0	507.0	507.0	507.0	507.0	507.0	507.0	507.0	507.0	507.0	507.0
2.5°	508.8	508.4	508.0	507.6	507.2	506.4	505.5	504.7	503.8	502.9	503.7
5°	507.0	506.4	505.9	505.4	504.9	503.9	502.6	501.3	500.0	498.7	499.6
7.5°	501.7	501.1	500.4	499.8	499.2	498.1	496.6	494.9	493.4	491.9	492.1
10°	497.3	496.6	495.8	495.1	494.4	493.0	491.0	489.0	487.0	484.9	484.6
12.5°	491.8	490.9	490.0	489.2	488.3	486.6	483.9	481.3	478.7	476.1	475.5
15°	482.1	481.0	479.9	478.8	477.7	475.3	471.9	468.5	464.9	461.5	459.6
17.5°	470.3	468.6	466.9	465.1	463.4	460.4	456.0	451.5	447.1	442.6	440.3
20°	461.5	459.5	457.5	455.3	453.3	449.8	444.6	439.6	434.5	429.4	426.9
22.5°	452.0	449.7	447.4	445.1	442.8	438.8	433.0	427.3	421.6	415.9	412.5
25°	437.7	434.3	431.1	427.9	424.6	419.6	412.8	406.2	399.4	392.7	388.5
27.5°	420.4	416.9	413.3	409.8	406.2	400.6	393.0	385.5	377.9	370.3	365.5
30°	408.3	404.5	400.5	396.7	392.8	386.8	378.6	370.5	362.3	354.2	349.0
32.5°	396.6	392.0	387.5	382.9	378.4	372.0	363.8	355.4	347.1	338.7	332.9
35°	377.1	371.9	366.7	361.5	356.3	349.2	340.2	331.2	322.3	313.4	306.9
37.5°	357.7	351.9	346.2	340.5	334.8	327.2	317.6	308.0	298.5	288.9	281.9
40°	344.1	338.0	331.8	325.7	319.6	311.6	301.7	291.9	282.0	272.1	264.8
42.5°	330.1	323.7	317.2	310.8	304.4	296.0	285.8	275.6	265.4	255.2	247.7
45°	308.3	301.4	294.6	287.8	280.9	272.2	261.5	250.7	240.0	229.3	222.2
47.5°	287.0	279.7	272.6	265.3	258.0	248.9	237.8	226.8	215.7	204.7	197.5
50°	271.6	264.4	257.1	249.8	242.7	233.4	222.2	211.0	199.8	188.5	181.5
52.5°	256.5	248.9	241.5	233.9	226.3	217.0	206.0	195.1	184.1	173.1	166.3
55°	234.4	226.5	218.5	210.6	202.6	193.2	182.1	171.1	160.1	149.1	143.0
57.5°	211.8	203.6	195.4	187.3	179.2	169.8	159.2	148.7	138.0	127.4	121.8
60°	196.3	188.2	180.1	171.9	163.7	154.4	143.9	133.4	122.9	112.4	107.1
62.5°	181.3	173.2	165.0	156.8	148.7	139.6	129.6	119.6	109.6	99.6	94.6
65°	158.2	150.0	141.8	133.5	125.2	116.5	107.3	98.2	89.0	79.8	76.3
67.5°	136.0	127.8	119.7	111.5	103.3	95.0	86.7	78.6	70.3	62.0	60.4
70°	120.7	112.7	104.7	96.8	88.9	81.4	74.3	67.3	60.3	53.2	52.2
72.5°	105.9	98.4	90.7	83.1	75.4	68.9	63.2	57.6	51.9	46.3	45.3
75°	84.4	77.3	70.2	63.0	55.8	50.6	47.1	43.6	40.2	36.7	36.0
77.5°	63.2	57.0	50.7	44.4	38.2	34.2	32.5	30.9	29.2	27.6	27.2
80°	50.0	44.8	39.6	34.4	29.2	26.1	25.0	24.0	23.0	22.0	21.6
82.5°	37.9	33.8	29.8	25.8	21.7	19.3	18.6	17.9	17.2	16.6	16.3
85°	19.7	17.6	15.5	13.3	11.2	9.9	9.6	9.3	9.0	8.7	8.7
87.5°	6.0	5.6	5.2	4.6	4.1	4.0	4.3	4.8	5.3	5.4	5.3
90°	0.4	1.4	2.8	3.5	4.2	5.4	7.2	9.6	11.8	12.1	11.8
92.5°	4.3	6.3	8.9	10.4	12.8	16.2	24.2	35.6	45.7	46.4	39.2
95°	12.5	13.9	17.5	20.7	26.4	34.9	51.4	82.4	123.8	139.9	122.4
97.5°	20.3	22.2	26.1	30.9	37.5	47.2	67.8	111.1	179.9	238.7	250.4
100°	27.5	28.6	31.7	37.5	44.6	54.6	73.5	117.0	194.1	281.9	333.3
102.5°	34.0	34.8	38.1	43.7	51.2	61.2	78.7	117.3	188.6	283.3	364.1
105°	43.5	44.9	47.5	52.8	60.7	70.7	87.5	119.2	178.0	264.4	359.3
107.5°	53.8	54.9	57.4	62.3	70.1	80.2	96.4	124.1	172.8	244.1	328.0
110°	60.7	62.1	64.2	68.9	76.3	86.7	102.4	128.1	171.7	234.4	308.3



TEST NUMBER: P331620-840

CATALOG NUMBER: SA2XXRDIP-C290D330U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	67.0	68.4	70.8	75.1	82.3	93.0	108.2	132.4	171.9	228.1	294.6
115°	76.7	78.5	80.7	84.9	92.1	101.7	117.0	138.8	173.4	221.3	277.6
117.5°	86.8	88.3	90.4	94.2	101.1	111.1	125.2	145.6	176.0	217.8	266.9
120°	93.1	94.5	96.7	99.9	107.0	117.0	131.0	150.3	177.7	215.9	261.2
122.5°	99.2	100.3	102.4	105.9	113.0	123.3	136.3	154.2	179.7	214.7	256.3
125°	107.0	108.2	110.3	114.5	121.7	131.7	144.5	160.6	182.7	212.7	249.4
127.5°	113.3	114.7	117.8	122.5	129.3	139.6	152.1	166.5	185.7	211.5	243.0
130°	117.0	118.5	122.0	127.0	134.2	144.1	156.6	170.2	188.0	210.9	238.7
132.5°	120.5	122.2	126.0	131.3	138.8	148.8	160.7	173.9	190.4	210.6	235.3
135°	125.6	127.0	131.3	136.6	144.9	154.8	166.3	178.7	193.1	210.2	230.5
137.5°	130.5	132.2	136.4	142.2	150.3	159.6	170.9	182.5	195.5	210.1	227.1
140°	134.2	135.6	139.9	145.6	153.4	162.7	173.4	184.5	196.6	209.8	225.1
142.5°	137.8	139.1	143.0	148.8	156.3	165.0	175.4	186.2	197.4	209.8	223.2
145°	143.4	144.9	148.5	153.8	161.0	168.7	178.4	188.4	198.3	209.0	220.6
147.5°	149.5	150.5	153.9	158.9	164.8	171.8	180.9	189.7	198.6	207.8	217.8
150°	153.4	154.5	157.3	162.0	167.3	173.8	182.0	190.2	198.3	206.9	215.5
152.5°	157.4	157.9	160.8	164.8	170.0	175.7	183.1	190.5	197.8	205.5	213.5
155°	163.1	163.4	165.5	169.5	173.4	178.7	184.8	190.9	196.9	203.0	209.8
157.5°	167.7	168.1	169.9	173.3	176.4	180.9	186.0	190.9	195.3	200.5	206.3
160°	170.9	171.3	172.7	175.5	178.4	182.4	186.6	190.9	194.5	198.7	203.7
162.5°	174.1	173.8	175.3	177.5	180.2	183.2	186.9	190.6	193.6	197.3	201.5
165°	177.7	177.3	178.0	180.2	182.0	184.1	187.3	189.9	192.0	194.5	197.6
167.5°	180.7	180.3	180.9	182.3	183.6	184.9	187.2	189.3	190.4	192.0	194.0
170°	182.7	182.0	182.4	183.4	184.1	185.2	186.9	188.7	189.5	190.6	192.0
172.5°	183.8	183.4	183.2	184.3	184.7	185.5	186.7	187.9	188.3	188.8	190.0
175°	185.2	184.8	184.5	185.2	185.2	185.5	186.2	186.9	186.6	186.9	187.3
177.5°	185.8	185.2	185.0	185.5	185.5	185.5	185.8	186.4	185.8	185.5	185.8
180°	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5



TEST NUMBER: P331620-840

CATALOG NUMBER: SA2XXRDIP-C290D330U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	507.0	507.0	507.0	507.0	507.0	507.0	507.0	507.0
2.5°	504.5	505.3	506.1	506.4	506.3	506.1	505.9	505.8
5°	500.5	501.4	502.3	502.6	502.3	502.0	501.7	501.4
7.5°	492.4	492.7	492.9	492.8	492.3	491.7	491.2	490.7
10°	484.3	484.0	483.7	483.2	482.6	482.0	481.4	480.8
12.5°	475.0	474.4	473.9	473.1	472.1	471.1	470.1	469.1
15°	457.7	455.7	453.7	452.3	451.3	450.2	449.2	448.2
17.5°	438.0	435.7	433.4	431.4	429.6	427.9	426.1	424.3
20°	424.3	421.7	419.2	416.8	414.5	412.3	410.1	407.9
22.5°	409.3	406.0	402.7	400.2	398.5	396.9	395.2	393.5
25°	384.4	380.1	376.0	373.1	371.6	370.0	368.5	367.0
27.5°	360.5	355.7	350.8	347.2	344.8	342.3	339.9	337.5
30°	343.8	338.6	333.4	329.4	326.6	323.9	321.1	318.4
32.5°	326.9	320.9	315.0	310.7	308.2	305.6	303.0	300.4
35°	300.5	294.1	287.6	283.3	281.0	278.8	276.6	274.4
37.5°	274.8	267.7	260.6	255.8	253.3	250.6	248.1	245.5
40°	257.6	250.3	243.1	238.1	235.5	232.9	230.1	227.5
42.5°	240.1	232.7	225.2	220.3	217.6	215.1	212.5	210.0
45°	214.9	207.6	200.5	195.6	193.2	190.7	188.2	185.8
47.5°	190.3	183.1	175.9	171.2	169.0	166.7	164.5	162.3
50°	174.5	167.4	160.4	155.8	153.7	151.6	149.4	147.2
52.5°	159.6	152.8	146.0	141.6	139.7	137.6	135.6	133.7
55°	136.8	130.8	124.6	120.6	118.7	116.7	114.8	112.9
57.5°	116.2	110.6	105.0	101.4	99.8	98.2	96.5	94.8
60°	102.0	96.8	91.6	88.2	86.5	84.9	83.3	81.7
62.5°	89.7	84.7	79.8	76.7	75.7	74.8	73.8	72.8
65°	72.9	69.4	65.9	64.0	63.7	63.4	63.1	62.8
67.5°	58.9	57.3	55.6	54.7	54.3	54.0	53.7	53.4
70°	51.2	50.2	49.2	48.5	48.0	47.6	47.2	46.8
72.5°	44.5	43.6	42.8	42.3	42.0	41.8	41.5	41.3
75°	35.2	34.5	33.8	33.4	33.3	33.2	33.1	33.0
77.5°	26.7	26.3	25.9	25.7	25.4	25.2	25.1	24.9
80°	21.2	20.8	20.4	20.2	20.2	20.2	20.2	20.2
82.5°	16.1	15.8	15.6	15.5	15.5	15.5	15.5	15.5
85°	8.7	8.7	8.7	8.7	8.7	8.7	8.7	8.7
87.5°	5.0	4.8	4.8	4.9	4.9	4.9	4.9	4.9
90°	11.4	10.7	11.4	11.8	11.8	11.8	11.8	11.8
92.5°	31.1	26.7	23.7	21.5	21.2	20.1	20.3	19.8
95°	93.5	71.7	56.8	48.9	44.2	41.4	40.3	40.7
97.5°	218.1	178.4	139.9	114.1	97.0	88.3	83.1	80.1
100°	325.8	281.6	232.7	189.5	159.9	144.5	134.2	127.7
102.5°	396.3	386.3	350.5	304.8	272.6	246.4	233.5	224.8
105°	433.5	473.8	478.5	466.8	444.5	422.4	407.1	402.1
107.5°	406.7	467.5	504.5	521.8	524.6	523.4	520.3	513.7
110°	383.5	447.5	493.1	522.4	537.8	544.5	547.8	547.3



TEST NUMBER: P331620-840

CATALOG NUMBER: SA2XXRDIP-C290D330U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	362.4	423.7	472.5	506.1	527.5	538.8	544.8	546.7
115°	336.5	391.4	438.2	474.9	500.3	516.6	525.9	529.2
117.5°	316.9	365.2	407.6	442.0	467.9	485.2	494.9	497.7
120°	307.2	351.4	389.3	421.7	446.8	463.5	473.8	477.5
122.5°	299.5	340.0	375.9	405.2	427.6	444.1	453.3	456.3
125°	288.3	325.1	356.5	383.2	403.9	417.5	426.4	429.3
127.5°	277.2	310.5	340.1	364.8	382.8	395.6	403.2	405.6
130°	270.1	300.8	329.0	352.5	370.0	382.1	389.3	392.1
132.5°	263.3	291.6	317.6	339.7	356.9	369.0	375.6	378.2
135°	253.7	277.2	300.8	320.7	336.1	347.9	354.4	355.8
137.5°	246.1	265.8	284.5	301.8	315.9	326.0	331.6	333.8
140°	241.2	258.3	274.8	290.4	301.8	311.1	316.5	318.6
142.5°	237.2	251.8	265.9	279.0	289.8	298.3	303.1	303.5
145°	231.6	243.4	254.4	264.8	273.3	279.4	283.0	284.0
147.5°	227.2	236.5	245.1	252.7	259.7	264.6	267.0	267.7
150°	224.1	232.0	239.4	245.8	251.2	255.5	257.6	258.0
152.5°	221.0	228.2	234.6	240.1	244.4	248.0	249.6	249.7
155°	216.6	222.3	227.6	231.6	235.5	238.0	239.4	238.7
157.5°	211.6	216.3	220.8	223.9	226.6	228.7	229.3	229.3
160°	208.3	212.3	216.2	218.7	221.3	223.0	223.4	223.4
162.5°	205.2	208.6	212.0	213.9	216.4	217.6	217.9	217.6
165°	200.6	203.0	205.5	206.9	208.3	209.8	209.8	209.4
167.5°	196.0	197.9	199.7	201.0	201.6	202.4	202.3	201.9
170°	193.8	194.8	196.2	196.9	197.3	198.3	198.0	197.3
172.5°	191.2	192.0	193.1	193.5	193.9	194.4	194.0	193.6
175°	188.4	188.7	189.1	189.5	189.5	189.9	189.5	188.7
177.5°	186.4	186.4	186.7	186.7	186.7	186.7	186.4	185.8
180°	185.5	185.5	185.5	185.5	185.5	185.5	185.5	185.5

(END OF REPORT)