

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331624-840

Luminaire Tested: **SA2XXRDIP-C290D530U840-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331624-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C290D530U840-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 530 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3178.8 lumens
Efficiency: N/A
Efficacy: 124.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 25.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331624-840

CATALOG NUMBER: SA2XXRDIP-C290D530U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331624-840

CATALOG NUMBER: SA2XXRDIP-C290D530U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									20
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR	0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40	33	33	33	33	28	28	28	28	28	28	28	28																
	1	94	90	86	83	85	81	78	76	65	63	61	50	49	47	36	35	35	28	28	28	28	24	24	24	24	24	24	24	24																
	2	86	79	73	68	77	71	67	62	57	54	51	44	42	40	32	31	30	24	24	24	24	21	21	21	21	21	21	21	21																
	3	79	70	63	57	71	63	57	52	51	47	43	39	37	34	29	27	26	21	21	21	21	18	18	18	18	18	18	18	18																
	4	72	62	54	49	65	56	50	45	45	41	37	35	32	30	26	24	22	18	18	18	18	16	16	16	16	16	16	16	16																
	5	66	55	47	42	59	50	43	38	41	36	32	32	28	26	23	21	20	16	16	16	16	14	14	14	14	14	14	14	14																
	6	61	49	42	36	55	45	38	33	37	32	28	29	25	23	21	19	17	14	14	14	14	13	13	13	13	13	13	13	13																
	7	56	45	37	32	51	41	34	29	33	28	25	26	23	20	20	17	16	13	13	13	13	11	11	11	11	11	11	11	11																
	8	52	40	33	28	47	37	30	26	30	25	22	24	20	18	18	16	14	11	11	11	11	10	10	10	10	10	10	10	10																
	9	49	37	30	25	44	34	27	23	28	23	20	22	19	16	17	14	13	10	10	10	10	9	9	9	9	9	9	9	9																
	10	45	34	27	22	41	31	25	21	26	21	18	20	17	15	16	13	12	9	9	9	9	8	8	8	8	8	8	8	8																

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8186	8186	8186
5°	8217	8083	8126
10°	8153	7950	7883
15°	8058	7714	7492
20°	7930	7378	7009
25°	7798	6996	6538
30°	7612	6604	5936
35°	7433	6177	5409
40°	7253	5735	4795
45°	7040	5236	4242
50°	6822	4735	3697
55°	6598	4197	3178
60°	6339	3630	2638
65°	6044	3049	2399
70°	5698	2511	2209
75°	5265	2289	2059
80°	4649	2046	1878
85°	3649	1612	1612



TEST NUMBER: P331624-840

CATALOG NUMBER: SA2XXRDIP-C290D530U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.4	1.5
10°-20°	130.3	4.1
20°-30°	183.0	5.8
30°-40°	199.5	6.3
40°-50°	183.4	5.8
50°-60°	144.1	4.5
60°-70°	93.9	3.0
70°-80°	48.4	1.5
80°-90°	14.4	0.5
90°-100°	24.3	0.8
100°-110°	89.1	2.8
110°-120°	238.2	7.5
120°-130°	393.1	12.4
130°-140°	418.1	13.2
140°-150°	388.6	12.2
150°-160°	312.4	9.8
160°-170°	201.3	6.3
170°-180°	69.3	2.2
0°-30°	360.7	11.3
0°-40°	560.2	17.6
0°-60°	887.7	27.9
0°-90°	1044.4	32.9
90°-120°	351.5	11.1
90°-150°	1551.4	48.8
90°-180°	2134.0	67.1
0°-180°	3178.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	507	507	507	507	507	
5°	507	504	499	502	501	48
15°	482	476	462	453	448	136
25°	438	422	393	375	367	201
35°	377	353	313	285	274	236
45°	308	277	229	198	186	238
55°	234	198	149	123	113	209
65°	158	121	80	65	63	157
75°	84	53	37	34	33	89
85°	20	11	9	9	9	23
90°	0	6	10	13	14	2
95°	34	18	21	23	23	42
105°	160	167	32	38	40	171
115°	303	312	325	93	43	298
125°	428	436	445	449	451	382
135°	530	538	543	548	548	409
145°	615	615	624	627	624	385
155°	677	673	679	682	678	312
165°	714	711	712	715	712	202
175°	730	726	727	730	726	69
180°	728	728	728	728	728	



TEST NUMBER: P331624-840

CATALOG NUMBER: SA2XXRDIP-C290D530U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	507.0	507.0	507.0	507.0	507.0	507.0	507.0	507.0	507.0	507.0	507.0
2.5°	508.8	508.4	508.0	507.6	507.2	506.4	505.5	504.7	503.8	502.9	503.7
5°	507.0	506.4	505.9	505.4	504.9	503.9	502.6	501.3	500.0	498.7	499.6
7.5°	501.7	501.1	500.4	499.8	499.2	498.1	496.6	494.9	493.4	491.9	492.1
10°	497.3	496.6	495.8	495.1	494.4	493.0	491.0	489.0	487.0	484.9	484.6
12.5°	491.8	490.9	490.0	489.2	488.3	486.6	483.9	481.3	478.7	476.1	475.5
15°	482.1	481.0	479.9	478.8	477.7	475.3	471.9	468.5	464.9	461.5	459.6
17.5°	470.3	468.6	466.9	465.1	463.4	460.4	456.0	451.5	447.1	442.6	440.3
20°	461.5	459.5	457.5	455.3	453.3	449.8	444.6	439.6	434.5	429.4	426.9
22.5°	452.0	449.7	447.4	445.1	442.8	438.8	433.0	427.3	421.6	415.9	412.5
25°	437.7	434.3	431.1	427.9	424.6	419.6	412.8	406.2	399.4	392.7	388.5
27.5°	420.4	416.9	413.3	409.8	406.2	400.6	393.0	385.5	377.9	370.3	365.5
30°	408.3	404.5	400.5	396.7	392.8	386.8	378.6	370.5	362.3	354.2	349.0
32.5°	396.6	392.0	387.5	382.9	378.4	372.0	363.8	355.4	347.1	338.7	332.9
35°	377.1	371.9	366.7	361.5	356.3	349.2	340.2	331.2	322.3	313.4	306.9
37.5°	357.7	351.9	346.2	340.5	334.8	327.2	317.6	308.0	298.5	288.9	281.9
40°	344.1	338.0	331.8	325.7	319.6	311.6	301.7	291.9	282.0	272.1	264.8
42.5°	330.1	323.7	317.2	310.8	304.4	296.0	285.8	275.6	265.4	255.2	247.7
45°	308.3	301.4	294.6	287.8	280.9	272.2	261.5	250.7	240.0	229.3	222.2
47.5°	287.0	279.7	272.6	265.3	258.0	248.9	237.8	226.8	215.7	204.7	197.5
50°	271.6	264.4	257.1	249.8	242.7	233.4	222.2	211.0	199.8	188.5	181.5
52.5°	256.5	248.9	241.5	233.9	226.3	217.0	206.0	195.1	184.1	173.1	166.3
55°	234.4	226.5	218.5	210.6	202.6	193.2	182.1	171.1	160.1	149.1	143.0
57.5°	211.8	203.6	195.4	187.3	179.2	169.8	159.2	148.7	138.0	127.4	121.8
60°	196.3	188.2	180.1	171.9	163.7	154.4	143.9	133.4	122.9	112.4	107.1
62.5°	181.3	173.2	165.0	156.8	148.7	139.6	129.6	119.6	109.6	99.6	94.6
65°	158.2	150.0	141.8	133.5	125.2	116.5	107.3	98.2	89.0	79.8	76.3
67.5°	136.0	127.8	119.7	111.5	103.3	95.0	86.7	78.6	70.3	62.0	60.4
70°	120.7	112.7	104.7	96.8	88.9	81.4	74.3	67.3	60.3	53.2	52.2
72.5°	105.9	98.4	90.7	83.1	75.4	68.9	63.2	57.6	51.9	46.3	45.3
75°	84.4	77.3	70.2	63.0	55.8	50.6	47.1	43.6	40.2	36.7	36.0
77.5°	63.2	57.0	50.7	44.4	38.2	34.2	32.5	30.9	29.2	27.6	27.2
80°	50.0	44.8	39.6	34.4	29.2	26.1	25.0	24.0	23.0	22.0	21.6
82.5°	37.9	33.8	29.8	25.8	21.7	19.3	18.6	17.9	17.2	16.6	16.3
85°	19.7	17.6	15.5	13.3	11.2	9.9	9.6	9.3	9.0	8.7	8.7
87.5°	6.0	5.6	5.2	4.7	4.4	4.3	4.4	4.6	4.8	5.0	5.0
90°	0.5	1.8	3.1	4.3	5.7	6.8	7.8	8.7	9.6	10.5	11.1
92.5°	10.6	10.5	10.4	10.3	10.2	10.4	10.8	11.3	11.7	12.2	12.5
95°	34.2	30.4	26.6	22.6	18.8	17.3	18.1	18.9	19.7	20.6	21.1
97.5°	68.0	57.1	46.3	35.3	24.4	19.9	21.8	23.7	25.7	27.5	28.0
100°	93.3	77.3	61.2	45.1	29.1	22.1	24.0	26.1	28.1	30.0	31.0
102.5°	121.1	117.8	114.3	110.9	107.6	97.5	80.9	64.2	47.6	30.9	32.1
105°	160.2	163.7	167.2	170.8	174.3	160.1	128.1	96.1	64.1	32.1	33.4
107.5°	204.8	207.6	210.5	213.3	216.1	198.3	160.1	121.7	83.3	45.0	43.7
110°	233.5	235.9	238.4	240.9	243.3	227.6	193.8	160.0	126.0	92.2	80.5



TEST NUMBER: P331624-840

CATALOG NUMBER: SA2XXRDIP-C290D530U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	260.4	262.7	264.8	267.0	269.1	266.1	257.7	249.3	241.0	232.7	189.9
115°	303.1	305.0	307.0	309.0	311.0	313.5	316.4	319.3	322.2	325.2	270.9
117.5°	341.1	343.4	345.6	347.8	350.0	352.1	354.2	356.2	358.2	360.1	347.1
120°	368.9	370.6	372.4	374.2	376.0	377.9	380.0	382.1	384.2	386.3	387.7
122.5°	392.5	394.4	396.3	398.1	399.9	402.0	404.2	406.6	408.9	411.2	412.0
125°	428.5	430.0	431.5	433.0	434.5	436.5	438.7	440.9	443.1	445.4	446.2
127.5°	461.0	462.7	464.4	466.1	467.8	469.5	471.1	472.8	474.4	476.2	477.3
130°	481.7	483.5	485.4	487.4	489.2	490.8	492.1	493.3	494.6	495.9	497.3
132.5°	502.8	504.3	505.9	507.6	509.2	510.6	511.9	513.2	514.4	515.7	516.8
135°	530.2	532.1	533.9	535.8	537.7	539.2	540.2	541.3	542.3	543.3	544.5
137.5°	558.0	559.2	560.5	561.8	563.1	564.4	565.6	566.8	567.9	569.2	570.4
140°	576.0	576.9	577.9	578.9	579.8	580.9	582.2	583.5	584.7	586.0	587.1
142.5°	591.2	592.1	592.9	593.7	594.6	595.7	597.2	598.6	600.2	601.7	602.6
145°	615.0	614.9	614.8	614.7	614.6	615.5	617.5	619.5	621.5	623.5	624.3
147.5°	635.8	635.3	634.9	634.5	634.0	634.8	636.7	638.7	640.7	642.7	643.3
150°	649.2	648.4	647.6	646.8	646.0	646.5	648.4	650.3	652.2	654.0	654.7
152.5°	660.7	659.7	658.8	657.9	657.0	657.4	659.2	661.1	662.8	664.6	665.3
155°	677.2	676.2	675.1	674.1	673.0	673.2	674.6	676.0	677.4	678.8	679.5
157.5°	690.1	689.3	688.4	687.5	686.6	686.7	687.6	688.6	689.6	690.6	691.4
160°	697.8	697.1	696.4	695.7	695.0	695.0	695.7	696.4	697.1	697.8	698.5
162.5°	704.5	703.8	703.1	702.4	701.8	701.7	702.3	702.9	703.5	704.1	704.9
165°	713.6	712.9	712.2	711.4	710.7	710.6	710.9	711.2	711.7	712.0	712.9
167.5°	720.3	719.6	718.9	718.2	717.5	717.3	717.6	718.0	718.3	718.6	719.4
170°	724.1	723.5	722.8	722.1	721.3	721.0	721.3	721.5	721.8	722.1	722.9
172.5°	726.7	726.0	725.3	724.6	723.9	723.6	723.9	724.1	724.3	724.6	725.4
175°	729.9	729.1	728.3	727.5	726.6	726.4	726.6	726.8	727.0	727.3	728.1
177.5°	730.4	729.8	729.1	728.5	727.8	727.5	727.6	727.7	727.8	727.9	728.6
180°	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3



TEST NUMBER: P331624-840

CATALOG NUMBER: SA2XXRDIP-C290D530U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	507.0	507.0	507.0	507.0	507.0	507.0	507.0	507.0
2.5°	504.5	505.3	506.1	506.4	506.3	506.1	505.9	505.8
5°	500.5	501.4	502.3	502.6	502.3	502.0	501.7	501.4
7.5°	492.4	492.7	492.9	492.8	492.3	491.7	491.2	490.7
10°	484.3	484.0	483.7	483.2	482.6	482.0	481.4	480.8
12.5°	475.0	474.4	473.9	473.1	472.1	471.1	470.1	469.1
15°	457.7	455.7	453.7	452.3	451.3	450.2	449.2	448.2
17.5°	438.0	435.7	433.4	431.4	429.6	427.9	426.1	424.3
20°	424.3	421.7	419.2	416.8	414.5	412.3	410.1	407.9
22.5°	409.3	406.0	402.7	400.2	398.5	396.9	395.2	393.5
25°	384.4	380.1	376.0	373.1	371.6	370.0	368.5	367.0
27.5°	360.5	355.7	350.8	347.2	344.8	342.3	339.9	337.5
30°	343.8	338.6	333.4	329.4	326.6	323.9	321.1	318.4
32.5°	326.9	320.9	315.0	310.7	308.2	305.6	303.0	300.4
35°	300.5	294.1	287.6	283.3	281.0	278.8	276.6	274.4
37.5°	274.8	267.7	260.6	255.8	253.3	250.6	248.1	245.5
40°	257.6	250.3	243.1	238.1	235.5	232.9	230.1	227.5
42.5°	240.1	232.7	225.2	220.3	217.6	215.1	212.5	210.0
45°	214.9	207.6	200.5	195.6	193.2	190.7	188.2	185.8
47.5°	190.3	183.1	175.9	171.2	169.0	166.7	164.5	162.3
50°	174.5	167.4	160.4	155.8	153.7	151.6	149.4	147.2
52.5°	159.6	152.8	146.0	141.6	139.7	137.6	135.6	133.7
55°	136.8	130.8	124.6	120.6	118.7	116.7	114.8	112.9
57.5°	116.2	110.6	105.0	101.4	99.8	98.2	96.5	94.8
60°	102.0	96.8	91.6	88.2	86.5	84.9	83.3	81.7
62.5°	89.7	84.7	79.8	76.7	75.7	74.8	73.8	72.8
65°	72.9	69.4	65.9	64.0	63.7	63.4	63.1	62.8
67.5°	58.9	57.3	55.6	54.7	54.3	54.0	53.7	53.4
70°	51.2	50.2	49.2	48.5	48.0	47.6	47.2	46.8
72.5°	44.5	43.6	42.8	42.3	42.0	41.8	41.5	41.3
75°	35.2	34.5	33.8	33.4	33.3	33.2	33.1	33.0
77.5°	26.7	26.3	25.9	25.7	25.4	25.2	25.1	24.9
80°	21.2	20.8	20.4	20.2	20.2	20.2	20.2	20.2
82.5°	16.1	15.8	15.6	15.5	15.5	15.5	15.5	15.5
85°	8.7	8.7	8.7	8.7	8.7	8.7	8.7	8.7
87.5°	5.2	5.2	5.2	5.3	5.3	5.4	5.4	5.5
90°	11.7	12.3	12.9	13.3	13.5	13.7	14.0	14.2
92.5°	12.8	13.1	13.4	13.6	13.8	13.9	14.1	14.2
95°	21.7	22.3	22.9	23.1	23.0	22.9	22.8	22.6
97.5°	28.5	28.9	29.4	29.7	29.8	30.0	30.1	30.3
100°	31.9	32.8	33.8	34.3	34.6	34.8	35.0	35.3
102.5°	33.3	34.5	35.7	36.6	36.9	37.2	37.5	37.9
105°	34.7	36.1	37.3	38.2	38.7	39.1	39.6	40.1
107.5°	42.4	41.1	39.8	39.4	39.8	40.3	40.7	41.2
110°	68.8	57.1	45.3	39.8	40.2	40.7	41.2	41.6



TEST NUMBER: P331624-840

CATALOG NUMBER: SA2XXRDIP-C290D530U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	147.1	104.4	61.7	40.6	40.9	41.3	41.7	42.0
115°	216.7	162.5	108.3	77.0	68.5	60.1	51.6	43.2
117.5°	334.0	320.8	307.7	287.3	259.5	231.9	204.2	176.4
120°	389.1	390.5	391.9	384.8	368.9	353.1	337.3	321.4
122.5°	412.8	413.7	414.5	413.4	410.4	407.3	404.2	401.1
125°	447.0	447.8	448.6	449.2	449.6	449.9	450.3	450.6
127.5°	478.5	479.7	480.9	481.5	481.6	481.7	481.7	481.8
130°	498.5	499.8	501.1	501.7	501.5	501.4	501.3	501.2
132.5°	518.0	519.1	520.2	520.6	520.5	520.4	520.3	520.2
135°	545.7	546.8	548.1	548.6	548.3	548.1	547.9	547.5
137.5°	571.5	572.6	573.8	574.1	573.7	573.3	573.0	572.6
140°	588.1	589.2	590.3	590.5	589.9	589.4	588.8	588.1
142.5°	603.6	604.5	605.5	605.7	605.1	604.5	603.9	603.3
145°	625.1	625.9	626.7	626.8	626.3	625.7	625.1	624.5
147.5°	643.9	644.5	645.1	645.1	644.7	644.2	643.7	643.2
150°	655.4	656.1	656.8	656.9	656.3	655.7	655.1	654.6
152.5°	666.0	666.7	667.4	667.3	666.6	665.8	665.0	664.3
155°	680.2	681.0	681.7	681.5	680.5	679.6	678.7	677.7
157.5°	692.2	693.0	693.8	693.8	692.8	691.9	690.9	690.0
160°	699.1	699.8	700.5	700.5	699.7	698.9	698.0	697.2
162.5°	705.7	706.5	707.3	707.2	706.2	705.2	704.2	703.2
165°	713.7	714.5	715.3	715.3	714.5	713.7	712.9	712.0
167.5°	720.2	721.1	722.0	721.9	720.7	719.7	718.6	717.6
170°	723.7	724.5	725.3	725.2	724.1	723.1	722.1	720.9
172.5°	726.2	727.0	727.8	727.7	726.7	725.6	724.6	723.5
175°	728.9	729.7	730.5	730.4	729.2	728.0	726.9	725.7
177.5°	729.2	729.9	730.5	730.4	729.6	728.7	727.9	727.1
180°	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3

(END OF REPORT)