

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331292

Luminaire Tested: **SA2XXDIP-C485D330U835-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331292  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXDIP-C485D330U835-4F0-1E-UDD-F1  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 330 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3148.4 lumens  
Efficiency: N/A  
Efficacy: 114.5 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 27.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331292

CATALOG NUMBER: SA2XXDIP-C485D330U835-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P331292

CATALOG NUMBER: SA2XXDIP-C485D330U835-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	79	79	79	68	68	68	63
1	101	96	92	89	94	90	87	84	79	77	74	69	67	66	60	59	57	53
2	92	84	78	72	86	79	73	69	70	65	62	61	58	55	53	50	48	44
3	84	74	66	60	78	70	63	58	61	56	52	54	50	46	47	44	41	38
4	77	66	57	51	71	62	54	49	55	49	44	48	43	40	42	38	35	32
5	70	58	50	44	66	55	48	42	49	43	38	43	38	35	38	34	31	28
6	65	53	44	38	61	50	42	37	44	38	33	39	34	30	34	30	27	25
7	60	48	39	34	56	45	38	32	40	34	30	36	31	27	31	27	24	22
8	56	43	35	30	52	41	34	29	37	31	26	33	28	24	29	25	22	20
9	52	40	32	27	49	38	30	26	34	28	24	30	25	22	27	23	20	18
10	49	36	29	24	46	35	28	23	31	25	21	28	23	20	25	21	18	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	12540	12540	12540
5°	12588	12407	12480
10°	12514	12281	12342
15°	12359	12122	12109
20°	12139	11883	11869
25°	11922	11589	11589
30°	11641	11320	11222
35°	11379	10996	10835
40°	11051	10673	10467
45°	10727	10351	10095
50°	10374	10017	9661
55°	10007	9627	9272
60°	9597	9164	8825
65°	9158	8703	8302
70°	8601	8143	7756
75°	7829	7498	7317
80°	6946	6732	6388
85°	5669	5391	4835



TEST NUMBER: P331292

CATALOG NUMBER: SA2XXDIP-C485D330U835-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	73.0	2.3
10°-20°	205.5	6.5
20°-30°	302.1	9.6
30°-40°	350.9	11.1
40°-50°	350.5	11.1
50°-60°	305.6	9.7
60°-70°	226.0	7.2
70°-80°	128.0	4.1
80°-90°	36.1	1.1
90°-100°	26.5	0.8
100°-110°	82.4	2.6
110°-120°	140.8	4.5
120°-130°	185.2	5.9
130°-140°	207.9	6.6
140°-150°	203.8	6.5
150°-160°	171.0	5.4
160°-170°	113.4	3.6
170°-180°	39.6	1.3
0°-30°	580.6	18.4
0°-40°	931.5	29.6
0°-60°	1587.6	50.4
0°-90°	1977.7	62.8
90°-120°	249.8	7.9
90°-150°	846.7	26.9
90°-180°	1171.0	37.2
0°-180°	3148.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	777	777	777	777	777	
5°	777	773	766	771	770	74
15°	739	735	725	728	724	208
25°	669	663	650	652	650	308
35°	577	570	558	553	550	360
45°	470	464	453	445	442	362
55°	356	351	342	333	329	318
65°	240	235	228	221	217	237
75°	126	124	120	116	117	134
85°	31	30	29	27	26	35
90°	0	5	12	12	12	2
95°	18	22	23	23	22	21
105°	76	77	78	78	78	80
115°	141	143	143	142	141	140
125°	206	209	208	207	206	184
135°	266	270	271	270	269	205
145°	323	325	328	328	326	202
155°	369	370	371	373	372	170
165°	402	401	401	404	402	113
175°	418	417	416	418	416	40
180°	419	419	419	419	419	



TEST NUMBER: P331292

CATALOG NUMBER: SA2XXDIP-C485D330U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	776.7	776.7	776.7	776.7	776.7	776.7	776.7	776.7	776.7	776.7	776.7
2.5°	780.3	779.6	779.0	778.3	777.6	776.6	775.1	773.7	772.2	770.7	772.1
5°	776.7	776.0	775.4	774.7	774.1	772.8	771.0	769.2	767.3	765.5	766.8
7.5°	769.8	768.8	767.8	766.7	765.7	764.3	762.4	760.6	758.7	756.8	758.2
10°	763.3	762.1	760.9	759.8	758.6	757.0	755.0	753.1	751.1	749.1	750.4
12.5°	754.3	753.3	752.2	751.2	750.2	748.7	746.7	744.7	742.7	740.7	741.6
15°	739.4	738.4	737.4	736.4	735.4	733.8	731.6	729.5	727.3	725.2	725.8
17.5°	720.2	719.3	718.3	717.3	716.3	714.7	712.5	710.3	708.1	705.9	706.7
20°	706.5	705.5	704.5	703.5	702.5	700.9	698.5	696.2	693.9	691.6	692.1
22.5°	692.8	691.4	690.0	688.6	687.2	685.4	683.2	681.0	678.8	676.6	676.7
25°	669.2	667.8	666.5	665.2	663.9	661.8	659.0	656.1	653.3	650.5	650.8
27.5°	642.3	641.1	639.9	638.7	637.5	635.8	633.6	631.3	629.1	626.9	626.4
30°	624.4	623.0	621.7	620.4	619.0	617.1	614.6	612.2	609.7	607.2	606.7
32.5°	605.2	604.2	603.1	602.0	601.0	599.1	596.5	593.9	591.3	588.7	587.8
35°	577.3	575.6	574.0	572.3	570.7	568.5	565.9	563.2	560.5	557.9	556.9
37.5°	545.8	544.3	542.9	541.4	539.9	537.9	535.2	532.6	529.9	527.3	526.0
40°	524.3	522.9	521.6	520.3	519.0	517.0	514.3	511.7	509.0	506.4	504.9
42.5°	503.4	502.0	500.7	499.4	498.1	496.1	493.4	490.8	488.1	485.4	483.8
45°	469.8	468.6	467.4	466.3	465.1	463.3	460.8	458.3	455.8	453.3	451.5
47.5°	436.3	435.2	434.1	433.0	431.9	430.1	427.5	424.9	422.3	419.7	417.8
50°	413.0	412.2	411.3	410.5	409.7	408.1	405.8	403.5	401.1	398.8	396.5
52.5°	390.3	389.2	388.1	387.0	385.9	384.3	382.1	379.9	377.7	375.5	373.6
55°	355.5	354.5	353.5	352.5	351.5	350.0	348.0	346.0	344.0	342.0	340.1
57.5°	320.5	319.7	318.9	318.2	317.4	315.9	313.7	311.5	309.3	307.1	305.1
60°	297.2	296.6	295.9	295.2	294.6	293.1	290.8	288.4	286.1	283.8	282.0
62.5°	274.5	273.5	272.4	271.3	270.3	268.9	267.1	265.3	263.5	261.7	260.0
65°	239.7	238.7	237.7	236.7	235.8	234.4	232.8	231.1	229.4	227.8	226.3
67.5°	204.3	203.5	202.7	201.9	201.1	200.0	198.5	197.0	195.5	194.0	192.9
70°	182.2	181.6	180.9	180.2	179.6	178.5	177.0	175.5	174.0	172.5	171.4
72.5°	159.5	158.9	158.2	157.5	156.9	156.1	155.1	154.1	153.2	152.2	151.0
75°	125.5	125.1	124.8	124.5	124.1	123.6	122.7	121.9	121.1	120.2	119.2
77.5°	95.0	94.4	93.9	93.3	92.7	92.3	92.0	91.6	91.3	91.0	90.5
80°	74.7	74.5	74.4	74.2	74.0	73.8	73.4	73.1	72.8	72.4	71.9
82.5°	55.6	55.5	55.5	55.5	55.4	55.3	55.1	54.9	54.7	54.5	53.9
85°	30.6	30.5	30.3	30.1	30.0	29.8	29.6	29.5	29.3	29.1	28.6
87.5°	10.8	10.7	10.7	10.6	10.5	10.5	10.6	10.7	10.8	10.8	10.4
90°	0.4	1.3	2.2	3.2	4.1	5.5	7.2	8.9	10.6	12.4	12.2
92.5°	6.3	7.0	7.7	8.4	9.1	9.6	10.0	10.4	10.8	11.2	11.3
95°	18.4	19.2	19.9	20.7	21.5	22.0	22.1	22.3	22.5	22.6	22.6
97.5°	33.6	34.3	34.9	35.6	36.3	36.8	37.1	37.4	37.7	38.0	38.0
100°	44.9	45.5	46.1	46.8	47.4	47.8	48.0	48.3	48.5	48.8	48.8
102.5°	56.7	57.2	57.7	58.2	58.7	59.2	59.4	59.7	60.0	60.3	60.4
105°	76.0	76.2	76.4	76.7	76.9	77.1	77.3	77.4	77.6	77.7	77.9
107.5°	95.3	95.7	96.0	96.4	96.7	96.9	96.9	96.9	96.9	96.9	96.9
110°	107.8	108.2	108.7	109.2	109.6	109.9	109.9	109.9	109.9	109.9	109.9



TEST NUMBER: P331292

CATALOG NUMBER: SA2XXDIP-C485D330U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	121.3	121.8	122.3	122.7	123.2	123.4	123.3	123.3	123.2	123.2	123.0
115°	141.3	141.8	142.3	142.7	143.2	143.4	143.2	143.0	142.9	142.7	142.7
117.5°	161.2	161.9	162.5	163.1	163.8	163.9	163.4	163.0	162.5	162.1	161.9
120°	174.5	175.2	175.8	176.4	177.0	177.0	176.4	175.8	175.2	174.5	174.5
122.5°	186.7	187.4	188.2	188.9	189.7	189.9	189.4	189.0	188.5	188.1	187.9
125°	205.6	206.3	207.0	207.7	208.4	208.7	208.4	208.2	208.0	207.7	207.5
127.5°	224.1	225.0	225.9	226.7	227.6	227.9	227.7	227.4	227.1	226.8	226.5
130°	235.7	236.7	237.7	238.7	239.7	240.2	240.0	239.9	239.7	239.5	239.4
132.5°	248.7	249.5	250.3	251.1	252.0	252.4	252.4	252.5	252.5	252.5	252.2
135°	266.0	266.9	267.8	268.6	269.5	270.0	270.2	270.3	270.5	270.6	270.5
137.5°	284.3	285.0	285.7	286.5	287.2	287.6	287.8	288.0	288.2	288.4	288.4
140°	295.4	296.1	296.8	297.5	298.2	298.7	299.1	299.5	299.9	300.3	300.3
142.5°	306.7	307.4	308.1	308.8	309.5	310.0	310.2	310.5	310.8	311.0	311.1
145°	322.9	323.5	324.0	324.6	325.1	325.6	326.1	326.6	327.0	327.5	327.6
147.5°	337.4	338.1	338.7	339.4	340.0	340.5	340.8	341.2	341.5	341.8	342.0
150°	347.3	347.8	348.2	348.7	349.2	349.6	349.9	350.2	350.5	350.8	351.1
152.5°	356.1	356.5	357.0	357.5	357.9	358.4	358.7	359.1	359.5	359.9	360.2
155°	369.2	369.4	369.7	369.9	370.1	370.4	370.6	370.8	371.1	371.3	371.7
157.5°	380.4	380.6	380.7	380.9	381.1	381.2	381.4	381.5	381.6	381.8	382.3
160°	387.2	387.4	387.5	387.7	387.8	388.0	388.0	388.1	388.2	388.3	388.7
162.5°	393.4	393.5	393.5	393.5	393.6	393.6	393.7	393.8	393.9	393.9	394.5
165°	401.7	401.6	401.5	401.5	401.4	401.3	401.3	401.3	401.3	401.3	401.9
167.5°	408.6	408.4	408.2	407.9	407.7	407.6	407.5	407.5	407.5	407.5	408.0
170°	412.3	412.1	411.8	411.6	411.4	411.2	411.1	411.0	411.0	410.9	411.4
172.5°	414.8	414.6	414.4	414.1	413.9	413.7	413.7	413.6	413.5	413.4	414.0
175°	418.0	417.7	417.5	417.2	417.0	416.8	416.7	416.5	416.3	416.2	416.7
177.5°	419.2	419.0	418.8	418.7	418.5	418.3	418.2	418.1	417.9	417.8	418.2
180°	418.7	418.7	418.7	418.7	418.7	418.7	418.7	418.7	418.7	418.7	418.7



TEST NUMBER: P331292

CATALOG NUMBER: SA2XXDIP-C485D330U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	776.7	776.7	776.7	776.7	776.7	776.7	776.7	776.7
2.5°	773.4	774.7	776.0	776.6	776.3	776.0	775.8	775.5
5°	768.2	769.5	770.8	771.3	771.0	770.6	770.3	770.0
7.5°	759.5	760.8	762.2	762.6	762.3	761.9	761.5	761.2
10°	751.7	753.1	754.4	754.8	754.3	753.8	753.3	752.8
12.5°	742.6	743.5	744.4	744.7	744.3	744.0	743.6	743.2
15°	726.5	727.2	727.8	727.7	726.9	726.1	725.3	724.4
17.5°	707.4	708.2	709.0	708.9	708.1	707.4	706.6	705.8
20°	692.6	693.1	693.6	693.5	692.8	692.1	691.5	690.8
22.5°	676.8	676.9	677.0	676.9	676.5	676.1	675.7	675.3
25°	651.2	651.5	651.8	651.8	651.5	651.2	650.8	650.5
27.5°	625.9	625.4	624.9	624.3	623.5	622.7	621.9	621.1
30°	606.2	605.7	605.2	604.6	603.9	603.3	602.6	601.9
32.5°	586.9	586.0	585.1	584.3	583.6	583.0	582.3	581.6
35°	555.9	554.9	553.9	553.0	552.2	551.3	550.5	549.7
37.5°	524.8	523.6	522.4	521.3	520.5	519.7	518.9	518.2
40°	503.4	501.9	500.4	499.3	498.6	498.0	497.3	496.6
42.5°	482.2	480.6	478.9	477.7	476.7	475.8	474.9	473.9
45°	449.7	447.9	446.0	444.8	444.1	443.5	442.8	442.1
47.5°	415.9	413.9	412.0	410.6	409.6	408.7	407.7	406.7
50°	394.2	391.8	389.5	387.9	387.1	386.3	385.4	384.6
52.5°	371.7	369.7	367.8	366.3	365.2	364.1	363.0	361.9
55°	338.1	336.1	334.1	332.7	331.8	331.0	330.2	329.4
57.5°	303.2	301.2	299.3	298.0	297.3	296.7	296.1	295.4
60°	280.1	278.3	276.5	275.3	274.8	274.3	273.8	273.3
62.5°	258.3	256.6	254.9	253.8	253.1	252.5	251.9	251.2
65°	224.8	223.3	221.8	220.6	219.8	219.0	218.2	217.3
67.5°	191.7	190.5	189.4	188.5	187.8	187.1	186.5	185.8
70°	170.2	169.0	167.9	167.0	166.3	165.6	165.0	164.3
72.5°	149.9	148.7	147.6	146.7	146.2	145.6	145.1	144.6
75°	118.2	117.3	116.3	115.9	116.3	116.6	116.9	117.3
77.5°	90.0	89.5	89.0	88.5	88.0	87.6	87.1	86.6
80°	71.4	70.9	70.5	70.0	69.7	69.4	69.0	68.7
82.5°	53.3	52.6	52.0	51.6	51.6	51.5	51.4	51.4
85°	28.1	27.6	27.1	26.8	26.6	26.5	26.3	26.1
87.5°	10.0	9.5	9.1	8.8	8.7	8.6	8.5	8.4
90°	12.1	11.9	11.7	11.7	11.8	11.9	11.9	12.0
92.5°	11.3	11.3	11.4	11.4	11.4	11.4	11.4	11.4
95°	22.6	22.6	22.6	22.5	22.4	22.2	22.1	21.9
97.5°	38.0	38.0	38.0	38.0	38.0	38.0	38.0	37.9
100°	48.8	48.8	48.8	48.7	48.6	48.6	48.5	48.4
102.5°	60.5	60.5	60.6	60.6	60.5	60.4	60.4	60.3
105°	78.0	78.2	78.4	78.4	78.4	78.4	78.4	78.4
107.5°	97.0	97.1	97.1	97.0	96.6	96.3	95.9	95.5
110°	109.9	109.9	109.9	109.8	109.5	109.3	109.1	108.8





TEST NUMBER: P331292

CATALOG NUMBER: SA2XXDIP-C485D330U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	122.8	122.6	122.4	122.2	122.1	121.9	121.7	121.5
115°	142.6	142.5	142.4	142.3	142.0	141.8	141.6	141.3
117.5°	161.7	161.5	161.3	161.1	160.9	160.7	160.4	160.2
120°	174.5	174.5	174.5	174.4	174.2	173.9	173.7	173.5
122.5°	187.7	187.5	187.3	187.2	187.0	186.8	186.6	186.5
125°	207.3	207.0	206.8	206.6	206.6	206.5	206.4	206.3
127.5°	226.3	226.0	225.7	225.4	225.2	224.9	224.7	224.4
130°	239.2	239.1	238.9	238.7	238.4	238.0	237.7	237.4
132.5°	251.8	251.5	251.2	250.9	250.6	250.4	250.1	249.9
135°	270.5	270.4	270.3	270.2	269.9	269.7	269.5	269.2
137.5°	288.3	288.2	288.2	288.0	287.7	287.4	287.1	286.7
140°	300.3	300.3	300.3	300.1	299.8	299.5	299.2	298.9
142.5°	311.2	311.2	311.3	311.2	310.9	310.5	310.2	309.9
145°	327.7	327.7	327.8	327.7	327.4	327.1	326.8	326.4
147.5°	342.1	342.3	342.5	342.4	342.1	341.8	341.5	341.2
150°	351.3	351.5	351.8	351.8	351.5	351.3	351.1	350.8
152.5°	360.5	360.8	361.1	361.1	360.8	360.5	360.2	359.9
155°	372.1	372.5	372.9	373.0	372.7	372.5	372.3	372.0
157.5°	382.8	383.4	383.9	384.0	383.6	383.2	382.9	382.5
160°	389.2	389.7	390.2	390.2	389.9	389.6	389.3	389.0
162.5°	395.0	395.5	396.1	396.1	395.8	395.4	395.0	394.6
165°	402.4	403.0	403.5	403.6	403.2	402.8	402.4	402.1
167.5°	408.6	409.1	409.7	409.8	409.4	408.9	408.5	408.1
170°	412.0	412.5	413.1	413.1	412.7	412.2	411.7	411.2
172.5°	414.5	415.1	415.6	415.7	415.2	414.7	414.3	413.8
175°	417.3	417.8	418.4	418.4	418.0	417.5	417.0	416.5
177.5°	418.6	418.9	419.3	419.3	418.9	418.6	418.2	417.8
180°	418.7	418.7	418.7	418.7	418.7	418.7	418.7	418.7

(END OF REPORT)