

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331294

Luminaire Tested: **SA2XXDIP-C485D530U835-4F0-1E-UDD-A**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331294  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXDIP-C485D530U835-4F0-1E-UDD-A  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 530 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4259.2 lumens  
Efficiency: N/A  
Efficacy: 129.9 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 32.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331294  
CATALOG NUMBER: SA2XXDIP-C485D530U835-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P331294

CATALOG NUMBER: SA2XXDIP-C485D530U835-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	69	69	69	56	56	56	50
1	98	94	90	87	91	87	84	81	74	72	70	62	60	59	51	50	49	43
2	90	83	77	72	83	77	72	67	65	62	58	55	52	50	45	43	42	37
3	82	73	66	61	76	68	62	57	58	53	50	49	46	43	40	38	36	32
4	76	65	57	52	70	61	54	49	52	47	43	44	40	37	36	34	31	28
5	70	58	50	45	64	54	47	42	47	41	37	40	36	32	33	30	28	25
6	64	52	45	39	59	49	42	37	42	37	33	36	32	29	30	27	25	22
7	60	48	40	34	55	44	37	33	38	33	29	33	29	26	28	25	22	20
8	55	43	36	31	51	41	34	29	35	30	26	30	26	23	26	22	20	18
9	52	40	32	27	48	37	31	26	32	27	23	28	24	21	24	21	18	16
10	48	36	29	25	45	34	28	23	30	25	21	26	22	19	22	19	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	15689	15689	15689	15689
5°	17590	15793	13994	15793
10°	20156	15662	12111	15662
15°	22298	15375	10700	15375
20°	21959	15067	9754	15067
25°	19800	14656	9155	14656
30°	16362	14001	8718	14001
35°	11925	13316	8406	13316
40°	9525	12507	8233	12507
45°	8323	11572	7999	11572
50°	7824	10665	7842	10665
55°	7212	9745	7631	9745
60°	6610	8767	7308	8767
65°	6021	7889	6991	7889
70°	5467	7034	6524	7034
75°	4847	6082	5777	6082
80°	4166	5040	4649	5040
85°	3742	3742	2760	3742



TEST NUMBER: P331294

CATALOG NUMBER: SA2XXDIP-C485D530U835-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	92.5	2.2
10°-20°	269.0	6.3
20°-30°	390.5	9.2
30°-40°	412.0	9.7
40°-50°	364.8	8.6
50°-60°	291.1	6.8
60°-70°	197.9	4.6
70°-80°	101.5	2.4
80°-90°	26.2	0.6
90°-100°	24.1	0.6
100°-110°	88.2	2.1
110°-120°	235.8	5.5
120°-130°	389.3	9.1
130°-140°	414.0	9.7
140°-150°	384.8	9.0
150°-160°	309.4	7.3
160°-170°	199.4	4.7
170°-180°	68.6	1.6
0°-30°	752.0	17.7
0°-40°	1164.1	27.3
0°-60°	1820.1	42.7
0°-90°	2145.6	50.4
90°-120°	348.1	8.2
90°-150°	1536.2	36.1
90°-180°	2114.0	49.6
0°-180°	4259.2	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	972	972	972	972	972	
5°	1085	974	863	974	1085	108
15°	1334	920	640	920	1334	368
25°	1111	823	514	823	1111	502
35°	605	676	426	676	605	393
45°	364	507	350	507	364	287
55°	256	346	271	346	256	230
65°	158	206	183	206	158	157
75°	78	98	93	98	78	83
85°	20	20	15	20	20	22
90°	14	0	14	0	14	7
95°	22	34	22	34	22	21
105°	40	159	40	159	40	41
115°	43	300	43	300	43	107
125°	446	424	446	424	446	386
135°	542	525	542	525	542	418
145°	618	609	618	609	618	387
155°	671	671	671	671	671	310
165°	705	707	705	707	705	199
175°	719	723	719	723	719	68
180°	721	721	721	721	721	



TEST NUMBER: P331294

CATALOG NUMBER: SA2XXDIP-C485D530U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7
2.5°	1016.6	1016.9	1017.4	1012.7	1012.1	1012.1	1007.9	1004.3	1000.1	994.4	995.0
5°	1085.3	1089.4	1090.9	1086.4	1079.7	1078.9	1072.6	1062.1	1052.4	1044.6	1039.0
7.5°	1167.3	1168.9	1165.3	1159.4	1154.4	1145.4	1133.6	1122.0	1105.8	1090.9	1079.9
10°	1229.4	1231.7	1225.3	1216.7	1209.6	1199.2	1182.0	1164.4	1143.2	1122.6	1106.2
12.5°	1276.6	1282.2	1274.0	1272.9	1260.7	1246.4	1225.9	1217.0	1187.1	1158.5	1140.8
15°	1334.0	1333.6	1334.4	1327.3	1318.3	1316.1	1294.4	1270.9	1228.7	1211.9	1182.7
17.5°	1317.4	1323.1	1325.7	1325.6	1325.4	1324.0	1317.0	1302.2	1281.0	1253.8	1220.2
20°	1278.0	1285.4	1286.6	1295.2	1300.0	1306.4	1309.0	1304.9	1291.8	1269.0	1239.9
22.5°	1217.0	1219.1	1222.6	1236.0	1246.5	1262.4	1270.7	1284.5	1279.5	1268.4	1244.1
25°	1111.4	1107.7	1120.7	1127.5	1151.7	1177.1	1195.4	1215.6	1233.5	1244.4	1237.3
27.5°	984.6	979.0	998.6	1016.4	1036.1	1063.6	1092.1	1125.8	1153.8	1188.9	1200.9
30°	877.6	881.0	899.7	918.7	948.6	987.4	1019.5	1056.5	1096.5	1135.7	1162.9
32.5°	762.3	775.2	787.0	816.2	842.5	885.8	932.9	979.1	1029.0	1073.5	1115.7
35°	605.0	619.9	636.4	657.7	694.6	737.6	783.5	845.9	913.9	974.7	1024.8
37.5°	509.2	506.9	516.3	531.7	561.6	596.3	649.1	710.8	790.8	862.3	932.9
40°	451.9	450.4	457.1	471.3	494.1	519.5	565.8	619.9	694.3	781.6	865.7
42.5°	412.4	413.3	417.1	427.1	442.7	463.6	498.3	544.4	612.4	694.7	785.0
45°	364.5	367.1	371.2	376.1	385.0	402.2	421.6	454.5	508.3	577.0	665.9
47.5°	330.0	330.1	334.2	338.5	343.8	353.5	369.4	390.0	427.9	483.9	560.3
50°	311.5	308.8	311.8	315.2	320.8	327.5	338.0	357.4	382.8	428.0	491.8
52.5°	288.8	288.8	291.5	292.8	297.8	304.5	314.1	327.5	350.5	385.9	438.4
55°	256.2	258.1	259.6	261.8	266.3	271.1	278.6	287.6	305.5	332.0	370.8
57.5°	225.6	226.2	227.7	231.9	234.8	239.2	246.3	254.5	266.1	285.8	315.0
60°	204.7	204.7	207.6	209.5	213.2	217.7	223.3	231.2	241.6	257.7	281.2
62.5°	185.5	185.2	186.4	189.5	192.3	196.5	202.1	208.8	218.6	232.9	252.2
65°	157.6	156.9	159.1	159.8	162.8	166.9	171.4	178.5	186.4	196.8	214.0
67.5°	130.7	131.6	132.8	134.2	135.9	140.2	143.2	148.2	154.8	163.5	175.2
70°	115.8	115.8	115.8	116.9	119.1	121.4	124.4	128.5	134.8	142.3	152.7
72.5°	99.0	100.2	101.4	100.8	103.6	104.9	108.5	110.8	116.9	121.7	130.9
75°	77.7	77.7	77.7	79.5	80.7	81.8	84.0	86.3	89.3	95.2	100.1
77.5°	58.0	57.8	58.2	58.6	59.8	61.2	61.8	63.9	66.6	69.4	73.5
80°	44.8	45.6	45.9	46.7	46.7	47.4	47.8	50.4	52.3	54.2	56.8
82.5°	34.7	34.8	34.9	35.0	35.3	35.8	36.7	37.6	38.2	39.8	41.8
85°	20.2	19.8	19.8	20.5	20.2	20.2	20.9	21.7	21.7	22.0	23.2
87.5°	10.6	10.5	10.8	10.4	10.4	10.6	10.5	10.1	10.3	10.5	10.6
90°	14.1	13.9	13.6	13.4	13.2	12.8	12.2	11.6	11.0	10.4	9.5
92.5°	14.1	14.0	13.8	13.7	13.5	13.3	13.0	12.7	12.4	12.1	11.6
95°	22.4	22.6	22.7	22.8	22.9	22.7	22.1	21.5	20.9	20.4	19.5
97.5°	30.0	29.8	29.7	29.5	29.4	29.1	28.6	28.2	27.7	27.2	25.4
100°	35.0	34.7	34.5	34.3	34.0	33.5	32.5	31.6	30.7	29.7	27.8
102.5°	37.5	37.1	36.8	36.5	36.2	35.4	34.2	33.0	31.8	30.6	27.1
105°	39.7	39.2	38.7	38.3	37.8	36.9	35.7	34.4	33.1	31.8	27.5
107.5°	40.8	40.3	39.9	39.4	39.0	39.4	40.7	42.0	43.3	44.6	42.5
110°	41.2	40.8	40.3	39.8	39.4	44.9	56.5	68.1	79.7	91.3	124.8



TEST NUMBER: P331294

CATALOG NUMBER: SA2XXDIP-C485D530U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	41.6	41.3	40.9	40.5	40.2	61.1	103.4	145.7	188.0	230.4	238.6
115°	42.8	51.1	59.5	67.8	76.2	107.2	160.9	214.6	268.3	322.0	319.1
117.5°	174.7	202.2	229.6	257.0	284.5	304.7	317.7	330.7	343.7	356.6	354.7
120°	318.3	334.0	349.7	365.3	381.0	388.1	386.7	385.3	383.9	382.5	380.4
122.5°	397.2	400.3	403.3	406.4	409.4	410.5	409.7	408.8	408.0	407.2	404.9
125°	446.2	445.9	445.5	445.2	444.8	444.2	443.4	442.6	441.8	441.0	438.8
127.5°	477.1	477.0	477.0	476.9	476.8	476.2	475.0	473.8	472.6	471.5	469.8
130°	496.3	496.4	496.5	496.6	496.8	496.2	494.9	493.6	492.4	491.1	489.8
132.5°	515.1	515.2	515.3	515.4	515.5	515.1	514.0	512.9	511.8	510.7	509.4
135°	542.2	542.5	542.7	542.9	543.2	542.7	541.5	540.4	539.2	538.0	537.0
137.5°	567.0	567.4	567.7	568.1	568.5	568.2	567.0	565.9	564.8	563.6	562.4
140°	582.4	583.0	583.6	584.1	584.7	584.5	583.4	582.4	581.4	580.3	579.0
142.5°	597.4	598.0	598.6	599.2	599.8	599.6	598.6	597.7	596.7	595.8	594.3
145°	618.4	619.0	619.6	620.2	620.7	620.6	619.8	619.0	618.2	617.4	615.4
147.5°	636.9	637.4	637.9	638.4	638.8	638.8	638.2	637.6	637.0	636.4	634.4
150°	648.2	648.7	649.3	649.9	650.5	650.4	649.7	649.0	648.3	647.6	645.8
152.5°	657.8	658.5	659.3	660.1	660.8	660.9	660.2	659.5	658.8	658.1	656.3
155°	671.1	672.1	673.0	673.9	674.8	675.0	674.3	673.6	672.9	672.2	670.8
157.5°	683.3	684.2	685.1	686.0	687.0	687.0	686.2	685.4	684.6	683.9	682.9
160°	690.4	691.2	692.1	692.9	693.7	693.7	693.0	692.3	691.7	691.0	690.3
162.5°	696.3	697.3	698.3	699.3	700.3	700.4	699.6	698.8	698.0	697.2	696.6
165°	705.0	705.9	706.7	707.5	708.3	708.3	707.5	706.7	705.9	705.0	704.7
167.5°	710.6	711.6	712.7	713.7	714.8	714.9	714.1	713.2	712.4	711.6	711.3
170°	713.9	715.0	716.0	717.0	718.1	718.2	717.4	716.6	715.8	715.0	714.7
172.5°	716.4	717.5	718.5	719.6	720.6	720.7	719.9	719.1	718.3	717.5	717.2
175°	718.6	719.8	720.9	722.1	723.3	723.4	722.6	721.8	721.0	720.2	719.9
177.5°	720.0	720.8	721.6	722.5	723.3	723.4	722.8	722.1	721.5	720.8	720.7
180°	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2



TEST NUMBER: P331294

CATALOG NUMBER: SA2XXDIP-C485D530U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7
2.5°	997.1	994.7	993.2	987.9	983.1	978.3	976.8	977.4	970.8	964.6	961.9
5°	1036.0	1028.5	1021.4	1011.3	999.4	986.3	979.6	974.4	961.3	947.1	938.9
7.5°	1070.8	1060.1	1046.4	1027.5	1010.1	989.5	976.4	964.9	945.7	925.7	913.5
10°	1092.0	1077.4	1059.9	1036.7	1015.4	990.4	972.9	955.3	932.9	909.0	894.1
12.5°	1110.2	1090.6	1073.3	1043.6	1018.4	987.1	966.3	941.6	918.0	889.6	874.9
15°	1153.6	1117.4	1084.5	1050.9	1019.9	976.2	953.1	919.8	888.8	853.7	836.9
17.5°	1187.1	1146.4	1094.7	1052.0	1015.8	967.4	933.4	893.6	856.9	816.8	794.0
20°	1206.3	1159.6	1103.9	1053.2	1009.8	954.6	917.6	876.9	833.9	788.7	764.1
22.5°	1217.6	1168.6	1113.5	1048.7	997.9	944.1	897.6	853.0	809.4	760.7	734.8
25°	1221.2	1176.4	1118.1	1044.9	982.9	922.1	866.0	822.7	770.1	724.5	686.8
27.5°	1203.4	1171.3	1115.3	1037.9	965.7	894.5	832.1	783.0	727.4	678.0	640.0
30°	1181.6	1162.9	1108.4	1030.7	951.9	875.4	806.7	751.0	695.8	645.7	606.9
32.5°	1147.9	1143.8	1095.9	1020.6	937.3	851.2	780.1	723.8	662.6	613.4	576.4
35°	1081.5	1099.5	1069.2	997.9	909.7	816.8	739.8	675.6	612.1	565.0	530.3
37.5°	992.7	1037.2	1029.3	964.6	872.5	779.3	694.3	627.2	566.7	519.2	485.1
40°	931.4	988.2	996.4	939.2	846.3	750.3	660.3	593.4	534.4	491.1	456.7
42.5°	865.7	932.0	954.6	908.8	817.6	719.8	629.8	560.6	502.2	460.0	429.6
45°	755.5	843.3	884.0	857.8	769.7	669.6	577.0	506.8	453.8	414.2	390.6
47.5°	652.5	748.4	803.2	793.9	716.4	617.3	525.8	458.4	406.8	375.2	354.1
50°	579.6	678.2	744.3	747.3	678.2	580.0	488.1	424.6	377.2	347.7	330.5
52.5°	516.3	610.4	682.5	698.3	635.5	541.1	454.3	391.2	349.4	322.3	306.9
55°	433.6	513.1	593.1	622.2	571.8	482.1	401.8	346.2	307.0	288.3	274.9
57.5°	360.5	426.8	500.6	532.8	501.7	425.0	349.7	301.4	269.6	253.2	242.9
60°	321.9	374.2	439.9	478.4	451.5	383.2	317.4	271.5	245.4	230.8	221.1
62.5°	286.1	332.4	387.9	423.1	408.5	344.0	285.2	244.6	222.1	208.4	201.4
65°	236.0	272.6	315.6	348.1	338.4	289.4	241.3	206.5	188.6	177.8	172.2
67.5°	194.3	220.8	250.6	279.0	271.2	236.5	197.9	170.8	157.4	148.1	144.8
70°	168.1	188.2	214.7	237.5	231.2	202.8	172.2	149.0	137.4	129.6	126.2
72.5°	143.0	159.5	179.8	198.4	194.1	170.5	145.0	127.5	118.6	111.4	108.6
75°	107.9	120.6	133.0	145.3	144.2	125.9	110.9	97.5	90.4	84.8	83.7
77.5°	79.7	86.8	95.2	102.5	100.5	90.0	78.3	70.6	65.4	61.6	61.0
80°	60.9	65.0	71.0	76.2	73.6	69.1	59.8	54.2	50.4	46.7	45.2
82.5°	44.1	48.3	51.8	54.7	52.7	48.5	42.7	38.9	36.7	34.1	33.5
85°	23.2	25.4	26.9	27.6	26.9	24.3	21.7	20.2	18.3	17.2	16.8
87.5°	10.7	10.5	10.3	10.7	9.5	9.3	7.8	6.7	6.6	6.6	6.2
90°	8.6	7.7	6.7	5.6	4.3	3.1	1.8	0.5	1.8	3.1	4.3
92.5°	11.2	10.7	10.3	10.1	10.2	10.3	10.4	10.5	10.4	10.3	10.2
95°	18.7	17.9	17.1	18.6	22.4	26.3	30.1	33.9	30.1	26.3	22.4
97.5°	23.5	21.6	19.7	24.2	35.0	45.8	56.5	67.3	56.5	45.8	35.0
100°	25.8	23.8	21.9	28.8	44.7	60.6	76.5	92.4	76.5	60.6	44.7
102.5°	63.6	80.1	96.5	106.5	109.8	113.2	116.6	119.9	116.6	113.2	109.8
105°	95.2	126.8	158.5	172.6	169.1	165.6	162.1	158.6	162.1	165.6	169.1
107.5°	120.5	158.5	196.4	214.0	211.2	208.4	205.6	202.8	205.6	208.4	211.2
110°	158.4	191.9	225.4	240.9	238.5	236.1	233.6	231.2	233.6	236.1	238.5





TEST NUMBER: P331294

CATALOG NUMBER: SA2XXDIP-C485D530U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	246.9	255.2	263.5	266.5	264.4	262.2	260.1	257.9	260.1	262.2	264.4
115°	316.2	313.3	310.4	308.0	306.0	304.0	302.0	300.1	302.0	304.0	306.0
117.5°	352.7	350.7	348.7	346.6	344.4	342.2	340.0	337.8	340.0	342.2	344.4
120°	378.4	376.3	374.2	372.3	370.5	368.8	367.0	365.3	367.0	368.8	370.5
122.5°	402.6	400.3	398.1	396.0	394.2	392.4	390.5	388.7	390.5	392.4	394.2
125°	436.6	434.4	432.2	430.3	428.8	427.3	425.8	424.3	425.8	427.3	428.8
127.5°	468.2	466.5	464.9	463.2	461.5	459.9	458.2	456.5	458.2	459.9	461.5
130°	488.5	487.3	486.0	484.4	482.6	480.7	478.8	477.0	478.8	480.7	482.6
132.5°	508.2	506.9	505.6	504.2	502.6	501.0	499.4	497.9	499.4	501.0	502.6
135°	536.0	534.9	533.9	532.4	530.6	528.7	526.9	525.0	526.9	528.7	530.6
137.5°	561.3	560.1	558.9	557.6	556.3	555.0	553.7	552.5	553.7	555.0	556.3
140°	577.8	576.5	575.2	574.1	573.2	572.3	571.3	570.4	571.3	572.3	573.2
142.5°	592.8	591.4	589.9	588.8	587.9	587.1	586.3	585.4	586.3	587.1	587.9
145°	613.4	611.5	609.5	608.6	608.7	608.8	608.9	609.0	608.9	608.8	608.7
147.5°	632.5	630.5	628.6	627.8	628.3	628.7	629.1	629.6	629.1	628.7	628.3
150°	643.9	642.1	640.2	639.7	640.5	641.3	642.1	642.9	642.1	641.3	640.5
152.5°	654.6	652.8	651.0	650.6	651.5	652.4	653.3	654.2	653.3	652.4	651.5
155°	669.4	668.0	666.6	666.4	667.5	668.5	669.6	670.6	669.6	668.5	667.5
157.5°	681.9	680.9	680.0	679.9	680.8	681.7	682.6	683.4	682.6	681.7	680.8
160°	689.6	688.9	688.2	688.2	688.9	689.6	690.3	691.0	690.3	689.6	688.9
162.5°	696.0	695.4	694.8	694.9	695.5	696.2	696.9	697.6	696.9	696.2	695.5
165°	704.3	704.0	703.7	703.8	704.5	705.2	705.9	706.6	705.9	705.2	704.5
167.5°	711.0	710.6	710.3	710.5	711.2	711.9	712.6	713.3	712.6	711.9	711.2
170°	714.5	714.3	714.0	714.3	715.0	715.7	716.4	717.0	716.4	715.7	715.0
172.5°	717.0	716.8	716.5	716.8	717.5	718.2	718.9	719.6	718.9	718.2	717.5
175°	719.7	719.5	719.3	719.5	720.4	721.2	722.0	722.8	722.0	721.2	720.4
177.5°	720.6	720.5	720.4	720.7	721.4	722.0	722.7	723.3	722.7	722.0	721.4
180°	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2



TEST NUMBER: P331294

CATALOG NUMBER: SA2XXDIP-C485D530U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7
2.5°	958.9	957.1	950.8	947.5	942.2	937.1	933.8	935.3	936.5	935.9	935.0
5°	931.4	924.3	913.5	904.1	897.4	885.1	879.9	877.3	875.0	872.4	869.8
7.5°	898.7	887.5	872.0	858.7	846.1	830.8	822.1	816.8	811.4	805.5	800.3
10°	875.4	859.7	843.3	824.6	809.7	795.8	783.5	775.3	767.8	760.7	755.5
12.5°	850.9	832.8	812.5	787.0	770.5	750.7	748.9	734.4	722.7	718.3	712.2
15°	811.9	786.5	760.7	730.5	717.4	699.5	688.3	677.1	667.0	659.9	658.0
17.5°	767.6	734.7	709.1	687.4	666.0	647.6	637.3	628.3	620.0	610.5	609.3
20°	733.8	705.5	677.5	658.4	636.4	617.7	605.0	596.0	588.9	583.3	578.5
22.5°	701.9	670.8	645.2	624.3	602.6	587.5	577.5	568.9	563.0	556.8	552.2
25°	650.6	626.3	598.3	574.8	556.8	547.1	538.9	531.4	527.7	523.6	518.4
27.5°	605.7	578.7	552.5	534.3	518.5	509.9	504.1	499.0	495.5	493.1	490.1
30°	574.0	546.7	526.2	508.3	495.2	486.6	482.9	479.9	475.8	474.3	472.8
32.5°	543.5	519.0	501.4	485.9	473.4	467.8	464.4	461.7	458.5	457.0	454.0
35°	500.4	479.9	462.7	454.1	444.0	439.2	436.6	432.8	429.9	428.4	428.0
37.5°	459.9	442.0	430.7	419.7	415.4	412.4	408.9	406.3	405.4	405.2	404.8
40°	433.6	419.0	408.9	400.0	398.1	393.6	390.6	388.4	388.4	388.8	388.4
42.5°	409.7	396.6	387.7	380.0	377.8	375.1	372.1	372.0	372.6	373.8	372.6
45°	373.5	364.1	357.8	354.0	349.9	347.3	346.9	348.1	348.4	348.8	349.9
47.5°	340.1	333.9	328.2	324.1	322.3	321.8	321.4	323.3	325.1	325.8	327.5
50°	320.4	313.3	308.5	305.9	304.4	303.6	304.4	306.6	308.1	310.0	311.1
52.5°	298.3	293.3	290.0	287.9	287.3	287.8	287.9	290.5	292.9	293.5	294.1
55°	267.8	264.0	263.3	259.9	261.4	261.0	262.9	264.4	266.6	268.9	269.3
57.5°	237.3	234.3	232.3	232.6	233.0	234.7	236.2	238.9	241.3	243.6	243.9
60°	217.0	215.5	214.4	214.4	215.1	217.4	219.2	221.8	223.3	224.8	225.9
62.5°	198.5	197.0	195.8	196.4	198.4	199.7	201.9	203.3	204.8	206.3	206.8
65°	169.2	168.4	169.6	170.3	170.7	172.5	175.2	176.3	177.8	178.5	181.1
67.5°	142.2	142.4	142.2	143.3	145.4	145.9	148.3	151.0	151.3	152.7	154.4
70°	124.0	124.7	125.5	126.2	128.1	128.8	130.7	131.8	133.3	134.4	135.6
72.5°	107.3	107.4	108.2	108.0	109.6	111.2	112.8	113.9	115.4	116.8	117.9
75°	82.5	82.5	83.3	83.7	85.5	87.4	87.0	87.8	89.3	90.8	91.5
77.5°	60.3	59.5	60.3	60.6	61.2	62.8	63.1	64.2	65.9	65.4	66.2
80°	45.9	44.8	45.9	46.3	46.3	48.2	48.2	48.9	50.0	48.9	50.0
82.5°	32.8	32.3	33.1	33.2	33.8	33.8	34.4	34.6	35.7	35.2	35.7
85°	16.4	16.1	16.4	16.1	16.4	16.8	16.8	16.4	16.4	17.2	16.1
87.5°	6.2	6.1	6.0	6.2	6.1	6.0	5.8	5.9	6.0	5.5	5.6
90°	5.6	6.7	7.7	8.6	9.5	10.4	11.0	11.6	12.2	12.8	13.2
92.5°	10.1	10.3	10.7	11.2	11.6	12.1	12.4	12.7	13.0	13.3	13.5
95°	18.6	17.1	17.9	18.7	19.5	20.4	20.9	21.5	22.1	22.7	22.9
97.5°	24.2	19.7	21.6	23.5	25.4	27.2	27.7	28.2	28.6	29.1	29.4
100°	28.8	21.9	23.8	25.8	27.8	29.7	30.7	31.6	32.5	33.5	34.0
102.5°	106.5	96.5	80.1	63.6	47.1	30.6	31.8	33.0	34.2	35.4	36.2
105°	172.6	158.5	126.8	95.2	63.5	31.8	33.1	34.4	35.7	36.9	37.8
107.5°	214.0	196.4	158.5	120.5	82.5	44.6	43.3	42.0	40.7	39.4	39.0
110°	240.9	225.4	191.9	158.4	124.8	91.3	79.7	68.1	56.5	44.9	39.4



TEST NUMBER: P331294

CATALOG NUMBER: SA2XXDIP-C485D530U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	266.5	263.5	255.2	246.9	238.6	230.4	188.0	145.7	103.4	61.1	40.2
115°	308.0	310.4	313.3	316.2	319.1	322.0	268.3	214.6	160.9	107.2	76.2
117.5°	346.6	348.7	350.7	352.7	354.7	356.6	343.7	330.7	317.7	304.7	284.5
120°	372.3	374.2	376.3	378.4	380.4	382.5	383.9	385.3	386.7	388.1	381.0
122.5°	396.0	398.1	400.3	402.6	404.9	407.2	408.0	408.8	409.7	410.5	409.4
125°	430.3	432.2	434.4	436.6	438.8	441.0	441.8	442.6	443.4	444.2	444.8
127.5°	463.2	464.9	466.5	468.2	469.8	471.5	472.6	473.8	475.0	476.2	476.8
130°	484.4	486.0	487.3	488.5	489.8	491.1	492.4	493.6	494.9	496.2	496.8
132.5°	504.2	505.6	506.9	508.2	509.4	510.7	511.8	512.9	514.0	515.1	515.5
135°	532.4	533.9	534.9	536.0	537.0	538.0	539.2	540.4	541.5	542.7	543.2
137.5°	557.6	558.9	560.1	561.3	562.4	563.6	564.8	565.9	567.0	568.2	568.5
140°	574.1	575.2	576.5	577.8	579.0	580.3	581.4	582.4	583.4	584.5	584.7
142.5°	588.8	589.9	591.4	592.8	594.3	595.8	596.7	597.7	598.6	599.6	599.8
145°	608.6	609.5	611.5	613.4	615.4	617.4	618.2	619.0	619.8	620.6	620.7
147.5°	627.8	628.6	630.5	632.5	634.4	636.4	637.0	637.6	638.2	638.8	638.8
150°	639.7	640.2	642.1	643.9	645.8	647.6	648.3	649.0	649.7	650.4	650.5
152.5°	650.6	651.0	652.8	654.6	656.3	658.1	658.8	659.5	660.2	660.9	660.8
155°	666.4	666.6	668.0	669.4	670.8	672.2	672.9	673.6	674.3	675.0	674.8
157.5°	679.9	680.0	680.9	681.9	682.9	683.9	684.6	685.4	686.2	687.0	687.0
160°	688.2	688.2	688.9	689.6	690.3	691.0	691.7	692.3	693.0	693.7	693.7
162.5°	694.9	694.8	695.4	696.0	696.6	697.2	698.0	698.8	699.6	700.4	700.3
165°	703.8	703.7	704.0	704.3	704.7	705.0	705.9	706.7	707.5	708.3	708.3
167.5°	710.5	710.3	710.6	711.0	711.3	711.6	712.4	713.2	714.1	714.9	714.8
170°	714.3	714.0	714.3	714.5	714.7	715.0	715.8	716.6	717.4	718.2	718.1
172.5°	716.8	716.5	716.8	717.0	717.2	717.5	718.3	719.1	719.9	720.7	720.6
175°	719.5	719.3	719.5	719.7	719.9	720.2	721.0	721.8	722.6	723.4	723.3
177.5°	720.7	720.4	720.5	720.6	720.7	720.8	721.5	722.1	722.8	723.4	723.3
180°	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2



TEST NUMBER: P331294

CATALOG NUMBER: SA2XXDIP-C485D530U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7
2.5°	932.0	931.4	931.4	928.7	931.4	931.4	932.0	935.0	935.9	936.5	935.3
5°	864.6	863.4	861.6	863.4	861.6	863.4	864.6	869.8	872.4	875.0	877.3
7.5°	797.9	793.4	792.7	788.3	792.7	793.4	797.9	800.3	805.5	811.4	816.8
10°	749.2	746.2	745.8	738.7	745.8	746.2	749.2	755.5	760.7	767.8	775.3
12.5°	712.1	704.9	706.4	702.3	706.4	704.9	712.1	712.2	718.3	722.7	734.4
15°	647.9	647.9	646.5	640.1	646.5	647.9	647.9	658.0	659.9	667.0	677.1
17.5°	601.9	601.1	597.5	599.3	597.5	601.1	601.9	609.3	610.5	620.0	628.3
20°	574.4	572.1	567.7	567.7	567.7	572.1	574.4	578.5	583.3	588.9	596.0
22.5°	548.4	548.2	543.5	545.0	543.5	548.2	548.4	552.2	556.8	563.0	568.9
25°	518.0	515.0	512.8	513.9	512.8	515.0	518.0	518.4	523.6	527.7	531.4
27.5°	489.2	487.5	487.4	484.3	487.4	487.5	489.2	490.1	493.1	495.5	499.0
30°	472.4	468.7	469.4	467.6	469.4	468.7	472.4	472.8	474.3	475.8	479.9
32.5°	453.3	452.0	451.2	449.6	451.2	452.0	453.3	454.0	457.0	458.5	461.7
35°	427.2	427.6	425.7	426.5	425.7	427.6	427.2	428.0	428.4	429.9	432.8
37.5°	404.5	405.7	404.8	405.0	404.8	405.7	404.5	404.8	405.2	405.4	406.3
40°	389.5	389.5	389.5	390.6	389.5	389.5	389.5	388.4	388.8	388.4	388.4
42.5°	375.2	374.6	374.0	373.9	374.0	374.6	375.2	372.6	373.8	372.6	372.0
45°	350.7	351.8	352.2	350.3	352.2	351.8	350.7	349.9	348.8	348.4	348.1
47.5°	328.5	328.6	328.5	330.1	328.5	328.6	328.5	327.5	325.8	325.1	323.3
50°	313.0	312.2	313.0	312.2	313.0	312.2	313.0	311.1	310.0	308.1	306.6
52.5°	296.5	296.7	296.2	296.1	296.2	296.7	296.5	294.1	293.5	292.9	290.5
55°	270.8	271.5	271.1	271.1	271.1	271.5	270.8	269.3	268.9	266.6	264.4
57.5°	244.1	244.8	245.3	243.6	245.3	244.8	244.1	243.9	243.6	241.3	238.9
60°	225.6	227.4	227.1	226.3	227.1	227.4	225.6	225.9	224.8	223.3	221.8
62.5°	208.5	209.2	209.1	209.0	209.1	209.2	208.5	206.8	206.3	204.8	203.3
65°	182.2	183.0	181.9	183.0	181.9	183.0	182.2	181.1	178.5	177.8	176.3
67.5°	153.9	154.2	155.0	155.5	155.0	154.2	153.9	154.4	152.7	151.3	151.0
70°	136.3	135.9	137.1	138.2	137.1	135.9	136.3	135.6	134.4	133.3	131.8
72.5°	117.8	118.6	118.2	119.1	118.2	118.6	117.8	117.9	116.8	115.4	113.9
75°	90.8	91.9	91.5	92.6	91.5	91.9	90.8	91.5	90.8	89.3	87.8
77.5°	65.6	65.7	65.6	66.2	65.6	65.7	65.6	66.2	65.4	65.9	64.2
80°	50.0	49.3	48.5	50.0	48.5	49.3	50.0	50.0	48.9	50.0	48.9
82.5°	34.8	35.3	34.5	34.5	34.5	35.3	34.8	35.7	35.2	35.7	34.6
85°	16.1	15.7	14.9	14.9	14.9	15.7	16.1	16.1	17.2	16.4	16.4
87.5°	5.7	5.4	5.5	5.2	5.5	5.4	5.7	5.6	5.5	6.0	5.9
90°	13.4	13.6	13.9	14.1	13.9	13.6	13.4	13.2	12.8	12.2	11.6
92.5°	13.7	13.8	14.0	14.1	14.0	13.8	13.7	13.5	13.3	13.0	12.7
95°	22.8	22.7	22.6	22.4	22.6	22.7	22.8	22.9	22.7	22.1	21.5
97.5°	29.5	29.7	29.8	30.0	29.8	29.7	29.5	29.4	29.1	28.6	28.2
100°	34.3	34.5	34.7	35.0	34.7	34.5	34.3	34.0	33.5	32.5	31.6
102.5°	36.5	36.8	37.1	37.5	37.1	36.8	36.5	36.2	35.4	34.2	33.0
105°	38.3	38.7	39.2	39.7	39.2	38.7	38.3	37.8	36.9	35.7	34.4
107.5°	39.4	39.9	40.3	40.8	40.3	39.9	39.4	39.0	39.4	40.7	42.0
110°	39.8	40.3	40.8	41.2	40.8	40.3	39.8	39.4	44.9	56.5	68.1



TEST NUMBER: P331294

CATALOG NUMBER: SA2XXDIP-C485D530U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	40.5	40.9	41.3	41.6	41.3	40.9	40.5	40.2	61.1	103.4	145.7
115°	67.8	59.5	51.1	42.8	51.1	59.5	67.8	76.2	107.2	160.9	214.6
117.5°	257.0	229.6	202.2	174.7	202.2	229.6	257.0	284.5	304.7	317.7	330.7
120°	365.3	349.7	334.0	318.3	334.0	349.7	365.3	381.0	388.1	386.7	385.3
122.5°	406.4	403.3	400.3	397.2	400.3	403.3	406.4	409.4	410.5	409.7	408.8
125°	445.2	445.5	445.9	446.2	445.9	445.5	445.2	444.8	444.2	443.4	442.6
127.5°	476.9	477.0	477.0	477.1	477.0	477.0	476.9	476.8	476.2	475.0	473.8
130°	496.6	496.5	496.4	496.3	496.4	496.5	496.6	496.8	496.2	494.9	493.6
132.5°	515.4	515.3	515.2	515.1	515.2	515.3	515.4	515.5	515.1	514.0	512.9
135°	542.9	542.7	542.5	542.2	542.5	542.7	542.9	543.2	542.7	541.5	540.4
137.5°	568.1	567.7	567.4	567.0	567.4	567.7	568.1	568.5	568.2	567.0	565.9
140°	584.1	583.6	583.0	582.4	583.0	583.6	584.1	584.7	584.5	583.4	582.4
142.5°	599.2	598.6	598.0	597.4	598.0	598.6	599.2	599.8	599.6	598.6	597.7
145°	620.2	619.6	619.0	618.4	619.0	619.6	620.2	620.7	620.6	619.8	619.0
147.5°	638.4	637.9	637.4	636.9	637.4	637.9	638.4	638.8	638.8	638.2	637.6
150°	649.9	649.3	648.7	648.2	648.7	649.3	649.9	650.5	650.4	649.7	649.0
152.5°	660.1	659.3	658.5	657.8	658.5	659.3	660.1	660.8	660.9	660.2	659.5
155°	673.9	673.0	672.1	671.1	672.1	673.0	673.9	674.8	675.0	674.3	673.6
157.5°	686.0	685.1	684.2	683.3	684.2	685.1	686.0	687.0	687.0	686.2	685.4
160°	692.9	692.1	691.2	690.4	691.2	692.1	692.9	693.7	693.7	693.0	692.3
162.5°	699.3	698.3	697.3	696.3	697.3	698.3	699.3	700.3	700.4	699.6	698.8
165°	707.5	706.7	705.9	705.0	705.9	706.7	707.5	708.3	708.3	707.5	706.7
167.5°	713.7	712.7	711.6	710.6	711.6	712.7	713.7	714.8	714.9	714.1	713.2
170°	717.0	716.0	715.0	713.9	715.0	716.0	717.0	718.1	718.2	717.4	716.6
172.5°	719.6	718.5	717.5	716.4	717.5	718.5	719.6	720.6	720.7	719.9	719.1
175°	722.1	720.9	719.8	718.6	719.8	720.9	722.1	723.3	723.4	722.6	721.8
177.5°	722.5	721.6	720.8	720.0	720.8	721.6	722.5	723.3	723.4	722.8	722.1
180°	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2



TEST NUMBER: P331294  
 CATALOG NUMBER: SA2XXDIP-C485D530U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7
2.5°	933.8	937.1	942.2	947.5	950.8	957.1	958.9	961.9	964.6	970.8	977.4
5°	879.9	885.1	897.4	904.1	913.5	924.3	931.4	938.9	947.1	961.3	974.4
7.5°	822.1	830.8	846.1	858.7	872.0	887.5	898.7	913.5	925.7	945.7	964.9
10°	783.5	795.8	809.7	824.6	843.3	859.7	875.4	894.1	909.0	932.9	955.3
12.5°	748.9	750.7	770.5	787.0	812.5	832.8	850.9	874.9	889.6	918.0	941.6
15°	688.3	699.5	717.4	730.5	760.7	786.5	811.9	836.9	853.7	888.8	919.8
17.5°	637.3	647.6	666.0	687.4	709.1	734.7	767.6	794.0	816.8	856.9	893.6
20°	605.0	617.7	636.4	658.4	677.5	705.5	733.8	764.1	788.7	833.9	876.9
22.5°	577.5	587.5	602.6	624.3	645.2	670.8	701.9	734.8	760.7	809.4	853.0
25°	538.9	547.1	556.8	574.8	598.3	626.3	650.6	686.8	724.5	770.1	822.7
27.5°	504.1	509.9	518.5	534.3	552.5	578.7	605.7	640.0	678.0	727.4	783.0
30°	482.9	486.6	495.2	508.3	526.2	546.7	574.0	606.9	645.7	695.8	751.0
32.5°	464.4	467.8	473.4	485.9	501.4	519.0	543.5	576.4	613.4	662.6	723.8
35°	436.6	439.2	444.0	454.1	462.7	479.9	500.4	530.3	565.0	612.1	675.6
37.5°	408.9	412.4	415.4	419.7	430.7	442.0	459.9	485.1	519.2	566.7	627.2
40°	390.6	393.6	398.1	400.0	408.9	419.0	433.6	456.7	491.1	534.4	593.4
42.5°	372.1	375.1	377.8	380.0	387.7	396.6	409.7	429.6	460.0	502.2	560.6
45°	346.9	347.3	349.9	354.0	357.8	364.1	373.5	390.6	414.2	453.8	506.8
47.5°	321.4	321.8	322.3	324.1	328.2	333.9	340.1	354.1	375.2	406.8	458.4
50°	304.4	303.6	304.4	305.9	308.5	313.3	320.4	330.5	347.7	377.2	424.6
52.5°	287.9	287.8	287.3	287.9	290.0	293.3	298.3	306.9	322.3	349.4	391.2
55°	262.9	261.0	261.4	259.9	263.3	264.0	267.8	274.9	288.3	307.0	346.2
57.5°	236.2	234.7	233.0	232.6	232.3	234.3	237.3	242.9	253.2	269.6	301.4
60°	219.2	217.4	215.1	214.4	214.4	215.5	217.0	221.1	230.8	245.4	271.5
62.5°	201.9	199.7	198.4	196.4	195.8	197.0	198.5	201.4	208.4	222.1	244.6
65°	175.2	172.5	170.7	170.3	169.6	168.4	169.2	172.2	177.8	188.6	206.5
67.5°	148.3	145.9	145.4	143.3	142.2	142.4	142.2	144.8	148.1	157.4	170.8
70°	130.7	128.8	128.1	126.2	125.5	124.7	124.0	126.2	129.6	137.4	149.0
72.5°	112.8	111.2	109.6	108.0	108.2	107.4	107.3	108.6	111.4	118.6	127.5
75°	87.0	87.4	85.5	83.7	83.3	82.5	82.5	83.7	84.8	90.4	97.5
77.5°	63.1	62.8	61.2	60.6	60.3	59.5	60.3	61.0	61.6	65.4	70.6
80°	48.2	48.2	46.3	46.3	45.9	44.8	45.9	45.2	46.7	50.4	54.2
82.5°	34.4	33.8	33.8	33.2	33.1	32.3	32.8	33.5	34.1	36.7	38.9
85°	16.8	16.8	16.4	16.1	16.4	16.1	16.4	16.8	17.2	18.3	20.2
87.5°	5.8	6.0	6.1	6.2	6.0	6.1	6.2	6.2	6.6	6.6	6.7
90°	11.0	10.4	9.5	8.6	7.7	6.7	5.6	4.3	3.1	1.8	0.5
92.5°	12.4	12.1	11.6	11.2	10.7	10.3	10.1	10.2	10.3	10.4	10.5
95°	20.9	20.4	19.5	18.7	17.9	17.1	18.6	22.4	26.3	30.1	33.9
97.5°	27.7	27.2	25.4	23.5	21.6	19.7	24.2	35.0	45.8	56.5	67.3
100°	30.7	29.7	27.8	25.8	23.8	21.9	28.8	44.7	60.6	76.5	92.4
102.5°	31.8	30.6	47.1	63.6	80.1	96.5	106.5	109.8	113.2	116.6	119.9
105°	33.1	31.8	63.5	95.2	126.8	158.5	172.6	169.1	165.6	162.1	158.6
107.5°	43.3	44.6	82.5	120.5	158.5	196.4	214.0	211.2	208.4	205.6	202.8
110°	79.7	91.3	124.8	158.4	191.9	225.4	240.9	238.5	236.1	233.6	231.2



TEST NUMBER: P331294

CATALOG NUMBER: SA2XXDIP-C485D530U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	188.0	230.4	238.6	246.9	255.2	263.5	266.5	264.4	262.2	260.1	257.9
115°	268.3	322.0	319.1	316.2	313.3	310.4	308.0	306.0	304.0	302.0	300.1
117.5°	343.7	356.6	354.7	352.7	350.7	348.7	346.6	344.4	342.2	340.0	337.8
120°	383.9	382.5	380.4	378.4	376.3	374.2	372.3	370.5	368.8	367.0	365.3
122.5°	408.0	407.2	404.9	402.6	400.3	398.1	396.0	394.2	392.4	390.5	388.7
125°	441.8	441.0	438.8	436.6	434.4	432.2	430.3	428.8	427.3	425.8	424.3
127.5°	472.6	471.5	469.8	468.2	466.5	464.9	463.2	461.5	459.9	458.2	456.5
130°	492.4	491.1	489.8	488.5	487.3	486.0	484.4	482.6	480.7	478.8	477.0
132.5°	511.8	510.7	509.4	508.2	506.9	505.6	504.2	502.6	501.0	499.4	497.9
135°	539.2	538.0	537.0	536.0	534.9	533.9	532.4	530.6	528.7	526.9	525.0
137.5°	564.8	563.6	562.4	561.3	560.1	558.9	557.6	556.3	555.0	553.7	552.5
140°	581.4	580.3	579.0	577.8	576.5	575.2	574.1	573.2	572.3	571.3	570.4
142.5°	596.7	595.8	594.3	592.8	591.4	589.9	588.8	587.9	587.1	586.3	585.4
145°	618.2	617.4	615.4	613.4	611.5	609.5	608.6	608.7	608.8	608.9	609.0
147.5°	637.0	636.4	634.4	632.5	630.5	628.6	627.8	628.3	628.7	629.1	629.6
150°	648.3	647.6	645.8	643.9	642.1	640.2	639.7	640.5	641.3	642.1	642.9
152.5°	658.8	658.1	656.3	654.6	652.8	651.0	650.6	651.5	652.4	653.3	654.2
155°	672.9	672.2	670.8	669.4	668.0	666.6	666.4	667.5	668.5	669.6	670.6
157.5°	684.6	683.9	682.9	681.9	680.9	680.0	679.9	680.8	681.7	682.6	683.4
160°	691.7	691.0	690.3	689.6	688.9	688.2	688.2	688.9	689.6	690.3	691.0
162.5°	698.0	697.2	696.6	696.0	695.4	694.8	694.9	695.5	696.2	696.9	697.6
165°	705.9	705.0	704.7	704.3	704.0	703.7	703.8	704.5	705.2	705.9	706.6
167.5°	712.4	711.6	711.3	711.0	710.6	710.3	710.5	711.2	711.9	712.6	713.3
170°	715.8	715.0	714.7	714.5	714.3	714.0	714.3	715.0	715.7	716.4	717.0
172.5°	718.3	717.5	717.2	717.0	716.8	716.5	716.8	717.5	718.2	718.9	719.6
175°	721.0	720.2	719.9	719.7	719.5	719.3	719.5	720.4	721.2	722.0	722.8
177.5°	721.5	720.8	720.7	720.6	720.5	720.4	720.7	721.4	722.0	722.7	723.3
180°	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2



TEST NUMBER: P331294  
 CATALOG NUMBER: SA2XXDIP-C485D530U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7
2.5°	976.8	978.3	983.1	987.9	993.2	994.7	997.1	995.0	994.4	1000.1	1004.3
5°	979.6	986.3	999.4	1011.3	1021.4	1028.5	1036.0	1039.0	1044.6	1052.4	1062.1
7.5°	976.4	989.5	1010.1	1027.5	1046.4	1060.1	1070.8	1079.9	1090.9	1105.8	1122.0
10°	972.9	990.4	1015.4	1036.7	1059.9	1077.4	1092.0	1106.2	1122.6	1143.2	1164.4
12.5°	966.3	987.1	1018.4	1043.6	1073.3	1090.6	1110.2	1140.8	1158.5	1187.1	1217.0
15°	953.1	976.2	1019.9	1050.9	1084.5	1117.4	1153.6	1182.7	1211.9	1228.7	1270.9
17.5°	933.4	967.4	1015.8	1052.0	1094.7	1146.4	1187.1	1220.2	1253.8	1281.0	1302.2
20°	917.6	954.6	1009.8	1053.2	1103.9	1159.6	1206.3	1239.9	1269.0	1291.8	1304.9
22.5°	897.6	944.1	997.9	1048.7	1113.5	1168.6	1217.6	1244.1	1268.4	1279.5	1284.5
25°	866.0	922.1	982.9	1044.9	1118.1	1176.4	1221.2	1237.3	1244.4	1233.5	1215.6
27.5°	832.1	894.5	965.7	1037.9	1115.3	1171.3	1203.4	1200.9	1188.9	1153.8	1125.8
30°	806.7	875.4	951.9	1030.7	1108.4	1162.9	1181.6	1162.9	1135.7	1096.5	1056.5
32.5°	780.1	851.2	937.3	1020.6	1095.9	1143.8	1147.9	1115.7	1073.5	1029.0	979.1
35°	739.8	816.8	909.7	997.9	1069.2	1099.5	1081.5	1024.8	974.7	913.9	845.9
37.5°	694.3	779.3	872.5	964.6	1029.3	1037.2	992.7	932.9	862.3	790.8	710.8
40°	660.3	750.3	846.3	939.2	996.4	988.2	931.4	865.7	781.6	694.3	619.9
42.5°	629.8	719.8	817.6	908.8	954.6	932.0	865.7	785.0	694.7	612.4	544.4
45°	577.0	669.6	769.7	857.8	884.0	843.3	755.5	665.9	577.0	508.3	454.5
47.5°	525.8	617.3	716.4	793.9	803.2	748.4	652.5	560.3	483.9	427.9	390.0
50°	488.1	580.0	678.2	747.3	744.3	678.2	579.6	491.8	428.0	382.8	357.4
52.5°	454.3	541.1	635.5	698.3	682.5	610.4	516.3	438.4	385.9	350.5	327.5
55°	401.8	482.1	571.8	622.2	593.1	513.1	433.6	370.8	332.0	305.5	287.6
57.5°	349.7	425.0	501.7	532.8	500.6	426.8	360.5	315.0	285.8	266.1	254.5
60°	317.4	383.2	451.5	478.4	439.9	374.2	321.9	281.2	257.7	241.6	231.2
62.5°	285.2	344.0	408.5	423.1	387.9	332.4	286.1	252.2	232.9	218.6	208.8
65°	241.3	289.4	338.4	348.1	315.6	272.6	236.0	214.0	196.8	186.4	178.5
67.5°	197.9	236.5	271.2	279.0	250.6	220.8	194.3	175.2	163.5	154.8	148.2
70°	172.2	202.8	231.2	237.5	214.7	188.2	168.1	152.7	142.3	134.8	128.5
72.5°	145.0	170.5	194.1	198.4	179.8	159.5	143.0	130.9	121.7	116.9	110.8
75°	110.9	125.9	144.2	145.3	133.0	120.6	107.9	100.1	95.2	89.3	86.3
77.5°	78.3	90.0	100.5	102.5	95.2	86.8	79.7	73.5	69.4	66.6	63.9
80°	59.8	69.1	73.6	76.2	71.0	65.0	60.9	56.8	54.2	52.3	50.4
82.5°	42.7	48.5	52.7	54.7	51.8	48.3	44.1	41.8	39.8	38.2	37.6
85°	21.7	24.3	26.9	27.6	26.9	25.4	23.2	23.2	22.0	21.7	21.7
87.5°	7.8	9.3	9.5	10.7	10.3	10.5	10.7	10.6	10.5	10.3	10.1
90°	1.8	3.1	4.3	5.6	6.7	7.7	8.6	9.5	10.4	11.0	11.6
92.5°	10.4	10.3	10.2	10.1	10.3	10.7	11.2	11.6	12.1	12.4	12.7
95°	30.1	26.3	22.4	18.6	17.1	17.9	18.7	19.5	20.4	20.9	21.5
97.5°	56.5	45.8	35.0	24.2	19.7	21.6	23.5	25.4	27.2	27.7	28.2
100°	76.5	60.6	44.7	28.8	21.9	23.8	25.8	27.8	29.7	30.7	31.6
102.5°	116.6	113.2	109.8	106.5	96.5	80.1	63.6	47.1	30.6	31.8	33.0
105°	162.1	165.6	169.1	172.6	158.5	126.8	95.2	63.5	31.8	33.1	34.4
107.5°	205.6	208.4	211.2	214.0	196.4	158.5	120.5	82.5	44.6	43.3	42.0
110°	233.6	236.1	238.5	240.9	225.4	191.9	158.4	124.8	91.3	79.7	68.1





TEST NUMBER: P331294

CATALOG NUMBER: SA2XXDIP-C485D530U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	260.1	262.2	264.4	266.5	263.5	255.2	246.9	238.6	230.4	188.0	145.7
115°	302.0	304.0	306.0	308.0	310.4	313.3	316.2	319.1	322.0	268.3	214.6
117.5°	340.0	342.2	344.4	346.6	348.7	350.7	352.7	354.7	356.6	343.7	330.7
120°	367.0	368.8	370.5	372.3	374.2	376.3	378.4	380.4	382.5	383.9	385.3
122.5°	390.5	392.4	394.2	396.0	398.1	400.3	402.6	404.9	407.2	408.0	408.8
125°	425.8	427.3	428.8	430.3	432.2	434.4	436.6	438.8	441.0	441.8	442.6
127.5°	458.2	459.9	461.5	463.2	464.9	466.5	468.2	469.8	471.5	472.6	473.8
130°	478.8	480.7	482.6	484.4	486.0	487.3	488.5	489.8	491.1	492.4	493.6
132.5°	499.4	501.0	502.6	504.2	505.6	506.9	508.2	509.4	510.7	511.8	512.9
135°	526.9	528.7	530.6	532.4	533.9	534.9	536.0	537.0	538.0	539.2	540.4
137.5°	553.7	555.0	556.3	557.6	558.9	560.1	561.3	562.4	563.6	564.8	565.9
140°	571.3	572.3	573.2	574.1	575.2	576.5	577.8	579.0	580.3	581.4	582.4
142.5°	586.3	587.1	587.9	588.8	589.9	591.4	592.8	594.3	595.8	596.7	597.7
145°	608.9	608.8	608.7	608.6	609.5	611.5	613.4	615.4	617.4	618.2	619.0
147.5°	629.1	628.7	628.3	627.8	628.6	630.5	632.5	634.4	636.4	637.0	637.6
150°	642.1	641.3	640.5	639.7	640.2	642.1	643.9	645.8	647.6	648.3	649.0
152.5°	653.3	652.4	651.5	650.6	651.0	652.8	654.6	656.3	658.1	658.8	659.5
155°	669.6	668.5	667.5	666.4	666.6	668.0	669.4	670.8	672.2	672.9	673.6
157.5°	682.6	681.7	680.8	679.9	680.0	680.9	681.9	682.9	683.9	684.6	685.4
160°	690.3	689.6	688.9	688.2	688.2	688.9	689.6	690.3	691.0	691.7	692.3
162.5°	696.9	696.2	695.5	694.9	694.8	695.4	696.0	696.6	697.2	698.0	698.8
165°	705.9	705.2	704.5	703.8	703.7	704.0	704.3	704.7	705.0	705.9	706.7
167.5°	712.6	711.9	711.2	710.5	710.3	710.6	711.0	711.3	711.6	712.4	713.2
170°	716.4	715.7	715.0	714.3	714.0	714.3	714.5	714.7	715.0	715.8	716.6
172.5°	718.9	718.2	717.5	716.8	716.5	716.8	717.0	717.2	717.5	718.3	719.1
175°	722.0	721.2	720.4	719.5	719.3	719.5	719.7	719.9	720.2	721.0	721.8
177.5°	722.7	722.0	721.4	720.7	720.4	720.5	720.6	720.7	720.8	721.5	722.1
180°	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2



TEST NUMBER: P331294

CATALOG NUMBER: SA2XXDIP-C485D530U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	971.7	971.7	971.7	971.7	971.7	971.7	971.7
2.5°	1007.9	1012.1	1012.1	1012.7	1017.4	1016.9	1016.6
5°	1072.6	1078.9	1079.7	1086.4	1090.9	1089.4	1085.3
7.5°	1133.6	1145.4	1154.4	1159.4	1165.3	1168.9	1167.3
10°	1182.0	1199.2	1209.6	1216.7	1225.3	1231.7	1229.4
12.5°	1225.9	1246.4	1260.7	1272.9	1274.0	1282.2	1276.6
15°	1294.4	1316.1	1318.3	1327.3	1334.4	1333.6	1334.0
17.5°	1317.0	1324.0	1325.4	1325.6	1325.7	1323.1	1317.4
20°	1309.0	1306.4	1300.0	1295.2	1286.6	1285.4	1278.0
22.5°	1270.7	1262.4	1246.5	1236.0	1222.6	1219.1	1217.0
25°	1195.4	1177.1	1151.7	1127.5	1120.7	1107.7	1111.4
27.5°	1092.1	1063.6	1036.1	1016.4	998.6	979.0	984.6
30°	1019.5	987.4	948.6	918.7	899.7	881.0	877.6
32.5°	932.9	885.8	842.5	816.2	787.0	775.2	762.3
35°	783.5	737.6	694.6	657.7	636.4	619.9	605.0
37.5°	649.1	596.3	561.6	531.7	516.3	506.9	509.2
40°	565.8	519.5	494.1	471.3	457.1	450.4	451.9
42.5°	498.3	463.6	442.7	427.1	417.1	413.3	412.4
45°	421.6	402.2	385.0	376.1	371.2	367.1	364.5
47.5°	369.4	353.5	343.8	338.5	334.2	330.1	330.0
50°	338.0	327.5	320.8	315.2	311.8	308.8	311.5
52.5°	314.1	304.5	297.8	292.8	291.5	288.8	288.8
55°	278.6	271.1	266.3	261.8	259.6	258.1	256.2
57.5°	246.3	239.2	234.8	231.9	227.7	226.2	225.6
60°	223.3	217.7	213.2	209.5	207.6	204.7	204.7
62.5°	202.1	196.5	192.3	189.5	186.4	185.2	185.5
65°	171.4	166.9	162.8	159.8	159.1	156.9	157.6
67.5°	143.2	140.2	135.9	134.2	132.8	131.6	130.7
70°	124.4	121.4	119.1	116.9	115.8	115.8	115.8
72.5°	108.5	104.9	103.6	100.8	101.4	100.2	99.0
75°	84.0	81.8	80.7	79.5	77.7	77.7	77.7
77.5°	61.8	61.2	59.8	58.6	58.2	57.8	58.0
80°	47.8	47.4	46.7	46.7	45.9	45.6	44.8
82.5°	36.7	35.8	35.3	35.0	34.9	34.8	34.7
85°	20.9	20.2	20.2	20.5	19.8	19.8	20.2
87.5°	10.5	10.6	10.4	10.4	10.8	10.5	10.6
90°	12.2	12.8	13.2	13.4	13.6	13.9	14.1
92.5°	13.0	13.3	13.5	13.7	13.8	14.0	14.1
95°	22.1	22.7	22.9	22.8	22.7	22.6	22.4
97.5°	28.6	29.1	29.4	29.5	29.7	29.8	30.0
100°	32.5	33.5	34.0	34.3	34.5	34.7	35.0
102.5°	34.2	35.4	36.2	36.5	36.8	37.1	37.5
105°	35.7	36.9	37.8	38.3	38.7	39.2	39.7
107.5°	40.7	39.4	39.0	39.4	39.9	40.3	40.8
110°	56.5	44.9	39.4	39.8	40.3	40.8	41.2



TEST NUMBER: P331294

CATALOG NUMBER: SA2XXDIP-C485D530U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	103.4	61.1	40.2	40.5	40.9	41.3	41.6
115°	160.9	107.2	76.2	67.8	59.5	51.1	42.8
117.5°	317.7	304.7	284.5	257.0	229.6	202.2	174.7
120°	386.7	388.1	381.0	365.3	349.7	334.0	318.3
122.5°	409.7	410.5	409.4	406.4	403.3	400.3	397.2
125°	443.4	444.2	444.8	445.2	445.5	445.9	446.2
127.5°	475.0	476.2	476.8	476.9	477.0	477.0	477.1
130°	494.9	496.2	496.8	496.6	496.5	496.4	496.3
132.5°	514.0	515.1	515.5	515.4	515.3	515.2	515.1
135°	541.5	542.7	543.2	542.9	542.7	542.5	542.2
137.5°	567.0	568.2	568.5	568.1	567.7	567.4	567.0
140°	583.4	584.5	584.7	584.1	583.6	583.0	582.4
142.5°	598.6	599.6	599.8	599.2	598.6	598.0	597.4
145°	619.8	620.6	620.7	620.2	619.6	619.0	618.4
147.5°	638.2	638.8	638.8	638.4	637.9	637.4	636.9
150°	649.7	650.4	650.5	649.9	649.3	648.7	648.2
152.5°	660.2	660.9	660.8	660.1	659.3	658.5	657.8
155°	674.3	675.0	674.8	673.9	673.0	672.1	671.1
157.5°	686.2	687.0	687.0	686.0	685.1	684.2	683.3
160°	693.0	693.7	693.7	692.9	692.1	691.2	690.4
162.5°	699.6	700.4	700.3	699.3	698.3	697.3	696.3
165°	707.5	708.3	708.3	707.5	706.7	705.9	705.0
167.5°	714.1	714.9	714.8	713.7	712.7	711.6	710.6
170°	717.4	718.2	718.1	717.0	716.0	715.0	713.9
172.5°	719.9	720.7	720.6	719.6	718.5	717.5	716.4
175°	722.6	723.4	723.3	722.1	720.9	719.8	718.6
177.5°	722.8	723.4	723.3	722.5	721.6	720.8	720.0
180°	721.2	721.2	721.2	721.2	721.2	721.2	721.2

(END OF REPORT)