

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331632-840

Luminaire Tested: **SA2XXRDIP-C290D725U840-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331632-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C290D725U840-4F0-1E-UDD-F4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 725 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3902.8 lumens
Efficiency: N/A
Efficacy: 125.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331632-840
CATALOG NUMBER: SA2XXRDIP-C290D725U840-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331632-840

CATALOG NUMBER: SA2XXRDIP-C290D725U840-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	102	102	102	102	91	91	91	91	70	70	70	52	52	52	35	35	35	27				
1	93	89	85	82	83	79	76	74	62	60	58	46	45	43	31	30	30	23				
2	85	78	72	67	75	70	65	61	55	51	48	41	38	37	28	26	25	20				
3	77	68	62	56	69	61	56	51	48	44	41	36	33	31	25	23	22	17				
4	71	61	53	48	63	55	48	43	43	39	35	32	29	27	22	21	19	15				
5	65	54	46	41	58	49	42	37	38	34	30	29	26	23	20	18	17	13				
6	60	48	41	35	53	44	37	32	35	30	26	26	23	21	18	16	15	12				
7	55	44	36	31	49	39	33	28	31	27	23	24	21	18	17	15	13	10				
8	51	40	32	27	46	36	29	25	29	24	21	22	19	16	15	13	12	9				
9	48	36	29	24	43	33	26	22	26	22	18	20	17	15	14	12	11	8				
10	44	33	26	21	40	30	24	20	24	20	16	18	15	13	13	11	10	8				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8186	8186	8186
5°	8217	8083	8126
10°	8153	7950	7883
15°	8058	7714	7492
20°	7930	7378	7009
25°	7798	6996	6538
30°	7612	6604	5936
35°	7433	6177	5409
40°	7253	5735	4795
45°	7040	5236	4242
50°	6822	4735	3697
55°	6598	4197	3178
60°	6339	3630	2638
65°	6044	3049	2399
70°	5698	2511	2209
75°	5265	2289	2059
80°	4649	2046	1878
85°	3649	1612	1612



TEST NUMBER: P331632-840

CATALOG NUMBER: SA2XXRDIP-C290D725U840-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.4	1.2
10°-20°	130.3	3.3
20°-30°	183.0	4.7
30°-40°	199.5	5.1
40°-50°	183.4	4.7
50°-60°	144.1	3.7
60°-70°	93.9	2.4
70°-80°	48.4	1.2
80°-90°	16.3	0.4
90°-100°	164.1	4.2
100°-110°	557.0	14.3
110°-120°	591.7	15.2
120°-130°	487.1	12.5
130°-140°	391.2	10.0
140°-150°	295.6	7.6
150°-160°	207.7	5.3
160°-170°	122.3	3.1
170°-180°	39.8	1.0
0°-30°	360.7	9.2
0°-40°	560.2	14.4
0°-60°	887.7	22.7
0°-90°	1046.3	26.8
90°-120°	1312.8	33.6
90°-150°	2486.7	63.7
90°-180°	2856.0	73.2
0°-180°	3902.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	507	507	507	507	507	
5°	507	504	499	502	501	48
15°	482	476	462	453	448	136
25°	438	422	393	375	367	201
35°	377	353	313	285	274	236
45°	308	277	229	198	186	238
55°	234	198	149	123	113	209
65°	158	121	80	65	63	157
75°	84	53	37	34	33	89
85°	20	11	9	9	9	23
90°	1	11	27	26	26	2
95°	28	68	309	117	90	29
105°	96	145	585	1046	890	102
115°	170	214	490	1010	1171	168
125°	237	280	470	818	950	210
135°	278	332	465	688	787	215
145°	317	365	463	574	628	199
155°	361	390	449	508	528	166
165°	393	405	430	456	463	111
175°	410	410	414	419	418	39
180°	410	410	410	410	410	



TEST NUMBER: P331632-840

CATALOG NUMBER: SA2XXRDIP-C290D725U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	507.0	507.0	507.0	507.0	507.0	507.0	507.0	507.0	507.0	507.0	507.0
2.5°	508.8	508.4	508.0	507.6	507.2	506.4	505.5	504.7	503.8	502.9	503.7
5°	507.0	506.4	505.9	505.4	504.9	503.9	502.6	501.3	500.0	498.7	499.6
7.5°	501.7	501.1	500.4	499.8	499.2	498.1	496.6	494.9	493.4	491.9	492.1
10°	497.3	496.6	495.8	495.1	494.4	493.0	491.0	489.0	487.0	484.9	484.6
12.5°	491.8	490.9	490.0	489.2	488.3	486.6	483.9	481.3	478.7	476.1	475.5
15°	482.1	481.0	479.9	478.8	477.7	475.3	471.9	468.5	464.9	461.5	459.6
17.5°	470.3	468.6	466.9	465.1	463.4	460.4	456.0	451.5	447.1	442.6	440.3
20°	461.5	459.5	457.5	455.3	453.3	449.8	444.6	439.6	434.5	429.4	426.9
22.5°	452.0	449.7	447.4	445.1	442.8	438.8	433.0	427.3	421.6	415.9	412.5
25°	437.7	434.3	431.1	427.9	424.6	419.6	412.8	406.2	399.4	392.7	388.5
27.5°	420.4	416.9	413.3	409.8	406.2	400.6	393.0	385.5	377.9	370.3	365.5
30°	408.3	404.5	400.5	396.7	392.8	386.8	378.6	370.5	362.3	354.2	349.0
32.5°	396.6	392.0	387.5	382.9	378.4	372.0	363.8	355.4	347.1	338.7	332.9
35°	377.1	371.9	366.7	361.5	356.3	349.2	340.2	331.2	322.3	313.4	306.9
37.5°	357.7	351.9	346.2	340.5	334.8	327.2	317.6	308.0	298.5	288.9	281.9
40°	344.1	338.0	331.8	325.7	319.6	311.6	301.7	291.9	282.0	272.1	264.8
42.5°	330.1	323.7	317.2	310.8	304.4	296.0	285.8	275.6	265.4	255.2	247.7
45°	308.3	301.4	294.6	287.8	280.9	272.2	261.5	250.7	240.0	229.3	222.2
47.5°	287.0	279.7	272.6	265.3	258.0	248.9	237.8	226.8	215.7	204.7	197.5
50°	271.6	264.4	257.1	249.8	242.7	233.4	222.2	211.0	199.8	188.5	181.5
52.5°	256.5	248.9	241.5	233.9	226.3	217.0	206.0	195.1	184.1	173.1	166.3
55°	234.4	226.5	218.5	210.6	202.6	193.2	182.1	171.1	160.1	149.1	143.0
57.5°	211.8	203.6	195.4	187.3	179.2	169.8	159.2	148.7	138.0	127.4	121.8
60°	196.3	188.2	180.1	171.9	163.7	154.4	143.9	133.4	122.9	112.4	107.1
62.5°	181.3	173.2	165.0	156.8	148.7	139.6	129.6	119.6	109.6	99.6	94.6
65°	158.2	150.0	141.8	133.5	125.2	116.5	107.3	98.2	89.0	79.8	76.3
67.5°	136.0	127.8	119.7	111.5	103.3	95.0	86.7	78.6	70.3	62.0	60.4
70°	120.7	112.7	104.7	96.8	88.9	81.4	74.3	67.3	60.3	53.2	52.2
72.5°	105.9	98.4	90.7	83.1	75.4	68.9	63.2	57.6	51.9	46.3	45.3
75°	84.4	77.3	70.2	63.0	55.8	50.6	47.1	43.6	40.2	36.7	36.0
77.5°	63.2	57.0	50.7	44.4	38.2	34.2	32.5	30.9	29.2	27.6	27.2
80°	50.0	44.8	39.6	34.4	29.2	26.1	25.0	24.0	23.0	22.0	21.6
82.5°	37.9	33.8	29.8	25.8	21.7	19.3	18.6	17.9	17.2	16.6	16.3
85°	19.7	17.6	15.5	13.3	11.2	9.9	9.6	9.3	9.0	8.7	8.7
87.5°	6.1	5.9	5.9	5.5	5.2	5.4	6.1	7.2	8.2	8.3	8.1
90°	0.8	3.1	6.4	7.9	9.5	11.8	15.8	21.3	26.1	26.9	26.1
92.5°	9.6	13.9	19.6	23.0	28.4	35.9	53.7	78.8	101.2	102.6	86.6
95°	27.7	30.8	38.7	45.7	58.4	77.4	113.7	182.4	274.0	309.4	270.7
97.5°	45.0	49.3	57.7	68.4	82.9	104.3	150.0	245.7	397.9	528.3	554.2
100°	60.8	63.1	70.3	82.9	98.7	120.8	162.6	258.9	429.4	623.6	737.3
102.5°	75.3	77.1	84.1	96.7	113.2	135.3	174.0	259.5	417.5	626.8	805.5
105°	96.3	99.5	105.0	116.8	134.2	156.3	193.4	263.7	393.9	584.9	795.0
107.5°	119.1	121.6	126.9	137.8	155.0	177.3	213.3	274.6	382.2	540.1	725.6
110°	134.2	137.3	142.1	152.4	169.0	191.9	226.5	283.4	379.7	518.7	682.1



TEST NUMBER: P331632-840

CATALOG NUMBER: SA2XXRDIP-C290D725U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	148.0	151.3	156.6	166.2	182.2	205.7	239.2	292.9	380.3	504.7	651.8
115°	169.8	173.7	178.4	187.8	203.7	225.0	258.9	307.1	383.6	489.5	614.2
117.5°	192.2	195.3	200.1	208.4	223.6	245.7	277.1	322.2	389.3	482.0	590.5
120°	206.0	209.2	213.9	221.1	236.8	258.9	289.7	332.3	393.1	477.6	577.8
122.5°	219.3	221.9	226.5	234.3	250.0	272.9	301.7	341.2	397.6	475.0	567.1
125°	236.8	239.2	243.9	253.4	269.2	291.2	319.7	355.3	404.1	470.5	551.8
127.5°	250.7	253.9	260.5	270.9	286.1	308.8	336.5	368.3	411.0	467.8	537.6
130°	258.9	262.1	269.9	281.0	296.8	318.9	346.6	376.6	416.1	466.6	528.2
132.5°	266.5	270.3	278.8	290.5	306.9	329.0	355.4	384.8	421.1	466.0	520.6
135°	277.9	281.0	290.5	302.4	320.5	342.6	367.9	395.5	427.1	464.9	510.0
137.5°	288.6	292.4	301.8	314.5	332.5	353.0	378.0	403.7	432.4	464.8	502.5
140°	296.8	299.9	309.4	322.0	339.4	360.0	383.6	408.1	434.9	464.1	498.2
142.5°	305.0	307.6	316.4	329.0	345.8	365.1	388.1	411.9	436.9	464.1	493.7
145°	317.3	320.5	328.4	340.2	356.0	373.3	394.8	416.8	438.9	462.6	487.9
147.5°	330.6	333.0	340.5	351.4	364.6	380.0	400.1	419.5	439.6	459.8	481.9
150°	339.4	341.8	348.1	358.4	370.2	384.5	402.6	420.7	438.9	457.9	476.8
152.5°	348.3	349.4	355.7	364.7	375.9	388.9	405.2	421.4	437.7	454.7	472.4
155°	360.7	361.5	366.3	375.0	383.6	395.5	408.9	422.3	435.8	449.2	464.1
157.5°	371.2	371.9	375.8	383.3	390.3	400.2	411.6	422.3	432.1	443.5	456.5
160°	378.1	378.9	382.0	388.4	394.8	403.3	412.8	422.3	430.2	439.7	450.8
162.5°	385.1	384.6	387.8	392.8	398.5	405.3	413.5	421.7	428.4	436.6	445.7
165°	393.1	392.3	393.9	398.7	402.6	407.4	414.4	420.0	424.7	430.2	437.4
167.5°	399.8	398.8	400.2	403.2	406.1	409.1	414.2	418.9	421.1	424.7	429.1
170°	404.1	402.6	403.3	405.8	407.4	409.7	413.6	417.6	419.2	421.5	424.7
172.5°	406.7	405.8	405.3	407.7	408.6	410.3	413.0	415.7	416.7	417.8	420.3
175°	409.7	408.9	408.1	409.7	409.7	410.5	412.0	413.6	412.8	413.6	414.4
177.5°	411.1	409.9	409.2	410.5	410.5	410.5	411.1	412.4	411.1	410.5	411.1
180°	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5



TEST NUMBER: P331632-840

CATALOG NUMBER: SA2XXRDIP-C290D725U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	507.0	507.0	507.0	507.0	507.0	507.0	507.0	507.0
2.5°	504.5	505.3	506.1	506.4	506.3	506.1	505.9	505.8
5°	500.5	501.4	502.3	502.6	502.3	502.0	501.7	501.4
7.5°	492.4	492.7	492.9	492.8	492.3	491.7	491.2	490.7
10°	484.3	484.0	483.7	483.2	482.6	482.0	481.4	480.8
12.5°	475.0	474.4	473.9	473.1	472.1	471.1	470.1	469.1
15°	457.7	455.7	453.7	452.3	451.3	450.2	449.2	448.2
17.5°	438.0	435.7	433.4	431.4	429.6	427.9	426.1	424.3
20°	424.3	421.7	419.2	416.8	414.5	412.3	410.1	407.9
22.5°	409.3	406.0	402.7	400.2	398.5	396.9	395.2	393.5
25°	384.4	380.1	376.0	373.1	371.6	370.0	368.5	367.0
27.5°	360.5	355.7	350.8	347.2	344.8	342.3	339.9	337.5
30°	343.8	338.6	333.4	329.4	326.6	323.9	321.1	318.4
32.5°	326.9	320.9	315.0	310.7	308.2	305.6	303.0	300.4
35°	300.5	294.1	287.6	283.3	281.0	278.8	276.6	274.4
37.5°	274.8	267.7	260.6	255.8	253.3	250.6	248.1	245.5
40°	257.6	250.3	243.1	238.1	235.5	232.9	230.1	227.5
42.5°	240.1	232.7	225.2	220.3	217.6	215.1	212.5	210.0
45°	214.9	207.6	200.5	195.6	193.2	190.7	188.2	185.8
47.5°	190.3	183.1	175.9	171.2	169.0	166.7	164.5	162.3
50°	174.5	167.4	160.4	155.8	153.7	151.6	149.4	147.2
52.5°	159.6	152.8	146.0	141.6	139.7	137.6	135.6	133.7
55°	136.8	130.8	124.6	120.6	118.7	116.7	114.8	112.9
57.5°	116.2	110.6	105.0	101.4	99.8	98.2	96.5	94.8
60°	102.0	96.8	91.6	88.2	86.5	84.9	83.3	81.7
62.5°	89.7	84.7	79.8	76.7	75.7	74.8	73.8	72.8
65°	72.9	69.4	65.9	64.0	63.7	63.4	63.1	62.8
67.5°	58.9	57.3	55.6	54.7	54.3	54.0	53.7	53.4
70°	51.2	50.2	49.2	48.5	48.0	47.6	47.2	46.8
72.5°	44.5	43.6	42.8	42.3	42.0	41.8	41.5	41.3
75°	35.2	34.5	33.8	33.4	33.3	33.2	33.1	33.0
77.5°	26.7	26.3	25.9	25.7	25.4	25.2	25.1	24.9
80°	21.2	20.8	20.4	20.2	20.2	20.2	20.2	20.2
82.5°	16.1	15.8	15.6	15.5	15.5	15.5	15.5	15.5
85°	8.7	8.7	8.7	8.7	8.7	8.7	8.7	8.7
87.5°	7.8	7.5	7.7	7.8	7.8	7.8	7.8	7.8
90°	25.2	23.7	25.2	26.1	26.1	26.1	26.1	26.1
92.5°	68.9	59.1	52.4	47.6	46.9	44.3	45.0	43.7
95°	206.8	158.6	125.5	108.2	97.9	91.6	89.2	90.0
97.5°	482.6	394.9	309.4	252.5	214.7	195.3	183.8	177.1
100°	720.7	622.9	514.7	419.2	353.7	319.7	296.8	282.6
102.5°	876.8	854.6	775.5	674.3	603.1	545.1	516.5	497.4
105°	959.2	1048.3	1058.6	1032.6	983.6	934.6	900.7	889.7
107.5°	899.8	1034.1	1116.2	1154.5	1160.6	1157.9	1151.1	1136.4
110°	848.6	990.0	1091.0	1155.7	1189.6	1204.7	1211.7	1210.9



TEST NUMBER: P331632-840

CATALOG NUMBER: SA2XXRDIP-C290D725U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	801.9	937.5	1045.5	1119.7	1166.9	1192.0	1205.5	1209.7
115°	744.4	866.0	969.4	1050.7	1106.7	1143.1	1163.6	1170.7
117.5°	701.1	807.9	901.7	978.0	1035.1	1073.5	1095.1	1101.1
120°	679.6	777.6	861.2	933.1	988.4	1025.4	1048.3	1056.2
122.5°	662.7	752.3	831.5	896.5	946.0	982.5	1002.9	1009.5
125°	637.8	719.1	788.6	847.8	893.6	923.6	943.3	949.7
127.5°	613.4	686.9	752.5	807.1	847.1	875.1	892.2	897.3
130°	597.5	665.5	727.8	779.9	818.6	845.5	861.2	867.6
132.5°	582.4	645.3	702.6	751.5	789.6	816.4	830.9	836.6
135°	561.3	613.4	665.5	709.6	743.7	769.7	783.9	787.1
137.5°	544.4	587.9	629.3	667.8	698.8	721.2	733.7	738.4
140°	533.6	571.6	607.8	642.6	667.8	688.3	700.2	705.0
142.5°	524.8	557.0	588.2	617.3	641.4	659.9	670.6	671.5
145°	512.3	538.4	562.9	585.7	604.7	618.1	626.0	628.3
147.5°	502.7	523.2	542.3	559.1	574.7	585.4	590.8	592.2
150°	495.7	513.1	529.7	543.9	555.7	565.2	570.0	570.8
152.5°	488.8	504.9	519.0	531.3	540.6	548.8	552.3	552.4
155°	479.2	491.8	503.6	512.3	521.0	526.5	529.7	528.2
157.5°	468.0	478.6	488.5	495.2	501.4	506.0	507.5	507.5
160°	461.0	469.7	478.4	483.9	489.5	493.4	494.1	494.1
162.5°	454.0	461.5	468.9	473.2	478.7	481.4	482.2	481.5
165°	443.6	449.2	454.7	457.9	461.0	464.1	464.1	463.4
167.5°	433.7	438.0	441.7	444.6	446.1	447.8	447.6	446.7
170°	428.7	431.0	434.1	435.8	436.6	438.9	438.1	436.6
172.5°	422.9	424.7	427.3	428.2	429.0	430.1	429.3	428.4
175°	416.8	417.6	418.4	419.2	419.2	420.0	419.2	417.6
177.5°	412.4	412.4	413.0	413.0	413.0	413.0	412.4	411.1
180°	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5

(END OF REPORT)