

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331304

Luminaire Tested: **SA2XXDIP-C485D725U835-4F0-1E-UDD-A1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331304
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C485D725U835-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 725 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4737.5 lumens
Efficiency: N/A
Efficacy: 123.4 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 38.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331304
CATALOG NUMBER: SA2XXDIP-C485D725U835-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331304

CATALOG NUMBER: SA2XXDIP-C485D725U835-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	45				
1	97	93	89	86	89	85	82	79	71	69	67	58	57	55	46	45	45	39				
2	89	82	76	71	81	75	70	66	63	59	56	52	49	47	41	40	38	33				
3	81	72	65	60	74	67	60	56	56	51	48	46	43	40	37	35	33	29				
4	75	64	57	51	68	59	53	47	50	45	41	41	38	35	33	31	29	25				
5	69	57	50	44	63	53	46	41	45	40	36	37	34	30	30	28	25	22				
6	63	52	44	38	58	48	41	36	41	35	31	34	30	27	28	25	23	20				
7	59	47	39	34	54	43	36	32	37	32	28	31	27	24	25	22	20	18				
8	54	42	35	30	50	39	33	28	34	29	25	28	24	21	23	20	18	16				
9	51	39	32	27	47	36	30	25	31	26	22	26	22	19	22	19	17	14				
10	47	36	29	24	44	33	27	23	29	24	20	24	20	18	20	17	15	13				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15689	15689	15689	15689
5°	17590	15793	13994	15793
10°	20156	15662	12111	15662
15°	22298	15375	10700	15375
20°	21959	15067	9754	15067
25°	19800	14656	9155	14656
30°	16362	14001	8718	14001
35°	11925	13316	8406	13316
40°	9525	12507	8233	12507
45°	8323	11572	7999	11572
50°	7824	10665	7842	10665
55°	7212	9745	7631	9745
60°	6610	8767	7308	8767
65°	6021	7889	6991	7889
70°	5467	7034	6524	7034
75°	4847	6082	5777	6082
80°	4166	5040	4649	5040
85°	3742	3742	2760	3742



TEST NUMBER: P331304

CATALOG NUMBER: SA2XXDIP-C485D725U835-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	92.5	2.0
10°-20°	269.0	5.7
20°-30°	390.5	8.2
30°-40°	412.0	8.7
40°-50°	364.8	7.7
50°-60°	291.1	6.1
60°-70°	197.9	4.2
70°-80°	101.5	2.1
80°-90°	28.2	0.6
90°-100°	58.7	1.2
100°-110°	182.3	3.8
110°-120°	311.6	6.6
120°-130°	409.8	8.6
130°-140°	459.9	9.7
140°-150°	450.9	9.5
150°-160°	378.2	8.0
160°-170°	250.9	5.3
170°-180°	87.7	1.9
0°-30°	752.0	15.9
0°-40°	1164.1	24.6
0°-60°	1820.1	38.4
0°-90°	2147.6	45.3
90°-120°	552.6	11.7
90°-150°	1873.2	39.5
90°-180°	2590.0	54.7
0°-180°	4737.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	972	972	972	972	972	
5°	1085	974	863	974	1085	108
15°	1334	920	640	920	1334	368
25°	1111	823	514	823	1111	502
35°	605	676	426	676	605	393
45°	364	507	350	507	364	287
55°	256	346	271	346	256	230
65°	158	206	183	206	158	157
75°	78	98	93	98	78	83
85°	20	20	15	20	20	23
90°	27	1	27	1	27	13
95°	48	41	48	41	48	54
105°	174	168	174	168	174	182
115°	313	313	313	313	313	309
125°	456	455	456	455	456	407
135°	596	589	596	589	596	458
145°	722	714	722	714	722	451
155°	823	817	823	817	823	379
165°	890	889	890	889	890	251
175°	922	925	922	925	922	88
180°	926	926	926	926	926	



TEST NUMBER: P331304

CATALOG NUMBER: SA2XXDIP-C485D725U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7
2.5°	1016.6	1016.9	1017.4	1012.7	1012.1	1012.1	1007.9	1004.3	1000.1	994.4	995.0
5°	1085.3	1089.4	1090.9	1086.4	1079.7	1078.9	1072.6	1062.1	1052.4	1044.6	1039.0
7.5°	1167.3	1168.9	1165.3	1159.4	1154.4	1145.4	1133.6	1122.0	1105.8	1090.9	1079.9
10°	1229.4	1231.7	1225.3	1216.7	1209.6	1199.2	1182.0	1164.4	1143.2	1122.6	1106.2
12.5°	1276.6	1282.2	1274.0	1272.9	1260.7	1246.4	1225.9	1217.0	1187.1	1158.5	1140.8
15°	1334.0	1333.6	1334.4	1327.3	1318.3	1316.1	1294.4	1270.9	1228.7	1211.9	1182.7
17.5°	1317.4	1323.1	1325.7	1325.6	1325.4	1324.0	1317.0	1302.2	1281.0	1253.8	1220.2
20°	1278.0	1285.4	1286.6	1295.2	1300.0	1306.4	1309.0	1304.9	1291.8	1269.0	1239.9
22.5°	1217.0	1219.1	1222.6	1236.0	1246.5	1262.4	1270.7	1284.5	1279.5	1268.4	1244.1
25°	1111.4	1107.7	1120.7	1127.5	1151.7	1177.1	1195.4	1215.6	1233.5	1244.4	1237.3
27.5°	984.6	979.0	998.6	1016.4	1036.1	1063.6	1092.1	1125.8	1153.8	1188.9	1200.9
30°	877.6	881.0	899.7	918.7	948.6	987.4	1019.5	1056.5	1096.5	1135.7	1162.9
32.5°	762.3	775.2	787.0	816.2	842.5	885.8	932.9	979.1	1029.0	1073.5	1115.7
35°	605.0	619.9	636.4	657.7	694.6	737.6	783.5	845.9	913.9	974.7	1024.8
37.5°	509.2	506.9	516.3	531.7	561.6	596.3	649.1	710.8	790.8	862.3	932.9
40°	451.9	450.4	457.1	471.3	494.1	519.5	565.8	619.9	694.3	781.6	865.7
42.5°	412.4	413.3	417.1	427.1	442.7	463.6	498.3	544.4	612.4	694.7	785.0
45°	364.5	367.1	371.2	376.1	385.0	402.2	421.6	454.5	508.3	577.0	665.9
47.5°	330.0	330.1	334.2	338.5	343.8	353.5	369.4	390.0	427.9	483.9	560.3
50°	311.5	308.8	311.8	315.2	320.8	327.5	338.0	357.4	382.8	428.0	491.8
52.5°	288.8	288.8	291.5	292.8	297.8	304.5	314.1	327.5	350.5	385.9	438.4
55°	256.2	258.1	259.6	261.8	266.3	271.1	278.6	287.6	305.5	332.0	370.8
57.5°	225.6	226.2	227.7	231.9	234.8	239.2	246.3	254.5	266.1	285.8	315.0
60°	204.7	204.7	207.6	209.5	213.2	217.7	223.3	231.2	241.6	257.7	281.2
62.5°	185.5	185.2	186.4	189.5	192.3	196.5	202.1	208.8	218.6	232.9	252.2
65°	157.6	156.9	159.1	159.8	162.8	166.9	171.4	178.5	186.4	196.8	214.0
67.5°	130.7	131.6	132.8	134.2	135.9	140.2	143.2	148.2	154.8	163.5	175.2
70°	115.8	115.8	115.8	116.9	119.1	121.4	124.4	128.5	134.8	142.3	152.7
72.5°	99.0	100.2	101.4	100.8	103.6	104.9	108.5	110.8	116.9	121.7	130.9
75°	77.7	77.7	77.7	79.5	80.7	81.8	84.0	86.3	89.3	95.2	100.1
77.5°	58.0	57.8	58.2	58.6	59.8	61.2	61.8	63.9	66.6	69.4	73.5
80°	44.8	45.6	45.9	46.7	46.7	47.4	47.8	50.4	52.3	54.2	56.8
82.5°	34.7	34.8	34.9	35.0	35.3	35.8	36.7	37.6	38.2	39.8	41.8
85°	20.2	19.8	19.8	20.5	20.2	20.2	20.9	21.7	21.7	22.0	23.2
87.5°	13.1	13.0	13.3	13.0	12.9	13.3	13.3	13.1	13.5	13.8	13.4
90°	26.6	26.4	26.2	26.1	25.9	26.0	26.3	26.7	27.0	27.4	23.5
92.5°	25.3	25.3	25.3	25.2	25.2	25.1	25.1	25.0	24.9	24.9	24.0
95°	48.5	48.8	49.2	49.5	49.9	50.0	50.0	50.0	50.0	50.0	49.7
97.5°	83.9	84.0	84.0	84.1	84.1	84.1	84.1	84.1	84.1	84.1	83.4
100°	107.1	107.3	107.4	107.6	107.8	107.9	107.9	107.9	107.9	107.9	107.3
102.5°	133.3	133.5	133.7	133.9	134.0	134.1	133.9	133.8	133.6	133.5	132.8
105°	173.5	173.5	173.5	173.5	173.5	173.4	173.0	172.7	172.3	172.0	171.6
107.5°	211.4	212.2	213.0	213.8	214.6	214.9	214.7	214.6	214.5	214.3	214.3
110°	240.7	241.3	241.8	242.3	242.8	243.1	243.1	243.1	243.1	243.1	243.1



TEST NUMBER: P331304

CATALOG NUMBER: SA2XXDIP-C485D725U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	268.9	269.3	269.6	270.0	270.4	270.8	271.2	271.6	272.1	272.5	272.6
115°	312.7	313.2	313.7	314.2	314.7	315.1	315.3	315.4	315.6	315.8	316.1
117.5°	354.4	354.9	355.4	356.0	356.5	356.9	357.4	357.8	358.2	358.6	359.6
120°	383.8	384.3	384.8	385.3	385.9	386.1	386.1	386.1	386.1	386.1	387.5
122.5°	412.6	412.9	413.3	413.7	414.1	414.5	414.9	415.3	415.7	416.1	417.1
125°	456.5	456.7	456.8	457.0	457.2	457.5	458.0	458.6	459.1	459.6	460.1
127.5°	496.5	497.1	497.6	498.2	498.7	499.3	499.9	500.6	501.2	501.8	502.4
130°	525.3	526.0	526.7	527.3	528.0	528.6	528.9	529.3	529.6	530.0	530.3
132.5°	552.8	553.3	553.9	554.4	555.0	555.7	556.4	557.2	558.0	558.7	558.6
135°	595.6	596.1	596.7	597.2	597.7	598.0	598.2	598.4	598.6	598.7	598.4
137.5°	634.4	635.1	635.8	636.5	637.2	637.6	637.7	637.9	638.0	638.1	637.7
140°	661.3	662.0	662.7	663.4	664.0	664.4	664.4	664.4	664.4	664.4	663.5
142.5°	685.7	686.4	687.0	687.7	688.4	688.7	688.6	688.4	688.3	688.2	687.6
145°	722.2	722.9	723.6	724.3	725.0	725.3	725.1	724.9	724.8	724.6	723.5
147.5°	754.9	755.6	756.2	756.9	757.6	757.7	757.3	756.9	756.5	756.2	755.5
150°	776.2	776.7	777.2	777.7	778.3	778.3	777.7	777.2	776.7	776.2	775.5
152.5°	796.2	796.8	797.5	798.2	798.8	798.8	798.2	797.5	796.8	796.2	795.3
155°	823.1	823.6	824.1	824.6	825.2	825.0	824.1	823.2	822.4	821.5	821.0
157.5°	846.2	847.0	847.9	848.7	849.5	849.4	848.2	847.0	845.8	844.6	844.3
160°	860.6	861.3	862.0	862.7	863.4	863.2	862.2	861.1	860.1	859.0	858.9
162.5°	873.1	873.9	874.8	875.6	876.4	876.3	875.1	873.9	872.7	871.5	871.4
165°	889.5	890.4	891.2	892.1	893.0	892.8	891.6	890.4	889.2	887.9	887.9
167.5°	903.0	903.9	904.8	905.7	906.6	906.4	905.2	904.0	902.8	901.5	901.6
170°	909.8	910.9	911.9	913.0	914.0	913.9	912.7	911.5	910.3	909.0	909.2
172.5°	915.5	916.5	917.5	918.6	919.6	919.5	918.3	917.1	915.9	914.7	914.9
175°	921.6	922.6	923.6	924.7	925.7	925.6	924.4	923.2	922.0	920.8	921.1
177.5°	924.4	925.2	926.0	926.9	927.7	927.7	926.9	926.0	925.2	924.4	924.6
180°	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2



TEST NUMBER: P331304

CATALOG NUMBER: SA2XXDIP-C485D725U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7
2.5°	997.1	994.7	993.2	987.9	983.1	978.3	976.8	977.4	970.8	964.6	961.9
5°	1036.0	1028.5	1021.4	1011.3	999.4	986.3	979.6	974.4	961.3	947.1	938.9
7.5°	1070.8	1060.1	1046.4	1027.5	1010.1	989.5	976.4	964.9	945.7	925.7	913.5
10°	1092.0	1077.4	1059.9	1036.7	1015.4	990.4	972.9	955.3	932.9	909.0	894.1
12.5°	1110.2	1090.6	1073.3	1043.6	1018.4	987.1	966.3	941.6	918.0	889.6	874.9
15°	1153.6	1117.4	1084.5	1050.9	1019.9	976.2	953.1	919.8	888.8	853.7	836.9
17.5°	1187.1	1146.4	1094.7	1052.0	1015.8	967.4	933.4	893.6	856.9	816.8	794.0
20°	1206.3	1159.6	1103.9	1053.2	1009.8	954.6	917.6	876.9	833.9	788.7	764.1
22.5°	1217.6	1168.6	1113.5	1048.7	997.9	944.1	897.6	853.0	809.4	760.7	734.8
25°	1221.2	1176.4	1118.1	1044.9	982.9	922.1	866.0	822.7	770.1	724.5	686.8
27.5°	1203.4	1171.3	1115.3	1037.9	965.7	894.5	832.1	783.0	727.4	678.0	640.0
30°	1181.6	1162.9	1108.4	1030.7	951.9	875.4	806.7	751.0	695.8	645.7	606.9
32.5°	1147.9	1143.8	1095.9	1020.6	937.3	851.2	780.1	723.8	662.6	613.4	576.4
35°	1081.5	1099.5	1069.2	997.9	909.7	816.8	739.8	675.6	612.1	565.0	530.3
37.5°	992.7	1037.2	1029.3	964.6	872.5	779.3	694.3	627.2	566.7	519.2	485.1
40°	931.4	988.2	996.4	939.2	846.3	750.3	660.3	593.4	534.4	491.1	456.7
42.5°	865.7	932.0	954.6	908.8	817.6	719.8	629.8	560.6	502.2	460.0	429.6
45°	755.5	843.3	884.0	857.8	769.7	669.6	577.0	506.8	453.8	414.2	390.6
47.5°	652.5	748.4	803.2	793.9	716.4	617.3	525.8	458.4	406.8	375.2	354.1
50°	579.6	678.2	744.3	747.3	678.2	580.0	488.1	424.6	377.2	347.7	330.5
52.5°	516.3	610.4	682.5	698.3	635.5	541.1	454.3	391.2	349.4	322.3	306.9
55°	433.6	513.1	593.1	622.2	571.8	482.1	401.8	346.2	307.0	288.3	274.9
57.5°	360.5	426.8	500.6	532.8	501.7	425.0	349.7	301.4	269.6	253.2	242.9
60°	321.9	374.2	439.9	478.4	451.5	383.2	317.4	271.5	245.4	230.8	221.1
62.5°	286.1	332.4	387.9	423.1	408.5	344.0	285.2	244.6	222.1	208.4	201.4
65°	236.0	272.6	315.6	348.1	338.4	289.4	241.3	206.5	188.6	177.8	172.2
67.5°	194.3	220.8	250.6	279.0	271.2	236.5	197.9	170.8	157.4	148.1	144.8
70°	168.1	188.2	214.7	237.5	231.2	202.8	172.2	149.0	137.4	129.6	126.2
72.5°	143.0	159.5	179.8	198.4	194.1	170.5	145.0	127.5	118.6	111.4	108.6
75°	107.9	120.6	133.0	145.3	144.2	125.9	110.9	97.5	90.4	84.8	83.7
77.5°	79.7	86.8	95.2	102.5	100.5	90.0	78.3	70.6	65.4	61.6	61.0
80°	60.9	65.0	71.0	76.2	73.6	69.1	59.8	54.2	50.4	46.7	45.2
82.5°	44.1	48.3	51.8	54.7	52.7	48.5	42.7	38.9	36.7	34.1	33.5
85°	23.2	25.4	26.9	27.6	26.9	24.3	21.7	20.2	18.3	17.2	16.8
87.5°	12.9	12.1	11.4	11.4	10.1	9.7	8.0	6.7	6.8	7.0	6.8
90°	19.7	15.9	12.1	9.1	7.0	5.0	2.9	0.8	2.9	5.0	7.0
92.5°	23.0	22.1	21.2	20.0	18.5	17.0	15.4	13.9	15.4	17.0	18.5
95°	49.3	49.0	48.6	47.6	45.9	44.1	42.4	40.6	42.4	44.1	45.9
97.5°	82.8	82.1	81.5	80.4	78.8	77.3	75.8	74.3	75.8	77.3	78.8
100°	106.8	106.3	105.8	104.8	103.4	102.0	100.7	99.3	100.7	102.0	103.4
102.5°	132.2	131.5	130.9	130.0	128.9	127.8	126.6	125.5	126.6	127.8	128.9
105°	171.3	170.9	170.6	170.1	169.6	169.1	168.6	168.1	168.6	169.1	169.6
107.5°	214.3	214.3	214.3	213.9	213.2	212.4	211.7	210.9	211.7	212.4	213.2
110°	243.1	243.1	243.1	242.6	241.5	240.5	239.4	238.4	239.4	240.5	241.5



TEST NUMBER: P331304

CATALOG NUMBER: SA2XXDIP-C485D725U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	272.8	272.9	273.0	272.6	271.5	270.5	269.5	268.4	269.5	270.5	271.5
115°	316.5	316.8	317.2	316.8	315.8	314.7	313.7	312.7	313.7	314.7	315.8
117.5°	360.6	361.5	362.5	362.3	360.9	359.5	358.1	356.7	358.1	359.5	360.9
120°	388.9	390.3	391.7	391.7	390.3	388.9	387.5	386.1	387.5	388.9	390.3
122.5°	418.1	419.1	420.0	419.7	418.0	416.4	414.7	413.0	414.7	416.4	418.0
125°	460.6	461.2	461.7	461.2	459.6	458.0	456.5	454.9	456.5	458.0	459.6
127.5°	503.1	503.7	504.3	503.6	501.7	499.7	497.7	495.7	497.7	499.7	501.7
130°	530.6	531.0	531.3	530.4	528.1	525.9	523.6	521.4	523.6	525.9	528.1
132.5°	558.6	558.5	558.4	557.5	555.6	553.8	552.0	550.1	552.0	553.8	555.6
135°	598.0	597.7	597.3	596.2	594.3	592.4	590.5	588.6	590.5	592.4	594.3
137.5°	637.2	636.8	636.3	635.3	633.8	632.2	630.6	629.1	630.6	632.2	633.8
140°	662.7	661.8	660.9	659.7	658.1	656.6	655.0	653.5	655.0	656.6	658.1
142.5°	687.0	686.4	685.8	684.7	683.2	681.6	680.0	678.5	680.0	681.6	683.2
145°	722.5	721.5	720.4	719.3	718.1	716.9	715.6	714.4	715.6	716.9	718.1
147.5°	754.8	754.1	753.4	752.3	750.8	749.4	747.9	746.5	747.9	749.4	750.8
150°	774.8	774.1	773.4	772.5	771.5	770.4	769.4	768.4	769.4	770.4	771.5
152.5°	794.5	793.7	792.8	791.9	790.9	789.8	788.8	787.7	788.8	789.8	790.9
155°	820.5	819.9	819.4	818.9	818.4	817.9	817.3	816.8	817.3	817.9	818.4
157.5°	844.0	843.7	843.4	843.1	842.7	842.4	842.0	841.7	842.0	842.4	842.7
160°	858.7	858.5	858.3	858.1	857.7	857.4	857.0	856.7	857.0	857.4	857.7
162.5°	871.2	871.0	870.8	870.7	870.6	870.6	870.5	870.4	870.5	870.6	870.6
165°	887.9	887.9	887.9	888.0	888.2	888.4	888.6	888.7	888.6	888.4	888.2
167.5°	901.6	901.7	901.7	902.0	902.5	903.0	903.5	904.0	903.5	903.0	902.5
170°	909.4	909.6	909.7	910.1	910.6	911.1	911.7	912.2	911.7	911.1	910.6
172.5°	915.0	915.2	915.4	915.7	916.2	916.8	917.3	917.8	917.3	916.8	916.2
175°	921.5	921.8	922.2	922.6	923.1	923.6	924.2	924.7	924.2	923.6	923.1
177.5°	924.9	925.2	925.5	925.8	926.2	926.7	927.1	927.5	927.1	926.7	926.2
180°	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2



TEST NUMBER: P331304

CATALOG NUMBER: SA2XXDIP-C485D725U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7
2.5°	958.9	957.1	950.8	947.5	942.2	937.1	933.8	935.3	936.5	935.9	935.0
5°	931.4	924.3	913.5	904.1	897.4	885.1	879.9	877.3	875.0	872.4	869.8
7.5°	898.7	887.5	872.0	858.7	846.1	830.8	822.1	816.8	811.4	805.5	800.3
10°	875.4	859.7	843.3	824.6	809.7	795.8	783.5	775.3	767.8	760.7	755.5
12.5°	850.9	832.8	812.5	787.0	770.5	750.7	748.9	734.4	722.7	718.3	712.2
15°	811.9	786.5	760.7	730.5	717.4	699.5	688.3	677.1	667.0	659.9	658.0
17.5°	767.6	734.7	709.1	687.4	666.0	647.6	637.3	628.3	620.0	610.5	609.3
20°	733.8	705.5	677.5	658.4	636.4	617.7	605.0	596.0	588.9	583.3	578.5
22.5°	701.9	670.8	645.2	624.3	602.6	587.5	577.5	568.9	563.0	556.8	552.2
25°	650.6	626.3	598.3	574.8	556.8	547.1	538.9	531.4	527.7	523.6	518.4
27.5°	605.7	578.7	552.5	534.3	518.5	509.9	504.1	499.0	495.5	493.1	490.1
30°	574.0	546.7	526.2	508.3	495.2	486.6	482.9	479.9	475.8	474.3	472.8
32.5°	543.5	519.0	501.4	485.9	473.4	467.8	464.4	461.7	458.5	457.0	454.0
35°	500.4	479.9	462.7	454.1	444.0	439.2	436.6	432.8	429.9	428.4	428.0
37.5°	459.9	442.0	430.7	419.7	415.4	412.4	408.9	406.3	405.4	405.2	404.8
40°	433.6	419.0	408.9	400.0	398.1	393.6	390.6	388.4	388.4	388.8	388.4
42.5°	409.7	396.6	387.7	380.0	377.8	375.1	372.1	372.0	372.6	373.8	372.6
45°	373.5	364.1	357.8	354.0	349.9	347.3	346.9	348.1	348.4	348.8	349.9
47.5°	340.1	333.9	328.2	324.1	322.3	321.8	321.4	323.3	325.1	325.8	327.5
50°	320.4	313.3	308.5	305.9	304.4	303.6	304.4	306.6	308.1	310.0	311.1
52.5°	298.3	293.3	290.0	287.9	287.3	287.8	287.9	290.5	292.9	293.5	294.1
55°	267.8	264.0	263.3	259.9	261.4	261.0	262.9	264.4	266.6	268.9	269.3
57.5°	237.3	234.3	232.3	232.6	233.0	234.7	236.2	238.9	241.3	243.6	243.9
60°	217.0	215.5	214.4	214.4	215.1	217.4	219.2	221.8	223.3	224.8	225.9
62.5°	198.5	197.0	195.8	196.4	198.4	199.7	201.9	203.3	204.8	206.3	206.8
65°	169.2	168.4	169.6	170.3	170.7	172.5	175.2	176.3	177.8	178.5	181.1
67.5°	142.2	142.4	142.2	143.3	145.4	145.9	148.3	151.0	151.3	152.7	154.4
70°	124.0	124.7	125.5	126.2	128.1	128.8	130.7	131.8	133.3	134.4	135.6
72.5°	107.3	107.4	108.2	108.0	109.6	111.2	112.8	113.9	115.4	116.8	117.9
75°	82.5	82.5	83.3	83.7	85.5	87.4	87.0	87.8	89.3	90.8	91.5
77.5°	60.3	59.5	60.3	60.6	61.2	62.8	63.1	64.2	65.9	65.4	66.2
80°	45.9	44.8	45.9	46.3	46.3	48.2	48.2	48.9	50.0	48.9	50.0
82.5°	32.8	32.3	33.1	33.2	33.8	33.8	34.4	34.6	35.7	35.2	35.7
85°	16.4	16.1	16.4	16.1	16.4	16.8	16.8	16.4	16.4	17.2	16.1
87.5°	6.9	7.2	7.7	8.4	8.9	9.4	9.0	8.9	8.8	8.2	8.2
90°	9.1	12.1	15.9	19.7	23.5	27.4	27.0	26.7	26.3	26.0	25.9
92.5°	20.0	21.2	22.1	23.0	24.0	24.9	24.9	25.0	25.1	25.1	25.2
95°	47.6	48.6	49.0	49.3	49.7	50.0	50.0	50.0	50.0	50.0	49.9
97.5°	80.4	81.5	82.1	82.8	83.4	84.1	84.1	84.1	84.1	84.1	84.1
100°	104.8	105.8	106.3	106.8	107.3	107.9	107.9	107.9	107.9	107.9	107.8
102.5°	130.0	130.9	131.5	132.2	132.8	133.5	133.6	133.8	133.9	134.1	134.0
105°	170.1	170.6	170.9	171.3	171.6	172.0	172.3	172.7	173.0	173.4	173.5
107.5°	213.9	214.3	214.3	214.3	214.3	214.3	214.5	214.6	214.7	214.9	214.6
110°	242.6	243.1	243.1	243.1	243.1	243.1	243.1	243.1	243.1	243.1	242.8



TEST NUMBER: P331304

CATALOG NUMBER: SA2XXDIP-C485D725U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	272.6	273.0	272.9	272.8	272.6	272.5	272.1	271.6	271.2	270.8	270.4
115°	316.8	317.2	316.8	316.5	316.1	315.8	315.6	315.4	315.3	315.1	314.7
117.5°	362.3	362.5	361.5	360.6	359.6	358.6	358.2	357.8	357.4	356.9	356.5
120°	391.7	391.7	390.3	388.9	387.5	386.1	386.1	386.1	386.1	386.1	385.9
122.5°	419.7	420.0	419.1	418.1	417.1	416.1	415.7	415.3	414.9	414.5	414.1
125°	461.2	461.7	461.2	460.6	460.1	459.6	459.1	458.6	458.0	457.5	457.2
127.5°	503.6	504.3	503.7	503.1	502.4	501.8	501.2	500.6	499.9	499.3	498.7
130°	530.4	531.3	531.0	530.6	530.3	530.0	529.6	529.3	528.9	528.6	528.0
132.5°	557.5	558.4	558.5	558.6	558.6	558.7	558.0	557.2	556.4	555.7	555.0
135°	596.2	597.3	597.7	598.0	598.4	598.7	598.6	598.4	598.2	598.0	597.7
137.5°	635.3	636.3	636.8	637.2	637.7	638.1	638.0	637.9	637.7	637.6	637.2
140°	659.7	660.9	661.8	662.7	663.5	664.4	664.4	664.4	664.4	664.4	664.0
142.5°	684.7	685.8	686.4	687.0	687.6	688.2	688.3	688.4	688.6	688.7	688.4
145°	719.3	720.4	721.5	722.5	723.5	724.6	724.8	724.9	725.1	725.3	725.0
147.5°	752.3	753.4	754.1	754.8	755.5	756.2	756.5	756.9	757.3	757.7	757.6
150°	772.5	773.4	774.1	774.8	775.5	776.2	776.7	777.2	777.7	778.3	778.3
152.5°	791.9	792.8	793.7	794.5	795.3	796.2	796.8	797.5	798.2	798.8	798.8
155°	818.9	819.4	819.9	820.5	821.0	821.5	822.4	823.2	824.1	825.0	825.2
157.5°	843.1	843.4	843.7	844.0	844.3	844.6	845.8	847.0	848.2	849.4	849.5
160°	858.1	858.3	858.5	858.7	858.9	859.0	860.1	861.1	862.2	863.2	863.4
162.5°	870.7	870.8	871.0	871.2	871.4	871.5	872.7	873.9	875.1	876.3	876.4
165°	888.0	887.9	887.9	887.9	887.9	887.9	889.2	890.4	891.6	892.8	893.0
167.5°	902.0	901.7	901.7	901.6	901.6	901.5	902.8	904.0	905.2	906.4	906.6
170°	910.1	909.7	909.6	909.4	909.2	909.0	910.3	911.5	912.7	913.9	914.0
172.5°	915.7	915.4	915.2	915.0	914.9	914.7	915.9	917.1	918.3	919.5	919.6
175°	922.6	922.2	921.8	921.5	921.1	920.8	922.0	923.2	924.4	925.6	925.7
177.5°	925.8	925.5	925.2	924.9	924.6	924.4	925.2	926.0	926.9	927.7	927.7
180°	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2



TEST NUMBER: P331304

CATALOG NUMBER: SA2XXDIP-C485D725U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7
2.5°	932.0	931.4	931.4	928.7	931.4	931.4	932.0	935.0	935.9	936.5	935.3
5°	864.6	863.4	861.6	863.4	861.6	863.4	864.6	869.8	872.4	875.0	877.3
7.5°	797.9	793.4	792.7	788.3	792.7	793.4	797.9	800.3	805.5	811.4	816.8
10°	749.2	746.2	745.8	738.7	745.8	746.2	749.2	755.5	760.7	767.8	775.3
12.5°	712.1	704.9	706.4	702.3	706.4	704.9	712.1	712.2	718.3	722.7	734.4
15°	647.9	647.9	646.5	640.1	646.5	647.9	647.9	658.0	659.9	667.0	677.1
17.5°	601.9	601.1	597.5	599.3	597.5	601.1	601.9	609.3	610.5	620.0	628.3
20°	574.4	572.1	567.7	567.7	567.7	572.1	574.4	578.5	583.3	588.9	596.0
22.5°	548.4	548.2	543.5	545.0	543.5	548.2	548.4	552.2	556.8	563.0	568.9
25°	518.0	515.0	512.8	513.9	512.8	515.0	518.0	518.4	523.6	527.7	531.4
27.5°	489.2	487.5	487.4	484.3	487.4	487.5	489.2	490.1	493.1	495.5	499.0
30°	472.4	468.7	469.4	467.6	469.4	468.7	472.4	472.8	474.3	475.8	479.9
32.5°	453.3	452.0	451.2	449.6	451.2	452.0	453.3	454.0	457.0	458.5	461.7
35°	427.2	427.6	425.7	426.5	425.7	427.6	427.2	428.0	428.4	429.9	432.8
37.5°	404.5	405.7	404.8	405.0	404.8	405.7	404.5	404.8	405.2	405.4	406.3
40°	389.5	389.5	389.5	390.6	389.5	389.5	389.5	388.4	388.8	388.4	388.4
42.5°	375.2	374.6	374.0	373.9	374.0	374.6	375.2	372.6	373.8	372.6	372.0
45°	350.7	351.8	352.2	350.3	352.2	351.8	350.7	349.9	348.8	348.4	348.1
47.5°	328.5	328.6	328.5	330.1	328.5	328.6	328.5	327.5	325.8	325.1	323.3
50°	313.0	312.2	313.0	312.2	313.0	312.2	313.0	311.1	310.0	308.1	306.6
52.5°	296.5	296.7	296.2	296.1	296.2	296.7	296.5	294.1	293.5	292.9	290.5
55°	270.8	271.5	271.1	271.1	271.1	271.5	270.8	269.3	268.9	266.6	264.4
57.5°	244.1	244.8	245.3	243.6	245.3	244.8	244.1	243.9	243.6	241.3	238.9
60°	225.6	227.4	227.1	226.3	227.1	227.4	225.6	225.9	224.8	223.3	221.8
62.5°	208.5	209.2	209.1	209.0	209.1	209.2	208.5	206.8	206.3	204.8	203.3
65°	182.2	183.0	181.9	183.0	181.9	183.0	182.2	181.1	178.5	177.8	176.3
67.5°	153.9	154.2	155.0	155.5	155.0	154.2	153.9	154.4	152.7	151.3	151.0
70°	136.3	135.9	137.1	138.2	137.1	135.9	136.3	135.6	134.4	133.3	131.8
72.5°	117.8	118.6	118.2	119.1	118.2	118.6	117.8	117.9	116.8	115.4	113.9
75°	90.8	91.9	91.5	92.6	91.5	91.9	90.8	91.5	90.8	89.3	87.8
77.5°	65.6	65.7	65.6	66.2	65.6	65.7	65.6	66.2	65.4	65.9	64.2
80°	50.0	49.3	48.5	50.0	48.5	49.3	50.0	50.0	48.9	50.0	48.9
82.5°	34.8	35.3	34.5	34.5	34.5	35.3	34.8	35.7	35.2	35.7	34.6
85°	16.1	15.7	14.9	14.9	14.9	15.7	16.1	16.1	17.2	16.4	16.4
87.5°	8.2	7.9	8.0	7.7	8.0	7.9	8.2	8.2	8.2	8.8	8.9
90°	26.1	26.2	26.4	26.6	26.4	26.2	26.1	25.9	26.0	26.3	26.7
92.5°	25.2	25.3	25.3	25.3	25.3	25.3	25.2	25.2	25.1	25.1	25.0
95°	49.5	49.2	48.8	48.5	48.8	49.2	49.5	49.9	50.0	50.0	50.0
97.5°	84.1	84.0	84.0	83.9	84.0	84.0	84.1	84.1	84.1	84.1	84.1
100°	107.6	107.4	107.3	107.1	107.3	107.4	107.6	107.8	107.9	107.9	107.9
102.5°	133.9	133.7	133.5	133.3	133.5	133.7	133.9	134.0	134.1	133.9	133.8
105°	173.5	173.5	173.5	173.5	173.5	173.5	173.5	173.5	173.4	173.0	172.7
107.5°	213.8	213.0	212.2	211.4	212.2	213.0	213.8	214.6	214.9	214.7	214.6
110°	242.3	241.8	241.3	240.7	241.3	241.8	242.3	242.8	243.1	243.1	243.1



TEST NUMBER: P331304

CATALOG NUMBER: SA2XXDIP-C485D725U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	270.0	269.6	269.3	268.9	269.3	269.6	270.0	270.4	270.8	271.2	271.6
115°	314.2	313.7	313.2	312.7	313.2	313.7	314.2	314.7	315.1	315.3	315.4
117.5°	356.0	355.4	354.9	354.4	354.9	355.4	356.0	356.5	356.9	357.4	357.8
120°	385.3	384.8	384.3	383.8	384.3	384.8	385.3	385.9	386.1	386.1	386.1
122.5°	413.7	413.3	412.9	412.6	412.9	413.3	413.7	414.1	414.5	414.9	415.3
125°	457.0	456.8	456.7	456.5	456.7	456.8	457.0	457.2	457.5	458.0	458.6
127.5°	498.2	497.6	497.1	496.5	497.1	497.6	498.2	498.7	499.3	499.9	500.6
130°	527.3	526.7	526.0	525.3	526.0	526.7	527.3	528.0	528.6	528.9	529.3
132.5°	554.4	553.9	553.3	552.8	553.3	553.9	554.4	555.0	555.7	556.4	557.2
135°	597.2	596.7	596.1	595.6	596.1	596.7	597.2	597.7	598.0	598.2	598.4
137.5°	636.5	635.8	635.1	634.4	635.1	635.8	636.5	637.2	637.6	637.7	637.9
140°	663.4	662.7	662.0	661.3	662.0	662.7	663.4	664.0	664.4	664.4	664.4
142.5°	687.7	687.0	686.4	685.7	686.4	687.0	687.7	688.4	688.7	688.6	688.4
145°	724.3	723.6	722.9	722.2	722.9	723.6	724.3	725.0	725.3	725.1	724.9
147.5°	756.9	756.2	755.6	754.9	755.6	756.2	756.9	757.6	757.7	757.3	756.9
150°	777.7	777.2	776.7	776.2	776.7	777.2	777.7	778.3	778.3	777.7	777.2
152.5°	798.2	797.5	796.8	796.2	796.8	797.5	798.2	798.8	798.8	798.2	797.5
155°	824.6	824.1	823.6	823.1	823.6	824.1	824.6	825.2	825.0	824.1	823.2
157.5°	848.7	847.9	847.0	846.2	847.0	847.9	848.7	849.5	849.4	848.2	847.0
160°	862.7	862.0	861.3	860.6	861.3	862.0	862.7	863.4	863.2	862.2	861.1
162.5°	875.6	874.8	873.9	873.1	873.9	874.8	875.6	876.4	876.3	875.1	873.9
165°	892.1	891.2	890.4	889.5	890.4	891.2	892.1	893.0	892.8	891.6	890.4
167.5°	905.7	904.8	903.9	903.0	903.9	904.8	905.7	906.6	906.4	905.2	904.0
170°	913.0	911.9	910.9	909.8	910.9	911.9	913.0	914.0	913.9	912.7	911.5
172.5°	918.6	917.5	916.5	915.5	916.5	917.5	918.6	919.6	919.5	918.3	917.1
175°	924.7	923.6	922.6	921.6	922.6	923.6	924.7	925.7	925.6	924.4	923.2
177.5°	926.9	926.0	925.2	924.4	925.2	926.0	926.9	927.7	927.7	926.9	926.0
180°	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2



TEST NUMBER: P331304

CATALOG NUMBER: SA2XXDIP-C485D725U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7
2.5°	933.8	937.1	942.2	947.5	950.8	957.1	958.9	961.9	964.6	970.8	977.4
5°	879.9	885.1	897.4	904.1	913.5	924.3	931.4	938.9	947.1	961.3	974.4
7.5°	822.1	830.8	846.1	858.7	872.0	887.5	898.7	913.5	925.7	945.7	964.9
10°	783.5	795.8	809.7	824.6	843.3	859.7	875.4	894.1	909.0	932.9	955.3
12.5°	748.9	750.7	770.5	787.0	812.5	832.8	850.9	874.9	889.6	918.0	941.6
15°	688.3	699.5	717.4	730.5	760.7	786.5	811.9	836.9	853.7	888.8	919.8
17.5°	637.3	647.6	666.0	687.4	709.1	734.7	767.6	794.0	816.8	856.9	893.6
20°	605.0	617.7	636.4	658.4	677.5	705.5	733.8	764.1	788.7	833.9	876.9
22.5°	577.5	587.5	602.6	624.3	645.2	670.8	701.9	734.8	760.7	809.4	853.0
25°	538.9	547.1	556.8	574.8	598.3	626.3	650.6	686.8	724.5	770.1	822.7
27.5°	504.1	509.9	518.5	534.3	552.5	578.7	605.7	640.0	678.0	727.4	783.0
30°	482.9	486.6	495.2	508.3	526.2	546.7	574.0	606.9	645.7	695.8	751.0
32.5°	464.4	467.8	473.4	485.9	501.4	519.0	543.5	576.4	613.4	662.6	723.8
35°	436.6	439.2	444.0	454.1	462.7	479.9	500.4	530.3	565.0	612.1	675.6
37.5°	408.9	412.4	415.4	419.7	430.7	442.0	459.9	485.1	519.2	566.7	627.2
40°	390.6	393.6	398.1	400.0	408.9	419.0	433.6	456.7	491.1	534.4	593.4
42.5°	372.1	375.1	377.8	380.0	387.7	396.6	409.7	429.6	460.0	502.2	560.6
45°	346.9	347.3	349.9	354.0	357.8	364.1	373.5	390.6	414.2	453.8	506.8
47.5°	321.4	321.8	322.3	324.1	328.2	333.9	340.1	354.1	375.2	406.8	458.4
50°	304.4	303.6	304.4	305.9	308.5	313.3	320.4	330.5	347.7	377.2	424.6
52.5°	287.9	287.8	287.3	287.9	290.0	293.3	298.3	306.9	322.3	349.4	391.2
55°	262.9	261.0	261.4	259.9	263.3	264.0	267.8	274.9	288.3	307.0	346.2
57.5°	236.2	234.7	233.0	232.6	232.3	234.3	237.3	242.9	253.2	269.6	301.4
60°	219.2	217.4	215.1	214.4	214.4	215.5	217.0	221.1	230.8	245.4	271.5
62.5°	201.9	199.7	198.4	196.4	195.8	197.0	198.5	201.4	208.4	222.1	244.6
65°	175.2	172.5	170.7	170.3	169.6	168.4	169.2	172.2	177.8	188.6	206.5
67.5°	148.3	145.9	145.4	143.3	142.2	142.4	142.2	144.8	148.1	157.4	170.8
70°	130.7	128.8	128.1	126.2	125.5	124.7	124.0	126.2	129.6	137.4	149.0
72.5°	112.8	111.2	109.6	108.0	108.2	107.4	107.3	108.6	111.4	118.6	127.5
75°	87.0	87.4	85.5	83.7	83.3	82.5	82.5	83.7	84.8	90.4	97.5
77.5°	63.1	62.8	61.2	60.6	60.3	59.5	60.3	61.0	61.6	65.4	70.6
80°	48.2	48.2	46.3	46.3	45.9	44.8	45.9	45.2	46.7	50.4	54.2
82.5°	34.4	33.8	33.8	33.2	33.1	32.3	32.8	33.5	34.1	36.7	38.9
85°	16.8	16.8	16.4	16.1	16.4	16.1	16.4	16.8	17.2	18.3	20.2
87.5°	9.0	9.4	8.9	8.4	7.7	7.2	6.9	6.8	7.0	6.8	6.7
90°	27.0	27.4	23.5	19.7	15.9	12.1	9.1	7.0	5.0	2.9	0.8
92.5°	24.9	24.9	24.0	23.0	22.1	21.2	20.0	18.5	17.0	15.4	13.9
95°	50.0	50.0	49.7	49.3	49.0	48.6	47.6	45.9	44.1	42.4	40.6
97.5°	84.1	84.1	83.4	82.8	82.1	81.5	80.4	78.8	77.3	75.8	74.3
100°	107.9	107.9	107.3	106.8	106.3	105.8	104.8	103.4	102.0	100.7	99.3
102.5°	133.6	133.5	132.8	132.2	131.5	130.9	130.0	128.9	127.8	126.6	125.5
105°	172.3	172.0	171.6	171.3	170.9	170.6	170.1	169.6	169.1	168.6	168.1
107.5°	214.5	214.3	214.3	214.3	214.3	214.3	213.9	213.2	212.4	211.7	210.9
110°	243.1	243.1	243.1	243.1	243.1	243.1	242.6	241.5	240.5	239.4	238.4



TEST NUMBER: P331304

CATALOG NUMBER: SA2XXDIP-C485D725U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	272.1	272.5	272.6	272.8	272.9	273.0	272.6	271.5	270.5	269.5	268.4
115°	315.6	315.8	316.1	316.5	316.8	317.2	316.8	315.8	314.7	313.7	312.7
117.5°	358.2	358.6	359.6	360.6	361.5	362.5	362.3	360.9	359.5	358.1	356.7
120°	386.1	386.1	387.5	388.9	390.3	391.7	391.7	390.3	388.9	387.5	386.1
122.5°	415.7	416.1	417.1	418.1	419.1	420.0	419.7	418.0	416.4	414.7	413.0
125°	459.1	459.6	460.1	460.6	461.2	461.7	461.2	459.6	458.0	456.5	454.9
127.5°	501.2	501.8	502.4	503.1	503.7	504.3	503.6	501.7	499.7	497.7	495.7
130°	529.6	530.0	530.3	530.6	531.0	531.3	530.4	528.1	525.9	523.6	521.4
132.5°	558.0	558.7	558.6	558.6	558.5	558.4	557.5	555.6	553.8	552.0	550.1
135°	598.6	598.7	598.4	598.0	597.7	597.3	596.2	594.3	592.4	590.5	588.6
137.5°	638.0	638.1	637.7	637.2	636.8	636.3	635.3	633.8	632.2	630.6	629.1
140°	664.4	664.4	663.5	662.7	661.8	660.9	659.7	658.1	656.6	655.0	653.5
142.5°	688.3	688.2	687.6	687.0	686.4	685.8	684.7	683.2	681.6	680.0	678.5
145°	724.8	724.6	723.5	722.5	721.5	720.4	719.3	718.1	716.9	715.6	714.4
147.5°	756.5	756.2	755.5	754.8	754.1	753.4	752.3	750.8	749.4	747.9	746.5
150°	776.7	776.2	775.5	774.8	774.1	773.4	772.5	771.5	770.4	769.4	768.4
152.5°	796.8	796.2	795.3	794.5	793.7	792.8	791.9	790.9	789.8	788.8	787.7
155°	822.4	821.5	821.0	820.5	819.9	819.4	818.9	818.4	817.9	817.3	816.8
157.5°	845.8	844.6	844.3	844.0	843.7	843.4	843.1	842.7	842.4	842.0	841.7
160°	860.1	859.0	858.9	858.7	858.5	858.3	858.1	857.7	857.4	857.0	856.7
162.5°	872.7	871.5	871.4	871.2	871.0	870.8	870.7	870.6	870.6	870.5	870.4
165°	889.2	887.9	887.9	887.9	887.9	887.9	888.0	888.2	888.4	888.6	888.7
167.5°	902.8	901.5	901.6	901.6	901.7	901.7	902.0	902.5	903.0	903.5	904.0
170°	910.3	909.0	909.2	909.4	909.6	909.7	910.1	910.6	911.1	911.7	912.2
172.5°	915.9	914.7	914.9	915.0	915.2	915.4	915.7	916.2	916.8	917.3	917.8
175°	922.0	920.8	921.1	921.5	921.8	922.2	922.6	923.1	923.6	924.2	924.7
177.5°	925.2	924.4	924.6	924.9	925.2	925.5	925.8	926.2	926.7	927.1	927.5
180°	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2



TEST NUMBER: P331304

CATALOG NUMBER: SA2XXDIP-C485D725U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7
2.5°	976.8	978.3	983.1	987.9	993.2	994.7	997.1	995.0	994.4	1000.1	1004.3
5°	979.6	986.3	999.4	1011.3	1021.4	1028.5	1036.0	1039.0	1044.6	1052.4	1062.1
7.5°	976.4	989.5	1010.1	1027.5	1046.4	1060.1	1070.8	1079.9	1090.9	1105.8	1122.0
10°	972.9	990.4	1015.4	1036.7	1059.9	1077.4	1092.0	1106.2	1122.6	1143.2	1164.4
12.5°	966.3	987.1	1018.4	1043.6	1073.3	1090.6	1110.2	1140.8	1158.5	1187.1	1217.0
15°	953.1	976.2	1019.9	1050.9	1084.5	1117.4	1153.6	1182.7	1211.9	1228.7	1270.9
17.5°	933.4	967.4	1015.8	1052.0	1094.7	1146.4	1187.1	1220.2	1253.8	1281.0	1302.2
20°	917.6	954.6	1009.8	1053.2	1103.9	1159.6	1206.3	1239.9	1269.0	1291.8	1304.9
22.5°	897.6	944.1	997.9	1048.7	1113.5	1168.6	1217.6	1244.1	1268.4	1279.5	1284.5
25°	866.0	922.1	982.9	1044.9	1118.1	1176.4	1221.2	1237.3	1244.4	1233.5	1215.6
27.5°	832.1	894.5	965.7	1037.9	1115.3	1171.3	1203.4	1200.9	1188.9	1153.8	1125.8
30°	806.7	875.4	951.9	1030.7	1108.4	1162.9	1181.6	1162.9	1135.7	1096.5	1056.5
32.5°	780.1	851.2	937.3	1020.6	1095.9	1143.8	1147.9	1115.7	1073.5	1029.0	979.1
35°	739.8	816.8	909.7	997.9	1069.2	1099.5	1081.5	1024.8	974.7	913.9	845.9
37.5°	694.3	779.3	872.5	964.6	1029.3	1037.2	992.7	932.9	862.3	790.8	710.8
40°	660.3	750.3	846.3	939.2	996.4	988.2	931.4	865.7	781.6	694.3	619.9
42.5°	629.8	719.8	817.6	908.8	954.6	932.0	865.7	785.0	694.7	612.4	544.4
45°	577.0	669.6	769.7	857.8	884.0	843.3	755.5	665.9	577.0	508.3	454.5
47.5°	525.8	617.3	716.4	793.9	803.2	748.4	652.5	560.3	483.9	427.9	390.0
50°	488.1	580.0	678.2	747.3	744.3	678.2	579.6	491.8	428.0	382.8	357.4
52.5°	454.3	541.1	635.5	698.3	682.5	610.4	516.3	438.4	385.9	350.5	327.5
55°	401.8	482.1	571.8	622.2	593.1	513.1	433.6	370.8	332.0	305.5	287.6
57.5°	349.7	425.0	501.7	532.8	500.6	426.8	360.5	315.0	285.8	266.1	254.5
60°	317.4	383.2	451.5	478.4	439.9	374.2	321.9	281.2	257.7	241.6	231.2
62.5°	285.2	344.0	408.5	423.1	387.9	332.4	286.1	252.2	232.9	218.6	208.8
65°	241.3	289.4	338.4	348.1	315.6	272.6	236.0	214.0	196.8	186.4	178.5
67.5°	197.9	236.5	271.2	279.0	250.6	220.8	194.3	175.2	163.5	154.8	148.2
70°	172.2	202.8	231.2	237.5	214.7	188.2	168.1	152.7	142.3	134.8	128.5
72.5°	145.0	170.5	194.1	198.4	179.8	159.5	143.0	130.9	121.7	116.9	110.8
75°	110.9	125.9	144.2	145.3	133.0	120.6	107.9	100.1	95.2	89.3	86.3
77.5°	78.3	90.0	100.5	102.5	95.2	86.8	79.7	73.5	69.4	66.6	63.9
80°	59.8	69.1	73.6	76.2	71.0	65.0	60.9	56.8	54.2	52.3	50.4
82.5°	42.7	48.5	52.7	54.7	51.8	48.3	44.1	41.8	39.8	38.2	37.6
85°	21.7	24.3	26.9	27.6	26.9	25.4	23.2	23.2	22.0	21.7	21.7
87.5°	8.0	9.7	10.1	11.4	11.4	12.1	12.9	13.4	13.8	13.5	13.1
90°	2.9	5.0	7.0	9.1	12.1	15.9	19.7	23.5	27.4	27.0	26.7
92.5°	15.4	17.0	18.5	20.0	21.2	22.1	23.0	24.0	24.9	24.9	25.0
95°	42.4	44.1	45.9	47.6	48.6	49.0	49.3	49.7	50.0	50.0	50.0
97.5°	75.8	77.3	78.8	80.4	81.5	82.1	82.8	83.4	84.1	84.1	84.1
100°	100.7	102.0	103.4	104.8	105.8	106.3	106.8	107.3	107.9	107.9	107.9
102.5°	126.6	127.8	128.9	130.0	130.9	131.5	132.2	132.8	133.5	133.6	133.8
105°	168.6	169.1	169.6	170.1	170.6	170.9	171.3	171.6	172.0	172.3	172.7
107.5°	211.7	212.4	213.2	213.9	214.3	214.3	214.3	214.3	214.3	214.5	214.6
110°	239.4	240.5	241.5	242.6	243.1	243.1	243.1	243.1	243.1	243.1	243.1



TEST NUMBER: P331304

CATALOG NUMBER: SA2XXDIP-C485D725U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	269.5	270.5	271.5	272.6	273.0	272.9	272.8	272.6	272.5	272.1	271.6
115°	313.7	314.7	315.8	316.8	317.2	316.8	316.5	316.1	315.8	315.6	315.4
117.5°	358.1	359.5	360.9	362.3	362.5	361.5	360.6	359.6	358.6	358.2	357.8
120°	387.5	388.9	390.3	391.7	391.7	390.3	388.9	387.5	386.1	386.1	386.1
122.5°	414.7	416.4	418.0	419.7	420.0	419.1	418.1	417.1	416.1	415.7	415.3
125°	456.5	458.0	459.6	461.2	461.7	461.2	460.6	460.1	459.6	459.1	458.6
127.5°	497.7	499.7	501.7	503.6	504.3	503.7	503.1	502.4	501.8	501.2	500.6
130°	523.6	525.9	528.1	530.4	531.3	531.0	530.6	530.3	530.0	529.6	529.3
132.5°	552.0	553.8	555.6	557.5	558.4	558.5	558.6	558.6	558.7	558.0	557.2
135°	590.5	592.4	594.3	596.2	597.3	597.7	598.0	598.4	598.7	598.6	598.4
137.5°	630.6	632.2	633.8	635.3	636.3	636.8	637.2	637.7	638.1	638.0	637.9
140°	655.0	656.6	658.1	659.7	660.9	661.8	662.7	663.5	664.4	664.4	664.4
142.5°	680.0	681.6	683.2	684.7	685.8	686.4	687.0	687.6	688.2	688.3	688.4
145°	715.6	716.9	718.1	719.3	720.4	721.5	722.5	723.5	724.6	724.8	724.9
147.5°	747.9	749.4	750.8	752.3	753.4	754.1	754.8	755.5	756.2	756.5	756.9
150°	769.4	770.4	771.5	772.5	773.4	774.1	774.8	775.5	776.2	776.7	777.2
152.5°	788.8	789.8	790.9	791.9	792.8	793.7	794.5	795.3	796.2	796.8	797.5
155°	817.3	817.9	818.4	818.9	819.4	819.9	820.5	821.0	821.5	822.4	823.2
157.5°	842.0	842.4	842.7	843.1	843.4	843.7	844.0	844.3	844.6	845.8	847.0
160°	857.0	857.4	857.7	858.1	858.3	858.5	858.7	858.9	859.0	860.1	861.1
162.5°	870.5	870.6	870.6	870.7	870.8	871.0	871.2	871.4	871.5	872.7	873.9
165°	888.6	888.4	888.2	888.0	887.9	887.9	887.9	887.9	887.9	889.2	890.4
167.5°	903.5	903.0	902.5	902.0	901.7	901.7	901.6	901.6	901.5	902.8	904.0
170°	911.7	911.1	910.6	910.1	909.7	909.6	909.4	909.2	909.0	910.3	911.5
172.5°	917.3	916.8	916.2	915.7	915.4	915.2	915.0	914.9	914.7	915.9	917.1
175°	924.2	923.6	923.1	922.6	922.2	921.8	921.5	921.1	920.8	922.0	923.2
177.5°	927.1	926.7	926.2	925.8	925.5	925.2	924.9	924.6	924.4	925.2	926.0
180°	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2



TEST NUMBER: P331304

CATALOG NUMBER: SA2XXDIP-C485D725U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	971.7	971.7	971.7	971.7	971.7	971.7	971.7
2.5°	1007.9	1012.1	1012.1	1012.7	1017.4	1016.9	1016.6
5°	1072.6	1078.9	1079.7	1086.4	1090.9	1089.4	1085.3
7.5°	1133.6	1145.4	1154.4	1159.4	1165.3	1168.9	1167.3
10°	1182.0	1199.2	1209.6	1216.7	1225.3	1231.7	1229.4
12.5°	1225.9	1246.4	1260.7	1272.9	1274.0	1282.2	1276.6
15°	1294.4	1316.1	1318.3	1327.3	1334.4	1333.6	1334.0
17.5°	1317.0	1324.0	1325.4	1325.6	1325.7	1323.1	1317.4
20°	1309.0	1306.4	1300.0	1295.2	1286.6	1285.4	1278.0
22.5°	1270.7	1262.4	1246.5	1236.0	1222.6	1219.1	1217.0
25°	1195.4	1177.1	1151.7	1127.5	1120.7	1107.7	1111.4
27.5°	1092.1	1063.6	1036.1	1016.4	998.6	979.0	984.6
30°	1019.5	987.4	948.6	918.7	899.7	881.0	877.6
32.5°	932.9	885.8	842.5	816.2	787.0	775.2	762.3
35°	783.5	737.6	694.6	657.7	636.4	619.9	605.0
37.5°	649.1	596.3	561.6	531.7	516.3	506.9	509.2
40°	565.8	519.5	494.1	471.3	457.1	450.4	451.9
42.5°	498.3	463.6	442.7	427.1	417.1	413.3	412.4
45°	421.6	402.2	385.0	376.1	371.2	367.1	364.5
47.5°	369.4	353.5	343.8	338.5	334.2	330.1	330.0
50°	338.0	327.5	320.8	315.2	311.8	308.8	311.5
52.5°	314.1	304.5	297.8	292.8	291.5	288.8	288.8
55°	278.6	271.1	266.3	261.8	259.6	258.1	256.2
57.5°	246.3	239.2	234.8	231.9	227.7	226.2	225.6
60°	223.3	217.7	213.2	209.5	207.6	204.7	204.7
62.5°	202.1	196.5	192.3	189.5	186.4	185.2	185.5
65°	171.4	166.9	162.8	159.8	159.1	156.9	157.6
67.5°	143.2	140.2	135.9	134.2	132.8	131.6	130.7
70°	124.4	121.4	119.1	116.9	115.8	115.8	115.8
72.5°	108.5	104.9	103.6	100.8	101.4	100.2	99.0
75°	84.0	81.8	80.7	79.5	77.7	77.7	77.7
77.5°	61.8	61.2	59.8	58.6	58.2	57.8	58.0
80°	47.8	47.4	46.7	46.7	45.9	45.6	44.8
82.5°	36.7	35.8	35.3	35.0	34.9	34.8	34.7
85°	20.9	20.2	20.2	20.5	19.8	19.8	20.2
87.5°	13.3	13.3	12.9	13.0	13.3	13.0	13.1
90°	26.3	26.0	25.9	26.1	26.2	26.4	26.6
92.5°	25.1	25.1	25.2	25.2	25.3	25.3	25.3
95°	50.0	50.0	49.9	49.5	49.2	48.8	48.5
97.5°	84.1	84.1	84.1	84.1	84.0	84.0	83.9
100°	107.9	107.9	107.8	107.6	107.4	107.3	107.1
102.5°	133.9	134.1	134.0	133.9	133.7	133.5	133.3
105°	173.0	173.4	173.5	173.5	173.5	173.5	173.5
107.5°	214.7	214.9	214.6	213.8	213.0	212.2	211.4
110°	243.1	243.1	242.8	242.3	241.8	241.3	240.7



TEST NUMBER: P331304

CATALOG NUMBER: SA2XXDIP-C485D725U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	271.2	270.8	270.4	270.0	269.6	269.3	268.9
115°	315.3	315.1	314.7	314.2	313.7	313.2	312.7
117.5°	357.4	356.9	356.5	356.0	355.4	354.9	354.4
120°	386.1	386.1	385.9	385.3	384.8	384.3	383.8
122.5°	414.9	414.5	414.1	413.7	413.3	412.9	412.6
125°	458.0	457.5	457.2	457.0	456.8	456.7	456.5
127.5°	499.9	499.3	498.7	498.2	497.6	497.1	496.5
130°	528.9	528.6	528.0	527.3	526.7	526.0	525.3
132.5°	556.4	555.7	555.0	554.4	553.9	553.3	552.8
135°	598.2	598.0	597.7	597.2	596.7	596.1	595.6
137.5°	637.7	637.6	637.2	636.5	635.8	635.1	634.4
140°	664.4	664.4	664.0	663.4	662.7	662.0	661.3
142.5°	688.6	688.7	688.4	687.7	687.0	686.4	685.7
145°	725.1	725.3	725.0	724.3	723.6	722.9	722.2
147.5°	757.3	757.7	757.6	756.9	756.2	755.6	754.9
150°	777.7	778.3	778.3	777.7	777.2	776.7	776.2
152.5°	798.2	798.8	798.8	798.2	797.5	796.8	796.2
155°	824.1	825.0	825.2	824.6	824.1	823.6	823.1
157.5°	848.2	849.4	849.5	848.7	847.9	847.0	846.2
160°	862.2	863.2	863.4	862.7	862.0	861.3	860.6
162.5°	875.1	876.3	876.4	875.6	874.8	873.9	873.1
165°	891.6	892.8	893.0	892.1	891.2	890.4	889.5
167.5°	905.2	906.4	906.6	905.7	904.8	903.9	903.0
170°	912.7	913.9	914.0	913.0	911.9	910.9	909.8
172.5°	918.3	919.5	919.6	918.6	917.5	916.5	915.5
175°	924.4	925.6	925.7	924.7	923.6	922.6	921.6
177.5°	926.9	927.7	927.7	926.9	926.0	925.2	924.4
180°	926.2	926.2	926.2	926.2	926.2	926.2	926.2

(END OF REPORT)