

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331310

Luminaire Tested: **SA2XXDIP-C485D725U835-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331310
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C485D725U835-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 725 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4569.7 lumens
Efficiency: N/A
Efficacy: 119.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 38.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331310
CATALOG NUMBER: SA2XXDIP-C485D725U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331310

CATALOG NUMBER: SA2XXDIP-C485D725U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	43
1	96	92	88	85	88	84	81	78	70	67	65	56	55	53	44	43	42	36
2	88	80	74	69	80	74	68	64	61	57	54	50	47	45	39	37	35	31
3	80	71	63	58	73	65	58	53	54	49	45	44	40	38	34	32	30	26
4	73	62	55	49	67	57	51	45	48	43	39	39	35	32	31	28	26	22
5	67	56	48	42	61	51	44	39	43	37	33	35	31	28	28	25	23	19
6	62	50	42	36	56	46	39	34	39	33	29	32	28	24	25	22	20	17
7	57	45	37	32	52	41	34	30	35	29	26	29	25	22	23	20	18	15
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	21	18	16	13
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	17	14	12
10	46	34	27	22	42	32	25	21	27	22	18	22	18	16	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12540	12540	12540
5°	12588	12407	12480
10°	12514	12281	12342
15°	12359	12122	12109
20°	12139	11883	11869
25°	11922	11589	11589
30°	11641	11320	11222
35°	11379	10996	10835
40°	11051	10673	10467
45°	10727	10351	10095
50°	10374	10017	9661
55°	10007	9627	9272
60°	9597	9164	8825
65°	9158	8703	8302
70°	8601	8143	7756
75°	7829	7498	7317
80°	6946	6732	6388
85°	5669	5391	4835



TEST NUMBER: P331310

CATALOG NUMBER: SA2XXDIP-C485D725U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.0	1.6
10°-20°	205.5	4.5
20°-30°	302.1	6.6
30°-40°	350.9	7.7
40°-50°	350.5	7.7
50°-60°	305.6	6.7
60°-70°	226.0	4.9
70°-80°	128.0	2.8
80°-90°	38.1	0.8
90°-100°	58.7	1.3
100°-110°	182.3	4.0
110°-120°	311.6	6.8
120°-130°	409.8	9.0
130°-140°	459.9	10.1
140°-150°	450.9	9.9
150°-160°	378.2	8.3
160°-170°	250.9	5.5
170°-180°	87.7	1.9
0°-30°	580.6	12.7
0°-40°	931.5	20.4
0°-60°	1587.6	34.7
0°-90°	1979.7	43.3
90°-120°	552.6	12.1
90°-150°	1873.2	41.0
90°-180°	2590.0	56.7
0°-180°	4569.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	777	777	777	777	777	
5°	777	773	766	771	770	74
15°	739	735	725	728	724	208
25°	669	663	650	652	650	308
35°	577	570	558	553	550	360
45°	470	464	453	445	442	362
55°	356	351	342	333	329	318
65°	240	235	228	221	217	237
75°	126	124	120	116	117	134
85°	31	30	29	27	26	35
90°	1	11	27	26	27	4
95°	41	48	50	50	48	47
105°	168	170	172	173	174	177
115°	313	317	316	315	313	309
125°	455	461	460	457	456	406
135°	589	597	599	598	596	454
145°	714	720	725	725	722	446
155°	817	819	822	825	823	376
165°	889	888	888	893	890	251
175°	925	922	921	926	922	88
180°	926	926	926	926	926	



TEST NUMBER: P331310

CATALOG NUMBER: SA2XXDIP-C485D725U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	776.7	776.7	776.7	776.7	776.7	776.7	776.7	776.7	776.7	776.7	776.7
2.5°	780.3	779.6	779.0	778.3	777.6	776.6	775.1	773.7	772.2	770.7	772.1
5°	776.7	776.0	775.4	774.7	774.1	772.8	771.0	769.2	767.3	765.5	766.8
7.5°	769.8	768.8	767.8	766.7	765.7	764.3	762.4	760.6	758.7	756.8	758.2
10°	763.3	762.1	760.9	759.8	758.6	757.0	755.0	753.1	751.1	749.1	750.4
12.5°	754.3	753.3	752.2	751.2	750.2	748.7	746.7	744.7	742.7	740.7	741.6
15°	739.4	738.4	737.4	736.4	735.4	733.8	731.6	729.5	727.3	725.2	725.8
17.5°	720.2	719.3	718.3	717.3	716.3	714.7	712.5	710.3	708.1	705.9	706.7
20°	706.5	705.5	704.5	703.5	702.5	700.9	698.5	696.2	693.9	691.6	692.1
22.5°	692.8	691.4	690.0	688.6	687.2	685.4	683.2	681.0	678.8	676.6	676.7
25°	669.2	667.8	666.5	665.2	663.9	661.8	659.0	656.1	653.3	650.5	650.8
27.5°	642.3	641.1	639.9	638.7	637.5	635.8	633.6	631.3	629.1	626.9	626.4
30°	624.4	623.0	621.7	620.4	619.0	617.1	614.6	612.2	609.7	607.2	606.7
32.5°	605.2	604.2	603.1	602.0	601.0	599.1	596.5	593.9	591.3	588.7	587.8
35°	577.3	575.6	574.0	572.3	570.7	568.5	565.9	563.2	560.5	557.9	556.9
37.5°	545.8	544.3	542.9	541.4	539.9	537.9	535.2	532.6	529.9	527.3	526.0
40°	524.3	522.9	521.6	520.3	519.0	517.0	514.3	511.7	509.0	506.4	504.9
42.5°	503.4	502.0	500.7	499.4	498.1	496.1	493.4	490.8	488.1	485.4	483.8
45°	469.8	468.6	467.4	466.3	465.1	463.3	460.8	458.3	455.8	453.3	451.5
47.5°	436.3	435.2	434.1	433.0	431.9	430.1	427.5	424.9	422.3	419.7	417.8
50°	413.0	412.2	411.3	410.5	409.7	408.1	405.8	403.5	401.1	398.8	396.5
52.5°	390.3	389.2	388.1	387.0	385.9	384.3	382.1	379.9	377.7	375.5	373.6
55°	355.5	354.5	353.5	352.5	351.5	350.0	348.0	346.0	344.0	342.0	340.1
57.5°	320.5	319.7	318.9	318.2	317.4	315.9	313.7	311.5	309.3	307.1	305.1
60°	297.2	296.6	295.9	295.2	294.6	293.1	290.8	288.4	286.1	283.8	282.0
62.5°	274.5	273.5	272.4	271.3	270.3	268.9	267.1	265.3	263.5	261.7	260.0
65°	239.7	238.7	237.7	236.7	235.8	234.4	232.8	231.1	229.4	227.8	226.3
67.5°	204.3	203.5	202.7	201.9	201.1	200.0	198.5	197.0	195.5	194.0	192.9
70°	182.2	181.6	180.9	180.2	179.6	178.5	177.0	175.5	174.0	172.5	171.4
72.5°	159.5	158.9	158.2	157.5	156.9	156.1	155.1	154.1	153.2	152.2	151.0
75°	125.5	125.1	124.8	124.5	124.1	123.6	122.7	121.9	121.1	120.2	119.2
77.5°	95.0	94.4	93.9	93.3	92.7	92.3	92.0	91.6	91.3	91.0	90.5
80°	74.7	74.5	74.4	74.2	74.0	73.8	73.4	73.1	72.8	72.4	71.9
82.5°	55.6	55.5	55.5	55.5	55.4	55.3	55.1	54.9	54.7	54.5	53.9
85°	30.6	30.5	30.3	30.1	30.0	29.8	29.6	29.5	29.3	29.1	28.6
87.5°	10.9	11.1	11.2	11.4	11.5	11.8	12.3	12.8	13.3	13.8	13.4
90°	0.8	2.9	5.0	7.0	9.1	12.1	15.9	19.7	23.5	27.4	27.0
92.5°	13.9	15.4	17.0	18.5	20.0	21.2	22.1	23.0	24.0	24.9	24.9
95°	40.6	42.4	44.1	45.9	47.6	48.6	49.0	49.3	49.7	50.0	50.0
97.5°	74.3	75.8	77.3	78.8	80.4	81.5	82.1	82.8	83.4	84.1	84.1
100°	99.3	100.7	102.0	103.4	104.8	105.8	106.3	106.8	107.3	107.9	107.9
102.5°	125.5	126.6	127.8	128.9	130.0	130.9	131.5	132.2	132.8	133.5	133.6
105°	168.1	168.6	169.1	169.6	170.1	170.6	170.9	171.3	171.6	172.0	172.3
107.5°	210.9	211.7	212.4	213.2	213.9	214.3	214.3	214.3	214.3	214.3	214.5
110°	238.4	239.4	240.5	241.5	242.6	243.1	243.1	243.1	243.1	243.1	243.1



TEST NUMBER: P331310

CATALOG NUMBER: SA2XXDIP-C485D725U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	268.4	269.5	270.5	271.5	272.6	273.0	272.9	272.8	272.6	272.5	272.1
115°	312.7	313.7	314.7	315.8	316.8	317.2	316.8	316.5	316.1	315.8	315.6
117.5°	356.7	358.1	359.5	360.9	362.3	362.5	361.5	360.6	359.6	358.6	358.2
120°	386.1	387.5	388.9	390.3	391.7	391.7	390.3	388.9	387.5	386.1	386.1
122.5°	413.0	414.7	416.4	418.0	419.7	420.0	419.1	418.1	417.1	416.1	415.7
125°	454.9	456.5	458.0	459.6	461.2	461.7	461.2	460.6	460.1	459.6	459.1
127.5°	495.7	497.7	499.7	501.7	503.6	504.3	503.7	503.1	502.4	501.8	501.2
130°	521.4	523.6	525.9	528.1	530.4	531.3	531.0	530.6	530.3	530.0	529.6
132.5°	550.1	552.0	553.8	555.6	557.5	558.4	558.5	558.6	558.6	558.7	558.0
135°	588.6	590.5	592.4	594.3	596.2	597.3	597.7	598.0	598.4	598.7	598.6
137.5°	629.1	630.6	632.2	633.8	635.3	636.3	636.8	637.2	637.7	638.1	638.0
140°	653.5	655.0	656.6	658.1	659.7	660.9	661.8	662.7	663.5	664.4	664.4
142.5°	678.5	680.0	681.6	683.2	684.7	685.8	686.4	687.0	687.6	688.2	688.3
145°	714.4	715.6	716.9	718.1	719.3	720.4	721.5	722.5	723.5	724.6	724.8
147.5°	746.5	747.9	749.4	750.8	752.3	753.4	754.1	754.8	755.5	756.2	756.5
150°	768.4	769.4	770.4	771.5	772.5	773.4	774.1	774.8	775.5	776.2	776.7
152.5°	787.7	788.8	789.8	790.9	791.9	792.8	793.7	794.5	795.3	796.2	796.8
155°	816.8	817.3	817.9	818.4	818.9	819.4	819.9	820.5	821.0	821.5	822.4
157.5°	841.7	842.0	842.4	842.7	843.1	843.4	843.7	844.0	844.3	844.6	845.8
160°	856.7	857.0	857.4	857.7	858.1	858.3	858.5	858.7	858.9	859.0	860.1
162.5°	870.4	870.5	870.6	870.6	870.7	870.8	871.0	871.2	871.4	871.5	872.7
165°	888.7	888.6	888.4	888.2	888.0	887.9	887.9	887.9	887.9	887.9	889.2
167.5°	904.0	903.5	903.0	902.5	902.0	901.7	901.7	901.6	901.6	901.5	902.8
170°	912.2	911.7	911.1	910.6	910.1	909.7	909.6	909.4	909.2	909.0	910.3
172.5°	917.8	917.3	916.8	916.2	915.7	915.4	915.2	915.0	914.9	914.7	915.9
175°	924.7	924.2	923.6	923.1	922.6	922.2	921.8	921.5	921.1	920.8	922.0
177.5°	927.5	927.1	926.7	926.2	925.8	925.5	925.2	924.9	924.6	924.4	925.2
180°	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2



TEST NUMBER: P331310

CATALOG NUMBER: SA2XXDIP-C485D725U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	776.7	776.7	776.7	776.7	776.7	776.7	776.7	776.7
2.5°	773.4	774.7	776.0	776.6	776.3	776.0	775.8	775.5
5°	768.2	769.5	770.8	771.3	771.0	770.6	770.3	770.0
7.5°	759.5	760.8	762.2	762.6	762.3	761.9	761.5	761.2
10°	751.7	753.1	754.4	754.8	754.3	753.8	753.3	752.8
12.5°	742.6	743.5	744.4	744.7	744.3	744.0	743.6	743.2
15°	726.5	727.2	727.8	727.7	726.9	726.1	725.3	724.4
17.5°	707.4	708.2	709.0	708.9	708.1	707.4	706.6	705.8
20°	692.6	693.1	693.6	693.5	692.8	692.1	691.5	690.8
22.5°	676.8	676.9	677.0	676.9	676.5	676.1	675.7	675.3
25°	651.2	651.5	651.8	651.8	651.5	651.2	650.8	650.5
27.5°	625.9	625.4	624.9	624.3	623.5	622.7	621.9	621.1
30°	606.2	605.7	605.2	604.6	603.9	603.3	602.6	601.9
32.5°	586.9	586.0	585.1	584.3	583.6	583.0	582.3	581.6
35°	555.9	554.9	553.9	553.0	552.2	551.3	550.5	549.7
37.5°	524.8	523.6	522.4	521.3	520.5	519.7	518.9	518.2
40°	503.4	501.9	500.4	499.3	498.6	498.0	497.3	496.6
42.5°	482.2	480.6	478.9	477.7	476.7	475.8	474.9	473.9
45°	449.7	447.9	446.0	444.8	444.1	443.5	442.8	442.1
47.5°	415.9	413.9	412.0	410.6	409.6	408.7	407.7	406.7
50°	394.2	391.8	389.5	387.9	387.1	386.3	385.4	384.6
52.5°	371.7	369.7	367.8	366.3	365.2	364.1	363.0	361.9
55°	338.1	336.1	334.1	332.7	331.8	331.0	330.2	329.4
57.5°	303.2	301.2	299.3	298.0	297.3	296.7	296.1	295.4
60°	280.1	278.3	276.5	275.3	274.8	274.3	273.8	273.3
62.5°	258.3	256.6	254.9	253.8	253.1	252.5	251.9	251.2
65°	224.8	223.3	221.8	220.6	219.8	219.0	218.2	217.3
67.5°	191.7	190.5	189.4	188.5	187.8	187.1	186.5	185.8
70°	170.2	169.0	167.9	167.0	166.3	165.6	165.0	164.3
72.5°	149.9	148.7	147.6	146.7	146.2	145.6	145.1	144.6
75°	118.2	117.3	116.3	115.9	116.3	116.6	116.9	117.3
77.5°	90.0	89.5	89.0	88.5	88.0	87.6	87.1	86.6
80°	71.4	70.9	70.5	70.0	69.7	69.4	69.0	68.7
82.5°	53.3	52.6	52.0	51.6	51.6	51.5	51.4	51.4
85°	28.1	27.6	27.1	26.8	26.6	26.5	26.3	26.1
87.5°	12.9	12.4	12.0	11.7	11.6	11.5	11.4	11.3
90°	26.7	26.3	26.0	25.9	26.1	26.2	26.4	26.6
92.5°	25.0	25.1	25.1	25.2	25.2	25.3	25.3	25.3
95°	50.0	50.0	50.0	49.9	49.5	49.2	48.8	48.5
97.5°	84.1	84.1	84.1	84.1	84.1	84.0	84.0	83.9
100°	107.9	107.9	107.9	107.8	107.6	107.4	107.3	107.1
102.5°	133.8	133.9	134.1	134.0	133.9	133.7	133.5	133.3
105°	172.7	173.0	173.4	173.5	173.5	173.5	173.5	173.5
107.5°	214.6	214.7	214.9	214.6	213.8	213.0	212.2	211.4
110°	243.1	243.1	243.1	242.8	242.3	241.8	241.3	240.7



TEST NUMBER: P331310

CATALOG NUMBER: SA2XXDIP-C485D725U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	271.6	271.2	270.8	270.4	270.0	269.6	269.3	268.9
115°	315.4	315.3	315.1	314.7	314.2	313.7	313.2	312.7
117.5°	357.8	357.4	356.9	356.5	356.0	355.4	354.9	354.4
120°	386.1	386.1	386.1	385.9	385.3	384.8	384.3	383.8
122.5°	415.3	414.9	414.5	414.1	413.7	413.3	412.9	412.6
125°	458.6	458.0	457.5	457.2	457.0	456.8	456.7	456.5
127.5°	500.6	499.9	499.3	498.7	498.2	497.6	497.1	496.5
130°	529.3	528.9	528.6	528.0	527.3	526.7	526.0	525.3
132.5°	557.2	556.4	555.7	555.0	554.4	553.9	553.3	552.8
135°	598.4	598.2	598.0	597.7	597.2	596.7	596.1	595.6
137.5°	637.9	637.7	637.6	637.2	636.5	635.8	635.1	634.4
140°	664.4	664.4	664.4	664.0	663.4	662.7	662.0	661.3
142.5°	688.4	688.6	688.7	688.4	687.7	687.0	686.4	685.7
145°	724.9	725.1	725.3	725.0	724.3	723.6	722.9	722.2
147.5°	756.9	757.3	757.7	757.6	756.9	756.2	755.6	754.9
150°	777.2	777.7	778.3	778.3	777.7	777.2	776.7	776.2
152.5°	797.5	798.2	798.8	798.8	798.2	797.5	796.8	796.2
155°	823.2	824.1	825.0	825.2	824.6	824.1	823.6	823.1
157.5°	847.0	848.2	849.4	849.5	848.7	847.9	847.0	846.2
160°	861.1	862.2	863.2	863.4	862.7	862.0	861.3	860.6
162.5°	873.9	875.1	876.3	876.4	875.6	874.8	873.9	873.1
165°	890.4	891.6	892.8	893.0	892.1	891.2	890.4	889.5
167.5°	904.0	905.2	906.4	906.6	905.7	904.8	903.9	903.0
170°	911.5	912.7	913.9	914.0	913.0	911.9	910.9	909.8
172.5°	917.1	918.3	919.5	919.6	918.6	917.5	916.5	915.5
175°	923.2	924.4	925.6	925.7	924.7	923.6	922.6	921.6
177.5°	926.0	926.9	927.7	927.7	926.9	926.0	925.2	924.4
180°	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2

(END OF REPORT)