

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331366

Luminaire Tested: **SA2XXDIP-C675D1080U835-4F0-1E-UDD-A**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331366
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C675D1080U835-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1080 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7239.4 lumens
Efficiency: N/A
Efficacy: 127.2 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 56.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331366
CATALOG NUMBER: SA2XXDIP-C675D1080U835-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331366

CATALOG NUMBER: SA2XXDIP-C675D1080U835-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	47	47	47	41				41
1	96	92	88	85	87	84	81	78	69	67	65	55	54	52	42	42	41				35	
2	88	81	75	70	80	74	69	65	61	57	54	49	46	44	38	36	35				30	
3	80	71	64	59	73	65	59	54	54	50	46	44	41	38	34	32	30				26	
4	74	63	56	50	67	58	51	46	48	43	40	39	36	33	31	28	26				22	
5	68	57	49	43	61	52	45	40	43	38	34	35	32	29	28	25	23				20	
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	25	23	21				18	
7	58	46	38	33	53	42	36	31	36	30	27	29	25	22	23	20	18				16	
8	54	42	34	29	49	39	32	27	32	27	24	27	23	20	21	19	17				14	
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	20	17	15				13	
10	47	35	28	23	43	32	26	22	27	23	19	23	19	16	18	16	14				12	

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	21447	21447	21447	21447
5°	24044	21585	19128	21585
10°	27552	21408	16554	21408
15°	30479	21016	14626	21016
20°	30015	20594	13332	20594
25°	27064	20035	12513	20035
30°	22365	19140	11915	19140
35°	16301	18203	11491	18203
40°	13019	17098	11255	17098
45°	11376	15817	10933	15817
50°	10693	14579	10721	14579
55°	9858	13320	10432	13320
60°	9032	11983	9991	11983
65°	8229	10785	9555	10785
70°	7468	9616	8917	9616
75°	6625	8309	7898	8309
80°	5700	6881	6360	6881
85°	5113	5113	3779	5113



TEST NUMBER: P331366

CATALOG NUMBER: SA2XXDIP-C675D1080U835-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.5	1.7
10°-20°	367.8	5.1
20°-30°	533.7	7.4
30°-40°	563.2	7.8
40°-50°	498.7	6.9
50°-60°	398.0	5.5
60°-70°	270.5	3.7
70°-80°	138.7	1.9
80°-90°	37.1	0.5
90°-100°	49.0	0.7
100°-110°	179.7	2.5
110°-120°	480.4	6.6
120°-130°	793.0	11.0
130°-140°	843.3	11.6
140°-150°	783.8	10.8
150°-160°	630.2	8.7
160°-170°	406.1	5.6
170°-180°	139.8	1.9
0°-30°	1028.0	14.2
0°-40°	1591.2	22.0
0°-60°	2487.8	34.4
0°-90°	2934.1	40.5
90°-120°	709.1	9.8
90°-150°	3129.2	43.2
90°-180°	4305.0	59.5
0°-180°	7239.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1328	1328	1328	1328	1328	
5°	1484	1332	1180	1332	1484	148
15°	1823	1257	875	1257	1823	503
25°	1519	1125	702	1125	1519	687
35°	827	924	583	924	827	538
45°	498	693	479	693	498	392
55°	350	473	371	473	350	314
65°	215	282	250	282	215	214
75°	106	133	127	133	106	113
85°	28	28	20	28	28	31
90°	29	1	29	1	29	14
95°	46	69	46	69	46	43
105°	81	323	81	323	81	84
115°	87	611	87	611	87	218
125°	909	864	909	864	909	786
135°	1104	1069	1104	1069	1104	851
145°	1260	1241	1260	1241	1260	788
155°	1367	1366	1367	1366	1367	631
165°	1436	1439	1436	1439	1436	405
175°	1464	1472	1464	1472	1464	139
180°	1469	1469	1469	1469	1469	



TEST NUMBER: P331366

CATALOG NUMBER: SA2XXDIP-C675D1080U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3
2.5°	1389.5	1389.9	1390.8	1384.2	1383.4	1383.4	1377.7	1372.8	1367.1	1359.3	1360.1
5°	1483.5	1489.1	1491.1	1485.0	1475.8	1474.8	1466.1	1451.8	1438.5	1427.8	1420.2
7.5°	1595.6	1597.8	1592.8	1584.7	1577.9	1565.7	1549.5	1533.7	1511.5	1491.2	1476.1
10°	1680.5	1683.6	1674.9	1663.2	1653.5	1639.2	1615.7	1591.7	1562.6	1534.5	1512.0
12.5°	1745.0	1752.6	1741.5	1739.9	1723.3	1703.7	1675.7	1663.6	1622.6	1583.5	1559.4
15°	1823.4	1822.9	1824.0	1814.3	1802.0	1798.9	1769.3	1737.2	1679.5	1656.5	1616.7
17.5°	1800.8	1808.5	1812.1	1812.0	1811.7	1809.8	1800.3	1780.0	1751.1	1713.8	1667.8
20°	1746.9	1757.1	1758.6	1770.4	1777.0	1785.7	1789.2	1783.6	1765.8	1734.6	1694.8
22.5°	1663.6	1666.4	1671.2	1689.5	1703.9	1725.6	1737.0	1755.9	1749.0	1733.8	1700.5
25°	1519.2	1514.1	1532.0	1541.1	1574.3	1609.0	1634.1	1661.6	1686.1	1700.9	1691.2
27.5°	1345.8	1338.2	1364.9	1389.3	1416.3	1453.9	1492.9	1538.9	1577.2	1625.1	1641.5
30°	1199.6	1204.2	1229.8	1255.8	1296.6	1349.7	1393.6	1444.2	1498.8	1552.4	1589.6
32.5°	1042.0	1059.7	1075.8	1115.7	1151.6	1210.9	1275.2	1338.4	1406.5	1467.4	1525.1
35°	827.0	847.4	869.9	899.0	949.5	1008.2	1071.0	1156.2	1249.2	1332.4	1400.8
37.5°	696.1	692.8	705.7	726.7	767.7	815.0	887.3	971.6	1080.9	1178.7	1275.2
40°	617.7	615.6	624.8	644.2	675.4	710.1	773.4	847.4	949.0	1068.4	1183.3
42.5°	563.8	565.0	570.1	583.8	605.1	633.7	681.1	744.1	837.1	949.6	1073.0
45°	498.2	501.8	507.4	514.1	526.3	549.8	576.3	621.3	694.8	788.7	910.2
47.5°	451.1	451.2	456.9	462.7	470.0	483.2	504.9	533.0	584.9	661.4	765.8
50°	425.7	422.2	426.3	430.8	438.5	447.7	462.0	488.5	523.2	585.0	672.3
52.5°	394.7	394.8	398.5	400.2	407.1	416.2	429.3	447.7	479.1	527.4	599.2
55°	350.2	352.7	354.8	357.8	364.0	370.6	380.8	393.1	417.6	453.8	506.9
57.5°	308.3	309.1	311.2	317.0	320.9	327.0	336.7	347.8	363.8	390.6	430.5
60°	279.7	279.7	283.8	286.4	291.5	297.6	305.3	316.0	330.3	352.2	384.4
62.5°	253.6	253.2	254.8	259.0	262.9	268.6	276.3	285.4	298.8	318.3	344.8
65°	215.4	214.4	217.5	218.5	222.6	228.2	234.3	244.0	254.7	269.0	292.5
67.5°	178.7	179.9	181.5	183.5	185.7	191.6	195.7	202.6	211.6	223.5	239.4
70°	158.2	158.2	158.2	159.8	162.8	165.9	170.0	175.6	184.3	194.5	208.8
72.5°	135.4	137.0	138.6	137.7	141.6	143.4	148.3	151.5	159.8	166.3	179.0
75°	106.2	106.2	106.2	108.7	110.3	111.8	114.9	117.9	122.0	130.2	136.8
77.5°	79.2	79.0	79.5	80.1	81.8	83.6	84.5	87.3	91.1	94.8	100.5
80°	61.3	62.3	62.8	63.8	63.8	64.8	65.3	68.9	71.5	74.0	77.6
82.5°	47.4	47.6	47.7	47.9	48.3	48.9	50.2	51.4	52.3	54.4	57.2
85°	27.6	27.1	27.1	28.1	27.6	27.6	28.6	29.6	29.6	30.1	31.6
87.5°	16.4	16.3	16.6	16.1	16.0	16.2	16.0	15.3	15.5	15.7	15.7
90°	28.7	28.2	27.8	27.3	26.8	26.0	24.8	23.6	22.4	21.3	19.4
92.5°	28.7	28.4	28.1	27.9	27.6	27.1	26.5	25.9	25.3	24.7	23.7
95°	45.7	45.9	46.2	46.4	46.7	46.2	45.0	43.8	42.6	41.5	39.8
97.5°	61.0	60.7	60.5	60.2	59.9	59.3	58.3	57.4	56.4	55.5	51.7
100°	71.2	70.8	70.3	69.8	69.3	68.2	66.3	64.4	62.5	60.6	56.6
102.5°	76.3	75.7	75.0	74.3	73.7	72.1	69.7	67.2	64.8	62.3	95.9
105°	80.8	79.8	78.9	78.0	77.0	75.2	72.6	70.0	67.4	64.8	129.3
107.5°	83.1	82.2	81.2	80.3	79.4	80.2	82.8	85.5	88.1	90.8	168.1
110°	84.0	83.0	82.1	81.1	80.2	91.5	115.2	138.8	162.4	186.0	254.3



TEST NUMBER: P331366

CATALOG NUMBER: SA2XXDIP-C675D1080U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	84.8	84.1	83.3	82.6	81.8	124.5	210.7	296.9	383.1	469.2	486.1
115°	87.2	104.2	121.2	138.2	155.2	218.4	327.8	437.1	546.5	655.9	650.0
117.5°	355.9	411.8	467.7	523.6	579.5	620.7	647.1	673.6	700.0	726.5	722.4
120°	648.5	680.3	712.2	744.1	776.0	790.6	787.7	784.9	782.0	779.2	775.0
122.5°	809.2	815.4	821.6	827.8	833.9	836.2	834.5	832.8	831.1	829.4	824.8
125°	908.9	908.2	907.5	906.8	906.1	904.9	903.2	901.6	899.9	898.3	893.8
127.5°	971.8	971.7	971.6	971.4	971.3	970.0	967.6	965.2	962.8	960.4	957.0
130°	1011.0	1011.2	1011.4	1011.7	1011.9	1010.7	1008.1	1005.5	1002.9	1000.3	997.7
132.5°	1049.2	1049.5	1049.7	1049.9	1050.2	1049.2	1047.0	1044.7	1042.5	1040.3	1037.7
135°	1104.5	1105.0	1105.4	1105.9	1106.4	1105.4	1103.1	1100.7	1098.4	1096.0	1093.9
137.5°	1154.9	1155.7	1156.5	1157.3	1158.1	1157.3	1155.0	1152.7	1150.4	1148.1	1145.7
140°	1186.4	1187.5	1188.7	1189.9	1191.1	1190.6	1188.5	1186.4	1184.2	1182.1	1179.5
142.5°	1217.0	1218.2	1219.3	1220.5	1221.7	1221.3	1219.4	1217.4	1215.5	1213.6	1210.6
145°	1259.7	1260.9	1262.1	1263.3	1264.4	1264.2	1262.5	1260.9	1259.2	1257.6	1253.6
147.5°	1297.3	1298.3	1299.3	1300.3	1301.3	1301.2	1300.0	1298.7	1297.5	1296.3	1292.3
150°	1320.3	1321.5	1322.7	1323.8	1325.0	1324.9	1323.5	1322.1	1320.7	1319.2	1315.5
152.5°	1339.9	1341.4	1343.0	1344.5	1346.1	1346.2	1344.8	1343.3	1341.9	1340.5	1336.9
155°	1367.1	1369.0	1370.9	1372.7	1374.6	1374.9	1373.5	1372.0	1370.6	1369.2	1366.4
157.5°	1391.9	1393.8	1395.6	1397.5	1399.3	1399.4	1397.8	1396.2	1394.6	1393.0	1391.0
160°	1406.4	1408.1	1409.7	1411.4	1413.0	1413.1	1411.7	1410.3	1408.9	1407.5	1406.1
162.5°	1418.3	1420.3	1422.4	1424.4	1426.4	1426.7	1425.0	1423.4	1421.8	1420.2	1419.0
165°	1436.2	1437.8	1439.5	1441.1	1442.8	1442.8	1441.1	1439.5	1437.8	1436.2	1435.5
167.5°	1447.4	1449.6	1451.7	1453.8	1455.9	1456.2	1454.5	1452.9	1451.2	1449.6	1448.9
170°	1454.2	1456.4	1458.5	1460.6	1462.7	1463.0	1461.3	1459.7	1458.0	1456.4	1455.9
172.5°	1459.3	1461.5	1463.6	1465.7	1467.9	1468.1	1466.4	1464.8	1463.1	1461.5	1461.0
175°	1463.8	1466.2	1468.5	1470.9	1473.3	1473.6	1472.0	1470.3	1468.7	1467.0	1466.5
177.5°	1466.6	1468.3	1470.0	1471.7	1473.4	1473.6	1472.2	1470.9	1469.6	1468.3	1468.1
180°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1



TEST NUMBER: P331366

CATALOG NUMBER: SA2XXDIP-C675D1080U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3
2.5°	1363.0	1359.7	1357.7	1350.3	1343.8	1337.3	1335.2	1336.0	1327.1	1318.5	1314.8
5°	1416.1	1405.9	1396.2	1382.4	1366.1	1348.2	1339.0	1331.8	1314.0	1294.6	1283.4
7.5°	1463.7	1449.1	1430.4	1404.4	1380.7	1352.6	1334.7	1318.9	1292.7	1265.4	1248.6
10°	1492.7	1472.7	1448.7	1417.1	1388.0	1353.8	1329.8	1305.8	1275.2	1242.5	1222.1
12.5°	1517.6	1490.7	1467.1	1426.5	1392.1	1349.3	1320.8	1287.0	1254.8	1216.0	1196.0
15°	1576.9	1527.4	1482.4	1436.5	1394.1	1334.4	1302.8	1257.3	1214.9	1167.0	1144.0
17.5°	1622.7	1567.1	1496.3	1437.9	1388.5	1322.4	1275.9	1221.5	1171.4	1116.5	1085.3
20°	1648.9	1585.0	1509.0	1439.6	1380.3	1304.8	1254.3	1198.6	1139.9	1078.1	1044.4
22.5°	1664.4	1597.3	1522.1	1433.4	1364.0	1290.5	1226.9	1165.9	1106.4	1039.8	1004.4
25°	1669.3	1608.0	1528.4	1428.3	1343.6	1260.4	1183.8	1124.6	1052.6	990.3	938.8
27.5°	1645.0	1601.1	1524.5	1418.7	1320.0	1222.7	1137.4	1070.3	994.3	926.7	874.9
30°	1615.2	1589.6	1515.1	1408.9	1301.2	1196.6	1102.6	1026.6	951.0	882.6	829.5
32.5°	1569.0	1563.5	1498.0	1395.0	1281.2	1163.5	1066.3	989.4	905.7	838.5	787.9
35°	1478.4	1502.9	1461.5	1364.0	1243.5	1116.4	1011.3	923.5	836.7	772.4	724.9
37.5°	1356.9	1417.7	1406.9	1318.6	1192.7	1065.2	949.1	857.3	774.6	709.7	663.1
40°	1273.1	1350.7	1362.0	1283.9	1156.8	1025.6	902.5	811.2	730.5	671.3	624.3
42.5°	1183.3	1274.0	1304.8	1242.2	1117.5	983.9	860.9	766.2	686.4	628.8	587.2
45°	1032.7	1152.7	1208.3	1172.6	1052.1	915.3	788.7	692.7	620.2	566.1	534.0
47.5°	891.9	1023.0	1097.8	1085.2	979.3	843.8	718.7	626.6	556.0	512.8	484.0
50°	792.3	927.0	1017.4	1021.5	927.0	792.8	667.2	580.4	515.6	475.3	451.8
52.5°	705.7	834.3	932.9	954.5	868.6	739.7	621.1	534.7	477.6	440.5	419.5
55°	592.7	701.4	810.6	850.5	781.5	659.0	549.3	473.2	419.6	394.1	375.7
57.5°	492.7	583.4	684.3	728.3	685.8	580.9	478.0	412.0	368.5	346.1	332.0
60°	440.0	511.5	601.3	653.9	617.2	523.8	433.9	371.1	335.4	315.5	302.2
62.5°	391.0	454.3	530.3	578.4	558.4	470.3	389.8	334.4	303.5	284.8	275.3
65°	322.6	372.7	431.4	475.8	462.5	395.6	329.8	282.3	257.8	243.0	235.3
67.5°	265.7	301.8	342.5	381.4	370.7	323.3	270.5	233.5	215.2	202.5	197.9
70°	229.7	257.3	293.5	324.7	316.0	277.2	235.3	203.7	187.9	177.1	172.5
72.5°	195.4	218.1	245.7	271.2	265.3	233.1	198.2	174.3	162.1	152.2	148.4
75°	147.5	164.9	181.7	198.6	197.0	172.0	151.6	133.2	123.5	115.9	114.3
77.5°	108.9	118.6	130.1	140.1	137.3	123.0	107.0	96.5	89.3	84.2	83.4
80°	83.2	88.8	97.0	104.1	100.6	94.4	81.7	74.0	68.9	63.8	61.8
82.5°	60.3	66.0	70.9	74.7	72.0	66.3	58.4	53.2	50.1	46.7	45.8
85°	31.6	34.7	36.8	37.8	36.8	33.2	29.6	27.6	25.0	23.5	23.0
87.5°	15.7	15.4	15.0	15.4	13.6	13.1	10.9	9.2	9.3	9.4	9.1
90°	17.5	15.6	13.7	11.5	8.9	6.3	3.7	1.1	3.7	6.3	8.9
92.5°	22.8	21.8	20.9	20.5	20.8	21.0	21.2	21.5	21.2	21.0	20.8
95°	38.2	36.5	34.8	37.9	45.7	53.5	61.3	69.1	61.3	53.5	45.7
97.5°	47.8	44.0	40.2	49.3	71.2	93.2	115.2	137.1	115.2	93.2	71.2
100°	52.6	48.5	44.5	58.7	91.1	123.4	155.8	188.2	155.8	123.4	91.1
102.5°	129.5	163.1	196.7	216.9	223.7	230.6	237.4	244.3	237.4	230.6	223.7
105°	193.8	258.3	322.8	351.5	344.4	337.3	330.3	323.2	330.3	337.3	344.4
107.5°	245.5	322.8	400.2	436.0	430.2	424.5	418.8	413.1	418.8	424.5	430.2
110°	322.6	390.8	459.1	490.8	485.8	480.9	475.9	470.9	475.9	480.9	485.8



TEST NUMBER: P331366

CATALOG NUMBER: SA2XXDIP-C675D1080U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	503.0	519.8	536.7	542.9	538.5	534.1	529.8	525.4	529.8	534.1	538.5
115°	644.1	638.2	632.3	627.3	623.3	619.3	615.3	611.3	615.3	619.3	623.3
117.5°	718.4	714.3	710.2	706.0	701.5	697.0	692.5	688.0	692.5	697.0	701.5
120°	770.7	766.5	762.2	758.3	754.8	751.2	747.7	744.1	747.7	751.2	754.8
122.5°	820.1	815.5	810.9	806.7	803.0	799.2	795.5	791.8	795.5	799.2	803.0
125°	889.3	884.8	880.3	876.5	873.5	870.4	867.3	864.3	867.3	870.4	873.5
127.5°	953.6	950.3	946.9	943.6	940.2	936.8	933.4	930.0	933.4	936.8	940.2
130°	995.1	992.5	989.9	986.7	983.0	979.2	975.4	971.6	975.4	979.2	983.0
132.5°	1035.1	1032.5	1029.9	1027.0	1023.8	1020.6	1017.4	1014.1	1017.4	1020.6	1023.8
135°	1091.7	1089.6	1087.5	1084.5	1080.8	1077.0	1073.2	1069.4	1073.2	1077.0	1080.8
137.5°	1143.3	1140.9	1138.4	1135.9	1133.3	1130.6	1128.0	1125.3	1128.0	1130.6	1133.3
140°	1176.9	1174.3	1171.7	1169.5	1167.6	1165.7	1163.8	1161.9	1163.8	1165.7	1167.6
142.5°	1207.6	1204.6	1201.7	1199.3	1197.6	1195.9	1194.2	1192.5	1194.2	1195.9	1197.6
145°	1249.5	1245.5	1241.5	1239.6	1239.9	1240.1	1240.3	1240.6	1240.3	1240.1	1239.9
147.5°	1288.3	1284.4	1280.4	1278.9	1279.8	1280.7	1281.6	1282.5	1281.6	1280.7	1279.8
150°	1311.7	1307.9	1304.1	1303.1	1304.7	1306.4	1308.0	1309.7	1308.0	1306.4	1304.7
152.5°	1333.3	1329.7	1326.1	1325.3	1327.1	1328.9	1330.8	1332.6	1330.8	1328.9	1327.1
155°	1363.5	1360.7	1357.9	1357.5	1359.6	1361.8	1363.9	1366.0	1363.9	1361.8	1359.6
157.5°	1389.0	1387.1	1385.1	1385.0	1386.8	1388.6	1390.4	1392.2	1390.4	1388.6	1386.8
160°	1404.6	1403.2	1401.8	1401.8	1403.2	1404.6	1406.1	1407.5	1406.1	1404.6	1403.2
162.5°	1417.8	1416.5	1415.3	1415.4	1416.8	1418.2	1419.7	1421.1	1419.7	1418.2	1416.8
165°	1434.8	1434.0	1433.3	1433.7	1435.1	1436.5	1437.9	1439.4	1437.9	1436.5	1435.1
167.5°	1448.2	1447.6	1446.9	1447.3	1448.7	1450.1	1451.6	1453.0	1451.6	1450.1	1448.7
170°	1455.4	1455.0	1454.5	1455.0	1456.4	1457.8	1459.2	1460.6	1459.2	1457.8	1456.4
172.5°	1460.5	1460.1	1459.6	1460.1	1461.5	1462.9	1464.3	1465.7	1464.3	1462.9	1461.5
175°	1466.1	1465.6	1465.1	1465.7	1467.4	1469.0	1470.7	1472.3	1470.7	1469.0	1467.4
177.5°	1467.9	1467.7	1467.5	1468.1	1469.4	1470.7	1472.1	1473.4	1472.1	1470.7	1469.4
180°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1



TEST NUMBER: P331366

CATALOG NUMBER: SA2XXDIP-C675D1080U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3
2.5°	1310.7	1308.3	1299.7	1295.2	1287.8	1280.9	1276.4	1278.5	1280.1	1279.3	1278.0
5°	1273.1	1263.4	1248.6	1235.9	1226.7	1209.8	1202.7	1199.1	1196.1	1192.5	1188.9
7.5°	1228.4	1213.1	1191.9	1173.7	1156.5	1135.6	1123.7	1116.5	1109.2	1101.1	1094.0
10°	1196.6	1175.1	1152.7	1127.1	1106.7	1087.8	1071.0	1059.8	1049.6	1039.9	1032.7
12.5°	1163.1	1138.4	1110.6	1075.7	1053.2	1026.2	1023.6	1003.8	987.9	981.9	973.5
15°	1109.8	1075.1	1039.9	998.5	980.6	956.1	940.8	925.5	911.7	902.0	899.5
17.5°	1049.2	1004.3	969.3	939.6	910.3	885.2	871.1	858.8	847.5	834.5	832.8
20°	1003.1	964.3	926.0	900.0	869.9	844.3	827.0	814.7	805.0	797.4	790.7
22.5°	959.4	916.9	881.9	853.4	823.7	803.1	789.4	777.6	769.5	761.0	754.8
25°	889.3	856.1	817.8	785.6	761.1	747.9	736.6	726.4	721.3	715.7	708.6
27.5°	827.9	791.0	755.2	730.3	708.8	697.0	689.0	682.1	677.3	674.0	670.0
30°	784.6	747.3	719.3	694.8	676.9	665.2	660.1	656.0	650.4	648.3	646.3
32.5°	743.0	709.4	685.4	664.1	647.1	639.4	634.7	631.1	626.7	624.6	620.5
35°	684.0	656.0	632.5	620.7	607.0	600.3	596.8	591.6	587.6	585.5	585.0
37.5°	628.6	604.2	588.8	573.7	567.9	563.8	558.9	555.4	554.2	553.9	553.4
40°	592.7	572.8	559.0	546.7	544.2	538.0	534.0	530.9	530.9	531.4	530.9
42.5°	560.0	542.1	530.0	519.4	516.4	512.7	508.6	508.4	509.3	511.0	509.3
45°	510.5	497.7	489.0	483.9	478.3	474.7	474.2	475.8	476.3	476.8	478.3
47.5°	464.9	456.5	448.6	443.0	440.5	439.9	439.3	442.0	444.4	445.3	447.7
50°	438.0	428.3	421.7	418.1	416.0	415.0	416.0	419.1	421.1	423.7	425.2
52.5°	407.8	400.9	396.3	393.6	392.8	393.4	393.6	397.1	400.3	401.2	402.0
55°	366.0	360.9	359.9	355.3	357.3	356.8	359.4	361.4	364.5	367.5	368.1
57.5°	324.4	320.3	317.5	317.9	318.5	320.8	322.9	326.5	329.8	333.0	333.3
60°	296.6	294.5	293.0	293.0	294.0	297.1	299.7	303.2	305.3	307.3	308.8
62.5°	271.3	269.2	267.7	268.5	271.2	273.0	276.0	277.9	279.9	282.0	282.7
65°	231.2	230.2	231.8	232.8	233.3	235.8	239.4	240.9	243.0	244.0	247.6
67.5°	194.4	194.6	194.4	195.8	198.8	199.4	202.8	206.3	206.7	208.7	211.0
70°	169.5	170.5	171.5	172.5	175.1	176.1	178.7	180.2	182.2	183.8	185.3
72.5°	146.6	146.8	147.8	147.6	149.8	152.0	154.2	155.7	157.7	159.7	161.2
75°	112.8	112.8	113.8	114.3	116.9	119.5	118.9	120.0	122.0	124.0	125.1
77.5°	82.4	81.3	82.4	82.9	83.7	85.9	86.3	87.7	90.0	89.3	90.5
80°	62.8	61.3	62.8	63.3	63.3	65.9	65.9	66.9	68.4	66.9	68.4
82.5°	44.8	44.1	45.2	45.3	46.1	46.2	47.1	47.3	48.8	48.1	48.8
85°	22.5	22.0	22.5	22.0	22.5	23.0	23.0	22.5	22.5	23.5	22.0
87.5°	9.2	9.3	9.2	9.6	9.6	9.6	9.4	9.6	9.9	9.3	9.4
90°	11.5	13.7	15.6	17.5	19.4	21.3	22.4	23.6	24.8	26.0	26.8
92.5°	20.5	20.9	21.8	22.8	23.7	24.7	25.3	25.9	26.5	27.1	27.6
95°	37.9	34.8	36.5	38.2	39.8	41.5	42.6	43.8	45.0	46.2	46.7
97.5°	49.3	40.2	44.0	47.8	51.7	55.5	56.4	57.4	58.3	59.3	59.9
100°	58.7	44.5	48.5	52.6	56.6	60.6	62.5	64.4	66.3	68.2	69.3
102.5°	216.9	196.7	163.1	129.5	95.9	62.3	64.8	67.2	69.7	72.1	73.7
105°	351.5	322.8	258.3	193.8	129.3	64.8	67.4	70.0	72.6	75.2	77.0
107.5°	436.0	400.2	322.8	245.5	168.1	90.8	88.1	85.5	82.8	80.2	79.4
110°	490.8	459.1	390.8	322.6	254.3	186.0	162.4	138.8	115.2	91.5	80.2



TEST NUMBER: P331366

CATALOG NUMBER: SA2XXDIP-C675D1080U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	542.9	536.7	519.8	503.0	486.1	469.2	383.1	296.9	210.7	124.5	81.8
115°	627.3	632.3	638.2	644.1	650.0	655.9	546.5	437.1	327.8	218.4	155.2
117.5°	706.0	710.2	714.3	718.4	722.4	726.5	700.0	673.6	647.1	620.7	579.5
120°	758.3	762.2	766.5	770.7	775.0	779.2	782.0	784.9	787.7	790.6	776.0
122.5°	806.7	810.9	815.5	820.1	824.8	829.4	831.1	832.8	834.5	836.2	833.9
125°	876.5	880.3	884.8	889.3	893.8	898.3	899.9	901.6	903.2	904.9	906.1
127.5°	943.6	946.9	950.3	953.6	957.0	960.4	962.8	965.2	967.6	970.0	971.3
130°	986.7	989.9	992.5	995.1	997.7	1000.3	1002.9	1005.5	1008.1	1010.7	1011.9
132.5°	1027.0	1029.9	1032.5	1035.1	1037.7	1040.3	1042.5	1044.7	1047.0	1049.2	1050.2
135°	1084.5	1087.5	1089.6	1091.7	1093.9	1096.0	1098.4	1100.7	1103.1	1105.4	1106.4
137.5°	1135.9	1138.4	1140.9	1143.3	1145.7	1148.1	1150.4	1152.7	1155.0	1157.3	1158.1
140°	1169.5	1171.7	1174.3	1176.9	1179.5	1182.1	1184.2	1186.4	1188.5	1190.6	1191.1
142.5°	1199.3	1201.7	1204.6	1207.6	1210.6	1213.6	1215.5	1217.4	1219.4	1221.3	1221.7
145°	1239.6	1241.5	1245.5	1249.5	1253.6	1257.6	1259.2	1260.9	1262.5	1264.2	1264.4
147.5°	1278.9	1280.4	1284.4	1288.3	1292.3	1296.3	1297.5	1298.7	1300.0	1301.2	1301.3
150°	1303.1	1304.1	1307.9	1311.7	1315.5	1319.2	1320.7	1322.1	1323.5	1324.9	1325.0
152.5°	1325.3	1326.1	1329.7	1333.3	1336.9	1340.5	1341.9	1343.3	1344.8	1346.2	1346.1
155°	1357.5	1357.9	1360.7	1363.5	1366.4	1369.2	1370.6	1372.0	1373.5	1374.9	1374.6
157.5°	1385.0	1385.1	1387.1	1389.0	1391.0	1393.0	1394.6	1396.2	1397.8	1399.4	1399.3
160°	1401.8	1401.8	1403.2	1404.6	1406.1	1407.5	1408.9	1410.3	1411.7	1413.1	1413.0
162.5°	1415.4	1415.3	1416.5	1417.8	1419.0	1420.2	1421.8	1423.4	1425.0	1426.7	1426.4
165°	1433.7	1433.3	1434.0	1434.8	1435.5	1436.2	1437.8	1439.5	1441.1	1442.8	1442.8
167.5°	1447.3	1446.9	1447.6	1448.2	1448.9	1449.6	1451.2	1452.9	1454.5	1456.2	1455.9
170°	1455.0	1454.5	1455.0	1455.4	1455.9	1456.4	1458.0	1459.7	1461.3	1463.0	1462.7
172.5°	1460.1	1459.6	1460.1	1460.5	1461.0	1461.5	1463.1	1464.8	1466.4	1468.1	1467.9
175°	1465.7	1465.1	1465.6	1466.1	1466.5	1467.0	1468.7	1470.3	1472.0	1473.6	1473.3
177.5°	1468.1	1467.5	1467.7	1467.9	1468.1	1468.3	1469.6	1470.9	1472.2	1473.6	1473.4
180°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1



TEST NUMBER: P331366

CATALOG NUMBER: SA2XXDIP-C675D1080U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3
2.5°	1274.0	1273.1	1273.1	1269.5	1273.1	1273.1	1274.0	1278.0	1279.3	1280.1	1278.5
5°	1181.8	1180.2	1177.7	1180.2	1177.7	1180.2	1181.8	1188.9	1192.5	1196.1	1199.1
7.5°	1090.6	1084.5	1083.6	1077.5	1083.6	1084.5	1090.6	1094.0	1101.1	1109.2	1116.5
10°	1024.0	1019.9	1019.4	1009.7	1019.4	1019.9	1024.0	1032.7	1039.9	1049.6	1059.8
12.5°	973.4	963.6	965.5	959.9	965.5	963.6	973.4	973.5	981.9	987.9	1003.8
15°	885.7	885.7	883.6	875.0	883.6	885.7	885.7	899.5	902.0	911.7	925.5
17.5°	822.7	821.7	816.8	819.2	816.8	821.7	822.7	832.8	834.5	847.5	858.8
20°	785.1	782.1	775.9	775.9	775.9	782.1	785.1	790.7	797.4	805.0	814.7
22.5°	749.6	749.4	742.9	744.9	742.9	749.4	749.6	754.8	761.0	769.5	777.6
25°	708.0	704.0	700.9	702.4	700.9	704.0	708.0	708.6	715.7	721.3	726.4
27.5°	668.6	666.4	666.2	662.0	666.2	666.4	668.6	670.0	674.0	677.3	682.1
30°	645.8	640.7	641.7	639.1	641.7	640.7	645.8	646.3	648.3	650.4	656.0
32.5°	619.6	617.8	616.8	614.6	616.8	617.8	619.6	620.5	624.6	626.7	631.1
35°	584.0	584.5	582.0	583.0	582.0	584.5	584.0	585.0	585.5	587.6	591.6
37.5°	552.9	554.5	553.3	553.6	553.3	554.5	552.9	553.4	553.9	554.2	555.4
40°	532.4	532.4	532.4	534.0	532.4	532.4	532.4	530.9	531.4	530.9	530.9
42.5°	512.8	512.0	511.2	511.1	511.2	512.0	512.8	509.3	511.0	509.3	508.4
45°	479.3	480.9	481.4	478.8	481.4	480.9	479.3	478.3	476.8	476.3	475.8
47.5°	449.0	449.2	449.0	451.3	449.0	449.2	449.0	447.7	445.3	444.4	442.0
50°	427.8	426.8	427.8	426.8	427.8	426.8	427.8	425.2	423.7	421.1	419.1
52.5°	405.3	405.5	404.9	404.7	404.9	405.5	405.3	402.0	401.2	400.3	397.1
55°	370.1	371.1	370.6	370.6	370.6	371.1	370.1	368.1	367.5	364.5	361.4
57.5°	333.7	334.6	335.3	333.0	335.3	334.6	333.7	333.3	333.0	329.8	326.5
60°	308.3	310.9	310.4	309.4	310.4	310.9	308.3	308.8	307.3	305.3	303.2
62.5°	285.1	286.0	285.9	285.7	285.9	286.0	285.1	282.7	282.0	279.9	277.9
65°	249.1	250.1	248.6	250.1	248.6	250.1	249.1	247.6	244.0	243.0	240.9
67.5°	210.4	210.7	211.9	212.6	211.9	210.7	210.4	211.0	208.7	206.7	206.3
70°	186.3	185.8	187.3	188.9	187.3	185.8	186.3	185.3	183.8	182.2	180.2
72.5°	161.0	162.1	161.6	162.7	161.6	162.1	161.0	161.2	159.7	157.7	155.7
75°	124.0	125.6	125.1	126.6	125.1	125.6	124.0	125.1	124.0	122.0	120.0
77.5°	89.6	89.8	89.6	90.5	89.6	89.8	89.6	90.5	89.3	90.0	87.7
80°	68.4	67.4	66.4	68.4	66.4	67.4	68.4	68.4	66.9	68.4	66.9
82.5°	47.6	48.2	47.2	47.2	47.2	48.2	47.6	48.8	48.1	48.8	47.3
85°	22.0	21.4	20.4	20.4	20.4	21.4	22.0	22.0	23.5	22.5	22.5
87.5°	9.5	9.2	9.3	9.0	9.3	9.2	9.5	9.4	9.3	9.9	9.6
90°	27.3	27.8	28.2	28.7	28.2	27.8	27.3	26.8	26.0	24.8	23.6
92.5°	27.9	28.1	28.4	28.7	28.4	28.1	27.9	27.6	27.1	26.5	25.9
95°	46.4	46.2	45.9	45.7	45.9	46.2	46.4	46.7	46.2	45.0	43.8
97.5°	60.2	60.5	60.7	61.0	60.7	60.5	60.2	59.9	59.3	58.3	57.4
100°	69.8	70.3	70.8	71.2	70.8	70.3	69.8	69.3	68.2	66.3	64.4
102.5°	74.3	75.0	75.7	76.3	75.7	75.0	74.3	73.7	72.1	69.7	67.2
105°	78.0	78.9	79.8	80.8	79.8	78.9	78.0	77.0	75.2	72.6	70.0
107.5°	80.3	81.2	82.2	83.1	82.2	81.2	80.3	79.4	80.2	82.8	85.5
110°	81.1	82.1	83.0	84.0	83.0	82.1	81.1	80.2	91.5	115.2	138.8



TEST NUMBER: P331366

CATALOG NUMBER: SA2XXDIP-C675D1080U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	82.6	83.3	84.1	84.8	84.1	83.3	82.6	81.8	124.5	210.7	296.9
115°	138.2	121.2	104.2	87.2	104.2	121.2	138.2	155.2	218.4	327.8	437.1
117.5°	523.6	467.7	411.8	355.9	411.8	467.7	523.6	579.5	620.7	647.1	673.6
120°	744.1	712.2	680.3	648.5	680.3	712.2	744.1	776.0	790.6	787.7	784.9
122.5°	827.8	821.6	815.4	809.2	815.4	821.6	827.8	833.9	836.2	834.5	832.8
125°	906.8	907.5	908.2	908.9	908.2	907.5	906.8	906.1	904.9	903.2	901.6
127.5°	971.4	971.6	971.7	971.8	971.7	971.6	971.4	971.3	970.0	967.6	965.2
130°	1011.7	1011.4	1011.2	1011.0	1011.2	1011.4	1011.7	1011.9	1010.7	1008.1	1005.5
132.5°	1049.9	1049.7	1049.5	1049.2	1049.5	1049.7	1049.9	1050.2	1049.2	1047.0	1044.7
135°	1105.9	1105.4	1105.0	1104.5	1105.0	1105.4	1105.9	1106.4	1105.4	1103.1	1100.7
137.5°	1157.3	1156.5	1155.7	1154.9	1155.7	1156.5	1157.3	1158.1	1157.3	1155.0	1152.7
140°	1189.9	1188.7	1187.5	1186.4	1187.5	1188.7	1189.9	1191.1	1190.6	1188.5	1186.4
142.5°	1220.5	1219.3	1218.2	1217.0	1218.2	1219.3	1220.5	1221.7	1221.3	1219.4	1217.4
145°	1263.3	1262.1	1260.9	1259.7	1260.9	1262.1	1263.3	1264.4	1264.2	1262.5	1260.9
147.5°	1300.3	1299.3	1298.3	1297.3	1298.3	1299.3	1300.3	1301.3	1301.2	1300.0	1298.7
150°	1323.8	1322.7	1321.5	1320.3	1321.5	1322.7	1323.8	1325.0	1324.9	1323.5	1322.1
152.5°	1344.5	1343.0	1341.4	1339.9	1341.4	1343.0	1344.5	1346.1	1346.2	1344.8	1343.3
155°	1372.7	1370.9	1369.0	1367.1	1369.0	1370.9	1372.7	1374.6	1374.9	1373.5	1372.0
157.5°	1397.5	1395.6	1393.8	1391.9	1393.8	1395.6	1397.5	1399.3	1399.4	1397.8	1396.2
160°	1411.4	1409.7	1408.1	1406.4	1408.1	1409.7	1411.4	1413.0	1413.1	1411.7	1410.3
162.5°	1424.4	1422.4	1420.3	1418.3	1420.3	1422.4	1424.4	1426.4	1426.7	1425.0	1423.4
165°	1441.1	1439.5	1437.8	1436.2	1437.8	1439.5	1441.1	1442.8	1442.8	1441.1	1439.5
167.5°	1453.8	1451.7	1449.6	1447.4	1449.6	1451.7	1453.8	1455.9	1456.2	1454.5	1452.9
170°	1460.6	1458.5	1456.4	1454.2	1456.4	1458.5	1460.6	1462.7	1463.0	1461.3	1459.7
172.5°	1465.7	1463.6	1461.5	1459.3	1461.5	1463.6	1465.7	1467.9	1468.1	1466.4	1464.8
175°	1470.9	1468.5	1466.2	1463.8	1466.2	1468.5	1470.9	1473.3	1473.6	1472.0	1470.3
177.5°	1471.7	1470.0	1468.3	1466.6	1468.3	1470.0	1471.7	1473.4	1473.6	1472.2	1470.9
180°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1



TEST NUMBER: P331366

CATALOG NUMBER: SA2XXDIP-C675D1080U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3
2.5°	1276.4	1280.9	1287.8	1295.2	1299.7	1308.3	1310.7	1314.8	1318.5	1327.1	1336.0
5°	1202.7	1209.8	1226.7	1235.9	1248.6	1263.4	1273.1	1283.4	1294.6	1314.0	1331.8
7.5°	1123.7	1135.6	1156.5	1173.7	1191.9	1213.1	1228.4	1248.6	1265.4	1292.7	1318.9
10°	1071.0	1087.8	1106.7	1127.1	1152.7	1175.1	1196.6	1222.1	1242.5	1275.2	1305.8
12.5°	1023.6	1026.2	1053.2	1075.7	1110.6	1138.4	1163.1	1196.0	1216.0	1254.8	1287.0
15°	940.8	956.1	980.6	998.5	1039.9	1075.1	1109.8	1144.0	1167.0	1214.9	1257.3
17.5°	871.1	885.2	910.3	939.6	969.3	1004.3	1049.2	1085.3	1116.5	1171.4	1221.5
20°	827.0	844.3	869.9	900.0	926.0	964.3	1003.1	1044.4	1078.1	1139.9	1198.6
22.5°	789.4	803.1	823.7	853.4	881.9	916.9	959.4	1004.4	1039.8	1106.4	1165.9
25°	736.6	747.9	761.1	785.6	817.8	856.1	889.3	938.8	990.3	1052.6	1124.6
27.5°	689.0	697.0	708.8	730.3	755.2	791.0	827.9	874.9	926.7	994.3	1070.3
30°	660.1	665.2	676.9	694.8	719.3	747.3	784.6	829.5	882.6	951.0	1026.6
32.5°	634.7	639.4	647.1	664.1	685.4	709.4	743.0	787.9	838.5	905.7	989.4
35°	596.8	600.3	607.0	620.7	632.5	656.0	684.0	724.9	772.4	836.7	923.5
37.5°	558.9	563.8	567.9	573.7	588.8	604.2	628.6	663.1	709.7	774.6	857.3
40°	534.0	538.0	544.2	546.7	559.0	572.8	592.7	624.3	671.3	730.5	811.2
42.5°	508.6	512.7	516.4	519.4	530.0	542.1	560.0	587.2	628.8	686.4	766.2
45°	474.2	474.7	478.3	483.9	489.0	497.7	510.5	534.0	566.1	620.2	692.7
47.5°	439.3	439.9	440.5	443.0	448.6	456.5	464.9	484.0	512.8	556.0	626.6
50°	416.0	415.0	416.0	418.1	421.7	428.3	438.0	451.8	475.3	515.6	580.4
52.5°	393.6	393.4	392.8	393.6	396.3	400.9	407.8	419.5	440.5	477.6	534.7
55°	359.4	356.8	357.3	355.3	359.9	360.9	366.0	375.7	394.1	419.6	473.2
57.5°	322.9	320.8	318.5	317.9	317.5	320.3	324.4	332.0	346.1	368.5	412.0
60°	299.7	297.1	294.0	293.0	293.0	294.5	296.6	302.2	315.5	335.4	371.1
62.5°	276.0	273.0	271.2	268.5	267.7	269.2	271.3	275.3	284.8	303.5	334.4
65°	239.4	235.8	233.3	232.8	231.8	230.2	231.2	235.3	243.0	257.8	282.3
67.5°	202.8	199.4	198.8	195.8	194.4	194.6	194.4	197.9	202.5	215.2	233.5
70°	178.7	176.1	175.1	172.5	171.5	170.5	169.5	172.5	177.1	187.9	203.7
72.5°	154.2	152.0	149.8	147.6	147.8	146.8	146.6	148.4	152.2	162.1	174.3
75°	118.9	119.5	116.9	114.3	113.8	112.8	112.8	114.3	115.9	123.5	133.2
77.5°	86.3	85.9	83.7	82.9	82.4	81.3	82.4	83.4	84.2	89.3	96.5
80°	65.9	65.9	63.3	63.3	62.8	61.3	62.8	61.8	63.8	68.9	74.0
82.5°	47.1	46.2	46.1	45.3	45.2	44.1	44.8	45.8	46.7	50.1	53.2
85°	23.0	23.0	22.5	22.0	22.5	22.0	22.5	23.0	23.5	25.0	27.6
87.5°	9.4	9.6	9.6	9.6	9.2	9.3	9.2	9.1	9.4	9.3	9.2
90°	22.4	21.3	19.4	17.5	15.6	13.7	11.5	8.9	6.3	3.7	1.1
92.5°	25.3	24.7	23.7	22.8	21.8	20.9	20.5	20.8	21.0	21.2	21.5
95°	42.6	41.5	39.8	38.2	36.5	34.8	37.9	45.7	53.5	61.3	69.1
97.5°	56.4	55.5	51.7	47.8	44.0	40.2	49.3	71.2	93.2	115.2	137.1
100°	62.5	60.6	56.6	52.6	48.5	44.5	58.7	91.1	123.4	155.8	188.2
102.5°	64.8	62.3	95.9	129.5	163.1	196.7	216.9	223.7	230.6	237.4	244.3
105°	67.4	64.8	129.3	193.8	258.3	322.8	351.5	344.4	337.3	330.3	323.2
107.5°	88.1	90.8	168.1	245.5	322.8	400.2	436.0	430.2	424.5	418.8	413.1
110°	162.4	186.0	254.3	322.6	390.8	459.1	490.8	485.8	480.9	475.9	470.9



TEST NUMBER: P331366

CATALOG NUMBER: SA2XXDIP-C675D1080U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	383.1	469.2	486.1	503.0	519.8	536.7	542.9	538.5	534.1	529.8	525.4
115°	546.5	655.9	650.0	644.1	638.2	632.3	627.3	623.3	619.3	615.3	611.3
117.5°	700.0	726.5	722.4	718.4	714.3	710.2	706.0	701.5	697.0	692.5	688.0
120°	782.0	779.2	775.0	770.7	766.5	762.2	758.3	754.8	751.2	747.7	744.1
122.5°	831.1	829.4	824.8	820.1	815.5	810.9	806.7	803.0	799.2	795.5	791.8
125°	899.9	898.3	893.8	889.3	884.8	880.3	876.5	873.5	870.4	867.3	864.3
127.5°	962.8	960.4	957.0	953.6	950.3	946.9	943.6	940.2	936.8	933.4	930.0
130°	1002.9	1000.3	997.7	995.1	992.5	989.9	986.7	983.0	979.2	975.4	971.6
132.5°	1042.5	1040.3	1037.7	1035.1	1032.5	1029.9	1027.0	1023.8	1020.6	1017.4	1014.1
135°	1098.4	1096.0	1093.9	1091.7	1089.6	1087.5	1084.5	1080.8	1077.0	1073.2	1069.4
137.5°	1150.4	1148.1	1145.7	1143.3	1140.9	1138.4	1135.9	1133.3	1130.6	1128.0	1125.3
140°	1184.2	1182.1	1179.5	1176.9	1174.3	1171.7	1169.5	1167.6	1165.7	1163.8	1161.9
142.5°	1215.5	1213.6	1210.6	1207.6	1204.6	1201.7	1199.3	1197.6	1195.9	1194.2	1192.5
145°	1259.2	1257.6	1253.6	1249.5	1245.5	1241.5	1239.6	1239.9	1240.1	1240.3	1240.6
147.5°	1297.5	1296.3	1292.3	1288.3	1284.4	1280.4	1278.9	1279.8	1280.7	1281.6	1282.5
150°	1320.7	1319.2	1315.5	1311.7	1307.9	1304.1	1303.1	1304.7	1306.4	1308.0	1309.7
152.5°	1341.9	1340.5	1336.9	1333.3	1329.7	1326.1	1325.3	1327.1	1328.9	1330.8	1332.6
155°	1370.6	1369.2	1366.4	1363.5	1360.7	1357.9	1357.5	1359.6	1361.8	1363.9	1366.0
157.5°	1394.6	1393.0	1391.0	1389.0	1387.1	1385.1	1385.0	1386.8	1388.6	1390.4	1392.2
160°	1408.9	1407.5	1406.1	1404.6	1403.2	1401.8	1401.8	1403.2	1404.6	1406.1	1407.5
162.5°	1421.8	1420.2	1419.0	1417.8	1416.5	1415.3	1415.4	1416.8	1418.2	1419.7	1421.1
165°	1437.8	1436.2	1435.5	1434.8	1434.0	1433.3	1433.7	1435.1	1436.5	1437.9	1439.4
167.5°	1451.2	1449.6	1448.9	1448.2	1447.6	1446.9	1447.3	1448.7	1450.1	1451.6	1453.0
170°	1458.0	1456.4	1455.9	1455.4	1455.0	1454.5	1455.0	1456.4	1457.8	1459.2	1460.6
172.5°	1463.1	1461.5	1461.0	1460.5	1460.1	1459.6	1460.1	1461.5	1462.9	1464.3	1465.7
175°	1468.7	1467.0	1466.5	1466.1	1465.6	1465.1	1465.7	1467.4	1469.0	1470.7	1472.3
177.5°	1469.6	1468.3	1468.1	1467.9	1467.7	1467.5	1468.1	1469.4	1470.7	1472.1	1473.4
180°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1



TEST NUMBER: P331366

CATALOG NUMBER: SA2XXDIP-C675D1080U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3
2.5°	1335.2	1337.3	1343.8	1350.3	1357.7	1359.7	1363.0	1360.1	1359.3	1367.1	1372.8
5°	1339.0	1348.2	1366.1	1382.4	1396.2	1405.9	1416.1	1420.2	1427.8	1438.5	1451.8
7.5°	1334.7	1352.6	1380.7	1404.4	1430.4	1449.1	1463.7	1476.1	1491.2	1511.5	1533.7
10°	1329.8	1353.8	1388.0	1417.1	1448.7	1472.7	1492.7	1512.0	1534.5	1562.6	1591.7
12.5°	1320.8	1349.3	1392.1	1426.5	1467.1	1490.7	1517.6	1559.4	1583.5	1622.6	1663.6
15°	1302.8	1334.4	1394.1	1436.5	1482.4	1527.4	1576.9	1616.7	1656.5	1679.5	1737.2
17.5°	1275.9	1322.4	1388.5	1437.9	1496.3	1567.1	1622.7	1667.8	1713.8	1751.1	1780.0
20°	1254.3	1304.8	1380.3	1439.6	1509.0	1585.0	1648.9	1694.8	1734.6	1765.8	1783.6
22.5°	1226.9	1290.5	1364.0	1433.4	1522.1	1597.3	1664.4	1700.5	1733.8	1749.0	1755.9
25°	1183.8	1260.4	1343.6	1428.3	1528.4	1608.0	1669.3	1691.2	1700.9	1686.1	1661.6
27.5°	1137.4	1222.7	1320.0	1418.7	1524.5	1601.1	1645.0	1641.5	1625.1	1577.2	1538.9
30°	1102.6	1196.6	1301.2	1408.9	1515.1	1589.6	1615.2	1589.6	1552.4	1498.8	1444.2
32.5°	1066.3	1163.5	1281.2	1395.0	1498.0	1563.5	1569.0	1525.1	1467.4	1406.5	1338.4
35°	1011.3	1116.4	1243.5	1364.0	1461.5	1502.9	1478.4	1400.8	1332.4	1249.2	1156.2
37.5°	949.1	1065.2	1192.7	1318.6	1406.9	1417.7	1356.9	1275.2	1178.7	1080.9	971.6
40°	902.5	1025.6	1156.8	1283.9	1362.0	1350.7	1273.1	1183.3	1068.4	949.0	847.4
42.5°	860.9	983.9	1117.5	1242.2	1304.8	1274.0	1183.3	1073.0	949.6	837.1	744.1
45°	788.7	915.3	1052.1	1172.6	1208.3	1152.7	1032.7	910.2	788.7	694.8	621.3
47.5°	718.7	843.8	979.3	1085.2	1097.8	1023.0	891.9	765.8	661.4	584.9	533.0
50°	667.2	792.8	927.0	1021.5	1017.4	927.0	792.3	672.3	585.0	523.2	488.5
52.5°	621.1	739.7	868.6	954.5	932.9	834.3	705.7	599.2	527.4	479.1	447.7
55°	549.3	659.0	781.5	850.5	810.6	701.4	592.7	506.9	453.8	417.6	393.1
57.5°	478.0	580.9	685.8	728.3	684.3	583.4	492.7	430.5	390.6	363.8	347.8
60°	433.9	523.8	617.2	653.9	601.3	511.5	440.0	384.4	352.2	330.3	316.0
62.5°	389.8	470.3	558.4	578.4	530.3	454.3	391.0	344.8	318.3	298.8	285.4
65°	329.8	395.6	462.5	475.8	431.4	372.7	322.6	292.5	269.0	254.7	244.0
67.5°	270.5	323.3	370.7	381.4	342.5	301.8	265.7	239.4	223.5	211.6	202.6
70°	235.3	277.2	316.0	324.7	293.5	257.3	229.7	208.8	194.5	184.3	175.6
72.5°	198.2	233.1	265.3	271.2	245.7	218.1	195.4	179.0	166.3	159.8	151.5
75°	151.6	172.0	197.0	198.6	181.7	164.9	147.5	136.8	130.2	122.0	117.9
77.5°	107.0	123.0	137.3	140.1	130.1	118.6	108.9	100.5	94.8	91.1	87.3
80°	81.7	94.4	100.6	104.1	97.0	88.8	83.2	77.6	74.0	71.5	68.9
82.5°	58.4	66.3	72.0	74.7	70.9	66.0	60.3	57.2	54.4	52.3	51.4
85°	29.6	33.2	36.8	37.8	36.8	34.7	31.6	31.6	30.1	29.6	29.6
87.5°	10.9	13.1	13.6	15.4	15.0	15.4	15.7	15.7	15.7	15.5	15.3
90°	3.7	6.3	8.9	11.5	13.7	15.6	17.5	19.4	21.3	22.4	23.6
92.5°	21.2	21.0	20.8	20.5	20.9	21.8	22.8	23.7	24.7	25.3	25.9
95°	61.3	53.5	45.7	37.9	34.8	36.5	38.2	39.8	41.5	42.6	43.8
97.5°	115.2	93.2	71.2	49.3	40.2	44.0	47.8	51.7	55.5	56.4	57.4
100°	155.8	123.4	91.1	58.7	44.5	48.5	52.6	56.6	60.6	62.5	64.4
102.5°	237.4	230.6	223.7	216.9	196.7	163.1	129.5	95.9	62.3	64.8	67.2
105°	330.3	337.3	344.4	351.5	322.8	258.3	193.8	129.3	64.8	67.4	70.0
107.5°	418.8	424.5	430.2	436.0	400.2	322.8	245.5	168.1	90.8	88.1	85.5
110°	475.9	480.9	485.8	490.8	459.1	390.8	322.6	254.3	186.0	162.4	138.8



TEST NUMBER: P331366

CATALOG NUMBER: SA2XXDIP-C675D1080U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	529.8	534.1	538.5	542.9	536.7	519.8	503.0	486.1	469.2	383.1	296.9
115°	615.3	619.3	623.3	627.3	632.3	638.2	644.1	650.0	655.9	546.5	437.1
117.5°	692.5	697.0	701.5	706.0	710.2	714.3	718.4	722.4	726.5	700.0	673.6
120°	747.7	751.2	754.8	758.3	762.2	766.5	770.7	775.0	779.2	782.0	784.9
122.5°	795.5	799.2	803.0	806.7	810.9	815.5	820.1	824.8	829.4	831.1	832.8
125°	867.3	870.4	873.5	876.5	880.3	884.8	889.3	893.8	898.3	899.9	901.6
127.5°	933.4	936.8	940.2	943.6	946.9	950.3	953.6	957.0	960.4	962.8	965.2
130°	975.4	979.2	983.0	986.7	989.9	992.5	995.1	997.7	1000.3	1002.9	1005.5
132.5°	1017.4	1020.6	1023.8	1027.0	1029.9	1032.5	1035.1	1037.7	1040.3	1042.5	1044.7
135°	1073.2	1077.0	1080.8	1084.5	1087.5	1089.6	1091.7	1093.9	1096.0	1098.4	1100.7
137.5°	1128.0	1130.6	1133.3	1135.9	1138.4	1140.9	1143.3	1145.7	1148.1	1150.4	1152.7
140°	1163.8	1165.7	1167.6	1169.5	1171.7	1174.3	1176.9	1179.5	1182.1	1184.2	1186.4
142.5°	1194.2	1195.9	1197.6	1199.3	1201.7	1204.6	1207.6	1210.6	1213.6	1215.5	1217.4
145°	1240.3	1240.1	1239.9	1239.6	1241.5	1245.5	1249.5	1253.6	1257.6	1259.2	1260.9
147.5°	1281.6	1280.7	1279.8	1278.9	1280.4	1284.4	1288.3	1292.3	1296.3	1297.5	1298.7
150°	1308.0	1306.4	1304.7	1303.1	1304.1	1307.9	1311.7	1315.5	1319.2	1320.7	1322.1
152.5°	1330.8	1328.9	1327.1	1325.3	1326.1	1329.7	1333.3	1336.9	1340.5	1341.9	1343.3
155°	1363.9	1361.8	1359.6	1357.5	1357.9	1360.7	1363.5	1366.4	1369.2	1370.6	1372.0
157.5°	1390.4	1388.6	1386.8	1385.0	1385.1	1387.1	1389.0	1391.0	1393.0	1394.6	1396.2
160°	1406.1	1404.6	1403.2	1401.8	1401.8	1403.2	1404.6	1406.1	1407.5	1408.9	1410.3
162.5°	1419.7	1418.2	1416.8	1415.4	1415.3	1416.5	1417.8	1419.0	1420.2	1421.8	1423.4
165°	1437.9	1436.5	1435.1	1433.7	1433.3	1434.0	1434.8	1435.5	1436.2	1437.8	1439.5
167.5°	1451.6	1450.1	1448.7	1447.3	1446.9	1447.6	1448.2	1448.9	1449.6	1451.2	1452.9
170°	1459.2	1457.8	1456.4	1455.0	1454.5	1455.0	1455.4	1455.9	1456.4	1458.0	1459.7
172.5°	1464.3	1462.9	1461.5	1460.1	1459.6	1460.1	1460.5	1461.0	1461.5	1463.1	1464.8
175°	1470.7	1469.0	1467.4	1465.7	1465.1	1465.6	1466.1	1466.5	1467.0	1468.7	1470.3
177.5°	1472.1	1470.7	1469.4	1468.1	1467.5	1467.7	1467.9	1468.1	1468.3	1469.6	1470.9
180°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1



TEST NUMBER: P331366

CATALOG NUMBER: SA2XXDIP-C675D1080U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3
2.5°	1377.7	1383.4	1383.4	1384.2	1390.8	1389.9	1389.5
5°	1466.1	1474.8	1475.8	1485.0	1491.1	1489.1	1483.5
7.5°	1549.5	1565.7	1577.9	1584.7	1592.8	1597.8	1595.6
10°	1615.7	1639.2	1653.5	1663.2	1674.9	1683.6	1680.5
12.5°	1675.7	1703.7	1723.3	1739.9	1741.5	1752.6	1745.0
15°	1769.3	1798.9	1802.0	1814.3	1824.0	1822.9	1823.4
17.5°	1800.3	1809.8	1811.7	1812.0	1812.1	1808.5	1800.8
20°	1789.2	1785.7	1777.0	1770.4	1758.6	1757.1	1746.9
22.5°	1737.0	1725.6	1703.9	1689.5	1671.2	1666.4	1663.6
25°	1634.1	1609.0	1574.3	1541.1	1532.0	1514.1	1519.2
27.5°	1492.9	1453.9	1416.3	1389.3	1364.9	1338.2	1345.8
30°	1393.6	1349.7	1296.6	1255.8	1229.8	1204.2	1199.6
32.5°	1275.2	1210.9	1151.6	1115.7	1075.8	1059.7	1042.0
35°	1071.0	1008.2	949.5	899.0	869.9	847.4	827.0
37.5°	887.3	815.0	767.7	726.7	705.7	692.8	696.1
40°	773.4	710.1	675.4	644.2	624.8	615.6	617.7
42.5°	681.1	633.7	605.1	583.8	570.1	565.0	563.8
45°	576.3	549.8	526.3	514.1	507.4	501.8	498.2
47.5°	504.9	483.2	470.0	462.7	456.9	451.2	451.1
50°	462.0	447.7	438.5	430.8	426.3	422.2	425.7
52.5°	429.3	416.2	407.1	400.2	398.5	394.8	394.7
55°	380.8	370.6	364.0	357.8	354.8	352.7	350.2
57.5°	336.7	327.0	320.9	317.0	311.2	309.1	308.3
60°	305.3	297.6	291.5	286.4	283.8	279.7	279.7
62.5°	276.3	268.6	262.9	259.0	254.8	253.2	253.6
65°	234.3	228.2	222.6	218.5	217.5	214.4	215.4
67.5°	195.7	191.6	185.7	183.5	181.5	179.9	178.7
70°	170.0	165.9	162.8	159.8	158.2	158.2	158.2
72.5°	148.3	143.4	141.6	137.7	138.6	137.0	135.4
75°	114.9	111.8	110.3	108.7	106.2	106.2	106.2
77.5°	84.5	83.6	81.8	80.1	79.5	79.0	79.2
80°	65.3	64.8	63.8	63.8	62.8	62.3	61.3
82.5°	50.2	48.9	48.3	47.9	47.7	47.6	47.4
85°	28.6	27.6	27.6	28.1	27.1	27.1	27.6
87.5°	16.0	16.2	16.0	16.1	16.6	16.3	16.4
90°	24.8	26.0	26.8	27.3	27.8	28.2	28.7
92.5°	26.5	27.1	27.6	27.9	28.1	28.4	28.7
95°	45.0	46.2	46.7	46.4	46.2	45.9	45.7
97.5°	58.3	59.3	59.9	60.2	60.5	60.7	61.0
100°	66.3	68.2	69.3	69.8	70.3	70.8	71.2
102.5°	69.7	72.1	73.7	74.3	75.0	75.7	76.3
105°	72.6	75.2	77.0	78.0	78.9	79.8	80.8
107.5°	82.8	80.2	79.4	80.3	81.2	82.2	83.1
110°	115.2	91.5	80.2	81.1	82.1	83.0	84.0



TEST NUMBER: P331366

CATALOG NUMBER: SA2XXDIP-C675D1080U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	210.7	124.5	81.8	82.6	83.3	84.1	84.8
115°	327.8	218.4	155.2	138.2	121.2	104.2	87.2
117.5°	647.1	620.7	579.5	523.6	467.7	411.8	355.9
120°	787.7	790.6	776.0	744.1	712.2	680.3	648.5
122.5°	834.5	836.2	833.9	827.8	821.6	815.4	809.2
125°	903.2	904.9	906.1	906.8	907.5	908.2	908.9
127.5°	967.6	970.0	971.3	971.4	971.6	971.7	971.8
130°	1008.1	1010.7	1011.9	1011.7	1011.4	1011.2	1011.0
132.5°	1047.0	1049.2	1050.2	1049.9	1049.7	1049.5	1049.2
135°	1103.1	1105.4	1106.4	1105.9	1105.4	1105.0	1104.5
137.5°	1155.0	1157.3	1158.1	1157.3	1156.5	1155.7	1154.9
140°	1188.5	1190.6	1191.1	1189.9	1188.7	1187.5	1186.4
142.5°	1219.4	1221.3	1221.7	1220.5	1219.3	1218.2	1217.0
145°	1262.5	1264.2	1264.4	1263.3	1262.1	1260.9	1259.7
147.5°	1300.0	1301.2	1301.3	1300.3	1299.3	1298.3	1297.3
150°	1323.5	1324.9	1325.0	1323.8	1322.7	1321.5	1320.3
152.5°	1344.8	1346.2	1346.1	1344.5	1343.0	1341.4	1339.9
155°	1373.5	1374.9	1374.6	1372.7	1370.9	1369.0	1367.1
157.5°	1397.8	1399.4	1399.3	1397.5	1395.6	1393.8	1391.9
160°	1411.7	1413.1	1413.0	1411.4	1409.7	1408.1	1406.4
162.5°	1425.0	1426.7	1426.4	1424.4	1422.4	1420.3	1418.3
165°	1441.1	1442.8	1442.8	1441.1	1439.5	1437.8	1436.2
167.5°	1454.5	1456.2	1455.9	1453.8	1451.7	1449.6	1447.4
170°	1461.3	1463.0	1462.7	1460.6	1458.5	1456.4	1454.2
172.5°	1466.4	1468.1	1467.9	1465.7	1463.6	1461.5	1459.3
175°	1472.0	1473.6	1473.3	1470.9	1468.5	1466.2	1463.8
177.5°	1472.2	1473.6	1473.4	1471.7	1470.0	1468.3	1466.6
180°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1

(END OF REPORT)