

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331330

Luminaire Tested: **SA2XXDIP-C675D330U835-4F0-1E-UDD-A**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331330
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C675D330U835-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 330 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4241.0 lumens
Efficiency: N/A
Efficacy: 121.2 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 35
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331330
CATALOG NUMBER: SA2XXDIP-C675D330U835-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331330

CATALOG NUMBER: SA2XXDIP-C675D330U835-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	112	112	112	112	106	106	106	106	94	94	94	83	83	83	74	74	74	69				
1	103	99	95	91	97	93	90	87	83	81	79	74	73	71	66	65	64	60				
2	94	87	81	76	89	82	77	73	74	70	66	66	63	60	59	57	55	51				
3	86	77	70	64	81	73	67	61	66	61	57	59	55	52	53	50	47	44				
4	79	69	61	55	75	65	58	53	59	53	49	53	49	45	48	44	41	38				
5	73	62	54	48	69	59	51	46	53	47	43	48	43	40	43	40	36	34				
6	68	56	48	42	64	53	46	40	48	42	38	44	39	35	40	36	32	30				
7	63	51	43	37	59	48	41	36	44	38	34	40	35	31	36	32	29	27				
8	59	46	39	33	55	44	37	32	41	35	30	37	32	28	34	29	26	24				
9	55	43	35	30	52	41	34	29	37	31	27	34	29	26	31	27	24	22				
10	51	39	32	27	49	38	31	26	35	29	25	32	27	23	29	25	22	20				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	21447	21447	21447	21447
5°	24044	21585	19128	21585
10°	27552	21408	16554	21408
15°	30479	21016	14626	21016
20°	30015	20594	13332	20594
25°	27064	20035	12513	20035
30°	22365	19140	11915	19140
35°	16301	18203	11491	18203
40°	13019	17098	11255	17098
45°	11376	15817	10933	15817
50°	10693	14579	10721	14579
55°	9858	13320	10432	13320
60°	9032	11983	9991	11983
65°	8229	10785	9555	10785
70°	7468	9616	8917	9616
75°	6625	8309	7898	8309
80°	5700	6881	6360	6881
85°	5113	5113	3779	5113



TEST NUMBER: P331330

CATALOG NUMBER: SA2XXDIP-C675D330U835-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.5	3.0
10°-20°	367.8	8.7
20°-30°	533.7	12.6
30°-40°	563.2	13.3
40°-50°	498.7	11.8
50°-60°	398.0	9.4
60°-70°	270.5	6.4
70°-80°	138.7	3.3
80°-90°	34.5	0.8
90°-100°	14.9	0.4
100°-110°	54.7	1.3
110°-120°	146.1	3.4
120°-130°	241.2	5.7
130°-140°	256.5	6.0
140°-150°	238.4	5.6
150°-160°	191.7	4.5
160°-170°	123.5	2.9
170°-180°	42.5	1.0
0°-30°	1028.0	24.2
0°-40°	1591.2	37.5
0°-60°	2487.8	58.7
0°-90°	2931.5	69.1
90°-120°	215.7	5.1
90°-150°	951.8	22.4
90°-180°	1309.0	30.9
0°-180°	4241.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1328	1328	1328	1328	1328	
5°	1484	1332	1180	1332	1484	148
15°	1823	1257	875	1257	1823	503
25°	1519	1125	702	1125	1519	687
35°	827	924	583	924	827	538
45°	498	693	479	693	498	392
55°	350	473	371	473	350	314
65°	215	282	250	282	215	214
75°	106	133	127	133	106	113
85°	28	28	20	28	28	30
90°	9	0	9	0	9	5
95°	14	21	14	21	14	13
105°	25	98	25	98	25	26
115°	26	186	26	186	26	66
125°	276	263	276	263	276	239
135°	336	325	336	325	336	259
145°	383	377	383	377	383	240
155°	416	416	416	416	416	192
165°	437	438	437	438	437	123
175°	445	448	445	448	445	42
180°	447	447	447	447	447	



TEST NUMBER: P331330

CATALOG NUMBER: SA2XXDIP-C675D330U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3
2.5°	1389.5	1389.9	1390.8	1384.2	1383.4	1383.4	1377.7	1372.8	1367.1	1359.3	1360.1
5°	1483.5	1489.1	1491.1	1485.0	1475.8	1474.8	1466.1	1451.8	1438.5	1427.8	1420.2
7.5°	1595.6	1597.8	1592.8	1584.7	1577.9	1565.7	1549.5	1533.7	1511.5	1491.2	1476.1
10°	1680.5	1683.6	1674.9	1663.2	1653.5	1639.2	1615.7	1591.7	1562.6	1534.5	1512.0
12.5°	1745.0	1752.6	1741.5	1739.9	1723.3	1703.7	1675.7	1663.6	1622.6	1583.5	1559.4
15°	1823.4	1822.9	1824.0	1814.3	1802.0	1798.9	1769.3	1737.2	1679.5	1656.5	1616.7
17.5°	1800.8	1808.5	1812.1	1812.0	1811.7	1809.8	1800.3	1780.0	1751.1	1713.8	1667.8
20°	1746.9	1757.1	1758.6	1770.4	1777.0	1785.7	1789.2	1783.6	1765.8	1734.6	1694.8
22.5°	1663.6	1666.4	1671.2	1689.5	1703.9	1725.6	1737.0	1755.9	1749.0	1733.8	1700.5
25°	1519.2	1514.1	1532.0	1541.1	1574.3	1609.0	1634.1	1661.6	1686.1	1700.9	1691.2
27.5°	1345.8	1338.2	1364.9	1389.3	1416.3	1453.9	1492.9	1538.9	1577.2	1625.1	1641.5
30°	1199.6	1204.2	1229.8	1255.8	1296.6	1349.7	1393.6	1444.2	1498.8	1552.4	1589.6
32.5°	1042.0	1059.7	1075.8	1115.7	1151.6	1210.9	1275.2	1338.4	1406.5	1467.4	1525.1
35°	827.0	847.4	869.9	899.0	949.5	1008.2	1071.0	1156.2	1249.2	1332.4	1400.8
37.5°	696.1	692.8	705.7	726.7	767.7	815.0	887.3	971.6	1080.9	1178.7	1275.2
40°	617.7	615.6	624.8	644.2	675.4	710.1	773.4	847.4	949.0	1068.4	1183.3
42.5°	563.8	565.0	570.1	583.8	605.1	633.7	681.1	744.1	837.1	949.6	1073.0
45°	498.2	501.8	507.4	514.1	526.3	549.8	576.3	621.3	694.8	788.7	910.2
47.5°	451.1	451.2	456.9	462.7	470.0	483.2	504.9	533.0	584.9	661.4	765.8
50°	425.7	422.2	426.3	430.8	438.5	447.7	462.0	488.5	523.2	585.0	672.3
52.5°	394.7	394.8	398.5	400.2	407.1	416.2	429.3	447.7	479.1	527.4	599.2
55°	350.2	352.7	354.8	357.8	364.0	370.6	380.8	393.1	417.6	453.8	506.9
57.5°	308.3	309.1	311.2	317.0	320.9	327.0	336.7	347.8	363.8	390.6	430.5
60°	279.7	279.7	283.8	286.4	291.5	297.6	305.3	316.0	330.3	352.2	384.4
62.5°	253.6	253.2	254.8	259.0	262.9	268.6	276.3	285.4	298.8	318.3	344.8
65°	215.4	214.4	217.5	218.5	222.6	228.2	234.3	244.0	254.7	269.0	292.5
67.5°	178.7	179.9	181.5	183.5	185.7	191.6	195.7	202.6	211.6	223.5	239.4
70°	158.2	158.2	158.2	159.8	162.8	165.9	170.0	175.6	184.3	194.5	208.8
72.5°	135.4	137.0	138.6	137.7	141.6	143.4	148.3	151.5	159.8	166.3	179.0
75°	106.2	106.2	106.2	108.7	110.3	111.8	114.9	117.9	122.0	130.2	136.8
77.5°	79.2	79.0	79.5	80.1	81.8	83.6	84.5	87.3	91.1	94.8	100.5
80°	61.3	62.3	62.8	63.8	63.8	64.8	65.3	68.9	71.5	74.0	77.6
82.5°	47.4	47.6	47.7	47.9	48.3	48.9	50.2	51.4	52.3	54.4	57.2
85°	27.6	27.1	27.1	28.1	27.6	27.6	28.6	29.6	29.6	30.1	31.6
87.5°	12.4	12.3	12.7	12.3	12.2	12.6	12.5	12.1	12.4	12.7	13.0
90°	8.7	8.6	8.4	8.3	8.2	7.9	7.5	7.2	6.8	6.5	5.9
92.5°	8.7	8.6	8.6	8.5	8.4	8.2	8.1	7.9	7.7	7.5	7.2
95°	13.9	14.0	14.0	14.1	14.2	14.0	13.7	13.3	13.0	12.6	12.1
97.5°	18.6	18.5	18.4	18.3	18.2	18.0	17.7	17.5	17.2	16.9	15.7
100°	21.7	21.5	21.4	21.2	21.1	20.7	20.2	19.6	19.0	18.4	17.2
102.5°	23.2	23.0	22.8	22.6	22.4	21.9	21.2	20.4	19.7	18.9	29.2
105°	24.6	24.3	24.0	23.7	23.4	22.9	22.1	21.3	20.5	19.7	39.3
107.5°	25.3	25.0	24.7	24.4	24.1	24.4	25.2	26.0	26.8	27.6	51.1
110°	25.5	25.3	25.0	24.7	24.4	27.8	35.0	42.2	49.4	56.6	77.3



TEST NUMBER: P331330

CATALOG NUMBER: SA2XXDIP-C675D330U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	25.8	25.6	25.3	25.1	24.9	37.9	64.1	90.3	116.5	142.7	147.8
115°	26.5	31.7	36.9	42.0	47.2	66.4	99.7	133.0	166.2	199.5	197.7
117.5°	108.3	125.3	142.3	159.3	176.3	188.8	196.8	204.9	212.9	221.0	219.7
120°	197.2	206.9	216.6	226.3	236.0	240.4	239.6	238.7	237.9	237.0	235.7
122.5°	246.1	248.0	249.9	251.8	253.6	254.3	253.8	253.3	252.8	252.3	250.9
125°	276.4	276.2	276.0	275.8	275.6	275.2	274.7	274.2	273.7	273.2	271.8
127.5°	295.6	295.5	295.5	295.5	295.4	295.0	294.3	293.6	292.8	292.1	291.1
130°	307.5	307.6	307.6	307.7	307.8	307.4	306.6	305.8	305.0	304.3	303.5
132.5°	319.1	319.2	319.3	319.3	319.4	319.1	318.4	317.8	317.1	316.4	315.6
135°	335.9	336.1	336.2	336.4	336.5	336.2	335.5	334.8	334.1	333.4	332.7
137.5°	351.3	351.5	351.8	352.0	352.2	352.0	351.3	350.6	349.9	349.2	348.5
140°	360.8	361.2	361.6	361.9	362.3	362.1	361.5	360.8	360.2	359.5	358.8
142.5°	370.1	370.5	370.9	371.2	371.6	371.5	370.9	370.3	369.7	369.1	368.2
145°	383.1	383.5	383.9	384.2	384.6	384.5	384.0	383.5	383.0	382.5	381.3
147.5°	394.6	394.9	395.2	395.5	395.8	395.8	395.4	395.0	394.6	394.3	393.1
150°	401.6	401.9	402.3	402.7	403.0	403.0	402.5	402.1	401.7	401.3	400.1
152.5°	407.5	408.0	408.5	408.9	409.4	409.4	409.0	408.6	408.1	407.7	406.6
155°	415.8	416.4	417.0	417.5	418.1	418.2	417.7	417.3	416.9	416.4	415.6
157.5°	423.4	423.9	424.5	425.0	425.6	425.6	425.2	424.7	424.2	423.7	423.1
160°	427.8	428.3	428.8	429.3	429.8	429.8	429.4	429.0	428.5	428.1	427.7
162.5°	431.4	432.0	432.6	433.2	433.9	433.9	433.4	432.9	432.5	432.0	431.6
165°	436.8	437.3	437.8	438.3	438.8	438.8	438.3	437.8	437.3	436.8	436.6
167.5°	440.2	440.9	441.5	442.2	442.8	442.9	442.4	441.9	441.4	440.9	440.7
170°	442.3	443.0	443.6	444.3	444.9	445.0	444.5	444.0	443.5	443.0	442.8
172.5°	443.9	444.5	445.2	445.8	446.5	446.5	446.0	445.5	445.0	444.5	444.4
175°	445.2	445.9	446.7	447.4	448.1	448.2	447.7	447.2	446.7	446.2	446.1
177.5°	446.1	446.6	447.1	447.6	448.1	448.2	447.8	447.4	447.0	446.6	446.5
180°	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8



TEST NUMBER: P331330

CATALOG NUMBER: SA2XXDIP-C675D330U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3
2.5°	1363.0	1359.7	1357.7	1350.3	1343.8	1337.3	1335.2	1336.0	1327.1	1318.5	1314.8
5°	1416.1	1405.9	1396.2	1382.4	1366.1	1348.2	1339.0	1331.8	1314.0	1294.6	1283.4
7.5°	1463.7	1449.1	1430.4	1404.4	1380.7	1352.6	1334.7	1318.9	1292.7	1265.4	1248.6
10°	1492.7	1472.7	1448.7	1417.1	1388.0	1353.8	1329.8	1305.8	1275.2	1242.5	1222.1
12.5°	1517.6	1490.7	1467.1	1426.5	1392.1	1349.3	1320.8	1287.0	1254.8	1216.0	1196.0
15°	1576.9	1527.4	1482.4	1436.5	1394.1	1334.4	1302.8	1257.3	1214.9	1167.0	1144.0
17.5°	1622.7	1567.1	1496.3	1437.9	1388.5	1322.4	1275.9	1221.5	1171.4	1116.5	1085.3
20°	1648.9	1585.0	1509.0	1439.6	1380.3	1304.8	1254.3	1198.6	1139.9	1078.1	1044.4
22.5°	1664.4	1597.3	1522.1	1433.4	1364.0	1290.5	1226.9	1165.9	1106.4	1039.8	1004.4
25°	1669.3	1608.0	1528.4	1428.3	1343.6	1260.4	1183.8	1124.6	1052.6	990.3	938.8
27.5°	1645.0	1601.1	1524.5	1418.7	1320.0	1222.7	1137.4	1070.3	994.3	926.7	874.9
30°	1615.2	1589.6	1515.1	1408.9	1301.2	1196.6	1102.6	1026.6	951.0	882.6	829.5
32.5°	1569.0	1563.5	1498.0	1395.0	1281.2	1163.5	1066.3	989.4	905.7	838.5	787.9
35°	1478.4	1502.9	1461.5	1364.0	1243.5	1116.4	1011.3	923.5	836.7	772.4	724.9
37.5°	1356.9	1417.7	1406.9	1318.6	1192.7	1065.2	949.1	857.3	774.6	709.7	663.1
40°	1273.1	1350.7	1362.0	1283.9	1156.8	1025.6	902.5	811.2	730.5	671.3	624.3
42.5°	1183.3	1274.0	1304.8	1242.2	1117.5	983.9	860.9	766.2	686.4	628.8	587.2
45°	1032.7	1152.7	1208.3	1172.6	1052.1	915.3	788.7	692.7	620.2	566.1	534.0
47.5°	891.9	1023.0	1097.8	1085.2	979.3	843.8	718.7	626.6	556.0	512.8	484.0
50°	792.3	927.0	1017.4	1021.5	927.0	792.8	667.2	580.4	515.6	475.3	451.8
52.5°	705.7	834.3	932.9	954.5	868.6	739.7	621.1	534.7	477.6	440.5	419.5
55°	592.7	701.4	810.6	850.5	781.5	659.0	549.3	473.2	419.6	394.1	375.7
57.5°	492.7	583.4	684.3	728.3	685.8	580.9	478.0	412.0	368.5	346.1	332.0
60°	440.0	511.5	601.3	653.9	617.2	523.8	433.9	371.1	335.4	315.5	302.2
62.5°	391.0	454.3	530.3	578.4	558.4	470.3	389.8	334.4	303.5	284.8	275.3
65°	322.6	372.7	431.4	475.8	462.5	395.6	329.8	282.3	257.8	243.0	235.3
67.5°	265.7	301.8	342.5	381.4	370.7	323.3	270.5	233.5	215.2	202.5	197.9
70°	229.7	257.3	293.5	324.7	316.0	277.2	235.3	203.7	187.9	177.1	172.5
72.5°	195.4	218.1	245.7	271.2	265.3	233.1	198.2	174.3	162.1	152.2	148.4
75°	147.5	164.9	181.7	198.6	197.0	172.0	151.6	133.2	123.5	115.9	114.3
77.5°	108.9	118.6	130.1	140.1	137.3	123.0	107.0	96.5	89.3	84.2	83.4
80°	83.2	88.8	97.0	104.1	100.6	94.4	81.7	74.0	68.9	63.8	61.8
82.5°	60.3	66.0	70.9	74.7	72.0	66.3	58.4	53.2	50.1	46.7	45.8
85°	31.6	34.7	36.8	37.8	36.8	33.2	29.6	27.6	25.0	23.5	23.0
87.5°	13.3	13.2	13.1	13.8	12.4	12.2	10.4	9.0	8.8	8.5	7.9
90°	5.3	4.7	4.2	3.5	2.7	1.9	1.1	0.3	1.1	1.9	2.7
92.5°	6.9	6.6	6.4	6.2	6.3	6.4	6.5	6.5	6.5	6.4	6.3
95°	11.6	11.1	10.6	11.5	13.9	16.3	18.6	21.0	18.6	16.3	13.9
97.5°	14.5	13.4	12.2	15.0	21.7	28.3	35.0	41.7	35.0	28.3	21.7
100°	16.0	14.8	13.5	17.9	27.7	37.5	47.4	57.2	47.4	37.5	27.7
102.5°	39.4	49.6	59.8	66.0	68.1	70.1	72.2	74.3	72.2	70.1	68.1
105°	59.0	78.6	98.2	106.9	104.8	102.6	100.4	98.3	100.4	102.6	104.8
107.5°	74.7	98.2	121.7	132.6	130.9	129.1	127.4	125.6	127.4	129.1	130.9
110°	98.1	118.9	139.6	149.3	147.8	146.3	144.7	143.2	144.7	146.3	147.8



TEST NUMBER: P331330

CATALOG NUMBER: SA2XXDIP-C675D330U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	153.0	158.1	163.2	165.1	163.8	162.5	161.1	159.8	161.1	162.5	163.8
115°	195.9	194.1	192.3	190.8	189.6	188.4	187.1	185.9	187.1	188.4	189.6
117.5°	218.5	217.3	216.0	214.7	213.4	212.0	210.6	209.3	210.6	212.0	213.4
120°	234.4	233.1	231.8	230.6	229.6	228.5	227.4	226.3	227.4	228.5	229.6
122.5°	249.4	248.0	246.6	245.4	244.2	243.1	242.0	240.8	242.0	243.1	244.2
125°	270.5	269.1	267.8	266.6	265.7	264.7	263.8	262.9	263.8	264.7	265.7
127.5°	290.1	289.0	288.0	287.0	286.0	284.9	283.9	282.8	283.9	284.9	286.0
130°	302.7	301.9	301.1	300.1	299.0	297.8	296.7	295.5	296.7	297.8	299.0
132.5°	314.8	314.0	313.2	312.4	311.4	310.4	309.4	308.5	309.4	310.4	311.4
135°	332.1	331.4	330.8	329.9	328.7	327.6	326.4	325.3	326.4	327.6	328.7
137.5°	347.7	347.0	346.3	345.5	344.7	343.9	343.1	342.3	343.1	343.9	344.7
140°	358.0	357.2	356.4	355.7	355.1	354.5	354.0	353.4	354.0	354.5	355.1
142.5°	367.3	366.4	365.5	364.8	364.3	363.7	363.2	362.7	363.2	363.7	364.3
145°	380.1	378.8	377.6	377.0	377.1	377.2	377.3	377.3	377.3	377.2	377.1
147.5°	391.9	390.6	389.4	389.0	389.2	389.5	389.8	390.1	389.8	389.5	389.2
150°	399.0	397.8	396.7	396.3	396.8	397.3	397.8	398.3	397.8	397.3	396.8
152.5°	405.5	404.4	403.3	403.1	403.6	404.2	404.8	405.3	404.8	404.2	403.6
155°	414.7	413.9	413.0	412.9	413.5	414.2	414.8	415.5	414.8	414.2	413.5
157.5°	422.5	421.9	421.3	421.2	421.8	422.3	422.9	423.4	422.9	422.3	421.8
160°	427.2	426.8	426.4	426.4	426.8	427.2	427.7	428.1	427.7	427.2	426.8
162.5°	431.2	430.8	430.5	430.5	430.9	431.4	431.8	432.2	431.8	431.4	430.9
165°	436.4	436.2	436.0	436.1	436.5	436.9	437.4	437.8	437.4	436.9	436.5
167.5°	440.5	440.3	440.1	440.2	440.6	441.1	441.5	441.9	441.5	441.1	440.6
170°	442.7	442.5	442.4	442.5	443.0	443.4	443.8	444.3	443.8	443.4	443.0
172.5°	444.2	444.1	443.9	444.1	444.5	444.9	445.4	445.8	445.4	444.9	444.5
175°	445.9	445.8	445.6	445.8	446.3	446.8	447.3	447.8	447.3	446.8	446.3
177.5°	446.5	446.4	446.4	446.5	446.9	447.3	447.7	448.1	447.7	447.3	446.9
180°	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8



TEST NUMBER: P331330

CATALOG NUMBER: SA2XXDIP-C675D330U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3
2.5°	1310.7	1308.3	1299.7	1295.2	1287.8	1280.9	1276.4	1278.5	1280.1	1279.3	1278.0
5°	1273.1	1263.4	1248.6	1235.9	1226.7	1209.8	1202.7	1199.1	1196.1	1192.5	1188.9
7.5°	1228.4	1213.1	1191.9	1173.7	1156.5	1135.6	1123.7	1116.5	1109.2	1101.1	1094.0
10°	1196.6	1175.1	1152.7	1127.1	1106.7	1087.8	1071.0	1059.8	1049.6	1039.9	1032.7
12.5°	1163.1	1138.4	1110.6	1075.7	1053.2	1026.2	1023.6	1003.8	987.9	981.9	973.5
15°	1109.8	1075.1	1039.9	998.5	980.6	956.1	940.8	925.5	911.7	902.0	899.5
17.5°	1049.2	1004.3	969.3	939.6	910.3	885.2	871.1	858.8	847.5	834.5	832.8
20°	1003.1	964.3	926.0	900.0	869.9	844.3	827.0	814.7	805.0	797.4	790.7
22.5°	959.4	916.9	881.9	853.4	823.7	803.1	789.4	777.6	769.5	761.0	754.8
25°	889.3	856.1	817.8	785.6	761.1	747.9	736.6	726.4	721.3	715.7	708.6
27.5°	827.9	791.0	755.2	730.3	708.8	697.0	689.0	682.1	677.3	674.0	670.0
30°	784.6	747.3	719.3	694.8	676.9	665.2	660.1	656.0	650.4	648.3	646.3
32.5°	743.0	709.4	685.4	664.1	647.1	639.4	634.7	631.1	626.7	624.6	620.5
35°	684.0	656.0	632.5	620.7	607.0	600.3	596.8	591.6	587.6	585.5	585.0
37.5°	628.6	604.2	588.8	573.7	567.9	563.8	558.9	555.4	554.2	553.9	553.4
40°	592.7	572.8	559.0	546.7	544.2	538.0	534.0	530.9	530.9	531.4	530.9
42.5°	560.0	542.1	530.0	519.4	516.4	512.7	508.6	508.4	509.3	511.0	509.3
45°	510.5	497.7	489.0	483.9	478.3	474.7	474.2	475.8	476.3	476.8	478.3
47.5°	464.9	456.5	448.6	443.0	440.5	439.9	439.3	442.0	444.4	445.3	447.7
50°	438.0	428.3	421.7	418.1	416.0	415.0	416.0	419.1	421.1	423.7	425.2
52.5°	407.8	400.9	396.3	393.6	392.8	393.4	393.6	397.1	400.3	401.2	402.0
55°	366.0	360.9	359.9	355.3	357.3	356.8	359.4	361.4	364.5	367.5	368.1
57.5°	324.4	320.3	317.5	317.9	318.5	320.8	322.9	326.5	329.8	333.0	333.3
60°	296.6	294.5	293.0	293.0	294.0	297.1	299.7	303.2	305.3	307.3	308.8
62.5°	271.3	269.2	267.7	268.5	271.2	273.0	276.0	277.9	279.9	282.0	282.7
65°	231.2	230.2	231.8	232.8	233.3	235.8	239.4	240.9	243.0	244.0	247.6
67.5°	194.4	194.6	194.4	195.8	198.8	199.4	202.8	206.3	206.7	208.7	211.0
70°	169.5	170.5	171.5	172.5	175.1	176.1	178.7	180.2	182.2	183.8	185.3
72.5°	146.6	146.8	147.8	147.6	149.8	152.0	154.2	155.7	157.7	159.7	161.2
75°	112.8	112.8	113.8	114.3	116.9	119.5	118.9	120.0	122.0	124.0	125.1
77.5°	82.4	81.3	82.4	82.9	83.7	85.9	86.3	87.7	90.0	89.3	90.5
80°	62.8	61.3	62.8	63.3	63.3	65.9	65.9	66.9	68.4	66.9	68.4
82.5°	44.8	44.1	45.2	45.3	46.1	46.2	47.1	47.3	48.8	48.1	48.8
85°	22.5	22.0	22.5	22.0	22.5	23.0	23.0	22.5	22.5	23.5	22.0
87.5°	7.6	7.4	7.1	7.2	6.9	6.6	6.3	6.3	6.4	5.7	5.7
90°	3.5	4.2	4.7	5.3	5.9	6.5	6.8	7.2	7.5	7.9	8.2
92.5°	6.2	6.4	6.6	6.9	7.2	7.5	7.7	7.9	8.1	8.2	8.4
95°	11.5	10.6	11.1	11.6	12.1	12.6	13.0	13.3	13.7	14.0	14.2
97.5°	15.0	12.2	13.4	14.5	15.7	16.9	17.2	17.5	17.7	18.0	18.2
100°	17.9	13.5	14.8	16.0	17.2	18.4	19.0	19.6	20.2	20.7	21.1
102.5°	66.0	59.8	49.6	39.4	29.2	18.9	19.7	20.4	21.2	21.9	22.4
105°	106.9	98.2	78.6	59.0	39.3	19.7	20.5	21.3	22.1	22.9	23.4
107.5°	132.6	121.7	98.2	74.7	51.1	27.6	26.8	26.0	25.2	24.4	24.1
110°	149.3	139.6	118.9	98.1	77.3	56.6	49.4	42.2	35.0	27.8	24.4



TEST NUMBER: P331330

CATALOG NUMBER: SA2XXDIP-C675D330U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	165.1	163.2	158.1	153.0	147.8	142.7	116.5	90.3	64.1	37.9	24.9
115°	190.8	192.3	194.1	195.9	197.7	199.5	166.2	133.0	99.7	66.4	47.2
117.5°	214.7	216.0	217.3	218.5	219.7	221.0	212.9	204.9	196.8	188.8	176.3
120°	230.6	231.8	233.1	234.4	235.7	237.0	237.9	238.7	239.6	240.4	236.0
122.5°	245.4	246.6	248.0	249.4	250.9	252.3	252.8	253.3	253.8	254.3	253.6
125°	266.6	267.8	269.1	270.5	271.8	273.2	273.7	274.2	274.7	275.2	275.6
127.5°	287.0	288.0	289.0	290.1	291.1	292.1	292.8	293.6	294.3	295.0	295.4
130°	300.1	301.1	301.9	302.7	303.5	304.3	305.0	305.8	306.6	307.4	307.8
132.5°	312.4	313.2	314.0	314.8	315.6	316.4	317.1	317.8	318.4	319.1	319.4
135°	329.9	330.8	331.4	332.1	332.7	333.4	334.1	334.8	335.5	336.2	336.5
137.5°	345.5	346.3	347.0	347.7	348.5	349.2	349.9	350.6	351.3	352.0	352.2
140°	355.7	356.4	357.2	358.0	358.8	359.5	360.2	360.8	361.5	362.1	362.3
142.5°	364.8	365.5	366.4	367.3	368.2	369.1	369.7	370.3	370.9	371.5	371.6
145°	377.0	377.6	378.8	380.1	381.3	382.5	383.0	383.5	384.0	384.5	384.6
147.5°	389.0	389.4	390.6	391.9	393.1	394.3	394.6	395.0	395.4	395.8	395.8
150°	396.3	396.7	397.8	399.0	400.1	401.3	401.7	402.1	402.5	403.0	403.0
152.5°	403.1	403.3	404.4	405.5	406.6	407.7	408.1	408.6	409.0	409.4	409.4
155°	412.9	413.0	413.9	414.7	415.6	416.4	416.9	417.3	417.7	418.2	418.1
157.5°	421.2	421.3	421.9	422.5	423.1	423.7	424.2	424.7	425.2	425.6	425.6
160°	426.4	426.4	426.8	427.2	427.7	428.1	428.5	429.0	429.4	429.8	429.8
162.5°	430.5	430.5	430.8	431.2	431.6	432.0	432.5	432.9	433.4	433.9	433.9
165°	436.1	436.0	436.2	436.4	436.6	436.8	437.3	437.8	438.3	438.8	438.8
167.5°	440.2	440.1	440.3	440.5	440.7	440.9	441.4	441.9	442.4	442.9	442.8
170°	442.5	442.4	442.5	442.7	442.8	443.0	443.5	444.0	444.5	445.0	444.9
172.5°	444.1	443.9	444.1	444.2	444.4	444.5	445.0	445.5	446.0	446.5	446.5
175°	445.8	445.6	445.8	445.9	446.1	446.2	446.7	447.2	447.7	448.2	448.1
177.5°	446.5	446.4	446.4	446.5	446.5	446.6	447.0	447.4	447.8	448.2	448.1
180°	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8



TEST NUMBER: P331330
 CATALOG NUMBER: SA2XXDIP-C675D330U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3
2.5°	1274.0	1273.1	1273.1	1269.5	1273.1	1273.1	1274.0	1278.0	1279.3	1280.1	1278.5
5°	1181.8	1180.2	1177.7	1180.2	1177.7	1180.2	1181.8	1188.9	1192.5	1196.1	1199.1
7.5°	1090.6	1084.5	1083.6	1077.5	1083.6	1084.5	1090.6	1094.0	1101.1	1109.2	1116.5
10°	1024.0	1019.9	1019.4	1009.7	1019.4	1019.9	1024.0	1032.7	1039.9	1049.6	1059.8
12.5°	973.4	963.6	965.5	959.9	965.5	963.6	973.4	973.5	981.9	987.9	1003.8
15°	885.7	885.7	883.6	875.0	883.6	885.7	885.7	899.5	902.0	911.7	925.5
17.5°	822.7	821.7	816.8	819.2	816.8	821.7	822.7	832.8	834.5	847.5	858.8
20°	785.1	782.1	775.9	775.9	775.9	782.1	785.1	790.7	797.4	805.0	814.7
22.5°	749.6	749.4	742.9	744.9	742.9	749.4	749.6	754.8	761.0	769.5	777.6
25°	708.0	704.0	700.9	702.4	700.9	704.0	708.0	708.6	715.7	721.3	726.4
27.5°	668.6	666.4	666.2	662.0	666.2	666.4	668.6	670.0	674.0	677.3	682.1
30°	645.8	640.7	641.7	639.1	641.7	640.7	645.8	646.3	648.3	650.4	656.0
32.5°	619.6	617.8	616.8	614.6	616.8	617.8	619.6	620.5	624.6	626.7	631.1
35°	584.0	584.5	582.0	583.0	582.0	584.5	584.0	585.0	585.5	587.6	591.6
37.5°	552.9	554.5	553.3	553.6	553.3	554.5	552.9	553.4	553.9	554.2	555.4
40°	532.4	532.4	532.4	534.0	532.4	532.4	532.4	530.9	531.4	530.9	530.9
42.5°	512.8	512.0	511.2	511.1	511.2	512.0	512.8	509.3	511.0	509.3	508.4
45°	479.3	480.9	481.4	478.8	481.4	480.9	479.3	478.3	476.8	476.3	475.8
47.5°	449.0	449.2	449.0	451.3	449.0	449.2	449.0	447.7	445.3	444.4	442.0
50°	427.8	426.8	427.8	426.8	427.8	426.8	427.8	425.2	423.7	421.1	419.1
52.5°	405.3	405.5	404.9	404.7	404.9	405.5	405.3	402.0	401.2	400.3	397.1
55°	370.1	371.1	370.6	370.6	370.6	371.1	370.1	368.1	367.5	364.5	361.4
57.5°	333.7	334.6	335.3	333.0	335.3	334.6	333.7	333.3	333.0	329.8	326.5
60°	308.3	310.9	310.4	309.4	310.4	310.9	308.3	308.8	307.3	305.3	303.2
62.5°	285.1	286.0	285.9	285.7	285.9	286.0	285.1	282.7	282.0	279.9	277.9
65°	249.1	250.1	248.6	250.1	248.6	250.1	249.1	247.6	244.0	243.0	240.9
67.5°	210.4	210.7	211.9	212.6	211.9	210.7	210.4	211.0	208.7	206.7	206.3
70°	186.3	185.8	187.3	188.9	187.3	185.8	186.3	185.3	183.8	182.2	180.2
72.5°	161.0	162.1	161.6	162.7	161.6	162.1	161.0	161.2	159.7	157.7	155.7
75°	124.0	125.6	125.1	126.6	125.1	125.6	124.0	125.1	124.0	122.0	120.0
77.5°	89.6	89.8	89.6	90.5	89.6	89.8	89.6	90.5	89.3	90.0	87.7
80°	68.4	67.4	66.4	68.4	66.4	67.4	68.4	68.4	66.9	68.4	66.9
82.5°	47.6	48.2	47.2	47.2	47.2	48.2	47.6	48.8	48.1	48.8	47.3
85°	22.0	21.4	20.4	20.4	20.4	21.4	22.0	22.0	23.5	22.5	22.5
87.5°	5.7	5.4	5.4	5.0	5.4	5.4	5.7	5.7	5.7	6.4	6.3
90°	8.3	8.4	8.6	8.7	8.6	8.4	8.3	8.2	7.9	7.5	7.2
92.5°	8.5	8.6	8.6	8.7	8.6	8.6	8.5	8.4	8.2	8.1	7.9
95°	14.1	14.0	14.0	13.9	14.0	14.0	14.1	14.2	14.0	13.7	13.3
97.5°	18.3	18.4	18.5	18.6	18.5	18.4	18.3	18.2	18.0	17.7	17.5
100°	21.2	21.4	21.5	21.7	21.5	21.4	21.2	21.1	20.7	20.2	19.6
102.5°	22.6	22.8	23.0	23.2	23.0	22.8	22.6	22.4	21.9	21.2	20.4
105°	23.7	24.0	24.3	24.6	24.3	24.0	23.7	23.4	22.9	22.1	21.3
107.5°	24.4	24.7	25.0	25.3	25.0	24.7	24.4	24.1	24.4	25.2	26.0
110°	24.7	25.0	25.3	25.5	25.3	25.0	24.7	24.4	27.8	35.0	42.2



TEST NUMBER: P331330

CATALOG NUMBER: SA2XXDIP-C675D330U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	25.1	25.3	25.6	25.8	25.6	25.3	25.1	24.9	37.9	64.1	90.3
115°	42.0	36.9	31.7	26.5	31.7	36.9	42.0	47.2	66.4	99.7	133.0
117.5°	159.3	142.3	125.3	108.3	125.3	142.3	159.3	176.3	188.8	196.8	204.9
120°	226.3	216.6	206.9	197.2	206.9	216.6	226.3	236.0	240.4	239.6	238.7
122.5°	251.8	249.9	248.0	246.1	248.0	249.9	251.8	253.6	254.3	253.8	253.3
125°	275.8	276.0	276.2	276.4	276.2	276.0	275.8	275.6	275.2	274.7	274.2
127.5°	295.5	295.5	295.5	295.6	295.5	295.5	295.5	295.4	295.0	294.3	293.6
130°	307.7	307.6	307.6	307.5	307.6	307.6	307.7	307.8	307.4	306.6	305.8
132.5°	319.3	319.3	319.2	319.1	319.2	319.3	319.3	319.4	319.1	318.4	317.8
135°	336.4	336.2	336.1	335.9	336.1	336.2	336.4	336.5	336.2	335.5	334.8
137.5°	352.0	351.8	351.5	351.3	351.5	351.8	352.0	352.2	352.0	351.3	350.6
140°	361.9	361.6	361.2	360.8	361.2	361.6	361.9	362.3	362.1	361.5	360.8
142.5°	371.2	370.9	370.5	370.1	370.5	370.9	371.2	371.6	371.5	370.9	370.3
145°	384.2	383.9	383.5	383.1	383.5	383.9	384.2	384.6	384.5	384.0	383.5
147.5°	395.5	395.2	394.9	394.6	394.9	395.2	395.5	395.8	395.8	395.4	395.0
150°	402.7	402.3	401.9	401.6	401.9	402.3	402.7	403.0	403.0	402.5	402.1
152.5°	408.9	408.5	408.0	407.5	408.0	408.5	408.9	409.4	409.4	409.0	408.6
155°	417.5	417.0	416.4	415.8	416.4	417.0	417.5	418.1	418.2	417.7	417.3
157.5°	425.0	424.5	423.9	423.4	423.9	424.5	425.0	425.6	425.6	425.2	424.7
160°	429.3	428.8	428.3	427.8	428.3	428.8	429.3	429.8	429.8	429.4	429.0
162.5°	433.2	432.6	432.0	431.4	432.0	432.6	433.2	433.9	433.9	433.4	432.9
165°	438.3	437.8	437.3	436.8	437.3	437.8	438.3	438.8	438.8	438.3	437.8
167.5°	442.2	441.5	440.9	440.2	440.9	441.5	442.2	442.8	442.9	442.4	441.9
170°	444.3	443.6	443.0	442.3	443.0	443.6	444.3	444.9	445.0	444.5	444.0
172.5°	445.8	445.2	444.5	443.9	444.5	445.2	445.8	446.5	446.5	446.0	445.5
175°	447.4	446.7	445.9	445.2	445.9	446.7	447.4	448.1	448.2	447.7	447.2
177.5°	447.6	447.1	446.6	446.1	446.6	447.1	447.6	448.1	448.2	447.8	447.4
180°	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8



TEST NUMBER: P331330

CATALOG NUMBER: SA2XXDIP-C675D330U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3
2.5°	1276.4	1280.9	1287.8	1295.2	1299.7	1308.3	1310.7	1314.8	1318.5	1327.1	1336.0
5°	1202.7	1209.8	1226.7	1235.9	1248.6	1263.4	1273.1	1283.4	1294.6	1314.0	1331.8
7.5°	1123.7	1135.6	1156.5	1173.7	1191.9	1213.1	1228.4	1248.6	1265.4	1292.7	1318.9
10°	1071.0	1087.8	1106.7	1127.1	1152.7	1175.1	1196.6	1222.1	1242.5	1275.2	1305.8
12.5°	1023.6	1026.2	1053.2	1075.7	1110.6	1138.4	1163.1	1196.0	1216.0	1254.8	1287.0
15°	940.8	956.1	980.6	998.5	1039.9	1075.1	1109.8	1144.0	1167.0	1214.9	1257.3
17.5°	871.1	885.2	910.3	939.6	969.3	1004.3	1049.2	1085.3	1116.5	1171.4	1221.5
20°	827.0	844.3	869.9	900.0	926.0	964.3	1003.1	1044.4	1078.1	1139.9	1198.6
22.5°	789.4	803.1	823.7	853.4	881.9	916.9	959.4	1004.4	1039.8	1106.4	1165.9
25°	736.6	747.9	761.1	785.6	817.8	856.1	889.3	938.8	990.3	1052.6	1124.6
27.5°	689.0	697.0	708.8	730.3	755.2	791.0	827.9	874.9	926.7	994.3	1070.3
30°	660.1	665.2	676.9	694.8	719.3	747.3	784.6	829.5	882.6	951.0	1026.6
32.5°	634.7	639.4	647.1	664.1	685.4	709.4	743.0	787.9	838.5	905.7	989.4
35°	596.8	600.3	607.0	620.7	632.5	656.0	684.0	724.9	772.4	836.7	923.5
37.5°	558.9	563.8	567.9	573.7	588.8	604.2	628.6	663.1	709.7	774.6	857.3
40°	534.0	538.0	544.2	546.7	559.0	572.8	592.7	624.3	671.3	730.5	811.2
42.5°	508.6	512.7	516.4	519.4	530.0	542.1	560.0	587.2	628.8	686.4	766.2
45°	474.2	474.7	478.3	483.9	489.0	497.7	510.5	534.0	566.1	620.2	692.7
47.5°	439.3	439.9	440.5	443.0	448.6	456.5	464.9	484.0	512.8	556.0	626.6
50°	416.0	415.0	416.0	418.1	421.7	428.3	438.0	451.8	475.3	515.6	580.4
52.5°	393.6	393.4	392.8	393.6	396.3	400.9	407.8	419.5	440.5	477.6	534.7
55°	359.4	356.8	357.3	355.3	359.9	360.9	366.0	375.7	394.1	419.6	473.2
57.5°	322.9	320.8	318.5	317.9	317.5	320.3	324.4	332.0	346.1	368.5	412.0
60°	299.7	297.1	294.0	293.0	293.0	294.5	296.6	302.2	315.5	335.4	371.1
62.5°	276.0	273.0	271.2	268.5	267.7	269.2	271.3	275.3	284.8	303.5	334.4
65°	239.4	235.8	233.3	232.8	231.8	230.2	231.2	235.3	243.0	257.8	282.3
67.5°	202.8	199.4	198.8	195.8	194.4	194.6	194.4	197.9	202.5	215.2	233.5
70°	178.7	176.1	175.1	172.5	171.5	170.5	169.5	172.5	177.1	187.9	203.7
72.5°	154.2	152.0	149.8	147.6	147.8	146.8	146.6	148.4	152.2	162.1	174.3
75°	118.9	119.5	116.9	114.3	113.8	112.8	112.8	114.3	115.9	123.5	133.2
77.5°	86.3	85.9	83.7	82.9	82.4	81.3	82.4	83.4	84.2	89.3	96.5
80°	65.9	65.9	63.3	63.3	62.8	61.3	62.8	61.8	63.8	68.9	74.0
82.5°	47.1	46.2	46.1	45.3	45.2	44.1	44.8	45.8	46.7	50.1	53.2
85°	23.0	23.0	22.5	22.0	22.5	22.0	22.5	23.0	23.5	25.0	27.6
87.5°	6.3	6.6	6.9	7.2	7.1	7.4	7.6	7.9	8.5	8.8	9.0
90°	6.8	6.5	5.9	5.3	4.7	4.2	3.5	2.7	1.9	1.1	0.3
92.5°	7.7	7.5	7.2	6.9	6.6	6.4	6.2	6.3	6.4	6.5	6.5
95°	13.0	12.6	12.1	11.6	11.1	10.6	11.5	13.9	16.3	18.6	21.0
97.5°	17.2	16.9	15.7	14.5	13.4	12.2	15.0	21.7	28.3	35.0	41.7
100°	19.0	18.4	17.2	16.0	14.8	13.5	17.9	27.7	37.5	47.4	57.2
102.5°	19.7	18.9	29.2	39.4	49.6	59.8	66.0	68.1	70.1	72.2	74.3
105°	20.5	19.7	39.3	59.0	78.6	98.2	106.9	104.8	102.6	100.4	98.3
107.5°	26.8	27.6	51.1	74.7	98.2	121.7	132.6	130.9	129.1	127.4	125.6
110°	49.4	56.6	77.3	98.1	118.9	139.6	149.3	147.8	146.3	144.7	143.2



TEST NUMBER: P331330

CATALOG NUMBER: SA2XXDIP-C675D330U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	116.5	142.7	147.8	153.0	158.1	163.2	165.1	163.8	162.5	161.1	159.8
115°	166.2	199.5	197.7	195.9	194.1	192.3	190.8	189.6	188.4	187.1	185.9
117.5°	212.9	221.0	219.7	218.5	217.3	216.0	214.7	213.4	212.0	210.6	209.3
120°	237.9	237.0	235.7	234.4	233.1	231.8	230.6	229.6	228.5	227.4	226.3
122.5°	252.8	252.3	250.9	249.4	248.0	246.6	245.4	244.2	243.1	242.0	240.8
125°	273.7	273.2	271.8	270.5	269.1	267.8	266.6	265.7	264.7	263.8	262.9
127.5°	292.8	292.1	291.1	290.1	289.0	288.0	287.0	286.0	284.9	283.9	282.8
130°	305.0	304.3	303.5	302.7	301.9	301.1	300.1	299.0	297.8	296.7	295.5
132.5°	317.1	316.4	315.6	314.8	314.0	313.2	312.4	311.4	310.4	309.4	308.5
135°	334.1	333.4	332.7	332.1	331.4	330.8	329.9	328.7	327.6	326.4	325.3
137.5°	349.9	349.2	348.5	347.7	347.0	346.3	345.5	344.7	343.9	343.1	342.3
140°	360.2	359.5	358.8	358.0	357.2	356.4	355.7	355.1	354.5	354.0	353.4
142.5°	369.7	369.1	368.2	367.3	366.4	365.5	364.8	364.3	363.7	363.2	362.7
145°	383.0	382.5	381.3	380.1	378.8	377.6	377.0	377.1	377.2	377.3	377.3
147.5°	394.6	394.3	393.1	391.9	390.6	389.4	389.0	389.2	389.5	389.8	390.1
150°	401.7	401.3	400.1	399.0	397.8	396.7	396.3	396.8	397.3	397.8	398.3
152.5°	408.1	407.7	406.6	405.5	404.4	403.3	403.1	403.6	404.2	404.8	405.3
155°	416.9	416.4	415.6	414.7	413.9	413.0	412.9	413.5	414.2	414.8	415.5
157.5°	424.2	423.7	423.1	422.5	421.9	421.3	421.2	421.8	422.3	422.9	423.4
160°	428.5	428.1	427.7	427.2	426.8	426.4	426.4	426.8	427.2	427.7	428.1
162.5°	432.5	432.0	431.6	431.2	430.8	430.5	430.5	430.9	431.4	431.8	432.2
165°	437.3	436.8	436.6	436.4	436.2	436.0	436.1	436.5	436.9	437.4	437.8
167.5°	441.4	440.9	440.7	440.5	440.3	440.1	440.2	440.6	441.1	441.5	441.9
170°	443.5	443.0	442.8	442.7	442.5	442.4	442.5	443.0	443.4	443.8	444.3
172.5°	445.0	444.5	444.4	444.2	444.1	443.9	444.1	444.5	444.9	445.4	445.8
175°	446.7	446.2	446.1	445.9	445.8	445.6	445.8	446.3	446.8	447.3	447.8
177.5°	447.0	446.6	446.5	446.5	446.4	446.4	446.5	446.9	447.3	447.7	448.1
180°	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8



TEST NUMBER: P331330

CATALOG NUMBER: SA2XXDIP-C675D330U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3
2.5°	1335.2	1337.3	1343.8	1350.3	1357.7	1359.7	1363.0	1360.1	1359.3	1367.1	1372.8
5°	1339.0	1348.2	1366.1	1382.4	1396.2	1405.9	1416.1	1420.2	1427.8	1438.5	1451.8
7.5°	1334.7	1352.6	1380.7	1404.4	1430.4	1449.1	1463.7	1476.1	1491.2	1511.5	1533.7
10°	1329.8	1353.8	1388.0	1417.1	1448.7	1472.7	1492.7	1512.0	1534.5	1562.6	1591.7
12.5°	1320.8	1349.3	1392.1	1426.5	1467.1	1490.7	1517.6	1559.4	1583.5	1622.6	1663.6
15°	1302.8	1334.4	1394.1	1436.5	1482.4	1527.4	1576.9	1616.7	1656.5	1679.5	1737.2
17.5°	1275.9	1322.4	1388.5	1437.9	1496.3	1567.1	1622.7	1667.8	1713.8	1751.1	1780.0
20°	1254.3	1304.8	1380.3	1439.6	1509.0	1585.0	1648.9	1694.8	1734.6	1765.8	1783.6
22.5°	1226.9	1290.5	1364.0	1433.4	1522.1	1597.3	1664.4	1700.5	1733.8	1749.0	1755.9
25°	1183.8	1260.4	1343.6	1428.3	1528.4	1608.0	1669.3	1691.2	1700.9	1686.1	1661.6
27.5°	1137.4	1222.7	1320.0	1418.7	1524.5	1601.1	1645.0	1641.5	1625.1	1577.2	1538.9
30°	1102.6	1196.6	1301.2	1408.9	1515.1	1589.6	1615.2	1589.6	1552.4	1498.8	1444.2
32.5°	1066.3	1163.5	1281.2	1395.0	1498.0	1563.5	1569.0	1525.1	1467.4	1406.5	1338.4
35°	1011.3	1116.4	1243.5	1364.0	1461.5	1502.9	1478.4	1400.8	1332.4	1249.2	1156.2
37.5°	949.1	1065.2	1192.7	1318.6	1406.9	1417.7	1356.9	1275.2	1178.7	1080.9	971.6
40°	902.5	1025.6	1156.8	1283.9	1362.0	1350.7	1273.1	1183.3	1068.4	949.0	847.4
42.5°	860.9	983.9	1117.5	1242.2	1304.8	1274.0	1183.3	1073.0	949.6	837.1	744.1
45°	788.7	915.3	1052.1	1172.6	1208.3	1152.7	1032.7	910.2	788.7	694.8	621.3
47.5°	718.7	843.8	979.3	1085.2	1097.8	1023.0	891.9	765.8	661.4	584.9	533.0
50°	667.2	792.8	927.0	1021.5	1017.4	927.0	792.3	672.3	585.0	523.2	488.5
52.5°	621.1	739.7	868.6	954.5	932.9	834.3	705.7	599.2	527.4	479.1	447.7
55°	549.3	659.0	781.5	850.5	810.6	701.4	592.7	506.9	453.8	417.6	393.1
57.5°	478.0	580.9	685.8	728.3	684.3	583.4	492.7	430.5	390.6	363.8	347.8
60°	433.9	523.8	617.2	653.9	601.3	511.5	440.0	384.4	352.2	330.3	316.0
62.5°	389.8	470.3	558.4	578.4	530.3	454.3	391.0	344.8	318.3	298.8	285.4
65°	329.8	395.6	462.5	475.8	431.4	372.7	322.6	292.5	269.0	254.7	244.0
67.5°	270.5	323.3	370.7	381.4	342.5	301.8	265.7	239.4	223.5	211.6	202.6
70°	235.3	277.2	316.0	324.7	293.5	257.3	229.7	208.8	194.5	184.3	175.6
72.5°	198.2	233.1	265.3	271.2	245.7	218.1	195.4	179.0	166.3	159.8	151.5
75°	151.6	172.0	197.0	198.6	181.7	164.9	147.5	136.8	130.2	122.0	117.9
77.5°	107.0	123.0	137.3	140.1	130.1	118.6	108.9	100.5	94.8	91.1	87.3
80°	81.7	94.4	100.6	104.1	97.0	88.8	83.2	77.6	74.0	71.5	68.9
82.5°	58.4	66.3	72.0	74.7	70.9	66.0	60.3	57.2	54.4	52.3	51.4
85°	29.6	33.2	36.8	37.8	36.8	34.7	31.6	31.6	30.1	29.6	29.6
87.5°	10.4	12.2	12.4	13.8	13.1	13.2	13.3	13.0	12.7	12.4	12.1
90°	1.1	1.9	2.7	3.5	4.2	4.7	5.3	5.9	6.5	6.8	7.2
92.5°	6.5	6.4	6.3	6.2	6.4	6.6	6.9	7.2	7.5	7.7	7.9
95°	18.6	16.3	13.9	11.5	10.6	11.1	11.6	12.1	12.6	13.0	13.3
97.5°	35.0	28.3	21.7	15.0	12.2	13.4	14.5	15.7	16.9	17.2	17.5
100°	47.4	37.5	27.7	17.9	13.5	14.8	16.0	17.2	18.4	19.0	19.6
102.5°	72.2	70.1	68.1	66.0	59.8	49.6	39.4	29.2	18.9	19.7	20.4
105°	100.4	102.6	104.8	106.9	98.2	78.6	59.0	39.3	19.7	20.5	21.3
107.5°	127.4	129.1	130.9	132.6	121.7	98.2	74.7	51.1	27.6	26.8	26.0
110°	144.7	146.3	147.8	149.3	139.6	118.9	98.1	77.3	56.6	49.4	42.2



TEST NUMBER: P331330

CATALOG NUMBER: SA2XXDIP-C675D330U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	161.1	162.5	163.8	165.1	163.2	158.1	153.0	147.8	142.7	116.5	90.3
115°	187.1	188.4	189.6	190.8	192.3	194.1	195.9	197.7	199.5	166.2	133.0
117.5°	210.6	212.0	213.4	214.7	216.0	217.3	218.5	219.7	221.0	212.9	204.9
120°	227.4	228.5	229.6	230.6	231.8	233.1	234.4	235.7	237.0	237.9	238.7
122.5°	242.0	243.1	244.2	245.4	246.6	248.0	249.4	250.9	252.3	252.8	253.3
125°	263.8	264.7	265.7	266.6	267.8	269.1	270.5	271.8	273.2	273.7	274.2
127.5°	283.9	284.9	286.0	287.0	288.0	289.0	290.1	291.1	292.1	292.8	293.6
130°	296.7	297.8	299.0	300.1	301.1	301.9	302.7	303.5	304.3	305.0	305.8
132.5°	309.4	310.4	311.4	312.4	313.2	314.0	314.8	315.6	316.4	317.1	317.8
135°	326.4	327.6	328.7	329.9	330.8	331.4	332.1	332.7	333.4	334.1	334.8
137.5°	343.1	343.9	344.7	345.5	346.3	347.0	347.7	348.5	349.2	349.9	350.6
140°	354.0	354.5	355.1	355.7	356.4	357.2	358.0	358.8	359.5	360.2	360.8
142.5°	363.2	363.7	364.3	364.8	365.5	366.4	367.3	368.2	369.1	369.7	370.3
145°	377.3	377.2	377.1	377.0	377.6	378.8	380.1	381.3	382.5	383.0	383.5
147.5°	389.8	389.5	389.2	389.0	389.4	390.6	391.9	393.1	394.3	394.6	395.0
150°	397.8	397.3	396.8	396.3	396.7	397.8	399.0	400.1	401.3	401.7	402.1
152.5°	404.8	404.2	403.6	403.1	403.3	404.4	405.5	406.6	407.7	408.1	408.6
155°	414.8	414.2	413.5	412.9	413.0	413.9	414.7	415.6	416.4	416.9	417.3
157.5°	422.9	422.3	421.8	421.2	421.3	421.9	422.5	423.1	423.7	424.2	424.7
160°	427.7	427.2	426.8	426.4	426.4	426.8	427.2	427.7	428.1	428.5	429.0
162.5°	431.8	431.4	430.9	430.5	430.5	430.8	431.2	431.6	432.0	432.5	432.9
165°	437.4	436.9	436.5	436.1	436.0	436.2	436.4	436.6	436.8	437.3	437.8
167.5°	441.5	441.1	440.6	440.2	440.1	440.3	440.5	440.7	440.9	441.4	441.9
170°	443.8	443.4	443.0	442.5	442.4	442.5	442.7	442.8	443.0	443.5	444.0
172.5°	445.4	444.9	444.5	444.1	443.9	444.1	444.2	444.4	444.5	445.0	445.5
175°	447.3	446.8	446.3	445.8	445.6	445.8	445.9	446.1	446.2	446.7	447.2
177.5°	447.7	447.3	446.9	446.5	446.4	446.4	446.5	446.5	446.6	447.0	447.4
180°	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8



TEST NUMBER: P331330
 CATALOG NUMBER: SA2XXDIP-C675D330U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3
2.5°	1377.7	1383.4	1383.4	1384.2	1390.8	1389.9	1389.5
5°	1466.1	1474.8	1475.8	1485.0	1491.1	1489.1	1483.5
7.5°	1549.5	1565.7	1577.9	1584.7	1592.8	1597.8	1595.6
10°	1615.7	1639.2	1653.5	1663.2	1674.9	1683.6	1680.5
12.5°	1675.7	1703.7	1723.3	1739.9	1741.5	1752.6	1745.0
15°	1769.3	1798.9	1802.0	1814.3	1824.0	1822.9	1823.4
17.5°	1800.3	1809.8	1811.7	1812.0	1812.1	1808.5	1800.8
20°	1789.2	1785.7	1777.0	1770.4	1758.6	1757.1	1746.9
22.5°	1737.0	1725.6	1703.9	1689.5	1671.2	1666.4	1663.6
25°	1634.1	1609.0	1574.3	1541.1	1532.0	1514.1	1519.2
27.5°	1492.9	1453.9	1416.3	1389.3	1364.9	1338.2	1345.8
30°	1393.6	1349.7	1296.6	1255.8	1229.8	1204.2	1199.6
32.5°	1275.2	1210.9	1151.6	1115.7	1075.8	1059.7	1042.0
35°	1071.0	1008.2	949.5	899.0	869.9	847.4	827.0
37.5°	887.3	815.0	767.7	726.7	705.7	692.8	696.1
40°	773.4	710.1	675.4	644.2	624.8	615.6	617.7
42.5°	681.1	633.7	605.1	583.8	570.1	565.0	563.8
45°	576.3	549.8	526.3	514.1	507.4	501.8	498.2
47.5°	504.9	483.2	470.0	462.7	456.9	451.2	451.1
50°	462.0	447.7	438.5	430.8	426.3	422.2	425.7
52.5°	429.3	416.2	407.1	400.2	398.5	394.8	394.7
55°	380.8	370.6	364.0	357.8	354.8	352.7	350.2
57.5°	336.7	327.0	320.9	317.0	311.2	309.1	308.3
60°	305.3	297.6	291.5	286.4	283.8	279.7	279.7
62.5°	276.3	268.6	262.9	259.0	254.8	253.2	253.6
65°	234.3	228.2	222.6	218.5	217.5	214.4	215.4
67.5°	195.7	191.6	185.7	183.5	181.5	179.9	178.7
70°	170.0	165.9	162.8	159.8	158.2	158.2	158.2
72.5°	148.3	143.4	141.6	137.7	138.6	137.0	135.4
75°	114.9	111.8	110.3	108.7	106.2	106.2	106.2
77.5°	84.5	83.6	81.8	80.1	79.5	79.0	79.2
80°	65.3	64.8	63.8	63.8	62.8	62.3	61.3
82.5°	50.2	48.9	48.3	47.9	47.7	47.6	47.4
85°	28.6	27.6	27.6	28.1	27.1	27.1	27.6
87.5°	12.5	12.6	12.2	12.3	12.7	12.3	12.4
90°	7.5	7.9	8.2	8.3	8.4	8.6	8.7
92.5°	8.1	8.2	8.4	8.5	8.6	8.6	8.7
95°	13.7	14.0	14.2	14.1	14.0	14.0	13.9
97.5°	17.7	18.0	18.2	18.3	18.4	18.5	18.6
100°	20.2	20.7	21.1	21.2	21.4	21.5	21.7
102.5°	21.2	21.9	22.4	22.6	22.8	23.0	23.2
105°	22.1	22.9	23.4	23.7	24.0	24.3	24.6
107.5°	25.2	24.4	24.1	24.4	24.7	25.0	25.3
110°	35.0	27.8	24.4	24.7	25.0	25.3	25.5



TEST NUMBER: P331330

CATALOG NUMBER: SA2XXDIP-C675D330U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	64.1	37.9	24.9	25.1	25.3	25.6	25.8
115°	99.7	66.4	47.2	42.0	36.9	31.7	26.5
117.5°	196.8	188.8	176.3	159.3	142.3	125.3	108.3
120°	239.6	240.4	236.0	226.3	216.6	206.9	197.2
122.5°	253.8	254.3	253.6	251.8	249.9	248.0	246.1
125°	274.7	275.2	275.6	275.8	276.0	276.2	276.4
127.5°	294.3	295.0	295.4	295.5	295.5	295.5	295.6
130°	306.6	307.4	307.8	307.7	307.6	307.6	307.5
132.5°	318.4	319.1	319.4	319.3	319.3	319.2	319.1
135°	335.5	336.2	336.5	336.4	336.2	336.1	335.9
137.5°	351.3	352.0	352.2	352.0	351.8	351.5	351.3
140°	361.5	362.1	362.3	361.9	361.6	361.2	360.8
142.5°	370.9	371.5	371.6	371.2	370.9	370.5	370.1
145°	384.0	384.5	384.6	384.2	383.9	383.5	383.1
147.5°	395.4	395.8	395.8	395.5	395.2	394.9	394.6
150°	402.5	403.0	403.0	402.7	402.3	401.9	401.6
152.5°	409.0	409.4	409.4	408.9	408.5	408.0	407.5
155°	417.7	418.2	418.1	417.5	417.0	416.4	415.8
157.5°	425.2	425.6	425.6	425.0	424.5	423.9	423.4
160°	429.4	429.8	429.8	429.3	428.8	428.3	427.8
162.5°	433.4	433.9	433.9	433.2	432.6	432.0	431.4
165°	438.3	438.8	438.8	438.3	437.8	437.3	436.8
167.5°	442.4	442.9	442.8	442.2	441.5	440.9	440.2
170°	444.5	445.0	444.9	444.3	443.6	443.0	442.3
172.5°	446.0	446.5	446.5	445.8	445.2	444.5	443.9
175°	447.7	448.2	448.1	447.4	446.7	445.9	445.2
177.5°	447.8	448.2	448.1	447.6	447.1	446.6	446.1
180°	446.8	446.8	446.8	446.8	446.8	446.8	446.8

(END OF REPORT)