

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331648-840

Luminaire Tested: **SA2XXRDIP-C485D330U840-4F0-1E-UDD-F**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331648-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXRDIP-C485D330U840-4F0-1E-UDD-F  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 330 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3037.6 lumens  
Efficiency: N/A  
Efficacy: 110.5 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 27.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331648-840  
CATALOG NUMBER: SA2XXRDIP-C485D330U840-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P331648-840

CATALOG NUMBER: SA2XXRDIP-C485D330U840-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	56
1	100	96	92	89	93	89	86	83	77	75	73	66	64	63	56	55	53	49
2	91	84	78	73	85	79	73	69	68	64	61	59	56	53	50	48	46	42
3	84	74	67	62	78	70	63	58	61	56	52	52	49	46	45	42	40	36
4	77	66	59	53	71	62	55	50	54	49	45	47	43	40	40	37	35	31
5	71	59	51	46	66	56	49	43	49	43	39	42	38	35	36	33	31	28
6	65	54	46	40	61	50	43	38	44	39	34	39	34	31	33	30	27	24
7	61	49	41	35	56	46	39	34	40	35	30	35	31	27	31	27	24	22
8	56	44	37	31	52	42	35	30	37	31	27	32	28	25	28	25	22	20
9	53	41	33	28	49	38	32	27	34	28	25	30	25	22	26	23	20	18
10	49	37	30	25	46	35	29	24	31	26	22	28	23	20	24	21	18	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	13454	13454	13454
5°	13506	13287	13361
10°	13404	13070	12959
15°	13249	12682	12318
20°	13036	12129	11519
25°	12818	11501	10750
30°	12515	10856	9758
35°	12220	10153	8889
40°	11921	9428	7885
45°	11574	8611	6976
50°	11215	7784	6081
55°	10849	6899	5222
60°	10424	5968	4334
65°	9941	5012	3947
70°	9361	4131	3635
75°	8659	3762	3387
80°	7643	3366	3087
85°	6002	2649	2649



TEST NUMBER: P331648-840

CATALOG NUMBER: SA2XXRDIP-C485D330U840-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	78.0	2.6
10°-20°	214.2	7.1
20°-30°	300.8	9.9
30°-40°	328.0	10.8
40°-50°	301.6	9.9
50°-60°	236.8	7.8
60°-70°	154.4	5.1
70°-80°	79.6	2.6
80°-90°	21.8	0.7
90°-100°	15.1	0.5
100°-110°	55.2	1.8
110°-120°	147.6	4.9
120°-130°	243.6	8.0
130°-140°	259.0	8.5
140°-150°	240.8	7.9
150°-160°	193.6	6.4
160°-170°	124.7	4.1
170°-180°	42.9	1.4
0°-30°	593.0	19.5
0°-40°	921.0	30.3
0°-60°	1459.4	48.0
0°-90°	1715.2	56.5
90°-120°	217.8	7.2
90°-150°	961.2	31.6
90°-180°	1322.0	43.5
0°-180°	3037.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	833	833	833	833	833	
5°	833	829	820	826	824	79
15°	793	783	759	745	737	223
25°	720	694	646	616	603	331
35°	620	580	515	469	451	388
45°	507	455	377	326	306	391
55°	385	325	245	202	186	344
65°	260	199	131	107	103	258
75°	139	87	60	55	54	147
85°	32	17	14	14	14	38
90°	0	4	7	8	9	2
95°	21	11	13	14	14	26
105°	99	104	20	23	25	106
115°	188	193	202	57	27	185
125°	266	270	276	278	279	237
135°	328	334	337	340	339	254
145°	381	381	386	388	387	238
155°	420	417	420	422	420	193
165°	442	440	441	443	441	125
175°	452	450	451	453	450	43
180°	451	451	451	451	451	



TEST NUMBER: P331648-840

CATALOG NUMBER: SA2XXRDIP-C485D330U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	833.3	833.3	833.3	833.3	833.3	833.3	833.3	833.3	833.3	833.3	833.3
2.5°	836.4	835.8	835.1	834.4	833.7	832.6	831.2	829.7	828.2	826.8	828.1
5°	833.3	832.5	831.7	830.9	830.0	828.5	826.4	824.2	822.0	819.8	821.3
7.5°	824.8	823.7	822.7	821.6	820.6	818.8	816.3	813.7	811.2	808.7	809.1
10°	817.6	816.4	815.2	814.1	812.8	810.6	807.3	803.9	800.5	797.2	796.7
12.5°	808.5	807.1	805.6	804.2	802.7	799.9	795.6	791.3	787.0	782.7	781.8
15°	792.6	790.8	789.0	787.1	785.3	781.5	775.8	770.1	764.5	758.7	755.6
17.5°	773.3	770.4	767.6	764.8	761.9	756.9	749.6	742.3	735.0	727.6	723.9
20°	758.7	755.4	752.0	748.7	745.3	739.4	731.0	722.7	714.3	705.9	701.8
22.5°	743.1	739.3	735.5	731.7	728.0	721.4	712.0	702.5	693.1	683.6	678.2
25°	719.5	714.2	708.8	703.4	698.0	689.8	678.7	667.7	656.6	645.6	638.7
27.5°	691.2	685.3	679.4	673.7	667.8	658.6	646.2	633.7	621.3	608.7	600.8
30°	671.3	664.9	658.5	652.2	645.8	635.9	622.5	609.0	595.6	582.3	573.7
32.5°	652.0	644.5	637.0	629.7	622.2	611.6	597.9	584.2	570.6	556.9	547.1
35°	620.0	611.4	602.9	594.3	585.7	574.1	559.4	544.6	529.9	515.1	504.5
37.5°	587.9	578.6	569.2	559.8	550.5	537.9	522.2	506.4	490.7	475.0	463.3
40°	565.6	555.6	545.5	535.5	525.4	512.3	496.0	479.8	463.5	447.3	435.4
42.5°	542.7	532.1	521.5	511.0	500.4	486.7	469.9	453.0	436.3	419.5	407.2
45°	506.9	495.6	484.3	473.1	461.9	447.5	429.9	412.3	394.7	377.1	365.2
47.5°	471.8	459.9	448.1	436.2	424.2	409.2	391.0	372.8	354.7	336.5	324.7
50°	446.5	434.5	422.7	410.8	398.9	383.7	365.3	346.9	328.4	309.9	298.4
52.5°	421.7	409.3	396.9	384.5	372.0	356.8	338.7	320.7	302.7	284.7	273.5
55°	385.4	372.3	359.2	346.2	333.2	317.5	299.4	281.3	263.2	245.1	235.1
57.5°	348.1	334.8	321.3	307.9	294.5	279.1	261.8	244.3	226.9	209.5	200.3
60°	322.8	309.4	296.0	282.6	269.1	253.9	236.6	219.3	202.1	184.8	176.2
62.5°	298.0	284.7	271.2	257.8	244.4	229.5	213.1	196.6	180.2	163.7	155.5
65°	260.2	246.6	233.1	219.4	205.9	191.6	176.5	161.4	146.3	131.2	125.5
67.5°	223.7	210.3	196.7	183.3	169.8	156.2	142.7	129.2	115.5	102.0	99.4
70°	198.3	185.3	172.2	159.2	146.0	133.7	122.2	110.6	99.1	87.5	85.8
72.5°	174.2	161.7	149.2	136.6	124.1	113.2	103.9	94.6	85.3	76.0	74.6
75°	138.8	127.0	115.3	103.6	91.8	83.1	77.5	71.7	66.0	60.3	59.2
77.5°	103.9	93.6	83.3	73.0	62.8	56.2	53.5	50.8	48.0	45.2	44.5
80°	82.2	73.6	65.1	56.6	48.0	42.9	41.2	39.6	37.9	36.2	35.5
82.5°	62.3	55.6	49.0	42.3	35.6	31.7	30.6	29.4	28.3	27.2	26.8
85°	32.4	28.9	25.3	21.9	18.4	16.4	15.9	15.3	14.8	14.3	14.3
87.5°	9.7	8.8	7.9	7.0	6.1	5.7	5.8	5.9	6.1	6.2	6.1
90°	0.3	1.1	1.9	2.7	3.5	4.2	4.7	5.4	6.0	6.6	6.9
92.5°	6.6	6.6	6.5	6.4	6.3	6.5	6.7	7.0	7.3	7.6	7.8
95°	21.2	18.8	16.5	14.0	11.6	10.7	11.2	11.7	12.2	12.7	13.1
97.5°	42.1	35.3	28.6	21.9	15.1	12.3	13.5	14.6	15.9	17.1	17.4
100°	57.8	47.9	37.9	28.0	18.1	13.6	14.9	16.2	17.4	18.6	19.2
102.5°	75.0	72.9	70.8	68.8	66.7	60.4	50.1	39.8	29.5	19.1	19.9
105°	99.3	101.4	103.6	105.8	108.0	99.2	79.4	59.6	39.7	19.9	20.7
107.5°	126.8	128.7	130.4	132.2	133.9	122.9	99.2	75.4	51.6	27.9	27.1
110°	144.6	146.1	147.7	149.3	150.8	141.0	120.1	99.1	78.1	57.2	49.9



TEST NUMBER: P331648-840

CATALOG NUMBER: SA2XXRDIP-C485D330U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	161.4	162.7	164.1	165.4	166.7	164.8	159.7	154.5	149.3	144.1	117.6
115°	187.7	188.9	190.3	191.5	192.7	194.2	196.0	197.8	199.7	201.5	167.8
117.5°	211.4	212.7	214.1	215.5	216.8	218.1	219.4	220.7	221.9	223.2	215.0
120°	228.5	229.6	230.8	231.9	232.9	234.1	235.4	236.7	238.0	239.3	240.2
122.5°	243.2	244.4	245.5	246.6	247.8	249.0	250.4	251.9	253.4	254.8	255.3
125°	265.5	266.4	267.3	268.3	269.2	270.4	271.8	273.2	274.5	275.9	276.4
127.5°	285.6	286.7	287.7	288.8	289.8	290.8	291.9	293.0	294.0	295.0	295.7
130°	298.4	299.6	300.7	301.9	303.1	304.1	304.9	305.7	306.5	307.3	308.0
132.5°	311.5	312.5	313.5	314.5	315.5	316.3	317.1	317.9	318.7	319.5	320.2
135°	328.5	329.6	330.8	331.9	333.2	334.1	334.7	335.4	336.0	336.7	337.4
137.5°	345.7	346.5	347.3	348.1	348.9	349.7	350.4	351.1	351.9	352.6	353.4
140°	356.9	357.5	358.0	358.6	359.2	359.9	360.7	361.5	362.3	363.0	363.8
142.5°	366.3	366.8	367.3	367.9	368.4	369.1	370.0	370.9	371.8	372.7	373.3
145°	381.0	381.0	380.9	380.8	380.7	381.3	382.5	383.8	385.1	386.3	386.8
147.5°	393.9	393.6	393.3	393.0	392.8	393.2	394.5	395.8	397.0	398.2	398.5
150°	402.2	401.7	401.2	400.7	400.2	400.6	401.7	402.9	404.0	405.3	405.7
152.5°	409.3	408.8	408.2	407.6	407.1	407.3	408.4	409.5	410.6	411.7	412.1
155°	419.6	418.9	418.3	417.6	417.0	417.1	418.0	418.8	419.7	420.5	421.0
157.5°	427.6	427.1	426.5	426.0	425.4	425.5	426.1	426.7	427.3	427.9	428.4
160°	432.3	431.9	431.4	431.0	430.6	430.6	431.0	431.4	431.9	432.3	432.7
162.5°	436.5	436.1	435.7	435.2	434.7	434.7	435.0	435.5	435.9	436.3	436.8
165°	442.1	441.7	441.2	440.8	440.4	440.3	440.5	440.7	440.9	441.1	441.6
167.5°	446.3	445.9	445.5	444.9	444.5	444.4	444.6	444.8	445.0	445.2	445.8
170°	448.7	448.2	447.8	447.4	446.9	446.8	446.9	447.1	447.2	447.4	447.9
172.5°	450.2	449.8	449.3	448.9	448.5	448.3	448.5	448.6	448.8	448.9	449.4
175°	452.2	451.7	451.2	450.7	450.2	450.0	450.2	450.3	450.5	450.6	451.1
177.5°	452.5	452.1	451.7	451.3	450.9	450.8	450.8	450.9	450.9	451.0	451.4
180°	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2



TEST NUMBER: P331648-840

CATALOG NUMBER: SA2XXRDIP-C485D330U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	833.3	833.3	833.3	833.3	833.3	833.3	833.3	833.3
2.5°	829.4	830.8	832.1	832.6	832.4	832.1	831.8	831.6
5°	822.8	824.4	825.9	826.4	825.9	825.4	824.9	824.4
7.5°	809.5	809.9	810.4	810.2	809.3	808.4	807.6	806.7
10°	796.2	795.7	795.2	794.5	793.5	792.4	791.4	790.4
12.5°	780.9	780.0	779.1	777.8	776.1	774.5	772.7	771.1
15°	752.3	749.2	746.0	743.6	741.8	740.2	738.5	736.9
17.5°	720.0	716.3	712.5	709.1	706.3	703.4	700.5	697.6
20°	697.5	693.4	689.1	685.2	681.6	677.8	674.2	670.4
22.5°	672.8	667.4	662.1	657.9	655.2	652.5	649.7	646.9
25°	631.9	625.0	618.1	613.4	610.9	608.3	605.9	603.4
27.5°	592.8	584.7	576.7	570.8	566.7	562.8	558.8	554.8
30°	565.1	556.6	548.1	541.5	536.9	532.5	528.0	523.4
32.5°	537.3	527.7	517.9	510.9	506.6	502.4	498.1	493.8
35°	494.0	483.4	472.9	465.7	462.1	458.4	454.7	451.0
37.5°	451.7	440.1	428.5	420.5	416.4	412.1	407.9	403.6
40°	423.4	411.5	399.6	391.5	387.2	382.8	378.4	374.1
42.5°	394.9	382.5	370.3	362.0	357.8	353.6	349.3	345.1
45°	353.3	341.4	329.5	321.5	317.5	313.5	309.4	305.5
47.5°	312.9	301.0	289.2	281.4	277.8	274.2	270.4	266.8
50°	286.8	275.3	263.7	256.2	252.7	249.1	245.6	242.1
52.5°	262.3	251.2	239.9	232.8	229.5	226.3	223.0	219.7
55°	225.0	214.9	204.9	198.2	195.1	191.9	188.7	185.5
57.5°	191.1	181.9	172.7	166.7	164.0	161.4	158.6	155.9
60°	167.6	159.2	150.6	145.0	142.3	139.6	136.9	134.2
62.5°	147.3	139.3	131.1	126.2	124.6	123.0	121.4	119.8
65°	119.9	114.1	108.5	105.3	104.8	104.3	103.8	103.3
67.5°	96.7	94.1	91.5	90.0	89.4	88.9	88.4	87.8
70°	84.1	82.5	80.8	79.6	79.0	78.3	77.6	77.0
72.5°	73.2	71.8	70.4	69.5	69.1	68.7	68.3	67.9
75°	58.0	56.9	55.6	54.9	54.8	54.6	54.4	54.3
77.5°	43.9	43.2	42.6	42.1	41.8	41.6	41.3	41.0
80°	34.8	34.2	33.5	33.2	33.2	33.2	33.2	33.2
82.5°	26.4	26.0	25.5	25.3	25.3	25.3	25.3	25.3
85°	14.3	14.3	14.3	14.3	14.3	14.3	14.3	14.3
87.5°	6.1	6.0	5.9	5.9	5.9	6.0	6.0	6.0
90°	7.3	7.6	8.0	8.3	8.4	8.5	8.7	8.8
92.5°	8.0	8.2	8.3	8.5	8.6	8.7	8.7	8.8
95°	13.4	13.8	14.1	14.3	14.2	14.1	14.1	14.0
97.5°	17.7	17.9	18.2	18.4	18.5	18.6	18.7	18.8
100°	19.8	20.4	20.9	21.3	21.4	21.6	21.7	21.9
102.5°	20.6	21.4	22.1	22.6	22.8	23.0	23.2	23.4
105°	21.5	22.3	23.1	23.6	23.9	24.2	24.5	24.8
107.5°	26.3	25.4	24.6	24.3	24.6	24.9	25.2	25.5
110°	42.6	35.3	28.1	24.6	24.9	25.2	25.5	25.8





TEST NUMBER: P331648-840

CATALOG NUMBER: SA2XXRDIP-C485D330U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	91.2	64.7	38.3	25.1	25.3	25.5	25.9	26.1
115°	134.3	100.7	67.1	47.7	42.4	37.3	32.0	26.8
117.5°	206.9	198.7	190.7	178.0	160.9	143.7	126.5	109.4
120°	241.1	242.0	242.8	238.3	228.5	218.7	208.9	199.1
122.5°	255.8	256.3	256.8	256.1	254.3	252.4	250.4	248.5
125°	276.9	277.4	277.9	278.3	278.5	278.7	278.9	279.1
127.5°	296.5	297.2	297.9	298.3	298.4	298.4	298.4	298.5
130°	308.8	309.6	310.4	310.8	310.7	310.6	310.6	310.5
132.5°	320.9	321.5	322.2	322.6	322.4	322.4	322.3	322.2
135°	338.1	338.8	339.5	339.8	339.7	339.5	339.4	339.2
137.5°	354.1	354.8	355.5	355.7	355.5	355.3	355.0	354.8
140°	364.4	365.1	365.7	365.9	365.5	365.2	364.8	364.4
142.5°	374.0	374.6	375.2	375.3	374.9	374.6	374.2	373.8
145°	387.3	387.8	388.3	388.4	388.0	387.7	387.3	386.9
147.5°	398.9	399.3	399.7	399.7	399.4	399.1	398.8	398.5
150°	406.1	406.5	407.0	407.0	406.7	406.3	405.9	405.6
152.5°	412.6	413.0	413.4	413.4	412.9	412.5	412.0	411.5
155°	421.4	421.8	422.3	422.2	421.6	421.1	420.5	419.9
157.5°	428.9	429.4	429.8	429.8	429.2	428.7	428.1	427.6
160°	433.2	433.6	434.0	434.0	433.5	433.0	432.5	432.0
162.5°	437.2	437.7	438.2	438.2	437.5	436.9	436.3	435.7
165°	442.1	442.6	443.1	443.1	442.6	442.1	441.6	441.1
167.5°	446.3	446.8	447.3	447.2	446.6	445.9	445.2	444.5
170°	448.4	448.9	449.4	449.3	448.7	448.0	447.4	446.7
172.5°	449.9	450.4	450.9	450.9	450.2	449.6	448.9	448.3
175°	451.6	452.1	452.6	452.5	451.8	451.1	450.3	449.6
177.5°	451.8	452.2	452.6	452.5	452.0	451.5	451.0	450.5
180°	451.2	451.2	451.2	451.2	451.2	451.2	451.2	451.2

(END OF REPORT)