

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331653-840

Luminaire Tested: **SA2XXRDIP-C485D530U840-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331653-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C485D530U840-4F0-1E-UDD-A4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 530 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3962.4 lumens
Efficiency: N/A
Efficacy: 120.8 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 32.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331653-840
CATALOG NUMBER: SA2XXRDIP-C485D530U840-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331653-840

CATALOG NUMBER: SA2XXRDIP-C485D530U840-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	47				47
1	98	94	90	87	90	87	83	81	73	71	69	60	59	57	49	48	47	41				41
2	90	83	77	72	82	77	72	67	65	61	58	54	51	49	44	42	41	36				36
3	82	74	67	61	76	68	62	57	58	53	50	48	45	43	39	37	35	31				31
4	76	66	58	53	70	61	54	49	52	47	43	44	40	37	36	33	31	28				28
5	70	59	51	46	64	55	48	43	47	42	38	40	36	33	33	30	28	25				25
6	65	53	46	40	60	50	43	38	43	37	33	36	32	29	30	27	25	22				22
7	60	48	41	35	55	45	38	34	39	34	30	33	29	26	28	25	23	20				20
8	56	44	37	32	52	41	35	30	36	31	27	31	27	24	26	23	21	18				18
9	52	41	33	29	48	38	32	27	33	28	24	28	24	22	24	21	19	17				17
10	49	37	30	26	45	35	29	25	31	26	22	26	22	20	22	19	17	15				15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	17525	17525	17525	17525
5°	19571	17634	15635	17634
10°	21713	17510	13554	17510
15°	22781	17254	10678	17254
20°	19749	16873	9241	16873
25°	12953	16352	8250	16352
30°	8720	15720	7467	15720
35°	7062	14927	6733	14927
40°	6279	14060	6232	14060
45°	5683	13047	5562	13047
50°	5172	12039	5152	12039
55°	4861	10925	4799	10925
60°	4066	9901	4017	9901
65°	3431	8989	3889	8989
70°	3172	8030	3668	8030
75°	2969	6987	3387	6987
80°	2734	5746	3013	5746
85°	2501	4539	2649	4539



TEST NUMBER: P331653-840

CATALOG NUMBER: SA2XXRDIP-C485D530U840-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.9	2.6
10°-20°	286.7	7.2
20°-30°	369.4	9.3
30°-40°	351.1	8.9
40°-50°	300.7	7.6
50°-60°	229.0	5.8
60°-70°	144.8	3.7
70°-80°	72.3	1.8
80°-90°	21.5	0.5
90°-100°	119.7	3.0
100°-110°	406.3	10.3
110°-120°	431.7	10.9
120°-130°	355.4	9.0
130°-140°	285.4	7.2
140°-150°	215.7	5.4
150°-160°	151.6	3.8
160°-170°	89.2	2.3
170°-180°	29.0	0.7
0°-30°	759.0	19.2
0°-40°	1110.1	28.0
0°-60°	1639.8	41.4
0°-90°	1878.4	47.4
90°-120°	957.8	24.2
90°-150°	1814.1	45.8
90°-180°	2084.0	52.6
0°-180°	3962.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1085	1085	1085	1085	1085	
5°	1208	1088	965	1088	1208	119
15°	1363	1032	639	1032	1363	368
25°	727	918	463	918	727	345
35°	358	757	342	757	358	229
45°	249	571	244	571	249	193
55°	173	388	170	388	173	152
65°	90	235	102	235	90	91
75°	48	112	54	112	48	50
85°	14	24	14	24	14	15
90°	19	1	19	1	19	11
95°	66	20	66	20	66	85
105°	649	70	649	70	649	628
115°	854	124	854	124	854	836
125°	693	173	693	173	693	626
135°	574	203	574	203	574	446
145°	458	232	458	232	458	291
155°	385	263	385	263	385	180
165°	338	287	338	287	338	97
175°	305	299	305	299	305	30
180°	299	299	299	299	299	



TEST NUMBER: P331653-840

CATALOG NUMBER: SA2XXRDIP-C485D530U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4
2.5°	1129.4	1130.3	1131.3	1129.1	1129.1	1127.3	1123.4	1120.3	1111.9	1110.6	1110.6
5°	1207.5	1206.8	1208.3	1203.4	1196.6	1195.1	1187.9	1178.5	1168.7	1157.7	1155.5
7.5°	1285.3	1284.1	1281.1	1280.2	1275.1	1263.6	1252.1	1239.8	1223.6	1207.6	1199.6
10°	1324.4	1336.9	1329.4	1316.2	1318.8	1301.1	1291.6	1275.5	1261.8	1238.1	1232.8
12.5°	1363.0	1368.0	1365.5	1358.1	1354.7	1342.4	1329.7	1315.6	1290.5	1269.2	1250.6
15°	1362.9	1370.1	1372.0	1369.7	1371.6	1370.8	1364.0	1352.3	1330.5	1307.1	1286.8
17.5°	1262.3	1267.3	1279.6	1288.0	1298.6	1320.9	1331.9	1336.3	1332.9	1319.6	1305.3
20°	1149.4	1141.1	1175.9	1193.6	1208.7	1246.4	1278.8	1291.2	1311.2	1310.9	1307.1
22.5°	989.6	991.5	1024.4	1045.4	1089.5	1127.2	1164.2	1211.0	1249.7	1275.3	1290.2
25°	727.1	741.4	774.3	802.8	851.9	922.1	985.8	1059.8	1129.4	1184.6	1237.0
27.5°	546.0	547.1	573.1	599.7	628.7	686.2	766.5	854.7	954.2	1036.2	1130.6
30°	467.7	465.3	476.4	492.5	517.5	561.9	622.3	709.0	808.2	931.9	1042.0
32.5°	412.1	412.2	420.5	432.5	453.1	483.1	524.5	594.9	688.7	810.3	939.4
35°	358.3	357.9	364.0	372.6	381.2	400.5	428.8	465.7	530.3	643.8	775.8
37.5°	319.6	321.3	324.3	329.7	339.2	349.9	367.0	391.7	437.7	504.8	615.7
40°	297.9	298.7	302.9	307.4	313.1	321.3	335.3	355.3	388.8	442.3	523.4
42.5°	278.0	278.7	281.8	285.9	290.3	298.7	310.2	327.5	354.8	396.5	463.4
45°	248.9	248.9	251.6	253.4	258.3	265.9	275.3	289.6	308.5	339.4	384.0
47.5°	221.6	221.7	223.4	226.6	229.7	235.6	244.9	256.6	270.3	294.3	332.2
50°	205.9	206.3	207.4	210.1	212.0	217.2	224.4	234.6	248.9	267.4	299.0
52.5°	193.2	193.0	194.4	195.6	196.8	200.7	206.0	215.0	227.8	243.9	270.1
55°	172.7	171.2	173.5	175.3	176.5	178.0	181.0	186.7	197.6	211.2	230.8
57.5°	147.0	146.4	148.0	149.8	153.3	157.4	160.0	163.6	169.3	178.9	198.4
60°	125.9	125.9	129.4	130.5	134.6	139.9	145.2	148.2	153.9	160.3	174.6
62.5°	107.2	107.6	109.2	110.3	112.6	119.1	126.5	133.1	138.5	144.6	154.1
65°	89.8	90.5	90.5	91.3	92.8	94.3	97.3	102.6	112.0	120.7	127.8
67.5°	76.1	76.4	76.6	77.4	77.8	79.4	80.6	83.0	85.1	93.4	102.3
70°	67.2	68.3	67.9	68.7	69.0	69.8	71.3	72.4	75.8	77.7	83.0
72.5°	58.7	59.5	59.5	59.9	60.9	61.0	62.2	63.3	65.5	67.2	70.0
75°	47.6	47.2	47.6	48.3	48.7	49.0	49.0	50.5	51.7	53.2	55.0
77.5°	36.7	37.1	37.0	37.1	37.1	37.8	37.7	38.4	39.5	40.3	41.2
80°	29.4	29.8	29.4	29.8	30.2	30.5	30.2	30.5	31.7	32.4	32.4
82.5°	22.8	22.8	23.1	23.1	23.2	23.3	23.8	23.9	24.7	24.5	24.8
85°	13.5	13.2	13.2	13.2	13.5	13.9	13.5	13.5	13.9	13.9	13.9
87.5°	8.6	8.9	8.9	8.9	8.9	8.8	8.6	9.1	8.9	9.4	8.9
90°	19.0	19.0	19.0	19.0	19.0	18.4	17.3	18.4	19.0	19.6	19.0
92.5°	31.9	32.8	32.4	34.2	34.6	38.3	43.1	50.2	63.2	74.8	73.8
95°	65.6	65.0	66.9	71.4	78.9	91.6	115.7	150.9	197.5	225.8	199.9
97.5°	129.3	134.1	142.5	156.6	184.2	225.8	288.1	352.1	404.2	385.4	290.2
100°	206.2	216.5	233.3	258.0	305.8	375.5	454.4	525.8	537.9	454.9	313.3
102.5°	362.8	376.9	397.7	440.0	491.9	565.8	623.5	639.6	587.6	457.3	304.6
105°	649.0	657.1	681.9	717.6	753.3	772.3	764.8	699.7	580.0	426.8	287.4
107.5°	829.1	839.8	844.8	846.7	842.2	814.4	754.5	656.4	529.4	394.0	278.8
110°	883.4	884.0	878.9	867.9	843.1	795.9	722.2	619.1	497.6	378.4	277.0



TEST NUMBER: P331653-840

CATALOG NUMBER: SA2XXRDIP-C485D530U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	882.5	879.4	869.6	851.3	816.9	762.8	684.0	585.0	475.4	368.2	277.5
115°	854.0	848.9	833.9	807.4	766.6	707.2	631.8	543.1	448.1	357.1	279.9
117.5°	803.2	798.9	783.2	755.2	713.5	657.8	589.4	511.5	430.8	351.6	284.1
120°	770.5	764.8	748.1	721.0	680.8	628.3	567.2	495.8	421.6	348.4	286.8
122.5°	736.5	731.6	716.8	690.1	654.0	606.6	548.9	483.4	413.7	346.6	290.0
125°	692.9	688.2	673.8	652.0	618.5	575.3	524.6	465.3	402.5	343.3	294.9
127.5°	654.6	650.9	638.4	617.9	588.9	549.0	501.2	447.5	392.2	341.3	299.8
130°	632.9	628.3	616.8	597.2	569.0	531.0	485.5	436.0	385.3	340.3	303.5
132.5°	610.4	606.2	595.6	576.0	548.3	512.6	470.8	425.0	379.7	339.9	307.2
135°	574.2	571.9	561.5	542.5	517.8	485.5	447.5	409.5	372.0	339.2	311.5
137.5°	538.7	535.2	526.1	509.8	487.3	459.1	429.0	397.2	366.6	339.1	315.5
140°	514.3	510.8	502.2	487.3	468.8	443.4	417.0	389.3	363.5	338.6	317.3
142.5°	489.9	489.2	481.5	467.9	450.4	429.2	406.4	382.8	360.2	338.6	318.7
145°	458.4	456.7	450.9	441.1	427.4	410.6	392.7	373.8	355.9	337.5	320.2
147.5°	432.0	431.0	427.1	419.3	407.9	395.7	381.7	366.8	351.5	335.4	320.6
150°	416.4	415.8	412.3	405.5	396.8	386.5	374.4	361.6	347.9	334.1	320.2
152.5°	403.0	402.9	400.4	394.4	387.6	378.6	368.4	356.6	344.7	331.7	319.3
155°	385.3	386.5	384.2	380.1	373.8	367.4	358.8	349.6	338.6	327.7	317.9
157.5°	370.2	370.2	369.2	365.8	361.3	356.4	349.1	341.4	333.0	323.6	315.3
160°	360.5	360.5	359.9	357.1	353.0	349.0	342.6	336.3	328.8	320.8	313.9
162.5°	351.3	351.7	351.2	349.2	345.2	342.1	336.7	331.2	325.2	318.5	312.5
165°	338.1	338.6	338.6	336.3	334.1	331.7	327.7	323.7	319.0	313.9	309.8
167.5°	325.9	326.6	326.7	325.4	324.4	322.2	319.5	316.4	313.1	309.8	307.2
170°	318.5	319.6	320.2	318.5	317.9	316.8	314.5	312.8	309.8	307.5	305.8
172.5°	312.5	313.2	313.8	313.0	312.4	311.6	309.8	308.6	306.6	304.8	304.0
175°	304.7	305.8	306.4	305.8	305.8	305.3	304.7	304.1	302.4	301.7	301.2
177.5°	299.9	300.8	301.3	301.3	301.3	301.3	300.8	300.8	299.9	299.4	299.9
180°	299.4	299.4	299.4	299.4	299.4	299.4	299.4	299.4	299.4	299.4	299.4



TEST NUMBER: P331653-840

CATALOG NUMBER: SA2XXRDIP-C485D530U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4
2.5°	1111.3	1108.9	1106.8	1101.4	1098.6	1092.6	1091.7	1091.4	1083.6	1076.0	1073.9
5°	1149.4	1143.5	1134.4	1123.8	1112.9	1101.6	1094.0	1088.0	1072.9	1058.5	1050.3
7.5°	1187.9	1175.0	1159.3	1139.3	1122.7	1104.0	1090.1	1077.6	1056.2	1035.7	1021.9
10°	1216.6	1195.5	1174.8	1147.2	1125.7	1104.6	1085.0	1068.0	1043.9	1016.7	997.4
12.5°	1234.4	1211.1	1182.6	1155.7	1127.8	1101.0	1074.7	1052.9	1024.6	996.5	973.6
15°	1258.5	1233.6	1198.9	1160.4	1124.6	1089.5	1059.3	1032.2	995.2	961.7	933.7
17.5°	1278.2	1243.9	1206.6	1162.2	1120.6	1076.1	1037.2	1002.5	961.4	920.9	888.1
20°	1284.4	1250.5	1207.5	1163.1	1114.0	1061.6	1019.8	982.0	937.9	893.7	856.1
22.5°	1280.5	1254.2	1206.3	1153.1	1102.9	1048.0	1000.8	956.9	908.1	863.0	819.3
25°	1253.9	1244.9	1199.6	1141.6	1084.2	1020.5	965.8	917.9	862.1	813.9	766.3
27.5°	1191.8	1211.4	1183.4	1121.5	1057.7	989.4	928.0	873.4	815.5	761.1	713.8
30°	1132.2	1177.0	1164.9	1107.6	1036.3	969.2	900.2	843.2	781.4	725.6	678.8
32.5°	1050.4	1124.5	1136.3	1088.3	1014.6	940.8	868.5	811.8	747.3	688.4	642.9
35°	920.2	1031.1	1082.0	1051.4	977.4	898.0	823.2	757.3	692.4	634.3	589.1
37.5°	764.9	915.8	1000.8	1002.9	935.0	852.3	771.0	705.5	639.0	582.1	533.1
40°	664.1	827.8	938.3	962.8	905.4	816.1	733.9	667.1	602.3	546.4	490.3
42.5°	573.6	736.7	872.5	915.1	869.6	780.8	698.3	628.5	565.4	512.6	455.2
45°	463.8	606.4	756.1	832.3	807.1	724.8	637.7	571.4	512.1	466.5	411.4
47.5°	391.3	491.8	636.6	739.7	739.2	664.2	578.6	514.9	460.0	417.3	372.6
50°	349.9	437.5	560.1	676.9	686.7	623.8	542.3	479.3	428.1	383.1	347.3
52.5°	312.9	385.0	495.1	607.2	635.1	580.6	501.6	443.4	393.6	352.3	321.6
55°	264.4	320.1	403.9	508.8	551.0	512.5	442.3	388.1	347.7	313.1	286.6
57.5°	223.6	265.5	332.6	417.1	466.3	442.0	384.3	340.1	305.6	274.2	253.4
60°	198.0	232.3	289.2	359.8	414.0	397.1	347.7	306.6	277.2	250.0	230.5
62.5°	173.9	203.4	252.2	309.4	359.2	352.1	311.8	277.3	251.6	226.8	210.3
65°	139.9	161.4	199.4	244.4	284.4	287.7	258.7	235.3	212.3	192.7	178.0
67.5°	111.4	125.4	152.3	190.1	220.0	230.8	213.0	195.1	176.8	161.7	149.0
70°	93.9	105.2	124.8	155.4	182.9	194.2	184.0	170.1	154.2	141.8	130.9
72.5°	76.1	87.2	101.6	124.0	147.6	159.9	156.3	146.2	133.4	123.1	112.8
75°	57.4	60.7	70.5	85.6	104.1	114.6	117.2	112.0	101.8	93.9	87.9
77.5°	42.4	44.4	49.1	57.1	69.1	78.5	82.4	81.8	74.7	70.2	64.5
80°	33.9	35.0	37.4	40.7	49.8	59.2	61.8	61.8	57.0	55.0	49.4
82.5°	25.8	26.7	28.0	29.9	34.1	42.3	45.2	45.8	42.7	40.3	35.9
85°	14.7	14.3	15.0	16.3	17.0	19.2	23.7	24.5	23.7	20.7	19.6
87.5°	8.3	7.8	7.2	6.5	6.6	6.7	7.7	8.9	8.0	7.6	7.2
90°	15.6	11.5	8.7	6.9	5.8	4.6	2.3	0.6	2.3	4.6	5.8
92.5°	57.5	39.2	26.2	20.7	16.9	14.2	10.1	7.1	10.1	14.2	16.9
95°	133.0	82.9	56.5	42.6	33.4	28.2	22.4	20.2	22.4	28.2	33.4
97.5°	179.3	109.5	76.1	60.5	49.9	42.0	36.0	32.8	36.0	42.0	49.9
100°	188.9	118.7	88.2	72.0	60.5	51.3	46.0	44.3	46.0	51.3	60.5
102.5°	189.3	126.9	98.7	82.6	70.6	61.4	56.2	54.9	56.2	61.4	70.6
105°	192.4	141.1	114.0	97.9	85.2	76.5	72.6	70.3	72.6	76.5	85.2
107.5°	200.3	155.6	129.4	113.1	100.6	92.6	88.7	86.8	88.7	92.6	100.6
110°	206.7	165.3	140.0	123.2	111.2	103.7	100.2	97.9	100.2	103.7	111.2



TEST NUMBER: P331653-840

CATALOG NUMBER: SA2XXRDIP-C485D530U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	213.7	174.5	150.1	132.9	121.3	114.2	110.4	108.1	110.4	114.2	121.3
115°	224.0	188.9	164.1	148.6	137.0	130.2	126.7	123.8	126.7	130.2	137.0
117.5°	235.1	202.2	179.3	163.1	152.1	145.9	142.5	140.2	142.5	145.9	152.1
120°	242.5	211.4	188.9	172.8	161.3	156.0	152.6	150.3	152.6	156.0	161.3
122.5°	248.9	220.2	199.0	182.5	171.0	165.3	161.9	160.0	161.9	165.3	171.0
125°	259.1	233.3	212.5	196.4	184.9	177.9	174.5	172.8	174.5	177.9	184.9
127.5°	268.7	245.5	225.3	208.7	197.6	190.1	185.2	182.9	185.2	190.1	197.6
130°	274.7	252.9	232.7	216.5	205.0	196.9	191.2	188.9	191.2	196.9	205.0
132.5°	280.7	259.2	240.0	223.9	212.0	203.4	197.2	194.4	197.2	203.4	212.0
135°	288.5	268.4	249.9	233.8	220.6	212.0	205.0	202.7	205.0	212.0	220.6
137.5°	294.5	275.8	257.5	242.6	229.4	220.3	213.3	210.6	213.3	220.3	229.4
140°	297.7	279.9	262.7	247.6	235.0	225.8	218.8	216.5	218.8	225.8	235.0
142.5°	300.5	283.2	266.3	252.3	240.0	230.9	224.4	222.6	224.4	230.9	240.0
145°	304.1	287.9	272.4	259.7	248.2	239.5	233.8	231.6	233.8	239.5	248.2
147.5°	306.1	291.9	277.2	266.0	256.4	248.4	242.9	241.2	242.9	248.4	256.4
150°	307.0	293.7	280.4	270.1	261.5	254.0	249.3	247.6	249.3	254.0	261.5
152.5°	307.4	295.6	283.7	274.3	266.1	259.5	254.9	254.1	254.9	259.5	266.1
155°	308.1	298.3	288.5	279.9	273.6	267.2	263.8	263.2	263.8	267.2	273.6
157.5°	308.1	300.2	292.0	284.8	279.6	274.2	271.4	270.7	271.4	274.2	279.6
160°	308.1	301.2	294.3	287.9	283.4	278.7	276.4	275.9	276.4	278.7	283.4
162.5°	307.6	301.6	295.7	290.7	286.6	282.9	280.5	280.9	280.5	282.9	286.6
165°	306.4	302.4	297.2	293.7	290.8	287.4	286.2	286.8	286.2	287.4	290.8
167.5°	305.6	302.3	298.4	296.3	294.2	292.0	290.9	291.6	290.9	292.0	294.2
170°	304.7	301.7	298.9	297.2	296.0	294.3	293.7	294.9	293.7	294.3	296.0
172.5°	303.3	301.3	299.3	298.1	297.4	295.7	296.0	296.7	296.0	295.7	297.4
175°	301.7	300.6	299.4	298.9	298.9	297.7	298.3	298.9	298.3	297.7	298.9
177.5°	300.8	299.9	299.4	299.4	299.4	298.5	299.0	299.9	299.0	298.5	299.4
180°	299.4	299.4	299.4	299.4	299.4	299.4	299.4	299.4	299.4	299.4	299.4



TEST NUMBER: P331653-840

CATALOG NUMBER: SA2XXRDIP-C485D530U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4
2.5°	1070.0	1067.8	1063.9	1057.9	1054.3	1047.9	1043.7	1046.1	1046.7	1046.1	1045.5
5°	1041.3	1033.3	1022.4	1011.8	1002.0	991.5	985.4	982.8	977.4	974.5	973.0
7.5°	1006.4	992.8	977.3	959.0	943.3	927.0	918.6	914.4	903.6	897.8	892.6
10°	980.5	959.0	943.5	919.4	904.7	883.2	868.5	868.9	854.1	845.9	839.8
12.5°	951.9	928.3	902.5	880.8	860.4	843.1	825.4	818.2	802.5	794.6	778.3
15°	904.3	876.8	849.7	820.2	799.5	772.7	747.1	715.8	690.5	668.6	662.6
17.5°	852.4	818.4	791.1	756.6	721.0	676.0	646.3	628.1	612.9	601.4	592.8
20°	816.9	782.1	753.2	701.0	653.2	622.6	600.8	586.8	571.0	558.6	551.7
22.5°	779.4	743.3	703.7	645.5	608.2	583.7	564.2	548.2	537.5	527.8	521.6
25°	726.3	686.7	621.5	581.5	551.4	525.7	512.1	502.3	491.0	477.8	471.8
27.5°	670.2	607.2	560.4	530.7	501.9	485.2	473.0	458.4	448.3	442.3	436.1
30°	628.2	565.3	528.8	496.2	475.9	457.5	443.1	434.8	425.1	414.9	410.7
32.5°	581.5	531.2	496.1	469.2	448.5	432.7	421.4	408.0	400.9	394.7	386.0
35°	523.4	485.3	453.3	431.4	411.8	399.0	385.8	377.9	365.1	359.8	356.4
37.5°	474.2	441.2	417.3	394.3	378.7	364.6	356.5	343.9	338.3	330.9	323.8
40°	446.5	414.0	391.1	372.2	354.9	344.3	334.2	324.0	315.7	312.3	303.6
42.5°	418.2	391.7	368.7	348.1	336.5	325.3	312.5	305.0	296.3	290.8	285.5
45°	379.0	355.7	336.0	319.0	306.2	294.6	286.2	273.8	268.9	257.9	253.4
47.5°	344.6	322.9	304.2	288.0	275.5	267.9	255.8	246.0	238.2	231.5	225.7
50°	320.1	302.1	284.0	269.6	258.3	247.4	235.0	230.0	217.9	214.6	211.2
52.5°	297.8	280.6	264.1	250.0	238.7	228.1	217.1	210.8	202.6	199.1	196.7
55°	266.6	250.0	234.2	221.8	210.5	199.4	192.7	184.8	181.0	178.3	175.3
57.5°	235.2	220.4	208.1	195.6	184.2	175.5	167.6	162.9	159.0	155.5	151.9
60°	215.3	201.0	190.1	178.3	166.7	159.6	153.5	147.8	143.3	138.0	136.5
62.5°	194.2	181.7	171.7	160.3	150.1	143.5	137.8	132.5	127.0	119.4	117.2
65°	165.2	155.4	144.8	135.4	126.3	120.0	111.6	105.6	103.3	102.6	102.2
67.5°	139.0	129.7	120.6	111.0	102.7	96.7	92.5	91.6	90.1	89.6	88.6
70°	121.4	112.8	103.7	94.6	86.7	85.6	84.1	82.6	80.7	80.0	79.2
72.5°	105.7	96.7	87.8	80.5	77.1	75.6	74.1	72.6	71.4	70.6	70.2
75°	81.1	72.8	66.8	64.1	62.2	61.1	58.9	57.7	57.0	55.8	55.4
77.5°	58.4	53.7	50.9	49.3	47.3	46.0	44.8	43.6	42.8	42.6	42.0
80°	44.5	42.2	40.4	38.1	37.4	35.9	35.4	34.3	34.7	33.5	33.5
82.5°	34.5	31.7	30.1	29.1	28.3	27.1	26.7	26.2	26.3	25.4	25.4
85°	17.8	17.0	16.3	15.5	15.5	14.3	14.7	14.3	14.3	13.5	13.2
87.5°	7.1	7.2	7.2	8.0	8.6	8.5	8.3	7.9	7.7	7.9	7.7
90°	6.9	8.7	11.5	15.6	19.0	19.6	19.0	18.4	17.3	18.4	19.0
92.5°	20.7	26.2	39.2	57.5	73.8	74.8	63.2	50.2	43.1	38.3	34.6
95°	42.6	56.5	82.9	133.0	199.9	225.8	197.5	150.9	115.7	91.6	78.9
97.5°	60.5	76.1	109.5	179.3	290.2	385.4	404.2	352.1	288.1	225.8	184.2
100°	72.0	88.2	118.7	188.9	313.3	454.9	537.9	525.8	454.4	375.5	305.8
102.5°	82.6	98.7	126.9	189.3	304.6	457.3	587.6	639.6	623.5	565.8	491.9
105°	97.9	114.0	141.1	192.4	287.4	426.8	580.0	699.7	764.8	772.3	753.3
107.5°	113.1	129.4	155.6	200.3	278.8	394.0	529.4	656.4	754.5	814.4	842.2
110°	123.2	140.0	165.3	206.7	277.0	378.4	497.6	619.1	722.2	795.9	843.1



TEST NUMBER: P331653-840
 CATALOG NUMBER: SA2XXRDIP-C485D530U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	132.9	150.1	174.5	213.7	277.5	368.2	475.4	585.0	684.0	762.8	816.9
115°	148.6	164.1	188.9	224.0	279.9	357.1	448.1	543.1	631.8	707.2	766.6
117.5°	163.1	179.3	202.2	235.1	284.1	351.6	430.8	511.5	589.4	657.8	713.5
120°	172.8	188.9	211.4	242.5	286.8	348.4	421.6	495.8	567.2	628.3	680.8
122.5°	182.5	199.0	220.2	248.9	290.0	346.6	413.7	483.4	548.9	606.6	654.0
125°	196.4	212.5	233.3	259.1	294.9	343.3	402.5	465.3	524.6	575.3	618.5
127.5°	208.7	225.3	245.5	268.7	299.8	341.3	392.2	447.5	501.2	549.0	588.9
130°	216.5	232.7	252.9	274.7	303.5	340.3	385.3	436.0	485.5	531.0	569.0
132.5°	223.9	240.0	259.2	280.7	307.2	339.9	379.7	425.0	470.8	512.6	548.3
135°	233.8	249.9	268.4	288.5	311.5	339.2	372.0	409.5	447.5	485.5	517.8
137.5°	242.6	257.5	275.8	294.5	315.5	339.1	366.6	397.2	429.0	459.1	487.3
140°	247.6	262.7	279.9	297.7	317.3	338.6	363.5	389.3	417.0	443.4	468.8
142.5°	252.3	266.3	283.2	300.5	318.7	338.6	360.2	382.8	406.4	429.2	450.4
145°	259.7	272.4	287.9	304.1	320.2	337.5	355.9	373.8	392.7	410.6	427.4
147.5°	266.0	277.2	291.9	306.1	320.6	335.4	351.5	366.8	381.7	395.7	407.9
150°	270.1	280.4	293.7	307.0	320.2	334.1	347.9	361.6	374.4	386.5	396.8
152.5°	274.3	283.7	295.6	307.4	319.3	331.7	344.7	356.6	368.4	378.6	387.6
155°	279.9	288.5	298.3	308.1	317.9	327.7	338.6	349.6	358.8	367.4	373.8
157.5°	284.8	292.0	300.2	308.1	315.3	323.6	333.0	341.4	349.1	356.4	361.3
160°	287.9	294.3	301.2	308.1	313.9	320.8	328.8	336.3	342.6	349.0	353.0
162.5°	290.7	295.7	301.6	307.6	312.5	318.5	325.2	331.2	336.7	342.1	345.2
165°	293.7	297.2	302.4	306.4	309.8	313.9	319.0	323.7	327.7	331.7	334.1
167.5°	296.3	298.4	302.3	305.6	307.2	309.8	313.1	316.4	319.5	322.2	324.4
170°	297.2	298.9	301.7	304.7	305.8	307.5	309.8	312.8	314.5	316.8	317.9
172.5°	298.1	299.3	301.3	303.3	304.0	304.8	306.6	308.6	309.8	311.6	312.4
175°	298.9	299.4	300.6	301.7	301.2	301.7	302.4	304.1	304.7	305.3	305.8
177.5°	299.4	299.4	299.9	300.8	299.9	299.4	299.9	300.8	300.8	301.3	301.3
180°	299.4	299.4	299.4	299.4	299.4	299.4	299.4	299.4	299.4	299.4	299.4



TEST NUMBER: P331653-840

CATALOG NUMBER: SA2XXRDIP-C485D530U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4
2.5°	1042.2	1042.8	1041.9	1042.5	1041.9	1042.8	1042.2	1045.5	1046.1	1046.7	1046.1
5°	971.1	966.5	965.8	964.7	965.8	966.5	971.1	973.0	974.5	977.4	982.8
7.5°	886.2	885.4	883.6	880.9	883.6	885.4	886.2	892.6	897.8	903.6	914.4
10°	831.5	829.7	829.3	826.7	829.3	829.7	831.5	839.8	845.9	854.1	868.9
12.5°	767.6	755.5	754.2	747.6	754.2	755.5	767.6	778.3	794.6	802.5	818.2
15°	653.6	651.3	643.8	638.8	643.8	651.3	653.6	662.6	668.6	690.5	715.8
17.5°	588.3	581.0	578.7	577.6	578.7	581.0	588.3	592.8	601.4	612.9	628.1
20°	546.4	539.7	538.6	537.8	538.6	539.7	546.4	551.7	558.6	571.0	586.8
22.5°	517.5	510.4	507.5	505.2	507.5	510.4	517.5	521.6	527.8	537.5	548.2
25°	468.0	465.3	463.8	463.1	463.8	465.3	468.0	471.8	477.8	491.0	502.3
27.5°	429.3	423.5	422.3	420.4	422.3	423.5	429.3	436.1	442.3	448.3	458.4
30°	407.3	405.4	402.7	400.5	402.7	405.4	407.3	410.7	414.9	425.1	434.8
32.5°	381.3	379.8	377.4	376.4	377.4	379.8	381.3	386.0	394.7	400.9	408.0
35°	352.6	347.3	345.1	341.6	345.1	347.3	352.6	356.4	359.8	365.1	377.9
37.5°	322.2	319.4	316.3	317.4	316.3	319.4	322.2	323.8	330.9	338.3	343.9
40°	298.7	296.8	296.0	295.7	296.0	296.8	298.7	303.6	312.3	315.7	324.0
42.5°	279.9	274.8	272.8	272.8	272.8	274.8	279.9	285.5	290.8	296.3	305.0
45°	251.6	246.6	243.3	243.6	243.3	246.6	251.6	253.4	257.9	268.9	273.8
47.5°	222.5	222.3	220.2	220.9	220.2	222.3	222.5	225.7	231.5	238.2	246.0
50°	208.5	206.3	204.8	205.1	204.8	206.3	208.5	211.2	214.6	217.9	230.0
52.5°	195.3	193.3	192.1	193.7	192.1	193.3	195.3	196.7	199.1	202.6	210.8
55°	173.5	171.2	170.9	170.5	170.9	171.2	173.5	175.3	178.3	181.0	184.8
57.5°	149.2	147.6	145.3	144.4	145.3	147.6	149.2	151.9	155.5	159.0	162.9
60°	131.6	128.6	124.8	124.4	124.8	128.6	131.6	136.5	138.0	143.3	147.8
62.5°	115.6	115.0	114.3	114.2	114.3	115.0	115.6	117.2	119.4	127.0	132.5
65°	101.5	101.1	101.5	101.8	101.5	101.1	101.5	102.2	102.6	103.3	105.6
67.5°	88.4	87.8	87.1	87.4	87.1	87.8	88.4	88.6	89.6	90.1	91.6
70°	78.5	78.1	77.7	77.7	77.7	78.1	78.5	79.2	80.0	80.7	82.6
72.5°	68.8	68.7	68.4	68.1	68.4	68.7	68.8	70.2	70.6	71.4	72.6
75°	55.0	54.3	54.3	54.3	54.3	54.3	55.0	55.4	55.8	57.0	57.7
77.5°	41.9	41.6	41.2	40.9	41.2	41.6	41.9	42.0	42.6	42.8	43.6
80°	33.2	32.8	32.4	32.4	32.4	32.8	33.2	33.5	33.5	34.7	34.3
82.5°	25.3	24.9	24.8	24.5	24.8	24.9	25.3	25.4	25.4	26.3	26.2
85°	13.5	13.9	13.5	14.3	13.5	13.9	13.5	13.2	13.5	14.3	14.3
87.5°	7.7	7.4	7.7	7.4	7.7	7.4	7.7	7.7	7.9	7.7	7.9
90°	19.0	19.0	19.0	19.0	19.0	19.0	19.0	19.0	18.4	17.3	18.4
92.5°	34.2	32.4	32.8	31.9	32.8	32.4	34.2	34.6	38.3	43.1	50.2
95°	71.4	66.9	65.0	65.6	65.0	66.9	71.4	78.9	91.6	115.7	150.9
97.5°	156.6	142.5	134.1	129.3	134.1	142.5	156.6	184.2	225.8	288.1	352.1
100°	258.0	233.3	216.5	206.2	216.5	233.3	258.0	305.8	375.5	454.4	525.8
102.5°	440.0	397.7	376.9	362.8	376.9	397.7	440.0	491.9	565.8	623.5	639.6
105°	717.6	681.9	657.1	649.0	657.1	681.9	717.6	753.3	772.3	764.8	699.7
107.5°	846.7	844.8	839.8	829.1	839.8	844.8	846.7	842.2	814.4	754.5	656.4
110°	867.9	878.9	884.0	883.4	884.0	878.9	867.9	843.1	795.9	722.2	619.1



TEST NUMBER: P331653-840

CATALOG NUMBER: SA2XXRDIP-C485D530U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	851.3	869.6	879.4	882.5	879.4	869.6	851.3	816.9	762.8	684.0	585.0
115°	807.4	833.9	848.9	854.0	848.9	833.9	807.4	766.6	707.2	631.8	543.1
117.5°	755.2	783.2	798.9	803.2	798.9	783.2	755.2	713.5	657.8	589.4	511.5
120°	721.0	748.1	764.8	770.5	764.8	748.1	721.0	680.8	628.3	567.2	495.8
122.5°	690.1	716.8	731.6	736.5	731.6	716.8	690.1	654.0	606.6	548.9	483.4
125°	652.0	673.8	688.2	692.9	688.2	673.8	652.0	618.5	575.3	524.6	465.3
127.5°	617.9	638.4	650.9	654.6	650.9	638.4	617.9	588.9	549.0	501.2	447.5
130°	597.2	616.8	628.3	632.9	628.3	616.8	597.2	569.0	531.0	485.5	436.0
132.5°	576.0	595.6	606.2	610.4	606.2	595.6	576.0	548.3	512.6	470.8	425.0
135°	542.5	561.5	571.9	574.2	571.9	561.5	542.5	517.8	485.5	447.5	409.5
137.5°	509.8	526.1	535.2	538.7	535.2	526.1	509.8	487.3	459.1	429.0	397.2
140°	487.3	502.2	510.8	514.3	510.8	502.2	487.3	468.8	443.4	417.0	389.3
142.5°	467.9	481.5	489.2	489.9	489.2	481.5	467.9	450.4	429.2	406.4	382.8
145°	441.1	450.9	456.7	458.4	456.7	450.9	441.1	427.4	410.6	392.7	373.8
147.5°	419.3	427.1	431.0	432.0	431.0	427.1	419.3	407.9	395.7	381.7	366.8
150°	405.5	412.3	415.8	416.4	415.8	412.3	405.5	396.8	386.5	374.4	361.6
152.5°	394.4	400.4	402.9	403.0	402.9	400.4	394.4	387.6	378.6	368.4	356.6
155°	380.1	384.2	386.5	385.3	386.5	384.2	380.1	373.8	367.4	358.8	349.6
157.5°	365.8	369.2	370.2	370.2	370.2	369.2	365.8	361.3	356.4	349.1	341.4
160°	357.1	359.9	360.5	360.5	360.5	359.9	357.1	353.0	349.0	342.6	336.3
162.5°	349.2	351.2	351.7	351.3	351.7	351.2	349.2	345.2	342.1	336.7	331.2
165°	336.3	338.6	338.6	338.1	338.6	338.6	336.3	334.1	331.7	327.7	323.7
167.5°	325.4	326.7	326.6	325.9	326.6	326.7	325.4	324.4	322.2	319.5	316.4
170°	318.5	320.2	319.6	318.5	319.6	320.2	318.5	317.9	316.8	314.5	312.8
172.5°	313.0	313.8	313.2	312.5	313.2	313.8	313.0	312.4	311.6	309.8	308.6
175°	305.8	306.4	305.8	304.7	305.8	306.4	305.8	305.8	305.3	304.7	304.1
177.5°	301.3	301.3	300.8	299.9	300.8	301.3	301.3	301.3	301.3	300.8	300.8
180°	299.4	299.4	299.4	299.4	299.4	299.4	299.4	299.4	299.4	299.4	299.4



TEST NUMBER: P331653-840

CATALOG NUMBER: SA2XXRDIP-C485D530U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4
2.5°	1043.7	1047.9	1054.3	1057.9	1063.9	1067.8	1070.0	1073.9	1076.0	1083.6	1091.4
5°	985.4	991.5	1002.0	1011.8	1022.4	1033.3	1041.3	1050.3	1058.5	1072.9	1088.0
7.5°	918.6	927.0	943.3	959.0	977.3	992.8	1006.4	1021.9	1035.7	1056.2	1077.6
10°	868.5	883.2	904.7	919.4	943.5	959.0	980.5	997.4	1016.7	1043.9	1068.0
12.5°	825.4	843.1	860.4	880.8	902.5	928.3	951.9	973.6	996.5	1024.6	1052.9
15°	747.1	772.7	799.5	820.2	849.7	876.8	904.3	933.7	961.7	995.2	1032.2
17.5°	646.3	676.0	721.0	756.6	791.1	818.4	852.4	888.1	920.9	961.4	1002.5
20°	600.8	622.6	653.2	701.0	753.2	782.1	816.9	856.1	893.7	937.9	982.0
22.5°	564.2	583.7	608.2	645.5	703.7	743.3	779.4	819.3	863.0	908.1	956.9
25°	512.1	525.7	551.4	581.5	621.5	686.7	726.3	766.3	813.9	862.1	917.9
27.5°	473.0	485.2	501.9	530.7	560.4	607.2	670.2	713.8	761.1	815.5	873.4
30°	443.1	457.5	475.9	496.2	528.8	565.3	628.2	678.8	725.6	781.4	843.2
32.5°	421.4	432.7	448.5	469.2	496.1	531.2	581.5	642.9	688.4	747.3	811.8
35°	385.8	399.0	411.8	431.4	453.3	485.3	523.4	589.1	634.3	692.4	757.3
37.5°	356.5	364.6	378.7	394.3	417.3	441.2	474.2	533.1	582.1	639.0	705.5
40°	334.2	344.3	354.9	372.2	391.1	414.0	446.5	490.3	546.4	602.3	667.1
42.5°	312.5	325.3	336.5	348.1	368.7	391.7	418.2	455.2	512.6	565.4	628.5
45°	286.2	294.6	306.2	319.0	336.0	355.7	379.0	411.4	466.5	512.1	571.4
47.5°	255.8	267.9	275.5	288.0	304.2	322.9	344.6	372.6	417.3	460.0	514.9
50°	235.0	247.4	258.3	269.6	284.0	302.1	320.1	347.3	383.1	428.1	479.3
52.5°	217.1	228.1	238.7	250.0	264.1	280.6	297.8	321.6	352.3	393.6	443.4
55°	192.7	199.4	210.5	221.8	234.2	250.0	266.6	286.6	313.1	347.7	388.1
57.5°	167.6	175.5	184.2	195.6	208.1	220.4	235.2	253.4	274.2	305.6	340.1
60°	153.5	159.6	166.7	178.3	190.1	201.0	215.3	230.5	250.0	277.2	306.6
62.5°	137.8	143.5	150.1	160.3	171.7	181.7	194.2	210.3	226.8	251.6	277.3
65°	111.6	120.0	126.3	135.4	144.8	155.4	165.2	178.0	192.7	212.3	235.3
67.5°	92.5	96.7	102.7	111.0	120.6	129.7	139.0	149.0	161.7	176.8	195.1
70°	84.1	85.6	86.7	94.6	103.7	112.8	121.4	130.9	141.8	154.2	170.1
72.5°	74.1	75.6	77.1	80.5	87.8	96.7	105.7	112.8	123.1	133.4	146.2
75°	58.9	61.1	62.2	64.1	66.8	72.8	81.1	87.9	93.9	101.8	112.0
77.5°	44.8	46.0	47.3	49.3	50.9	53.7	58.4	64.5	70.2	74.7	81.8
80°	35.4	35.9	37.4	38.1	40.4	42.2	44.5	49.4	55.0	57.0	61.8
82.5°	26.7	27.1	28.3	29.1	30.1	31.7	34.5	35.9	40.3	42.7	45.8
85°	14.7	14.3	15.5	15.5	16.3	17.0	17.8	19.6	20.7	23.7	24.5
87.5°	8.3	8.5	8.6	8.0	7.2	7.2	7.1	7.2	7.6	8.0	8.9
90°	19.0	19.6	19.0	15.6	11.5	8.7	6.9	5.8	4.6	2.3	0.6
92.5°	63.2	74.8	73.8	57.5	39.2	26.2	20.7	16.9	14.2	10.1	7.1
95°	197.5	225.8	199.9	133.0	82.9	56.5	42.6	33.4	28.2	22.4	20.2
97.5°	404.2	385.4	290.2	179.3	109.5	76.1	60.5	49.9	42.0	36.0	32.8
100°	537.9	454.9	313.3	188.9	118.7	88.2	72.0	60.5	51.3	46.0	44.3
102.5°	587.6	457.3	304.6	189.3	126.9	98.7	82.6	70.6	61.4	56.2	54.9
105°	580.0	426.8	287.4	192.4	141.1	114.0	97.9	85.2	76.5	72.6	70.3
107.5°	529.4	394.0	278.8	200.3	155.6	129.4	113.1	100.6	92.6	88.7	86.8
110°	497.6	378.4	277.0	206.7	165.3	140.0	123.2	111.2	103.7	100.2	97.9



TEST NUMBER: P331653-840

CATALOG NUMBER: SA2XXRDIP-C485D530U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	475.4	368.2	277.5	213.7	174.5	150.1	132.9	121.3	114.2	110.4	108.1
115°	448.1	357.1	279.9	224.0	188.9	164.1	148.6	137.0	130.2	126.7	123.8
117.5°	430.8	351.6	284.1	235.1	202.2	179.3	163.1	152.1	145.9	142.5	140.2
120°	421.6	348.4	286.8	242.5	211.4	188.9	172.8	161.3	156.0	152.6	150.3
122.5°	413.7	346.6	290.0	248.9	220.2	199.0	182.5	171.0	165.3	161.9	160.0
125°	402.5	343.3	294.9	259.1	233.3	212.5	196.4	184.9	177.9	174.5	172.8
127.5°	392.2	341.3	299.8	268.7	245.5	225.3	208.7	197.6	190.1	185.2	182.9
130°	385.3	340.3	303.5	274.7	252.9	232.7	216.5	205.0	196.9	191.2	188.9
132.5°	379.7	339.9	307.2	280.7	259.2	240.0	223.9	212.0	203.4	197.2	194.4
135°	372.0	339.2	311.5	288.5	268.4	249.9	233.8	220.6	212.0	205.0	202.7
137.5°	366.6	339.1	315.5	294.5	275.8	257.5	242.6	229.4	220.3	213.3	210.6
140°	363.5	338.6	317.3	297.7	279.9	262.7	247.6	235.0	225.8	218.8	216.5
142.5°	360.2	338.6	318.7	300.5	283.2	266.3	252.3	240.0	230.9	224.4	222.6
145°	355.9	337.5	320.2	304.1	287.9	272.4	259.7	248.2	239.5	233.8	231.6
147.5°	351.5	335.4	320.6	306.1	291.9	277.2	266.0	256.4	248.4	242.9	241.2
150°	347.9	334.1	320.2	307.0	293.7	280.4	270.1	261.5	254.0	249.3	247.6
152.5°	344.7	331.7	319.3	307.4	295.6	283.7	274.3	266.1	259.5	254.9	254.1
155°	338.6	327.7	317.9	308.1	298.3	288.5	279.9	273.6	267.2	263.8	263.2
157.5°	333.0	323.6	315.3	308.1	300.2	292.0	284.8	279.6	274.2	271.4	270.7
160°	328.8	320.8	313.9	308.1	301.2	294.3	287.9	283.4	278.7	276.4	275.9
162.5°	325.2	318.5	312.5	307.6	301.6	295.7	290.7	286.6	282.9	280.5	280.9
165°	319.0	313.9	309.8	306.4	302.4	297.2	293.7	290.8	287.4	286.2	286.8
167.5°	313.1	309.8	307.2	305.6	302.3	298.4	296.3	294.2	292.0	290.9	291.6
170°	309.8	307.5	305.8	304.7	301.7	298.9	297.2	296.0	294.3	293.7	294.9
172.5°	306.6	304.8	304.0	303.3	301.3	299.3	298.1	297.4	295.7	296.0	296.7
175°	302.4	301.7	301.2	301.7	300.6	299.4	298.9	298.9	297.7	298.3	298.9
177.5°	299.9	299.4	299.9	300.8	299.9	299.4	299.4	299.4	298.5	299.0	299.9
180°	299.4	299.4	299.4	299.4	299.4	299.4	299.4	299.4	299.4	299.4	299.4



TEST NUMBER: P331653-840

CATALOG NUMBER: SA2XXRDIP-C485D530U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4
2.5°	1091.7	1092.6	1098.6	1101.4	1106.8	1108.9	1111.3	1110.6	1110.6	1111.9	1120.3
5°	1094.0	1101.6	1112.9	1123.8	1134.4	1143.5	1149.4	1155.5	1157.7	1168.7	1178.5
7.5°	1090.1	1104.0	1122.7	1139.3	1159.3	1175.0	1187.9	1199.6	1207.6	1223.6	1239.8
10°	1085.0	1104.6	1125.7	1147.2	1174.8	1195.5	1216.6	1232.8	1238.1	1261.8	1275.5
12.5°	1074.7	1101.0	1127.8	1155.7	1182.6	1211.1	1234.4	1250.6	1269.2	1290.5	1315.6
15°	1059.3	1089.5	1124.6	1160.4	1198.9	1233.6	1258.5	1286.8	1307.1	1330.5	1352.3
17.5°	1037.2	1076.1	1120.6	1162.2	1206.6	1243.9	1278.2	1305.3	1319.6	1332.9	1336.3
20°	1019.8	1061.6	1114.0	1163.1	1207.5	1250.5	1284.4	1307.1	1310.9	1311.2	1291.2
22.5°	1000.8	1048.0	1102.9	1153.1	1206.3	1254.2	1280.5	1290.2	1275.3	1249.7	1211.0
25°	965.8	1020.5	1084.2	1141.6	1199.6	1244.9	1253.9	1237.0	1184.6	1129.4	1059.8
27.5°	928.0	989.4	1057.7	1121.5	1183.4	1211.4	1191.8	1130.6	1036.2	954.2	854.7
30°	900.2	969.2	1036.3	1107.6	1164.9	1177.0	1132.2	1042.0	931.9	808.2	709.0
32.5°	868.5	940.8	1014.6	1088.3	1136.3	1124.5	1050.4	939.4	810.3	688.7	594.9
35°	823.2	898.0	977.4	1051.4	1082.0	1031.1	920.2	775.8	643.8	530.3	465.7
37.5°	771.0	852.3	935.0	1002.9	1000.8	915.8	764.9	615.7	504.8	437.7	391.7
40°	733.9	816.1	905.4	962.8	938.3	827.8	664.1	523.4	442.3	388.8	355.3
42.5°	698.3	780.8	869.6	915.1	872.5	736.7	573.6	463.4	396.5	354.8	327.5
45°	637.7	724.8	807.1	832.3	756.1	606.4	463.8	384.0	339.4	308.5	289.6
47.5°	578.6	664.2	739.2	739.7	636.6	491.8	391.3	332.2	294.3	270.3	256.6
50°	542.3	623.8	686.7	676.9	560.1	437.5	349.9	299.0	267.4	248.9	234.6
52.5°	501.6	580.6	635.1	607.2	495.1	385.0	312.9	270.1	243.9	227.8	215.0
55°	442.3	512.5	551.0	508.8	403.9	320.1	264.4	230.8	211.2	197.6	186.7
57.5°	384.3	442.0	466.3	417.1	332.6	265.5	223.6	198.4	178.9	169.3	163.6
60°	347.7	397.1	414.0	359.8	289.2	232.3	198.0	174.6	160.3	153.9	148.2
62.5°	311.8	352.1	359.2	309.4	252.2	203.4	173.9	154.1	144.6	138.5	133.1
65°	258.7	287.7	284.4	244.4	199.4	161.4	139.9	127.8	120.7	112.0	102.6
67.5°	213.0	230.8	220.0	190.1	152.3	125.4	111.4	102.3	93.4	85.1	83.0
70°	184.0	194.2	182.9	155.4	124.8	105.2	93.9	83.0	77.7	75.8	72.4
72.5°	156.3	159.9	147.6	124.0	101.6	87.2	76.1	70.0	67.2	65.5	63.3
75°	117.2	114.6	104.1	85.6	70.5	60.7	57.4	55.0	53.2	51.7	50.5
77.5°	82.4	78.5	69.1	57.1	49.1	44.4	42.4	41.2	40.3	39.5	38.4
80°	61.8	59.2	49.8	40.7	37.4	35.0	33.9	32.4	32.4	31.7	30.5
82.5°	45.2	42.3	34.1	29.9	28.0	26.7	25.8	24.8	24.5	24.7	23.9
85°	23.7	19.2	17.0	16.3	15.0	14.3	14.7	13.9	13.9	13.9	13.5
87.5°	7.7	6.7	6.6	6.5	7.2	7.8	8.3	8.9	9.4	8.9	9.1
90°	2.3	4.6	5.8	6.9	8.7	11.5	15.6	19.0	19.6	19.0	18.4
92.5°	10.1	14.2	16.9	20.7	26.2	39.2	57.5	73.8	74.8	63.2	50.2
95°	22.4	28.2	33.4	42.6	56.5	82.9	133.0	199.9	225.8	197.5	150.9
97.5°	36.0	42.0	49.9	60.5	76.1	109.5	179.3	290.2	385.4	404.2	352.1
100°	46.0	51.3	60.5	72.0	88.2	118.7	188.9	313.3	454.9	537.9	525.8
102.5°	56.2	61.4	70.6	82.6	98.7	126.9	189.3	304.6	457.3	587.6	639.6
105°	72.6	76.5	85.2	97.9	114.0	141.1	192.4	287.4	426.8	580.0	699.7
107.5°	88.7	92.6	100.6	113.1	129.4	155.6	200.3	278.8	394.0	529.4	656.4
110°	100.2	103.7	111.2	123.2	140.0	165.3	206.7	277.0	378.4	497.6	619.1



TEST NUMBER: P331653-840

CATALOG NUMBER: SA2XXRDIP-C485D530U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	110.4	114.2	121.3	132.9	150.1	174.5	213.7	277.5	368.2	475.4	585.0
115°	126.7	130.2	137.0	148.6	164.1	188.9	224.0	279.9	357.1	448.1	543.1
117.5°	142.5	145.9	152.1	163.1	179.3	202.2	235.1	284.1	351.6	430.8	511.5
120°	152.6	156.0	161.3	172.8	188.9	211.4	242.5	286.8	348.4	421.6	495.8
122.5°	161.9	165.3	171.0	182.5	199.0	220.2	248.9	290.0	346.6	413.7	483.4
125°	174.5	177.9	184.9	196.4	212.5	233.3	259.1	294.9	343.3	402.5	465.3
127.5°	185.2	190.1	197.6	208.7	225.3	245.5	268.7	299.8	341.3	392.2	447.5
130°	191.2	196.9	205.0	216.5	232.7	252.9	274.7	303.5	340.3	385.3	436.0
132.5°	197.2	203.4	212.0	223.9	240.0	259.2	280.7	307.2	339.9	379.7	425.0
135°	205.0	212.0	220.6	233.8	249.9	268.4	288.5	311.5	339.2	372.0	409.5
137.5°	213.3	220.3	229.4	242.6	257.5	275.8	294.5	315.5	339.1	366.6	397.2
140°	218.8	225.8	235.0	247.6	262.7	279.9	297.7	317.3	338.6	363.5	389.3
142.5°	224.4	230.9	240.0	252.3	266.3	283.2	300.5	318.7	338.6	360.2	382.8
145°	233.8	239.5	248.2	259.7	272.4	287.9	304.1	320.2	337.5	355.9	373.8
147.5°	242.9	248.4	256.4	266.0	277.2	291.9	306.1	320.6	335.4	351.5	366.8
150°	249.3	254.0	261.5	270.1	280.4	293.7	307.0	320.2	334.1	347.9	361.6
152.5°	254.9	259.5	266.1	274.3	283.7	295.6	307.4	319.3	331.7	344.7	356.6
155°	263.8	267.2	273.6	279.9	288.5	298.3	308.1	317.9	327.7	338.6	349.6
157.5°	271.4	274.2	279.6	284.8	292.0	300.2	308.1	315.3	323.6	333.0	341.4
160°	276.4	278.7	283.4	287.9	294.3	301.2	308.1	313.9	320.8	328.8	336.3
162.5°	280.5	282.9	286.6	290.7	295.7	301.6	307.6	312.5	318.5	325.2	331.2
165°	286.2	287.4	290.8	293.7	297.2	302.4	306.4	309.8	313.9	319.0	323.7
167.5°	290.9	292.0	294.2	296.3	298.4	302.3	305.6	307.2	309.8	313.1	316.4
170°	293.7	294.3	296.0	297.2	298.9	301.7	304.7	305.8	307.5	309.8	312.8
172.5°	296.0	295.7	297.4	298.1	299.3	301.3	303.3	304.0	304.8	306.6	308.6
175°	298.3	297.7	298.9	298.9	299.4	300.6	301.7	301.2	301.7	302.4	304.1
177.5°	299.0	298.5	299.4	299.4	299.4	299.9	300.8	299.9	299.4	299.9	300.8
180°	299.4	299.4	299.4	299.4	299.4	299.4	299.4	299.4	299.4	299.4	299.4



TEST NUMBER: P331653-840
 CATALOG NUMBER: SA2XXRDIP-C485D530U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4	1085.4
2.5°	1123.4	1127.3	1129.1	1129.1	1131.3	1130.3	1129.4
5°	1187.9	1195.1	1196.6	1203.4	1208.3	1206.8	1207.5
7.5°	1252.1	1263.6	1275.1	1280.2	1281.1	1284.1	1285.3
10°	1291.6	1301.1	1318.8	1316.2	1329.4	1336.9	1324.4
12.5°	1329.7	1342.4	1354.7	1358.1	1365.5	1368.0	1363.0
15°	1364.0	1370.8	1371.6	1369.7	1372.0	1370.1	1362.9
17.5°	1331.9	1320.9	1298.6	1288.0	1279.6	1267.3	1262.3
20°	1278.8	1246.4	1208.7	1193.6	1175.9	1141.1	1149.4
22.5°	1164.2	1127.2	1089.5	1045.4	1024.4	991.5	989.6
25°	985.8	922.1	851.9	802.8	774.3	741.4	727.1
27.5°	766.5	686.2	628.7	599.7	573.1	547.1	546.0
30°	622.3	561.9	517.5	492.5	476.4	465.3	467.7
32.5°	524.5	483.1	453.1	432.5	420.5	412.2	412.1
35°	428.8	400.5	381.2	372.6	364.0	357.9	358.3
37.5°	367.0	349.9	339.2	329.7	324.3	321.3	319.6
40°	335.3	321.3	313.1	307.4	302.9	298.7	297.9
42.5°	310.2	298.7	290.3	285.9	281.8	278.7	278.0
45°	275.3	265.9	258.3	253.4	251.6	248.9	248.9
47.5°	244.9	235.6	229.7	226.6	223.4	221.7	221.6
50°	224.4	217.2	212.0	210.1	207.4	206.3	205.9
52.5°	206.0	200.7	196.8	195.6	194.4	193.0	193.2
55°	181.0	178.0	176.5	175.3	173.5	171.2	172.7
57.5°	160.0	157.4	153.3	149.8	148.0	146.4	147.0
60°	145.2	139.9	134.6	130.5	129.4	125.9	125.9
62.5°	126.5	119.1	112.6	110.3	109.2	107.6	107.2
65°	97.3	94.3	92.8	91.3	90.5	90.5	89.8
67.5°	80.6	79.4	77.8	77.4	76.6	76.4	76.1
70°	71.3	69.8	69.0	68.7	67.9	68.3	67.2
72.5°	62.2	61.0	60.9	59.9	59.5	59.5	58.7
75°	49.0	49.0	48.7	48.3	47.6	47.2	47.6
77.5°	37.7	37.8	37.1	37.1	37.0	37.1	36.7
80°	30.2	30.5	30.2	29.8	29.4	29.8	29.4
82.5°	23.8	23.3	23.2	23.1	23.1	22.8	22.8
85°	13.5	13.9	13.5	13.2	13.2	13.2	13.5
87.5°	8.6	8.8	8.9	8.9	8.9	8.9	8.6
90°	17.3	18.4	19.0	19.0	19.0	19.0	19.0
92.5°	43.1	38.3	34.6	34.2	32.4	32.8	31.9
95°	115.7	91.6	78.9	71.4	66.9	65.0	65.6
97.5°	288.1	225.8	184.2	156.6	142.5	134.1	129.3
100°	454.4	375.5	305.8	258.0	233.3	216.5	206.2
102.5°	623.5	565.8	491.9	440.0	397.7	376.9	362.8
105°	764.8	772.3	753.3	717.6	681.9	657.1	649.0
107.5°	754.5	814.4	842.2	846.7	844.8	839.8	829.1
110°	722.2	795.9	843.1	867.9	878.9	884.0	883.4



TEST NUMBER: P331653-840

CATALOG NUMBER: SA2XXRDIP-C485D530U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	684.0	762.8	816.9	851.3	869.6	879.4	882.5
115°	631.8	707.2	766.6	807.4	833.9	848.9	854.0
117.5°	589.4	657.8	713.5	755.2	783.2	798.9	803.2
120°	567.2	628.3	680.8	721.0	748.1	764.8	770.5
122.5°	548.9	606.6	654.0	690.1	716.8	731.6	736.5
125°	524.6	575.3	618.5	652.0	673.8	688.2	692.9
127.5°	501.2	549.0	588.9	617.9	638.4	650.9	654.6
130°	485.5	531.0	569.0	597.2	616.8	628.3	632.9
132.5°	470.8	512.6	548.3	576.0	595.6	606.2	610.4
135°	447.5	485.5	517.8	542.5	561.5	571.9	574.2
137.5°	429.0	459.1	487.3	509.8	526.1	535.2	538.7
140°	417.0	443.4	468.8	487.3	502.2	510.8	514.3
142.5°	406.4	429.2	450.4	467.9	481.5	489.2	489.9
145°	392.7	410.6	427.4	441.1	450.9	456.7	458.4
147.5°	381.7	395.7	407.9	419.3	427.1	431.0	432.0
150°	374.4	386.5	396.8	405.5	412.3	415.8	416.4
152.5°	368.4	378.6	387.6	394.4	400.4	402.9	403.0
155°	358.8	367.4	373.8	380.1	384.2	386.5	385.3
157.5°	349.1	356.4	361.3	365.8	369.2	370.2	370.2
160°	342.6	349.0	353.0	357.1	359.9	360.5	360.5
162.5°	336.7	342.1	345.2	349.2	351.2	351.7	351.3
165°	327.7	331.7	334.1	336.3	338.6	338.6	338.1
167.5°	319.5	322.2	324.4	325.4	326.7	326.6	325.9
170°	314.5	316.8	317.9	318.5	320.2	319.6	318.5
172.5°	309.8	311.6	312.4	313.0	313.8	313.2	312.5
175°	304.7	305.3	305.8	305.8	306.4	305.8	304.7
177.5°	300.8	301.3	301.3	301.3	301.3	300.8	299.9
180°	299.4	299.4	299.4	299.4	299.4	299.4	299.4

(END OF REPORT)