

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331349

Luminaire Tested: **SA2XXDIP-C675D725U835-4F0-1E-UDD-A1**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331349  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXDIP-C675D725U835-4F0-1E-UDD-A1  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 725 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5524.1 lumens  
Efficiency: N/A  
Efficacy: 120.4 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 45.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331349

CATALOG NUMBER: SA2XXDIP-C675D725U835-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P331349

CATALOG NUMBER: SA2XXDIP-C675D725U835-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	53
1	99	95	91	88	92	88	85	82	75	73	71	64	62	61	53	52	51	46
2	91	83	77	73	84	78	72	68	67	63	60	57	54	51	47	45	44	39
3	83	74	67	61	77	69	63	57	59	55	51	50	47	44	42	40	38	34
4	76	66	58	52	70	61	54	49	53	48	44	45	41	38	38	35	33	29
5	70	59	51	45	65	55	48	43	48	42	38	41	37	33	35	31	29	26
6	65	53	45	39	60	50	42	37	43	38	33	37	33	30	32	28	26	23
7	60	48	40	35	56	45	38	33	39	34	30	34	30	26	29	26	23	21
8	56	44	36	31	52	41	34	29	36	30	27	31	27	24	27	23	21	19
9	52	40	33	28	48	38	31	26	33	28	24	29	25	21	25	21	19	17
10	49	37	30	25	45	35	28	24	31	25	22	27	23	20	23	20	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	21447	21447	21447	21447
5°	24044	21585	19128	21585
10°	27552	21408	16554	21408
15°	30479	21016	14626	21016
20°	30015	20594	13332	20594
25°	27064	20035	12513	20035
30°	22365	19140	11915	19140
35°	16301	18203	11491	18203
40°	13019	17098	11255	17098
45°	11376	15817	10933	15817
50°	10693	14579	10721	14579
55°	9858	13320	10432	13320
60°	9032	11983	9991	11983
65°	8229	10785	9555	10785
70°	7468	9616	8917	9616
75°	6625	8309	7898	8309
80°	5700	6881	6360	6881
85°	5113	5113	3779	5113



TEST NUMBER: P331349

CATALOG NUMBER: SA2XXDIP-C675D725U835-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	126.5	2.3
10°-20°	367.8	6.7
20°-30°	533.7	9.7
30°-40°	563.2	10.2
40°-50°	498.7	9.0
50°-60°	398.0	7.2
60°-70°	270.5	4.9
70°-80°	138.7	2.5
80°-90°	37.1	0.7
90°-100°	58.7	1.1
100°-110°	182.3	3.3
110°-120°	311.6	5.6
120°-130°	409.8	7.4
130°-140°	459.9	8.3
140°-150°	450.9	8.2
150°-160°	378.2	6.8
160°-170°	250.9	4.5
170°-180°	87.7	1.6
0°-30°	1028.0	18.6
0°-40°	1591.2	28.8
0°-60°	2487.8	45.0
0°-90°	2934.1	53.1
90°-120°	552.6	10.0
90°-150°	1873.2	33.9
90°-180°	2590.0	46.9
0°-180°	5524.1	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1328	1328	1328	1328	1328	
5°	1484	1332	1180	1332	1484	148
15°	1823	1257	875	1257	1823	503
25°	1519	1125	702	1125	1519	687
35°	827	924	583	924	827	538
45°	498	693	479	693	498	392
55°	350	473	371	473	350	314
65°	215	282	250	282	215	214
75°	106	133	127	133	106	113
85°	28	28	20	28	28	31
90°	27	1	27	1	27	13
95°	48	41	48	41	48	54
105°	174	168	174	168	174	182
115°	313	313	313	313	313	309
125°	456	455	456	455	456	407
135°	596	589	596	589	596	458
145°	722	714	722	714	722	451
155°	823	817	823	817	823	379
165°	890	889	890	889	890	251
175°	922	925	922	925	922	88
180°	926	926	926	926	926	



TEST NUMBER: P331349

CATALOG NUMBER: SA2XXDIP-C675D725U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3
2.5°	1389.5	1389.9	1390.8	1384.2	1383.4	1383.4	1377.7	1372.8	1367.1	1359.3	1360.1
5°	1483.5	1489.1	1491.1	1485.0	1475.8	1474.8	1466.1	1451.8	1438.5	1427.8	1420.2
7.5°	1595.6	1597.8	1592.8	1584.7	1577.9	1565.7	1549.5	1533.7	1511.5	1491.2	1476.1
10°	1680.5	1683.6	1674.9	1663.2	1653.5	1639.2	1615.7	1591.7	1562.6	1534.5	1512.0
12.5°	1745.0	1752.6	1741.5	1739.9	1723.3	1703.7	1675.7	1663.6	1622.6	1583.5	1559.4
15°	1823.4	1822.9	1824.0	1814.3	1802.0	1798.9	1769.3	1737.2	1679.5	1656.5	1616.7
17.5°	1800.8	1808.5	1812.1	1812.0	1811.7	1809.8	1800.3	1780.0	1751.1	1713.8	1667.8
20°	1746.9	1757.1	1758.6	1770.4	1777.0	1785.7	1789.2	1783.6	1765.8	1734.6	1694.8
22.5°	1663.6	1666.4	1671.2	1689.5	1703.9	1725.6	1737.0	1755.9	1749.0	1733.8	1700.5
25°	1519.2	1514.1	1532.0	1541.1	1574.3	1609.0	1634.1	1661.6	1686.1	1700.9	1691.2
27.5°	1345.8	1338.2	1364.9	1389.3	1416.3	1453.9	1492.9	1538.9	1577.2	1625.1	1641.5
30°	1199.6	1204.2	1229.8	1255.8	1296.6	1349.7	1393.6	1444.2	1498.8	1552.4	1589.6
32.5°	1042.0	1059.7	1075.8	1115.7	1151.6	1210.9	1275.2	1338.4	1406.5	1467.4	1525.1
35°	827.0	847.4	869.9	899.0	949.5	1008.2	1071.0	1156.2	1249.2	1332.4	1400.8
37.5°	696.1	692.8	705.7	726.7	767.7	815.0	887.3	971.6	1080.9	1178.7	1275.2
40°	617.7	615.6	624.8	644.2	675.4	710.1	773.4	847.4	949.0	1068.4	1183.3
42.5°	563.8	565.0	570.1	583.8	605.1	633.7	681.1	744.1	837.1	949.6	1073.0
45°	498.2	501.8	507.4	514.1	526.3	549.8	576.3	621.3	694.8	788.7	910.2
47.5°	451.1	451.2	456.9	462.7	470.0	483.2	504.9	533.0	584.9	661.4	765.8
50°	425.7	422.2	426.3	430.8	438.5	447.7	462.0	488.5	523.2	585.0	672.3
52.5°	394.7	394.8	398.5	400.2	407.1	416.2	429.3	447.7	479.1	527.4	599.2
55°	350.2	352.7	354.8	357.8	364.0	370.6	380.8	393.1	417.6	453.8	506.9
57.5°	308.3	309.1	311.2	317.0	320.9	327.0	336.7	347.8	363.8	390.6	430.5
60°	279.7	279.7	283.8	286.4	291.5	297.6	305.3	316.0	330.3	352.2	384.4
62.5°	253.6	253.2	254.8	259.0	262.9	268.6	276.3	285.4	298.8	318.3	344.8
65°	215.4	214.4	217.5	218.5	222.6	228.2	234.3	244.0	254.7	269.0	292.5
67.5°	178.7	179.9	181.5	183.5	185.7	191.6	195.7	202.6	211.6	223.5	239.4
70°	158.2	158.2	158.2	159.8	162.8	165.9	170.0	175.6	184.3	194.5	208.8
72.5°	135.4	137.0	138.6	137.7	141.6	143.4	148.3	151.5	159.8	166.3	179.0
75°	106.2	106.2	106.2	108.7	110.3	111.8	114.9	117.9	122.0	130.2	136.8
77.5°	79.2	79.0	79.5	80.1	81.8	83.6	84.5	87.3	91.1	94.8	100.5
80°	61.3	62.3	62.8	63.8	63.8	64.8	65.3	68.9	71.5	74.0	77.6
82.5°	47.4	47.6	47.7	47.9	48.3	48.9	50.2	51.4	52.3	54.4	57.2
85°	27.6	27.1	27.1	28.1	27.6	27.6	28.6	29.6	29.6	30.1	31.6
87.5°	15.9	15.9	16.3	15.8	15.8	16.2	16.3	16.0	16.4	16.9	16.6
90°	26.6	26.4	26.2	26.1	25.9	26.0	26.3	26.7	27.0	27.4	23.5
92.5°	25.3	25.3	25.3	25.2	25.2	25.1	25.1	25.0	24.9	24.9	24.0
95°	48.5	48.8	49.2	49.5	49.9	50.0	50.0	50.0	50.0	50.0	49.7
97.5°	83.9	84.0	84.0	84.1	84.1	84.1	84.1	84.1	84.1	84.1	83.4
100°	107.1	107.3	107.4	107.6	107.8	107.9	107.9	107.9	107.9	107.9	107.3
102.5°	133.3	133.5	133.7	133.9	134.0	134.1	133.9	133.8	133.6	133.5	132.8
105°	173.5	173.5	173.5	173.5	173.5	173.4	173.0	172.7	172.3	172.0	171.6
107.5°	211.4	212.2	213.0	213.8	214.6	214.9	214.7	214.6	214.5	214.3	214.3
110°	240.7	241.3	241.8	242.3	242.8	243.1	243.1	243.1	243.1	243.1	243.1



TEST NUMBER: P331349

CATALOG NUMBER: SA2XXDIP-C675D725U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	268.9	269.3	269.6	270.0	270.4	270.8	271.2	271.6	272.1	272.5	272.6
115°	312.7	313.2	313.7	314.2	314.7	315.1	315.3	315.4	315.6	315.8	316.1
117.5°	354.4	354.9	355.4	356.0	356.5	356.9	357.4	357.8	358.2	358.6	359.6
120°	383.8	384.3	384.8	385.3	385.9	386.1	386.1	386.1	386.1	386.1	387.5
122.5°	412.6	412.9	413.3	413.7	414.1	414.5	414.9	415.3	415.7	416.1	417.1
125°	456.5	456.7	456.8	457.0	457.2	457.5	458.0	458.6	459.1	459.6	460.1
127.5°	496.5	497.1	497.6	498.2	498.7	499.3	499.9	500.6	501.2	501.8	502.4
130°	525.3	526.0	526.7	527.3	528.0	528.6	528.9	529.3	529.6	530.0	530.3
132.5°	552.8	553.3	553.9	554.4	555.0	555.7	556.4	557.2	558.0	558.7	558.6
135°	595.6	596.1	596.7	597.2	597.7	598.0	598.2	598.4	598.6	598.7	598.4
137.5°	634.4	635.1	635.8	636.5	637.2	637.6	637.7	637.9	638.0	638.1	637.7
140°	661.3	662.0	662.7	663.4	664.0	664.4	664.4	664.4	664.4	664.4	663.5
142.5°	685.7	686.4	687.0	687.7	688.4	688.7	688.6	688.4	688.3	688.2	687.6
145°	722.2	722.9	723.6	724.3	725.0	725.3	725.1	724.9	724.8	724.6	723.5
147.5°	754.9	755.6	756.2	756.9	757.6	757.7	757.3	756.9	756.5	756.2	755.5
150°	776.2	776.7	777.2	777.7	778.3	778.3	777.7	777.2	776.7	776.2	775.5
152.5°	796.2	796.8	797.5	798.2	798.8	798.8	798.2	797.5	796.8	796.2	795.3
155°	823.1	823.6	824.1	824.6	825.2	825.0	824.1	823.2	822.4	821.5	821.0
157.5°	846.2	847.0	847.9	848.7	849.5	849.4	848.2	847.0	845.8	844.6	844.3
160°	860.6	861.3	862.0	862.7	863.4	863.2	862.2	861.1	860.1	859.0	858.9
162.5°	873.1	873.9	874.8	875.6	876.4	876.3	875.1	873.9	872.7	871.5	871.4
165°	889.5	890.4	891.2	892.1	893.0	892.8	891.6	890.4	889.2	887.9	887.9
167.5°	903.0	903.9	904.8	905.7	906.6	906.4	905.2	904.0	902.8	901.5	901.6
170°	909.8	910.9	911.9	913.0	914.0	913.9	912.7	911.5	910.3	909.0	909.2
172.5°	915.5	916.5	917.5	918.6	919.6	919.5	918.3	917.1	915.9	914.7	914.9
175°	921.6	922.6	923.6	924.7	925.7	925.6	924.4	923.2	922.0	920.8	921.1
177.5°	924.4	925.2	926.0	926.9	927.7	927.7	926.9	926.0	925.2	924.4	924.6
180°	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2



TEST NUMBER: P331349

CATALOG NUMBER: SA2XXDIP-C675D725U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3
2.5°	1363.0	1359.7	1357.7	1350.3	1343.8	1337.3	1335.2	1336.0	1327.1	1318.5	1314.8
5°	1416.1	1405.9	1396.2	1382.4	1366.1	1348.2	1339.0	1331.8	1314.0	1294.6	1283.4
7.5°	1463.7	1449.1	1430.4	1404.4	1380.7	1352.6	1334.7	1318.9	1292.7	1265.4	1248.6
10°	1492.7	1472.7	1448.7	1417.1	1388.0	1353.8	1329.8	1305.8	1275.2	1242.5	1222.1
12.5°	1517.6	1490.7	1467.1	1426.5	1392.1	1349.3	1320.8	1287.0	1254.8	1216.0	1196.0
15°	1576.9	1527.4	1482.4	1436.5	1394.1	1334.4	1302.8	1257.3	1214.9	1167.0	1144.0
17.5°	1622.7	1567.1	1496.3	1437.9	1388.5	1322.4	1275.9	1221.5	1171.4	1116.5	1085.3
20°	1648.9	1585.0	1509.0	1439.6	1380.3	1304.8	1254.3	1198.6	1139.9	1078.1	1044.4
22.5°	1664.4	1597.3	1522.1	1433.4	1364.0	1290.5	1226.9	1165.9	1106.4	1039.8	1004.4
25°	1669.3	1608.0	1528.4	1428.3	1343.6	1260.4	1183.8	1124.6	1052.6	990.3	938.8
27.5°	1645.0	1601.1	1524.5	1418.7	1320.0	1222.7	1137.4	1070.3	994.3	926.7	874.9
30°	1615.2	1589.6	1515.1	1408.9	1301.2	1196.6	1102.6	1026.6	951.0	882.6	829.5
32.5°	1569.0	1563.5	1498.0	1395.0	1281.2	1163.5	1066.3	989.4	905.7	838.5	787.9
35°	1478.4	1502.9	1461.5	1364.0	1243.5	1116.4	1011.3	923.5	836.7	772.4	724.9
37.5°	1356.9	1417.7	1406.9	1318.6	1192.7	1065.2	949.1	857.3	774.6	709.7	663.1
40°	1273.1	1350.7	1362.0	1283.9	1156.8	1025.6	902.5	811.2	730.5	671.3	624.3
42.5°	1183.3	1274.0	1304.8	1242.2	1117.5	983.9	860.9	766.2	686.4	628.8	587.2
45°	1032.7	1152.7	1208.3	1172.6	1052.1	915.3	788.7	692.7	620.2	566.1	534.0
47.5°	891.9	1023.0	1097.8	1085.2	979.3	843.8	718.7	626.6	556.0	512.8	484.0
50°	792.3	927.0	1017.4	1021.5	927.0	792.8	667.2	580.4	515.6	475.3	451.8
52.5°	705.7	834.3	932.9	954.5	868.6	739.7	621.1	534.7	477.6	440.5	419.5
55°	592.7	701.4	810.6	850.5	781.5	659.0	549.3	473.2	419.6	394.1	375.7
57.5°	492.7	583.4	684.3	728.3	685.8	580.9	478.0	412.0	368.5	346.1	332.0
60°	440.0	511.5	601.3	653.9	617.2	523.8	433.9	371.1	335.4	315.5	302.2
62.5°	391.0	454.3	530.3	578.4	558.4	470.3	389.8	334.4	303.5	284.8	275.3
65°	322.6	372.7	431.4	475.8	462.5	395.6	329.8	282.3	257.8	243.0	235.3
67.5°	265.7	301.8	342.5	381.4	370.7	323.3	270.5	233.5	215.2	202.5	197.9
70°	229.7	257.3	293.5	324.7	316.0	277.2	235.3	203.7	187.9	177.1	172.5
72.5°	195.4	218.1	245.7	271.2	265.3	233.1	198.2	174.3	162.1	152.2	148.4
75°	147.5	164.9	181.7	198.6	197.0	172.0	151.6	133.2	123.5	115.9	114.3
77.5°	108.9	118.6	130.1	140.1	137.3	123.0	107.0	96.5	89.3	84.2	83.4
80°	83.2	88.8	97.0	104.1	100.6	94.4	81.7	74.0	68.9	63.8	61.8
82.5°	60.3	66.0	70.9	74.7	72.0	66.3	58.4	53.2	50.1	46.7	45.8
85°	31.6	34.7	36.8	37.8	36.8	33.2	29.6	27.6	25.0	23.5	23.0
87.5°	16.2	15.4	14.7	14.9	13.3	12.8	10.8	9.1	9.1	9.2	8.8
90°	19.7	15.9	12.1	9.1	7.0	5.0	2.9	0.8	2.9	5.0	7.0
92.5°	23.0	22.1	21.2	20.0	18.5	17.0	15.4	13.9	15.4	17.0	18.5
95°	49.3	49.0	48.6	47.6	45.9	44.1	42.4	40.6	42.4	44.1	45.9
97.5°	82.8	82.1	81.5	80.4	78.8	77.3	75.8	74.3	75.8	77.3	78.8
100°	106.8	106.3	105.8	104.8	103.4	102.0	100.7	99.3	100.7	102.0	103.4
102.5°	132.2	131.5	130.9	130.0	128.9	127.8	126.6	125.5	126.6	127.8	128.9
105°	171.3	170.9	170.6	170.1	169.6	169.1	168.6	168.1	168.6	169.1	169.6
107.5°	214.3	214.3	214.3	213.9	213.2	212.4	211.7	210.9	211.7	212.4	213.2
110°	243.1	243.1	243.1	242.6	241.5	240.5	239.4	238.4	239.4	240.5	241.5





TEST NUMBER: P331349

CATALOG NUMBER: SA2XXDIP-C675D725U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	272.8	272.9	273.0	272.6	271.5	270.5	269.5	268.4	269.5	270.5	271.5
115°	316.5	316.8	317.2	316.8	315.8	314.7	313.7	312.7	313.7	314.7	315.8
117.5°	360.6	361.5	362.5	362.3	360.9	359.5	358.1	356.7	358.1	359.5	360.9
120°	388.9	390.3	391.7	391.7	390.3	388.9	387.5	386.1	387.5	388.9	390.3
122.5°	418.1	419.1	420.0	419.7	418.0	416.4	414.7	413.0	414.7	416.4	418.0
125°	460.6	461.2	461.7	461.2	459.6	458.0	456.5	454.9	456.5	458.0	459.6
127.5°	503.1	503.7	504.3	503.6	501.7	499.7	497.7	495.7	497.7	499.7	501.7
130°	530.6	531.0	531.3	530.4	528.1	525.9	523.6	521.4	523.6	525.9	528.1
132.5°	558.6	558.5	558.4	557.5	555.6	553.8	552.0	550.1	552.0	553.8	555.6
135°	598.0	597.7	597.3	596.2	594.3	592.4	590.5	588.6	590.5	592.4	594.3
137.5°	637.2	636.8	636.3	635.3	633.8	632.2	630.6	629.1	630.6	632.2	633.8
140°	662.7	661.8	660.9	659.7	658.1	656.6	655.0	653.5	655.0	656.6	658.1
142.5°	687.0	686.4	685.8	684.7	683.2	681.6	680.0	678.5	680.0	681.6	683.2
145°	722.5	721.5	720.4	719.3	718.1	716.9	715.6	714.4	715.6	716.9	718.1
147.5°	754.8	754.1	753.4	752.3	750.8	749.4	747.9	746.5	747.9	749.4	750.8
150°	774.8	774.1	773.4	772.5	771.5	770.4	769.4	768.4	769.4	770.4	771.5
152.5°	794.5	793.7	792.8	791.9	790.9	789.8	788.8	787.7	788.8	789.8	790.9
155°	820.5	819.9	819.4	818.9	818.4	817.9	817.3	816.8	817.3	817.9	818.4
157.5°	844.0	843.7	843.4	843.1	842.7	842.4	842.0	841.7	842.0	842.4	842.7
160°	858.7	858.5	858.3	858.1	857.7	857.4	857.0	856.7	857.0	857.4	857.7
162.5°	871.2	871.0	870.8	870.7	870.6	870.6	870.5	870.4	870.5	870.6	870.6
165°	887.9	887.9	887.9	888.0	888.2	888.4	888.6	888.7	888.6	888.4	888.2
167.5°	901.6	901.7	901.7	902.0	902.5	903.0	903.5	904.0	903.5	903.0	902.5
170°	909.4	909.6	909.7	910.1	910.6	911.1	911.7	912.2	911.7	911.1	910.6
172.5°	915.0	915.2	915.4	915.7	916.2	916.8	917.3	917.8	917.3	916.8	916.2
175°	921.5	921.8	922.2	922.6	923.1	923.6	924.2	924.7	924.2	923.6	923.1
177.5°	924.9	925.2	925.5	925.8	926.2	926.7	927.1	927.5	927.1	926.7	926.2
180°	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2



TEST NUMBER: P331349

CATALOG NUMBER: SA2XXDIP-C675D725U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3
2.5°	1310.7	1308.3	1299.7	1295.2	1287.8	1280.9	1276.4	1278.5	1280.1	1279.3	1278.0
5°	1273.1	1263.4	1248.6	1235.9	1226.7	1209.8	1202.7	1199.1	1196.1	1192.5	1188.9
7.5°	1228.4	1213.1	1191.9	1173.7	1156.5	1135.6	1123.7	1116.5	1109.2	1101.1	1094.0
10°	1196.6	1175.1	1152.7	1127.1	1106.7	1087.8	1071.0	1059.8	1049.6	1039.9	1032.7
12.5°	1163.1	1138.4	1110.6	1075.7	1053.2	1026.2	1023.6	1003.8	987.9	981.9	973.5
15°	1109.8	1075.1	1039.9	998.5	980.6	956.1	940.8	925.5	911.7	902.0	899.5
17.5°	1049.2	1004.3	969.3	939.6	910.3	885.2	871.1	858.8	847.5	834.5	832.8
20°	1003.1	964.3	926.0	900.0	869.9	844.3	827.0	814.7	805.0	797.4	790.7
22.5°	959.4	916.9	881.9	853.4	823.7	803.1	789.4	777.6	769.5	761.0	754.8
25°	889.3	856.1	817.8	785.6	761.1	747.9	736.6	726.4	721.3	715.7	708.6
27.5°	827.9	791.0	755.2	730.3	708.8	697.0	689.0	682.1	677.3	674.0	670.0
30°	784.6	747.3	719.3	694.8	676.9	665.2	660.1	656.0	650.4	648.3	646.3
32.5°	743.0	709.4	685.4	664.1	647.1	639.4	634.7	631.1	626.7	624.6	620.5
35°	684.0	656.0	632.5	620.7	607.0	600.3	596.8	591.6	587.6	585.5	585.0
37.5°	628.6	604.2	588.8	573.7	567.9	563.8	558.9	555.4	554.2	553.9	553.4
40°	592.7	572.8	559.0	546.7	544.2	538.0	534.0	530.9	530.9	531.4	530.9
42.5°	560.0	542.1	530.0	519.4	516.4	512.7	508.6	508.4	509.3	511.0	509.3
45°	510.5	497.7	489.0	483.9	478.3	474.7	474.2	475.8	476.3	476.8	478.3
47.5°	464.9	456.5	448.6	443.0	440.5	439.9	439.3	442.0	444.4	445.3	447.7
50°	438.0	428.3	421.7	418.1	416.0	415.0	416.0	419.1	421.1	423.7	425.2
52.5°	407.8	400.9	396.3	393.6	392.8	393.4	393.6	397.1	400.3	401.2	402.0
55°	366.0	360.9	359.9	355.3	357.3	356.8	359.4	361.4	364.5	367.5	368.1
57.5°	324.4	320.3	317.5	317.9	318.5	320.8	322.9	326.5	329.8	333.0	333.3
60°	296.6	294.5	293.0	293.0	294.0	297.1	299.7	303.2	305.3	307.3	308.8
62.5°	271.3	269.2	267.7	268.5	271.2	273.0	276.0	277.9	279.9	282.0	282.7
65°	231.2	230.2	231.8	232.8	233.3	235.8	239.4	240.9	243.0	244.0	247.6
67.5°	194.4	194.6	194.4	195.8	198.8	199.4	202.8	206.3	206.7	208.7	211.0
70°	169.5	170.5	171.5	172.5	175.1	176.1	178.7	180.2	182.2	183.8	185.3
72.5°	146.6	146.8	147.8	147.6	149.8	152.0	154.2	155.7	157.7	159.7	161.2
75°	112.8	112.8	113.8	114.3	116.9	119.5	118.9	120.0	122.0	124.0	125.1
77.5°	82.4	81.3	82.4	82.9	83.7	85.9	86.3	87.7	90.0	89.3	90.5
80°	62.8	61.3	62.8	63.3	63.3	65.9	65.9	66.9	68.4	66.9	68.4
82.5°	44.8	44.1	45.2	45.3	46.1	46.2	47.1	47.3	48.8	48.1	48.8
85°	22.5	22.0	22.5	22.0	22.5	23.0	23.0	22.5	22.5	23.5	22.0
87.5°	8.8	8.9	9.3	10.1	10.4	10.8	10.3	10.2	10.2	9.3	9.3
90°	9.1	12.1	15.9	19.7	23.5	27.4	27.0	26.7	26.3	26.0	25.9
92.5°	20.0	21.2	22.1	23.0	24.0	24.9	24.9	25.0	25.1	25.1	25.2
95°	47.6	48.6	49.0	49.3	49.7	50.0	50.0	50.0	50.0	50.0	49.9
97.5°	80.4	81.5	82.1	82.8	83.4	84.1	84.1	84.1	84.1	84.1	84.1
100°	104.8	105.8	106.3	106.8	107.3	107.9	107.9	107.9	107.9	107.9	107.8
102.5°	130.0	130.9	131.5	132.2	132.8	133.5	133.6	133.8	133.9	134.1	134.0
105°	170.1	170.6	170.9	171.3	171.6	172.0	172.3	172.7	173.0	173.4	173.5
107.5°	213.9	214.3	214.3	214.3	214.3	214.3	214.5	214.6	214.7	214.9	214.6
110°	242.6	243.1	243.1	243.1	243.1	243.1	243.1	243.1	243.1	243.1	242.8



TEST NUMBER: P331349

CATALOG NUMBER: SA2XXDIP-C675D725U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	272.6	273.0	272.9	272.8	272.6	272.5	272.1	271.6	271.2	270.8	270.4
115°	316.8	317.2	316.8	316.5	316.1	315.8	315.6	315.4	315.3	315.1	314.7
117.5°	362.3	362.5	361.5	360.6	359.6	358.6	358.2	357.8	357.4	356.9	356.5
120°	391.7	391.7	390.3	388.9	387.5	386.1	386.1	386.1	386.1	386.1	385.9
122.5°	419.7	420.0	419.1	418.1	417.1	416.1	415.7	415.3	414.9	414.5	414.1
125°	461.2	461.7	461.2	460.6	460.1	459.6	459.1	458.6	458.0	457.5	457.2
127.5°	503.6	504.3	503.7	503.1	502.4	501.8	501.2	500.6	499.9	499.3	498.7
130°	530.4	531.3	531.0	530.6	530.3	530.0	529.6	529.3	528.9	528.6	528.0
132.5°	557.5	558.4	558.5	558.6	558.6	558.7	558.0	557.2	556.4	555.7	555.0
135°	596.2	597.3	597.7	598.0	598.4	598.7	598.6	598.4	598.2	598.0	597.7
137.5°	635.3	636.3	636.8	637.2	637.7	638.1	638.0	637.9	637.7	637.6	637.2
140°	659.7	660.9	661.8	662.7	663.5	664.4	664.4	664.4	664.4	664.4	664.0
142.5°	684.7	685.8	686.4	687.0	687.6	688.2	688.3	688.4	688.6	688.7	688.4
145°	719.3	720.4	721.5	722.5	723.5	724.6	724.8	724.9	725.1	725.3	725.0
147.5°	752.3	753.4	754.1	754.8	755.5	756.2	756.5	756.9	757.3	757.7	757.6
150°	772.5	773.4	774.1	774.8	775.5	776.2	776.7	777.2	777.7	778.3	778.3
152.5°	791.9	792.8	793.7	794.5	795.3	796.2	796.8	797.5	798.2	798.8	798.8
155°	818.9	819.4	819.9	820.5	821.0	821.5	822.4	823.2	824.1	825.0	825.2
157.5°	843.1	843.4	843.7	844.0	844.3	844.6	845.8	847.0	848.2	849.4	849.5
160°	858.1	858.3	858.5	858.7	858.9	859.0	860.1	861.1	862.2	863.2	863.4
162.5°	870.7	870.8	871.0	871.2	871.4	871.5	872.7	873.9	875.1	876.3	876.4
165°	888.0	887.9	887.9	887.9	887.9	887.9	889.2	890.4	891.6	892.8	893.0
167.5°	902.0	901.7	901.7	901.6	901.6	901.5	902.8	904.0	905.2	906.4	906.6
170°	910.1	909.7	909.6	909.4	909.2	909.0	910.3	911.5	912.7	913.9	914.0
172.5°	915.7	915.4	915.2	915.0	914.9	914.7	915.9	917.1	918.3	919.5	919.6
175°	922.6	922.2	921.8	921.5	921.1	920.8	922.0	923.2	924.4	925.6	925.7
177.5°	925.8	925.5	925.2	924.9	924.6	924.4	925.2	926.0	926.9	927.7	927.7
180°	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2



TEST NUMBER: P331349

CATALOG NUMBER: SA2XXDIP-C675D725U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3
2.5°	1274.0	1273.1	1273.1	1269.5	1273.1	1273.1	1274.0	1278.0	1279.3	1280.1	1278.5
5°	1181.8	1180.2	1177.7	1180.2	1177.7	1180.2	1181.8	1188.9	1192.5	1196.1	1199.1
7.5°	1090.6	1084.5	1083.6	1077.5	1083.6	1084.5	1090.6	1094.0	1101.1	1109.2	1116.5
10°	1024.0	1019.9	1019.4	1009.7	1019.4	1019.9	1024.0	1032.7	1039.9	1049.6	1059.8
12.5°	973.4	963.6	965.5	959.9	965.5	963.6	973.4	973.5	981.9	987.9	1003.8
15°	885.7	885.7	883.6	875.0	883.6	885.7	885.7	899.5	902.0	911.7	925.5
17.5°	822.7	821.7	816.8	819.2	816.8	821.7	822.7	832.8	834.5	847.5	858.8
20°	785.1	782.1	775.9	775.9	775.9	782.1	785.1	790.7	797.4	805.0	814.7
22.5°	749.6	749.4	742.9	744.9	742.9	749.4	749.6	754.8	761.0	769.5	777.6
25°	708.0	704.0	700.9	702.4	700.9	704.0	708.0	708.6	715.7	721.3	726.4
27.5°	668.6	666.4	666.2	662.0	666.2	666.4	668.6	670.0	674.0	677.3	682.1
30°	645.8	640.7	641.7	639.1	641.7	640.7	645.8	646.3	648.3	650.4	656.0
32.5°	619.6	617.8	616.8	614.6	616.8	617.8	619.6	620.5	624.6	626.7	631.1
35°	584.0	584.5	582.0	583.0	582.0	584.5	584.0	585.0	585.5	587.6	591.6
37.5°	552.9	554.5	553.3	553.6	553.3	554.5	552.9	553.4	553.9	554.2	555.4
40°	532.4	532.4	532.4	534.0	532.4	532.4	532.4	530.9	531.4	530.9	530.9
42.5°	512.8	512.0	511.2	511.1	511.2	512.0	512.8	509.3	511.0	509.3	508.4
45°	479.3	480.9	481.4	478.8	481.4	480.9	479.3	478.3	476.8	476.3	475.8
47.5°	449.0	449.2	449.0	451.3	449.0	449.2	449.0	447.7	445.3	444.4	442.0
50°	427.8	426.8	427.8	426.8	427.8	426.8	427.8	425.2	423.7	421.1	419.1
52.5°	405.3	405.5	404.9	404.7	404.9	405.5	405.3	402.0	401.2	400.3	397.1
55°	370.1	371.1	370.6	370.6	370.6	371.1	370.1	368.1	367.5	364.5	361.4
57.5°	333.7	334.6	335.3	333.0	335.3	334.6	333.7	333.3	333.0	329.8	326.5
60°	308.3	310.9	310.4	309.4	310.4	310.9	308.3	308.8	307.3	305.3	303.2
62.5°	285.1	286.0	285.9	285.7	285.9	286.0	285.1	282.7	282.0	279.9	277.9
65°	249.1	250.1	248.6	250.1	248.6	250.1	249.1	247.6	244.0	243.0	240.9
67.5°	210.4	210.7	211.9	212.6	211.9	210.7	210.4	211.0	208.7	206.7	206.3
70°	186.3	185.8	187.3	188.9	187.3	185.8	186.3	185.3	183.8	182.2	180.2
72.5°	161.0	162.1	161.6	162.7	161.6	162.1	161.0	161.2	159.7	157.7	155.7
75°	124.0	125.6	125.1	126.6	125.1	125.6	124.0	125.1	124.0	122.0	120.0
77.5°	89.6	89.8	89.6	90.5	89.6	89.8	89.6	90.5	89.3	90.0	87.7
80°	68.4	67.4	66.4	68.4	66.4	67.4	68.4	68.4	66.9	68.4	66.9
82.5°	47.6	48.2	47.2	47.2	47.2	48.2	47.6	48.8	48.1	48.8	47.3
85°	22.0	21.4	20.4	20.4	20.4	21.4	22.0	22.0	23.5	22.5	22.5
87.5°	9.3	8.9	9.0	8.6	9.0	8.9	9.3	9.3	9.3	10.2	10.2
90°	26.1	26.2	26.4	26.6	26.4	26.2	26.1	25.9	26.0	26.3	26.7
92.5°	25.2	25.3	25.3	25.3	25.3	25.3	25.2	25.2	25.1	25.1	25.0
95°	49.5	49.2	48.8	48.5	48.8	49.2	49.5	49.9	50.0	50.0	50.0
97.5°	84.1	84.0	84.0	83.9	84.0	84.0	84.1	84.1	84.1	84.1	84.1
100°	107.6	107.4	107.3	107.1	107.3	107.4	107.6	107.8	107.9	107.9	107.9
102.5°	133.9	133.7	133.5	133.3	133.5	133.7	133.9	134.0	134.1	133.9	133.8
105°	173.5	173.5	173.5	173.5	173.5	173.5	173.5	173.5	173.4	173.0	172.7
107.5°	213.8	213.0	212.2	211.4	212.2	213.0	213.8	214.6	214.9	214.7	214.6
110°	242.3	241.8	241.3	240.7	241.3	241.8	242.3	242.8	243.1	243.1	243.1



TEST NUMBER: P331349

CATALOG NUMBER: SA2XXDIP-C675D725U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	270.0	269.6	269.3	268.9	269.3	269.6	270.0	270.4	270.8	271.2	271.6
115°	314.2	313.7	313.2	312.7	313.2	313.7	314.2	314.7	315.1	315.3	315.4
117.5°	356.0	355.4	354.9	354.4	354.9	355.4	356.0	356.5	356.9	357.4	357.8
120°	385.3	384.8	384.3	383.8	384.3	384.8	385.3	385.9	386.1	386.1	386.1
122.5°	413.7	413.3	412.9	412.6	412.9	413.3	413.7	414.1	414.5	414.9	415.3
125°	457.0	456.8	456.7	456.5	456.7	456.8	457.0	457.2	457.5	458.0	458.6
127.5°	498.2	497.6	497.1	496.5	497.1	497.6	498.2	498.7	499.3	499.9	500.6
130°	527.3	526.7	526.0	525.3	526.0	526.7	527.3	528.0	528.6	528.9	529.3
132.5°	554.4	553.9	553.3	552.8	553.3	553.9	554.4	555.0	555.7	556.4	557.2
135°	597.2	596.7	596.1	595.6	596.1	596.7	597.2	597.7	598.0	598.2	598.4
137.5°	636.5	635.8	635.1	634.4	635.1	635.8	636.5	637.2	637.6	637.7	637.9
140°	663.4	662.7	662.0	661.3	662.0	662.7	663.4	664.0	664.4	664.4	664.4
142.5°	687.7	687.0	686.4	685.7	686.4	687.0	687.7	688.4	688.7	688.6	688.4
145°	724.3	723.6	722.9	722.2	722.9	723.6	724.3	725.0	725.3	725.1	724.9
147.5°	756.9	756.2	755.6	754.9	755.6	756.2	756.9	757.6	757.7	757.3	756.9
150°	777.7	777.2	776.7	776.2	776.7	777.2	777.7	778.3	778.3	777.7	777.2
152.5°	798.2	797.5	796.8	796.2	796.8	797.5	798.2	798.8	798.8	798.2	797.5
155°	824.6	824.1	823.6	823.1	823.6	824.1	824.6	825.2	825.0	824.1	823.2
157.5°	848.7	847.9	847.0	846.2	847.0	847.9	848.7	849.5	849.4	848.2	847.0
160°	862.7	862.0	861.3	860.6	861.3	862.0	862.7	863.4	863.2	862.2	861.1
162.5°	875.6	874.8	873.9	873.1	873.9	874.8	875.6	876.4	876.3	875.1	873.9
165°	892.1	891.2	890.4	889.5	890.4	891.2	892.1	893.0	892.8	891.6	890.4
167.5°	905.7	904.8	903.9	903.0	903.9	904.8	905.7	906.6	906.4	905.2	904.0
170°	913.0	911.9	910.9	909.8	910.9	911.9	913.0	914.0	913.9	912.7	911.5
172.5°	918.6	917.5	916.5	915.5	916.5	917.5	918.6	919.6	919.5	918.3	917.1
175°	924.7	923.6	922.6	921.6	922.6	923.6	924.7	925.7	925.6	924.4	923.2
177.5°	926.9	926.0	925.2	924.4	925.2	926.0	926.9	927.7	927.7	926.9	926.0
180°	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2



TEST NUMBER: P331349

CATALOG NUMBER: SA2XXDIP-C675D725U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3
2.5°	1276.4	1280.9	1287.8	1295.2	1299.7	1308.3	1310.7	1314.8	1318.5	1327.1	1336.0
5°	1202.7	1209.8	1226.7	1235.9	1248.6	1263.4	1273.1	1283.4	1294.6	1314.0	1331.8
7.5°	1123.7	1135.6	1156.5	1173.7	1191.9	1213.1	1228.4	1248.6	1265.4	1292.7	1318.9
10°	1071.0	1087.8	1106.7	1127.1	1152.7	1175.1	1196.6	1222.1	1242.5	1275.2	1305.8
12.5°	1023.6	1026.2	1053.2	1075.7	1110.6	1138.4	1163.1	1196.0	1216.0	1254.8	1287.0
15°	940.8	956.1	980.6	998.5	1039.9	1075.1	1109.8	1144.0	1167.0	1214.9	1257.3
17.5°	871.1	885.2	910.3	939.6	969.3	1004.3	1049.2	1085.3	1116.5	1171.4	1221.5
20°	827.0	844.3	869.9	900.0	926.0	964.3	1003.1	1044.4	1078.1	1139.9	1198.6
22.5°	789.4	803.1	823.7	853.4	881.9	916.9	959.4	1004.4	1039.8	1106.4	1165.9
25°	736.6	747.9	761.1	785.6	817.8	856.1	889.3	938.8	990.3	1052.6	1124.6
27.5°	689.0	697.0	708.8	730.3	755.2	791.0	827.9	874.9	926.7	994.3	1070.3
30°	660.1	665.2	676.9	694.8	719.3	747.3	784.6	829.5	882.6	951.0	1026.6
32.5°	634.7	639.4	647.1	664.1	685.4	709.4	743.0	787.9	838.5	905.7	989.4
35°	596.8	600.3	607.0	620.7	632.5	656.0	684.0	724.9	772.4	836.7	923.5
37.5°	558.9	563.8	567.9	573.7	588.8	604.2	628.6	663.1	709.7	774.6	857.3
40°	534.0	538.0	544.2	546.7	559.0	572.8	592.7	624.3	671.3	730.5	811.2
42.5°	508.6	512.7	516.4	519.4	530.0	542.1	560.0	587.2	628.8	686.4	766.2
45°	474.2	474.7	478.3	483.9	489.0	497.7	510.5	534.0	566.1	620.2	692.7
47.5°	439.3	439.9	440.5	443.0	448.6	456.5	464.9	484.0	512.8	556.0	626.6
50°	416.0	415.0	416.0	418.1	421.7	428.3	438.0	451.8	475.3	515.6	580.4
52.5°	393.6	393.4	392.8	393.6	396.3	400.9	407.8	419.5	440.5	477.6	534.7
55°	359.4	356.8	357.3	355.3	359.9	360.9	366.0	375.7	394.1	419.6	473.2
57.5°	322.9	320.8	318.5	317.9	317.5	320.3	324.4	332.0	346.1	368.5	412.0
60°	299.7	297.1	294.0	293.0	293.0	294.5	296.6	302.2	315.5	335.4	371.1
62.5°	276.0	273.0	271.2	268.5	267.7	269.2	271.3	275.3	284.8	303.5	334.4
65°	239.4	235.8	233.3	232.8	231.8	230.2	231.2	235.3	243.0	257.8	282.3
67.5°	202.8	199.4	198.8	195.8	194.4	194.6	194.4	197.9	202.5	215.2	233.5
70°	178.7	176.1	175.1	172.5	171.5	170.5	169.5	172.5	177.1	187.9	203.7
72.5°	154.2	152.0	149.8	147.6	147.8	146.8	146.6	148.4	152.2	162.1	174.3
75°	118.9	119.5	116.9	114.3	113.8	112.8	112.8	114.3	115.9	123.5	133.2
77.5°	86.3	85.9	83.7	82.9	82.4	81.3	82.4	83.4	84.2	89.3	96.5
80°	65.9	65.9	63.3	63.3	62.8	61.3	62.8	61.8	63.8	68.9	74.0
82.5°	47.1	46.2	46.1	45.3	45.2	44.1	44.8	45.8	46.7	50.1	53.2
85°	23.0	23.0	22.5	22.0	22.5	22.0	22.5	23.0	23.5	25.0	27.6
87.5°	10.3	10.8	10.4	10.1	9.3	8.9	8.8	8.8	9.2	9.1	9.1
90°	27.0	27.4	23.5	19.7	15.9	12.1	9.1	7.0	5.0	2.9	0.8
92.5°	24.9	24.9	24.0	23.0	22.1	21.2	20.0	18.5	17.0	15.4	13.9
95°	50.0	50.0	49.7	49.3	49.0	48.6	47.6	45.9	44.1	42.4	40.6
97.5°	84.1	84.1	83.4	82.8	82.1	81.5	80.4	78.8	77.3	75.8	74.3
100°	107.9	107.9	107.3	106.8	106.3	105.8	104.8	103.4	102.0	100.7	99.3
102.5°	133.6	133.5	132.8	132.2	131.5	130.9	130.0	128.9	127.8	126.6	125.5
105°	172.3	172.0	171.6	171.3	170.9	170.6	170.1	169.6	169.1	168.6	168.1
107.5°	214.5	214.3	214.3	214.3	214.3	214.3	213.9	213.2	212.4	211.7	210.9
110°	243.1	243.1	243.1	243.1	243.1	243.1	242.6	241.5	240.5	239.4	238.4



TEST NUMBER: P331349

CATALOG NUMBER: SA2XXDIP-C675D725U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	272.1	272.5	272.6	272.8	272.9	273.0	272.6	271.5	270.5	269.5	268.4
115°	315.6	315.8	316.1	316.5	316.8	317.2	316.8	315.8	314.7	313.7	312.7
117.5°	358.2	358.6	359.6	360.6	361.5	362.5	362.3	360.9	359.5	358.1	356.7
120°	386.1	386.1	387.5	388.9	390.3	391.7	391.7	390.3	388.9	387.5	386.1
122.5°	415.7	416.1	417.1	418.1	419.1	420.0	419.7	418.0	416.4	414.7	413.0
125°	459.1	459.6	460.1	460.6	461.2	461.7	461.2	459.6	458.0	456.5	454.9
127.5°	501.2	501.8	502.4	503.1	503.7	504.3	503.6	501.7	499.7	497.7	495.7
130°	529.6	530.0	530.3	530.6	531.0	531.3	530.4	528.1	525.9	523.6	521.4
132.5°	558.0	558.7	558.6	558.6	558.5	558.4	557.5	555.6	553.8	552.0	550.1
135°	598.6	598.7	598.4	598.0	597.7	597.3	596.2	594.3	592.4	590.5	588.6
137.5°	638.0	638.1	637.7	637.2	636.8	636.3	635.3	633.8	632.2	630.6	629.1
140°	664.4	664.4	663.5	662.7	661.8	660.9	659.7	658.1	656.6	655.0	653.5
142.5°	688.3	688.2	687.6	687.0	686.4	685.8	684.7	683.2	681.6	680.0	678.5
145°	724.8	724.6	723.5	722.5	721.5	720.4	719.3	718.1	716.9	715.6	714.4
147.5°	756.5	756.2	755.5	754.8	754.1	753.4	752.3	750.8	749.4	747.9	746.5
150°	776.7	776.2	775.5	774.8	774.1	773.4	772.5	771.5	770.4	769.4	768.4
152.5°	796.8	796.2	795.3	794.5	793.7	792.8	791.9	790.9	789.8	788.8	787.7
155°	822.4	821.5	821.0	820.5	819.9	819.4	818.9	818.4	817.9	817.3	816.8
157.5°	845.8	844.6	844.3	844.0	843.7	843.4	843.1	842.7	842.4	842.0	841.7
160°	860.1	859.0	858.9	858.7	858.5	858.3	858.1	857.7	857.4	857.0	856.7
162.5°	872.7	871.5	871.4	871.2	871.0	870.8	870.7	870.6	870.6	870.5	870.4
165°	889.2	887.9	887.9	887.9	887.9	887.9	888.0	888.2	888.4	888.6	888.7
167.5°	902.8	901.5	901.6	901.6	901.7	901.7	902.0	902.5	903.0	903.5	904.0
170°	910.3	909.0	909.2	909.4	909.6	909.7	910.1	910.6	911.1	911.7	912.2
172.5°	915.9	914.7	914.9	915.0	915.2	915.4	915.7	916.2	916.8	917.3	917.8
175°	922.0	920.8	921.1	921.5	921.8	922.2	922.6	923.1	923.6	924.2	924.7
177.5°	925.2	924.4	924.6	924.9	925.2	925.5	925.8	926.2	926.7	927.1	927.5
180°	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2



TEST NUMBER: P331349

CATALOG NUMBER: SA2XXDIP-C675D725U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3
2.5°	1335.2	1337.3	1343.8	1350.3	1357.7	1359.7	1363.0	1360.1	1359.3	1367.1	1372.8
5°	1339.0	1348.2	1366.1	1382.4	1396.2	1405.9	1416.1	1420.2	1427.8	1438.5	1451.8
7.5°	1334.7	1352.6	1380.7	1404.4	1430.4	1449.1	1463.7	1476.1	1491.2	1511.5	1533.7
10°	1329.8	1353.8	1388.0	1417.1	1448.7	1472.7	1492.7	1512.0	1534.5	1562.6	1591.7
12.5°	1320.8	1349.3	1392.1	1426.5	1467.1	1490.7	1517.6	1559.4	1583.5	1622.6	1663.6
15°	1302.8	1334.4	1394.1	1436.5	1482.4	1527.4	1576.9	1616.7	1656.5	1679.5	1737.2
17.5°	1275.9	1322.4	1388.5	1437.9	1496.3	1567.1	1622.7	1667.8	1713.8	1751.1	1780.0
20°	1254.3	1304.8	1380.3	1439.6	1509.0	1585.0	1648.9	1694.8	1734.6	1765.8	1783.6
22.5°	1226.9	1290.5	1364.0	1433.4	1522.1	1597.3	1664.4	1700.5	1733.8	1749.0	1755.9
25°	1183.8	1260.4	1343.6	1428.3	1528.4	1608.0	1669.3	1691.2	1700.9	1686.1	1661.6
27.5°	1137.4	1222.7	1320.0	1418.7	1524.5	1601.1	1645.0	1641.5	1625.1	1577.2	1538.9
30°	1102.6	1196.6	1301.2	1408.9	1515.1	1589.6	1615.2	1589.6	1552.4	1498.8	1444.2
32.5°	1066.3	1163.5	1281.2	1395.0	1498.0	1563.5	1569.0	1525.1	1467.4	1406.5	1338.4
35°	1011.3	1116.4	1243.5	1364.0	1461.5	1502.9	1478.4	1400.8	1332.4	1249.2	1156.2
37.5°	949.1	1065.2	1192.7	1318.6	1406.9	1417.7	1356.9	1275.2	1178.7	1080.9	971.6
40°	902.5	1025.6	1156.8	1283.9	1362.0	1350.7	1273.1	1183.3	1068.4	949.0	847.4
42.5°	860.9	983.9	1117.5	1242.2	1304.8	1274.0	1183.3	1073.0	949.6	837.1	744.1
45°	788.7	915.3	1052.1	1172.6	1208.3	1152.7	1032.7	910.2	788.7	694.8	621.3
47.5°	718.7	843.8	979.3	1085.2	1097.8	1023.0	891.9	765.8	661.4	584.9	533.0
50°	667.2	792.8	927.0	1021.5	1017.4	927.0	792.3	672.3	585.0	523.2	488.5
52.5°	621.1	739.7	868.6	954.5	932.9	834.3	705.7	599.2	527.4	479.1	447.7
55°	549.3	659.0	781.5	850.5	810.6	701.4	592.7	506.9	453.8	417.6	393.1
57.5°	478.0	580.9	685.8	728.3	684.3	583.4	492.7	430.5	390.6	363.8	347.8
60°	433.9	523.8	617.2	653.9	601.3	511.5	440.0	384.4	352.2	330.3	316.0
62.5°	389.8	470.3	558.4	578.4	530.3	454.3	391.0	344.8	318.3	298.8	285.4
65°	329.8	395.6	462.5	475.8	431.4	372.7	322.6	292.5	269.0	254.7	244.0
67.5°	270.5	323.3	370.7	381.4	342.5	301.8	265.7	239.4	223.5	211.6	202.6
70°	235.3	277.2	316.0	324.7	293.5	257.3	229.7	208.8	194.5	184.3	175.6
72.5°	198.2	233.1	265.3	271.2	245.7	218.1	195.4	179.0	166.3	159.8	151.5
75°	151.6	172.0	197.0	198.6	181.7	164.9	147.5	136.8	130.2	122.0	117.9
77.5°	107.0	123.0	137.3	140.1	130.1	118.6	108.9	100.5	94.8	91.1	87.3
80°	81.7	94.4	100.6	104.1	97.0	88.8	83.2	77.6	74.0	71.5	68.9
82.5°	58.4	66.3	72.0	74.7	70.9	66.0	60.3	57.2	54.4	52.3	51.4
85°	29.6	33.2	36.8	37.8	36.8	34.7	31.6	31.6	30.1	29.6	29.6
87.5°	10.8	12.8	13.3	14.9	14.7	15.4	16.2	16.6	16.9	16.4	16.0
90°	2.9	5.0	7.0	9.1	12.1	15.9	19.7	23.5	27.4	27.0	26.7
92.5°	15.4	17.0	18.5	20.0	21.2	22.1	23.0	24.0	24.9	24.9	25.0
95°	42.4	44.1	45.9	47.6	48.6	49.0	49.3	49.7	50.0	50.0	50.0
97.5°	75.8	77.3	78.8	80.4	81.5	82.1	82.8	83.4	84.1	84.1	84.1
100°	100.7	102.0	103.4	104.8	105.8	106.3	106.8	107.3	107.9	107.9	107.9
102.5°	126.6	127.8	128.9	130.0	130.9	131.5	132.2	132.8	133.5	133.6	133.8
105°	168.6	169.1	169.6	170.1	170.6	170.9	171.3	171.6	172.0	172.3	172.7
107.5°	211.7	212.4	213.2	213.9	214.3	214.3	214.3	214.3	214.3	214.5	214.6
110°	239.4	240.5	241.5	242.6	243.1	243.1	243.1	243.1	243.1	243.1	243.1





TEST NUMBER: P331349

CATALOG NUMBER: SA2XXDIP-C675D725U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	269.5	270.5	271.5	272.6	273.0	272.9	272.8	272.6	272.5	272.1	271.6
115°	313.7	314.7	315.8	316.8	317.2	316.8	316.5	316.1	315.8	315.6	315.4
117.5°	358.1	359.5	360.9	362.3	362.5	361.5	360.6	359.6	358.6	358.2	357.8
120°	387.5	388.9	390.3	391.7	391.7	390.3	388.9	387.5	386.1	386.1	386.1
122.5°	414.7	416.4	418.0	419.7	420.0	419.1	418.1	417.1	416.1	415.7	415.3
125°	456.5	458.0	459.6	461.2	461.7	461.2	460.6	460.1	459.6	459.1	458.6
127.5°	497.7	499.7	501.7	503.6	504.3	503.7	503.1	502.4	501.8	501.2	500.6
130°	523.6	525.9	528.1	530.4	531.3	531.0	530.6	530.3	530.0	529.6	529.3
132.5°	552.0	553.8	555.6	557.5	558.4	558.5	558.6	558.6	558.7	558.0	557.2
135°	590.5	592.4	594.3	596.2	597.3	597.7	598.0	598.4	598.7	598.6	598.4
137.5°	630.6	632.2	633.8	635.3	636.3	636.8	637.2	637.7	638.1	638.0	637.9
140°	655.0	656.6	658.1	659.7	660.9	661.8	662.7	663.5	664.4	664.4	664.4
142.5°	680.0	681.6	683.2	684.7	685.8	686.4	687.0	687.6	688.2	688.3	688.4
145°	715.6	716.9	718.1	719.3	720.4	721.5	722.5	723.5	724.6	724.8	724.9
147.5°	747.9	749.4	750.8	752.3	753.4	754.1	754.8	755.5	756.2	756.5	756.9
150°	769.4	770.4	771.5	772.5	773.4	774.1	774.8	775.5	776.2	776.7	777.2
152.5°	788.8	789.8	790.9	791.9	792.8	793.7	794.5	795.3	796.2	796.8	797.5
155°	817.3	817.9	818.4	818.9	819.4	819.9	820.5	821.0	821.5	822.4	823.2
157.5°	842.0	842.4	842.7	843.1	843.4	843.7	844.0	844.3	844.6	845.8	847.0
160°	857.0	857.4	857.7	858.1	858.3	858.5	858.7	858.9	859.0	860.1	861.1
162.5°	870.5	870.6	870.6	870.7	870.8	871.0	871.2	871.4	871.5	872.7	873.9
165°	888.6	888.4	888.2	888.0	887.9	887.9	887.9	887.9	887.9	889.2	890.4
167.5°	903.5	903.0	902.5	902.0	901.7	901.7	901.6	901.6	901.5	902.8	904.0
170°	911.7	911.1	910.6	910.1	909.7	909.6	909.4	909.2	909.0	910.3	911.5
172.5°	917.3	916.8	916.2	915.7	915.4	915.2	915.0	914.9	914.7	915.9	917.1
175°	924.2	923.6	923.1	922.6	922.2	921.8	921.5	921.1	920.8	922.0	923.2
177.5°	927.1	926.7	926.2	925.8	925.5	925.2	924.9	924.6	924.4	925.2	926.0
180°	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2



TEST NUMBER: P331349

CATALOG NUMBER: SA2XXDIP-C675D725U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3
2.5°	1377.7	1383.4	1383.4	1384.2	1390.8	1389.9	1389.5
5°	1466.1	1474.8	1475.8	1485.0	1491.1	1489.1	1483.5
7.5°	1549.5	1565.7	1577.9	1584.7	1592.8	1597.8	1595.6
10°	1615.7	1639.2	1653.5	1663.2	1674.9	1683.6	1680.5
12.5°	1675.7	1703.7	1723.3	1739.9	1741.5	1752.6	1745.0
15°	1769.3	1798.9	1802.0	1814.3	1824.0	1822.9	1823.4
17.5°	1800.3	1809.8	1811.7	1812.0	1812.1	1808.5	1800.8
20°	1789.2	1785.7	1777.0	1770.4	1758.6	1757.1	1746.9
22.5°	1737.0	1725.6	1703.9	1689.5	1671.2	1666.4	1663.6
25°	1634.1	1609.0	1574.3	1541.1	1532.0	1514.1	1519.2
27.5°	1492.9	1453.9	1416.3	1389.3	1364.9	1338.2	1345.8
30°	1393.6	1349.7	1296.6	1255.8	1229.8	1204.2	1199.6
32.5°	1275.2	1210.9	1151.6	1115.7	1075.8	1059.7	1042.0
35°	1071.0	1008.2	949.5	899.0	869.9	847.4	827.0
37.5°	887.3	815.0	767.7	726.7	705.7	692.8	696.1
40°	773.4	710.1	675.4	644.2	624.8	615.6	617.7
42.5°	681.1	633.7	605.1	583.8	570.1	565.0	563.8
45°	576.3	549.8	526.3	514.1	507.4	501.8	498.2
47.5°	504.9	483.2	470.0	462.7	456.9	451.2	451.1
50°	462.0	447.7	438.5	430.8	426.3	422.2	425.7
52.5°	429.3	416.2	407.1	400.2	398.5	394.8	394.7
55°	380.8	370.6	364.0	357.8	354.8	352.7	350.2
57.5°	336.7	327.0	320.9	317.0	311.2	309.1	308.3
60°	305.3	297.6	291.5	286.4	283.8	279.7	279.7
62.5°	276.3	268.6	262.9	259.0	254.8	253.2	253.6
65°	234.3	228.2	222.6	218.5	217.5	214.4	215.4
67.5°	195.7	191.6	185.7	183.5	181.5	179.9	178.7
70°	170.0	165.9	162.8	159.8	158.2	158.2	158.2
72.5°	148.3	143.4	141.6	137.7	138.6	137.0	135.4
75°	114.9	111.8	110.3	108.7	106.2	106.2	106.2
77.5°	84.5	83.6	81.8	80.1	79.5	79.0	79.2
80°	65.3	64.8	63.8	63.8	62.8	62.3	61.3
82.5°	50.2	48.9	48.3	47.9	47.7	47.6	47.4
85°	28.6	27.6	27.6	28.1	27.1	27.1	27.6
87.5°	16.3	16.2	15.8	15.8	16.3	15.9	15.9
90°	26.3	26.0	25.9	26.1	26.2	26.4	26.6
92.5°	25.1	25.1	25.2	25.2	25.3	25.3	25.3
95°	50.0	50.0	49.9	49.5	49.2	48.8	48.5
97.5°	84.1	84.1	84.1	84.1	84.0	84.0	83.9
100°	107.9	107.9	107.8	107.6	107.4	107.3	107.1
102.5°	133.9	134.1	134.0	133.9	133.7	133.5	133.3
105°	173.0	173.4	173.5	173.5	173.5	173.5	173.5
107.5°	214.7	214.9	214.6	213.8	213.0	212.2	211.4
110°	243.1	243.1	242.8	242.3	241.8	241.3	240.7



TEST NUMBER: P331349

CATALOG NUMBER: SA2XXDIP-C675D725U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	271.2	270.8	270.4	270.0	269.6	269.3	268.9
115°	315.3	315.1	314.7	314.2	313.7	313.2	312.7
117.5°	357.4	356.9	356.5	356.0	355.4	354.9	354.4
120°	386.1	386.1	385.9	385.3	384.8	384.3	383.8
122.5°	414.9	414.5	414.1	413.7	413.3	412.9	412.6
125°	458.0	457.5	457.2	457.0	456.8	456.7	456.5
127.5°	499.9	499.3	498.7	498.2	497.6	497.1	496.5
130°	528.9	528.6	528.0	527.3	526.7	526.0	525.3
132.5°	556.4	555.7	555.0	554.4	553.9	553.3	552.8
135°	598.2	598.0	597.7	597.2	596.7	596.1	595.6
137.5°	637.7	637.6	637.2	636.5	635.8	635.1	634.4
140°	664.4	664.4	664.0	663.4	662.7	662.0	661.3
142.5°	688.6	688.7	688.4	687.7	687.0	686.4	685.7
145°	725.1	725.3	725.0	724.3	723.6	722.9	722.2
147.5°	757.3	757.7	757.6	756.9	756.2	755.6	754.9
150°	777.7	778.3	778.3	777.7	777.2	776.7	776.2
152.5°	798.2	798.8	798.8	798.2	797.5	796.8	796.2
155°	824.1	825.0	825.2	824.6	824.1	823.6	823.1
157.5°	848.2	849.4	849.5	848.7	847.9	847.0	846.2
160°	862.2	863.2	863.4	862.7	862.0	861.3	860.6
162.5°	875.1	876.3	876.4	875.6	874.8	873.9	873.1
165°	891.6	892.8	893.0	892.1	891.2	890.4	889.5
167.5°	905.2	906.4	906.6	905.7	904.8	903.9	903.0
170°	912.7	913.9	914.0	913.0	911.9	910.9	909.8
172.5°	918.3	919.5	919.6	918.6	917.5	916.5	915.5
175°	924.4	925.6	925.7	924.7	923.6	922.6	921.6
177.5°	926.9	927.7	927.7	926.9	926.0	925.2	924.4
180°	926.2	926.2	926.2	926.2	926.2	926.2	926.2

(END OF REPORT)